Cool MOS™ Power Transistor

V_{DS} @ T_{jmax}	650	V
$R_{DS(on)}$	0.38	Ω
I_D	11	A

Feature

- New revolutionary high voltage technology
- Ultra low gate charge
- Periodic avalanche rated
- Extreme dv/dt rated
- High peak current capability
- Improved transconductance
- PG-TO-220-3-31;-3-111: Fully isolated package (2500 VAC; 1 minute)
- Pb-free lead plating; RoHS compliant
- Qualified according to JEDEC[0)] for target applications

PG-TO220FP



PG-TO262



PG-TO220



Type	Package	Ordering Code	Marking
SPP11N60C3	PG-TO220	Q67040-S4395	11N60C3
SPI11N60C3	PG-TO262	Q67042-S4403	11N60C3
SPA11N60C3	PG-TO220FP	Q67040-S4408	11N60C3
SPA11N60C3E8185	PG-TO220		11N60C3



Maximum Ratings

Parameter	Symbol	Value		Unit
		SPP_I	SPA	
Continuous drain current	I_D			A
T_C = 25 °C		11	11[1)]	
T_C = 100 °C		7	7[1)]	
Pulsed drain current, t_p limited by T_{jmax}	$I_{D\ puls}$	33	33	A
Avalanche energy, single pulse I_D=5.5A, V_{DD}=50V	E_{AS}	340	340	mJ
Avalanche energy, repetitive t_{AR} limited by T_{jmax}[2)] I_D=11A, V_{DD}=50V	E_{AR}	0.6	0.6	
Avalanche current, repetitive t_{AR} limited by T_{jmax}	I_{AR}	11	11	A
Gate source voltage static	V_{GS}	±20	±20	V
Gate source voltage AC (f >1Hz)	V_{GS}	±30	±30	
Power dissipation, T_C = 25°C	P_{tot}	125	33	W
Operating and storage temperature	T_j , T_{stg}	-55...+150		°C
Reverse diode dv/dt [7)]	dv/dt	15		V/ns

Maximum Ratings

Parameter	Symbol	Value	Unit
Drain Source voltage slope V_{DS} = 480 V, I_D = 11 A, T_j = 125 °C	dv/dt	50	V/ns

Thermal Characteristics

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Thermal resistance, junction - case	R_{thJC}	-	-	1	K/W
Thermal resistance, junction - case, FullPAK	R_{thJC_FP}	-	-	3.8	
Thermal resistance, junction - ambient, leaded	R_{thJA}	-	-	62	
Thermal resistance, junction - ambient, FullPAK	R_{thJA_FP}	-	-	80	
SMD version, device on PCB:	R_{thJA}				
@ min. footprint		-	-	62	
@ 6 cm^2 cooling area [3)]		-	35	-	
Soldering temperature, wavesoldering 1.6 mm (0.063 in.) from case for 10s [4)]	T_{sold}	-	-	260	°C

Electrical Characteristics, at T_j=25°C unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0V, I_D=0.25mA	600	-	-	V
Drain-Source avalanche breakdown voltage	$V_{(BR)DS}$	V_{GS}=0V, I_D=11A	-	700	-	
Gate threshold voltage	$V_{GS(th)}$	I_D=500µA, V_{GS}=V_{DS}	2.1	3	3.9	
Zero gate voltage drain current	I_{DSS}	V_{DS}=600V, V_{GS}=0V,				µA
		T_j=25°C	-	0.1	1	
		T_j=150°C	-	-	100	
Gate-source leakage current	I_{GSS}	V_{GS}=30V, V_{DS}=0V	-	-	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=10V, I_D=7A				Ω
		T_j=25°C	-	0.34	0.38	
		T_j=150°C	-	0.92	-	
Gate input resistance	R_G	f=1MHz, open drain	-	0.86	-	

Electrical Characteristics

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Transconductance	g_{fs}	$V_{DS} \geq 2*I_D*R_{DS(on)max}$, I_D=7A	-	8.3	-	S
Input capacitance	C_{iss}	V_{GS}=0V, V_{DS}=25V, f=1MHz	-	1200	-	pF
Output capacitance	C_{oss}		-	390	-	
Reverse transfer capacitance	C_{rss}		-	30	-	
Effective output capacitance,[5)] energy related	$C_{o(er)}$	V_{GS}=0V, V_{DS}=0V to 480V	-	45	-	
Effective output capacitance,[6)] time related	$C_{o(tr)}$		-	85	-	
Turn-on delay time	$t_{d(on)}$	V_{DD}=380V, V_{GS}=0/10V, I_D=11A, R_G=6.8Ω	-	10	-	ns
Rise time	t_r		-	5	-	
Turn-off delay time	$t_{d(off)}$		-	44	70	
Fall time	t_f		-	5	9	

Gate Charge Characteristics

Parameter	Symbol	Conditions	min.	typ.	max.	Unit
Gate to source charge	Q_{gs}	V_{DD}=480V, I_D=11A	-	5.5	-	nC
Gate to drain charge	Q_{gd}		-	22	-	
Gate charge total	Q_g	V_{DD}=480V, I_D=11A, V_{GS}=0 to 10V	-	45	60	
Gate plateau voltage	$V_{(plateau)}$	V_{DD}=480V, I_D=11A	-	5.5	-	V

[0]J-STD20 and JESD22

[1]Limited only by maximum temperature

[2]Repetitve avalanche causes additional power losses that can be calculated as $P_{AV}=E_{AR}*f$.

[3]Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical without blown air.

[4]Soldering temperature for TO-263: 220°C, reflow

[5]$C_{o(er)}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

[6]$C_{o(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

[7]ISD<=ID, di/dt<=400A/us, VDClink=400V, Vpeak<VBR, DSS, Tj<Tj,max.
Identical low-side and high-side switch.

Electrical Characteristics

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Inverse diode continuous forward current	I_S	T_C=25°C	-	-	11	A
Inverse diode direct current, pulsed	I_{SM}		-	-	33	
Inverse diode forward voltage	V_{SD}	V_{GS}=0V, I_F=I_S	-	1	1.2	V
Reverse recovery time	t_{rr}	V_R=480V, I_F=I_S ,	-	400	600	ns
Reverse recovery charge	Q_{rr}	di_F/dt=100A/µs	-	6	-	µC
Peak reverse recovery current	I_{rrm}		-	41	-	A
Peak rate of fall of reverse recovery current	di_{rr}/dt	T_j=25°C	-	1200	-	A/µs

Typical Transient Thermal Characteristics

Symbol	Value		Unit	Symbol	Value		Unit
	SPP_I	SPA			SPP_I	SPA	
R_{th1}	0.015	0.15	K/W	C_{th1}	0.0001878	0.0001878	Ws/K
R_{th2}	0.03	0.03		C_{th2}	0.0007106	0.0007106	
R_{th3}	0.056	0.056		C_{th3}	0.000988	0.000988	
R_{th4}	0.197	0.194		C_{th4}	0.002791	0.002791	
R_{th5}	0.216	0.413		C_{th5}	0.007285	0.007401	
R_{th6}	0.083	2.522		C_{th6}	0.063	0.412	



1 Power dissipation

$P_{tot} = f(T_C)$



2 Power dissipation FullPAK

$P_{tot} = f(T_C)$



3 Safe operating area

$I_D = f(V_{DS})$

parameter : $D = 0$, T_C=25°C



4 Safe operating area FullPAK

$I_D = f(V_{DS})$

parameter: $D = 0$, T_C = 25°C



5 Transient thermal impedance

$Z_{thJC} = f(t_p)$

parameter: $D = t_p/T$



6 Transient thermal impedance FullPAK

$Z_{thJC} = f(t_p)$

parameter: $D = t_p/t$



7 Typ. output characteristic

$I_D = f(V_{DS})$; T_j=25°C

parameter: t_p = 10 µs, V_{GS}



8 Typ. output characteristic

$I_D = f(V_{DS})$; T_j=150°C

parameter: t_p = 10 µs, V_{GS}



9 Typ. drain-source on resistance

$R_{DS(on)}=f(I_D)$

parameter: T_j=150°C, V_{GS}



10 Drain-source on-state resistance

$R_{DS(on)} = f(T_j)$

parameter : I_D = 7 A, V_{GS} = 10 V



11 Typ. transfer characteristics

$I_D= f(V_{GS})$; $V_{DS}\geq 2 \times I_D \times R_{DS(on)max}$

parameter: t_p = 10 µs



12 Typ. gate charge

$V_{GS} = f(Q_{Gate})$

parameter: I_D = 11 A pulsed



13 Forward characteristics of body diode

$I_F = f(V_{SD})$

parameter: T_j , tp = 10 µs



14 Typ. switching time

$t = f(I_D)$, inductive load, T_j=125°C

par.: V_{DS}=380V, V_{GS}=0/+13V, R_G=6.8Ω



15 Typ. switching time

$t = f(R_G)$, inductive load, T_j=125°C

par.: V_{DS}=380V, V_{GS}=0/+13V, I_D=11 A



16 Typ. drain current slope

di/dt = f(R_G), inductive load, T_j = 125°C

par.: V_{DS}=380V, V_{GS}=0/+13V, I_D=11A



17 Typ. drain source voltage slope

$dv/dt = f(R_G)$, inductive load, T_j = 125°C

par.: V_{DS}=380V, V_{GS}=0/+13V, I_D=11A



18 Typ. switching losses

$E = f(I_D)$, inductive load, T_j=125°C

par.: V_{DS}=380V, V_{GS}=0/+13V, R_G=6.8Ω



19 Typ. switching losses

$E = f(R_G)$, inductive load, T_j=125°C

par.: V_{DS}=380V, V_{GS}=0/+13V, I_D=11A



20 Avalanche SOA

$I_{AR} = f(t_{AR})$

par.: $T_j \leq$ 150 °C



21 Avalanche energy

$E_{AS} = f(T_j)$

par.: I_D = 5.5 A, V_{DD} = 50 V



22 Drain-source breakdown voltage

$V_{(BR)DSS} = f(T_j)$



23 Avalanche power losses

$P_{AR} = f(f)$

parameter: E_{AR}=0.6mJ



24 Typ. capacitances

$C = f(V_{DS})$

parameter: V_{GS}=0V, f=1 MHz



25 Typ. C_{oss} stored energy

$E_{oss}=f(V_{DS})$



Definition of diodes switching characteristics



Outline PG-TO220 FullPAK



NOTES:
ALL DIMENSIONS REFER TO JEDEC STANDARD TO-281
AND DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS
OR GATE BURRS
GATE BURRS ARE LESS THAN 0.5 mm

DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
A	4.50	4.90
A1	2.34	2.85
A2	2.42	2.86
b	0.65	0.90
b1	0.95	1.38
b2	0.95	1.51
b3	0.65	1.38
b4	0.65	1.51
c	0.40	0.63
D	15.67	16.15
D1	8.97	9.83
E	10.00	10.65
e	2.54	
H	28.70	29.75
L	12.78	13.75
L1	2.83	3.45
øP	3.00	3.30
Q	3.15	3.50

DOCUMENT NO.
Z8B00003319

REVISION
07

SCALE 5:1

EUROPEAN PROJECTION



ISSUE DATE
27.01.2017

PG-TO-262-3-1 (I²-PAK)



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.300	4.500	0.169	0.177
A1	2.150	2.650	0.085	0.104
b	0.650	0.850	0.026	0.033
b1	0.635	1.400	0.025	0.055
c	0.400	0.600	0.016	0.024
c1	1.170	1.370	0.046	0.054
D	9.050	9.450	0.356	0.372
D1	6.900	7.650	0.272	0.301
E	9.800	10.200	0.386	0.402
E1	7.250	8.600	0.285	0.339
e	2.540		0.100	
e1	5.080		0.200	
N	3		3	
L	13.000	14.000	0.512	0.551
L1	4.350	4.750	0.171	0.187
L2	0.700	1.300	0.028	0.051

REFERENCE
JEDEC TO262

SCALE



EUROPEAN PROJECTION



ISSUE DATE
01-06-2005

FILE
TO262_1

PG-TO-220-3-1, PG-TO-220-3-21



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.30	4.57	0.169	0.180
A1	1.17	1.40	0.046	0.055
A2	2.15	2.72	0.085	0.107
b	0.65	0.86	0.026	0.034
b1	0.95	1.40	0.037	0.055
b2	0.95	1.15	0.037	0.045
b3	0.65	1.15	0.026	0.045
c	0.33	0.60	0.013	0.024
D	14.81	15.95	0.583	0.628
D1	8.51	9.45	0.335	0.372
D2	12.19	13.10	0.480	0.516
E	9.70	10.36	0.382	0.408
E1	6.50	8.60	0.256	0.339
e	2.54		0.100	
e1	5.08		0.200	
N	3		3	
H1	5.90	6.90	0.232	0.272
L	13.00	14.00	0.512	0.551
L1	-	4.80	-	0.189
øP	3.60	3.89	0.142	0.153
Q	2.60	3.00	0.102	0.118

DOCUMENT NO.
Z8B00003318

SCALE
0 2.5 5mm

EUROPEAN PROJECTION

ISSUE DATE
23-08-2007

REVISION
05

Revision History

SPx11N60C3

Revision: 2018-02-09, Rev. 2.3

Previous Revision

Revision	Date	Subjects (major changes since last revision)
3.3	2018-02-09	Outline FullPAK update

We Listen to Your Comments
Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:
erratum@infineon.com

Published by
Infineon Technologies AG
81726 München, Germany

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie") .

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.
In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.
The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Information
For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (**www.infineon.com**).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.