

Final datasheet

IHM-B module with Trench/Fieldstop IGBT4 and emitter controlled 4 diode

Features

- Electrical features
 - $V_{CES} = 4500\text{ V}$
 - $I_{C\text{ nom}} = 1200\text{ A} / I_{CRM} = 2400\text{ A}$
 - High DC stability
 - High short-circuit capability
 - High dynamic robustness
 - Low $V_{CE,sat}$
 - Trench IGBT 4
 - $V_{CE,sat}$ with positive temperature coefficient
- Mechanical features
 - AlSiC base plate for increased thermal cycling capability
 - Package with CTI > 600
 - IHM B housing
 - Isolated base plate
 - Standard housing



Typical appearance

Potential applications

- High-power converters
- Medium-voltage converters
- Power transmission and distribution

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	3
3	Diode, Inverter	5
4	Characteristics diagrams	7
5	Circuit diagram	11
6	Package outlines	12
7	Module label code	13
	Revision history	14
	Disclaimer	15

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 1 \text{ min}$	6.0	kV
Partial discharge extinction voltage	V_{isol}	RMS, $f = 50 \text{ Hz}$, $Q_{PD} \leq 10 \text{ pC}$	3.5	kV
DC stability	$V_{CE(D)}$	$T_{vj} = 25 \text{ °C}$, 100 Fit	2900	V
Material of module baseplate			AlSiC	
Creepage distance	d_{Creep}	terminal to heatsink	32.2	mm
Clearance	d_{Clear}	terminal to heatsink	19.1	mm
Comparative tracking index	CTI		> 600	

Table 2 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Stray inductance module	L_{sCE}				6		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	T _C = 25 °C, per switch			0.08		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	T _C = 25 °C, per switch			0.095		mΩ
Storage temperature	T_{stg}			-40		150	°C
Mounting torque for module mounting	M	- Mounting according to valid application note	M6, Screw	4.25		5.75	Nm
Terminal connection torque	M	- Mounting according to valid application note	M4, Screw	1.8		2.1	Nm
			M8, Screw	8		10	
Weight	G				1200		g

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		$T_{vj} = -40 \text{ °C}$	4300	V
			$T_{vj} = 150 \text{ °C}$	4500	
Continuous DC collector current	I_{CDC}	$T_{vj \text{ max}} = 150 \text{ °C}$	$T_C = 110 \text{ °C}$	1200	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj \text{ op}}$		2400	A
Gate-emitter peak voltage	V_{GES}			-20/20	V

Table 4 **Characteristic values**

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 1200\ A, V_{GE} = 15\ V$	$T_{vj} = 25\ ^\circ C$		2.30	2.75	V
			$T_{vj} = 125\ ^\circ C$		2.70	3.25	
			$T_{vj} = 150\ ^\circ C$		2.85	3.40	
Gate threshold voltage	V_{GETh}	$I_C = 112\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$		5.5	6	6.5	V
Gate charge	Q_G	$V_{GE} = \pm 15\ V, V_{CC} = 2800\ V$			35		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\ ^\circ C$			0.39		Ω
Input capacitance	C_{ies}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			223		nF
Reverse transfer capacitance	C_{res}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$			4.1		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 4500\ V, V_{GE} = 0\ V$	$T_{vj} = 25\ ^\circ C$			5	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$				400	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 1200\ A, V_{CC} = 2800\ V, V_{GE} = \pm 15\ V, R_{Gon} = 1.3\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.330		μs
			$T_{vj} = 125\ ^\circ C$		0.360		
			$T_{vj} = 150\ ^\circ C$		0.370		
Rise time (inductive load)	t_r	$I_C = 1200\ A, V_{CC} = 2800\ V, V_{GE} = \pm 15\ V, R_{Gon} = 1.3\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.260		μs
			$T_{vj} = 125\ ^\circ C$		0.270		
			$T_{vj} = 150\ ^\circ C$		0.280		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 1200\ A, V_{CC} = 2800\ V, V_{GE} = \pm 15\ V, R_{Goff} = 9.1\ \Omega$	$T_{vj} = 25\ ^\circ C$		9.300		μs
			$T_{vj} = 125\ ^\circ C$		9.800		
			$T_{vj} = 150\ ^\circ C$		9.900		
Fall time (inductive load)	t_f	$I_C = 1200\ A, V_{CC} = 2800\ V, V_{GE} = \pm 15\ V, R_{Goff} = 9.1\ \Omega$	$T_{vj} = 25\ ^\circ C$		0.740		μs
			$T_{vj} = 125\ ^\circ C$		1.730		
			$T_{vj} = 150\ ^\circ C$		2.040		
Turn-on time (resistive load)	t_{on_R}	$I_C = 500\ A, V_{CC} = 2000\ V, V_{GE} = \pm 15\ V, R_{Gon} = 1.3\ \Omega$	$T_{vj} = 25\ ^\circ C$	1.24			μs
Turn-on energy loss per pulse	E_{on}	$I_C = 1200\ A, V_{CC} = 2800\ V, L_\sigma = 150\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 1.3\ \Omega, di/dt = 3700\ A/\mu s (T_{vj} = 150\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		4100		mJ
			$T_{vj} = 125\ ^\circ C$		5800		
			$T_{vj} = 150\ ^\circ C$		6350		
Turn-off energy loss per pulse	E_{off}	$I_C = 1200\ A, V_{CC} = 2800\ V, L_\sigma = 150\ nH, V_{GE} = \pm 15\ V, R_{Goff} = 9.1\ \Omega, dv/dt = 1000\ V/\mu s (T_{vj} = 150\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$		5500		mJ
			$T_{vj} = 125\ ^\circ C$		6900		
			$T_{vj} = 150\ ^\circ C$		7300		

(table continues...)

Table 4 (continued) **Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
SC data	I_{SC}	$V_{GE} \leq 15 \text{ V}$, $V_{CC} = 3000 \text{ V}$, $V_{CEmax} = V_{CES} - L_{SCE} \cdot di/dt$ $t_p \leq 10 \mu\text{s}$, $T_{vj} = 150 \text{ }^\circ\text{C}$		6400		A
Thermal resistance, junction to case	R_{thJC}	per IGBT			9.40	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per IGBT, $\lambda_{grease} = 1 \text{ W/(m}\cdot\text{K)}$		4.10		K/kW
Temperature under switching conditions	$T_{vj op}$		-40		150	$^\circ\text{C}$

3 Diode, Inverter

Table 5 **Maximum rated values**

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = -40 \text{ }^\circ\text{C}$	4500	V
			$T_{vj} = 150 \text{ }^\circ\text{C}$	4500	
Continuous DC forward current	I_F			1200	A
Repetitive peak forward current	I_{FRM}	$t_p = 1 \text{ ms}$		2400	A
I^2t - value	I^2t	$t_p = 10 \text{ ms}$, $V_R = 0 \text{ V}$	$T_{vj} = 125 \text{ }^\circ\text{C}$	760	kA^2s
			$T_{vj} = 150 \text{ }^\circ\text{C}$	710	
Maximum power dissipation	P_{RQM}		$T_{vj} = 150 \text{ }^\circ\text{C}$	2400	kW
Minimum turn-on time	t_{onmin}			10	μs

Table 6 **Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 1200 \text{ A}$, $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	2.50	2.95	V
			$T_{vj} = 125 \text{ }^\circ\text{C}$	2.40	2.85	
			$T_{vj} = 150 \text{ }^\circ\text{C}$	2.30	2.75	
Peak reverse recovery current	I_{RM}	$V_{CC} = 2800 \text{ V}$, $I_F = 1200 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt = 3700 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ }^\circ\text{C}$)	$T_{vj} = 25 \text{ }^\circ\text{C}$	1400		A
			$T_{vj} = 125 \text{ }^\circ\text{C}$	1640		
			$T_{vj} = 150 \text{ }^\circ\text{C}$	1750		

(table continues...)

Table 6 (continued) Characteristic values


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Recovered charge	Q_r	$V_{CC} = 2800 \text{ V}$, $I_F = 1200 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt =$ $3700 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ }^\circ\text{C}$)	$T_{vj} = 25 \text{ }^\circ\text{C}$	1000		μC
			$T_{vj} = 125 \text{ }^\circ\text{C}$	2000		
			$T_{vj} = 150 \text{ }^\circ\text{C}$	2380		
Reverse recovery energy	E_{rec}	$V_{CC} = 2800 \text{ V}$, $I_F = 1200 \text{ A}$, $V_{GE} = -15 \text{ V}$, $-di_F/dt =$ $3700 \text{ A}/\mu\text{s}$ ($T_{vj} = 150 \text{ }^\circ\text{C}$)	$T_{vj} = 25 \text{ }^\circ\text{C}$	1500		mJ
			$T_{vj} = 125 \text{ }^\circ\text{C}$	3300		
			$T_{vj} = 150 \text{ }^\circ\text{C}$	4000		
Thermal resistance, junction to case	R_{thJC}	per diode			15.6	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per diode, $\lambda_{grease} = 1 \text{ W}/(\text{m}\cdot\text{K})$		6.20		K/kW
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		150	$^\circ\text{C}$

4 Characteristics diagrams

Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{GE} = 15\text{ V}$



Output characteristic field (typical), IGBT, Inverter

$I_C = f(V_{CE})$


$T_{vj} = 150\text{ }^\circ\text{C}$



Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$


$V_{CE} = 20\text{ V}$



Gate charge characteristic (typical), IGBT, Inverter

$V_{GE} = f(Q_G)$

$I_C = 1200\text{ A}, T_{vj} = 25\text{ }^\circ\text{C}$




4 Characteristics diagrams

Capacity characteristic (typical), IGBT, Inverter

$$C = f(V_{CE})$$


$f = 100 \text{ kHz}$, $V_{GE} = 0 \text{ V}$, $T_{vj} = 25^\circ \text{C}$



Switching times (typical), IGBT, Inverter

$$t = f(I_C)$$


$R_{Goff} = 9.1 \Omega$, $R_{Gon} = 1.3 \Omega$, $V_{CC} = 2800 \text{ V}$, $V_{GE} = -15 \text{ V} / 15 \text{ V}$, $T_{vj} = 150^\circ \text{C}$



Switching times (typical), IGBT, Inverter

$$t = f(R_G)$$


$I_C = 1200 \text{ A}$, $V_{CC} = 2800 \text{ V}$, $V_{GE} = -15 \text{ V} / 15 \text{ V}$, $T_{vj} = 150^\circ \text{C}$



Switching losses (typical), IGBT, Inverter

$$E = f(I_C)$$


$R_{Goff} = 9.1 \Omega$, $R_{Gon} = 1.3 \Omega$, $V_{CC} = 2800 \text{ V}$, $V_{GE} = -15 / 15 \text{ V}$



4 Characteristics diagrams


Switching losses (typical), IGBT, Inverter

$E = f(R_G)$
 $I_C = 1200\text{ A}, V_{CC} = 2800\text{ V}, V_{GE} = -15 / 15\text{ V}$




Reverse bias safe operating area (RBSOA), IGBT, Inverter

$I_C = f(V_{CE})$
 $R_{Goff} = 9.1\text{ }\Omega, V_{GE} = \pm 15\text{ V}, V_{CC} \leq 3200\text{ V}, T_{vj} = 150\text{ }^\circ\text{C}$




Transient thermal impedance, IGBT, Inverter

$Z_{th} = f(t)$



Forward characteristic (typical), Diode, Inverter


$I_F = f(V_F)$



4 Characteristics diagrams


Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$
 $R_{Gon} = R_{Gon}(IGBT)$, $V_{CC} = 2800\text{ V}$




Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$
 $I_F = 1200\text{ A}$, $V_{CC} = 2800\text{ V}$




Safe operating area (SOA), Diode, Inverter

$I_R = f(V_R)$
 $T_{vj} = 150\text{ }^{\circ}\text{C}$



Transient thermal impedance, Diode, Inverter

$Z_{th} = f(t)$



5 Circuit diagram




Figure 1

6 Package outlines




Figure 2

7 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
	 71549142846550549911530	 71549142846550549911530	

Figure 3



Revision history

Revision history

Document revision	Date of release	Description of changes
1.00	2023-12-14	Initial version

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-12-14

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2023 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABI543-001

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infiniteon:](#)

[FZ1200R45HL4BPSA1](#)