

BGSC2341ML10

RF Digitally Tunable Capacitor + SPDT Switch

Features

- Designed for high-linearity applications
- Ultra low R_{ON} resistance of 0.87 Ω at each SPDT throw in ON state
- High operating RF Voltage handling 40 V
- 0.25-2.00 pF Tuning range at 1.8 GHz
- Operating frequencies: 0.4 3.8 GHz
- High ESD Robustness
- MIPI 2.1 RFFE compliant control interface
- 2 default USID selectable via USID_SEL pin
- Supply voltage range: 1.65 to 1.95 V
- Small form factor 1.1 mm x 1.5 mm (MSL1, 260°C per JEDEC J-STD-020)
- RoHS and WEEE compliant package



- Impedance Tuning
- Antenna Tuning
- Inductance Tuning

Product Validation

Qualified for industrial applications according to the relevant tests of JEDEC47/20/22.

Block diagram





1.1 x 1.5 mm²

BGSC2341ML10

RF Digitally Tunable Capacitor + SPDT Switch

Table of Contents

Table of Contents

Та	ble of Contents	1
1	Features	2
2	Maximum Ratings	3
3	DC Characteristics	4
4	RF Small Signal Characteristics	5
5	RF Large Signal Parameters	8
6	MIPI RFFE Specification	10
7	Application Information	17
8	Package Information	18



Features

1 Features

- Designed for high-linearity applications
- Ultra low R_{ON} resistance of 0.87 Ω at each SPDT throw in ON state
- High operating RF Voltage handling 40 V
- 0.25-2.00 pF Tuning range at 1.8 GHz
- Operating frequencies: 0.4 3.8 GHz
- High ESD Robustness
- MIPI 2.1 RFFE compliant control interface
- 2 default USID selectable via USID_SEL pin
- Supply voltage range: 1.65 to 1.95 V
- Small form factor 1.1 mm x 1.5 mm (MSL1, 260°C per JEDEC J-STD-020)
- RoHS and WEEE compliant package



Description

The BGSC2341ML10 is a versatile Integrated Circuit (IC) ideal for RF tuning applications such as tunable impedance matching, antenna tuning, tunable filtering. This IC integrates a 8 states tunable capacitor and an extremely low Ron Single Pole Double Throw (SPDT) RF switch function; both controlled by on-chip MIPI2.1 RFFE digital interface. Last but not the least, the BGSC2341ML10 exhibits very good linearity in high RF power conditions and up to RF Voltage of 40 V which is a key attribute in application like antenna tuning. It does not require any additional High Voltage Supply Controller IC and can be powered by a single 1.8 V Power Supply at an extremely low current consumption level. With 1.1 mm x 1.5 mm package dimensions, it is a compact solution fitting well to any small form factor mobile phone-like applications.



Product Name	Marking	Package	Ordering Information
BGSC2341ML10	C2	TSLP-10-2	BGSC 2341ML10 E6327





Maximum Ratings

2 Maximum Ratings



Figure 1: RF operating voltage measurement configuration (Switches 1,2 OFF and C1-Tuner position in Isolation Mode)

Parameter	Symbol Values				Unit	Note / Test Condition	
		Min.	Тур.	Max.	1		
Frequency Range	f	0.4	-	3.8	GHz	1)	
Storage temperature range	T _{STG}	-55	-	150	°C	-	
RF input power	P _{RF_max}	-	-	39	dBm	Pulsed RF input duty cycle of 25 % and 4620 µs in ON-state, measured per 3GPP TS 45.005	
RF voltage	V _{RF_max}	-	-	45	V	Short term peaks (1 μ s in 0.1% duty cycle), exceeding typical linearity, R_{ON} and C_{OFF} parameters, in Isolation mode, test condition schematic in Fig. 1	
ESD robustness, CDM ³⁾	V _{ESD_{CDM}}	-1	-	+1	kV		
ESD robustness, HBM ⁴⁾	V _{ESDHBM}	-750	-	+750	V		
Junction temperature	Tj	-	-	125	°C	-	
Thermal resistance junction - soldering point	R _{thJS}	-	40	43	K/W	-	
RFFE Supply Voltage	V _{IO}	-0.5	-	2.2	V	-	
RFFE Control Voltage Levels	V _{SCLK} , V _{SDAT} , V _{USID SEL}	-0.7	-	V _{IO} +0.7 (max. 2.2)	V	_	

Table 1: Maximum Ratings at $T_A = 25 \text{ °C}$, unless otherwise specified

¹⁾ Switch has a low-pass response. For higher frequencies, losses have to be considered for their impact on thermal heating. The DC voltage at RF ports V_{RFDC} has to be 0V.

²⁾ Note: Consider any ripple voltages on top of V_{DD} . A high RF ripple at the V_{DD} can exceed the maximum ratings by $V_{DD} = V_{DC} + V_{Ripple}$.

³⁾ Field-Induced Charged-Device Model ANSI/ESDA/JEDEC JS-002. Simulates charging/discharging events that occur in production equipment and processes. Potential for CDM ESD events occurs whenever there is metal-to-metal contact in manufacturing.

 $^{4)}$ Human Body Model ANSI/ESDA/JEDEC JS-001 (R = $1.5~{\rm k}\Omega,$ C = $100~{\rm pF}).$

⁵⁾ IEC 61000-4-2 ($R = 330 \Omega$, C = 150 pF), contact discharge.

Attention: Stresses above the max. values listed here may cause permanent damage to the device. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the integrated circuit. Exposure to conditions at or below absolute maximum rating but above the specified maximum operation conditions may affect device reliability and life time. Functionality of the device might not be given under these conditions.



DC Characteristics

3 DC Characteristics

Table 2: DC Characteristics at $T_A = -40 \,^{\circ}$ C to 85 $^{\circ}$ C

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Тур.	Max.		
RFFE supply voltage	V _{IO}	1.65	1.8	1.95	V	-
RFFE input high voltage ¹	V _{IH}	0.7*V _{IO}	-	V _{IO}	V	-
RFFE input low voltage ¹	V _{IL}	0	-	0.3*V _{IO}	V	-
RFFE output high voltage ¹	V _{OH}	0.8*V _{IO}	-	V _{IO}	V	-
RFFE output low voltage ¹	V _{OL}	0	-	0.2*V _{I0}	V	-
RFFE control input capacitance	C _{Ctrl}	-	-	2	pF	-
REEE supply surront	,	-	1.7	9	μA	VIO shutdown mode
KFFE supply current	1010	-	65	110	μΑ	Power up mode

¹SCLK and SDATA

BGSC2341ML10

RF Digitally Tunable Capacitor + SPDT Switch



RF Small Signal Characteristics

4 RF Small Signal Characteristics



Figure 2: RF measurement equivalent circuit

Table 3: Parametric specifications of DC the equivalent circuit

Parameter	Symbol	Values		Values Unit		STATE / Notes
		Min.	Тур.	Max.		
SPDT						
R _{ON} DC ON resistance	R _{ON}	0.66	0.87	1.08	Ω	$V_{IO} = 1.65 - 1.95 V$,
R _{OFF} DC OFF resistance	R _{OFF}	77	110	133	KΩ	$T_A = -40 ^{\circ}\text{C} + 85 ^{\circ}\text{C}$



RF Small Signal Characteristics

Parameter	Symbol		Values			STATE / Notes
		Min.	Тур.	Max.		
C _{P,ESD} SHUNT capacitance	C _{P,ESD}	190	220	285	fF	
C-Tuner	·	L.		1		
C _{tune} State 0	Co	245	260	285	fF	
C _{tune} State 1	<i>C</i> ₁	440	460	520	fF	$V_{0} = 1.65 - 1.95 V$
C _{tune} State 2	<i>C</i> ₂	635	665	750	fF	$\int T_{A} = 25^{\circ}C$
C _{tune} State 3	<i>C</i> ₃	835	870	970	fF	
C _{tune} State 4	<i>C</i> ₄	1030	1075	1210	fF	
C _{tune} State 5	<i>C</i> ₅	1220	1280	1430	fF	
C _{tune} State 6	<i>C</i> ₆	1435	1500	1675	fF	
C _{tune} State 7	C ₇	1685	1775	2000	fF	
C _{P,tune} SHUNT capacitance	C _{P,tune}	175	205	245	fF	
SPDT						
C _{OFF} OFF capacitance	C _{OFF}	185	200	225	fF	
C _{P,RF} SHUNT capacitance	C _{P,RF}	120	165	225	fF	

Table 4: Parametric specifications of the RF equivalent circuit @ f= 900 MHz^(1,2,3)

¹⁾ Network analyser input power: $P_{IN} = 0 \, dBm$

²⁾ On application board without any matching components.

³⁾ This C-tuner has a monotonic behaviour: C value will increase if programming a growing C state and decrease if programming a decreasing C state.

Parameter	Symbol		Values		Unit	STATE / Notes
		Min.	Тур.	Max.		
C _{P,ESD} SHUNT capacitance	C _{P,ESD}	200	215	270	fF	
C-Tuner	·					
C _{tune} State 0	Co	250	270	300	fF	
C _{tune} State 1	<i>C</i> ₁	460	500	560	fF	$V_{10} = 1.65 - 1.95 V_{10}$
C _{tune} State 2	C ₂	670	725	810	fF	$T_{\star} = 25^{\circ}C$
C _{tune} State 3	<i>C</i> ₃	900	1000	1100	fF	
C _{tune} State 4	C ₄	1110	1200	1360	fF	
C _{tune} State 5	C ₅	1350	1475	1650	fF	
C _{tune} State 6	<i>C</i> ₆	1595	1750	1950	fF	
C _{tune} State 7	C ₇	1855	2000	2300	fF	
<i>C_{P,tune}</i> SHUNT capacitance	C _{P,tune}	160	185	230	fF	
SPDT						
C _{OFF} OFF capacitance	C _{OFF}	185	205	230	fF	
C _{P,RF} SHUNT capacitance	C _{P,RF}	110	155	265	fF	
1) Network analyser input newer: D. = 0	dBm				•	

Table 5: Parametric specifications of the RF equivalent circuit @ f= 1.8 GHz $^{(1,2,3)}$

¹⁾ Network analyser input power: $P_{IN} = 0 \, dBm$

 $^{\rm 2)}$ On application board without any matching components.

³⁾ This C-tuner has a monotonic behaviour: C value will increase if programming a growing C state and decrease if programming a decreasing C state.



RF Small Signal Characteristics

Table 6: Parametric specifications of the RF equivalent circuit @ f= 2.7 GHz $^{(1,2,3)}$

Parameter	Symbol	Values			Unit	STATE / Notes
		Min.	Тур.	Max.		
C _{P,ESD} SHUNT capacitance	C _{P,ESD}	205	225	260	fF	
C-Tuner				1		
C _{tune} State 0	Co	260	290	320	fF	
C _{tune} State 1	<i>C</i> ₁	500	550	610	fF	$V_{0} = 1.65 - 1.95 V$
C _{tune} State 2	C ₂	755	840	935	fF	$T_{1,0} = 1.05$ $1.05 V_{1,0}$
C _{tune} State 3	<i>C</i> ₃	1050	1180	1300	fF	$\gamma_A = 25$ C
C _{tune} State 4	C ₄	1275	1400	1610	fF	
C _{tune} State 5	C ₅	1590	1800	2000	fF	
C _{tune} State 6	C ₆	1940	2200	2460	fF	
C _{tune} State 7	C ₇	2345	2660	3240	fF	
C _{P,tune} SHUNT capacitance	C _{P,tune}	155	180	210	fF	
SPDT		1	·	1		
C _{OFF} OFF capacitance	C _{OFF}	190	215	250	fF	
C _{P,RF} SHUNT capacitance	C _{P,RF}	120	155	185	fF	
¹⁾ Network analyser input power: $P_{IN} = 0$	dBm					

²⁾ On application board without any matching components.

³⁾ This C-tuner has a monotonic behaviour: C value will increase if programming a growing C state and decrease if programming a decreasing C state.



RF Large Signal Parameters

5 RF Large Signal Parameters

Parameter	Symbol		Values		Unit	Note / Test Condition
		Min.	Тур.	Max.		
RF operating voltage	V _{RF_peak}	-	-	40	V	In Isolation mode, test condition
						schematic in Fig. 1 for H2/H3 < -
						35dBm @ 50Ω, <i>T</i> _A = 25 °C
Harmonic Generation up to 12.7	5 GHz ^(1,2)					
All RF Ports - Second Order Har-	P _{H2}	-	-71	-65	dBm	$25 \text{dBm}, f_0 = 824 \text{MHz}$
monics						
All RF Ports - Third Order Harmon-	P _{H3}	-	-84	-79	dBm	25 dBm, f_0 = 824 MHz
ics						
All RF Ports - Second Order Har-	P _{H2}	-	-44	-39	dBm	$35 \mathrm{dBm}, f_0 = 824 \mathrm{MHz}$
monics						
All RF Ports - Third Order Harmon-	P _{H3}	-	-56	-50	dBm	$35 \mathrm{dBm}, f_0 = 824 \mathrm{MHz}$
ics						
All RF Ports - Second Order Har-	P _{H2}	-	-48	-46	dBm	$33 \text{dBm}, f_0 = 1800 \text{MHz},$
monics						$T_A = 25 ^{\circ}\text{C}$
All RF Ports - Third Order Harmon-	P _{H3}	-	-52	-51	dBm	33 dBm, f_0 = 1800 MHz,
ics						$T_A = 25 ^{\circ}\text{C}$
All RF Ports	P _{Hx}	-	-87	-65	dBm	26 dBm , f_0 = 663 MHz, T_A = 25 °C
Intermodulation Distortion IMD	2 ^(1,2)				-	
IIP2, low	IIP2,l	100	111	-	dBm	
IIP2, high	llP2,h	100	116	-	dBm	IIP2 conditions Table 8
Intermodulation Distortion IMD	3 ^(1,2)					
IIP3	IIP3	70	73	-	dBm	IIP3 conditions Table 9

Table 7: RF large signal specifications at $T_{4} = -40 + 85$ °C unless otherwise specified

¹⁾ Terminating Port Impedance: $Z_0 = 50 \Omega$ ²⁾ On application board without any matching components

Table 8: IIP2 conditions table

Band	In-Band Frequency	Blocker Frequency 1	Blocker Power 1	Blocker Frequency 2	Blocker Power 2
	[MHz]	[MHz]	[dBm]	[MHz]	[dBm]
Band 1 Low	2140	1950	20	190	-15
Band 1 High	2140	1950	20	4090	-15
Band 5 Low	881.5	836.5	20	45	-15
Band 5 High	881.5	836.5	20	1718	-15



RF Large Signal Parameters

Table 9: IIP3 conditions table

Band	In-Band Frequency	Blocker Frequency 1 Blocker Power 1 E		Blocker Frequency 2	Blocker Power 2
	[MHz]	[MHz]	[dBm]	[MHz]	[dBm]
Band 1	2140	1950	20	1760	-15
Band 5	881.5	836.5	20	791.5	-15



MIPI RFFE Specification

6 MIPI RFFE Specification

Warning: Register_0 and Register_1 RF switch control bits are identical. Writing both Registers Register_0 and Register_1 simultaneously will lead to undefined behavior. The unused register (Register_0 or Register_1) must remain 0x00.

The MIPI RFFE interface is working in systems following the 'MIPI Alliance Specification for RF Front-End Control Interface version 2.1 - 18 December 2017', the 'MIPI Alliance Errata 01 for MIPI RFFE Specification version 2.1 - 24 February 2019', and the 'Qualcomm RFFE Vendor specification 80-N7876-1 Rev. W.'

Table 10: MIPI Features

Feature	Supported	Comment
MIPI RFFE 2.1 standard	Yes	Backward compatible to MIPI 2.0 standard
Register 0 write command sequence	Yes	
Register read and write command sequence	Yes	
Extended register read and write command sequence	Yes	
Masked write command sequence	Yes	Indicated as MW in below register mapping tables
Support for standard frequency range operations for	Yes	Up to 26 MHz for read and write
SCLK		
Support for extended frequency range operations for	Yes	Up to 52 MHz for write
SCLK		
Half speed read	Yes	Up to 26 MHz
Full speed read	Yes	Up to 26 MHz
Full speed write	Yes	
Longer Reach RFFE Bus Length Feature	Yes	
Programmable driver strength	Yes	Up to 80 pF
Programmable Group SID	Yes	
Programmable USID	Yes	
Trigger functionality	Yes	
Extended Triggers and Trigger Masks	Yes	
Broadcast / GSID write to PM TRIG register	Yes	
Reset	Yes	Via VIO, PM TRIG or software register
Status / error sum register	Yes	
Extended product ID register	Yes	
Revision ID register	Yes	
Group SID register	Yes	
USID_SEL pin	Yes	See Table 14

Table 11: Startup Behavior

Feature	State	Comment
Power status	Low power	Lower power mode after start-up
		Default power mode is HIGH
Trigger function	Enabled	Enabled after start-up. Programmable via behavior control register



MIPI RFFE Specification

Table 12: Switching Time Behavior

Parameter	Symbol		Values		Unit	STATE / Notes	
		Min.	Тур.	Max.			
Power Up Settling Time	t _{PUP}	-	6.5	13	μs	Time from Power Up plus Switch command 50% last SCLK falling edge to 90% RF-Signal, see Fig. 3	
SW1, SW2 SPST Switching Time	t _{STsw1,sw2}	-	10.5	16	μs	Time switching between RF states 50% last SCLK falling edge to 90% RF-Signal, see Fig. 3	
C1 C-Tuner Switching Time	t _{STc1}	-	9.5	17	μ s		



Figure 3: BGSC2341ML10 Switching Time Behavior



MIPI RFFE Specification

Table 13: Register Mapping, Table I

Register Address	Register Name	Data Bits	Function	Description	Default	Broadcast_ID Support	Trigger Support	R/W
0x00	REGISTER_0	7:0	MODE_CTRL	RF Switches and C-Tuner Control	00000000	No	Yes	R/W
							Trigger 0-10	мw
0x01	REGISTER_1	7:0	MODE_CTRL	RF Switches and C-Tuner Control	00000000	No	Yes	R/W
							Trigger 0-10	мw
0x1C	PM_TRIG	7	PWR_MODE(1)	0: Normal operation (ACTIVE)	1	Yes	No	R/W
			Operation Mode	1: Low Power Mode (LOW POWER)				мw
		6	PWR_MODE(0)	0: No action (ACTIVE)	0			
			State Bit Vector	1: Powered Reset (STARTUP to ACTIVE to LOW POWER)				
		5	TRIGGER_MASK_2	0: Data masked (held in shadow REG)	0	No		
				1: Data not masked (ready for transfer to active REG)				
		4	TRIGGER_MASK_1	0: Data masked (held in shadow REG)	0			
				1: Data not masked (ready for transfer to active REG)				
		3	TRIGGER_MASK_0	0: Data masked (held in shadow REG)	0			
				1: Data not masked (ready for transfer to active REG)				
	2		TRIGGER_2	0: No action (data held in shadow REG)	0	Yes		
				1: Data transferred to active REG				
			TRIGGER_1	0: No action (data held in shadow REG)	0			
				1: Data transferred to active REG				
		0	TRIGGER_0	0: No action (data held in shadow REG)	0			
				1: Data transferred to active REG				
0x1D	PRODUCT_ID	7:0	PRODUCT_ID	This is a read-only register. However, during the programming of the USID a write command sequence is performed on this register, even though the write does not change its value.	01001101	No	No	R
0x1E	MAN_ID	7:0	MANUFACTURER_ID [7:0]	This is a read-only register. However, during the programming of the USID, a write command sequence is performed on this register, even though the write does not change its value.	00011010	No	No	R
0x1F	MAN_USID	7:4	MANUFACTURER_ID [11:8]	These bits are read-only. However, dur- ing the programming of the USID, a write command sequence is performed on this register even though the write does not change its value.	01			
		3:0	USID[1:0]	USID_SEL pin	See Tab. 10	No	No	R/W



MIPI RFFE Specification

Table 14: Register Mapping, Table II

Register Address	Register Name	Data Bits	Function	Description	Default	Broadcast_ID Support	Trigger Support	R/W
0x20	EXT_PRODUCT_ID	7:0	EXT_PRODUCT_ID	Extension to PRODUCT_ID in register 0x1D. This is a read-only register. How- ever, during the programming of the USID a write command sequence is per- formed on this register, even though the write does not change its value.	0000000	No	No	R
0x21	REV_ID	7:4	MAIN_REVISION	Chip main revision	0001	No	No	R
		3:0	SUB_REVISION	Chip sub revision	0000			
0x22	GSID	7:4	GSID0[3:0]	Primary Group Slave ID.	0000	No	No	R/W
		3:0	GSID1[3:0]	Secondary Group Slave ID.	0000			
0x23	UDR_RST	7	UDR_RST	Reset all configurable non-RFFE Re- served registers to default values. 0: Normal operation 1: Software reset	0	Yes	No	R/W
		6:0	RESERVED	Reserved for future use	0000000			
0x24	ERR_SUM	7	RESERVED	Reserved for future use	0	No	No	R
		6	COMMAND_FRAME_PARITY_ERR	Command Sequence received with par- ity error — discard command.	0			
		5	COMMAND_LENGTH_ERR	Command length error.	0			
		4	ADDRESS_FRAME_PARITY_ERR	Address frame with parity error.	0			
		3	DATA_FRAME_PARITY_ERR	Data frame with parity error.	0			
		2	READ_UNUSED_REG	Read command to an invalid address.	0			
		1	WRITE_UNUSED_REG	Write command to an invalid address.	0			
		0	BID_GID_ERR	Read command with a BROADCAST_ID or GROUP_ID.	0			
0x2B	BUS_LD	7:4	RESERVED	Reserved for future use	0x0	No	No	R/W
		3:0	BUS_LD[3:0]	Set approximate bus load, default 50 pF 0x8-0xF: Spare	0x4			



MIPI RFFE Specification

Table 15: Register Mapping, Table III

Register Address	Register Name	Data Bits	Function	Description	Default	Broadcast_ID Support	Trigger Support	R/W
0x2D	EXT_TRIG_MASK	7	TRIGGER_MASK_10	0: Data writes to registers tied to EXT_TRIGGER_10 are masked. Data is held in shadow registers until the EXT_TRIGGER_10 bit is set to 1. 1: Data writes to registers tied to EXT_TRIGGER_10 are not masked. Data writes go directly to the active registers.	1	No	No	R/W MW
		6	TRIGGER_MASK_9	0: Data writes to registers tied to EXT_TRIGGER_9 are masked. Data is held in shadow registers until the EXT_TRIGGER_9 bit is set to 1. 1: Data writes to registers tied to EXT_TRIGGER_9 are not masked. Data writes go directly to the active registers.	1			
		5	TRIGGER_MASK_8	0: Data writes to registers tied to EXT_TRIGGER_8 are masked. Data is held in shadow registers until the EXT_TRIGGER_8 bit is set to 1. 1: Data writes to registers tied to EXT_TRIGGER_8 are not masked. Data writes go directly to the active registers.	1	-		
		4	TRIGGER_MASK_7	 Data writes to registers tied to EXT_TRIGGER_7 are masked. Data is held in shadow registers until the EXT_TRIGGER_7 bit is set to 1. Data writes to registers tied to EXT_TRIGGER_7 are not masked. Data writes go directly to the active registers. 	1	-		
		3	TRIGGER_MASK_6	 0: Data writes to registers tied to EXT_TRIGGER_6 are masked. Data is held in shadow registers until the EXT_TRIGGER_6 bit is set to 1. 1: Data writes to registers tied to EXT_TRIGGER_6 are not masked. Data writes go directly to the active registers. 	1			
		2	TRIGGER_MASK_5	0: Data writes to registers tied to EXT_TRIGGER_5 are masked. Data is held in shadow registers until the EXT_TRIGGER_5 bit is set to 1. 1: Data writes to registers tied to EXT_TRIGGER_5 are not masked. Data writes go directly to the active registers.	1			
		1	TRIGGER_MASK_4	 0: Data writes to registers tied to EXT_TRIGGER_4 are masked. Data is held in shadow registers until the EXT_TRIGGER_4 bit is set to 1. 1: Data writes to registers tied to EXT_TRIGGER_4 are not masked. Data writes go directly to the active registers. 	1			
		0	TRIGGER_MASK_3	0: Data writes to registers tied to EXT_TRIGGER_3 are masked. Data is held in shadow registers until the EXT_TRIGGER_3 bit is set to 1. 1: Data writes to registers tied to EXT_TRIGGER_3 are not masked. Data writes go directly to the active registers.	1			



MIPI RFFE Specification

Table 16: Register Mapping, Table IV

Register Address	Register Name	Data Bits	Function	Description	Default	Broadcast_ID Support	Trigger Support	R/W
0x2E	EXT_TRIG	7	TRIGGER_10	0: No action. Data is held in shadow reg- isters.	0	Yes	No	R/W
				1: Data is transferred from shadow reg- isters to active registers for refisters tied to EXT_TRIGGER_10				MW
		6	TRIGGER_9	0: No action. Data is held in shadow reg- isters.	0			
				1: Data is transferred from shadow reg- isters to active registers for refisters tied to EXT_TRIGGER_9				
		5	TRIGGER_8	0: No action. Data is held in shadow reg- isters.	0			
				1: Data is transferred from shadow reg- isters to active registers for refisters tied to EXT_TRIGGER_8				
		4	TRIGGER_7	0: No action. Data is held in shadow reg- isters.	0			
		1: Data is transferred from shadow registers to active registers for refisters tied to EXT_TRIGGER_7 3 TRIGGER_6 0: No action. Data is held in shadow registers. 1: Data is transferred from shadow registers. 1: Data is transferred from shadow registers for refisters tied to EXT_TRIGGER_6	1: Data is transferred from shadow reg- isters to active registers for refisters tied to EXT_TRIGGER_7					
			0					
		2	TRIGGER_5	0: No action. Data is held in shadow reg- isters.	0			
			1: Data is transferred from shadow reg- isters to active registers for refisters tied to EXT_TRIGGER_5					
		1	TRIGGER_4	0: No action. Data is held in shadow reg- isters.	0			
				1: Data is transferred from shadow reg- isters to active registers for refisters tied to EXT_TRIGGER_4				
		0	TRIGGER_3	0: No action. Data is held in shadow reg- isters.	0			
				1: Data is transferred from shadow reg- isters to active registers for refisters tied to EXT_TRIGGER_3				



MIPI RFFE Specification

Table 17: USID_SEL Selection

Address	Symbol	Configuration	Ext. Condition at USID_SEL Port
USID_SEL6=0110	Addr ₆	default	ground
USID_SEL9=1001	Addr ₉	default	to V _{IO}



Figure 4: BGSC2341ML10 USID_SEL Pin Configuration

Table 18: Switch MIPI Control Combinations (truth table) ¹⁾

		REGISTER_0 :C-Tuner control register							
State	Mode	D7	D6	D5	D4	D3	D2	D1	DO
0	C _{tune} State 0	Х	Х	0	Х	X	0	0	0
1	C _{tune} State 1	Х	Х	0	Х	X	0	0	1
2	C _{tune} State 2	Х	Х	0	Х	X	0	1	0
3	C _{tune} State 3	Х	Х	0	Х	X	0	1	1
4	C _{tune} State 4	Х	Х	0	Х	X	1	0	0
5	C _{tune} State 5	Х	Х	0	Х	X	1	0	1
6	C _{tune} State 6	Х	Х	0	Х	X	1	1	0
7	C _{tune} State 7	Х	Х	0	Х	Х	1	1	1
8	SPDT ALL OFF	Х	Х	0	0	0	Х	Х	Х
9	SPDT RF SW1 ON	Х	Х	0	0	1	Х	X	Х
10	SPDT RF SW2 ON	Х	Х	0	1	0	Х	X	Х
11	SPDT RF SW1,SW2 ON	Х	Х	0	1	1	Х	Х	Х

 $^{1)}\mbox{measured}$ according to the measurement set-up of Fig. 2

Combination of any state here above mentioned in Table 15 can be programmed in one single MIPI sequence. As an example, programmation of RF1 ON RF2 ON C tuner in state 1 can be done in one MIPI data frame with register 0x1=0bxx011001.

BGSC2341ML10

RF Digitally Tunable Capacitor + SPDT Switch



Application Information

7 Application Information

Pin Configuration and Function



Figure 5: BGSC2341ML10 Pin Configuration (top view)

Pin No.	Name	Pin Type	Function
1	NC	-	Not Connected
2	RF3	I/O	Input/Output Tunable Capacitor Port
3	GND	I/O	Ground
4	SCLK	1	MIPI Control Signal SCLOCK(Default)
5	SDAT	I/O	MIPI Control Signal SDATA(Default)
6	VIO	1	MIPI/DC Voltage Supply
7	USID_SEL	1	USID_SEL hardware pin for USID selection (see Table.17)
8	RF2	I/O	Input/Output RF Switch 2
9	RF1	I/O	Input/Output RF Switch 1
10	RFC	I/O	Input/Output RF Common Port

Table 19: Pin Definition and Function of BGSC2341ML10 in Swap Configuration:USID=0111

Table 20: ESD robustness, System Level Test (SLT)

	Symbol	Values		Unit	Note / Test Condition		
		Min.	Тур.	Max.			
ESD SLT ¹⁾	V _{ESD_{SLT}}	-8 ²⁾	-	+8 2)	kV	RF vs system GND, with 27 nH shunt inductor	

¹⁾ IEC 61000-4-2 ($R = 330 \Omega$, C = 150 pF), contact discharge.

²⁾ For RFC path only.



Package Information

8 Package Information



Figure 6: TSLP-10-2 Package Outline (top, side and bottom views)





Package Information



Year	"Y"	Year	"Y"
2010	0	2020	0
2011	1	2021	1
2012	2	2022	2
2013	3	2023	3
2014	4	2024	4
2015	5	2025	5
2016	6	2026	6
2017	7	2027	7
2018	8	2028	8
2019	9	2029	9

Table 21: Year date code marking - digit "Y"

Table 22: Week date code marking - digit "W"

Week	"W"	Week	"W"	Week	"W"	Week	"W"	Week	"W"
1	А	12	Ν	23	4	34	h	45	v
2	В	13	Р	24	5	35	j	46	x
3	С	14	Q	25	6	36	k	47	у
4	D	15	R	26	7	37	l	48	z
5	E	16	S	27	а	38	n	49	8
6	F	17	Т	28	b	39	р	50	9
7	G	18	U	29	с	40	q	51	2
8	Н	19	V	30	d	41	r	52	3
9	J	20	W	31	e	42	s		
10	к	21	Y	32	f	43	t		
11	L	22	Z	33	g	44	u		



Package Information



Figure 8: Footprint Recommendation



Figure 9: TSLP-10-2 Carrier Tape



Revision History	
Page or Item	Subjects (major changes since previous revision)
Revision 2.3, 2021-09-19	
	4th version of the final datasheet
	with update in Table 4-6 (capacitance performance) and Table 18 (truth table)

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2021-09-19 Published by Infineon Technologies AG 81726 Munich, Germany

© 2021 Infineon Technologies AG. All Rights Reserved.

Do you have a question about any aspect of this document? Email: erratum@infineon.com

Document reference Doc_Number

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party. In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications. The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Infineon: BGSC2341ML10E6327XTSA1