

EasyPACK™ module with CoolSiC™ Trench MOSFET**Features**

- Electrical features
 - $V_{DS} = 1200\text{ V}$
 - $I_{DN} = 400\text{ A}$ / $I_{DRM} = 800\text{ A}$
 - Low switching losses
 - High current density
 - Low inductive design
- Mechanical features
 - PressFIT contact technology
 - Integrated NTC temperature sensor
 - Rugged mounting due to integrated mounting clamps

**Potential applications**

- High-frequency switching application
- Solar applications
- UPS systems
- DC/DC converter
- Servo drives

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068


Description

Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	MOSFET	3
3	Body diode	5
4	NTC-Thermistor	6
5	Characteristics diagrams	7
6	Circuit diagram	12
7	Package outlines	13
8	Module label code	14
	Revision history	15
	Disclaimer	16

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50 \text{ Hz}$, $t = 1 \text{ min}$	3.0	kV
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Creepage distance	d_{Creep}	terminal to heatsink	9.6	mm
Creepage distance	d_{Creep}	terminal to terminal	11.3	mm
Clearance	d_{Clear}	terminal to heatsink	9.2	mm
Clearance	d_{Clear}	terminal to terminal	10.0	mm
Comparative tracking index	CTI		> 400	
Relative thermal index (electrical)	RTI	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Stray inductance module	L_{SCE}			5		nH
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_H = 25^\circ\text{C}$, per switch		0.235		mΩ
Storage temperature	T_{stg}		-40		125	°C
Mounting torque for module mounting	M	- Mounting according to valid application note	M5, Screw	1.3	1.5	Nm
Weight	G			78		g

Note: The current under continuous operation is limited to 25 A rms per connector pin.

2 MOSFET

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Drain-source voltage	V_{DSS}	$T_{vj} = 25^\circ\text{C}$	1200	V
Implemented drain current	I_{DN}		400	A
Continuous DC drain current	I_{DDC}	$T_{vj} = 175^\circ\text{C}$, $V_{GS} = 18 \text{ V}$ $T_H = 75^\circ\text{C}$	400	A
Repetitive peak drain current	I_{DRM}	verified by design, t_p limited by T_{vjmax}	800	A
Gate-source voltage, max. transient voltage	V_{GS}	$D = 0.01$	-10/23	V

(table continues...)

Table 3 (continued) Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Gate-source voltage, max. static voltage	V_{GS}		-7/20	V

Table 4 Recommended values

Parameter	Symbol	Note or test condition	Values	Unit
On-state gate voltage	$V_{GS(on)}$		15...18	V
Off-state gate voltage	$V_{GS(off)}$		-5...0	V

Table 5 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source on-resistance	$R_{DS(on)}$	$I_D = 400\text{ A}$	$V_{GS} = 18\text{ V}, T_{vj} = 25\text{ }^{\circ}\text{C}$		1.44	2.27	mΩ
			$V_{GS} = 18\text{ V}, T_{vj} = 125\text{ }^{\circ}\text{C}$		2.33		
			$V_{GS} = 18\text{ V}, T_{vj} = 175\text{ }^{\circ}\text{C}$		3.09		
			$V_{GS} = 15\text{ V}, T_{vj} = 25\text{ }^{\circ}\text{C}$		1.71		
Gate threshold voltage	$V_{GS(th)}$	$I_D = 224\text{ mA}, V_{DS} = V_{GS}, T_{vj} = 25\text{ }^{\circ}\text{C}$, (tested after 1ms pulse at $V_{GS} = +20\text{ V}$)		3.45	4.3	5.15	V
Total gate charge	Q_G	$V_{DS} = 800\text{ V}, V_{GS} = -3/18\text{ V}$			1.6		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\text{ }^{\circ}\text{C}$			0.9		Ω
Input capacitance	C_{ISS}	$f = 100\text{ kHz}, V_{DS} = 800\text{ V}, V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		48.4		nF
Output capacitance	C_{OSS}	$f = 100\text{ kHz}, V_{DS} = 800\text{ V}, V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		2.4		nF
Reverse transfer capacitance	C_{rss}	$f = 100\text{ kHz}, V_{DS} = 800\text{ V}, V_{GS} = 0\text{ V}$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		0.158		nF
C_{OSS} stored energy	E_{OSS}	$V_{DS} = 800\text{ V}, V_{GS} = -3/18\text{ V}, T_{vj} = 25\text{ }^{\circ}\text{C}$			945		μJ
Drain-source leakage current	I_{DSS}	$V_{DS} = 1200\text{ V}, V_{GS} = -3\text{ V}$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		0.32	660	μA
Gate-source leakage current	I_{GSS}	$V_{DS} = 0\text{ V}, T_{vj} = 25\text{ }^{\circ}\text{C}$	$V_{GS} = 20\text{ V}$			400	nA
Turn-on delay time (inductive load)	$t_{d\text{ on}}$	$I_D = 400\text{ A}, R_{Gon} = 3.6\text{ }\Omega, V_{DS} = 600\text{ V}, V_{GS} = -3/18\text{ V}$	$T_{vj} = 25\text{ }^{\circ}\text{C}$		108		ns
			$T_{vj} = 125\text{ }^{\circ}\text{C}$		101		
			$T_{vj} = 175\text{ }^{\circ}\text{C}$		98.2		

(table continues...)

Table 5 (continued) **Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rise time (inductive load)	t_r	$I_D = 400\text{ A}$, $R_{Gon} = 3.6\ \Omega$, $V_{DS} = 600\text{ V}$, $V_{GS} = -3/18\text{ V}$	$T_{vj} = 25\text{ °C}$	137		ns
			$T_{vj} = 125\text{ °C}$	124		
			$T_{vj} = 175\text{ °C}$	124		
Turn-off delay time (inductive load)	$t_{d\ off}$	$I_D = 400\text{ A}$, $R_{Goff} = 1\ \Omega$, $V_{DS} = 600\text{ V}$, $V_{GS} = -3/18\text{ V}$	$T_{vj} = 25\text{ °C}$	136		ns
			$T_{vj} = 125\text{ °C}$	150		
			$T_{vj} = 175\text{ °C}$	156		
Fall time (inductive load)	t_f	$I_D = 400\text{ A}$, $R_{Goff} = 1\ \Omega$, $V_{DS} = 600\text{ V}$, $V_{GS} = -3/18\text{ V}$	$T_{vj} = 25\text{ °C}$	32.2		ns
			$T_{vj} = 125\text{ °C}$	33.7		
			$T_{vj} = 175\text{ °C}$	34.3		
Turn-on energy loss per pulse	E_{on}	$I_D = 400\text{ A}$, $V_{DS} = 600\text{ V}$, $L_\sigma = 18\text{ nH}$, $V_{GS} = -3/18\text{ V}$, $R_{Gon} = 3.6\ \Omega$, $di/dt = 8.7\text{ kA}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	17.7		mJ
			$T_{vj} = 125\text{ °C}$	17.9		
			$T_{vj} = 175\text{ °C}$	18.7		
Turn-off energy loss per pulse	E_{off}	$I_D = 400\text{ A}$, $V_{DS} = 600\text{ V}$, $L_\sigma = 18\text{ nH}$, $V_{GS} = -3/18\text{ V}$, $R_{Goff} = 1\ \Omega$, $dv/dt = 14\text{ kV}/\mu\text{s}$ ($T_{vj} = 175\text{ °C}$)	$T_{vj} = 25\text{ °C}$	2.83		mJ
			$T_{vj} = 125\text{ °C}$	3.28		
			$T_{vj} = 175\text{ °C}$	3.52		
Thermal resistance, junction to heat sink	R_{thJH}	per MOSFET		0.128		K/W
Temperature under switching conditions	$T_{vj\ op}$		-40		175	°C

Note: The selection of positive and negative gate-source voltages impacts losses and the long-term behavior of the MOSFET and body diode. The design guidelines described in Application Note AN 2018-09 and AN 2021-13 must be considered to ensure sound operation of the device over the planned lifetime.

$T_{vj,op} > 150\text{ °C}$ is allowed for operation at overload conditions for MOSFET and body diode. For detailed specifications, please refer to AN 2021-13.

3 Body diode

Table 6 **Maximum rated values**

Parameter	Symbol	Note or test condition		Values	Unit
DC body diode forward current	I_{SD}	$T_{vj} = 175\text{ °C}$, $V_{GS} = -3\text{ V}$	$T_H = 75\text{ °C}$	160	A

Table 7 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_{SD}	$I_{SD} = 400 \text{ A}$, $V_{GS} = -3 \text{ V}$	$T_{vj} = 25 \text{ °C}$	3.98	5.05	V
			$T_{vj} = 125 \text{ °C}$	3.75		
			$T_{vj} = 175 \text{ °C}$	3.65		

4 NTC-Thermistor

Table 8 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	$T_{NTC} = 25 \text{ °C}$		5		kΩ
Deviation of R_{100}	$\Delta R/R$	$T_{NTC} = 100 \text{ °C}$, $R_{100} = 493 \text{ Ω}$	-5		5	%
Power dissipation	P_{25}	$T_{NTC} = 25 \text{ °C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15 \text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15 \text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15 \text{ K}))]$		3433		K


Note: Specification according to the valid application note.

5 Characteristics diagrams

Output characteristic (typical), MOSFET

$I_D = f(V_{DS})$


$V_{GS} = 18\text{ V}$



Output characteristic (typical), MOSFET

$I_D = f(V_{DS})$


$V_{GS} = 15\text{ V}$



Drain source on-resistance (typical), MOSFET

$R_{DS(on)} = f(I_D)$


$V_{GS} = 18\text{ V}$



Drain source on-resistance (typical), MOSFET

$R_{DS(on)} = f(T_{vj})$


$I_D = 400\text{ A}, V_{GS} = 18\text{ V}$



5 Characteristics diagrams


Output characteristic field (typical), MOSFET

$I_D = f(V_{DS})$
 $T_{vj} = 175\text{ °C}$




Transfer characteristic (typical), MOSFET

$I_D = f(V_{GS})$
 $V_{DS} = 20\text{ V}$




Gate-source threshold voltage (typical), MOSFET

$V_{GS(th)} = f(T_{vj})$
 $V_{GS} = V_{DS}$



Gate charge characteristic (typical), MOSFET


$V_{GS} = f(Q_G)$
 $I_D = 400\text{ A}, T_{vj} = 25\text{ °C}$



Capacity characteristic (typical), MOSFET

$$C = f(V_{DS})$$


$f = 100 \text{ kHz}$, $T_{vj} = 25 \text{ °C}$, $V_{GS} = -3 \text{ V}$



Forward characteristic body diode (typical), MOSFET

$$I_{SD} = f(V_{SD})$$


$T_{vj} = 25 \text{ °C}$



Forward voltage of body diode (typical), MOSFET

$$V_{SD} = f(T_{vj})$$


$I_{SD} = 400 \text{ A}$



Switching losses (typical), MOSFET

$$E = f(I_D)$$


$R_{Goff} = 1 \text{ } \Omega$, $R_{Gon} = 3.6 \text{ } \Omega$, $V_{DS} = 600 \text{ V}$, $V_{GS} = -3/18 \text{ V}$



Switching losses (typical), MOSFET

$$E = f(R_G)$$


$V_{DS} = 600 \text{ V}$, $I_D = 400 \text{ A}$, $V_{GS} = -3/18 \text{ V}$



Switching times (typical), MOSFET

$$t = f(I_D)$$


$R_{Goff} = 1 \text{ } \Omega$, $R_{Gon} = 3.6 \text{ } \Omega$, $V_{DS} = 600 \text{ V}$, $T_{vj} = 175 \text{ } ^\circ\text{C}$, $V_{GS} = -3/18 \text{ V}$



Switching times (typical), MOSFET

$$t = f(R_G)$$


$V_{DS} = 600 \text{ V}$, $I_D = 400 \text{ A}$, $T_{vj} = 175 \text{ } ^\circ\text{C}$, $V_{GS} = -3/18 \text{ V}$



Current slope (typical), MOSFET

$$di/dt = f(R_G)$$


$V_{DS} = 600 \text{ V}$, $I_D = 400 \text{ A}$, $V_{GS} = -3/18 \text{ V}$



5 Characteristics diagrams


Voltage slope (typical), MOSFET

$dv/dt = f(R_G)$
 $V_{DS} = 600\text{ V}$, $I_D = 400\text{ A}$, $V_{GS} = -3/18\text{ V}$




Reverse bias safe operating area (RBSOA), MOSFET

$I_D = f(V_{DS})$
 $R_{Goff} = 1\text{ Ω}$, $T_{vj} = 175\text{ °C}$, $V_{GS} = -3/18\text{ V}$




Transient thermal impedance, MOSFET

$Z_{th} = f(t)$



Temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



6 **Circuit diagram**




Figure 1

Package outlines




Figure 2

8 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	<i>Content</i>	<i>Digit</i>	<i>Example</i>
	Module serial number	1 – 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 – 21	15
	Date code (production week)	22 – 23	30
Example			
			
71549142846550549911530		71549142846550549911530	

Figure 3

Revision history

Document revision	Date of release	Description of changes
0.10	2021-04-27	Target datasheet
1.00	2022-03-08	Final datasheet
1.10	2022-04-13	- Correction of switching times dimension. - Add of missing dv/dt and di/dt in table for dynamic parameters

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2022-04-13

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2022 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any
aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAV103-003

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[FF2MR12W3M1HB11BPSA1](#)