


HybridPACK™ Drive module with CoolSiC™ Automotive MOSFET

Features


- Electrical features
 - $V_{DS} = 1200\text{ V}$
 - $I_{D\text{ nom}} = 400\text{ A}$
 - New semiconductor material - Silicon Carbide
 - Low R_{DSon}
 - Low Switching Losses
 - Low Q_g and Cr_{ss}
 - Low Inductive Design $<10\text{ nH}$
 - $T_{vj\text{ op}} = 150\text{ }^{\circ}\text{C}$
- Mechanical features
 - 4.2 kV DC 1 sec Insulation
 - High Creepage and Clearance Distances
 - Compact design
 - High Power Density
 - Direct Cooled PinFin Base Plate
 - High Performance Si3N4 Ceramic
 - Guiding elements for PCB and cooler assembly
 - Integrated NTC temperature sensor
 - PressFIT Contact Technology
 - RoHS compliant
 - UL 94 V0 module frame



Potential applications

- Automotive Applications
- Hybrid Electrical Vehicles (H)EV
- Motor Drives
- Commercial Agriculture Vehicles

Description



Type	Package	Marking
FS03MR12A6MA1B	HybridPACK™ Drive Module	SP001720764

Table of contents

	Description	1
	Features	1
	Potential applications	1
	Table of contents	2
1	Package	3
2	MOSFET	3
3	Body diode	5
4	NTC-Thermistor	6
5	Characteristics diagrams	7
6	Circuit diagram	11
7	Package outlines	12
8	Module label code	13
	Revision history	14
	Disclaimer	15

1 Package

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 0$ Hz, $t = 1$ sec	4.2	kV
Material of module baseplate			Ni+Cu ¹⁾	
Internal isolation		basic insulation (class 1, IEC 61140)	Si3N4	
Creepage distance	d_{Creep}	terminal to heatsink	9.0	mm
Creepage distance	d_{Creep}	terminal to terminal	9.0	mm
Clearance	d_{Clear}	terminal to heatsink	4.5	mm
Clearance	d_{Clear}	terminal to terminal	4.5	mm
Comparative tracking index	CTI		> 200	

1) Ni plated Cu baseplate

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Pressure drop in cooling circuit	Δp	$\Delta V/\Delta t = 10 \text{ dm}^3/\text{min}$, 50% water/50% ethylenglycol, $T_F = 60^\circ\text{C}$		64 ¹⁾		mbar
Maximum pressure in cooling circuit	p	$T_{\text{baseplate}} < 40^\circ\text{C}$ (relative pressure)			2.5	bar
		$T_{\text{baseplate}} > 40^\circ\text{C}$ (relative pressure)			2.0	
Stray inductance module	L_{SCE}			8.5		nH
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_F = 25^\circ\text{C}$, per switch		0.75		mΩ
Storage temperature	T_{stg}		-40		125	°C
Mounting torque for modul mounting	M	Screw M4 baseplate to heatsink	1.8	2.0	2.2	Nm
Weight	G			720		g

1) Cooler design and flow direction according to application note AN-HPDPERF-ASSEMBLY.

2 MOSFET

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Drain-source voltage	V_{DSS}	$T_{vj} = 25^\circ\text{C}$	1200	V
DC drain current	$I_{D \text{ nom}}$	$V_{GS} = 15 \text{ V}$, $T_F = 60^\circ\text{C}$	400	A
Pulsed drain current	$I_{D \text{ pulse}}$	verified by design, t_p limited by $T_{vj \text{ max}}$	800	A
Gate-source voltage	V_{GSS}		-10/+20	V

Table 4 **Characteristic values**

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source on resistance	$R_{DS(on)}$	$I_D = 400 \text{ A}$, $V_{GS} = 15 \text{ V}$	$T_{vj} = 25 \text{ °C}$		2.75	3.70	mΩ
			$T_{vj} = 125 \text{ °C}$		4.00		
			$T_{vj} = 150 \text{ °C}$		4.55		
Gate threshold voltage	$V_{GS(th)}$	$I_D = 240 \text{ mA}$, $V_{GS} = V_{DS}$, (tested after 1 ms pulse at $V_{GS} = +20 \text{ V}$)	$T_{vj} = 25 \text{ °C}$	3.25	4.40	5.55	V
Total gate charge	Q_G	$V_{DS} = 600 \text{ V}$, $V_{GS} = -5/+15 \text{ V}$			1.32		μC
Internal gate resistor	R_{Gint}		$T_{vj} = 25 \text{ °C}$		0.23		Ω
Input capacitance	C_{iss}	$f = 1 \text{ MHz}$, $V_{DS} = 600 \text{ V}$, $V_{GS} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		42.6		nF
Output capacitance	C_{oss}	$f = 1 \text{ MHz}$, $V_{DS} = 600 \text{ V}$, $V_{GS} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		1.86		nF
Reverse transfer capacitance	C_{rss}	$f = 1 \text{ MHz}$, $V_{DS} = 600 \text{ V}$, $V_{GS} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		0.17		nF
C_{OSS} stored energy	E_{OSS}	$V_{DS} = 600 \text{ V}$, $V_{GS} = -5/+15 \text{ V}$	$T_{vj} = 25 \text{ °C}$		438		μJ
Drain-source leakage current	I_{DSX}	$V_{GS} = -5 \text{ V}$, $V_{DSS} = 1200 \text{ V}$	$T_{vj} = 25 \text{ °C}$			100	μA
Gate-source leakage current	I_{GSS}	$V_{GS} = 20 \text{ V}$, $V_{DS} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$			400	nA
Turn-on delay time, inductive load	$t_{d on}$	$I_D = 400 \text{ A}$, $R_{Gon} = 5.1 \text{ Ω}$, $V_{GS} = -5/+15 \text{ V}$, $V_{DS} = 600 \text{ V}$	$T_{vj} = 25 \text{ °C}$		77		ns
			$T_{vj} = 125 \text{ °C}$		62		
			$T_{vj} = 150 \text{ °C}$		59		
Rise time (inductive load)	t_r	$I_D = 400 \text{ A}$, $R_{Gon} = 5.1 \text{ Ω}$, $V_{GS} = -5/+15 \text{ V}$, $V_{DS} = 600 \text{ V}$	$T_{vj} = 25 \text{ °C}$		79		ns
			$T_{vj} = 125 \text{ °C}$		70		
			$T_{vj} = 150 \text{ °C}$		69		
Turn-off delay time, inductive load	$t_{d off}$	$I_D = 400 \text{ A}$, $R_{Goff} = 5.1 \text{ Ω}$, $V_{GS} = -5/+15 \text{ V}$, $V_{DS} = 600 \text{ V}$	$T_{vj} = 25 \text{ °C}$		263		ns
			$T_{vj} = 125 \text{ °C}$		287		
			$T_{vj} = 150 \text{ °C}$		294		
Fall time (inductive load)	t_f	$I_D = 400 \text{ A}$, $R_{Goff} = 5.1 \text{ Ω}$, $V_{GS} = -5/+15 \text{ V}$, $V_{DS} = 600 \text{ V}$	$T_{vj} = 25 \text{ °C}$		64		ns
			$T_{vj} = 125 \text{ °C}$		64		
			$T_{vj} = 150 \text{ °C}$		65		
Turn-on energy loss per pulse	E_{on}	$I_D = 400 \text{ A}$, $R_{Gon} = 5.1 \text{ Ω}$, $V_{GS} = -5/+15 \text{ V}$, $V_{DS} = 600 \text{ V}$, $L_\sigma = 20 \text{ nH}$	$T_{vj} = 25 \text{ °C}$, $di/dt = 4 \text{ kA/μs}$		19.48		mJ
			$T_{vj} = 125 \text{ °C}$, $di/dt = 4.6 \text{ kA/μs}$		19.85		
			$T_{vj} = 150 \text{ °C}$, $di/dt = 4.6 \text{ kA/μs}$		20.16		

Table 4 Characteristic values (continued)

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Turn-off energy loss per pulse	E_{off}	$I_D = 400\text{ A}$, $R_{Goff} = 5.1\ \Omega$, $V_{GS} = -5/+15\text{ V}$, $V_{DS} = 600\text{ V}$, $L_\sigma = 20\text{ nH}$	$T_{vj} = 25\text{ °C}$, $du/dt = 7.3\text{ kV}/\mu\text{s}$	17.61		mJ
			$T_{vj} = 125\text{ °C}$, $du/dt = 7.2\text{ kV}/\mu\text{s}$	17.95		
			$T_{vj} = 150\text{ °C}$, $du/dt = 7.1\text{ kV}/\mu\text{s}$	18.21		
Short circuit data	I_{SC}	$V_{GS} = -5/+15\text{ V}$, $V_{DD} = 800\text{ V}$, $V_{DSmax} = V_{DSS} - L_{SDS} \cdot di/dt$, $R_G = 5.1\ \Omega$	$t_{SC} = 3\ \mu\text{s}$, $T_{vj} = 25\text{ °C}$	5300		A
			$t_{SC} = 3\ \mu\text{s}$, $T_{vj} = 150\text{ °C}$	4800		
Thermal resistance, junction to cooling fluid	R_{thJF}	per MOSFET, $\Delta V/\Delta t = 10.0\text{ dm}^3/\text{min}$; fluid = 50% water/50% ethylenglycol, $T_F = 60\text{ °C}$		0.1	0.108 ¹⁾	K/W
Temperature under switching conditions	$T_{vj\text{ op}}$		-40		150	°C

1) EoL criteria see AQG324, verified by characterization with 4.5 sigma. Cooler design and flow direction according to application note AN-HPDPERF-ASSEMBLY

3 Body diode

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
DC body diode forward current	I_{SD}	$T_{vjmax} = 175\text{ °C}$, $V_{GS} = -5\text{ V}$ $T_F = 60\text{ °C}$	210	A
Pulsed body diode current	$I_{SD\text{ pulse}}$	verified by design, t_p limited by T_{vjmax}	800	A

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Forward voltage	V_{DSR}	$I_{SD} = 400\text{ A}$, $V_{GS} = -5\text{ V}$	$T_{vj} = 25\text{ °C}$	4.42	6.15	V
			$T_{vj} = 125\text{ °C}$	4.22		
			$T_{vj} = 150\text{ °C}$	4.16		
Peak reverse recovery current	I_{rrm}	$I_{SD} = 400\text{ A}$, $V_r = 600\text{ V}$, $V_{GS} = -5\text{ V}$	$T_{vj} = 25\text{ °C}$	165		A
			$T_{vj} = 125\text{ °C}$	287		
			$T_{vj} = 150\text{ °C}$	309		

Table 6 Characteristic values (continued)

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Recovered charge	Q_{rr}	$I_{SD} = 400 \text{ A}$, $V_r = 600 \text{ V}$, $V_{GS} = -5 \text{ V}$	$T_{vj} = 25 \text{ °C}$	11.20		μC
			$T_{vj} = 125 \text{ °C}$	18.10		
			$T_{vj} = 150 \text{ °C}$	19.30		
Reverse recovery energy	E_{rec}	$I_{SD} = 400 \text{ A}$, $V_r = 600 \text{ V}$, $V_{GS} = -5 \text{ V}$	$T_{vj} = 25 \text{ °C}$, $-di/dt = 5.9 \text{ kA}/\mu\text{s}$	1.4		mJ
			$T_{vj} = 125 \text{ °C}$, $-di/dt = 6.9 \text{ kA}/\mu\text{s}$	4.1		
			$T_{vj} = 150 \text{ °C}$, $-di/dt = 6.9 \text{ kA}/\mu\text{s}$	4.7		

4 NTC-Thermistor

Table 7 Characteristic values


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Rated resistance	R_{25}	$T_{NTC} = 25 \text{ °C}$		5		k Ω
Deviation of R_{100}	$\Delta R/R$	$T_{NTC} = 25 \text{ °C}$, $R_{100} = 493 \text{ }\Omega$	-5		5	%
Power dissipation	P_{25}	$T_{NTC} = 25 \text{ °C}$			20	mW
B-value	$B_{25/50}$	$R_2 = R_{25} \exp[B_{25/50}(1/T_2 - 1/(298,15 \text{ K}))]$		3375		K
B-value	$B_{25/80}$	$R_2 = R_{25} \exp[B_{25/80}(1/T_2 - 1/(298,15 \text{ K}))]$		3411		K
B-value	$B_{25/100}$	$R_2 = R_{25} \exp[B_{25/100}(1/T_2 - 1/(298,15 \text{ K}))]$		3433		K

5 Characteristics diagrams

pressure drop in cooling circuit,

$\Delta p = f(\Delta V/\Delta t)$


$T_F = 60\text{ }^{\circ}\text{C}$, fluid = 50% water/50% ethylenglycol



output characteristic (typical), MOSFET

$I_D = f(V_{DS})$


$V_{GS} = 15\text{ V}$



output characteristic (typical), MOSFET

$I_D = f(V_{DS})$


$T_{vj} = 25\text{ }^{\circ}\text{C}$



transfer characteristic (typical), MOSFET

$I_D = f(V_{GS})$


$V_{DS} = 20\text{ V}$



5 Characteristics diagrams


Drain source on-resistance (typical), MOSFET

$R_{DS(on)} = f(T_{vj})$
 $I_D = 400\text{ A}$, $V_{GS} = 15\text{ V}$




drain source on-resistance (typical), MOSFET

$R_{DS(on)} = f(I_D)$
 $V_{GS} = 15\text{ V}$




capacity characteristic (typical), MOSFET

$C = f(V_{DS})$
 $f = 1\text{ MHz}$, $V_{GS} = 0.0\text{ V}$, $T_{vj} = 25\text{ °C}$



switching losses (typical), MOSFET


$E = f(R_G)$
 $I_D = 400\text{ A}$, $V_{DS} = 600\text{ V}$, $V_{GS} = -5.0/15.0\text{ V}$



5 Characteristics diagrams


switching losses (typical), MOSFET

$E = f(I_D)$
 $V_{DS} = 600\text{ V}$, $R_{Goff} = 5.1\ \Omega$, $R_{Gon} = 5.1\ \Omega$, $V_{GS} = -5.0/15.0\text{ V}$




thermal impedance , MOSFET

$R_{thJF} = f(dv/dt)$
fluid = 50% water/50% ethylenglycol , $T_F = 60\text{ °C}$




transient thermal impedance , MOSFET

$Z_{th} = f(t)$
 $\Delta V/\Delta t = 10\text{ dm}^3/\text{min}$, fluid = 50% water/50% ethylenglycol , $T_F = 60\text{ °C}$



forward characteristic body diode (typical), MOSFET


$I_{SD} = f(V_{SD})$
 $T_{vj} = 25\text{ °C}$



5 Characteristics diagrams


Switching losses body diode (typical), MOSFET

$E_{rec} = f(I_{SD})$
 $V_r = 600\text{ V}$, $R_{Gon} = 5.1\ \Omega$, $V_{GS} = -5.0/15.0\text{ V}$




Switching losses body diode (typical), MOSFET

$E_{rec} = f(R_G)$
 $V_r = 600\text{ V}$, $I_{SD} = 400\text{ A}$, $V_{GS} = -5.0/15.0\text{ V}$




Reverse bias safe operating area (RBSOA), MOSFET

$I_D = f(V_{DS})$
 $R_{Goff} = 5.1\ \Omega$, $V_{GS} = +15\text{ V}/-5\text{ V}$, $T_{vj} = 150\text{ °C}$



temperature characteristic (typical), NTC-Thermistor

$R = f(T_{NTC})$



6 Circuit diagram




Figure 2

7 Package outlines

7 Package outlines




Figure 3

8 Module label code

Module label code				
Code format	Data Matrix		Barcode Code128	
Encoding	ASCII text		Code Set A	
Symbol size	16x16		23 digits	
Standard	IEC24720 and IEC16022		IEC8859-1	
Code content	<i>Content</i> Module serial number Module material number Production order number Date code (production year) Date code (production week)	<i>Digit</i> 1 – 5 6 - 11 12 - 19 20 – 21 22 – 23		<i>Example</i> 71549 142846 55054991 15 30
Example	  71549142846550549911530 71549142846550549911530			


Packing label code				
Code format	Barcode Code128			
Encoding	Code Set A			
Symbol size	34 digits			
Standard	IEC8859-1			
Code content	<i>Content</i> Module serial number Module material number Production order number Date code (production year) Date code (production week)	<i>Identifier</i> X 1T S 9D Q	<i>Digit</i> 2 – 9 12 – 19 21 – 25 28 – 31 33 – 34	<i>Example</i> 95056609 2X0003E0 754389 1139 15
Example	 X950566091T2X0003E0S754389D1139Q15			

Figure 4

Revision history

Revision history

Revision	Date of release	Description of changes
v1.0	2017-11-06	Target datasheet
v1.1	2018-11-28	Target datasheet
-	-	Datasheet migrated to new system:" • Layout changed • Revision number scheme changed: 0.xy = Target/Preliminary; 1.xy = Final
1.00	2021-03-23	Final datasheet

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2021-03-23

Published by

**Infineon Technologies AG
81726 Munich, Germany**

**© 2021 Infineon Technologies AG
All Rights Reserved.**

**Do you have a question about any
aspect of this document?**

Email: erratum@infineon.com

**Document reference
IFX-**

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[FS03MR12A6MA1BBPSA1](#)