

## MAX14934–MAX14936

## Four-Channel, 5kV<sub>RMS</sub> Digital Isolators

### General Description

The MAX14934–MAX14936 are a family of four-channel, 5kV<sub>RMS</sub> digital isolators utilizing Maxim's proprietary process technology. For applications requiring 2.75kV<sub>RMS</sub> of isolation, see the MAX14930–MAX14932. The MAX14934–MAX14936 family transfers digital signals between circuits with different power domains at ambient temperatures up to +125°C.

The MAX14934–MAX14936 family offers all three possible unidirectional channel configurations to accommodate any four-channel design, including SPI, RS-232, RS-485, and large digital IO modules. For applications requiring bidirectional channels, such as I<sup>2</sup>C, refer to the MAX14937.

Devices are available with data rates from DC up to 1Mbps, 25Mbps, or 150Mbps. Each device is also available in either a default high or default low configuration. The default is the state an output goes to when its input is unpowered. See the [Ordering Information/Selector Guide](#) for the suffixes associated with each option.

Independent 1.71V to 5.5V supplies on each side of the isolator also make the devices suitable for use as level translators.

The MAX14934–MAX14936 are available in a 16-pin wide body (10.3mm x 7.5mm) SOIC package. All devices are rated for operation at ambient temperatures of -40°C to +125°C.

[Ordering Information/Selector Guide](#) appears at end of data sheet.

### Benefits and Features

- Robust Galvanic Isolation of Digital Signals
  - Withstands 5kV<sub>RMS</sub> for 60s (V<sub>ISO</sub>)
  - Continuously Withstands 848V<sub>RMS</sub> (V<sub>IOWM</sub>)
  - 1200V<sub>p</sub> Repetitive Peak Voltage (V<sub>IORM</sub>)
  - Withstands ±10kV Surge per IEC 61000-4-5
- Interfaces Directly with Most Micros and FPGAs
  - Accepts 1.71V to 5.5V Supplies
- Many Options Support Broad Applications
  - 3 Data Rates (1Mbps, 25Mbps, 150Mbps)
  - 3 Channel Direction Configuration
  - 2 Output Default States (High or Low)
- Low Power Consumption at High Data Rates
  - At 1.8V:
    - 2.5mA per Channel Typical at 1Mbps
    - 5.25mA per Channel Typical at 100Mbps
  - At 3.3V:
    - 2.6mA per Channel Typical at 1Mbps
    - 7.1mA per Channel Typical at 100Mbps

### Safety Regulatory Approvals


(see [Safety Regulatory Approvals](#))

- UL According to UL1577
- cUL According to CSA Bulletin 5A
- VDE 0884-10

### Applications

- Fieldbus Communications for Industrial Automation
- Isolated SPI, RS-232, RS-485/RS-422
- General Multichannel Isolation Applications
- Battery Management
- Medical Systems

### Functional Diagram



## Absolute Maximum Ratings

$V_{DDA}$  to  $GNDA$ ,  $V_{DDB}$  to  $GNDB$  ..... -0.3V to +6V  
 $INA_{-}$ ,  $ENA$  to  $GNDA$  ..... -0.3V to +6V  
 $INB_{-}$ ,  $ENB$  to  $GNDB$  ..... -0.3V to +6V  
 $OUTA_{-}$  to  $GNDA$  ..... -0.3V to ( $V_{DDA} + 0.3V$ )  
 $OUTB_{-}$  to  $GNDB$  ..... -0.3V to ( $V_{DDB} + 0.3V$ )  
 Short-Circuit Duration  
     ( $OUTA_{-}$  to  $GNDA$ ,  $OUTB_{-}$  to  $GNDB$ ) ..... Continuous

Continuous Power Dissipation ( $T_A = +70^{\circ}C$ )  
     Wide SOIC (derate 14.1mW/ $^{\circ}C$  above  $+70^{\circ}C$ ) ..... 1126.8mW  
 Operating Temperature Range .....  $-40^{\circ}C$  to  $+125^{\circ}C$   
 Maximum Junction Temperature .....  $+150^{\circ}C$   
 Storage Temperature Range .....  $-65^{\circ}C$  to  $+150^{\circ}C$   
 Lead Temperature (soldering, 10s) .....  $+300^{\circ}C$   
 Soldering Temperature (reflow) .....  $+260^{\circ}C$

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

## Package Thermal Characteristics (Note 1)

Wide SOIC

Junction-to-Ambient Thermal Resistance ( $\theta_{JA}$ ) .....  $71^{\circ}C/W$

Junction-to-Case Thermal Resistance ( $\theta_{JC}$ ) .....  $23^{\circ}C/W$

**Note 1:** Package thermal resistances were obtained using the method described in JEDEC specification JESD51-7, using a four-layer board. For detailed information on package thermal considerations, refer to [www.maximintegrated.com/thermal-tutorial](http://www.maximintegrated.com/thermal-tutorial).

## DC Electrical Characteristics

( $V_{DDA} - V_{GNDA} = +1.71V$  to  $+5.5V$ ,  $V_{DDB} - V_{GNDB} = +1.71V$  to  $+5.5V$ ,  $C_L = 15pF$ ,  $T_A = -40^{\circ}C$  to  $+125^{\circ}C$ , unless otherwise noted. Typical values are at  $V_{DDA} - V_{GNDA} = +3.3V$ ,  $V_{DDB} - V_{GNDB} = +3.3V$ ,  $V_{GNDA} = V_{GNDB}$ ,  $T_A = +25^{\circ}C$ , unless otherwise noted.) (Note 2)

| PARAMETER                                 | SYMBOL                 | CONDITIONS          | MIN  | TYP  | MAX  | UNITS |
|-------------------------------------------|------------------------|---------------------|------|------|------|-------|
| <b>POWER SUPPLY</b>                       |                        |                     |      |      |      |       |
| Operating Supply Voltage                  | $V_{DDA}$              | Relative to $GNDA$  | 1.71 |      | 5.5  | V     |
|                                           | $V_{DDB}$              | Relative to $GNDB$  | 1.71 |      | 5.5  | V     |
| Undervoltage Lockout Threshold            | $V_{UVLO_{-}}$         | $V_{DD_{-}}$ rising | 1.45 | 1.58 | 1.71 | V     |
| Undervoltage Lockout Threshold Hysteresis | $V_{UVLO_{-}}$<br>HYST |                     |      | 50   |      | mV    |

**DC Electrical Characteristics (continued)**

( $V_{DDA} - V_{GNDA} = +1.71V$  to  $+5.5V$ ,  $V_{DDB} - V_{GNDB} = +1.71V$  to  $+5.5V$ ,  $C_L = 15pF$ ,  $T_A = -40^{\circ}C$  to  $+125^{\circ}C$ , unless otherwise noted. Typical values are at  $V_{DDA} - V_{GNDA} = +3.3V$ ,  $V_{DDB} - V_{GNDB} = +3.3V$ ,  $V_{GNDA} = V_{GNDB}$ ,  $T_A = +25^{\circ}C$ , unless otherwise noted.) (Note 2)

| PARAMETER                  | SYMBOL    | CONDITIONS                   |                  | MIN | TYP  | MAX  | UNITS |
|----------------------------|-----------|------------------------------|------------------|-----|------|------|-------|
| Supply Current (MAX14934_) | $I_{DDA}$ | 500kHz square wave           | $V_{DDA} = 5V$   |     | 1.2  | 1.9  | mA    |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 1.2  | 1.9  |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 1.2  | 1.9  |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 1.1  | 1.9  |       |
|                            |           | 12.5MHz square wave (Note 3) | $V_{DDA} = 5V$   |     | 2.1  | 2.7  |       |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 2    | 2.7  |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 2    | 2.7  |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 2    | 2.6  |       |
|                            |           | 50MHz square wave (Note 3)   | $V_{DDA} = 5V$   |     | 5    | 6.6  |       |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 4.6  | 6.1  |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 4.5  | 6.0  |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 4.5  | 6.0  |       |
|                            | $I_{DDB}$ | 500kHz square wave           | $V_{DDB} = 5V$   |     | 8.1  | 11.2 |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 7.9  | 11.1 |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 7.9  | 11.0 |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 7.7  | 10.8 |       |
|                            |           | 12.5MHz square wave (Note 3) | $V_{DDB} = 5V$   |     | 12.8 | 15.9 |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 11.1 | 14.2 |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 10.2 | 13.4 |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 9.4  | 12.4 |       |
|                            |           | 50MHz square wave (Note 3)   | $V_{DDB} = 5V$   |     | 27.2 | 35.4 |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 21.7 | 27.8 |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 17.6 | 23.0 |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 14.4 | 18.9 |       |

**DC Electrical Characteristics (continued)**

( $V_{DDA} - V_{GNDA} = +1.71V$  to  $+5.5V$ ,  $V_{DDB} - V_{GNDB} = +1.71V$  to  $+5.5V$ ,  $C_L = 15pF$ ,  $T_A = -40^{\circ}C$  to  $+125^{\circ}C$ , unless otherwise noted. Typical values are at  $V_{DDA} - V_{GNDA} = +3.3V$ ,  $V_{DDB} - V_{GNDB} = +3.3V$ ,  $V_{GNDA} = V_{GNDB}$ ,  $T_A = +25^{\circ}C$ , unless otherwise noted.) (Note 2)

| PARAMETER                  | SYMBOL    | CONDITIONS                   |                  | MIN | TYP  | MAX  | UNITS |
|----------------------------|-----------|------------------------------|------------------|-----|------|------|-------|
| Supply Current (MAX14935_) | $I_{DDA}$ | 500kHz square wave           | $V_{DDA} = 5V$   |     | 3.4  | 5.3  | mA    |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 3.3  | 5.3  |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 3.3  | 5.3  |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 3.2  | 5.1  |       |
|                            |           | 12.5MHz square wave (Note 3) | $V_{DDA} = 5V$   |     | 5.6  | 7.1  |       |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 5    | 6.6  |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 4.7  | 6.4  |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 4.5  | 6.1  |       |
|                            |           | 50MHz square wave (Note 3)   | $V_{DDA} = 5V$   |     | 12.4 | 16.0 |       |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 10.1 | 13.0 |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 9.1  | 11.6 |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 8.2  | 10.4 |       |
|                            | $I_{DDB}$ | 500kHz square wave           | $V_{DDB} = 5V$   |     | 6.5  | 9.2  |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 6.4  | 9.1  |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 6.3  | 9.1  |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 6.2  | 8.9  |       |
|                            |           | 12.5MHz square wave (Note 3) | $V_{DDB} = 5V$   |     | 10.3 | 12.8 |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 8.9  | 11.6 |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 8.2  | 11.0 |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 7.6  | 10.3 |       |
|                            |           | 50MHz square wave (Note 3)   | $V_{DDB} = 5V$   |     | 22.7 | 29.1 |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 17.7 | 23.0 |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 14.7 | 19.4 |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 11.9 | 15.9 |       |

**DC Electrical Characteristics (continued)**

( $V_{DDA} - V_{GNDA} = +1.71V$  to  $+5.5V$ ,  $V_{DDB} - V_{GNDB} = +1.71V$  to  $+5.5V$ ,  $C_L = 15pF$ ,  $T_A = -40^{\circ}C$  to  $+125^{\circ}C$ , unless otherwise noted. Typical values are at  $V_{DDA} - V_{GNDA} = +3.3V$ ,  $V_{DDB} - V_{GNDB} = +3.3V$ ,  $V_{GNDA} = V_{GNDB}$ ,  $T_A = +25^{\circ}C$ , unless otherwise noted.) (Note 2)

| PARAMETER                  | SYMBOL    | CONDITIONS                   |                  | MIN | TYP  | MAX  | UNITS |
|----------------------------|-----------|------------------------------|------------------|-----|------|------|-------|
| Supply Current (MAX14936_) | $I_{DDA}$ | 500kHz square wave           | $V_{DDA} = 5V$   |     | 5.2  | 7.2  | mA    |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 5.2  | 7.2  |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 5.2  | 7.2  |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 5    | 7.0  |       |
|                            |           | 12.5MHz square wave (Note 3) | $V_{DDA} = 5V$   |     | 8.2  | 10.0 |       |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 7.2  | 9.1  |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 6.7  | 8.7  |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 6.3  | 8.2  |       |
|                            |           | 50MHz square wave (Note 3)   | $V_{DDA} = 5V$   |     | 18   | 23.3 |       |
|                            |           |                              | $V_{DDA} = 3.3V$ |     | 14.2 | 18.4 |       |
|                            |           |                              | $V_{DDA} = 2.5V$ |     | 12.3 | 16.1 |       |
|                            |           |                              | $V_{DDA} = 1.8V$ |     | 10.5 | 13.6 |       |
|                            | $I_{DDB}$ | 500kHz square wave           | $V_{DDB} = 5V$   |     | 5.2  | 7.2  |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 5.2  | 7.2  |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 5.2  | 7.2  |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 5    | 7.0  |       |
|                            |           | 12.5MHz square wave (Note 3) | $V_{DDB} = 5V$   |     | 8.2  | 10.0 |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 7.2  | 9.1  |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 6.7  | 8.7  |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 6.3  | 8.2  |       |
|                            |           | 50MHz square wave (Note 3)   | $V_{DDB} = 5V$   |     | 18   | 23.3 |       |
|                            |           |                              | $V_{DDB} = 3.3V$ |     | 14.2 | 18.4 |       |
|                            |           |                              | $V_{DDB} = 2.5V$ |     | 12.3 | 16.1 |       |
|                            |           |                              | $V_{DDB} = 1.8V$ |     | 10.5 | 13.6 |       |

**DC Electrical Characteristics (continued)**

(V<sub>DDA</sub> - V<sub>GNDA</sub> = +1.71V to +5.5V, V<sub>DDB</sub> - V<sub>GNDB</sub> = +1.71V to +5.5V, C<sub>L</sub> = 15pF, T<sub>A</sub> = -40°C to +125°C, unless otherwise noted. Typical values are at V<sub>DDA</sub> - V<sub>GNDA</sub> = +3.3V, V<sub>DDB</sub> - V<sub>GNDB</sub> = +3.3V, V<sub>GNDA</sub> = V<sub>GNDB</sub>, T<sub>A</sub> = +25°C, unless otherwise noted.) (Note 2)

| PARAMETER                | SYMBOL           | CONDITIONS                                                                            |                                  | MIN                    | TYP  | MAX | UNITS |
|--------------------------|------------------|---------------------------------------------------------------------------------------|----------------------------------|------------------------|------|-----|-------|
| LOGIC INPUTS AND OUTPUTS |                  |                                                                                       |                                  |                        |      |     |       |
| Input High Voltage       | V <sub>IH</sub>  | ENA, INA_ relative to GNDA                                                            |                                  | 0.7 x V <sub>DDA</sub> |      | V   |       |
|                          |                  | ENB, INB_ relative to GNDB                                                            |                                  | 0.7 x V <sub>DDB</sub> |      |     |       |
| Input Low Voltage        | V <sub>IL</sub>  | ENA, INA_ relative to GNDA                                                            | 1.71V ≤ V <sub>DDA</sub> ≤ 1.89V | 0.6                    |      | V   |       |
|                          |                  |                                                                                       | 2.25V ≤ V <sub>DDA</sub> ≤ 5.5V  | 0.8                    |      |     |       |
|                          |                  | ENB, INB_ relative to GNDB                                                            | 1.71V ≤ V <sub>DDB</sub> ≤ 1.89V | 0.6                    |      |     |       |
|                          |                  |                                                                                       | 2.25V ≤ V <sub>DDB</sub> ≤ 5.5V  | 0.8                    |      |     |       |
| Input Hysteresis         | V <sub>HYS</sub> | V <sub>INA_</sub> relative to GNDA or V <sub>INB_</sub> relative to GNDB              | MAX1493_A/D                      | 410                    |      | mV  |       |
|                          |                  |                                                                                       | MAX1493_B/E                      | 410                    |      |     |       |
|                          |                  |                                                                                       | MAX1493_C/F                      | 80                     |      |     |       |
| Input Leakage Current    | I <sub>L</sub>   | V <sub>INA_</sub> = 0 or V <sub>DDA</sub> , V <sub>INB_</sub> = 0 or V <sub>DDB</sub> |                                  | -1                     |      | +1  | μA    |
| Input Capacitance        | C <sub>IN</sub>  | INA_, INB_, f = 1MHz                                                                  |                                  | 2                      |      |     | pF    |
| EN_ Pullup Current       | I <sub>PU</sub>  |                                                                                       |                                  | -4                     | -2.3 | -1  | μA    |
| Output Voltage High      | V <sub>OH</sub>  | V <sub>OUTA_</sub> relative to GNDA, I <sub>OUTA_</sub> = -4mA (Note 4)               |                                  | V <sub>DDA</sub> - 0.4 |      | V   |       |
|                          |                  | V <sub>OUTB_</sub> relative to GNDB, I <sub>OUTB_</sub> = -4mA (Note 4)               |                                  | V <sub>DDB</sub> - 0.4 |      |     |       |
| Output Voltage Low       | V <sub>OL</sub>  | V <sub>OUTA_</sub> relative to GNDA, I <sub>OUTA_</sub> = 4mA (Note 4)                |                                  | 0.4                    |      | V   |       |
|                          |                  | V <sub>OUTB_</sub> relative to GNDB, I <sub>OUTB_</sub> = 4mA (Note 4)                |                                  | 0.4                    |      |     |       |

### Dynamic Electrical Characteristics (MAX1493\_A/D)

( $V_{DDA} - V_{GNDA} = +1.71V$  to  $+5.5V$ ,  $V_{DDB} - V_{GNDB} = +1.71V$  to  $+5.5V$ ,  $C_L = 15pF$ ,  $T_A = -40^{\circ}C$  to  $+125^{\circ}C$ , unless otherwise noted. Typical values are at  $V_{DDA} - V_{GNDA} = +3.3V$ ,  $V_{DDB} - V_{GNDB} = +3.3V$ ,  $V_{GNDA} = V_{GNDB}$ ,  $T_A = +25^{\circ}C$ , unless otherwise noted.) (Notes 2, 3)

| PARAMETER                                                     | SYMBOL             | CONDITIONS                                                | MIN                                                           | TYP  | MAX  | UNITS       |
|---------------------------------------------------------------|--------------------|-----------------------------------------------------------|---------------------------------------------------------------|------|------|-------------|
| <b>INPUT AND OUTPUT CHANNELS</b>                              |                    |                                                           |                                                               |      |      |             |
| Common-Mode Transient Immunity                                | CMTI               | IN__ = GND_ or VDD_ (Note 5)                              |                                                               | 25   |      | kV/ $\mu$ s |
| Maximum Data Rate                                             | DR <sub>MAX</sub>  |                                                           | 1                                                             |      |      | Mbps        |
| Minimum Pulse Width                                           | PW <sub>MIN</sub>  | INA_ to OUTB_, INB_ to OUTA_                              |                                                               |      | 1    | $\mu$ s     |
| Glitch Rejection                                              |                    | INA_ to OUTB_, INB_ to OUTA_                              |                                                               | 32   |      | ns          |
| Propagation Delay (Figure 1)                                  | t <sub>PLH</sub>   | INA_ to OUTB_,<br>INB_ to OUTA_,<br>C <sub>L</sub> = 15pF | 4.5V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 5.5V   | 38.2 | 54.1 | ns          |
|                                                               |                    |                                                           | 3.0V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 3.6V   | 38.7 | 54.6 |             |
|                                                               |                    |                                                           | 2.25V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 2.75V | 39.7 | 55.6 |             |
|                                                               |                    |                                                           | 1.71V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 1.89V | 42.9 | 58.4 |             |
|                                                               | t <sub>PHL</sub>   | INA_ to OUTB_,<br>INB_ to OUTA_,<br>C <sub>L</sub> = 15pF | 4.5V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 5.5V   | 38.6 | 55.3 |             |
|                                                               |                    |                                                           | 3.0V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 3.6V   | 38.9 | 55.6 |             |
|                                                               |                    |                                                           | 2.25V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 2.75V | 39.8 | 56.1 |             |
|                                                               |                    |                                                           | 1.71V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 1.89V | 42.3 | 60.2 |             |
| Pulse-Width Distortion                                        | PWD                | t <sub>PLH</sub> - t <sub>PHL</sub>                       | 4.5V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 5.5V   | 0.4  | 4.5  | ns          |
|                                                               |                    |                                                           | 3.0V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 3.6V   | 0.2  | 4.3  |             |
|                                                               |                    |                                                           | 2.25V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 2.75V | 0.1  | 3.9  |             |
|                                                               |                    |                                                           | 1.71V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 1.89V | 0.6  | 4.7  |             |
| Propagation Delay Skew<br>Part-to-Part (Same Channel)         | t <sub>SPLH</sub>  |                                                           | 4.5V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 5.5V   |      | 26.6 | ns          |
|                                                               |                    |                                                           | 3.0V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 3.6V   |      | 26.6 |             |
|                                                               |                    |                                                           | 2.25V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 2.75V |      | 26.6 |             |
|                                                               |                    |                                                           | 1.71V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 1.89V |      | 26.9 |             |
|                                                               | t <sub>SPHL</sub>  |                                                           | 4.5V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 5.5V   |      | 27.9 |             |
|                                                               |                    |                                                           | 3.0V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 3.6V   |      | 27.7 |             |
|                                                               |                    |                                                           | 2.25V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 2.75V |      | 27.6 |             |
|                                                               |                    |                                                           | 1.71V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 1.89V |      | 29.7 |             |
| Propagation Delay Skew<br>Channel-to-Channel (Same Direction) | t <sub>SCSLH</sub> |                                                           | 4.5V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 5.5V   |      | 6.7  | ns          |
|                                                               |                    |                                                           | 3.0V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 3.6V   |      | 6.7  |             |
|                                                               |                    |                                                           | 2.25V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 2.75V |      | 6.7  |             |
|                                                               |                    |                                                           | 1.71V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 1.89V |      | 6.7  |             |
|                                                               | t <sub>SCSHL</sub> |                                                           | 4.5V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 5.5V   |      | 6.7  |             |
|                                                               |                    |                                                           | 3.0V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 3.6V   |      | 6.7  |             |
|                                                               |                    |                                                           | 2.25V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 2.75V |      | 6.7  |             |
|                                                               |                    |                                                           | 1.71V $\leq$ V <sub>DDA</sub> , V <sub>DDB</sub> $\leq$ 1.89V |      | 6.7  |             |

### Dynamic Electrical Characteristics (MAX1493\_A/D) (Continued)

(V<sub>DDA</sub> - V<sub>GND A</sub> = +1.71V to +5.5V, V<sub>DDB</sub> - V<sub>GND B</sub> = +1.71V to +5.5V, C<sub>L</sub> = 15pF, T<sub>A</sub> = -40°C to +125°C, unless otherwise noted. Typical values are at V<sub>DDA</sub> - V<sub>GND A</sub> = +3.3V, V<sub>DDB</sub> - V<sub>GND B</sub> = +3.3V, V<sub>GND A</sub> = V<sub>GND B</sub>, T<sub>A</sub> = +25°C, unless otherwise noted.) (Notes 2, 3)

| PARAMETER                                                            | SYMBOL             | CONDITIONS                                               | MIN                                                 | TYP | MAX  | UNITS |
|----------------------------------------------------------------------|--------------------|----------------------------------------------------------|-----------------------------------------------------|-----|------|-------|
| Propagation Delay Skew<br>Channel-to-Channel (Opposing<br>Direction) | t <sub>SCOLH</sub> | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V        |                                                     |     | 26.6 | ns    |
|                                                                      |                    | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V        |                                                     |     | 26.6 |       |
|                                                                      |                    | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V      |                                                     |     | 26.6 |       |
|                                                                      |                    | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V      |                                                     |     | 26.9 |       |
|                                                                      | t <sub>SCOHL</sub> | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V        |                                                     |     | 27.9 |       |
|                                                                      |                    | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V        |                                                     |     | 27.7 |       |
|                                                                      |                    | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V      |                                                     |     | 27.6 |       |
|                                                                      |                    | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V      |                                                     |     | 29.7 |       |
| Rise Time (Figure 1)                                                 | t <sub>R</sub>     | OUTA_/<br>OUTB_,<br>10% to 90%,<br>C <sub>L</sub> = 15pF | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 2   |      | ns    |
|                                                                      |                    |                                                          | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 2   |      |       |
|                                                                      |                    |                                                          | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 2   |      |       |
|                                                                      |                    |                                                          | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 2   |      |       |
| Fall Time (Figure 1)                                                 | t <sub>F</sub>     | OUTA_/<br>OUTB_,<br>90% to 10%,<br>C <sub>L</sub> = 15pF | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 2   |      | ns    |
|                                                                      |                    |                                                          | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 2   |      |       |
|                                                                      |                    |                                                          | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 2   |      |       |
|                                                                      |                    |                                                          | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 2   |      |       |
| Enable to Data Valid                                                 | t <sub>EN</sub>    | ENA to OUTA_,<br>ENB to OUTB_,<br>C <sub>L</sub> = 15pF  | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |     | 5.1  | ns    |
|                                                                      |                    |                                                          | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |     | 5.5  |       |
|                                                                      |                    |                                                          | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |     | 6.7  |       |
|                                                                      |                    |                                                          | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |     | 16.3 |       |
| Enable to Three-State                                                | t <sub>TRI</sub>   | ENA to OUTA_,<br>ENB to OUTB_,<br>C <sub>L</sub> = 15pF  | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |     | 2.7  | ns    |
|                                                                      |                    |                                                          | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |     | 4.4  |       |
|                                                                      |                    |                                                          | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |     | 7.0  |       |
|                                                                      |                    |                                                          | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |     | 11.7 |       |

### Dynamic Electrical Characteristics (MAX1493\_B/E)

(V<sub>DDA</sub> - V<sub>GND A</sub> = +1.71V to +5.5V, V<sub>DDB</sub> - V<sub>GND B</sub> = +1.71V to +5.5V, C<sub>L</sub> = 15pF, T<sub>A</sub> = -40°C to +125°C, unless otherwise noted. Typical values are at V<sub>DDA</sub> - V<sub>GND A</sub> = +3.3V, V<sub>DDB</sub> - V<sub>GND B</sub> = +3.3V, V<sub>GND A</sub> = V<sub>GND B</sub>, T<sub>A</sub> = +25°C, unless otherwise noted.) (Notes 2, 3)

| PARAMETER                                                        | SYMBOL             | CONDITIONS                                                | MIN                                                 | TYP  | MAX  | UNITS |
|------------------------------------------------------------------|--------------------|-----------------------------------------------------------|-----------------------------------------------------|------|------|-------|
| <b>INPUT AND OUTPUT CHANNELS</b>                                 |                    |                                                           |                                                     |      |      |       |
| Common-Mode Transient Immunity                                   | CMTI               | IN__ = GND_ or V <sub>DD</sub> _ (Note 5)                 |                                                     | 25   |      | kV/μs |
| Maximum Data Rate                                                | DR <sub>MAX</sub>  |                                                           | 25                                                  |      |      | Mbps  |
| Minimum Pulse Width                                              | PW <sub>MIN</sub>  | INA_ to OUTB_, INB_ to OUTA_                              |                                                     |      | 40   | ns    |
| Glitch Rejection                                                 |                    | INA_ to OUTB_, INB_ to OUTA_                              |                                                     | 15   |      | ns    |
| Propagation Delay (Figure 1)                                     | t <sub>PLH</sub>   | INA_ to OUTB_,<br>INB_ to OUTA_,<br>C <sub>L</sub> = 15pF | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 20.9 | 27.5 | ns    |
|                                                                  |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 21.4 | 28.7 |       |
|                                                                  |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 22.4 | 31.2 |       |
|                                                                  |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 25.7 | 36.9 |       |
|                                                                  | t <sub>PHL</sub>   | INA_ to OUTB_,<br>INB_ to OUTA_,<br>C <sub>L</sub> = 15pF | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 21.1 | 28.8 |       |
|                                                                  |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 21.5 | 29.8 |       |
|                                                                  |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 22.3 | 31.9 |       |
|                                                                  |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 24.9 | 37.4 |       |
| Pulse-Width Distortion                                           | PWD                | t <sub>PLH</sub> - t <sub>PHL</sub>                       | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 0.2  | 2.6  | ns    |
|                                                                  |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 0.1  | 2.6  |       |
|                                                                  |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 0.1  | 2.4  |       |
|                                                                  |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 0.7  | 3.2  |       |
| Propagation Delay Skew<br>Part-to-Part (Same Channel)            | t <sub>SPLH</sub>  |                                                           | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |      | 11.7 | ns    |
|                                                                  |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |      | 11.5 |       |
|                                                                  |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |      | 11.3 |       |
|                                                                  |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |      | 13.6 |       |
|                                                                  | t <sub>SPHL</sub>  |                                                           | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |      | 9.8  |       |
|                                                                  |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |      | 9.8  |       |
|                                                                  |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |      | 11.1 |       |
|                                                                  |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |      | 14.4 |       |
| Propagation Delay Skew<br>Channel-to-Channel<br>(Same Direction) | t <sub>SCSLH</sub> |                                                           | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |      | 3    | ns    |
|                                                                  |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |      | 3    |       |
|                                                                  |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |      | 3    |       |
|                                                                  |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |      | 3    |       |
|                                                                  | t <sub>SCSHL</sub> |                                                           | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |      | 3    |       |
|                                                                  |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |      | 3    |       |
|                                                                  |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |      | 3    |       |
|                                                                  |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |      | 3    |       |

**Dynamic Electrical Characteristics (MAX1493\_B/E) (Continued)**

( $V_{DDA} - V_{GNDA} = +1.71V$  to  $+5.5V$ ,  $V_{DDB} - V_{GNDB} = +1.71V$  to  $+5.5V$ ,  $C_L = 15pF$ ,  $T_A = -40^{\circ}C$  to  $+125^{\circ}C$ , unless otherwise noted. Typical values are at  $V_{DDA} - V_{GNDA} = +3.3V$ ,  $V_{DDB} - V_{GNDB} = +3.3V$ ,  $V_{GNDA} = V_{GNDB}$ ,  $T_A = +25^{\circ}C$ , unless otherwise noted.) (Notes 2, 3)

| PARAMETER                                                            | SYMBOL      | CONDITIONS                                                                       | MIN                                         | TYP | MAX  | UNITS |
|----------------------------------------------------------------------|-------------|----------------------------------------------------------------------------------|---------------------------------------------|-----|------|-------|
| Propagation Delay Skew<br>Channel to Channel (Opposing<br>Direction) | $t_{SCOLH}$ | $4.5V \leq V_{DDA}$ , $V_{DDB} \leq 5.5V$                                        |                                             |     | 11.7 | ns    |
|                                                                      |             | $3.0V \leq V_{DDA}$ , $V_{DDB} \leq 3.6V$                                        |                                             |     | 11.5 |       |
|                                                                      |             | $2.25V \leq V_{DDA}$ , $V_{DDB} \leq 2.75V$                                      |                                             |     | 11.3 |       |
|                                                                      |             | $1.71V \leq V_{DDA}$ , $V_{DDB} \leq 1.89V$                                      |                                             |     | 13.6 |       |
|                                                                      | $t_{SCOHL}$ | $4.5V \leq V_{DDA}$ , $V_{DDB} \leq 5.5V$                                        |                                             |     | 9.8  |       |
|                                                                      |             | $3.0V \leq V_{DDA}$ , $V_{DDB} \leq 3.6V$                                        |                                             |     | 9.8  |       |
|                                                                      |             | $2.25V \leq V_{DDA}$ , $V_{DDB} \leq 2.75V$                                      |                                             |     | 11.1 |       |
|                                                                      |             | $1.71V \leq V_{DDA}$ , $V_{DDB} \leq 1.89V$                                      |                                             |     | 14.4 |       |
| Rise Time (Figure 1)                                                 | $t_R$       | $OUTA_{\downarrow} /$<br>$OUTB_{\downarrow}$ ,<br>10% to 90%,<br>$C_L = 15pF$    | $4.5V \leq V_{DDA}$ , $V_{DDB} \leq 5.5V$   | 2   |      | ns    |
|                                                                      |             |                                                                                  | $3.0V \leq V_{DDA}$ , $V_{DDB} \leq 3.6V$   | 2   |      |       |
|                                                                      |             |                                                                                  | $2.25V \leq V_{DDA}$ , $V_{DDB} \leq 2.75V$ | 2   |      |       |
|                                                                      |             |                                                                                  | $1.71V \leq V_{DDA}$ , $V_{DDB} \leq 1.89V$ | 2   |      |       |
| Fall Time (Figure 1)                                                 | $t_F$       | $OUTA_{\downarrow} /$<br>$OUTB_{\downarrow}$ ,<br>90% to 10%,<br>$C_L = 15pF$    | $4.5V \leq V_{DDA}$ , $V_{DDB} \leq 5.5V$   | 2   |      | ns    |
|                                                                      |             |                                                                                  | $3.0V \leq V_{DDA}$ , $V_{DDB} \leq 3.6V$   | 2   |      |       |
|                                                                      |             |                                                                                  | $2.25V \leq V_{DDA}$ , $V_{DDB} \leq 2.75V$ | 2   |      |       |
|                                                                      |             |                                                                                  | $1.71V \leq V_{DDA}$ , $V_{DDB} \leq 1.89V$ | 2   |      |       |
| Enable to Data Valid                                                 | $t_{EN}$    | $ENA$ to $OUTA_{\downarrow}$ ,<br>$ENB$ to $OUTB_{\downarrow}$ ,<br>$C_L = 15pF$ | $4.5V \leq V_{DDA}$ , $V_{DDB} \leq 5.5V$   |     | 5.1  | ns    |
|                                                                      |             |                                                                                  | $3.0V \leq V_{DDA}$ , $V_{DDB} \leq 3.6V$   |     | 5.5  |       |
|                                                                      |             |                                                                                  | $2.25V \leq V_{DDA}$ , $V_{DDB} \leq 2.75V$ |     | 6.7  |       |
|                                                                      |             |                                                                                  | $1.71V \leq V_{DDA}$ , $V_{DDB} \leq 1.89V$ |     | 16.3 |       |
| Enable to Three-State                                                | $t_{TRI}$   | $ENA$ to $OUTA_{\downarrow}$ ,<br>$ENB$ to $OUTB_{\downarrow}$ ,<br>$C_L = 15pF$ | $4.5V \leq V_{DDA}$ , $V_{DDB} \leq 5.5V$   |     | 2.7  | ns    |
|                                                                      |             |                                                                                  | $3.0V \leq V_{DDA}$ , $V_{DDB} \leq 3.6V$   |     | 4.4  |       |
|                                                                      |             |                                                                                  | $2.25V \leq V_{DDA}$ , $V_{DDB} \leq 2.75V$ |     | 7.0  |       |
|                                                                      |             |                                                                                  | $1.71V \leq V_{DDA}$ , $V_{DDB} \leq 1.89V$ |     | 11.7 |       |

### Dynamic Electrical Characteristics (MAX1493\_C/F)

( $V_{DDA} - V_{GNDA} = +1.71V$  to  $+5.5V$ ,  $V_{DDB} - V_{GNDB} = +1.71V$  to  $+5.5V$ ,  $C_L = 15pF$ ,  $T_A = -40^{\circ}C$  to  $+125^{\circ}C$ , unless otherwise noted. Typical values are at  $V_{DDA} - V_{GNDA} = +3.3V$ ,  $V_{DDB} - V_{GNDB} = +3.3V$ ,  $V_{GNDA} = V_{GNDB}$ ,  $T_A = +25^{\circ}C$ , unless otherwise noted.) (Notes 2, 3)

| PARAMETER                                                  | SYMBOL             | CONDITIONS                                                | MIN                                                 | TYP | MAX  | UNITS |
|------------------------------------------------------------|--------------------|-----------------------------------------------------------|-----------------------------------------------------|-----|------|-------|
| <b>INPUT AND OUTPUT CHANNELS</b>                           |                    |                                                           |                                                     |     |      |       |
| Common-Mode Transient Immunity                             | CMTI               | IN__ = GND_ or V <sub>DD</sub> _ (Note 5)                 |                                                     | 25  |      | kV/μs |
| Maximum Data Rate                                          | DR <sub>MAX</sub>  |                                                           | 150                                                 |     |      | Mbps  |
| Minimum Pulse Width                                        | PW <sub>MIN</sub>  | INA_ to OUTB_, INB_ to OUTB_                              |                                                     |     | 6.67 | ns    |
| Propagation Delay (Figure 1)                               | t <sub>PLH</sub>   | INA_ to OUTB_,<br>INB_ to OUTA_,<br>C <sub>L</sub> = 15pF | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 5.1 | 7.5  | ns    |
|                                                            |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 5.2 | 8.1  |       |
|                                                            |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 5.8 | 9.7  |       |
|                                                            |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 8.1 | 14   |       |
|                                                            | t <sub>PHL</sub>   | INA_ to OUTB_,<br>INB_ to OUTA_,<br>C <sub>L</sub> = 15pF | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 4.9 | 7.4  |       |
|                                                            |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 5.3 | 8.3  |       |
|                                                            |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 5.9 | 10.2 |       |
|                                                            |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 8.2 | 14.9 |       |
| Pulse-Width Distortion                                     | PWD                | t <sub>PLH</sub> - t <sub>PHL</sub>                       | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 0.2 | 1    | ns    |
|                                                            |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 0.1 | 1    |       |
|                                                            |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 0.1 | 1    |       |
|                                                            |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 0.1 | 1    |       |
| Propagation Delay Skew Part-to-Part (Same Channel)         | t <sub>SPLH</sub>  |                                                           | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |     | 3.0  | ns    |
|                                                            |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |     | 3.3  |       |
|                                                            |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |     | 4.3  |       |
|                                                            |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |     | 7.1  |       |
|                                                            | t <sub>SPHL</sub>  |                                                           | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |     | 2.8  |       |
|                                                            |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |     | 3.4  |       |
|                                                            |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |     | 4.6  |       |
|                                                            |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |     | 7.9  |       |
| Propagation Delay Skew Channel-to-Channel (Same Direction) | t <sub>SCSLH</sub> |                                                           | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |     | 0.9  | ns    |
|                                                            |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |     | 1.2  |       |
|                                                            |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |     | 1.4  |       |
|                                                            |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |     | 1.6  |       |
|                                                            | t <sub>SCSHL</sub> |                                                           | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |     | 0.9  |       |
|                                                            |                    |                                                           | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |     | 1.2  |       |
|                                                            |                    |                                                           | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |     | 1.4  |       |
|                                                            |                    |                                                           | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |     | 1.6  |       |

**Dynamic Electrical Characteristics (MAX1493\_C/F) (continued)**

(V<sub>DDA</sub> - V<sub>GND A</sub> = +1.71V to +5.5V, V<sub>DDB</sub> - V<sub>GND B</sub> = +1.71V to +5.5V, C<sub>L</sub> = 15pF, T<sub>A</sub> = -40°C to +125°C, unless otherwise noted. Typical values are at V<sub>DDA</sub> - V<sub>GND A</sub> = +3.3V, V<sub>DDB</sub> - V<sub>GND B</sub> = +3.3V, V<sub>GND A</sub> = V<sub>GND B</sub>, T<sub>A</sub> = +25°C, unless otherwise noted.) (Notes 2, 3)

| PARAMETER                                                            | SYMBOL               | CONDITIONS                                                                          | MIN                                                 | TYP | MAX  | UNITS |
|----------------------------------------------------------------------|----------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------|-----|------|-------|
| Propagation Delay Skew<br>Channel-to-Channel (Opposing<br>Direction) | t <sub>SCOLH</sub>   | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V                                   |                                                     |     | 3    | ns    |
|                                                                      |                      | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V                                   |                                                     |     | 3.3  |       |
|                                                                      |                      | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V                                 |                                                     |     | 4.3  |       |
|                                                                      |                      | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V                                 |                                                     |     | 7.1  |       |
|                                                                      | t <sub>SCOHL</sub>   | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V                                   |                                                     |     | 2.8  |       |
|                                                                      |                      | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V                                   |                                                     |     | 3.4  |       |
|                                                                      |                      | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V                                 |                                                     |     | 4.6  |       |
|                                                                      |                      | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V                                 |                                                     |     | 7.9  |       |
| Rise Time (Figure 1)                                                 | t <sub>R</sub>       | OUTA_ <sub>↓</sub><br>OUTB_ <sub>↑</sub> ,<br>10% to 90%,<br>C <sub>L</sub> = 15pF  | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 2   |      | ns    |
|                                                                      |                      |                                                                                     | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 2   |      |       |
|                                                                      |                      |                                                                                     | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 2   |      |       |
|                                                                      |                      |                                                                                     | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 2   |      |       |
| Fall Time (Figure 1)                                                 | t <sub>F</sub>       | OUTA_ <sub>↓</sub><br>OUTB_ <sub>↓</sub> ,<br>90% to 10%,<br>C <sub>L</sub> = 15pF  | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   | 2   |      | ns    |
|                                                                      |                      |                                                                                     | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   | 2   |      |       |
|                                                                      |                      |                                                                                     | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V | 2   |      |       |
|                                                                      |                      |                                                                                     | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V | 2   |      |       |
| Enable to Data Valid                                                 | t <sub>EN</sub>      | ENA to OUTA_ <sub>↓</sub> ,<br>ENB to OUTB_ <sub>↓</sub> ,<br>C <sub>L</sub> = 15pF | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |     | 5.1  | ns    |
|                                                                      |                      |                                                                                     | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |     | 5.5  |       |
|                                                                      |                      |                                                                                     | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |     | 6.7  |       |
|                                                                      |                      |                                                                                     | 1.71V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V |     | 16.3 |       |
| Enable to Three-State                                                | t <sub>TRI</sub>     | ENA to OUTA_ <sub>↓</sub> ,<br>ENB to OUTB_ <sub>↓</sub> ,<br>C <sub>L</sub> = 15pF | 4.5V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 5.5V   |     | 2.7  | ns    |
|                                                                      |                      |                                                                                     | 3.0V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 3.6V   |     | 4.4  |       |
|                                                                      |                      |                                                                                     | 2.25V ≤ V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 2.75V |     | 7.0  |       |
|                                                                      |                      |                                                                                     | V <sub>DDA</sub> , V <sub>DDB</sub> ≤ 1.89V         |     | 11.7 |       |
| Peak Eye Diagram Jitter                                              | T <sub>JIT(PK)</sub> | V <sub>DDA</sub> , V <sub>DDB</sub> = 5.0V                                          |                                                     | 140 |      | ps    |
|                                                                      |                      | V <sub>DDA</sub> , V <sub>DDB</sub> = 3.3V                                          |                                                     | 130 |      |       |
|                                                                      |                      | V <sub>DDA</sub> , V <sub>DDB</sub> = 2.5V                                          |                                                     | 140 |      |       |
|                                                                      |                      | V <sub>DDA</sub> , V <sub>DDB</sub> = 1.8V                                          |                                                     | 160 |      |       |

## ESD Protection

| PARAMETER | SYMBOL | CONDITIONS                 | MIN | TYP | MAX | UNITS |
|-----------|--------|----------------------------|-----|-----|-----|-------|
| ESD       |        | Human Body Model, All Pins |     | ±4  |     | kV    |

**Note 2:** All devices are 100% production tested at  $T_A = +125^{\circ}\text{C}$ . Specifications over temperature are guaranteed by design.

**Note 3:** Not production tested. Guaranteed by design.

**Note 4:** All currents into the device are positive. All currents out of the device are negative.

**Note 5:** CMTI is the maximum sustainable common-mode voltage slew rate while maintaining the correct output. CMTI applies to both rising and falling common-mode voltage edges. Tested with the transient generator connected between GNDA and GNDB ( $V_{CM} = 1000\text{V}$ ).

## Safety Regulatory Approvals

|                                                                                                                                                                                                                                                                           |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>UL</b>                                                                                                                                                                                                                                                                 |
| The MAX14934–MAX14936 are certified under UL1577. For more details, refer to File E351759.                                                                                                                                                                                |
| Rated up to 5000V <sub>RMS</sub> isolation voltage for single protection.                                                                                                                                                                                                 |
| <b>cUL (Equivalent to CSA notice 5A)</b>                                                                                                                                                                                                                                  |
| The MAX14934/MAX14936 are certified up to 5000V <sub>RMS</sub> for single protection. For more details, refer to File 351759.                                                                                                                                             |
| <b>VDE</b>                                                                                                                                                                                                                                                                |
| The MAX14934–MAX14936 is certified to DIN V VDE V 0884-10 (VDE V 0884-10): 2006-12. For details, see file ref. 5015017-4880-0001/217630/EC22/SCT. Basic Insulation, Maximum Transient Isolation Voltage 8400V <sub>PK</sub> , Maximum Working Voltage 848V <sub>RMS</sub> |

## IEC Insulation Testing

|                                                                                                                                                |
|------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>TUV</b>                                                                                                                                     |
| The MAX14934/MAX14936 are tested under TUV.                                                                                                    |
| IEC60950-1: Up to 1200VP (848V <sub>RMS</sub> ) working voltage for basic insulation.                                                          |
| IEC61010-1 (ed. 3): Up to 848V <sub>RMS</sub> working voltage for basic insulation. For details, see Technical Report number 095-72100581-100. |
| IEC60601-1 (ed. 3): For details see Technical Report number 095-72100581-200.                                                                  |
| Basic insulation 1 MOOP, 1200V <sub>PK</sub> (848V <sub>RMS</sub> )                                                                            |
| Withstand isolation voltage for 60s (Viso) 5000V <sub>RMS</sub>                                                                                |

Insulation Characteristics

| PARAMETER                                    | SYMBOL            | CONDITIONS                                                                 | VALUE              | UNITS            |
|----------------------------------------------|-------------------|----------------------------------------------------------------------------|--------------------|------------------|
| Partial Discharge Test Voltage               | V <sub>PR</sub>   | Method B1 = V <sub>IORM</sub> × 1.875<br>(t = 1s, partial discharge < 5pC) | 2250               | V <sub>P</sub>   |
| Maximum Repetitive Peak Isolation Voltage    | V <sub>IORM</sub> |                                                                            | 1200               | V <sub>P</sub>   |
| Maximum Working Isolation Voltage            | V <sub>IOWM</sub> |                                                                            | 848                | V <sub>RMS</sub> |
| Maximum Transient Isolation Voltage          | V <sub>IOTM</sub> | t = 1s                                                                     | 8400               | V <sub>P</sub>   |
| Maximum Withstand Isolation Voltage          | V <sub>ISO</sub>  | f <sub>SW</sub> = 60Hz, duration = 60s                                     | 5000               | V <sub>RMS</sub> |
| Maximum Surge Isolation Voltage              | V <sub>IOSM</sub> | Basic insulation 1.2/50μs pulse                                            | 10                 | kV               |
| Insulation Resistance                        | R <sub>S</sub>    | T <sub>A</sub> = +150°C<br>V <sub>IO</sub> = 500V                          | > 10 <sup>12</sup> | Ω                |
| Barrier Capacitance Input to Output (Note 6) | C <sub>IO</sub>   | f <sub>SW</sub> = 1MHz                                                     | 2                  | pF               |
| Minimum Creepage Distance                    | CPG               | Wide SOIC                                                                  | 8                  | mm               |
| Minimum Clearance Distance                   | CLR               | Wide SOIC                                                                  | 8                  | mm               |
| Internal Clearance                           |                   | Distance through insulation                                                | 0.015              | mm               |
| Comparative Tracking Resistance Index        | CTI               | Material Group II (IEC 60112)                                              | 575                |                  |
| Climatic Category                            |                   |                                                                            | 40/125/21          |                  |
| Pollution Degree (DIN VDE 0110, Table 1)     |                   |                                                                            | 2                  |                  |

**Note 6.** Capacitance is measured with all pins on side A and side B tied together.














Figure 1. Test Circuit (A) and Timing Diagram (B)

## Typical Operating Characteristics

( $V_{DDA} - V_{GNDA} = +3.3V$ ,  $V_{DDB} - V_{GNDB} = +3.3V$ ,  $V_{GNDA} = V_{GNDB}$ ,  $T_A = +25^\circ C$ , unless otherwise noted.)




## Pin Configurations




## Pin Description

| PIN      |          |          | NAME             | FUNCTION                                                                                              | VOLTAGE<br>RELATIVE TO |
|----------|----------|----------|------------------|-------------------------------------------------------------------------------------------------------|------------------------|
| MAX14934 | MAX14935 | MAX14936 |                  |                                                                                                       |                        |
| 1        | 1        | 1        | V <sub>DDA</sub> | Power Supply. Bypass V <sub>DDA</sub> with a 0.1μF ceramic capacitor as close as possible to the pin. | GNDA                   |
| 2, 8     | 2, 8     | 2, 8     | GNDA             | Ground Reference for Side A                                                                           | —                      |
| 3        | 3        | 3        | INA1             | Logic Input 1 on Side A. INA1 corresponds to OUTB1.                                                   | GNDA                   |
| 4        | 4        | 4        | INA2             | Logic Input 2 on Side A. INA2 corresponds to OUTB2.                                                   | GNDA                   |
| 5        | 5        | —        | INA3             | Logic Input 3 on Side A. INA3 corresponds to OUTB3.                                                   | GNDA                   |
| 6        | —        | —        | INA4             | Logic Input 4 on Side A. INA4 corresponds to OUTB4.                                                   | GNDA                   |
| 7        | —        | —        | I.C.             | Internally Connected. Leave unconnected or connect to GNDA or V <sub>DDA</sub> .                      | —                      |
| —        | 6        | 5        | OUTA1            | Logic Output 1 on Side A                                                                              | GNDA                   |
| —        | —        | 6        | OUTA2            | Logic Output 2 on Side A                                                                              | GNDA                   |
| —        | 7        | 7        | ENA              | Active-High Enable for Side A. ENA has an internal 2μA pullup to V <sub>DDA</sub> .                   | GNDA                   |
| 9, 15    | 9, 15    | 9, 15    | GNDB             | Ground Reference for Side B                                                                           | —                      |
| 10       | 10       | 10       | ENB              | Active-High Enable for Side B. ENB has an internal 2μA pullup to V <sub>DDB</sub> .                   | GNDB                   |
| 11       | —        | —        | OUTB4            | Logic Output 4 on Side B                                                                              | GNDB                   |
| —        | 11       | 12       | INB1             | Logic Input 1 on Side B. INB1 corresponds to OUTA1.                                                   | GNDB                   |
| —        | —        | 11       | INB2             | Logic Input 2 on Side B. INB2 corresponds to OUTA2.                                                   | GNDB                   |
| 12       | 12       | —        | OUTB3            | Logic Output 3 on Side B                                                                              | GNDB                   |
| 13       | 13       | 13       | OUTB2            | Logic Output 2 on Side B                                                                              | GNDB                   |
| 14       | 14       | 14       | OUTB1            | Logic Output 1 on Side B                                                                              | GNDB                   |
| 16       | 16       | 16       | V <sub>DDB</sub> | Power Supply. Bypass V <sub>DDB</sub> with a 0.1μF ceramic capacitor as close as possible to the pin. | GNDB                   |

## Typical Operating Circuit



## Typical Operating Circuit (continued)



## Detailed Description

The MAX14934–MAX14936 are a family of four-channel digital isolators. The MAX14934–MAX14936 family transfers digital signals between circuits with different power domains. The devices are rated for 5kV<sub>RMS</sub> isolation voltage for 60 seconds. This family of digital isolators offers low-power operation, high electromagnetic interference (EMI) immunity, and stable temperature performance through Maxim's proprietary process technology. The devices isolate different ground domains and block high-voltage/high-current transients from sensitive or human interface circuitry.

The MAX14934–MAX14936 family offers three unidirectional channel configurations for design convenience. The MAX14934 features four channels transferring digital signals in one direction for applications such as isolated digital I/O. The MAX14935 has three channels transmitting data in one direction and one channel transmitting in the opposite direction, making it ideal for applications such as isolated SPI and RS-485 communication. The MAX14936 provides further design flexibility with two channels in each direction for isolated RS-232 or other applications.

Devices are available with data rates from DC up to 1Mbps (A/D versions), 25Mbps (B/E versions), or 150Mbps (C/F versions). Each device can also be ordered with default-high or default-low outputs. This is the state an output will go to when the input side of the device is unpowered.

The devices have two supply inputs, V<sub>DDA</sub> and V<sub>ddb</sub>, that independently set the logic levels on either side of the device. V<sub>DDA</sub> and V<sub>ddb</sub> are referenced to GNDA and GNDB, respectively. The MAX14934–MAX14936 family also features a refresh circuit to ensure output accuracy when an input remains in the same state indefinitely.

### Digital Isolation

The MAX14934–MAX14936 family provides galvanic isolation for digital signals that are transmitted between two ground domains. Up to 1200V<sub>PEAK</sub> of continuous isolation is supported, as well as transient differences of up to 5kV<sub>RMS</sub> for up to 60 seconds.

### Level Shifting

The wide supply voltage range of both V<sub>DDA</sub> and V<sub>ddb</sub> allows the MAX14934–MAX14936 family to be used for level translation in addition to isolation. V<sub>DDA</sub> and V<sub>ddb</sub> can be independently set to any voltage from 1.71V to 5.5V. The supply voltage sets the logic level on the corresponding side of the isolator.

## Unidirectional Channels

Each channel of the MAX14934–MAX14936 is unidirectional; it only passes data in one direction, as indicated in the functional diagram. Each device features four unidirectional channels that operate independently with guaranteed data rates from DC up to 1Mbps (A/D versions), 25Mbps (B/E versions), or 150Mbps (C/F versions). The output driver of each channel is push-pull, eliminating the need for pullup resistors. The outputs are able to drive both TTL and CMOS logic inputs.

## Startup and Undervoltage Lockout

The V<sub>DDA</sub> and V<sub>ddb</sub> supplies are both internally monitored for undervoltage conditions. Undervoltage events can occur during power-up, power-down, or during normal operation due to a sagging supply voltage. When an undervoltage condition is detected on either supply, all outputs go to their default states regardless of the status of the inputs (Table 1). Figure 2 through Figure 5 show the behavior of the outputs during power-up and power-down.

## Applications Information

### Power-Supply Sequencing

The MAX14934–MAX14936 do not require special power-supply sequencing. The logic levels are set independently on either side by V<sub>DDA</sub> and V<sub>ddb</sub>. Each supply can be present over the entire specified range regardless of the level or presence of the other supply.

### Power-Supply Decoupling

To reduce ripple and the chance of introducing data errors, bypass V<sub>DDA</sub> and V<sub>ddb</sub> with 0.1μF ceramic capacitors to GNDA and GNDB, respectively. Place the bypass capacitors as close to the power-supply input pins as possible.

Table 1. Output Behavior During Undervoltage Conditions

| V <sub>IN</sub> | V <sub>DDA</sub> | V <sub>DDB</sub> | ENA | ENB | V <sub>OUTA</sub> | V <sub>OUTB</sub> |
|-----------------|------------------|------------------|-----|-----|-------------------|-------------------|
| 1               | Powered          | Powered          | 1   | 1   | 1                 | 1                 |
|                 |                  |                  | 0   | 0   | Hi-Z              | Hi-Z              |
| 0               | Powered          | Powered          | 1   | 1   | 0                 | 0                 |
|                 |                  |                  | 0   | 0   | Hi-Z              | Hi-Z              |
| X               | Undervoltage     | Powered          | 1   | 1   | Default           | Default           |
|                 |                  |                  | 0   | 0   | Hi-Z              | Hi-Z              |
| X               | Powered          | Undervoltage     | 1   | 1   | Default           | Default           |
|                 |                  |                  | 0   | 0   | Hi-Z              | Hi-Z              |




Figure 2. Undervoltage Lockout Behavior (MAX1493\_A/BC High)




Figure 3. Undervoltage Lockout Behavior (MAX1493\_A/BC Low)




Figure 4. Undervoltage Lockout Behavior (MAX1493\_D/E/F High)



Figure 5. Undervoltage Lockout Behavior (MAX1493\_D/E/F Low)

## Ordering Information/Selector Guide

| PART          | CHANNEL CONFIGURATION | DATA RATE (Mbps) | OUTPUT       | TEMP RANGE (°C) | PIN-PACKAGE  |
|---------------|-----------------------|------------------|--------------|-----------------|--------------|
| MAX14934AAWE+ | 4/0                   | 1                | Default high | -40 to +125     | 16 wide SOIC |
| MAX14934BAWE+ | 4/0                   | 25               | Default high | -40 to +125     | 16 wide SOIC |
| MAX14934CAWE+ | 4/0                   | 150              | Default high | -40 to +125     | 16 wide SOIC |
| MAX14934DAWE+ | 4/0                   | 1                | Default low  | -40 to +125     | 16 wide SOIC |
| MAX14934EAW+  | 4/0                   | 25               | Default low  | -40 to +125     | 16 wide SOIC |
| MAX14934FAWE+ | 4/0                   | 150              | Default low  | -40 to +125     | 16 wide SOIC |
| MAX14935AAWE+ | 3/1                   | 1                | Default high | -40 to +125     | 16 wide SOIC |
| MAX14935BAWE+ | 3/1                   | 25               | Default high | -40 to +125     | 16 wide SOIC |
| MAX14935CAWE+ | 3/1                   | 150              | Default high | -40 to +125     | 16 wide SOIC |
| MAX14935DAWE+ | 3/1                   | 1                | Default low  | -40 to +125     | 16 wide SOIC |
| MAX14935EAW+  | 3/1                   | 25               | Default low  | -40 to +125     | 16 wide SOIC |
| MAX14935FAWE+ | 3/1                   | 150              | Default low  | -40 to +125     | 16 wide SOIC |
| MAX14936AAWE+ | 2/2                   | 1                | Default high | -40 to +125     | 16 wide SOIC |
| MAX14936BAWE+ | 2/2                   | 25               | Default high | -40 to +125     | 16 wide SOIC |
| MAX14936CAWE+ | 2/2                   | 150              | Default high | -40 to +125     | 16 wide SOIC |
| MAX14936DAWE+ | 2/2                   | 1                | Default low  | -40 to +125     | 16 wide SOIC |
| MAX14936EAW+  | 2/2                   | 25               | Default low  | -40 to +125     | 16 wide SOIC |
| MAX14936FAWE+ | 2/2                   | 150              | Default low  | -40 to +125     | 16 wide SOIC |

+Denotes a lead(Pb)-free/RoHS-compliant package.

### Chip Information

PROCESS: BICMOS

### Package Information

For the latest package outline information and land patterns (footprints), go to [www.maximintegrated.com/packages](http://www.maximintegrated.com/packages). Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

| PACKAGE TYPE | PACKAGE CODE | OUTLINE NO.             | LAND PATTERN NO.        |
|--------------|--------------|-------------------------|-------------------------|
| 16 Wide SOIC | W16M+8       | <a href="#">21-0042</a> | <a href="#">90-0107</a> |

## Revision History

| REVISION NUMBER | REVISION DATE | DESCRIPTION                                                                                                                                                                                                                                                                                                 | PAGES CHANGED |
|-----------------|---------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| 0               | 9/14          | Initial release                                                                                                                                                                                                                                                                                             | —             |
| 1               | 12/14         | Removed future product notation from MAX14935DAWE+ in <i>Ordering Information</i> table, changed “basic insulation” to “single protection” in <i>Safety Regulatory Approvals</i> table, and updated third bullet of <i>Many Options Support Broad Applications</i> in <i>Features and Benefits</i> section. | 1, 13, 22     |
| 2               | 3/15          | Changed future product status for: MAX14934DAWE+, MAX14936AAWE+, MAX14936BAWE+, MAX14936DAWE+, MAX14936EAWWE+, and MAX14936FAWE+.                                                                                                                                                                           | 22            |
| 3               | 7/15          | Updated <i>Benefits and Features</i> section, <i>Safety Regulatory Approvals</i> , <i>Insulation Characteristics</i> tables, and <i>Pin Configuration</i> tables.                                                                                                                                           | 1, 13, 14, 16 |
| 4               | 4/16          | Fixed typos, updated <i>Safety Regulatory Approvals</i> , and updated <i>Ordering Information/Selection Guide</i> .                                                                                                                                                                                         | 1, 13, 14, 21 |
| 5               | 5/16          | Updated TUV information and created <i>IEC Insulation Testing</i> table                                                                                                                                                                                                                                     | 1, 13         |
| 6               | 1/17          | Updated Figure 1 text and removed VDE pending                                                                                                                                                                                                                                                               | 1, 13, 14     |

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at [www.maximintegrated.com](http://www.maximintegrated.com).

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the *Electrical Characteristics* table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Maxim Integrated:

[MAX14935DAWE+](#) [MAX14935EAW+](#) [MAX14935FAWE+](#) [MAX14935BAWE+](#) [MAX14935CAWE+](#)  
[MAX14934BAWE+](#) [MAX14934EAW+](#) [MAX14934CAWE+](#) [MAX14934DAWE+](#) [MAX14934FAWE+](#)  
[MAX14934EAW+T](#) [MAX14934FAWE+T](#) [MAX14935BAWE+T](#) [MAX14935CAWE+T](#) [MAX14935EAW+T](#)  
[MAX14935FAWE+T](#) [MAX14936AAWE+](#) [MAX14936BAWE+](#) [MAX14936AAWE+T](#) [MAX14936EAW+](#)  
[MAX14936BAWE+T](#) [MAX14936DAWE+](#) [MAX14936DAWE+T](#) [MAX14936EAW+T](#) [MAX14936FAWE+T](#)  
[MAX14936FAWE+](#) [MAX14934AAWE+](#) [MAX14935AAWE+](#) [MAX14934BAWE+T](#) [MAX14934CAWE+T](#)  
[MAX14935DAWE+T](#)