



Focus Product Selector Guide



Microchip is a leading provider of semiconductor supplier of smart, connected and secure embedded control solutions, providing low-risk product development, lower total system cost and faster time to market for thousands of diverse customer applications worldwide. Offering outstanding technical support along with dependable delivery and quality, Microchip serves over 125,000 customers across the industrial, automotive, consumer, aerospace and defense, communications and computing markets worldwide.

8-bit Microcontrollers

Microchip's PIC® and AVR® microcontrollers (MCUs) represent two dominant architectures for embedded design. With a combined 45 years' experience developing commercially available and cost-effective 8-bit MCUs, Microchip is the supplier of choice for many due to its strong legacy and history of innovation in 8-bit. Our current lineup of 8-bit PIC and AVR MCUs incorporates the latest technologies to enhance system performance while reducing power consumption and development time. With more than 1,200 devices, Microchip offers the industry's largest 8-bit portfolio. Key features include Core Independent Peripherals, low-power performance with picoPower® and eXtreme Low Power (XLP) technology, industry-leading robustness driven by best-in-class EMI/EMC performance and simplified development with our suite of easy-to-use development tools. For more information visit: www.microchip.com/8bit.

16-bit PIC Microcontrollers

The PIC24 is a cost-effective, low-power family of MCUs, featuring devices with eXtreme Low Power (XLP) technology, 16 MIPS performance and dual partition memory up to 1024 KB of Flash with a rich set of Core Independent Peripherals (CIPs). Our portfolio offers an upgrade in features and peripherals for applications that are pushing the boundaries of 8-bit MCU capabilities, offering more memory, more pins and faster peripherals in the same ecosystem for easy migration. The PIC24 MCUs also feature dedicated peripherals and functions to help increase the reliability in safety critical applications and with AEC Q100 qualification, the high-performance PIC24 MCUs offer 3V, 5V and up to 150°C robust operations. For more information visit: www.microchip.com/16bit.

dsPIC® Digital Signal Controllers

The dsPIC family of Digital Signal Controllers (DSCs) features a fully implemented Digital Signal Processor (DSP) engine with up to 100 MIPS performance capable of high-efficiency, high-precision variable speed, constant torque PI control and Field Oriented Control (FOC) motor control. Equipped with high-speed Analog-to-Digital Converters (ADCs), op-amps, and comparators coupled with functional safety features and operations up to 150°C, the dsPIC33 family is ideal for PMSM, ACIM and BLDC motor control in industrial, medical, automotive and consumer applications.

The dsPIC family also offers dual cores with up to 100 MIPS equipped with high speed PWMs, ADCs, PGAs to handle very tight control loop execution and separate time-critical control loops from housekeeping making them ideal for demanding power conversion applications and lighting in industrial, medical, automotive and consumer applications. The dsPIC33 MCUS also offer the capability to live update firmware, which is critical for server applications that cannot afford any downtime. For more information visit: www.microchip.com/dspic.

32-bit Microcontrollers

From simple embedded control to advanced graphics and secure Internet of Things (IoT) applications, Microchip portfolio of 32-bit MCUs can meet your design challenge. Spanning a wide range of options—from offering the industry's lowest power consumption to delivering the highest performance—these MCUs run at up to 600 DMIPS and deliver ample code and data space with up to 2048 KB Flash and 512 KB RAM with 32 MB integrated DDR2 DRAM or 128 MB externally addressable options. They are supported by novel and easy-to-use software solutions to speed up your application development. For more information visit: www.microchip.com/32bit.

32-bit Arm® Microprocessors

As you push beyond the boundaries of 32-bit MCUs, the SAM9 (ARM9) and SAMA5 (Cortex® A5) microprocessor (MPU) families provide the power and performance needed for demanding applications. They feature up to 600 MHz (942 DMIPS) operation and support for up to 512 MB of external DDR2 or DDR3 DRAM. Microchip's MPUs offer a rich set of peripherals and user interfaces including Gigabit Ethernet MACs, high-speed USB, hardware video decoding, capacitive touch, 12-bit CMOS image (camera) sensors, I²S audio interfaces and advanced 24-bit graphic LCD controllers with overlays. They deliver market-leading low power (down to 0.3 mW sleep) and advanced security features needed for Internet-connected gateways and cost-sensitive industrial and consumer applications. The MPU devices come with free Linux® OS and third-party tools and software, and low-cost hardware development boards are available to ease development. For more information visit: www.microchip.com/mpu.

Microchip: A Partner in Your Success

Analog and Interface Products

Microchip's integrated analog technology, peripherals and features are engineered to meet today's demanding design requirements. Our extensive spectrum of analog products addresses thermal management, power management, battery management, mixed-signal, linear, interface and safety and security solutions. Our broad portfolio of stand-alone analog and interface devices offers highly integrated solutions that combine various analog functions in space-saving packages and support a variety of bus interfaces. Many of these devices support functionality that enhances the analog features currently available on PIC microcontrollers. Microchip extends power solutions with a broad portfolio of Silicon diodes, MOSFETs and IGBTs and Silicon Carbide (SiC) MOSFETs and Schottky Barrier Diodes (SBDs). For more information visit: www.microchip.com/analog.

Security and Authentication Products

Microchip offers a variety of crypto element devices that offer an ideal way to provide the three pillars of security—authentication, data integrity, and confidentiality—in applications such as disposables, accessories and nodes used in home automation, industrial networking, medical and other applications. Crypto devices employ ultra-secure, hardware-based cryptographic key storage and cryptographic countermeasures such as tamper detection, which offer higher security than software-based key storage. For more information visit: www.microchip.com/security.

Timing and Communication Products

Microchip has an expansive, wide-ranging clock and timing portfolio that delivers total solutions for your complex timing requirements. Our oscillator products offer both low-jitter and low-power online-configurable products with the option of choosing a traditional quartz-based solution or going with our MEMS silicon-based resonator products. The clock generation line offers online configurable, single chip, multiple-frequency clock tree solutions. Rounding out the portfolio, our clock and data distribution product line includes one of the industry's largest portfolios of buffers, logic translators and multiplexers.

With the right combination of products, configuration tools and technical support, Microchip's Timing and Communications products are ideal for all designs, from simple to high-performance systems. For more information visit: www.microchip.com/timing.

Real-Time Clock/Calendar

Microchip offers a family of highly integrated, low-cost Real-Time Clock/Calendar devices with battery backup capability, digital trimming, plus on-board EEPROM and SRAM memory. For more information visit: www.microchip.com/clock.

Memory Products

Microchip's broad portfolio of memory devices includes Serial EEPROM, Serial SRAM, Serial Flash, Serial NVSRAM, Serial EERAM, Parallel EEPROM, Parallel OTP (One-Time Programmable) and Parallel Flash devices. Our innovative, low-power designs and extensive testing have ensured industry-leading robustness and endurance, along with best-in-class quality, at low costs. For more information visit: www.microchip.com/memory.

Wireless Products

The Microchip wireless portfolio is focused on offering extremely low-power operation and is designed for sensing or command/control operation products. This extensive portfolio is comprised of solutions for Wi-Fi®, Bluetooth®, LoRa® technology, 802.15.4 (such as zigbee® or MiWi™ wireless networking protocol) along with proprietary 2.4 GHz and Sub-GHz communications. The Timberwolf™ platform is the latest-generation audio processor. The hardware architecture is ideal for today's growing need for hands-free communications and Human To Machine (H2M) voice interfaces. This field-upgradable platform is designed for multiple end-market applications. For more information visit: www.microchip.com/wireless.

High-Throughput USB and Ethernet Interface Solutions

High-speed networking is the backbone of many industrial, IoT, consumer and automotive applications. Microchip offers a complete portfolio of Ethernet PHYs, switches, controllers and bridge devices, enabling up to 10 Gigabit-speed communications in harsh environments. The USB offering spans low cost to SuperSpeed and incorporates value-rich solutions such as USB smart hub controllers, power delivery and charging, transceivers/switches, Flash media controllers and security solutions. For more information visit www.microchip.com/usb and www.microchip.com/ethernet.



MOST® Technology

Media Oriented Systems Transport (MOST) technology is the accepted standard in high-bandwidth automotive infotainment systems. It is broadly standardized from the physical layer up to the application level. Various speed grades and physical layers are available. The highly flexible and scalable MOST platform can transmit A/V streaming, packet, and isochronous and control data. It is also approved to transmit DVD and Blu-ray™ content using Digital Transmission Content Protection (DTCP). For more information visit: www.microchip.com/automotiveproducts.

Embedded Controllers and Super I/O

Microchip's computing-related products include state-of-the-art embedded controllers based on the innovative eSPI bus technology, Input/Output (I/O) devices, keyboard controllers, root of trust, secure boot and authentication devices and system-management devices. These components serve the computing industry, including major OEMs and motherboard manufacturers worldwide. Applications include traditional computing applications such as notebooks and desktops, and embedded computing which is found in a variety of applications such as information kiosks, networking equipment, automatic teller machines and devices for the oil and gas industries. For more information visit: www.microchip.com/computing.

Touch, Multi-Touch and 3D Gesture Control

Microchip offers the most feature-rich solutions in capacitive sensing for applications ranging from single-touch buttons and proximity sensing to touchpads, touch screens and free-space 3D gesture control. Turnkey solutions (maXTouch® technology) as well as MCUs/MPUs solutions (PIC, AVR and SAM) come with Graphical User Interface (GUI) software tools and code configurators for easy design-in cycles that shorten your time to market. For more information please visit: www.microchip.com/touch.

Power over Ethernet (PoE) Systems and ICs

Microchip offers a comprehensive end-to-end portfolio of PoE solutions comprised of PoE ICs and PoE Injectors/Systems. Microchip's PoE ICs product line is the broadest in the market with PSE ICs featuring 1 to 8 ports, presenting the highest integration level and lowest total BOM cost. The PD ICs line provides solutions with and without integrated PWM controllers and is used as a compact way to convert PoE input power to one or more output voltages. The PoE Injectors/Systems line includes stand-alone PoE Injectors/Midspans and Switches ranging from single-port to multi-port solutions. These off-the-shelf products can be added by customers to their portfolio while saving the development efforts on their side. The PoE Injectors support best-of-breed PoE deployments making it easier than ever to install PoE-enabled Ethernet-based devices in both indoor, outdoor and industrial environments. The PoE multi-port injectors increase the flexibility and longevity of Ethernet networks.

FPGAs

Our unique, low-power, non-volatile technology sets Microchip's Field Programmable Gate Arrays (FPGAs) apart from traditional SRAM-based devices. With an extensive heritage of reliability, Microchip's FPGAs and SoCs meet demands for low power, and security in a variety of applications.

In wired and wireless communications, defense and aviation, and industrial embedded applications, Microchip FPGAs deliver ample resources at the lowest power, highest reliability and greatest security. Microchip FPGAs demonstrate value in applications such as hardware acceleration, artificial intelligence, image processing and edge computing with robust DSP and memory resources.

Table of Contents

8-bit PIC Microcontrollers	6	Timing and Communication Products	33
8-bit AVR Microcontrollers	7	Oscillators	33
16-bit Microcontrollers and dsPIC		Clock and Data Distribution	33
Digital Signal Controllers	10	High-Speed Communication	49
32-bit Microcontrollers	13	Memory Products	50
32-bit Microprocessors	16	Wireless Products	55
Analog and Interface Products	18	Wireless Audio	56
Thermal Management	18	USB Products	58
Power Management	18	Ethernet Products	59
Display and LED Drivers	24	Automotive Products	60
High-Voltage Interface	25	Embedded Controllers and Super I/O	62
Linear	27	Security Products	63
Mixed Signal	27	Touch and 3D Gesture Control	63
Interface (CAN)	30	Power Discretes and Modules	65
Interface (LIN)	30	Power over Ethernet	70
Ultrasound	31	FPGA	74
CO and Smoke Detector ICs	32	Terms and Definitions	75
Motor Drivers	32		

8-bit PIC® Microcontrollers

8-bit AVR® Microcontrollers

Product Family		8-bit AVR® Microcontrollers																																						
		Pin Count Range	Program Flash Memory (KB)	Boot Code (KB)	SRAM (B)	EEPROM (B)	Speed (MHz)	Analog				Waveform Control			Timing		Logic, Crypto and Math		Safety and Monitoring		Communications		User Interface		Low Power and System Flexibility															
								ADC (# of bits)	Comparators	ADC Gain Stage	DAC (# of bits)	Temperature Sensors	Internal Voltage Reference	OPAMPs	8-bit PWM	12-bit PWM	16-bit PWM	Quadrature Decoder	Waveform Extension	Real-Time Counter	8-bit Timer/Counters	12-bit Timer Counter	16-bit Timer/Counters	CCL	MULT	Crypto (AES/DES)	GRC	POR	BOD	WDT	UART	USART	USB	I2C	SPI	IRCOM	QTouch® Technology with PTC	LCD	External Bus Interface	DMA Channels
ATtiny4/9	6	0.5–1		0.032			12	✓																															4	SOT-23, UDFN
ATtiny5/10	6	0.5–1		0.032			12	10	✓																														4	SOT-23, UDFN
ATtiny102/ATtiny104	8–14	1		0.032			12	10	✓		✓							2																			4	SOIC 150 mil, UDFN		
ATtiny13A	8–20	1		0.064	0.064	20	10	✓										2																			3 ✓	PDIP, SOIC, SOIC 150 mil, SOJ, VDFN, WQFN		
ATtiny20/40	14–20	2/4		0.128			12	10	✓		✓			2	2	2	1	1																		4	WLCS, SOIC 150 mil, TSSOP, UFBGA, VQFN, SOIC 300 mil			
ATtiny24A/44A/84A	14–20	2/4/08		Up to 0.512	Up to 0.512	20	10	✓	✓	✓	✓	✓	✓	2	2	2	1	1	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	4 ✓	PDIP, SOIC 150 mil, UFBGA, VQFN, WQFN				
ATtiny25(V)/45(V)/85(V)	8–20	2/4/08		Up to 0.512	Up to 0.512	20	10	✓	✓	✓	✓	✓	✓	4				2		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	3	PDIP, SOIC, SOIC 150 mil, SOJ, WQFN, TSSOP						
ATtiny48/88	28–32	4/8		Up to 0.512	0.064	12	10	✓		✓	✓	1	1				1	1			✓	✓	✓										3 ✓	SPDIP, VQFN, TQFP						
ATtiny87/167	20–32	8/16		0.512	0.512	20	10	✓		✓	✓	1	2				1	1	✓		✓	✓	✓	1	1	2									4	SOIC 300 mil, TSSOP, WQFN, VQFN				
ATtiny261A/461A/861A	20–32	2/4/8		Up to 0.512	Up to 0.512	20	10	✓	✓	✓	✓						1	1			✓	✓	✓											4 ✓	PDIP, SOIC 300 mil, TSSOP, VQFN					
ATtiny42X/82X/162X/322X	8–20	4/8/16/32		Up to 2	Up to 0.256	20	12	✓	✓	✓	✓							✓	3	✓	✓	✓	✓	✓	2	1									✓ ✓ 3 ✓	VQFN, SOIC 150 mil, SOIC 300 mil, TSSOP				
ATtiny21X/41X/81X/161X/321X	8–24	2/4/8/16/32		Up to 2	Up to 0.256	20	10	✓		8	✓	✓	8	1	3		✓	1	3	✓	✓	✓	✓	1	1	1	✓							✓ ✓ 3 ✓	VQFN, SOIC 150 mil, SOIC 300 mil					
ATtiny20X/40X/80X/160X	8–24	2/4/8/16		Up to 1	Up to 0.256	20	10	✓		✓	✓	7	3				✓	2	✓	✓	✓	✓	✓	✓	1	1	1							✓ ✓ 3 ✓	VQFN, SOIC 150 mil, SOIC 300 mil					
ATmega80X/160X/320X/480X	28–48	32/48		Up to 6	0.256	20	10	✓		✓	✓	10	3				✓	5	✓	✓	✓	✓	✓	4	1	1	1							✓ ✓ 3 ✓	VQFN, QFN TQFP, SSOP					
ATtiny441/841	14–20	4/8		Up to 0.512	Up to 0.512	16	10	✓	✓	✓	✓	1	2				1	2			✓	✓	✓	2	1	1							4 ✓	SOIC 150 mil, VQFN, WQFN						
ATtiny1634	20	16		1	0.256	12	10	✓		✓	✓	2	2				1	1	✓		✓	✓	✓	2	1								4 ✓	SOIC 300 mil, WQFN						
ATtiny2313A	20	2		0.128	0.128	20	10	✓		✓	✓	2	2				1	1	✓		✓	✓	✓	1	1	2							3 ✓	PDIP, SOIC 300 mil, WQFN						
ATmega8A/16A/32A	32–44	8/16/32		1/1/02	0.5/0.5/1	16	10	✓				2	1				✓	2	1	✓		✓	✓	1	1	1							5	SPDIP, TQFP, VQFN, PDIP						
ATmega8U2/16U2/32U2	32	32	4	2	1	20	10	1		✓	✓	4	6				✓	2	3	✓		✓	✓	✓	2	2	2	✓						6	TQFP, VQFN					
ATmega16U4/32U4	32	8/16/32	4	0.5/0.5/1	0.5/0.5/1	16	10	1		✓	✓	5	-				1	1	✓		✓	✓	✓	1	1	1							6	TQFP, VQFN						
ATmega48PB/88PB/168PB	32	4/8/16	1/1/2	0.5/1/1	0.25/0.5/1	20	10	1		✓	✓	4	2				✓	2	1	✓		✓	✓	1	1	1							6	TQFP, VQFN						
ATmega64A/128A	64	64/128	8	4	2/4	16	10	1	✓		✓	2	6				2	2	✓		✓	✓	✓	2	1	1							6	TQFP, VQFN						
ATmega164PA/324PA/644PA	44	16/64/128	4/4/08	1/4/16	0.5/2/4	20	10	1	✓		✓	4	2/2/4				✓	2	1/1/2	✓		✓	✓	✓	2	1	1						6 ✓	PDIP, TQFP, VQFN, VFPGA						
ATmega165PA/325PA	44	16/32	4	2	1/2	0.5/1	16/30	10	1		✓	2	2				✓	2	1	✓		✓	✓	✓	3	2	2	✓					6 ✓	TQFP, VQFN						
ATmega169PA/329PA	64	16/32	2	1/2	0.5/1	16/30	10	1		✓	✓	2	2				✓	2	1	✓		✓	✓	✓	1	1	1						5	TQFP, VQFN						

1: LIN port also **2:** Peripheral Touch Controller **3:** Only on the ATTiny5/10 **4:** Not on the ATTiny212/214/412/414/416 **5:** Only on the ATmega1281/2561 **6:** Only on the ATmega328PB **7:** Only on the C3 and C4

8-bit AVR® Microcontrollers

Product Family	Pin Count Range	Program Flash Memory (KB)	Boot Code (KB)	SRAM (B)	EEPROM (B)	Speed (MHz)	Analog			Waveform Control			Timing		Logic, Crypto and Math	Safety and Monitoring	Communications		User Interface	Low Power and System Flexibility		Packages							
							ADC (# of bits)		Comparators	DAC (# of bits)		Temperature Sensor	Internal Voltage Reference		OPAMPs		Quadrature Decoder		Waveform Extension		Real-Time Counter		8-bit Timer/Counters		12-bit Timer Counter		16-bit Timer/Counters		
							ADC Gain Stage	DAC Gain Stage																					
ATmega324PB	64	16/32	2	1/2	0.5/1	16/30	10	1		✓	✓	4	6	✓	2	3	✓	2	1	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATmega328PB	32	32	4	2	1	20	10	✓		✓	✓	4	6	✓	2	3	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATmega640/1280/2560	100	64/128/256	8	8	4	16	10	✓	✓		✓	4	6/12	✓	2	4	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TFBGA, TQFP	
ATmega645P	64	64	8	4	2	16	10	✓	✓		✓	2	2	✓	2	1	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATmega649P	64	64	4	4	2	16	10	✓	✓		✓	2	2	✓	2	1	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATmega1281/2561	64	128/256	8	8	4	16	10	✓	✓		✓	4	6/12	✓	2	4	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATmega3250PA	100	32	8	2	1	20	10	✓	✓		✓	2	2	✓	2	1	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP	
ATmega3290A/6490A	100	32/64	4	2/4	1/2	20	10	✓	✓		✓	2	2	✓	2	1	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP		
ATmega3290P/6490P	100	32/64	8	2/4	1/2	20	10	✓	✓		✓	2	2	✓	2	1	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP		
ATmega6450A	100	64	8	4	2	20	10	✓	✓		✓	2	2	✓	2	1	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP	
ATmega6450P	100	64	8	4	2	20	10	✓	✓		✓	2	2	✓	2	1	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP	
ATxmega64A1U/128A1U	100	64/128	4/8	4/8	2	32	12	✓	✓	12	✓	✓		8	✓	✓	✓	8	✓	✓	✓	✓	✓	✓	✓	✓	✓	TFBGA, TQFP, VFBGA	
ATxmega64A3U/128A3U/192A3U/256A3U	64	64/128/192/256	4/8/8/8	4/8/16/16	2/2/2/4	32	12	✓	✓	12	✓	✓		7	✓	✓	✓	7	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATxmega256A3BU	64	256	8	16	4	32	12	✓	✓	12	✓	✓		7	✓	✓	✓	7	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATxmega16A4U/32A4U/64A4U/128A4U	44-49	16/32/64/128	4/4/4/8	2/4/4/8	1/1/2/2	32	12	✓	✓	12	✓	✓		5	✓	✓	✓	5	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN, VFBGA		
ATxmega64B1/128B1	100	64/128	4/8	4/8	2/2	32	12	✓	✓	12	✓	✓		3	✓	✓	✓	3	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VFBGA	
ATxmega64B3/128B3	64	64/128	4/8	4/8	2/2	32	12	✓	✓	12	✓	✓		2	✓	✓	✓	2	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATxmega32D3/64D3/128D3/192D3/256D3/384D3	64	32/64/128/192/256/384	4/4/8/8/8/8	4/4/8/16/16/32	1/2/2/2/4/4	32	12	✓	✓	12	✓	✓		5	✓	✓	✓	5	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN	
ATxmega16D4/32D4/64D4/128D4	44-49	16/32/64/128	4/4/4/8	2/4/4/8	1/1/2/2	32	12			12	✓	✓		4	✓	✓	✓	4	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, VQFN, VFBGA	
ATxmega8E5/16E5/32E5	32	8/16/32	2/4/4	1/2/4	0.5/0.5/1	32	12	✓	✓	12	✓	✓		3	✓	✓	✓	3	✓	✓	✓	✓	✓	✓	✓	✓	TQFP, QFN		
AVR28/32/48/64DAXXX	28-64	32/64/128			4/8/16	512	20	12	✓	10	✓	✓	17	1	6	✓	1	7	✓	✓	✓	✓	✓	✓	✓	✓	VQFN, TQFP, SOIC, SSOP		
AVR28/32/48/64DBXXX	28-64	32/64/128			4/8/16	512	20	12	✓	10	✓	✓	17	1	6	✓	1	7	✓	✓	✓	✓	✓	✓	✓	✓	VQFN, TQFP, SOIC, SSOP		

1: LIN port also 2: Peripheral Touch Controller 3: Only on the ATtiny5/10 4: Not on the ATtiny212/214/412/414/416 5: Only on the ATmega1281/2561 6: Only on the ATmega328PB 7: Only on the C3 and C4

8-bit PIC and AVR MCU Terminology

Intelligent Analog: Sensor Interfacing and Signal Conditioning	
ADC: Analog-to-Digital Converter	General-purpose 10-/12-bit ADC
ADC Gain Stage: Analog-to-Digital Converter Gain Stage	Programmable gain stage, providing amplification steps on the differential input voltage
Comp: Comparator	General-purpose rail-to-rail comparator
DAC: Digital-to-Analog Converter	Programmable voltage reference with multiple internal and external connections
VREF: Voltage Reference	Stable fixed voltage reference for use with integrated analog peripherals
OPAMP: Operational Amplifier	Individual configurable OPAMPs supporting rail-to-rail inputs
Waveform Control: PWM Drive and Waveform Generation	
PWM: Pulse-Width Modulation	General-purpose 10-bit PWM control
16-bit PWM: Standalone 16-bit PWM and 16-bit Timer/Counter	1. High-resolution 16-bit PWM with edge- and center-aligned modes 2. General-purpose 16-bit timer/counter
Timing and Measurements: Signal Measurement with Timing and Counter Control	
8-/12-/16-bit Timer	General-purpose 8-/12-/16-bit timer/counter
Logic, Crypto and Math: Customizable Logic and Math Functions	
CCL: Configurable Custom Logic	1. Integrated combinational and sequential logic 2. Customer interconnection and re-routing of digital peripherals
MULT: Hardware Multiplier	MULTIPLY function of two 8-bit values with 16-bit result
Crypto (AES/DES)	Data encryption and decryption can be easily performed for both internally stored data or for small external data packets
Safety and Monitoring: Hardware Monitoring and Fault Detection	
CRC/SCAN: Cyclical Redundancy Check with Memory Scan	Automatically calculates CRC checksum of Program/DataEE memory for NVM integrity

Communications: General, Industrial, Lighting and Automotive	
USART: Universal Asynchronous Receiver Transmitter	1. General-purpose serial communications 2. Support for LIN/IrDA®
I ² C: Inter-Integrated Circuit	General-purpose 2-wire serial communications
SPI: Serial Peripheral Interface	General-purpose 4-wire serial communications
IRCOM: Infrared Communication Module	Encodes and decodes data according to the IrDA communication protocol
User Interface: Capacitive Touch Sensing and LCD Control	
LCD: Liquid Crystal Display	Highly integrated segmented LCD controller
QTouch® Technology: Microchip Proprietary Touch Technology	Provides a simple-to-use solution to create touch-sensitive interfaces
QTouch Technology with PTC: QTouch Technology with Peripheral Touch Controller	Provides a simple-to-use solution to create touch-sensitive interfaces with a Peripheral Touch Controller
Low Power and System Flexibility: Low-Power Technology, Peripheral and Interconnects	
DMA: Direct Memory Access	Moves data between memories and peripherals without CPU overhead, improving overall system performance and efficiency
Event System	Flexible routing of peripheral events, ability to control peripheral independent from the CPU
External Bus Interface	Highly flexible module for interfacing external memories and memory-addressable peripherals
picoPower® Technology	Low-power technology
Sleep Modes	Low-power saving modes, IDLE, power-down, power-save, standby and extended standby
SleepWalking	Ability to put the CPU core to sleep until a relevant event occurs
MVIO: Multi-Voltage I/O	Ability to have separate supply voltage on selected pins

Product Family		Maximum MIPS		Program Flash Memory (KB)		RAM (KB)		Pin Count		Peripheral Function Focus																Packages																											
										Intelligent Analog				Waveform Control				Timing and Measurements				Safety and Monitoring				Communication				User Interface		Secure Data		System Flexibility																			
										ADC resolution ¹	DAC resolution ²	CVref	HS Comp	OPA/PGA	SCCP	MCCP	PWM	MC PWM	SMPS PWM	IC and OC	PWM Resolution (ns)	16-bit Timer	32-bit Timer	RTCC	QEI	LVD	WDT/WWDAT	DMT	CRC	Class B Safety ³	USB	CAN	UART	LIN	IrDA [®]	i ² C	SPI	I ² S [™]	SENT	Parallel Port	CTMU and mTouch [®] Sensing	LCD (Segments)	GFX	Cryptographic Engine	Secure Key Storage	RNG	Dual Partition Flash	CLC	PPS	PTG	DMA	IDLE, SLEEP and PMD	DOZE
PIC24 Family																																																					
PIC24FJ64GA004	16	16–64	4–8	28–44	10		✓			✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (ML)																	
PIC24FJ64GA104	16	32–64	8	28–44	10		✓			✓		✓	15	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (ML)																	
PIC24FJ64GB004	16	32–64	8	28–44	10		✓			✓		✓	15	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (ML)																	
PIC24FJ128GA010	16	64–128	8	64–100	10		✓			✓		✓	62	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (ML)																	
PIC24FJ256GA110	16	64–256	16	64–100	10		✓			✓		✓	15	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																		
PIC24FJ256GB110	16	64–256	16	64–100	10		✓			✓		✓	15	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																		
PIC24FJ128GA204	16	64–128	8	28–44	12		✓			✓		✓	15	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	SPDIP (SP), SOIC (SO), SSOP (SS), QFN (MM), TQFP (PT), QFN (ML)																	
PIC24FJ128GB204	16	64–128	8	28–44	12		✓			✓		✓	15	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	SPDIP (SP), SOIC (SO), SSOP (SS), QFN (MM), TQFP (PT), QFN (ML)																	
PIC24FJ128GA310	16	64–128	8	64–100	12		✓	✓		✓		✓	15	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																		
PIC24FJ128GC010	16	64–128	8	64–100	16	10	✓	✓		✓		✓	15	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																			
PIC24FJ256DA210	16	128–256	24–96	64–100	10		✓			✓		✓	15	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																		
PIC24FJ256GB210	16	128–256	96	64–100	10		✓			✓		✓	62	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																		
PIC24FJ256GA412	16	64–256	8–16	64–121	12	10	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (ML), XBGA (BG)																			
PIC24FJ256GB412	16	64–256	8–16	64–121	12	10	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (ML), XBGA (BG)																			
PIC24FJ256GA705	16	64–256	16	24–48	12		✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	QFN (ML), UQFN (M6), SOIC (SO), SSOP (SS), SPDIP (SP), TQFP (PT), UQFN (M4)																		
PIC24FJ1024GA610	16	128–1024	32	64–100	12		✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (ML), TFBGA (BG)																		
PIC24FJ1024GB610	16	128–1024	32	64–100	12		✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (ML), TFBGA (BG)																		
dsPIC33EV Family – 5V Operating Range																																																					
dsPIC33EV256GM006	70	32–256	4–16	28–64	12	7	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	SPDIP (SP), SOIC (SO), QFN (MM, ML), TQFP (PT)																		
dsPIC33EV256GM106	70	32–256	4–16	28–64	12	7	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	SPDIP (SP), SOIC (SO), QFN (MM, ML), TQFP (PT)																		
dsPIC33EP Family																																																					
dsPIC33EP64GS2/506	70	16–64	2–8	28–64	12	12	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	SOIC (SO), SSOP (SS), UQFN (M6, MX, 2N), QFN (MM, ML), TQFP (PT)																		
dsPIC33EP128GS808	70	64–128	8	28–80	12	12	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	SOIC (SO), UQFN (2N), QFN (MM, ML), TQFP (PT)																		
dsPIC33EP512GP506	70	32–512	4–48	28–64	12	4	✓	✓		✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	SPDIP (SP), SOIC (SO), QFN (MM, ML, MR), TQFP (PT)																	
dsPIC33EP512MC206	70	32–512	4–48	28–64	12	4	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																		
dsPIC33EP512MC506	70	32–512	4–48	28–64	12	4	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																		
dsPIC33EP512GM310	70	128–512	16–48	44–100	12	4	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	QFN (ML, MR), TQFP (PT, PF), TFBGA (BG)																		
dsPIC33EP512GM6/710	70	128–512	16–48	44–100	12	4	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	QFN (ML, MR), TQFP (PT, PF), TFBGA (BG)																		
dsPIC33EP512MU814	70	256–512	28–52	64–144	12	4	✓			✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT, PF), QFN (MR), LQFP (PL)																		
dsPIC33EP512GP806	70	512	52	64	12	4	✓			✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	TQFP (PT), QFN (MR)																		

1: 16-bit PIC[®] MCU offers SAR ADC, high-speed ADC and Delta-Sigma ADC 2: 16-bit PIC MCU offers general-purpose DAC and audio DAC 3: Class B Safety Features: L1: Includes WDT, oscillator fail-safe, illegal opcode detect, TRAP, reset trace, register lock, frequency check, CodeGuard[™] security, PWM lock* L2: Includes features of L1 + CRC L3: Includes features of L1 + Flash ECC + DMT *PWM lock available in devices with MC PWM/SMPS PWM peripheral

16-bit Microcontrollers and dsPIC® Digital Signal Controllers

1: 16-bit PIC® MCU offers SAR ADC, high-speed ADC and Delta-Sigma ADC **2:** 16-bit PIC MCU offers general-purpose DAC and audio DAC **3:** Class B Safety Features: L1: Includes WDT, oscillator fail-safe, illegal opcode detect, TRAP, reset trace, register lock, frequency check, Code-Guard™ security, PWM lock* L2: Includes features of L1 + CRC L3: Includes features of L1 + Flash ECC + DMT *PWM lock available in devices with MC PWM/SMPS PWM peripheral

16-bit MCUs and DSCs Terminology

Integrated Analog: Sensor Interfacing and Signal Conditioning	
ADC: Analog-to-Digital Converter	General-purpose ADC with up to 10-/12-/16-bit resolution
HS ADC: High-Speed Analog-to-Digital Converter	High-speed SAR ADC with 12-bit resolution and sampling speed of 10 Msps
ΔΣ ADC: Delta-Sigma Analog-to-Digital Converter	Bipolar differential inputs configurable gain integrated PGA Delta-Sigma ADC
DAC: Digital-to-Analog Converter	General-purpose DAC with resolution up 16-bit resolution
ΔΣ DAC: Delta-Sigma Digital-to-Analog Converter	Second-order digital bipolar, two output channel Delta-Sigma DAC with stereo operation support
CV_{REF}: Internal Voltage Reference	Programmable voltage reference with multiple internal and external connections
HS Comp: High-Speed Comparator	General-purpose rail-to-rail comparator with <1 ns response time
OPA: Operational Amplifier	General-purpose op amp for internal and external signal source conditioning
Waveform Control: PWM Drive and Waveform Generation	
CCP/ECCP: (Enhanced) Capture/Compare/PWM	Multi-purpose timers with functionality of the comparable input capture, output compare and PWM with four outputs
SCCP: Single Capture/Compare/PWM	Multi-purpose 16-/32-bit input capture, output compare and PWM
MCCP: Multiple Capture/Compare/PWM	Multi-purpose 16-/32-bit input capture, output compare and PWM with up to six outputs and an extended range of output control features
PWM: Pulse Width Modulation	16-bit PWM with up to nine independent time bases
MC PWM: Motor Control Pulse-Width Modulation	Motor control 16-bit PWM with multiple synchronized pulse-width modulation, up to six outputs with four duty cycle generators and resolution up to 1 ns
SMPS PWM: Power Supply Pulse-Width Modulation	Power supply 16-bit PWM with multiple synchronized pulse-width modulation, up to eight outputs with four independent time bases and resolution up to 1 ns
IC: Input Capture	Input capture with an independent timer base to capture an external event
OC: Output Compare	Output compare with an independent time base to compare value with compare registers and generate a single output pulse, or a train of output pulses on a compare match event
Clocks and Timers: Signal Measurement with Timing and Counter Control	
8-/16-/32-bit Timer	General-purpose 8-/16-/32-bit timer/counter with compare capability
RTCC: Real-Time Clock/Calendar	Real-time clock and calendar with a Binary-Coded Decimal (BCD) clock calendar to maintain accurate timing with external 32.768 kHz crystal
QEI: Quadrature Encoder Interface	Quadrature encoder interface to increment encoders for obtaining mechanical position data
Safety and Monitoring: Hardware Monitoring and Fault Detection	
LVD: Low-Voltage Detection	LVD detects drops in system operating voltage using an internal reference voltage for comparison, especially in battery-powered applications
WDT: Watchdog Timer	System supervisory circuit that generates a reset when software timing anomalies are detected within a configurable critical window
DMT: Dead Man Timer	System supervisory circuit that generates a reset when instruction sequence anomalies are detected within a configurable critical window
CRC: Cyclical Redundancy Check with Memory Scan	Automatically calculates CRC checksum of Program/DataEE memory for NVM integrity and a general-purpose 16-bit CRC for use with memory and communications data
Class B Safety	Hardware Class B support with Flash error correction, backup system oscillator, WDT, DMT, CRC scan, etc.

Communications: General, Industrial, Lighting and Automotive	
USB OTG: Universal Serial Bus	USB 2.0 full-speed (host and device), low-speed (host) and On-The-Go (OTG) support
CAN: Controller Area Network	Industrial- and automotive-centric communication bus
UART: Universal Asynchronous Receiver Transmitter	General-purpose full-duplex, 8-bit or 9-bit data serial communications with optional ISO 7816 Smart Card support
LIN: Local Interconnect Network	1. Industrial- and automotive-centric communication bus 2. Support for LIN when using the EUSART
IrDA®: Infrared Data Association	IrDA encoder and decoder logic support through UART
I²C: Inter-Integrated Circuit	General purpose 2-wire inter IC serial interface for communicating with other peripherals or microcontroller devices
SPI: Serial Peripheral Interface	General-purpose 4-wire synchronous serial interface for communicating with other peripherals or microcontroller devices
I²S: Data Converter Interface	3-wire synchronous half duplex serial interface to handle the stereo data
SENT: Single-Edge Nibble Transmission	SENT is an unidirectional, single-wire serial communications protocol designed for point-to-point transmission of signal values
Parallel Port	General-purpose parallel communication interface
User Interface: Capacitive Touch Sensing and LCD Control	
CTMU and mTouch® Sensing: Microchip Proprietary Capacitive Touch Technology Using Charge Time Measurement Unit	Capacitive sensing for touch buttons, sliders and system measurements and detection (e.g. water level, intrusion detection, etc.) using an analog CTMU that provides accurate differential time measurement between pulse sources and asynchronous pulse generation
LCD: Liquid Crystal Display	Highly integrated segmented LCD controller
GFX: Graphics Controller	Highly integrated graphics controller supporting direct interface with display glasses with built-in analog drive for individual pixel control
Secure Data: Hardware-Integrated Cryptographic Engine	
Cryptographic Engine	Independent NIST-standard encryption and decryption engine
Secure Key Storage	Multiple option for key storage, selection and management
RNG: Random Number Generator	Hardware true random number generation
System Flexibility: System Peripherals and Interconnects	
Dual Partition Flash	Dual partition Flash operation, allowing the support of robust bootloader systems and fail-safe storage of application code, with options designed to enhance code security
CLC: Configurable Logic Cell	Integrated combinational and sequential logic with custom interconnection and re-routing of digital peripherals
PPS: Peripheral Pin Select	I/O pin remapping of digital peripherals for greater design flexibility and improved EMI board layout
PTG: Peripheral Trigger Generator	User-programmable sequencer, capable of generating complex trigger signal sequences to coordinate the operation of other peripherals
DMA: Direct Memory Access	Direct memory access for transfer of data between the CPU and its peripherals without CPU assistance
IDLE, SLEEP and PMD	Low-power saving modes
DOZE	Ability to run the CPU core slower than the system clock used by the internal peripherals
XLP: eXtreme Low Power Technology	XLP technology devices with extreme low-power operation modes for battery/low-power applications
V_{BAT}	Hardware-based power mode that maintains only the most critical operations when a power loss occurs on V _{DD}

32-bit Microcontroller Quick Reference Guide

Product Family	Core	Max. Operation Freq. (MHz)	Program Flash Memory (kB)	RAM (kB)	Pin Count	Peripheral Function Focus																		Packages				
						Intelligent Analog			Waveform Control		Timing and Measurements			Safety and Monitoring		Communication				User Interface		Security		System Flexibility				
PIC32MM GPL	microAptiv	25	16-64	4-8	20-36	14 ^{1/2}	200k	1 ⁵	2	3	3	8	7/3		W		2	2		2				✓	SSOP, SOIC, SPDIP, QFN, UQFN, VQFN			
PIC32MM GP*	microAptiv	25	64-256	16-32	28-64	24 ^{1/2}	200k	1 ⁵	3	9	9	24	21/9		W	1F+P*		3	3	3	3				4 ✓	SSOP, SOIC, SPDIP, QFN, UQFN, VQFN		
PIC32MX 1/2 ⁴ /5 ⁴ *	M4K	50	16-512	4-64	28-100	48 ¹⁰	1M		3	5	5	5	5/2		W	B	1F+P*	1+	5	2	4	4 P ¹⁶				4	SOIC, SSOP, SPDIP, QFN, VTIA, TQFP, TFBGA*	
PIC32MX 1/2 XLP	M4K	72	128-256	32-64	28-44	13 ¹⁰	1M		3	5	5	5	5/2		W+D	B	1F+P		2	2	2	2 P ¹²		P		4	SOIC, QFN, TQFP	
PIC32MX 3/4 ⁴ *	M4K	120	32-512	16-128	64-124	16 ¹⁰	1M		2	5	5	5	5/2		W	B	1F+P*		5	2	2	2 P ¹⁶		P		4	TQFP, QFN, TFBGA, VTIA	
PIC32MX 5	M4K	80	64-512	16-64	64-100	16 ¹⁰	1M		2	5	5	5	5/2		W	B	1F+P	1	6	5	4	P ¹⁶		P		8	QFN, TQFP, TFBGA, VTIA	
PIC32MX 6	M4K	80	64-512	32-128	64-100	16 ¹⁰	1M		2	5	5	5	5/2		W	B	1H+P	1	6	5	4	P ¹⁶		P		8	QFN, TQFP, TFBGA, VTIA	
PIC32MX 7	M4K	80	128-512	32-128	64-100	16 ¹⁰	1M		2	5	5	5	5/2		W	B	1F+P	2	1	6	5	4	P ¹⁶		P		8	QFN, TQFP, TFBGA, VTIA
PIC32MK GP/MC	microAptiv	120	512-1024	128-256	64-100	42 ¹²	16M	3 ¹²	504	12	16	16	14/16	E	W+D	B	2F+P	4	6	6	6	6 P ²⁴		P		✓	13 QFN, TQFP	
PIC32MZ EF ⁽³⁾	M-Class	252	512-2048	128-512	64-144	48 ¹²	18M		2	9	9	9	9/4		W+D	B	1H+P	2	1	6	5	6	✓ 6 P/E ²⁴	P+E	A,S,T		✓	18 QFN, TQFP, TFBGA, VTIA, LQFP
PIC32MZ DA ⁽²⁾	microAptiv	200	1024-2048	256-640	169-288	45 ¹²	18M		2	9	9	9	9/4		W+D	B	1H+P	2	1	6	5	6	1 ✓ 6 P/E ²⁴	G	P+E	A,S,T		✓ 26 LFBGA, LQFP
SAM																												
SAM D09	CM0+	48	8-16	4	14-24	10 ¹²	350k		6	3	4	2/1		W	B		2	2	2	2					6	6 QFN, SOIC		
SAM D10	CM0+	48	8-16	4	14-24	10 ¹²	350k	1 ¹⁰	2	6	3	12	2/1	1	W	B+T		3	3	3	3	P ⁷²				6	6 QFN, SOIC, WLCSP	
SAM D11	CM0+	48	16	4	14-24	10 ¹²	350k	1 ¹⁰	2	6	3	12	2/1	1	W	B+T	1F+P		3	3	3	3	P ⁷²				6	6 QFN, SOIC, WLCSP
SAM D20	CM0+	48	16-256	2-32	32-64	20 ¹²	350k	1 ¹⁰	2	16	8	16	5/2		W	B+T		6	6	6	6	P ²⁵⁶				8	TQFP, QFN, WLCSP, UFBGA	
SAM D21	CM0+	48	32-256	4-32	32-64	20 ¹²	350k	1 ¹⁰	2	18	8	24	5/2	3	W	B+T	1F+P		6	6	6	6	1 P ²⁵⁶				12	12 TQFP, QFN, WLCSP, UFBGA
SAM D21L	CM0+	48	32-64	4-8	32-48	18 ¹²	350k	1 ¹⁰	4	18	13	24	5/2	3	W	B+T		5	5	5	5					12	12 TQFP, QFN	
SAM DA1 ⁽³⁾	CM0+	48	16-64	4-8	32-64	20 ¹²	350k	1 ¹⁰	2	18	8	24	5/2	3	W	B+T	1F+P		6	6	6	6	1 P ²⁵⁶				12	8 TQFP, QFN
SAM L10	CM23	32	16-64	4-16	24-32	10 ¹²	1M	1 ¹⁰	203	6	6	6	3/1		W	B+T		3	3	3	3	P ^{100, D+}	T	✓ ²⁵⁶ 2 ✓		8	8 ✓ SSOP, WLCSP, VQFN, TQFP	
SAM L11	CM23	32	16-64	8-16	24-32	10 ¹²	1M	1 ¹⁰	203	6	6	6	3/1		W	B+T		3	3	3	3	P ^{100, D+}	A,S,T	✓ ✓ ✓ ²⁵⁶ 2 ✓ ✓		8	8 ✓ SSOP, WLCSP, VQFN, TQFP	
SAM L11-KPH	CM23	32	32-64	8-16	24-32	10 ¹²	1M	1 ¹⁰	203	6	6	6	3/1		W	B+T		3	3	3	3	P ^{100, D+}	A,S,T	✓ ✓ ✓ ²⁵⁶ 2 ✓ ✓ ✓		8	8 ✓ VQFN, TQFP	

Note 1: USARTs with SPI mode are taken into account Note 2: DRAM Memory Support: PIC32MZ DA with DDR2 (32 MB embedded or 128 MB external); SAM S7x/E7x/V7x with SDRAM (external) Note 3: Automotive Grade Devices Note 4: Terminology in following table Note 5: SAM C20/C21 are true 5V devices; SAM C21 also comes with 3x 16-bit Delta-Sigma ADC *: Variants with USB function +: Variants with CAN function

32-bit Microcontroller Quick Reference Guide

Product Family	Core	Max. Operation Freq. (MHz)	Program Flash Memory (kB)	RAM (kB)	Pin Count	Peripheral Function Focus																		Packages									
						Intelligent Analog			Waveform Control			Timing and Measurements			Safety and Monitoring			Communication			User Interface			Security			System Flexibility						
SAM L21	CM0+	48	32-256	4-32	32-64	20 ¹²	1M	2 ¹²	203	24	8	24	5/2	2		W	B+T	1 ^{F+P}	6	6	6	6	P ¹⁶⁹		A,T		12 16 ✓	TQFP, QFN, WLCSP					
SAM L22	CM0+	32	64-256	8-32	48-100	20 ¹²	1M		2	12	8	12	4/2	1		W	B+T	1 ^{F+P}	6	6	6	6	P ²⁵⁶	S ³²⁰	A,T	✓	8 16 ✓	TQFP, QFN, WLCSP, UFBGA					
SAM C20	CM0+	48	32-256	4/32	32-64	12 ¹²	1M		2	14	6	18	5/2	2		W	B+T		4	4	4	4	P ²⁵⁶				6 6 ✓	TQFP, QFN, WLCSP					
SAM C21 ^(*)	CM0+	48	32-256	4-32	32-100	20 ¹²	1M	1 ¹⁰	4	18	8	24	5/2	2		W	B+T	2 ^{FD}	8	8	8	8	P ²⁵⁶				12 12 ✓	TQFP, QFN, WLCSP					
SAM4N	CM4	100	512-1024	64-80	48-100	16 ¹⁰	510k	1 ¹⁰		18	12	4	2/-		D	W		3/4	3	4						23	LQFP, TFBGA, VFBGA, QFN						
SAM4S	CM4	120	128-2048	64-160	48-100	16 ¹²	1M	2 ¹²	1	18	12	4	2/-		D	W	1 ^{F+P}	2/2	2	3	1	✓	1	E ²⁴		✓	14 22	LQFP, TFBGA, VFBGA, QFN, WLCSP					
SAM4E	CM4F	120	512-1024	128	100-144	24 ¹²	300k	2 ¹²	1	24	18	4	-/3		D	W	1 ^{F+P}	2	1	2/2	2	3	1	✓	E ²⁴		E	33	LFBGA, TFBGA, LQFP				
SAM4L	CM4	48	128-512	32-64	48-100	16 ¹²	300k	1 ¹⁰	4	18	12	5	2/-			W	1 ^{F+P}	4/1	4	5	✓	1	P ³²	S ¹⁶⁰	A,T	✓	4 16	LQFP, WLCSP					
SAM G	CM4F	120	256-512	64-176	49-100	8 ¹²	500k		6	6	6	2/-			W	1 ^{F+P}	8	8	8	8	2				✓	6 30	LQFP, QFN, WLCSP						
SAM D5x	CM4F	120	256-1024	128-256	64-128	32 ¹²	1M	2 ¹²	2	25	16	24	8/4	2	D	W	B+T	1 ^{F+P}	8	8	8	8	2	✓	✓	1	P ²⁵⁶	A,S,E,R,T	✓	✓	32 32 ✓	TQFP, QFN, WLCSP	
SAM E5x	CM4F	120	256-1024	128-256	64-128	32 ¹²	1M	2 ¹²	2	25	16	24	8/4	2	D	W	B+T	1 ^{F+P}	2 ^{FD}	1	8	8	8	2	✓	✓	1	P ²⁵⁶	A,S,E,R,T	✓	✓	32 32 ✓	TQFP, QFN
SAM S7x ⁽²⁾	CM7	300	512-2048	256-384	64-144	24 ¹²	1.7M	2 ¹²	1	44	24	8	4/-		D	W	1 ^{H+P}	3/5	3	5	1	✓	✓	2	E ²⁴		E	A,S,T	✓	12 24	LQFP, LFBGA, TFBGA, UFBGA, VFBGA, QFN		
SAM E7x ⁽²⁾	CM7	300	512-2048	256-384	64-144	24 ¹²	1.7M	2 ¹²	1	44	24	8	4/-		D	W	1 ^{H+P}	2 ^{FD}	1	3/5	3	5	1	✓	✓	2	E ²⁴		E	A,S,T	✓	12 24	LQFP, LFBGA, TFBGA, UFBGA
SAM V7x ⁽²⁾⁽³⁾	CM7	300	512-2048	256-384	64-144	24 ¹²	1.7M	2 ¹²	1	44	24	8	4/-		D	W	1 ^{H+P}	2 ^{FD}	1	3/5	3	5	1	✓	✓	2	E ²⁴		E	A,S,T	✓	12 24	LQFP, TFBGA, LFBGA

Note 1: USARTs with SPI mode are taken into account Note 2: DRAM Memory Support: PIC32MZ DA with DDR2 (32 MB embedded or 128 MB external); SAM S7x/E7x/V7x with SDRAM (external) Note 3: Automotive Grade Devices Note 4: Terminology in following table Note 5: SAM C20/C21 are true 5V devices; SAM C21 also comes with 3x 16-bit Delta-Sigma ADC *: Variants with USB function +: Variants with CAN function

32-bit MCUs Terminology

Timing and Measurements: Signal Measurement With Timing and Counter Control	
TCC: Timer/Counters for Control	Selected SAM products have TCCs for applications like Switch Mode Power Supplies (SMPS), lighting and motor control. The TCCs support up to 96 MHz and 24-bit resolution.
QEI: Quadrature Encoder Interface QDEC: Quadrature Decoder	QEI to increment encoders for obtaining mechanical position data typical for automation or motor control applications. QDEC performs the input lines filtering, decoding of quadrature signals and connects to the timers/counters in order to read the position and speed of the motor through the user interface.
Communications: General, Industrial, Lighting and Automotive	
SERCOM: Serial Communication Module	The SERCOM is software that is configurable to operate as I2C, SPI or USART, giving you extended flexibility to mix serial interfaces and greater freedom in PCB layout. Each SERCOM instance can be assigned to different I/O pins through I/O multiplexing, further increasing versatility.
I2S: Inter-IC Sound Controller	The Inter-IC Sound Controller provides a bidirectional, synchronous digital audio link with external audio devices.
PMP: Parallel Master Port EBI: External Bus Interface	PMP/EBI provide a high-speed and convenient interface to external parallel memory devices, graphic LCDs and camera sensors.
Safety and Monitoring: Hardware Monitoring and Fault Detection	
DMT: Dead Man Timer	The primary function of the DMT is to reset the processor in the event of a software malfunction. A DMT is typically used in mission-critical and safetycritical applications, where any single failure of a software functionality and sequencing must be detected.
User Interface: Capacitive Touch Sensing and LCD Control	
PTC: Peripheral Touch Controller	An embedded peripheral touch controller makes it easy to add capacitive touch sensing to your project with buttons, sliders, wheels and proximity. By offering superb sensitivity and noise tolerance as well as self-calibration, the PTC eliminates the need for external components and minimizes CPU overhead. The PTC supports up to 256 channels on 64-pin devices, 120 channels on 64-pin devices and 60 channels on 32-pin devices. PTC with Driven Shield + can achieve better noise immunity and moisture tolerance.

Development Tools

PIC32 and SAM Products

Tool	Description
MPLAB® X IDE	MPLAB® X is the Integrated Development Environment (IDE) for developing and debugging PIC32 and SAM MCU applications, in addition to Microchips 8- and 16-bit Microcontrollers. It is based on the open-source NetBeans IDE from Oracle and runs under Windows®, Mac OS® and Linux®, and connects seamlessly to a range of debuggers, programmers and development kits.
MPLAB Harmony Configurator	The MPLAB Harmony Configurator (MHC) is a time-saving hardware configuration utility for MPLAB Harmony, Microchip's award winning software framework. Developers use MHC to get visual understanding and control of the configuration of their target device and application. MHC is a fully integrated tool within MPLAB X IDE.
MPLAB Harmony Software Framework	MPLAB Harmony is a flexible, abstracted, fully integrated firmware development platform for PIC32 and SAM microcontrollers. It takes key elements of modular and object oriented design, adds in the flexibility to use a Real-Time Operating System (RTOS) or work without one. MPLAB Harmony provides a framework of software modules that are easy to use, configurable for your specific needs, and in a format that allows for maximum re-use and reduces time to market.
MPLAB Harmony Graphics Suite	MPLAB Harmony Graphics Suite is Microchip's industry-leading graphics toolset for PIC32 and SAM Microcontrollers. Providing a fully-integrated easy to use WYSIWYG editor, graphics asset management and code generator within the MPLAB Harmony framework, the suite allows you to go from concept to glass in minutes without writing a single line of code. Additionally the integrated Display Manager plug-in enables quick support for new and unsupported displays in MPLAB Harmony.
Touch Interface	MPLAB Harmony supports both capacitive and resistive touch. With automatic generation and configuration of event handlers for touch events, it allows quick development of touch enabled graphics solutions.

System Flexibility: System Peripherals and Interconnects	
CLC/CCL: Configurable Custom Logic	The CCL is a programmable logic peripheral which can be connected to the device pins, events or to other internal peripherals. This allows you to eliminate logic gates for simple glue logic function on the PCB.
EVSYS: Event System	The Event System allows autonomous, low-latency and configurable communication between peripherals. Several peripherals can be configured to generate and/or report to signals known as events. Communication is made without CPU intervention and without consuming system resources such as Bus or RAM bandwidth. This reduces the load on the CPU and other system resources, compared to a traditional interrupt-based system.
Dual Panel/Bank Flash	Dual Bank Flash allows live field firmware/program update on one bank while CPU can continue executing code from another Flash bank.
Security: Chip-Level Security, Crypto Acceleration, Secure Key Provisioning and Storage and Tamper Detection	
TrustZone	TrustZone® for ARMv8-M provides hardware-enforced security isolation between trusted and the untrusted resources on a Cortex™-M23 based device, while maintaining the efficient exception handling.
TrustRAM	TrustRAM provides secure key storage against software attacks and can resist microprobing. It also prevents data remanence and facilitates rapid erase on tamper event.
DataFlash	DataFlash provides secure key storage against software attacks. It also allows data scrambling and facilitates rapid erase on tamper event.
Secure Boot	Secure Boot authenticates the Flash content at startup and ensures the desired code is executed.
Kinibi-M	A modular secure application development framework that makes implementation of security simple.

SAM Products

Tool	Description
Atmel Studio 7	Atmel Studio 7 is the Integrated Development Platform (IDP) for developing and debugging AVR® and Arm®-based SAM MCU applications. Atmel Studio 7 provides you with a seamless easy-to-use environment to develop and debug applications written in C/C++ or assembly code. It connects seamlessly to a range of debuggers, programmers and development kits.
Atmel START	Atmel START is an innovative online tool for intuitive, graphical configuration and deployment of embedded software. It lets you select and configure software components, drivers and middleware, as well as deploy complete example projects tailored to the needs of your application. Atmel START is completely platform independent, and able to generate project files for a number of IDEs. The configuration engine lets you review dependencies between software components and available hardware resources in the selected MCU, and automatically suggests solutions to any conflicts that in your chosen setup.
ASF Software Framework for SAM	ASF provides software drivers and libraries to build applications for AVR and SAM devices. It is architected for readability and performance, and contains a number of advanced middleware components for 32-bit SAM devices such as USB device, TCP/IP, Wi-Fi, RTOS kernel (FreeRTOS), Bluetooth, file system and more.
Data Visualizer	Track and profile your applications run-time behavior using the powerful Data Visualizer. It provides an oscilloscope view of signals such as GPIO, SPI, UART, etc. The Data Visualizer also provides live power measurements when used together with a supported probe or board, such as the power debugger. Profiling your applications power usage has never been easier.
QTouch® Composer	The QTouch Composer allows you to seamlessly develop capacitive touch functionality for your application. This simplifies the design process by tying together the tools required to edit the code in Studio 7 and tune the touch design in QTouch Composer.

32-bit Microprocessors

Product	Core Sub-System				Memory												Connectivity						User Interface				Security			Control			Extended Temperature Range (-40 to 105°C Ambient)										
	Core	VFPU/NEON/Trustzone	Clock Speed (MHz) ^a	Core Operating Voltage	Memory												Connectivity						User Interface				Security			Control													
					L1 Cache Memory (KB) (Instruction/Data)			L2 Cache (KB)			NAND			USB			Ethernet			LCD Overlay		Graphic LCD		Camera Interface		Secure Boot		Environmental Monitors		Control													
	DDR Bus Width 16/32	SLC ECC (bit)	MLC ECC (bit)	UART	SPI	TWI (I ² C)	SSC (and I ² S ^m)	CAN	Device Only	Device and Host	Host Only	10/100 Ethernet MAC	10/100/1000 MAC	IEEE 1588 Support	SD/eMMC	Class D/PDM/Audio PLL	Max I/O Pins	Graphic LCD	LCD Overlay	Resistive (R) and/or PCAP (P) Touchscreen	Hardware Video Decoder	Camera Interface	Security Level	Secure Boot	Anti-Tamper Pins	Environmental Monitors	32-bit Timers	PWM Channels	10-bit ADC Channels	12-bit ADC Channels													
ATSAMA5D21	Cortex®-A5	1/1/1	500	1.2V	128	2 × 32	128	-	1 HS	1 HS	1 HS	1 - Y	1	1/1/1	72	1	Y	R	-	1	Adv.	Y	6	-	5	4	-	12	-	BGA 196, 11 × 11, 0.75 mm pitch													
ATSAMA5D22	Cortex-A5	1/1/1	500	1.2V	128	2 × 32	128	-	2	1/1/1	1/1/1	16	32	32	9	6	6	4	1	-	1 HS	1 HS	1 - Y	1	1/1/1	72	1	Y	R, P	-	1	Adv.	Y	6	-	12	Y	BGA 196, 11 × 11, 0.75 mm pitch					
ATSAMA5D23	Cortex-A5	1/1/1	500	1.2V	128	2 × 32	128	-	2	1/1/1	1/1/1	16	32	32	9	6	6	4	1	-	1 HS	1 HS	1 - Y	1	1/1/1	72	1	Y	R, P	-	1	PCI Pre-certified	Y	6	Y	5	4	-	12	Y	BGA 196, 11 × 11, 0.75 mm pitch		
ATSAMA5D24	Cortex-A5	1/1/1	500	1.2V	128	2 × 32	128	-	2	1/1/1	1/1/1	32	32	32	10	7	7	4	-	-	1 HS	1 HS	1 - Y	2	1/1/1	105	1	Y	R, P	-	1	Med.	Y	2	-	6	4	-	12	-	BGA 256, 8 × 8, 0.4 mm pitch		
ATSAMA5D26	Cortex-A5	1/1/1	500	1.2V	128	2 × 32	128	-	2	1/1/1	1/1/1	32	32	32	10	7	7	4	-	-	1 HS	1 HS	1 - Y	2	1/1/1	128	1	Y	R	-	1	Adv.	Y	8	-	6	4	-	12	Y	BGA 289, 14 × 14, 0.8 mm pitch		
ATSAMA5D27	Cortex-A5	1/1/1	500	1.2V	128	2 × 32	128	-	2	1/1/1	1/1/1	32	32	32	10	7	7	4	2	-	1 HS	1 HS	1 - Y	2	1/1/1	128	1	Y	R, P	-	1	Adv.	Y	8	-	6	4	-	12	Y	BGA 289, 14 × 14, 0.8 mm pitch		
ATSAMA5D28	Cortex-A5	1/1/1	500	1.2V	128	2 × 32	128	-	2	1/1/1	1/1/1	32	32	32	10	7	7	4	2	-	1 HS	1 HS	1 - Y	2	1/1/1	128	1	Y	R, P	-	1	PCI Pre-certified	Y	8	Y	6	4	-	12	Y	BGA 289, 14 × 14, 0.8 mm pitch		
ATSAMA5D31	Cortex-A5	1/-/-	536	1.2V	128	2 × 32	-	-	1/1/1	-	32	24	24	7	6	3	2	-	-	1 HS	2 HS	1 - Y	3	-	160	1	Y	R	-	1	Med.	Y	-	-	5	4	-	12	-	BGA 324, 15 × 15, 0.8 mm pitch, BGA 324, 12 × 12, 0.5 mm pitch			
ATSAMA5D33	Cortex-A5	1/-/-	536	1.2V	128	2 × 32	-	-	1/1/1	-	32	24	24	5	6	3	2	-	-	1 HS	2 HS	-	1 Y	2	-	160	1	Y	R	-	1	Med.	Y	-	-	5	4	-	12	-	BGA 324, 15 × 15, 0.8 mm pitch.		
ATSAMA5D34	Cortex-A5	1/-/-	536	1.2V	128	2 × 32	-	-	1/1/1	-	32	24	24	5	6	3	2	2	-	1 HS	2 HS	-	1 Y	3	-	160	1	Y	R	-	1	Med.	Y	-	-	5	4	-	12	-	BGA 324, 15 × 15, 0.8 mm pitch		
ATSAMA5D35	Cortex-A5	1/-/-	536	1.2V	128	2 × 32	-	-	1/1/1	-	32	24	24	7	6	3	2	2	-	1 HS	2 HS	1	1 Y	3	-	160	-	-	R	-	1	Med.	Y	-	-	6	4	-	12	Y	BGA 324, 15 × 15, 0.8 mm pitch		
ATSAMA5D36	Cortex-A5	1/1/1	536	1.2V	128	2 × 32	-	-	1/1/1	-	32	24	24	7	6	3	2	2	-	1 HS	2 HS	1	1 Y	3	-	160	1	Y	R	-	1	Med.	Y	-	-	6	4	-	12	Y	BGA 324, 15 × 15, 0.8 mm pitch		
ATSAMA5D41	Cortex-A5	1/1/1	600	1.8V	128	2 × 32	128	-	1/1/1	-	32	24	24	8	8	4	2	-	-	1 HS	2 HS	2	-	Y	2	-	152	1	Y	R	-	1	Adv.	Y	8	-	9	4	5	-	-	BGA 289, 14 × 14, 0.8 mm pitch.	
ATSAMA5D42	Cortex-A5	1/1/1	600	1.8V	128	2 × 32	128	-	1/1/1	-	32	24	24	8	8	4	2	-	-	1 HS	2 HS	2	-	Y	2	-	152	1	Y	R	-	1	Adv.	Y	8	-	9	4	5	-	-	BGA 361, 16 × 16, 0.8 mm pitch	
ATSAMA5D43	Cortex-A5	1/1/1	600	1.8V	128	2 × 32	128	-	1/1/1	-	32	24	24	8	8	4	2	-	-	1 HS	2 HS	2	-	Y	2	-	152	1	Y	R	30 fps, 720p	1	Adv.	Y	8	-	9	4	5	-	-	BGA 289, 14 × 14, 0.8 mm pitch	
ATSAMA5D44	Cortex-A5	1/1/1	600	1.8V	128	2 × 32	128	-	1/1/1	-	32	24	24	8	8	4	2	-	-	1 HS	2 HS	2	-	Y	2	-	152	1	Y	R	30 fps, 720p	1	Adv.	Y	8	-	9	4	5	-	-	BGA 361, 16 × 16, 0.8 mm pitch	
ATSAMA5D27-C-D1G	Cortex-A5	1/1/1	500	1.1V-1.32V	128	32/32	128	-	2	128	-	2	32	32	10	7	7	2/2	2	-	1 HS	1 HS, 1 HSIC	1	-	Y	2	1/1/1	128	1	Y	Y	-	1	Adv.	Y	8	-	6	4	-	12	-	BGA 289, 14 × 14, 0.8 mm pitch.
ATSAMA5D27-C-D5M	Cortex-A5	1/1/1	500	1.1V-1.32V	128	32/32	128	-	2	64	-	2	32	32	10	7	7	2/2	2	-	1 HS	1 HS, 1 HSIC	1	-	Y	2	1/1/1	128	1	Y	Y	-	1	Adv.	Y	8	-	6	4	-	12	-	BGA 289, 14 × 14, 0.8 mm pitch
ATSAMA5D28-C-D1G	Cortex-A5	1/1/1	500	1.1V-1.32V	128	32/32	128	-	2	128	-	2	32	32	10	7	7	2/2	2	-	1 HS	1 HS, 1 HSIC	1	-	Y	2	1/1/1	128	1	Y	Y	-	1	PCI Pre-certified	Y	8	-	6	4	-	12	-	BGA 289, 14 × 14, 0.8 mm pitch
ATSAMA5D225-C-D1M	Cortex-A5	1/1/1	500	1.1V-1.32V	128	32/32	128	-	2	16	-	2	32	32	9	7	7	2/2	1	-	1 HS	1 HS, 1 HSIC	1	-	Y	2	1/1/1	90	1	Y	Y	-	1	Adv.	Y	6	-	5	4	-	12	-	BGA 196, 11 × 11, 0.75 mm pitch
ATSAMA5D27-SOM1	Cortex-A5	1/1/1	500	3.3V	128	32/32	128	-	1	128	-	-	8	6	5	1	2	-	-	1 HS	1 HS, 1 HSIC	1	-	Y	2	1/1/1	103	1	Y	Y	-	1	Adv.	Y	7	-	5	4	-	4	-	Module 176, 40 × 38, 0.8 mm pitch.	

* Clock speed: Max. clock speed @ +85°C. Notes: 1. Temperature Range: -40°C to +85°C (ambient) 2. UART: Support for RS485, ISO7816, IrDA®, LIN, modem control lines and SPI on selected UARTs. 3. TWI: Two-Wire Interface; interconnects components on a two-wire bus. 4. SSC: Serial Synchronous Controller, supports many serial synchronous communications protocols used in audio and telecom applications such as I²S, short or long frame sync. 5. 16-bit and 32-bit Timers: Capture/compare, waveform generation and PWM modes. 6. ECC: Error Correction Code controller. 7. Security level: Adv. = hardware encryption engine + on the fly DDR encryption/decryption + secure storage + tamper pins; Med. = hardware encryption engine only. 8. Y = Yes 9. Camera Interface: For CMOS-type image sensor, ITU-R BT.601/656 external interface, programmable frame capture rate, up to 12-bit data interface, SAV and EAV synchronization, preview path with scaling, output is in YCbCr format; Bayer RAW is supported on the ATSAMA5D2 series. 10. Graphics LCD: 24-bit parallel interface; supports STN and TFT displays, up to 16-bits per pixel in STN color mode, up to 16M colors in TFT mode. 11. Video Decoder: Hardware video decoding and image post processing: H.264, MPEG4, H.263, MPEG2, JPEG, VP8. 12. eMMC™: V4.3 – MLC NAND Flash supported through eMMC interface; V4.5 support for the ATSAMA5D2 series. 13. USB: High speed (HS), Full Speed (FS), High Speed Inter-Chip (HSIC) 14. Peripheral implementation varies among products. Consult individual product datasheets for a detailed description.

Product	32-bit Microprocessors																											Packages																																
	Core Sub-System			Memory						Connectivity										User Interface			Security		Control																																			
	Core	Clock Speed (MHz)*	Core Operating Voltage	SRAM (KB)	L1 Cache Memory (KB) (Instruction/Data)		LPSDR/SDRAM	External Bus Interface	DDR2/LPDDR/LPDDR2		NAND		UART		SPI		TWI (I ² C)		SSC (I ² S)		CAN		Device Only		Device and Host		Host Only		Ethernet 10/100 Ethernet MAC		SD/eMMC		Soft Modem		Max I/O Pins		Graphic LCD		LCD Overlay		Resistive Touchscreen		Hardware Video Decoder		Camera Interface		Security Level		Secure Boot		16-bit Timers		32-bit Timers		PWM Channels		10-bit ADC Channels			
	ATSAM9																																																											
ATSAM9M10/M11	ARM926EJ-S	400	1.0V	64	2 × 32	1/1	2	1/1/-	1	-	5	6	2	2	-	-	1 HS	2 HS	1	2	-	160	1	Y	Y	30fps, D1	1	Med. (M11)	-	6	-	4	8	BGA 324, 15 × 15, 0.8 mm pitch																										
ATSAM9G45/G46	ARM926EJ-S	400	1.0V	64	2 × 32	1/1	2	1/1/-	1	-	5	6	2	2	-	-	1 HS	2 HS	1	2	-	160	1	-	Y	-	1	Med. (G46)	-	6	-	4	8	BGA 324, 15 × 15, 0.8 mm pitch																										
ATSAM9X35	ARM926EJ-S	400	1.0V	32	2 × 16	1/1	1	1/1/-	24	24	7	5	3	1	2	-	1 HS	1 HS, 1 FS	1	2	Y	105	1	Y	Y	-	-	-	-	-	6	4	12	BGA 217, 15 × 15, 0.8 mm pitch																										
ATSAM9X25	ARM926EJ-S	400	1.0V	32	2 × 16	1/1	1	1/1/-	24	24	7	6	3	1	2	-	1 HS	1 HS, 1 FS	2	2	Y	105	-	-	-	-	-	-	-	-	6	4	12	BGA 217, 15 × 15, 0.8 mm pitch																										
ATSAM9G35	ARM926EJ-S	400	1.0V	32	2 × 16	1/1	1	1/1/-	24	24	6	5	3	1	-	-	1 HS	1 HS, 1 FS	1	2	Y	105	1	Y	Y	-	-	-	-	-	6	4	12	BGA 217, 15 × 15, 0.8 mm pitch																										
ATSAM9G25	ARM926EJ-S	400	1.0V	32	2 × 16	1/1	1	1/1/-	24	24	7	6	3	1	-	-	1 HS	1 HS, 1 FS	1	2	Y	105	-	-	-	-	-	1	-	-	-	6	4	12	BGA 217, 15 × 15, 0.8 mm pitch, BGA 247, 10 × 10, 0.5 mm pitch																									
ATSAM9G15	ARM926EJ-S	400	1.0V	32	2 × 16	1/1	1	1/1/-	24	24	5	5	3	1	-	-	1 HS	1 HS, 1 FS	-	2	Y	105	1	Y	Y	-	-	-	-	-	6	4	12	BGA 217, 15 × 15, 0.8 mm pitch																										
ATSAM9CN12	ARM926EJ-S	400	1.0V	32	2 × 16	1/1	1	1/1/-	24	24	7	6	2	1	-	-	1 FS	-	1 FS	-	1	-	105	1	-	Y	-	-	Med.	Y	6	-	4	12	BGA 217, 15 × 15, 0.8 mm pitch, BGA 247, 10 × 10, 0.5 mm pitch																									
ATSAM9CN11	ARM926EJ-S	400	1.0V	32	2 × 16	1/1	1	1/1/-	24	24	7	6	2	1	-	-	1 FS	-	1 FS	-	1	-	105	1	-	Y	-	-	-	-	-	6	-	4	12	BGA 217, 15 × 15, 0.8 mm pitch, BGA 247, 10 × 10, 0.5 mm pitch																								
ATSAM9N12	ARM926EJ-S	400	1.0V	32	2 × 16	1/1	1	1/1/-	24	24	7	6	2	1	-	-	1 FS	-	1 FS	-	1	-	105	1	-	Y	-	-	-	-	-	6	-	4	12	BGA 217, 15 × 15, 0.8 mm pitch, BGA 247, 10 × 10, 0.5 mm pitch																								
ATSAM9G20	ARM926EJ-S	400	1.0V	32	2 × 32	-/1	1	-	1	-	7	6	1	1	-	-	1 FS	-	2 FS	1	1	-	96	-	-	-	-	-	Y	-	-	-	6	-	4	BGA 217, 15 × 15, 0.8 mm pitch																								
ATSAM9G10	ARM926EJ-S	266	1.2V	16	2 × 16	-/1	1	-	1	-	4	5	1	3	-	-	1 FS	-	2 FS	-	1	-	96	1	-	-	-	-	-	-	-	3	-	-	BGA 217, 15 × 15, 0.8 mm pitch																									
ATSAM9263	ARM926EJ-S	240	1.3V	96	2 × 16	-/1	2	-	1	-	4	5	1	2	1	1 FS	-	2 FS	1	2	-	160	1	-	-	-	-	Y	-	-	3	-	4	-	BGA 324, 15 × 15, 0.8mm pitch																									
ATSAM9261	ARM926EJ-S	190	1.2V	160	2 × 16	-/1	1	-	1	-	4	5	1	3	-	-	1 FS	-	2 FS	-	1	-	96	1	-	-	-	-	-	-	-	3	-	-	BGA 217, 15 × 15, 0.8 mm pitch																									
ATSAM9260	ARM926EJ-S	190	1.2V	8	2 × 8	-/1	1	-	1	-	7	6	1	1	-	-	1 FS	-	2 FS	1	1	-	96	-	-	-	-	-	Y	-	-	6	-	-	4	BGA 217, 15 × 15, 0.8 mm pitch, QFP 208, 28 × 28, 0.5 mm pitch																								

* Clock speed: Max. clock speed @ +85°C. Notes: 1. Temperature Range: -40°C to +85°C (ambient) 2. UART: Support for RS485, ISO7816, IrDA, LIN, modem control lines and SPI on selected UARTs. 3. TWI: Two-Wire Interface; interconnects components on a two-wire bus. 4. SSC: Serial Synchronous Controller, supports many serial synchronous communications protocols used in audio and telecom applications such as I²S, short or long frame sync. 5. 16-bit and 32-bit Timers: Capture/compare, waveform generation and PWM modes. 6. ECC: Error Correction Code controller. 7. Security level: Adv. = hardware encryption engine + on the fly DDR encryption/decryption + secure storage + tamper pins; Med. = hardware encryption engine only. 8. Y = Yes 9. Camera Interface: For CMOS-type image sensor, ITU-R BT, 601/656 external interface, programmable frame capture rate, up to 12-bit data interface, SAV and EAV synchronization, preview path with scaling, output is in YCbCr format; Raw Bayer is supported on the ATSAM4D2 series. 10. Graphics LCD: 24-bit parallel interface; supports STN and TFT displays, up to 16-bits per pixel in STN color mode, up to 16M colors in TFT mode. 11. Video Decoder: Hardware video decoding and image post processing: H.264, MPEG4, H.263, MPEG2, JPEG, VP8. 12. eMMC™: V4.3 – MLC NAND Flash supported through eMMC interface; V4.5 support for the ATSAM4D2 series. 13. USB: High speed (HS), Full Speed (FS), High Speed Inter-Chip (HSIC) 14. Peripheral implementation varies among products. Consult individual product datasheets for a detailed description.

Thermal Management: Temperature Sensors

Product	Description	# Temps. Monitored	Typical/Max Accuracy (°C)	Temp. Range (°C)	Vcc Range (V)	Typical Supply Current (µA)	Alerts	Resistance Error Correction	Beta Compensation	Packages
MCP9501/2/3/4	Temperature Switch Replacing MAX6501/2/3/4	1	1.0/3.0	-40 to +125	+2.7 to +5.5	25	-	-	-	5-pin SOT-23
MCP9509/10	Resistor-Programmable Temperature Switch	1	0.5/3.5	-40 to +125	+2.7 to +5.5	30	-	-	-	5-pin SOT-23
MCP9800/1/2/3	SMBus/I ² C Temperature Sensor	1	0.5/1.0	-55 to +125	+2.7 to +5.5	200	1	-	-	5-pin SOT-23
MCP9804	SMBus/I ² C Temperature Sensor	1	0.25/1.0	-40 to +125	+2.7 to +5.5	200	1	-	-	8-pin DFN, 8-pin MSOP
MCP9808	SMBus/I ² C Temperature Sensor	1	0.25/0.5	-40 to +125	+2.7 to +5.5	200	1	-	-	8-pin DFN, 8-pin MSOP
MCP98244	SMBus/I ² C Temperature Sensor with EEPROM	1	0.5/3.0	-40 to +125	+2.2 to +3.6	100	1	-	-	8-pin TDFN
MCP9902/3/4	Lower Temperature Multi-Temperature Sensors	2/3/4	0.25/1.0	-40 to +125	+3.0 to +3.6	200	1	✓	Automatic	8-pin WDFN, 10-pin VDFN
TCN75A	SMBus/I ² C Temperature Sensor	1	0.5/3.0	-40 to +125	+2.7 to +5.5	200	1	-	-	8-pin MSOP, 8-pin SOIC
AT30TS74	SMBus/I ² C Temperature Sensor	1	1.0/2.0	-55 to +125	+1.7 to +5.5	160	-	-	-	4/5 ball WL CSP
AT30TS750A	SMBus/I ² C Temperature Sensor with NVM	1	0.5/1.0	-55 to +125	+1.7 to +5.5	150	-	-	-	8-pin SOIC, 8-pin MSOP, 8-pin UDFN
AT30TS752A/4A/8A	SMBus/I ² C Temperature Sensor with NVM, 2/4/8 KB Serial EEPROM	1	0.5/1.0	-55 to +125	+1.7 to +5.5	150	-	-	-	8-pin SOIC, 8-pin MSOP, 8-pin UDFN
MCP9700/01	Linear Active Thermistor IC	1	1.0/4.0	-40 to +150	+2.3 to +5.5	6	-	-	-	3-pin SOT-23, 3-pin TO-92, 5-pin SC-70
MCP9700/01A	Linear Active Thermistor IC	1	1.0/2.0	-40 to +150	+2.3 to +5.5	6	-	-	-	3-pin SOT-23, 3-pin TO-92, 5-pin SC-70
EMC1033	SMBus/I ² C Multi-Temperature Sensor	3	1.0/3.0	-40 to +125	+3.0 to +3.6	50	2	✓	-	8-pin MSOP
EMC1043	SMBus/I ² C Multi-Temperature Sensor	3	0.5/1.0	-40 to +125	+3.0 to +3.6	105	-	✓	Configurable	8-pin MSOP
EMC1046/7	SMBus/I ² C Multi-Temperature Sensor with Hottest of Zones	6/7	0.25/1.0	-40 to +125	+3.0 to +3.6	395	-	✓	Automatic	10-pin MSOP
EMC1412/3/4	SMBus/I ² C Multi-Temperature Sensor	2/3/4	0.25/1.0	-40 to +125	+3.0 to +3.6	430	2	✓	Automatic	8-pin TDFN, 8-pin MSOP, 10-pin DFN, 10-pin MSOP
EMC1422/3/4	SMBus/I ² C Multi-Temperature Sensor with Shutdown	2/3/4	0.25/1.0	-40 to +125	+3.0 to +3.6	430	1	✓	Automatic	8-pin MSOP, 10-pin MSOP
EMC1438	SMBus/I ² C Multi-Temperature Sensor with Hottest of Zones	8	0.25/1.0	-40 to +125	+3.0 to +3.6	450	1	✓	Automatic	16-pin QFN

Thermal Management: Sensor Conditioning ICs

Product	Description	Typical T _c Accuracy (°C)	Typical T _h Accuracy (°C)	Temperature Range (°C)	Vcc Range (V)	Max Supply Current (µA)	Packages
MCP9600	Fully Integrated thermocouple EMF to temperature converter. Supports thermocouple types K, J, T, N, S, E, B and R.	1	1	-40 to +125	2.7 to 5.5	500	5 x 5 MQFN
MCP96L00	Fully Integrated thermocouple EMF to temperature converter. Supports thermocouple types K, J, T, N, S, E, B and R.	1	4	-40 to +125	2.7 to 5.5	500	5 x 5 MQFN
MCP96RL00	Fully Integrated thermocouple EMF to temperature converter. Supports thermocouple types K, J, T, N, S, E, B and R.	1	6	-40 to +125	2.7 to 5.5	500	5 x 5 MQFN

Thermal Management: Fan Controllers

Product	Description	# Fan Drivers	PWM/Linear Control	# External Temp. Inputs	Typical Accuracy (°)	Max. Accuracy (°)	Vcc Range (V)	Interface	Alerts	Fan Speed Lookup Table	Packages
EMC2101	Programmable Fan Controller with Thermal Management	1	PWM	2	0.5	1.0	+3.0 to +3.6	SMBus/I ² C	✓	✓	8-pin MSOP, 8-pin SOIC
EMC2103-1	Programmable Fan Controller with Thermal Management	1	PWM	1	0.5	1.0	+3.0 to +3.6	SMBus/I ² C	✓	✓	12-pin QFN
EMC2104	Programmable Multi-Fan Controller with Thermal Management	2	PWM	4	0.25	1.0	+3.0 to +3.6	SMBus/I ² C	✓	✓	20-pin QFN
EMC2301/2/3/5	Programmable Fan Controller	1/2/3/5	PWM	-	-	-	+3.0 to +3.6	SMBus/I ² C	✓	-	8-pin MSOP, 10-pin MSOP, 12-pin QFN, 16-pin QFN

Power Management: Switching Regulators

Product	Input Voltage Range (V)	Output Voltage (V)	Operating Temp. Range (°C)	Switching Frequency (kHz)	Output Current (mA)	Features			Packages
Single Output Switching Regulator - Step Down Regulator									
MCP1601/3	2.7 to 5.5	0.9V to V _{in}	-40 to +85	750	500	UVLO, Auto-Switching, LDO/Overtemperature and Overcurrent Protection			8-pin MSOP

Power Management: Switching Regulators								
Product	Input Voltage Range (V)	Output Voltage (V)	Operating Temp. Range (°C)	Switching Frequency (kHz)	Output Current (mA)	Features		Packages
Single Output Switching Regulator - Step Down Regulator								
MCP1612	2.7 to 5.5	0.8 to 5.5	-40 to +85	1400	1000	Overall Efficiency > 94%, Soft Start, Overtemperature and Overcurrent Protection		8-pin MSOP, 8-pin (3 x 3) DFN
MIC23030/1	2.7 to 5.5	1.0, 1.2, 1.5, 1.8, Adj	-40 to +125	8000/4000	400	HyperLight Load® Mode		6-pin 1.6 x 1.6 MLF
MIC23050/1	2.7 to 5.5	1.0, 1.2, 1.8, 3.3/1-1.2, 1-1.8, 1.15-1.4, 0.95-1.25	-40 to +125	4000	600	HyperLight Load Mode		8-pin 2 x 2 MLF
MIC23150/3	2.7 to 5.5	1.0, 1.2, 1.35, 1.8, 3.3/1.8, Adj	-40 to +125	4000	2000	HyperLight Load Mode		8-pin 2 x 2 MLF
MIC23155	2.7 to 5.5	1.8, Adj	-40 to +125	3000	2000	Power Good, HyperLight Load Mode		10-pin 2.5 x 2.5 MFL
MIC23303	2.7 to 5.5	Adj	-40 to +125	4000	3000	Power Good, HyperLight Load Mode		12-pin 3 x 3 MLF
MCP16311/12	4.4 to 30.0	2.0 to 24.0	-40 to +125	500	1000	PFM/PWM Operation, Enable Function		8-pin MSOP, 8-pin (2 x 3) TDFN
MCP16301	4.0 to 30	2.0 to 15	-40 to +85	500	600	Integrated N-channel, UVLO, Soft Start, Overtemperature Protection		6-pin SOT-23
MIC24045	4.5 to 19	0.7 to 3.3	-40 to +125	400-790	6000	I ² C Programmable, 4.5V-19V Input		20-pin (3 x 3) QFN
MIC24046	4.5 to 19	0.7 to 3.3	-40 to +125	400-790	6000	Pin Selectable, 4.5V-19V Input		20-pin (3 x 3) QFN
MIC24051/53/55	4.5 to 19	Adj.	-40 to +125	600	600/9000/1200	Power Good, Soft Start, COT Regulation Scheme		28-pin (5 x 6) QFN
MIC24052/54/56	4.5 to 19	Adj.	-40 to +125	600	600/9000/1200	Power Good, Soft Start, HyperLight Load Mode		28-pin (5 x 6) QFN
MIC26601/ MIC26901/ MIC26950	4.5 to 28	Adj.	-40 to +125	600	6000/9000/12000	Power Good, Soft Start, Hyper Speed Control® Architecture		28-pin (5 x 6) QFN
MIC26603/ MIC26903	4.5 to 28	Adj.	-40 to +125	600	6000	Power Good, Soft Start, HyperLight Load Mode		28-pin (5 x 6) QFN
MIC27600	4.5 to 36	Adj.	-40 to +125	300	7000	Soft Start, COT Regulation scheme - Hyper Speed Control Architecture, Thermal Shutdown		28-pin (5 x 6) QFN
MIC28510	4.5 to 75	Adj.	-40 to +125	100-500	4000	Soft Start, COT Regulation scheme - Hyper Speed Control Architecture, Thermal Shutdown		28-pin (5 x 6) QFN
MIC28511/12/13 (-1/2)	4.6 to 60/70/45	Adj.	-40 to +125	200-680	3000/2000/4000	Power Good, Soft Start, HyperLight Load Mode, Hyper Speed Control		24-pin (3 x 4) FCQFN
MIC28514/15	4.5 to 75	Adj.	-40 to +125	270-800	5000	Power Good, Adjustable Soft Start (MIC28514), Hyper Speed Control Architecture, Selectable HyperLight Load/CCM mode (MIC28515)		6 x 6 mm PQFN
MCP1623/4	0.65 to 5.5	2.0 to 5.5	-40 to +85	500	425	Integrated synchronous boost regulator, 0.65V start-up voltage, soft start, true load disconnect		6-pin SOT-23, 8-pin (2 x 3) DFN
MCP16251/2	0.82 to 5.5	1.8 to 5.5	-40 to +85	500	650	True load disconnect shutdown (MCP16251)/ Input to output bypass shutdown (MCP16252)		6-pin SOT-23, 8-pin (2 x 3) DFN
MCP1640/B/ C/D	0.65 to 5.5	2.0 to 5.5	-40 to +85	500	800	Integrated synchronous boost regulator, 0.65V start-up voltage, soft start, true load disconnect or input-to-output bypass option		6-pin SOT-23, 8-pin (2 x 3) DFN
MCP1642B/D	0.65 to 5.5	1.8 to 5.5	-40 to +85	1000	1800	Integrated synchronous boost regulator, 0.65V start-up voltage, soft start, enable, power good output, true load disconnect or input-to-output bypass option		8-pin MSOP, 8-pin (2 x 3) DFN
MIC2877	2.5 to 5.5	Up to V _{IN}	-40 to +125	6500	4800	6.5A ISW, Synchronous Boost Regulator with Bidirectional Load Disconnect and Bypass Mode		8-pin 2 x 2 mm FTQFN
MIC2145	2.4 to 16	Up to 16	-40 to +85	450	900	High-Efficiency 2.5W Boost Converter		8-pin MSOP, 3 x 3 MLF
MIC2253	2.5 to 10	Up to 30	-40 to +125	1000	3500	3.5A, 1 MHz High-Efficiency Boost Regulator with OVP and Soft Start		12-pin 3 x 3 MLF
MIC2290	2.5 to 10	Up to 34	-40 to +125	1200	750	PWM Boost Regulator with Internal Schottky Diode		8-pin 2 x 2 MLF
MIC2295/96	2.5 to 10	Up to 34	-40 to +125	1200/600	1700	High Power Density 1.2A Boost Regulator		5-pin SOT23, 2 x 2 MLF
MCP1663/4	2.4 to 5.5	Up to 32	-40 to +85	500	1800	High-efficiency (up to 92%), fixed-frequency, non-synchronous, 300 mV feedback for LED driving (MCP1664)		5-pin SOT-23, 8-pin (2 x 3) TDFN
MCP1665	2.7 to 5	Up to 32	-40 to +85	500	3600	3.6A Integrated Switch PFM/PWM Boost Regulator		10-pin 2 x 2 VQFN
MIC2601/02	4.5 to 20	Up to 40	-40 to +125	1200/2000	1700	1.2A, 1.2 MHz/2 MHz Wide Input Range Integrated Switch Boost Regulator		8-pin 2 x 2 MLF

Power Management: Switching Regulators

Product	Input Voltage Range (V)	Output Voltage (V)	Operating Temp. Range (°C)	Switching Frequency (kHz)	Output Current (mA)	Features	Packages
Single Output Switching Regulator - Step Down Regulator							
MIC2171/72	3 to 40	Up to 65	-40 to +85	100	2500/1250	100 kHz 2.5A/1.25A Switching Regulator	5-pin TO220, TO263/8-pin SOIC, 8-pin DIP
Multiple Output Switching Regulators							
MIC2800/10	2.9 to 5.5	Adj./Adj.	-40 to +125	2.0 MHz	600/300/300	600 mA Buck Regulator, 2 × 300 mA LDO, LowQ Mode (MIC2810)	16-pin (3 x 3) MLF
MIC2238/30	2.5 to 5.5	1.28/1.65, 1.8/1.2, 1.8/1.545, 1.8/1.575, 1.8/3.3, 1.8/1.6, 2.5/1.2, 3.3/1.2, 3.3/3.3, Adj./Adj.	-40 to +125	2.5 MHz	800/800	Power Good, Soft Start, Current Limit Protection, Dual Output Voltages	12-pin (3 x 3) MLF
MIC23250	2.7 to 5.5	0.9/1.1, 1.2/1.0, 1.2/1.6, 1.2/1.8, 1.2/2.8, 1.2/3.3, 1.575/1.8, 2.6/3.3, Adj./Adj.	-40 to +125	4.0 MHz	400/400	20 mVpp in HyperLight Load® Mode, Soft Start, Ultra-Fast Transient Response	10-pin (2 x 2) MLF, 12-pin (2.5 x 2.5) MLF
MIC23254	2.5 to 5.5	1.0/1.8	-40 to +125	4.0 MHz	400/400	20 mVpp in HyperLight Load Mode, Soft Start, Ultra-Fast Transient Response	10-pin (2 x 2) Thin MLF
MIC23450	2.7 to 5.5	Adj./Adj./Adj.	-40 to +125	3.0 MHz	2000/2000/2000	Power Good, Soft Start, HyperLight Load Mode	32-pin (5 x 5) QFN
MIC24420	4.5 to 15	Adj./Adj.	-40 to +125	1 MHz	2500/2500	Power Good, Soft Start	24-pin (4 x 4) MLF
MIC24421	4.5 to 15	Adj./Adj.	-40 to +125	500 kHz	2500/2500	Power Good, Soft Start	24-pin (4 x 4) MLF
MIC23158	2.7 to 5.5	Adj./Adj.	-40 to +125	3.0 MHz	2000/2000	Power Good, Soft Start, HyperLight Load Mode	20-pin (3 x 4) MLF
MIC23159	2.7 to 5.5	Adj./Adj.	-40 to +125	3.0 MHz	2000/2000	Power Good, Soft Start, HyperLight Load Mode	20-pin (3 x 4) MLF
MIC23451	2.7 to 5.5	Adj./Adj./Adj.	-40 to +125	3.0 MHz	2000/2000/2000	Power Good, Soft Start, HyperLight Load Mode	26-pin (4 x 4) QFN
MIC7400/1	2.4 to 5.5	1.1, 1.8, 1.05, 1.25, 12 or Configurable	-40 to +125	2 MHz Boost, 1.3 MHz Bucks	DC to DC Bucks: 3,000, DC/DC Boost 200	Highly integrated-configurable, featuring five buck regulators, one boost regulator and global Power Good indicator/enable pin	36-pin 4.5 x 4.5 QFN

Power Management: Inductorless Offline Switches

Product	V _{IN} (VAC)	Adjustable V _{OUT} (V)	Fixed V _{OUT} (V)	I _{OUT} Max. (mA)	Load Regulation (%/mA)	Packages
SR086	80–285	9.0–50	3.3	100	0.025	8-Lead SOIC with Heat Slug
SR10	80–285	6.0–28	6.0, 12, 24	60	—	8-Lead SOIC

Power Management: PWM Controllers

Power Management ICs & Controllers								
Product	Supported Topologies	Supported Outputs	Input Voltage Range (V)	Output Voltage (V)	Operating Frequency (Hz)	Operating Temperature Range (°C)	Features	Packages
MIC2103/4	Sync. Buck	1	4.5–75	0.8–24	200–600 kHz	−40 to +125	HyperLight Load® Mode, External Clock Sync, Power Good, Soft Start, Internal Compensation and Voltage Bias	16-pin 3 x 3 MLF
MIC2124	Sync. Buck	1	3.0–18	0.8–12	300 kHz	−40 to +125	Soft Start, Internal Voltage Bias	10-pin MSOP
MIC2130/1	Sync. Buck	1	8.0–40	0.7–24	150 or 400 kHz	−40 to +125	Power Good, Soft Start, Internal Voltage Bias	16-pin e-TSSOP, 16-pin 4 x 4 MLF
MIC2150/1	Sync. Buck	2	4.5–14.5	0.7–5.5	500 kHz	−40 to +125	Power Good, Soft Start, Internal Voltage Bias	24-pin 4 x 4 MLF
MIC2183	Sync. Buck	1	2.9–14	1.3–12	200/400 kHz	−40 to +125	External Clock Sync, Soft Start, Internal Voltage Bias	16-pin SOP, 16-pin QSOP
MIC2184	Async. Buck	1	2.9–14	1.3–12	200/400 kHz	−40 to +125	External Clock Sync, Soft Start, Internal Voltage Bias	16-pin SOP, 16-pin QSOP
MIC2185/86	Boost, SEPIC, Ćuk	1	2.9–14	3.3–14	100/200/400 kHz	−40 to +125	Skip Mode, External Clock Sync, Soft Start, Internal Voltage Bias	16-pin SOIC, 16-pin QSOP
MIC38HC42/3/4/5	Forward, Flyback	1	9.0 up to 20	–	Adj. to 500 kHz	−40 to +85	Forward, Flyback Supported Topologies	8-pin PDIP, 14-pin PDIP, 8-pin SOIC, 14-pin SOIC
MIC9130/1	Forward, Flyback	1	9.0–180	–	Adj. up to 1.5 MHz	−40 to +125	Forward, Flyback Supported Topologies, External Clock Sync	16-pin SOIC, 16-pin QSOP
MCP1630/1/2	Flyback, Boost, SEPIC, Ćuk	1	3.0–5.5	–	Sync. up to 2 MHz	−40 to +125	External Clock Sync, Current Limit/Short Circuit Protection, Soft Start, Internal Voltage Bias, UVLO, Peak Current Control Mode	20-pin TSSOP, 20-pin SSOP, 20 pin 4 x 4 QFN
MCP1631HV	Flyback, Boost, SEPIC, Ćuk	1	3.5–16	–	Sync. to 2 MHz	−40 to +125	External Clock Sync, Current Limit/Short Circuit Protection	20-pin TSSOP, 20-pin SSOP
MCP19035	Sync. Buck	1	4.5–30	–	300/600 kHz	−40 to +125	Power Good, Soft Start, Internal Voltage Bias, UVLO, Current Limit/Short Circuit Protection	10-pin 3 x 3 DFN
MIC2128/27A	Sync. Buck	1	4.5–75	0.6–32	270–800kHz	−40 to +125	Internal and External soft start, Internal LDO, Short Circuit Protection, Current limit	16-pin 3 x 3 DFN

Power Management: Hybrid PWM Controllers											
Part #	Input Voltage Range (V)	Output Voltage (V)	Topologies Supported	Channels	Integrated MCU	Program Memory (KWords)	RAM (bytes)	GPIO	Product Features Integrated MCU, LDO, MOSFET Drivers, 10b A/D Converter, Temp Sensor, User-Configurable Operation and:	Packages	
MCP19110 MCP19111	4.5–32	0.5 to 90% of V_{IN}	Sync. Buck	1	✓	4	256	11 14	Configurable and dynamically changeable internal analog compensation network	24-pin 4x4 QFN 28-pin 5x5 QFN	
MCP19114 MCP19115	4.5–42	Topology Dependent	Boost, Flyback, SEPIC, Ćuk	1	✓	4	256	8 12	Excellent regulation for constant current applications	24-pin 4x4 QFN 28-pin 5x5 QFN	
MCP19116 MCP19117	4.5–42	Topology Dependent	Boost, Flyback, SEPIC, Ćuk	1	✓	8	336	8 12	Improved current regulation accuracy, additional code space (compared to MCP19114 or MCP19115)	24-pin 4x4 QFN 28-pin 5x5 QFN	
MCP19118 MCP19119	4.5–40	0.5 to 90% of V_{IN}	Sync. Buck	1	✓	4	256	11 14	Configurable and dynamically changeable internal analog compensation network	24-pin 4x4 QFN 28-pin 5x5 QFN	
MCP19122 MCP19123	4.5–40	0.3–16	Sync. Buck	1	✓	4	256	12 16	Emulated average current mode control, programmable gain feedback amplifier, multiphase operation, improved regulation accuracy and current measurement accuracy (compared to MCP19110/1/8/9)	24-pin 4x4 QFN 28-pin 5x5 QFN	
MCP19124 MCP19125	4.5–42	Topology Dependent	Boost, Flyback, SEPIC, Ćuk	1	✓	4	256	8 12	Dual independent voltage and current control loops allow seamless transitions from constant voltage to constant current regulation	24-pin 4x4 QFN 28-pin 5x5 QFN	
MCP19214 MCP19215	4.5–42	Topology Dependent	Boost, Flyback, SEPIC, Ćuk	2	✓	8	336	8 12	Dual channels, which can be configured to control two outputs, or one bidirectional system	28-pin 5x5 QFN 32-pin 5x5 QFN	
Power Management: Power Modules											
Product	Input Voltage Range (V)	Output Voltage (V)	Operating Temp. Range (°C)	Control Scheme	Switching Frequency (kHz)	Vout Max. (V)	Output Current (A)	Features			Packages
MIC28304-1/-2	4.5 to 70	Adj.	-40 to +125	COT	600	24	3	HyperLight Load® Mode, Hyper Speed Control® Architecture, Power Good, Soft Start			64-pin (12 x 12) QFN
MIC45205-1/-2	4.5 to 26	Adj.	-40 to +125	COT	200–600	5.5	6	HyperLight Load Mode, Hyper Speed Control Architecture, Power Good, Soft Start			52-pin (8 x 8) QFN
MIC45208-1/-2	4.5 to 26	Adj.	-40 to +125	COT	200–600	5.5	10	HyperLight Load Mode, Hyper Speed Control Architecture, Power Good, Soft Start			52-pin (10 x 10) QFN
MIC45212-1/-2	4.5 to 26	Adj.	-40 to +125	COT	200–600	5.5	14	HyperLight Load Mode, Hyper Speed Control Architecture, Power Good, Soft Start			64-pin (12 x 12) QFN
MIC33030	2.7 to 5.5	1.2, 1.8, Adj.	-40 to +125	PWM	8,000	3.6	0.4	HyperLight Load Mode			10-pin (2.5 x 2.0) MLF®
MIC33050	2.7 to 5.5	1.0, 1.2, 1.8, 3.3, Adj.	-40 to +125	PWM	4,000	3.3	0.6	HyperLight Load Mode			12-pin (3 x 3) MLF
MIC33153	2.7 to 5.5	1.2, Adj.	-40 to +125	PWM	4,000	3.6	1.2	HyperLight Load Mode, Power Good, Soft Start			14-pin (3 x 3.5) MLF
MIC3385	2.7 to 5.5	1.5, Adj.	-40 to +125	PWM	8,000	5.5	0.6	LowQ			14-pin (3 x 3.5) MLF
MIC28303-1/-2	4.5 to 50	Adj.	-40 to +125	COT	600	24	3	HyperLight Load Mode, Hyper Speed Control Architecture, Power Good, Soft Start			64-pin (12 x 12) QFN
MIC45116-1/-2	4.5 to 20	Adj.	-40 to +125	COT	600	17	6	HyperLight Load Mode, Hyper Speed Control Architecture, Power Good, Soft Start			52-pin (8 x 8) QFN
MIC45404	4.5 to 19	Selectable	-40 to +125	Fixed	400–790	3.3	5	Power Good, Soft Start			64-pin (6 x 10) QFN
Power Management: Linear Regulators											
Part #	$\pm V_{IN}$ Min (V)		$\pm V_{IN}$ Max (V)		Output Voltage (V)	Max Output Current (mA)	Typical Line Regulation (%/V)		Typical Load Regulation (%/mA)	Packages	
LR8	12		450		1.2–440	10	0.003		0.15	3-Lead TO-252, 3-Lead TO-92, 3-Lead SOT-89	
LR12	12		100		1.2–88	50	0.003		0.06	3-Lead TO-252, 8-Lead SOIC, 3-Lead TO-92	

Power Management: DDR Termination Regulators											
Product	I _{out}	V _{IN} Min. (V)	V _{IN} Max. (V)	V _{out} (V)	PWR Good	VTT Accuracy	External Transistor	Sync Buck	Frequency	Features	Packages
MIC5166	±3A	0.9	3.6	1/2 of V _{IN}	Y	±40 mV	-	-	-	Integrated FETs	3 × 3 DFN
MIC5167	±6A	2.6	5.5	Adj. down to 0.35V	Y	±12 mV	-	Y	1 MHz	Integrated Sync-Buck	4 × 4 DFN
Power Management: Charge Pump DC-to-DC Converters											
Product	Configuration	Input Voltage Range (V)	Output Voltage (V)	Typical Output Current (mA)	Switching Frequency (kHz)	Supply Current (I _S , floating output, μA, 25°C)	Output Resistance (Ω, at typical output current, 25°C)	Power Conversion Efficiency (%)	Features		Packages
Inverting or Doubling Charge Pumps											
TC7660S/H	Inverting or doubling	1.5–12	–V _{IN} or 2* V _{IN}	20	10, 45, or 120	80 or 1000	55 or 60	98% at 1 mA, 85% at 10 mA	Boost pin increases switching frequency, high-voltage oscillator		8-pin SOIC and 8-pin PDIP
TC7662A/B	Inverting or doubling	1.5–15	–V _{IN} or 2* V _{IN}	20 or 40	10, 12 or 35	80 or 190	50 or 65	96% at 1 mA, 97% at 7.5 mA	Boost pin increases switching frequency, no low-voltage terminal required		8-pin SOIC and 8-pin PDIP
Regulated Charge Pumps											
MCP1252/3	Regulated	2.0–5.5	3.3, 5.0, or Adjustable	150	650, 1000	60	N/A	81% at 10 mA	Shutdown, power good, regulated output, adjustable version		8-pin MSOP
Power Management: Power MOSFET Drivers											
Product	Drivers	Configuration		Peak Output Current (source/sink, A)	Max Supply Voltage (V)	Output Resistance (source/sink, Ω)	Propagation Delay (T _{D1} /T _{D2} , ns)	Rise/Fall Time (T _r , T _f , ns)	Packages		
Low-Side Power MOSFET Drivers											
MCP14A0051/2	Single	Inverting/Non-Inverting		0.5/0.5	18	6.5/4.5	40/31	51/39	6-pin SOT-23, 6-pin 2 x 2 DFN		
MIC4416/7	Single	Non-Inverting/Inverting/Complementary		1.2/1.2	18	3.5/3.5	42/42	3.5/3.5	SOT-143		
MIC4467/8/9	Quad	Inverting/Non-Inverting/Complementary		1.2/1.2	18	5/5	35/55	5/5	16-pin WSOIC, 14-pin PDIP		
MCP14A0151/2	Single	Inverting/Non-Inverting		1.5/1.5	18	17/10	41/32	18.5/17	6-pin SOT-23, 6-pin 2 x 2 DFN		
MCP14A0153/4/5	Dual	Inverting/Non-Inverting/Complementary		1.5/1.5	18	4.5/3	32/24	11/10	8-pin SOIC, 8-pin MSOP, 8-pin 2 x 3 DFN		
MCP14E6/7/8	Dual	Inverting/Non-Inverting/Complementary		2.0/2.0	18	5/5	45/45	12/15	8-pin SOIC, 8-pin PDIP, 8-pin 6 x 5 DFN		
MIC4478/9/80	Dual	Non-Inverting/Inverting/Complementary		2.5/2.5	32	6/3	160/70	120/45	8-pin SOIC, 8-pin ePAD SOIC		
MCP14E9/10/11	Dual	Inverting/Non-Inverting/Complementary		3.0/3.0	18	4/4	45/45	14/17	8-pin SOIC, 8-pin PDIP, 8-pin 6 x 5 DFN		
MAQ4123/4/5	Dual	Inverting/Non-Inverting/Complementary		3.0/3.0	20	5/5	40/60	11/11	8-pin ePAD SOIC		
MIC4123/4/5	Dual	Inverting/Non-Inverting/Complementary		3.0/3.0	20	5/5	44/59	11/11	8-pin ePAD SOIC		
MCP14E3/4/5	Dual	Inverting/Non-Inverting/Complementary		4.0/4.0	18	2.5/2.5	46/50	15/18	8-pin SOIC, 8-pin PDIP, 8-pin 6 x 5 DFN		
MCP14A0451/2	Single	Non-Inverting/Inverting		4.5/4.5	18	1.6/1.2	16/19.5	9/9.5	8-pin MSOP, 8-pin SOIC 8 pin 2 x 2 WDFN		
MCP14A0601/2	Single	Non-Inverting/Inverting		6.0/6.0	18	1.2/0.9	22/22	10/10	8-pin MSOP, 8-pin SOIC 8 pin 2 x 3 WDFN		
MCP14A031/2	Single	Non-Inverting/Inverting		3.0/3.0	18	2.2/1.5	15/18	18/17	8-pin MSOP, 8-pin SOIC, 8-pin, 2 x 2 DFN		
MIC4120/29	Single	Non-Inverting/Inverting		6.0/6.0	20	5/5	45/50	12/13	8-pin ePAD SOIC, 8-pin 3 x 3 MLF		
MIC4421A/22A	Single	Inverting/Non-Inverting		9.0/9.0	18	0.8/0.6	15/35	20/24	8-pin PDIP, 8-pin SOIC, 5-pin TO-220		
MIC4451/2	Single	Inverting/Non-Inverting		12.0/12.0	18	0.8/0.6	25/40	20/24	8-pin SOIC, 8-pin PDIP, 5-pin TO-220		
High-Side Power MOSFET Drivers											
MIC5011/13	High-Side or Low-Side Single	Non-Inverting		950 μA*/225 μA*	32	N/A	N/A	25 μs/4 μs	8-pin SOIC, 8-pin PDIP		
MIC5014/15	High-Side or Low-Side Single	Non-Inverting/Inverting		800 μA*	30	N/A	N/A	90 μs/6 μs	8-pin SOIC, 8-pin PDIP		
MIC5018/19	High-Side or Low-Side Single	Non-Inverting		10 μA*	9	N/A	N/A	750 μs/10 μs	4-pin SOT-143		
MIC5021	High-Side or Low-Side Single	Non-Inverting		5600 μA*	36	N/A	500/800	400 ns/400 ns	8-pin SOIC, 8-pin PDIP		
MIC5060	High-Side or Low-Side Single	Non-Inverting		800 μA*	30	N/A	N/A	90 μs/6 μs	8-pin 3 x 3 MLF		
Synchronous Drivers											
MCP14628/MCP14700	Half Bridge Driver	Dual Inputs		2.0/3.5	5.5 (36V Boot Pin)	1/1 (0.5 on low side)	15/22	10/10	8-pin SOIC, 8-pin 3 x 3 DFN		
MIC4100/1	Half Bridge Driver	Dual Inputs		2.0/2.0	16 (100V Boot Pin)	2.5/2.0	27/27	10/10	8-pin SOIC		
MIC4102	Half Bridge Driver	Single PWM		3.0/2.0	16 (100V Boot Pin)	1.5/2.0	60/75	10/6	8-pin SOIC		

Power Management: Power MOSFET Drivers														
Product	Drivers	Configuration	Peak Output Current (source/sink, A)	Max Supply Voltage (V)	Output Resistance (source/sink, Ω)	Propagation Delay (T _{D1} /T _{D2} , ns)	Rise/Fall Time (T _r , T _f , ns)	Packages						
MIC4103/4	Half Bridge Driver	Dual Inputs	3.0/2.0	16 (100V Boot Pin)	1.5/2.0	24/24	10/6	8-pin SOIC						
MIC4600	Half Bridge Driver	Dual Inputs, Single PWM	1.0/1.0	28	2.0/1.5	26/55	15/13.5	16-pin 3 x 3 QFN						
MIC4604	Half Bridge Driver	Dual Inputs	1.0/1.0	16 (85V Boot Pin)	4.4/4.0	33/34	20/20	8-pin SOIC, 10-pin 2.5 x 2.5 TDFN						
MIC4605	Half Bridge Driver	Dual Inputs, Single PWM	1.0/1.0	16 (85V Boot Pin)	10/6	35/35	20/20	8-pin SOIC, 10-pin 2.5 x 2.5 TDFN						
MIC4606	Full Bridge Driver	Dual Inputs, Single PWM	1.0/1.0	16 (85V Boot Pin)	10/6	35/35	20/20	16-pin 4 x 4 QFN						
MIC4607	3 Phase Driver	Dual Inputs, Single PWM	1.0/1.0	16 (85V Boot Pin)	10/6	35/35	20/20	28-pin TSSOP, 28-pin 4 x 5 QFN						
MIC4608	Half Bridge Driver	Dual Inputs, Single PWM	1.0/1.0	20 (600V Boot Pin)	8/9.2	450/450	31/31	14-pin SOIC						
MIC4609	3 Phase Driver	Dual Inputs	1.0/1.0	20 (600V Boot Pin)	8/9.2	450/450	31/31	28-pin SOIC						
Power Management: Power Switches														
Part #	Description			USB Port Power Switch (55 mΩ)	High-Speed USB 2.0 Switch	Battery Charger Emulation Profiles	8 Resistor Set Current Limits	Charging Indicator Output	Attach Detection Output	Current Measurement	Power Allocation	Interface	Packages	
USB Port Power Controllers														
UCS1001-3/4	USB Port Power Controller with Charger Emulation			1	1	9	Up to 2.4A	-3 option	-4 option	-	-	Discrete I/O	20-pin 4 x 4 QFN	
UCS1002-2	Programmable USB Port Power Controller with Charger Emulation			1	1	9 + 1 Programmable	Up to 2.4A	Y	-	Y	Y	I ² C/SMBus	20-pin 4 x 4 QFN	
UCS1003-1	Programmable USB Port Power Controller with Charger Emulation			1	1	9 + 1 Programmable	Up to 3A	-	Y	Y	Y	I ² C/SMBus	20-pin 4 x 4 QFN	
UCS81003	Programmable USB Port Power Controller - Automotive			1	1	9 + 1 Programmable	Up to 3A	-	Y	Y	Y	I ² C/SMBus	28-pin 5 x 5 QFN	
Power Management: Power Switches														
Part #	Channels	V _{IN} Range (V)	Fixed Current Limit Min.			Adj. Current Limit Max.	R _{DS(on)} (mΩ)	Reverse Blocking	Enable Logic	UVLO	Thermal Protection	Fault Flag	Current Measurement	Packages
Current Limit USB Protection Switches														
MIC200x/201x	Single	2.5–5.5	500 mA, 800 mA, 1.2A			Up to 2A	70/100/170	-	Active Low, Active High	Y	Y	-/Y	-	5-pin SOT23, 6-pin SOT23, 2 x 2
MIC2025/75	Single	2.7–5.5	500 mA			-	90	Y	Active Low, Active High	Y	Y	Y	-	8-pin SOIC, 8-pin MSOP
MIC2033/39	Single	2.5–5.5	475 mA, 517 mA, 760 mA, 950 mA, 1.14A			2.5A	75	-	Active Low, Active High	Y	Y	Y	-	6-pin SOT-23, 2 x 2 TDFN
MIC2042/43	Single	0.8–5.5	-			3.0A	60	Y	Active Low, Active High	Y	Y	Y	-	8-pin SOIC, 14-pin TSSOP
MIC2044/45	Single	0.8–5.5	-			6.0A	30	Y	Active Low, Active High	Y	Y	Y	-	16-pin TSSOP
MIC2544/48	Single	2.7–5.5	-			1.5A	80	Y	Active Low, Active High	-	Y	Y	-	8-pin SOIC, 8-pin MSOP
MIC2545A/49A	Single	2.7–5.5	-			3.0A	35	Y	Active Low, Active High	-	Y	Y	-	8-pin SOIC, 8-pin PDIP, 14-pin TSSOP
MIC2026/76	Dual	2.7–5.5	500 mA			-	90	Y	Active Low, Active High	Y	Y	Y	-	8-pin SOIC, 8-pin PDIP
MIC2506	Dual	2.7–7.5	1.0A			-	75	Y	Active Low, Active High	-	Y	Y	-	8-pin SOIC, 8-pin PDIP
MIC2546/47	Dual	2.7–5.5	-			1.5A	80	Y	Active Low, Active High	-	Y	Y	-	16-pin SOIC, 16-pin TSSOP
UCS2113/2114	Dual	2.9–5.5	-			3.4A	40/18	Y	Active Low, Active High	Y	Y	Y	Y	20-pin 4 x 4 QFN, 20-pin 3 x 3 QFN
Power Management: Power Switches														
Part #	Channels	V _{IN} Range (V)	Max. Switch Current (A)	R _{DS(on)} (mΩ)	Soft Start (μs)		Load Discharge (Ω)		Enable Logic	Reverse Blocking		Packages		
Load Switches														
MIC94040/1/2/3/4/5	Single	1.7–5.5	3.0	28	100 (94042), 900 (94044/5)		250 (94041/3), 200 (94045)		Active High	-		1.2 x 1.2		
MIC94070/1/2/3	Single	1.7–5.5	1.2	120	800 (94072/3)		200 (94071/3)		Active High	-		6-pin SC70, 1.2 x 1.6*		
MIC94080/1/2/3/4/5	Single	1.7–5.5	2.0	67	800 (94082/3), 120 (94084/5)		250 (94081/3/5)		Active High	-		0.85 x 0.85		
MIC94161/2/3/4/5	Single	1.7–5.5	3.0	15.5	2700 (94161/4/5), 60 (94162/3)		200 (94162/4)		Active High	Y		1.5 x 1 WL CSP		
MIC95410	Single	0.5–5.5	7.0	6.6	1100		2300		Active High	-		1.2 x 2		
MIC94066/7/8/9	Dual	1.7–5.5	2	85	800 (94068/9)		200 (94067/9)		Active High	-		2 x 2		

Power Management: LDO Single Output										
Product	Output Current (mA)	V _{IN} Min. (V)	V _{IN} Max. (V)	V _{OUT} (V)	Voltage Drop Typ. (mV)	I _{GND} Typ. (μA)	Output Accuracy (%)	PSRR 1 kHz (dB)	Features	Packages
MIC5280/1/2/3	25/50/100/150	4.5	120	3.3, 5.0, Adj.	1100	31 μA/6 μA	±2/±3	80/90	High Input Voltage, Load Dump, Reverse Battery Protection	8-pin SOIC
MCP1790/1	70	6	30	3.0, 3.3, 5.0	700	70 μA	±0.2	90	High Input	3-pin SOT-223, 3-pin DDPAK, 5-pin DDPAK, 5-pin SOT-223
MIC5233	100	2.3	36	1.8, 2.5, 3.0, 3.3, 5.0, Adj	270	18 μA	±1	50	High Input Voltage, Reverse Battery and Current Protection	3-pin SOT-223, 5-pin SOT-23
MCP1810	150	2.5	5.5	1.2, 1.8, 2.5, 3.0, 3.3, 4.2	380	0.02 μA	±1	40	Ultra Low Quiescent Current	2x2 DFN
MIC5365	150	2.5	5.5	1.0, 1.2, 1.3, 1.5, 1.8, 2.0, 2.5, 2.6, 2.7, 2.8, 2.85, 2.9, 3.0, 3.3	155	32 μA	±2	80	High PSRR	5-pin SC70, 5-pin TSOT, 4-pin UDFN
MCP1711	150	1.4	6	1.2–5.0	500	0.6 μA	±1	20	Ultra Low I _q , Capless	4-pin UQFN, 5-pin SOT-23
MCP1703A	250	2.7	16	1.2–5.5	625	2 μA	±0.4	35	High Input, Low I _q	3-pin SOT-89, 3-pin SOT-23A, 3-pin SOT-223, 8-pin DFN
MIC5501/2/3/4	300	2.5	5.5	1.2, 1.8, 2.8, 3.0, 3.3	160	38 μA	±2	60	Low Dropout	4-pin UDFN, 5-pin SOT-23
MIC5239	500	2.3	30	1.5, 1.8, 2.5, 3.0, 3.3, 5.0, Adj	350	23 μA	±1	50	Reverse Battery and Current Protection	8-pin MSOP, 8-pin SOIC, 3-pin SOT-223
MIC5524	500	2.5	5.5	1.2, 1.8, 2.8, 3.0, 3.3	260	38 μA	±2	65	Low Noise	4-pin UDFN
MIC39100	1000	2.25	16	1.8, 2.5, 3.3, 5.0	410	6.5 mA	±1	55	Reverse Battery and Current Protection	3-pin SOT-223
MIC29151	1500	2.25	26	3.3, 5.0, 12	350	22 mA	±1	—	Load Dump, Reverse Current Protection	5-pin TO-220, 5-pin DDPAK
MIC29301	3000	2.25	26	3.3, 5.0, 12	370	37 mA	±1	—	Load Dump, Reverse Current Protection	5-pin TO-220, 5-pin DDPAK
MIC29751	7500	2.5	26	3.3, 5.0	425	120 mA	±1	—	Load Dump, Reverse Current Protection	5-pin TO-247

Display and LED Drivers: Electroluminescent Backlight Drivers									
Part #	Type	Input Voltage Min. (V)	Input Voltage Max. (V)	Nominal Output Voltage (V)	Max. Switch Resistance (Ω)	Output Regulation	Max. Lamp Size Per Device (in ²)	Packages	
16-Segment Drivers									
HV509	16-Segment Drivers		2	5.5	±50 to ±200	—	—	6.5	32-pin VQFN
Single Lamp Drivers									
HV833	Single Lamp Driver		1.8	6.5	±90	4	Y	12	8-pin MSOP
HV852	Single Inductorless Lamp Driver		2.4	5	±80	—	Y	1.5	10-pin WDFN, 8-pin MSOP
HV859	Single Lamp Driver		1.8	5	±105	6	Y	5	8-pin WDFN, 8-pin MSOP
Dual Lamp Drivers									
HV861	Dual Lamp Drivers		2.5	4.5	±90	7	Y	5	16-pin WQFN

Display and LED Drivers: LED Drivers										
Part #	Topology	Input Voltage (V)	Dimming	I _q Typ. (mA)	Switching Frequency (Hz)	Switching MOSFET	Dithered	ILED Accuracy	V _{FB} (V)	Packages
General Purpose LED Drivers										
HV9801A	Buck	15–450	4-Level Switch	1.0	100k	External FET	—	N/A	0.25	16-pin SOIC 150 mil, 8-pin SOIC 150 mil
HV9803B	Buck	7–13.2	PWM/Linear	1.5	100k	External FET	—	±2%	0.28	8-pin SOIC 150 mil
HV9805	2-Stage	102–265	—	2.5	370k	0.7A FET	—	N/A	1.25	10-pin MSOP
HV98100/HV98101	Buck - Boost	9.5–17.5	—	0.2	320k	External FET	—	±5%	0.2	6-pin SOT23
HV9910B/HV9910C	Buck	8–450/15–450	PWM/Linear	1.0	100k	External FET	—	±5%	0.25	16-pin SOIC 150 mil, 8-pin SOIC 150 mil
HV9918/HV9919B	Buck	4.5–40	PWM	1.5	2M	0.7A FET/Ext. FET	—	±5%	0.23	8-pin WDFN
HV9930	Ćuk	8–200	PWM	1.0	Variable	External FET	—	N/A	0.12	8-pin SOIC 150 mil
HV9961/HV9861A	Buck	8–450/15–450	PWM/Linear	1.5	100k	External FET	—	±3%	0.27	16-pin SOIC 150 mil, 8-pin SOIC 150 mil
MIC3202	Buck	6–37	PWM	1.2	Hyst to 1.0M	1A FET	Y	±5%	2	8-pin SOIC
MIC3230/1/2	Boost	6–45	PWM	3.2	Programmable	External FET	Optional	±3%	0.25	10-pin MSOP, 12-pin VDFN, 16-pin TSSOP EP

Display and LED Drivers: LED Drivers									
Part #	V _{IN} (V)	V _{OUT} (V)	Ouput Current (mA)	Dimming	Parallelable	Features	Packages		
Linear Regulators									
CL2	5.0–90		5.0–90	20	External FET		Yes	—	
CL220	Buck		5.0–220	20	External FET		Yes	—	
CL320	6.5–90		4.0–90	20	PWM		Yes	OTP, Separate ENABLE Pin	
								SOIC-8 with Heat Slug	

Display and LED Drivers: LED Drivers											
Part #	V _{IN} (V)	# of White LEDs	Dimming	I _Q (mA)	V _{DROPOUTLED} @ 20 mA	I _{LED} Matching	Ext LDOs	V _{DROPOUT}	I _{QLD} O	Comments	Packages
Linear LED Drivers											
MIC2860-2D	3-5.5	2 @ 30.2 mA	1-Wire, 32-Steps	0.7	52 mV	±0.5%	–	–	–		6-pin SC70, 6-pin SOT-23
MIC2860-2P	Buck	2 @ 30.2 mA	PWM down to 250 Hz	0.7	52 mV	±0.5%	–	–	–		6-pin SC70, 6-pin SOT-23
MIC4811	3-5.5	6 @ 50 mA	PWM (200 Hz–500 kHz)	1.7	100 mV @ 50 mA	±1.0%	–	–	–	DAM	10-pin MSOP
MIC4812	3-5.5	6 @ 100 mA	PWM (200 Hz–500 kHz)	3.2	190 mV @ 100 mA	±1.0%	–	–	–	DAM	10-pin eMSOP
Display and LED Drivers: LED Drivers											
Part #	V _{IN} (VAC)		V _{OUT} (V)	Output Current (Peak mA)		Dimming	Parallelable		Features		Packages
Sequential LED Drivers											
CL8800	90–275		70–350	115		External Dimmer	Yes		6-Stage		QFN-33
CL8801	90–275		70–350	200		External Dimmer	Yes		4-Stage		QFN-33
CL88020	90–135		70–190	115		External Dimmer	Yes		4-Tap		SOIC-8 EP
High-Voltage Interface: Driver Arrays											
Part #	Output Channels	V _{OUT} Operating (V) - Transient		V _{OUT} Operating (V) - Sustained		Input Structure	Output Structure		I _{OUT} per Channel (mA)	Min. Data Clock (MHz)	Packages
Source											
HV57009	64	95		85		Serial	P-Ch Open Drain		-2 (Programmable)	16	80-pin PQFP
MIC2981/82	8	50		50		Parallel	Darlington Open Emitter		-500	–	18-pin PDIP, 18-pin SOIC 300 mil
Sink											
HV5222	32	250		225		Serial	N-Ch Open Drain		100	8	44-pin CERQUAD, 44-pin PLCC, 44-pin PQFP
HV5630	32	315		300		Serial	N-Ch Open Drain		100	8	44-pin PLCC
MIC58P01	8	80		80		Parallel	Darlington Open Collector		400	–	24-pin SOIC 300 mil, 28-pin PLCC
Source-Sink											
HV507	64	320		300		Serial	Half-Bridge		±1.0	8	80-pin PQFP
HV508	2	60		45		Parallel	Half-Bridge		-2.8, +0.38	–	8-pin SOIC 150 mil
HV513	8	275		250		Serial	Half-Bridge		±20	8	24-pin SOIC 300 mil, 32-pin WQFN
HV57908	64	90		80		Serial	Half-Bridge		-1.25	8	80-pin PQFP
HV582	96	85		80		Serial	Half-Bridge		±75	30	169-pin TFBGA
HV583	128	90		80		Serial	Half-Bridge		±30	40	169-pin TFBGA
HV6810	10	90		80		Serial	Half-Bridge		-250	5	20-pin SOIC 300 mil
HV7224	40	260		240		Serial	Half-Bridge		±70	3	64-pin PQFP
HV7620	32	225		200		Serial	Half-Bridge		±50	10	64-pin PQFP
High-Voltage Interface: Amplifiers and MEMS Drivers											
Part #	Output Channels	Slew Rate (V/μs)	Closed Loop Gain (V/V)	Feedback Resistance (MΩ)	Source Current Max. (μA)	Sink Current Max. (μA)	Output Capacitive Load Max. (pF)		Packages		
HV256	32	2		72		12	715		3000		100-pin MQFP
HV264	4	9		66.7		5.3	3000		15		24-pin TSSOP
High-Voltage Interface: MOSFETs - Interface											
Part #	BV _{DSX} Min. (V)		R _{DS} (on) Max. (Ω)		V _{Gs (off)} Min. (V)		V _{Gs (off)} Max. (V)		Packages		
Depletion-Mode N-Channel											
LND01	9		1.4		-0.8		-3		5-pin SOT-23		
DN1509	90		6		-1.8		-3.5		3-pin SOT-89, 5-pin SOT-23		
DN2625	250		3.5		-1.5		-2.1		8-pin VDFN, 3-pin DPAK		
DN2530	300		12		-1		-3.5		3-pin TO-92, 3-pin SOT-89		
DN2450	500		10		-1.5		-3.5		3-pin DPAK, 3-pin SOT-89		
LND150	500		1000		-1		-3		3-pin TO-92, 3-pin SOT-89, 3-pin SOT-23		
DN2470	700		42		-1.5		-3.5		3-pin DPAK		

High-Voltage Interface: MOSFETs Interface								
Part #	BV _{DSS} Min. (V)	R _{Ds(on)} Max. (Ω)	C _{iss} Max. (pF)	V _{Gs(th)} Max. (V)	Packages			
Enhancement-Mode N-Channel								
TN0702	20	1.3	200	1.0	3-pin TO-92			
TN0104	40	2.0	70	1.6	3-pin TO-92, 3-pin SOT-89			
VN0808	80	4.0	50	2.0	3-pin TO-92			
VN2210	100	0.4	500	2.4	3-pin TO-92, 3-pin TO-39			
TN0620	200	6.0	150	1.6	3-pin TO-92			
TN2640	400	5.0	225	2.0	3-pin DPAK, 3-pin TO-92, 8-pin SOIC 150 mil			
VN2450	500	13.0	150	4.0	3-pin TO-92, 3-pin SOT-89			
VN2460	600	20.0	150	4.0	3-pin TO-92, 3-pin SOT-89			
Enhancement-Mode P-Channel								
TP2502	-20	2.0	125	-2.4	3-pin SOT-89			
TP0604	-40	2.0	150	-2.4	3-pin TO-92			
VP0808	-80	5.0	150	-4.5	3-pin TO-92			
TP2510	-100	3.5	125	-2.4	3-pin SOT-89			
TP2520	-200	12.0	125	-2.0	3-pin SOT-89			
TP2640	-400	15.0	300	-2.0	3-pin TO-92, 8-pin SOIC 150 mil			
VP2450	-500	30.0	190	-3.5	3-pin TO-92, 3-pin SOT-89			
High-Voltage Interface: MOSFETs Interface								
Part #	BV _{DSS} N-Channel (V)	BV _{DSS} P-Channel (V)	R _{Ds(on)} N-Channel Max. (Ω)	R _{Ds(on)} P-Channel Max. (Ω)	V _{Gs(th)} Max. (V)	Details	Packages	
Complementary (Enhancement Mode MOSFET Arrays)								
TC6320	200	-200	7.0	8.0	2.0	N- and P-Channel Pair	8-pin SOIC, 8-pin VDFN	
TC6321	200	-200	7.0	8.0	2.0	N- and P-Channel Pair	8-pin SOIC, 8-pin VDFN	
TC8220	200	-200	5.3	6.5	2.0	2 N- and P-Channel Pairs	12-pin VDFN	
High-Voltage Interface: Application Specific								
Part #	DC/DC	Input Voltage Min. (V)	Input Voltage Max. (V)	Output Voltage Min. (V _{RMS})	Output Voltage Max. (V _{RMS})	Load Min. (pF)	Load Max. (pF)	Packages
Liquid Lens Driver								
HV892	Internal Charge Pump	2.65	5.5	10	60	100	200	10-pin WDFN
High-Voltage Interface: Application Specific								
Part #	# of Channels	Input Voltage Min. (V)	Input Voltage Max. (V)	Output Voltage Min. (V)	Output Voltage Max. (V)	Input to Output Isolation (V)	Packages	
Complementary MOSFET LEVEL Translator Driver								
HT0440	2	3.15	5.5	6	10	±400	10-pin VDFN, 8-pin SOIC 150 mil	
HT0740	1	3.15	5.5	4.5	8.5	±400	8-pin SOIC 150 mil	
High-Voltage Interface: Application Specific								
Part #	V _{IN} (V)	Gain	Rise and Fall Time (μs)	V _{SENSE} Max. (mV)	Quiescent Current Max. (μA)	Packages		
High-Side Current Monitor								
HV7800	8.0–450	Fixed, 1	0.7–2.0	500	50	5-pin SOT-23		
HV7801	8.0–450	Fixed, 5	0.7–2.0	500	50	5-pin SOT-23		
HV7802	8.0–450	Adjustable	0.7–1.4	500	50	8-pin MSOP		

High-Voltage Interface: Application Specific														
Part #	V _{IN} Min. (V)	V _{IN} Max. (V)	I _{IN} Max. (mA)	Oscillator Frequency Min. (kHz)	Oscillator Frequency Max. (kHz)	Oscillator Frequency F _{SYNC} Max. (kHz)	Max. Output Duty Cycle (%)	Typical Current Sense Pull-In (V)	Typical Current Sense Hold	External Adjustable Regulator Output Voltage (V)	External Adjustable Regulator Output Current (mA)	Packages		
Relay Driver and Controller														
HV9901	10	450	2	20	140	150	99.5	0.883	Adjustable	2.0–5.5	0–1.0	14-pin SOIC		
Linear: Op Amps														
Product	# Per Package	GBWP (MHz)	I _O Typical (µA)	V _{OS} Max (mV)	Operating Voltage (V)	Packages		Product	# Per Package	GBWP (MHz)	I _O Typical (µA)	V _{OS} Max (mV)	Operating Voltage (V)	Packages
MCP661/2/3/4/5/9	1/2/1/4/2/4	60	6000	8	2.5 to 5.5	SOIC, MSOP, DFN, TSSOP, QFN, SOT		MCP6V01/2/3	1/2/1	1.3	300	0.002	1.8 to 5.5	SOIC, DFN, TDFN
MCP651/1S/2/3/4/5/9	1/1/2/1/4/2/4	50	6000	0.2	2.5 to 5.5	SOIC, MSOP, DFN, TSSOP, QFN, SOT		MCP6V06/7/8	1/2/1	1.3	300	0.003	1.8 to 5.5	SOIC, DFN, TDFN
MCP631/2/3/4/5/9	1/2/1/4/2/4	24	2500	8	2.5 to 5.5	SOIC, MSOP, DFN, TSSOP, QFN, SOT		MCP6071/2/4	1/2/4	1.2	110	0.15	1.8 to 6.0	SOIC, TSSOP, DFN, SOT
MCP621/1S/2/3/4/5/9	1/1/2/1/4/2/4	20	2500	0.2	2.5 to 5.5	SOIC, MSOP, DFN, TSSOP, QFN, SOT		MCP6H01/2/4	1/2/4	1.2	135	4.5	3.5 to 16	SOIC, TSSOP, TDFN, SOT, SC70
MCP6H91/2/4	1/2/4	10	2000	4	3.5 to 12.0	DFN, SOIC, TSSOP		MCP6001/2/4	1/2/4	1	100	4.5	1.8 to 6.0	PDIP, SOIC, MSOP, TSSOP, TDFN, SOT, SC70
MCP6V91/2/4	1/2/4	10	1100	0.009	2.4 to 5.5	TSSOP, MSOP, TDFN, SOT, SC70		MCP6401/2/4	1/2/4	1	45	4.5	1.8 to 6.0	SOIC, TSSOP, TDFN, SOT, SC70
MCP6021/2/3/4	1/2/1/4	10	1000	0.5	2.5 to 5.5	PDIP, SOIC, MSOP, TSSOP, SOT		MCP6V61/2/4	1/2/4	1	80	0.008	1.8 to 5.5	TSSOP, MSOP, TDFN, SOT, SC70
MCP6291/2/3/4/5	1/2/1/4/2	10	1000	3	2.4 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT		MCP6061/2/4	1/2/4	0.73	60	0.15	1.8 to 6.0	SOIC, TSSOP, DFN, SOT
MCP6491/2/4	1/2/4	7.5	530	1.5	2.4 to 5.5	SOT, SC70, MSOP, TDFN, SOIC, TSSOP		MCP6241/2/4	1/2/4	0.55	50	5	1.8 to 5.5	PDIP, SOIC, MSOP, TSSOP, TDFN, SOT, SC70
MCP6H81/2/4	1/2/4	5.5	700	4	3.5 to 12.0	DFN, SOIC, TSSOP		MCP6051/2/4	1/2/4	0.385	30	0.15	1.8 to 6.0	SOIC, TSSOP, DFN, SOT
MCP6V81/2/4	1/2/4	5	500	0.009	2.2 to 5.5	TSSOP, MSOP, TDFN, SOT, SC70		MCP6V31/2/4	1/2/4	0.3	23	0.008	1.8 to 5.5	TSSOP, MSOP, TDFN, SOT, SC70
MCP6281/2/3/4/5	1/2/1/4/2	5	445	3	2.2 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT		MCP6231/2/4	1/2/4	0.3	20	5	1.8 to 6.0	PDIP, SOIC, MSOP, TSSOP, TDFN, SOT, SC70
MCP6481/2/4	1/2/4	4	240	1.5	2.2 to 5.5	SOT, SC70, MSOP, TDFN, SOIC, TSSOP		MCP616/7/8/9	1/2/1/4	0.19	19	0.15	2.3 to 5.5	PDIP, SOIC, MSOP, TSSOP
MCP6286	1	3.5	540	1.5	2.2 to 5.5	SOT		MCP606/7/8/9	1/2/1/4	0.155	19	0.25	2.5 to 6.0	PDIP, SOIC, TSSOP, SOT
MCP601/2/3/4	1/2/1/4	2.8	230	2	2.7 to 6.0	PDIP, SOIC, TSSOP, SOT		MCP6141/2/3/4	1/2/1/4	0.1	0.6	3	1.4 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT
MCP6H71/2/4	1/2/4	2.7	480	4	3.5 to 12.0	DFN, SOIC, TSSOP		MCP6421/2/4	1/2/4	0.09	4.4	1	1.8 to 5.5	SOT, SC70, MSOP, SOIC, TSSOP
MCP6271/2/3/4/5	1/2/1/4/2	2	170	3	2.0 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT		MCP6V11/2/4	1/2/4	0.08	7.5	0.008	1.6 to 5.5	TSSOP, MSOP, TDFN, SOT, SC70
MCP6471/2/4	1/2/4	2	100	1.5	2 to 5.5	SOT, SC70, MSOP, TDFN, SOIC, TSSOP		MCP6041/2/3/4	1/2/1/4	0.014	0.6	3	1.4 to 6.0	PDIP, SOIC, MSOP, TSSOP, SOT
MCP6V26/7/8	1/2/1	2	620	0.002	2.3 to 5.5	SOIC, MSOP, DFN		MCP6031/2/3/4	1/2/1/4	0.01	0.9	0.15	1.8 to 5.5	SOIC, MSOP, TSSOP, DFN, SOT
MCP6V71/2/4	1/2/4	2	170	0.008	2.0 to 5.5	TSSOP, MSOP, TDFN, SOT, SC70		MCP6441/2/4	1/2/4	0.009	0.45	4.5	1.4 to 6.0	SOIC, MSOP, TSSOP, SOT, SC70
MCP6V51	1	2	470	0.015	4.5 to 45	SOT, MSOP								
Linear: Instrumentation Amps														
Product	Bandwidth (kHz)		I _O Typical (µA)		V _{OS} Max (µV)		Operating Voltage (V)		Features			Packages		
MCP6N11	500		800		350		1.8 to 5.5		Rail-to-rail input/output, enable pin, mCal technology			SOIC, TDFN		
MCP6N16	500		1100		17		1.8 to 5.5		Rail-to-rail input/output, enable pin, enhanced EMI rejection			MSOP, DFN		
Linear: Current Sense Amplifiers														
Part #	# per Package	Input Common-Mode Range (V)	V _{OS} Max (uV)	V _{OS} Drift Max (nV/°C)	Max Gain Error (%)	Bandwidth (kHz)	I _Q Max (mA)	Operating Voltage (V)	Temperature Range (°C)	Features		Packages		
MCP6C02	1	3 to 65	16 (G=20), 14 (G=50), 12 (G=100)	85 (G=20), 70 (G=50), 65, (G=100)	1.6	500 (G=20), 500 (G=50), 350 (G=100)	0.75	2 to 5.5	-40 to +125	Bidirectional Current Sense Amplifier, Enhanced EMI Rejection		6-pin SOT-23		
MCP6C04	1	3 to 52	30 (G=20), 27 (G=50), 24 (G=100)	180 (G=20), 140 (G=50), 130 (G=100)	1.6	500 (G=20), 500 (G=50), 350 (G=100)	0.84	2 to 5.5	-40 to +125	Bidirectional Current Sense Amplifier, Enhanced EMI Rejection		6-pin SOT-23		
Mixed Signal: Successive Approximation Register (SAR) Analog-to-Digital Converters														
Product	Resolution (bits)		Maximum Sampling Rate (samples/sec)		# of Input Channels		Input Type		Interface		Max. Supply Current (µA)	Temperature Range (°C)	Packages	
MCP3021/3221	10/12		22k		1		Single-ended		I ^C		250	-40 to +125	SOT-23A	
MCP3001/2/4/8	10		200k		1/2/4/8		Single-ended		SPI		500–550	-40 to +85	PDIP, SOIC, MSOP, TSSOP	
MCP3201/2/4/8	12		100k		1/2/4/8		Single-ended		SPI		400–550	-40 to +85	PDIP, SOIC, MSOP, TSSOP	
MCP3301/2/4	13		100k		1/2/4		Differential		SPI		450	-40 to +85	PDIP, SOIC, MSOP, TSSOP	
MCP33111D	12		1M		1		Differential		SPI		2250	-40 to +85	10-pin MSOP, 10-pin TDFN	
MCP33121D	14		1M		1		Differential		SPI		2250	-40 to +85	10-pin MSOP, 10-pin TDFN	
MCP33131D	16		1M		1		Differential		SPI		2250	-40 to +85	10-pin MSOP, 10-pin TDFN	

Mixed Signal: Digital-to-Analog Converters													
Product	Resolution (Bits)	DAC Channels	Memory	DNL (\pm Lsb)	INL (\pm Lsb)	Packages	Product	Resolution (Bits)	DAC Channels	Memory	DNL (\pm Lsb)	INL (\pm Lsb)	Packages
MCP48FEB01/11/21	8/10/12	1	EEPROM	0.25/0.5/1	0.5/1.5/6	MSOP-8	MCP47DA1	6	1	Volatile	0.35	0.7	SOT23-6, SC70-6
MCP48FEB02/12/22	8/10/12	2	EEPROM	0.25/0.5/1	0.5/1.5/6	MSOP-8	MCP4706/16/26	8/10/12	1	EEPROM	0.05/0.188/0.75	0.907/3.625/14.5	SOT23-6, 2 x 2 DFN-6
MCP48FVB01/11/21	8/10/12	1	Volatile	0.25/0.5/1	0.5/1.5/6	MSOP-8	MCP4725	12	1	EEPROM	0.75	14.5	SOT23-6
MCP48FVB02/12/22	8/10/12	2	Volatile	0.25/0.5/1	0.5/1.5/6	MSOP-8	MCP4728	12	4	EEPROM	0.75	13	MSOP-10
MCP47FEB01/11/21	8/10/12	1	EEPROM	0.25/0.5/1	0.5/1.5/6	MSOP-8	MCP4801/11/21	8/10/12	1	Volatile	0.5/0.5/0.75	1/3.5/12	MSOP-8, 2 x 3 DFN-8, SOIC-8, PDIP-8
MCP47FEB02/12/22	8/10/12	2	EEPROM	0.25/0.5/1	0.5/1.5/6	MSOP-8	MCP4802/12/22	8/10/12	2	Volatile	0.5/0.5/0.75	1/3.5/12	MSOP-8, 2 x 3 DFN-8, SOIC-8, PDIP-8
MCP47FVB01/11/21	8/10/12	1	Volatile	0.25/0.5/1	0.5/1.5/6	MSOP-8	MCP4901/11/21	8/10/12	1	Volatile	0.5/0.5/0.75	1/3.5/12	MSOP-8, 2 x 3 DFN-8, SOIC-8, PDIP-8
MCP47FVB02/12/22	8/10/12	2	Volatile	0.25/0.5/1	0.5/1.5/6	MSOP-8	MCP4902/12/22	8/10/12	2	Volatile	0.5/0.5/0.75	1/3.5/12	MSOP-8, 2 x 3 DFN-8, SOIC-8, PDIP-8
MCP47CVB01/11/21	8/10/12	1	Volatile	0.1/0.25/1	0.1/0.25/1	10-pin MSOP, 16-pin QFN, 10-pin DFN	MCP48CVB01/11/21	8/10/12	1	Volatile	0.1/0.25/1	0.1/0.25/1	10-pin MSOP, 16-pin QFN, 10-pin DFN
MCP47CVB02/12/22	8/10/12	2	Volatile	0.1/0.25/1	0.1/0.25/1	10-pin MSOP, 16-pin QFN, 10-pin DFN	MCP48CVB02/12/22	8/10/12	2	Volatile	0.1/0.25/1	0.1/0.25/1	10-pin MSOP, 16-pin QFN, 10-pin DFN
MCP47CMB01/11/21	8/10/12	1	MTP	0.1/0.25/1	0.1/0.25/1	10-pin MSOP, 16-pin QFN, 10-pin DFN	MCP48CMB01/11/21	8/10/12	1	MTP	0.1/0.25/1	0.1/0.25/1	10-pin MSOP, 16-pin QFN, 10-pin DFN
MCP47CMB02/12/22	8/10/12	2	MTP	0.1/0.25/1	0.1/0.25/1	10-pin MSOP, 16-pin QFN, 10-pin DFN	MCP48CMB02/12/22	8/10/12	2	MTP	0.1/0.25/1	0.1/0.25/1	10-pin MSOP, 16-pin QFN, 10-pin DFN

Mixed Signal: Energy Meter and Power Monitoring ICs												
Product	Dynamic Range	Typical Accuracy	ADC Channels	ADC Resolution	SINAD	Gain Selection	Output Type	Analog V _{DD} (V)	Digital V _{DD} (V)	Temperature Range (°C)	Features	Packages
MCP3918/10/19	10000:1	0.1%	1/2/3	24	94.5 dB	1 to 32	SPI/2-Wire	2.7–3.6	2.7–3.6	-40 to +125	Two Channel, 24-bit AFE with Phase Correction, Programmable Data Rate up to 125 kSPS, 16-bit CRC, Register Map Lock, 2-wire Interface	4 mm x 4 mm QFN-20, SSOP-20
MCP3911/12/13/14	10000:1	0.1%	2/4/6/8	24	94.5 dB	1 to 32	SPI	2.7–3.6	2.7–3.6	-40 to +125	Two Channel, 24-bit AFE with Phase Correction, Programmable Data Rate up to 125 kSPS, 16-bit CRC, Register Map Lock	4 mm x 4 mm QFN-20, SSOP-20
MCP39F511N	4000:1	0.5%	3	24	94.5 dB	1 to 32	UART/Single-wire	2.7–3.6	2.7–3.6	-40 to +125	Dual-channel power monitoring IC with active, reactive and apparent power, active and reactive energy, PF, RMS current/voltage, frequency, event notifications, EEPROM, PWM output	5 mm x 5 mm QFN-28
MCP39F511A	4000:1	0.1%	2	24	94.5 dB	1 to 32	UART/Single-wire	2.7–3.6	2.7–3.6	-40 to +125	AC/DC Dual-mode Power monitoring IC with active, reactive and apparent power, active and reactive energy, PF, RMS current/voltage, frequency, event notifications, EEPROM, PWM output	5 mm x 5 mm QFN-28

Mixed Signal: Current/DC Power Measurement ICs														
Product	# Current Sensors	Description			Full Scale Range (mV)	Current Measurement Max. Accr. (%)	Effective Sampling Interval Min. to Max. (msec)	Bus Voltage Range (V)	# Temp. Monitors (Ambient, Remote)	Temp. Accuracy Typ./Max. (°C)	Alert/Therm.	Peak Detection	Interface	Packages
PAC1710/20	1/2	Current/DC Power Sensor			10, 20, 40, 80	±1	2.5 to 2600	0 to +40	N/A	N/A	1	–	SMBus/I ² C	10-pin DFN
PAC1921	1	SMBus/I ² C Current/Power Sensor with Analog Output			100	±1	2.5 to 2900	0 to +32	N/A	N/A	–	–	SMBus/I ² C	10-pin DFN
PAC1934	4	SMBus/I ² C Current/Power Sensor with Accumulator			100	±0.9	0.98 to 125	0 to +32	N/A	N/A	1	–	SMBus/I ² C	WL CSP
EMC1701/2/4	1	Current/DC Power Sensor with Temperature Monitoring			10, 20, 40, 80	±1	2.5 to 2600	+3 to +24	1, 0/1/3	±0.25/±1.0	2	Y	SMBus/I ² C	12-pin QFN, 10-pin MSOP, 16-pin QFN, 14-pin SOIC

Mixed Signal: Digital Potentiometers											
Product	# of Taps	Memory	Channels	Interface	Resistance (kΩ)	Temperature Range (°C)	Packages				
MCP4011/12/13/14	64	Volatile	1	Up/Down	2.1, 5, 10, 50	-40 to +125	DFN, SOT-23				
MCP4017/18/19	128	Volatile	1	I ² C	5, 10, 50, 100	-40 to +125	SC70				
MCP40D17/D18/D19	128	Volatile	1	I ² C	5, 10, 50, 100	-40 to +125	SC70				
MCP4021/22/23/24	64	Nonvolatile	1	Up/Down	2.1, 5, 10, 50	-40 to +125	DFN, SOT-23				
MCP4141/42	128	Nonvolatile	1	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN				
MCP4241/42	128	Nonvolatile	2	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN				
MCP4131/32	128	Volatile	1	SPI	5, 10, 50, 100	-40 to +125	QFN, DFN				
MCP4231/32	128	Volatile	2	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN				
MCP4151/52	256	Volatile	1	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN				

Mixed Signal: Digital Potentiometers							
Product	# of Taps	Memory	Channels	Interface	Resistance (kΩ)	Temperature Range (°C)	Packages
MCP41HV31	128	Volatile	1	SPI	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP41HV51	256	Volatile	1	SPI	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4161/62	256	Nonvolatile	1	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN
MCP4251/52	256	Volatile	2	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN
MCP4261/62	256	Nonvolatile	2	SPI	5, 10, 50, 100	-40 to +125	MSOP, QFN, DFN
MCP4341/42	129	Nonvolatile	4	SPI	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4361/62	257	Nonvolatile	4	SPI	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4331/32	129	Volatile	4	SPI	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4351/52	257	Volatile	4	SPI	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4431/32	129	Volatile	4	I ² C	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4441/42	129	Nonvolatile	4	I ² C	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4451/52	257	Volatile	4	I ² C	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4461/62	257	Nonvolatile	4	I ² C	5, 10, 50, 102	-40 to +125	TSSOP, QFN
MCP4531/32	128	Volatile	1	I ² C	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4631/32	128	Volatile	2	I ² C	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4541/42	128	Nonvolatile	1	I ² C	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP46HV31	128	Volatile	1	I ² C	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP45HV51	256	Volatile	1	I ² C	5, 10, 50, 100	-40 to +125	TSSOP, QFN
MCP4641/42	128	Nonvolatile	2	I ² C	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4551/52	256	Volatile	1	I ² C	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4651/52	256	Volatile	2	I ² C	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4561/62	256	Nonvolatile	1	I ² C	5, 10, 50, 100	-40 to +125	MSOP, DFN
MCP4661/62	256	Nonvolatile	2	I ² C	5, 10, 50, 100	-40 to +125	MSOP, DFN

Mixed Signal: Delta-Sigma Analog-to-Digital Converters									
Product	Resolution (bits)	Maximum Sampling Rate (samples/sec)	# of Input Channels	Interface	Typical Supply Current (µA)	Temperature Range (°C)	Features	Packages	
MCP3461	16	153.6k	2	SPI	930	-40 to +125	One Differential or Two Single-ended Input Channels, 153.6 kSPS, Low-Noise 16-Bit Delta-Sigma ADCs	3 mm x 3 mm UQFN-20	
MCP3462	16	153.6k	4	SPI	930	-40 to +125	Two Differential or Four Single-ended Input Channels, 153.6 kSPS, Low-Noise 16-Bit Delta-Sigma ADCs	3 mm x 3 mm UQFN-20	
MCP3464	16	153.6k	8	SPI	930	-40 to +125	Four Differential or Eight Single-ended Input Channels, 153.6 kSPS, Low-Noise 16-Bit Delta-Sigma ADCs	3 mm x 3 mm UQFN-20	
MCP3561	24	153.6k	2	SPI	930	-40 to +125	One Differential or Two Single-ended Input Channels, 153.6 kSPS, Low-Noise 24-Bit Delta-Sigma ADCs	3 mm x 3 mm UQFN-20	
MCP3562	24	153.6k	4	SPI	930	-40 to +125	Two Differential or Four Single-ended Input Channels, 153.6 kSPS, Low-Noise 24-Bit Delta-Sigma ADCs	3 mm x 3 mm UQFN-20	
MCP3564	24	153.6k	8	SPI	930	-40 to +125	Four Differential or Eight Single-ended Input Channels, 153.6 kSPS, Low-Noise 24-Bit Delta-Sigma ADCs	3 mm x 3 mm UQFN-20	
MCP3910	24	125k	2	SPI/2-Wire	2500	-40 to +125	Two Channel, 125 kSPS, 24-bit Simultaneously Sampling Delta-Sigma ADCs with 2-Wire Mode, AEC-Q100 Grade 1	4 mm x 4 mm QFN-20, SSOP-20	
MCP3911	24	125k	2	SPI	2500	-40 to +125	Two Channel, 125 kSPS, 24-bit Simultaneously Sampling Delta-Sigma ADCs, AEC-Q100 Grade 1	4 mm x 4 mm QFN-20, SSOP-20	
MCP3912	24	125k	4	SPI	4700	-40 to +125	Four Channel, 125 kSPS, 24-bit Simultaneously Sampling Delta-Sigma ADCs, AEC-Q100 Grade 1	4 mm x 4 mm QFN-20, SSOP-20	
MCP3913	24	125k	6	SPI	7400	-40 to +125	Six Channel, 125 kSPS, 24-bit Simultaneously Sampling Delta-Sigma ADCs, AEC-Q100 Grade 1	4 mm x 4 mm QFN-20, SSOP-20	
MCP3914	24	125k	8	SPI	9800	-40 to +125	Eight Channel, 125 kSPS, 24-bit Simultaneously Sampling Delta-Sigma ADCs, AEC-Q100 Grade 1	4 mm x 4 mm QFN-20, SSOP-20	
MCP3918	24	125k	1	SPI/2-Wire	1300	-40 to +125	Single Channel, 125 kSPS, 24-bit Simultaneously Sampling Delta-Sigma ADCs, AEC-Q100 Grade 1	4 mm x 4 mm QFN-20, SSOP-20	
MCP3919	24	125k	3	SPI/2-Wire	3500	-40 to +125	Three Channel, 125 kSPS, 24-bit Simultaneously Sampling Delta-Sigma ADCs, AEC-Q100 Grade 1	4 mm x 4 mm QFN-20, SSOP-20	

Mixed Signal: Pipelined Analog-to-Digital Converters												
Product	Resolution (bits)	Maximum Sampling Rate (Msamples/sec)	# of Input Channels	Power Dissipation (mW)	Interface	Input Channel BW (MHz)	SNR (dB)	SFDR (dB)	Temperature Range (°C)	Features		
MCP37D10-200	12	200	1	338	Serial DDR LVDS or Parallel CMOS	650	67	96	-40 to +85	Digital down-converter, decimation filters, noise-shaping requantizer		124-pin VTLA, 121-pin TFBGA
MCP37210-200	12	200	1	338	Serial DDR LVDS or Parallel CMOS	650	67	96	-40 to +85	Decimation filters, noise-shaping requantizer		124-pin VTLA, 121-pin TFBGA
MCP37D11-200	12	200	8-mux, Diff	468	Serial DDR LVDS or Parallel CMOS	1.2, 1.8	71.3	90	-40 to +85	Decimation filters, digital down-converter, noise-shaping requantizer		124-pin VTLA, 121-pin TFBGA
MCP37211-200	12	200	8-mux, Diff	468	Serial DDR LVDS or Parallel CMOS	1.2, 1.8	71.3	90	-40 to +85	Decimation filters, noise-shaping requantizer		124-pin VTLA, 121-pin TFBGA
MCP37D20-200	14	200	1	348	Serial DDR LVDS or Parallel CMOS	650	67.8	96	-40 to +85	Digital down-converter, decimation filters		124-pin VTLA, 121-pin TFBGA
MCP37220-200	14	200	1	348	Serial DDR LVDS or Parallel CMOS	650	67.8	96	-40 to +85	Decimation filters, noise-shaping requantizer		124-pin VTLA, 121-pin TFBGA
MCP37D21-200	14	200	8-mux, Diff	490	Serial DDR LVDS or Parallel CMOS	1.2, 1.8	74.2	90	-40 to +85	Decimation filters, digital down-converter		124-pin VTLA, 121-pin TFBGA
MCP37221-200	14	200	8-mux, Diff	490	Serial DDR LVDS or Parallel CMOS	1.2, 1.8	74.2	90	-40 to +85	Decimation filters		124-pin VTLA, 121-pin TFBGA
MCP37D31-200	16	200	8-mux, Diff	490	Serial DDR LVDS or Parallel CMOS	500	74	90	-40 to +85	Decimation filters		124-pin VTLA, 121-pin TFBGA
MCP37231-200	16	200	8-mux, Diff	490	Serial DDR LVDS or Parallel CMOS	500	74	90	-40 to +85	Digital down-converter, decimation filters		124-pin VTLA, 121-pin TFBGA

Interface: CAN Products

Product	Description and Features	Operating Voltage (V)	Operating Temperature Range (°C)	Packages
ATA6560	CAN Transceiver with stand-by and silent mode, 5V I/O, CAN FD ready, 5 Mbps, AECQ100 Grade 1	4.5–5.5	-40 to +125	VDFN8, SOIC8
ATA6561	CAN Transceiver with stand-by mode, compatible with 3.3V and 5V microcontroller, CAN FD ready, 5 Mbps, AECQ100 Grade 1	4.5–5.5	-40 to +125	VDFN8, SOIC8
ATA6562	CAN Transceiver with stand-by and silent mode, 5V I/O, wake-up pattern, CAN FD ready, 5 Mbps, AECQ100 Grade 0, 1	4.5–5.5	-40 to +125/150	VDFN8, SOIC8
ATA6563	CAN Transceiver with stand-by mode, compatible with 3.3V and 5V microcontroller, wake-up pattern, CAN FD ready, 5 Mbps, AECQ100 Grade 0, 1	4.5–5.5	-40 to +125/150	VDFN8, SOIC8
ATA6564	CAN Transceiver with silent mode, compatible with 3.3V and 5V microcontroller, CAN FD ready, 5 Mbps, AECQ100 Grade 0, 1	4.5–5.5	-40 to +125/150	VDFN8, SOIC8
ATA6565	Dual CAN Transceiver with stand-by mode, 5V I/O, wake up pattern, CAN FD ready, 5 Mbps, AECQ100 Grade 0, 1	4.5–5.5	-40 to +125/150	VDFN14, SO14
ATA6566	CAN Transceiver with stand-by mode, compatible with 3.3V and 5V microcontroller, wake-up pattern, CAN FD ready, 2 Mbps, AECQ100 Grade 0, 1, suitable for the Japanese market	4.5–5.5	-40 to +125/150	VDFN8, SOIC8
ATA6570	CAN Partial Networking Transceiver with Wake pin and Window Watchdog, compatible with 3.3V and 5V microcontroller, wake-up pattern or wake-up frame, CAN FD ready, 5 Mbps, AECQ100 Grade 1	4.55–28	-40 to +125	SOIC14
MCP2515	Stand-Alone CAN 2.0B Controller with SPI Interface	2.7–5.5	-40 to +125	18-pin PDIP, 18-pin SOIC, 20-pin TSSOP
MCP2517FD	External CAN FD Controller with SPI Interface, ISO 11898-1:2015 Compliant, 32-bit Time Stamp, Supports CAN 2.0B and CAN FD, Highly Configurable 31 FIFOs and 32 Filters	2.7–5.5	-40 to +150	14-pin SOIC, 14-pin VDFN
MCP25625	Integrated High-Speed CAN Transceiver and CAN 2.0B Controller	2.7–5.5	-40 to +125	28-pin SSOP, 28-pin 6 × 6 QFN

Interface: LIN Products

Product	Description	V _{REG} Output Voltage (V)	Operating Temperature Range (°C)	V _{REG} Output Current (mA)	Supply Voltage Range (V)	Max. Baud Rate	LIN Specification Supported	Packages
ATA663211	LIN Transceiver	—	-40 to +125	—	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN8, SOIC8
ATA663201	LDO, pin compatible with ATA663231 LIN SBC	3.3	-40 to +125	85	5–28	—	—	VDFN8
ATA663203	LDO, pin compatible with ATA663254 LIN SBC	5.0	-40 to +125	85	5–28	—	—	VDFN8
ATA663231	LIN Transceiver with integrated V _{REG} , pinout acc. to OEM hardware recommendation	3.3	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN8
ATA663254	LIN Transceiver with integrated V _{REG} , pinout acc. to OEM hardware recommendation	5.0	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN8, SOIC8
ATA663232	LIN Transceiver with integrated V _{REG} and Wake Pin, pinout acc. to OEM hardware recommendation	3.3	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN8
ATA663255	LIN Transceiver with integrated V _{REG} and Wake Pin, pinout acc. to OEM hardware recommendation	5.0	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN8
ATA6625	LIN Transceiver with integrated V _{REG} , classic pinout	5.0	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN8, SOIC8
ATA663331	LIN Transceiver with integrated V _{REG} and 2 relay driver	3.3	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN16
ATA663354	LIN Transceiver with integrated V _{REG} and 2 relay driver	5.0	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN16
ATA663431	LIN Transceiver with integrated V _{REG} and WWDT	3.3	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN16

Interface: LIN Products												
Product	Description		V _{REG} Output Voltage (V)	Operating Temperature Range (°C)	V _{REG} Output Current (mA)	Supply Voltage Range (V)	Max. Baud Rate	LIN Specification Supported	Packages			
ATA663454	LIN Transceiver with integrated V _{REG} and WWDT		5.0	-40 to +125	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	VDFN16			
ATSAMHA1G14A	LIN System-in-Package (SiP) Solution incl. Arm® Cortex® M0+ MCU, 16 KB Flash memory		3.3	-40 to +85	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN48			
ATSAMHA1G15A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 32 KB Flash memory		3.3	-40 to +85	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN48			
ATSAMHA1G16A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 64 KB Flash memory		3.3	-40 to +85	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN48			
ATSAMHA1E14A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 16 KB Flash memory		3.3	-40 to +85	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN32			
ATSAMHA1E15A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 32 KB Flash memory		3.3	-40 to +85	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN32			
ATSAMHA1E16A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 64 KB Flash memory		3.3	-40 to +85	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN32			
ATSAMHA0E14A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 16 KB Flash memory		3.3	-40 to +105	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN32			
ATSAMHA0E15A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 32 KB Flash memory		3.3	-40 to +105	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN32			
ATSAMHA0E16A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 64 KB Flash memory		3.3	-40 to +105	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN32			
ATSAMHA0G14A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 16 KB Flash memory		3.3	-40 to +105	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN48			
ATSAMHA0G15A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 32 KB Flash memory		3.3	-40 to +105	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN48			
ATSAMHA0G16A	LIN System-in-Package (SiP) Solution incl. Arm Cortex M0+ MCU, 64 KB Flash memory		3.3	-40 to +105	85	5–28	20 kBaud	2.0, 2.1, 2.2, 2.2A, SAEJ2602-2	QFN48			
Ultrasound: T/R Switch ICs												
Product	Number of Channels	Voltage (V)	RSW	Diode Clamps	V _{TRIP} (V)	BW (MHz)	Packages					
MD0100	1 or 2	±100	15	No	±2.0	100	3-pin SOT-89, 8-pin VDFN					
MD101	4	±100	15	Yes	±2.0	100	18-pin VDFN					
MD0105	4	±100	15	Yes	±2.0	100	18-pin VDFN					
Ultrasound: Arbitrary Waveform Generator												
Product	Resolution	Amplitude Control	Apodization	Input Voltage (V)	Typical Delay Time (ns)	Output Current (A)	Packages					
MD2131	7.5° Phase	PWM	8-bit SPI	2.5	4	0–3.0	40-pin WQFN					
MD2134	±127 steps	PWM	8-bit SPI	2.5	4	0–3.0	40-pin WQFN					
Ultrasound: MOSFET Driver												
Product	Number of Drivers	Input Voltage Min. (V)	Input Voltage Max. (V)	Output Voltage Bipolar (V)	Output Voltage Unipolar (V)	Packages						
MD1210	2	1.2	5	–	0–12	12-pin QFN						
MD1711	12	1.8	5.5	–	0–12	48-pin LQFP, 48-pin VQFN						
MD1712	12	1.8	5.5	–	0–12	48-pin LQFP, 48-pin VQFN						
MD1715	2	1.8	3.6	–	0–12	40-pin VQFN						
MD1810	4	1.2	5	±5.0	0–12	16-pin QFN						
MD1811	4	1.2	5	±5.0	0–12	16-pin QFN						
MD1820	4	1.7	5.25	±5.0	0–12	16-pin VQFN						
MD1822	4	1.7	5.25	±5.0	0–12	16-pin VQFN						
Ultrasound: High-Voltage Ultrasound Transmitters												
Product	Number of Channels	Output Voltage (V)	Number Output Levels	HD2 (dB)	Output Current (A)	Features			Packages			
HV7321	4	±80	5	-44	±2.5	Built-in T/R switches, output protection diodes and clamp diodes			64-pin VQFN (9 x 9 mm)			
HV7350	8	±60	3	-40	±1.0	Built-in floating power supplies			56-pin VQFN			
HV7351	8	±70	3	-40	±3.0	Programmable launch delay, 4 transmit waveforms, clock up to 200 MHz			80-pin VQFN			
HV7360	1	±100	3	–	±2.5	Built-in coupling capacitors			22-pin CABGA			
HV7361	1	±100	3	–	±2.5	Built-in T/R switch, 8 capacitors			22-pin CABGA			
HV748	4	±75	2	-40	±1.25	Built-in coupling, 4 current modes			48-pin VQFN			

Ultrasound: MOSFET Array										
Product	BVdss/BVdss N-Channel (V)		BVdss/BVdss P-Channel (V)		Rds(on) N-Channel max (Ω)	Rds(on) P-Channel max (Ω)	Vgs(th) max (V)	Note	Package	
TC6320	200		-200		7	8	2	N- and P-Channel pair	8-pin SOIC, 8-pin VDFN	
TC8020	200		-200		8	9.5	3	Six N- and P-Channel pairs	56-pin VQFN	
TC8220	200		-200		5.3	6.5	2	Two N- and P-Channel Pairs	12-pin VDFN	
CO and Smoke Detector ICs										
Product	Horn Driver	Detection Method	Low Battery Detection	Alarm Memory	Alarm Interconnect	Hush/Sensitivity Timer	Operating Temperature Range (°C)	Packages		
RE46C191	Yes	Photo	Yes	Yes	Yes	Yes	-10 to +60	16-pin SOIC		
RE46C317/8	Yes	Just Driver	No	No	No	No	-10 to +60	PDIP, SOIC		
RE46C803	Yes	CO	No	No	No	No	-10 to +60	20-pin SSOP		
Motor Drivers: Stepper Motors, DC Motors and 3-Phase BLDC Fan Controllers										
Product	Motor Type	Input Voltage Range (V)	Internal/External FETs	Output Current (mA)	Control Scheme	Motor Speed Output	Protections	Operating Temp. Range (°C)	Features	Packages
ATA6826C	DC Motor	7 to 40	Internal	1000	SPI	N/A	Short Circuit, Overtemperature, Power Supply Fail	-40 to 125	3 half bridge outputs, No shoot-through, Very low quiescent current <2 μA	SO14
ATA6831C(2C)	DC Motor	7 to 40	Internal	1000	SPI	N/A	Short Circuit, Overtemperature, Power Supply Fail	-40 to 125 (150)	3 half bridge outputs, No shoot through, Very low quiescent current <2 μA, PWM input	18-pin 4 x 4 QFN
ATA6836C(8C)	DC Motor	7 to 40	Internal	650 (950)	SPI	N/A	Short Circuit, Overtemperature, Power Supply Fail	-40 to 125	6 half bridge outputs, No shoot through, Very low quiescent current <2 μA	24-pin 5 x 5 QFN, SO28
ATA6823C(4C)	DC Motor	7 to 20	Internal	100	PWM, DIR	N/A	Short Circuit, Overtemperature, Over/Under Voltage, Chargepump Fall	-40 to 125 (150)	Dead time adjust, Charge pump supply for external battery reverse protection NMOS, LDO 3.3V/5V, Window Watchdog, LIN TRX (HV interface)	32-pin 7 x 7 QFN, 32-pin 7 x 7 TQFP
MCP8026	3-Phase Brushless Motors	6 to 28	External	500	Direct PWM	N/A	Overcurrent, Overvoltage, Undervoltage, Overtemperature, 48V Load Dump Protection, Short Circuit, Shoot Through	-40 to +150	3 Op Amps, Adj. Buck Regulator, 5V LDO, 12V LDO, Thermal Warning, Dead Time, Blanking Time, Level Translator, Motor Enable, Sleep Mode (MCP8026)	40-pin 5 x 5 QFN, 48-pin 7 x 7 TQFP
MCP8025A	3-Phase Brushless Motor	6 to 19	External	500	Direct PWM	N/A	Overcurrent, Overvoltage, Undervoltage, Overtemperature, 48V Load Dump Protection, Short Circuit, Shoot Through	-40 to +150	Sleep Mode, LIN Transceiver, AZ Output, Adj. Buck Regulator, LDO, Op Amp, Overcurrent Comparator, Fault Output, Thermal Warning, Selectable Dead Time and Blanking Time	40-pin 5 x 5 QFN, 48-pin 7 x 7 TQFP
MTS62C19A/MTS2916A	One Bipolar Stepper Motor or Two DC Motors	10 to 40	Internal	750	Direct PWM Input, Current Limit Control, Microstepping	No	Overtemperature, Under Voltage	-40 to +105	Dual Full-Bridge Motor Driver for Stepper Motors, Pin Compatible with Allegro 6219	24-pin SOIC
MCP8063	3-Phase Brushless Motor	2 to 14	Internal	750	Sensorless Sinusoidal	Frequency Generator	Overtemperature, Motor Lock-up, Overcurrent, Overvoltage	-40 to +125	3-Phase BLDC 180° Sinusoidal Sensorless Fan Motor Driver, Overcurrent limitation, Output Switching Frequency at 23 kHz	Thermally Enhanced 8-pin 4 x 4 DFN
MTD650X	3-Phase Brushless Motor	2 to 14 (5,5)	Internal	500-800	Sensorless Sinusoidal	Frequency Generator	Overtemperature, Motor Lock-up, Overcurrent, Overvoltage	-30 (-40) to +95 (125)	3-Phase BLDC 180° Sinusoidal Sensorless Drive, Direction Control, Programmable BEMF Coefficient Range, 20 kHz+ Output Switching Frequency, Programmable Start-up RPM and Slew Rate, Selectable Start-up Strength and Phase Target Regulation	SOP, DFN, QFN

Oscillators: Ultra-Low Jitter									
Product	Output Frequency (MHz)	Output Logic	Input Function	Frequency Stability (ppm)	Temperature Range (C)	Supply Voltage (V)	Phase Noise (ps RMS)	Package	
MX57	10 to 860	LVCMOS, LVPECL, LVDS, HCSL	OE on Pin1 or OE on pin2	±50	-40 to 85	2.375 to 3.63	0.16 (12k–20M)	7.0 x 5.0 mm 6-pin	
MX55	10 to 860	LVCMOS, LVPECL, LVDS, HCSL	OE on Pin1 or OE on pin3	±50	-40 to 85	2.375 to 3.63	0.16 (12k–20M)	5.0 x 3.2 mm 6-pin	
MX574BBD322M265	322.265625	HCSL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.143/0.098	7.0 x 5.0 mm 6-pin	
MX555ANR133M333	133.3333	LVPECL	OE on pin2	±50	-40 to 85	2.375 to 3.63	0.143/0.092	5.0 x 3.2 mm 6-pin	
MX553BBA156M250	156.25	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.165/0.11	5.0 x 3.2 mm 6-pin	
MX553BBB156M250	156.25	LVDS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.162/0.093	5.0 x 3.2 mm 6-pin	
MX573BBA156M250	156.25	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.165/0.11	7.0 x 5.0 mm 6-pin	
MX553BBA312M500	312.5	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.155/0.108	5.0 x 3.2 mm 6-pin	
MX575ABA25M0000	25	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.152/0.088	7.0 x 5.0 mm 6-pin	
MX573LBB148M500	148.5	LVDS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.149/0.096	7.0 x 5.0 mm 6-pin	
MX555ABD100M000	100	HCSL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.22/0.1	5.0 x 3.2 mm 6-pin	
MX573NBA622M080	622.08	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.148/0.103	7.0 x 5.0 mm 6-pin	
MX573BBB156M250	156.25	LVDS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.162/0.093	5.0 x 3.2 mm 6-pin	
MX554BBD322M265	322.265625	HCSL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.154/0.1	5.0 x 3.2 mm 6-pin	
MX574BBD322M265	322.265625	HCSL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.154/0.1	7.0 x 5.0 mm 6-pin	
MX573BBA312M500	312.5	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.148/0.103	7.0 x 5.0 mm 6-pin	
MX573BBB312M500	312.5	LVDS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.175/0.08	7.0 x 5.0 mm 6-pin	
MX555ABA25M0000	25	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.152/0.08	5.0 x 3.2 mm 6-pin	
MX575ABA200M000	200	LVDS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.22/0.1	7.0 x 5.0 mm 6-pin	
MX555ABA200M000	200	LVDS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.22/0.1	5.0 x 3.2 mm 6-pin	
MX575ABC200M000	200	LVCMOS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.128/0.089	7.0 x 5.0 mm 6-pin	
MX575ABC125M000	125	LVCMOS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.128/0.089	7.0 x 5.0 mm 6-pin	
MX553ABA212M500	212.5	LVDS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.175/0.08	5.0 x 3.2 mm 6-pin	
MX573ABA212M500	212.5	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.175/0.08	7.0 x 5.0 mm 6-pin	
MX555ABA150M000	150	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.143/0.098	5.0 x 3.2 mm 6-pin	
MX575ABD100M000	100	HCSL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.22/0.1	7.0 x 5.0 mm 6-pin	
MX555ABD100M000	100	HCSL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.22/0.1	5.0 x 3.2 mm 6-pin	
MX575ABA100M000	100	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.152, 0.112	7.0 x 5.0 mm 6-pin	
MX555ABC50M0000	50	LVCMOS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.142, 0.1	5.0 x 3.2 mm 6-pin	
MX575ABC50M0000	50	LVCMOS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.142, 0.1	7.0 x 5.0 mm 6-pin	
MX555ABA50M0000	50	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.142, 0.101	5.0 x 3.2 mm 6-pin	
MX575ABA50M0000	50	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.142, 0.101	7.0 x 5.0 mm 6-pin	
MX555ABC25M0000	25	LVCMOS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.131, 0.077	5.0 x 3.2 mm 6-pin	
MX575ABC25M0000	25	LVCMOS	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.131, 0.077	7.0 x 5.0 mm 6-pin	
MX574BBF644M531	644.5125	LVPECL	OE on pin1	±50	-40 to 85	2.375 to 3.63	0.139, 0.101	7.0 x 5.0 mm 6-pin	

Clock and Data Distribution: Buffers																	
Product	Buffer Type	Fanout	Input MUX	Input Type	EEPROM	Termination	Output Type	Supply Voltage (V)	Output Frequency (Max) (MHz)	Host BUS	Output Data Rate (Max) (Gbps)	Propagation Delay (Max) (ps)	Within Device Skew (Max) (ps)	Output Enable	Runt Pulse Eliminator (RPE)	Fail-Safe Input (FSI)	Packages
PL123-02N	Fanout	1:2		LVCMOS			LVCMOS	1.8/2.5/3.3	200				500			6/DFN	
PL123-05	Zero Delay	1:5		LVCMOS			LVCMOS	3.3	100/134				250			8/SOIC	
PL123-09	Zero Delay	1:9		LVCMOS			LVCMOS	3.3	100/134				250			16/SOIC 16/TSSOP	
PL123E-05	Zero Delay	1:5		LVCMOS			LVCMOS	2.5/3.3	220/167/200/134							8/SOIC	
PL123E-09	Zero Delay	1:9		LVCMOS			LVCMOS	2.5/3.3	220/167/200/134							16/SOIC	
PL133-21	Fanout	1:2		LVCMOS/Sine Wave			LVCMOS	1.8/2.5/3.3	150				500			6/UDFN	
PL133-27	Fanout	1:2		LVCMOS/Sine Wave			LVCMOS	1.8/2.5/3.3	150				500			6/UDFN	

Clock and Data Distribution: Buffers

Product	Buffer Type	Fanout	Input MUX	Input Type	EEPROM	Termination	Output Type	Supply Voltage (V)	Output Frequency (Max) (MHz)	Host BUS	Output Data Rate (Max) (Gbps)	Propagation Delay (Max) (ps)	Within Device Skew (Max) (ps)	Output Enable	Runt Pulse Eliminator (RPE)	Fail-Safe Input (FSI)	Packages
PL133-37	Fanout	1:3		LVCMOS/Sine Wave			LVCMOS	1.8/2.5/3.3	150				250				6/SOT-23
PL133-47	Fanout	1:4		LVCMOS			LVCMOS	2.5/3.3	150			9200	250				8/SOIC 150mil
PL133-67	Fanout	1:6		LVCMOS			LVCMOS	2.5/3.3	150			9200	250				16/TSSOP
PL133-97	Fanout	1:9		LVCMOS			LVCMOS	2.5/3.3	150			9200	250				16/QFN
PL133-97	Fanout	1:9		LVCMOS			LVCMOS	1.8/2.5/3.3	0.15			9200	250	Yes			16/VQFN
PL135-27	Fanout	1:2		Crystal Oscillator			LVCMOS	1.8/2.5/3.3	40				500				6/UDFN
PL135-37	Fanout	1:3		Crystal Oscillator			LVCMOS	1.8/2.5/3.3	40				250				8/SOIC 150mil
PL135-47	Fanout	1:4		Crystal			LVCMOS	1.8/2.5/3.3	0.04				250	Yes			16/TSSOP
PL135-67	Fanout	1:6		Crystal			LVCMOS	1.8/2.5/3.3	0.04				250	Yes			16/WQFN
PL138-48	Fanout	1:4	2:1	LVDS/LVPECL/LVHSTL/SSTL/HCSL/LVCMOS			LVPECL	2.5/3.3	800			890	37				16/QFN and 20/TSSOP
SY100E222L	Fanout	1:15	2:1	LVECL/LVPECL			LVPECL	3.3	1500			1520	50				52/LQFP
SY100EL11V	Fanout	1:2		ECL			ECL	3.3/5	800			365	20				8/SOIC
SY100EL14V	Fanout	1:5	2:1	ECL/PECL			PECL	3.3/5				880	50	Yes			20/SOIC
SY100EP111U	Fanout	1:10	2:1	LVPECL/LVECL/HSTL			PECL	2.5/3.3	3000			400	25				32/TQFP
SY100EP11U	Fanout	1:2		LVPECL/PECL/ECL			PECL	2.5/3.3/5	3			300	20				8/MSOP 8/SOIC
SY100EP14U	Fanout	1:5	2:1	PECL, LVPECL, ECL, HSTL			ECL	2.5/3.3/5	2			600	25	Yes			20/TSSOP
SY100EP15V	Fanout	1:4	2:1	PECL, LVPECL, ECL, HSTL			LVPECL	2.5/3.3/5	2.5			425	25	Yes			16/TSSOP 32/TQFP
SY10EP11U	Fanout	1:2		LVPECL/PECL/ECL			PECL	2.5/3.3/5	3			300	20				8/MSOP 8/SOIC
SY54020AR	Fanout	1:4		ANY			CML	2.5	3.2		3.2	400	20	Yes			16/MLF
SY56011R	Fanout	1:2		ANY			CML	2.5	4.5		6.4	280	15				16/QFN
SY56020R	Fanout	1:4		ANY			CML	2.5	4.5		6.4	280	15	Yes			16/QFN
SY58011U	Fanout	1:2		ANY			CML	2.5/3.3	7		10.7	250	15				16/QFN
SY58012U	Fanout	1:2		ANY			LVPECL	2.5/3.3	5		5	260	15				16/MLF
SY58020U	Fanout	1:4		ANY			CML	2.5/3.3	6			250	15				16/QFN
SY58021U	Fanout	1:4		ANY			LVPECL	2.5/3.3	4		5	300	15				16/QFN
SY58031U	Fanout	1:8		ANY			CML	2.5/3.3	5			270	20				16/QFN
SY58032U	Fanout	1:8		ANY			LVPECL	2.5/3.3	4			330	20				32/MLF
SY58035U	Fanout	1:6	2:1	ANY			LVPECL	2.5/3.3	4.5			230	20				32/MLF
SY58606U	Fanout	1:2		ANY			CML	2.5/3.3	2.5		4.25	400	15		Yes		16/QFN
SY58607U	Fanout	1:2		ANY			LVPECL	2.5/3.3	2.5		3.2	450	20			Yes	16/QFN
SY58608U	Fanout	1:2		ANY			LVDS	2.5	2		3.2	420	20			Yes	16/QFN
SY75572L	PCIe Fanout	1:2	2:1	HCSL/LVDS			HCSL	3.3	267				50	Yes			16/VQFN
SY75576L	PCIe Fanout	1:4	2:1	HCSL/LVDS			HCSL/LVDS	3.3	267				50	Yes			20/TSSOP
SY89112U	Fanout	1:12	2:1	ANY			LVPECL	2.5/3.3	3			550	25				44/QFN
SY89311U	Fanout	1:2		ECL/PECL/LVPECL/LVECL			ECL/PECL/LVPECL/LVECL	2.5/3.3/5	3			300	20				8/MLF

Clock and Data Distribution: Buffers																	
Product	Buffer Type	Fanout	Input MUX	Input Type	EEPROM	Termination	Output Type	Supply Voltage (V)	Output Frequency (Max) (MHz)	Host BUS	Output Data Rate (Max) (Gbps)	Propagation Delay (Max) (ps)	Within Device Skew (Max) (ps)	Output Enable	Runt Pulse Eliminator (RPE)	Fail-Safe Input (FSI)	Packages
SY89467U	Fanout	1:20	2:1	ANY			LVPECL	2.5/3.3	1.5			1200	20			Yes	64/TQFP
SY89468U	Fanout	1:20	2:1	ANY			LVDS	2.5	1.5			1200	25			Yes	64/TQFP
SY897132L	Link Replicator	1:2	2:1	LVPECL			LVPECL	3.3	0.8		1.5	4000		Yes			28/TSSOP
SY89830U	Fanout	1:4	2:1	ECL/PECL/ LVPECL/ LVECL			ECL/PECL/ LVPECL/ LVECL	2.5/3.3/5	2.5			450	25				16/TSSOP
SY89831U	Fanout	1:4		ANY			LVPECL	2.5/3.3	2			390	20				16/VQFN
SY89832U	Fanout	1:4		ANY			LVDS	2.5	2			570	20				16/VQFN
SY89833AL	Fanout	1:4		ANY			LVDS	3.3	2			600	20				16/VQFN
SY89833L	Fanout	1:4		ANY			LVDS	3.3	2			600	20				16/VQFN
SY89835U	Fanout	1:2		LVDS			LVDS	2.5	3.2		2	500	20			Yes	8/MLF
SY89837U	Fanout	1:8	2:1	ANY			LVPECL	2.5/3.3	1.5			975	40		Yes	Yes	32/VQFN
SY89838U	Fanout	1:8	2:1	ANY			LVDS	2.5	1.5			950	40		Yes	Yes	32/VQFN
SY89846U	Fanout	1:5	2:1	ANY			LVPECL	2.5/3.3	1.5			900	20			Yes	32/VQFN
SY89847U	Fanout	1:5	2:1	ANY			LVDS	2.5	1.5			1000	20			Yes	32/VQFN
SY898530U	Fanout	1:16		LVDS/ LVPECL/ LVHSTL/ SSTL/HCSL			LVPECL	3.3	0.5			2000	50				48/TQFP
SY898535XL	Fanout	1:4	2:1	XTAL/ LVCMS/ LVTTL			LVPECL	3.3	0.24			1750	30				20/TSSOP
SY89854U	Fanout	1:4		ANY			LVPECL	2.5/3.3	3.5			340	20				16/VQFN
ZL40200	Fanout	1:2	1:1	LVPECL, LVDS, HCSL, CML		External	LVPECL	2.5/3.3	750								16/QFN
ZL40201	Fanout	1:2	1:1	LVPECL, LVDS, HCSL, CML		Internal	LVPECL	2.5/3.3	750								16/QFN
ZL40202	Fanout	1:4	1:1	LVPECL, LVDS, HCSL, CML		External	LVPECL	2.5/3.3	750								16/QFN
ZL40203	Fanout	1:4	1:1	LVPECL, LVDS, HCSL, CML		Internal	LVPECL	2.5/3.3	750								16/QFN
ZL40204	Fanout	1:6	1:1	LVPECL, LVDS, HCSL, CML		External	LVPECL	2.5/3.3	750								32/QFN
ZL40205	Fanout	1:6	1:1	LVPECL, LVDS, HCSL, CML		Internal	LVPECL	2.5/3.3	750								32/QFN
ZL40206	Fanout	1:8	1:1	LVPECL, LVDS, HCSL, CML		External	LVPECL	2.5/3.3	750								32/QFN
ZL40207	Fanout	1:8	1:1	LVPECL, LVDS, HCSL, CML		Internal	LVPECL	2.5/3.3	750								32/QFN
ZL40208	Fanout	1:6	2:1	LVPECL, LVDS, HCSL, CML		External	LVPECL	2.5/3.3	750								32/QFN
ZL40209	Fanout	1:6	2:1	LVPECL, LVDS, HCSL, CML		Internal	LVPECL	2.5/3.3	750								32/QFN
ZL40210	Fanout	1:8	2:1	LVPECL, LVDS, HCSL, CML		External	LVPECL	2.5/3.3	750								32/QFN

Clock and Data Distribution: Buffers

Clock and Data Distribution: Buffers																	
Product	Buffer Type	Fanout	Input MUX	Input Type	EEPROM	Termination	Output Type	Supply Voltage (V)	Output Frequency (Max) (MHz)	Host BUS	Output Data Rate (Max) (Gbps)	Propagation Delay (Max) (ps)	Within Device Skew (Max) (ps)	Output Enable	Runt Pulse Eliminator (RPE)	Fail-Safe Input (FSI)	Packages
ZL40234	Fanout	1:4	2:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS			LVPECL, LVDS, HCSL	2.5/3.3	1600								32/qfn
ZL40235	Fanout	1:4	2:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS			LVPECL, LVDS, HCSL	2.5/3.3	1600	SPI				YES			32/qfn
ZL40240	Fanout	1:10	2:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS			LVC MOS	2.5/3.3	250	SPI				YES			32/qfn
ZL40241	Fanout	1:10	2:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS			LVC MOS	2.5/3.3	250								32/qfn
ZL40260	Fanout	1:10	2:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS			LVPECL	2.5/3.3	1600								32/qfn
ZL40250	Programmable Fanout	1:6	3:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS	External		LVDS, LVPECL, HCSL, CMOS, HSTL	2.5/3.3	1000	SPI/I2C				YES			56/QFN
ZL40251	Programmable Fanout	1:6	3:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS	Internal		LVDS, LVPECL, HCSL, CMOS, HSTL	2.5/3.3	1000	SPI/I2C				YES			56/QFN
ZL40252	Programmable Fanout	1:10	3:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS	External		LVDS, LVPECL, HCSL, CMOS, HSTL	2.5/3.3	1000	SPI/I2C				YES			56/QFN
ZL40253	Programmable Fanout	1:10	3:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS	Internal		LVDS, LVPECL, HCSL, CMOS, HSTL	2.5/3.3	1000	SPI/I2C				YES			56/QFN
ZL40255	Programmable Fanout	1:10	3:1	LVPECL, HCSL, LVDS, SSTL, CML, LVC MOS	Internal		CML	2.5/3.3	1000	SPI/I2C				YES			32/QFN
ZL40292	DB2000/PCIe Fanout	1:20	1:1	HCSL			LPHCSL	3.3	250					YES			72/QFN
ZL40293	PCIe Fanout	1:20	1:1	HCSL			LPHCSL	3.3	250					YES			72/QFN
ZL40294	DB2000/PCIe Fanout	1:20	1:1	HCSL			LPHCSL	3.3	250					YES			80/GQFN
ZL40295	PCIe Fanout	1:20	1:1	HCSL			LPHCSL	3.3	250					YES			80/GQFN
ZL40262	PCIe Fanout	1:1	1:2	HCSL			HCSL		400					YES			20/QFN
ZL40264	PCIe Fanout	1:1	1:4	HCSL			HCSL		400					YES			20/QFN

Clock and Data Distribution: Dividers												
Product	Divide by	MUX: Fanout	Input Type	Output Type	Supply Voltage (V)	Output Frequency (Max) (GHz)	Propagation Delay (Max) (ps)	Within Device Skew (Max) (ps)	Internal Termination	Output Enable	Fail-Safe Input (FSI)	Packages
SY89872U	2, 4, 8, 16	1:2	ANY	LVDS	2.5V	2	750	15	Yes	Yes		16/QFN
SY89876L	1, 2, 4, 8, 16	1:2	ANY	LVDS	3.3V	2	870	15	Yes			16/QFN
SY89875U	1, 2, 4, 8, 16	1:2	ANY	LVDS	2.5V	2	870	15	Yes	Yes		16/QFN
SY89871UMG	2, 4, 8, 16	1:3	ANY	LVPECL	2.5/3.3	3.2	670	15	Yes	Yes		16/QFN
SY100EP32V	2	1:1	ECL	ECL	5/3.3	4	440					8/MSOP, 8/SOIC
SY100EL33	4	1:1	ECL	ECL	3.3	3.8	630					8/SOIC
SY89874U	1, 2, 4, 8, 16	1:2	ANY	LVPECL	2.5/3.3V	2.5	790	15	Yes	Yes		16/QFN
SY89873L	2, 4, 8, 16	1:2	ANY	LVDS	3.3V	2	800	15	Yes	Yes		16/QFN
SY89874AU	1, 2, 4, 8, 16	1:2	ANY	LVPECL	2.5/3.3V	2.5	570	15	Yes	Yes		16/QFN
SY89200U	1, 2, 4	1:3	ANY	LVDS	2.5	1.5	900	25	Yes			32/QFN
SY89202U	1, 2, 4	1:8	ANY	LVPECL	2.5/3.3	1.5	930	25	Yes	Yes		32/VQFN
SY89228U	3, 5	1:1	ANY	LVPECL	2.5/3.3V	1	1500		Yes		Yes	16/QFN
SY100S834L	1, 2, 4 or 2, 4, 8	1:1	ECL/PECL	ECL/PECL	3.3		1200	50		Yes		16/SOIC
SY89230U	3, 5	1:1	ANY	LVPECL	2.5/3.3V	3.2	850		Yes		Yes	16/QFN
SY100EL32V	2	1:1	LVPECL	LVPECL	3.3/5	3	630					8/SOIC
SY100EP33V	4	1:1	ECL	ECL	5/3.3	4	500					16/SOIC
SY100EL34	2, 4, 8	1:3	ECL/PECL	ECL/PECL	5		1200	50		Yes		16/SOIC
SY100EL34L	2, 4, 8	1:3	ECL/PECL	ECL/PECL	3.3		1200	50		Yes		16/SOIC
SY89218U	1, 2, 4	2:15	ANY	LVDS	2.5	1.5	1600	35	Yes		Yes	64/TQFP
SY89221U	1, 2, 4	2:15	ANY	LVPECL	2.5/3.3V	1.5	1600	35	Yes		Yes	64/TQFP
SY89231U	3, 5	1:1	ANY	LVDS	2.5V	3.2	810		Yes	Yes		16/QFN
Clock and Data Distribution: Drivers and Receivers												
Product	Function	Channels	Feature	Input Type	Output Type	Supply Voltage (V)	Output Frequency (Max) (GHz)	Output Data Rate (Max) (Gbps)	Propagation Delay (Max) (ps)	Icc (mA)	Fail Safe Input (FSI)	Packages
SY89251V	Receiver	Single	Output Enable	ECL/LVPECL	ECL/LVPECL	3.3/5V			380	26		8/DFN
SY100EL16V	Receiver	Single		ECL/PECL	ECL/PECL	3.3/5V			425	26		8MSOP/SOIC
SY58600U	Driver/Receiver	Single	Internal Termination	ANY	CML	2.5/3.3V	10.7	7	220	65		8/MLF
SY58603U	Buffer	Single	Fail-Safe Input (FSI)	ANY	CML	2.5/3.3V	4.25	2.5	350	50	Yes	8/DFN
SY58605U	Buffer	Single	Fail-Safe Input (FSI)	ANY	LVDS	2.5V	3.2	2	420	50	Yes	8/DFN
SY89250V	Receiver	Single	Output Enable	LVECL/LVPECL	PECL	3.3/5V		0.8	380	46		8/MLF
SY58604U	Buffer	Single	Fail-Safe Input (FSI)	ANY	LVPECL	2.5/3.3V	3.2	2.5	450	45	Yes	8/DFN
SY54016AR	Driver/Receiver	Single	Internal Termination	ANY	CML	2.5V	3.2	3.2	280	16		8/MLF
SY100EL17	Receiver	Quad		ECL/LVPECL	ECL/LVPECL	3.3/5V			610	26		20/SOIC
SY58601U	Driver/Receiver	Single	Internal Termination	ANY	LVPECL	2.5/3.3V	5	5	220	60		8/MLF
SY54016R	Driver/Receiver	Single	Fail-Safe Input (FSI)	ANY	CML	2.5V	2.5		420	40		8/MLF
SY58016L	Driver/Receiver	Single	Internal Termination	CML/PECL	CML	3.3V	10.7	7	150	75		16/MLF
SY58602U	Driver/Receiver	Single	Internal Termination	ANY	LVPECL	2.5/3.3	10.7	7	220	65		8/QFN
SY56016R	Driver/Receiver	Single	Input Equalization	ANY	CML	2.5V	6.4	5	250	42		10/MLF

Clock and Data Distribution: Translators

Product	No. of Channels	Core Supply Voltage (V)	Input Type	Output Type	Output Voltage (V)	Output Frequency (Max) (GHz)	Propagation Delay (Max) (ps)	Within Device Skew (Max) (ps)	Packages
SY89321L	Single	3.3	LVPECL/CML/LVDS	LVTTL	3.3	0.275	2500		8/MLF
SY100ELT22	Dual	5	TTL	PECL	2.5/3.8	0.15	600	100	8/SOIC
SY100EPT21	Single	3.3	LVPECL	LVTTL	3.3	0.275	2500	500	8/MSOP 8/SOIC
SY100ELT22L	Dual	3.3	LVTTL	LVPECL	2.5/3.9	0.15	600	100	8/SOIC
SY100ELT23L	Dual	3.3	LVPECL	LVTTL	2	0.16	2500	300	8/SOIC
SY55857L	Dual	3.3	ANY	LVPECL	3.3	2.5	400	50	10/MSOP
SY89323L	Dual	3.3	LVPECL	LVTTL	3.3	0.275	250	50	8/MLF
SY89329V	Single	3.3/8	LVTTL	LVPECL	3.3/7	0.8	600		8/MLF
PL130-07	Single	2.5/3.4	Sine Wave/ LVCMOS	LVCMOS	2.5/3.4	0.2			16/QFN, 8/TSSOP, 8/SOIC
SY100EPT22	Dual	3.3/6	TTL/LVTTL/CMOS/LVCMOS	PECL/LVPECL	3.3/6	0.8	600	500	8/MSOP 8/SOIC
SY89322V	Dual	3.3/7	LVTTL	LVPECL	3.3/6	0.8	600	100	8/MLF
SY10/100EPT20	Single	3.3/5	TTL/LVTTL/CMOS/LVCMOS	PECL/LVPECL	3.3/5	0.35	600	500	8/MSOP 8/SOIC
SY55855V	Dual	3.3/6	PECL/LVPECL/CML	LVDS	3.3/5	0.75	700	50	10/MSOP
SY100ELT23	Dual	5	PECL	TTL	2.5	0.16	3500	300	8/SOIC
SY100EPT23	Dual	3.3	LVPECL	LVTTL	3.3	0.275	2500	300	8/MSOP 8/SOIC
SY89327L	Single	3.3	ANY	LVPECL	3.3	2.5	400		8/QFN
SY100ELT21L	Single	3.3	LVPECL	LVTTL	2.5/3.7	0.15	2500		8/SOIC
SY100ELT25	Single	5	ECL	TTL	5	0.5	3600		8/SOIC
SY89328L	Single	3.3	LVPECL/LVTTL	LVTTL/LVPECL	3.3	0.275	600		8/MLF
SY100EPT28	Single	3.3	LVPECL/LVTTL	LVPECL/LVTTL	3.3	0.275	2500		8/MSOP 8/SOIC
PL130-09	Single	2.5/3.6	Sine Wave/TTL/CMOS/LVDS	LVDS	2.5/3.6	1			8/SOP,16/QFN

Clock and Data Distribution: Multiplexers

Product	MUX: Fanout	No. of Channels	Input Type	Output Type	Supply Voltage (V)	Output Frequency (Max) (GHz)	Output Data Rate (Max) (Gbps)	Propagation Delay (Max) (ps)	Within Device Skew (Max) (ps)	Crosspoint	Runt Pulse Eliminator (RPE)	Fail-Safe Input (FSI)	Packages
SY58609U	2:1	Single	ANY	CML	2.5/3.3V	3	4.25	450	20			Yes	16/QFN
SY58018U	2:1	Single	ANY	LVPECL	2.5/3.3V	4	5	240	15				16/QFN
SY58611U	2:1	Single	ANY	LVDS	2.5V	2.5	3.2	470	20			Yes	16/QFN
SY89474U	2:2	Single	ANY	LVDS	2.5V	2.5	2.5	470	20				24/QFN
SY100EP57	4:1	Single	PECL/ECL	PECL/ECL	3.3V/5V	3		520					20/TSSOP
SY89544U	4:1	Single	ANY	LVDS	2.5V	4	3.2	510	20				32/MLF
SY89840U	2:1	Single	ANY	LVPECL	2.5/3.3V	2		880			Yes	Yes	16/QFN
SY89841U	2:1	Single	ANY	LVDS	2.5V	2		870			Yes	Yes	16/MLF
SY89547L	4:2	Single	ANY	LVDS	3.3V	4	3.2	540	20				32/MLF
SY58028U	4:2	Single	ANY	CML	2.5/3.3V	7	10.7	340	20				32/MLF
SY58610U	2:1	Single	ANY	LVPECL	2.5/3.3V	2.5	3.2	470	20			Yes	16/QFN
SY58017U	2:1	Single	ANY	CML	2.5/3.3V	7	10.7	240	15				16/MLF
SY58038U	8:2	Single	ANY	LVPECL	2.5/3.3V	5	4.5	500	15				44/QFN
SY100EP56	2:1	Dual	PECL/ECL	PECL/ECL	3.3V/5V	3		470	100				20/TSSOP
SY89853U	2:1	Dual	ANY	LVPECL	2.5/3.3V	2.5	2.5	360	20				32/QFN
SY89545L	4:1	Single	ANY	LVDS	3.3V	3	3.2	600	25				32/MLF
SY56034AR	2:6	Single	ANY	CML	2.5V	5	6.4	300	25	Yes			32/QFN
SY89859U	8:2	Single	ANY	LVPECL	2.5/3.3V	2.5	3.5	640	20				44/QFN
SY89543L	2:1	Dual	ANY	LVDS	3.3V	3	3.2	510	25				32/MLF
SY58029U	4:2	Single	ANY	LVPECL	2.5/3.3V	4	5	390	15				32/MLF
SY89855U	4:2	Single	ANY	LVPECL	2.5/3.3V	2.5	2.5	410	20				32/QFN
SY89465U	2:10	Single	ANY	LVDS	2.5V	2		1200	25		Yes	Yes	44/QFN
SY89844U	2:2	Single	ANY	LVDS	2.5V	2		870	20		Yes	Yes	24/QFN
SY58026U	2:1	Dual	ANY	LVPECL	2.5/3.3V	6	5	310	15				32/MLF

Clock and Data Distribution: Multiplexers													
Product	MUX: Fanout	No. of Channels	Input Type	Output Type	Supply Voltage (V)	Output Frequency (Max) (GHz)	Output Data Rate (Max) (Gbps)	Propagation Delay (Max) (ps)	Within Device Skew (Max) (ps)	Crosspoint	Runt Pulse Eliminator (RPE)	Fail-Safe Input (FSI)	Packages
SY58019U	2:1	Single	ANY	LVPECL	2.5/3.3V	7	10.7	240	15				16/MLF
SY58025U	2:1	Dual	ANY	CML	2.5/3.3V	6	10.7	290	15				32/MLF
SY58030U	4:2	Single	ANY	LVPECL	2.5/3.3V	7	10.7	340	20				32/MLF
Clock and Data Distribution: Skew Management													
Product	No. of Channels	Input Type	Output Type	Propagation Delay Resolution (Typ) (ps/step)	Propagation Delay (Min) (ns)	Propagation Delay (Max)(ns)	Fine Tune	Supply Voltage (V)	Output Frequency (Max) (GHz)	Packages			
SY100EP195V	Single	ANY	ECL	10	2.2	12.2		3.3/5	2.5	32/TQFP			
SY100EP196V	Single	ANY	ECL	10	2.2	12.2	Yes	3.3/5	2.5	32/TQFP			
SY55856U	Dual	CML	CML	50	0.35	0.7		2.5/3.3	2.5	32/TQFP			
SY89295U	Single	LVPECL/LVTTL	LVPECL	10	3.2	14.8		2.5/3.3	1.5	32/TQFP 32/VQFN			
SY89296U	Single	LVPECL/LVTTL	LVPECL	10	3.2	14.8	Yes	2.5/3.3	1.5	32/TQFP 32/VQFN			
SY89297U	Dual	ANY	CML	5	2	7		3.3	1.6	24/VQFN			
Clock and Data Distribution: High Temperature Oscillators													
Part Family	Type	Footprint (mm)		Output Frequency (MHz)	Temperature Stability (ppm)		Temperature Range (°C)	Output Logic		Supply Voltage (V)			
HM-4201-RTCM1	Real time clock module	13 x 13		0.000512	150		-40 to 200	CMOS		3.3			
HT-RTC-XO	Real time clock XO	multiple options, see specification		0.032768	100		-55 to 200	CMOS		1.8, 2.5, 3.3, 5			
HX-171	High temp OCXO	28 x 38		10 to 20	0.005		-40 to 150	CMOS		5			
PX-420	High temp XO	13 x 13		0.5 to 40	200		-55 to 230	CMOS		3.3, 5			
PX-570	High temp XO	8.5 x 8		0.5 to 40	200		-55 to 230	CMOS		1.8, 2.5, 3, 3.3, 5			
PX-610	High temp XO	09.65		0.032768 to 40	200		-55 to 230	CMOS		1.8, 2.5, 3.3, 5			
PX-702	High temp XO	7 x 5		0.5 to 50	200		-55 to 230	CMOS		1.8, 2.5, 3, 3.3, 5			
VX-400	High temp VCXO	20 x 13		1 to 32.768	-55 to 200		CMOS	3.3, 5		3.3, 5			
VX-708	High temp VCXO	7 x 5		2 to 40	-55 to 180		CMOS	3.3		3.3			
Clock and Data Distribution: Disciplined Oscillator Module													
Part Family	Type	Footprint (mm)	Output Standard (MHz)	Temperature Stability (ppb)	Temperature Range Min (°C)	Holdover 24 hours - constant temperature us	1pps RMS (1 sigma) accuracy to UTC ns	Phase Noise 10 Hz dBc/Hz	Phase Noise 100 kHz dBc/Hz	Phase Noise 100 kHz dBc/Hz			
MD-013	High Stability GNSSDOCXO	115 x 60	19	0.4	-40 to 85	1.5	10	-125	-145				
MD-174	Low noise GNSSDOCXO	50 x 40	10	5	-40 to 85	15	20	-135	-170				
MD-175	High Stability GNSSDOCXO	50 x 40	10	0.4	-40 to 85	1.5	10	-125	-145				
MD-2610-OCXO	Compact GNSSDOCXO	25 x 20	10	5	-40 to 85	8	20	-120	-150				
OCXO													
Part Family	Type	Footprint (mm)	Output Frequency (MHz)	Temperature Stability (ppb)	Temperature Range (°C)	Aging Per Year (ppb)	Phase Noise 10 Hz dBc/Hz	Phase Noise 10 kHz dBc/Hz	Carrier (MHz)	Supply Voltage (V)			
EX-219	Low Power Space OCXO	26 x 24	10 to 120	100	-40 to +85	200	-90	-145	10	3.3, 5			
EX-421	Low power OCXO	13 x 13	10 to 100	30	-40 to +85	100	-125	-165	10	3.3, 5			
MX-503	Microprocessor corrected TCXO	14 x 9	8 to 50	30	-40 to +85	250	-93	-154	20	3.3, 5			
MX-600	Microprocessor corrected TCXO	9 x 7	8 to 40	30	-40 to +85	250	-100	-153	10	3.3			
OX-043	Low g OCXO	51 x 51	8 to 15	30	-40 to +85	40	-135	-170	10	12, 15			
OX-046	Low g OCXO	51 x 51	50 to 250	200	-40 to +85	200	-100	-175	100	12, 15			
OX-171	High stability OCXO	38 x 28	5 to 20	0.8	-40 to +85	15	-125	-145	10	3.3, 5, 12			
OX-208	High Stability OCXO	25 x 25	5 to 20	0.8	-40 to +85	20	-125	-155	10	3.3, 5			
OX-221	High Stability OCXO	25 x 22	10 to 30.72	3	-40 to +85	60	-122	-151	10	3.3			
OX-228	High stability OCXO	25 x 22	10 to 20	1	-40 to +85	200	-108	-162	50	3.3			
OX-249	Space OCXO	35 x 20	10 to 120	100	-40 to +85	200	-108	-162	50	5			

OCXO										
Part Family	Type	Footprint (mm)	Output Frequency (MHz)	Temperature Stability (ppb)	Temperature Range (°C)	Aging Per Year (ppb)	Phase Noise 10 Hz dBc/Hz	Phase Noise 10 kHz dBc/Hz	Carrier (MHz)	Supply Voltage (V)
OX-304	Low noise OCXO	20 x 20	10 to 20	20	-40 to +85	30	-135	-173	10	12
OX-305	Low noise OCXO	20 x 20	80 to 120	200	-40 to +85	200	-105	-178	100	12
OX-401	1588 OCXO	20 x 13	10 to 40	25	-40 to +85	100	-121	-152	20	3.3, 5
OX-405	Low noise OCXO	20 x 13	80 to 120	50	-40 to +85	300	-95	-155	100	3.3, 5
OX-502	Standard OCXO	14 x 9	10 to 40	10	-40 to +85	500	-90	-150	20	3.3
OX-601	Standard OCXO	9 x 7	10 to 40	10	-40 to +85	500	-90	-150	20	3.3
TCXO										
Part Family	Type	Footprint (mm)	Output Frequency (MHz)	Temperature Stability -40 to 85 ppm	Phase Noise 10 Hz dBc/Hz	Phase Noise 10 kHz dBc/Hz	Carrier (MHz)	Output Logic	Supply Voltage (V)	
DOC200103	Space TCXO	multiple options, see specification	0.3 to 425	2				CMOS, Sine	3.3, 5, 12	
DOC207139	Space TCXO	35 x 25	12 to 200	2				LVDS	3.3	
TX-321	Low noise TCXO	23 x 18	5 to 50	1	-116	-162	10	CMOS	3.3, 5	
TX-707	Low g TCXO	7 x 5	8 to 52	1	-100	-158	10	CMOS, Clipped Sine	3.3, 5	
TX-708	Low g TCXO	7 x 5	96 to 160	1	-75	-140	150	CMOS	3.3	
VT-706	Stratum 3 TCXO	7 x 5	5 to 52	0.2	-102	-154	10	CMOS	3, 3.3, 5	
VT-803	Stratum 3 TCXO	5 x 3.2	10 to 52	0.28	-91	-150	26	CMOS, Clipped Sine	2.5, 3.3, 5	
VT-820	Standard TCXO	3.2 x 2.5	8 to 45	0.5	-91	-149	10	Clipped Sine	1.8, 2.5, 3, 3.3	
VT-841	Standard TCXO	2.5 x 2	10 to 52	1	-91	-148	19.2	Clipped Sine	1.8, 2.5, 3.3	
VT-860	Standard TCXO	2 x 1.6	13 to 52	0.5	-90	-145	26	Clipped Sine	1.8, 2.5, 3, 3.3	
VCSO and PSO										
Part Family	Type	Footprint (mm)	Output Frequency (MHz)	Temperature Range (°C)	Jitter 12k-20 MHz fs-rms	Carrier (MHz)	Output Logic			
DOC206559	Space VCSO	16 x 16	300 to 1500	-40 to +85		1000	Sine			
DOC206906	Space VCSO	16 x 16	300 to 1000	-40 to +85	0.5	1000	LVPECL			
VS-501	Single frequency VCSO	14 x 9	600 to 3000	-10 to +85	12	1700	Sine, Balanced or Differential Sinewave, LVPECL			
VS-504	Dual frequency VCSO	14 x 9	600 to 3000	-10 to +85	12	1980	Sine, Balanced or Differential Sinewave, LVPECL			
VS-507	Single frequency VCSO	14 x 9	3000 to 6000	-40 to +85	10	5898.24	Sine, Balanced or Differential Sinewave			
VS-702	Single frequency VCSO	7 x 5	150 to 1000	-40 to +85	100	622.08	LVPECL, LVDS			
VS-709	Dual frequency VCSO	7 x 5	120 to 1200	-40 to +85	120	698.81	LVPECL, LVDS			
VS-800	Single frequency VCSO	5 x 3.2	800 to 3200	-40 to +85	6	2949.12	Sine, Balanced or Differential Sinewave			
VCXO										
Part Family	Type	Footprint (mm)	Output Frequency (MHz)	Temperature Range (°C)	Pull Range (ppm)	Phase Noise 10 Hz dBc/Hz	Phase Noise 100 kHz dBc/Hz	Carrier (MHz)	Output Logic	Supply Voltage (V)
VX-501	Low noise VCXO	14 x 9	10 to 1200	-40 to +85	65	-76	-166	100	CMOS, Sine, LVPECL, LVDS	3.3, 5
VX-706	Low noise VCXO	7 x 5	40 to 300	-40 to +85	60	-72	-166	122.88	CMOS, LVPECL	3.3, 5
VX-805	Low noise VCXO	5 x 3.2	100 to 204.8	-40 to +105	50	-68	-157	122.88	LVPECL	3.3
VX-505	Mil temp range VCXO	14 x 9	20 to 800	-55 to +125	60	-76	-161	100	CMOS, LVPECL	3.3, 5
DOC204898	Space VCXO	25 x 25	100 to 700	-40 to +85	20			700	LVPECL	3.3
DOC204899	Space VCXO	25 x 25	80 to 200	-40 to +85	20			200	LVDS	3.3
DOC206218	Space VCXO	14 x 9	1 to 100	-40 to +85	50	-85	-159	16	CMOS	3.3, 5
VV-800	Standard VCXO	5 x 3.2	1.544 to 77.76	-40 to +85	150	-63	-157	61.44	CMOS	3.3, 5
VX-705	Standard VCXO	7 x 5	77.76 to 170	-40 to +85	50	-66	-151	122.88	CMOS, LVPECL	3.3

XO												
Part Family	Type	Footprint (mm)	Output Frequency (MHz)	Temperature Stability (ppm)	Temperature Range Min (°C)	Jitter 12k-20 MHz fs-rms	Carrier (MHz)	Output Logic	Supply Voltage (V)			
DOC203679	Space XO	16 x 16	12 to 200	50	-55 to +125	0.09	200	LVDS	3.3			
DOC203810	Space XO	multiple options, see specification	100 to 700	50	-55 to +125	0.3	700	LVPECL	3.3			
DOC204900	Space XO	multiple options, see specification	12 to 160	50	-55 to +125	0.14	100	CMOS	2.5, 3.3			
DOC206379	Space XO, 300k rad	16 x 16	12 to 100	50	-55 to +125	0.08	100	CMOS	3.3, 5			
DOC206903	Space XO, 300 krad	16 x 16	12 to 200	50	-55 to +125	0.09	200	LVDS	3.3			
M55310/28B	Mil temp range XO	14 x 9	1 to 85	50	-55 to +125			TTL	3.3			
M55310/30B	Mil temp range XO	14 x 9	0.45 to 85	50	-55 to +125			CMOS	3.3			
OS-68338	Space XO	multiple options, see specification	0.35 to 100	50	-55 to +125	0.16	40	CMOS, TTL	3.3, 5			
PS-702	High frequency SO	7 x 5	150 to 1000	50	-40 to +85	100	622.08	LVPECL, LVDS	3.3			
PX-700	Precision XO	7 x 5	1 to 800	50	-55 to +125	500	100	CMOS, TTL, LVPECL, LVDS	2.5, 3.3, 5			
PX-706	Standard XO	7 x 5	40 to 300	25	-40 to +85	48	100	CMOS, LVPECL	3.3, 5			
VC-711	Low jitter XO	7 x 5	10 to 170	100	-40 to +105	100	156.25	LVPECL, LVDS	2.5, 3.3			
VC-801	Standard XO	5 x 3.2	0.03277 to 125	50	-55 to +125	500	125	CMOS	1.8, 2.5, 3.3, 5			
VC-806	Standard XO	5 x 3.2	25 to 250	25	-40 to +85	300	155.52	LVPECL, LVDS	2.5, 3.3			
VC-820	Standard XO	3.2 x 2.5	0.625 to 133	50	-55 to +125	61	125	CMOS	1.8, 2.5, 3.3			
VC-827	Low jitter XO	3.2 x 2.5	20 to 170	100	-40 to +105	130	156.25	LVPECL, LVDS	2.5, 3.3			
VC-840	Standard XO	2.5 x 2	0.75 to 60	25	-40 to +105	177	25	CMOS	1.8, 2.5, 3.3			
Low-Power Oscillators												
Product	Output Frequency Min. (MHz)	Output Frequency Max (MHz)	Output Logic	Frequency Stability (ppm)	Temp. Range (°C)	Supply Voltage (V)	Current (Typ) (mA)	Period Jitter (ps RMS)	# Outputs	Dimensions	Output Drive Strength (pf)	
DSC60X1B	0.002	80	LVC MOS	±20, ±25, ±50	-40 to +125	1.71-3.63	1.3	10	1	1.6 x 1.2 mm 4-pin	15	
DSC60X3B	0.002	80	LVC MOS	±20, ±25, ±51	-40 to +125	1.71-3.63	1.3	10	1	2.0 x 1.6 mm 4-pin	5	
DSC61X1B	0.002	100	LVC MOS	±20, ±25, ±56	-40 to +125	1.71-3.63	3.0	7.0	1	2.5 x 2.0 mm 4-pin	15	
DSC61X2B	0.002	100	LVC MOS	±20, ±25, ±57	-40 to +125	1.71-3.63	3.0	7.0	1	3.2 x 2.5 mm 4-pin*	5.0 x 3.2 mm 4-pin*	25
DSC1001	1	170	LVC MOS	±10, ±25, ±50	-40 to +105	1.62-3.63	5.0	6.0	1	5.0 x 2.0 mm 4-pin	15	
DSC1003	1	170	LVC MOS	±10, ±25, ±50	-40 to +105	1.62-3.63	6.0	5.0	1	3.2 x 2.5 mm 4-pin	5.0 x 3.2 mm 4-pin	25
DSC1004	1	170	LVC MOS	±10, ±25, ±50	-40 to +105	1.62-3.63	7.0	5.0	1	7.0 x 5.0 mm 4-pin	40	
Low-Jitter Oscillators												
Product	Output Frequency Min. (MHz)	Output Frequency Max (MHz)	Output Logic	Frequency Stability (ppm)	Temperature Range (°C)	Supply Voltage (V)	Current (Typ) (mA)	Period Jitter (ps RMS)	# Outputs	Dimensions	Output Drive Strength (pf)	
MX57	10	860	LVC MOS, LVPECL, LVDS, HCSL	±20, ±50	-40 to +85	2.375-3.63	70		0.16	1	7.0 x 5.0 mm 6-pin	
MX55	10	860	LVC MOS, LVPECL, LVDS, HCSL	±20, ±50	-40 to +85	2.375-3.63	70		0.16	1	5.0 x 3.2 mm 6-pin	
DSC11x1	2.3	170	LVC MOS	±10, ±25, ±50	-55 to +125	2.25-3.63	25	3	1.70/0.3 (200k-20M)	1	15	
DSC11x2	2.3	460	LVPECL	±10, ±25, ±50	-40 to +105	2.25-3.63	51	2.5	1.70/0.3 (200k-20M)	1		
DSC11x3	2.3	460	LVDS	±10, ±25, ±50	-40 to +105	2.25-3.63	29	2.5	1.70/0.3 (200k-20M)	1		
DSC11x4	2.3	460	HCSL	±10, ±25, ±50	-40 to +105	2.25-3.63	30	2.5	1.70/0.3 (200k-20M)	1	2.5 x 2.0 mm 6-pin	
DSC12x1	2.5	170	LVC MOS	±20, ±25, ±55	-40 to +125	2.25-3.63	27		0.65	1	3.2 x 2.5 mm 6-pin	
DSC12x2	2.5	450	LVPECL	±20, ±25, ±55	-40 to +105	2.25-3.63	50		0.65	1	5.0 x 3.2 mm 6-pin	
DSC12x3	2.5	450	LVDS	±20, ±25, ±55	-40 to +125	2.25-3.63	32		0.65	1	7.0 x 5.0 mm 6-pin	
DSC12x4	2.5	450	HCSL	±20, ±25, ±55	-40 to +105	2.25-3.63	40		0.65	1	15	
DSC2x10	2.3	170	LVC MOS	±10, ±25, ±50	-55 to +125	2.25-3.63	25	3	1.70/0.3 (200k-20M)	1		
DSC2x20	2.3	460	LVPECL	±10, ±25, ±50	-40 to +105	2.25-3.63	51	2.5	1.70-0.3 (200k-20M)	1		
DSC2x30	2.3	460	LVDS	±10, ±25, ±50	-40 to +105	2.25-3.63	29	2.5	1.70/0.3 (200k-20M)	1	3.2 x 2.5 mm 14-pin	
DSC2x40	2.3	460	HCSL	±10, ±25, ±50	-40 to +105	2.25-3.63	30	2.5	1.70/0.3 (200k-20M)	1		

Spread Spectrum Oscillators																
Product	Output Frequency Min. (MHz)	Output Frequency Max (MHz)	Output Logic	Frequency Stability (ppm)	Temp. Range (°C)	Supply Voltage (V)	Current (Typ) (mA)	Period Jitter (ps RMS)	# Outputs	Dimensions	Output Drive Strength (pf)					
DSC6x1B	1	100	LVC MOS	±20, ±25, ±50	-40 to +125	1.71–3.63	3	7	1	1.6 x 1.2 mm 4-pin 2.0 x 1.6 mm 4-pin 2.5 x 2.0 mm 4-pin 3.2 x 2.5 mm 4-pin*	10					
DSC63x2B	1	100	LVC MOS	±20, ±25, ±53	-40 to +125	1.71–3.63	3	7	1		25					
Automotive Oscillators																
Product	Output Frequency Min. (MHz)	Output Frequency Max (MHz)	Output Logic	Frequency Stability (ppm)	Temperature Range (°C)	Supply Voltage (V)	Current (Typ) (mA)	Period Jitter (ps RMS)	Phase Noise (ps RMS)	# Outputs	Dimensions	Output Drive Strength (pf)				
DSA60x1	0.002	80	LVC MOS	±20, ±25, ±50	-40 to +125	1.71–3.63	1.3	10		1	1.6 x 1.2 mm 4-pin 2.0 x 1.6 mm 4-pin 2.5 x 2.0 mm 4-pin 3.2 x 2.5 mm 4-pin*	10				
DSA60x3	0.002	80	LVC MOS	±20, ±25, ±50	-40 to +125	1.71–3.63	1.3	10		1		5				
DSA61x1	0.002	100	LVC MOS	±20, ±25, ±50	-40 to +125	1.71–3.63	3.0	7.0		1	2.5 x 2.0 mm 4-pin 3.2 x 2.5 mm 4-pin*	10				
DSA61x2	0.002	100	LVC MOS	±20, ±25, ±50	-40 to +125	1.71–3.63	3.0	7.0		1		25				
DSA63x1	1	100	LVC MOS	±20, ±25, ±50	-40 to +125	1.71–3.63	3	7		1	5.0 x 3.2 mm 4-pin* 7.0 x 5.0 mm 4-pin*	10				
DSA63x2	1	100	LVC MOS	±20, ±25, ±50	-40 to +125	1.71–3.63	3	7		1		25				
DSA1001	1	170	LVC MOS	±20, ±25, ±50	-40 to +105	1.62–3.63	5.0	6.0		1	2.5 x 2.0 mm 4-pin	15				
DSA11x1	2.3	170	LVC MOS	±20, ±25, ±50	-55 to +125	2.25–3.63	25	3	1.70/0.3 (200k-20M)	1	2.5 x 2.0 mm 6-pin 3.2 x 2.5 mm 6-pin 5.0 x 3.2 mm 6-pin	15				
DSA2311	2.3	170	LVC MOS	±25, ±50	-55 to +125	2.25–3.63	21	3	1.70/0.3 (200k-20M)	2	2.5 x 2.0 mm 6-pin	15				
DSA557-03	100	100	HCSL	±25, ±50	-40 to +105	2.25–3.63	60		PCIe Gen 1/2/3/4	2	3.2 x 2.5 mm 14-pin					
Advanced Jitter Attenuators (OTN)																
Part	DPLLs or Paths	DPLL BW (Hz)	Inputs	Diff. Outputs	CMOS Outputs	Low-Jitter APPLs	GP Clock Gen	Typ. Jitter (psRMS)	Input Frequency	Output Frequency	NV Memory	Host Bus	2K/8K Align	1 Hz Align	NCO (ppb)	Package
ZL30152	1	14–896	2 D/SE	4	2	1	0	0.7	1 kHz to 750 MHz	1 kHz to 750 MHz	OTP	SPI/I2C				64-pin LBGA
ZL30155	2	14–896	4 D/SE	8	4	2	0	0.7	1 kHz to 750 MHz	1 kHz to 750 MHz	OTP	SPI/I2C				100-pin LBGA
ZL30157	2	14–896	4 D/SE	8–12	4–12	1	1	0.7	1 kHz to 750 MHz	1 kHz to 750 MHz	OTP	SPI/I2C				100-pin LBGA
ZL30160	4	14–896	4 D/SE	8	4–12	2	2	0.7	1 kHz to 750 MHz	1 kHz to 750 MHz	OTP	SPI/I2C				100-pin LBGA
ZL30165	4	5–806	8 D/SE	8	8	4	0	0.65	1 kHz to 750 MHz	1 Hz to 750 MHz	OTP	SPI/I2C			0.001	144-pin LBGA
ZL30166	3	5–896	9 D/SE + 2 SE	8	8	4	0	0.65	1 kHz to 750 MHz	1 Hz to 750 MHz	OTP	SPI/I2C	✓	0.001	145-pin LBGA	
ZL30167	2	5–896	9 D/SE + 2 SE	8	8	4	0	0.65	1 kHz to 750 MHz	1 Hz to 750 MHz	OTP	SPI/I2C	✓	0.001	146-pin LBGA	
ZL30168	4	5–896	8D/SE	8	8	4	0	0.65	1 kHz to 750 MHz	1 Hz to 750 MHz	OTP	SPI/I2C			0.001	147-pin LBGA
ZL30169	1	14–500	2 D/SE + 2 SE	3	6	1	0	0.25	1 kHz to 1250 MHz	1 Hz to 1035 MHz	Int EE	SPI/I2C	✓	0.01	32-pin QFN	
ZL30182	2	5–500	4 D/SE + 2 SE	6	12	2	0	0.25	1 kHz to 1250 MHz	1 Hz to 1035 MHz	Int EE	SPI/I2C	✓	0.01	64-pin LGA	
ZL30174	3	14–470	5 D/10 SE	6	14	3	1	0.18	1 kHz to 900 MHz	1 Hz to 900 MHz	Int EE	SPI/I2C	✓	✓		100-pin AQFN
IEEE 1588 Timing Solutions																
Part No.	DPLLs	BW (Hz)	Inputs	Input Frequency	Embedded PPS & EPP2S	Diff. Outputs	CMOS Outputs	Output Frequency	Low-Jitter APPLs	GP Clock Gen	Jitter (psRMS)	Pkg size (mm)				
ZL30361	1 NCO	0.1 to 896	11	1 Hz to 750 MHz		6	6	1 Hz to 750 MHz	3	0	0.67	144-pin LBGA				
ZL30362	4 NCO	0.1 to 896	11	1 Hz to 750 MHz		8	8	1 Hz to 750 MHz	4	0	0.67	144-pin LBGA				
ZL30363	2 NCO	0.1 to 896	11	1 Hz to 750 MHz		8	8	1 Hz to 750 MHz	4	0	0.67	144-pin LBGA				
ZL30364	3 NCO	0.1 to 896	11	1 Hz to 750 MHz		8	8	1 Hz to 750 MHz	4	0	0.67	144-pin LBGA				
ZL30365	4 or (4 NCO)	5 to 890	8 D/SE	1 Hz to 750 MHz	8	8	8	1 Hz to 750 MHz	4	0	0.67	144-pin LBGA				
ZL30367	2 or (2 NCO)	5 to 890	9 D/SE+2 SE	1 Hz to 750 MHz	6	6	6	1 Hz to 750 MHz	3	0	0.67	144-pin LBGA				
ZL30721	1 NCO	0.1 to 10	2 D/SE + 1 SE	8 kHz to 1250 MHz		3	6	<1 Hz to 1035 MHz	1	0	0.26	64-pin LGA				
ZL30722	1 NCO	0.1 to 500	2 D/SE + 1 SE	8 kHz to 1250 MHz		3	6	<1 Hz to 1035 MHz	1	0	0.26	32-pin QFN				
ZL30723	2 NCO	0.1 to 500	4 D/SE + 1 SE	8 kHz to 1250 MHz		6	12	<1 Hz to 1035 MHz	2	0	0.26	64-pin LGA				
ZL30701	1 or (1 NCO)	0.1m to 470	5 D/10 SE	0.5 Hz to 900 MHz	✓	6	14	0.5 Hz to 900 MHz	2 or 3	1	0.19	100-pin AQFN				

IEEE 1588 Timing Solutions

Part No.	DPLLS	BW (Hz)	Inputs	Input Frequency	Embedded PPS & EPP2S	Diff. Outputs	CMOS Outputs	Output Frequency	Low-Jitter APPLLs	GP Clock Gen	Jitter (psRMS)	Pkg size (mm)
ZL30702	2 or (2 NCO)	0.1m to 470	5 D/10 SE	0.5 Hz to 900 MHz	✓	6	14	0.5 Hz to 900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30703	3 or (3 NCO)	0.1m to 470	5 D/10 SE	0.5 Hz to 900 MHz	✓	6	14	0.5 Hz to 900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30704	4 or (4 NCO)	0.1m to 470	5 D/10 SE	0.5 Hz to 900 MHz	✓	6	14	0.5 Hz to 900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30771	1 or (1 NCO)	0.1m to 470	10 D/10 SE	0.5 Hz to 900 MHz	✓	8	16 + 2	0.5 Hz to 1045 MHz	2	1	0.19	80-lead LGA
ZL30772	2 or (2 NCO)	0.1m to 470	10 D/10 SE	0.5 Hz to 900 MHz	✓	8	16 + 2	0.5 Hz to 1045 MHz	2	1	0.19	80-lead LGA
ZL30773	3 or (3 NCO)	0.1m to 470	10 D/10 SE	0.5 Hz to 900 MHz	✓	8	16 + 2	0.5 Hz to 1045 MHz	2	1	0.19	80-lead LGA

General-Purpose Jitter Attenuators

Product	Independent Output Freq. Families	Inputs	Diff Input Freq. Range	Low-Jitter APPLLs	Typical Jitter fs RMS	DPLL Features: Ref. Switching/ Holdover/ DPLL Bandwidth	NCO Mode	NCO ppb	Diff Outputs	CMOS Outputs	Output Freq. Range	NV Memory	Host Bus	Supply Voltage	Package
ZL30159	1	1 XTAL, 1 D	1 Hz to 750 M	1	<1000				0	2	1 Hz–177.5 M		SPI/I2C	3.3 + 1.8	64-pin LBGA
ZL30252	1	1 XTAL/SE, 3 D/SE	1 kHz to 1250 M	1	1601	Glitchless/Digital Hold/ 14 Hz–500 Hz	✓	0.01	0–3	0–6	<1 Hz–1035 M2	Ext EE3	SPI/I2C	3.3 + 1.8	32-pin QFN
ZL30253	1	1 XTAL/SE, 3 D/SE	1 kHz to 1250 M	1	1601	Glitchless/Digital Hold/ 14 Hz–500 Hz	✓	0.01	0–3	0–6	<1 Hz–1035 M2	Int EE3	SPI/I2C	3.3 + 1.8	32-pin QFN
ZL30254	1	1 XTAL, 2 SE		1	<1 ps	Glitchless/Digital Hold/ 25 Hz			2	0	125 MHz or 156.25 MHz		None	3.3 + 1.8	32-pin QFN
ZL30255	2	2 XTAL/SE, 6 D/SE	1 kHz to 1250 M	2	1601	Glitchless/Digital Hold/ 14 Hz–500 Hz	✓	0.01	0–6	0–12	<1 Hz–1035 M2	Int EE3	SPI/I2C	3.3 + 1.8	32-pin QFN
ZL30256	3	5 D/10 SE	1 kHz to 1045 M	3	190	Glitchless/Digital Hold 14 Hz–470 Hz	✓	~0.0000035	0–8	0–16 + 2	1 Hz–1045 M	Int EE4	SPI/I2C	3.3 + 1.8	80-lead LGA

Synchronous Ethernet (SyncE) Silicon Timing Solutions

Part	DPLLS	BW (Hz)	Inputs	Input Frequency	Embedded PPS & EPP2S	Diff. Outputs	CMOS Outputs	Output Frequency	Low-Jitter APPLLs	GP Clock Gen	Jitter (psRMS)	Package size (mm)
ZL30161	1 or (1 NCO)	0.1m–1k	11	1 Hz–750 MHz		6	6	1 Hz–750 MHz	3	0	0.67	144-pin LBGA
ZL30162	4 or (4 NCO)	0.1m–1k	11	1 Hz–750 MHz		8	8	1 Hz–750 MHz	4	0	0.67	144-pin LBGA
ZL30163	2 or (2 NCO)	0.1m–1k	11	1 Hz–750 MHz		8	8	1 Hz–750 MHz	4	0	0.67	144-pin LBGA
ZL30164	3 or (3 NCO)	0.1m–1k	11	1 Hz–750 MHz		8	8	1 Hz–750 MHz	4	0	0.67	144-pin LBGA
ZL30621	1 or (1 NCO)	0.1m–10	2 D/SE + 1 SE	8 kHz–1250 MHz		3	6	<1 Hz–1035 MHz	1	0	0.26	64-pin LGA
ZL30622	1 or (1 NCO)	0.1m–500	2 D/SE + 1 SE	8 kHz–1250 MHz		3	6	<1 Hz–1035 MHz	1	0	0.26	32-pin QFN
ZL30623	2 or (2 NCO)	0.1m–500	4 D/SE + 1 SE	8 kHz–1250 MHz		6	12	<1 Hz–1035 MHz	2	0	0.26	64-pin LGA
ZL30601	1 or (1 NCO)	0.1m–470	5 D/10 SE	0.5 Hz–900 MHz	✓	6	14	0.5 Hz–900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30602	2 or (2 NCO)	0.1m–470	5 D/10 SE	0.5 Hz–900 MHz	✓	6	14	0.5 Hz–900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30603	3 or (3 NCO)	0.1m–470	5 D/10 SE	0.5 Hz–900 MHz	✓	6	14	0.5 Hz–900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30604	4 or (4 NCO)	0.1m–470	5 D/10 SE	0.5 Hz–900 MHz	✓	6	14	0.5 Hz–900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30671	1 or (1 NCO)	0.1m–470	10 D/10 SE	0.5 Hz–900 MHz	✓	8	16 + 2	0.5 Hz–1045 MHz	2	1	0.19	80-lead LGA
ZL30672	2 or (2 NCO)	0.1m–470	10 D/10 SE	0.5 Hz–900 MHz	✓	8	16 + 2	0.5 Hz–1045 MHz	2	1	0.19	80-lead LGA
ZL30673	3 or (3 NCO)	0.1m–470	10 D/10 SE	0.5 Hz–900 MHz	✓	8	16 + 2	0.5 Hz–1045 MHz	2	1	0.19	80-lead LGA
ZL30151	1	1–500	2 D/SE + 1 SE	1 kHz–650 MHz		0–3	0–6	<1 Hz–650 MHz	1	0	0.26	32-pin QFN
ZL30611	1 or (1 NCO)	14–470	5 D/10 SE	0.5 Hz–900 MHz	✓	6	14	0.5 Hz–900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30612	2 or (2 NCO)	14–470	5 D/10 SE	0.5 Hz–900 MHz	✓	6	14	0.5 Hz–900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30614	4 or (4 NCO)	14–470	5 D/10 SE	0.5 Hz–900 MHz	✓	6	14	0.5 Hz–900 MHz	2 or 3	1	0.19	100-pin AQFN
ZL30681	1 or (1 NCO)	14–470	10 D/10 SE	0.5 Hz–900 MHz	✓	8	16 + 2	0.5 Hz–1045 MHz	2	1	0.19	80-lead LGA
ZL30682	2 or (2 NCO)	14–470	10 D/10 SE	0.5 Hz–900 MHz	✓	8	16 + 2	0.5 Hz–1045 MHz	2	1	0.19	80-lead LGA
ZL30683	3 or (3 NCO)	14–470	10 D/10 SE	0.5 Hz–900 MHz	✓	8	16 + 2	0.5 Hz–1045 MHz	2	1	0.19	80-lead LGA

Programmable Oscillators												
Product	Output Frequency Min. (MHz)	Output Frequency Max (MHz)	Output Logic	Frequency Stability (ppm)	Temperature Range (°C)	Supply Voltage (V)	Current (Typ) (mA)	Period Jitter (ps RMS)	Phase Noise (ps RMS) (12k-20 MHz)	# Outputs	Dimensions	Output Drive Strength (pf)
DSC8001	1	170	LVCMOS	±10, ±25, ±50	-40 to +105	1.62-3.63	5.0	6.0		1	2.5 x 2.0 mm 4-pin 3.2 x 2.5 mm 4-pin 5.0 x 3.2 mm 4-pin 7.0 x 5.0 mm 4-pin	15
DSC8003	1	170	LVCMOS	±10, ±25, ±50	-40 to +105	1.62-3.63	6.0	5.0		1	3.2 x 2.5 mm 4-pin 5.0 x 3.2 mm 4-pin 7.0 x 5.0 mm 4-pin	25
DSC8004	1	170	LVCMOS	±10, ±25, ±50	-40 to +105	1.62-3.63	7.0	5.0		1	5.0 x 3.2 mm 4-pin 7.0 x 5.0 mm 4-pin	40
DSC81x1	2.3	170	LVCMOS	±10, ±25, ±50	-40 to +105	2.25-3.63	25	3	1.70/0.3 (200k-20M)	1	2.5 x 2.0 mm 6-pin 3.2 x 2.5 mm 6-pin	15
DSC81x2	2.3	460	LVPECL	±10, ±25, ±50	-40 to +105	2.25-3.63	51	2.5	1.70/0.3 (200k-20M)	1	3.2 x 2.5 mm 6-pin	
DSC81x3	2.3	460	LVDS	±10, ±25, ±50	-40 to +105	2.25-3.63	29	2.5	1.70/0.3 (200k-20M)	1	5.0 x 3.2 mm 6-pin	
DSC81x4	2.3	460	HCSL	±10, ±25, ±50	-40 to +105	2.25-3.63	30	2.5	1.70/0.3 (200k-20M)	1	7.0 x 5.0 mm 6-pin	

555 Timers										
Product	Max Astable Frequency (MHz)	Monostable Accuracy (%)	Monostable Drift over Temp (ppm)	Monostable Drift over Supply (%V)	Astable Accuracy (%)	Astable Drift over Temp (ppm)	Astable Drift over Supply (%V)	Temperature Range (°C)	Supply Voltage (V)	Current (Typ) (uA)
MIC1555	5	2	100	0.5	2	150	0.5	-55 to +125	2.7 to 18	240
MIC1557	5	2	100	0.5	2	150	0.5	-55 to +125	2.7 to 18	255

High Frequency TCXO										
Product	Output Frequency Min. (MHz)	Output Frequency Max (MHz)	Output Logic	Frequency Stability (ppm)	Temp. Range (°C)	Supply Voltage (V)	Current (Typ) (mA)	Phase Noise (ps RMS) (12k-20 MHz)	# Outputs	Dimensions
MXT57	10	860	LVCMOS, LVPECL, LVDS, HCSL	±2.5, ±5.0	-40 to +85	2.375-3.63	80	0.5	1	7.0 x 5.0 mm 6-pin

Multi-Output Oscillators										
Product	Output Frequency Min (MHz)	Output Frequency Max (MHz)	Output Logic	Frequency Stability (ppm)	Temp. Range (°C)	Supply Voltage (V)	Phase Noise (ps RMS) (12k - 20MHz)	# Outputs	Dimensions	
MX85	10	860	LVPECL, LVDS, HCSL, LVCMOS	±25, ±50	-40 to +85	2.375-3.63	0.2	5	5.0 x 7.0 mm 38-pin	
DSC2311	2.3	170	LVCMOS	±25, ±50	-55 to +125	2.25-3.63	1.70/0.3 (200k-20M)	2	2.5 x 2.0 mm 6-pin	
DSC20xx	2.3	460	LVCMOS, LVPECL, LVDS, HCSL	±25, ±50	-40 to +105	2.25-3.63	1.70/0.3 (200k-20M)	2	3.2 x 2.5 mm 14-pin	
DSC21xx	2.3	460	LVCMOS, LVPECL, LVDS, HCSL	±25, ±50	-40 to +105	2.25-3.63	1.70/0.3 (200k-20M)	2	3.2 x 2.5 mm 14-pin	
DSC22xx	2.3	460	LVCMOS, LVPECL, LVDS, HCSL	±25, ±50	-40 to +105	2.25-3.63	1.70/0.3 (200k-20M)	2	3.2 x 2.5 mm 14-pin	
DSC400-xxxx	2.3	460	LVCMOS, LVPECL, LVDS, HCSL	±25, ±50	-40 to +105	2.25-3.63	1.70/0.3 (200k-20M)	4	5.0 x 3.2 mm 20-pin	
DSC612	0.002	100	LVCMOS	±20, ±25, ±50	-40 to +125	1.71-3.63		2	1.6 x 1.2 mm 6-pin 2.0 x 1.6 mm 6-pin 2.5 x 2.0 mm 6-pin	
DSC613	0.002	100	LVCMOS	±20, ±25, ±50	-40 to +125	1.71-3.63		3		
DSC557-03	100	100	HCSL/LVDS	±25, ±50	-40 to +105	2.25-3.63	PCIe Gen 1/2/3/4	2	3.2 x 2.5 mm 14-pin	
DSC557-04	100	100	HCSL/LVDS	±25, ±50	-40 to +105	2.25-3.63	PCIe Gen 1/2/3/4	3	5.0 x 3.2 mm 20-pin	
DSC557-05	100	100	HCSL/LVDS	±25, ±50	-40 to +105	2.25-3.63	PCIe Gen 1/2/3/4	4		

Clock Generators

Product	Category	Phase Jitter (ps) (Typ, 12 KHz to 20 MHz)	Period Jitter (ps)(peak to peak)	Inputs	No. of outputs	Output Logic	Output Frequency Min. (MHz)	Output Frequency Max. (MHz)	Voltage (V)	Temp. Range (°C)	Dimensions	Frequency Stability (ppm)
DSC2030	Low Power Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	1	LVDS	2.3	460	2.25-3.63	-40 to +105	14-pin QFN, 3.2 x 2.5 mm	±25, ±50
PL611s-02	Low Power Clock Generators		70	Crystal or Reference	2	LVC MOS	1	200	1.8-3.3	-45 to +85	DFN-6L, SOT-6L	
DSC2210	Low Power Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	1	LVC MOS	2.3	170	2.25-3.63	-40 to +105	14-pin QFN, 3.2 x 2.5 mm	±25, ±50
SM802	Low-Jitter Clock Generators	0.2		25 MHz Crystal/Ref	8	LVPECL, LVDS, HCSL, LVC MOS			2.5-3.3	-40 to +85	24-pin QFN 4 x 4	
PL902	Clock Conditioning			Reference	3	LVC MOS	1.25	200	2.5-3.3	-45 to +85		
DSC2010	Low Power Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	1	LVC MOS	2.3	170	2.25-3.63	-40 to +105	14-pin QFN, 3.2 x 2.5 mm	
DSC612	Low Power Clock Generators		140	Integrated MEMS	2	LVC MOS	0.002	100	1.71-3.63	-40 to +125	1.6 x 1.2 mm, 2.0 x 1.6 mm, 2.5 x 2.0 mm	±20, ±25, ±50
DSC613	Low Power Clock Generators		140	Integrated MEMS	3	LVC MOS	0.002	100	1.71-3.63	-40 to +125	1.6 x 1.2 mm, 2.0 x 1.6 mm, 2.5 x 2.0 mm	±20, ±25, ±50
PL602032	Low-Jitter Clock Generators	2	25	25 MHz Crystal	2	HCSL	100	100	2.25-3.63	-40 to +85	16 pin QFN 3 x 3	
PL602041	Low-Jitter Clock Generators	0.22	10	25 MHz Crystal	4	HCSL	100	100	2.25-3.63	-40 to +85	24-pin QFN 4 x 4	
PL607041	Low-Jitter Clock Generators	0.78		25 MHz Crystal	4	HCSL	100	100	2.25-3.63	-40 to +85	24-pin QFN 4 x 4	
PL602081	Low-Jitter Clock Generators	0.22	10	25 MHz Crystal	8	HCSL	100	100	2.25-3.63	-40 to +85	44-pin QFN 7 x 7	
PL607081	Low-Jitter Clock Generators	0.78		25 MHz Crystal	8	HCSL	100	100	2.25-3.63	-40 to +85	44-pin QFN 7 x 7	
PL602-21	Low-Jitter Clock Generators	2	25	25 MHz Crystal/Ref	1	HCSL	100	100	2.25-3.63	-40 to +85	8-pin SOP/ 6-pin SOT	
DSC557-04	Low-Jitter Clock Generators	PCIe Gen1/2/3/4	30	Integrated MEMS	3	HCSL	100	100	2.25-3.63	-40 to +105	20-pin QFN 5.0 x 3.2 mm	±25, ±50
DSC557-05	Low-Jitter Clock Generators	PCIe Gen1/2/3/4	30	Integrated MEMS	4	HCSL	100	100	2.25-3.63	-40 to +105	20-pin QFN 5.0 x 3.2 mm	±25, ±50
DSA557-03	Low-Jitter Clock Generators	PCIe Gen1/2/3/4		Integrated MEMS	2	HCSL	100	100	2.25-3.63	-40 to +105	14-pin QFN 3.2 x 2.5 mm	±50 ppm ±100 ppm
DSA557-04	Low-Jitter Clock Generators	PCIe Gen1/2/3/4		Integrated MEMS	3	HCSL	100	100	2.25-3.63	-40 to +105	20-pin QFN 5.0 x 3.2 mm	±50 ppm ±100 ppm
DSA557-05	Low-Jitter Clock Generators	PCIe Gen1/2/3/4		Integrated MEMS	4	HCSL	100	100	2.25-3.63	-40 to +105	20-pin QFN 5.0 x 3.2 mm	±50 ppm ±100 ppm
DSC557-03	Low-Jitter Clock Generators	PCIe Gen1/2/3/4	30	Integrated MEMS	2	HCSL/LVDS/LVC MOS	100	100	2.25-3.63	-40 to +105	14-pin QFN 3.2 x 2.5 mm	±25, ±50
PL602033	Low-Jitter Clock Generators	2	25	25MHz Crystal	2	LVC MOS/HCSL	125	125	2.5-3.3	-45 to +85	16 pin QFN 3 x 3	
PL602-22	Low-Jitter Clock Generators		25	25MHz Crystal	1	HCSL	125	125	2.5-3.3	-45 to +85	8-pin SOP/ 6-pin SOT	
PL613-21	Low Power Clock Generators		300	Crystal or Reference	4	LVC MOS	156.25	125	1.8-3.3	-45 to +85	QFN-16L, TSSOP-16L	
PL611s-18	Low Power Clock Generators		70	Crystal or Reference	2	LVC MOS	.5 KHz	125	1.8-3.3	-45 to +85	DFN-6L, SOT-6L	
PL611s-19	Low Power Clock Generators		70	Reference	2	LVC MOS	.5 KHz	125	1.8-3.3	-45 to +85	DFN-6L, SOT-6L	
PL904	Clock Conditioning	0.5			2	LVPECL,LVDS, HCSL,LVC MOS		12-850	2.5-3.3	-45 to +85		
PL500-37	VCXO	0.1		Crystal	1	CMOS	36	130	2.5/3.3	-45 to +85	Die, SOT-6L, SOP-8L	
PL602-15	None	2	25	25MHz Crystal	2	HCSL	156.25	156.25	2.5-3.3	-45 to +85	8-pin SOP/ 6-pin SOT	
SM803020	Low-Jitter Clock Generators	0.18			12	PECL	200	156.25		-45 to +85		
DSC2311	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	LVC MOS	200	170	2.25-3.63	-55 to +125	6-pin DFN, 2.5 x 2.0 mm	±25, ±50
DSC2011	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	LVC MOS	2.3	170	2.25-3.63	-55 to +125	14-pin QFN, 3.2 x 2.5 mm	±25, ±50
DSA2311	Low-Jitter Clock Generators		3		2	LVC MOS x 2	2.3	170		-40 to +125	2.5 x 2.0 mm 6-pin	±20, ±25, ±50
PL500-16	VCXO	0.1		Crystal	1	CMOS	4	18	2.5/3.3	-45 to +85	Die, SOT-6L, SOP-8L	
PL602034	None		25	25MHz Crystal	2	LVC MOS/HCSL	200	200	2.5-3.3	-45 to +85	8-pin SOP/ 6-pin SOT	
PL602-23	None		25	25MHz Crystal	1	LVC MOS/HCSL	200	200	2.5-3.3	-45 to +85	8-pin SOP/ 6-pin SOT	
PL671-25	Clock Conditioning		100	Crystal or Reference	2	CMOS	1	200	2.5-3.3	-45 to +85	SOP-8L	
PL671-29	Clock Conditioning		100	Crystal or Reference	1	CMOS	1	200	2.5-3.3	-45 to +85	SOP-8L	
PL671-30	Clock Conditioning		100	Crystal or Reference	1	CMOS	1	200	2.5-3.3	-45 to +85	SOP-8L	

Clock Generators													
Product	Category	Phase Jitter (ps) (Typ, 12 KHz to 20 MHz)	Period Jitter (ps)(peak to peak)	Inputs	No. of outputs	Output Logic	Output Frequency Min. (MHz)	Output Frequency Max. (MHz)	Voltage (V)	Temp. Range (°C)	Dimensions	Frequency Stability (ppm)	
PL671-01	Clock Conditioning		100	Crystal or Reference	3	CMOS	1	200	2.5–3.3	-45 to +85	SOP-8L, SOT23-6L		
PL671-02	Clock Conditioning		100	Crystal or Reference	3	CMOS	1	200	2.5–3.3	-45 to +85	SOT23-6L		
PL613-05	Low Power				3	LVC MOS	1	200	1.8–3.3	-45 to +85			
PL611-01	Low Power Clock Generators	3	40	Crystal or Reference	3	LVC MOS	1	200	2.5–3.3	-45 to +85	DFN-6L, SOT-6L		
PL613-01	Low Power Clock Generators		300	Crystal or Reference	8	LVC MOS	1	200	1.8–3.3	-45 to +85	QFN-16L, TSSOP-16L		
PL611-31	Low Power Clock Generators	2.5	40	Crystal or Reference	3	PECL, LVDS, HCSL, CMOS	5	200	2.5–3.3	-45 to +85	SOP-8L		
PL602031	None	2	25	25MHz Crystal	2	LVC MOS/HCSL	25	25	2.5–3.3	-45 to +85	16-pin QFN 3 × 3		
PL602-27	None	2	25	25MHz Crystal	1	LVC MOS/HCSL	250	250	2.5–3.3	-45 to +85			
PL602082	None	0.22	10	25MHz Crystal	8	HCSL	25	250	2.5–3.3	-45 to +85			
PL607082	None				8	HCSL	25	250	2.5–3.3	-45 to +85			
PL500-17	VCXO	0.1		Crystal	1	CMOS	17	36	2.5/3.3	-45 to +85	Die, SOT-6L, SOP-8L		
PL500-15	VCXO	0.1		Crystal	1	CMOS	1	4	2.5/3.3	-45 to +85	Die, SOT-6L, SOP-8L		
PL611-30	Low-Power Clock Generators	2.5	40	Crystal or Reference	3	PECL, LVDS, HCSL, CMOS	5	400	2.5–3.3	-45 to +85	DFN-6L, SOT-6L		
DSC2040	Low-Power Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	1	HCSL	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
DSC2044	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	HCSL	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
DSC2041	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	HCSL, LVC MOS	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
DSC2042	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	HCSL, LVPECL	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
DSC2211	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	LVC MOS	2.3	460	2.25–3.63	-55 to +125	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
DSC400	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	4	LVC MOS/LVPECL/LVDS/HCSL	2.3	460	2.25V to 3.63V	-40 to +105	5.0 × 3.2 mm 20-pin	±20/25/50 ppm	
DSC2033	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	LVDS	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
DSC2233	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	LVDS	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
DSC2031	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	LVDS, LVC MOS	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5mm	±25, ±50	
DSC2022	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	LVPECL	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
DSC2222	Low-Jitter Clock Generators	1.70/0.3 (200k-20M)	30	Integrated MEMS	2	LVPECL	2.3	460	2.25–3.63	-40 to +105	14-pin QFN, 3.2 × 2.5 mm	±25, ±50	
SM803	Low-Jitter Clock Generators	0.18	5	Crystal or Reference	12	CMOS, PECL, LVDS, HCSL	12	850					
SM813	Low-Jitter Clock Generators	0.115	5	Crystal or Reference	12	PECL, LVDS, HCSL, CMOS	12	850	2.5–3.3	-45 to +85	48-, 76-pin QFN		
ZL30250	Low-Jitter Clock Generators	0.16	1 XTAL/SE, 3 D/SE	3D/GSE		CML, CMOS	<1Hz	1.035	3.3+1.8	-40 to +85	32-pin QFN		
ZL30251	Low-Jitter Clock Generators	0.16	1 XTAL/SE, 3 D/SE	3D/6SE		CML, CMOS	<1Hz	1.035	3.3+1.8	-40 to +85	32-pin QFN		
ZL30244	Low-Jitter Clock Generators	0.16	2 XTAL/SE, 6 D/SE	6D/12SE		CML, CMOS	<1Hz	1.035	3.3+1.8	-40 to +85	64-pin LGA		
ZL30245	Low-Jitter Clock Generators	0.16	2 XTAL/SE, 6 D/SE	6D/12SE		CML, CMOS	<1Hz	1.035	3.3+1.8	-40 to +85	64-pin LGA		
ZL30260	Low-Jitter Clock Generators	0.18	1 XTAL/SE, 3 D/SE	6D/12SE	LVDS, LVPECL, HCSL, CMOS, HSTL	<1Hz	1.035	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN			
ZL30261	Low-Jitter Clock Generators	0.18	1 XTAL/SE, 3 D/SE	6D/12SE	LVDS, LVPECL, HCSL, CMOS, HSTL	<1Hz	1.035	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN			
ZL30262	Low-Jitter Clock Generators	0.18	1 XTAL/SE, 3 D/SE	10D/20SE	LVDS, LVPECL, HCSL, CMOS, HSTL	<1Hz	1.035	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN			
ZL30263	Low-Jitter Clock Generators	0.18	1 XTAL/SE, 3 D/SE	10D/20SE	LVDS, LVPECL, HCSL, CMOS, HSTL	<1Hz	1.035	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN			
ZL30264	Low-Jitter Clock Generators	0.18	1 XTAL/SE, 3 D/SE	6D/12SE	LVDS, LVPECL, HCSL, CMOS, HSTL	<1Hz	1.035	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN			
ZL30265	Low-Jitter Clock Generators	0.18	1 XTAL/SE, 3 D/SE	6D/12SE	LVDS, LVPECL, HCSL, CMOS, HSTL	<1Hz	1.035	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN			
ZL30266	Low-Jitter Clock Generators	0.18	1 XTAL/SE, 3 D/SE	10D/20SE	LVDS, LVPECL, HCSL, CMOS, HSTL	<1Hz	1.035	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN			
ZL30267	Low-Jitter Clock Generators	0.18	1 XTAL/SE, 3 D/SE	10D/20SE	LVDS, LVPECL, HCSL, CMOS, HSTL	<1Hz	1.035	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN			
ZL30281	PCIe Clock Generators	0.16	1 XTAL	3D/6SE	CML, CMOS	25 M, 100 M	N/A	3.3+1.8	-40 to +85	32-pin QFN			

Clock Generators													
Product	Category	Phase Jitter (ps) (Typ, 12 KHz to 20 MHz)	Period Jitter (ps)(peak to peak)	Inputs	No. of outputs	Output Logic	Output Frequency Min. (MHz)	Output Frequency Max. (MHz)	Voltage (V)	Temp. Range (°C)	Dimensions	Frequency Stability (ppm)	
ZL30282	PCIe Clock Generators	0.18		1 XTAL	6D/12SE	LVDS, LVPECL, HCSL, CMOS, HSTL	25 M, 75 M, 100 M	N/A	2.5 V only, 3.3 V only, 1.8 V + 2.5 V, 1.8 V + 3.3 V	-40 to +85	56-pin QFN		
SM806	Low+B123:N123-Jitter Clock Generators	0.079	6	Crystal or Reference	12	PECL, LVDS, HCSL, CMOS	12	850	2.5–3.3	-45 to +85	24-, 48-pin QFN		
MX87	Low-Jitter Clock Generators	0.079	6	Crystal Integrated/ Reference	6	PECL, LVDS, HCSL, CMOS	12	850	2.5–3.3	-45 to +85	48-pin QFN		

High-Speed Communication: Limiting Amplifiers										
Product	Product Type	Data Rate Capability	Power Supply (V)	Data Input Type	Data Output Type	LOS/SD	Packages			
SY84113BU	Fiber Optic Post Amplifiers			1.25 Gbps	2.5	PECL	CML	LOS (TTL)		16-pin VQFN
SY88053CL	Limiting Amplifiers - Burst Mode and Limiting Amplifiers - Continuous Mode			12.5 Gbps	3.3	CML/PECL	CML	SD/LOS (TTL)		16-pin VQFN
SY88063CL	Limiting Amplifiers - Burst Mode and Limiting Amplifiers - Continuous Mode			12.5 Gbps	3.3	CML/PECL	CML	SD/LOS (TTL)		16-pin VQFN
SY88073L	Limiting Amplifiers - Continuous Mode			12.5 Gbps	3.3	CML/PECL	CML	SD/LOS (TTL)		16-pin VQFN
SY88083L	Limiting Amplifiers - Continuous Mode			12.5 Gbps	3.3	CML/PECL	CML	SD/LOS (TTL)		16-pin VQFN
SY88147DL	Limiting Amplifiers - Continuous Mode			1.25 Gbps	3.3	PECL	PECL	LOS (TTL)		10-pin MSOP
SY88149CL	Limiting Amplifiers - Continuous Mode			1.25 Gbps	3.3	PECL	PECL	LOS (TTL)		10-pin MSOP
SY88149HAL	Limiting Amplifiers - Burst Mode			1.25 Gbps	3.3	CML/PECL	PECL	SD/LOS (TTL)		16-pin VQFN
SY88149NDL	Limiting Amplifiers - Burst Mode			1.25 Gbps	3.3	CML/PECL	PECL	SD/LOS (TTL)		Please call for package information
SY88303BL	Limiting Amplifiers - Continuous Mode			3.2 Gbps	3.3	PECL	CML	LOS (TTL)		10-pin MSOP, 16-pin VQFN
SY88343BL	Limiting Amplifiers - Continuous Mode			3.2 Gbps	3.3	PECL	CML	LOS (TTL)		10-pin MSOP, 16-pin VQFN
SY88349NDL	Limiting Amplifiers - Burst Mode			2.5 Gbps	3.3	CML/PECL	PECL	SD/LOS (TTL)		Please call for package information
SY88353BL	Limiting Amplifiers - Continuous Mode			3.2 Gbps	3.3	PECL with Internal 500 to V _{REF}	CML	LOS (TTL)		16-pin VQFN
SY88403BL	Limiting Amplifiers - Continuous Mode			4.25 Gbps	3.3	PECL	CML	LOS (TTL)		10-pin MSOP, 16-pin VQFN
SY88773V	Limiting Amplifiers - Continuous Mode			3.2 Gbps	3.3, 5.0	PECL	CML	LOS (TTL)		16-pin VQFN
SY88803V	Limiting Amplifiers - Continuous Mode			0.16 Gbps	3.3, 5.0	PECL	PECL	LOS (TTL)		10-pin MSOP
SY88813V	Limiting Amplifiers - Continuous Mode			0.16 Gbps	3.3, 5.0	PECL	PECL	SD (PECL)		10-pin MSOP
SY88843V	Limiting Amplifiers - Continuous Mode			3.2 Gbps	3.3, 5.0	PECL	CML	SD (TTL)		Please call for package information
SY88893V	Fiber Optic Post Amplifiers			0.155 Gbps		PECL	PECL	SD (TTL)		10-pin MSOP
SY88903AL	Limiting Amplifiers - Continuous Mode			1.25 Gbps	3.3	PECL	PECL	LOS (TTL)		10-pin MSOP
SY88903V	Limiting Amplifiers - Continuous Mode			1.25 Gbps	3.3, 5.0	PECL	PECL	LOS (TTL)		10-pin MSOP
SY88923AV	Fiber Optic Post Amplifiers			3.2 Gbps	3.3, 5	PECL	PECL	LOS (TTL)		10-pin MSOP
SY88933AL	Limiting Amplifiers - Continuous Mode			1.25 Gbps	3.3	PECL	PECL	SD (TTL)		10-pin MSOP
SY88073L	Limiting Amplifiers - Continuous Mode			12.5 Gbps	3.3	CML/PECL	CML	SD/LOS (TTL)		16-pin VQFN
SY88063CL	Limiting Amplifiers - Burst Mode and Limiting Amplifiers - Continuous Mode			12.5 Gbps	3.3	CML/PECL	CML	SD/LOS (TTL)		16-pin VQFN
SY88053CL	Limiting Amplifiers - Burst Mode and Limiting Amplifiers - Continuous Mode			12.5 Gbps	3.3	CML/PECL	CML	SD/LOS (TTL)		16-pin VQFN
SY84403BL	Limiting Amplifiers - Continuous Mode			4.25 Gbps	3.3	PECL with Internal 500 to V _{REF}	CML	LOS (TTL)		Please call for package information
SY84113BU	Fiber Optic Post Amplifiers			1.25 Gbps	2.5	PECL	CML	LOS (TTL)		16-pin VQFN

High-Speed Communication: Laser Diode Drivers															
Product	Product Type	Data Rate Capability	Power Supply (V)	Data Input Type	Modulation Current	Bias Current	Packages								
SY84782U	DFB/FP Laser Drivers	1.25 Gbps	2.5	CML	90	80	16-pin VQFN								
SY88022AL	DFB/FP Laser Drivers	11.3 Gbps	3.3	Please call for package information				Please call for package information							
SY88024L	VCSEL Drivers	11.3 Gbps	3.3	Please call for package information				16-pin VQFN							
SY88422L	DFB/FP Laser Drivers	4.25 Gbps	3.3	10-pin MSOP				10-pin MSOP							
SY88822V	DFB/FP Laser Drivers	0.155 Gbps	3.3, 5.0	16-pin VQFN				16-pin VQFN							
SY88922V	DFB/FP Laser Drivers	2.5 Gbps	3.3, 5.0	16-pin VQFN				16-pin VQFN							
SY88932L	DFB/FP Laser Drivers	4.25 Gbps	3.3	CML	60	90	16-pin VQFN								
SY88982L	DFB/FP Laser Drivers	2.7 Gbps	3.3	16-pin VQFN				16-pin VQFN							
SY88992L	VCSEL Drivers	4.25 Gbps	3.3	16-pin VQFN				16-pin VQFN							
High-Speed Communication: Laser Diode Drivers															
Product	Product Type	Data Rate Capability	Power Supply (V)	LA Data Input Type	LA Data Output Type	LDD Data Input Type	LDD Modulation Current (mA)	LDD Bias Current (mA)	Packages						
SY88432L	Transceivers	4.25 Gbps	3.3	CML	CML	CML	60	24-pin VQFN							
High-Speed Communication: Fiber Optic Module Controllers															
Product	Product Type	Power Supply (V)			Serial Interface			Packages							
MIC3001GML	FOM Controllers	3.3			I ² C SMBus Compliant			Please call for package information							
MIC3003GFL	FOM Controllers	3.3			I ² C SMBus Compliant			Please call for package information							
MIC3003GML	FOM Controllers	3.3			I ² C SMBus Compliant			Please call for package information							
High-Speed Communication: Clock and Data Recovery															
Product	Product Type	Data Rate Capability	Power Supply (V)	Data Input Type	Data Output Type	Packages									
SY69753AL	Clock and Data Recovery	125–155 Mbps	3.3	PECL		32/TQFP									
SY87700AL	Clock and Data Recovery	32–208 Mbps	3.3	PECL		Please call for package information									
SY87701AL	Clock and Data Recovery	28–1300 Mbps	3.3	PECL		Please call for package information									
Memory Products: Serial Flash															
Product	Bus	Density	Organization	Max. Clock Frequency	Operating Voltage	Temperature Range	E/W Endurance (Minimum)	Data Retention (Minimum)	Write Speed (Typical)	Max. Standby Current	Hard Pin Protect	Software Protect	Protected Array Size	Packages	
SST25VF512A	x 1	512 KB	x 8	33 MHz	2.7–3.6V	-40°C to +85°C	100k	100 Years	14 µs (Byte Program)	8 µA	Y	Y	Various	8L-SOIC, 8C-WSON	
SST25VF010A	x 1	1 MB	x 8	33 MHz	2.7–3.6V	-40°C to +85°C	100k	100 Years	14 µs (Byte Program)	8 µA	Y	Y	Various	8L-SOIC, 8C-WSON	
SST25VF020B	x 1	2 MB	x 8	80 MHz	2.7–3.6V	-40°C to +85°C	100k	100 Years	7 µs (Word Program)	5 µA	Y	Y	Various	8L-SOIC, 8C-WSON	
SST25WF020A	x 1	2 MB	x 8	40 MHz	1.65–1.95V	-40°C to +85°C	100k	20 Years	3 ms (Page Program)	10 µA	Y	Y	Various	8L-SOIC, 8C-WSON, 8C-USON, 9B-WLCSP	
SST25VF040B	x 1	4 MB	x 8	40 MHz	2.7–3.6V	-40°C to +85°C	100k	100 Years	7 µs (Word Program)	5 µA	Y	Y	Various	8L-SOIC, 8C-WSON	
SST26WF040B/BA	x 1, x 2, x 4	4 MB	x 8	104 MHz	1.65–1.95V	-40°C to +85°C	100k	100 Years	1 ms (Page Program)	40 µA	Y	Y	Various	8L-SOIC, 8C-WSON, 8C-USON, 8B-WLCSP	
SST25VF080B	x 1	8 MB	x 8	40 MHz	2.7–3.6V	-40°C to +85°C	100k	100 Years	7 µs (Word Program)	5 µA	Y	Y	Various	8L-SOIC, 8C-WSON, 8B-XFBGA	
SST26WF080B/BA	x 1, x 2, x 4	8 MB	x 8	104 MHz	1.65–1.95V	-40°C to +85°C	100k	100 Years	1 ms (Page Program)	40 µA	Y	Y	Various	8L-SOIC, 8C-WSON, 8C-USON, 8B-WLCSP	
SST26WF016B/BA	x 1, x 2, x 4	16 MB	x 8	104 MHz	1.65–1.95V	-40°C to +85°C	100k	100 Years	1 ms (Page Program)	40 µA	Y	Y	Various	8L-SOIC, 8C-WSON, 8B-WLCSP	
SST26VF016B	x 1, x 2, x 4	16 MB	x 8	104 MHz	2.3–3.6V	-40°C to +105°C	100k	100 Years	1 ms (Page Program)	45 µA	Y	Y	Various	8L-SOIC, 8L-SOIJ, 8C-WSON	
SST26VF032B/BA	x 1, x 2, x 4	32 MB	x 8	104 MHz	2.3–3.6V	-40°C to +105°C	100k	100 Years	1 ms (Page Program)	45 µA	Y	Y	Various	8L-SOIJ, 8C-WSON, 24B-TBGA	

Memory Products: Serial Flash

Product	Bus	Density	Organization	Max. Clock Frequency	Operating Voltage	Temperature Range	E/W Endurance (Minimum)	Data Retention (Minimum)	Write Speed (Typical)	Max. Standby Current	Hard Pin Protect	Software Protect	Protected Array Size	Packages
SST26VF064B/BA	x 1, x 2, x 4	64 MB	x 8	104 MHz	2.3–3.6V	–40°C to +105°C	100k	100 Years	1 ms (Page Program)	45 µA	Y	Y	Various	8L-SOJ, 16L-SOIC, 8C-WSON, 8C-TDFN-S, 24B-TBGA
SST26WF064C	x 1, x 2, x 4	64 MB	x 8	104 MHz	1.65–1.95V	–40°C to +85°C	100k	100 years	1.5 ms (Page Program)	40 µA	Y	Y	Various	8L-SOJ, 16L-SOIC, 8C-WSON, 24B-TBGA

Memory Products: Parallel Flash

Product	Density	Bus	Organization	Access Time (ns)	Operating Voltage	Temperature Range (°C)	E/W Endurance (Minimum)	Data Retention (Minimum)	Write Speed (Typical)	Typ. Standby Current	Hard Pin Protect	Software Protect	Protected Array Size (KB)	Special/ Unique Features	Packages
SST39SF010A	1 MB	x 8	x 8	70	4.5–5.5V	–40 to +85	100K	100 Years	14 µs (Byte Program)	30 µA	–	–	N/A	Fast read, program and erase; Low power; Small erase sector	32L-PLCC, 32L-PDIP, 32L-TSOP
SST39LF010	1 MB	x 8	x 8	55	3.0–3.6V	0 to 70	100K	100 Years	14 µs (Byte Program)	1 µA	–	–	N/A	Fast read, program and erase; Low power; Small erase sector	48B-TFBGA, 32L-TSOP, 32L-PLCC
SST39VF010	1 MB	x 8	x 8	70	2.7–3.6V	–40 to +85	100K	100 Years	14 µs (Byte Program)	1 µA	–	–	N/A	Fast read, program and erase; Low power; Small erase sector	48B-TFBGA, 32L-TSOP, 32L-PLCC
SST39SF020A	2 MB	x 8	x 8	55, 70	4.5–5.5V	–40 to +85	100K	100 Years	14 µs (Byte Program)	30 µA	–	–	N/A	Fast read, program and erase; Low power; Small erase sector	32L-PLCC, 32L-PDIP, 32L-TSOP
SST39VF020	2 MB	x 8	x 8	70	2.7–3.6V	–40 to +85	100K	100 Years	14 µs (Byte Program)	1 µA	–	–	N/A	Fast read, program and erase; Low power; Small erase sector	48B-TFBGA, 32L-TSOP, 32L-PLCC
SST39SF040	4 MB	x 8	x 8	70	4.5–5.5V	–40 to +85	100K	100 Years	14 µs (Byte Program)	30 µA	–	–	N/A	Fast read, program and erase; Low power; Small erase sector	32L-PLCC, 32L-PDIP, 32L-TSOP
SST39WF400B	4 MB	x 16	x 16	70	1.65–1.95V	–40 to +85	100K	100 Years	28 µs (Word Program)	40 µA	–	–	N/A	Fast read, program and erase; Low power; Small erase sector	48B-TFBGA, 48B-WFBGA, 48B-XFBGA
SST39VF40xC	4 MB	x 16	x 16	70	2.7–3.6V	–40 to +85	100K	100 Years	7 µs (Word Program)	3 µA	Y	–	8	Fast read, program and erase; Low power; Small erase sector; Industry-standard command set and boot block structure	48B-TFBGA, 48L-TSOP, 48B-WFBGA
SST39WF800B	8 MB	x 16	x 16	70	1.65–1.95V	–40 to +85	100K	100 Years	28 µs (Word Program)	40 µA	–	–	N/A	Fast read, program and erase; Low power; Small erase sector	48B-TFBGA, 48B-WFBGA, 48B-XFBGA
SST39LF80xC	8 MB	x 16	x 16	55	3.0–3.6V	0 to 70	100K	100 Years	7 µs (Word Program)	3 µA	Y	–	N/A	Fast read, program and erase; Low power; Small erase sector; Industry-standard command set and boot block structure	48B-TFBGA, 48L-TSOP, 48B-WFBGA
SST39VF80xC	8 MB	x 16	x 16	70	2.7–3.6V	–40 to +85	100K	100 Years	7 µs (Word Program)	3 µA	Y	–	N/A	Fast read, program and erase; Low power; Small erase sector; Industry-standard command set and boot block structure	48B-TFBGA, 48L-TSOP, 48B-WFBGA
SST39WF160x	16 MB	x 16	x 16	70	1.65–1.95V	–40 to +85	100K	100 Years	28 µs (Word Program)	40 µA	Y	–	64	Fast read, program and erase; Low power; Small erase sector	48B-TFBGA, 48B-WFBGA, 48B-XFBGA
SST39VF160xC	16 MB	x 16	x 16	70	2.7–3.6V	–40 to +85	100K	100 Years	7 µs (Word Program)	3 µA	Y	–	8	Fast read, program and erase; Low power; Small erase sector; Industry-standard command set and boot block structure	48B-TFBGA, 48L-TSOP, 48B-WFBGA
SST39VF320xC	32 MB	x 16	x 16	70	2.7–3.6V	–40 to +85	100K	100 Years	7 µs (Word Program)	4 µA	Y	–	8	Fast read, program and erase; Low power; Small erase sector; Industry-standard command set and boot block structure	48B-TFBGA, 48L-TSOP
SST38VF640xB	64 MB	x 16	x 16	70	2.7–3.6V	–40 to +85	100K	100 Years	7 µs/1.75 µs (Write Buffer Program)	3 µA	Y	Y	32, 8	Fast read, program and erase; Low power; Industry-standard command set and boot block structure, Security features	48B-TFBGA, 48L-TSOP

Memory Products: Serial EEPROM

Bus	Product	Density	Organization	Max. Clock Frequency	Operating Voltage (V)	Temperature Range	E/W Endurance (Minimum)	Data Retention (Minimum)	Factory Programmed Serial Number	Max. Standby Current (@ 5.5V, 25°C)	Hard Pin Protect	Software Protect	Protected Array Size	5 ku Pricing (\$)	Special/Unique Features	Packages
Single Wire	AT21CS01	1 KB	x 8	125 kbps	1.7–3.6	-40°C to +85°C	1M	100 Years	Y	2.5 μA	–	Y	W, ¾, ½, ¼	0.42	Two pins only: SI/O and GND. 256-bit security register with 64-bit serial number	SOIC (SS), SOT-23 (ST), UDFN (MA), WLCSP (U), XSFN (MS)
	AT21CS11	1 KB	x 8	125 kbps	2.7 to 4.5	-40°C to +85°C	1M	100 Years	Y	2.5 μA	–	Y	W, ¾, ½, ¼	0.42	Two pins only: SI/O and GND. 256-bit security register with 64-bit serial number	SOIC (SS), SOT-23 (ST), UDFN (MA), WLCSP (U), XSFN (MS)
	24xx00	128 b	x 8	400 kHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	1 μA	–	–	–	0.14	No address pins - single slave address	PDIP (P), SOIC (SN), TSSOP (ST), DFN (MNY), 5-SOT-23 (OT)
	24xx01/014	1 KB	x 8	400 kHz	1.7–5.5	-40°C to +150°C	1M	200 Years	N	1 μA	Y	–	W, ½	0.14	Three address pins - cascade up to eight devices to share a common 2-wire bus. 014 has page size = 16 Bytes	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT), SC70 (LT)
	AT24C01C	1 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 μA	Y	–	W	0.09	Three address pins - cascade up to eight devices to share a common 2-wire bus	PDIP (P), SOIC (SS), SOT-23 (ST), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
	AT24CS01	1 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	6 μA	Y	–	W	0.15	Unique 128-bit serial number separate from the main memory array	SOIC (SS), TSOT (ST), TSSOP (X), UDFN (MA)
	AT24CSW01	1 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	0.8 μA	–	Y	W, ¾, ½, ¼	0.10	Software Slave Address, 256-bit security register separate from the main array (128-bit register factory-programmed, 128-bit user programmable and permanently lockable), write protect can also be permanently locked	WLCSP (U)
	24xx02/024/025	2 KB	x 8	400 kHz	1.7–5.5 1.5–3.6	-40°C to +125°C	1M	200 Years	N	1 μA	Y	–	W, ½	0.16	Three address pins - cascade up to eight devices to share a common 2-wire bus. 024 and 025 has page size =16 Bytes; 025 has no write protect	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT), SC70 (LT)
	24xx02E48/ E64/ UID	2 KB	x 8	400 kHz	1.7–5.5 1.5–3.6	-40°C to +125°C	1M	200 Years	Y	1 μA	Y	–	W, ½	0.18	Three address pins - cascade up to eight devices to share a common 2-wire bus, unique EUI-48/EUI-64 MAC address and unique ID options available	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT), SC70 (LT)
	AT24C02C	2 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 μA	Y	–	W	0.08	Three address pins - cascade up to eight devices to share a common 2-wire bus	PDIP (P), SOIC (SS), SOT-23 (ST), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
I ^C	AT24CS02	2 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	6 μA	Y	–	W	0.16	Unique 128-bit serial number separate from the main memory array	SOIC (SS), TSOT (ST), TSSOP (X), UDFN (MA)
	AT24CSW02	2 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	0.8 μA	–	Y	W, ¾, ½, ¼	0.11	Software Slave Address, 256-bit security register separate from the main array (128-bit register factory-programmed, 128-bit user programmable and permanently lockable), write protect can also be permanently locked	WLCSP (U)
	AT24HC02C	2 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 μA	Y	–	½	0.11	Three address pins - cascade up to eight devices to share a common 2-wire bus, half array write protect	PDIP (P), SOIC (SS), TSSOP (X)
	AT24MAC402/602	2 KB	x 8	1 MHz	1.7–5.5	-40°C to +85°C	1M	100 Years	Y	6 μA	Y	Y	W, ½	0.22	Unique IEEE -provided 48/64-bit pre-programmed MAC/EUI address, unique read-only 128-bit serial number	SOIC (SS), TSOT (ST), TSSOP (X), UDFN (MA)
	24xx04/44	4 KB	x 8	400 kHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	1 μA	Y	–	W, ½	0.17	04 has three address pins - cascade up to eight devices, 044 has two address pins - cascade up to four devices, 044 has lower current specs	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT), WLCSP (CS)
	AT24C04C	4 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 μA	Y	–	W	0.12	Two address pins - cascade up to four devices to share a common 2-wire bus.	PDIP (P), SOIC (SS), SOT-23 (ST), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
	AT24CS04	4 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	6 μA	Y	–	W	0.18	Unique 128-bit serial number separate from the main memory array	SOIC (SS), TSOT (ST), TSSOP (X), UDFN (MA)
	AT24CSW04	4 KB	x 8	1 MHz	1.7–5.5	-40°C to +85°C	1M	100 Years	Y	0.8 μA	–	Y	W, ¾, ½, ¼	0.13	Software Slave Address, 256-bit security register separate from the main array (128-bit register factory-programmed, 128-bit user programmable and permanently lockable), write protect can also be permanently locked	WLCSP (U)
	AT24HC04B	4 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	0.8 μA	Y	–	½	0.13	Two address pins - cascade up to four devices to share a common 2-wire bus, half array write protect	PDIP (PU), SOIC (S), TSSOP (T)
	24xx08	8 KB	x 8	400 kHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	1 μA	Y	–	W, ½	0.19	Three address pins - cascade up to eight devices to share a common 2-wire bus, 16 byte page write buffer	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT),
24xx	AT24C08C	8 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 μA	Y	–	W	0.12	One address pin - cascade up to two devices to share a common 2-wire bus	PDIP (P), SOIC (SS), SOT-23 (ST), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
	AT24CS08	8 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	6 μA	Y	–	W	0.20	Unique 128-bit serial number separate from the main memory array	SOIC (SS), TSOT (ST), TSSOP (X), UDFN (MA)
	AT24CSW08	8 KB	x 8	1 MHz	1.7–5.5	-40°C to +85°C	1M	100 Years	Y	0.8 μA	–	Y	W, ¾, ½, ¼	0.21	Software Slave Address, 256-bit security register separate from the main array (128-bit register factory-programmed, 128-bit user programmable and permanently lockable), write protect can also be permanently locked	WLCSP (U)
	24xx16	16 KB	x 8	400 kHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	1 μA	Y	–	W, ½	0.20	Three address pins - cascade up to eight devices to share a common 2-wire bus, 16 byte page write buffer	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT), WLCSP (CS)
	AT24C16C	16 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6.0 μA	Y	–	W	0.12	No address pins - single slave address	PDIP (P), SOIC (SS), SOT-23 (ST), TSSOP (X), UDFN (MA), VFBGA (C), XDFN (ME)

Memory Products: Serial EEPROM

Bus	Product	Density	Organization	Max. Clock Frequency	Operating Voltage (V)	Temperature Range	E/W Endurance (Minimum)	Data Retention (Minimum)	Factory Programmed Serial Number	Max. Standby Current (@ 5.5V, 35°C)	Hard Pin Protect	Software Protect	Protected Array Size	5 ku Pricing (\$)	Special/Unique Features	Packages
I ² C	AT24CS16	16 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	6 µA	Y	–	W	0.23	Unique 128-bit serial number separate from the main memory array	SOIC (SS), TSOT (ST), TSSOP (X), UDFN (MA)
	24xx32A	32 KB	x 8	400 kHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	1 µA	Y	–	W, 1/4	0.25	Three address pins - cascade up to eight devices to share a common 2-wire bus, 32 byte page write buffer	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT), WLCSP (CS)
	AT24C32D	32 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	0.8 uA	Y	–	W	0.13	Three address pins - cascade up to eight devices to share a common 2-wire bus	SOIC (SS), SOT-23 (ST), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C), XDFN (ME)
	AT24CS32	32 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	6 µA	Y	–	W	0.27	Unique 128-bit serial number separate from the main memory array	SOIC (SS), TSOT (ST), TSSOP (X), UDFN (MA)
	24xx64	64 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M, 10M	200 Years	N	1 µA	Y	–	W, 1/4	0.28	Three address pins - cascade up to eight devices to share a common 2-wire bus, 32 byte page write buffer	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT), WLCSP (CS)
	24xx65	64 KB	x 8	1 MHz	1.8–6	-40°C to +125°C	1M, 10M	200 Years	N	1 µA	–	Y	up to 15 4 KB blks	0.28	Three address pins, software WP, high endurance block, page size up to 64 Bytes	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 5-SOT-23 (OT), WLCSP (CS)
	AT24C64D	64 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 µA	Y	–	W	0.15	Three address pins - cascade up to eight devices to share a common 2-wire bus	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C), WLCSP (U), XDFN (ME)
	AT24CS64	64 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	Y	6 µA	Y	–	W	0.32	Unique 128-bit serial number separate from the main memory array	SOIC (SS), TSSOP (X), UDFN (MA)
	24xx128	128 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	1 µA	Y	–	W	0.40	Three address pins - cascade up to eight devices to share a common 2-wire bus	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), WLCSP (CS)
	AT24C128C	128 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 µA	Y	–	W	0.22	Three address pins - cascade up to eight devices to share a common 2-wire bus	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C), WLCSP (U), XDFN (ME)
	24xx256	256 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	1 µA	Y	–	W	0.59	Three address pins - cascade up to eight devices to share a common 2-wire bus	PDIP (P), SOIC (SN), TSSOP (ST), SOIJ (SM), MSOP (MS), DFN (MF), WLCSP (CS), TDFN (MNY)
	24xx256UID	256 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	200 Years	Y	1 µA	Y	–	W	0.68	Three address pins - cascade up to eight devices to share a common 2-wire bus, EUI-48, EUI-64 and unique ID options available	PDIP (P), SOIC (SN), TSSOP (ST), SOIJ (SM), MSOP (MS), DFN (MF), WLCSP (CS), TDFN (MNY)
	AT24C256C	256 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 µA	Y	–	W	0.34	Three address pins - cascade up to eight devices to share a common 2-wire bus	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
	24xx512	512 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	1 µA	Y	–	W	0.90	Three address pins - cascade up to eight devices to share a common 2-wire bus	PDIP (P), SOIC (SN), TSSOP (ST), DFN (MF), SOIJ (SM), WLCSP (CS)
	AT24C512C	512 KB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	40 Years	N	6 µA	Y	–	W	0.65	Three address pins - cascade up to eight devices to share a common 2-wire bus	SOIC (SS), SOIJ (S), TSSOP (X), UDFN (MA), VFBGA (C), WLCSP (U)
	24xx1025/26	1 MB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	200 Years	N	5 µA	Y	–	W	2.22	Two address pins - cascade up to four devices to share a common 2-wire bus, 25 and 26 difference is address pins	PDIP (P), SOIC (SN), SOIJ (SM)
	AT24CM01	1 MB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	40 Years	N	6 µA	Y	–	W	0.99	Two address pins - cascade up to four devices to share a common 2-wire bus.	SOIC (SS), SOIJ (S), TSSOP (X), WLCSP (U)
	AT24CM02	2 MB	x 8	1 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	6 µA	Y	–	W	1.16	Two address pins - cascade up to four devices to share a common 2-wire bus.	SOIC (SS), WLCSP (U)
SPI	25xx010A	1 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, 1/2, 1/4	0.28	5 MHz @ 2.5V, Status register, 16 byte page	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 6-SOT-23 (OT)
	AT25010B	1 KB	x 8	20 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	3.5 µA	Y	Y	W, 1/2, 1/4	0.12	Supports SPI Modes 0 (0, 0) and 3 (1, 1)	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
	25xx020A	2 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, 1/2, 1/4	0.29	5 MHz @ 2.5V, Status register, 16 byte page, Unique EUI-48/EUI-64 MAC address and unique ID options available	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 6-SOT-23 (OT)
	25xx020E48/ E64/ UID	2 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	Y	1 µA	Y	Y	W, 1/2, 1/4	0.30	5 MHz @ 2.5V, Status register, 16 byte page, Unique EUI-48/EUI-64 MAC address and unique ID options available	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 6-SOT-23 (OT)
	AT25020B	2 KB	x 8	20 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	3.5 µA	Y	Y	W, 1/2, 1/4	0.15	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP)
	25xx040A	4 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, 1/2, 1/4	0.31	5 MHz @ 2.5V, Status register, 16 byte page	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY), 6-SOT-23 (OT)
	AT25040B	4 KB	x 8	20 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	3.5 µA	Y	Y	W, 1/2, 1/4	0.13	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
	25xx080C/D	8 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, 1/2, 1/4	0.37	16/32 byte page, 5 MHz @ 2.5V, Status register	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY)

Memory Products: Serial EEPROM																
Bus	Product	Density	Organization	Max. Clock Frequency	Operating Voltage (V)	Temperature Range	E/W Endurance (Minimum)	Data Retention (Minimum)	Factory Programmed Serial Number	Max. Standby Current (@ 5.5V, 85°C)	Hard Pin Protect	Software Protect	Protected Array Size	5 ku Pricing (\$)	Special/Unique Features	Packages
SPI	AT25080B	8 KB	x 8	5 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	13 µA	Y	Y	W, ½, ¼	0.16	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C), WLCSP (U), XDFN (ME)
	25xx160C/D	16 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, ½, ¼	0.39	16/32 byte page, 5 MHz @ 2.5V, Status register	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY)
	AT25160B	16 KB	x 8	5 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	13 µA	Y	Y	W, ½, ¼	0.17	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C), XDFN (ME)
	25xx320A	32 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, ½, ¼	0.42	5 MHz @ 2.5V, Status register, 32 byte page	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY)
	AT25320B	32 KB	x 8	5 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	13 µA	Y	Y	W, ½, ¼	0.22	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C), XDFN (ME)
	25xx640A	64 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, ½, ¼	0.43	5 MHz @ 2.5V, Status register, 32 byte page	PDIP (P), SOIC (SN), TSSOP (ST), MSOP (MS), DFN (MNY, MF)
	AT25640B	64 KB	x 8	5 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	13 µA	Y	Y	W, ½, ¼	0.32	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C), XDFN (ME)
	25xx128	128 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, ½, ¼	0.65	5 MHz @ 2.5V, Status register, 64 byte page	PDIP (P), SOIC (SN), TSSOP (ST), DFN (MF)
	AT25128B	128 KB	x 8	20 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	5.0 µA	Y	Y	W, ½, ¼	0.41	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
	25xx256	256 KB	x 8	10 MHz	1.8–5.5	-40°C to +150°C	1M	200 Years	N	1 µA	Y	Y	W, ½, ¼	0.87	5 MHz @ 2.5V, Status register, 64 byte page	PDIP (P), SOIC (SN), TSSOP (ST), DFN (MF), SOIJ (SM)
	AT25256B	256 KB	x 8	20 MHz	1.7–5.5	-40°C to +125°C	1M	100 Years	N	5.0 µA	Y	Y	W, ½, ¼	0.75	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), SOIJ (S), TSSOP (X), UDFN (MA), UDFN (MAP), VFBGA (C)
	25xx512	512 KB	x 8	20 MHz	1.8–5.5	-40°C to +125°C	1M	200 Years	N	10 µA	Y	Y	W, ½, ¼	1.21	10 MHz @ 2.5V, Deep power down, Status register, Page/sector/chip erase	PDIP (P), SOIC (SN), DFN (MF), SOIJ (SM)
	AT25512	512 KB	x 8	20 MHz	1.8–5.5	-40°C to +85°C	1M	40 Years	N	5.0 µA	Y	Y	W, ½, ¼	0.95	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (S), TSSOP (T), UDFN (Y)
	25xx1024	1 MB	x 8	20 MHz	1.8–5.5	-40°C to +125°C	1M	200 Years	N	12 µA	Y	Y	W, ½, ¼	2.28	10 MHz @ 2.5V, Deep power down, Status register, Page/sector/chip erase	PDIP (P), DFN (MF), SOIJ (SM)
	AT25M01	1 MB	x 8	20 MHz	1.7–5.5	-40°C to +85°C	1M	100 Years	N	5.0 µA	Y	Y	W, ½, ¼	1.18	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), SOIJ (S), UDFN (MF), WLCSP (U)
	AT25M02	2 MB	x 8	5 MHz	1.7–5.5	-40°C to +85°C	1M	40 Years	N	3.0 µA	Y	Y	W, ½, ¼	1.24	Supports SPI Modes 0 (0,0) and 3 (1,1)	SOIC (SS), WLCSP (U)

Memory Products: Serial RAM																
Bus	Product	Density	Organization	Max. Clock Frequency	Operating Voltage (V)	Temperature Range (°C)	E/W Endurance (Minimum)	Data Retention (Minimum)	Max. Standby Current (@ 5.5V, 85°C)	Hard Pin Protect	Software Protect	Protected Array Size	Special/Unique Features	Serial SRAM		Packages
SPI	23x640	64 KB	x 8	20 MHz	1.5–1.95, 2.7–3.6	-40 to +125	8	Volatile	4 µA	-	-	-	Zero write cycle time, Infinite endurance, Volatile RAM, Byte/page/sequential read-write modes	PDIP (P), SOIC (SN), TSSOP (ST)		
	23x256	256 KB	x 8	20 MHz	1.5–1.95, 2.7–3.6	-40 to +125	8	Volatile	4 µA	-	-	-	Zero write cycle time, Infinite endurance, Volatile RAM, Byte/page/sequential read-write modes	PDIP (P), SOIC (SN), TSSOP (ST)		
	23xx512	512 KB	x 8	20 MHz	1.7–2.2, 2.5–5.5	-40 to +125	8	Volatile	4 µA	-	-	-	Fast Speed: Quad SPI available (80 MHz), Infinite endurance, Zero write times, 5V capable	SOIC (SN), PDIP (P), TSSOP (ST)		
	23xx1024	1024 KB	x 8	20 MHz	1.7–2.2, 2.5–5.5	-40 to +125	8	Volatile	4 µA	-	-	-	Fast Speed: Quad SPI available (80 MHz), Infinite endurance, Zero write times, 5V capable	SOIC (SN), PDIP (P), TSSOP (ST)		

Memory Products: Serial RAM															Special/ Unique Features	Packages	
Bus	Product	Density	Organization	Max. Clock Frequency	Operating Voltage (V)	Temperature Range (°C)	E/W Endurance (Minimum)	Data Retention (Minimum)	Max. Standby Current (@ 5.5V, 85°C)	Hard Pin Protect	Software Protect	Protected Array Size					
Serial NVSRAM																	
SPI	23LCV512	512 KB	x 8	20 MHz	2.5–5.5	–40 to +85	8	20 Years via battery	4 µA	–	–	–	Battery-backed non-volatile SRAM, Infinite endurance, Zero write times	SOIC (SN), PDIP (P), TSSOP (ST)			
	23LCV1024	1024 KB	x 8	20 MHz	2.5–5.5	–40 to +85	8	20 Years via battery	4 µA	–	–	–	Battery backed non-volatile SRAM, Infinite endurance, Zero write times	SOIC (SN), PDIP (P), TSSOP (ST)			
Serial EERAM																	
I ^C	47x04	4 KB	x 8	1 MHz	2.7–3.6, 4.5–5.5	–40 to +125	8	200 Years	40 µA	–	Y	W to 1/64	Unlimited endurance to SRAM, Data automatically backed up to EEPROM and power down (with small external capacitor)	SOIC (SN), PDIP (P), TSSOP (ST)			
	47x16	16 KB	x 8	1 MHz	2.7–3.6, 4.5–5.5	–40 to +125	8	200 Years	40 µA	–	Y	W to 1/64	Unlimited endurance to SRAM, Data automatically backed up to EEPROM and at power down (with small extenal capacitor)	SOIC (SN), PDIP (P), TSSOP (ST)			
Memory Products: Real-Time Clock/Calendar (RTCC)																	
Bus	Product	Pins	Timing Features				Memory			Power		Unique Features ⁽²⁾			Packages		
I ^C	MCP7940M	8	±127 ppm	1 sec.	–	IRQ/CLK	64	0	0	1.8	–	–	–	–	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY), PDIP (P)		
	MCP7940N	8	±127 ppm	1 sec.	–	IRQ/CLK	64	0	0	1.8	1.3	Power Fail Timestamp	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY), PDIP (P)				
	MCP7940x	8	±127 ppm	1 sec.	–	IRQ/CLK	64	0	64	1.8	1.3	Power Fail Timestamp	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY)				
	MCP7941x	8	±127 ppm	1 sec.	–	IRQ/CLK	64	1	64	1.8	1.3	Power Fail Timestamp	SOIC (SN), TSSOP (ST), MSOP (MS), TDFN (MNY)				
	MCP7951x	10	±255 ppm	0.01 sec.	–	IRQ/CLK	64	1	128	1.8	1.3	Power Fail Timestamp	SOIC (SL), TSSOP (ST)				
SPI	MCP7952x	10	±255 ppm	0.01 sec.	–	IRQ/CLK	64	2	128	1.8	1.3	Power Fail Timestamp	MSOP (MS), TDFN (MN)				
	MCP795W1x	14	±255 ppm	0.01 sec.	Y	IRQ/CLK/WDT RST	64	1	128	1.8	1.3	Power Fail Timestamp, Event Detects (x 2)	SOIC (SL), TSSOP (ST)				
	MCP795W2x	14	±255 ppm	0.01 sec.	Y	IRQ/CLK/WDT RST	64	2	128	1.8	1.3	Power Fail Timestamp, Event Detects (x 2)	SOIC (SL), TSSOP (ST)				
Wireless Products: Wi-Fi® Modules																	
Product	Radio		Pin Count	Antenna		Frequency Range (GHz)	Sensitivity (dBm)	Power Output (dBm)	Tx Power Consumption (mA)	Rx Power Consumption (mA)	Tested Throughput Mbps		Encryption/ Security			Interface	Packages (Dimensions)
ATSAMW25	802.11 b/g/n		51	Chip, PCB, U.FL		2.412–2.472	–98	17	264	61	TCP: 10 UDP: 15	TCP: 8 UDP: 11	WEP, WPA/WPA2 Personal and Enterprise, TLS			SPI	51/Module (33.9 x 14.9 mm)
ATWINC15x0	802.11 b/g/n		28	Chip, PCB, U.FL		2.412–2.472	–89	17	264	61	TCP: 11 UDP: 19	TCP: 10 UDP: 12	WEP, WPA/WPA2 Personal and Enterprise, TLS			SPI	28/Module (21.7 x 14.7mm)
ATWINC3400-MR	802.11 b/g/n and BLE		36	Chip		2.412–2.484	–96	4 (BLE), 14 (Wi-Fi)	350 (Wi-Fi), 45 (BLE)	92 (Wi-Fi), 45 (BLE)	TCP: 3 UDP: 6	TCP: 5 UDP: 5	WEP, WPA/WPA2 Personal			SPI, UART	37/Module (22.4 x 14.7 mm)
ATWILC1000-MR	802.11 b/g/n		28	PCB		2.412–2.484	–96	15	289	52.5	Linux® TCP: 26 UDP: 46	Linux TCP: 20 UDP: 25	WEP, WPA/WPA2 Personal and Enterprise, TLS (Linux) WEP, WPA/WPA2 Personal and Enterprise (RTOS)			SPI, SDIO	29/Module (21.5 x 14.5 mm)
ATWILC3000-MR	802.11 b/g/n and BLE		36	Chip		2.412–2.484	–96	4 (BLE), 14 (Wi-Fi)	295 (Wi-Fi), 110 (BLE)	86 (Wi-Fi), 45 (BLE)	Linux TCP: 28 UDP: 16	Linux TCP: 20 UDP: 24	WEP, WPA/WPA2 Personal and Enterprise, TLS (Linux) WEP, WPA/WPA2 Personal (RTOS)			SPI, SDIO, UART	37/Module (22.4 x 14.7 mm)

Wireless Products: IEEE 802.15.4 Transceivers/Modules

Product	Pin Count	Antenna	Frequency Range (GHz)			Sensitivity (dBm)	Power Output (dBm)	RSSI	Tx Power Consumption (mA)	Rx Power Consumption (mA)	Clock (MHz)	Sleep	MAC	MAC Features	Protocols	Encryption	Interface	Packages (Dimensions)
AT86RF215	48	–	.3895	-2.483		-123	+14.5	Yes	62	28	26	.03 mA	Yes	–	zigbee®, MiWi™ wireless networking protocol	–	I/Q	48 QFN
AT86RF233	32	–	2.4			-101	4	Yes	13.8	11.8	16	.02 mA	Yes	CSMA-CA	zigbee, MiWi wireless networking protocol	AES128	SPI	32 QFN
AT86RF212B	32	–	.769	–.930		-110	11	Yes	18	9.2	16	.2 mA	Yes	CSMA-CA	zigbee, MiWi wireless networking protocol	AES128	SPI	32 QFN
MR.F24J40	40	–	2.405	–2.48		-95	0	Yes	23	19	20	2 μA	Yes	CSMA-CA	zigbee, MiWi wireless networking protocol	AES128	4-wire SPI	40/QFN
MRF24J40MA	12	PCB	2.405	–2.48		-94	0	Yes	23	19	20	2 μA	Yes	CSMA-CA	zigbee, MiWi wireless networking protocol	AES128	4-wire SPI	12/Module (17.8 × 27.9 mm)
MRF24J40MD	12	PCB	2.405	–2.48		-104	+19	Yes	140	32	20	10 μA	Yes	CSMA-CA	zigbee, MiWi wireless networking protocol	AES128	4-wire SPI	12/Module (17.8 × 27.9 mm)
MRF24J40ME	12	U.FL	2.405	–2.48		-104	+19	Yes	140	32	20	10 μA	Yes	CSMA-CA	zigbee, MiWi wireless networking protocol	AES128	4-wire SPI	12/Module (17.8 × 27.9 mm)

1. Indicates off current for sleep column. 2. Supported in the provided stack.

Wireless Products: Bluetooth®

Product	Functionality	No Shield Option	Rx Sensitivity (dBm)	Power Output (dBm) (typ.)	Sleep	Profiles	Interface	Pin Count	Packages (Dimensions)
RN4020	Data, Single-Mode BLE	No	-92.5	7	Dormant < 700 nA, deep sleep < 5.0 μA	GAP, GATT, SM, L2CAP, integrated public profiles	UART, PIO, AIO, SPI	24	11.5 × 19.5 mm Module
ATBTLC1000-ZR	Data, Single-Mode BLE	No	-93	-20 to +3.5	1.17 μA	L2CAP, SM, ATT, GATT, GAP, Integrated public profiles	UART	24	12.7 × 20 × 2.1 mm Module
ATSAMB11-ZR	Data, Single-Mode BLE	No	-95	-20 to +3.5	2 μA	L2CAP, SM, ATT, GATT, GAP, Integrated public profiles	UART	39	15.4 × 22.9 × 2.1 mm Module
BM70	Data, Single-Mode BLE	Yes	-90	0	Power Saving 1 μA	GAP, GATT, SM, L2CAP, Integrated public profiles	UART, I²C, SPI, ADC, PWM, GPIOs	33	22 × 12 × 2.4 mm 15 × 12 × 1.8 mm Module
BM71	Data, Single-Mode BLE	Yes	-90	0	Power Saving 1 μA	GAP, GATT, SM, L2CAP, Integrated public profiles	UART, I²C, SPI, ADC, PWM, GPIOs	17	9 × 11.5 × 2.1 mm 6 × 8 × 1.6 mm Module
BM78	Data, Dual-Mode	Yes	-90 (BR/EDR) -92 LE	2	Deep Power Down 130 μA	GAP, SPP, SDP, RFCOMM, L2CAP GAP, GATT, ATT, SMP, L2CAP	UART, I²C, GPIOs	33	22 × 12 × 2.4 mm 15 × 12 × 1.8 mm Module
RN4678	Data, Dual-Mode	Yes	-90 (BR/EDR) -92 LE	2	Deep Power Down 130 μA	GAP, SPP, SDP, RFCOMM, L2CAP GAP, GATT, ATT, SMP, L2CAP	UART, I²C, GPIOs	33	22 × 12 × 2.4 mm 15 × 12 × 1.8 mm Module
BM20	Audio	Yes	-91	4	System Off 2 μA	HFP, HSP, A2DP, AVRCP, SPP, PCAP	Analog audio out, mic in, line in, UART	40	29 × 15 × 2.5 mm Module
BM23	Audio	Yes	-91	4	System Off 2 μA	HFP, HSP, A2DP, AVRCP, SPP, PCAP	I²S Digital audio out, mic in, line in, UART	43	29 × 15 × 2.5 mm Module
BM62	Audio	Yes	-90	+2 (Class 2)	System < 10 μA	HFP, AVRCP, A2DP, HSP, SPP	UART	37	29 × 15 × 2.5 mm Module
BM83	Audio (BBC, AAC, LDAC)	No	-90	8.5 dBm (Class 1)	System < 10 μA	HFP, HSP, A2DP, AVRCP, SPP, PCAP, MAP, DIS, ANO5	Line in, mic in, ADC, IS, I²C, UART, USB, GPIOs	50	32 × 15 mm Module
BM64	Audio	Yes	-90	+15 (Class 1), +2 (Class 2)	System < 10 μA	HFP, AVRCP, A2DP, HSP, SPP	UART	43	32 × 15 × 2.5 mm Module

Wireless Products: Bluetooth ICs

IS2062	Audio	Yes	-90	+2 (Class 2)	System < 20 μA	HFP, AVRCP, A2DP, HSP, SPP	UART	56	LGA (7 × 7 mm) Module
IS2063	Audio		-90	+2 (Class 2)	System < 20 μA	HFP, AVRCP, A2DP, HSP, SPP	UART	82	BGA (5 × 5 mm) Module
IS2064	Audio	Yes	-90	+15 (Class 1), +2 (Class 2)	System < 20 μA	HFP, AVRCP, A2DP, HSP, SPP	UART	68, 61	68 LGA (8 × 8 × 1.0), 68 QFN (8 × 8 × 0.9), 61 BGA (5 × 5 × 0.9) Module
IS2066	Audio (SBC, AAC)		-90	+2 (Class 2)	–	HFP, AVRCP, A2DP, HSP, SPP	mic in, analog out, DAC	50	BGA (5 × 3.5 mm) Module
IS2021S	Audio	No	-90	4	Showdown 1 μA	Audio: HFP, HSP, A2DP, AVRCP, SPP, PBAP	UART	48, 56, 68	5 × 6.5 mm 48 QFN package (IS2021S) 7 × 7 mm 56 QFN package (IS2020S, IS2023S) 8 × 8 mm 68 QFN package (IS2025S) Module

Wireless Products: Sub-GHz Transceivers/Modules														
Product	Pin Count	Frequency Range (MHz)	Sensitivity (dBm)	Power Output (dBm)	RSSI	TX Power Consumption (mA)	RX Power Consumption (mA)	Clock	Sleep	Interface	Packages			
MRF89XAM8A	12	868	-113	12.5	Yes	25 mA @ +10 dBm	3	12.8 MHz	0.1 µA	4-wire SPI	12/Module (17.8 x 27.9 mm)			
MRF89XAM9A	12	915	-113	12.5	Yes	25 mA @ +10 dBm	3	12.8 MHz	0.1 µA	4-wire SPI	12/Module (17.8 x 27.9 mm)			
MRF89XA	32	868/915/950	-113	12.5	Yes	25 mA @ +10 dBm	3	12.8 MHz	0.1 µA	4-wire SPI	32-pin TQFN			
ATSAMR30	32/48	779/930	up to -110	11	Yes	18.2 mA @ 5 dBm	9.4	48 MHz	0.45	SPI, USART, I²C, LIN	(5 x 5 mm) 32-pin QFN, (7 x 7 mm) 48-pin QFN			
ATSAMR30M	32/48	779/930	up to -105	8.7	Yes	18.7 mA @ 5 dBm	9.4	48 MHz	0.45	SPI, USART, I²C, LIN	(11 x 127 mm) Module			
Wireless Products: Sub-GHz Transmitters														
Product	Pin Count	Frequency Range (MHz)		Modulation		Data Rate (Kbps)			Tx Power (dBm)		Operating Voltage (V)	Packages		
MICRF114	6	285–445		OOK		115.2 (NRZ), 57.6 (Manchester Encoded)			10		1.8–3.6	6-pin SOT-23		
MICRF113	6	300–450		ASK		20			10		1.8–3.6	6-pin SOT-23		
MICRF112	10	300–450		ASK/FSK		50 (ASK), 10 (FSK)			10		1.8–3.6	10-pin MSOP, 10-pin DFN		
Wireless Products: Sub-GHz Receivers														
Product	Pin Count	Frequency Range (MHz)	Sensitivity (dBm)	Power Output (dBm)	RSSI	Modulation	RX Power Consumption (mA)	Sleep	Interface	Packages				
MICRF219A	16	300–450	-110	-	Yes	ASK/OOK	4.3	-	-	16-pin QSOP				
MICRF220	16	300–450	-110	-	Yes	ASK/OOK	4.3	-	-	16-pin QSOP				
MICRF221	16	850–950	-109	-	Yes	ASK/OOK	9	-	-	16-pin QSOP				
MICRF229	16	400–450	-112	-	Yes	ASK/OOK	6	-	-	16-pin QSOP				
MICRF230	16	400–450	-112	-	Yes	ASK/OOK	6	-	-	16-pin QSOP				
Wireless Products: LoRa® Technology Modems														
Product	Pin Count	Frequency Range (MHz)	Sensitivity (dBm)	Power Output (dBm)	RSSI	TX Power Consumption (mA)		RX Power Consumption (mA)	Sleep	Interface	Packages			
RN2483	47	433/868	-148	14	N/A	40 mA @ +14 dBm (868 MHz)		14.2	1 µA	UART	47/Module (17.8 x 26.7 x 3 mm)			
RN2903	47	915	-146	18.5	N/A	124 mA @ +18.5 dBm		13.5	2 µA	UART	47/Module (17.8 x 26.7 x 3 mm)			
ATSAMR34	64	137–1020	-136	20	N/A	95 mA @ +17 dBm		20	1.5 µA	USB, UART, SPI, I²C	64-pin QFN			
Wireless Products: rfPIC Transmitters + PIC® MCUs														
Product	I/O Pins	Frequency Range (MHz)	Program Memory (Bytes)	EEPROM (bytes)	RAM (bytes)	Digital Timer	Watchdog Timer	Max. Speed (MHz)	ICSP™ Programming Capability	Modulation	Data Rate (kbps)	Output Power (dBm)	Operating Voltage	Packages
PIC12F529T39A	6	310–928	2.3K	64	201	1	1	8	Yes	OOK/FSK	100	10	2.0–3.7	14-pin TSSOP
PIC12LF1840T39A	6	310–928	7.1K	256	256	2	1	32	Yes	OOK/FSK	100	10	1.8–3.6	14-pin TSSOP
PIC16LF1824T39A	20	310–928	4K	256	256	1	1	32	Yes	OOK/FSK	100	10	1.8–3.6	20-pin TSSOP
rfPIC12F675F	6	380–450	1.7K	128	64	1	1	20	Yes	ASK/FSK	40	10	2.0–5.5	20-pin SSOP
rfPIC12F675H	6	850–930	1.7K	128	64	1	1	20	Yes	ASK/FSK	40	10	2.0–5.5	20-pin SSOP
rfPIC12F675K	6	290–350	1.7K	128	64	1	1	20	Yes	ASK/FSK	40	10	2.0–5.5	20-pin SSOP
Timberwolf™ Audio Processors														
Product	Pincount		Host Interface		Peripherals		Audio Interface			IP Camera	Auto Speech Recognition (ASR)		Auto (aftermarket)	USB Audio
ZL38050	56/64		SPI, I²C		GPIOs, UART, SPI		Digital Mic (1), Stereo DAC, I²S/TDM (2)			✓				
ZL38051	56/64		SPI, I²C		GPIOs, UART, SPI		Digital Mic (2), Stereo DAC, I²S/TDM (2)			✓				
ZL38052	56/64		SPI, I²C		GPIOs, UART, SPI		Digital Mic (2), Stereo DAC, I²S/TDM (2)			✓				
ZL38AMB	56/64		SPI, I²C		GPIOs, UART, SPI		Digital Mic (2), Stereo DAC, I²S/TDM (2)			✓				
ZL38063	64		SPI, I²C		GPIOs, UART, SPI		Digital Mic (3), Stereo DAC, I²S/TDM (2)			✓				
ZL38067	56/64		SPI, I²C		GPIOs, UART, SPI		Digital Mic (1), Stereo DAC, I²S/TDM (2)			✓				
ZL38080	64		SPI, I²C		GPIOs, UART, SPI		Digital Mic (1), Stereo DAC, I²S/TDM (2)			✓				
ZL38090	56/64		SPI, I²C		GPIOs, UART, SPI		Digital Mic (1), Stereo DAC, I²S/TDM (2)			✓				

USB Products							
Product	Description	Processor Interface	# of Downstream Ports	Card Formats	Industrial Version	Packages	
USB 2.0 Hubs/Controllers							
USB2412	Hi-Speed USB 2.0 2-Port Hub	USB 2.0	2	–	–	28-pin QFN	
USB2422	Small-footprint, 2-Port Value Hub, Commercial and Industrial Temperature with USB Battery Charging 1.1	USB 2.0	2	–	✓	24-pin QFN	
USB251XB/ USB2517	Hi-Speed USB 2.0 Hub with Battery Charger Detection	USB 2.0	2, 3, 4, 7 port options	–	✓	36- or 64-pin QFN	
USB2524	4-Port Hi-Speed USB 2.0 Multi-Switch Hub	USB 2.0 × 2	4	–	–	56-pin QFN	
USB3503	3-Port Hi-Speed USB 2.0 HSIC Hub for Mobile Applications	HSIC	3	–	✓	25-ball WLCSP	
USB3803	3-Port Hi-Speed USB 2.0 Hub for Mobile Applications	USB 2.0	3	–	✓	25-ball WLCSP	
USB3X13	3-Port Hi-Speed USB 2.0 Smart Hub for Mobile Applications	USB 2.0 or HSIC	3 (USB 2.0 ×2/HSIC ×1)	–	✓	30-ball WLCSP	
USB253X	USB2.0 Hi-Speed Smart Hub with Battery Charging Detection	USB 2.0	2, 3, 4 port options	–	✓	36-pin QFN	
USB46X4	Hi-Speed USB 2.0 Controller Hub with USB and HSIC Interfaces	USB 2.0 or HSIC	4 (USB 2.0 ×4 or USB 2.0 ×2/HSIC ×2)	–	✓ Automotive	48-pin QFN	
USB8460X	Automotive Smart Hub, Host/Device Switching, USB/HSIC interfaces	USB 2.0	2 or 4 ports	–	Automotive only	48-pin QFN	
USB491X	Automotive Smart Hub, Multi-Host Endpoint Reflector	USB 2.0	3 or 5 ports	–	Automotive only	48- or 64-pin QFN	
USB4715	Smart Hub, FlexConnect on all ports	USB 2.0	4 ports	–	✓ Automotive	48-pin QFN	
USB492X	Automotive Smart Hub, Dual Upstream architecture	USB 2.0	3 or 5 ports	–	Automotive only	48- or 64-pin QFN	
USB 3.x Hubs/Controllers							
USB5537B	SuperSpeed Hub with Battery Charger Detection	USB 3.0	2, 3, 4 or 7 port options	–	–	64- or 72-pin QFN	
USB5734	SuperSpeed Smart Hub with I/O Bridging and FlexConnect	USB 3.1 Gen1	4	–	✓	64-pin QFN	
USB574X	SuperSpeed Smart Hub with FlexConnect	USB 3.1 Gen1	2 or 4 port options	–	✓	56-pin QFN	
USB58XX	SuperSpeed Smart Hub with I/O Bridging and FlexConnect with USB-C™ support downstream	USB 3.1 Gen1	6 or 7 port options	–	✓	100-pin QFN	
USB59X	SuperSpeed Smart Hub with I/O Bridging and FlexConnect with USB-C support upstream and downstream	USB 3.1 Gen1	6	–	✓	100-pin QFN	
USB553XB	SuperSpeed USB 3.0 Hub with Battery Charger Detection	USB 3.0	2, 3, 4 or 7 port options	–	✓	64- or 72-pin QFN	
USB5734	SuperSpeed USB 3.1 Gen1 Smart Hub Controller with I/O Bridging and FlexConnect	USB 3.1 Gen1	4	–	✓ Automotive	64-pin QFN	
USB5744	SuperSpeed USB 3.1 Gen1 Small Form Factor Hub Controller	USB 3.1 Gen1	4	–	✓	56-pin QFN	
USB Products							
Product	Description	Processor Interface	# of Downstream Ports	Card Formats	Industrial Version	Packages	
USB-C™ Power and Charging							
UTC200X	USB-C Controller	I/O	1 DFP or 1 UFP	–	✓ Automotive	16-pin QFN	
USB Transceivers/Switches							
USB333X	Mobile Hi-Speed USB 2.0 Transceiver with Multi-frequency Support	ULPI	–	–	✓	25-ball WLCSP	
USB334X	Hi-Speed USB 2.0 Transceiver with Multi-frequency Support	ULPI	–	–	Automotive	24- or 32-pin QFN	
USB3300	Hi-Speed USB 2.0 Transceiver (24 MHz reference clock support)	ULPI	–	–	✓	32-pin QFN	
USB3740B	Hi-Speed USB 2.0 Switch with Extremely Low Power	USB 2.0	–	–	✓	10-pin QFN	
USB375XA-X	Hi-Speed USB 2.0 Port Protection with Switch and Charger Detection	USB 2.0	–	–	✓	16-pin QFN	
USB Flash Media Controllers							
USB224X	Hi-Speed USB 2.0 Multi-Format Flash Media Controller	USB 2.0	–	SD™/MMC/eMMC™/MS/xD	✓	36-pin QFN	
USB225X	Hi-Speed USB 2.0 Multi-Format Flash Media Controller	USB 2.0	–	SD/MMC/eMMC/MS/xD/CF	✓	128-pin VTQFP	
USB264X	Hi-Speed USB 2.0 Multi-Format Flash Media Hub Controller	USB 2.0	2	SD/MMC/eMMC/MS/xD	✓ Automotive	48-pin QFN	
USB2660	Hi-Speed USB 2.0 Multi-Format Flash Media Hub Controller	USB 2.0	2	SD/MMC/eMMC/MS/xD (×2)	✓	64-pin QFN	
USB4640	USB 2.0 Hi-Speed Smart Hub with HSIC interface Option	HSIC	2	SD/MMC/eMMC/MS/xD	✓	48-pin QFN	

USB Products							
USB-C™/Power Delivery Controllers							
Product	Description	PD Version	Interface	Port Power Controller	Industrial Version	# of Pins	Packages
UPD360	PD 2.0 Compliant USB-C PD Controller with Integrated PPC	PD 2.0	I²C, SPI	Yes	No	44	BGA
UPD350	PD 3.0 Compliant USB-C PD Controller	PD 3.0	I²C, SPI	No	Yes + Auto	28, 40	QFN
UTC2000	USB-C Controller	Type-C	None	No	Yes + Auto	16	QFN
USB Security							
Product	Description	Processor Interface	# of Downstream Ports	Card Formats	Industrial Version	Package	
SEC1110	Smart Card Controller	USB 2.0	–	Smart Card	✓	16-pin QFN	
SEC1210	Smart Card Controller with Multi-Interface Support	USB, UART	–	Smart Card x2	✓	24-pin QFN	
Ethernet Products							
Product	Description	Interface (Upstream)	Wake-on-LAN	EEE	Industrial Version	Packages	
Ethernet Controllers							
ENC28J60	10Base-T Ethernet Controller	SPI	–	–	✓	28-pin SPDIP, SSOP, SOIC, QFN	
ENC624J600	10Base-T/100Base-TX Ethernet Controller with Security	SPI/Parallel	–	–	✓	24-pin TQFN, QFN, 64-pin TQFN	
LAN9217	10Base-T/100Base-TX Ethernet Controller with 16-bit/MII interface	16-bit Host Bus/MII	–	–	–	100-pin TQFP	
LAN9218	10Base-T/100Base-TX Ethernet Controller with 32-bit interface	32-bit Host Bus	–	–	✓	100-pin TQFP	
LAN9221	10Base-T/100Base-TX Ethernet Controller with 16-bit interface	16-bit Host Bus	–	–	✓	56-pin QFN	
LAN9250	10Base-T/100Base-TX Ethernet Controller	SPI, SQI™, HBI	✓	✓	–	64-pin QFN, 64-pin TQFP-EP	
LAN9420	10Base-T/100Base-TX Ethernet Controller with 32-bit PCI interface	32-bit PCI 3.0	–	–	✓	128-pin VTQFP	
LAN89218	TrueAuto, 10Base-T/100Base-TX Ethernet Controller with 32-bit interface	32-bit Host Bus	–	–	Automotive	100-pin TQFP	
KSZ8851	10/100Base-TX Ethernet Controller	8-/16-/32-bit or SPI	✓	–	Automotive	32-pin QFN, 48-pin LQFP, 128-pin PQFP	
KSZ8852	2-Port 10/100Base-TX Ethernet Controller	8-/16-/32-bit	✓	✓	✓	64-pin LQFP	
KSZ8441	10/100Base-TX/FX Ethernet Controller with 1588v2 PTP and Clock Synchronization	8-/16-/32-bit or PCI	✓	✓	✓	64-pin LQFP	
Ethernet Products							
Product	Description	Interface (Upstream)	Wake-on-LAN	EEE	Industrial Version	Packages	
Ethernet Bridges							
LAN9500A	USB 2.0 to 10/100 Ethernet Bridge	USB 2.0	✓	–	✓	56-pin QFN	
LAN9730	USB HSIC 2.0 to 10/100 Ethernet Bridge	USB 2.0 (HSIC), MII	–	–	✓	56-pin QFN	
LAN7500	USB 2.0 to 10/100/1000 Ethernet Bridge	USB 2.0	✓	–	✓	56-pin QFN	
LAN7800/01/50	USB 3.1 Gen1 to 10/100/1000 Ethernet Bridge (Optional RGMII Output)	USB 3.1/2.0/HSIC	✓	✓	Automotive	48-pin SQFN/56-SQFN/64-SQFN	
LAN9512	USB 2.0 to 10/100 Ethernet Bridge with 2-Port USB 2.0 Hub	USB 2.0	–	–	✓	64-pin QFN	
LAN9513	USB 2.0 to 10/100 Ethernet Bridge with 3-Port USB 2.0 Hub	USB 2.0	–	–	✓	64-pin QFN	
LAN9514	USB 2.0 to 10/100 Ethernet Bridge with 4-Port USB 2.0 Hub	USB 2.0	–	–	✓	64-pin QFN	
LAN89730	USB 2.0 to 10/100 Ethernet Bridge	USB 2.0	✓	–	Automotive	56-pin QFN	
LAN89530	USB 2.0 to 10/100 Ethernet Bridge	USB 2.0	✓	–	Automotive	56-pin QFN	
LAN7430	PCIe 3.1 to 10/100/1000 Ethernet Bridge	PCIe 3.1 at 2.5GT/s	✓	✓	✓	48-pin SQFN	
LAN7431	PCIe 3.1 to RGMII Bridge	PCIe 3.1 at 2.5GT/s	✓	✓	Automotive	72-pin SQFN	
Ethernet Transceivers (PHY)							
LAN8720A	Small-Footprint, Low Power Consumption, Full-Featured 10/100 Ethernet Transceivers	RMII	–	–	✓	24-pin QFN	
LAN8740A	Small-Footprint, 10/100 PHY Family Featuring Energy Efficient Ethernet and Wake-on-LAN	MII/RMII	✓	✓	✓	32-pin QFN	
KSZ8051	Small-Footprint, 10/100 PHY Family Featuring Wake-on-LAN	MII/RMII	–	–	✓	32-pin QFN	
KSZ8061	Small-Footprint, 10/100 PHY Family Ultra-Deep Sleep Standby and Quiet-WIRE® Technology	MII/RMII	–	–	✓	32-/48-pin QFN	

Ethernet Products							
Product	Description	Interface (Upstream)	Wake-on-LAN	EEE	Industrial Version	Packages	
Ethernet Bridges							
KSZ8081	Small-Footprint, 10/100 PHY Family Featuring Wake-on-LAN and Low-Power Voltage Drive	MII/RMII	–	–	✓	24-/32-pin QFN, 48-pin LQFP	
KSZ8091	Small-Footprint, 10/100 PHY Family Featuring Energy Efficient Ethernet, Wake-on-LAN and Low-Power Voltage Drive	MII/RMII	✓	✓	✓	24-/32-pin QFN, 48-pin LQFP	
KSZ9031	MII/GMII/RGMII 10/100/1000 Ethernet Transceiver Family Featuring Energy Efficient Ethernet and Wake-on-LAN	MII/RMII/RGMII	✓	✓	✓	Automotive	48-/64-pin QFN
LAN88730	Small-Footprint, Full-Featured 10/100 Ethernet Transceivers	MII/RMII	–	–	Automotive		32-pin QFN
Ethernet Products							
Product	Description	Interface (Upstream)	IEEE 1588v2	Cable Diagnostics	100 FX (Fiber Support)	Packages	
EtherCAT® Controllers							
LAN9252	2/3-Port 100 EtherCAT Slave Controller	SPI/SQI™/8/16/32 Host Bus	Clock Synchronization	✓	✓	64-pin QFN, 64-pin TQFP-EP	
Ethernet Switches							
LAN9352	2-Port 10/100Base-TX	SPI/SQI/HBI	✓	✓	–	72-pin QFN, 80-pin TQFP-EP	
LAN9303	3-Port 10/100 Managed Ethernet Switch	MII/RMII/Turbo MII	–	–	–	56-pin QFN	
LAN9303M	3-Port 10/100 Managed Ethernet Switch with Dual MII/KMII/Turbo MII	2x MII/RMII/Turbo MII	–	–	–	72-pin QFN	
LAN9353	3-Port 10/100 Managed Ethernet Switch with Single MII/RMII/Turbo MII or Dual RMII	MII/RMII/Turbo MII	✓	✓	✓	64-pin QFN, 64-pin TQFP-EP	
LAN9354	3-Port 10/100 Managed Ethernet Switch with Single RMII	RMII	✓	✓	✓	56-pin QFN	
LAN9355	3-Port 10/100 Managed Ethernet Switch with Dual MII/RMII/Turbo MII	MII/RMII/Turbo MII	✓	✓	✓	88-pin QFN, 80-pin TQFP-EP	
KSZ8863	3-Port 10/100Base-TX/FX Switch with MII/RMII Interface	MII/RMII	–	✓	✓	48-pin LQFP	
KSZ8873	3-Port 10/100Base-TX/FX Switch with MII/RMII Interface (Automotive Qualified)	MII/RMII	–	✓	✓	64-pin VQFN	
KSZ8463	3-Port 10/100Base-TX/1588v2 Switch with MII/RMII Interface	MII/RMII	✓	✓	✓	64-pin LQFP	
KSZ8864	4-Port Switch with 2x 10/100Base-TX + 2x MII/RMII Interface (Automotive Qualified)	MII/RMII	–	✓	–	64-pin VQFN	
KSZ8794	4-Port Switch with 3x 10/100Base-TX + 1x RGMII/MII/RMII Interface	MII/GMII/RGMII	–	✓	–	64-pin VQFN	
KSZ8795	5-Port Switch with 4x 10/100Base-TX + 1x GMII/RGMII/MII/RMII Interface	GMII/RGMII/MII/RMII	–	✓	–	80-pin LQFP	
KSZ8775	5-Port Switch with 3x 10/100Base-TX + 2x RGMII/MII/RMII Interface	MII/GMII/RGMII	–	✓	–	80-pin LQFP	
KSZ8765	5-Port Switch with 2x 10/100Base-TX + 2x 100Base-FX + 1x GMII/RGMII/MII/RMII Interface	MII/GMII/RGMII	–	✓	✓	64-pin QFN, 80-pin LQFP	
KSZ8895	5-Port 10/100Base-TX/FX Switch with MII/RMII Interface (Automotive Qualified)	MII/RMII	–	✓	–	128-pin PQFP	
KSZ8567	7-Port 10/100 Switch with IEEE 1588, Traffic Scheduling and Shaping	SGMII/RGMII/MII/RMII	✓	✓	SSMII	128-pin TQFP	
KSZ9897	6/7-Port Gigabit Switch	SGMII/RGMII/MII/RMII	–	✓	–	128-pin TQFP	
KSZ9567	7-Port Gigabit Switch with IEEE 1588, Traffic Scheduling and Shaping	SGMII/RGMII/MII/RMII	✓	✓	SGMII	128-pin TQFP	
KSZ9477	7-Port Gigabit Switch with DLR, HSR, IEEE 1588, Traffic Scheduling and Shaping	SGMII/RGMII/MII/RMII	✓	✓	✓	128-pin TQFP	
KSZ9563	3-Port Gigabit Switch with IEEE 1588, Traffic Scheduling and Shaping	RGMII	✓	✓	–	64-pin VQFN	
KSZ9893	3-Port Gigabit Switch	RGMII	–	✓	–	64-pin VQFN	
KSZ8563	3-Port 10/100 Switch with IEEE 1588, Traffic Scheduling and Shaping	RGMII	✓	✓	–	64-pin VQFN	

Automotive: Media Oriented Systems Transport (MOST®) Network Interface Controllers
Intelligent Network Interface Controller (INIC) for MOST Networks

Product	Features	Interface	Ambient Temperature Range	Pin	Package
OS81110 INIC	Fully-encapsulated, single-chip, single MOST150 network port, embedded network management, supports MOST embedded Ethernet channel and isochronous channels (MOST150)	MOST150 FOT or external MOST150 coax transceiver, I ^C , I ^S /SPDIF, TSI, SPI, RMCK, JTAG, MediaLB® 3-Pin, MediaLB bus 6-Pin	-40°C to 105°C	48	QFN
OS81082 INIC	Fully-encapsulated, single-chip, embedded network management (MOST50)	MOST50 electrical (UTP), I ^C , I ^S ®, MediaLB	-40°C to 95°C	64	ETQFP
OS81092 INIC	ROM version of OS81082 INIC (MOST50)	MOST50 electrical (UTP), I ^C , I ^S , MediaLB	-40°C to 105°C	48	QFN
OS81050 INIC	Fully-encapsulated, single-chip with embedded network management (MOST25)	MOST25 FOT, I ^C , I ^S , MediaLB	Standard range: -40 to 85 Extended range: -40 to 105	44	QFP, ETQFP
OS81060 INIC	ROM version of OS81050 INIC (MOST25)	MOST25 FOT, I ^C , I ^S , MediaLB	-40°C to 105°C (targeted)	40	QFN
OS81118AF INIC	Fully-encapsulated, single-chip, single MOST150 network port, embedded network management, integrated MOST150 coaxial transceiver, supports MOST embedded Ethernet channel, isochronous channels (MOST150), and USB 2.0 high-speed port	MOST150 FOT or MOST150 coaxial physical layer, USB 2.0 high-speed, GPIO, I ^C , I ^S , SPI, RMCK, JTAG, MediaLB 3-Pin, MediaLB bus 6-Pin	-40°C to +85°C	72	QFN
OS81118BF INIC	Fully-encapsulated, single-chip, single MOST150 network port, embedded network management, supports MOST embedded Ethernet channel, isochronous channels (MOST150), and USB 2.0 high-speed port	MOST150 FOT or external MOST150 coaxial transceiver, USB 2.0 high-speed, GPIO, I ^C , I ^S , SPI, RMCK, JTAG, MediaLB 3-Pin, MediaLB bus 6-Pin	-40°C to +85°C	72	QFN
OS81119AF INIC	Fully-encapsulated, single-chip, double MOST150 network ports, embedded network management, integrated MOST150 coaxial transceiver, supports MOST embedded Ethernet channel, isochronous channels (MOST150), and USB 2.0 high-speed port	MOST150 FOT or MOST150 coaxial physical layer, USB 2.0 high-speed, GPIO, I ^C , I ^S , SPI, RMCK, JTAG, MediaLB 3-Pin, MediaLB Bus 6-Pin	-40°C to +85°C	88	QFN
OS82150 (MOST150 Coaxial Transceiver)	MOST150 Coaxial Transceiver, integrates coaxial cable driver and coaxial cable receiver in a single package	MOST150 coaxial physical layer, interface to MOST150 INIC	-40°C to +105°C	16	QFN

Automotive: Power Management Companion
For Diagnostics, Status Monitoring and Power Supply

Product	Features	Interface	Temperature Range (°C)	Pin	Packages
MPM8500	Power management companion for diagnostics, status monitoring and power supply	LIN 2.0, I ^C	-40 to 105	24	QFN

Automotive: Multimedia I/O Companion
Multimedia I/O Port Expander

Product	Features	Interface	Temperature Range	Pin	Packages
OS85650	Low-cost multimedia I/O port expander, DTCP co-processor	MediaLB® bus 3-pin and 6-pin, Host Bus Interface (HBI), 2 × multi-channel streaming ports, 2 × TSI, 2 × SPI, I ^C	-40°C to 105°C	128	ETQFP
OS85652	Low-cost multimedia I/O port expander	MediaLB bus 3-pin and 6-pin, Host Bus Interface (HBI), 2 × multi-channel streaming ports, 2 × TSI, 2 × SPI, I ^C	-40°C to 105°C	128	ETQFP
OS85656	Low-cost multimedia I/O port expander well-suited for streaming applications	MediaLB bus 3-pin, streaming port I ^S (FSYN, FCLK, 4 × In, 4 × Out, @ 512 Fs), serial transport stream interface (TSI), I ^C	-40°C to 105°C	48	QFN
OS85654	Low-cost multimedia I/O port expander well-suited for streaming applications, DTCP co-processor	MediaLB bus 3-pin, streaming port I ^S (FSYN, FCLK, 4 × In, 4 × Out, @ 512 Fs), serial transport stream interface (TSI), I ^C	-40°C to 105°C	48	QFN

Automotive: Ethernet Controllers
10/100 Ethernet Controllers with USB 2.0, HSIC or HBI

Product	Features	Interface	Temperature Range (°C)	Pin	Packages
LAN89218	High-performance, single-chip controller with HP Auto-MDIX support*	MAC/PHY, 10Base-T/100Base-TX, 32- and 16-bit Host Bus Interface (HBI)	-40 to 85	100	TQFP
LAN89530	Hi-Speed USB 2.0 to 10/100 Ethernet controller	USB 2.0	-40 to 85	56	QFN

*HP Auto-MDIX eliminates the need for special crossover cables when connecting LAN devices together.

Automotive: Ethernet Switch
10/100 Managed Ethernet Switch with HP Auto-MDIX Support

Product	Features	Interface	Temperature Range (°C)	Ports	Pin	Packages
LAN89303	High performance, small-footprint, full-featured, single MII/RMII/Turbo MII support	MII/RMII, 2 × 10/100 PHYs, 3 × 10/100 MACs	-40 to 85	4	56	QFN

Automotive: Ethernet Transceiver
10/100 Ethernet Transceiver with HP Auto-MDIX Support*, Featuring flexPWR® Technology

Product	Features	Interface	Temperature Range (°C)	Pin	Packages
LAN88730	Small footprint, low-power consumption, full featured	10Base-T/100Base-TX, MII/RMII	LAN88730AM: -40 to 85 LAN88730BM: -40 to 105	32	QFN

*HP Auto MDIX eliminates the need for special crossover cables when connecting LAN devices together.

Automotive: Hi-Speed USB 2.0 Hub USB 2.0 Hub Featuring MultiTRAK™ Technology									
Product	Features	Interface	Temperature Range (°C)	Ports	Pin	Packages			
USB82512	Versatile, cost effective, energy efficient, incorporating MultiTRAK, PortMap, PortSwap, PHYBoost technologies	SMBus/I²C	–40 to 85	2	36	QFN			
USB82513	Versatile, cost effective, energy efficient, incorporating MultiTRAK, PortMap, PortSwap, PHYBoost technologies	SMBus/I²C	–40 to 85	3	36	QFN			
USB82514	Versatile, cost effective, energy efficient, incorporating MultiTRAK, PortMap, PortSwap, PHYBoost technologies	SMBus/I²C	–40 to 85	4	36	QFN			
Automotive: Hi-Speed USB 2.0 Hub and Flash Media Card Controllers USB 2.0 Hub and Card Controller Combos									
Product	Features	Socket Type	Supports			Temperature Range (°C)	USB Ports	Pin	Packages
USB82640	USB Hub/Card Reader combo with PortMap, PortSwap and PHYBoost Technologies	Single	SD™/SD High Capacity™/MultiMediaCard™/Memory Stick®/MS PRO™, MS PRO-HG™			–40 to 85	2	48	QFN
USB82642	USB bridge/card reader combo with USB to SDIO and USB to I²C bridging functionality and PortMap, PortSwap and PHYBoost technologies	Single	SD/SD High Capacity/MultiMediaCard/Memory Stick/MS PRO, MS PRO-HG			–40 to 85	2	48	QFN
USX2730	USB Card Reader only	Single	SD/SD High Capacity/MultiMediaCard			–40 to 85	0	48	QFN
Automotive: Hi-Speed USB 2.0 Transceiver USB 2.0 Transceiver with 1.8V ULPI Interface									
Product	Features	Interface	Temperature Range (°C)	Ports	Pin	Packages			
USB83340	Multi-frequency reference clock	1.8V to 3.3V ULPI	–40 to 105	1	32	QFN			
Automotive: Hi-Speed USB 2.0 Battery Charger Standalone USB Battery Charger									
Product	Features	Temperature Range (°C)			Supports	Pin	Packages		
UCS81001	USB battery charger supporting BC1.2, China charging, Apple® and RIM® charging profiles as well as programmable charging profiles for unforeseen peripherals	–40 to 85			USB, I²C, SMBus	28	QFN		
UCS81002	USB battery charger supporting BC1.2, China charging, Apple and RIM charging profiles as well as programmable charging profiles for unforeseen peripherals	–40 to 85			USB, I²C, SMBus	28	QFN		

Automotive: Hi-Speed USB 2.0 Charger Controllers and Port Protection													
Product	Features					Temperature Range (°C)		Supports		Pin		Packages	
UCS81003	USB port charger controller supporting BC1.2, China charging, Apple® and RIM® charging profiles as well as programmable charging profiles for unforeseen peripherals and integrated current monitoring					−40 to 85		USB, I²C, SMBus		28		QFN	
UCS2113	Dual USB port power protection switch and current monitor					−40 to 105		I²C, SMBus		20		QFN	
Automotive: Wireless Audio Radio Frequency Digital Audio Transceiver													
Product	Features					Typical Sink Mode Power Consumption			PA Output Power	Audio		Qualification	
KLR83012	Wirelessly streams uncompressed lossless audio up to 25m over robust 2.4 GHz radio link, multi-point to multi-point connectivity, strong Wi-Fi® coexistence, data channel for audio playback control, very low power consumption					20 mW			1.5 dBm	16 bit, 44.1 Ks/s stereo		AEC Q100	
Automotive: Capacitive Touch Sensors													
Product	Features			Input Channels		LED Drivers		Proximity Included		Interface		Pin	
CAP81188	Reset, wake and alert, automatic recalibration, base capacitance compensation			8		8		✓		I²C/SPI/BC-Link		24	
Embedded Controllers and Super I/O: Embedded Controllers													
Product	Description			Core	Code Storage	Data RAM	EEPROM	Crypto Engine	GPIO	Host Interface	Operating Temperature (°C)	UART	MAF/SAF
MEC1418-I/SZ	High-performance 32-bit embedded microcontroller with 128 KB of SRAM and 32 KB of Boot ROM, eSPI, LPC, I²C			MIPS	192 KB SRAM (Code + Data)	PO SRAM	N/A	No	106	eSPI, LPC, I²C	−40 to +85	Full	MAF
MEC1428-SZ-C	High-performance 32-bit embedded microcontroller with 224 KB of SRAM and 32 KB of Boot ROM, eSPI, LPC, I²C			MIPS	192 KB SRAM (Code + Data)	PO SRAM	N/A	Yes	65	eSPI, LPC, I²C	0 to +70	Full	MAF/SAF
MEC1701H-C1-SZ	High-performance 32-bit embedded microcontroller with 224 KB of SRAM and 32 KB of Boot ROM and Secure Boot, eSPI, LPC, I²C			Arm Cortex-M4F	224 KB	32 KB	N/A	Yes	123	eSPI, LPC, I²C	0 to +70	2	MAF
MEC1703H-C1-SZ	High-performance 32-bit embedded microcontroller with 224 KB of SRAM and 32 KB of Boot ROM and Secure Boot, eSPI, LPC, I²C			Arm Cortex-M4F	224 KB	32 KB	2 KB	Yes	148	eSPI, LPC, I²C	0 to +70	2	MAF
MEC1704Q-C1-I/SZ	High-performance 32-bit embedded microcontroller with 316 KB of SRAM and 64 KB of Boot ROM and Secure Boot, eSPI, LPC, I²C			Arm Cortex-M4F	316 KB	64 KB	N/A	Yes	123	eSPI, LPC, I²C	−40 to +85	2	MAF
MEC1705Q-C1-I/SZ	High-performance 32-bit embedded microcontroller with 316 KB of SRAM and 64 KB of Boot ROM and Secure Boot eSPI, LPC, I²C			Arm Cortex-M4F	316 KB	64 KB	2 KB	Yes	148	eSPI, LPC, I²C	−40 to +85	2	MAF
Embedded Controllers and Super I/O: Super I/O													
	Description			Operating Temperature	GPIO	Security Key Register	PECI Support			SMBus Interface		Intruder Detection	Resume Reset
SCH3221	LPC IO with multiple serial ports, 8042 KBC, reset generation and HWM			−40°C to +85°C	33	No	No			No		No	No
SCH3222	LPC IO with multiple serial ports, 8042 KBC, reset generation and HWM			−40°C to +85°C	23	Yes	No			No		No	Yes
SCH3223	LPC IO with multiple serial ports, 8042 KBC, reset generation and HWM			−40°C to +85°C	19	Yes	No			No		No	Yes
SCH3224	LPC IO with multiple serial ports, 8042 KBC, reset generation and HWM			−40°C to +85°C	24	Yes	No			No		No	Yes
SCH3226	LPC IO with multiple serial ports, 8042 KBC, reset generation and HWM			−40°C to +85°C	40	Yes	No			No		No	Yes
SCH3227	LPC IO with multiple serial ports, 8042 KBC, reset generation and HWM			−40°C to +85°C	40	Yes	No			No		No	Yes

Security Products																			
Product	Core	Max Speed	Ram (KB)	Operating Temperature	Package	RNG	Monotonic Counter	Crypto Algorithms					OTP - User Programmable	Memory Protection Unit	Debug Interface	Floating Point Unit			
CEC1302	Arm® Cortex®-M4	48	128	0°C to +70°C	144-pin WFBGA	Yes	No	AES128, AES129, AES256, SHA-1, SHA-256, RSA-512 to RSA-2048					500-bits	No	5-pin	Yes			
CEC1702	Arm Cortex-M4	96	480	0°C to +70°C	84-pin WFBGA	Yes	Yes	AES128, AES129, AES256, SHA-1, SHA-256, SHA-384, SHA-512, RSA-1024 to RSA-4096, ECDSA, EC-KCDSA, Support for Curve 25519, Ed25519					2500-bits	Yes	5-pin and SWD	Yes			
Security Products																			
Product	Typical Sleep Current	Typical Application		Interface (Designator)	Tamper Detection Pin	Memory Density	Temp Range (°C)	Min Vcc Supply	Unique ID	RNG	Monotonic Counters	Crypto Algorithms		Key Size	Individual Slots	TLS Stack Support	Cloud Support		
ECC508A	30 nA Typ 2 µA Max	Authentication for IP connected node and accessory authentication		I²C (DA) Single wire (CZ)	1	4.5 Kb	-40 to +85	2.0V	72-bit serial number	FIPS	2	FIPS186-3 ECDSA, NIST P256, NIST SHA256 with HMAC option, ECDH		256-bit keys	16	CycloneSSL, WolfSSL, OpenSSL, WINC TLS	AWS, Azure	SOIC (MAH), UDFN (SSH), 3 contacts (RBH)	Yes
ECC108A	30 nA Typ 2 µA Max	Accessory authentication		I²C (DA) Single wire (CZ)	1	4.5 Kb	-40 to +85	2.0V	72-bit serial number	FIPS	2	FIPS186-3 ECDSA, NIST P256, NIST B283, NIST K283, NIST SHA256 with HMAC option		256-bits and 283-bits keys	16	N/A	N/A	SOIC (MAH), UDFN (SSH), 3 contacts (RBH)	Yes
SHA204A	30 nA Typ 2 µA Max	Disposable/accessory authentication		I²C (DA) Single wire (CZ)		4.5 Kb	-40 to +85	2.0V	72-bit serial number	FIPS	2	NIST SHA256 with HMAC Option		256-bit keys	16	N/A	N/A	SOIC (MAH), UDFN (SSH) 3 contacts, (RBH), SOT-23 (STU), TSSOP (XHD) XDFN (MXH)	Yes
AES132	100 µA @3.3V Vcc 250 µA @5.5V Vcc	Secure storage		SPI (Q) I²C (R)		16x 2 Kb	-40 to +85	2.0V	64-bit serial number	FIPS	16	AES-CCM for authentication, MAC Capability		Up to 16x 128-bit keys		N/A	N/A	SOIC (8S1), UDFN (8MA2)	No
Touch and 3D Gesture Control: Capacitive Touch Controllers																			
Product	Buttons	LED Drivers	Additional Features							Proximity	Interface	Safety certified Touch VDE/UL 60730 class B		Voltage (V)	Pins	Packages			
AT42QT1010	1	–	adjustable sensitivity, noise filtering							✓	GPIO			1.8–5.5	6/8	SOT-23, UDFN			
AT42QT1011	1	–	adjustable sensitivity, noise filtering							✓	GPIO			1.8–5.5	6/8	SOT-23, UDFN			
AT42QT1012	1	–	adjustable sensitivity, noise rejection filters, low-power mode							✓	GPIO			1.8–5.5	6/8	SOT-23, UDFN			
AT42QT1040	4	–	adjustable sensitivity, noise rejection filters, low-power mode, Adjacent key suppression (AKS)								GPIO			1.8–5.5	20	VQFN			
AT42QT1050	5	–	adjustable sensitivity, noise rejection filters, low-power mode, Adjacent key suppression (AKS)								I²C/GPIO			1.8–5.5	12/20	VQFN, WLCSP			
AT42QT1060	6	–	adjustable sensitivity, noise rejection filters, low-power mode, Adjacent key suppression (AKS)								I²C/GPIO			1.8–5.5	28	VQFN			
AT42QT1070	7	–	adjustable sensitivity, noise rejection filters, low-power mode, Adjacent key suppression (AKS)								I²C/GPIO			1.8–5.5	14/20	SOIC, VQFN			
AT42QT2100	10	–	slider/wheel, adjustable sensitivity, noise rejection filters, low-power mode, Adjacent key suppression (AKS)								SPI/GPIO			2.0–5.5	32	VQFN			
AT42QT1110	11	–	adjustable sensitivity, noise rejection filters, low-power mode, Adjacent key suppression (AKS)								SPI/GPIO			3.0–5.5	32	TQFP, VQFN			
AT42QT2120	12	–	slider/wheel, adjustable sensitivity, noise rejection filters, low-power mode, Adjacent key suppression (AKS)							✓	I²C			1.8–5.5	20	SOIC, TSSOP, VQFN			
AT42QT2160	16	–	slider/wheel, adjustable sensitivity, noise rejection filters, low-power mode, Adjacent key suppression (AKS)								I²C			1.8–5.5	28	VQFN			
AT42QT1244	24	–	IEC/EN/UL60730 Class B safety, FMEA, adjustable sensitivity, noise rejection filters, Adjacent key suppression (AKS)								I²C	✓		3.0–5.5	32	TQFP, VQFN			
AT42QT1245	24	–	IEC/EN/UL60730 Class B safety, FMEA, adjustable sensitivity, noise rejection filters, Adjacent key suppression (AKS)								SPI	✓		3.0–5.5	32	TQFP, VQFN			
AT42QT1481	48	–	IEC/EN/UL60730 Class B safety, FMEA, adjustable sensitivity, noise rejection filters								SPI/UART	✓		4.8–5.3	44	TQFP			
AT42QT2640	64	–	IEC/EN/UL60730 Class B safety, FMEA, adjustable sensitivity, noise rejection filters								SPI	✓		4.8–5.3	44	TQFP			
CAP1133	3	3	alert, automatic calibration, base capacitance compensation							✓	I²C			3.0–3.6	10	QFN			
CAP1106	6	–	alert, automatic calibration, base capacitance compensation							✓	I²C			3.0–3.6	10	QFN			
CAP1126	6	2	slider, reset, alert, automatic calibration, base capacitance compensation							✓	I²C/SPI			3.0–3.6	16	QFN			
CAP1166	6	6	slider, reset, alert, automatic calibration, base capacitance compensation							✓	I²C/SPI			3.0–3.6	20	QFN			
CAP1128	8	2	slider, reset, alert, automatic calibration, base capacitance compensation								I²C/SPI			3.0–3.6	20	QFN			
CAP1188	8	8	slider, reset, alert, automatic calibration, base capacitance compensation							✓	I²C/SPI			3.0–3.6	24	QFN			
CAP1114	14	11	slider, reset, alert, automatic calibration, base capacitance compensation							✓	I²C			3.0–3.6	32	QFN			
CAP1203	3	–	alert, automatic calibration, base capacitance compensation								I²C			3.3–5.0	8	QFN			
CAP1293	3	–	alert, automatic calibration, base capacitance compensation							✓	I²C					QFN			

Touch and 3D Gesture Control: Capacitive Touch Controllers											
Product	Buttons	LED Drivers	Additional Features			Proximity	Interface	Safety certified Touch VDE/UL 60730 class B	Voltage (V)	Pins	Packages
CAP1206	6	–	alert, automatic calibration, base capacitance compensation			–	I ² C	–	–	–	QFN
CAP1296	6	–	alert, automatic calibration, base capacitance compensation			✓	I ² C	–	–	–	QFN
CAP1208	8	–	alert, automatic calibration, base capacitance compensation			–	I ² C	–	–	–	QFN
CAP1298	8	–	alert, automatic calibration, base capacitance compensation			✓	I ² C	–	3.3–5.0	16	QFN
CAP1214	14	11	slider, reset, alert, automatic calibration, base capacitance compensation, audio output			✓	I ² C	–	3.0–3.6	32	QFN
MTCH102	2	–	optimized for button replacement, adjustable sensitivity, noise rejection filters, active guard, low-power mode			✓	GPIO	–	2.1–3.6	8	MSOP, UDFN
MTCH105	5	–	optimized for button replacement, adjustable sensitivity, noise rejection filters, active guard, low-power mode			✓	GPIO	–	2.1–3.6	14/16	TSSOP, QFN
MTCH108	8	–	optimized for button replacement, adjustable sensitivity, noise rejection filters, active guard, low-power mode			✓	GPIO	–	2.1–3.6	20	SSOP, UQFN

Touch and 3D Gesture Control: Projected Capacitive Multi-touch Touchpad and Touchscreen Controllers (Turnkey Solutions)												
Product	Channels	Surface Gestures	Additional Features			Automotive	Temp Range (°C)	Low Power	Interface	Voltage	Pin	Package
ATMXT144U	144	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			–	–40 to +85	Y	I ² C	1.8–3.3V	38	QFN
ATMXT225T	224	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			Y	–40 to +105	Y	I ² C, SPI	3.1–3.3V	100	TQFP
ATMXT336U	336	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			–	–40 to +85	Y	I ² C	1.8–3.3V	56	XQFN
ATMXT449T	448	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			Y	–40 to +105	Y	I ² C, SPI	3.1–3.3V	100	TQFP
ATMXT640U	640	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			–	–40 to +85	Y	I ² C	1.8–3.3V	88	UFBGA
ATMXT641T	640	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			Y	–40 to +105	Y	I ² C, SPI	3.1–3.3V	100	TQFP
ATMXT799T	798	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			Y	–40 to +105	Y	I ² C, SPI	3.1–3.3V	144	LQFP
MXT1066T2	1066	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			–	–40 to +85	Y	–	1.8–3.3V	114	UFBGA
MXT1189T	1188	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			Y	–40 to +105	Y	I ² C, SPI	3.1–3.3V	144	LQFP
MXT1664T3	1664	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			–	–40 to +85	Y	I ² C, USB	1.8–3.3V	136	UFBGA
MXT1665T	1664	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			Y	–40 to +105	Y	I ² C, SPI	3.1–3.3V	144	LQFP
MXT2952T2	2912	Single and dual finger	Self and mutual capacitance, glove and thick lens, moisture support			–	–40 to +85	Y	I ² C, USB	1.8–3.3V	162	UFBGA

Touch and 3D Gesture Control: 3D Gesture Controllers														
Product	Channels	Position Tracking	Additional Features			Automotive	Temperature Range		Low Power	Interface		Voltage	Pin	Package
MGC3030	5	–	Gesture port, auto wake/sleep, touch detection			–	–20°C to +85°C		Y	I ² C, EDI (gesture port)		3.3V	28	SSOP
MGC3130	5	Y	Gesture port, auto wake/sleep, touch detection			–	–20°C to +85°C		Y	I ² C, EDI (gesture port)		3.3V	28	QFN
MGC3140	5	Y	Gesture port, auto wake/sleep, touch detection			Y	–40°C to +125°C		Y	I ² C, EDI (gesture port)		3.3V	48	UQFN

Power Discretes: Silicon Carbide (SiC) MOSFETs						
Part Number	Voltage	RDS(on)		Package		
MSCxxxSMA070B	700V	15–90 mΩ		TO-247		
MSCxxxSMA070S	700V	15–90 mΩ		D3PAK		
MSCxxxSMA120B	1200V	25–280 mΩ		TO-247		
MSCxxxSMA120S	1200V	25–360 mΩ		D3PAK		
MSCxxxSMA120J	1200V	25–80 mΩ		SOT-227		
MSCxxxSMA170B	1700V	45–750 mΩ		TO-247		
MSCxxxSMA170S	1700V	45–750 mΩ		D3PAK		
Power Discretes: Silicon Carbide (SiC) Diodes						
Part Number	Voltage	RDS(on)		Package		
MSCxxxSDA070K	700V	10-30A		TO-220		
MSCxxxSDA070B	700V	10-50 A		TO-247		
MSCxxxSDA070S	700V	30-50A		D3PAK		
MSCxxxSDA120K	1200V	10-30A		TO-220		
MSCxxxSDA120B	1200V	10-50A		TO-247		
MSCxxxSDA120S	1200V	10-30A		D3PAK		
MSCxxxSDA170B	1700V	10-50 A		TO-247		
Power Discretes: Insulated Gate Bipolar Transistors (IGBTs)						
Standard Series	Voltage Range (V)	Technology	Easy to Parallel	Short Circuit Safe Operating Range (SOA)		Parameter
MOS 7™	1200	Punch-Through	-	-		Ultra-low gate charge
MOS 8™	600, 650, 900, 1200	Punch-Through, Non-Punch-Through	-	-		Highest efficiency
Field Stop Trench Gate	600, 1200	Field Stop	Yes	Yes		Lowest conduction loss
Power Discretes: Power MOS 8™ MOSFETs/FREDFETs						
MOSFET Part Number	FREDFET Part Number	BVDSS (V)	Rds(on)Max (Ω)	Id (A)	Id (A)	Package Style
APTxM120xx	APTxF120xx	1200	2.4–0.29	8–35	7-33	TO-247, D3PAK, T-MAX®, TO-264, ISOTOP
APTxM100xx	APTxF100xx	1000	2.0–0.18	8–45	7-42	TO-247, D3PAK, T-MAX, TO-264, ISOTOP
APTxM80xx	APTxF80xx	800	0.9–0.10	13–60	12-57	TO-247, D3PAK, T-MAX, TO-264, ISOTOP
APTxM60xx	APTxF80xx	600	0.37–0.055	36–84	19-84	TO-247, D3PAK, T-MAX, TO-264, ISOTOP
APTxM50xx	APTxF50xx	500	0.24–0.036	56–103	24-103	TO-247, D3PAK, T-MAX, TO-264, ISOTOP
Power Discretes: Low-Voltage Power MOS V® MOSFETs/FREDFETs						
MOSFET Part Number	FREDFET Part Number	BVDSS (V)	Rds(on)Max (Ω)	Id (A)	Id (A)	Package Style
APT30MxxxxRx	APT30MxxxxFRx	300	0.085–0.019	40–130	48–130	TO-247, D3PAK, ISOTOP
APT20MxxxxRx	APT20MxxxxFRx	200	0.045–0.011	56–175	56–175	TO-247, D3PAK, T-MAX®, TO-264, ISOTOP

Power Discretes: Ultra-Fast, MOS7® MOSFETs

MOSFET Part Number	BVDSS (V)	Rds(on)Max (Ω)	Id (A)	FREDFET Part Number	Package Style
APT120xxxxLLx	1200	4.700-0.570	3.5-22	APT120xxxFLLx	TO-247, D3PAK, T-MAX®
APT100xxxxLLx	1000	0.900-0.210	12-37	APT100xxxFLLx	TO-247, D3PAK, T-MAX, TO-264, ISOTOP
APT80xxxxLLx	800	0.200-0.140	33-52	APT80xxxFLLx	TO-247, D3PAK, T-MAX, TO-264, ISOTOP
APT50xxxxLLx	500	0.140-0.038	35-88	APT50xxxFLLx	TO-247, D3PAK, T-MAX, TO-264, ISOTOP

Power Discretes: Ultra-fast, MOS 7R MOSFET

MOSFET Part Number	BVDSS (V)	Rds(on)Max (Ω)	Id (A)	Package Style
APT36N90BC3G	900	0.12	36	TO-247
APTxN80xxC3G	800	0.450-0.145	11-34	TO-247, T-MAX®, TO-264
APTxN65xxCxx	650	0.070-0.035	47-94	TO-247, D3PAK, T-MAX, TO-264
APTxN60xxCxx	600	0.125-0.035	30-106	TO-247, D3PAK, T-MAX, TO-264, ISOTOP

Power Discretes: Linear MOSFETs

Part Number	BVDSS (V)	Rds(on)Max (Ω)	Id (A)	SOA (W)
APL602xxx	600	0.125	43-49	325
APL502xxx	500	0.90	52-58	325

Power Discretes: Silicon and Silicon Carbide Diodes

Series	Voltage Ratings	Features	Applications	Comment
D	200, 300, 400, 600, 1000, 1200	Medium Vf, Medium speed	Freewheeling diode, Output rectifier, DC-DC converter	Proprietary platinum process
DQ	600, 1000, 1200	High speed, Avalanche rated	PFC, Freewheeling diode, DC-DC converter	Stepped EPI improves softness Proprietary platinum process
Schottky	200	Low Vf, Avalanche rated	Output rectifier, Freewheeling diode, DC-DC converter	APL602xxx
SiC Schottky	700, 1200, 1700	Zero reverse recovery	PFC, Freewheeling diode, DC-DC converter	Low switching losses, high power density and high-temperature operation

Power Discretes: High-Voltage RF MOSFETs

Part Number	Pout(W)	Freq.(MHz)	Package Style	Class of Operation	Comments
ARFxXXXXXX	90-750	25-120	TO-247, M174, TO-264, T3A, T3, T3C, T1, T2	A-E	The ARF family of RF power MOSFETs is optimized for applications requiring frequencies as high as 150 MHz and operating voltages as high as 400V
VRFxXXXXXX	30-600	30-175	M113, M174, M177, M208, T2	-	The VRF family of RF MOSFETs includes improved replacements for industry-standard RF transistors. They provide improved ruggedness by increasing the Bvdss over 30 percent from the industry-standard 125V to 170V minimum
DRFxXXXXXX	400-2000	30	T2B, T4, T4A, T5	D-E	The DRF family of RF solutions integrate drivers, bypass capacitors and RF MOSFETs into a single package

Power Modules: Standard Configurations							
Electrical Topology	IGBT 600V to 1700V	MOSFET 75V to 1200V	DIODE 200V to 1700V	Mix Si–SiC 600V to 1200V	SiC DIODE 600V to 1200V	SiC MOSFET 600V to 1700V	Packages
Asymmetrical Bridge	50A to 300A	64A to 207A	–	–	–	–	SP1, SP3F, SP4, SP6
Boost buck	100A	70A	–	–	–	–	SP3F
Boost and Buck Chopper	30A to 600A	17A to 370A	–	15A to 107A	–	50A and 100A	SOT-227, SP1, SP3F, SP4, SP6, D3
Common Anode	–	–	400A	–	–	–	SP6
Common Cathode	–	–	400A	–	100A to 600A	–	D1P, SP6
Dual boost and Buck Chopper	50A to 90A	17A to 100A	–	40A	–	–	SP1, SP3F
Dual Common Source	50A to 600A	45A to 370A	–	–	–	–	SP4, SP6
Dual Diode	–	–	–	–	20A to 100A	–	SOT-227
Full Bridge	20A to 300A	6A to 207A	30A to 200A	–	20A to 200A	110A	SOT-227, SP1, SP2, SP3F, SP4, SP6
Full Bridge With PFC	38A	29A and 38A	–	38A	–	–	SP3F
Full Bridge With Fast Rectifier Diode Bridge	38A and 50A	29A and 38A	–	38A	–	–	SP3F
Full bridge With Series and Parallel Diodes	–	13A to 62A	–	11A to 38A	–	–	SP4
Interleaved PFC	–	38A and 70A	–	–	–	–	SP1, SP3F
Linear Single and Dual Switch	–	14A and 33A	–	–	–	–	SP1, SP3F
Phase Leg	30A to 600A	25A to 370A	400A	–	100A to 600A	40A to 586A	SP1, SP2, SP3F, SP4, SP6, SP6LI, D1P, D3
Phase Leg With Gate Driver	300A to 400A	–	–	–	–	–	LP8
Phase Leg With PFC	–	27A and 38A	–	–	–	–	SP3F
Phase Leg With Series and Parallel Diodes	–	26A to 225A	–	21A to 110A	–	–	SP4, SP6
Single switch	400A to 750A	97A to 640A	400A to 500A	–	–	–	SP6, D4, LP4
Single Switch With Series and Parallel Diodes	–	86A to 310A	–	86A and 110A	–	–	SP6
Single Switch With Series Diodes	475A	110A to 160A	–	–	–	–	SP6
3-Level NPC Inverter	20A to 300A	30A to 75A	–	–	–	20A to 160A	SP1, SP3F, SP6
3-Level T-Type Inverter	40A to 200A	–	–	–	–	20A and 50A	SP3F, SP6
3-Phase Bridge	30A to 75A	–	–	40A and 90A	50A	–	SP1, SP3F
Triple Dual Common Source	50A to 150A	21A and 54A	–	–	–	–	SP6-P
Triple Phase Leg	30A to 150A	17A to 100A	–	50A and 87A	–	55A to 150A	SP3F, SP6-P

Hi Rel Discrete Solutions (HRDS) Product Portfolio

Product Family	Type	Polarity	Rated Voltage	Rated Current	Rated Power	Max Tj (°C)	Package	Qual Level	CHIP Availability	RAD HARD Availability
Bipolar Transistor	Power Transistor	NPN/PNP	40V to 760V	0.2A to 50A	0.75W to 300W	150 to 200	Metal/Ceramic - TO's and LCC's	MIL-PRF-19500 up to JANS	on Select	on Select
	Darlington Transistor	NPN/PNP	40V to 450V	5A to 20A	1W to 175W	175 to 200	Metal - TO's	MIL-PRF-19500 up to JANTXV	on Select	on Select
	Small Signal Transistor	NPN/PNP, Singles, Duals and Quads	10V to 450V	0.01A to 3A	0.15W to 5W	175 to 200	Metal/Ceramic - TO's, LCC's FP and DIP's	MIL-PRF-19500 up to JANS	on Select	on Select
	Small Signal RF Transistor	NPN/PNP	12V to 30V	0.03 to 0.04A	0.2W to 1W	200	Metal/Ceramic - TO's and LCC's	MIL-PRF-19500 up to JANS	on Select	on Select
Field Effect Transistor	JFET	P, N and Matched	30V to 50V	0.0015A to 0.175A	0.3W to 0.5W	175 to 200	Metal/Ceramic - TO's and LCC's	To be Qualified	on Select	on Select
	MOSFET's	N Channel	100V to 250V	12.4A to 56A	75W to 250W	150	Metal/Ceramic - TO's and LCC's	To be Qualified	on Select	Yes
Diode	Small Signal Diodes	PN, Singles and Duals	50V to 225V	0.075A to 0.3A		175 to 200	Glass - DO's and Metal/Ceramic - LCC's	MIL-PRF-19500 up to JANS	on Select	Not Applicable
	Rectifier	PN, Singles,Duals, Stacked, Bridge	50V to 1600V	0.12A to 300A		150 to 200	Glass/Metal - DO's and Metal/Ceramic - LCC's	MIL-PRF-19500 up to JANS	on Select	Not Applicable
	High Voltage Rectifier	PN Single and Stacked	1000V to 3000V	0.1A		175	Glass - DO's	MIL-PRF-19500 up to JANTX	Not Applicable	Not Applicable
	Power Schottky	N and N Dual	15V to 150V	3A to 150A		125 to 150	Metal/Ceramic - TO's, LCC's, ThinKey	MIL-PRF-19500 up to JANS	on Select	Not Applicable
	Small Signal Schottky - Hermetic	N and N Dual	20V to 100V	0.033A to 1A		125 to 150	Glass - DO's and Metal/Ceramic - LCC's	MIL-PRF-19500 up to JANS	on Select	Not Applicable
	Small Signal Schottky - Non Hermetic	N and N Dual	20V to 100V	0.033A to 1A		125 to 150	Plastic - DO's, PowerMite	Up to MX level	on Select	Not Applicable
Regulators/TVS	TVS - Hermetic	Unipolar and Bipolar	5V to 185V	1.7A to 440A	500W to 5000W	175	Glass/Metal - DO's and Ceramic - ThinKey	MIL-PRF-19500 up to JANS	on Select	Not Applicable
	TVS - Non Hermetic	Unipolar and Bipolar	5V to 185V	1.7A to 440A	500W to 5000W	175	Plastic - DO's, PowerMite and PLAD	Up to MX level	on Select	Not Applicable
	Voltage Regulator (Zener)	PN	1.8V to 390V	0.00046A to 12.4A	0.5W to 50W	175	Glass/Metal - DO's and Metal - TO's	MIL-PRF-19500 up to JANS	on Select	Not Applicable
	Temperature Compensated Zeners	PN/NP	6.2V to 49.6V	0.0005A to 0.01A	to 0.5W	100 to 175	Glass - DO's	MIL-PRF-19500 up to JANS	on Select	on Select
	Current Regulators	JFET	50V to 100V	0.0002A to 0.01A	0.5W	175	Glass - DO's	MIL-PRF-19500 up to JANS	on Select	Not Applicable
Modules	Arrays and Bridges	PN and Arrays	60V to 1000V	0.3A to 25A	0.5W and up	150	DIP's and Epoxy Filled Cases	MIL-PRF-19500 up to JANTX	Not Applicable	Not Applicable

Motor and Actuator Drives

Part Number	Product	Description	Power rating (kVA)	Nominal High Voltage Input (V)	Nominal Low Voltage Input (V)	Nom. Output Current (A)	Max. Output Current (A)	Power Architecture	Semiconductor Technology	Operating Temp. Range (°C)	Dimensions (mm)	Package
MAICMMC40X120A	PCM510	Power Core Module (PCM) with telemetry monitoring, control, communications, power bridge and fully integrated gate drive	5	540	15	12.5	25	3-phase bridge	SiC MOSFET or Si IGBT	-55 to +110	105 x 85 x 30	Right-angle connector
MAICMMC40X120B	PCM510	Power Core Module (PCM) with telemetry monitoring, control, communications, power bridge and fully integrated gate drive	5	540	15	12.5	25	3-phase bridge	SiC MOSFET or Si IGBT	-55 to +110	105 x 85 x 30	Straight connector
MAIPDMC40X120A	HPD510	Hybrid Power Drive (HPD) with power bridge and fully integrated gate drive	5	540	15	12.5	25	3-phase bridge	SiC MOSFET or Si IGBT	-55 to +110	105 x 85 x 25	Screw terminals
MAIPDMC40X120C	HPD520	Hybrid Power Drive (HPD) with power bridge and fully integrated gate drive	5	540	15	12.5	25	3-phase bridge	SiC MOSFET or Si IGBT	-55 to +110	92 x 82 x 19	Soldered pins

Radiation Hardened Power Supplies

Part Number	Product	Description	Power rating (W)	Nominal Voltage Input (V)	Outputs	Efficiency	Nom. Output Current (A)	Radiation	Power Architecture	Features	Operating Temp. Range (°C)	Dimensions (mm)	Weight
SA50-120-5S	SA Series DC - DC Converters	Space grade non-hybrid DC-DC Converter Single Output	50	120	Single 3.3V to 28V	85%	2A to 10A	100kRad	Forward Converter	Enable; Sync; Adjust; Parallel	-55 to +105	2 x 3 x 0.5	110 gm
SA50-120-5-15T	SA Series DC - DC Converters	Space grade non-hybrid DC-DC Converter Triple Output	50	120	Triple (Dual) 3.3V to 28V	85%	1A to 10A	100kRad	Forward Converter	Enable; Sync	-55 to +105	2 x 3 x 0.5	110 gm

Integrated Power Solutions: Relays

Hermetically Sealed Power Relays	#of Poles	Latch/Non-Latch	Suppressed Coils Available	Space grade Available per NASA EEE-INST-002	Contact Rating @28 VDC or 115V 400 Hz				Coil AC/DC Coil	DC Coil Voltages (M)	Pull-in power (mW)	Contact Resistance (Ohms)	Insulation Resistance @500Vdc	Dielectric @Vac	Temperature Rating (°C)	Design to meet or exceed MIL-PRF Reference				Dimensions in Inches less mounting Brackets (L x Wx H)	
					Resistive Load (ohms)	Inductive Load (ohms)	Motor Load (ohms)	Low Level 10–50 μA @ 10–50 mv								Gold Plated plug-in Solder pin 3 long pins Solder Hook	Gold Plated plug-in Solder pin 3 long pins Solder Hook				
BR10	2PDT	Non-latch	No	1	—	—	X	DC	6, 12, 18, 26	100	0.050Ω	10 K MΩ	250–500	65–125	MIL-PRF-39016	✓	✓	✓	✓	0.5 x 0.24 x 0.4	
BR13	2PDT	Non-latch	No	2–3–5	—	—	X	DC	6, 12, 26, 115	40, 100, 250	0.050Ω	10 K MΩ	500–1000	65–125	MIL-PRF-39016	—	✓	✓	✓	0.81 x 0.41 x 0.90	
BR15	4PDT	Non-latch	✓	5–7.5–10	1.75–2.5–3.5	—	X	115 VAC/DC	6, 12, 26, 115	400, 500, 1000	0.010Ω	10 K MΩ	1000–1250	65–125	MIL-PRF-39016	✓	✓	—	✓	1 x 1 x 1.3	
BR19	2PDT	Non-latch	No	5, 7.5, 10	1.75–2.5–3.5	—	X	115 VAC/DC	6, 12, 26, 48, 115	175, 500	0.010Ω	10 K MΩ	1000–1250	65–125	MIL-PRF-39016	✓	✓	✓	—	1.08 x 0.52 x 1.3	
BR20	2PDT	Latch	No	10	3.5	4	X	DC	6, 12, 26, 48, 115	130, 250	0.010Ω	10 K MΩ	1000–1250	65–125	MIL-PRF-39016	✓	✓	—	✓	1.08 x 0.52x 1.3	
BR23	4PDT	Latch	✓	10	3.5	4	X	DC	6, 12, 26, 48, 115	250, 500	0.010Ω	10 K MΩ	500–1250	65–125	MIL-PRF-39016	✓	✓	—	✓	1 x 1 x 1.3	
BR24	2PDT	Non-latch	Yes	No	10	3.5	4	X	DC	6, 12, 26	400	0.010Ω	10 K MΩ	500–1000	65–125	MIL-PRF-39016	✓	✓	—	✓	1.02 x 0.52 x 0.89
BR26	2PDT	Non-latch	No	2	—	—	X	DC	6, 12, 26	250	0.050Ω	10 K MΩ	500–1000	65–125	MIL-PRF-39016	✓	✓	—	✓	0.81 x 0.4 x 0.41	
BR246	2PDT	Non-latch	Yes	✓	10	8	2.5	—	115 VAC/DC	6, 12, 28, 48	500	0.010Ω	100 MΩ	1000–1250	65–125	MIL-PRF-83536	✓	✓	✓	✓	1.03 x.53 x 1.01
BR247	2PDT	Latch	Yes	✓	10	8	2.5	—	115 VAC/DC	6, 12, 28, 49	500	0.010Ω	100 MΩ	1000–1250	65–125	MIL-PRF-83536	✓	✓	✓	✓	1.03 x.53 x 1.01
BR230	4PDT	Non-latch	Yes	✓	10	8	2.5	—	115 VAC/DC	6, 12, 28, 50	500	0.010Ω	100 MΩ	1000–1250	65–125	MIL-PRF-83536	✓	✓	—	✓	1.03 x 1.0 3x 1.01
BR231	4PDT	Latch	Yes	✓	10	8	2.5	—	115 VAC/DC	6, 12, 28, 51	500	0.010Ω	100 MΩ	1000–1250	65–125	MIL-PRF-83536	✓	✓	—	✓	1.03 x 1.03 x 1.01
BR250	2PDT	Non-latch	Yes	✓	25	15	5	—	115 VAC/DC	6, 12, 28, 52	500	0.006Ω	100 MΩ	1000–1250	65–125	MIL-PRF-83536	✓	✓	—	✓	1.03 x.53 x 1.01
BR246-SXXX	2PDT	Non-latch	Yes	—	10	8	2.5	—	115 VAC/DC	6, 12, 28, 48	500	0.010Ω	100 MΩ	1000–1250	40–200	MIL-PRF-83536	—	✓	—	✓	1.03 x 0.53 x 1.01
BR250-SXXX	2PDT	Non-latch	Yes	—	25	15	5	—	115 VAC/DC	6, 12, 28, 52	500	0.006Ω	100 MΩ	1000–1250	40–200	MIL-PRF-83536	—	✓	—	✓	1.03 x 0.53 x 1.01

Integrated Power Solutions: Remote Power Controllers

Remote Power Controllers	#of Poles	Latch/Non-Latch	Contact Rating @28 VDC or 115V 400 Hz				Coil AC/DC Coil	Contact Voltage Drop at Rated Current	Insulation Resistance @500 Vdc	Dielectric @Vac	MIL-PRF Reference	Options				Bi-Directional	Temperature Rating	Features
			Resistive Load (ohms)	Motor Load (ohms)	Factory Current Trip Currents	Factory Current Trip Times						Factory Current Trip Currents	Factory Current Trip Times	Adjusted to Customers Specifications	Auxiliary Switch			
701	SPST	Magnetic Latching	5–200 Amps @ 28 VDC	5–200 Amps @ 28 VDC	28 VDC	.225 mv	100 MΩ	1350–1500	MIL-PRF-83383	✓	✓	✓	✓	✓	✓	—	-55°C to 85°C	1500 watts of Peak Power Dissipation transient suppression
702	SPST	Magnetic Latching	5–200 Amps @ 28 VDC or 115/208V 400 Hz	5–200 Amps @ 28 VDC or 115/208V 400 Hz	28 VDC or 115 VAC 400 Hz	.225 mv	100 MΩ	1350–1500	MIL-PRF-83383	✓	✓	✓	✓	✓	✓	—	-55°C to 85°C	
703	3PST Magnetic Latching	Magnetic Latching	5–150 Amps @ 115/208V 400 Hz	5–150 Amps @ 115/208V 400 Hz	28 VDC or 115 VAC 400 Hz	.225 mv	100 MΩ	1350–1500	MIL-PRF-83383	✓	✓	✓	✓	✓	✓	—	-55°C to 85°C	

PoE PSE ICs																	
Product	Description	Product Type	Standards Supported	Ports	2-Pair Power	4-Pair Power	Maximum Current	PoE Class (0-8)	PoE Type (1-4)	FETs	Sense Resistor	Operating Temperature	PoE Controller	Host Interface	Temperature Grade	Package Type	Package Carrier
PD69101ILQ-TR	IEEE 802.3at single port PoE PSE controller + manager, industrial temp	PSE IC	IEEE 802.3af IEEE 802.3at	1	36.25W	NA	0.725A	0-4	1-2	Internal 0.3Ω	External 0.5Ω	-40°C to 85°C	Auto mode	Serial monitoring	Industrial	24 QFN 4 mm x 5 mm	Tape and reel
PD69101ILQ-013155	IEEE 802.3at single port PoE PSE controller + manager	PSE IC	IEEE 802.3af IEEE 802.3at	1	36.25W	NA	0.725A	0-4	1-2	Internal 0.3Ω	External 0.5Ω	-10°C to 85°C	Auto mode	Serial monitoring	Commercial	24 QFN 4 mm x 5 mm	Tape and reel
PD69104B1ILQ-TR	IEEE 802.3at/UPoE 4 ports PSE controller + manager	PSE IC	IEEE 802.3af IEEE 802.3at Dual-IEEE 802.3at UPoE	4	36W	72W	0.725A	0-4	1-2	Internal 0.3Ω	External 0.36Ω	-10°C to 85°C	Auto mode	I ^C UART	Commercial	48 QFN 8 mm x 8 mm	Tape and reel
PD69200X-GGGG	IEEE 802.3at/bt/PoH 96 ports PSE controller w/power management for PD69204T4, PD69208M and PD69208T4	PSE IC	IEEE 802.3af IEEE 802.3at IEEE 802.3bt UPoE PoH	96	NA	NA	NA	NA	NA	NA	NA	-40°C to 85°C	NA	I ^C UART	Industrial	32 QFN 5 mm x 5 mm	Tray/ Tape and reel
PD69200C-021819	IEEE 802.3at/PoH PoE Controller - IEEE 802.3bt upgradable	PSE IC	IEEE 802.3af IEEE 802.3at UPoE PoH	96	NA	NA	NA	NA	NA	NA	NA	-40°C to 85°C	NA	I ^C UART	Industrial	32 QFN 5 mm x 5 mm	Tray/ Tape and reel
PD69204T4ILQ-TR/ PD69204T4ILQ-TR-LE	IEEE 802.3at/bt Type 4/PoH 4 ports, fully integrated PSE manager, industrial temp	PSE IC	IEEE 802.3af IEEE 802.3at IEEE 802.3bt UPoE PoH	4	47.5W	95W	0.94A	0-8	1-4	Internal	Internal	-40°C to 85°C	PD69200/ PD69210/ Marvell ISSR	NA	Industrial	56 QFN 8 mm x 8 mm	Tape and reel
PD69208T4ILQ-TR/ PD69208T4ILQ-TR-LE	IEEE 802.3at/bt Type 4/PoH 8 ports, fully integrated PSE manager, industrial temp	PSE IC	IEEE 802.3af IEEE 802.3at IEEE 802.3bt UPoE PoH	8	47.5W	95W	0.94A	0-8	1-4	Internal	Internal	-40°C to 85°C	PD69200/ PD69210/ Marvell ISSR	NA	Industrial	56 QFN 8 mm x 8 mm	Tape and reel
PD69208MILQ-TR/ PD69208MILQ-TR-LE	IEEE 802.3at/bt Type 3 8 ports, fully integrated PSE manager, industrial temp	PSE IC	IEEE 802.3af IEEE 802.3at IEEE 802.3bt UPoE PoH	8	35.7W	71.4W	0.627A	0-6	1-3	Internal	Internal	-40°C to 85°C	PD69200/ PD69210/ Marvell ISSR	NA	Industrial	56 QFN 8 mm x 8 mm	Tape and reel
PD69210X-GGGG	IEEE 802.3at/bt/PoH 96 ports PSE controller w/ power management for PD69204T4, PD69208M and PD69208T4	PSE IC	IEEE 802.3af IEEE 802.3at IEEE 802.3bt UPoE PoH	96	NA	NA	NA	NA	NA	NA	NA	-40°C to 85°C	NA	I ^C UART	Industrial	32 QFN 5 mm x 5 mm	Tray

PoE PSE EVBs													
Product	Description		Product Type	Standards Supported		Number of Ports	2-Pair Power	4-Pair Power	PoE Class (0-8)	PoE Type (1-4)	PD-PSE Power Forwarding	Host Interface	Featured Devices
PD-IM-7401	IEEE 802.3at, Dual-port PSE EVB featuring PD69101		PSE IC	IEEE 802.3af, IEEE 802.3at		2	36W	NA	0-4	1-2	No	Serial	PD69101
PD-IM-7504B	IEEE 802.3at/UPoE, 4 ports PSE EVB featuring PD69104B1		PSE IC	IEEE 802.3af, IEEE 802.3at		4	36W	72W	0-4	1-2	No	I ² C, UART	PD69104B1
PD-IM-7504B-Surge	IEEE 802.3at/UPoE, 4 ports PSE EVB featuring PD69104B1, 6kV surge protection		PSE IC	IEEE 802.3af, IEEE 802.3at		4	36W	72W	0-4	1-2	No	I ² C, UART	PD69104B1
PD-IM-7604+4MH	IEEE 802.3 at/bt Type 3, 4 x 2-pair + 4 x 4-Pair ports PSE EVB featuring PD69208M and PD69200, LED stream support		PSE IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt		8	35.7W	71.4W	0-6	1-3	No	USB (PC)	PD69208M, PD69200
PD-IM-7604+4T4H	IEEE 802.3 at/bt Type 4, 4 x 2-pair + 4 x 4-Pair ports PSE EVB featuring PD69208T4, PD69204T4 and PD69200, LED stream support		PSE IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt, PoH		8	47.5W	95W	0-8	1-4	No	USB (PC)	PD69208T4, PD69204T4, PD69200
PD-IM-7608M	IEEE 802.3 at/bt Type 3, 8 ports PSE EVB featuring PD69208M and PD69200, LED stream support		PSE IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt		8	35.7W	71.4W	0-4	1-2	No	USB (PC)	PD69208M, PD69200
PD-IM-7608M-2	IEEE 802.3 at/bt Type 3, 2 PoE Inputs and 8 PSE ports out EVB PSE EVB featuring PD69208M, PD69200, PD70224 IdealBridge™ and PD70211 PD ICs		PSE IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt		8	35.7W	71.4W	0-6	1-3	Yes	I ² C, USB (PC) SPI (Internal Use)	PD69208M, PD69200 PD70224, PD70211
PD-IM-7624M-Surge	IEEE 802.3 at/bt Type 3, 24 ports PSE EVB featuring PD69208M and PD69200, 6kV surge protection		PSE IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt		24	35.7W	71.4W	0-6	1-3	No	I ² C, UART USB (PC)	PD69208M, PD69200
PD-IM-7648MH	IEEE 802.3 at/bt Type 3, 48 ports PSE EVB featuring PD69208M and PD69200, LED stream support		PSE IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt		48	35.7W	71.4W	0-6	1-3	No	I ² C, UART, USB (PC)	PD69208M, PD69200
PD-IM-7648T4	IEEE 802.3 at/bt Type 4, 48 ports PSE EVB featuring PD69208T4 and PD69200, LED stream support		PSE IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt, PoH		48	47.5W	95W	0-8	1-4	No	I ² C, UART, USB (PC)	PD69208T4, PD69200

PoE PD ICs														
Product	Description	Product Type	Standards Supported	IC Type	PoE Type	PoE Class	Output Power	Maximum Current	Maximum Channel Resistance	Operating Temperature	Temperature Grade	Integrated PWM Controller	Package Type	Package Carrier
PD70100ILD-TR	IEEE 802.3af PD Front-end IC w/internal 0.6 Ohm FET	PD IC	IEEE 802.3af	PD Front end	AT/BT Type 1	1-3	15.4W	0.45A	0.6Ω	-40°C to +85°C	Industrial	No	12 DFN 4 mm x 3 mm	Tape and reel
PD70101ILQ-TR	IEEE 802.3af PD Front-end and PWM controller IC w/internal 0.6 Ohm FET	PD IC	IEEE 802.3af	PD Front end + PWM controller	AT/BT Type 1	1-3	15.4W	0.45A	0.6Ω	-40°C to +85°C	Industrial	Yes	32 QFN 5 mm x 5 mm	Tape and reel
PD70200ILD-TR	IEEE 802.3at PD Front-end IC w/internal 0.6 Ohm FET	PD IC	IEEE 802.3af, IEEE 802.3at, Dual-IEEE 802.3at	PD Front end	AT/BT Type 2	1-4	47W	1.2A	0.6Ω	-40°C to +85°C	Industrial	No	12-DFN 4 mm x 3 mm	Tape and reel
PD70201ILQ-TR	IEEE 802.3at PD Front-end and PWM controller IC w/internal 0.6 Ohm FET	PD IC	IEEE 802.3af, IEEE 802.3at, Dual-IEEE 802.3at	PD Front end + PWM controller	AT/BT Type 2	1-4	47W	1.2A	0.6Ω	-40°C to +85°C	Industrial	Yes	32 QFN 5 mm x 5 mm	Tape and reel
PD70210AILD-TR	IEEE 802.3at/PoH PD Front-end IC w/ internal 0.3 Ohm FET	PD IC	IEEE 802.3af, IEEE 802.3at, Dual-IEEE 802.3at PoH	PD Front end	AT/BT Type 2/PoH	1-4	95W	2A	0.3Ω	-40°C to +85°C	Industrial	No	16 DFN 5 mm x 4 mm	Tape and reel
PD70210ILD-TR	IEEE 802.3at/PoH PD Front-end IC w/ internal 0.3 Ohm FET and Auxiliary pin	PD IC	IEEE 802.3af, IEEE 802.3at, Dual-IEEE 802.3at PoH	PD Front end	AT/BT Type 2/PoH	1-4	95W	2A	0.3Ω	-40°C to +85°C	Industrial	No	16 DFN 5 mm x 4 mm	Tape and reel
PD70210ALILQ-TR	IEEE 802.3at/PoH PD Front-end and PWM controller IC w/ internal 0.3 Ohm FET, Large Package	PD IC	IEEE 802.3af, IEEE 802.3at, Dual-IEEE 802.3at PoH	PD Front end	AT/BT Type 2/PoH	1-4	95W	2A	0.3Ω	-40°C to +85°C	Industrial	No	38 QFN 5 mm x 7 mm	Tape and reel
PD70211ILQ-TR	IEEE 802.3at/PoH PD Front-end and PWM controller IC w/ internal 0.3 Ohm FET	PD IC	IEEE 802.3af, IEEE 802.3at, Dual-IEEE 802.3at PoH	PD Front end + PWM controller	AT/BT Type 2/PoH	1-4	95W	2A	0.3Ω	-40°C to +85°C	Industrial	Yes	36 QFN 6 mm x 6 mm	Tape and reel
PD70224ILQ-TR	IEEE 802.3at/bt/PoH IdealBridge™ Dual MOSFET-bridge rectifier	PD IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt PoH	Ideal diode bridge	AT/BT Type 4/PoH	1-8	95W	2A	0.76Ω	-40°C to +85°C	Industrial	NA	40 QFN 6 mm x 8 mm	Tape and reel
PD70224LILQ-TR	IEEE 802.3at/bt/PoH IdealBridge™ Dual MOSFET-bridge rectifier, Large package	PD IC	IEEE 802.3af, IEEE 802.3at, IEEE 802.3bt PoH	Ideal diode bridge	AT/BT Type 4/PoH	1-8	95W	2A	0.76Ω	-40°C to +85°C	Industrial	NA	52 QFN 7.5 mm x 10 mm	Tape and reel

PoE PD EVBs														
Product	Description	Product Type	Standards Supported	IC Used	Power	PoE Class (1-8)	PoE Type (1-4)	Output Voltage	Output Current	PD-PSE Power Forwarding	Diode Bridge	Auxiliary Power Priority	Topology	
PD70100EVB15B	IEEE 802.3af/bt Type 1 PD EVB featuring PD70100 w/3 output voltages	PD EVB	IEEE 802.3af IEEE 802.3at	PD70100	15W	3	1	12V 3.3V 1.8V	0.6A 2A 0.6A	No	Standard	Yes	Buck	
PD70101EVB3F	IEEE 802.3af/bt Type 1 PD EVB featuring PD70101 w/isolated flyback converter, 3.3V 1Amp output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70101	3.3W	3	1	3.3V	1A	No	Standard	Yes	Flyback	
PD70101EVB6F	IEEE 802.3af/bt Type 1 PD EVB featuring PD70101 w/isolated flyback converter, 5V 1.2Amp output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70101	6W	3	1	5V	1.2A	No	Standard	Yes	Flyback	
PD70101EVB15F-5	IEEE 802.3af/bt Type 1 PD EVB featuring PD70101 w/isolated flyback converter, 5V 2.6Amp output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70101	13W	3	1	5V	2.6A	No	Standard	Yes	Flyback	
PD70101EVB15F-12	IEEE 802.3af/bt Type 1 PD EVB featuring PD70101 w/isolated flyback converter, 12V 1.1Amp output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70101	13.2W	3	1	12V	1.1A	No	Standard	Yes	Flyback	
PD70201EVB25F-3	IEEE 802.3at/bt Type 2 PD EVB featuring PD70201 w/isolated flyback converter, 3.3V 7.5A output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70201	25W	4	2	3.3V	7.5A	No	Ideal	No	Flyback	
PD70201EVB25F-5	IEEE 802.3at/bt Type 2 PD EVB featuring PD70201 w/isolated flyback converter, 5V 5Amp output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70201	25W	4	2	5V	5A	No	Ideal	No	Flyback	
PD70201EVB25F-12	IEEE 802.3at/bt Type 2 PD EVB featuring PD70201 w/isolated flyback converter, 12V 2.1Amp output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70201	25W	4	2	12V	2.1A	No	Ideal	No	Flyback	
PD70201EVB25F-D-5	IEEE 802.3at/bt Type 2 PD Compact EVB featuring PD70201 w/ isolated flyback converter, 5V 5Amp output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70201	25W	4	2	5V	5A	No	Ideal	Yes	Flyback	
PD70201EVB25FW-3	Dual-IEEE 802.3at Type 2 (4 pair) PD EVB featuring PD70201, 4 pair supply w/isolated Forward converter, 3.3V 7.5A output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70201	25W	4	2	3.3V	7.5A	No	Ideal	Yes	Active clamp forward	
PD70201EVB47F	IEEE 802.3at/bt Type 2 PD EVB featuring PD70201 w/isolated flyback converter, 12V 4Amp output	PD EVB	IEEE 802.3af IEEE 802.3at	PD70201	48W	4	2	12V	4A	No	Ideal	Yes	Flyback	
PD70201EVB-U-25F-5	IEEE 802.3at/bt Type 2 PD EVB featuring PD70201 w/isolated flyback converter, 5V 5Amp output, 17-54V Input range	PD EVB	IEEE 802.3af IEEE 802.3at	PD70201	25W	4	2	5V	5A	No	Standard	Yes	Flyback	
PD70210EVB	IEEE 802.3at/bt Type 2/PoH PD EVB featuring PD70210A PD and PD70224 IdealBridge™	PD EVB	IEEE 802.3af IEEE 802.3at	PD70210A	72W	4	2	NA	2A	No	Ideal	Yes	NA	
PD70211EVB50FW-3	Dual-IEEE 802.3at/bt Type 2/PoH PD EVB featuring PD70211, 4 pair supply w/isolated Forward converter, 3.3V 15A output	PD EVB	IEEE 802.3af IEEE 802.3at PoH	PD70211	50W	4	2	3.3V	15A	No	Ideal	Yes	Active clamp forward	
PD70211EVB50FW-5	Dual-IEEE 802.3at/bt Type 2/PoH PD EVB featuring PD70211, 4 pair supply w/isolated Forward converter, 5V 10A output	PD EVB	IEEE 802.3af IEEE 802.3at PoH	PD70211	50W	4	2	5V	10A	No	Ideal	Yes	Active clamp forward	
PD70211EVB51F-12	Dual-IEEE 802.3at/bt Type 2/PoH PD EVB featuring PD70211, 4 pair supply w/isolated Forward converter, 12V 4.17A output	PD EVB	IEEE 802.3af IEEE 802.3at PoH	PD70211	51W	4	2	12V	4.25A	No	Ideal	Yes	Flyback	
PD70211EVB72FW-12	Dual-IEEE 802.3at/bt Type 2/PoH PD EVB featuring PD70211, 4 pair supply w/isolated Forward converter, 12V 6A output	PD EVB	IEEE 802.3af IEEE 802.3at PoH	PD70211	72W	4	2	12V	6A	No	Ideal	Yes	Active clamp forward	
PD70224EVB	Dual IEEE 802.3at/bt Type 2/PoH PD EVB featuring PD70210 PD and PD70224 IdealBridge™	PD EVB	IEEE 802.3af IEEE 802.3at PoH	PD70210 PD70224	72W	4	2	NA	NA	No	Ideal	No	NA	
PD70224EVB-wAuxPwr	Dual IEEE 802.3at/bt Type 2/PoH PD EVB featuring PD70210A PD and PD70224 IdealBridge™	PD EVB	IEEE 802.3af IEEE 802.3at PoH	PD70210A PD70224	72W	4	2	NA	NA	No	Ideal	Yes	NA	

PoE Systems									
Product	Description	Operating Environment	Power Per Port	Number of Ports	Data Rate	Managed	Input Power	Package Type	
PD-3501GC/AC-XX	IEEE 802.3af compliant single port PoE midspan	Indoor	15.4W	1	1G	No	AC	Standalone unit	
PD-3504G/AC-XX	IEEE 802.3af compliant 4 ports PoE midspan	Indoor	15.4W	4	1G	No	AC	Standalone unit	
PD-6512G/AC/M-XX	IEEE 802.3af compliant 12 ports PoE midspan	Indoor	15.4W	12	1G	Yes	AC	Standalone unit	
PD-6524G/AC/M/F-XX	IEEE 802.3af compliant 24 ports PoE midspan	Indoor	15.4W	24	1G	Yes	AC	Standalone unit	
PD-9001GC/AC-XX	IEEE 802.3at compliant single port PoE midspan	Indoor	30W	1	1G	No	AC	Standalone unit	
PD-9001GR/SP/AC-XX**	IEEE 802.3at compliant single port PoE midspan with surge protection	Indoor	30W	1	1G	No	AC	Standalone unit	
PD-9001-25GR/AC-XX	IEEE 802.3at compliant single port PoE midspan with 2.5G data rate	Indoor	30W	1	2.5G	No	AC	Standalone unit	
PD-9001-10GR/AC-XX	IEEE 802.3at compliant single port PoE midspan with 10G data rate	Indoor	30W	1	10G	No	AC	Standalone unit	
PD-9004G/AC-XX	IEEE 802.3at compliant 4 ports PoE midspan	Indoor	30W	4	1G	No	AC	Standalone unit	
PD-9006G/ACDC/M-XX	IEEE 802.3at compliant 6 ports PoE midspan	Indoor	30W	6	1G	Yes	AC and DC	Standalone unit	
PD-9012G/ACDC/M-XX	IEEE 802.3at compliant 12 ports PoE midspan	Indoor	30W	12	1G	Yes	AC and DC	Standalone unit	
PD-9024G/ACDC/M-XX	IEEE 802.3at compliant 24 ports PoE midspan	Indoor	30W	24	1G	Yes	AC and DC	Standalone unit	
PD-9501GC/AC-XX	IEEE 802.3at compliant single port PoE midspan	Indoor	60W	1	1G	No	AC	Standalone unit	
PD-9501GR/SP/AC-XX**	IEEE 802.3at compliant single port PoE midspan with surge protection	Indoor	60W	1	1G	No	AC	Standalone unit	
PD-9501G-SFP/AC-XX	IEEE 802.3at compliant PoE media converter to extend existing network distance with fiber cabling	Indoor	60W	1	1G	No	AC	Standalone unit	
PD-9501G/24VDC-XX	IEEE 802.3at compliant single port PoE midspan	Indoor	60W	1	1G	No	DC	Standalone unit	
PD-9501G/48VDC-XX	IEEE 802.3at compliant single port PoE midspan	Indoor	60W	1	1G	No	DC	Standalone unit	
PD-9506GC/AC-XX	IEEE 802.3bt compliant 6 ports EEPoE midspan	Indoor	60W	6	1G	Yes	AC and DC	Standalone unit	
PD-9512GC/AC-XX	IEEE 802.3bt compliant 12 ports EEPoE midspan	Indoor	60W	12	1G	Yes	AC and DC	Standalone unit	
PD-9524GC/AC-XX	IEEE 802.3bt compliant 24 ports EEPoE midspan	Indoor	60W	24	1G	Yes	AC and DC	Standalone unit	
PDS-208G/F/M/AC-XX*	IEEE 802.3at compliant 8 ports digital ceiling PoE switch	Indoor	60W	8	1G	Yes	AC	Standalone unit	
PD-9601GC/AC-XX	IEEE 802.3bt compliant single port PoE midspan	Indoor	90W	1	1G	No	AC	Standalone unit	
PD-9606GC/AC-XX	IEEE 802.3bt compliant 6 ports PoE midspan	Indoor	90W	6	1G	Yes	AC and DC	Standalone unit	
PD-9612GC/AC-XX	IEEE 802.3bt compliant 12 ports PoE midspan	Indoor	90W	12	1G	Yes	AC and DC	Standalone unit	
PD-9624GC/AC-XX	IEEE 802.3bt compliant 24 ports PoE midspan	Indoor	90W	24	1G	Yes	AC and DC	Standalone unit	
PDS-408G/AC-XX*	IEEE 802.3bt compliant 8 ports digital ceiling PoE switch	Indoor	90W	8	1G	Yes	AC	Standalone unit	
PD-9001GO-ET/AC	IEEE 802.3at compliant single port PoE midspan with surge protection and ability to withstand extreme temperatures	Outdoor	30W	1	1G	No	AC	Standalone unit	
PD-9501GO-ET/AC	IEEE 802.3at compliant single port PoE midspan with surge protection and ability to withstand extreme temperatures	Outdoor	60W	1	1G	No	AC	Standalone unit	
PD-9501GO/12-24VDC	IEEE 802.3at compliant single port PoE midspan with surge protection	Outdoor	60W	1	1G	No	DC	Standalone unit	
PD-9501GO/48VDC	IEEE 802.3at compliant single port PoE midspan with surge protection	Outdoor	60W	1	1G	No	DC	Standalone unit	
PDS-104GO/AC/M-IN	IEEE 802.3at compliant 4 ports outdoor PoE switch with surge protection and international power cord	Outdoor	60W	4	1G	Yes	AC	Standalone unit	
PDS-104GO/AC/M-NA	IEEE 802.3at compliant 4 ports outdoor PoE switch with surge protection and North America power cord	Outdoor	60W	4	1G	Yes	AC	Standalone unit	
PD-9601GO/AC	IEEE 802.3at compliant single port PoE midspan with surge protection	Outdoor	90W	1	1G	No	AC	Standalone unit	
PD-9001GI/DC	IEEE 802.3at compliant single port, industrial grade PoE midspan	Industrial	30W	1	1G	No	DC	Standalone unit	
PD-9501GI/DCF	IEEE 802.3at compliant single port, industrial grade PoE midspan	Industrial	60W	1	1G	No	DC	Standalone unit	
PD-AS-601/5	Single port PoE splitter for contemporary devices unable to accept power via Ethernet	Indoor	10W	1	1G	NA	PoE	Standalone unit	
PD-AS-951/12-24	Single port PoE splitter for contemporary devices unable to accept power via Ethernet	Indoor	54W	1	1G	NA	PoE	Standalone unit	
PD-POE-EXTENDER	Single port PoE extender to extend Ethernet network range beyond 100m	Indoor	30W	1	1G	NA	DC	Standalone unit	
PD-OUT/SP11	Single port PoE surge protector for Ethernet networks with outdoor PoE midspans and powered devices	Outdoor	NA	1	1G	NA	DC	Standalone unit	
PD-AFAT-TESTER	PoE tester for for RJ-45 outlet	Indoor	NA	NA	1G	NA	PoE	Standalone unit	

*Any individual port can operate at up to 72 W.

**Includes integrated surge protection.

***Limited lifetime includes a limitation of 16 years warranty on the power supply and fans.

XX Indicates power cord code: EU (Europe), UK (United Kingdom), US (North America), BR (Brazil), JP (Japan), AU (Australia)

Broad Range FPGA Supplier (1-500K LE)			
Features	SmartFusion®, ProASIC®3, IGLOO®	SmartFusion2 IGLOO2	PolarFire®
Logic Elements	100–30K	5K–150K	100–480K
Transceiver Rate	–	1–5 Gbps	250 Mbps–12.7 Gbps
I/O Speeds	400 Mbps LVDS	667 Mbps DDR3, 750 Mbps LVDS	1600 Mbps DDR4, 1.6 Gbps LVDS
DSP (18x18 Multipliers)	–	240	1480
Max RAM	144 Kb	5 Mb	33 Mb
Processor Option	Hard 100 MHz, Arm® Cortex®-M3	Hard 166 MHz, Arm Cortex-M3, Soft RISC-V	Soft RISC-V, Hard Crypto Processor
On-Board Flash	Up to 512 KB code store	Up To 512 KB code store	56 KB secure NVM
Family Type	CPLD Replacements, Smallest Packages	Low Density FPGAs with more resources and lowest power	Mid-Range Density FPGAs, Lowest Power, Cost Optimized

Terms and Definitions

1 KB.....1024 bytes
 1 Kw 1024 words
 18F/PIC18 16-bit instruction word: 75/83 instructions
 ADC Analog to Digital Converter
 ADC2/ADCC ADC with Computation
 AngTMR Angular Timer
 AUSART Addressable Universal Synchronous Asynchronous Receiver Transmitter
 BL/Baseline 12-bit instruction word: 33 instructions
 BOR/PBOR.....Brown Out Reset/ Programmable Brown Out Reset
 BTLE Bluetooth® Low Energy
 CAN Controller Area Network
 CCP/ECCP Capture Compare PWM/ Enhanced Capture Compare PWM
 CLC Configurable Logic Cell
 COG Complementary Output Generator
 Comp.....Capacitive Sensing Implemented via Comparator
 CRC/SCAN.....Cyclical Redundancy Check with Memory Scanner
 CTMU mTouch® Sensing: Charge Time Measurement Unit
 CVD Charge Voltage Divide (Capacitive Sensing Implemented via ADC)
 CWG Complementary Waveform Generator
 DAC Digital-to-Analog Converter
 DOZE Low-Power Doze Mode
 DSM.....Data Signal Modulator
 dsPIC® DSC 16-bit Core with DSP
 EBL.....Enhanced Baseline
 EEPROM Electrically Erasable Programmable Read Only Memory
 EMR/Enhanced 14-bit instruction word: 49 instructions

Mid-Range.....(Denoted as PIC1XF1XXX)
 ESD Electrostatic Discharge
 EUSART Enhanced Universal Synchronous Asynchronous Receiver Transmitter
 EWDT/WDT Extended Watchdog Timer/ Watchdog Timer
 HC I/O High-Current I/O
 HEF High-Endurance Flash (128B of Nonvolatile Data Storage)
 HLT Hardware Limit Timer
 HV High Voltage
 ICD In-Circuit Debug
 ICE In-Circuit Emulation
 ICSP™ In-Circuit Serial Programming™
 IDE Integrated Development Environment
 IDLE Low-Power Idle Mode
 Inst Amp Instrumentation Amplifier
 LCD Liquid Crystal Display
 LDO Low Drop-Out Voltage Regulator
 LF Low-Power Flash
 LPBOR.....Low-Power Brown Out Reset
 MI²C/I²C Master Inter-Integrated Circuit Bus/ Inter-Integrated Circuit Bus
 MathACC Math Accelerator
 MIPS Million Instructions Per Second
 MR/Mid-Range 14-bit instruction word: 35 instructions
 MSSP/SSP Master/Synchronous Serial Port (I²C and SPI Peripheral)
 mTouch.....Proprietary Touch Sensing Technology
 NCO Numerically Controlled Oscillator
 Op Amp Operational Amplifier
 PIC10/12/16/18 8-bit Core
 PIC24.....16-bit Core
 PIC32.....32-bit Core
 PLVD Programmable Low Voltage Detect
 PMD Low-Power Peripheral Module Disable
 PMP Parallel Master Port
 POR/POOR....Power ON Reset/Power ON/OFF Reset
 PPS Peripheral Pin Select
 PRG Programmable Ramp Generator
 PSMC Programmable Switch Mode Controller (16-bit PWM)
 PWM Pulse-Width Modulation
 QEI Quadrature Encoder Interface
 RAM Random Access Memory
 RTCC Real-Time Clock Calendar
 SlopeComp Slope Compensation
 SMT 24-bit Signal Measurement Timer
 Source/Sink Current.....All Products Support 25 mA per I/O
 SR Latch.....Set Reset Latch
 SRAM Static Random Access Memory
 SPI Serial Peripheral Interface
 TEMP Temperature Indicator
 T1G Timer 1 Gate
 USART Universal Synchronous Asynchronous Receiver Transmitter
 USB Universal Serial Bus
 USB (Full Speed) 12 MB Data Rate
 USB OTG USB On-The-Go
 WWDT Window Watchdog Timer
 XLP eXtreme Low-Power Technology
 ZCD Zero-Cross Detection

Packaging

For detailed dimensions, view our package drawings and dimensions specifications at: www.microchip.com/packaging.

Support

Microchip is committed to supporting its customers in developing products faster and more efficiently. We maintain a worldwide network of field applications engineers and technical support ready to provide product and system assistance. For more information, please visit www.microchip.com:

- Technical Support: www.microchip.com/support
- Evaluation samples of any Microchip device: www.microchip.com/sample
- Knowledge base and peer help: www.microchip.com/forums
- Sales and Global Distribution: www.microchip.com/sales

Training

If additional training interests you, Microchip offers several resources including in-depth technical training and reference material, self-paced tutorials and significant online resources.

- Overview of Technical Training Resources: www.microchip.com/training
- MASTERs Conferences: www.microchip.com/masters
- Developer Help Website: www.microchip.com/developerhelp
- Technical Training Centers: www.microchip.com/seminars

Sales Office Listing

AMERICAS

Atlanta, GA
Tel: 678-957-9614
Austin, TX
Tel: 512-257-3370
Boston, MA
Tel: 774-760-0087
Chandler, AZ (HQ)
Tel: 480-792-7200
Chicago, IL
Tel: 630-285-0071
Dallas, TX
Tel: 972-818-7423
Detroit, MI
Tel: 248-848-4000
Houston, TX
Tel: 281-894-5983
Indianapolis, IN
Tel: 317-773-8323
Tel: 317-536-2380
Los Angeles, CA
Tel: 949-462-9523
Tel: 951-273-7800
Raleigh, NC
Tel: 919-844-7510
New York, NY
Tel: 631-435-6000
San Jose, CA
Tel: 408-735-9110
Tel: 408-436-4270
Canada - Toronto
Tel: 905-695-1980

EUROPE

Austria - Wels
Tel: 43-7242-2244-39
Denmark - Copenhagen
Tel: 45-4450-2828
Finland - Espoo
Tel: 358-9-4520-820
France - Paris
Tel: 33-1-69-53-63-20
Germany - Garching
Tel: 49-8931-9700
Germany - Haan
Tel: 49-2129-3766-400
Germany - Heilbronn
Tel: 49-7131-67-3636
Germany - Karlsruhe
Tel: 49-721-62537-0
Germany - Munich
Tel: 49-89-627-144-0
Germany - Rosenheim
Tel: 49-8031-354-560

EUROPE

Israel - Ra'anana
Tel: 972-9-744-7705
Italy - Milan
Tel: 39-0331-742611
Italy - Padova
Tel: 39-049-7625286
Netherlands - Drunen
Tel: 31-416-690399
Norway - Trondheim
Tel: 47-7289-7561
Poland - Warsaw
Tel: 48-22-3325737
Romania - Bucharest
Tel: 40-21-407-87-50
Spain - Madrid
Tel: 34-91-708-08-90
Sweden - Gothenberg
Tel: 46-31-704-60-40
Sweden - Stockholm
Tel: 46-8-5090-4654
UK - Wokingham
Tel: 44-118-921-5800

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733
China - Beijing
Tel: 86-10-8569-7000
China - Chengdu
Tel: 86-28-8665-5511
China - Chongqing
Tel: 86-23-8980-9588
China - Dongguan
Tel: 86-769-8702-9880
China - Guangzhou
Tel: 86-20-8755-8029
China - Hangzhou
Tel: 86-571-8792-8115
China - Hong Kong SAR
Tel: 852-2943-5100
China - Nanjing
Tel: 86-25-8473-2460
China - Qingdao
Tel: 86-532-8502-7355
China - Shanghai
Tel: 86-21-3326-8000
China - Shenyang
Tel: 86-24-2334-2829
China - Shenzhen
Tel: 86-755-8864-2200
China - Suzhou
Tel: 86-186-6233-1526
China - Wuhan
Tel: 86-27-5980-5300
China - Xiamen
Tel: 86-592-2388138
China - Xian
Tel: 86-29-8833-7252

ASIA/PACIFIC

China - Zhuhai
Tel: 86-756-321-0040
India - Bangalore
Tel: 91-80-3090-4444
India - New Delhi
Tel: 91-11-4160-8631
India - Pune
Tel: 91-20-4121-0141
Japan - Osaka
Tel: 81-6-6152-7160
Japan - Tokyo
Tel: 81-3-6880-3770
Korea - Daegu
Tel: 82-53-744-4301
Korea - Seoul
Tel: 82-2-554-7200
Malaysia - Kuala Lumpur
Tel: 60-3-7651-7906
Malaysia - Penang
Tel: 60-4-227-8870
Philippines - Manila
Tel: 63-2-634-9065
Singapore
Tel: 65-6334-8870
Taiwan - Hsin Chu
Tel: 886-3-577-8366
Taiwan - Kaohsiung
Tel: 886-7-213-7830
Taiwan - Taipei
Tel: 886-2-2508-8600
Thailand - Bangkok
Tel: 66-2-694-1351
Vietnam - Ho Chi Minh
Tel: 84-28-5448-2100



www.microchip.com

Microchip Technology Inc. | 2355 W. Chandler Blvd. | Chandler AZ, 85224-6199

The Microchip name and logo, the Microchip logo, AVR, dsPIC, Hyper Speed Control, HyperLight Load, IGLOO, maXTouch, MediaLB, MOST, MPLAB, PIC, picoPower, PolarFire, ProASIC, QTouch, Quiet-WIRE and SmartFusion are registered trademarks and ICSP, MiWi, MultiSwitch and SQI, are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries. Arm and Cortex are registered trademarks of ARM Limited (or its subsidiaries) in the EU and other countries. mTouch is a registered trademark of Microchip Technology Inc in the U.S.A. The LoRa name and associated logo are trademarks of Semtech Corporation or its subsidiaries. USB-C and USB Type-C are trademarks of the USB Developers Forum. All other trademarks mentioned herein are property of their respective companies.

© 2019, Microchip Technology Incorporated. All Rights Reserved. 7/19

DS00001308T

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[PD69200C-021819](#)