

# MCP73833/4

## Stand-Alone Linear Li-Ion / Li-Polymer Charge Management Controller

#### Features

- Complete Linear Charge Management Controller
  - Integrated Pass Transistor
  - Integrated Current Sense
  - Integrated Reverse Discharge Protection
- Constant Current / Constant Voltage Operation
   with Thermal Regulation
- High Accuracy Preset Voltage Regulation:
- 4.2V, 4.35V, 4.4V, or 4.5V, <u>+</u> 0.75%
- Programmable Charge Current: 1A Maximum
- Preconditioning of Deeply Depleted Cells
  - Selectable Current Ratio
- Selectable Voltage Threshold
- Automatic End-of-Charge Control
  - Selectable Current Threshold
  - Selectable Safety Time Period
- Automatic Recharge
- Selectable Voltage Threshold
- Two Charge Status Outputs
- Cell Temperature Monitor
- · Low-Dropout Linear Regulator Mode
- Automatic Power-Down when Input Power Removed
- Under Voltage Lockout
- Numerous Selectable Options Available for a Variety of Applications:
  - Refer to Section 1.0 "Electrical Characteristics" for Selectable Options
  - Refer to the Product Identification System for Standard Options
- · Available Packages:
  - DFN-10 (3 mm x 3 mm)
  - MSOP-10

#### Applications

- Lithium-Ion / Lithium-Polymer Battery Chargers
- Personal Data Assistants
- Cellular Telephones
- Digital Cameras
- MP3 Players
- Bluetooth Headsets
- USB Chargers

#### Description

The MCP73833/4 is a highly advanced linear charge management controller for use in space-limited, cost sensitive applications. The MCP73833/4 is available in a 10-Lead, 3 mm x 3 mm DFN package or a 10-Lead, MSOP package. Along with its small physical size, the low number of external components required makes the MCP73833/4 ideally suited for portable applications. For applications charging from a USB port, the MCP73833/4 can adhere to all the specifications governing the USB power bus.

The MCP73833/4 employs a constant current/constant voltage charge algorithm with selectable preconditioning and charge termination. The constant voltage regulation is fixed with four available options: 4.20V, 4.35V, 4.40V, or 4.50V, to accomodate new, emerging battery charging requirements. The constant current value is set with one external resistor. The MCP73833/ 4 limits the charge current based on die temperature during high power or high ambient conditions. This thermal regulation optimizes the charge cycle time while maintaining device reliability.

Several options are available for the preconditioning threshold, preconditioning current value, charge termination value, and automatic recharge threshold. The preconditioning value and charge termination value are set as a ratio, or percentage, of the programmed constant current value. Preconditioning can be set to 100%. Refer to Section 1.0 "Electrical Characteristics" for available options and the "Product Indentification System" for standard options.

The MCP73833/4 is fully specified over the ambient temperature range of -40 $^\circ$ C to +85 $^\circ$ C.

#### Package Types



## **Typical Application**



#### Functional Block Diagram



### 1.0 ELECTRICAL CHARACTERISTICS

#### **Absolute Maximum Ratings**

V <sub>DD</sub> 7.0V
All Inputs and Outputs w.r.t. $V_{SS}$ 0.3 to $(V_{DD}\text{+}0.3)V$
Maximum Junction Temperature, ${\rm T}_{\rm J}$ . Internally Limited
Storage temperature65°C to +150°C
ESD protection on all pins:
Human Body Model (HBM) (1.5 k $\Omega$ in Series with 100 pF) $\geq 4~kV$
Machine Model (MM) (200 pF, No Series Resistance)

\*Notice: Stresses above those listed under "Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

## DC CHARACTERISTICS

Parameters	Sym	Min	Тур	Max	Units	Conditions
Supply Input	1				1	
Supply Voltage	V <sub>DD</sub>	3.75	_	6	V	Charging
		V <sub>REG</sub> (Typ- ical)+0.3V	_	6	V	Charge Complete, Standby
Supply Current	I <sub>SS</sub>	—	2000	3000	μA	Charging
		—	150	300	μA	Charge Complete
		—	100	300	μA	Standby (No Battery or PROG Floating)
		—	50	100	μA	Shutdown ( $V_{DD} \le V_{BAT}$ , or $V_{DD} < V_{STOP}$ )
UVLO Start Threshold	V <sub>START</sub>	3.4	3.55	3.7	V	V <sub>DD</sub> Low-to-High
UVLO Stop Threshold	V <sub>STOP</sub>	3.3	3.45	3.6	V	V <sub>DD</sub> High-to-Low
UVLO Hysteresis	V <sub>HYS</sub>	—	100		mV	
Voltage Regulation (Constant Vol	tage Mode, Syste	m Test Mode	<del>)</del> )			
Regulated Output Voltage	V <sub>REG</sub>	4.168	4.20	4.232	V	V <sub>DD</sub> =[V <sub>REG</sub> (Typical)+1V]
		4.318	4.35	4.382	V	I <sub>OUT</sub> =10 mA
		4.367	4.40	4.433	V	T <sub>A</sub> =-5°C to +55°C
		4.467	4.50	4.533	V	
Line Regulation	$ (\Delta V_{BAT}/V_{BAT}) /\Delta V_{DD} $	—	0.10	0.30	%/V	V <sub>DD</sub> =[V <sub>REG</sub> (Typical)+1V] to 6V, I <sub>OUT</sub> =10 mA
Load Regulation	$ \Delta V_{BAT} / V_{BAT} $	—	0.10	0.30	%	I <sub>OUT</sub> =10 mA to 100 mA V <sub>DD</sub> =[V <sub>REG</sub> (Typical)+1V]
Supply Ripple Attenuation	PSRR	_	58	-	dB	I <sub>OUT</sub> =10 mA, 10Hz to 1 kHz
		—	47	—	dB	I <sub>OUT</sub> =10 mA, 10Hz to 10 kHz
		—	25	_	dB	I <sub>OUT</sub> =10 mA, 10Hz to 1 MHz
Current Regulation (Fast Charge	Constant Current	t Mode)				
Fast Charge Current Regulation	I <sub>REG</sub>	90	100	110	mA	PROG = 10 kΩ
		900	1000	1100	mA	PROG = 1.0 kΩ
						T <sub>A</sub> =-5°C to +55°C
Maximum Output Current Limit	I <sub>MAX</sub>	—	1200	—	mA	PROG < 833Ω

## **DC CHARACTERISTICS (CONTINUED)**

**Electrical Specifications:** Unless otherwise specified, all limits apply for  $V_{DD}$ = [ $V_{REG}$ (Typical)+0.3V] to 6V,  $T_A$ =-40°C to 85°C. Typical values are at +25°C,  $V_{DD}$ = [ $V_{REG}$ (Typical)+1.0V]

Parameters	Sym	Min	Тур	Мах	Units	Conditions
Preconditioning Current Regulation	on (Trickle Charg	e Constant	Current N	/lode)		
Precondition Current Ratio	I <sub>PREG</sub> / I <sub>REG</sub>	7.5	10	12.5	%	PROG = 1.0 kΩ to 10 kΩ
		15	20	25	%	T <sub>A</sub> =-5°C to +55°C
		30	40	50	%	
		_	100	_	%	
Precondition Voltage Threshold	V <sub>PTH</sub> / V <sub>REG</sub>	64	66.5	70	%	V <sub>BAT</sub> Low-to-High
Ratio		69	71.5	75	%	
Precondition Hysteresis	V <sub>PHYS</sub>	—	100	—	mV	V <sub>BAT</sub> High-to-Low
Charge Termination		•			•	
Charge Termination Current Ratio	I <sub>TERM</sub> / I <sub>REG</sub>	3.75	5	6.25	%	PROG = 1.0 kΩ to 10 kΩ
		5.6	7.5	9.4	%	T <sub>A</sub> =-5°C to +55°C
		7.5	10	12.5	%	
		15	20	25	%	
Automatic Recharge	•				•	•
Recharge Voltage Threshold Ratio	V <sub>RTH</sub> / V <sub>REG</sub>	—	94.0	_	%	V <sub>BAT</sub> High-to-Low
		_	96.5	_	%	
Pass Transistor ON-Resistance	•					
ON-Resistance	R <sub>DSON</sub>	—	300	_	mΩ	V <sub>DD</sub> = 3.75V
						T <sub>J</sub> = 105°C
Battery Discharge Current						
Output Reverse Leakage Current	I <sub>DISCHARGE</sub>	—	0.15	2	μA	PROG Floating
		—	0.25	2	μA	$V_{DD} \leq V_{BAT}$
		—	0.15	2	μA	$V_{DD} < V_{STOP}$
		—	-5.5	-15	μA	Charge Complete
Status Indicators - STAT1, STAT2,	PG					
Sink Current	I <sub>SINK</sub>	—	15	25	mA	
Low Output Voltage	V <sub>OL</sub>	—	0.4	1	V	I <sub>SINK</sub> = 4 mA
Input Leakage Current	I <sub>LK</sub>	—	0.01	1	μA	High Impedance, 6V on pin
PROG Input						
Charge Impedance Range	R <sub>PROG</sub>	1	—	20	kΩ	
Standy Impedance	R <sub>PROG</sub>	70	—	200	kΩ	Minimum Impedance for Standby
Thermistor Bias						
Thermistor Current Source	I <sub>THERM</sub>	47	50	53	μA	2 kΩ < R <sub>THERM</sub> < 50 kΩ
Thermistor Comparator						
Upper Trip Threshold	V <sub>T1</sub>	1.20	1.23	1.26	V	V <sub>THERM</sub> Low-to-High
Upper Trip Point Hysteresis	V <sub>T1HYS</sub>	_	-50		mV	
Lower Trip Threshold	V <sub>T2</sub>	0.235	0.25	0.265	V	V <sub>THERM</sub> High-to-Low
Lower Trip Point Hysteresis	V <sub>T2HYS</sub>	_	50	_	mV	
System Test (LDO) Mode					•	
Input High Voltage Level	V <sub>IH</sub>	(V <sub>DD</sub> -0.1)	_	_	V	
THERM Input Sink Current	I <sub>SINK</sub>	3	6	20	μA	Stand-by or system test mode
Bypass Capacitance	C <sub>BAT</sub>	1	_	_	μF	I <sub>OUT</sub> < 250 mA
Bypass Capacitance	Uni Uni			1	1 .	

## **DC CHARACTERISTICS (CONTINUED)**

<b>Electrical Specifications:</b> Unless otherwise specified, all limits apply for V <sub>DD</sub> = [V <sub>REG</sub> (Typical)+0.3V] to 6V, T <sub>A</sub> =-40°C to 85°C. Typical values are at +25°C, V <sub>DD</sub> = [V <sub>REG</sub> (Typical)+1.0V]						
Parameters	Sym	Min	Тур	Max	Units	Conditions
Automatic Power Down						
Automatic Power Down Entry Threshold	V <sub>PD</sub>	—	V <sub>BAT</sub> + 50 mV	_	V	$2.3V \le V_{BAT} \le V_{REG}$ V <sub>DD</sub> Falling
Automatic Power Down Exit Thresh- old	V <sub>PDEXIT</sub>	—	V <sub>BAT</sub> + 150 mV	—	V	$2.3V \le V_{BAT} \le V_{REG}$ V <sub>DD</sub> Rising
Timer Enable Input (TE)						
Input High Voltage Level	V <sub>IH</sub>	2.0	—	_	V	
Input Low Voltage Level	V <sub>IL</sub>	—	—	0.6	V	
Input Leakage Current	I <sub>LK</sub>	—	0.01	1	μA	V <sub>TE</sub> = 6V
Thermal Shutdown						
Die Temperature	T <sub>SD</sub>	_	150	_	°C	
Die Temperature Hysteresis	T <sub>SDHYS</sub>	—	10	_	°C	

## **AC CHARACTERISTICS**

**Electrical Specifications:** Unless otherwise specified, all limits apply for  $V_{DD}$ = [ $V_{REG}$ (Typical)+0.3V] to 6V,  $T_A$ =-40°C to 85°C. Typical values are at +25°C,  $V_{DD}$ = [ $V_{REG}$ (Typical)+1.0V]

Parameters	Sym	Min	Тур	Max	Units	Conditions
UVLO Start Delay	t <sub>START</sub>		—	5	ms	V <sub>DD</sub> Low-to-High
Current Regulation	<u> </u>			•	•	
Transition Time Out of Preconditioning	t <sub>DELAY</sub>	_	_	1	ms	V <sub>BAT</sub> <v<sub>PTH to V<sub>BAT</sub>&gt;V<sub>PTH</sub></v<sub>
Current Rise Time Out of Preconditioning	t <sub>RISE</sub>	_	—	1	ms	I <sub>OUT</sub> Rising to 90% of I <sub>REG</sub>
Preconditioning Comparator Filter Time	t <sub>PRECON</sub>	0.4	1.3	3.2	ms	Average V <sub>BAT</sub> Rise/Fall
Termination Comparator Filter Time	t <sub>TERM</sub>	0.4	1.3	3.2	ms	Average I <sub>OUT</sub> Falling
Charge Comparator Filter Time	t <sub>CHARGE</sub>	0.4	1.3	3.2	ms	Average V <sub>BAT</sub> Falling
Thermistor Comparator Filter Time	t <sub>THERM</sub>	0.4	1.3	3.2	ms	Average THERM Rise/Fall
Elapsed Timer						
Elapsed Timer Period	t <sub>ELAPSED</sub>	0	0	0	Hours	Timer Disabled
		3.6	4.0	4.4	Hours	
		5.4	6.0	6.6	Hours	
		7.2	8.0	8.8	Hours	
Status Indicators					•	
Status Output turn-off	t <sub>OFF</sub>		_	200	μs	I <sub>SINK</sub> = 1 mA to 0 mA
Status Output turn-on	t <sub>ON</sub>		_	200	μs	I <sub>SINK</sub> = 0 mA to 1 mA

## **TEMPERATURE SPECIFICATIONS**

Parameters	Symbol	Min	Тур	Max	Units	Conditions
Temperature Ranges						
Specified Temperature Range	T <sub>A</sub>	-40	—	+85	°C	
Operating Temperature Range	T <sub>A</sub>	-40	—	+125	°C	
Storage Temperature Range	T <sub>A</sub>	-65	_	+150	°C	
Thermal Package Resistances						
Thermal Resistance, MSOP-10	$\theta_{JA}$	_	113	_	°C/W	4-Layer JC51-7 Standard Board, Natural Convection
Thermal Resistance, DFN-10, 3 mm x 3 mm	$\theta_{JA}$	_	41	—	°C/W	4-Layer JC51-7 Standard Board, Natural Convectior

## 2.0 TYPICAL PERFORMANCE CURVES

**Note:** The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.

**Note:** Unless otherwise indicated,  $V_{DD}$  = 5.2V,  $V_{REG}$  = 4.20V,  $I_{OUT}$  = 10 mA and  $T_A$ = +25°C, Constant-voltage mode.



FIGURE 2-1:Battery Regulation Voltage $(V_{BAT})$  vs. Supply Voltage  $(V_{DD})$ .



**FIGURE 2-2:** Battery Regulation Voltage  $(V_{BAT})$  vs. Ambient Temperature  $(T_A)$ .



**FIGURE 2-3:** Output Leakage Current  $(I_{DISCHARGE})$  vs. Battery Regulation Voltage  $(V_{BAT})$ .



**FIGURE 2-4:** Charge Current  $(I_{OUT})$  vs. Programming Resistor  $(R_{PROG})$ .



**FIGURE 2-5:** Charge Current  $(I_{OUT})$  vs. Supply Voltage  $(V_{DD})$ .



**FIGURE 2-6:** Charge Current  $(I_{OUT})$  vs. Supply Voltage  $(V_{DD})$ .

## **TYPICAL PERFORMANCE CURVES (Continued)**

Note: Unless otherwise indicated,  $V_{DD}$  = 5.2V,  $V_{REG}$  = 4.20V,  $I_{OUT}$  = 10 mA and  $T_A$ = +25°C, Constant-voltage mode.



**FIGURE 2-7:** Charge Current  $(I_{OUT})$  vs. Junction Temperature  $(T_J)$ .



**FIGURE 2-8:** Charge Current  $(I_{OUT})$  vs. Junction Temperature  $(T_J)$ .



FIGURE 2-9:Thermistor Bias Current $(I_{THRERM})$  vs. Supply Voltage ( $V_{DD}$ ).



**FIGURE 2-10:** Thermistor Bias Current  $(I_{THRERM})$  vs. Ambient Temperature  $(T_A)$ .



**FIGURE 2-11:** Power Supply Ripple Rejection (PSRR).



**FIGURE 2-12:** Power Supply Ripple Rejection (PSRR).

## **TYPICAL PERFORMANCE CURVES (Continued)**

Note: Unless otherwise indicated,  $V_{DD}$  = 5.2V,  $V_{REG}$  = 4.20V,  $I_{OUT}$  = 10 mA and  $T_A$ = +25°C, Constant-voltage mode.











Line Transient Response.





Load Transient Response.









FIGURE 2-17: Complete Charge Cycle (180 mA Li-Ion Battery).



FIGURE 2-18: Charge Cycle Start -Preconditioning (180 mAh Li-Ion Battery).

## 3.0 PIN DESCRIPTIONS

Descriptions of the pins are listed in Table 3-1.

Pin	No.	Symbol	Function
DFN-10	MSOP-10	Symbol	Function
1	1	V <sub>DD</sub>	Battery Management Input Supply
2	2	V <sub>DD</sub>	Battery Management Input Supply
3	3	STAT1	Charge Status Output
4	4	STAT2	Charge Status Output
5	5	V <sub>SS</sub>	Battery Management 0V Reference
6	6	PROG	Current Regulation Set and Charge Control Enable
7	7	PG, TE	MCP73833: Power Good output, MCP73834: Timer Enable input
8	8	THERM	Thermistor input
9	9	V <sub>BAT</sub>	Battery Charge Control Output
10	10	V <sub>BAT</sub>	Battery Charge Control Output
11	_	EP	Exposed Thermal Pad (EP); must be connected to V <sub>SS</sub> .

#### TABLE 3-1: PIN FUNCTION TABLE

## 3.1 Battery Management Input Supply (V<sub>DD</sub>)

A supply voltage of [V\_{REG} (typical) + 0.3V] to 6V is recommended. Bypass to V\_{SS} with a minimum of 1  $\mu F.$ 

## 3.2 Charge Status Outputs (STAT1, STAT2)

STAT1 and STAT2 are open-drain logic outputs for connection to a LED for charge status indication. Alternatively, a pull-up resistor can be applied for interfacing to a host microcontroller.

## 3.3 Battery Management 0V Reference (V<sub>SS</sub>)

Connect to negative terminal of battery and input supply.

#### 3.4 Current Regulation Set (PROG)

Preconditioning, fast charge, and termination currents are scaled by placing a resistor from PROG to  $V_{SS}$ .

The charge management controller can be disabled by allowing the PROG input to float.

### 3.5 Power Good Indication (PG) MCP73833 Only

The power good ( $\overline{PG}$ ) option is a pseudo open-drain output. The  $\overline{PG}$  output can sink current, but not source current. However, there is a diode path back to the input, and, as such, the  $\overline{PG}$  output should only be pulled up to the input. The  $\overline{PG}$  output is low whenever the input to the MCP73833 is above the UVLO threshold and greater than the battery voltage.

#### 3.6 Timer Enable Input (TE) MCP73834 Only

The timer enable  $(\overline{\text{TE}})$  input option is used to enable or disable the internal timer. A low signal on this pin enables the internal timer and a high signal disables the internal timer. The TE input can be used to disable the timer when the charger is supplying current to charge the battery and power the system load. The TE input is compatible with 1.8V logic.

#### 3.7 Thermistor Input (THERM)

An internal 50  $\mu$ A current source provides the bias for most common 10 k $\Omega$  negative-temperature coefficient thermistors (NTC). The MCP73833/4 compares the voltage at the THERM pin to factory set thersholds of 1.20V and 0.25V, typically.

## 3.8 Battery Charge Control Output (V<sub>BAT</sub>)

Connect to positive terminal of battery. Drain terminal of internal P-channel MOSFET pass transistor. Bypass to V<sub>SS</sub> with a minimum of 1  $\mu$ F to ensure loop stability when the battery is disconnected.

## 3.9 Exposed Thermal Pad (EP)

There is an internal electrical connection between the Exposed Thermal Pad (EP) and the  $V_{SS}\,\text{pin};$  they must be connected to the same potential.

## 4.0 FUNCTIONAL DESCRIPTION

The MCP73833/4 is a highly advanced linear charge management controller. Refer to the functional block diagram and Figure 4-1 that depicts the operational flow algorithm from charge initiation to completion and automatic recharge.





#### 4.1 Under Voltage Lockout (UVLO)

An internal under voltage lockout (UVLO) circuit monitors the input voltage and keeps the charger in shutdown mode until the input supply rises above the UVLO threshold. The UVLO circuitry has a built-in hysteresis of 100 mV.

In the event a battery is present when the input power is applied, the input supply must rise +150 mV above the battery voltage before the MCP73833/4 becomes operational.

The UVLO circuit places the device in shutdown mode if the input supply falls to within +50 mV of the battery voltage.

The UVLO circuit is always active. At any time the input supply is below the UVLO threshold or within +50 mV of the voltage at the V<sub>BAT</sub> pin, the MCP73833/4 is placed in a shutdown mode.

During any UVLO condition, the battery reverse discharge current shall be less than 2  $\mu A.$ 

#### 4.2 Charge Qualification

For a charge cycle to begin, all UVLO conditions must be met and a battery or output load must be present.

A charge current programming resistor must be connected from PROG to  $V_{SS}$ . If the PROG pin is open or floating, the MCP73833/4 is disabled and the battery reverse discharge current is less than 2  $\mu$ A. In this manner, the PROG pin acts as a charge enable and can be used as a manual shutdown.

If the input supply voltage is above the UVLO threshold, but below  $V_{REG}$ (Typical)+0.3V, the MCP73833/4 will pulse the STAT1 and PG outputs as the device determines if a battery is present.

#### 4.3 Preconditioning

If the voltage at the  $V_{BAT}$  pin is less than the preconditioning threshold, the MCP73833/4 enters a preconditioning or trickle charge mode. The preconditioning threshold is factory set. Refer to **Section 1.0** "**Electrical Characteristics**" for preconditioning threshold options.

In this mode, the MCP73833/4 supplies a percentage of the charge current (established with the value of the resistor connected to the PROG pin) to the battery. The percentage or ratio of the current is factory set. Refer to **Section 1.0** "**Electrical Characteristics**" for preconditioning current options.

When the voltage at the  $V_{BAT}$  pin rises above the preconditioning threshold, the MCP73833/4 enters the constant current or fast charge mode.

#### 4.4 Constant Current - Fast Charge Mode

During the constant current mode, the programmed charge current is supplied to the battery or load. The charge current is established using a single resistor from PROG to  $V_{SS}$ . The program resistor and the charge current are calculated using Equation 4-1:

#### **EQUATION 4-1:**

Where:		$I_{REG} = \frac{1000V}{R_{PROG}}$
R <sub>PROG</sub>	=	kilo-ohms
I <sub>REG</sub>	=	milliampere

Constant current mode is maintained until the voltage at the  $V_{BAT}$  pin reaches the regulation voltage,  $V_{REG}$ .

When constant current mode is invoked, the internal timer is reset.

#### 4.4.1 TIMER EXPIRED DURING CONSTANT CURRENT - FAST CHARGE MODE

If the internal timer expires before the recharge voltage threshold is reached, a timer fault is indicated and the charge cycle terminates. The MCP73833/4 remains in this condition until the battery is removed, the input power is removed, or the PROG pin is opened. If the battery is removed or the PROG pin is opened, the MCP73833/4 enters the Standby mode where it remains until a battery is reinserted or the PROG pin is reconnected. If the input power is removed, the MCP73833/4 is in Shutdown. When the input power is reapplied, a normal start-up sequence ensues.

#### 4.5 Constant Voltage Mode

When the voltage at the  $V_{BAT}$  pin reaches the regulation voltage,  $V_{REG}$ , constant voltage regulation begins. The regulation voltage is factory set to 4.20V, 4.35V, 4.40V, or 4.50V with a tolerance of ± 0.75%.

#### 4.6 Charge Termination

The charge cycle is terminated when, during constant voltage mode, the average charge current diminishes below a percentage of the programmed charge current (established with the value of the resistor connected to the PROG pin) or the internal timer has expired. A 1 ms filter time on the termination comparator ensures that transient load conditions do not result in premature charge cycle termination. The percentage or ratio of the current is factory set. The timer period is factory set and can be disabled. Refer to **Section 1.0 "Electrical Characteristics"** for charge termination current ratio and timer period options.

The charge current is latched off and the MCP73833/4 enters a charge complete mode.

#### 4.7 Automatic Recharge

The MCP73833/4 continuously monitors the voltage at the V<sub>BAT</sub> pin in the charge complete mode. If the voltage drops below the recharge threshold, another charge cycle begins and current is once again supplied to the battery or load. The recharge threshold is factory set. Refer to **Section 1.0 "Electrical Characteristics"** for recharge threshold options.

#### 4.8 Thermal Regulation

The MCP73833/4 limits the charge current based on the die temperature. The thermal regulation optimizes the charge cycle time while maintaining device reliability. Figure 4-2 depicts the thermal regulation for the MCP73833/4.



FIGURE 4-2:

Thermal Regulation.

#### 4.9 Thermal Shutdown

The MCP73833/4 suspends charge if the die temperature exceeds  $+150^{\circ}$ C. Charging will resume when the die temperature has cooled by approximately  $+10^{\circ}$ C. The thermal shutdown is a secondary safety feature in the event that there is a failure within the thermal regulation circuitry.

### 5.0 DETAILED DESCRIPTION

#### 5.1 Analog Circuitry

#### 5.1.1 BATTERY MANAGEMENT INPUT SUPPLY (V<sub>DD</sub>)

The V<sub>DD</sub> input is the input supply to the MCP73833/4. The MCP73833/4 automatically enters a Power-down mode if the voltage on the V<sub>DD</sub> input falls below the UVLO voltage (V<sub>STOP</sub>). This feature prevents draining the battery pack when the V<sub>DD</sub> supply is not present.

#### 5.1.2 CURRENT REGULATION SET (PROG)

Fast charge current regulation can be scaled by placing a programming resistor ( $R_{PROG}$ ) from the PROG input to  $V_{SS}$ . The program resistor and the charge current are calculated using the Equation 5-1:

#### EQUATION 5-1:



The preconditioning trickle-charge current and the charge termination current are ratiometric to the fast charge current based on the selected device options.

#### 5.1.3 BATTERY CHARGE CONTROL OUTPUT (V<sub>BAT</sub>)

The battery charge control output is the drain terminal of an internal P-channel MOSFET. The MCP73833/4 provides constant current and voltage regulation to the battery pack by controlling this MOSFET in the linear region. The battery charge control output should be connected to the positive terminal of the battery pack.

## 5.1.4 TEMPERATURE QUALIFICATION (THERM)

The MCP73833/4 continuously monitors battery temperature during a charge cycle by measuring the voltage between the THERM and V<sub>SS</sub> pins. An internal 50  $\mu$ A current source provides the bias for most common 10 k $\Omega$  negative-temperature coefficient (NTC) or positive-temperature coefficient (PTC) thermistors.The current source is controlled, avoiding measurement sensitivity to fluctuations in the supply voltage (V<sub>DD</sub>). The MCP73833/4 compares the voltage at the THERM pin to factory set thersholds of 1.20V and 0.25V, typically. Once a volage outside the thresholds is detected during a charge cycle, the MCP73833/4 immediately suspends the charge cycle. The MCP73833/4 suspends charge by turning off the

pass transistor and holding the timer value. The charge cycle resumes when the voltage at the THERM pin returns to the normal range.

If temperature monitoring is not required, place a standard 10 k $\Omega$  resistor from THERM to V\_{SS}.

#### 5.1.4.1 System Test (LDO) Mode

The MCP73833/4 can be placed in a system test mode. In this mode, the MCP73833/4 operates as a low dropout linear regulator (LDO). The output voltage is regulated to the factory set voltage regulation option. The available output current is limitted to the programmed fast charge current. For stability, the V<sub>BAT</sub> output must be bypassed to V<sub>SS</sub> with a minimum capacitance of 1  $\mu$ F for output currents up to 250 mA. A minimum capacitance of 4.7  $\mu$ F is required for output currents above 250 mA.

The system test mode is entered by driving the THERM input greater than ( $V_{DD}$ -100 mV) with no battery connected to the output. In this mode, the MCP73833/4 can be used to power the system without a battery present.

**Note 1:** I<sub>THERM</sub> is disabled during shutdown, stand-by, and system test modes.

- 2: A pull-down current source on the THERM input is active only in stand-by and system test modes.
- **3:** During system test mode, the PROG input sets the available output current limit.
- 4: System test mode shall be exited by releasing the THERM input or cycling input power.

## 5.2 Digital Circuitry

#### 5.2.1 STATUS INDICATORS AND POWER GOOD (PG - OPTION)

The charge status outputs have two different states: Low (L), and High Impedance (Hi-Z). The charge status outputs can be used to illuminate LEDs. Optionally, the charge status outputs can be used as an interface to a host microcontroller. Table 5-1 summarize the state of the status outputs during a charge cycle.

TABLE 5-1:STATUS OUTPUTS

Charge Cycle State	STAT1	STAT2	PG
Shutdown	Hi-Z	Hi-Z	Hi-Z
Standby	Hi-Z	Hi-Z	L
Charge in Progress	L	Hi-Z	L
Charge Complete (EOC)	Hi-Z	L	L
Temperature Fault	Hi-Z	Hi-Z	L
Timer Fault	Hi-Z	Hi-Z	L
System Test Mode	L	L	L

#### 5.2.2 POWER GOOD (PG) OPTION

The power good ( $\overline{PG}$ ) option is a pseudo open-drain output. The PG output can sink current, but not source current. However, there is a diode path back to the input, and as such, the PG output should only be pulled up to the input. The PG output is low whenever the input to the MCP73833 is above the UVLO threshold and greater than the battery voltage. If the supply voltage is above the UVLO, but below V<sub>REG</sub>(Typical)+0.3V, the MCP73833 will pulse the PG output as the device determines if a battery is present.

#### 5.2.3 TIMER ENABLE (TE) OPTION

The timer enable  $(\overline{\text{TE}})$  input option is used to enable or disable the internal timer. A low signal on this pin enables the internal timer and a high signal disables the internal timer. The  $\overline{\text{TE}}$  input can be used to disable the timer when the charger is supplying current to charge the battery and power the system load. The  $\overline{\text{TE}}$  input is compatible with 1.8V logic.

#### 5.2.4 DEVICE DISABLE (PROG)

The current regulation set input pin (PROG) can be used to terminate a charge at any time during the charge cycle, as well as to initiate a charge cycle or initiate a recharge cycle.

Placing a programming resistor from the PROG input to  $V_{SS}$  enables the device. Allowing the PROG input to float or by applying a logic-high input signal, disables the device and terminates a charge cycle. When disabled, the device's supply current is reduced to 100 µA, typically.

## 6.0 APPLICATIONS

The MCP73833/4 is designed to operate in conjunction with a host microcontroller or in stand-alone applications. The MCP73833/4 provides the preferred charge algorithm for Lithium-Ion and Lithium-Polymer cells Constant-current followed by Constant-voltage. Figure 6-1 depicts a typical stand-alone application circuit, while Figures 6-2 and 6-3 depict the accompanying charge profile.



FIGURE 6-1:

Typical Application Circuit.







**FIGURE 6-3:** Typical Charge Cycle Start with Thermal Regulation (1700 mAh Li-Ion Battery).

### 6.1 Application Circuit Design

Due to the low efficiency of linear charging, the most important factors are thermal design and cost, which are a direct function of the input voltage, output current and thermal impedance between the battery charger and the ambient cooling air. The worst-case scenario is when the device has transitioned from the Preconditioning mode to the Constant-current mode. In this situation, the battery charger has to dissipate the maximum power. A trade-off must be made between the charge current, cost and thermal requirements of the charger.

#### 6.1.1 COMPONENT SELECTION

Selection of the external components in Figure 6-1 is crucial to the integrity and reliability of the charging system. The following discussion is intended as a guide for the component selection process.

#### 6.1.1.1 Current Programming Resistor (R<sub>PROG</sub>)

The preferred fast charge current for Lithium-Ion cells is at the 1C rate, with an absolute maximum current at the 2C rate. For example, a 500 mAh battery pack has a preferred fast charge current of 500 mA. Charging at this rate provides the shortest charge cycle times without degradation to the battery pack performance or life.

#### 6.1.1.2 Thermal Considerations

The worst-case power dissipation in the battery charger occurs when the input voltage is at the maximum and the device has transitioned from the Preconditioning mode to the Constant-current mode. In this case, the power dissipation is:

PowerDissip	oatio	$n = (V_{DDMAX} - V_{PTHMIN}) \times I_{REGMAX}$	
Where:			
V <sub>DDMAX</sub> I <sub>REGMAX</sub> V <sub>PTHMIN</sub>	= = =	the maximum input voltage the maximum fast charge current the minimum transition threshold voltage	
Power dissipation with a 5V, ±10% input voltage source			

is:

$$PowerDissipation = (5.5V - 2.7V) \times 550mA = 1.54W$$

This power dissipation with the battery charger in the MSOP-10 package will cause thermal regulation to be entered as depicted in Figure 6-3. Alternatively, the DFN-10 (3 mm x 3 mm) package could be utilized to reduce charge cycle times.

#### 6.1.1.3 External Capacitors

The MCP73833/4 is stable with or without a battery load. In order to maintain good AC stability in the Constant-voltage mode, a minimum capacitance of 4.7  $\mu$ F is recommended to bypass the V<sub>BAT</sub> pin to V<sub>SS</sub>. This capacitance provides compensation when there is no battery load. In addition, the battery and interconnections appear inductive at high frequencies. These elements are in the control feedback loop during Constant-voltage mode. Therefore, the bypass capacitance may be necessary to compensate for the inductive nature of the battery pack.

Virtually any good quality output filter capacitor can be used, independent of the capacitor's minimum Effective Series Resistance (ESR) value. The actual value of the capacitor (and its associated ESR) depends on the output load current. A 4.7  $\mu$ F ceramic, tantalum or aluminum electrolytic capacitor at the output is usually sufficient to ensure stability for output currents up to a 500 mA.

#### 6.1.1.4 Reverse-Blocking Protection

The MCP73833/4 provides protection from a faulted or shorted input. Without the protection, a faulted or shorted input would discharge the battery pack through the body diode of the internal pass transistor.

#### 6.1.1.5 Charge Inhibit

The current regulation set input pin (PROG) can be used to terminate a charge at any time during the charge cycle, as well as to initiate a charge cycle or initiate a recharge cycle.

Placing a programming resistor from the PROG input to  $V_{SS}$  enables the device. Allowing the PROG input to float or by applying a logic-high input signal, disables the device and terminates a charge cycle. When disabled, the device's supply current is reduced to 100 µA, typically.

#### 6.1.1.6 Temperature Monitoring

The charge temperature window can be set by placing fixed value resistors in series-parallel with a thermistor. The resistance values of  $R_{T1}$  and  $R_{T2}$  can be calculated with the following equations in order to set the temperature window of interest.

For NTC thermistors:

$$24k\Omega = R_{TI} + \frac{R_{T2} \times R_{COLD}}{R_{T2} + R_{COLD}}$$
$$5k\Omega = R_{T1} + \frac{R_{T2} \times R_{HOT}}{R_{T2} + R_{HOT}}$$

Where:

R <sub>T1</sub>	=	the fixed series resistance
$R_{T2}$	=	the fixed parallel resistance
$R_{COLD}$	=	the thermistor resistance at the lower temperature of interest
R <sub>HOT</sub>	=	the thermistor resistance at the upper temperature of interest

For example, by utilizing a 10 k $\Omega$  at 25C NTC thermistor with a sensitivity index,  $\beta$ , of 3892, the charge temperature range can be set to 0C - 50C by placing a 1.54 k $\Omega$  resistor in series (R<sub>T1</sub>), and a 69.8 k $\Omega$  resistor in parallel (R<sub>T2</sub>) with the thermistor as depicted in Figure 6-1.

#### 6.1.1.7 Charge Status Interface

A status output provides information on the state of charge. The output can be used to illuminate external LEDs or interface to a host microcontroller. Refer to Table 5-1 for a summary of the state of the status output during a charge cycle.

#### 6.2 PCB Layout Issues

For optimum voltage regulation, place the battery pack as close as possible to the device's V<sub>BAT</sub> and V<sub>SS</sub> pins, recommended to minimize voltage drops along the high current-carrying PCB traces.

If the PCB layout is used as a heatsink, adding many vias in the heatsink pad can help conduct more heat to the backplane of the PCB, thus reducing the maximum junction temperature. Figures 6-4 and 6-5 depict a typical layout with PCB heatsinking.



FIGURE 6-4:

Typical Layout (Top).



FIGURE 6-5:

Typical Layout (Bottom).

## 7.0 PACKAGING INFORMATION

## 7.1 Package Marking Information

#### 10-Lead DFN (3x3)

	XXXX
	YYWW
0	NNN

Part Number *	Marking Code	Part Number *	Marking Code		
MCP73833-AMI/MF	AAAA				
MCP73833-BZI/MF	AAAB				
MCP73833-FCI/MF	AAAC	MCP73834-FCI/MF	BAAC		
MCP73833-GPI/MF	AAAD	MCP73834-GPI/MF	BAAD		
MCP73833-NVI/MF	AAAF	MCP73834-NVI/MF	BAAF		
MCP73833-6SI/MF	AAAH	MCP73834-6SI/MF	BAAH		
MCP73833-CNI/MF	AAAK	MCP73834-CNI/MF	BAAK		
* Consult Eastery for Alternative Device Ontions					

Example:



<sup>c</sup> Consult Factory for Alternative Device Options.

#### 10-Lead MSOP



Part Number *	Marking Code	Part Number *	Marking Code		
MCP73833-AMI/UN	833AMI				
MCP73833-BZI/UN	833BZI				
MCP73833-FCI/UN	833FCI	MCP73834-FCI/UN	834FCI		
MCP73833-GPI/UN	833GPI	MCP73834-GPI/UN	834GPI		
MCP73833-NVI/UN	833NVI	MCP73834-NVI/UN	834NVI		
MCP73833-CNI/UN	833CNI	MCP73834-CNI/UN	834CNI		
* Consult Fosters for Alternative Device Ontions					



Consult Factory for Alternative Device Options.

Legend	I: XXX Y YY WW NNN ©3 *	Customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC designator for Matte Tin (Sn) This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package.
Note:	be carrie	nt the full Microchip part number cannot be marked on one line, it will d over to the next line, thus limiting the number of available s for customer-specific information.

#### 10-Lead Plastic Dual Flat, No Lead Package (MF) – 3x3x0.9 mm Body [DFN]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units	MILLIMETERS			
Dim	ension Limits	MIN	NOM	MAX	
Number of Pins	N		10		
Pitch	е		0.50 BSC		
Overall Height	А	0.80	0.90	1.00	
Standoff	A1	0.00 0.02 0.05			
Contact Thickness	A3	0.20 REF			
Overall Length	D	3.00 BSC			
Exposed Pad Length	D2	2.20 2.35 2.48			
Overall Width	E	3.00 BSC			
Exposed Pad Width	E2	1.40	1.58	1.75	
Contact Width	b	0.18	0.25	0.30	
Contact Length	act Length L 0.30 0.		0.40	0.50	
Contact-to-Exposed Pad	К 0.20 – –			-	

#### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package may have one or more exposed tie bars at ends.
- 3. Package is saw singulated.
- 4. Dimensioning and tolerancing per ASME Y14.5M.
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-063B



#### 10-Lead Plastic Micro Small Outline Package (UN) [MSOP]

	UTIILS			IVILLIIVIE I ERS			
	Dimension Limits	MIN	NOM	MAX			
Number of Pins	N	10					
Pitch	е		0.50 BSC				
Overall Height	A	-	-	1.10			
Molded Package Thickness	Molded Package Thickness A2 0.75 0.85						
Standoff	A1	0.00 – 0.15					
Overall Width	E	4.90 BSC					
Molded Package Width	E1	3.00 BSC					
Overall Length	D	3.00 BSC					
Foot Length	h L 0.40 0.60		0.80				
Footprint	L1	0.95 REF					
Foot Angle	Angle $\phi$		-	8°			
Lead Thickness	С	0.08	-	0.23			
Lead Width	b	0.15 – 0.33					

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15 mm per side.

3. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-021B

### APPENDIX A: REVISION HISTORY

#### Revision B (May 2009)

The following is the list of modifications:

- 1. Added the MCP73833-6SI/MF and MCP73834-6SI/MF10-lead DFN packages.
- 2. Updated DFN pinout.
- 3. Updated Package Outline Drawings.
- 4. Updated Appendix A Revision History.

#### **Revision A (September 2006)**

• Original Release of this Document.

#### **PRODUCT IDENTIFICATION SYSTEM**

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO. XX	¥ ¥	Examples: * *
Device Outpu Optior	ut Temp. Package ns*	<ul> <li>a) MCP73833-AMI/UN: 10-lead MSOP pkg.</li> <li>b) MCP73833-BZI/UN: 10-lead MSOP pkg.</li> <li>c) MCP73833-CNI/MF: 10-lead DFN pkg.</li> </ul>
Device:	MCP73833: <u>1A</u> Fully Integrated Charger, PG function on pin 7 MCP73833T: <u>1A</u> Fully Integrated Charger, PG function on pin 7 (Tape and Reel) MCP73834: <u>1A</u> Fully Integrated Charger, TE function on pin 7 MCP73834T: <u>1A</u> Fully Integrated Charger, TE function on pin 7 (Tape and Reel)	<ul> <li>d) MCP73833-FCI/UN: 10-lead MSOP pkg.</li> <li>e) MCP73833-GPI/UN: 10-lead MSOP pkg.</li> <li>f) MCP73833-NVI/MF: 10-lead DFN pkg.</li> <li>g) MCP73833-6SI/MF: 10-lead DFN pkg.</li> <li>a) MCP73834-CNI/MF: 10-lead DFN pkg.</li> <li>b) MCP73834-FCI/UN: 10-lead MSOP pkg.</li> <li>c) MCP73834-GPI/UN: 10-lead MSOP pkg.</li> <li>d) MCP73834-OVI/MF: 10-lead DFN pkg.</li> <li>e) MCP73834-SI/MF: 10-lead DFN pkg.</li> </ul>
Output Options * *	<ul> <li>* Refer to table below for different operational options.</li> <li>* * Consult Factory for Alternative Device Options.</li> </ul>	* * Consult Factory for Alternative Device Options
Temperature:	$I = -40^{\circ}C \text{ to } +85^{\circ}C$	
Package Type:	<ul> <li>MF = Plastic Dual Flat No Lead (DFN) (3x3x0.9 mm Body), 10-lead</li> <li>UN = Plastic Micro Small Outline Package (MSOP), 10-lead</li> </ul>	

Part Number	V <sub>REG</sub>	I <sub>PREG</sub> /I <sub>REG</sub>	V <sub>PTH</sub> /V <sub>REG</sub>	I <sub>TERM</sub> /I <sub>REG</sub>	V <sub>RTH</sub> /V <sub>REG</sub>	Timer Period
MCP73833-AMI/MF	4.20V	10%	71.5%	7.5%	96.5%	0 hours
MCP73833-BZI/MF	4.20V	100%	N/A	7.5%	96.5%	0 hours
MCP73833-CNI/MF	4.20V	10%	71.5%	20%	94%	4 hours
MCP73833-FCI/MF	4.20V	10%	71.5%	7.5%	96.5%	6 hours
MCP73833-GPI/MF	4.20V	100%	N/A	7.5%	96.5%	6 hours
MCP73833-NVI/MF	4.35V	10%	71.5%	7.5%	96.5%	6 hours
MCP73833-6SI/MF	4.50V	10%	71.5%	7.5%	96.5%	6 hours
MCP73833-AMI/UN	4.20V	10%	71.5%	7.5%	96.5%	0 hours
MCP73833-FCI/UN	4.20V	10%	71.5%	7.5%	96.5%	6 hours
MCP73834-BZI/MF	4.20V	100%	N/A	7.5%	96.5%	0 hours
MCP73834-CNI/MF	4.20V	10%	71.5%	20%	94%	4 hours
MCP73834-FCI/MF	4.20V	10%	71.5%	7.5%	96.5%	6 hours
MCP73834-NVI/MF	4.35V	10%	71.5%	7.5%	96.5%	6 hours
MCP73834-6SI/MF	4.50V	10%	71.5%	7.5%	96.5%	6 hours
MCP73834-FCI/UN	4.20V	10%	71.5%	7.5%	96.5%	6 hours

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

#### Trademarks

The Microchip name and logo, the Microchip logo, Accuron, dsPIC, KEELOQ, KEELOQ logo, MPLAB, PIC, PICmicro, PICSTART, rfPIC, SmartShunt and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

FilterLab, Hampshire, Linear Active Thermistor, MXDEV, MXLAB, SEEVAL, SmartSensor and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Application Maestro, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, dsSPEAK, ECAN, ECONOMONITOR, FanSense, In-Circuit Serial Programming, ICSP, ICEPIC, Mindi, MiWi, MPASM, MPLAB Certified logo, MPLIB, MPLINK, mTouch, nanoWatt XLP, PICkit, PICDEM, PICDEM.net, PICtail, PIC<sup>32</sup> logo, PowerCal, PowerInfo, PowerMate, PowerTool, REAL ICE, rfLAB, Select Mode, Total Endurance, TSHARC, WiperLock and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

All other trademarks mentioned herein are property of their respective companies.

© 2009, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.



## QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV ISO/TS 16949:2002

Microchip received ISO/TS-16949:2002 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELoQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.



## WORLDWIDE SALES AND SERVICE

#### AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://support.microchip.com Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Cleveland Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

**Dallas** Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Farmington Hills, MI Tel: 248-538-2250 Fax: 248-538-2260

Kokomo Kokomo, IN Tel: 765-864-8360 Fax: 765-864-8387

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Santa Clara Santa Clara, CA Tel: 408-961-6444 Fax: 408-961-6445

Toronto Mississauga, Ontario, Canada Tel: 905-673-0699 Fax: 905-673-6509

#### ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway Harbour City, Kowloon Hong Kong Tel: 852-2401-1200 Fax: 852-2401-3431 Australia - Sydney

Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

**China - Beijing** Tel: 86-10-8528-2100 Fax: 86-10-8528-2104

**China - Chengdu** Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

**China - Hong Kong SAR** Tel: 852-2401-1200 Fax: 852-2401-3431

China - Nanjing Tel: 86-25-8473-2460

Fax: 86-25-8473-2470 China - Qingdao Tel: 86-532-8502-7355

Fax: 86-532-8502-7205 China - Shanghai Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

**China - Shenyang** Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

**China - Shenzhen** Tel: 86-755-8203-2660 Fax: 86-755-8203-1760

**China - Wuhan** Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

**China - Xiamen** Tel: 86-592-2388138 Fax: 86-592-2388130

**China - Xian** Tel: 86-29-8833-7252 Fax: 86-29-8833-7256

**China - Zhuhai** Tel: 86-756-3210040 Fax: 86-756-3210049 ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444 Fax: 91-80-3090-4080

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-2566-1512 Fax: 91-20-2566-1513

**Japan - Yokohama** Tel: 81-45-471- 6166 Fax: 81-45-471-6122

Korea - Daegu Tel: 82-53-744-4301 Fax: 82-53-744-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857 Fax: 60-3-6201-9859

Malaysia - Penang Tel: 60-4-227-8870 Fax: 60-4-227-4068

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-6578-300 Fax: 886-3-6578-370

Taiwan - Kaohsiung Tel: 886-7-536-4818 Fax: 886-7-536-4803

Taiwan - Taipei Tel: 886-2-2500-6610 Fax: 886-2-2508-0102

**Thailand - Bangkok** Tel: 66-2-694-1351 Fax: 66-2-694-1350

#### EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**UK - Wokingham** Tel: 44-118-921-5869 Fax: 44-118-921-5820

03/26/09

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Microchip:

MCP73834T-CNI/UN MCP73833-AMI/UN MCP73833T-FCI/MF MCP73833-BZI/MF MCP73833-AMI/MF MCP73833-BZI/UN MCP73833T-BZI/UN MCP73834T-NVI/MF MCP73833T-FCI/UN MCP73834T-CNI/MF MCP73833T-BZI/MF MCP73833-NVI/MF MCP73834T-NVI/UN MCP73833-NVI/UN MCP73833T-CNI/MF MCP73833T-CNI/UN MCP73833T-AMI/MF MCP73834-NVI/UN MCP73833T-AMI/UN MCP73834-NVI/MF MCP73833-FCI/UN MCP73834T-FCI/MF MCP73834-FCI/MF MCP73833-FCI/MF MCP73834-CNI/UN MCP73833T-NVI/MF MCP73834-CNI/MF MCP73833-CNI/MF MCP73833-CNI/UN MCP73833-FCI/UN MCP73834-FCI/UN MCP73833T-NVI/UN MCP73833-GPI/MF MCP73833-GPI/UN MCP73833T-GPI/MF MCP73833T-GPI/UN MCP73833T-NVI/UN MCP73834-GPI/UN MCP73834T-GPI/MF MCP73834T-GPI/UN