

# **Universal High-Brightness LED Driver**

# **Features**

- · Switch mode controller for single switch LED drivers
- · Enhanced drop-in replacement to the HV9910B
- · Open loop peak current controller
- · Internal 15 to 450V linear regulator
- · Constant frequency or constant off-time operation
- · Linear and PWM dimming capability
- · Requires few external components for operation
- · Over-temperature protection

# **Applications**

- · DC/DC or AC/DC LED driver applications
- · RGB back-lighting LED driver
- · Back lighting of flat panel displays
- · General purpose constant current source
- · Signage and decorative LED lighting
- Chargers

# **Description**

HV9910C is an open-loop, current-mode control, LED driver IC. This IC can be programmed to operate in either a constant frequency or constant off-time mode. It includes a 15-450V linear regulator which allows it to work with a wide range of input voltages without the need for an external low voltage supply. HV9910C includes a TTL-compatible, PWM-dimming input that can accept an external control signal with a duty ratio of 0-100% and a frequency of up to a few kilohertz. It also includes a 0-250mV linear-dimming input which can be used for linear dimming of the LED current. Unlike the HV9910B, the HV9910C is equipped with built-in thermal-shutdown protection.

HV9910C is ideally suited for buck LED drivers. Since the HV9910C operates in open-loop current mode control, the controller achieves good output current regulation without the need for any loop compensation. Also, being an open-loop controller, PWM-dimming response is limited only by the rate of rise of the inductor current, enabling a very fast rise and fall times of the LED current. HV9910C requires only three external components (apart from the power stage) to produce a controlled LED current. This makes HV9910C an ideal solution for low-cost LED drivers.

# TO OUR VALUED CUSTOMERS

It is our intention to provide our valued customers with the best documentation possible to ensure successful use of your Microchip products. To this end, we will continue to improve our publications to better suit your needs. Our publications will be refined and enhanced as new volumes and updates are introduced.

If you have any questions or comments regarding this publication, please contact the Marketing Communications Department via E-mail at **docerrors@microchip.com**. We welcome your feedback.

#### **Most Current Data Sheet**

To obtain the most up-to-date version of this data sheet, please register at our Worldwide Web site at:

#### http://www.microchip.com

You can determine the version of a data sheet by examining its literature number found on the bottom outside corner of any page. The last character of the literature number is the version number, (e.g., DS30000000A is version A of document DS30000000).

#### **Errata**

An errata sheet, describing minor operational differences from the data sheet and recommended workarounds, may exist for current devices. As device/documentation issues become known to us, we will publish an errata sheet. The errata will specify the revision of silicon and revision of document to which it applies.

To determine if an errata sheet exists for a particular device, please check with one of the following:


- · Microchip's Worldwide Web site; http://www.microchip.com
- · Your local Microchip sales office (see last page)

When contacting a sales office, please specify which device, revision of silicon and data sheet (include literature number) you are using.


# **Customer Notification System**

Register on our web site at www.microchip.com to receive the most current information on all of our products.

# Pin Diagram



# **Typical Application Circuit**



# 1.0 ELECTRICAL CHARACTERISTICS

# **ABSOLUTE MAXIMUM RATINGS**

V <sub>IN</sub> to GND	0.5V to +470V
V <sub>DD</sub> to GND	
CS, LD, PWMD, GATE	
Junction temperature	40°C to +125°C
Storage temperature	65°C to +150°C
Continuous power dissipation ( $T_A = +2$ )	5°C)
8-lead SOIC	650 mW
16-lead SOIC	1300 mW
8-lead SOIC with heat slug	1300 mW

**Note**: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions, above those indicated in the operational listings of this specification, is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

# 1.1 ELECTRICAL SPECIFICATIONS

TABLE 1-1: ELECTRICAL CHARACTERISTICS (SHEET 1 OF 2)<sup>1</sup>

Symbol	Parameter	Note	Min	Тур	Max	Units	Conditions
Input							
V <sub>INDC</sub>	Input DC supply voltage range <sup>2</sup>	3	15	-	450	V	DC input voltage
I <sub>IN(MAX)</sub>	Supply current	-	-	0.8	1.5	mA	Pin PWMD to V <sub>DD</sub> , no capacitance at GATE
I <sub>INSD</sub>	Shut-down mode supply current	-	-	0.5	1.0	mA	Pin PWMD to GND
Internal Reg	gulator						
V <sub>DD</sub>	Internally regulated voltage	-	7.25	7.50	7.75	V	$V_{IN}$ = 15V, $I_{DD(ext)}$ = 0, PWMD = $V_{DD}$ , 500pF at GATE; $R_{OSC}$ = 249k $\Omega$
$\Delta V_{DD}$ , line	Line regulation of V <sub>DD</sub>	-	0	-	1.0	V	$V_{IN}$ = 15 - 450V, $I_{DD(ext)}$ = 0, PWMD = $V_{DD}$ , 500pF at GATE; $R_{OSC}$ = 249k $\Omega$
$\Delta V_{DD}$ , load	Load regulation of V <sub>DD</sub>	-	0	-	0.1	V	$I_{DD(ext)} = 0 - 1.0 \text{mA},$ $PWMD = V_{DD}, 500 \text{pF at GATE};$ $ROSC = 249 \text{k}\Omega$
UVLO	V <sub>DD</sub> under voltage lockout threshold	3	6.45	6.70	6.95	V	V <sub>DD</sub> rising
ΔUVLO	V <sub>DD</sub> under voltage lockout hysteresis	-	-	500	-	mV	V <sub>DD</sub> falling
I <sub>IN(MAX)</sub>	Maximum regulator current	4	5.0	-	-	mA	V <sub>DD</sub> = UVLO - ∆UVLO
PWM Dimm	ing						
V <sub>EN(lo)</sub>	PWMD input low voltage	3	-	-	1.0	V	V <sub>IN</sub> = 15 - 450V
V <sub>EN(hi)</sub>	PWMD input high voltage	3	2.4	-	-	V	V <sub>IN</sub> = 15 - 450V
R <sub>EN</sub>	Internal pull-down resistance at PWMD	-	50	100	150	kΩ	V <sub>PWMD</sub> = 5.0V

TABLE 1-1: ELECTRICAL CHARACTERISTICS (CONTINUED) (SHEET 2 OF 2)<sup>1</sup>

Symbol	Parameter	Note	Min	Тур	Max	Units	Conditions
Current Sei	nse Comparator						
V <sub>CS</sub>	Current sense pull-in threshold voltage	-	225	250	275	mV	-40°C < T <sub>A</sub> < +125°C
V <sub>OFFSET</sub>	Offset voltage for LD comparator	3	-12	-	+12	mV	
т	Current sense blanking	1	150	215	280	ns	$0 < T_A < +85$ °C, $V_{LD} = V_{DD}$ , $V_{CS} = V_{CS,TH} + 50$ mV after $T_{BLANK}$
T <sub>BLANK</sub>	interval	ı	145	215	315	115	$ \begin{array}{l} -40 < T_{A} < +125^{\circ}\text{C},  V_{LD} = V_{DD}, \\ V_{CS} = V_{CS,TH} + 50\text{mV after} \\ T_{BLANK} \end{array} $
t <sub>DELAY</sub>	Delay to output	ı	-	80	150	ns	$V_{IN}$ = 15V, VLD = 0.15, $V_{CS}$ = 0 to 0.22V after $t_{BLANK}$
Oscillator							
f	Oscillator fraguency	-	20	25	30	kHz	$R_{OSC}$ = 1.00M $\Omega$
f <sub>OSC</sub>	Oscillator frequency	1	80	100	120	KIIZ	$R_{OSC}$ = 249k $\Omega$
Gate Driver	•						
I <sub>SOURCE</sub>	Maximum GATE sourcing current	-	0.165	-	-	А	V <sub>GATE</sub> = 0V
I <sub>SINK</sub>	Maximum GATE sinking current	-	0.165	-	-	Α	V <sub>GATE</sub> = V <sub>DD</sub>
t <sub>RISE</sub>	GATE output rise time	4	-	30	50	ns	C <sub>GATE</sub> = 500pF
t <sub>FALL</sub>	GATE output fall time	4	-	30	50	ns	C <sub>GATE</sub> = 500pF
Over-Temp	erature Protection						
T <sub>SD</sub>	Shut-down temperature	-	128	-	150	°C	
$\Delta T_{SD}$	Hysteresis	ı	10	-	30	°C	
I <sub>SD</sub>	T <sub>SD</sub> -mode V <sub>IN</sub> current	-	-	-	350	μA	

- 1 Specifications are  $T_A = 25^{\circ}C$ ,  $V_{IN} = 15V$  unless otherwise noted.
- 2 Also limited by package-power dissipation limit; Whichever is lower.
- 3 Applies over the full operating ambient temperature range of -40°C <  $T_A$  < +125°C.
- 4 For design guidance only.

TABLE 1-2: THERMAL RESISTANCE

Package	θја
8-Lead SOIC	101°C/W
16-Lead SOIC	83°C/W
8-Lead SOIC (with heat slug)	84°C/W

# 2.0 PIN DESCRIPTION

The descriptions of the pins are listed in Table 2-1.

TABLE 2-1: PIN DESCRIPTION

			1						
Piı	n #	Function	Description						
8-Lead SOIC	16-Lead SOIC	Tunction	Description						
1	1	VIN	Input of an 15 - 450V linear regulator.						
2	4	CS	Current sense pin used to sense the FET current by means of an external sense resistor. When this pin exceeds the lower of either the internal 250mV or the voltage at the LD pin, the GATE output goes low.						
3	5	GND	Ground return for all internal circuitry. Must be electrically connected to the power ground.						
4	8	GATE	Output GATE driver for an external N-channel power MOSFET.						
5	9	PWMD	TTL-compatible, PWM-dimming input of the IC. When this pin is pulled to GND or left open, the GATE driver is turned off. When the pin is pulled high, the GATE driver operates normally.						
6	12	VDD	Power supply pin for all internal circuits. It must be bypassed with a low ESR capacitor to GND (≥0.1µF).						
7	13	LD	Linear-dimming input and sets the current sense threshold as long as the voltage at the pin is less than 250mV (typ).						
8	14	RT	Sets the oscillator frequency. When a resistor is connected between RT and GND, the HV9910C operates in constant frequency mode. When the resistor is connected between RT and GATE, the IC operates in constant off-time mode.						
-	2, 3, 6, 7, 10, 11, 15, 16	NC	No connection						

# 3.0 APPLICATION INFORMATION

HV9910C is optimized to drive buck LED drivers using open-loop, peak-current mode control. This method of control enables fairly accurate LED current control without the need for high side current sensing or the design of any closed loop controllers. The IC uses very few external components and enables both Linear and PWM-dimming of the LED current.

A resistor connected to the RT pin programs the frequency of operation (or the off-time). The oscillator produces pulses at regular intervals. These pulses set the SR flip-flop in the HV9910C which causes the GATE driver to turn on. The same pulses also start the blanking timer, which inhibits the reset input of the SR flip flop and prevents false turn-offs due to the turn-on spike. When the FET turns on, the current through the inductor starts ramping up. This current flows through the external sense resistor, R<sub>CS</sub>, and produces a ramp voltage at the CS pin. The comparators are constantly comparing the CS pin voltage to both the voltage at the LD pin and the internal 250mV. Once the blanking timer is complete, the output of these comparators is allowed to reset the flip-flop. When the output of either one of the two comparators goes high, the flip-flop is reset and the GATE output goes low. The GATE goes low until the SR flip-flop is set by the oscillator. Assuming a 30% ripple in the inductor, the current sense resistor R<sub>CS</sub> can be set using:

$$R_{CS} = \frac{0.25V(orV_{LD})}{1.15 \bullet I_{LED}}$$

Constant frequency peak current mode control has an inherent disadvantage - at duty cycles greater than 0.5, the control scheme goes into subharmonic oscillations. To prevent this, an artificial slope is typically added to the current sense waveform. This slope compensation scheme will affect the accuracy of the LED current in the present form. However, a constant offtime peak current control scheme does not have this problem and can easily operate at duty cycles greater than 0.5. This control scheme also gives inherent input voltage rejection, making the LED current almost insensitive to input voltage variations. However, this scheme leads to variable frequency operation and the frequency range depends greatly on the input and output voltage variation. Using HV9910C, it is easy to switch between the two modes of operation by changing one connection (see Section 3.3 "Oscillator").

# 3.1 Input Voltage Regulator

HV9910C can be powered directly from its  $V_{IN}$  pin and can work from 15 - 450VDC at its  $V_{IN}$  pin. When a voltage is applied at the  $V_{IN}$  pin, HV9910C maintains a constant 7.5V at the  $V_{DD}$  pin. This voltage is used to power the IC and any external-resistor dividers needed

to control the IC. The V<sub>DD</sub> pin must be bypassed by a low-ESR capacitor to provide a low impedance path for the high frequency current of the output GATE driver.

HV9910C can also be operated by supplying a voltage at the  $V_{DD}$  pin greater than the internally regulated voltage. This will turn off the internal linear regulator of the IC and the HV9910C will operate directly off the voltage supplied at the  $V_{DD}$  pin. This external voltage at the  $V_{DD}$  pin should not exceed 12V.

Although the V<sub>IN</sub> pin of the HV9910C is rated up to 450V, the actual maximum voltage that can be applied is limited by the power dissipation in the IC. For example, if an 8-lead SOIC HV9910C (junction to ambient thermal resistance  $R_{\theta j\text{-}a}$  = 101°C/W) draws about  $I_{IN}$  = 2.0mA from the V<sub>IN</sub> pin, and has a maximum allowable temperature rise of the junction temperature limited to  $\Delta T$  = 75°C, the maximum voltage at the V<sub>IN</sub> pin would be

$$V_{IN(MAX)} = \frac{\Delta T}{R_{\Theta ja}} \bullet \frac{1}{I_{IN}}$$
$$= \frac{75^{\circ}C}{101^{\circ}C/W} \bullet \frac{1}{2mA}$$
$$= 371V$$

In these cases, to operate HV9910C from higher input voltages, a Zener diode can be added in series with the  $V_{IN}$  pin to divert some of the power loss from HV9910C to the Zener diode. In the above example, using a 100V Zener diode will allow the circuit to easily work up to 450V.

**Note:** The Zener diode will increase the minimum input voltage required to turn on the HV9910C to 115V.

The input current drawn from the  $V_{\rm IN}$  pin is a sum of the 1.5mA (maximum) current drawn by the internal circuit and the current drawn by the GATE driver. The GATE driver depends on the switching frequency and the GATE charge of the external FET.

$$I_{IN} = 1.5 \text{mA} + Q_g \bullet f_s$$

In the above equation,  $f_s$  is the switching frequency and  $Q_g$  is the GATE charge of the external FET, which can be obtained from the data sheet of the FET.

#### 3.2 Current Sense

The current sense input of HV9910C goes to the non-inverting inputs of two comparators. The inverting terminal of one comparator is tied to an internal 250mV reference, whereas the inverting terminal of the other comparator is connected to the LD pin. The outputs of both these comparators are fed into an OR GATE and

the output of the OR GATE is fed into the reset pin of the flip-flop. Thus, the comparator which has the lowest voltage at the inverting terminal determines when the GATE output is turned off.

The outputs of the comparators also include a 150-280ns blanking time which prevents spurious turn-offs of the external FET due to the turn-on spike normally present in peak-current mode control. In rare cases, this internal blanking might not be enough to filter out the turn-on spike. In these instances, an external RC filter needs to be added between the external sense resistor (RCS) and the CS pin.

Please note that the comparators are fast (with a typical 80ns response time). A proper layout minimizing external inductances will prevent false triggering of these comparators.

# 3.3 Oscillator

The oscillator in HV9910C is controlled by a single resistor connected at the RT pin. The equation governing the oscillator time period  $T_{\rm osc}$  is given by:

$$T_{OSC}(\mu s) = \frac{R_{OSC}(k\Omega)}{25}$$

If the resistor is connected between RT and GND, HV9910C operates in a constant frequency mode and the above equation determines the time period. If the resistor is connected between RT and GATE, HV9910C operates in a constant off-time mode and the above equation determines the off-time.

# 3.4 Gate Output

The gate output of the HV9910C is used to drive an external FET. It is recommended that the GATE charge of the external FET be less than 25nC for switching frequencies ≤ 100kHz and less than 15nC for switching frequencies > 100kHz.

# 3.5 Linear Dimming

The Linear Dimming pin is used to control the LED current. There are two cases when it may be necessary to use the Linear Dimming pin.

- In some cases, when using the internal 250mV, it may not be possible to find the exact R<sub>CS</sub> value required to obtain the LED current. In these cases, an external voltage divider from the V<sub>DD</sub> pin can be connected to the LD pin to obtain a voltage (less than 250mV) corresponding to the desired voltage across RCS.
- Linear dimming may be desired to adjust the current level to reduce the intensity of the LEDs. In these cases, an external 0-250mV voltage

can be connected to the LD pin to adjust the LED current during operation.

To use the internal 250mV, the LD pin can be connected to  $\ensuremath{V_{DD}}.$ 

Note:

Although the LD pin can be pulled to GND, the output current will not go to zero. This is due to the presence of a minimum ontime, which is equal to the sum of the blanking time and the delay to output time, or about 450ns. This minimum on-time causes the FET to be on for a minimum of 450ns, and thus the LED current when LD = GND is not zero. This current is also dependent on the input voltage, inductance value, forward voltage of the LEDs, and circuit parasitics. To get zero LED current, the PWMD pin has to be used.

# 3.6 PWM Dimming


PWM Dimming can be achieved by driving the PWMD pin with a low frequency square wave signal. When the PWM signal is zero, the GATE driver is turned off; when the PWMD signal if high, the GATE driver is enabled. The PWMD signal does not turn off the other parts of the IC, therefore, the response of HV9910C to the PWMD signal is almost instantaneous. The rate of rise and fall of the LED current is thus determined solely by the rise and fall times of the inductor current.

To disable PWM Dimming and enable the HV9910C permanently, connect the PWMD pin to  $V_{DD}$ .

# 3.7 Over-Temperature Protection

The auto-recoverable thermal shutdown at 140°C (typ.) junction temperature with 20°C hysteresis is featured to avoid thermal runaway. When the junction temperature reaches  $T_{SD}$  = 140°C (typ.), HV9910C enters a low power consumption shut-down mode with  $I_{IN}$  <350µA.


FIGURE 3-1: INTERNAL BLOCK DIAGRAM




# 4.0 PACKAGING INFORMATION

# 4.1 Package Marking Information

# 8-Lead SOIC



#### 16-Lead SOIC



X = Product Code

YY = Year Sealed

WW = Week Sealed


NNN = Traceability Code

e# = JEDEC Symbol

• = Pin 1 Indicator

Note: The JEDEC environmental marking symbols (e#) illustrated are examples only, and might not reflect the actual value for the listed package code.

FIGURE 4-1: 8-LEAD SOIC (NARROW BODY) PACKAGE OUTLINE (LG)



#### Notes:

1. This chamfer feature is optional. A Pin 1 identifier must be located in the index area indicated. The Pin 1 identifier can be: a molded mark/identifier; an embedded metal marker; or a printed indicator.

Symb	ol	Α	A1	A2	b	D	Е	E1	е	h	L	L1	L2	θ	θ1
Dimension	MIN	1.35*	0.10	1.25	0.31	4.80*	5.80*	3.80*	4.07	0.25	0.40	4.04	0.05	0°	5°
	NOM	-	-	-	-	4.90	6.00	3.90	1.27 BSC	-	-	1.04 REF	0.25 BSC	-	-
(mm)	MAX	1.75	0.25	1.65*	0.51	5.00*	6.20*	4.00*	ВОО	0.50	1.27		ВОО	8°	15°


JEDEC Registration MS-012, Variation AA, Issue E, Sep 2005.

Drawings not to scale.

<sup>\*</sup> This dimension is not specified in the JEDEC drawing.

<sup>†</sup> This dimension differs from the JEDEC drawing.

FIGURE 4-2: 16-LEAD SOIC (NARROW BODY) PACKAGE OUTLINE (NG)



#### Notes:

1. This chamfer feature is optional. A Pin 1 identifier must be located in the index area indicated. The Pin 1 identifier can be: a molded mark/identifier; an embedded metal marker; or a printed indicator.

Symb	ol	Α	A1	A2	b	D	Е	E1	е	h	L	L1	L2	θ	θ1
Dimension	MIN	1.35*	0.10	1.25	0.31	9.80*	5.80*	3.80*	1 27	0.25	0.40	1.01	0.05	0°	5°
	NOM	-	-	-	-	9.90	6.00	3.90	1.27 BSC	-	-	1.04 REF	0.25 BSC	-	-
(mm)	MAX	1.75	0.25	1.65*	0.51	10.00*	6.20*	4.00*	500	0.50	1.27	111	500	8°	15°


JEDEC Registration MS-012, Variation AC, Issue E, Sep 2005.

<sup>\*</sup> This dimension is not specified in the JEDEC drawing.

<sup>†</sup> This dimension differs from the JEDEC drawing.

Drawings not to scale.

FIGURE 4-3: 8-LEAD SOIC (NARROW BODY) PACKAGE OUTLINE (SG)



# Notes:

1. This chamfer feature is optional. A Pin 1 identifier must be located in the index area indicated. The Pin 1 identifier can be: a molded mark/identifier; an embedded metal marker; or a printed indicator.

Symb	ol	Α	A1	A2	b	D	D1	Е	E1	E2	е	h	L	L1	L2	θ	θ1
Dimension	MIN	1.25*	0.00	1.25	0.31	4.80*	3.30†	5.80*	3.80*	2.29†		0.25	0.40	4.04	0.05	0°	5°
	NOM	-	-	-	-	4.90	-	6.00	3.90	-	1.27 BSC	-	-	1.04 REF	0.25 BSC	-	-
(mm)	MAX	1.70	0.15	1.55*	0.51	5.00*	3.81†	6.20*	4.00*	2.79†	200	0.50	1.27	1 1	200	8°	15°

JEDEC Registration MS-012, Variation BA, Issue E, Sep 2005.

Drawings not to scale.

<sup>\*</sup> This dimension is not specified in the JEDEC drawing.

<sup>†</sup> This dimension differs from the JEDEC drawing.

# **APPENDIX A: REVISION HISTORY**

# Revision A (August 2014)

• Original Release of this Document.

# THE MICROCHIP WEB SITE

Microchip provides online support via our WWW site at www.microchip.com. This web site is used as a means to make files and information easily available to customers. Accessible by using your favorite Internet browser, the web site contains the following information:

- Product Support Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- General Technical Support Frequently Asked Questions (FAQ), technical support requests, online discussion groups, Microchip consultant program member listing
- Business of Microchip Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

# CUSTOMER CHANGE NOTIFICATION SERVICE

Microchip's customer notification service helps keep customers current on Microchip products. Subscribers will receive e-mail notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, access the Microchip web site at www.microchip.com. Under "Support", click on "Customer Change Notification" and follow the registration instructions.

# **CUSTOMER SUPPORT**

Users of Microchip products can receive assistance through several channels:

- · Distributor or Representative
- · Local Sales Office
- Field Application Engineer (FAE)
- · Technical Support

Customers should contact their distributor, representative or Field Application Engineer (FAE) for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in the back of this document.

Technical support is available through the web site at: http://microchip.com/support

# PRODUCT IDENTIFICATION SYSTEM

 $\label{thm:condition} \mbox{To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales of fice. \\$ 

	XX - X - X	a	Examples: a) HV9910CLG-G:	8-lead SOIC package, 2500/Reel.
	p.i.o.i.o	b	) HV9910CNG-G	16-lead SOIC package, 45/Tube
Device:	HV9910C= Universal High-Brightness LED Driver	С	HV9910CNG-G-M934:	16-lead SOIC package, 2500/Reel.
		d	l) HV9910CSG-G:	8-lead SOIC package
Package:	LG = 8-lead SOIC			with heat slug, 2500/Reel.
	NG = 16-lead SOIC			2000/1 (00).
	SG = 8-lead SOIC with head slug			
Environmental	G = Lead (Pb)-free/ROHS-compliant package			
Reel:	(nothing) = Reel for LG and SG packages, Tube for NG package			
	M934 = Reel for NG package			

# Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

# QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

#### **Trademarks**

The Microchip name and logo, the Microchip logo, dsPIC, FlashFlex, KEELOQ, KEELOQ logo, MPLAB, PIC, PICmicro, PICSTART, PIC<sup>32</sup> logo, rfPIC, SST, SST Logo, SuperFlash and UNI/O are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

FilterLab, Hampshire, HI-TECH C, Linear Active Thermistor, MTP, SEEVAL and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

Analog-for-the-Digital Age, Application Maestro, BodyCom, chipKIT, chipKIT logo, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, dsSPEAK, ECAN, ECONOMONITOR, FanSense, HI-TIDE, In-Circuit Serial Programming, ICSP, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mTouch, Omniscient Code Generation, PICC, PICC-18, PICDEM, PICDEM.net, PICkit, PICtail, REAL ICE, rfLAB, Select Mode, SQI, Serial Quad I/O, Total Endurance, TSHARC, UniWinDriver, WiperLock, ZENA and Z-Scale are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the  $\mbox{U.S.A.}$ 

GestIC and ULPP are registered trademarks of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2014, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

Printed on recycled paper.

ISBN: 978-1-63276-529-1

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.



# **Worldwide Sales and Service**

#### **AMERICAS**

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199

Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/

support
Web Address:

www.microchip.com

Atlanta

Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

**Boston** 

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

Cleveland

Independence, OH Tel: 216-447-0464 Fax: 216-447-0643

Dallas

Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI

Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323

Fax: 317-773-5453

Los Angeles

Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

New York, NY Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110

**Canada - Toronto** Tel: 905-673-0699 Fax: 905-673-6509

#### ASIA/PACIFIC

**Asia Pacific Office** 

Suites 3707-14, 37th Floor Tower 6, The Gateway Harbour City, Kowloon Hong Kong

Tel: 852-2943-5100 Fax: 852-2401-3431

**Australia - Sydney** Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

**China - Beijing** Tel: 86-10-8569-7000 Fax: 86-10-8528-2104

**China - Chengdu** Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

**China - Chongqing** Tel: 86-23-8980-9588 Fax: 86-23-8980-9500

**China - Hangzhou** Tel: 86-571-8792-8115 Fax: 86-571-8792-8116

China - Hong Kong SAR Tel: 852-2943-5100 Fax: 852-2401-3431

**China - Nanjing** Tel: 86-25-8473-2460 Fax: 86-25-8473-2470

**China - Qingdao** Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

**China - Shanghai** Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

**China - Shenyang** Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

**China - Shenzhen** Tel: 86-755-8864-2200 Fax: 86-755-8203-1760

**China - Wuhan** Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

**China - Xian** Tel: 86-29-8833-7252 Fax: 86-29-8833-7256

**China - Xiamen**Tel: 86-592-2388138
Fax: 86-592-2388130 **China - Zhuhai** 

Tel: 86-756-3210040 Fax: 86-756-3210049

#### ASIA/PACIFIC

**India - Bangalore** Tel: 91-80-3090-4444

Fax: 91-80-3090-4123 India - New Delhi

Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

**India - Pune** Tel: 91-20-3019-1500

**Japan - Osaka** Tel: 81-6-6152-7160 Fax: 81-6-6152-9310

**Japan - Tokyo** Tel: 81-3-6880- 3770 Fax: 81-3-6880-3771

Korea - Daegu Tel: 82-53-744-4301 Fax: 82-53-744-4302 Korea - Seoul

Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Kuala Lumpur Tel: 60-3-6201-9857

**Malaysia - Penang** Tel: 60-4-227-8870 Fax: 60-4-227-4068

Fax: 60-3-6201-9859

**Philippines - Manila** Tel: 63-2-634-9065 Fax: 63-2-634-9069

**Singapore** Tel: 65-6334-8870 Fax: 65-6334-8850

**Taiwan - Hsin Chu** Tel: 886-3-5778-366 Fax: 886-3-5770-955

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600 Fax: 886-2-2508-0102 **Thailand - Bangkok** 

Tel: 66-2-694-1351 Fax: 66-2-694-1350

### **EUROPE**

Austria - Wels

Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

**Denmark - Copenhagen** Tel: 45-4450-2828

Fax: 45-4485-2829

**France - Paris** Tel: 33-1-69-53-63-20

Fax: 33-1-69-30-90-79 **Germany - Dusseldorf** 

Tel: 49-2129-3766400

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Pforzheim Tel: 49-7231-424750

Italy - Milan

Tel: 39-0331-742611 Fax: 39-0331-466781

**Italy - Venice** Tel: 39-049-7625286

**Netherlands - Drunen** Tel: 31-416-690399 Fax: 31-416-690340

Poland - Warsaw Tel: 48-22-3325737

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820

03/25/14

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Microchip:

HV9910CLG-G HV9910CNG-G HV9910CNG-G M934 HV9910CNG-G-M934 HV9910CSG-G