

## 4-Channel, 205V, High-Voltage Amplifiers Array

### Features

- Four Independent High Voltage Amplifiers
- Up to +205 V Output Voltage
- Gain of 82 V/V with Internal Feedback Resistors
- 0.02 V/ $\mu$ s Minimum Output Slew Rate
- Less than 10 ms Settling Time
- Less than 1 k $\Omega$  Output Impedance
- Up to 200 pF Output Load
- 30 kHz Gain Bandwidth Product
- 24-lead TSSOP Package

### Application

- MEMS Driver


### General Description

The HV265 device is a 4-channel high-voltage operational amplifier array with an optional internal feedback resistor network.

The amplifier array IC operates on a 225 V high-voltage supply and a 5 V low-voltage supply. Each channel has its independent input and output ports. When the internal feedback resistor network is used, the closed-loop gain is set to 82 V/V. High value SiCr resistors are used for internal feedback networks to minimize the power consumption. The input accepts voltage in the range of 0.05V and 2.5V.


The output impedance of the amplifier is less than 1 k $\Omega$  and the output can drive a capacitive load up to 200 pF. The amplifier is designed to have good temperature stability and low output drift.

### Typical Application Circuit




# HV265

## Package Types (Top View)



## Block Diagram



NOTES:

## 1.0 ELECTRICAL CHARACTERISTICS

### Absolute Maximum Ratings †

Low supply voltage ( $V_{DD}$ )	-0.5V to 6.5V
High supply voltage ( $V_{PP}$ )	-0.5V to 250V
Input analog voltage ( $V_{IN}$ )	-0.3V to $V_{DD}$
Maximum junction temperature	+125°C
Storage temperature	-65°C to +150°C
ESD Rating low voltage pins	2 kV HBM, 500 V CDM, 750 V CDM corner lead
ESD Rating high voltage pins	500 V HBM, 500 V CDM, 750 V CDM corner lead

† **Notice:** Stresses above those listed under “Maximum Ratings” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

**TABLE 1-1: OPERATING SUPPLY VOLTAGES**

<b>Electrical Specifications:</b> Unless otherwise specified: $T_A = +25^\circ\text{C}$ . <b>Boldface</b> specifications apply over the $T_A$ range of -40 to +85°C.						
Parameter	Sym.	Min.	Typ.	Max.	Units	Conditions
High Voltage Supply	$V_{PP}$	50	—	225	V	<b>Note 1</b>
Low Voltage Supply	$V_{DD}$	4.5	5.0	5.5	V	

**Note 1:** Specification is obtained by characterization and is not 100% tested.

### ELECTRICAL CHARACTERISTICS

<b>Electrical Specifications:</b> unless otherwise specified, $V_{DD} = 5.0\text{V}$ , $V_{PP} = 225\text{V}$ , $T_A = +25^\circ\text{C}$ .						
Parameter	Sym.	Min.	Typ.	Max.	Units	Conditions
Input Ground Range	$R_{GND}$	0	0	$V_{DD}$	V	
Input Analog Voltage	$V_{IN}$	0	—	3.3	V	
Quiescent $V_{PP}$ Supply Current	$I_{PPQ}$	—	300	500	$\mu\text{A}$	$V_{IN} = 0$ or 5V
Quiescent $V_{DD}$ Supply Current	$I_{DDQ}$	—	3	5	mA	$V_{IN} = 0$ or 5V
$V_{PP}$ Supply Current	$I_{PP}$	—	—	<b>500</b>	$\mu\text{A}$	$V_{IN} = 2V_{P-P}$ 100 Hz sine, $C_L = 200$ pF
$V_{DD}$ Supply Current	$I_{DD}$	—	—	<b>5</b>	mA	$V_{IN} = 2V_{P-P}$ 100 Hz sine, $C_L = 200$ pF
HV <sub>OUT</sub> Output Voltage Range	HV <sub>OUT</sub>	<b>1.85</b>		<b><math>V_{PP} - 10</math></b>	V	$C_L = 200$ pF
HV <sub>OUT</sub> Sink Current	$I_{SINK}$	3			mA	$C_L = 200$ pF
HV <sub>OUT</sub> Source Current	$I_{SOURCE}$	3			mA	$C_L = 200$ pF
HV <sub>OUT</sub> High Level Output	$V_{OH}$	204.8			V	$C_L = 200$ pF, $V_{IN} = 2.7\text{V}$
HV <sub>OUT</sub> Input DC Offset	HV <sub>OS</sub>			$\pm 16$	mV	<b>Note 3</b> $C_L = 200$ pF
HV <sub>OUT</sub> Drift Over Time (Room Temperature)	Drift		$\pm 30$		mV	<b>Note 3</b> $C_L = 200$ pF, $V_{IN} = 2.5\text{V}$
HV <sub>OUT</sub> Temperature Coefficient (Drift Over Temperature)	Temp.		$\pm 115$		mV	<b>Note 3</b> $C_L = 200$ pF, $V_{IN} = 2.5\text{V}$ , $T_J = -40^\circ\text{C}$ to $85^\circ\text{C}$

**Note 1:** Recommended Operating Conditions:  $V_{IN} = 0\text{V}$ ,  $V_{DD} = 5.0\text{V}$ ,  $V_{PP} = +225\text{V}$  unless noted.  $T_J = 25^\circ\text{C}$

**2:** Design guidance only.

**3:** Specification is obtained by characterization and is not 100% tested.

## AC ELECTRICAL CHARACTERISTICS

Electrical Specifications: unless otherwise specified, $V_{DD} = 5.0V$ , $V_{PP} = 225V$ , $T_A = +25^{\circ}C$ .						
Parameter	Sym.	Min.	Typ.	Max.	Units	Conditions
HV <sub>OUT</sub> Output Impedance	$Z_{OUT}$			1000	$\Omega$	<b>Note 3</b> $V_{IN} = 1.25 V_{DC}$ Test Frequency = 100 Hz $C_L = 200$ pF
Gain Bandwidth Product	GBWP	30			kHz	<b>Note 3</b> $C_L = 200$ pF
Slew Rate (HV <sub>OUT</sub> from 10% to 90% and from 90% to 10%)	SR	<b>0.02</b>	-	-	V/ $\mu$ s	$C_L = 200$ pF
Settling Time (Within 1% of final HV <sub>OUT</sub> )	$t_{ST}$			10	ms	<b>Note 3</b> $C_L = 200$ pF, $V_{IN} = 0$ to 2.4 V
Feedback Impedance $R_f + R_i$	$R_{FB}$	4.9	7.0	-	M $\Omega$	<b>Note 2</b>
Closed Loop Gain (dVo/dVin) (Internal Feedback Resistor Network)	$A_V$	<b>75.4</b>	<b>82</b>	<b>88.4</b>	V/V	$C_L = 200$ pF
HV <sub>OUT</sub> Capacitive Load	$C_L$	0		200	pF	<b>Note 2</b>
Output Referred Noise	$V_N$			10	mV <sub>RMS</sub>	<b>Note 3</b> Noise from 1 Hz to 10 kHz.
$V_{DD}$ Power Supply Rejection	PSRR1	30			dB	<b>Note 3</b> 1 kHz
$V_{PP}$ Power Supply Rejection	PSRR2	50			dB	<b>Note 3</b> 1 kHz
Crosstalk Rejection	Xtalk	80			dB	<b>Note 3</b> $V_{IN} = 0$ to 2.5V 100 Hz sine, $C_L = 200$ pF

**Note 1:** Recommended Operating Conditions:  $V_{IN}=0V$ ,  $V_{DD}=5.0V$ ,  $V_{PP}=+225V$  unless noted.  $T_J=25^{\circ}C$

**2:** Design guidance only.


**3:** Specification is obtained by characterization and is not 100% tested.

## TEMPERATURE SPECIFICATIONS


Electrical Specifications: unless otherwise specified, $V_{DD} = 5.0V$ , $V_{PP} = 225V$						
Parameters	Sym.	Min.	Typ.	Max.	Units	Conditions
<b>Temperature Ranges</b>						
Operating Junction Temperature Range	$T_J$	-40	—	+85	°C	
Maximum Junction Temperature	$T_{J(MAX)}$	—	—	+125	°C	
Storage Temperature Range	$T_A$	-65	—	+150	°C	
<b>Package Thermal Resistances</b>						
Thermal Resistance, 24L-TSSOP	$\theta_{JA}$	—	87	—	°C/W	

## 1.1 Typical Performance Curves


**Note:** The graphs and tables provided below are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g. outside specified power supply range) and therefore outside the warranted range.




**FIGURE 1-1:** Typical Small-Signal Pulse Response ( $V_{IN}=0.9\sim 1.1V$  pulse 100 Hz.  $C_L=200$  pF).




**FIGURE 1-4:** Typical Fall Time ( $V_{IN} = 0\sim 2V$  Pulse 100 Hz.  $C_L=200$  pF).




**FIGURE 1-2:** Typical Large-Signal Pulse Response ( $V_{IN} = 0\sim 2V$  pulse 100 Hz.  $C_L=200$  pF).



**FIGURE 1-5:** Typical Bode Plot of Small Signal Input ( $V_{IN}=100$  mVp-p with 1.25 VDC).




**FIGURE 1-3:** Typical Rise Time ( $V_{IN} = 0\sim 2V$  Pulse 100 Hz.  $C_L=200$  pF).




**FIGURE 1-6:** Typical Crosstalk Rejection vs Frequency.


**Note:** The graphs and tables provided below are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g. outside specified power supply range) and therefore outside the warranted range.




**FIGURE 1-7:** Typical Crosstalk Rejection in Time Domain (Source  $V_{IN} = 0\sim 2.5V$  Sine).




**FIGURE 1-10:** Typical  $HV_{OUT}$  Drift Over Time.  $V_{PP}=225V$ ,  $V_{DD}=5.0V$ ,  $V_{IN}=2.5V$  @  $T_A=25^\circ C$ .




**FIGURE 1-8:** Distribution of Input Offset at  $T_A = 25^\circ C$ .



**FIGURE 1-11:** Typical Power Supply Rejection from  $V_{DD}$  vs Frequency.



**FIGURE 1-9:** Distribution of Typical  $HV_{OUT}$  Drift Over Temperature ( $V_{IN} = 2.5VDC$  in Reference to  $T_A = 20^\circ C$ ).



**FIGURE 1-12:** Typical Power Supply Rejection from  $V_{PP}$  vs Frequency.



NOTES:

## 2.0 PIN DESCRIPTION

The descriptions of the pins are listed in [Table 2-1](#).

**TABLE 2-1: PIN FUNCTION TABLE**

Pin Number	Symbol	Description
1	V <sub>IN1</sub>	Amplifier Input 1
2	RGND1	Resistor Ground 1. Typically grounded.
3	GND	Low Voltage Ground
4	V <sub>IN2</sub>	Amplifier Input 2
5	RGND2	Resistor Ground 2. Typically grounded.
6	VDD	Positive Low Voltage Supply
7	GND	Low Voltage Ground
8	V <sub>IN3</sub>	Amplifier Input 3
9	RGND3	Resistor Ground 3. Typically grounded.
10	GND	Low Voltage Ground
11	V <sub>IN4</sub>	Amplifier Input 4
12	RGND4	Resistor Ground 4. Typically grounded.
13	NC	No Connection
14	FB4	Feedback Input 4
15	HV <sub>OUT4</sub>	High Voltage Output 4
16	FB3	Feedback Input 3
17	HV <sub>OUT3</sub>	High Voltage Output 3
18	HVGND	High Voltage Ground
19	VPP	Positive High Voltage Supply
20	FB2	Feedback Input 2
21	HV <sub>OUT2</sub>	High Voltage Output 2
22	FB1	Feedback Input 1
23	HV <sub>OUT1</sub>	High Voltage Output 1
24	NC	No Connection

### 3.0 DEVICE DESCRIPTION

#### 3.1 Power-On/Power-Off Sequence

The device can be damaged by an improper power-up/down sequence. The acceptable power-on/off sequences are shown in [Table 3-1](#) and [Table 3-2](#). The

user may add an external diode across  $V_{PP}$  and  $V_{DD}$  for additional protection. The anode of the diode is connected to  $V_{DD}$  and the cathode is connected to  $V_{PP}$ . Any low-current high-voltage diode such as a 1N4004 is adequate.

**TABLE 3-1: ACCEPTABLE POWER-ON SEQUENCES**

Option 1		Option 2	
Steps	Description	Steps	Description
1	$V_{DD}$	1	$V_{DD}$
2	$V_{PP}$	2	Inputs
3	Inputs	3	$V_{PP}$

**TABLE 3-2: ACCEPTABLE POWER-OFF SEQUENCES**


Option 1		Option 2	
Steps	Description	Steps	Description
1	Inputs	1	$V_{PP}$
2	$V_{PP}$	2	Inputs
3	$V_{DD}$	3	$V_{DD}$

NOTES:


## 4.0 PACKAGING INFORMATION

### 4.1 Package Marking Information

24-Lead TSSOP



Example




<b>Legend:</b>	XX...X	Product Code or Customer-specific information
	Y	Year code (last digit of calendar year)
	YY	Year code (last 2 digits of calendar year)
	WW	Week code (week of January 1 is week '01')
	NNN	Alphanumeric traceability code
	(e3)	Pb-free JEDEC designator for Matte Tin (Sn)
	*	This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package.

**Note:** In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.


## 24-Lead Thin Shrink Small Outline Package (QE) - 4.40 mm Body [TSSOP] Supertex Legacy & Micrel Legacy Package

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



## 24-Lead Thin Shrink Small Outline Package (QE) - 4.40 mm Body [TSSOP] Supertex Legacy & Micrel Legacy Package

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



DETAIL B

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Leads	N	24		
Lead Pitch	e	0.65 BSC		
Overall Height	A	0.85	-	1.20
Standoff	A1	0.05	0.10	0.15
Molded Package Thickness	A2	0.80	1.00	1.15
Foot Length	L	0.45	0.60	0.75
Footprint	L1	1.00 REF		
Foot Angle	θ	0°	4°	8°
Overall Width	E	6.40 BSC		
Overall Length	D	7.70	7.80	7.90
Molded Package Width	E1	4.30	4.40	4.50
Lead Width	b	0.19	-	0.30
Mold Draft Angle Top	α	12° REF		

**Notes:**

- Pin 1 visual index feature may vary, but must be located within the hatched area.
- Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-284A Sheet 2 of 2

## 24-Lead Thin Shrink Small Outline Package (QE) - 4.40 mm Body [TSSOP] Supertex Legacy & Micrel Legacy Package

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

Dimension Limits	Units	MILLIMETERS		
		MIN	NOM	MAX
Contact Pitch	E	0.65 BSC		
Contact Pad Spacing	C		5.80	
Contact Pad Width (X24)	X1			0.45
Contact Pad Length (X24)	Y1			1.50
Contact Pad to Center Pad (X20)	G1	0.20		

**Notes:**

- Dimensioning and tolerancing per ASME Y14.5M  
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-2284A



## APPENDIX A: REVISION HISTORY

### Revision A (July 2019)

- Original release of this document.

NOTES:

## PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

<u>PART NO.</u>	<u>-X</u>	<u>/XX</u>
Device	Temperature Range	Package
Device:	HV265: 4-Channel, 205V, High-Voltage Amplifiers Array	
Temperature Range:	I = -40°C to +85°C	
Package:	QE = 24LD TSSOP 4.4mm	

**Example:**

a) HV265-I/QE: 4-Channel 205V High-Voltage Amplifier Array, -40°C to +85°C, 24LD TSSOP package

# HV265

---

NOTES:

---

**Note the following details of the code protection feature on Microchip devices:**

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

---

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Klear, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TempTrackr, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, Vite, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KlearNet, KlearNet logo, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICKit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2019, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-4776-4

For information regarding Microchip's Quality Management Systems, please visit [www.microchip.com/quality](http://www.microchip.com/quality).

## Worldwide Sales and Service

### AMERICAS

**Corporate Office**  
2355 West Chandler Blvd.  
Chandler, AZ 85224-6199  
Tel: 480-792-7200  
Fax: 480-792-7277  
Technical Support:  
<http://www.microchip.com/support>  
Web Address:  
[www.microchip.com](http://www.microchip.com)

**Atlanta**  
Duluth, GA  
Tel: 678-957-9614  
Fax: 678-957-1455

**Austin, TX**  
Tel: 512-257-3370

**Boston**  
Westborough, MA  
Tel: 774-760-0087  
Fax: 774-760-0088

**Chicago**  
Itasca, IL  
Tel: 630-285-0071  
Fax: 630-285-0075

**Dallas**  
Addison, TX  
Tel: 972-818-7423  
Fax: 972-818-2924

**Detroit**  
Novi, MI  
Tel: 248-848-4000

**Houston, TX**  
Tel: 281-894-5983

**Indianapolis**  
Noblesville, IN  
Tel: 317-773-8323  
Fax: 317-773-5453  
Tel: 317-536-2380

**Los Angeles**  
Mission Viejo, CA  
Tel: 949-462-9523  
Fax: 949-462-9608  
Tel: 951-273-7800

**Raleigh, NC**  
Tel: 919-844-7510

**New York, NY**  
Tel: 631-435-6000

**San Jose, CA**  
Tel: 408-735-9110  
Tel: 408-436-4270

**Canada - Toronto**  
Tel: 905-695-1980  
Fax: 905-695-2078

### ASIA/PACIFIC

**Australia - Sydney**  
Tel: 61-2-9868-6733

**China - Beijing**  
Tel: 86-10-8569-7000

**China - Chengdu**  
Tel: 86-28-8665-5511

**China - Chongqing**  
Tel: 86-23-8980-9588

**China - Dongguan**  
Tel: 86-769-8702-9880

**China - Guangzhou**  
Tel: 86-20-8755-8029

**China - Hangzhou**  
Tel: 86-571-8792-8115

**China - Hong Kong SAR**  
Tel: 852-2943-5100

**China - Nanjing**  
Tel: 86-25-8473-2460

**China - Qingdao**  
Tel: 86-532-8502-7355

**China - Shanghai**  
Tel: 86-21-3326-8000

**China - Shenyang**  
Tel: 86-24-2334-2829

**China - Shenzhen**  
Tel: 86-755-8864-2200

**China - Suzhou**  
Tel: 86-186-6233-1526

**China - Wuhan**  
Tel: 86-27-5980-5300

**China - Xian**  
Tel: 86-29-8833-7252

**China - Xiamen**  
Tel: 86-592-2388138

**China - Zhuhai**  
Tel: 86-756-3210040

### ASIA/PACIFIC

**India - Bangalore**  
Tel: 91-80-3090-4444

**India - New Delhi**  
Tel: 91-11-4160-8631

**India - Pune**  
Tel: 91-20-4121-0141

**Japan - Osaka**  
Tel: 81-6-6152-7160

**Japan - Tokyo**  
Tel: 81-3-6880-3770

**Korea - Daegu**  
Tel: 82-53-744-4301

**Korea - Seoul**  
Tel: 82-2-554-7200

**Malaysia - Kuala Lumpur**  
Tel: 60-3-7651-7906

**Malaysia - Penang**  
Tel: 60-4-227-8870

**Philippines - Manila**  
Tel: 63-2-634-9065

**Singapore**  
Tel: 65-6334-8870

**Taiwan - Hsin Chu**  
Tel: 886-3-577-8366

**Taiwan - Kaohsiung**  
Tel: 886-7-213-7830

**Taiwan - Taipei**  
Tel: 886-2-2508-8600

**Thailand - Bangkok**  
Tel: 66-2-694-1351

**Vietnam - Ho Chi Minh**  
Tel: 84-28-5448-2100

### EUROPE

**Austria - Wels**  
Tel: 43-7242-2244-39  
Fax: 43-7242-2244-393

**Denmark - Copenhagen**  
Tel: 45-4450-2828  
Fax: 45-4485-2829

**Finland - Espoo**  
Tel: 358-9-4520-820

**France - Paris**  
Tel: 33-1-69-53-63-20  
Fax: 33-1-69-30-90-79

**Germany - Garching**  
Tel: 49-8931-9700

**Germany - Haan**  
Tel: 49-2129-3766400

**Germany - Heilbronn**  
Tel: 49-7131-72400

**Germany - Karlsruhe**  
Tel: 49-721-625370

**Germany - Munich**  
Tel: 49-89-627-144-0  
Fax: 49-89-627-144-44

**Germany - Rosenheim**  
Tel: 49-8031-354-560

**Israel - Ra'anana**  
Tel: 972-9-744-7705

**Italy - Milan**  
Tel: 39-0331-742611  
Fax: 39-0331-466781

**Italy - Padova**  
Tel: 39-049-7625286

**Netherlands - Drunen**  
Tel: 31-416-690399  
Fax: 31-416-690340

**Norway - Trondheim**  
Tel: 47-7288-4388

**Poland - Warsaw**  
Tel: 48-22-3325737

**Romania - Bucharest**  
Tel: 40-21-407-87-50

**Spain - Madrid**  
Tel: 34-91-708-08-90  
Fax: 34-91-708-08-91

**Sweden - Gothenberg**  
Tel: 46-31-704-60-40

**Sweden - Stockholm**  
Tel: 46-8-5090-4654

**UK - Wokingham**  
Tel: 44-118-921-5800  
Fax: 44-118-921-5820

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[HV265-I/QE](#)