

# **MIC5249**

# 300 mA µCap LDO with Programmable Power-On Reset Delay

#### Features

- 300 mA Output Current
- High PSRR: 65 dB@120 Hz
- · Stable with Ceramic Output Capacitor
- Power-on-Reset (POR) Output with Adjustable
   Delay Time
- High Output Accuracy:
  - ±1.0% Initial Accuracy
  - ±3.0% Over Temperature
- Low Dropout Voltage of 340 mV @ 300 mA
- Low Quiescent Current: 85 μA
- Zero Current Shutdown Mode
- Thermal Shutdown and Current-Limit Protection
- Tiny MSOP-8 Package

#### Applications

- Cellular Phones
- PDAs
- Fiber Optic Modules

#### **General Description**

The MIC5249 is an efficient, precise 300 mA CMOS voltage regulator with power on reset (POR) delay which can be implemented via an external capacitor. It offers 1% initial accuracy, extremely low dropout voltage (typically 400 mV @ 300 mA), and low ground current (typically 85 mA) over load.

Designed specifically for noise-critical applications in hand-held or battery-powered devices, the MIC5249 comes equipped with a noise reduction feature to filter the output noise via an external capacitor. Other features of the MIC5249 include a logic-compatible enable pin, current limit, thermal shutdown, ultra-fast transient response, and an active clamp to speed up device turnoff.

The MIC5249 also works with low-ESR ceramic capacitors, reducing the amount of board space necessary for power applications, critical in hand-held wireless devices.

The MIC5249 is available in the MSOP-8 package.

# Package Type



#### **Typical Application Circuit**



#### Functional Block Diagram



# 1.0 ELECTRICAL CHARACTERISTICS

#### Absolute Maximum Ratings †

Supply Voltage (V <sub>IN</sub> )	
Enable Input Voltage (V <sub>EN</sub> )	
Power Dissipation (P <sub>D</sub> ), Note 1	Internally Limited
ESD Rating, Note 2.	ESD Sensitive

# **Operating Ratings ‡**

Supply Voltage (VIN)	
Enable Input Voltage (V <sub>EN</sub> )	0V to V <sub>IN</sub>

**† Notice:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

**‡** Notice: The device is not guaranteed to function outside its operating ratings.

- **Note 1:** The maximum allowable power dissipation of any  $T_A$  (ambient temperature) is  $P_{D(MAX)} = (T_{J(MAX)} T_A)/\theta_{JA}$ . Exceeding the maximum allowable power dissipation will result in excessive die temperature, and the regulator will go into thermal shutdown.
  - **2:** Devices are ESD sensitive. Handling precautions are recommended. Human body model,  $1.5 \text{ k}\Omega$  in series with 100 pF.

<b>Electrical Characteristics:</b> V <sub>IN</sub> = V <sub>OUT</sub> + 1V; I <sub>OUT</sub> = 100 μA; T <sub>J</sub> = +25°C; <b>Bold</b> values indicate –40°C to +125°C unless noted.									
Parameters	Symbol	Min.	Тур.	Max.	Units	Conditions			
Output Voltage	V	-1.0	—	+1.0	0/	Variation from nominal Varia			
Accuracy	V OUT	-3.0		+3.0	70				
Line Regulation	ΔV <sub>OUT</sub> / (V <sub>OUT</sub> x ΔV <sub>IN</sub> )	-0.3	0.02	+0.3	%/V	$V_{IN} = V_{OUT} + 1V$ to 6V			
Load Regulation	ΔV <sub>OUT</sub> /V <sub>OUT</sub>	_	1.5	3.0	%	I <sub>OUT</sub> = 0.1 mA to 300 mA			
		—	1	—		I <sub>OUT</sub> = 100 μA			
Dropout Voltage	V <sub>DO</sub>	—	160	225 <b>275</b>	mV	I <sub>OUT</sub> = 150 mA			
		—	340	500 <b>600</b>		I <sub>OUT</sub> = 300 mA			
Ground Pin Current		_	85	150	ıιΔ	I <sub>OUT</sub> = 0 mA			
	'GND		100	200	μΛ	I <sub>OUT</sub> = 300 mA			
Ground Pin Current in Shutdown	I <sub>SHDN</sub>	_	0.35	1	μA	V <sub>EN</sub> < 0.4V (Regulator OFF)			
Ripple Rejection	PSRR		65	_	dB	f = 120 Hz; C <sub>OUT</sub> = 2.2 μF			
Current Limit	I <sub>LIM</sub>	300	440		mA	V <sub>OUT</sub> = 0V			
Enable Input									
Enable Input Voltage	V <sub>IL</sub>	—		0.4	V	Logic low (regulator shutdown)			
	V <sub>IH</sub>	V <sub>IH</sub> 1.6 —			•	Logic high (regulator enabled)			
Enable Input Current	Ι <sub>IL</sub>	—	0.01	—	μА	V <sub>IL</sub> < 0.4V (regulator shutdown)			
	I <sub>IH</sub>	_	0.01	—	۳, ,	V <sub>IH</sub> > 1.6V (regulator enabled)			

# ELECTRICAL CHARACTERISTICS

# **ELECTRICAL CHARACTERISTICS (CONTINUED)**

<b>Electrical Characteristics:</b> V <sub>IN</sub> = V <sub>OUT</sub> + 1V; I <sub>OUT</sub> = 100 μA; T <sub>J</sub> = +25°C; <b>Bold</b> values indicate –40°C to +125°C unless noted.										
Parameters Symbol Min. Typ. Max. Units Conditions										
Delay Input										
Delay Pin Current Source	I <sub>DELAY_TH</sub>	—	0.55	1	μA	—				
Delay Pin Threshold Voltage	V <sub>DELAY_TH</sub>	_	1.4		V	Threshold for RESET = Logic high				
RESET Output										
Reset Low Threshold	V <sub>THL</sub>	89	91			% of V <sub>OUT</sub> (Flag ON)				
Reset High Threshold	V <sub>THH</sub>	—	93	96	%	% of V <sub>OUT</sub> (Flag OFF)				
Reset Output Logic-Low Voltage	V <sub>OL</sub>	_	0.02	0.1	V	I <sub>RESET</sub> = 100 μA output in fault condi- tion				
Flag Leakage Current	I <sub>RESET</sub>	_	0.01	_	μA	Flag OFF				

# **TEMPERATURE SPECIFICATIONS**

Parameters	Symbol	Min.	Тур.	Max.	Units	Conditions			
Temperature Ranges									
Junction Temperature Range	Τ <sub>J</sub>	-40	-	+125	°C	Note 1			
Storage Temperature Range	Τ <sub>S</sub>	-65	_	+150	°C	—			
Lead Temperature	—	_	_	+260	°C	Soldering, 5 sec.			
Package Thermal Resistances									
Thermal Resistance, MSOP-8	$\theta_{JA}$		160	_	°C/W	_			

**Note 1:** The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T<sub>A</sub>, T<sub>J</sub>, θ<sub>JA</sub>). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +125°C rating. Sustained junction temperatures above +125°C can impact the device reliability.

# 2.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 2-1.

Pin Number	Pin Name	Description
1	CBYP	Reference Bypass. Connect external 0.01µF capacitor to GND to reduce output noise. May be left open.
2	DELAY	Delay Set Input. Connect external capacitor to GND to set the delay of the Error Flag.
3	GND	Ground.
4	VIN	Supply input.
5	VOUT	Regulator output.
6	NC	No connect.
7	RESET	RESET Output. Open-drain output. Active low indicates an output undervoltage condition.
8	ENABLE	Enable Input: CMOS-compatible input. Logic high = enable; Logic low = shutdown. Do not leave open.

#### TABLE 2-1: PIN FUNCTION TABLE

# 3.0 APPLICATION INFORMATION

#### 3.1 Enable/Shutdown

The MIC5249 comes with an active-high enable pin that allows the regulator to be disabled. Forcing the enable pin low disables the regulator and sends it into a "zero" off-mode-current state. In this state, current consumed by the regulator goes nearly to zero. Forcing the enable pin high enables the output voltage. This part is CMOS and the enable pin cannot be left floating; a floating enable pin may cause an indeterminate state on the output.

#### 3.2 Input Capacitor

The MIC5249 is a high-performance, high-bandwidth device. Therefore, it requires a well-bypassed input supply for optimal performance. A 1.0  $\mu$ F capacitor is required from the input to ground to provide stability. Low-ESR ceramic capacitors provide optimal performance at a minimum of space. Additional high-frequency capacitors such as small valued NPO dielectric type capacitors help to filter out high frequency noise and are good practice in any RF-based circuit.

#### 3.3 Output Capacitor

The MIC5249 requires an output capacitor of 2.2  $\mu$ F or greater to maintain stability. The design is optimized for use with low-ESR ceramic chip capacitors. High-ESR capacitors may cause high frequency oscillation. The maximum recommended ESR is 300 m $\Omega$ . The output capacitor can be increased, but performance has been optimized for a 2.2  $\mu$ F ceramic output capacitor and does not improve significantly with larger capacitance.

X7R/X5R dielectric-type ceramic capacitors are recommended because of their temperature performance. X7R-type capacitors change capacitance by 15% over their operating temperature range and are the most stable type of ceramic capacitors. Z5U and Y5V dielectric capacitors change value by as much as 50% and 60%, respectively, over their operating temperature ranges. To use a ceramic chip capacitor with Y5V dielectric, the value must be much higher than anX7R ceramic capacitor to ensure the same minimum capacitance over the equivalent operating temperature range.

#### 3.4 DELAY Pin Input

The power-on-reset (POR) function can be implemented on the MIC5249 by adding an external capacitor from the DELAY pin to ground. This external capacitor sets the delay time ( $t_{\text{DELAY}}$ ) of the RESET output.

The capacitor value required can be easily calculated using the formula:

**EQUATION 3-1:** 

$$C_{DELAY} = \left(\frac{T_{DELAY} \times I_{DELAY}}{V_{DELAY}}\right)$$
  
Where:  
$$I_{DELAY} = 0.55 \ \mu A$$
$$V_{DELAY} = 1.4V$$

When no capacitor is used, there will be no delay and the POR output acts like a standard error FLAG output.

#### 3.5 RESET Output

The RESET output of the MIC5249 provides the power-on reset signal based on the capacitor from the DELAY pin to ground when input power is applied to the regulator. The reset signal stays low for a preset time period after power is applied to the regulator, and then goes high.

The reset output is an active-low, open-drain output that drives low when a fault condition AND an undervoltage detection occurs. Internal circuitry intelligently monitors overcurrent, overtemperature and dropout conditions and ORs these outputs together to indicate some fault condition. The output of that OR gate is ANDed with an output voltage monitor that detects an undervoltage condition. The output drives an open-drain transistor to indicate a fault. This prevents chattering or inadvertent triggering of the reset. There set must be pulled up using a resistor form the RESET pin to either the input or the output.

# 3.6 Bypass Pin Output

A bypass capacitor is required from the noise bypass pin to ground to reduce output voltage noise. The capacitor bypasses the internal reference. A  $0.01 \,\mu\text{F}$ capacitor is recommended for applications that require low-noise outputs. The bypass capacitor can be increased, further reducing noise and improving PSRR. Turn-on time increases slightly with respect to bypass capacitance. A unique quick-start circuit allows the MIC5249 to drive a large capacitor on the bypass pin without significantly slowing the turn-on time.

#### 3.7 Active Shutdown

The MIC5249 also features an active shutdown clamp, which is a N-Channel MOSFET that turns on when the device is disabled. This allows the output capacitor and load to discharge, de-energizing the load.

#### 3.8 No-Load Stability

The MIC5249 will remain stable and in regulation with no load unlike many other voltage regulators. This is especially important in CMOS RAM keep-alive application.

#### 3.9 Thermal Considerations

The MIC5249 is designed to provide 300 mA of continuous current in a very small package. Maximum power dissipation can be calculated based on the output current and the voltage drop across the device. To determine the maximum power dissipation of the package, use the junction-to-ambient thermal resistance of the device and the following basic equation:

#### **EQUATION 3-2:**

$$P_{D(MAX)} = \left(\frac{T_{J(MAX)} - T_A}{\theta_{JA}}\right)$$

Where:

The maximum junction temperature of the die, 125°C
The ambient operating temperature
Layout independent

Table 3-1 shows examples of the junction-to-ambient thermal resistance for MIC5249.

#### TABLE 3-1: MSOP-8 THERMAL RESISTANCE

Package	θ <sub>JA</sub> Recommended Minimum Footprint
MSOP-8	160°C/W

The actual power dissipation of the regulator circuit can be determined using the equation:

#### **EQUATION 3-3:**

$$P_D = (V_{IN} - V_{OUT})I_{OUT} + V_{IN} \times I_{GND}$$

Substituting  $P_{D(MAX)}$  for  $P_D$  and solving for the operating conditions that are critical to the application will give the maximum operating conditions for the regulator circuit. For example, when operating the MIC5249-3.0YMM at 50°C with a minimum footprint layout, the maximum input voltage for a set output current can be determined as follows:

#### **EQUATION 3-4:**

$$P_{D(MAX)} = (125^{\circ}C - 50^{\circ}C)/(160^{\circ}C/W)$$

The junction-to-ambient thermal resistance for the minimum footprint is 160°C/W, from Table 3-1. The maximum power dissipation must not be exceeded for proper operation. Using the output voltage of 3.0V, and an output current of 300 mA, the maximum input voltage can be determined. Because this device is CMOS and the ground current is typically 90  $\mu$ A over the load range, the power dissipation contributed by the ground current is < 1.0% and can be ignored for this calculation:

#### **EQUATION 3-5:**

$$468mW = (V_{IN} - 3.0V)300mA$$
$$468mW = V_{IN} \times 300mA - 900mW$$
$$1368mW = V_{IN} \times 300mA$$
$$V_{IN(MAX)} = 4.56V$$

Therefore, a 3.0V application at 300 mA of output current can accept a maximum input voltage of 4.56V in the MSOP-8 package. For a full discussion of heat sinking and thermal effects on the voltage regulators, refer to the Regulator Thermals section of Designing with Low-Dropout Voltage Regulators handbook.

# 4.0 PACKAGING INFORMATION

# 4.1 Package Marking Information



Legend:	: XXX Y YY WW NNN €3 * •, ▲, ▼ mark).	Product code or customer-specific information Year code (last digit of calendar year) Year code (last 2 digits of calendar year) Week code (week of January 1 is week '01') Alphanumeric traceability code Pb-free JEDEC <sup>®</sup> designator for Matte Tin (Sn) This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package. Pin one index is identified by a dot, delta up, or delta down (triangle
Note:	In the ever be carried characters the corpora Underbar (	nt the full Microchip part number cannot be marked on one line, it will l over to the next line, thus limiting the number of available for customer-specific information. Package may or may not include ate logo. () and/or Overbar (¯) symbol may not be to scale.



#### 8-Lead MSOP Package Outline and Recommended Land Pattern

NOTES:

# APPENDIX A: REVISION HISTORY

### **Revision A (October 2021)**

- Converted Micrel document MIC5249 to Microchip data sheet DS20006602A.
- Minor text changes throughout.

NOTES:

# **PRODUCT IDENTIFICATION SYSTEM**

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO.	- <u>xx</u>	×	<u>xx</u>	<u>-xx</u>	Examples	:	
Device	Voltage Option Ter	Junction nperature Range	Package	Media Type	a) MIC5249	9-1.8YMM	300 mA μCap LDO with Programmable Power-On Reset Delay, 1.8V, –40°C to +125°C, 8-Lead MSOP, 100/Tube
Device:	MIC5249: 3 F	00 mA µCap LDO witl Reset Delay	h Programma	ble Power-On	b) MIC5249	9-1.8YMM-TR	300 mA µCap LDO with Programmable Power-On Reset Delay, 1.8V, –40°C to +125°C, 8-Lead MSOP, 2,500/Reel
Voltage Option	1.5 = 1.5V 1.8 = 1.8V 2.5 = 2.5V 2.6 = 2.6V 2.8 = 2.8V				c) MIC5249	9-2.85YMM	300 mA μCap LDO with Programmable Power-On Reset Delay, 2.85V, –40°C to +125°C, 8-Lead MSOP, 100/Tube
	2.85 = 2.85 3.0 = 3.0V 3.3 = 3.3V	J			c) MIC5249 TR	9-2.85YMM-	300 mA µCap LDO with Programmable Power-On Reset Delay, 2.85V, −40°C to +125°C, 8-Lead MSOP, 2,500/Reel
Junction Temperature Range:	Y = -	-40°C to +125°C			Note 1:	Tape and Rec catalog part r	el identifier only appears in the number description. This identifier is
Package:	MM = 8	B-Lead MSOP (Pb-Fre	e)			the device pa Sales Office f	ring purposes and is not printed on ckage. Check with your Microchip or package availability with the
Media Type:	<blank> = TR = 2</blank>	100/Tube 2,500/Reel				lape and Ree	ei option.

NOTES:

#### Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
  mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to
  continuously improving the code protection features of our products.

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at https:// www.microchip.com/en-us/support/design-help/client-supportservices.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WAR-RANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDI-RECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSE-QUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, TrueTime, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, GridTime, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, NVM Express, NVMe, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, Symmcom, and Trusted Time are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2021, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-5224-9213-9

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



# **Worldwide Sales and Service**

#### AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

**Chicago** Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110 Tel: 408-436-4270

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000 China - Chengdu

Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

**China - Wuhan** Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138 China - Zhuhai

Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631 India - Pune

Tel: 91-20-4121-0141

**Japan - Osaka** Tel: 81-6-6152-7160

Japan - Tokyo Tel: 81-3-6880- 3770

Korea - Daegu Tel: 82-53-744-4301

Korea - Seoul Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu

Tel: 886-3-577-8366 Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

Tel: 31-416-690399 Fax: 31-416-690340

**EUROPE** 

Austria - Wels

Tel: 43-7242-2244-39

Tel: 45-4485-5910

Fax: 45-4485-2829

Tel: 358-9-4520-820

Tel: 33-1-69-53-63-20

Fax: 33-1-69-30-90-79

Germany - Garching

Tel: 49-2129-3766400

Germany - Heilbronn

Germany - Karlsruhe

Tel: 49-7131-72400

Tel: 49-721-625370

Germany - Munich

Tel: 49-89-627-144-0

Fax: 49-89-627-144-44

Germany - Rosenheim

Tel: 49-8031-354-560

Israel - Ra'anana

Italy - Milan

Italy - Padova

Tel: 972-9-744-7705

Tel: 39-0331-742611

Fax: 39-0331-466781

Tel: 39-049-7625286

**Netherlands - Drunen** 

Tel: 49-8931-9700

Germany - Haan

Finland - Espoo

France - Paris

Fax: 43-7242-2244-393

**Denmark - Copenhagen** 

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

**Sweden - Stockholm** Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Microchip:

 MIC5249-2.5YMM
 MIC5249-2.6YMM
 MIC5249-3.3YMM
 MIC5249-3.0YMM
 MIC5249-1.5YMM
 MIC5249-2.8YMM

 MIC5249-2.85YMM
 MIC5249-1.8YMM
 MIC5249-2.8YMM-TR
 MIC5249-2.6YMM-TR
 MIC5249-2.6YMM-TR

 MIC5249-3.0YMM-TR
 MIC5249-2.5YMM
 MIC5249-2.8YMM-TR
 MIC5249-2.85YMM-TR
 MIC5249-2.6YMM-TR