

MIC5236

Low Quiescent Current µCap LDO Regulator

Features

- Ultra-Low Quiescent Current ($I_Q = 20 \ \mu A @ I_O = 100 \ \mu A$)
- Wide Input Range: 2.3V to 30V
- Low Dropout:
- 230 mV @50 mA;
- 300 mV @150 mA
- Fixed 2.5V, 3.0V, 3.3V, 5.0V, and Adjustable Outputs
- ±1.0% Initial Output Accuracy
- Stable with Ceramic or Tantalum Output Capacitor
- Load Dump Protection: –20V to +60V Input Transient Survivability
- Logic Compatible Enable Input
- Low Output Flag Indicator
- Overcurrent Protection
- Thermal Shutdown
- Reverse-Leakage Protection
- Reverse-Battery Protection
- High-Power SOIC-8 and MSOP-8 Package Options

Applications

- Keep-Alive Supply in Notebook and Portable Personal Computers
- Logic Supply from High-Voltage Batteries
- · Automotive Electronics
- · Battery-Powered Systems

General Description

The MIC5236 is a low quiescent current, μ Cap low-dropout regulator. With a maximum operating input voltage of 30V and a quiescent current of 20 μ A, it is ideal for supplying keep-alive power in systems with high-voltage batteries.

Capable of 150 mA output, the MIC5236 has a dropout voltage of only 300 mV. It can also survive an input transient of -20V to +60V.

As a μ Cap LDO, the MIC5236 is stable with either a ceramic or a tantalum output capacitor. It only requires a 1.0 μ F output capacitor for stability.

The MIC5236 includes a logic compatible enable input and an undervoltage error flag indicator. Other features of the MIC5236 include thermal shutdown, current-limit, overvoltage shutdown, load-dump protection, reverse leakage protections, and reverse battery protection.

Available in the thermally enhanced SOIC-8 and MSOP-8, the MIC5236 comes in fixed 2.5V, 3.0V, 3.3V, 5.0V, and adjustable voltages. For other output voltages, contact Microchip.

Package Types



Typical Application Circuits



Functional Block Diagram



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

Supply Voltage (V _{IN}), Note 1	
Power Dissipation (P _D), Note 2	Internally Limited
ESD Rating, Note 3	

Operating Ratings ‡

Supply Voltage (V _{IN})	+ 2.3V to +30V
-----------------------------------	----------------

† Notice: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

‡ Notice: The device is not guaranteed to function outside its operating ratings.

- Note 1: The absolute maximum positive supply voltage (60V) must be of limited duration (≤100 ms) and duty cycle (≤1%). The maximum continuous supply voltage is 30V.
 - 2: The maximum allowable power dissipation of any T_A (ambient temperature) is $P_{D(MAX)} = (T_{J(MAX)} T_A) \div \theta_{JA}$. Exceeding the maximum allowable power dissipation will result in excessive die temperature, and the regulator will go into thermal shutdown. The θ_{JA} of the MIC5236-x.xYM (all versions) is 63°C/W, and the MIC5236-x.xYMM (all versions) is 80°C/W, mounted on a PC board (see Package Thermal Resistance for further details).
 - 3: Devices are ESD sensitive. Handling precautions recommended. Human body model, $1.5 \text{ k}\Omega$ in series with 100pF.

ELECTRICAL CHARACTERISTICS

Electrical Characteristics: V_{IN} = 6.0V; V_{EN} = 2.0V; C_{OUT} = 4.7 µF, I_{OUT} = 100 µA; T_J = 25°C, **bold** values indicate -40°C ≤ T_J ≤ +125°C; unless noted

Parameter	Symbol	Min.	Тур.	Max.	Units	Conditions
Output Voltage Accuracy	V _{OUT}	-1	—	1	%	Variation from nominal V_{OUT}
Output Voltage Temperature Coefficient	ΔV _{OUT} /ΔT	_	50	_	ppm/°C	Note 1
Line Regulation	$\Delta V_{OUT}/V_{OUT}$		0.2	0.5	%	V _{IN} = V _{OUT} + 1V to 30V
Lood Regulation			0.15	0.3	%	I _{OUT} = 100 μA to 50 mA,
	AVOUT/VOUT	—	0.3	0.6	%	Note 2
		_	50	100	mV	Ι _{ΟUT} = 100 μΑ
	ΔV	_	230	400	mV	I _{OUT} = 50 mA
Dropout voltage, Note 5		_	270	_	mV	I _{OUT} = 100 mA
		_	300	500	mV	I _{OUT} = 150 mA
		_	20	30	μA	V _{EN} ≥ 2.0V, I _{OUT} = 100 µA
	I _{GND}		0.5	0.8	mA	V _{EN} ≥ 2.0V, I _{OUT} = 50 mA
Ground Pin Current		_	1.5	_	mA	V _{EN} ≥ 2.0V, I _{OUT} = 100 mA
		_	2.8	4.0	mA	
		_		5.0	mA	$v_{\rm EN} \ge 2.00$, $v_{\rm OUT} = 150$ mA
Ground Pin in Shutdown	I _{GND(SHDN)}	_	0.1	1	μA	V _{EN} ≤ 0.6V, V _{IN} = 3
Short Circuit Current	I _{SC}	_	260	350	mA	V _{OUT} = 0V
Output Noise	e _n		160	_	μVrms	10 Hz to 100 kHz, V _{OUT} = 3.0V, C _L = 1.0 µF

ELECTRICAL CHARACTERISTICS (CONTINUED)

Electrical Characteristics: V_{IN} = 6.0V; V_{EN} = 2.0V; C_{OUT} = 4.7 µF, I_{OUT} = 100 µA; T_J = 25°C, **bold** values indicate -40°C ≤ T_J ≤ +125°C; unless noted

Parameter	Symbol	Min.	Тур.	Max.	Units	Conditions				
/ERR Output										
Low Threshold	V	90	94	—	%	0/ of \/				
High Threshold	V/ERR		95	98	%	70 OI VOUT				
/EPP Output Low Voltage	V		150	250	mV	$V_{IN} = V_{OUT(nom)} - 0.12V_{OUT}$				
PERR Output Low Voltage	V OL		150	400	mV	Ι _{ΟL} = 200 μΑ				
/EPP Output Lookago	I		0.1	1	μA	1/2 - 30/2				
/ENR Output Leakage	LEAK		0.1	2	μA	v _{OH} = 30 v				
Enable Input										
Input Low Voltage	V _{IL}		_	0.6	V	Regulator off				
Input High Voltage	V _{IH}	2.0	_	_	V	Regulator on				
			0.01	1.0	μA	$\lambda = 0.6 \lambda / regulator off$				
			_	2.0	μA	VEN - 0.0V, regulator on				
Enable Input Current	I _{IN}		0.15	1.0	μA	V = 2.0V regulator on				
			_	2.0	μA	VEN - 2.0V, regulator on				
			0.5	2.5	μA	$V_{-1} = 30V$ regulator on				
			_	5.0	μA	VEN - 50 V, regulator off				

Note 1: Output voltage temperature coefficient is defined as the worst-case voltage change divided by the total temperature range.

2: Regulation is measured at constant junction temperature using pulse testing with a low duty-cycle. Changes in output voltage due to heating effects are covered by the specification for thermal regulation.

3: Dropout voltage is defined as the input to output differential at which the output voltage drops 2% below its nominal value measured at 1.0V differential.

TEMPERATURE SPECIFICATIONS (Note 1)

	•								
Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions			
Temperature Ranges									
Junction Temperature Range	TJ	-40		+125	°C	—			
Maximum Junction Temperature	T _{J(MAX)}	_	—	+150	°C	—			
Lead Temperature	—	—	_	+260	°C	Soldering, 5 seconds			
Storage Temperature	Τ _S	-65	—	+150	°C	—			
Package Thermal Resistance									
Thermal Resistance, SOIC-8	θ _{JA}	—	80	—	°C/W	—			
Thermal Resistance, MSOP-8	θ _{JA}		63	_	°C/W	_			

Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T_A, T_J, θ_{JA}). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +125°C rating. Sustained junction temperatures above +125°C can impact the device reliability.

2.0 **TYPICAL PERFORMANCE CURVES**

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.



FIGURE 2-1: Current.







FIGURE 2-2:







FIGURE 2-5: Ground Pin Current vs. Output Current.



Voltage.



FIGURE 2-7: Ground Current vs. Supply Voltage.



FIGURE 2-8:

Temperature.



FIGURE 2-9: Temperature.



FIGURE 2-10: Ground Current vs. Temperature.



FIGURE 2-11: Output Voltage vs. Temperature.



FIGURE 2-12: Short Circuit Current vs. Temperature.







Temperature.



FIGURE 2-15: Current Limit vs. Output Voltage.



FIGURE 2-16: Input Current.





FIGURE 2-18: Current Limit Induced Error Flag.



FIGURE 2-19: Reverse Current (Open Input).



FIGURE 2-20: Reverse Current (Grounded Input).



3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3-1.

TABLE 3-1:	PIN FUNCTION TABLE
------------	---------------------------

Pin Number	Pin Name	Description
1	/ERR	Error (Output): Open-collector output is active-low when the output is out of regulation due to insufficient input voltage or excessive load. An external pull-up resistor is required.
1	ADJ	Adjustable Feedback Input. Connect to voltage divider network.
2	IN	Power Supply Input.
3	OUT	Regulated Output.
4	EN	Enable (Input): Logic low = shutdown; logic high = enabled.
5-8	GND	Ground: Pins 5, 6, 7, and 8 are internally connected in common via the leadframe.

4.0 APPLICATION INFORMATION

The MIC5236 provides all of the advantages of the MIC2950: wide input voltage range, load dump (positive transients up to 60V), and reversed-battery protection, with the added advantages of reduced quiescent current and smaller package. Additionally, when disabled, quiescent current is reduced to 0.1 μ A.

4.1 Enable

A low on the enable pin disables the part, forcing the quiescent current to less than 0.1 μ A. Thermal shutdown and the error flag are not functional while the device is disabled. The maximum enable bias current is 2 μ A for a 2.0V input. An open collector pull-up resistor tied to the input voltage should be set low enough to maintain 2V on the enable input. Figure 4-1 shows an open collector output driving the enable pin through a 200 k Ω pull-up resistor tied to the input voltage.

In order to avoid output oscillations, slow transitions from low to high should be avoided.





4.2 Input Capacitor

An input capacitor may be required when the device is not near the source power supply or when supplied by a battery. Small, surface mount, ceramic capacitors can be used for bypassing. Larger values may be required if the source supply has high ripple.

4.3 Output Capacitor

The MIC5236 has been designed to minimize the effect of the output capacitor ESR on the closed loop stability. As a result, ceramic or film capacitors can be used at the output. Figure 4-2 displays a range of ESR values for a 10 μ F capacitor. Virtually any 10 μ F capacitor with an ESR less than 3.4 Ω is sufficient for stability over the entire input voltage range. Stability can also be maintained throughout the specified load and line conditions with 1 μ F film or ceramic capacitors.



4.4 Error Detection Comparator Output

The ERR pin is an open collector output which goes low when the output voltage drops 5% below its internally programmed level. It senses conditions such as excessive load (current limit), low input voltage, and overtemperature conditions. Once the part is disabled via the enable input, the error flag output is not valid. Overvoltage conditions are not reflected in the error flag output. The error flag output is also not valid for input voltages less than 2.3V.

The error output has a low voltage of 400 mV at a current of 200 μ A. In order to minimize the drain on the source used for the pull-up, a value of 200 k Ω to 1 M Ω is suggested for the error flag pull-up. This will guarantee a maximum low voltage of 0.4V for a 30V pull-up potential. An unused error flag can be left unconnected.



FIGURE 4-3: E

Error Output Timing.

4.5 Reverse Current Protection

The MIC5236 is designed to limit the reverse current flow from output to input in the event that the MIC5236 output has been tied to the output of another power supply. See Figure 2-19 and Figure 2-20 detailing the reverse current flow with the input grounded and open.

4.6 Thermal Shutdown

The MIC5236 has integrated thermal protection. This feature is only for protection purposes. The device should never be intentionally operated near this temperature as this may have detrimental effects on the life of the device. The thermal shutdown may become inactive while the enable input is transitioning a high to a low. When disabling the device via the enable pin, transition from a high to low quickly. This will ensure that the output remains disabled in the event of a thermal shutdown.

4.7 Current Limit

Figure 4-4 displays a method for reducing the steady state short circuit current. The duration that the supply delivers current is set by the time required for the error flag output to discharge the 4.7 μ F capacitor tied to the enable pin. The off time is set by the 200 k Ω resistor as it recharges the 4.7 μ F capacitor, enabling the regulator. This circuit reduces the short circuit current from 280 mA to 15 mA while allowing for regulator restart once the short is removed.



FIGURE 4-4: Remote Enable with Short Circuit Current Foldback.

4.8 Thermal Characteristics

The MIC5236 is a high input voltage device, intended to provide 150 mA of continuous output current in two very small profile packages. The power SOIC-8 and power MSOP-8 allow the device to dissipate about 50% more power than their standard equivalents.

4.8.1 POWER SOIC-8 THERMAL CHARACTERISTICS

SOIC-8 package featuring half the thermal resistance of a standard SOIC-8 package. Lower thermal resistance means more output current or higher input voltage for a given package size.

Lower thermal resistance is achieved by joining the four ground leads with the die attach paddle to create a single-piece electrical and thermal conductor. This concept has been used by MOSFET manufacturers for years, proving very reliable and cost effective for the user.

Thermal resistance consists of two main elements, θ_{JC} (junction-to-case thermal resistance) and θ_{CA} (case-to-ambient thermal resistance). See Figure 4-5. θ_{JC} is the resistance from the die to the leads of the package. θ_{CA} is the resistance from the leads to the ambient air and it includes θ_{CS} (case-to-sink thermal resistance) and θ_{SA} (sink-to-ambient thermal resistance).



Using the power SOIC-8 reduces the θ_{JC} dramatically and allows the user to reduce θ_{CA} . The total thermal resistance, θ_{JA} (junction-to-ambient thermal resistance) is the limiting factor in calculating the maximum power dissipation capability of the device. Typically, the power SOIC-8 has a θ_{JC} of 20°C/W, this is significantly lower than the standard SOIC-8 which is typically 75°C/W. θ_{CA} is reduced because pins 5 through 8 can now be soldered directly to a ground plane which significantly reduces the case-to-sink thermal resistance and sink to ambient thermal resistance.

Low-dropout linear regulators from Microchip are rated to a maximum junction temperature of 125°C. It is important not to exceed this maximum junction temperature during operation of the device. To prevent this maximum junction temperature from being exceeded, the appropriate ground plane heat sink must be used.



FIGURE 4-6: Copper Area vs. Power-SOIC Power Dissipation (ΔT_{JA}).

Figure 4-6 shows copper area versus power dissipation with each trace corresponding to a different temperature rise above ambient. From these curves, the minimum area of copper necessary for the part to operate safely can be determined. The maximum allowable temperature rise must be calculated to determine operation along which curve.

EQUATION 4-1:

$$\Delta T = T_{J(MAX)} - T_{A(MAX)}$$

Where:

 $T_{J(MAX)} = 125$ °C $T_{A(MAX)} =$ Maximum ambient operating temperature

For example, the maximum ambient temperature is 50° C, the Δ T is determined as follows:

EQUATION 4-2:

$$\Delta T = 125^{\circ}C - 50^{\circ}C$$
$$\Delta T = 75^{\circ}C$$

Using Figure 4-6, the minimum amount of required copper can be determined based on the required power dissipation. Power dissipation in a linear regulator is calculated as follows:

EQUATION 4-3:

$$P_D = (V_{IN} - V_{OUT})I_{OUT} + V_{IN} \times I_{GND}$$

If we use a 3V output device and a 28V input at moderate output current of 25 mA, then our power dissipation is as follows:

EQUATION 4-4:

$$P_D = (28V - 3V) \times 25mA + 28V \times 250\mu A$$
$$P_D = 625mW + 7mW = 632mW$$

From Figure 4-6, the minimum amount of copper required to operate this application at a ΔT of 75°C is 25 mm².

4.8.2 QUICK METHOD

Determine the power dissipation requirements for the design along with the maximum ambient temperature at which the device will be operated. Refer to Figure 4-7, which shows safe operating curves for three different ambient temperatures: 25°C, 50°C, and 85°C. From these curves, the minimum amount of copper can be determined by knowing the maximum power dissipation required. If the maximum ambient temperature is 50°C and the power dissipation is as above, 632 mW, the curve in Figure 4-7 shows that the required area of copper is 25 mm².

The θ_{JA} of this package is ideally 63°C/W, but it will vary depending upon the availability of copper ground plane to which it is attached.



Power-SOIC Power Dissipation (T_A)



FIGURE 4-8: Copper Area vs. Power-MSOP Power Dissipation (ΔT_{JA})

The same method of determining the heat sink area used for the power SOIC-8 can be applied directly to the power MSOP-8. The same two curves showing power dissipation versus copper area are reproduced for the power MSOP-8 and they can be applied identically, see Figure 4-8 and Figure 4-9.



FIGURE 4-9: Copper Area vs. Power-MSOP Power Dissipation (T_A)

4.9 Power MSOP-8 Thermal Characteristics

The power MSOP-8 package follows the same idea as the power SOIC-8 package, using four ground leads with the die attach paddle to create a single-piece electrical and thermal conductor, reducing thermal resistance and increasing power dissipation capability.

4.9.1 QUICK METHOD

Determine the power dissipation requirements for the design along with the maximum ambient temperature at which the device will be operated. Refer to Figure 4-9, which shows safe operating curves for three different ambient temperatures, 25°C, 50°C, and 85°C. From these curves, the minimum amount of copper can be determined by knowing the maximum power dissipation required. If the maximum ambient temperature is 50°C, and the power dissipation is 639 mW, the curve in Figure 4-9 shows that the required area of copper is 110 mm², when using the power MSOP-8.

4.10 Adjustable Regulator Application



Application

The MIC5236YM/MM can be adjusted from 1.24V to 20V by using two external resistors (Figure 4-10). The resistors set the output voltage based on the following equation:

EQUATION 4-5:

$$V_{OUT} = V_{REF} + \left(1 + \frac{R1}{R2}\right)$$

Where: V_{REF} = 1.23V

5.0 PACKAGING INFORMATION

5.1 Package Marking Information



	Y	Year code (last digit of calendar year)
	YY	Year code (last 2 digits of calendar year)
	WW	Week code (week of January 1 is week '01')
	NNN	Alphanumeric traceability code
	(e3)	Pb-free JEDEC [®] designator for Matte Tin (Sn)
	*	This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package.
	●, ▲, ` mark).	Pin one index is identified by a dot, delta up, or delta down (triangle
Note:	In the even be carrie character the corpo	ent the full Microchip part number cannot be marked on one line, it will ad over to the next line, thus limiting the number of available is for customer-specific information. Package may or may not include rate logo.
	Underbar	(_) and/or Overbar (¯) symbol may not be to scale.



8-Lead SOIC Package Outline and Recommended Land Pattern



8-Lead MSOP Package Outline and Recommended Land Pattern

APPENDIX A: REVISION HISTORY

Revision A (August 2021)

- Converted Micrel document MIC5236 to Microchip data sheet DS20006574A.
- Minor text changes throughout.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART No.	- <u>X.X</u>	<u>x</u>	<u>xx</u>	- <u>XX</u>	E	kample	es:	
Device	Output Voltage	Junction Temp. Range	Package	Media Type	a)	MIC52	236-2.5YM:	MIC5236, 2.5V Output Voltage, -40°C to +125°C Temp. Range, 8-Lead SOIC, 95/Tube
Device:	MIC5236	: Low Quieso tor = Adjustable	ent Current μCa	p LDO Regula-	b)	MIC52	236-3.0YM-TR:	MIC5236, 3.0V Output Voltage, -40°C to +125°C Temp. Range, 8-Lead SOIC, 2500/Reel
Output Voltage:	-2.5 = -3.0 = -3.3 = -5.0 =	2.5V 3.0V 3.3V 5.0V			c)	MIC52	236-3.3YMM:	MIC5236, 3.3V Output Voltage, -40°C to +125°C Temp. Range, 8-Lead MSOP, 100/Tube
Junction Temperature Range:	Y =	–40°C to +125°C			d)	MIC52	236-5.0YMM-TR:	MIC5236, 5.0V Output Voltage, -40°C to +125°C Temp. Range, 8-Lead MSOP, 2500/Reel
Package:	M = MM =	8-Lead SOIC 8-Lead MSOP			e)	MIC52	236YMM:	MIC5236, Adj. Output Voltage, -40°C to +125°C Temp. Range, 8-Lead MSOP, 100/Tube
Media Type:	<blank> <blank> -TR =</blank></blank>	= 95/Tube (SOIC c = 100/Tube (MSO 2500/Reel	option only) P option only)		Nd	ote 1:	Tape and Reel ide catalog part numb used for ordering the device packag Sales Office for p Tape and Reel op	entifier only appears in the ber description. This identifier is purposes and is not printed on ge. Check with your Microchip ackage availability with the tion.

NOTES:

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
- Microchip is willing to work with any customer who is concerned about the integrity of its code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
 mean that we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are
 committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection
 feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or
 other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WAR-RANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDI-RECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUEN-TIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries

 $\ensuremath{\mathsf{SQTP}}$ is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2021, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-8793-7

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000 China - Chengdu

Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen Tel: 86-592-2388138 China - Zhuhai

Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631 India - Pune

Tel: 91-20-4121-0141 Japan - Osaka

Tel: 81-6-6152-7160 Japan - Tokyo

Tel: 81-3-6880- 3770 Korea - Daegu

Tel: 82-53-744-4301 Korea - Seoul

Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu

Tel: 886-3-577-8366 Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100 Tel: 45-4485-5910 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

EUROPE

Austria - Wels

Tel: 43-7242-2244-39

Fax: 43-7242-2244-393

Denmark - Copenhagen

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

Germany - Haan Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-72400

Germany - Karlsruhe Tel: 49-721-625370

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

Sweden - Gothenberg Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip:

MIC5236-5.0YMM MIC5236-3.0YM MIC5236YM MIC5236-3.3YMM MIC5236-5.0YM MIC5236YMM MIC5236-3.0YMM MIC5236-2.5YM MIC5236-3.3YM MIC5236-2.5YMM MIC5236-3.3YM TR MIC5236-5.0YMM TR MIC5236-3.0YMM TR MIC5236-5.0YM TR MIC5236YM TR MIC5236YMM TR MIC5236-2.5YM TR MIC5236-3.0YM TR MIC5236-3.3YMM TR MIC5236-2.5YMM TR MIC5236-3.3YM-TR MIC5236-5.0YM-TR MIC5236-2.5YM-TR MIC5236-3.3YMM-TR MIC5236-2.5YMM TR MIC5236-3.0YM-TR MIC5236-5.0YMM-TR MIC5236-2.5YM-TR MIC5236-3.3YMM-TR MIC5236YM-TR MIC5236-3.0YM-TR MIC5236-5.0YMM-TR MIC5236-2.5YM-TR MIC5236-3.3YMM-TR MIC5236YM-TR MIC5236-3.0YM-TR MIC5236-5.0YMM-TR MIC5236-2.5YMM-TR MIC5236-3.0YM-TR MIC5236-3.0YM-TR MIC5236-3.0YMM-TR MIC5236-3.0YMM-TR MIC5236-3.0YM-TR MIC5236-3.0YM-TR MIC5236-3.0YM-TR MIC5236-3.0YMM-TR MIC5236-3.0YMM-TR MIC5236-3.0YM-TR MI