

## Ionization Smoke Detector Companion IC

### Features

- Low Quiescent Current
- Operation from 3V Battery or AC with 3V Battery Backup
- 9V Boost Converter
- Horn Driver
- 4V Regulated Voltage for Microcontroller Operation in AC Condition
- Low Leakage DETECT Input (+/- 1 pA)
- Alarm Interconnect
- Internal Operational Amplifiers:
  - Rail-to-rail Input and Output
  - 10 kHz Gain Bandwidth Product
  - Unity Gain Stable


### Applications

- Smoke Detector

### Description


The RE46C600 is a low-power CMOS ionization smoke detector companion IC. The RE46C600 provides all of the analog, interface, and power regulation functions for a microcontroller-based ionization smoke detector. It is intended for use in both 3V battery and AC battery-backed applications. It features a boost converter and driver circuit suitable for driving a piezoelectric horn, a 4V regulator for microcontroller voltage regulation, an operational amplifier and an IO for communication with interconnected units.

### Package Types



# RE46C600

## Functional Block Diagram



## 1.0 ELECTRICAL CHARACTERISTICS

### 1.1 Absolute Maximum Ratings†

$V_{DD}$ .....	+5V
$V_O$ , LX.....	+15V
$I_O$ .....	+18V
Input Voltage Range Except ACDET, FEED .....	$V_{IN1} = -0.3V$ to $V_{REG} + 0.3V$
ACDET .....	$V_{IN2} = -0.3V$ to $V_O + 0.3V$
FEED Input Voltage Range .....	$V_{INFD} = -10V$ to $+22V$
Input Current except FEED .....	$I_{IN} = 10$ mA
Output Current $V_{REG}$ .....	$I_{REG} = 50$ mA
Sink Current $OP_{OUT}$ .....	$I_{OPO} = 20$ mA
Output Current IHS, IHB .....	$I_{HS} = I_{HB} = 75$ mA
Storage Temperature .....	$T_{STG} = -55^{\circ}C$ to $+125^{\circ}C$
HBM ESD.....	1500V
Maximum Junction Temperature .....	$T_J = +150^{\circ}C$

† **Notice:** Stresses above those listed under “Maximum Ratings” may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operation listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

## DC ELECTRICAL CHARACTERISTICS

Unless otherwise indicated, all parameters apply at  $T_A = -10^{\circ}C$  to  $+60^{\circ}C$ ,  $V_{DD} = 3V$ ,  $V_{SS} = 0V$ ,  $C_5 = 10 \mu F$ ,  $C_4 = 10 \mu F$ , ACDET low. (Note 1) (Note 2) (Note 3)

Parameter	Sym.	Test Pin	Min.	Typ.	Max.	Units	Conditions
Supply Voltage	$V_{DD}$	10	2	—	3.6	V	Operating, battery-only operation
			2	—	4.2	V	Operating, AC operation, ACDET high, VREGEN high
	$V_O$	16	7	—	14	V	—
Standby $I_{DD}$	$I_{DDSTBY1}$	10	—	0.9	1.6	$\mu A$	Inputs low, No loads, boost regulator not running, $V_O = 10V$
	$I_{DDSTBY2}$		—	34	50	$\mu A$	AC operation, ACDET high, VREGEN high, $V_O = 10V$
Standby $I_{VO}$	$I_{VOSTBY1}$	16	—	—	0.8	$\mu A$	Inputs low, No loads, boost regulator not running, $V_O = 10V$
	$I_{VOSTBY2}$		—	52	68	$\mu A$	AC operation, ACDET high, VREGEN high, $V_O = 10V$

- Note 1:** By default,  $V_O$  is forced externally with the inductor disconnected and the Boost converter is NOT running, with the exception of  $V_{VO}$  and  $V_{EFF}$ .
- Note 2:** Typical values are for design information only.
- Note 3:** The limits shown are 100% tested at  $25^{\circ}C$  only. Test limits are guard-banded, based on temperature characterization to warrant compliance at temperature extremes.
- Note 4:** In this test, ACDET = High and VREGEN = High.

# RE46C600

## DC ELECTRICAL CHARACTERISTICS (CONTINUED)

Unless otherwise indicated, all parameters apply at  $T_A = -10^{\circ}\text{C}$  to  $+60^{\circ}\text{C}$ ,  $V_{DD} = 3\text{V}$ ,  $V_{SS} = 0\text{V}$ ,  $C_5 = 10\text{ }\mu\text{F}$ ,  $C_4 = 10\text{ }\mu\text{F}$ , ACDET low. (Note 1) (Note 2) (Note 3)

Parameter	Sym.	Test Pin	Min.	Typ.	Max.	Units	Conditions
Quiescent $I_{DD}$	$I_{DDQ}$	10	—	34	50	$\mu\text{A}$	Inputs low, No loads, $V_O = 10\text{V}$ , $V_{LX} = 0.5\text{V}$ , HRNEN high, ACDET low
Quiescent $I_{VO}$	$I_{VOQ1}$	16	—	27	33	$\mu\text{A}$	Inputs low, No loads, $V_O = 10\text{V}$ , $V_{LX} = 0.5\text{V}$ , HRNEN high, ACDET low
	$I_{VOQ2}$		—	257	314	$\mu\text{A}$	Inputs low, No loads, $V_O = 10\text{V}$ , $V_{LX} = 0.5\text{V}$ , IOEN high, ACDET low
Input Leakage Low	$I_{IL}$	11, 12, 13, 6	—	—	-100	nA	IOEN, ACDET, VREGEN, HRNEN, Inputs $V_{IN} = V_{SS}$
	$I_{ILOP}$	7	—	—	-1	pA	DETECT input, $V_{IN} = V_{SS}$ , $T_a = 27^{\circ}\text{C}$ , 0-40% RH
	$I_{ILF}$	3	—	-15	-50	$\mu\text{A}$	FEED = -10V, $V_O = 14\text{V}$
Input Leakage High	$I_{IH1}$	11, 13, 6	—	—	100	nA	IOEN, VREGEN, HRNEN Inputs $V_{DD} = 4.2\text{V}$ , $V_{IN} = 4.2\text{V}$ (Note 4)
	$I_{IH2}$	12	—	—	100	nA	ACDET Input, $V_{IN} = 14\text{V}$ , $V_O = 14\text{V}$
	$I_{IHOP}$	7	—	—	1	pA	DETECT input, $V_{DD} = 4.2\text{V}$ , $V_{IN} = 4.2\text{V}$ , $T_a = 27^{\circ}\text{C}$ , 0-40% RH (Note 4)
	$I_{IHF}$	3	—	20	50	$\mu\text{A}$	FEED = +22V, $V_O = 14\text{V}$
Output Off Leakage High	$I_{IHOZ}$	1	—	—	1	$\mu\text{A}$	$LX = V_O = 14\text{V}$
Input Voltage Low	$V_{IL1}$	11, 13, 6	—	—	1	V	IOEN, VREGEN, HRNEN Inputs
	$V_{IL2}$	12, 3	—	—	3	V	ACDET, FEED Inputs, $V_O = 10\text{V}$
Input Voltage High	$V_{IH1}$	11, 13, 6	2.3	—	—	V	IOEN, VREGEN, HRNEN Inputs
	$V_{IH2}$	12, 3	7	—	—	V	ACDET, FEED Inputs, $V_O = 10\text{V}$
Output Voltage Low	$V_{OL}$	4, 5	—	0.3	0.5	V	HS or HB, $I_{OUT} = 16\text{ mA}$ , $V_O = 10\text{V}$ , HRNEN = $V_{SS}$
Output Voltage High	$V_{OH}$	4, 5	9.5	9.7	—	V	HS or HB, $I_{OUT} = -16\text{ mA}$ , $V_O = 10\text{V}$ , HRNEN high
	$V_{OHIO}$	14	3	—	—	V	IO output, $I_{OUT} = -4\text{ mA}$ , $V_O = 10\text{V}$ , IOEN high
$V_O$ Output Voltage	$V_{VO}$	16	8.2	9	9.8	V	HRNEN high, $I_{OUT} = 10\text{ mA}$
$V_O$ Efficiency	$V_{EFF}$	—	—	85	—	%	$I_{LOAD} = 10\text{ mA}$ , HRNEN high

- Note 1:** By default,  $V_O$  is forced externally with the inductor disconnected and the Boost converter is NOT running, with the exception of  $V_{VO}$  and  $V_{EFF}$ .
- Note 2:** Typical values are for design information only.
- Note 3:** The limits shown are 100% tested at  $25^{\circ}\text{C}$  only. Test limits are guard-banded, based on temperature characterization to warrant compliance at temperature extremes.
- Note 4:** In this test, ACDET = High and VREGEN = High.

## DC ELECTRICAL CHARACTERISTICS (CONTINUED)

Unless otherwise indicated, all parameters apply at  $T_A = -10^\circ\text{C}$  to  $+60^\circ\text{C}$ ,  $V_{DD} = 3\text{V}$ ,  $V_{SS} = 0\text{V}$ ,  $C_5 = 10\text{ }\mu\text{F}$ ,  $C_4 = 10\text{ }\mu\text{F}$ , ACDET low. (Note 1) (Note 2) (Note 3)

Parameter	Sym.	Test Pin	Min.	Typ.	Max.	Units	Conditions
$V_{\text{REG}}$ Voltage	$V_{\text{REG}}$	15	3.92	4	4.08	V	$I_{\text{OUT}} < 20\text{ mA}$ , VREGEN high, ACDET high, $V_O = 10\text{V}$
$V_{\text{REG}}$ Load Regulation	$V_{\text{REGLD}}$	15	—	30	50	mV	$I_{\text{OUT}} = 0$ to $20\text{ mA}$ , HRNEN = High, VREGEN high, ACDET high, $V_O = 10\text{V}$
$V_{\text{REG}}$ Line Regulation	$V_{\text{REGLN}}$	15	—	—	5	mV	$V_O = 7$ to $14\text{V}$ , $I_{\text{OUT}} = 1\text{ mA}$ , HRNEN high, VREGEN high, ACDET high
IO Output Current	$IO_{\text{IH1}}$	14	25	—	60	$\mu\text{A}$	$IOEN = V_{SS}$ , $IO = 1\text{V}$ , $VO = 10\text{V}$
	$IO_{\text{IH2}}$	14	—	—	150	$\mu\text{A}$	$IOEN = V_{SS}$ , $IO = 15\text{V}$ , $VO = 10\text{V}$
	$IO_{\text{IOH1}}$	14	-4	-5	—	mA	$IOEN$ high, $IO = 3\text{V}$ , $VO = 10\text{V}$
	$IO_{\text{IOH2}}$	14	—	-5	-16	mA	$IOEN$ high, $IO = V_{SS}$ , $VO = 10\text{V}$
	$IO_{\text{IOL1}}$	14	—	10	—	mA	IO Dump Current, at falling edge of $IOEN$ , $IOEN = V_{SS}$ , $IO = 1\text{V}$ , $VO = 10\text{V}$
IO Dump	$T_{\text{IODUMP}}$	14	—	500	—	ms	IO Dump duration, at falling edge of $IOEN$ , $VO = 10\text{V}$
Input Offset Voltage	$V_{\text{GOS1}}$	7, 8, 9	-3	—	3	mV	$V_{DD} = 2\text{V}$ , $V_{\text{CM}} = 0.3\text{V}$ or $V_{\text{CM}} = 1.7\text{V}$
Common-Mode Voltage Range	$V_{\text{CMR}}$	7, 8, 9	0.3	—	$V_{DD} - 0.3$	V	—
Common-Mode Rejection Ratio	CMRR	7, 8, 9	—	80	—	dB	$V_{\text{CM}} = 0.3\text{V}$ to $V_{DD} - 0.3\text{V}$

- Note 1:** By default,  $V_O$  is forced externally with the inductor disconnected and the Boost converter is NOT running, with the exception of  $V_{VO}$  and  $V_{\text{EFF}}$ .
- Note 2:** Typical values are for design information only.
- Note 3:** The limits shown are 100% tested at  $25^\circ\text{C}$  only. Test limits are guard-banded, based on temperature characterization to warrant compliance at temperature extremes.
- Note 4:** In this test, ACDET = High and VREGEN = High.

## TEMPERATURE CHARACTERISTICS

**Electrical Characteristics:** Unless otherwise indicated.

Parameter	Sym.	Min.	Typ.	Max.	Units	Conditions
<b>Temperature Ranges</b>						
Operating Temperature Range	$T_A$	-10	—	+60	$^\circ\text{C}$	—
Storage Temperature Range	$T_{\text{STG}}$	-55	—	+125	$^\circ\text{C}$	—
<b>Thermal Package Resistances</b>						
Thermal Resistance, 16L-PDIP	$\theta_{JA}$	—	+70	—	$^\circ\text{C/W}$	—
Thermal Resistance, 16L-SOIC	$\theta_{JA}$	—	+86.1	—	$^\circ\text{C/W}$	—

# RE46C600

---

NOTES:

## 2.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in [Table 2-1](#).

**TABLE 2-1: PIN FUNCTION TABLE**

RE46C600	Name	Description
PDIP, SOIC		
1	LX	Open-drain NMOS output used to drive the boost converter inductor. The inductor should be connected from this pin to the positive supply through a low-resistance path.
2	V <sub>SS</sub>	Connect to the negative supply voltage.
3	FEED	Usually connected to the feedback electrode (F) of the piezoelectric horn through a current-limiting resistor. If not used, this pin must be connected to V <sub>SS</sub> .
4	HS	HS is a complementary output to HB and connects to the ceramic electrode (M) of the piezoelectric transducer.
5	HB	This pin is connected to the metal electrode (G) of a piezoelectric transducer.
6	HRNEN	Logic input to control the operation of the horn driver.
7	DETECT	Noninverting input of the op amp.
8	GUARD	Inverting input of the op amp.
9	OPOUT	Output of the op amp.
10	V <sub>DD</sub>	Connect to the positive supply voltage.
11	IOEN	Logic input to drive the IO to V <sub>VO</sub> .
12	ACDET	AC detect pin.
13	VREGEN	Logic input to enable the regulator.
14	IO	Output pin for connection to remote units. This pin has an internal pull-down device. High level is V <sub>VO</sub> .
15	V <sub>REG</sub>	Regulated output voltage. Nominal output is 4V.
16	V <sub>O</sub>	Regulated output voltage. Nominal output is 9V.

# RE46C600

---

NOTES:



## 3.0 DEVICE DESCRIPTION

### 3.1 Introduction

The RE46C600 provides the necessary analog and interface functions to build a microcontroller-based ionization smoke detector. This includes a low-leakage op amp, a voltage regulator for the microcontroller, a horn driver, a detector interconnect function, a boost regulator for 3-volt operation, and a power-control system that allows operation from 3V battery or AC-derived power with or without battery backup. The RE46C600 provides a simple means for the microcontroller to control the operation of the ion smoke detector and provides the necessary signaling functions during an alarm condition.

### 3.2 Ionization Sensor Detect Circuit

The RE46C600 provides a low-leakage, high-impedance op amp for an ionization smoke sensor. The unity gain stable op amp provides rail-to-rail inputs and output. The op amp output is monitored by the microcontroller to determine the smoke density.

### 3.3 Power Control System

The power control system allows the RE46C600 to be powered from a 3V battery or AC-derived power. AC power is supplied as a DC voltage derived from an AC power supply. The DC voltage is diode-connected to the  $V_O$  pin of the RE46C600. A 3V battery is connected to the  $V_{DD}$  pin for low-voltage systems. When only a 3V battery is available, the internal circuitry is powered from  $V_{DD}$ . When AC power is available, the internal circuitry is powered from  $V_{REG}$ , which is a regulated 4V.

The AC detect (ACDET) pin will disable the boost converter if ACDET is high. For a 3V battery-only system, the ACDET pin should be connected to  $V_{SS}$ , which will enable the boost converter. Under this condition, the boost converter will turn on as necessary to achieve the desired output voltage at  $V_O$ .

### 3.4 Boost Regulator

The boost regulator only operates in low-voltage applications. The ACDET pin will disable the boost converter if ACDET is high. The boost regulator can be enabled with HORNEN, or with IOEN asserted high. The boost regulator is a fixed off-time boost converter with peak current limiting. In boost operation, the peak current is nominally 0.8A. The boost regulator provides a nominal 9V on the  $V_O$  pin.

### 3.5 Voltage Regulator

The voltage regulator provides a nominal 4V output at the  $V_{REG}$  pin and is intended to power a microcontroller when AC-supplied power is available. The voltage regulator is disabled if ACDET is low. The voltage regulator is enabled if both ACDET and VREGEN are high. VREGEN has a pull-up current to  $V_{DD}$ . In normal operation, the regulator will source current up to 20 mA, but the current sinking capability is typically under 1  $\mu$ A. The voltage regulator is powered from the  $V_O$  pin. In low-voltage applications, the regulator is disabled.

### 3.6 Interconnect Operation

The interconnect circuitry provides the means for the smoke detector to be connected to other smoke detectors. The IO pin is an output-only pin that connects to other detectors. IOEN connects to the microcontroller and determines when IO is driven high. When IOEN is asserted high, the IO output acts as a current source that is biased from  $V_O$ . In low-voltage applications when IOEN is asserted high, the boost regulator will be active. This ensures there is adequate IO drive capability.

An internal sink device on the IO pin helps to discharge the interconnect line. This charge dump device is activated automatically when IOEN transitions from high to low.

### 3.7 Horn Driver

The horn driver drives a standard three-terminal piezoelectric horn connected to the HB, HS, and FEED pins. The alarm is sounded when the microcontroller drives the HRNEN pin with the required horn modulation pattern. In low-voltage applications when HRNEN is asserted high, the boost regulator is active. This ensures there is adequate horn drive capability to achieve the necessary sound pressure levels. The horn will begin to sound before the boost regulator reaches the high boost level.

# RE46C600

---

NOTES:

## 4.0 APPLICATION NOTES

### 4.1 Boost Regulator

The boost converter in Active mode (nominal  $V_O = 9V$ ) can draw current pulses of greater than 1A and is therefore very sensitive to series resistance. Critical components of this resistance are the inductor DC resistance, the internal resistance of the battery, and the resistance in the connections from the inductor to the battery, from the inductor to the LX pin, from the inductor through the boost capacitor, and from the  $V_{SS}$  pin to the battery. In order to function properly under full load at  $V_{DD} = 2V$ , the total of the inductor and interconnect resistances should not exceed  $0.3\Omega$ .

The internal battery resistance should be no more than  $0.5\Omega$  and a low-ESR capacitor of 10  $\mu F$  or more should be connected in parallel with the battery to average the current draw over the boost converter switching cycle.

The Schottky diode and inductor should be specified with a maximum operating current of 1.5A or higher. The boost capacitor should have a low ESR.

The horn driver requires a high voltage, so the piezoelectric horn can achieve the necessary sound pressure levels. The interconnect function provided by IO needs a high voltage to provide proper interconnect operation with interconnected alarms.


### 4.2 Operation Truth Table

Table 4-1 summarizes the basic logic inputs required to enable various operating modes for the RE46C600.

**TABLE 4-1: RE46C600 TRUTH TABLE**

Inputs				Outputs			
ACDET	VREGEN	HRNEN	IOEN	Boost Reg	$V_{REG}$	HORN	IO
0	0	0	0	Off	Off	Off	Off
0	1	0	0	Off	Off	Off	Off
0	0	1	0	On	Off	On	Off
0	1	1	0	On	Off	On	Off
0	0	0	1	On	Off	Off	On
0	1	0	1	On	Off	Off	On
0	0	1	1	On	Off	On	On
0	1	1	1	On	Off	On	On
1	0	0	0	Off	Off	Off	Off
1	1	0	0	Off	On	Off	Off
1	0	1	0	Off	Off	On	Off
1	1	1	0	Off	On	On	Off
1	0	0	1	Off	Off	Off	On
1	1	0	1	Off	On	Off	On
1	0	1	1	Off	Off	On	On
1	1	1	1	Off	On	On	On





**FIGURE 4-3:** Typical Application: AC Only.

# RE46C600


---

NOTES:


## 5.0 PACKAGING INFORMATION

### 5.1 Package Marking Information


16-Lead PDIP




Example



16-Lead SOIC



Example




<b>Legend:</b>	XX...X	Customer-specific information
	Y	Year code (last digit of calendar year)
	YY	Year code (last 2 digits of calendar year)
	WW	Week code (week of January 1 is week '01')
	NNN	Alphanumeric traceability code
	<sup>(e3)</sup>	Pb-free JEDEC designator for Matte Tin (Sn)
	*	This package is Pb-free. The Pb-free JEDEC designator <sup>(e3)</sup> can be found on the outer packaging for this package.

**Note:** In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information.

# RE46C600

## 16-Lead Plastic Dual In-Line (P) – 300 mil Body [PDIP]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		INCHES		
Dimension Limits		MIN	NOM	MAX
Number of Pins	N	16		
Pitch	e	.100 BSC		
Top to Seating Plane	A	–	–	.210
Molded Package Thickness	A2	.115	.130	.195
Base to Seating Plane	A1	.015	–	–
Shoulder to Shoulder Width	E	.290	.310	.325
Molded Package Width	E1	.240	.250	.280
Overall Length	D	.735	.755	.775
Tip to Seating Plane	L	.115	.130	.150
Lead Thickness	c	.008	.010	.015
Upper Lead Width	b1	.045	.060	.070
Lower Lead Width	b	.014	.018	.022
Overall Row Spacing §	eB	–	–	.430

### Notes:

- Pin 1 visual index feature may vary, but must be located within the hatched area.
- § Significant Characteristic.
- Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed .010" per side.
- Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-017B







# RE46C600

## 16-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Pins	N	16		
Pitch	e	1.27 BSC		
Overall Height	A	-	-	1.75
Molded Package Thickness	A2	1.25	-	-
Standoff §	A1	0.10	-	0.25
Overall Width	E	6.00 BSC		
Molded Package Width	E1	3.90 BSC		
Overall Length	D	9.90 BSC		
Chamfer (Optional)	h	0.25	-	0.50
Foot Length	L	0.40	-	1.27
Footprint	L1	1.04 REF		
Lead Angle	$\theta$	0°	-	-
Foot Angle	$\phi$	0°	-	8°
Lead Thickness	c	0.10	-	0.25
Lead Width	b	0.31	-	0.51
Mold Draft Angle Top	$\alpha$	5°	-	15°
Mold Draft Angle Bottom	$\beta$	5°	-	15°


### Notes:

- Pin 1 visual index feature may vary, but must be located within the hatched area.
- § Significant Characteristic
- Dimension D does not include mold flash, protrusions or gate burrs, which shall not exceed 0.15 mm per end. Dimension E1 does not include interlead flash or protrusion, which shall not exceed 0.25 mm per side.
- Dimensioning and tolerancing per ASME Y14.5M
  - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
  - REF: Reference Dimension, usually without tolerance, for information purposes only.
- Datums A & B to be determined at Datum H.

Microchip Technology Drawing No. C04-108C Sheet 2 of 2

## 16-Lead Plastic Small Outline (SL) - Narrow, 3.90 mm Body [SOIC]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



### RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E	1.27 BSC		
Contact Pad Spacing	C		5.40	
Contact Pad Width	X			0.60
Contact Pad Length	Y			1.50
Distance Between Pads	Gx	0.67		
Distance Between Pads	G	3.90		

#### Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2108A

# RE46C600

---

NOTES:

## APPENDIX A: REVISION HISTORY

### Revision D (September 2021)

- Updated the [Functional Block Diagram](#).
- Updated [Section 1.1 “Absolute Maximum Ratings†”](#).

### Revision C (December 2020)

- Initial public release of this document.
- Updated [Section 1.1 “Absolute Maximum Ratings†”](#).

### Revision B (July 2020)

- Document not publicly released.
- Updated [Section 1.1, Absolute Maximum Ratings†](#) and the [DC Electrical Characteristics](#) table.
- Minor typographical edits.

### Revision A (February 2018)

- Initial Release of this Document.  
(Document not publicly released.)

# RE46C600

---

NOTES:

## PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

<b>PART NO.</b>			
<b>Device</b>	<b>Package</b>	<b>Number of Pins</b>	<b>Tape and Reel</b>
<div> <div> <b>Device:</b> RE46C600 Ionization Smoke Detector Companion IC </div> <div> <b>Package:</b> E = Plastic Dual In-Line - 300 mil Body, 16-Lead (PDIP)  S = Plastic Small Outline - Narrow, 3.90 mm Body, 16-Lead (SOIC) </div> <div> <b>Tape and Reel:</b> T = Tape and Reel </div> </div>			
<b>Examples:</b> <div> a) RE46C600E16: Ionization Smoke Detector Companion IC, 16LD PDIP package </div> <div> b) RE46C600S16: Ionization Smoke Detector Companion IC, 16LD SOIC package </div> <div> c) RE46C600S16T: Ionization Smoke Detector Companion IC, 16LD SOIC package, Tape and Reel </div>			

# RE46C600

---

NOTES:



---

**Note the following details of the code protection feature on Microchip devices:**

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
- Microchip is willing to work with any customer who is concerned about the integrity of its code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

---

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

**Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2018-2021, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-8814-9

For information regarding Microchip's Quality Management Systems, please visit [www.microchip.com/quality](http://www.microchip.com/quality).

## Worldwide Sales and Service

### AMERICAS

**Corporate Office**  
2355 West Chandler Blvd.  
Chandler, AZ 85224-6199  
Tel: 480-792-7200  
Fax: 480-792-7277  
Technical Support:  
<http://www.microchip.com/support>  
Web Address:  
[www.microchip.com](http://www.microchip.com)

**Atlanta**  
Duluth, GA  
Tel: 678-957-9614  
Fax: 678-957-1455

**Austin, TX**  
Tel: 512-257-3370

**Boston**  
Westborough, MA  
Tel: 774-760-0087  
Fax: 774-760-0088

**Chicago**  
Itasca, IL  
Tel: 630-285-0071  
Fax: 630-285-0075

**Dallas**  
Addison, TX  
Tel: 972-818-7423  
Fax: 972-818-2924

**Detroit**  
Novi, MI  
Tel: 248-848-4000

**Houston, TX**  
Tel: 281-894-5983

**Indianapolis**  
Noblesville, IN  
Tel: 317-773-8323  
Fax: 317-773-5453  
Tel: 317-536-2380

**Los Angeles**  
Mission Viejo, CA  
Tel: 949-462-9523  
Fax: 949-462-9608  
Tel: 951-273-7800

**Raleigh, NC**  
Tel: 919-844-7510

**New York, NY**  
Tel: 631-435-6000

**San Jose, CA**  
Tel: 408-735-9110  
Tel: 408-436-4270

**Canada - Toronto**  
Tel: 905-695-1980  
Fax: 905-695-2078

### ASIA/PACIFIC

**Australia - Sydney**  
Tel: 61-2-9868-6733

**China - Beijing**  
Tel: 86-10-8569-7000

**China - Chengdu**  
Tel: 86-28-8665-5511

**China - Chongqing**  
Tel: 86-23-8980-9588

**China - Dongguan**  
Tel: 86-769-8702-9880

**China - Guangzhou**  
Tel: 86-20-8755-8029

**China - Hangzhou**  
Tel: 86-571-8792-8115

**China - Hong Kong SAR**  
Tel: 852-2943-5100

**China - Nanjing**  
Tel: 86-25-8473-2460

**China - Qingdao**  
Tel: 86-532-8502-7355

**China - Shanghai**  
Tel: 86-21-3326-8000

**China - Shenyang**  
Tel: 86-24-2334-2829

**China - Shenzhen**  
Tel: 86-755-8864-2200

**China - Suzhou**  
Tel: 86-186-6233-1526

**China - Wuhan**  
Tel: 86-27-5980-5300

**China - Xian**  
Tel: 86-29-8833-7252

**China - Xiamen**  
Tel: 86-592-2388138

**China - Zhuhai**  
Tel: 86-756-3210040

### ASIA/PACIFIC

**India - Bangalore**  
Tel: 91-80-3090-4444

**India - New Delhi**  
Tel: 91-11-4160-8631

**India - Pune**  
Tel: 91-20-4121-0141

**Japan - Osaka**  
Tel: 81-6-6152-7160

**Japan - Tokyo**  
Tel: 81-3-6880-3770

**Korea - Daegu**  
Tel: 82-53-744-4301

**Korea - Seoul**  
Tel: 82-2-554-7200

**Malaysia - Kuala Lumpur**  
Tel: 60-3-7651-7906

**Malaysia - Penang**  
Tel: 60-4-227-8870

**Philippines - Manila**  
Tel: 63-2-634-9065

**Singapore**  
Tel: 65-6334-8870

**Taiwan - Hsin Chu**  
Tel: 886-3-577-8366

**Taiwan - Kaohsiung**  
Tel: 886-7-213-7830

**Taiwan - Taipei**  
Tel: 886-2-2508-8600

**Thailand - Bangkok**  
Tel: 66-2-694-1351

**Vietnam - Ho Chi Minh**  
Tel: 84-28-5448-2100

### EUROPE

**Austria - Wels**  
Tel: 43-7242-2244-39  
Fax: 43-7242-2244-393

**Denmark - Copenhagen**  
Tel: 45-4485-5910  
Fax: 45-4485-2829

**Finland - Espoo**  
Tel: 358-9-4520-820

**France - Paris**  
Tel: 33-1-69-53-63-20  
Fax: 33-1-69-30-90-79

**Germany - Garching**  
Tel: 49-8931-9700

**Germany - Haan**  
Tel: 49-2129-3766400

**Germany - Heilbronn**  
Tel: 49-7131-72400

**Germany - Karlsruhe**  
Tel: 49-721-625370

**Germany - Munich**  
Tel: 49-89-627-144-0  
Fax: 49-89-627-144-44

**Germany - Rosenheim**  
Tel: 49-8031-354-560

**Israel - Ra'anana**  
Tel: 972-9-744-7705

**Italy - Milan**  
Tel: 39-0331-742611  
Fax: 39-0331-466781

**Italy - Padova**  
Tel: 39-049-7625286

**Netherlands - Drunen**  
Tel: 31-416-690399  
Fax: 31-416-690340

**Norway - Trondheim**  
Tel: 47-7288-4388

**Poland - Warsaw**  
Tel: 48-22-3325737

**Romania - Bucharest**  
Tel: 40-21-407-87-50

**Spain - Madrid**  
Tel: 34-91-708-08-90  
Fax: 34-91-708-08-91

**Sweden - Gothenberg**  
Tel: 46-31-704-60-40

**Sweden - Stockholm**  
Tel: 46-8-5090-4654

**UK - Wokingham**  
Tel: 44-118-921-5800  
Fax: 44-118-921-5820

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[RE46C600E16](#) [RE46C600S16](#) [RE46C600S16T](#)