



Microtips

TECHNOLOGY

Model No: AWK-800480T50PC09

Approved By	

Tel: 1 (888) 499-8477

Fax: (407) 273-0771

E-mail: mtusainfo@microtipsusa.com

Web: www.microtipsusa.com

<i>Product Specification</i>	<i>Model:</i>	AWK-800480T50PC09	<i>Rev. No.</i>	<i>Issued Date.</i>	<i>Page.</i>
			B	2019/09/24	2/26

Revision Record

Rev No.	Rev Date	Contents	Note
A	2019/07/18	New issue.	
B	2019/09/24	Modify backlight voltage	

<i>Product Specification</i>	<i>Model:</i>	AWK-800480T50PC09	<i>Rev. No.</i>	<i>Issued Date.</i>	<i>Page.</i>
			<i>B</i>	2019/09/24	3/26

Table of Contents

List	Description	Page No.
	Cover	1
	Revision Record	2
	Table of Contents	3
1	Scope	4
2	General Information	4
3	External Dimensions	5
4	Interface Description	6
5	Absolute Maximum Ratings	7
6	DC Characteristics	7
7	Timing Characteristics	8
8	Backlight Characteristics	15
9	Optical Characteristics	16
10	Reliability Test Conditions and Methods	18
11	Inspection Standard	19
12	Handling Precautions	23
13	Precaution for Use	25

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	4/26

1. Scope

This specification defines general provisions as well as inspection standards for TFT module supplied by Microtips Technology. If the event of unforeseen problem or unspecified items may occur naturally shall negotiate and agree to solution

2. General Information

TFT


ITEM	STANDARD VALUES	UNITS
LCD type	5.0" TFT	--
Dot arrangement	800 (RGB)×480	dots
Color filter array	RGB vertical stripe	--
Display mode	Normally Black IPS	-
Eyes Viewing Direction	80/80/80/80	
Driver IC	ST7262	--
Module size	121.7(W)×76.8(H)×4.75(T)	mm
Active area	108.0(W)×64.80(H)	mm
Dot pitch	0.135(W)×0.135(H)	mm
Interface	24-bit Parallel RGB Interface	--
Operating temperature	-30 ~ +85	°C
Storage temperature	-30 ~ +85	°C
Back Light	16 White LEDS	--

CTP

Item	Standard Values	Units
CTP type	Glass + Glass + FPC	--
CTP Driver IC	FT5436	--
Surface hardness	6	H
Transmittance	≥83	%
Operation Voltage	2.8 - 3.6	V
CTP size	121.70 (W)×76.80 (H)×1.95(T)	mm
LENS Viewing area	107.4(W)×64.2(H)	mm
CTP Interface	I ² C	-
Pointing Stick	5	-

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	5/26

3. External Dimensions



Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	6/26

4. Interface Description

PIN NO.	PIN NAME	DESCRIPTION
1	VLED-	LED backlight (Cathode).
2	VLED+	LED backlight (Anode).
3	GND	Ground.
4	VDD	Power supply
5~12	R0~R7	Red Data
13~20	G0~G7	Green Data
21~28	B0~B7	Blue Data
29	GND	Ground.
30	PCLK	Clock
31	DISP	Display on/off
32	HSYNC	Horizontal sync input in RGB mode.
33	VSYNC	Vertical sync input in RGB mode.
34	DE	Data enable input. Active high to enable the input data bus.
35	NC	NC
36	GND	Ground.
37	NC	NC
38	NC	NC
39	NC	NC
40	NC	NC

CTP

Pin	Symbol	Description
1	VCC	Digital Power.
2	GND	Power ground
3	SCL	I ² C_clock.
4	SDA	I ² C_date.
5	INT	Interruption signal.
6	RST	Rest pin.Active low to enter reset state.

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	7/26

5. Absolute Maximum Ratings

Item	Symbol	Min.	Max.	Unit
Power supply	VDD	-0.3	4.0	V
CTP Power supply	VCC	-0.3	3.6	V
Input Voltage	V _{in}	-0.3	VDD +0.3	V
Operating Temperature	TOP	-30	85	°C
Storage Temperature	TST	-30	85	°C
Storage Humidity	HD	20	90	%RH

6. DC Characteristics


Item	Symbol	Min.	Typ.	Max.	Unit	Remark
Power supply	VDD	3.0	3.3	3.6	V	-
Power supply current	IVDD	TBD	TBD	TBD	mA	-
CTP Power supply	VCC	2.8	3.3	3.6	V	-
Input High Voltage	V _{IH}	0.7VDD	-	VDD	V	-
Input Low Voltage	V _{IL}	GND	-	0.3 VDD	V	-
Output High Voltage	V _{OH}	VDD-0.4	-	VDD	V	-
Output Low Voltage	V _{OL}	GND	-	GND+0.4	V	-
I/O Leak Current	ILI	-1	-	1	uA	-

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	8/26

7. Timing Characteristics

7.1. AC Timing characteristics

System Bus Timing for RGB Interface




Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	9/26

Item	Symbol	Min.	Typ.	Max.	Unit	Conditions
CLK Pulse Duty	Tcw	40	50	60	%	
HSYNC Width	Thw	2	-	-	DCLK	
HSYNC Period	Th	55	60	65	us	
VSYNC Setup Time	Tvst	12	-	-	ns	
VSYNC Hold Time	Tvhd	12	-	-	ns	
HSYNC Setup Time	Thst	12	-	-	ns	
HSYNC Hold Time	Thhd	12	-	-	ns	
Data Setup Time	Tdsu	12	-	-	ns	
Data Hold Time	Tdhd	12	-	-	ns	
DE Setup Time	Tdest	12	-	-	ns	
DE Hold Time	Tdehd	12	-	-	ns	


7.2. RGB INTERFACE

SYNC Mode




Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	10/26

SYNC-DE Mode



Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	11/26

DE Mode



RGB Mode Selection Table	DCLK	HSYNC	VSYNC	DE
SYNC - DE Mode	Input	Input	Input	Input
SYNC Mode	Input	Input	Input	GND
DE Mode	Input	GND	GND	Input

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	12/26

Parallel 24-bit RGB Interface Timing Table						
Item	Symbol	Min.	Typ.	Max.	Unit	Remark
DCLK Frequency	Fclk	23	25	27	MHz	
HSYNC	Period Time	Th	808	816	896	DCLK
	Display Period	Thdisp	800			DCLK
	Back Porch	Thbp	4	8	48	DCLK
	Front Porch	Thfp	4	8	48	DCLK
	Pulse Width	Thw	2	4	8	DCLK
VSYNC	Period Time	Tv	488	496	504	HSYNC
	Display Period	Tvdisp	480			HSYNC
	Back Porch	Tvbp	4	8	12	HSYNC
	Front Porch	Tvfp	4	8	12	HSYNC
	Pulse Width	Tvw	2	4	8	HSYNC


7.3. CTP Timing

7.3.1 AC Characteristics

Table 3-3 AC Characteristics of TX & RX


Item	Symbol	Test Condition	Min	Typ	Max	Unit	Note
TX acceptable clock	ftx		--	150	--	KHz	
TX output rise time	Ttxr		--	140	--	nS	
TX output fall time	Ttxf		--	140	--	nS	
RX input voltage	Trxi		1.2	--	1.6	V	

7.3.2 I2C




I2C Serial Data Transfer Format

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	13/26





I2C master write, slave read




I2C master read, slave write

7.3.3 POWER ON/Reset Sequence

Reset should be pulled down to be low before powering on and powering down. I2C shouldn't be used by other devices during Reset time after VDD powering on (Trtp). INT signal will be sent to the host after initializing all parameters and then start to report points to the host. If Power is down, the voltage of supply must be below 0.3V and Trst is more than 1ms.




Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	14/26



Power on Sequence


Reset time must be enough to guarantee reliable reset, the time of starting to report point after resetting approach to the time of starting to report point after powering on.



Reset Sequence

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	15/26


8. Backlight Characteristic



Item	Symbol	MIN	TYP	MAX	UNIT	Test Condition
Supply Voltage	Vf	22	24	26	V	If=80mA
Supply Current	If	-	80	-	mA	
Life Time	-	-	20000	-	Hr	If=80mA
Backlight Color	White					


Note 1: The LED Supply Voltage is defined by the number of LED at Ta=25°C and If =80mA.

Note 2: LED current is measured by utilizing a high frequency current meter as shown below:



Note 3: The “LED life time” is defined as the module brightness decrease to 50% original brightness at Ta=25°C and If = 80mA. The LED lifetime could be decreased if operating If is larger than 80mA.

Note 4: LED light bar circuit:




Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	16/26

9. Optical Characteristics


Item	Conditions	Min.	Typ.	Max.	Unit	Note
Viewing Angle (CR>10)	Horizontal	θL	-	80	-	(1),(2),(6)
		θR	-	80	-	
	Vertical	θT	-	80	-	
		θB	-	80	-	
Luminous Intensity for LCM	-	750	800	-	cd/m2	If=40mA
Uniformity for LCM	-	80	-	-	%	If=40mA
Contrast Ratio	Center	(800)	(1000)	-	-	(1),(3),(6)
Response Time	Rising + Falling	-	30	40	ms	(1),(4),(6)
CF Color Chromaticity (CIE1931)	White x	0.260	0.310	0.360	-	(1), (6)
	White y	0.289	0.339	0.389	-	
	Red x	0.523	0.573	0.623	-	
	Red y	0.303	0.353	0.403	-	
	Green x	0.318	0.368	0.418	-	
	Green y	0.526	0.576	0.626	-	
	Blue x	0.088	0.138	0.188	-	
	Blue y	0.044	0.094	0.144	-	

Note (1) Measurement Setup: The LCD module should be stabilized at given temp. 25°C for 15 minutes to avoid abrupt temperature change during measuring. In order to stabilize the luminance, the measurement should be executed after lighting backlight for 15 minutes in a windless room.



Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	17/26

Note (2) Definition of Viewing Angle




Note (3) Definition of Contrast Ratio (CR)

The contrast ratio can be calculated by the following expression

$$\text{Contrast Ratio (CR)} = L_{63} / L_0$$

L63: Luminance of gray level 63, L0: Luminance of gray level 0

Note (4) Definition of response time



Note (5) Definition of Transmittance (Module is without signal input)

$$\text{Transmittance} = \text{Center Luminance of LCD} / \text{Center Luminance of Back Light} \times 100\%$$

Note (6) Definition of color chromaticity (CIE1931)

Color coordinates measured at the center point of LCD

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	18/26

10. Reliability Test Conditions and Methods

No.	Test Items	Test Condition	Inspection After Test
①	High Temperature Storage	85°C±2°C×96Hours	Inspection after 2~4hours storage at room temperature, the samples should be free from defects: 1, Air bubble in the LCD. 2, Seal leak. 3, Non-display. 4, Missing segments. 5, Glass crack. 6, Current IDD is twice higher than initial value. 7, The surface shall be free from damage. 8, The electric characteristic requirements shall be satisfied.
②	Low Temperature Storage	-30°C±2°C×96Hours	
③	High Temperature Operating	85°C±2°C×96Hours	
④	Low Temperature Operating	-30°C±2°C×96Hours	
⑤	Temperature Cycle(Storage)	-20°C (30min) ↔ 25°C (5min) ↔ 70°C (30min) 1 cycle Total 10cycle	
⑥	Damp Proof Test (Storage)	50°C±5°C×90%RH×96Hours	
⑦	Vibration Test	Frequency:10Hz~55Hz~10Hz Amplitude:1.5mm X,Y,Z direction for total 3hours (packing condition test will be tested by a carton)	
⑧	Drooping Test	Drop to the ground from 1M height one time every side of carton. (packing condition test will be tested by a carton)	
⑨	ESD Test	Voltage:±8KV,R:330Ω,C:150PF,Air Mode,10times	

REMARK:

- 1, The Test samples should be applied to only one test item.
- 2, Sample side for each test item is 5~10pcs.
- 3,For Damp Proof Test, Pure water(Resistance> 10MΩ)should be used.
- 4,In case of malfunction defect caused by ESD damage, if it would be recovered to normal state after resetting, it would be judge as a good part.
- 5, EL evaluation should be accepted from reliability test with humidity and temperature: Some defects such as black spot/blemish can happen by natural chemical reaction with humidity and Fluorescence EL has.
- 6, Failure Judgment Criterion: Basic Specification Electrical Characteristic, Mechanical Characteristic, Optical Characteristic.

<i>Product Specification</i>	<i>Model:</i>	AWK-800480T50PC09	<i>Rev. No.</i>	<i>Issued Date.</i>	<i>Page.</i>
			B	2019/09/24	19/26

11. Inspection Standard

11.1 Scope

Specifications contain

11.1.1 Display Quality Evaluation

11.1.2 Mechanics Specification

11.2 Sampling Plan

Unless there is other agreement, the sampling plan for incoming inspection shall follow MIL-STD-105E.

11.2.1 Lot size: Quantity per shipment as one lot (different model as different lot).

11.2.2 Sampling type: Normal inspection, single sampling.

11.2.3 Sampling level: Level II.

11.2.4 AQL: Acceptable Quality Level

Major defect: AQL=0.65

Minor defect: AQL=1.5

11.3 Panel Inspection Condition

11.3.1 Environment:

Room Temperature: 25±5°C.

Humidity: 65±5% RH.

Illumination: 300 ~ 700 Lux.

11.3.2 Inspection Distance:

35±5 cm

11.3.3 Inspection Angle:

The vision of inspector should be perpendicular to the surface of the Module.

11.3.4 Inspection time :

Perceptibility Test Time: 20 seconds max.


Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	20/26

11.4 Inspection Plan








Class	Item	Judgment	Class
Packing & Indicate	1. Outside and inside package.	"MODEL NO.", "LOT NO." and "QUANTITY" should indicate on the package.	Minor
	2. Model mixed and quantity.	Other model mixed.....Rejected. Quantity short or over.....Rejected.	Critical
	3. Product indication.	"MODEL NO." should indicate on the product.	Major
Assembly	4. Dimension, LCD glass scratch and scribe defect.	According to specification or drawing.	Major
Appearance	5. Viewing area.	Polarizer edge or LCD's sealing line is visible in the viewing area.....Rejected.	Minor
	6. Blemish, black spot, white spot in the LCD and LCD glass cracks.	According to standard of visual inspection.(inside viewing area)	Minor
	7. Blemish, black spot, white spot and scratch on the polarizer.	According to standard of visual inspection.(inside viewing area)	Minor
	8. Bubble in polarizer.	According to standard of visual inspection.(inside viewing area)	Minor
	9. LCD's rainbow color.	Strong deviation color (or newton ring) of LCD.....Rejected. Or according to limited sample.(if needed, and inside viewing area)	Minor
Electrical	10. Electrical and optical characteristics.(contrast Vop chromaticity....etc)	According to specification or drawing.(inside viewing area)	Critical
	11. Missing line.	Missing dot line character.....Rejected.	Critical
	12.Short circuit. Wrong pattern display.	No display, wrong pattern display, current consumption. Out of specification.....Rejected.	Critical
	13. Dot defect.(for color and TFT)	According to standard of visual Inspection.	Minor

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	21/26

11.5 Standard Of Visual Inspection




NO.	CLASS	ITEM	JUDGMENT																				
11.5.1	Minor	Black and white spot. Foreign materiel. Dust. Blemish. Scratch.	(A) Round type: Unit: mm <table><tr><td>Diameter (mm.)</td><td>Acceptable Q'tv</td></tr><tr><td>$\Phi \leq 0.2$</td><td>Disregard</td></tr><tr><td>$0.2 < \Phi \leq 0.25$</td><td>1(Distance>5mm)</td></tr><tr><td>$0.25 < \Phi$</td><td>0</td></tr></table> <p>Note: $\Phi = (\text{length}+\text{width})/2$</p> <p>(B) Linear type: Unit: mm <table><tr><td>Length</td><td>Width (mm.)</td><td>Acceptable Q'tv</td></tr><tr><td>--</td><td>$W \leq 0.03$</td><td>Disregard</td></tr><tr><td>$L \leq 5.0$</td><td>$0.03 < W \leq 0.05$</td><td>2(Distance>5mm)</td></tr><tr><td>--</td><td>$0.05 < W$</td><td>FOLLOW ROUND TYPE</td></tr></table></p>	Diameter (mm.)	Acceptable Q'tv	$\Phi \leq 0.2$	Disregard	$0.2 < \Phi \leq 0.25$	1(Distance>5mm)	$0.25 < \Phi$	0	Length	Width (mm.)	Acceptable Q'tv	--	$W \leq 0.03$	Disregard	$L \leq 5.0$	$0.03 < W \leq 0.05$	2(Distance>5mm)	--	$0.05 < W$	FOLLOW ROUND TYPE
Diameter (mm.)	Acceptable Q'tv																						
$\Phi \leq 0.2$	Disregard																						
$0.2 < \Phi \leq 0.25$	1(Distance>5mm)																						
$0.25 < \Phi$	0																						
Length	Width (mm.)	Acceptable Q'tv																					
--	$W \leq 0.03$	Disregard																					
$L \leq 5.0$	$0.03 < W \leq 0.05$	2(Distance>5mm)																					
--	$0.05 < W$	FOLLOW ROUND TYPE																					
11.5.2	Minor	Dent on polarizer.	Unit: mm. <table><tr><td>Diameter</td><td>Acceptable Q'tv</td></tr><tr><td>$\Phi \leq 0.2$</td><td>Disregard</td></tr><tr><td>$0.2 < \Phi \leq 0.5$</td><td>2(Distance>5mm)</td></tr><tr><td>$0.5 < \Phi$</td><td>0</td></tr></table>	Diameter	Acceptable Q'tv	$\Phi \leq 0.2$	Disregard	$0.2 < \Phi \leq 0.5$	2(Distance>5mm)	$0.5 < \Phi$	0												
Diameter	Acceptable Q'tv																						
$\Phi \leq 0.2$	Disregard																						
$0.2 < \Phi \leq 0.5$	2(Distance>5mm)																						
$0.5 < \Phi$	0																						
11.5.3	Minor	Bubble in polarizer.	Unit: mm. <table><tr><td>Diameter</td><td>Acceptable Q'tv</td></tr><tr><td>$\Phi \leq 0.2$</td><td>Disregard</td></tr><tr><td>$0.2 < \Phi \leq 0.5$</td><td>2(Distance>5mm)</td></tr><tr><td>$0.5 < \Phi$</td><td>0</td></tr></table>	Diameter	Acceptable Q'tv	$\Phi \leq 0.2$	Disregard	$0.2 < \Phi \leq 0.5$	2(Distance>5mm)	$0.5 < \Phi$	0												
Diameter	Acceptable Q'tv																						
$\Phi \leq 0.2$	Disregard																						
$0.2 < \Phi \leq 0.5$	2(Distance>5mm)																						
$0.5 < \Phi$	0																						
11.5.4	Minor	Dot defect	<table><tr><td>Items</td><td>Acceptable Q'tv</td></tr><tr><td>Bright dot</td><td>$N \leq 1$</td></tr><tr><td>Dark dot</td><td>$N \leq 1$</td></tr><tr><td>Total dot</td><td>$N \leq 2$</td></tr></table> <p>Pixel define : </p> <p>Note1: The definition of dot: The size of a defective dot over 1/2 of whole dot is regarded as one defective dot.</p> <p>Note 2: Bright dot: Dots appear bright and unchanged in size in which LCD panel is displaying under black pattern.</p> <p>Note 3: The bright dot defect must be visible through 2% ND filter</p> <p>Note 4: Dark dot: Dots appear dark and unchanged in size in which LCD panel is displaying under pure red, green, blue pattern.</p>	Items	Acceptable Q'tv	Bright dot	$N \leq 1$	Dark dot	$N \leq 1$	Total dot	$N \leq 2$												
Items	Acceptable Q'tv																						
Bright dot	$N \leq 1$																						
Dark dot	$N \leq 1$																						
Total dot	$N \leq 2$																						

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	22/26

No.	Class	Item	Judgment
11.5.5	Minor	LCD glass chipping.	 $Y > S$ Reject
11.5.6	Minor	LCD glass chipping.	 $X \text{ or } Y > S$ Reject
11.5.7	Major	LCD glass crack.	 $Y > (1/2) T$ Reject
11.5.8	Major	LCD glass scribe defect.	 <p>1. $a > L/3$, $A > 1.5\text{mm}$ Reject 2. B : According to dimension</p>
11.5.9	Minor	LCD glass chipping. (on the terminal area)	 $\Phi = (x+y)/2 > 2.5\text{mm}$ Reject
11.5.10	Minor	LCD glass chipping. (on the terminal surface)	 $Y > (1/3) T$ Reject
11.5.11	Minor	LCD glass chipping.	 $Y > T$ Reject

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	23/26

11.6. Inspection Standard Of Touch Panel

No.	Class	Items		Judgment
11.6.1	Major	Touch panel crack.		 Reject
11.6.2	Minor	Touch panel chipping.	Corner.	
			Edge.	
11.6.3	Minor	Scratch. Dust and foreign materiel. (linear type)	$W \leq 0.03$	Accept
			$0.03\text{mm} < W \leq 0.07\text{mm}$, $L \leq 5.0\text{mm}$ (Distance > 5mm)	Accept 2 ea Max.
			$W > 0.07\text{mm}$	Reject
11.6.4	Minor	Scratch. Dust and foreign materiel (round type: $\phi = (\text{length} + \text{width})/2$)	$\Phi \leq 0.2\text{mm}$	Accept
			$0.2\text{mm} < \Phi \leq 0.25\text{mm}$ (Distance > 5mm)	Accept 1 ea Max.
			$\Phi > 0.25\text{mm}$	Reject
11.6.5	Minor	Touch panel dent / fish eyes.	$\Phi \leq 0.2\text{mm}$	Accept
			$0.2\text{mm} < \Phi \leq 0.5\text{mm}$ (Distance > 5mm)	Accept 2 ea Max.
			$\Phi > 0.5\text{mm}$	Reject
11.6.6	Minor	Touch panel air bubble.	$\Phi \leq 0.2\text{mm}$	Accept
			$0.2\text{mm} < \Phi \leq 0.5\text{mm}$ (Distance > 5mm)	Accept 2 ea Max.
			$\Phi > 0.5\text{mm}$	Reject
11.6.7	Minor	Touch panel printing area scratch.	$W \leq 0.03\text{mm}$	Accept
			$0.03\text{mm} < W \leq 0.05\text{mm}$, $L \leq 5.0\text{mm}$ (Distance > 5mm)	Accept 2 ea Max.
			$W > 0.05$ ($W > 0.05$ follow 11.6.4 round type)	Reject
11.6.8	Minor	Touch panel white haze mark / dust.		Can not be removed Reject

Product Specification	Model:	AWK-800480T50PC09	Rev. No.	Issued Date.	Page.
			B	2019/09/24	24/26

12. Handling Precautions

12.1 Mounting Method

The LCD panel of Microtips TFT module consists of two thin glass plates with polarizers which easily be damaged. And since the module is so constructed as to be fixed by utilizing fitting holes in the printed circuit board.

Extreme care should be needed when handling the LCD modules.

12.2 Caution of LCD Handling And Cleaning

When cleaning the display surface, Use soft cloth with solvent

[Recommended below] and wipe lightly

- Isopropyl alcohol
- Ethyl alcohol

Do not wipe the display surface with dry or hard materials that will damage the polarizer surface.

Do not use the following solvent:

- Water
- Aromatics

Do not wipe ITO pad area with the dry or hard materials that will damage the ITO patterns

Do not use the following solvent on the pad or prevent it from being contaminated:

- Soldering flux
- Chlorine (Cl) , Sulfur (S)

If goods were sent without being silicon coated on the pad, ITO patterns could be damaged due to the corrosion as time goes on.

If ITO corrosion happens by miss-handling or using some materials such as Chlorine (Cl), Sulfur (S) from customer, Responsibility is on customer.

12.3 Caution Against Static Charge

The LCD module uses C-MOS LSI drivers, so we recommend that you:

Connect any unused input terminal to power or ground, do not input any signals before power is turned on, and ground your body, work/assembly areas, and assembly equipment to protect against static electricity.

12.4 Packing

- Module employs LCD elements and must be treated as such.
- Avoid intense shock and falls from a height.
- To prevent modules from degradation, do not operate or store them exposed directly to sunshine or high temperature/humidity

<i>Product Specification</i>	<i>Model:</i>	AWK-800480T50PC09	<i>Rev. No.</i>	<i>Issued Date.</i>	<i>Page.</i>
			B	2019/09/24	25/26

12.5 Caution for operation

- It is an indispensable condition to drive LCD's within the specified voltage limit since the higher voltage than the limit causes the shorter LCD life.
- An electrochemical reaction due to direct current causes LCD's undesirable deterioration, so that the use of direct current drive should be avoided.
- Response time will be extremely delayed at lower temperature than the operating temperature range and on the other hand at higher temperature LCD's show dark color in them. However those phenomena do not mean malfunction or out of order with LCD's, which will come back in the specified operation temperature.
- If the display area is pushed hard during operation, some font will be abnormally displayed but it resumes normal condition after turning off once.
- Slight dew depositing on terminals is a cause for electro-chemical reaction resulting in terminal open circuit.

Usage under the maximum operating temperature, 50%Rh or less is required.

12.6 Storing

In the case of storing for a long period of time for instance, for years for the purpose or replacement use, the following ways are recommended.

- Storage in a polyethylene bag with the opening sealed so as not to enter fresh air outside in it. And with no desiccant.
- Placing in a dark place where neither exposure to direct sunlight nor light's keeping the storage temperature range.
- Storing with no touch on polarizer surface by anything else.

[It is recommended to store them as they have been contained in the inner container at the time of delivery from us]

12.7 Safety

- It is recommendable to crash damaged or unnecessary LCD's into pieces and wash off liquid crystal by either of solvents such as acetone and ethanol, which should be burned up later.
- When any liquid leaked out of a damaged glass cell comes in contact with your hands, please wash it off well with soap and water

<i>Product Specification</i>	<i>Model:</i>	AWK-800480T50PC09	<i>Rev. No.</i>	<i>Issued Date.</i>	<i>Page.</i>
			B	2019/09/24	26/26

13. Precaution for Use

13.1

A limit sample should be provided by the both parties on an occasion when the both parties agreed its necessity. Judgment by a limit sample shall take effect after the limit sample has been established and confirmed by the both parties.

13.2

On the following occasions, the handing of problem should be decided through discussion and agreement between responsible of the both parties.

- When a question is arisen in this specification
- When a new problem is arisen which is not specified in this specifications
- When an inspection specifications change or operating condition change in customer is reported to Microtips TFT , and some problem is arisen in this specification due to the change
- When a new problem is arisen at the customer's operating set for sample evaluation in the customer site.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microtips Technology:](#)

[AWK-800480T50PC09](#)