General-purpose Relay

Slim and Space-saving Power Plug-in Relay

- Reduces wiring work by 60% when combined with the P2RF-□-PU Push-In Plus Socket (according to actual OMRON measurements).
- Lockable test button models available.
- Built-in mechanical operation indicator.
- Provided with nameplate.
- AC type is equipped with a coil-disconnection self-diagnostic function (LED type).
- High switching power (1-pole: 10 A).

🔊 🛞 🗁 C E LR



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

(S): Models with mechanical operation indicator and Nameplate

Model Number Structure

Model Number Legend



NDI: LED indicator and diode with test button

Note: Contact your OMRON representative for Relays with gold-plated contacts.

Ordering Information When your order, specify the rated voltage.

List of Models

Classification	Coil ratings	Contact form		
	Containigs	SPDT	DPDT	
General-purpose		G2R-1-S (S)	G2R-2-S (S)	
LED indicator	AC 24, 48, 110, 120, 230, 240 DC 6, 12, 24, 48	G2R-1-SN (S)	G2R-2-SN (S)	
LED indicator with test button	000, 12, 24, 40	G2R-1-SNI (S)	G2R-2-SNI (S)	
Diode		G2R-1-SD (S)	G2R-2-SD (S)	
LED indicator and diode	DC 6, 12, 24, 48	G2R-1-SND (S)	G2R-2-SND (S)	
LED indicator and diode with test button		G2R-1-SNDI (S)	G2R-2-SNDI (S)	

4. Rated Coil Voltage

5. Mechanical operation indicator and Nameplate

2. Refer to Connecting Sockets, below, for applicable Socket models.

 When ordering, add the rated coil voltage and "(S)" to the model number. Rated coil voltages are given in the coil ratings table. Example: G2R-1-S <u>12 VDC</u> (S)

-Rated coil voltage

OMRON

Accessories (Order Separately) Connecting Sockets

		Track/surface	-mounting Socket	Back-mounting Socket		
Applicable Relay model		Push-In Plus Terminal Blocks	Screw terminals *	PCB terminals	Solder terminals	
No. of poles		Model	Models	Models	Model	
1 pole	G2R-1-S (S)	P2RF-05-PU	P2RFZ-05-E P2RF-05 P2RF-05-E	P2R-05P P2R-057P	P2R-05A	
2 poles	G2R-2-S (S)	P2RF-08-PU	P2RFZ-08-E P2RF-08 P2RF-08-E	P2R-08P P2R-087P	P2R-08A	

Accessories for Push-In Plus Terminal Block Sockets (P2RF-□-PU) Short Bars

Pitch	No. of poles	Colors	Model *	Minimum order (quantity)
7.75 mm	2		PYDN-7.75-020□	
	3	Red (R) Blue (S) Yellow (Y)	PYDN-7.75-030	
	4		PYDN-7.75-040	10
	20		PYDN-7.75-200	
15.5 mm	8		PYDN-15.5-080	

Note: Use the Short Bars for crossover wiring within one Socket or between Sockets. * Replace the box (\Box) in the model number with the code for the covering color.

Labels

Model	Minimum order (sheet) (quantity per sheet)
XW5Z-P4.0LB1	5 1 sheet (60 pieces)

Accessories for Screw Terminal Sockets (P2RFZ-□-E) Short Bars

Pitch	No. of poles	Colors	Model	Minimum order (set)
6.8 mm	10		P2DN-6.8-100S	
15.7 mm	10	Blue (S)	P2DN-15.7-100S	10 short bars and 20 caps.

Note: 1. Use the Short Bars for crossover wiring within one Socket or between Sockets.
2. Cannot be used on the P2RF-□-E.

Labels

Model	Minimum order (sheet) (quantity per sheet)
XW5Z-P2.5LB1	5 1 sheet (72 pieces)

Accessories for Short Bars (P2DN) Cap

Model	Minimum order (bag)
P2DN-CP100	1 (100 pcs./bag)

Mounting Tracks

Applicable Socket	Des	cription	Model	Minimum order (quantity)
Track-connecting Socket		50 cm (ℓ) × 7.3 mm (t):	PFP-50N	
	Mounting track	1 m (ℓ) × 7.3 mm (t):	PFP-100N	
		1 m (ℓ) × 16 mm (t):	PFP-100N2	
	End plate *1		PFP-M	10
	Spacer		PFP-S	10
Back-connecting Socket	Mounting plate *2		P2R-P	1

*1. When mounting DIN rail, please use End Plate (PFP-M).

*2. Used to mount several P2R-05A and P2R-08A Connecting Sockets side by side.

Specifications

Coil Ratings

Rat	ed voltage	Rated current*		d current* Coil		ctance (H) /alue)	Must operate voltage	Must release voltage	Max. voltage	Power consumption	
		50 Hz	60 Hz	resistance	Armature OFF	Armature ON	ture % of rated v		age	(approx.)	
	24 V	43.5 mA	37.4 mA	253 Ω	0.81	1.55					
	48 V	21.8 mA	18.8 mA	1,040 Ω	3.12	6.17			- may 1109/		
A.C.	110 V	9.5 mA	8.2 mA	5,566 Ω	13.33	26.83	000/ may	000/			
AC	120 V	8.6 mA	7.5 mA	7,286 Ω	16.13	32.46	80% max.	80% max. 30% max	50 % max.	max. 110%	0.9 VA at 60 Hz
	230 V	4.4 mA	3.8 mA	27,172 Ω	72.68	143.90					
	240 V	4.2 mA	3.7 mA	27,800 Ω	90.58	182.34	1				

Rated voltage		Rated current*	Coil	Coil inductance (H) (ref. value)		Must operate voltage	Must release voltage	Max. voltage	Power consumption
			resistance	Armature OFF	Armature ON	% of rated voltage		(approx.)	
	6 V	87.0 mA	69 Ω	0.25	0.48				
DC	12 V	43.2 mA	278 Ω	0.98	2.35	70% max	% max. 15% min.	110%	0.53 W
DC	24 V	21.6 mA	1,113 Ω	3.60	8.25	70% max.			
	48 V	11.4 mA	4,220 Ω	15.2	29.82				

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C with tolerances of +15%/-20% for the AC rated current and ±10% for the DC coil resistance.

2. The AC coil resistance and inductance values are reference values only (at 60 Hz).

3. Operating characteristics were measured at a coil temperature of 23°C.

4. The maximum voltage is the maximum possible value of the voltage that can be applied to the relay coil. It is not the maximum voltage that can be applied continuously.

Contact Ratings

Number of poles	1 pole		2 poles		
Load	Resistive loadInductive loadR $(\cos\phi = 1)$ $(\cos\phi = 0.4; L/R = 7 ms)$ (cost cost cost cost cost cost cost cost		Resistive load $(\cos\phi = 1)$	Inductive load $(\cos\phi = 0.4; L/R = 7 ms)$	
Rated load	10 A at 250 VAC; 7.5 A at 250 VAC; 10 A at 30 VDC 5 A at 30 VDC		5 A at 250 VAC; 5 A at 30 VDC	2 A at 250 VAC; 3 A at 30 VDC	
Rated carry current	10 A		5 A		
Max. switching voltage	440 VAC, 125 VDC		380 VAC, 125 VDC		
Max. switching current	10 A	10 A			
Max. switching power	2,500 VA, 1,875 VA, 300 W 150 W		1,250 VA, 500 VA, 150 W 90 W		
Failure rate (reference value) *	100 mA at 5 VDC		10 mA at 5 VDC		

Note: P level: $\lambda_{60} = 0.1 \times 10^{-6}$ /operation

* This value was measured at a switching frequency of 120 operations per minute.

Characteristics

Item		1 pole	2 poles			
Contact configration	SPDT					
Contact structure	Single					
Contact resistance	100 m Ω max.					
Operate (set) time	15 ms max.					
Release (reset) time	AC: 10 ms max (w/built-in diod	x.; DC: 5 ms max. e: 20 ms max.)	AC: 15 ms max.; DC: 10 ms max. (w/built-in diode: 20 ms max.)			
Max. operating frequency	Mechanical: Electrical:	18,000 operations/hr 1,800 operations/hr (under rated lo	ad)			
Insulation resistance	1,000 MΩ min.	1,000 MΩ min. (at 500 VDC)				
Dielectric strength *	5,000 VAC, 50/60 Hz for 1 min between coil and contacts; 1,000 VAC, 50/60 Hz for 1 min between contacts of same polarity		5,000 VAC, 50/60 Hz for 1 min between coil and contacts; 3,000 VAC, 50/60 Hz for 1 min between contacts of different polarity 1,000 VAC, 50/60 Hz for 1 min between contacts of same polarity			
Vibration resistance	Destruction: Malfunction:	10 to 55 to 10 Hz, 0.75 mm single 10 to 55 to 10 Hz, 0.75 mm single	amplitude (1.5 mm double amplitude) amplitude (1.5 mm double amplitude)			
Shock resistance	Destruction: Malfunction:	1,000 m/s ² 200 m/s ² when energized; 100 m/s	² when not energized			
Endurance	Mechanical: Electrical:	Mechanical: AC coil: 10,000,000 operations min.; DC coil: 20,000,000 operations min. (at 18,000 operations/hr) Electrical: 100,000 operations min. (at 1,800 operations/hr under rated load)				
Ambient temperature	Operating:	Operating: -40°C to 70°C (with no icing or condensation)				
Ambient humidity	Operating:	5% to 85%				
Weight	Approx. 20 g					

Note: Values in the above table are the initial values.

* These values are relay only. Prease refer to the "Products Related to Common Sockets and DIN Tracks Data Sheet" for connecting sockets.

Approved Standards UL 508 (File No. E41643)

Model	Contact form	Coil ratings	Contact ratings	Opera- tions
G2R-1-S (S)	SPDT	5 to 110 VDC 6 to 240 VAC	10 A, 30 VDC (resistive) 10 A, 250 VAC (general use)	100 × 10 ³
			TV-3 (NO contact only)	25 × 10 ³
G2R-2-S (S)	DPDT		5 A, 30 VDC (resistive) 5 A, 250 VAC (general use)	100 × 10 ³
			TV-3 (NO contact only)	25×10^{3}

CSA 22.2 No.0, No.14 (File No. LR31928)

Model	Contact form	Coil ratings	Contact ratings	Opera- tions
G2R-1-S (S)	SPDT	5 to 110 VDC 6 to 240 VAC	10 A, 30 VDC (resistive) 10 A, 250 VAC (general use)	100 × 10 ³
			TV-3 (NO contact only)	25 × 10 ³
G2R-2-S (S)	DPDT		5 A, 30 VDC (resistive) 5 A, 250 VAC (general use)	100 × 10 ³
			TV-3 (NO contact only)	25 × 10 ³

IEC/VDE (Certificate No. 40015012 EN 61810-1)

Contact form	Coil ratings	Contact ratings	Operations
1 pole	6, 12, 24, 48 VDC 24, 110, 120, 230, 240 VAC	5 A, 440 VAC (cos¢ = 1.0) 10 A, 250 VAC (cos¢ = 1.0) 10 A, 30 VDC (0 ms)	100 × 10 ³
2 poles	6, 12, 24, 48 VDC 24, 110, 120, 230, 240 VAC	5 A, 250 VAC (cosø =1.0) 5 A, 30 VDC (0 ms)	100 × 10 ³

LR

Number of poles	Coil ratings	Coil ratings Contact ratings	
1 pole	5 to 110 VDC 6 to 240 VDC	10 A, 250 VAC (general use) 7.5 A, 250 VAC (PF0.4) 10 A, 30 VDC (resistive) 5A, 30VDC (L/R=7ms)	100 × 10 ³
2 poles	5 to 110 VDC 6 to 240 VDC	5 A, 250 VAC (general use) 2 A, 250 VAC (PF0.4) 5 A, 30 VDC (resistive) 3A, 30VDC (L/R=7ms)	100 × 10 ³

Engineering Data

Maximum Switching Power



Endurance



Ambient Temperature vs Maximum Coil Voltage



Ambient temperature (°C)

Dimensions

(Unit: mm)

Note: All units are in millimeters unless otherwise indicated.

SPDT Relays

G2R-1-S (S), G2R-1-SN (S), G2R-1-SNI (S) G2R-1-SD (S), G2R-1-SND (S), G2R-1-SNDI (S)













G2R-1-SN (S), G2R-1-SNI (S) (AC) G2R-1-SN (S), G2R-1-SNI (S) (DC)



G2R-1-SND (S), G2R-1-SNDI (S) (DC)



DPDT Relays

G2R-2-S (S), G2R-2-SN (S), G2R-2-SNI (S) G2R-2-SD (S), G2R-2-SND (S), G2R-2-SNDI (S)







Terminal Arrangement/Internal Connections (Bottom View)

G2R-2-S (S)

91

8

G2R-2-SD (S) (DC)



°2 93 <u></u>م

67 96

11

8

4

2 , 3

7

6



G2R-2-SN (S), G2R-2-SNI (S) (AC)





G2R-2-SND (S), G2R-2-SNDI (S) (DC)



Track/Surface Mounting Sockets P2RF-05-PU



Accessories for P2RF-□-PU Short Bars PYDN-7.75-□□ (7.75 mm)



PYDN-15.5-080 (15.5 mm)



Application	Pitch	No. of poles	L (Length)	Colors	Model *	Maximum carry current	
	7.75 mm	2	15.1		PYDN-7.75-020		
For Contact terminals (common)		3	22.85		PYDN-7.75-030]	
		n)	4	30.6	Red (R) Blue (S)	PYDN-7.75-040	20 A
		20	154.6	Yellow (Y)	PYDN-7.75-200		
For Coil terminals	15.5 mm	8	115.85		PYDN-15.5-080		

*Replace the box (\Box) in the model number with the code for the covering color.

Note: 1. Use the Short Bars for crossover wiring within one Socket or between Sockets.
2. When using short bar to coil terminals of PYF-□□-PU, make sure to use PYDN-31.0-080□ (31 mm).

When using short bar to coil terminals of P2RF- \Box -PU, make sure to use PYDN-15.5-080 \Box (15.5 mm).





Mounting Height of Relay with Track/Surface Mounting Sockets













P2R-05P (1-pole)











(5)







1.2



Terminal Arrangement (Bottom View)











7.5



14.5 max







08

Panel Cutout 13.6±0.1



Recommended thickness of the panel is 1.6 to 2.0 mm



Mounting Height of Relay with Back-connecting Sockets



Mounting Tracks



It is recommended to use a panel 1.6 to 2.0 mm thick.

PFP-100N2 4.5 Ţ 35±0.3 27 29.2 24 £ 15 25 25 25 25 15 1.5 1,000

12 OMRON



Mounting Plate

P2R-P



Safety Precautions

Be sure to read the *Common Precautions for All Relay* in the website at the following URL: http://www.ia.omron.com/.

Refer to *Products Related to Common Sockets and DIN Tracks* for precautions on the applicable Sockets. Refer to *PYF-*___-PU/P2RF-___-PU for precautions on Push-In Plus Terminal Block Sockets.

Warning Indications

	Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing to prevent failure to operate, malfunction, or undesirable effects on product performance.

- 🕂 Cation
- Do not use the test button for any purpose other than testing. Be sure not to touch the test button accidentally as this will turn the contacts ON. Before using the test button, confirm that circuits, the load, and any other connected item will operate safely.
- Check that the test button is released before turning ON relay circuits.
- If the test button is pulled out too forcefully, it may bypass the momentary testing position and go straight into the locked position.
- Use an insulated tool when you operate the test button.

Precautions for Correct Use

About the Built-in Diodes

The diodes that are built into the Relays are designed to absorb reverse voltage from the Relay's coil. If a large surge in voltage is applied to the diode from an external source, the element will be destroyed.

If there is the possibility of large voltage surges that could be applied to the elements from an external source, take any necessary surge absorption measures.

Latching Levers

- Turn OFF the power supply when operating the latching lever. After you use the latching lever always return it to its original state.
- Do not use the latching lever as a switch.The latching lever can be used for 100 operations minimum.

Relav Replacement

To replace the Relay, turn OFF the power supply to the load and Relay coil sides to prevent unintended operation and possible electrical shock.

Coil tape color

Pink tape is used for the AC coil type and blue tape is used for the DC coil type, making it easy to distinguish AC and DC.

Using a short-circuit bar

- Use the short-circuit bar that is suitable for the socket you are using and the location of use.
- Note that the P2DN short-circuit bar for the P2RFZ-E Socket has both a short-circuit bar for shorting coil terminals and a short-circuit bar for shorting contact COM terminals.
- The short-circuit bar can be cut to match any number of poles. Cut with a tool as appropriate for the number of relays and sockets. When using a cut short-circuit bar, take care to avoid injuring yourself on the cut surface.

• When cutting with a tool, insert the tool from the plastic part and cut along the slot in the plastic part between terminals. If you cut a part other than the slot in the plastic part between terminals, it may not be possible to attach the insulating cap.



• When using a cut short-circuit bar (P2DN), always use the provided cap to protect the charger part.



• The proper orientation for installing the short-circuit bar is with the molded part facing inward.



- Use the short-circuit bar to short-circuit two or more coil terminals, or two or more contact COM terminals.
- Do not use a deformed short-circuit bar. Risk of failure, malfunctioning, or deterioration of characteristics.
- In socket terminals, insert the short-circuit bar in the correct orientation all the way into all terminals, and then secure with screws.
- Install the short -circuit bar before wiring.

Equivalent Labels from Other Companies and Recommended Label Printers

Use the following label printer.

The following table gives the manufacturer's model number as of March 2017.

Manufacturer	Omron	Phoenix Contact	Weidmuller	Cembre
Label	XW5Z-P4.0LB1	UCT-TM6	MF 10/6	MG-CPM-04 41391
	XW5Z-P2.5LB2	UCT-TMF5		
Label printer	*	BLUEMARK CLED, THERMOMA RK CARD SET PLUS, THERMOMA RK CARD	PrintJet ADVCANCED, Plotter MCP Plus, Plotter MCP Basic	Markingenius MG3

* When using a printing tool, use a Phoenix Contact label printer. Note: Ask the label manufacturer or printer manufacturer for details.



OMRON AUTOMATION AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • automation.omron.com

OMRON CANADA, INC. • HEAD OFFICE Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • automation.omron.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE Ciudad de México • 52.55.5901.4300 • 01.800.386.6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE San Pedro Garza García, N.L. • 81.12.53.7392 • 01.800.386.6766 • mela@omron. com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE Eugenio Garza Sada,León, Gto • 01.800.386.6766 • mela@omron.com

Authorized Distributor:

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE São Paulo, SP, Brasil • 55 11 5171-8920 • automation.omron.com

OMRON ARGENTINA • SALES OFFICE Buenos Aires, Argentina • +54.11.4521.8630 • +54.11.4523.8483 mela@omron.com

OTHER OMRON LATIN AMERICA SALES +54.11.4521.8630 • +54.11.4523.8483 • mela@omron.com

Controllers & I/O

Machine Automation Controllers (MAC)
 Motion Controllers

Programmable Logic Controllers (PLC)
 Temperature Controllers
 Remote I/O

Robotics

Industrial Robots
 Mobile Robots

Operator Interfaces

• Human Machine Interface (HMI)

Motion & Drives

- Machine Automation Controllers (MAC)
 Motion Controllers
 Servo Systems
- Frequency Inverters

Vision, Measurement & Identification

Vision Sensors & Systems • Measurement Sensors • Auto Identification
Systems

Sensing

- Photoelectric Sensors Fiber-Optic Sensors Proximity Sensors
- Rotary Encoders Ultrasonic Sensors

Safety

Safety Light Curtains
 Safety Laser Scanners
 Programmable Safety Systems

- Safety Mats and Edges
 Safety Door Switches
 Emergency Stop Devices
- Safety Switches & Operator Controls Safety Monitoring/Force-guided Relays

Control Components

- Power Supplies Timers Counters Programmable Relays
- Digital Panel Meters
 Monitoring Products

Switches & Relays

- Limit Switches Pushbutton Switches Electromechanical Relays
- Solid State Relays

Software

Programming & Configuration
 Runtime

© 2020 Omron. All Rights Reserved.

Printed in U.S.A.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

 G2R-2S-DC5
 G2R-2S-DC24
 G2R-2S-AC220
 G2R-2S-DC12
 G2R-2S-AC120
 G2R-2S-AC24
 G2R-2S-AC24