

Switches  
Potentiometers  
Encoders



## COMMON CONTENTS

Page

◆ Push Switches, Detector Switches, Multi Function Switches, Light Touch Switches .....	ES2 to ES156
■ CONTENTS .....	ES2
■ INDEX .....	ES4
■ Push Switches .....	ES7
■ Detector Switches .....	ES19
■ Multi Function Switches .....	ES54
■ Light Touch Switches .....	ES59
◆ Rotary Potentiometers, Carbon Composition Trimmer Potentiometers, Position Sensors, Encoders .....	EV1 to ES61
■ CONTENTS .....	EV1
■ INDEX .....	EV2
■ Rotary Potentiometers .....	EV4
■ Carbon Composition Trimmer Potentiometers .....	EV15
■ Position Sensors .....	EV25
■ Encoders .....	EV35






## CONTENTS

Product	Type/Series	Part Numbers	Page
Common	Index / Glossary of words and Terms / RoHS Directive		ES4
Push Switches	Contents / Quick Selection Guide		ES7
	Checklist / Application Notes / Common Specifications / Minimum Quantity/Packing Unit		ES9
	ESB33 Vertical Push Switches	ESB33	ES13
	ESB30 Push Switches	ESB30	ES15
	ESE20C / 20D Momentary Push Switches	ESE20C/20D	ES17
Detector Switches	Contents / Quick Selection Guide		ES19
	Checklist / Application Notes / Common Specifications / Minimum Quantity/Packing Unit		ES21
	09HL Detector Switches	ESE58	ES25
	1VR Detector Switches	ESE16	ES28
	1VL Detector Switches	ESE13	ES30
	1HL Detector Switches	ESE18	ES33
	2HL Detector Switches	ESE31	ES38
	2N Detector Switches	ESE22	ES40
	5N Detector Switches	ESE11	ES43
	1HW Detector Switches	ESE23	ES49
	2W Detector Switches	ESE24	ES51










## CONTENTS

Product	Type/Series	Part Numbers	Page
Multi Function Switches	Contents / Quick Selection Guide / Minimum Quantity/Packing Unit		ES54
	Jog Ball	EVQWJN	ES57
Light Touch Switches	Contents / Quick Selection Guide		ES59
	Checklist / Application Notes / Common Specifications / Minimum Quantity/Packing Unit		ES62
	4 mm Square SMD Light Touch Switches	EVQP6/6P6/7P6/9P6	ES66
	4.5 mm Square SMD Light Touch Switches	EVQPQ	ES70
	4.9 mm Square SMD Light Touch Switches	EVQPL/3PL/5PL/PT	ES73
	6 mm Square Thin Type SMD Light Touch Switches	EVQP0/Q2	ES76
	3.0 mmx2.0 mm SMD Light Touch Switches	EVPAW	ES80
	3.0 mmx2.6 mm SMD Light Touch Switches	EVPAF	ES83
	3.5 mmx2.9 mm SMD Light Touch Switches	EVPAA	ES86
	4.7 mmx3.5 mm SMD Light Touch Switches	EVQP2/P9/3P2	ES89
	6.0 mmx3.5 mm SMD Light Touch Switches	EVQPE1/PN/5P	ES93
	3.5 mmx2.9 mm Side-operational SMD Light Touch Switches	EVQP7/P3/9P7	ES95
	3.5 mmx2.9 mm Side-operational Half Dive / SMD Light Touch Switches	EVPAN	ES99
	Small-sized Side-operational SMD Light Touch Switches	EVQPU	ES102
	2.8 mmx2.3 mm Side-operational Edge Mount Light Touch Switches	EVPAV	ES106
	4.5 mmx2.2 mm Side-operational Edge Mount Light Touch Switches	EVPAE	ES108
	6.2 mmx2.5 mm Side-operational Edge Mount Light Touch Switches	EVQP4	ES110
	6.1 mmx4.0 mm Side-operational SMD Light Touch Switches	EVQPS	ES113
	5N Type Light Touch Switches	EVQPA/PB	ES117
	5N Type Side-operational Light Touch Switches	EVQPF	ES120
	5N Type 2R Light Touch Switches	EVQ2	ES122
	5N Type Side-operational 4R Light Touch Switches	EVQPC	ES124
	Round Type 2R Light Touch Switches	EVQ11	ES126
	6.0 mmx3.5 mm Light Touch Switches	EVQPE	ES128
	6.0 mmx3.5 mm 2R Light Touch Switches	EVQPJ	ES130
	Over Travel Light Touch Switches	EVQP0	ES132
	4 mm Square Double-action SMD Light Touch Switches	EVPAH	ES134
	6 mm Square Thin Type Double-action SMD Light Touch Switches	EVQPR/Q0/3PR	ES137
	4.7 mmx3.5 mm Double-action Side-operational SMD Light Touch Switches	EVPAJ	ES140
	6.2 mmx3.7 mm Double-action Side-operational Edge Mount / SMD Light Touch Switches	EVQQ0	ES143
	6 mm Square Long Travel SMD Light Touch Switches	EVQP0/P1/9P	ES146
	6 mm Square Long Travel 2 terminals SMD Light Touch Switches	EVPAS	ES149
	6 mm Square Long Travel 2R Light Touch Switches	EVQPV	ES152
8 mm Square Long Travel SMD Light Touch Switches	EVQQ1	ES154	
8 mm Square Long Travel 2R Light Touch Switches	EVQQJ	ES156	
10 mm Square Center Space Long Travel SMD Light Touch Switches	EVPAD	ES158	

## Index

<p>ES13</p>  <p>ESB33 Vertical Push Switches (ESB33)</p>	<p>ES15</p>  <p>ESB30 Push Switches (ESB30)</p>	<p>ES17</p>  <p>ESE20C/20D Momentary Push Switches (ESE20C/20D)</p>	<p>ES25</p>  <p>09HL Detector Switches (ESE58)</p>
<p>ES28</p>  <p>1VR Detector Switches (ESE16)</p>	<p>ES30</p>  <p>1VL Detector Switches (ESE13)</p>	<p>ES33</p>  <p>1HL Detector Switches (ESE18)</p>	<p>ES38</p>  <p>2HL Detector Switches (ESE31)</p>
<p>ES40</p>  <p>2N Detector Switches (ESE22)</p>	<p>ES43</p>  <p>5N Detector Switches (ESE11)</p>	<p>ES49</p>  <p>1HW Detector Switches (ESE23)</p>	<p>ES51</p>  <p>2W Detector Switches (ESE24)</p>
<p>ES57</p>  <p>Jog Ball (EVQWJN)</p>	<p>ES66</p>  <p>4 mm Square SMD Light Touch Switches (EVQP6/6P6/7P6/9P6)</p>	<p>ES70</p>  <p>4.5 mm Square SMD Light Touch Switches (EVQPQ)</p>	<p>ES73</p>  <p>4.9 mm Square SMD Light Touch Switches (EVQPL/3PL/5PL/PT)</p>
<p>ES76</p>  <p>6 mm Square Thin Type SMD Light Touch Switches (EVQP0/Q2)</p>	<p><b>NEW</b> ES80</p>  <p>3.0 mm x 2.0 mm SMD Light Touch Switches (EVPAW)</p>	<p>ES83</p>  <p>3.0 mm x 2.6 mm SMD Light Touch Switches (EVPAF)</p>	<p>ES86</p>  <p>3.5 mm x 2.9 mm SMD Light Touch Switches (EVPAA)</p>
<p>ES89</p>  <p>4.7 mm x 3.5 mm SMD Light Touch Switches (EVQP2/P9/3P2)</p>	<p>ES93</p>  <p>6.0 mm x 3.5 mm SMD Light Touch Switches (EVQPE1/PN/5P)</p>	<p>ES95</p>  <p>3.5 mm x 2.9 mm Side-operational SMD Light Touch Switches (EVQP7/P3/9P7)</p>	<p>ES99</p>  <p>3.5 mm x 2.9 mm Side-operational Half Dive / SMD Light Touch Switches (EVPAN)</p>

## Index

<p>ES102</p>  <p>Small-sized Side-operational SMD Light Touch Switches (EVQPU)</p>	<p><b>NEW</b> ES106</p>  <p>2.8 mm x 2.3 mm Side-operational Edge Mount Light Touch Switches (EVPAV)</p>	<p>ES108</p>  <p>4.5 mm x 2.2 mm Side-operational Edge Mount Light Touch Switches (EVPAE)</p>	<p>ES110</p>  <p>6.2 mm x 2.5 mm Side-operational Edge Mount Light Touch Switches (EVQP4)</p>
<p>ES113</p>  <p>6.1 mm x 4.0 mm Side-operational SMD Light Touch Switches (EVQPS)</p>	<p>ES117</p>  <p>5N Type Light Touch Switches (EVQPA/PB)</p>	<p>ES120</p>  <p>5N Type Side-operational Light Touch Switches (EVQPF)</p>	<p>ES122</p>  <p>5N Type 2R Light Touch Switches (EVQ2)</p>
<p>ES124</p>  <p>5N Type Side-operational 4R Light Touch Switches (EVQPC)</p>	<p>ES126</p>  <p>Round Type 2R Light Touch Switches (EVQ11)</p>	<p>ES128</p>  <p>6.0 mm x 3.5 mm Light Touch Switches (EVQPE)</p>	<p>ES130</p>  <p>6.0 mm x 3.5 mm 2R Light Touch Switches (EVQPJ)</p>
<p>ES132</p>  <p>Over Travel Light Touch Switches (EVQPO)</p>	<p>ES134</p>  <p>4 mm Square Double-action SMD Light Touch Switches (EVPAH)</p>	<p>ES137</p>  <p>6 mm Square Thin Type Double-action SMD Light Touch Switches (EVQPR/Q0/3PR)</p>	<p>ES140</p>  <p>4.7 mm x 3.5 mm Double-action Side-operational SMD Light Touch Switches (EVPAJ)</p>
<p>ES143</p>  <p>6.2 mm x 3.7 mm Double-action Side-operational Edge Mount / SMD Light Touch Switches (EVQQ0)</p>	<p>ES146</p>  <p>6 mm Square Long Travel SMD Light Touch Switches (EVQP0/P1/9P)</p>	<p><b>NEW</b> ES149</p>  <p>6 mm Square Long Travel 2 terminals SMD Light Touch Switches (EVPAS)</p>	<p>ES152</p>  <p>6 mm Square Long Travel 2R Light Touch Switches (EVQPV)</p>
<p>ES154</p>  <p>8 mm Square Long Travel SMD Light Touch Switches (EVQQ1)</p>	<p>ES156</p>  <p>8 mm Square Long Travel 2R Light Touch Switches (EVQQJ)</p>	<p>ES158</p>  <p>10 mm Square Center Space Long Travel SMD Light Touch Switches (EVPAD)</p>	

## ■ Glossary of Words and Terms

### ● Rating

Maximum working voltage and current of switches

### ● Contact resistance

Resistance value of contact position, included specific resistance of material and usually measured by voltage drop at 1 A 5 Vdc.


### ● Switching timing

Two timing modes: shorting and non-shorting.

The change-over sequence of each circuit for two or more circuits is expressed by this timing.


#### ① Shorting

Common terminals are connected with the other one or more terminals when switching.



#### ② Non-shorting

Common terminals are connected with none of the other terminals.



## ■ RoHS Directive

**RoHS Directive : The restriction of the use of certain hazardous substances in electrical and electronic equipment**

The products introduced in this catalog conform to the RoHS Directive\* (enforced in July 2006).


(Newly ordered products will conform to the RoHS Directive.)

Please contact our sales staff for inquiries about the RoHS compliance of currently used products.

**CONTENTS**

	Page
■ Quick Selection Guide .....	ES8
■ Checklist Before Inquiry .....	ES9
■ Application Notes .....	ES10
■ Common Specifications .....	ES11
■ Minimum Quantity/Packing Unit .....	ES12
■ ESB33 Vertical Push Switches (ESB33) .....	ES13
■ ESB30 Push Switches (ESB30) .....	ES15
■ ESE20C/20D Momentary Push Switches (ESE20C/20D) .....	ES17

### ■ Quick Selection Guide

Type, Series	Country of origin	Lock Travel				Term. Pitch (mm)	Poles		Page
		1.5 mm	2.45 mm	2.5 mm	2.8 mm		1	2	
ESB33 Vertical Push Switches (H=6.0) 	China	○				2.5		○	ES13
ESB30 Push Switches (H=12.5) 	Japan			○		2.5		○	ES15
ESE20C/20D Momentary Push Switches (H=8.9) 	China					6.0x8.0	○		ES17

Country of origin : As of April 2013

### ■ Checklist Before Inquiry

When specifying Push Switches, please take advantage of our standard products for better price and delivery. Please inquire about the following items before ordering.

Item			Information (Requirements)	
Common	C-1	Inquiry purpose		New use, Modification, Others ( )
	C-2	Modification	Previous supplier	
			Conventional part No.	
			Purpose	
	C-3	Application	Equipment	
			Environment	Indoor/Outdoor use, Stationary/Portable set, High humidity, SO <sub>2</sub> , NaCl
Temperature			( °C) to ( °C)	
Rating			0.1 A 12 Vdc, 0.1 A 24 Vdc, 0.2 A 24 Vdc, 0.3 A 30 Vdc, 1.0 A 30 Vdc	
Shapes/Dimensions	M-1	Operation	Operation type	Vertical, Horizontal
			Operating force	When specially requested ( N)
	M-2	Circuit Diagram	Number of poles	1-pole, 2-pole
			Number of contacts	1-contact, 2-contact
			Switching mode (timing)	Not requested, Non-shorting (NS)
	M-3	Travel	Lock travel	0.8 mm, 1.3 mm, 1.5 mm, 2.4 mm, 2.5 mm, 2.8 mm
			Full travel	1.5 mm, 2.0 mm, 2.3 mm, 2.5 mm, 3.2 mm, 3.5 mm, 4.5 mm
	M-4	Terminals	Shape	PWB, Forming shape: ( )
			Pitch	2.0 mm, 5.0 mm
	M-5	Lever	Top dimensions	Width ( mm) × Height ( mm) × Length ( mm)
			Material	UL filed (Flame retardant: 94HB, 94V-0)
Others	L-1	Anti-electrostatic		When specially requested ( )
	L-2	Soldering conditions		Temp. ( °C), Time ( s), Specific gravity of flux ( ), Preheat condition ( )
	L-3	Special requirements for endurance		
	L-4	Special requirements for safety		
	L-5	Other questionnaires		

Notes:

- When you specify custom types (custom-made), new tooling and jigs, and/or equipment may be required. It will be necessary to confirm your estimates of quantity and development schedule as accurately as possible.
- Please inform us if you designate your own part number.

### Application Notes

When using our Push Switches, please observe the following items ("prohibited items") and be cautious of the following in order to prevent dangerous accidents and deterioration of performance.

#### 1. Prohibited items and notes on mounting


- When soldering (including preheating), do not solder in the locked condition.
- When soldering using a soldering iron, soldering conditions vary with the tip shape of the soldering iron, wattage, and PWB thickness. Thoroughly check the conditions in advance, including the heat resistance rating of the solder.
- Do not apply a load to terminals when soldering. Care should be taken in this regard because a load may deteriorate electric and mechanical characteristics.
- Since the push switches are not sealed, do not wash them.
- When mounting a push switch to a through-hole type PWB, the influence of thermal stress on the switch is greater than that on one-sided PWB. Be sure to check the influence as well as the heat resistance rating of the solder.

#### 2. Notes on circuit conditions

- To ensure reliability, use switches within the rated range, as designated in "Product Specifications for Information."
- To avoid malfunction of a set due to bounce generated by turning the switch ON and OFF, and/or due to chatter generated by external vibrations, etc., take the following into consideration in design.
  - Read contact multiple times. (In Case of microcomputer Processing)
  - Set a delay time. (Recommendation: 3 or more times of reading with the cycle of 3 ms or over)
  - Prepare a CR integrating circuit. (Recommendation: A time constant of 6 ms or over)
- When circuits of a two-circuit type are connected in parallel, switching timing (non-shorting, etc.) described in the specifications is not assured.


#### 3. Prohibited items and notes on mounting and operating conditions

- In principle, operate the center of the lever.




- For mounting an operation button:

- Design so that the button is mounted to the center of the lever.




- Design a set so that the gap (a) between the cabinet and the button is as small as possible. (a)=0.1 to 0.3mm



- Design so that the load in removal and mounting of the button is within the range of the switch's strength rating of the operational part.
- If multiple switches are placed side by side, or a switch is placed near another part, the gap between the switch and the adjacent switch/part must be at least 1mm to prevent affect of flux and to ensure proper insulation distance.

- Design and use so that external stress is not continuously applied to the soldering parts in a set. External stress may cause pattern peeling and solder cracks on a PWB.
- When mounting a switch, check the ON/OFF position.
- Contact lubricant, which is used in push switches, may flow out to the exterior of the switch due to the structure. For design review, sufficiently check the operating conditions.
- Do not pull the switch rod while it is locked. Otherwise, the self-locking function may be broken, resulting in a locking failure or malfunction. Make sure that the switch is released especially when attaching/detaching a button to the rod and assembling/disassembling the target product. (This applies to the self-locking switches) Set the strength for detaching your button (knob) from our switch rod to a maximum of 10 N in order to minimize the possibility of a breakdown of the locking function. When designing your button, refer to the following shape and dimensions. Before adopting our switches, check the requirements carefully.

#### Reference of Customer's button design



- Design to avoid operation with continuous lateral pressure (more than 500 mN on the lever).
- Do not mount a switch by bending switch terminals.
- Avoid the following ambient surroundings and other conditions because they may affect performance:
  - Under an atmosphere of corrosive gas such as Cl<sub>2</sub>, H<sub>2</sub>S, NO<sub>x</sub>, or SO<sub>2</sub>
  - In atmospheres of residual water drops, dew condensation, or adhesive water drops
  - In liquids such as water, salt solution, oil, chemicals, and organic solvents
  - In direct sunlight
  - In dusty locations
- Do not apply a shock to the switch lever during mounting of the switch on the printed circuit board and installation in the target product.

#### 4. Prohibited items and notes on storage conditions

Since contact characteristics and soldering quality may deteriorate due to sulfuration and oxidation of contacts and terminals, pay heed to the following items.

- For storage and transport of the switches, avoid unpacking them, and store them at room temperature and room humidity. Use them as soon as possible, generally within 3 months, or within a maximum of 6 months after delivery.
- Do not store the switches under conditions of high temperature and/or high humidity, or in a location where corrosive gas may be generated.
- If some units remain after unpacking, store them after applying adequate moisture-proof and gas-proof treatment.

#### 5. For use in equipment for which safety requested

Although care is taken to ensure switch quality, variation of contact resistance (increase), short circuits, open circuits, and temperature rise are some problems that might be generated. To design a set which places maximum emphasis on safety, review the affect of any single fault of a switch in advance and perform virtually fail-safe design to ensure maximum safety by:

- preparing a protective circuit or a protective device to improve system safety, and
- preparing a redundant circuit to improve system safety so that the single fault of a switch does not cause a dangerous situation.

- For actual use, be sure to refer to "Product Specifications for Information."

### ■ Common Specifications(Standard)

Mechanical Specifications	Lever Strength	To withstand 80 N push force applied in operating direction for 15 seconds													
	Terminal Strength	To withstand 5 N push force applied on the end of terminal in any direction for 1 minute without damage and/or loosening													
Electrical Specifications	Voltage drop	0.1 V max. between terminals after 4 or 5 switching operations under the rated load													
	Insulation Resistance	Terminal to Terminal and Terminal to Frame: 100 MΩ min. (at 500 Vdc) (Does not apply to the insulation resistance during switching operations)													
	Dielectric Withstanding Voltage	Terminal to Terminal and Terminal to Frame: 500 Vac for 1 minute													
Environmental Specifications	Temperature Range	-10 °C to +70 °C (Standard)													
	Heat Resistance	+70 °C for 96 hours (Standard)													
	Low Temperature Resistance	-10 °C for 96 hours (Standard)													
	Humidity Resistance	40 °C, 90 % to 95 % RH for 96 hours													
	Non-loaded Life	Number of operations : 10000 cycles	Voltage drop : 0.5V max. (ESB32) Voltage drop : 0.2V max. (ESB20, ESB30, ESB32)												
	Loaded Life	<table border="1"> <thead> <tr> <th>Type</th> <th>No. of operations</th> <th>Voltage drop</th> </tr> </thead> <tbody> <tr> <td>ESB33</td> <td>30000 cycles</td> <td>0.5 V max.</td> </tr> <tr> <td>ESB30</td> <td>30000 cycles</td> <td>0.2 V max</td> </tr> <tr> <td>ESE20</td> <td>30000 cycles</td> <td>0.2 V max.</td> </tr> </tbody> </table>			Type	No. of operations	Voltage drop	ESB33	30000 cycles	0.5 V max.	ESB30	30000 cycles	0.2 V max	ESE20	30000 cycles
Type	No. of operations	Voltage drop													
ESB33	30000 cycles	0.5 V max.													
ESB30	30000 cycles	0.2 V max													
ESE20	30000 cycles	0.2 V max.													

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Minimum Quantity/Packing Unit

Please place an order by an integer multiple of the Quantity/Carton.


Type, Series	Part No.	Packaging	Quantity/Carton (Export)	Min. Q'ty/ Packing Unit
ESB33 Vertical Push Switches	ESB33□□□□	Polyethylene Bag (Bulk)	2000 pcs. (8000 pcs.)	100 pcs.
		Embossed Taping (Reel Pack)	1800 pcs. (7200 pcs.)	300 pcs.
ESB30 Push Switches	ESB30□□□□□	Tray Pack	2400 pcs. (9600 pcs.)	480 pcs.
ESE20C/20D Momentary Push Switches	ESE20□□□□□	Polyethylene Bag (Bulk)	1200 pcs. (4800 pcs.)	60 pcs.

## ESB33 Vertical Push Switches

Type: **ESB33 (H=6.0 mm)**

### ■ Features


- Low profile (H=6.0 mm)
- 3 N and 5 N operating force availables



### ■ Recommended Applications

- Operation switches for automobiles (heater control switches etc.)
- Secondary power switches for lower voltage in consumer electronic equipment and different types of mode switches

### ■ Explanation of Part Numbers



### ■ Specifications

Rating	50 $\mu$ A 3 Vdc to 0.2 A 14 Vdc (Resistive load)
Travel	Lock travel=1.5 mm Full travel=2.3 mm
Mounting Height	6.0 mm
Poles and Throws	2-poles 2-throws
Operating Mode	Self-lock, Non-lock
Switching Mode	Non-shorting
Minimum Quantity/Packing Unit	100 pcs. Polyethylene Bag (Bulk) / 300 pcs. Embossed Taping (Reel Pack)
Quantity/Cartron	2000 pcs. Polyethylene Bag (Bulk) / 1800 pcs. Embossed Taping (Reel Pack)

### ■ Standard Products

Operating Mode	Terminals	Packaging	Operating Force	Part Numbers	Lever Color
PP	Wave Soldering	Polyethylene Bag (Bulk)	3.0 N $\pm$ 1.0 N	ESB33133	Light Yellow
NL				ESB33134	
PP	Surface Mount	Embossed Taping (Reel )	3.0 N $\pm$ 1.0 N	ESB33535	Light Yellow
NL				ESB33536	

Note: PP=Self-lock NL=Non-lock


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012



## ESB30 Push Switches

Type: **ESB30 (H=12.5 mm)**




### ■ Features

- Reduced interlock operation switching noise (-10 dB compared to the current value)
- Simultaneous locking prevention mechanism

### ■ Recommended Applications

- Operation switches for automobiles (air conditioners switches, Hazard switches, etc.)
- Secondary power switches for lower voltage in consumer electronic equipment and different types of mode switches

### ■ Explanation of Part Numbers



### ■ Specifications

Rating	50 $\mu$ A 3 Vdc to 0.2 A 14 Vdc (Resistive load)
Travel	Lock Travel=2.5 mm Full Travel=3.5 mm
Mounting Height	12.5 mm
Poles and Throws	2-poles 2-throws
Operating Mode	Self-lock, Non-lock
Switching Mode	Non-shorting
Operating Force	2.0 N $\pm$ 1.0 N, 3.5 N $\pm$ 1.5 N
Minimum Quantity/Packing Unit	480 pcs. (Tray Pack)
Quantity/Carton	2400 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### Standard Products

Operating Force	Lever Height	Lock Travel	Operating Mode	Terminal Shape	
				Straight	Formed
2 N±1.0 N	20.5 mm	2.5 mm	PP	ESB30B132	ESB30B102
			NL	ESB30B304	ESB30B305
3.5 N±1.5 N	20.5 mm	2.5 mm	PP	ESB30B103	ESB30B133
			NL	ESB30B332	ESB30B333

Note: PP=Self-lock, NL=Non-lock

### Dimensions in mm (not to scale)

**ESB30B132**  
2-poles 2-throws

Lock Travel	Full Travel
2.5 mm	3.5 mm

F-S Characteristics

(A) details

(A) details

PWB mounting hole for reference  
(Tolerance:±0.05)  
View from terminal side

Circuit diagram  
(View from terminal side)

Forming dimension of terminal  
(Except for common terminal)


### Application Notes:

- Operating force should be applied at the center of the lever.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## ESE20C/20D Momentary Push Switches

Type: **ESE20C/ESE20D**  
(H=8.9 mm)




### ■ Features

- User-friendly tactile feedback when operated
- Long over-travel

### ■ Recommended Applications

- Operation switches for automobiles (switches for heater controls, overdrive, steering, etc.)
- Secondary power switches for lower voltage in consumer electronic equipment and different types of mode switches

### ■ Explanation of Part Numbers



### ■ Specifications

Rating	0.01 A 5 Vdc to 0.1 A 14 Vdc (Resistive load)
Full Travel	2.5 mm
Mounting Height	8.9 mm
Poles and Throws	1-pole 1-throw
Operating Mode	Non-lock
Operating Force	2.0 N±1.0 N, 4.0 N±1.5 N
Minimum Quantity/Packing Unit	60 pcs. Polyethylene Bag (Bulk)
Quantity/Carton	1200 pcs.


### ■ Standard Products

Full Travel	Operating Force	Lever Height	Terminal Shape	
			Straight	Formed
2.5 mm	2.0 N±1.0 N	12.5 mm	ESE20*323	ESE20*321
		17.5 mm	ESE20*423	ESE20*421
	4.0 N±1.5 N	12.5 mm	ESE20*343	ESE20*341
		17.5 mm	ESE20*443	ESE20*441

\*C : For automotive use    D : For consumer products

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)



### ■ Application Notes:


- Operating force should be applied at the center of the lever.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## CONTENTS

	Page
■ Quick Selection Guide .....	ES20
■ Checklist Before Inquiry .....	ES21
■ Application Notes .....	ES22
■ Common Specifications .....	ES23
■ Minimum Quantity/Packing Unit .....	ES24
■ 9HL Detector Switches (ESE58) .....	ES25
■ 1VR Detector Switches (ESE16) .....	ES28
■ 1VL Detector Switches (ESE13) .....	ES30
■ 1HL Detector Switches (ESE18) .....	ES33
■ 2HL Detector Switches (ESE31) .....	ES38
■ 2N Detector Switches (ESE22) .....	ES40
■ 5N Detector Switches (ESE11) .....	ES43
■ 1HW Detector Switches (ESE23) .....	ES49
■ 2W Detector Switches (ESE24) .....	ES51

### ■ Quick Selection Guide

Type, Series	Appearance	Part No.	Country of origin	Poles & Throws	Page
09HL Detector Switches		ESE58	Japan	1-1	ES25
1VR Detector Switches		ESE16	Japan	1-1	ES28
1VL Detector Switches		ESE13	Japan	1-1	ES30
1HL Detector Switches		ESE18	Japan	1-1	ES33
2HL Detector Switches		ESE31	Japan/China	1-1	ES38
2N Detector Switches		ESE22	Japan	1-1	ES40
5N Detector Switches		ESE11	Japan/China	1-1	ES43
1HW Detector Switches		ESE23	Japan	1-2	ES49
2W Detector Switches		ESE24	Japan	1-2	ES51

Country of origin : As of April 2013

### ■ Checklist Before Inquiry

When specifying Detector Switches, please take advantage of our standard products for better pricing and delivery. Please inquire about the following items before ordering.

Item			Information (Requirements)		
Common	C-1	Inquiry purpose		New use, Modification, Others ( )	
	C-2	Modification	Previous supplier		
			Conventional part No.		
			Purpose		
	C-3	Application	Equipment		
			Design standard of pushing distance of lever		At switching on (when not pushing) : Pushing distance (Pushing the point of lever <input type="text"/> mm) At switching off (when not pushing) : Object of detection is <input type="checkbox"/> apart from the point of lever <input type="checkbox"/> not apart from the point of lever (Pushing about <input type="text"/> mm)
Operation frequency			<input type="checkbox"/> Operate the switches every day. ( <input type="text"/> times a day) <input type="checkbox"/> Almost everytime, the switches are stayed in the released condition. ( <input type="text"/> times a week / month / year) <input type="checkbox"/> Almost everytime, the switches are pushed in the designed position. ( <input type="text"/> times a week / month / year)		
Temperature			( °C) to ( °C)		
Rating			<input type="text"/> mA <input type="text"/> V <input type="text"/> dc <input type="text"/> mA <input type="text"/> V <input type="text"/> ac Do you give "inrush current" to switches ? : <input type="checkbox"/> YES <input type="checkbox"/> NO		
Shapes/Dimensions	M-1	Operation	Operation type		Vertical, Horizontal
	M-2	Mounting	Mounting height	Vertical	PWB to upper surface of housing: ( mm)
				Horizontal	PWB to center rod: ( mm)
M-3	Terminals		PWB, Solder lug		
Others	L-1	Surface Mount	Connection		Manual soldering, Wave soldering, Reflow Soldering
			Packing Unit		Polyethylene Bag (Bulk), Embossed Taping (Reel Pack)
	L-2	Special requirements for endurance			
	L-3	Special requirements for safety			
L-4	Other questionnaires				

\* The Electrical Appliance and Material Safety Law (Japan) was revised on March 1st. 1988.  
Power switches described here are not under jurisdiction of this law, but comply with its technical requirements.

Notes:

1. When selecting Switches, please consider using our standard products for better prices and short delivery times.
2. Please inform the following items when ordering.


## Application Notes

When using our Slide Switches, please observe the following items ("prohibited items") and be cautious of the following in order to prevent dangerous accidents and deterioration of performance.

### 1. Prohibited items and notes on mounting

- When soldering (including preheating), set the lever to the release position.
- When soldering using a soldering iron, soldering conditions vary with the tip shape of the soldering iron, wattage, and PWB thickness. Thoroughly check the conditions in advance, including the heat resistance rating of the solder.
- Do not apply a load to terminals when soldering. Care should be taken in this regard because a load may deteriorate electric and mechanical characteristics.
- Since the detector switches are not sealed, do not wash them.
- When mounting a detector switch to a through-hole type PWB, the influence of thermal stress on the switch is greater than that on one-sided PWB. Be sure to check the influence as well as the heat resistance rating of the solder.
- For reflow soldering

When performing reflow soldering using a hot-air oven or an infrared oven, observe the following conditions. Since the temperature applied to a switch and its terminals varies with the type and size of the PWB and the mounting density of the parts, sufficiently check the conditions in advance.



### 2. Notes on circuit conditions

- To ensure reliability, use detector switches within the rated range, as designated in "Product Specifications for Information."
- To avoid malfunction of a set due to bounce generated by turning the switch ON and OFF, and/or due to chatter generated by external vibrations, etc., take the following into consideration in design.
  - Read contact multiple times.  
(In Case of microcomputer Processing )
  - Set a delay time.  
(Recommendation: 3 or more times of reading with the cycle of 3 ms or over)
  - Prepare a CR integrating circuit.  
(Recommendation: A time constant of 6 ms or over )

### 3. Prohibited items and notes on mounting and operating conditions

- Design so that the load applied to the lever when a set is used is within the rated range of the switch's lever strength.

- If multiple switches are placed side by side, or a switch is placed near another part, the gap between the switch and the adjacent switch/part must be at least 1 mm to prevent affect of flux and to ensure proper insulation distance.
- Design and use so that external stress is not continuously applied to the soldering parts in a set in any direction. External stress may cause pattern peeling and solder cracks on a PWB.
- When mounting a switch (mounting to chassis or button mounting), take care so that no foreign matter enters the switch.
- Contact lubricant, which is used in detector switches, may flow out to the exterior of the switch due to the structure. For design review, sufficiently check the operating conditions.
- Avoid the following ambient surroundings and other conditions because they may affect performance:
  - Under an atmosphere of corrosive gas such as Cl<sub>2</sub>, H<sub>2</sub>S, NO<sub>x</sub>, or SO<sub>2</sub>
  - In atmospheres of residual water drops, dew condensation, or adhesive water drops
  - In liquids such as water, salt solution, oil, chemicals, and organic solvents
  - In direct sunlight
  - In dusty locations

### 4. Prohibited items and notes on storage conditions

Since contact characteristics and soldering quality may deteriorate due to sulfuration and oxidation of contacts and terminals, pay heed to the following items.

- For storage and transport of the switches, avoid unpacking them, and store them at room temperature and room humidity. Use them as soon as possible, generally within 3 months, or within a maximum of 6 months after delivery.
- Do not store the switches under conditions of high temperature and/or high humidity, or in a location where corrosive gas may be generated.
- If some units remain after unpacking, store them after applying adequate moisture-proof and gas-proof treatment.

### 5. For use in equipment for which safety is requested

Although care is taken to ensure switch quality, variation of contact resistance (increase), short circuits, open circuits, and temperature rise are some problems that might be generated.

To design a set which places maximum emphasis on safety, review the affect of any single fault of a switch in advance and perform virtually fail-safe design to ensure maximum safety by:

- preparing a protective circuit or a protective device to improve system safety, and
- preparing a redundant circuit to improve system safety so that the single fault of a switch does not cause a dangerous situation.

### 6. For actual use, be sure to refer to "Product Specifications for Information."

### ■ Common Specifications (Standard)

Mechanical Specifications	Lever Strength	To withstand 10 N push force applied in operating direction for 15 seconds (ESE11, 22, 24, 31) To withstand 2 N push force applied in operating direction for 15 seconds (ESE13, 16, 18, 23) To withstand 1 N push force applied in operating direction for 15 seconds (ESE58)
	Terminal Strength	To withstand 3 N push force applied on the end of terminal in any direction for 1 minute [0.5 N : ESE13, 16, 18, 23, 58]
Electrical Specifications	Contact Resistance	500 mΩ max.
	Insulation Resistance	Terminal to Terminal and Terminal to Outer Metal Part: 100 MΩ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	Terminal to Terminal and Terminal to Outer Metal Part: 100 Vac for 1 minute
Environmental Specifications	Operating Temperature Range	-10 °C to +70 °C (ESE11, 22, 24, 31) -10 °C to +60 °C (ESE13, 16, 18, 23, 58)
	Heat Resistance	+80 °C for 96 hours (ESE11, 22, 24) +85 °C for 96 hours (ESE31) +70 °C for 96 hours (ESE13, 16, 18, 23, 58)
	Low Temperature Resistance	-25 °C for 96 hours -40 °C for 96 hours (ESE31)
	Humidity Resistance	40 °C, 90 % to 95 % RH for 96 hours 60 °C, 90 % to 95 % RH for 96 hours (ESE31)
	Non-loaded Life	Number of operations 50000 cycles Contact resistance : 1 Ω max. (ESE11, 13, 24) Contact resistance : 3 Ω max. (ESE22, 31) Voltage drop : 1.5 V max. (ESE16, 18, 58) Voltage drop : 1.0 V max. (ESE23)
	Loaded Life	Number of operations 50000 cycles Contact resistance : 1 Ω max. (ESE11, 13, 24) Contact resistance : 3 Ω max. (ESE22, 31) Voltage drop : 1.5 V max. (ESE16, 18, 58) Voltage drop : 1.0 V max. (ESE23)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

### ■ Minimum Quantity/Packing Unit

Please place an order by an integer multiple of the Quantity/Carton.

Type, Series	Part No.	Packaging	Quantity/Carton (Export)	Min. Q'ty/ Packing Unit
09HL Detector Switches Type: ESE58	ESE58□	Embossed Taping (Reel Pack)	30000 pcs. (120000 pcs.)	5000 pcs.
1VR Detector Switches Type: ESE16	ESE16□	Embossed Taping (Reel Pack)	24000 pcs. (96000 pcs.)	4000 pcs.
1VL Detector Switches Type: ESE13	ESE13V□	Embossed Taping (Reel Pack)	18000 pcs. (72000 pcs.)	3000 pcs.
	ESE13H□		30000 pcs. (120000 pcs.)	5000 pcs.
1HL Detector Switches Type: ESE18	ESE18□	Embossed Taping (Reel Pack)	30000 pcs. (120000 pcs.)	5000 pcs.
2HL Detector Switches Type: ESE31	ESE31□	Embossed Taping (Reel Pack)	15000 pcs. (60000 pcs.)	2500 pcs.
2N Detector Switches Type: ESE22	ESE22MV21T	Embossed Taping (Reel Pack)	6000 pcs. (24000 pcs.)	1000 pcs.
	ESE22MH22 ESE22MH24		24000 pcs. (96000 pcs.)	4000 pcs.
	ESE22MH27T ESE22MH28T ESE22MH52 ESE22MH54		18000 pcs. (72000 pcs.)	3000 pcs.
	ESE22MH51 ESE22MH53 ESE22MH57 ESE22MH58 ESE22MV21 ESE22MH21 ESE22MH23 ESE22MH27 ESE22MH28	Polyethylene Bag (Bulk)	10000 pcs. (40000 pcs.)	500 pcs.
5N Detector Switches Type: ESE11	ESE11SV□ ESE11MV□ ESE11SH□ ESE11MH□ ESE11HS□ ESE11SF□	Polyethylene Bag (Bulk)	10000 pcs. (40000 pcs.)	200 pcs.
	ESE11MV2		8000 pcs	200 pcs.
	ESE11MV□T (Excluding : ESE11MV2)	Embossed Taping (Reel Pack)	4800 pcs. (19200 pcs.)	800 pcs.
	ESE11MH□T		9000 pcs. (36000 pcs.)	1500 pcs.
1HW Detector Switches Type: ESE23	ESE 23□	Embossed Taping (Reel Pack)	24000 pcs. (96000 pcs.)	4000 pcs.
2W Detector Switches Type: ESE24	ESE24SH□ ESE24SV□ ESE24MH□ ESE24MV□	Polyethylene Bag (Bulk)	10000 pcs. (50000 pcs.)	200 pcs.
	[ ESE24SH1 ESE24SH6 ESE24SH7 ESE24SV2 ESE24SV8 ]		[ 8000 pcs. (40000 pcs.) ]	[ 160 pcs. ]
	ESE24MH□T	Embossed Taping (Reel Pack)	6000 pcs. (24000 pcs.)	1000 pcs.
ESE24MV□T	3000 pcs. (12000 pcs.)		500 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 09HL Detector Switches

Type: **ESE58**




#### ■ Features

- Thin body: 0.9 mm.
- Circuit type: Normally-open and normally-closed types are available.
- Lineup with variations in right-left operations.

#### ■ Recommended Applications

- Detection of media in portable electronic equipment (Mobile phones/Digital still cameras/DVCs, etc.)

#### ■ Explanation of Part Numbers




#### ■ Specifications

Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance	500 m $\Omega$ max. (Initial)
Insulation Resistance	100 M $\Omega$ min. (100 Vdc)
Dielectric Withstanding Voltage	100 Vac for 1 minute
Operating Force	300 mN max.
Mounting Height	0.9 mm
Poles and Throws	1-pole 1-throw
Full Travel (Pushing distance)	With boss : 1.5 mm (1.5 mm) Without boss : 1.25 mm (1.5 mm)
Operating Life	50000 cycles min.
Temperature Range	-10 $^{\circ}$ C to +60 $^{\circ}$ C
Heat Resistance	+70 $^{\circ}$ C for 96 hours
Low Temperature Resistance	-25 $^{\circ}$ C for 96 hours
Humidity Resistance	+40 $^{\circ}$ C 90 % to 95 % RH for 96 hours
Minimum Quantity/Packing Unit	5000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton	30000 pcs.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)




Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)




### ■ Circuit Diagram



### ■ Packaging Specifications

#### Standard Reel Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 1VR Detector Switches

Type: **ESE16**




#### ■ Features

- External Dimensions: 2.2 mm×3.35 mm (Height:1.5 mm)
- Light operating force: 250 mN or less
- Auto mounting supported: Can be mounted by standard nozzles

#### ■ Recommended Applications

- Detection of media in portable electronic equipment (Mobile phones / Digital still cameras / Camcorders)

#### ■ Explanation of Part Numbers




#### ■ Specifications


Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance	500 m $\Omega$ max. (Initial)
Insulation Resistance	10 M $\Omega$ max. (100 Vdc)
Dielectric Withstanding Voltage	100 Vac for 1 minute
Operating Force	250 mN max.
Mounting Height	1.5 mm
Poles and Throws	1-pole 1-throw
Full Travel (Pushing distance)	1.5 mm (1.0 mm)
Operating Life	50000 cycles min.
Temperature Range	-10 °C to +60 °C
Heat Resistance	+70 °C for 96 hours
Low Temperature Resistance	-25 °C for 96 hours
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours
Minimum Quantity/Packing Unit	4000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton	24000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)




### ■ Circuit Diagram



### ■ Packaging Specifications

#### Standard Reel Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 1VL Detector Switches

Type: **ESE13**




#### ■ Features

- Thin type : Height=1.2 mm
- Highly reliable contact
- SMD type (Embossed taping, Reflow soldering)

#### ■ Recommended Applications

- Detection of media in portable electronic equipment (Mobile phones / Digital still cameras / Camcorders)

#### ■ Explanation of Part Numbers




#### ■ Specifications

Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)	
Contact Resistance	500 m $\Omega$ max. (Initial)	
Insulation Resistance	100 M $\Omega$ min. (100 Vdc)	
Dielectric Withstanding Voltage	100 Vac for 1 minute	
Operating Force	300 mN max.	
Mounting Height	1.2 mm	
Poles and Throws	1-pole 1-throw	
Full Travel (Pushing distance)	Type V : 2.15 mm (2.15 mm) Type H : 3.05 mm (2.15 mm)	
Operating Life	50000 cycles min.	
Temperature Range	-10 °C to +60 °C	
Heat Resistance	+70 °C for 96 hours	
Low Temperature Resistance	-25 °C for 96 hours	
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours	
Minimum Quantity/Packing Unit	ESE13H	5000 pcs. Embossed Taping (Reel Pack)
	ESE13V	3000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton	ESE13H	30000 pcs.
	ESE13V	18000 pcs.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)




Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)




### ■ Circuit Diagram



### ■ Packaging Specifications


Standard Reel Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 1HL Detector Switches

Type: **ESE18**




#### ■ Features

- Thin body: 1.2 mm
- Circuit type: Normally-open and normally-closed types are available.
- Travel: Standard stroke type: 1.5 mm  
Long stroke type: 2.15 mm
- Surface mounted type: Packed with embossed tape. Supports reflow soldering.

#### ■ Recommended Applications

- Detection of media in portable electronic equipment (Mobile phones/CD-ROM/DVD players, Digital still cameras)

#### ■ Explanation of Part Numbers



#### ■ Specifications

Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)						
Contact Resistance	500 m $\Omega$ max. (Initial)						
Insulation Resistance	100 M $\Omega$ min. (100 Vdc)						
Dielectric Withstanding Voltage	100 Vac for 1 minute						
Operating Force	300 mN max.						
Mounting Height	1.2 mm						
Poles and Throws	1-pole 1-throw						
Full Travel (Pushing distance)	<table style="width: 100%; border: none;"> <tr> <td style="border: none;">· Standard stroke type</td> <td style="border: none;">· Long stroke type</td> </tr> <tr> <td style="border: none;">With boss : 1.4 mm (1.5 mm)</td> <td style="border: none;">With boss : 1.4 mm (2.15 mm)</td> </tr> <tr> <td style="border: none;">Without boss : 2.1 mm (1.5 mm)</td> <td style="border: none;">Without boss : 2.1 mm (2.15 mm)</td> </tr> </table>	· Standard stroke type	· Long stroke type	With boss : 1.4 mm (1.5 mm)	With boss : 1.4 mm (2.15 mm)	Without boss : 2.1 mm (1.5 mm)	Without boss : 2.1 mm (2.15 mm)
· Standard stroke type	· Long stroke type						
With boss : 1.4 mm (1.5 mm)	With boss : 1.4 mm (2.15 mm)						
Without boss : 2.1 mm (1.5 mm)	Without boss : 2.1 mm (2.15 mm)						
Operating Life	50000 cycles min.						
Temperature Range	-10 °C to +60 °C						
Heat Resistance	+70 °C for 96 hours						
Low Temperature Resistance	-25 °C for 96 hours						
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours						
Minimum Quantity/Packing Unit	5000 pcs. Embossed Taping (Reel Pack)						
Quantity/Carton	30000 pcs.						


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)

<p><b>No. 1</b></p> <p><b>Standard stroke type</b> ESE18L J-bent terminals 1-pole 1-throw</p> <p>Normal open with Boss ESE18L11B</p> <p>Normal open without Boss ESE18L11A</p> <p>Normal closed with Boss ESE18L61B</p> <p>Normal closed without Boss ESE18L61A</p>	<p>PWB mounting hole for reference (Pitch tolerance: ±0.05)</p>
<p><b>No. 2</b></p> <p><b>Standard stroke type</b> ESE18L Straight terminals 1-pole 1-throw</p> <p>Normal open with Boss ESE18L11D</p> <p>Normal open without Boss ESE18L11C</p> <p>Normal closed with Boss ESE18L61D</p> <p>Normal closed without Boss ESE18L61C</p>	<p>PWB mounting hole for reference (Pitch tolerance: ±0.05)</p>
<p><b>No. 3</b></p> <p><b>Long stroke type</b> ESE18L J-bent terminals 1-pole 1-throw</p> <p>Normal open with Boss ESE18L12B</p> <p>Normal open without Boss ESE18L12A</p> <p>Normal closed with Boss ESE18L62B</p> <p>Normal closed without Boss ESE18L62A</p>	<p>PWB mounting hole for reference (Pitch tolerance: ±0.05)</p>


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)




Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)




### ■ Circuit Diagram



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Packaging Specifications


Standard Reel Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 2HL Detector Switches

Type: **ESE31**




#### ■ Features

- Increased the mounting strength Mounting strength: 80 N
- Decreased the profile of the switch body Height: 1.7 mm
- Increased the contact reliability and lifespan.  
Lifespan: 100,000 operations or more

#### ■ Recommended Applications

- Detection of media in portable electronic equipment

#### ■ Explanation of Part Numbers




#### ■ Specifications


Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance	500 m $\Omega$ max. (Initial)
Insulation Resistance	100 M $\Omega$ min. (100 Vdc)
Dielectric Withstanding Voltage	100 Vac for 1 minute
Operating Force	390 mN max.
Mounting Height	1.7 mm
Poles and Throws	1-pole 1-throw
Full Travel (Pushing distance)	3.2 mm (2.15 mm)
Operating Life	50000 cycles min.
Temperature Range	-10 °C to +70 °C
Heat Resistance	+85 °C for 96 hours
Low Temperature Resistance	-40 °C for 96 hours
Humidity Resistance	+60 °C 90 % to 95 % RH for 96 hours
Minimum Quantity/Packing Unit	2500 pcs. Embossed Taping (Reel Pack)
Quantity/Carton	15000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)




### ■ Circuit Diagram



### ■ Packaging Specifications


Standard Reel Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 2N Detector Switches

Type: **ESE22**




#### ■ Features

- Can be operated with different actuation angles (horizontally and vertically)
- Reflow soldering
- Light operating force

#### ■ Recommended Applications

- Detection of media in portable electronic equipment

#### ■ Explanation of Part Numbers



#### ■ Specifications

Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance	500 m $\Omega$ max. (Initial)
Insulation Resistance	100 M $\Omega$ min. (100 Vdc)
Dielectric Withstanding Voltage	100 Vac for 1 minute
Operating Force	300 mN max.
Mounting Height	<ul style="list-style-type: none"> <li>· Type MV                    4.1 mm    · Type MH    2.1 mm</li> <li>· Type MH with Frame   2.85 mm</li> </ul>
Poles and Throws	1-pole 1-throw
Full Travel (Pushing distance)	<ul style="list-style-type: none"> <li>· Type MV                    4.25 mm(2.05 mm)   · Type MH   1.2 mm(2.0 mm)</li> <li>· Type MH with Frame   0.6 mm(2.0 mm)</li> </ul>
Operating Life	50000 cycles min.
Temperature Range	-10 °C to +70 °C
Heat Resistance	+80 °C for 96 hours
Low Temperature Resistance	-25 °C for 96 hours
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours
Minimum Quantity/Packing Unit	500 pcs. Polyethylene Bag (Bulk)
	<ul style="list-style-type: none"> <li>· Type MV                    1000 pcs. Embossed Taping (Reel Pack)</li> <li>· Type MH with Frame   3000 pcs. Embossed Taping (Reel Pack)</li> <li>· Type MH                    4000 pcs. Embossed Taping (Reel Pack)</li> </ul>
	10000 pcs. Polyethylene Bag (Bulk)
Quantity/Carton	10000 pcs. Polyethylene Bag (Bulk)
	<ul style="list-style-type: none"> <li>· Type MV                    6000 pcs. Embossed Taping (Reel Pack)</li> <li>· Type MH with Frame   18000 pcs. Embossed Taping (Reel Pack)</li> <li>· Type MH                    24000 pcs. Embossed Taping (Reel Pack)</li> </ul>
	10000 pcs. Polyethylene Bag (Bulk)


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.





### 5N Detector Switches

Type: **ESE11**




#### ■ Features

- Wide range of customizable features including operational directions
- Light operating force
- Wide available range for reflow soldering

#### ■ Recommended Applications

- Detection of media in portable electronic equipment

#### ■ Explanation of Part Numbers




#### ■ Specifications

Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance	500 m $\Omega$ max. (Initial)
Insulation Resistance	100 M $\Omega$ min. (100 Vdc)
Dielectric Withstanding Voltage	100 Vac for 1 minute
Operating Force	350 mN max. (Full Travel)
Mounting Height	<ul style="list-style-type: none"> <li>· Type SV 4.9 mm</li> <li>· Type MV 4.9 mm (MV2, 7 : 5.4 mm)</li> <li>· Type SH 5.25 mm</li> <li>· Type MH 4.25 mm</li> <li>· Type HS, SF 3.6 mm</li> </ul>
Poles and Throws	1-pole 1-throw
Full Travel (Pushing distance)	<ul style="list-style-type: none"> <li>· Type SV 6.1 mm (2.4 mm)</li> <li>· Type MV 6.1 mm (2.4 mm)</li> <li>· Type SH 3.0 mm (2.4 mm)</li> <li>· Type MH 1.7 mm (2.4 mm)</li> <li>· Type HS, SF 6.3 mm (2.4 mm)</li> </ul>
Operating Life	50000 cycles min.
Temperature Range	-10 °C to +70 °C
Heat Resistance	+80 °C for 96 hours
Low Temperature Resistance	-25 °C for 96 hours
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

Minimum Quantity/Packing Unit	ESE11SV□ ESE11MV□ ESE11SH□ ESE11MH□ ESE11HS□ ESE11SF□	200 pcs. Polyethylene Bag (Bulk)
	ESE11MV□T (Excluding : ESE11MV2)	800 pcs. Embossed Taping (Reel Pack)
	ESE11MH□T	1500 pcs. Embossed Taping (Reel Pack)
Quantity/ Carton	ESE11SV□ ESE11MV□ ESE11SH□ ESE11MH□ ESE11HS□ ESE11SF□	10000 pcs. Polyethylene Bag (Bulk)
	ESE11MV2	8000 pcs. Polyethylene Bag (Bulk)
	ESE11MV□T (Excluding : ESE11MV2)	4800 pcs. Embossed Taping (Reel Pack)
	ESE11MH□T	9000 pcs. Embossed Taping (Reel Pack)


### ■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.




■ Dimensions in mm (not to scale)




Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)




Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Circuit Diagram



### ■ Packaging Specifications


Standard Reel Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 1HW Detector Switches

Type: **ESE23**



Bidirectional operation, midpoint auto-return Type


#### ■ Features

- External dimensions : 4.1 mm×5.0 mm, Height 1.5 mm
- Long over-travel (through-operation available)
- Usable as an operation switch (an input device)

#### ■ Recommended Applications

- Detection of media in portable electronic equipment (CD-ROM, DVD, Digital still cameras, etc.)
- Operating switches for other electronic equipment.

#### ■ Explanation of Part Numbers




#### ■ Specifications


Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance	500 m $\Omega$ max. (Initial)
Insulation Resistance	100 M $\Omega$ min. (100 Vdc)
Dielectric Withstanding Voltage	100 Vac for 1 minute
Operating Force	300 mN max.
Mounting Height	1.5 mm
Poles and Throws	1-pole 2-throws (OFF at midpoint)
Full Travel (Pushing distance)	With Boss 1.0 mm (1.5 mm) Without Boss 2.2 mm (1.5 mm)
Operating Life	50000 cycles min.
Temperature Range	-10 °C to +60 °C
Heat Resistance	+70 °C for 96 hours
Low Temperature Resistance	-25 °C for 96 hours
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours
Minimum Quantity/Packing Unit	4000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton	24000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)




### ■ Circuit Diagram



### ■ Packaging Specifications


Standard Reel Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 2W Detector Switches

Type: **ESE24**



Bidirectional operation, auto-return to midpoint type.


#### ■ Features

- A lever-type detector switch with high reliability using sliding mechanical contacts
- Long over-travel (through-operation available)
- Used as an operation switch (an input device)

#### ■ Recommended Applications

- Detection of media in portable electronic equipment (CD-ROM, DVD, Digital still cameras, etc.)
- Operating switches for other electronic equipment.

#### ■ Explanation of Part Number



6th & 7th	Mounting Method & Style
SV	Vertical type for wave soldering
SH	Horizontal type for wave soldering
MV	Vertical type for reflow soldering
MH	Horizontal type for reflow soldering


#### ■ Specifications

Rating	50 $\mu$ A 3 Vdc to 10 mA 5 Vdc (Resistive load)	
Contact Resistance	500 m $\Omega$ max. (Initial)	
Insulation Resistance	100 M $\Omega$ min. (100 Vdc)	
Dielectric Withstanding Voltage	100 Vac for 1 minute	
Operating Force	350 mN max.	
Mounting Height	<ul style="list-style-type: none"> <li>· Type SV 5.6 mm</li> <li>· Type SH 4.65 mm</li> <li>· Type MV 5.6 mm</li> <li>· Type MH 3.0 mm</li> </ul>	
Poles and Throws	1-pole 2-throws (OFF at midpoint)	
Full Travel (Pushing distance)	<ul style="list-style-type: none"> <li>· Type SV 6.1 mm (2.45 mm)</li> <li>· Type SH 2.6 mm (2.45 mm)</li> <li>· Type MV 6.1 mm (2.45 mm)</li> <li>· Type MH 1.4 mm (2.45 mm)</li> </ul>	
Operating Life	50000 cycles min.	
Temperature Range	-10 °C to +70 °C	
Heat Resistance	+80 °C for 96 hours	
Low Temperature Resistance	-25 °C for 96 hours	
Humidity Resistance	+40 °C 90 % to 95 % RH for 96 hours	
Minimum Quantity/Packing Unit	ESE24MH, MV, SV, SH	200 pcs. Polyethylene Bag (Bulk) *1
	ESE24MH□T	1000 pcs. Embossed Taping (Reel Pack) *2
	ESE24MV□T	500 pcs. Embossed Taping (Reel Pack)
Quantity/Carton	ESE24MH, MV, SV, SH	10000 pcs. Polyethylene Bag (Bulk)
	ESE24MH□T	6000 pcs. Embossed Taping (Reel Pack)
	ESE24MV□T	3000 pcs. Embossed Taping (Reel Pack)

\*1 ESE24SH type: 160 pcs. (Polyethylene Bag), 8000 pcs. (Reel Pack)  
 \*2 ESE24SV, ESE24SH are excluded

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
 Should a safety concern arise regarding this product, please be sure to contact us immediately.


■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Circuit Diagram

1-pole 2-throws (N . O)




Terminal No. Lever position	①	c	②
ⓕ		○	
ⓐ	○	○	
ⓑ		○	○

### ■ Packaging Specifications


Standard Reel Dimensions in mm (not to scale)

#### Taping Reel




#### Embossed Carrier Taping

ESE24MH□T



ESE24MV□T



CONTENTS

Page

■ Quick Selection Guide .....	ES55
■ Minimum Quantity/Packing Unit .....	ES56
■ Jog Ball (EVQWJN) .....	ES57

### ■ Quick Selection Guide

Type, Series	Appearance	Part Numbers	Country of origin	External Dimensions L×W×H (mm)	Operating Force	Applicable Soldering * SMD	Page
Jog Ball		EVQWJN	China	10.7×9.3×6.0	Push : 1.0 N, 1.3 N, 1.6 N (Use of EVQP6 Type)	* Reflow Soldering	ES57

Country of origin : As of April 2013

### ■ Minimum Quantity/Packing Unit

Please place an order by an integer multiple of the Quantity/Carton.

Type, Series	Part Numbers	Packaging	Quantity/Carton	Min.Q'ty/ Packing Unit
Jog Ball	EVQWJN	Tray Pack	1000 pcs.	200 pcs.

### Jog Ball


Type: **EVQWJN**



#### ■ Features

- External dimensions : 10.7 mm×9.3 mm, Height: 6.0 mm,  
Ball diameter : φ5.5 mm
- Long life : 1 million operations (each direction)  
Magnetic detection method.  
(Non-contact type)
- High resolution : 11 pulses/360°
- The ball rotation and push operation provide superior operability
- Light transmitting type (LED mounted on a PWB)


#### ■ Usage Example



#### ■ Recommended Applications

- Menu selection and confirmation operations of portable electronic equipment (Mobile phones, Digital cameras, Portable audio players, PDAs, and HPCs), car navigation systems, remote controllers, etc.

#### ■ Explanation of Part Numbers



#### ■ Specifications

Electrical	Rating		· 20 mA 15 Vdc (Use of EVQP6 Type) · 3 Vdc (Use of AN48840B Type)
Mechanical	Operating Force	Push	1.0 N, 1.3 N, 1.6 N (Use of EVQP6 Type)
	Resolution	Rotate	11 pulses/ 360°
	Travel	Push	0.9 mm
Endurance	Operating life	Rotate	1000000 cycles min.
		Push	1000000 cycles min. (Use of EVQP6 Type)
Temperature Range			-20 °C to +70 °C
Minimum Quantity/Packing Unit			200 pcs. (Tray Pack)
Quantity / Carton			1000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.



## CONTENTS

	Page
■ Quick Selection Guide .....	ES60
■ Checklist Befor Inquiry .....	ES62
■ Application Notes .....	ES63
■ Common Specifications .....	ES64
■ Minimum Quantity/Packing Unit .....	ES65
■ 4 mm Square SMD Light Touch Switches (EVQP6/6P6/7P6/9P6) .....	ES66
■ 4.5 mm Square SMD Light Touch Switches (EVQPQ) .....	ES70
■ 4.9 mm Square SMD Light Touch Switches (EVQPL/3PL/5PL/PT) .....	ES73
■ 6 mm Square Thin Type SMD Light Touch Switches (EVQP0/Q2) .....	ES76
■ 3.0 mm×2.0 mm SMD Light Touch Switches (EVPAW) .....	ES80
■ 3.0 mm×2.6 mm SMD Light Touch Switches (EVPAF) .....	ES83
■ 3.5 mm×2.9 mm SMD Light Touch Switches (EVPAA) .....	ES86
■ 4.7 mm×3.5 mm SMD Light Touch Switches (EVQP2/P9/3P2) .....	ES89
■ 6.0 mm×3.5 mm SMD Light Touch Switches (EVQPE1/PN/5P) .....	ES93
■ 3.5 mm×2.9 mm Side-operational SMD Light Touch Switches (EVQP7/P3/9P7) .....	ES95
■ 3.5 mm×2.9 mm Side-operational Half Dive / SMD Light Touch Switches (EVPAN) .....	ES99
■ Small-sized Side-operational SMD Light Touch Switches (EVQPU) .....	ES102
■ 2.8 mm×2.3 mm Side-operational Edge Mount Light Touch Switches (EVPAV) .....	ES106
■ 4.5 mm×2.2 mm Side-operational Edge Mount Light Touch Switches (EVPAE) .....	ES108
■ 6.2 mm×2.5 mm Side-operational Edge Mount Light Touch Switches (EVQP4) .....	ES110
■ 6.1 mm×4.0 mm Side-operational SMD Light Touch Switches (EVQPS) .....	ES113
■ 5N Type Light Touch Switches (EVQPA/PB) .....	ES117
■ 5N Type Side-operational Light Touch Switches (EVQPF) .....	ES120
■ 5N Type 2R Light Touch Switches (EVQ2) .....	ES122
■ 5N Type Side-operational 4R Light Touch Switches (EVQPC) .....	ES124
■ Round Type 2R Light Touch Switches (EVQ11) .....	ES126
■ 6.0 mm×3.5 mm Light Touch Switches (EVQPE) .....	ES128
■ 6.0 mm×3.5 mm 2R Light Touch Switches (EVQPJ) .....	ES130
■ Over Travel Light Touch Switches (EVQP0) .....	ES132
■ 4 mm Square Double-action SMD Light Touch Switches (EVPAH) .....	ES134
■ 6 mm Square Thin Type Double-action SMD Light Touch Switches (EVQPR/Q0/3PR) .....	ES137
■ 4.7 mm×3.5 mm Double-action Side-operational SMD Light Touch Switches (EVPAJ) .....	ES140
■ 6.2 mm×3.7 mm Double-action Side-operational Edge Mount / SMD Light Touch Switches (EVQQ0) .....	ES143
■ 6 mm Square Long Travel SMD Light Touch Switches (EVQP0/P1/9P) .....	ES146
■ 6 mm Square Long Travel 2 terminals SMD Light Touch Switches (EVPAS) .....	ES149
■ 6 mm Square Long Travel 2R Light Touch Switches (EVQPV) .....	ES152
■ 8 mm Square Long Travel SMD Light Touch Switches (EVQQ1) .....	ES154
■ 8 mm Square Long Travel 2R Light Touch Switches (EVQQJ) .....	ES156
■ 10 mm Square Center Space Long Travel SMD Light Touch Switches (EVPAD) .....	ES158



## ■ Quick Selection Guide

Type, Series	Appearance	Part Numbers	Country of origin	External Dimensions L×W×H (mm)	Operating Force	Applicable Soldering *SMD	Variety	Page
4 mm Square SMD		EVQP6	Japan Malaysia	4.1×4.1×0.35 4.1×4.1×0.58	1.6 N 2.4 N	*Reflow	Push Plate:With, Without Ground Terminal:With, Without Positioning Boss:Without	ES66
		EVQ6P6 EVQ7P6 EVQ9P6		4.1×4.1×0.43	1.0 N 1.6 N 2.4 N		Push Plate:Without Ground Terminal:With Positioning Boss:Without	
4.5 mm Square SMD		EVQPQ	Japan	4.5×4.5×0.55	1.6 N 2.4 N	*Reflow	Push Plate:Without Ground Terminal:Without Positioning Boss:Without	ES70
4.9 mm Square SMD		EVQPL	Japan Malaysia	4.9×4.9×0.8	1.0 N	*Reflow	Push Plate:With, Without Ground Terminal:With Positioning Boss:Without	ES73
		EVQ3PL EVQ5PL EVQPT		4.9×4.9×1.5	1.6 N 2.6 N 3.5 N			
6 mm Square Thin Type SMD		EVQP0 EVQQ2	Malaysia	6.5×6.0×2.0 6.5×6.0×2.5 6.5×6.0×3.1	0.5 N, 0.6 N 1.0 N, 1.3 N 1.6 N, 2.6 N 3.5 N	*Reflow	Push Plate:With Ground Terminal:With, Without Positioning Boss:Without	ES76
<b>NEW</b> 3.0 mm×2.0 mm SMD		EVPAW	Japan China	3.0×2.0×0.6	1.6 N 2.4 N 3.3 N	*Reflow	Push Plate:With	ES80
3.0 mm×2.6 mm SMD		EVPAF	Japan Malaysia China	3.0×2.6×0.65	1.3 N 1.6 N	*Reflow	Push Plate:With	ES83
				3.0×2.6×0.7	2.4 N 3.4 N			
3.5 mm×2.9 mm SMD		EVPA A	Japan China	3.5×2.9×1.7	1.0 N, 1.6 N 2.4 N, 3.5 N 5.0 N	*Reflow	Push Plate:With Ground Terminal:With, Without Positioning Boss:Without	ES86
4.7 mm×3.5 mm SMD		EVQP2 EVQP9 EVQ3P2	Japan	4.7×3.5×2.1 4.7×3.5×2.5	1.0 N, 1.6 N 2.4 N, 2.5 N 3.5 N, 5.0 N	*Reflow	Push Plate:With Push Travel:Middle, Short Ground Terminal:With, Without Positioning Boss:Without	ES89
6.0 mm×3.5 mm SMD		EVQPE1 EVQPN EVQ5P	Japan	6.0×3.5×4.3 6.0×3.5×5.0	1.0 N 1.6 N 2.4 N	*Reflow	Push Plate:With Embossed Taping Ground Terminal:Without Positioning Boss:Without	ES93
3.5 mm×2.9 mm Side-operational SMD		EVQP7 EVQP3 EVQ9P7	Japan China Malaysia	3.5×2.9×1.35	1.6 N 2.2 N	*Reflow	Terminal:Straight, J-bent, L-shape Ground Terminal:With, Without Positioning Boss:With, Without	ES95
3.5 mm×2.9 mm Side-operational Half Dive / SMD		EVPAN	Japan Malaysia	3.5×2.9×1.2	1.6 N 2.2 N	*Reflow	Terminal:Straight L-shape	ES99
Small-sized Side-operational SMD		EVQPU	Japan China	4.7×3.5×1.65	1.6 N 2.2 N	*Reflow	Terminal:Straight, J-bent Ground Terminal:With, Without Positioning Boss:With, Without	ES102
<b>NEW</b> 2.8 mm×2.3 mm Side-operational Edge Mount		EVPAV	Japan China	2.8×2.3×1.95	1.6 N	*Reflow	Ground Terminal:With (Cover Plate)	ES106
4.5 mm×2.2 mm Side-operational Edge Mount		EVPAE	Japan	4.5×2.25×2.9	1.6 N 3.0 N	*Reflow	Ground Terminal:With (Cover Plate)	ES108
6.2 mm×2.5 mm Side-operational Edge Mount		EVQP4	Japan	6.2×2.55×3.5	1.0 N, 1.6 N 2.4 N, 2.5 N 3.5 N, 5.0 N	*Reflow Mounted on pc board edge	Push Plate:With Push Travel:Middle, Short Ground Terminal:With (Cover Plate)	ES110
6.1 mm×4.0 mm Side-operational SMD		EVQPS	Japan	6.1×4.0×1.8	1.6 N 2.2 N	*Reflow	Terminal : Straight, J-bent Ground Terminal:With, Without Positioning Boss:With, Without	ES113

Country of origin : As of April 2013

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

Type, Series	Appearance	Part Numbers	Country of origin	External Dimensions L×W×H (mm)	Operating Force	Applicable Soldering *SMD	Variety	Page
5N Type		EVQPA	Japan Malaysia China	6.0×6.0×4.3 6.0×6.0×5.0 6.0×6.0×7.0	1.0 N 1.3 N 1.6 N	Manual Wave Soldering	Push Plate:With Ground Terminal:With, Without	ES117
		EVQPB	Japan China	6.0×6.0×9.5	2.6 N			
5N Type Side-operational		EVQPF	Japan	7.5×7.1×7.15 7.5×7.1×7.85 7.5×7.1×9.85 7.5×7.1×12.35	1.0 N 1.3 N 1.6 N 2.6 N	Manual Wave Soldering	Push Plate:With	ES120
5N Type 2R		EVQ2	Japan Malaysia	6.0×6.0×4.3 6.0×6.0×5.0 6.0×6.0×7.0 6.0×6.0×9.5	1.0 N 1.3 N 1.6 N 2.6 N	Wave Soldering	Push Plate:With Ground Terminal:With, Without	ES122
5N Type Side-operational 4R		EVQPC	Japan	7.5×7.1×9.25	1.0 N 1.3 N 1.6 N 2.6 N	Wave Soldering	Push Plate:With	ES124
Round Type 2R		EVQ11	Japan Malaysia China	6.0×6.0×4.3 6.0×6.0×5.0 6.0×6.0×7.0 6.0×6.0×9.5	1.0 N 1.3 N 1.6 N 2.6 N	Wave Soldering	Push Plate:With Ground Terminal:Without	ES126
6.0 mm×3.5 mm		EVQPE	Japan	6.0×3.5×4.3 6.0×3.5×5.0	1.0 N 1.6 N 2.4 N	Wave Soldering	Push Plate:With Bulk Ground Terminal:Without Positioning Boss:Without	ES128
6.0 mm×3.5 mm 2R		EVQPJ	Japan	6.0×3.5×4.3 6.0×3.5×5.0	1.0 N 1.6 N 2.4 N	Wave Soldering	Push Plate:With Radial Taping Ground Terminal:Without Positioning Boss:Without	ES130
Over Travel		EVQP0	Japan China	6.2×6.2×7.45	0.74 N 1.3 N	Wave Soldering	Push Plate:With Ground Terminal:Without	ES132
4 mm Square Double-action SMD		EVPAH	Japan	4.0×4.1×0.59	① 0.8 N, 0.9 N, 1.0 N ② 1.6 N, 2.0 N, 2.6 N	*Reflow	Push Plate:With Terminal:J-bent Ground Terminal:With (Cover Plate)	ES134
6 mm Square Thin Type Double-action SMD		EVQPR EVQQ0 EVQ3PR	Japan	6.0×6.0×0.9 6.0×6.0×0.95	① 0.7 N, 1.0 N ② 2.6 N	*Reflow	Push Plate:With, Without Ground Terminal:With, Without Positioning Boss:With, Without	ES137
4.7 mm×3.5 mm Double-action Side-operational SMD		EVPAJ	Japan	4.7×3.5×1.2	① 1.6 N ② 2.6 N	*Reflow	Straight L-shape	ES140
6.2 mm×3.7 mm Double-action Side-operational Edge Mount / SMD		EVQQ0	Japan	6.2×3.75×3.5	① 1.0 N ② 2.6 N	*Reflow Mounted on pc board edge/Reflow	Push Plate:With Ground Terminal:With (Cover Plate)	ES143
6 mm Square Long Travel SMD		EVQP0 EVQP1 EVQ9P	Japan	6.0×6.1×5.0	1.6 N, 2.0 N 2.2 N, 2.5 N 3.0 N, 3.5 N	*Reflow	Push Plate:With Push Travel: 1.0 mm, 1.3 mm Ground Terminal:Without	ES146
6 mm Square <b>NEW</b> Long Travel 2 terminals SMD		EVPAS	Japan	6.0×6.1×5.0	1.6 N, 2.0 N 2.2 N, 2.5 N 3.0 N, 3.5 N	*Reflow	Push Plate:With Push Travel: 1.0 mm, 1.3 mm Ground Terminal:Without	ES149
6 mm Square Long Travel 2R		EVQPV	Japan	6.0×6.1×5.0	1.6 N 2.0 N 2.2 N 2.5 N 3.5 N	Wave Soldering	Push Plate:With Push Travel: 1.0 mm, 1.3 mm Ground Terminal:Without	ES152
8 mm Square Long Travel SMD		EVQQ1	Japan	8.5×8.5×6.5	4.0 N 5.0 N	*Reflow	Push Plate:With Ground Terminal:Without	ES154
8 mm Square Long Travel 2R		EVQQJ	Japan	8.0×8.0×5.0 8.0×8.0×5.5 8.0×8.0×6.1	0.8 N 1.3 N 2.5 N 3.0 N	Wave Soldering	Push Plate:With Push Travel: 1.0 mm, 1.2 mm, 1.75mm Ground Terminal:Without	ES156
10 mm Square Center Space Long Travel SMD		EVPAD	Japan	9.8×9.8×4.7	4.0 N	*Reflow	Push Plate:With Push Travel:1.0 mm Ground Terminal:Without	ES158

Country of origin : As of April 2013

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

### ■ Checklist Before Inquiry

When specifying Light Touch Switches, please take advantage of our standard products for better price and delivery. Please inquire about the following items before ordering.

Item			Information (Requirements)	
Common	C-1	Inquiry purpose	New use, Modification, Others ( )	
	C-2	Modification	Previous supplier	
			Conventional part No.	
			Purpose	
	C-3	Application	Equipment	
			Environment	Indoor/Outdoor use, Stationary/Portable set, Car installation High humidity, SO <sub>2</sub> , NaCl
Temperature			( °C) to ( °C)	
Electrical Specifications	E-1	Ratings	( mA), ( V dc )	
Shapes/Dimensions	M-1	Operation	Operation type	· Vertical (The push plate operation is perpendicular to the printed circuit board) · Horizontal (The push plate operation is parallel to the printed circuit board)
			Operating force	( N)
			Travel	( mm)
	M-2	Anti-electrostatic	Ground Terminal: With, Without	
	M-3	Shapes	Dimensions	( ) mm × ( ) mm, height( ) mm
			Terminal Type (Reflow)	Flat Terminal, J-bent Terminal
Positioning			Positioning Boss: with, without	
Others	L-1	Soldering	Soldering	Manual, Flow, Reflow
			Soldering Conditions	Temp.( °C ), Time ( s )
	L-2	Packing Unit	Polyethylene Bag (Bulk), Embossed Taping (Reel Pack), Raial Taping (Reel Pack), Stick	
	L-3	Special requirements for endurance		
	L-4	Special requirements for safety		
	L-5	Other questionnaires		

Notes:

1. When selecting Switches, please consider using our standard products for better prices and short delivery times.
2. Please inform the following items when ordering.

## ■ ⚠ Application Notes

When using our Light Touch Switches, please observe the following items (“prohibited items”) and be cautious of the following in order to prevent dangerous accidents and deterioration of performance.

### 1. Notes on soldering conditions

When performing solder dipping, check the soldering conditions according to the “Product Specification for Information,” because the conditions vary with the product. Do not wash the switch after solder dipping because flux may enter the switch, resulting in contact failure. Avoid use of jumper cables near the switches because flux may attach to them.

1. Control the liquid level so that flux does not enter the switch from the top.
2. When performing manual soldering, perform it at a temperature of 350 °C within 3 seconds.
3. Do not apply a load to the switch lever after soldering.
4. For reflow soldering  
When performing reflow soldering using a hot-air oven or an infrared oven, observe the following conditions. Since the temperature applied to a switch and its terminals varies with the type and size of the PWB and the mounting density of the parts, sufficiently check the conditions in advance.
5. When a board with double-sided through holes is used, do not make through holes immediately under the switch case. Otherwise, the switch case may fuse.

### 2. Notes on design of a set

1. For switch mounting holes, refer to the “Recommended PWB piercing plan” as described in “Dimensions.”
2. For shapes of operating parts in a set, refer to recommended shapes described in “Product Specifications for Information.”

### 3. Other prohibited items and notes

1. Take care not to apply excessive load to a switch. Doing so may cause terminal deformation, contact failure, and/or malfunction.
2. Sufficiently check any generation of corrosive gas from the components in a set under actual operating conditions. Corrosive gas may cause contact failure and corrosive stress cracking of metal.
3. To prevent contact failure due to foreign matter (such as chips of a PWB and flux) entering a switch, take care when handling a PWB after mounting. Do not stack the PWB's.

### 4. Prohibited items and notes on storage conditions

Do not store the switches under high temperatures and/or high humidity, or in a location where corrosive gas may be generated. Store the switches at room temperature and room humidity in a packed condition. Use them within a maximum of 6 months after delivery. Check the date of manufacture on the package box and apply the “first-in-first-out” rule. If unpacked switches must be stored as inventory, store them in a polyethylene bag to keep out air.

### 5. Prohibited items on fire and smoking

1. Absolutely avoid use of a switch beyond its rated range because doing so may cause a fire.  
If misuse or abnormal use may result in conditions in which the switch is used out of its rated range, take proper measures such as current interruption using a protective circuit.
2. The grade of nonflammability for resin used in Light Touch Switches is “94HB”, which is based on UL94 Standards (flammability test for plastic materials). Prohibit use in a location where a spreading fire may be generated or prepare against a spreading fire.

### 6. For use in equipment for which safety requested

Although care is taken to ensure switch quality, variation of contact resistance (increase), short circuits, open circuits, and temperature rise are some problems that might be generated.

To design a set which places maximum emphasis on safety, review the affect of any single fault of a switch in advance and perform virtually fail-safe design to ensure maximum safety by:


1. preparing a protective circuit or a protective device to improve system safety, and
2. preparing a redundant circuit to improve system safety so that the single fault of a switch does not cause a dangerous situation.

### 7. For actual use, be sure to refer to “Product Specifications for Information.”

### ■ Common Specifications


#### ■ Packaging Methods for Radial Taping

##### ● Drawing-out of taped products



Drawing-out can be done from top or bottom of an inner carton.

##### ● Pull-strength of taped products



- Taped products shall not be fully drawn-out from the tape when pulling in direction A at 5.0 N max.
- Taped products shall not be drawn-out from the tape when pulling in direction B at 1.0N for 3 seconds.

### ■ Minimum Quantity/Packing Unit

Please place an order by an integer multiple of the Quantity/Carton.

Type, Series	Part No.	Packaging	Quantity/ Carton	Min. Q'ty Packing Unit	Notes	
4 mm Square SMD Light Touch Switches	EVQP6/6P6/7P6/9P6	Embossed Taping (Reel Pack)	50000 pcs.	10000 pcs.		
4.5 mm Square SMD Light Touch Switches	EVQPQ		50000 pcs.	10000 pcs.		
4.9 mm Square SMD Light Touch Switches	EVQPL/3PL/5PL/PT		25000 pcs.	5000 pcs.		
6 mm Square Thin Type SMD Light Touch Switches	EVQP0		20000 pcs.	4000 pcs.	H=2.0 mm	
	EVQQ2		10000 pcs.	2000 pcs.	H=2.5 mm, 3.1 mm	
3.0 mmx2.0 mm SMD Light Touch Switches	EVPAW		50000 pcs.	10000 pcs.		
3.0 mmx2.6 mm SMD Light Touch Switches	EVPAF		40000 pcs.	8000 pcs.		
3.5 mmx2.9 mm SMD Light Touch Switches	EVPA A		25000 pcs.	5000 pcs.		
4.7 mmx3.5 mm SMD Light Touch Switches	EVQP2/P9/3P2		20000 pcs.	4000 pcs.		
6.0 mmx3.5 mm SMD Light Touch Switches	EVQPE1/PN/5P		10000 pcs.	2000 pcs.	H=5.0 mm	
			12500 pcs.	2500 pcs.	H=4.3 mm	
3.5 mmx2.9 mm Side-operational SMD Light Touch Switches	EVQP7/P3/9P7		25000 pcs.	5000 pcs.		
3.5 mmx2.9 mm Side-operational Half Dive / SMD Light Touch Switches	EV PAN		35000 pcs.	7000 pcs.		
Small-sized Side-operational SMD Light Touch Switches	EVQPU		20000 pcs.	4000 pcs.		
2.8 mmx2.3 mm Side-operational Edge Mount Light Touch Switches	EVPAV		40000 pcs.	8000 pcs.		
4.5 mmx2.2 mm Side-operational Edge Mount Light Touch Switches	EVPAE		17500 pcs.	3500 pcs.		
6.2 mmx2.5 mm Side-operational Edge Mount Light Touch Switches	EVQP4		12500 pcs.	2500 pcs.		
6.1 mmx4.0 mm Side-operational SMD Light Touch Switches	EVQPS		Embossed Taping (Reel Pack)	16000 pcs.	4000 pcs.	
5N Type Light Touch Switches	EVQPA/PB		Polyethylene Bag (Bulk)	10000 pcs.	500 pcs.	
5N Type Side-operational Light Touch Switches	EVQPF			10000 pcs.	500 pcs.	
5N Type 2R Light Touch Switches	EVQ2	Radial Taping (Reel Pack)	10000 pcs.	1000 pcs.		
5N Type Side-operational 4R Light Touch Switches	EVQPC		7000 pcs.	700 pcs.		
Round Type 2R Light Touch Switches	EVQ11		25000 pcs.	2500 pcs.		
6.0 mmx3.5 mm Light Touch Switches	EVQPE	Polyethylene Bag (Bulk)	10000 pcs.	1000 pcs.		
6.0 mmx3.5 mm 2R Light Touch Switches	EVQPJ	Radial Taping (Reel Pack)	20000 pcs.	2000 pcs.		
Over Travel Light Touch Switches	EVQP0	Polyethylene Bag (Bulk)	10000 pcs.	500 pcs.		
4 mm Square Double-action SMD Light Touch Switches	EVPAH	Embossed Taping (Reel Pack)	40000 pcs.	8000 pcs.		
6 mm Square Thin Type Double-action SMD Light Touch Switches	EVQPR/Q0/3PR	Embossed Taping (Reel Pack)	25000 pcs.	5000 pcs.		
4.7 mmx3.5 mm Double-action Side-operational SMD Light Touch Switches	EVPAJ	Embossed Taping (Reel Pack)	25000 pcs.	5000 pcs.		
6.2 mmx3.7 mm Double-action Side-operational Edge Mount / SMD Light Touch Switches	EVQQ0	Embossed Taping (Reel Pack)	12500 pcs.	2500 pcs.		
6 mm Square Long Travel SMD Light Touch Switches	EVQP0/P1/9P	Embossed Taping (Reel Pack)	10000 pcs.	2000 pcs.		
6 mm Square Long Travel 2 terminals SMD Light Touch Switches	EVPAS	Embossed Taping (Reel Pack)	10000 pcs.	2000 pcs.		
6 mm Square Long Travel 2R Light Touch Switches	EVQPV	Radial Taping (Reel Pack)	25000 pcs.	2500 pcs.		
8 mm Square Long Travel SMD Light Touch Switches	EVQQ1	Embossed Taping (Reel Pack)	10000 pcs.	1000 pcs.		
8 mm Square Long Travel 2R Light Touch Switches	EVQQJ	Radial Taping (Reel Pack)	10000 pcs.	1000 pcs.		
10 mm Square Center Space Long Travel SMD Light Touch Switches	EVPAD	Embossed Taping (Reel Pack)	5000 pcs.	1000 pcs.		

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 4 mm Square SMD Light Touch Switches

Type: **EVQP6/EVQ6P6/EVQ7P6/EVQ9P6**




#### ■ Features

- External dimensions : 4.1 mm×4.1 mm  
Height :Without Push Plate 0.35 mm, With Push Plate 0.58 mm  
:Without Push Plate-With Ground Terminal 0.43 mm
- Long-life :1000000 cycles min.  
(Operating Force 1.6 N Type)
- Dust-proof structure

#### ■ Recommended Applications

- Operating switches for portable electronic equipment  
(Mobile phones, Camcorders, Portable audio players, etc.).

#### ■ Explanation of Part Numbers



#### ■ Product Chart

Height Packaging Operating Force	Without Push Plate H=0.35 mm	With Push Plate H=0.58 mm	Without Push Plate With Ground Terminal H=0.43 mm
	Embossed	Embossed	Embossed
1.0 N	—	—	EVQ7P6
1.6 N	EVQP6D	EVQP6L	EVQ6P6
2.4 N	EVQP6P	EVQP6Y	EVQ9P6

#### ■ Specifications



Type		Snap action / Push-on type SPST	
		Without Push Plate	With Push Plate
Electrical	Rating	10 μA 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	500 mΩ max.	
	Insulation Resistance	50 MΩ min.	
	Dielectric Withstanding Voltage	100 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 10 ms max. (OFF)	
Mechanical	Operating Force	1.0 N, 1.6 N, 2.4 N	
	Travel	0.2 mm (EVQ7P6 : 0.15 mm)	
Endurance	Operating Life	1.0 N, 1.6 N : 1000000 cycles min. 2.4 N : 500000 cycles min.	
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		10000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		50000 pcs.	

Note: Non washable


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.




■ Dimensions in mm (not to scale)

<p>No. 3</p> <p>EVQ7P6 EVQ6P6 EVQ9P6</p> <p>(Embossed Taping)</p> <p>Surface mount For reflow soldering Without push plate With Ground Terminal</p> 	 <p>Circuit diagram</p> <p>PWB land pattern for reference Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.</p>		
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Operating Life</p>
<p>EVQ7P6B40</p>	<p>1.0 N</p>	<p>0.43 mm</p>	<p>1000000 cycles</p>
<p>EVQ6P6B40</p>	<p>1.6 N</p>	<p>0.43 mm</p>	<p>1000000 cycles</p>
<p>EVQ9P6B40</p>	<p>2.4 N</p>	<p>0.43 mm</p>	<p>500000 cycles</p>

### Recommended Reflow Soldering Conditions




### Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	$P_1$	$P_2$	$P_0$	$D_0$ Dia.	$t_1$	$t_2$
EVQP6	0.35/0.58	4.0±0.2	5.0±0.2	12.0 <sup>+0.3</sup> <sub>-0.1</sub>	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.30±0.05	0.5/0.7 <sup>+0.2</sup> <sub>-0.1</sub>
EVQ6P6	0.43											
EVQ7P6												
EVQ9P6												

### Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	$\phi 380.0 \pm 2.0$	$\phi 80.0 \pm 1.0$	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	2.0±0.5


  

Item	W	T	t	r
Rate (mm)	13.5±1.5	17.5±1.0	1.0 to 3.0	1.0±0.5

### Recommended Shape of Test Pole



### Recommended Operating Conditions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

### 4.5 mm Square SMD Light Touch Switches

Type: **EVQPQ**




#### ■ Features

- External dimensions: 4.5 mm×4.5 mm, Height 0.55 mm
- Lightweight: 20 mg (1/2 compared with conventional type)

#### ■ Recommended Applications

- Operation switches for portable electronic equipment (Camcorders, Portable audio players, etc.)

#### ■ Explanation of Part Numbers




#### ■ Specifications

Type		Snap action/Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	100 m $\Omega$ max.
	Insulation Resistance	50 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	3 ms max. (ON) 10 ms max. (OFF)
Mechanical	Operating Force	1.6 N $\pm$ 0.5 N 2.4 N $\pm$ 0.6 N
	Travel	0.2 mm $\pm$ 0.1 mm
Endurance	Operating Life	200000 cycles min. (1.6 N), 50000 cycles min. (2.4 N)
Operating Temperature		-20 °C to +70 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		10000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		50000 pcs.

Note: Non washable


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)




■ Before using this product


- If the inclination of the actuator is widened by using soft materials, such as rubber, for the setting side of the operation section (connecting area between button and actuator), it may cause functional problems.



## Recommended Reflow Soldering Conditions




## Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQPQ	0.55	5.0 <sup>+0.30</sup> <sub>-0.25</sub>	4.6 <sup>+0.3</sup> <sub>-0</sub>	12.0±0.1	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.30±0.05	0.65 <sup>+0.2</sup> <sub>-0.1</sub>

## Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ370.0±2.0	φ50.0 min.	φ13.0±0.5	φ21.0±1.0	2.0±0.5


  

Item	W	T	t	r
Rate (mm)	14.0±1.5	—	1.0 to 3.0	1.0±0.5

## Recommended Shape of Test Pole



## Recommended Operating Conditions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 4.9 mm Square SMD Light Touch Switches

Type: **EVQPL/EVQ3PL**  
**EVQ5PL/EVQPT**




#### ■ Features

- External dimensions : 4.9 mm×4.9 mm,  
Height: 0.8 mm(Without push plate), 1.5 mm(With push plate)

#### ■ Recommended Applications

- Operation switches for portable electronic equipment (Notebook PC, Camcorders, Portable audio players, etc.)
- Operation switches for car audio systems

#### ■ Explanation of Part Numbers



#### ■ Product Chart

Height	H=0.8 mm	H=1.5 mm (With Push Plate)
Packaging	Embossed	Embossed
Operating Force		
1.0 N	EVQPLB	EVQPLD, EVQPT5
1.6 N	EVQPLF	EVQPLH, EVQPT9
2.6 N	EVQPLK	EVQPLM
3.5 N	EVQ5PL	EVQ3PL



#### ■ Specifications

Type		Snap action/Push-on type SPST	
Electrical	Rating	10 μA 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	50 mΩ max.	
	Insulation Resistance	50 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 8 ms max. (OFF)	
Mechanical	Operating Force	1.0 N±0.5 N 1.6 N±0.5 N	2.6 N±0.6 N 3.5 N±1.0 N
	Travel	0.25 mm <sup>+0.10</sup> / <sub>-0.20</sub> mm	
Endurance	Operating Life	500000 cycles min.	200000 cycles min.
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		5000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		25000 pcs.	

Note: Non washable


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)


<p>No. 1</p> <p>EVQPLB EVQPLF EVQPLK EVQ5PL</p> <p>(Embossed Taping)</p> <p>Surface mount For reflow soldering Without push plate</p> 	 <p>Be careful not to scratch the film</p> <p>Operating part</p> <p>PWB land pattern for reference</p> <p>Circuit diagram</p>		
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Operating Life</p>
<p>EVQPLBA08</p>	<p>1.0 N</p>	<p>0.8 mm</p>	<p>500000 cycles</p>
<p>EVQPLFA08</p>	<p>1.6 N</p>	<p>0.8 mm</p>	<p>500000 cycles</p>
<p>EVQPLKA08</p>	<p>2.6 N</p>	<p>0.8 mm</p>	<p>200000 cycles</p>
<p>EVQ5PLA08</p>	<p>3.5 N</p>	<p>0.8 mm</p>	<p>200000 cycles</p>
<p>No. 2</p> <p>EVQPLD/PT5 EVQPLH/PT9 EVQPLM EVQ3PL</p> <p>(Embossed Taping)</p> <p>Surface mount For reflow soldering With push plate</p> 	 <p>Operating part</p> <p>PWB land pattern for reference</p> <p>Circuit diagram</p>		
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Operating Life</p>
<p>EVQPLDA15/PT5A15</p>	<p>1.0 N</p>	<p>1.5 mm</p>	<p>500000/2000000 cycles</p>
<p>EVQPLHA15/PT9A15</p>	<p>1.6 N</p>	<p>1.5 mm</p>	<p>500000/2000000 cycles</p>
<p>EVQPLMA15</p>	<p>2.6 N</p>	<p>1.5 mm</p>	<p>200000 cycles</p>
<p>EVQ3PLA15</p>	<p>3.5 N</p>	<p>1.5 mm</p>	<p>200000 cycles</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Recommended Reflow Soldering Conditions




### ● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQPL EVQ3PL EVQ5PL EVQPT	0.8/1.5	5.0±0.2	5.0±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>0</sub>	0.35±0.05	1.0/1.7±0.2

### ● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ370.0±2.0	φ50.0 min.	φ13.0±0.5	φ21.0±1.0	2.0±0.5


  

Item	W	T	t	r
Rate (mm)	14.0±1.5	—	1.0 to 3.0	1.0±0.5

### ■ Recommended Shape of Test Pole



### ■ Recommended Operating Conditions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

### 6 mm Square Thin Type SMD Light Touch Switches

Type: **EVQP0**  
**EVQQ2**




#### ■ Features

- External dimensions : 6.5 mm×6.0 mm, Height 1.8 mm (Excluding the push plate)
- With or without ground terminal, height, operating force
- Overstroke travel

#### ■ Recommended Applications

- Operating switches for other electronic equipment
- Operation switches for PC mouse
- Car audio systems

#### ■ Explanation of Part Numbers





#### ■ Specifications

Travel Type		Short Push Travel	Overstroke Travel
Type		Snap action/Push-on type SPST	
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	100 m $\Omega$ max.	
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	10 ms max. (ON, OFF)	
Mechanical	Operating Force	0.5 N, 1.0 N, 1.3 N, 1.6 N, 2.6 N, 3.5 N	0.6 N, 1.0 N
	Travel	0.25 mm (0.2 mm : 0.5N, 1.0N)	0.3 mm
Endurance	Operating Life	0.5 N : 2000000 cycles min. 1.0 N, 1.3 N, 1.6 N : 1000000 cycles min. 2.6 N : 200000 cycles min. 3.5 N : 100000 cycles min.	0.6 N : 2000000 cycles min. 1.0 N : 1000000 cycles min.
Operating Temperature		-40 °C to +85 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		H=2.0 mm	4000 pcs. Embossed Taping (Reel Pack)
		H=2.5 mm, 3.1 mm	2000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		H=2.0 mm	20000 pcs.
		H=2.5 mm, 3.1 mm	10000 pcs.

Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


<p>No. 1</p> <p><b>EVQP0</b></p> <p>Overstroke travel : 0.35 mm With J-bent terminals</p> 	 <p style="text-align: center;">Circuit Diagram</p> <p style="text-align: center;">PWB land pattern for reference</p>				
Part Numbers	Operating Force	Height	Push Plate Color	Ground Terminal	Operating Life
EVQP0N02B	0.6 N	2.5 mm	Blue	Without	2000000 cycles
EVQP0P02B	0.6 N	2.5 mm	Blue	With	2000000 cycles
EVQP0Q02Q	1.0 N	2.5 mm	Gray	Without	1000000 cycles
EVQP0S02Q	1.0 N	2.5 mm	Gray	With	1000000 cycles

### ■ Dimensions in mm (not to scale)


No. 2											
<b>EVQQ2</b> Short push travel : 0.25 mm With J-bent terminals						<table border="1"> <thead> <tr> <th>Height</th> </tr> </thead> <tbody> <tr> <td>H</td> </tr> <tr> <td>2.0±0.2</td> </tr> <tr> <td>2.5±0.2</td> </tr> <tr> <td>3.1±0.2</td> </tr> </tbody> </table>	Height	H	2.0±0.2	2.5±0.2	3.1±0.2
Height											
H											
2.0±0.2											
2.5±0.2											
3.1±0.2											
		<p>Circuit Diagram</p>		<p>PWB land pattern for reference</p>							
Part Numbers	Operating Force	H=Height	Push Plate Color	Ground Terminal	Operating Life						
EVQQ2B01W	0.5 N	2.0 mm	White	Without	2000000 cycles						
EVQQ2B02W	0.5 N	2.5 mm	White	Without	2000000 cycles						
EVQQ2B03W	0.5 N	3.1 mm	White	Without	2000000 cycles						
EVQQ2D01W	0.5 N	2.0 mm	White	With	2000000 cycles						
EVQQ2D02W	0.5 N	2.5 mm	White	With	2000000 cycles						
EVQQ2D03W	0.5 N	3.1 mm	White	With	2000000 cycles						
EVQQ2F01W	1.0 N	2.0 mm	White	Without	1000000 cycles						
EVQQ2F02W	1.0 N	2.5 mm	White	Without	1000000 cycles						
EVQQ2F03W	1.0 N	3.1 mm	White	Without	1000000 cycles						
EVQQ2H01W	1.0 N	2.0 mm	White	With	1000000 cycles						
EVQQ2H02W	1.0 N	2.5 mm	White	With	1000000 cycles						
EVQQ2H03W	1.0 N	3.1 mm	White	With	1000000 cycles						
EVQQ2K01W	1.3 N	2.0 mm	White	Without	1000000 cycles						
EVQQ2K02W	1.3 N	2.5 mm	White	Without	1000000 cycles						
EVQQ2K03W	1.3 N	3.1 mm	White	Without	1000000 cycles						
EVQQ2M01W	1.3 N	2.0 mm	White	With	1000000 cycles						
EVQQ2M02W	1.3 N	2.5 mm	White	With	1000000 cycles						
EVQQ2M03W	1.3 N	3.1 mm	White	With	1000000 cycles						
EVQQ2P01W	1.6 N	2.0 mm	White	Without	1000000 cycles						
EVQQ2P02W	1.6 N	2.5 mm	White	Without	1000000 cycles						
EVQQ2P03W	1.6 N	3.1 mm	White	Without	1000000 cycles						
EVQQ2S01W	1.6 N	2.0 mm	White	With	1000000 cycles						
EVQQ2S02W	1.6 N	2.5 mm	White	With	1000000 cycles						
EVQQ2S03W	1.6 N	3.1 mm	White	With	1000000 cycles						
EVQQ2U01W	2.6 N	2.0 mm	White	Without	200000 cycles						
EVQQ2U02W	2.6 N	2.5 mm	White	Without	200000 cycles						
EVQQ2U03W	2.6 N	3.1 mm	White	Without	200000 cycles						
EVQQ2W01W	2.6 N	2.0 mm	White	With	200000 cycles						
EVQQ2W02W	2.6 N	2.5 mm	White	With	200000 cycles						
EVQQ2W03W	2.6 N	3.1 mm	White	With	200000 cycles						
EVQQ2Y01W	3.5 N	2.0 mm	White	Without	100000 cycles						
EVQQ2Y02W	3.5 N	2.5 mm	White	Without	100000 cycles						
EVQQ2Y03W	3.5 N	3.1 mm	White	Without	100000 cycles						
EVQQ2201W	3.5 N	2.0 mm	White	With	100000 cycles						
EVQQ2202W	3.5 N	2.5 mm	White	With	100000 cycles						
EVQQ2203W	3.5 N	3.1 mm	White	With	100000 cycles						

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### Recommended Reflow Soldering Conditions




### Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P1	P2	P0	D0 Dia	t1	t2
EVQQ2	2.0	6.7±0.2	7.4±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0.1</sub>	0.30±0.05	2.2±0.2
	2.5/3.1											3.2±0.2
EVQP0	2.5											2.8±0.2

### Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5


  

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	—	—

### Recommended Shape of Test Pole



### Recommended Operating Conditions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

**NEW**

## 3.0 mm×2.0 mm SMD Light Touch Switches

Type: **EVPAW**


### ■ Features

- External dimensions: 3.0 mm×2.0 mm, Height 0.6 mm
- High operability  
Equipped with an actuator (push plate)

### ■ Recommended Applications

- Operation switches for portable electronic equipment  
(Mobile phone, Portable audio)

### ■ Explanation of Part Numbers



### ■ Specifications

Type		Snap action/Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	500 m $\Omega$ max.
	Insulation Resistance	50 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.6 N, 2.4 N, 3.3 N
	Travel	1.6 N, 2.4 N : 0.13 mm    3.3 N : 0.15 mm
Endurance	Operating Life	300000 cycles min.
Operating Temperature		-40 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		10000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		50000 pcs.

Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012







■ Dimensions in mm (not to scale)

EVPAW

(Embossed Taping)

General dimension tolerance :  $\pm 0.05$   
( ) dimensions are reference dimensions.

This reference specifications are subject to change.





PWB land pattern for reference

Soldering thickness  $t=0.08\pm0.01$

\* If you design different stencil mask and land pattern, or apply different soldering thickness compared with our recommended pattern as described above, please ask us in advance.

Part Numbers	Operating Force	Height	Operating Life
EVPAWBA2A	1.6 N	0.6 mm	300000 cycles
EVPAWCA2A	2.4 N	0.6 mm	300000 cycles
EVPAWEA2A	3.3 N	0.6 mm	300000 cycles


■ Recommended Reflow Soldering Conditions



\*Reflow temperature may vary by location even in the same reflow condition. Please check the reflow temperature at terminals and at the top of a switch to make sure the both temperatures are within the specification. If even one of them is out of the specifications, please adjust.

● Embossed Carrier Taping

Tape width=12.0 mm




Taping condition : Lack of products in the middle of taping should be one MAX, but total quantity specified in the specifications should be secured.  
 Peeling off strength of top tape : It should be within 0.2N to 1.0N at 165 degree in peeling off angle.  
 Joint of carrier tape : One joint per one reel may exist.

Unit: mm

Part No.	Height	A	B	C	D	E	F	G	H	I	J	K	t
EVPAW	0.6	12.0±0.3	1.75±0.10	5.5±0.1	8.0±0.1	4.0±0.1	2.0±0.1	1.5±0.3	3.8±0.2	2.3±0.2	0.75±0.20	(10.25)	0.3 <sup>+0.15</sup> <sub>-0.10</sub>

● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5

Item	F	G
Rate (mm)	13.5±1.0	17.5±1.0

### 3.0 mm×2.6 mm SMD Light Touch Switches

Type: **EVPAF**




#### ■ Features

- External dimensions: 3.0 mm×2.6 mm, Height 0.65 mm
- High operability  
Equipped with an actuator (push plate)
- Low temperature use

#### ■ Recommended Applications

- Operation switches for portable electronic equipment  
(Mobile phone, Portable audio)

#### ■ Explanation of Part Numbers



#### ■ Specifications















Type		Snap action/Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	500 m $\Omega$ max.
	Insulation Resistance	50 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.3 N, 1.6 N, 2.4 N, 3.4 N
	Travel	0.15 mm
Endurance	Operating Life	1.3 N, 1.6 N, 3.4 N : 100000 cycles min., 2.4 N : 500000 cycles min.
Operating Temperature		-40 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		8000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		40000 pcs.

Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.


00 Oct. 2012

■ Dimensions in mm (not to scale)


<p>No. 1</p> <p><b>EVPAF</b> (Embossed Taping) With J-bent terminals</p> 	<div style="display: flex; justify-content: space-between;"> <div style="width: 45%;">  <p>(Without the remainder of the gate)</p>   </div> <div style="width: 45%;">    <p>PWB land pattern for reference</p> <p>Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.</p> </div> </div>		
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Operating Life</p>
<p>EVPAFKB65</p>	<p>1.3 N</p>	<p>0.65 mm</p>	<p>100000 cycles</p>
<p>EVPAFFB65</p>	<p>1.6 N</p>	<p>0.65 mm</p>	<p>100000 cycles</p>
<p>No. 2</p> <p><b>EVPAF</b> (Embossed Taping) With J-bent terminals</p> 	<div style="display: flex; justify-content: space-between;"> <div style="width: 45%;">  <p>(Without the remainder of the gate)</p>   </div> <div style="width: 45%;">    <p>PWB land pattern for reference</p> <p>Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.</p> </div> </div>		
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Operating Life</p>
<p>EVPAF5B70</p>	<p>3.4 N</p>	<p>0.7 mm</p>	<p>100000 cycles</p>
<p>EVPAF7B70</p>	<p>2.4 N</p>	<p>0.7 mm</p>	<p>500000 cycles</p>

<b>No. 3</b>  <b>EVPAF</b>  <b>Low profile</b> (Embossed Taping)  With J-bent terminals			<p>Circuit diagram</p>
	<p>(Without the remainder of the gate)</p>		
	<p>PWB land pattern for reference</p> <p>Part of A-A' terminal is exposed at  area. Any land pattern or vias shall not be provided at  area.</p>		
Part Numbers	Operating Force	Height	Operating Life
EVPOAFB65	1.6 N	0.65 mm	500000 cycles
EVPAF7B65	2.4 N	0.65 mm	500000 cycles
EVPAF5B65	3.4 N	0.65 mm	100000 cycles

### Recommended Reflow Soldering Conditions




### Embossed Carrier Taping



Part No.	Height	A	B	W	F	E	P1	P2	P0	D0 Dia	t1	t2
EVPAF EVPOAF	0.65/0.70	3.75±0.2	2.95±0.2	12.0±0.3	5.5±0.1	1.75±0.1	8.0±0.1	2.0±0.1	4.0±0.1	1.5±0.3	0.3±0.1	0.8±0.2

Unit: mm

### Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	-	-

### Recommended Shape of Test Pole



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 3.5 mm×2.9 mm SMD Light Touch Switches

Type: **EVPAA**




#### ■ Features

- External dimensions : 3.5 mm×2.9 mm, Height 1.7 mm
- High operating force available  
(Operating force : 5.0 N max.)
- Optional ground terminal

#### ■ Recommended Applications

- Operation switches for portable electronic equipment  
(Mobile phones, Digital still cameras, etc.)
- Operating switches for keyless entry systems

#### ■ Explanation of Part Numbers



#### ■ Specifications

Type		Snap action/Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	100 m $\Omega$ max.
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.0 N, 1.6 N, 2.4 N, 3.5 N, 5.0 N
	Travel	0.15 mm±0.1 mm
Endurance	Operating Life	1000000 cycles min. (1.0 N) 200000 cycles min. (1.6 N, 2.4 N, 3.5 N) 100000 cycles min. (5.0 N)
Operating Temperature		-40 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		5000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		25000 pcs.

Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

■ Dimensions in mm (not to scale)

**EVPAA**







(Embossed Taping)

Thickness : 1.7 mm

With J-bent terminals



(Tolerance  $\pm 0.2$ )




PWB land pattern for reference


Part Numbers	Ground Terminal	Operating Force	Push Plate Color	Operating Life
EVPAA002K	Without	1.0 N	Black	1000000 cycles
EVPAA102K	With	1.0 N	Black	1000000 cycles
EVPAA202K	Without	1.6 N	Black	200000 cycles
EVPAA302K	With	1.6 N	Black	200000 cycles
EVPAA402W	Without	2.4 N	White	200000 cycles
EVPAA502W	With	2.4 N	White	200000 cycles
EVPAA602W	Without	3.5 N	White	200000 cycles
EVPAA702W	With	3.5 N	White	200000 cycles
EVPAA802Q	Without	5.0 N	Grey	100000 cycles
EVPAA902Q	With	5.0 N	Grey	100000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## ■ Recommended Reflow Soldering Conditions




## ● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P1	P2	P0	D0 Dia	t1	t2
EVPAA	1.7	4.5±0.2	3.8±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.3±0.1	1.85±0.20

## ● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	$\phi 380.0 \pm 2.0$	$\phi 80.0 \pm 1.0$	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	2.0±0.5


  

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	—	—

## ■ Recommended Shape of Test Pole



## ■ Recommended Operating Conditions




Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

### 4.7 mm×3.5 mm SMD Light Touch Switches

Type: **EVQP2/EVQP9/EVQ3P2**




#### ■ Features

- External dimensions : 4.7 mm×3.5 mm,  
Height : Middle Push Travel 2.5 mm  
Short Push Travel 2.1 mm, 2.5 mm
- High operating force and long operational life
- High mountability with J-bent (4 terminals)

#### ■ Recommended Applications

- Operation switches for portable electronic equipment (Mobile phones, Digital still cameras, Camcorders, Portable audio players, etc.)
- Keyless entry systems (automotive)
- Car audio equipment

#### ■ Explanation of Part Numbers



#### ■ Specifications

Travel Type		Middle Push Travel	Short Push Travel
Type		Snap action / Push-on type SPST	
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	100 m $\Omega$ max.	
	Insulation Resistance	100 M $\Omega$ min.	
	Dielectric Withstanding Voltage	250 Vac (1 minute)	
	Bouncing	10 ms max. (ON, OFF)	
Mechanical	Operating Force	2.5 N, 3.5 N, 5.0 N	1.0 N, 1.6 N, 2.4 N, 3.5 N, 5.0 N
	Travel	0.70 mm $\pm$ 0.20 mm	0.25 mm <sup>+0.05</sup> <sub>-0.15</sub> mm
Endurance	Operating Life	2.5 N: 1000000 cycles min. 3.5 N: 500000 cycles min. 5.0 N: 200000 cycles min.	1.0 N, 1.6 N: 1000000 cycles min. 2.4 N: 500000 cycles min. 3.5 N: 200000 cycles min. 5.0 N: 200000 cycles min.
Operating Temperature		-40 °C to +85 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		4000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		20000 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

<p>No. 1</p> <p>EVQP2 EVQ3P2</p> <p>Middle push travel With J-bent terminals (With Ground terminal)</p>	
---	--

Part Numbers	Ground Terminal	Operating Force	Height	Push Plate Color	Operating Life
EVQP2B02B	With	2.5 N	2.5 mm	Blue	1000000 cycles
EVQP2D02Q	With	3.5 N	2.5 mm	Grey	500000 cycles
EVQP2F02K	With	5.0 N	2.5 mm	Black	200000 cycles
EVQP2H02B	Without	2.5 N	2.5 mm	Blue	1000000 cycles
EVQP2K02Q	Without	3.5 N	2.5 mm	Grey	500000 cycles
EVQ3P202K	Without	5.0 N	2.5 mm	Black	200000 cycles


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


Part Numbers	Ground Terminal	Operating Force	H=Height	Push Plate Color	Operating Life
EVQP2P02M	With	1.0 N	2.1 mm	Natural	1000000 cycles
EVQP2P02W	With	1.0 N	2.5 mm	Natural	1000000 cycles
EVQP2R02M	With	1.6 N	2.1 mm	Natural	1000000 cycles
EVQP2R02W	With	1.6 N	2.5 mm	Natural	1000000 cycles
EVQP2T02M	With	2.4 N	2.1 mm	Natural	500000 cycles
EVQP2T02W	With	2.4 N	2.5 mm	Natural	500000 cycles
EVQP2V02M	With	3.5 N	2.1 mm	Natural	200000 cycles
EVQP2V02W	With	3.5 N	2.5 mm	Natural	200000 cycles
EVQP2002M	Without	1.0 N	2.1 mm	Natural	1000000 cycles
EVQP2002W	Without	1.0 N	2.5 mm	Natural	1000000 cycles
EVQP2202M	Without	1.6 N	2.1 mm	Natural	1000000 cycles
EVQP2202W	Without	1.6 N	2.5 mm	Natural	1000000 cycles
EVQP2402M	Without	2.4 N	2.1 mm	Natural	500000 cycles
EVQP2402W	Without	2.4 N	2.5 mm	Natural	500000 cycles
EVQP2602M	Without	3.5 N	2.1 mm	Natural	200000 cycles
EVQP2602W	Without	3.5 N	2.5 mm	Natural	200000 cycles
EVQP9H02M	With	5.0 N	2.1 mm	Natural	200000 cycles
EVQP9H02W	With	5.0 N	2.5 mm	Natural	200000 cycles
EVQP9P02M	Without	5.0 N	2.1 mm	Natural	200000 cycles
EVQP9P02W	Without	5.0 N	2.5 mm	Natural	200000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately. 00 Oct. 2012

### Recommended Reflow Soldering Conditions




### Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQP2	2.1	6.0±0.2	4.7±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>0</sub>	0.3±0.1	2.7±0.2
EVQP9	2.5											
EVQ3P2												

### Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ370.0±2.0	φ50.0 min.	φ13.0±0.5	φ21.0±1.0	2.0±0.5


  

Item	W	T	t	r
Rate (mm)	14.0±1.5	—	1.0 to 3.0	1.0±0.5

### Recommended Shape of Test Pole



### Recommended Operating Conditions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 6.0 mm×3.5 mm SMD Light Touch Switches

Type: **EVQPE1/EVQPN/EVQ5P**




#### ■ Features

- External dimensions : 6.0 mm×3.5 mm, Height 4.3 mm, 5.0 mm

#### ■ Recommended Applications

- Operating switches for other electronic equipment


#### ■ Explanation of Part Numbers



#### ■ Product Chart

Operating Force	Type	SMD	Height
1.0 N±0.5 N		EVQPE1	H=4.3 mm H=5.0 mm
1.6 N±0.5 N		EVQPNF	
2.4 N±0.6 N		EVQ5PN	

#### ■ Specifications


Type	Snap action/Push-on type SPST	
Electrical	Circuit Diagram	
	Rating	10 μA 2 Vdc to 50 mA 12 Vdc (Resistive load)
	Contact Resistance	100 mΩ max.
	Insulation Resistance	100 MΩ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.0 N±0.5N (Low force type) 1.6 N±0.5 N (Standard) 2.4 N±0.6 N
	Travel	0.25 mm <sup>+0.20</sup> / <sub>-0.10</sub> mm
Endurance	Operating Life	50000 cycles min.      30000 cycles min.
Operating Temperature		-30 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		2000 pcs. Embossed Taping(Reel Pack) (H = 5.0 mm)      2500 pcs. Embossed Taping(Reel Pack) (H = 4.3 mm)
Quantity/Carton		10000 pcs. (H = 5.0 mm)      12500 pcs. (H = 4.3 mm)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.


### ■ Dimensions in mm (not to scale)

EVQPE1 EVQPNF EVQ5PN (Embossed Taping)				
	Part Numbers	Operating Force	H=Height	Push Plate Color
EVQPE104K	1.0 N	4.3 mm	Black	50000 cycles
EVQPE105K	1.0 N	5.0 mm	Black	50000 cycles
EVQPNF04M	1.6 N	4.3 mm	Natural	50000 cycles
EVQPNF05M	1.6 N	5.0 mm	Natural	50000 cycles
EVQ5PN04K	2.4 N	4.3 mm	Black	30000 cycles
EVQ5PN05K	2.4 N	5.0 mm	Black	30000 cycles

### ■ Recommended Reflow Soldering Conditions




### ● Embossed Carrier Taping



Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQPE1 EVQPN EVQ5P	4.3/5.0	5.8±0.2	7.9±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>0</sub>	0.4±0.05	4.5/5.2±0.2

Unit: mm

### ● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ370.0±2.0	φ50.0 min.	φ13.0±0.5	φ21.0±1.0	2.0±0.5

Item	W	T	t	r
Rate (mm)	14.0±1.5	—	1.0 to 3.0	1.0±0.5

### 3.5 mm×2.9 mm Side-operational SMD Light Touch Switches

Type: **EVQP7/EVQP3/EVQ9P7**




#### ■ Features

- External dimensions : 3.5 mm×2.9 mm, Height 1.35 mm
- A wide range of terminal type : L-shape, J-bent, Straight
- High mount ability
- Push plate strength enhanced type

#### ■ Recommended Applications

- Operation switches for portable electronic equipment (Mobile phones, Digital still cameras, Camcorders, Portable audio players, etc.)

#### ■ Explanation of Part Numbers





#### ■ Specifications

Type		Snap action / Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 50 mA 12 Vdc (Resistive load)
	Contact Resistance	500 m $\Omega$ max.
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac (1 minute)
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.6 N, 2.2 N
	Push Travel	0.2 mm
	Push Strength	30 N (1 minute)
Endurance	Operating Life	100000 cycles min.
Operating Temperature		-20 °C to +70 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		5000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		25000 pcs.



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

<p>No. 1</p> <p>EVQP7A EVQP7J</p> <p>(Embossed Taping)</p> <p>With straight terminals Without boss</p> 				
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQP7A01K</p>	<p>2.2 N</p>	<p>1.35 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQP7J01K</p>	<p>1.6 N</p>	<p>1.35 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>No. 2</p> <p>EVQP7C EVQP7L</p> <p>(Embossed Taping)</p> <p>With straight terminals With boss</p> 				
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQP7C01K</p>	<p>2.2 N</p>	<p>1.35 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQP7L01K</p>	<p>1.6 N</p>	<p>1.35 mm</p>	<p>Black</p>	<p>100000 cycles</p>







Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)


<p>No. 3</p> <p>EVQP7B EVQP7K</p> <p>(Embossed Taping)</p> <p>With J-bent terminals Without boss</p> 				
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQP7B01K</p>	<p>2.2 N</p>	<p>1.35 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQP7K01K</p>	<p>1.6 N</p>	<p>1.35 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>No. 4</p> <p>EVQP7D EVQP7M</p> <p>(Embossed Taping)</p> <p>With J-bent terminals With boss</p> 				
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQP7D01K</p>	<p>2.2 N</p>	<p>1.35 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQP7M01K</p>	<p>1.6 N</p>	<p>1.35 mm</p>	<p>Black</p>	<p>100000 cycles</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)


<p>No. 5</p> <p>EVQP3 EVQ9P</p> <p>(Embossed Taping)</p> <p>With L-shape terminals Without boss</p> 	  	  <p>Circuit diagram</p>  <p>PWB land pattern for reference</p>		
Part Numbers	Operating Force	Height	Push Plate Color	Operating Life
EVQP3401K	2.2 N	1.35 mm	Black	100000 cycles
EVQ9P701K	1.6 N	1.35 mm	Black	100000 cycles

### ■ Recommended Reflow Soldering Conditions



### ● Embossed Carrier Taping

Tape width=12.0 mm



### ● Straight terminals, L-shape terminals type

Unit: mm


Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQP7, EVQP3 EVQ9P7	1.35	5.2±0.2	4.5±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.3±0.1	1.5±0.2

### ● J-bent type

Unit: mm

Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQP7, EVQP3	1.35	4.5±0.2	4.5±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.3±0.1	1.5±0.2

### ● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5
Item	W	T	t	r	
Rate (mm)	13.5±1.0	17.5±1.0	1.0 to 3.0	1.0±0.5	

### 3.5 mm×2.9 mm Side-operational Half Dive /SMD Light Touch Switches

Type: **EVPAN**




#### ■ Features

- External dimensions : 3.5 mm×2.9 mm, Height 1.2 mm
- Printed circuit board on height : 0.7 mm
- High mount ability

#### ■ Recommended Applications

- Operation switches for portable electronic equipment (Mobile phones, Digital still cameras, Camcorders, Portable audio players, etc.)

#### ■ Explanation of Part Numbers





#### ■ Specifications

Type		Snap action / Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 50 mA 12 Vdc (Resistive load)
	Contact Resistance	500 m $\Omega$ max.
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac (1 minute)
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.6 N, 2.2 N
	Push Travel	0.2 mm
	Push Strength	70 N (1 minute)
Endurance	Operating Life	100000 cycles min.
Operating Temperature		-20 °C to +70 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		7000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		35000 pcs.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


<p>EVPANA EVPAND</p> <p>(Embossed Taping)</p> <p>Straight terminals</p> 	 <p>PWB land pattern for reference</p>			
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVPANAA1A</p>	<p>1.6 N</p>	<p>0.7 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVPANDA1A</p>	<p>2.2 N</p>	<p>0.7 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVPANBA1A</p>	<p>1.6 N</p>	<p>0.7 mm</p>	<p>Black</p>	<p>500000 cycles</p>
<p>EVPAND EVPANB</p> <p>(Embossed Taping)</p> <p>Straight terminals</p> 	 <p>PWB land pattern for reference</p>			
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVPANDE1A</p>	<p>2.2 N</p>	<p>0.7 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVPANBE1A</p>	<p>1.6 N</p>	<p>0.7 mm</p>	<p>Black</p>	<p>500000 cycles</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.


## Recommended Solder Mask



## Recommended Reflow Soldering Conditions



## Embossed Carrier Taping




## Straight terminals

Unit: mm

Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVPAN	1.2	5.6±0.2	4.5±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.3±0.1	1.35±0.20

## Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	1.0~3.0	1.0±0.5

## Small-sized Side-operational SMD Light Touch Switches

Type: **EVQPU**




### ■ Features

- External dimensions : 4.7 mm×3.5 mm, Height 1.65 mm
- A wide range of terminal type : J-bent, Straight

### ■ Recommended Applications

- Operation switches for portable electronic equipment  
(Mobile phones, Digital still cameras, Camcorders, Portable audio players, etc.)

### ■ Explanation of Part Numbers





### ■ Specifications

Type		Snap action / Push-on type SPST	
Electrical	Rating	10 $\mu$ A 2 Vdc to 50 mA 12 Vdc (Resistive load)	
	Contact Resistance	500 m $\Omega$ max.	
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	10 ms max. (ON, OFF)	
Mechanical	Operating Force	1.6 N <sup>+0.7</sup> <sub>-0.4</sub> N	2.2 N <sup>+0.8</sup> <sub>-0.7</sub> N
	Travel	0.3 mm <sup>+0.1</sup> <sub>-0.2</sub> mm	
	Push Strength	30 N (1 minute)	
Endurance	Operating Life	100000 cycles min.	
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		4000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		20000 pcs.	



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

<p>No. 1</p> <p><b>EVQPUJ</b> <b>EVQPUA</b></p> <p>(Embossed Taping)</p> <p>With straight terminals Without boss</p> 				
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQPUJ02K</p>	<p>1.6 N</p>	<p>1.65 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQPUA02K</p>	<p>2.2 N</p>	<p>1.65 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>No. 2</p> <p><b>EVQPUL</b> <b>EVQPUC</b></p> <p>(Embossed Taping)</p> <p>With straight terminals With boss</p> 				
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQPUL02K</p>	<p>1.6 N</p>	<p>1.65 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQPUC02K</p>	<p>2.2 N</p>	<p>1.65 mm</p>	<p>Black</p>	<p>100000 cycles</p>


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


<p>No. 3</p> <p><b>EVQPUK EVQPUB</b></p> <p>(Embossed Taping)</p> <p>With J-bent terminals Without boss</p> 				
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQPUK02K</p>	<p>1.6 N</p>	<p>1.65 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQPUB02K</p>	<p>2.2 N</p>	<p>1.65 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>No. 4</p> <p><b>EVQPUM EVQPUD</b></p> <p>(Embossed Taping)</p> <p>With J-bent terminals With boss</p> 				
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQPUM02K</p>	<p>1.6 N</p>	<p>1.65 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQPUD02K</p>	<p>2.2 N</p>	<p>1.65 mm</p>	<p>Black</p>	<p>100000 cycles</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Recommended Reflow Soldering Conditions




### ● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	$P_1$	$P_2$	$P_0$	$D_0$ Dia.	$t_1$	$t_2$
EVQPU	1.65	$7.0 \pm 0.2$	$5.75 \pm 0.20$	$12.0 \pm 0.3$	$5.78 \pm 0.20$	$1.75 \pm 0.10$	$8.0 \pm 0.1$	$2.0 \pm 0.1$	$4.0 \pm 0.1$	$1.5_{-0}^{+0.1}$	$0.35 \pm 0.05$	$2.4 \pm 0.2$

### ● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	$\phi 370.0 \pm 2.0$	$\phi 50.0$ min.	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	$2.0 \pm 0.5$

Item	W	T	t	r
Rate (mm)	$14.0 \pm 1.5$	—	1.0 to 3.0	$1.0 \pm 0.5$

## 2.8 mm×2.3 mm Side-operational Edge Mount Light Touch Switches

Type: **EVPAV**




### ■ Features

- External dimensions : 2.8 mm×2.3 mm (Excluding the push plate), Height 1.95 mm (Printed circuit board being as low as 0.975 mm)
- Improved soldering strength in the operating direction

### ■ Recommended Applications

- Operation switches for portable electronic equipment (Mobile phones, Digital still cameras, Camcorders, Portable audio players, etc.)

### ■ Explanation of Part Numbers



### ■ Specifications

Type		Snap action / Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	500 m $\Omega$ max.
	Insulation Resistance	50 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac (1 minute)
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.6 N
	Push Travel	0.13 mm
	Push Strength	50 N (15 seconds)
Endurance	Operating Life	300000 cycles min.
Operating Temperature		-40 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk)
		-20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		8000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		40000 pcs.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)


**EVPAV**



General dimension tolerance :  $\pm 0.1$   
 ( ) dimensions are reference dimensions.  
 This reference specifications are subject to change.





Adhesive      Push plate




Circuit Diagram


This product is designed to be smaller than the conventional type, which lowered the film peel off strength. Therefore please avoid to apply force to a push plate from side, or/and avoid set-knob to touch push plate during insertion to a set-case.





\*1 These dimensions are from the outer shape to the center of push plate.  
 \*2 These dimensions are from the center of datum A.






PWB land pattern for reference


Soldering thickness  $t=0.1\pm 0.02$

\* Height from surface of PCB : 0.975 mm

### ■ Recommended Reflow Soldering Conditions



### ● Embossed Carrier Taping



Taping condition : Lack of products in the middle of taping should be one MAX, but total quantity specified in the specifications should be secured.


Peeling off strength of top tape : It should be within 0.2N to 1.0N at 165 degree in peeling off angle.

Joint of carrier tape : One joint per one reel may exist.

Unit: mm

Part No.	Height	A	B	C	D	E	F	G	H	I	J	K	L	t
EVPAV	1.95	8.0±0.3	1.75±0.10	3.5±0.1	4.0±0.1	4.0±0.1	2.0±0.1	1.5 <sup>+0.1</sup> <sub>0</sub>	3.1±0.2	2.8±0.2	1.35±0.20	2.7±0.2	(6.25)	0.3±0.1

### ● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5
Item	F	G			
Rate (mm)	9.4±1.0	13.4±1.0			

### 4.5 mm×2.2 mm Side-operational Edge Mount

### Light Touch Switches

Type: **EVPAE**




#### ■ Features

- External dimensions : 4.5 mm×2.25 mm (Excluding the push plate), Height 2.9 mm (Printed circuit board being as low as 0.95 mm)
- Improved soldering strength in the operating direction
- Long operational life
- Measure against electro static discharge(ESD)

#### ■ Recommended Applications

- Operation switches for portable electronic equipment (Mobile phones, Digital still cameras, Camcorders, Portable audio players, etc.)

#### ■ Explanation of Part Numbers



#### ■ Specifications

Type		Snap action / Push-on type SPST
Electrical	Rating	10 μA 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	1000 mΩ max.
	Insulation Resistance	100 MΩ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac (1 minute)
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.6 N, 3.0 N
	Push Travel	0.15 mm
	Push Strength	50 N (1 minute)
Endurance	Operating Life	200000 cycles min.
Operating Temperature		-40 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk)
		-20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		3500 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		17500 pcs.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.



### 6.2 mm×2.5 mm Side-operational Edge Mount

### Light Touch Switches

Type: **EVQP4**




#### ■ Features

- External dimensions : 6.2 mm×2.55 mm (Excluding the push plate), Height 3.5 mm (EVQP4 Type : Printed circuit board being as low as 1.35 mm)
- Side-operational middle stroke type ( 0.7 mm ) with a high operating force (5.0 N)
- Improved soldering strength in the operating direction when mounted on PC board edge

#### ■ Recommended Applications

- Operation switches for portable electronic equipment (Mobile phones, Digital still cameras, Camcorders, Portable audio players, etc.)
- Keyless entry (car electronics)
- Car audio equipment

#### ■ Explanation of Part Numbers





#### ■ Specifications

Travel Type		Middle Push Travel	Short Push Travel
Type		Snap action / Push-on type SPST	
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	100 m $\Omega$ max.	
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac (1 minute)	
	Bouncing	10 ms max. (ON, OFF)	
Mechanical	Operating Force	2.5 N, 3.5 N, 5.0 N	1.0 N, 1.6 N, 2.4 N, 3.5 N
	Travel	0.70 mm $\pm$ 0.2 mm	0.25 mm $^{+0.05}_{-0.15}$ mm
	Push Strength	50 N (1 minute)	
Endurance	Operating Life	2.5 N: 1000000 cycles min.	1.0 N, 1.6 N: 1000000 cycles min.
		3.5 N: 500000 cycles min.	2.4 N: 500000 cycles min.
		5.0 N: 200000 cycles min.	3.5 N: 200000 cycles min.
Operating Temperature		-40 $^{\circ}$ C to +85 $^{\circ}$ C	
Storage Temperature		-40 $^{\circ}$ C to +85 $^{\circ}$ C (Bulk) -20 $^{\circ}$ C to +60 $^{\circ}$ C (Taping)	
Minimum Quantity/Packing Unit		2500 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		12500 pcs.	


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


<p>No. 1</p> <p>EVQP4</p> <p>Middle push travel</p> 	 <p>* Height from surface of PCB : 1.35 mm</p>			
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQP4HB3B</p>	<p>2.5 N</p>	<p>3.5 mm</p>	<p>Blue</p>	<p>1000000 cycles</p>
<p>EVQP4KB3Q</p>	<p>3.5 N</p>	<p>3.5 mm</p>	<p>Grey</p>	<p>500000 cycles</p>
<p>EVQP4MB3K</p>	<p>5.0 N</p>	<p>3.5 mm</p>	<p>Black</p>	<p>200000 cycles</p>
<p>No. 2</p> <p>EVQP4</p> <p>Short push travel</p> 	 <p>* Height from surface of PCB : 1.35 mm</p>			
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQP40B3M</p>	<p>1.0 N</p>	<p>3.5 mm</p>	<p>Natural</p>	<p>1000000 cycles</p>
<p>EVQP42B3M</p>	<p>1.6 N</p>	<p>3.5 mm</p>	<p>Natural</p>	<p>1000000 cycles</p>
<p>EVQP44B3M</p>	<p>2.4 N</p>	<p>3.5 mm</p>	<p>Natural</p>	<p>500000 cycles</p>
<p>EVQP46B3M</p>	<p>3.5 N</p>	<p>3.5 mm</p>	<p>Natural</p>	<p>200000 cycles</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Recommended Reflow Soldering Conditions




### ● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	$P_1$	$P_2$	$P_0$	$D_0$ Dia.	$t_1$	$t_2$
EVQP4	3.5	6.5±0.2	3.9±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.4±0.1	3.75±0.20

### ● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	$\phi 370.0 \pm 2.0$	$\phi 50.0$ min.	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	2.0±0.5

Item	W	T	t	r
Rate (mm)	14.0±1.5	—	1.0 to 3.0	1.0±0.5

### 6.1 mm×4.0 mm Side-operational SMD Light Touch Switches

Type: **EVQPS**




#### ■ Features

- External dimensions : 6.1 mm×4.0 mm, Height 1.8 mm
- Terminal shapes : straight, J-bent

#### ■ Recommended Applications

- Operating switches for other electronic equipment

#### ■ Explanation of Part Numbers





#### ■ Specifications

Type		Snap action / Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 50 mA 12 Vdc (Resistiv load)
	Contact Resistance	500 m $\Omega$ max.
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	1.6 N <sup>+0.7</sup> <sub>-0.4</sub> N      2.2 N <sup>+0.8</sup> <sub>-0.7</sub> N
	Travel	0.3 mm <sup>+0.1</sup> <sub>-0.2</sub> mm
	Push Strength	30 N for 1 minute
Endurance	Operating Life	100000 cycles min.
Operating Temperature		-20 °C to +70 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		4000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		16000 pcs.



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

<p>No. 1</p> <p>EVQPSD EVQPSH</p> <p>J-bent terminals, with Boss</p> 	 <p>PWB land pattern for reference (Tolerance:±0.1)</p> <p>Circuit Diagram</p>			
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQPSD02K</p>	<p>1.6 N</p>	<p>1.8 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQPSH02K</p>	<p>2.2 N</p>	<p>1.8 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>No. 2</p> <p>EVQPSM EVQPSR</p> <p>Straight terminals, with Boss</p> 	 <p>PWB land pattern for reference (Tolerance:±0.1)</p> <p>Circuit Diagram</p>			
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQPSM02K</p>	<p>1.6 N</p>	<p>1.8 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQPSR02K</p>	<p>2.2 N</p>	<p>1.8 mm</p>	<p>Black</p>	<p>100000 cycles</p>


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


<p>No. 3</p> <p>EVQPSC EVQPSG</p> <p>J-bent terminals, without Boss</p> 	 <p>PWB land pattern for reference (Tolerance:±0.1)</p> <p>Circuit Diagram</p>			
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQPSC02K</p>	<p>1.6 N</p>	<p>1.8 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQPSG02K</p>	<p>2.2 N</p>	<p>1.8 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>No. 4</p> <p>EVQPSL EVQPSQ</p> <p>Straight terminals, without Boss</p> 	 <p>PWB land pattern for reference (Tolerance:±0.1)</p> <p>Circuit Diagram</p>			
<p>Part Numbers</p>	<p>Operating Force</p>	<p>Height</p>	<p>Push Plate Color</p>	<p>Operating Life</p>
<p>EVQPSL02K</p>	<p>1.6 N</p>	<p>1.8 mm</p>	<p>Black</p>	<p>100000 cycles</p>
<p>EVQPSQ02K</p>	<p>2.2 N</p>	<p>1.8 mm</p>	<p>Black</p>	<p>100000 cycles</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### Recommended Reflow Soldering Conditions




### Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	$P_1$	$P_2$	$P_0$	$D_0$ Dia.	$t_1$	$t_2$
EVQPS	1.8	$6.8 \pm 0.2$	$8.0 \pm 0.2$	$16.0 \pm 0.3$	$7.5 \pm 0.1$	$1.75 \pm 0.10$	$8.0 \pm 0.1$	$2.0 \pm 0.1$	$4.0 \pm 0.1$	$1.5^{+0.1}_{-0}$	$0.30 \pm 0.05$	$2.7 \pm 0.2$

### Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	$\phi 370.0 \pm 2.0$	$\phi 50.0$ min.	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	$2.0 \pm 0.5$

Item	W	T	t	r
Rate (mm)	$18.0 \pm 1.5$	—	1.0 to 3.0	$1.0 \pm 0.5$

### 5N Type Light Touch Switches

Type: **EVQPA/EVQPB**




#### ■ Features

- Wealth of product types: With or without a ground terminal, vertical type, snap-in terminals, etc.
- Can be automatically dip-soldered: Integral molding of the terminals and main body prevents the escape of flux.

#### ■ Recommended Applications

- Operating switches for other electronic equipment

#### ■ Explanation of Part Numbers



#### ■ Product Chart

○=In production

Operating Force	Positioning Pin	Ground Terminal	Height			
			4.3 mm	5.0 mm	7.0 mm	9.5 mm
1.0 N	Without positioning pin	With ground terminal	○	○	○	○
		Without ground terminal	○	○	○	○
1.3 N	Without positioning pin	With ground terminal	○	○	○	○
		Without ground terminal	○	○	○	○
1.6 N	Without positioning pin	With ground terminal	○	○	○	○
		Without ground terminal	○	○	○	○
2.6 N	Without positioning pin	With ground terminal	○	○	○	○
		Without ground terminal	○	○	○	○

#### ■ Specifications

Type		Snap action/Push-on type SPST	
Electrical	Circuit Diagram		
	Rating	10 μA 2 Vdc to 20 mA 15 Vdc (Resistiv load)	
	Contact Resistance	50 mΩ max.	
	Insulation Resistance	50 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
Bouncing	3 ms max. (ON) 8 ms max. (OFF)		
Mechanical	Operating Force	1.0 N±0.4 N 1.3 N±0.4 N 1.6 N±0.5 N	2.6 N±0.6 N
	Travel	0.25 mm±0.10 mm	
Endurance	Operating Life	100000 cycles min.*	50000 cycles min.
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk)	
Minimum Quantity/ Packing Unit	Top-push	500 pcs. Polyethylene Bag (Bulk)	
Quantity/Cartron	Top-push	10000 pcs.	

\*1 million cycles also available, consult our salesmen.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

<p>No. 1</p> <p>EVQPA</p> <p>Without ground terminal</p>				
Part Numbers	Operating Force	H=Height	Push Plate Color	Operating Life
EVQPAC04M	1.0 N	4.3 mm	White	100000 cycles
EVQPAC05R	1.0 N	5.0 mm	Red	100000 cycles
EVQPAC07K	1.0 N	7.0 mm	Black	100000 cycles
EVQPAC09K	1.0 N	9.5 mm	Black	100000 cycles
EVQPAD04M	1.3 N	4.3 mm	White	100000 cycles
EVQPAD05R	1.3 N	5.0 mm	Red	100000 cycles
EVQPAD07K	1.3 N	7.0 mm	Black	100000 cycles
EVQPAD09K	1.3 N	9.5 mm	Black	100000 cycles
EVQPAE04M	1.6 N	4.3 mm	White	100000 cycles
EVQPAE05R	1.6 N	5.0 mm	Red	100000 cycles
EVQPAE07K	1.6 N	7.0 mm	Black	100000 cycles
EVQPAE09K	1.6 N	9.5 mm	Black	100000 cycles
EVQPAG04M	2.6 N	4.3 mm	White	50000 cycles
EVQPAG05R	2.6 N	5.0 mm	Red	50000 cycles
EVQPAG07K	2.6 N	7.0 mm	Black	50000 cycles
EVQPAG09K	2.6 N	9.5 mm	Black	50000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

<p>No. 2</p> <p><b>EVQPB</b></p> <p>With ground terminal</p>				
				
Part Numbers	Operating Force	H=Height	Push Plate Color	Operating Life
EVQPBC04M	1.0 N	4.3 mm	White	100000 cycles
EVQPBC05R	1.0 N	5.0 mm	Red	100000 cycles
EVQPBC07K	1.0 N	7.0 mm	Black	100000 cycles
EVQPBC09K	1.0 N	9.5 mm	Black	100000 cycles
EVQPBD04M	1.3 N	4.3 mm	White	100000 cycles
EVQPBD05R	1.3 N	5.0 mm	Red	100000 cycles
EVQPBD07K	1.3 N	7.0 mm	Black	100000 cycles
EVQPBD09K	1.3 N	9.5 mm	Black	100000 cycles
EVQPBE04M	1.6 N	4.3 mm	White	100000 cycles
EVQPBE05R	1.6 N	5.0 mm	Red	100000 cycles
EVQPBE07K	1.6 N	7.0 mm	Black	100000 cycles
EVQPBE09K	1.6 N	9.5 mm	Black	100000 cycles
EVQPBG04M	2.6 N	4.3 mm	White	50000 cycles
EVQPBG05R	2.6 N	5.0 mm	Red	50000 cycles
EVQPBG07K	2.6 N	7.0 mm	Black	50000 cycles
EVQPBG09K	2.6 N	9.5 mm	Black	50000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 5N Type Side-operational Light Touch Switches

Type: **EVQPF**




### ■ Features

- Wealth of product types: Horizontal type, snap-in terminals, etc.
- Can be automatically dip-soldered: Integral molding of the terminals and main body prevents the escape of flux.

### ■ Recommended Applications

- Operating switches for other electronic equipment

### ■ Explanation of Part Numbers



### ■ Specifications

Type		Snap action/Push-on type SPST	
Electrical	Circuit Diagram		
	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistiv load)	
	Contact Resistance	50 m $\Omega$ max.	
	Insulation Resistance	50 M $\Omega$ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
Mechanical	Bouncing	3 ms max. (ON) 8 ms max. (OFF)	
	Operating Force	1.0 N $\pm$ 0.4 N 1.3 N $\pm$ 0.4 N 1.6 N $\pm$ 0.5 N	2.6 N $\pm$ 0.6 N
	Travel	0.25 mm $\pm$ 0.10 mm	
Endurance	Operating Life	100000 cycles min.*	50000 cycles min.
Operating Temperature		-20 $^{\circ}$ C to +70 $^{\circ}$ C	
Storage Temperature		-40 $^{\circ}$ C to +85 $^{\circ}$ C (Bulk)	
Minimum Quantity/ Packing Unit	Top-push	500 pcs. Polyethylene Bag (Bulk)	
Quantity/Cartron	Top-push	10000 pcs.	

\*1 million cycles also available, consult our salesmen.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

EVQPF				
Part Numbers	Operating Force	$\ell$ = Push Plate Place	Push Plate Color	Operating Life
EVQPF003M	1.0 N	3.15 mm	White	100000 cycles
EVQPF004R	1.0 N	3.85 mm	Red	100000 cycles
EVQPF006K	1.0 N	5.85 mm	Black	100000 cycles
EVQPF008K	1.0 N	8.35 mm	Black	100000 cycles
EVQPF103M	1.3 N	3.15 mm	White	100000 cycles
EVQPF104R	1.3 N	3.85 mm	Red	100000 cycles
EVQPF106K	1.3 N	5.85 mm	Black	100000 cycles
EVQPF108K	1.3 N	8.35 mm	Black	100000 cycles
EVQPF203M	1.6 N	3.15 mm	White	100000 cycles
EVQPF204R	1.6 N	3.85 mm	Red	100000 cycles
EVQPF206K	1.6 N	5.85 mm	Black	100000 cycles
EVQPF208K	1.6 N	8.35 mm	Black	100000 cycles
EVQPF303M	2.6 N	3.15 mm	White	50000 cycles
EVQPF304R	2.6 N	3.85 mm	Red	50000 cycles
EVQPF306K	2.6 N	5.85 mm	Black	50000 cycles
EVQPF308K	2.6 N	8.35 mm	Black	50000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 5N Type 2R Light Touch Switches

Type: **EVQ2**



### ■ Features

- Wealth of product types: With or without a ground terminal, vertical type, snap-in terminals, etc.
- Can be automatically dip-soldered: Integral molding of the terminals and main body prevents the escape of flux.

### ■ Recommended Applications

- Operating switches for electronic equipment

### ■ Explanation of Part Numbers



### ■ Product Chart

○=Standard

Operating Force	Positioning Pin	Ground Terminal	Height			
			4.3 mm	5.0 mm	7.0 mm	9.5 mm
1.0 N	Without positioning pin	With ground terminal	○	○	○	○
		Without ground terminal	○	○	○	○
1.3 N	Without positioning pin	With ground terminal	○	○	○	○
		Without ground terminal	○	○	○	○
1.6 N	Without positioning pin	With ground terminal	○	○	○	○
		Without ground terminal	○	○	○	○
2.6 N	Without positioning pin	With ground terminal	○	○	○	○
		Without ground terminal	○	○	○	○

### ■ Specifications

Type		Snap action/Push-on type SPST	
Electrical	Circuit Diagram		
	Rating	10 μA 2 Vdc to 20 mA 15 Vdc (Resistiv load)	
	Contact Resistance	50 mΩ max.	
	Insulation Resistance	50 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 8 ms max. (OFF)	
Mechanical	Operating Force	1.0 N±0.4 N 1.3 N±0.4 N 1.6 N±0.5 N	2.6 N±0.6 N
	Travel	0.25 mm±0.10 mm	
Endurance	Operating Life	100000 cycles min.*	50000 cycles min.
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)	
Minimum Quantity/ Packing Unit	Top-push	1000 pcs. Radial Taping (Reel Pack)	
Quantity/Carton	Top-push	10000 pcs.	

\*1 million cycles also available, consult our salesmen.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.


■ Dimensions in mm (not to scale)

**EVQ2**


With ground terminal

2-terminals type

Without ground terminal



The direction of (P) or (Q) side is randomly settled.



E-E' Section

Adhesive tape shall not extend beyond base paper.

Adhesive tape

JIS C0806-2 shall be applied to the items not specified here.

PWB mounting hole for reference  
(Pitch tolerance: ±0.1)  
View from mounting side

Part Numbers	Operating Force	H=Height	Push Plate Color	Operating Life
EVQ21304M	1.0 N	4.3 mm	White	100000 cycles
EVQ21305R	1.0 N	5.0 mm	Red	100000 cycles
EVQ21307K	1.0 N	7.0 mm	Black	100000 cycles
EVQ21309K	1.0 N	9.5 mm	Black	100000 cycles
EVQ21404M	1.3 N	4.3 mm	White	100000 cycles
EVQ21405R	1.3 N	5.0 mm	Red	100000 cycles
EVQ21407K	1.3 N	7.0 mm	Black	100000 cycles
EVQ21409K	1.3 N	9.5 mm	Black	100000 cycles
EVQ21504M	1.6 N	4.3 mm	White	100000 cycles
EVQ21505R	1.6 N	5.0 mm	Red	100000 cycles
EVQ21507K	1.6 N	7.0 mm	Black	100000 cycles
EVQ21509K	1.6 N	9.5 mm	Black	100000 cycles
EVQ22704M	2.6 N	4.3 mm	White	50000 cycles
EVQ22705R	2.6 N	5.0 mm	Red	50000 cycles
EVQ22707K	2.6 N	7.0 mm	Black	50000 cycles
EVQ22709K	2.6 N	9.5 mm	Black	50000 cycles


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 5N Type Side-operational 4R Light Touch Switches

Type: **EVQPC**

#### ■ Features


- Wealth of product types: Horizontal type, snap-in terminals, etc.
- Can be automatically dip-soldered: Integral molding of the terminals and main body prevents the escape of flux.



#### ■ Recommended Applications

- Operating switches for electronic equipment

#### ■ Explanation of Part Numbers




#### ■ Specifications

Type		Snap action/Push-on type SPST	
Electrical	Circuit Diagram		
	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistiv load)	
	Contact Resistance	50 m $\Omega$ max.	
	Insulation Resistance	50 M $\Omega$ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
Mechanical	Bouncing	3 ms max. (ON) 8 ms max. (OFF)	
	Operating Force	1.0 N $\pm$ 0.4 N 1.3 N $\pm$ 0.4 N 1.6 N $\pm$ 0.5 N	2.6 N $\pm$ 0.6 N
	Travel	0.25 mm $\pm$ 0.10 mm	
Endurance	Operating Life	100000 cycles min.*	50000 cycles min.
Operating Temperature		-20 $^{\circ}$ C to +70 $^{\circ}$ C	
Storage Temperature		-40 $^{\circ}$ C to +85 $^{\circ}$ C (Bulk) -20 $^{\circ}$ C to +40 $^{\circ}$ C (Taping)	
Minimum Quantity/Packing Unit		700 pcs. Radial Taping (Reel Pack)	
Quantity/Carton		7000 pcs.	

\*1 million cycles also available, consult our salesmen.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### Round Type 2R Light Touch Switches


Type: **EVQ11**

#### ■ Features


- External dimensions : 6.0 mm×6.0 mm, Height 3.9 mm (Excluding the push plate)
- The cast-processed terminals improve the mountability

#### ■ Recommended Applications

- Operating switches for electronic equipment



#### ■ Explanation of Part Numbers




#### ■ Specifications

Type	Snap action/Push-on type SPST		
Electrical	Circuit Diagram		
	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	50 m $\Omega$ max.	
	Insulation Resistance	50 M $\Omega$ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 8 ms max. (OFF)	
Mechanical	Operating Force	1.0 N $\pm$ 0.4 N 1.3 N $\pm$ 0.4 N 1.6 N $\pm$ 0.5 N	2.6 N $\pm$ 0.6 N
	Travel	0.25 mm $\pm$ 0.10 mm	
Endurance	Operating Life	100000 cycles min. *	50000 cycles min.
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)	
Minimum Quantity/Packing Unit		2500 pcs. Radial Taping (Reel Pack)	
Quantity/Carton		25000 pcs.	

\* 1 million cycles also available, consult our salesmen.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)



Part Numbers	Operating Force	H=Height	Push Plate Color	Operating Life
EVQ11A04M	1.0N	4.3 mm	White	100000 cycles
EVQ11A05R	1.0N	5.0 mm	Red	100000 cycles
EVQ11A07K	1.0N	7.0 mm	Black	100000 cycles
EVQ11A09K	1.0N	9.5 mm	Black	100000 cycles
EVQ11D04K	1.0N	4.3 mm	Black	1000000 cycles
EVQ11D05B	1.0N	5.0 mm	Blue	1000000 cycles
EVQ11D07K	1.0N	7.0 mm	Black	1000000 cycles
EVQ11D09K	1.0N	9.5 mm	Black	1000000 cycles
EVQ11G04M	1.3N	4.3 mm	White	100000 cycles
EVQ11G05R	1.3N	5.0 mm	Red	100000 cycles
EVQ11G07K	1.3N	7.0 mm	Black	100000 cycles
EVQ11G09K	1.3N	9.5 mm	Black	100000 cycles
EVQ11K04K	1.3N	4.3 mm	Black	1000000 cycles
EVQ11K05B	1.3N	5.0 mm	Blue	1000000 cycles
EVQ11K07K	1.3N	7.0 mm	Black	1000000 cycles
EVQ11K09K	1.3N	9.5 mm	Black	1000000 cycles
EVQ11L04M	1.6N	4.3 mm	White	100000 cycles
EVQ11L05R	1.6N	5.0 mm	Red	100000 cycles
EVQ11L07K	1.6N	7.0 mm	Black	100000 cycles
EVQ11L09K	1.6N	9.5 mm	Black	100000 cycles
EVQ11Y04K	1.6N	4.3 mm	Black	1000000 cycles
EVQ11Y05B	1.6N	5.0 mm	Blue	1000000 cycles
EVQ11Y07K	1.6N	7.0 mm	Black	1000000 cycles
EVQ11Y09K	1.6N	9.5 mm	Black	1000000 cycles
EVQ11U04M	2.6N	4.3 mm	White	50000 cycles
EVQ11U05R	2.6N	5.0 mm	Red	50000 cycles
EVQ11U07K	2.6N	7.0 mm	Black	50000 cycles
EVQ11U09K	2.6N	9.5 mm	Black	50000 cycles
EVQ11V04K	2.6N	4.3 mm	Black	100000 cycles
EVQ11V05B	2.6N	5.0 mm	Blue	100000 cycles
EVQ11V07K	2.6N	7.0 mm	Black	100000 cycles
EVQ11V09K	2.6N	9.5 mm	Black	100000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 6.0 mm×3.5 mm Light Touch Switches

Type: **EVQPE**




### ■ Features

- External dimensions : 6.0 mm×3.5 mm, Height 4.3 mm, 5.0 mm
- Wave soldering available

### ■ Recommended Applications

- Operating switches for other electronic equipment


### ■ Explanation of Part Numbers



### ■ Product Chart


Operating Force \ Type	Bulk Type	Height
1.0 N±0.5 N	EVQPE4	H=4.3 mm H=5.0 mm
1.6 N±0.5 N	EVQPE5	
2.4 N±0.6 N	EVQPE6	

### ■ Specifications

Type	Snap action/Push-on type SPST	
Electrical	Circuit Diagram	
	Rating	10 μA 2 Vdc to 50 mA 12 Vdc (Resistive load)
	Contact Resistance	100 mΩ max.
	Insulation Resistance	100 MΩ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
Mechanical	Bouncing	10 ms max. (ON, OFF)
	Operating Force	1.0 N±0.5N (Low force type) 1.6 N±0.5 N (Standard) 2.4 N±0.6 N
Endurance	Travel	0.25 mm <sup>+0.20</sup> / <sub>-0.10</sub> mm
	Operating Life	50000 cycles min.   30000 cycles min.
Operating Temperature		-30 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk)
Minimum Quantity/Packing Unit		1000 pcs. Polyethylene Bag (Bulk)
Quantity/Carton		10000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

<p>EVQPE4 EVQPE5 EVQPE6</p> <p>(Bulk)</p> 	 <p>Circuit diagram</p> <p>PWB mounting hole for reference (Pitch tolerance: ±0.1) View from mounting side</p>			
Part Numbers	Operating Force	H=Height	Push Plate Color	Operating Life
EVQPE404Q	1.0 N	4.3 mm	Grey	50000 cycles
EVQPE405Q	1.0 N	5.0 mm	Grey	50000 cycles
EVQPE504K	1.6 N	4.3 mm	Black	50000 cycles
EVQPE505K	1.6 N	5.0 mm	Black	50000 cycles
EVQPE604T	2.4 N	4.3 mm	Brown	30000 cycles
EVQPE605T	2.4 N	5.0 mm	Brown	30000 cycles

### 6.0 mm×3.5 mm 2R Light Touch Switches


Type: **EVQPJ**

#### ■ Features


- External dimensions : 6.0 mm×3.5 mm, Height 4.3 mm, 5.0 mm
- Wave soldering available

#### ■ Recommended Applications

- Operating switches for other electronic equipment



#### ■ Explanation of Part Numbers



#### ■ Product Chart


Operating Force	Type	Radial Taping	Height
1.0 N±0.5 N		EVQPJG	H=4.3 mm H=5.0 mm
1.6 N±0.5 N		EVQPJH	
2.4 N±0.6 N		EVQPJJ	

#### ■ Specifications

Type	Snap action/Push-on type SPST		
Electrical	Circuit Diagram		
	Rating	10 μA 2 Vdc to 50 mA 12 Vdc (Resistive load)	
	Contact Resistance	100 mΩ max.	
	Insulation Resistance	100 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
Mechanical	Bouncing	10 ms max. (ON, OFF)	
	Operating Force	1.0 N±0.5N (Low force type) 1.6 N±0.5 N (Standard)	2.4 N±0.6 N
	Travel	0.25 mm <sup>+0.20</sup> / <sub>-0.10</sub> mm	
Endurance	Operating Life	50000 cycles min.	30000 cycles min.
Operating Temperature		-30 °C to +85 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)	
Minimum Quantity/Packing Unit		2000 pcs. Radial Taping (Reel Pack)	
Quantity/Carton		20000 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)



## Over Travel Light Touch Switches

Type: **EVQP0**





### ■ Features

- External dimensions : 6.2 mm×6.2 mm, Height 7.45 mm
- Comfortable for long-time operation due to over-travel
- Excellent light-touch operational feel

### ■ Recommended Applications

- Operating switches for other electronic equipment
- Operation switches for PC mouse

### ■ Explanation of Part Numbers



### ■ Specifications


Type		Snap action / Push-on type SPST	
Electrical	Rating	10 $\mu$ A 2 Vdc to 50 mA 30 Vdc (Resistive load)	
	Contact Resistance	100 m $\Omega$ max. (1 $\Omega$ max. after life test)	
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	600 Vac for 1 minute	
	Bouncing	3 ms max. (ON), 8 ms max. (OFF)	
Mechanical	Operating Force	EVQP0E : 0.74 N max.	EVQP0D : 1.3 N max.
	Returning Force	0.1 N min.	
	Pre-travel	0.5 mm max.	
	Movement Differential (MD)	0.12 mm max.	
	Over Travel	0.2 mm max.	
Endurance	Operating Life	EVQP0E : 5000000 cycles min.	EVQP0D : 1000000 cycles min.
Operating Temperature		-20 $^{\circ}$ C to +70 $^{\circ}$ C	
Storage Temperature		-45 $^{\circ}$ C to +85 $^{\circ}$ C	
Minimum Quantity/Packing Unit		500 pcs. Polyethylene Bag (Bulk)	
Quantity/Carton		10000 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

EVQP0

(Bulk)




Part Numbers	Operating Force	Height	Push Plate Color	Operating Life
EVQP0E07K	0.74 N	7.45 mm	Black	5000000 cycles
EVQP0D07K	1.30 N	7.45 mm	Black	1000000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

### 4 mm Square Double-action SMD Light Touch Switches

Type: **EVPAH**




#### ■ Features

- External dimensions : 4.0 mm×4.1 mm, Height 0.59 mm
- Long operation life
- Wide selection of double action operating variations

#### ■ Recommended Applications

- Camera function (Digital still cameras, Camcorders, Mobile phones, etc.) for shutter switches.

#### ■ Explanation of Part Numbers



#### ■ Specifications





Type		Snap action/Push-on type SPDT
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	500 m $\Omega$ max.
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	3 ms max. (ON), 20 ms max. (OFF)
Mechanical	Operating Force	1st : 0.8 N, 0.9 N, 1.0 N 2nd : 1.6 N, 2.0 N, 2.6 N
	Travel	1st: 0.15 mm    2nd: 0.3 mm
Endurance	Operating Life	1.6 N : 100000 cycles min. 2.0 N : 100000 cycles min. 2.6 N : 30000 cycles min.
Operating Temperature		-20 °C to +70 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		8000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		40000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


EVPAH

With J-bent terminals




Circuit Diagram

\* C or/and C' shall be used as common/ground terminal.




PWB land pattern for reference  
(View from mounting side)




Please do not Provide any Land pattern in this area.

Part Numbers	Boss	Ground Terminal	Operating Force		Height	Operating Life
			1 th	2 th		
EVPAHAG6A	Without	With	0.8 N	1.6 N	0.59	100000 cycles
EVPAHBG6A	Without	With	0.9 N	2.0 N	0.59	100000 cycles
EVPAHCG6A	Without	With	1.0 N	2.6 N	0.59	30000 cycles

### Recommended Reflow Soldering Conditions




### Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVPAH	0.59	4.36±0.2	4.4±0.2	12.0 <sup>+0.3</sup> <sub>-0.1</sub>	5.5±0.1	1.75±0.1	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0.1</sub>	0.3±0.05	1.25 <sup>+0.2</sup> <sub>-0.1</sub>

### Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5


  

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	1.0 to 3.0	1.0±0.5

### Recommended Shape of Test Pole



### Recommended Operating Conditions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 6 mm Square Thin Type Double-action SMD Light Touch Switches

Type: **EVQPR/EVQQ0/EVQ3PR**




#### ■ Features

- External dimensions : 6.0 mm×6.0 mm,  
Height : 0.9 mm (Without push plate)  
0.95 mm (With push plate)
- Wide selection of double action operating variations  
With push plate : 1st 0.7 N, 2nd 2.6 N  
Without push plate : 1st 1.0 N, 2nd 2.6 N
- Wide selection of double action operating variations

#### ■ Recommended Applications

- Camera function  
(Digital still cameras, Camcorders, Mobile phones, etc.)
- Operating switches for menu scrolling and confirmation for portable equipment.

#### ■ Explanation of Part Numbers






#### ■ Specifications

Type		Snap action/Push-on type SPDT	
Push Plate type		With Push Plate	Without Push Plate
Electrical	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	100 m $\Omega$ max.	
	Insulation Resistance	50 M $\Omega$ min.	
	Dielectric Withstanding Voltage	100 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 20 ms max. (OFF)	
Mechanical	Operating Force	1st : 0.7 N	1st : 1.0 N
		2nd : 2.6 N	2nd : 2.6 N
	Travel	1st: 0.4 mm	2nd: 0.6 mm
Endurance	Operating Life	30000 cycles min.	
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		5000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		25000 pcs.	


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)


<p>No. 1</p> <p>With Push Plate</p> <p>EVQQ0 EVQPR</p> <p>(Mounting base with Boss) (With ground terminal)</p> 	 <p>Either ⑤ or ⑥ type will be used because of variety of molding dies.</p> <p>Recommended solder thickness <math>t=0.15\pm0.03</math></p> <p>Circuit diagram</p> <p>PWB land pattern for reference (View from mounting side)</p>				
<p>Part Numbers</p>	<p>Ground Terminal</p>	<p>Boss</p>	<p>Operating Force</p>	<p>Height</p>	<p>Operating Life</p>
<p>EVQQ04A10</p>	<p>Without</p>	<p>Without</p>	<p>1st/0.7 N, 2nd/2.6 N</p>	<p>0.95 mm</p>	<p>30000 cycles</p>
<p>EVQPR7A10</p>	<p>Without</p>	<p>With</p>	<p>1st/0.7 N, 2nd/2.6 N</p>	<p>0.95 mm</p>	<p>30000 cycles</p>
<p>EVQPR5A10</p>	<p>With</p>	<p>Without</p>	<p>1st/0.7 N, 2nd/2.6 N</p>	<p>0.95 mm</p>	<p>30000 cycles</p>
<p>EVQPR9A10</p>	<p>With</p>	<p>With</p>	<p>1st/0.7 N, 2nd/2.6 N</p>	<p>0.95 mm</p>	<p>30000 cycles</p>
<p>No. 2</p> <p>Without Push Plate</p> <p>EVQPR EVQ3PR</p> <p>(Mounting base with Boss) (With ground terminal)</p> 	 <p>Either ⑤ or ⑥ type will be used because of variety of molding dies.</p> <p>Recommended solder thickness <math>t=0.15\pm0.03</math></p> <p>Circuit diagram</p> <p>PWB land pattern for reference (View from mounting side)</p>				
<p>Part Numbers</p>	<p>Ground Terminal</p>	<p>Boss</p>	<p>Operating Force</p>	<p>Height</p>	<p>Operating Life</p>
<p>EVQPRBA09</p>	<p>Without</p>	<p>Without</p>	<p>1st/1.0 N, 2nd/2.6 N</p>	<p>0.9 mm</p>	<p>30000 cycles</p>
<p>EVQ3PRA09</p>	<p>Without</p>	<p>With</p>	<p>1st/1.0 N, 2nd/2.6 N</p>	<p>0.9 mm</p>	<p>30000 cycles</p>
<p>EVQPRDA09</p>	<p>With</p>	<p>Without</p>	<p>1st/1.0 N, 2nd/2.6 N</p>	<p>0.9 mm</p>	<p>30000 cycles</p>
<p>EVQPRHA09</p>	<p>With</p>	<p>With</p>	<p>1st/1.0 N, 2nd/2.6 N</p>	<p>0.9 mm</p>	<p>30000 cycles</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### Recommended Reflow Soldering Conditions




### Embossed Carrier Taping



Unit: mm


Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQPR/Q0/3PR	0.9, 0.95	6.3±0.3	6.3±0.3	12.0±0.3	5.50±0.15	1.75±0.15	8.00±0.15	2.00±0.15	4.00±0.15	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.30±0.05	1.7 <sup>+0.2</sup> <sub>-0.1</sub>

### Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.2	φ21.0±0.8	2.0±0.5
Item	W	T	t	r	
Rate (mm)	13.5±1.0	17.5±1.0	1.0 to 3.0	1.0±0.5	

### Recommended Shape of Test Pole




### Recommended Operating Conditions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 4.7 mm×3.5 mm Double-action Side-operational SMD Light Touch Switches

Type: **EVPAJ**




#### ■ Features

- External dimensions : 4.7 mm×3.5 mm (Without push plate), Height : 1.2 mm
- With ground terminal

#### ■ Recommended Applications

- Camera function  
(Digital still cameras, Camcorders, Mobile phones, etc.)
- Operating switches for menu scrolling and confirmation for portable equipment.













#### ■ Explanation of Part Numbers



#### ■ Specifications


Type	Snap action/Push-on type SPDT	
	Rating	10 $\mu$ A 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	500 m $\Omega$ max.
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	3 ms max. (ON) 20 ms max. (OFF)
Mechanical	Operating Force (1st Action)	1.6 N
	Operating Force (2nd Action)	2.6 N
	Travel (1st Action)	0.15 mm
	Travel (2nd Action)	0.4 mm
	Push Strength	30 N for 15 seconds
Endurance	Operating Life	100000 cycles min.
Operating Temperature		-20 °C to +70 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		5000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		25000 pcs.

■ Dimensions in mm (not to scale)


<p>EVPAJ</p> <p>(Embossed Taping) With Ground Terminal</p> <p>Part Numbers : EVPAJAC1A</p> 	     <p>Circuit Diagram</p> <p>Please do not Provide any Land pattern in this area.</p>  <p>Push plate side</p> <p>PWB land pattern for reference(View from mounting side)</p>
<p>EVPAJ</p> <p>L-shape</p> <p>Part Numbers : EVPAJAE1A</p> 	     <p>Circuit Diagram</p> <p>Please do not Provide any Land pattern in this area.</p>  <p>Push plate side</p> <p>PWB land pattern for reference(View from mounting side)</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### Recommended Reflow Soldering Conditions




### Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	$P_1$	$P_2$	$P_0$	$D_0$ Dia.	$t_1$	$t_2$
EVPAJ	1.2	$6.8 \pm 0.2$	$4.9 \pm 0.2$	$12.0^{+0.3}_{-0.1}$	$5.78 \pm 0.1$	$1.75 \pm 0.1$	$8.0 \pm 0.1$	$2.0 \pm 0.1$	$4.0 \pm 0.1$	$1.5^{+0.1}_{-0}$	$0.3 \pm 0.05$	$1.95^{+0.3}_{-0}$

### Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	$\phi 380.0 \pm 2.0$	$\phi 80.0 \pm 1.0$	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	$2.0 \pm 0.5$

Item	W	T	t	r
Rate (mm)	$13.5 \pm 1.0$	$17.5 \pm 1.0$	-	-

6.2 mm×3.7 mm Double-action  
Side-operational Edge Mount / SMD  
Light Touch Switches

Type: **EVQQ0**




### ■ Features

- External dimensions : 6.2 mm×3.75 mm (Excluding the push plate), Height : 3.5 mm (EVQQ0C Type : Printed circuit board being as low as 1.35 mm)
- Good operability due to long stroke : 1st 0.4 mm, 2nd 0.5 mm
- Improved soldering strength in the operating direction when mounted on PC board edge

### ■ Recommended Applications

- Camera function  
(Digital still cameras, Camcorders, Mobile phones, etc.)
- Operating switches for menu scrolling and confirmation for portable equipment.

### ■ Explanation of Part Numbers



### ■ Specifications

Type	Snap action/Push-on type SPDT	
Electrical	Circuit Diagram	
	Rating	10 μA 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance	500 mΩ max.
	Insulation Resistance	100 MΩ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	100 Vac for 1 minute
Mechanical	Bouncing	5 ms max. (ON) 20 ms max. (OFF)
	Operating Force (1st Action)	1.0 N
	Operating Force (2nd Action)	2.6 N
	Travel (1st Action)	0.4 mm
	Travel (2nd Action)	0.5 mm
Endurance	Operating Life	30 N for 1 minute
Operating Temperature		1st Action with click : 200000 cycles min.
Storage Temperature		-20 °C to +70 °C
Minimum Quantity/Packing Unit		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Quantity/Carton		2500 pcs. Embossed Taping (Reel Pack)
		12500 pcs.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


<p>No. 1</p> <p><b>EVQQ0C0</b> (Embossed Taping)</p> 	<p>* Height from surface of PCB : 1.35 mm</p>		
<p>Part Numbers</p> <p>EVQQ0C03K</p>	<p>Operating Force</p> <p>1st Action/1.0 N (With click) 2nd Action/2.6 N</p>	<p>Height</p> <p>3.5 mm</p>	<p>Operating Life</p> <p>200000 cycles</p>
<p>No. 2</p> <p><b>EVQQ0G0</b> (Embossed Taping)</p> 	<p>Between washer and terminals. (Initial condition : 0 to 0.1 mm)</p> <p>Mounting Surface Between portion (A) and (B) on washer.</p> <p>PWB land pattern for reference (View from mounting side) (Tolerance : ±0.1)</p>		
<p>Part Numbers</p> <p>EVQQ0G03K</p>	<p>Operating Force</p> <p>1st Action/1.0 N (With click) 2nd Action/2.6 N</p>	<p>Height</p> <p>3.5 mm</p>	<p>Operating Life</p> <p>200000 cycles</p>

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Recommended Reflow Soldering Conditions




### ● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQQ0C	3.5	6.6±0.2	5.7±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>0</sub>	0.4±0.1	3.8±0.2
EVQQ0G			5.8±0.2									3.7±0.2

### ● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	$\phi 380.0 \pm 2.0$	$\phi 80.0 \pm 1.0$	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	2.0±0.5

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	1.0 to 3.0	1.0±0.5

### 6 mm Square Long Travel SMD Light Touch Switches

Type: **EVQP0/EVQP1/EVQ9P**




#### ■ Features

- External dimensions : 6.0 mm×6.1 mm, Height 5.0 mm  
(Including the push plate)
- Steady and low contact resistance (100 mΩ max.)
- Excellent solderability (J-bent-type terminals)

#### ■ Recommended Applications

- Operating switches for car electronic equipment.
- Input on operating switches for telephones, electronic musical instruments, etc.

#### ■ Explanation of Part Numbers



#### ■ Specifications


Type		Snap action/Push-on type SPST	
Electrical	Rating	10 μA 2 Vdc to 50 mA 12 Vdc (Resistive load)	
	Contact Resistance	100 mΩ max.	
	Insulation Resistance	100 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	10 ms max. (ON, OFF)	
Mechanical	Operating Force	1.6 N±0.5 N, 2.0 N±0.6 N 2.5 N±0.6 N 3.0 N±0.8 N 3.5 N±1.0 N	2.2 N±0.6 N 2.5 N±0.6 N
	Travel	1.3 mm±0.2 mm	1.0 mm±0.2 mm
Endurance	Operating Life	3.5 N type: 30000 cycles min. 1.6 N, 2.0 N, 2.2 N, 2.5 N, 3.0 N types: 100000 cycles min.	
Operating Temperature		-40 °C to +85 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		2000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		10000 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

EVQP0  
EVQP1  
EVQ9P


(Embossed Taping)




Part Numbers	Operating Force	Travel	H=Height	Push Plate Color	Operating Life
EVQP1K05M	2.2 N	1.0 mm	5.0 mm	Natural	100000 cycles
EVQP1Y05M	2.5 N	1.0 mm	5.0 mm	Natural	100000 cycles
EVQP1905M	1.6 N	1.3 mm	5.0 mm	Natural	100000 cycles
EVQP1F05M	2.0 N	1.3 mm	5.0 mm	Natural	100000 cycles
EVQP1D05M	2.5 N	1.3 mm	5.0 mm	Natural	100000 cycles
EVQP0405M	3.0 N	1.3 mm	5.0 mm	Natural	100000 cycles
EVQ9P105M	3.5 N	1.3 mm	5.0 mm	Natural	30000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Recommended Reflow Soldering Conditions




### ● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	$P_1$	$P_2$	$P_0$	$D_0$ Dia.	$t_1$	$t_2$
EVQP0 EVQP1 EVQ9P	5.0	6.4±0.2	7.9±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.4±0.1	5.25±0.20

### ● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	$\phi 370.0 \pm 2.0$	$\phi 50.0$ min.	$\phi 13.0 \pm 0.5$	$\phi 21.0 \pm 1.0$	2.0±0.5

Item	W	T	t	r
Rate (mm)	14.0±1.5	—	1.0 to 3.0	1.0±0.5

6 mm Square Long Travel 2 terminals  
SMD Light Touch Switches

Type: **EVPAS**




■ **Features**

- External dimensions : 6.0 mm×6.1 mm, Height 5.0 mm  
(Including the push plate)
- Steady and low contact resistance (100 mΩ max.)
- Excellent solderability (J-bent-type terminals)

■ **Recommended Applications**

- Operating switches for car electronic equipment.
- Input on operating switches for telephones, electronic musical instruments, etc.

■ **Explanation of Part Numbers**



■ **Specifications**





Type		Snap action/Push-on type SPST	
Electrical	Rating	10 μA 2 Vdc to 50 mA 12 Vdc (Resistive load)	
	Contact Resistance	100 mΩ max.	
	Insulation Resistance	100 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	10 ms max. (ON, OFF)	
Mechanical	Operating Force	1.6 N±0.5 N, 2.0 N±0.6 N 2.5 N±0.6 N 3.0 N±0.8 N 3.5 N±1.0 N	2.2 N±0.6 N 2.5 N±0.6 N
	Travel	1.3 mm±0.2 mm	1.0 mm±0.2 mm
Endurance	Operating Life	3.5 N type: 30000 cycles min. 1.6 N, 2.0 N, 2.2 N, 2.5 N, 3.0 N types: 100000 cycles min.	
Operating Temperature		-40 °C to +90 °C	
Storage Temperature		-40 °C to +90 °C (Bulk) -20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		2000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		10000 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.



■ Dimensions in mm (not to scale)

EVPASP

(Embossed Taping)



Circuit diagram




PWB land pattern for reference


Part Numbers	Operating Force	Travel	H=Height	Push Plate Color	Operating Life
EVPASCB1A	2.2 N	1.0 mm	5.0 mm	Black	100000 cycles
EVPASDB1A	2.5 N	1.0 mm	5.0 mm	Black	100000 cycles
EVPASAC1A	1.6 N	1.3 mm	5.0 mm	Black	100000 cycles
EVPASBC1A	2.0 N	1.3 mm	5.0 mm	Black	100000 cycles
EVPASDC1A	2.5 N	1.3 mm	5.0 mm	Black	100000 cycles
EVPASEC1A	3.0 N	1.3 mm	5.0 mm	Black	100000 cycles
EVPASFC1A	3.5 N	1.3 mm	5.0 mm	Black	30000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Recommended Reflow Soldering Conditions




### ● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	$P_1$	$P_2$	$P_0$	$D_0$ Dia.	$t_1$	$t_2$
EVPAS	5.0	6.8±0.2	7.7±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.4±0.1	5.25±0.20

### ● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5

Item	F	G
Rate (mm)	13.5±1.0	17.5±1.0

## 6 mm Square Long Travel 2R Light Touch Switches

Type: **EVQPV**




### ■ Features

- External dimensions : 6.0 mm×6.1 mm, Height 5.0 mm  
(Including the push plate)
- High mountability, section terminals and radial taping package
- Low contact resistance and steady contact characteristics

### ■ Recommended Applications

- Operating switches for car electronic equipment.
- Input on operating switches for telephones, electronic musical instruments, etc.

### ■ Explanation of Part Numbers



### ■ Specifications


Type		Snap action/Push-on type SPST	
Electrical	Rating	10 μA 2 Vdc to 50 mA 12 Vdc (Resistive load)	
	Contact Resistance	100 mΩ max.	
	Insulation Resistance	100 MΩ min. (at 100 Vdc)	
	Dielectric Withstanding Voltage	250 Vac for 1 minute	
	Bouncing	10 ms max. (ON, OFF)	
Mechanical	Operating Force	2.2 N	1.6 N, 2.0 N, 2.5 N, 3.5 N
	Travel	1.0 mm±0.2 mm	1.3 mm±0.2 mm
Endurance	Operating Life	100000 cycles min. (3.5 N type : 30000 cycles min.)	
Operating Temperature		-30 °C to +85 °C	
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)	
Minimum Quantity/Packing Unit		2500 pcs. Radial Taping (Reel Pack)	
Quantity/Carton		25000 pcs.	

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

## EVQPV

(Radial Taping)



Part Numbers	Operating Force	Travel	H=Height	Push Plate Color	Operating Life
EVQPA05K	2.2 N	1.0 mm	5.0 mm	Black	100000 cycles
EVQPV205K	1.6 N	1.3 mm	5.0 mm	Black	100000 cycles
EVQPVG05K	2.0 N	1.3 mm	5.0 mm	Black	100000 cycles
EVQPVF05K	2.5 N	1.3 mm	5.0 mm	Black	100000 cycles
EVQPVW05K	3.5 N	1.3 mm	5.0 mm	Black	30000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 8 mm Square Long Travel SMD Light Touch Switches

Type: **EVQQ1**




### ■ Features

- External dimensions : 8.5 mm×8.5 mm, Height 6.5 mm (Including the push plate)
- High operating force which prevents incorrect operation
- Reliable contact (dust-proof design)

### ■ Recommended Applications

- Operating switches for car electronic equipment, car audio systems, etc.
- Steering switches

### ■ Explanation of Part Numbers







### ■ Specifications


Type	Snap action/Push-on 1-pole 1-throw SPST	
Electrical	Rating	10 $\mu$ A 2 Vdc to 50 mA 12 Vdc (Resistive load)
	Contact Resistance	100 m $\Omega$ max.
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	4 N, 5 N
	Travel	1.0 mm
Endurance	Operating Life	100000 cycles min.
Operating Temperature		-40 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		1000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		10000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.


### ■ Dimensions in mm (not to scale)

<p><b>EVQQ1</b> (Embossed Taping)</p> 		
		
	 <p>PWB land pattern for reference</p>	
	 <p>Circuit diagram</p>	
Part Numbers	Operating Force	Push Plate Color
EVQQ1D06M	4.0 N	Natural
EVQQ1E06K	5.0 N	Black

### ■ Recommended Reflow Soldering Conditions




### ● Embossed Carrier Taping



Part No.	Height	A	B	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	D <sub>0</sub> Dia.	t <sub>1</sub>	t <sub>2</sub>
EVQQ1	6.5	8.9±0.2	10.1±0.2	16.0±0.3	7.5±0.1	1.75±0.10	12.0±0.1	2.0±0.1	4.0±0.1	1.5 <sup>+0.1</sup> <sub>-0</sub>	0.40±0.05	6.8±0.2

Unit: mm

### ● Standard Reel Dimensions in mm (not to scale)




Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.5	φ21.0±1.0	2.0±0.5

Item	W	T	t	r
Rate (mm)	17.5±0.5	21.5±1.0	1.0 to 3.0	1.0±0.5

## 8 mm Square Long Travel 2R Light Touch Switches

Type: **EVQQJ**




### ■ Features

- External dimensions : 8.0 mm×8.0 mm, Height 5.0 mm, 5.5 mm, 6.1 mm (Including the push plate)
- Long life (self-cleaning)
- Low contact resistance with metal contacts
- Small bouncing

### ■ Recommended Applications

- Operating Switches for car air conditioners, car audio systems, etc.
- Push switches for camcorders
- Ten-key switches for telephones

### ■ Explanation of Part Numbers



### ■ Specifications

Type		Snap action/Push-on 1-pole 1-throw SPST			
Electrical	Rating	10 $\mu$ A 2 Vdc to 5 mA 12 Vdc. (Resistive load)			
	Contact Resistance	200 m $\Omega$ max.			
	Insulation Resistance	50 M $\Omega$ min. (at 100 Vdc)			
	Dielectric Withstanding Voltage	250 Vac for 1 minute			
	Bouncing	10 ms max. (ON, OFF)			
Mechanical	Operating Force	0.8 N $\pm$ 0.4 N	1.3 N $\pm$ 0.6 N	2.5 N $\pm$ 0.6 N	3.0 N $\pm$ 0.6 N
	Travel	1.0 mm	1.0 mm	1.2 mm	1.75 mm
Endurance	Operating Life	1000000 cycles min.	100000 cycles min.	100000 cycles min.	100000 cycles min.
Operating Temperature		-20 °C to +70 °C			
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +40 °C (Taping)			
Minimum Quantity/Packing Unit		1000 pcs. Radial Taping (Reel Pack)			
Quantity/Carton		10000 pcs.			

### ■ Application Notes:









- Washing is not allowed.
- Inclination of pushing knob shall be 3 ° max.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

EVQQJ

(Radial Taping)




PWB mounting hole for reference  
(Pitch tolerance: ±0.1)  
View from mounting side

Part Numbers	Operating Force	Travel	H=Height	h=Mounting Base	Push Plate Color	Operating Life
EVQQJJ05Q	0.8 N	1.0 mm	5.0 mm	3.5 mm max.	Grey	1000000 cycles
EVQQJE05D	1.3 N	1.0 mm	5.0 mm	3.6 mm max.	Orange	100000 cycles
EVQQJD05B	2.5 N	1.2 mm	5.5 mm	3.8 mm max.	Blue	100000 cycles
EVQQJF06Q	3.0 N	1.75 mm	6.1 mm	4.0 mm max.	Grey	100000 cycles

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 10 mm Square Center Space Long Travel SMD Light Touch Switches

Type: **EVPAD**




#### ■ Features

- The open center space allows for flexibility in choosing a LED  
Up to a 4.2-mm diameter chip LED can be mounted.
- Provides an excellent operational feel.
  - Crisp tactile feedback
  - Long stroke (1 mm)
- Supports auto reflow soldering.

#### ■ Recommended Applications

- Operating switches for car electronic equipment (car audio systems, car air conditioners, etc.)

#### ■ Explanation of Part Numbers



#### ■ Specifications

Type		Snap action/Push-on type SPST
Electrical	Rating	10 $\mu$ A 2 Vdc to 50 mA 12 Vdc (Resistive load)
	Contact Resistance	100 m $\Omega$ max.
	Insulation Resistance	100 M $\Omega$ min. (at 100 Vdc)
	Dielectric Withstanding Voltage	250 Vac for 1 minute
	Bouncing	10 ms max. (ON, OFF)
Mechanical	Operating Force	4.0 N $\pm$ 0.8 N
	Travel	1.0 mm $\pm$ 0.15 mm
Endurance	Operating Life	100000 cycles min.
Operating Temperature		-40 °C to +85 °C
Storage Temperature		-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit		1000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		5000 pcs.




Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.



## CONTENTS

Products	Type/Series	Part Numbers	Page
Common	Index / RoHs Directives		EV2
Rotary Potentiometers	Contents / Quick Selection Guide		EV4
	Checklist / Application Notes / Common Specifications / Minimum Quantity/Packing Unit		EV6
	18 mm Square Rotary Potentiometers (High Rotational Torque)	EVCX	EV12
	39/20 mm Center Space Rotary Potentiometers	EWVYE/K/M	EV13
	44/25 mm Center Space Rotary Potentiometers	EWVYG/H/J/L	EV14
Carbon Composition Trimmer Potentiometers	Contents / Quick Selection Guide		EV15
	Application Notes / Common Specifications / Minimum Quantity/Packing Unit		EV17
	6FF Square Trimmer Potentiometers	EVNCYA	EV20
	6FE Square Trimmer Potentiometers	EVND	EV22
Position Sensors	Contents / Quick Selection Guide		EV25
	Checklist / Application Notes / Minimum Quantity/Packing Unit		EV27
	10 mm GS Sensors	EVWAE/D	EV30
	Linear Position Sensors	EVAW7	EV32
	15 mm Position Sensors	EVWBE	EV34
Encoders	Contents / Quick Selection Guide		EV35
	Checklist / Application Notes / Minimum Quantity/Packing Unit		EV37
	10 mm Square GS Encoders	EVQVX	EV40
	10 mm Square SMD Encoders	EVQVV	EV42
	Edge Drive Jog Encoders	EVQWK	EV44
	11 mm Square GS Encoders	EVER/U/V/Y	EV46
	12 mm Square GS Encoders	EVEG/H/K/L	EV49
	12 mm Square GS Encoders with Push-on Switch	EVEJB	EV52
	16 mm Square Encoders	EVEP/Q	EV54
	18 mm Square Encoders (High Rotational Torque)	EVQW	EV56
	20/12 mm Center Space Encoders	EVQV6	EV57
	27/17 mm Center Space Encoders	EVQWF/VP	EV58
	27/18 mm Center Space Encoders	EVQV5	EV59
	38/25 mm Center Space Encoders	EVQVN	EV60
	60/40 mm Center Space Encoders	EVQV0	EV61

## Index

<p>EV12</p>  <p>18 mm Square Rotary Potentiometers (High Rotation Torque) (EVCX)</p>	<p>EV13</p>  <p>39/20 mm Center Space Rotary Potentiometers (EWVYE, EWVYK, EWVYM)</p>	<p>EV14</p>  <p>44/25 mm Center Space Rotary Potentiometers (EWVYG, EWVYH, EWVYJ, EWVYL)</p>	<p>EV20</p>  <p>6FF Square Trimmer Potentiometers (EVNCYA)</p>
<p>EV22</p>  <p>6FE Square Trimmer Potentiometers (EVND)</p>	<p>EV30</p>  <p>10 mm GS Sensors (EVWAE, EVWAD)</p>	<p>EV32</p>  <p>Linear Position Sensors (EVAW7)</p>	<p>EV34</p>  <p>15 mm Position Sensors (EVBWE)</p>
<p>EV40</p>  <p>10 mm Square GS Encoders (EVQVX)</p>	<p>EV42</p>  <p>10 mm Square SMD Encoders (EVQVV)</p>	<p>EV44</p>  <p>Edge Drive Jog Encoders (EVQWK)</p>	<p>EV46</p>  <p>11 mm Square GS Encoders (EVER, EVEU, EVEV, EVEY)</p>
<p>EV49</p>  <p>12 mm Square GS Encoders (EVEG, EVEH, EVEK, EVEL)</p>	<p>EV52</p>  <p>12 mm Square GS Encoders with Push-on Switch (EVEJB)</p>	<p>EV54</p>  <p>16 mm Square Encoders (EVEP, EVEQ)</p>	<p>EV56</p>  <p>18 mm Square Encoders (High Rotational Torque) (EVQW)</p>

## Index

<p>EV57</p>  <p>20/12 mm Center Space Encoders (EVQV6)</p>	<p>EV58</p>  <p>27/17 mm Center Space Encoders (EVQWF, EVQVP)</p>	<p>EV59</p>  <p>27/18 mm Center Space Encoders (EVQV5)</p>	<p>EV60</p>  <p>38/25 mm Center Space Encoders (EVQVN)</p>
<p>EV61</p>  <p>60/40 mm Center Space Encoders (EVQV0)</p>			

### ■ RoHS Directives

RoHS Directives : The restriction of the use of certain hazardous substances in electrical and electronic equipment

The products introduced in this catalog conform to the RoHS Directives\* (enforced in July 2006).

(Newly ordered products will conform to the RoHS Directive.)

Please contact our sales staff for inquiries about the RoHS compliance of currently used products.

**CONTENTS**

	Page
■ Quick Selection Guide .....	EV5
■ Checklist Before Inquiry .....	EV6
■ Application Notes .....	EV7
■ Common Specifications .....	EV8
■ Minimum Quantity/Packing Unit .....	EV11
■ 18 mm Square Rotary Potentiometers (High Rotational Torque / EVCX) .....	EV12
■ 39/20 mm Center Space Rotary Potentiometers (EWVYE, EWVYK, EWVYM) .....	EV13
■ 44/25 mm Center Space Rotary Potentiometers (EWVYG, EWVYH, EWVYJ, EWVYL) .....	EV14

### ■ Quick Selection Guide

Type, Series	Appearance	Part Numbers	Country of origin	Nominal Total Resistance	Taper	Rotation Angle	Page
18 mm Square (High Rotational Torque)		EVCX	Japan	5 k $\Omega$ to 100 k $\Omega$ $\pm$ 20 %	Custom design	280 °	EV12
39/20 mm Center Space		EWVYE EWVYK EWVYM	Malaysia	10 k $\Omega$ $\pm$ 20 %	B	300 °	EV13
44/25 mm Center Space		EWVYG EWVYH EWVYJ EWVYL	Malaysia	10 k $\Omega$ $\pm$ 20 %	B	300 °	EV14

Country of origin : As of April 2013

## ■ Checklist Before Inquiry

When you specify Potentiometers, please take advantages of our standard products for better price and delivery. Please provide the following items before ordering.

				Checklist	
				Item	Information (Requirements)
Common	C-1	Inquiry purpose		New use, Modification, Others ( )	
	C-2	Modification	Previous supplier		
			Conventional part No.		
	C-3	Application	Purpose		
			Equipment		
			Environment	Indoor/Outdoor use, Stationary/Portable set, High humidity, SO <sub>2</sub> , NaCl	
			Temperature	( °C) to ( °C)	
	C-4	Adjustment	Operation	General use, Edge drive, Low torque	
			Method	Manual, Automatic	
			Direction	Top, Bottom, Vertical, Horizontal	
	C-5	Mounting	Driver shape	Plus/Minus screw slot, Hexagonal driver, Knob (Shape; )	
			Method	Manual, Automatic	
Mounter			Panaset (Model: ), Other mounter (Maker/Model: / ), Parts feeder		
C-6	Soldering	Method	Manual soldering, Flow soldering, Reflow soldering		
		Conditions	Temp. ( °C), Time ( s), Dipping times( )		
		Washing	Machine, Soaking, Applied solvent ( )		
Electrical	E-1	Application	Circuit	Volume, Tone, Balance, Circuit regulation, Others ( )	
			Stereo tone use	General tone, High-cut tone, Bass, Treble	
	E-2	Conditions	Current	ac, dc	
			Rating	Max. operating power ( W), Operating voltage ( V)	
	E-3	Resistance	Applied current	Small current use, Applying current ( mA)	
			Total value/Tolerance	( Ω) / ±20 %, ±30 %, Others (± %)	
	E-4	Taper	A, B, C, D, G, BH, 15A, 1B, 15C, 10A, 4B, H, Others ( )		
	E-5	Tracking error	Range	( dB) to ( dB)	
Specifications			±( dB)		
E-6	Tap	Necessity/Position	Necessary, Unnecessary / 40 %, 50 %, 60 %, Others ( )		
E-7	Other requirements				
Shapes/Dimensions	M-1	Shape	Size	φ14, φ16, φ18	
			Structure	Units	Single, 1-shaft 2 gang, 1-shaft 3 gang, 1-shaft 4 gang, 2-shaft 2 gang, 2-shaft 3 gang, 2-shaft 4 gang, 2-shaft 5 gang, Others ( )
	M-2	Shaft/Lever	Shape	Side Adjustment type, Top Adjustment type	
			Type	F type (flat), S type (slotted), P type (18 teeth serrations)	
	M-3	Mounting	Type	Bushing, Soldering, Screw mounting, Others ( )	
			(Type with bushing)	Screw dia.: M6, M7, M9, M10, 3/8" Screw pitch: 0.75 mm, 1.0 mm, 32NEF Bushing length: 5 mm, 7 mm, 10 mm, 15 mm, 17.5 mm, 20 mm, 22.5 mm, 25 mm, 27.5 mm, 30 mm, 32.5 mm, 35 mm, 37 mm, 39 mm, 42.5 mm	
	M-4	Terminals	Type	Solder lug, PWB	
			(PWB terminals)	Length from mounting surface: ( mm), Layout pattern: ( )	
	Additional functions				
	M-5	Switch	Type	Rotary, Pull-Push, Push-ON, Others ( )	
Function			SPST, SPDT, DPST, DPDT		
Rating			Voltage: ( V), Current: ( A), Inrush current: ( A)		
Terminal type			Solder lug, PWB (Height from PWB to shaft center: mm)		
M-6	Detents	Detents	1 point, 11 points, 41 points, Others ( points)		
		Position	Midpoint, at 180 °, at 200 °, Others (at )		
Others	L-1	Special requirements for endurance			
	L-2	Other questionnaires			

Notes:

- When you specify custom types (custom-made), new tooling and jigs, and/or equipment may be required. It will be necessary to confirm your estimates of quantity and development schedule as accurately as possible.
- Please inform us if you designate your own part number.

\* Previous notations for potentiometer shape "Stand-up type" (Shaft is parallel to PWB.) and "Lay-down type" (Shaft is vertical to PWB.) – have been changed in this edition to "Horizontal type" or "Side-adjust type" (Shaft or knob is parallel to PWB.) and "Vertical type" or "Top-adjust type" (Shaft or knob is vertical to PWB.).

■ ⚠ **Application Notes**


When using our Rotary Potentiometers, please observe the following items to prevent dangerous accidents and deterioration of performance.

**1. Prohibited items and notes in design stage**

1. Use within the rating  
The Power Rating or Maximum Voltage varies with the size and type of a product. Also, the Power Rating must be reduced according to a Power Derating Curve. When a potentiometer is used with a current of less than a few micro-amperes, the influence of contact resistance increases because of the circuit diagram. Check the potentiometer under actual operating conditions.

2. Migration  
Some potentiometers cannot be used with dc voltage. If a potentiometer is to be used with dc voltage, specify this when ordering, or check the availability referring to the "Product Specifications for Information."

3. Anodization  
When a potentiometer is used with dc voltage under conditions of high humidity, the terminal at the side of the wiper (terminal 2) must be a positive electrode, as shown in the figure at right.



4. Recommended Circuit Configuration  
It is recommended that you use the variable resistor for voltage adjustments. If it is used for current adjustments, then it may be influenced by the contact resistance between the resistor body and the slide, depending on the target circuit conditions. Conducting a test under actual operating conditions is highly recommended.

5. Soldering conditions  
When performing solder dipping, check the soldering conditions according to the "Product Specifications for Information," because the conditions vary with the product.

Do not wash a potentiometer after solder dipping because flux may invade the potentiometer, resulting in contact failure. Avoid use of jumper cables near the potentiometers because flux may attach to them.

6. Shaft rotation wobble  
If the shaft is long, the rotation wobble increases in proportion to its length. To secure the quality of a set, we recommend use of the types with a bushing.

7. Operating temperature conditions  
Tactile feeling in operation is given serious consideration, and rotation torque increases under low temperatures (below -10 °C) depending on the product. If a potentiometer is expected to be used under low temperatures, specify this in advance.

**2. Prohibited items and notes on handling**

1. Terminal clinch  
Bending and unbending of terminals after mounting to a PWB must be one cycle or less. More than one bending/unbending cycle may result in damage.

2. Stress on the terminals  
Do not apply excessive stress to terminals during handling. Set soldering conditions with consideration given to stress on the terminals.

3. Chemical resistance  
Before using a potentiometer with an insulated shaft, be sure to check the reactivity of the shaft with any chemicals to be used.

4. Potentiometers with a push lock type switch  
Handle the potentiometer with the shaft locked. If a lateral pressure above 0.4 N·m (4 kg·cm) is applied to the shaft when it is unlocked, the shaft may be bent.

5. Storage conditions  
Do not store the potentiometers under high temperatures and/or high humidity, or in a location where corrosive gas may be generated. Store the potentiometers at room temperature and room humidity in a packed condition. Use them within a maximum of 6 months. Check the date of manufacture on the package box and apply the "first-in-first-out" rule.  
If unpacked potentiometers must be stored as inventory, store them in a polyethylene bag to keep out air.

**3. Prohibited items on fire and smoking**

1. Absolutely avoid use of a potentiometer beyond its rated range because doing so may cause a fire. If misuse or abnormal use may result under conditions in which the potentiometer is used out of its rated range, take proper measures such as current interruption using a protective circuit.

2. The grade of nonflammability for resin used in potentiometers is "94HB," which is based on UL94 Standards (flammability test for plastic materials). Prohibit use in a location where a spreading fire may be generated or prepare against a spreading fire.

**4. For use in equipment for which safety is requested**

Although care is taken to ensure potentiometer quality, inferior characteristics, short circuits, and open circuits are some problems that might be generated. To design a set which places maximum emphasis on safety, review the affect of any single fault of a potentiometer in advance and perform virtually fail-safe design to ensure maximum safety by:

1. preparing a protective circuit or a protective device to improve system safety, and
2. preparing a redundant circuit to improve system safety so that the single fault of a potentiometer does not cause a dangerous situation.

For notes on use, the following sources were referred:

Technical report EIAJ RCR-2191A "Guideline of Notabilia for potentiometers for Use in Electronic Equipment" issued by the Japan Electronics and Information Technology Industries Association  
(Issued by March 2002)

Refer to this Technical Report for additional details.

5. For actual use, be sure to refer to "Product Specifications for Information."

### ■ Common Specifications

#### ● Electrical Specifications


##### 1. Taper

Measuring Method		$\frac{\text{Out-put Voltage between Terminal 1 \& 2}}{\text{Operating Voltage between Terminal 1 \& 3}} \times 100(\%)$	$\frac{\text{Out-put Voltage between Terminal 2 \& 3}}{\text{Operating Voltage between Terminal 1 \& 3}} \times 100(\%)$
Taper		Effective Rotation Angle	
EIAJ	Panasonic	50 %	50 % *
15A	A	10 to 25	—
1B	B	40 to 60	—
15C	C	—	10 to 25
10A	D	6 to 15	—
4B	G	40 to 60	—
H	BH	Linear taper	

Notes:

- \* Angle from terminal 3 side.
- ( ) is per JIS (Japanese Industrial Standard). Unless otherwise specified, we consider it at 50 % rotation, however, upon request above JIS can be applied.
- [ ] is only reference value.

## Standard Taper



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### 2. Tracking

The tracking should be calculated as follows.

$$\text{Tracking (dB)} = 20 \log (VR_2/VR_1)$$


Where:

VR<sub>1</sub>= Voltage between terminal 1 & 2 of section R<sub>1</sub>

VR<sub>2</sub>= Voltage between terminal 1 & 2 of section R<sub>2</sub>

Test voltage between terminal 1 & 3

shall be 2 V to 5 V (1000±200 Hz).



In case of a potentiometer with a tap, the measurement should be made by connecting a fixed resistor between tap terminal and terminal 1. Unless otherwise specified, tolerance of the fixed resistor shall be ±10 %. If your requirements different, inform us of your specifications.

## ● Mechanical Specifications

### 1. Shaft Angle

Shaft angle against mounting surface shall be 90°. Shaft bend and shaft wobble shall be  $a \times L/30$  (mm) max. when 50 mN·m moment applied to the measuring point of shaft.

Where:


a= Constant Value as shown below

L= Distance between mounting surface and measuring point on the shaft


Size	Shaft material	Shape & Type		Shaft wobble (a)	Bending moment
14 mm square 18 mm square (Common)	Metal shaft	Without switch	1-shaft type	0.3 mm	50 mN·m
		With push switch		0.5 mm	
	Insulated shaft	With bushing	Single	0.5 mm	
		Snap-in		0.7 mm	

### 2. Nut Tightening Torque

When nut is tightened as specified below, unevenness of shaft rotation shall not occur.



Mounted State



Bushing Dia., etc.	Tightening Strength
M7 to M9	1.0 N·m

### ■ Minimum Quantity/Packing Unit


Please place an order by an integer multiple of the Quantity/Carton.

Type, Series	Part No.	Packaging	Quantity/ Carton	Minimum Quantity/ Packing Unit	Notes
18 mm Square Rotary Potentiometers (High Rotational Torque )	EVCX	Tray Pack	800 pcs.	80 pcs.	
39/20 mm Center Space Rotary Potentiometers	EWVYE EWVYK EWVYM	Tray Pack	250 pcs.	50 pcs.	
44/25 mm Center Space Rotary Potentiometers	EWVYG EWVYH EWVYJ EWVYL	Tray Pack	250 pcs.	50 pcs.	

\* : With bushing : L=L+7.5 mm

### 18 mm Square Rotary Potentiometers (High Rotational Torque)

Type: **EVCX**




#### ■ Features

- External dimensions: 18.0 mm×18.0 mm, Height 8.0 mm
- Output accuracy (±3 %)
- Potentiometers and encoders available in the same shape and dimensions

#### ■ Recommended Applications

- Function switching/adjusting for control panels of car air conditioners
- Signal input for monitors, audio/visual equipment


#### ■ Explanation of Part Numbers



#### ■ Specifications

Type	Top Adjustment type, with or without bushing	
Mechanical	Rotation Angle	280 °
	Rotation Torque	20 mN·m to 100 mN·m
	Detent Pitch	10 ° to 30 °
	Shaft Stopper Strength	0.8 N·m min.
Electrical	Nominal Total Resistance	5 kΩ to 100 kΩ (Tolerance ±20 %)
	Power Rating	0.05 W
	Potentiometers Type	Single, Dual
	Insulation Resistance	100 MΩ min. at 250 Vdc
	Dielectric Withstand Voltage	300 Vac for 1 minute
	Noise Level	100 mV max.
Endurance	Operating Life	15000 cycles min.
Minimum Quantity/ Packing Unit		80 pcs. (Tray Pack)
Quantity/ Carton		800 pcs.

#### ■ Dimensions in mm (not to scale)









## CONTENTS

	Page
■ Quick Selection Guide .....	EV16
■ Application Notes .....	EV17
■ Common Specifications .....	EV18
■ Minimum Quantity/Packing Unit .....	EV19
■ 6FF Square Trimmer Potentiometers (EVNCYA) .....	EV20
■ 6FE Square Trimmer Potentiometers (EVND) .....	EV22

### ■ Quick Selection Guide

Type, Series	Appearance	Part Numbers	Country of origin	Nominal Total Resistance	Taper	Rotation Angle	Page
6FF Square		EVNCYA	Malaysia	1 kΩ 2 kΩ 5 kΩ 10 kΩ 20 kΩ 50 kΩ 100 kΩ 200 kΩ 500 kΩ 1 MΩ	B	210 °	EV20
6FE Square		EVND	Malaysia				EV22

Country of origin : As of April 2013

### ■ ⚠ Application Notes

When using our Trimmer Potentiometers, please observe the following cautionary items to prevent dangerous accidents and deterioration of device performance.

#### 1. Prohibited items and notes in design stage

##### 1. Use within the rating


The affect of the ambient temperature on trimmer potentiometers cannot be ignored. When using under a high temperature, reduce the load according to the Power Derating Curve.

##### 2. Handling trimmer potentiometers

Do not apply excessive stress to a trimmer potentiometer after mounting to a PWB.

##### 3. Anodization

When dc is applied to a wiper (terminal 2), anodization may occur at the contact part of the wiper with the resistive element, resulting in abnormal resistance variation. When dc is used, to prevent anodization, the resistive element should be connected to the negative side and the wiper should be connected to the positive side, as shown in the figure at right.



##### 4. Recommended Circuit Configuration

It is recommended that you use the variable resistor for voltage adjustments. If it is used for current adjustments, then it may be influenced by the contact resistance between the resistor body and the slide, depending on the target circuit conditions. Conducting a test under actual operating conditions is highly recommended.

##### 5. Soldering conditions

##### 1) Perform soldering for a short time on a trimmer potentiometer. Extended soldering time, particularly under high temperature, may result in deterioration of the device.

The soldering temperature must be below 260°C, and soldering time within 5 seconds, and the load on a terminal must be less than 5 N.

##### 2) When performing solder dipping of PWB piercing type trimmer potentiometers, dry the flux sufficiently before solder dipping. (If the flux is not dried, it may contaminate the trimmer and affect characteristics.)

##### 3) Do not wash a trimmer potentiometer after solder dipping because flux may invade it, resulting in contact failure. Avoid a placement of a jumper cable where flux remains near the main body of a trimmer potentiometer.

#### 2. Cautionary notes regarding handling

##### 1. Storage

Do not store trimmer potentiometers under high temperatures and /or conditions of high humidity, or in a location where corrosive gas may be generated. In particular, when storing for long periods, do not unpack the trimmer potentiometers. Store in its original packaging.

##### 2. Operational direction

Since the stopper strength at the rear side is 35 mN·m, which is smaller than at the front side, operation for adjustment from the front side is recommended.

##### 3. Operating temperature range

Use in the range of -20 °C to +70 °C.

##### 4. Storage temperature

Store in the range of -40 °C to +75 °C.

#### 3. Prohibited items on fire and smoking

##### 1. Absolutely avoid use of a trimmer potentiometer beyond its rated range because doing so may cause a fire. If improperly used, the trimmer potentiometer may be operated out of its rated range, take proper measures such as current interruption using a protective circuit.

##### 2. The grade of nonflammability for resin used in trimmer potentiometers is "94HB," which is based on UL94 Standards (flammability test for plastic materials). Prohibit use in a location where a spreading fire may be generated or prepare against a spreading fire.

#### 4. For use in equipment for which safety is requested

Although care is taken to ensure trimmer potentiometer quality, short and open circuit are some problems that may occur. Design a circuit which places maximum emphasis on safety, review the affect of any single fault of a trimmer potentiometer in advance and perform virtually fail-safe design to ensure maximum safety by:

1. preparing a protective circuit or a protective device to improve system safety, and
2. preparing a redundant circuit to improve system safety so that the single fault of a trimmer potentiometer does not cause a dangerous situation.

For notes on use, the following sources were referred:

Technical report EIAJ RCR-2191A "Guideline of Notabilia for potentiometers for Use in Electronic Equipment" issued by the Japan Electronics and Information Technology Industries Association  
(Issued by March 2002)

Refer to this Technical Report for additional details.

#### 5. For actual use, be sure to refer to "Product Specifications for Information."

### Common Specifications

#### Electrical Specifications

##### 1. Nominal Total Resistance and Tolerance

Type	Nominal Total Resistance										Tolerance (%)	
	1 k	2 k	5 k	10 k	20 k	50 k	100 k	200 k	500 k	1 M		
6 mm Square Carbon Composition	○	○	○	○	○	○	○	○	○	○	○	±30


##### 2. Power Rating and Voltage Rating

###### 2-1. Power Rating

When the ambient temperature is within the following parameter (see table below), the maximum operating voltage which can be applied between terminal 1 and 3 is as follows. For potentiometers operated in ambient temperatures above 50 °C, Power Rating shall be derated in accordance with the figure below.

Type	Power Rating (W)	Max. Operating Voltage (V)	Ambient Temperature (°C)
6 mm Square Carbon Composition	0.1	$R \leq 500 \text{ k}\Omega$ : 50, $R > 500 \text{ k}\Omega$ : 25	50 max.

Power Derating Curve



###### 2-2. Voltage Rating


$$E = \sqrt{P \cdot R}$$

E=Voltage rating (V)  
 P=Power rating (W)  
 R=Nominal total resistance ( $\Omega$ )

The voltage rating should be maximum operating voltage when E shall exceed maximum operating voltage shown in the table.


### Packaging Specifications for Radial Taping

#### Drawing-out of taped products



Drawing-out can be from top or bottom of inner carton.

#### Pull-strength of taped products



- Taped products shall not be fully drawn-out from the tape when pulling off in direction A at 5.0 N max.
- Taped products shall not be drawn-out from the tape when pulling off in direction B at 1.0 N for 3 seconds.

### ■ Minimum Quantity/Packing Unit

Please place an order by an integer multiple of the Quantity/Carton.


Type, Series	Part No.	Packaging	Quantity/ Carton	Minimum Quantity/ Packing Unit	Notes
6FF Square Trimmer Potentiometers Type: EVNCYA	EVNCYA	Radial Taping (Reel Pack)	10000 pcs.	1000 pcs.	
6FE Square Trimmer Potentiometers Type: EVND	EVND2A EVND8A	Polyethylene Bag (Bulk)	5000 pcs.	500 pcs.	
	EVNDJA EVNDXA EVNDCA	Radial Taping (Reel Pack)	10000 pcs.	1000 pcs.	

### 6FF Square Trimmer Potentiometers

Type: **EVNCYA**

#### ■ Features


- Box-shaped, automatic mounting
- Radial taping supported
- High reliability (dustproof structure)



#### ■ Recommended Applications

- Audio Visual Equipment, Home Electrical Appliances

#### ■ Explanation of Part Numbers




#### ■ Specifications

Electrical Specifications	Nominal Total Resistance	1 kΩ, 2 kΩ, 5 kΩ, 10 kΩ, 20 kΩ, 50 kΩ, 100 kΩ, 200 kΩ, 500 kΩ, 1 MΩ
	Taper	B
	Rating	R ≤ 500 kΩ : 0.1 W 50 V (50 °C) R > 500 kΩ : 0.1 W 25 V (50 °C)
	Residual Resistance	1 kΩ ≤ R ≤ 2 kΩ : 60 Ω max. 2 kΩ < R ≤ 1 MΩ : 3 % max., or 200 Ω max. whichever smaller
Mechanical Specifications	Rotation Angle	210 ° ± 20 °
	Rotation Torque	2 mN·m to 25 mN·m
	Stopper Strength	Surface : 50 mN·m, reverse side : 35 mN·m
Endurance	Operating Life	100 cycles
	Resistance to Soldering Heat	240 °C to 280 °C : 5 s max., 280 °C to 300 °C : 3 s max.
	Resistance to Damp	After 350 hours : R ≤ 100 kΩ +15 % -0 %, : 100 kΩ < R ≤ 1 MΩ +20 % -0 %
	Endurance under Damp	After 350 hours : 1.5 h ON 0.5 h OFF : R ≤ 100 kΩ ± 15 %, : 100 kΩ < R ≤ 1 MΩ ± 20 %
	Endurance under High Temperature	70 °C ± 3 °C After 250 hours +5 %, -15 %
Minimum Quantity/Packing Unit		1000 pcs. Radial Taping (Reel Pack)
Quantity/Carton		10000 pcs.

Note : R=Nominal Total Resistance

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)




### 6FE Square Trimmer Potentiometers

Type: **EVND**

#### ■ Features


- Top-adjust or side-adjust available
- Radial taping supported
- High reliability (dustproof construction)



#### ■ Recommended Applications

- Audio Visual Equipment, Home Electrical Appliances

#### ■ Explanation of Part Numbers



#### ■ Specifications


Electrical Specifications	Nominal Total Resistance	1 k $\Omega$ , 2 k $\Omega$ , 5 k $\Omega$ , 10 k $\Omega$ , 20 k $\Omega$ , 50 k $\Omega$ , 100 k $\Omega$ , 200 k $\Omega$ , 500 k $\Omega$ , 1 M $\Omega$
	Taper	B
	Rating	R $\leq$ 500 k $\Omega$ : 0.1 W 50 V (50 °C) R>500 k $\Omega$ : 0.1 W 25 V (50 °C)
	Residual Resistance	1 k $\Omega$ $\leq$ R $\leq$ 2 k $\Omega$ : 60 $\Omega$ max. 2 k $\Omega$ <R $\leq$ 1 M $\Omega$ : 3 % max., or 200 $\Omega$ max. whichever smaller
Mechanical Specifications	Rotation Angle	210 ° $\pm$ 20 °
	Rotation Torque	2 mN·m to 25 mN·m
	Stopper Strength	Surface : 75 mN·m, reverse side : 35 mN·m
Endurance	Operating Life	100 cycles
	Resistance to Soldering Heat	240 °C to 280 °C : 5 s max., 280 °C to 300 °C : 3 s max.
	Resistance to Damp	After 350 hours : R $\leq$ 100 k $\Omega$ +15 % -0 %, : 100 k $\Omega$ <R $\leq$ 1 M $\Omega$ +20 % -0 %
	Endurance under Damp	After 350 hours : 1.5 h ON 0.5 h OFF : R $\leq$ 100 k $\Omega$ $\pm$ 15 %, : 100 k $\Omega$ <R $\leq$ 1 M $\Omega$ $\pm$ 20 %
	Endurance under High Temperature	70 °C $\pm$ 3 °C After 250 hours +5 %, -15 %
Minimum Quantity/Packing Unit		EVND2A, EVND8A : 500 pcs. Polyethylene Bag (Bulk) EVNDJA, EVNDXA, EVNDCA : 1000 pcs. Radial Taping (Reel Pack)
Quantity/Carton		EVND2A, EVND8A : 5000 pcs. EVNDJA, EVNDXA, EVNDCA : 10000 pcs.

Note : R=Nominal Total Resistance


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)

● Side-adjust ..... EVND2A

<p>No. 1</p> 	 <p style="text-align: center;">PWB mounting hole for reference (Pitch tolerance: <math>\pm 0.1</math>) View from mounting side</p> <table border="1" style="width: 100%; margin-top: 10px;"> <tr> <td style="width: 50%;">Knob color</td> <td style="width: 50%;">Orange yellow</td> </tr> </table>	Knob color	Orange yellow
Knob color	Orange yellow		

● Top-adjust ..... EVND8A

<p>No. 2</p> 	 <p style="text-align: center;">PWB mounting hole for reference (Pitch tolerance: <math>\pm 0.1</math>) View from mounting side</p> <table border="1" style="width: 100%; margin-top: 10px;"> <tr> <td style="width: 50%;">Knob color</td> <td style="width: 50%;">Orange yellow</td> </tr> </table>	Knob color	Orange yellow
Knob color	Orange yellow		



**CONTENTS**

	Page
■ Quick Selection Guide .....	EV26
■ Checklist Before Inquiry .....	EV27
■ Application Notes .....	EV28
■ Minimum Quantity/Packing Unit .....	EV29
■ 10 mm GS Sensors (EVWAE, EVWAD) .....	EV30
■ Linear Position Sensors (EVAW7) .....	EV32
■ 15 mm Position Sensors (EVWBE) .....	EV34

### ■ Quick Selection Guide

Type, Series	Appearance	Part Numbers	Country of origin	Total Resistance	Linearity	Life	Page
10 mm GS Sensors		EVWAE EVWAD	Japan	5 k $\Omega$ $\pm$ 30 % 10 k $\Omega$ $\pm$ 30 %	$\pm$ 2 %	1000000 cycles	EV30
Linear Position Sensors		EVAW7	Malaysia	4.7 k $\Omega$ $\pm$ 30 % 10 k $\Omega$ $\pm$ 30 %	$\pm$ 1 % $\pm$ 2 %	10000 cycles	EV32
15 mm Position Sensors		EVWBE	Vietnam	10.5 k $\Omega$ $\pm$ 30 % 21 k $\Omega$ $\pm$ 30 %	$\pm$ 2 %	100000 cycles	EV34

Country of origin : As of April 2013

## ■ Checklist Before Inquiry

When specifying Position Sensors, please take advantage of our standard products for better price and delivery. Please provide the following items before ordering.

Checklist					
Common	C-1	Inquiry purpose	New use, Modification, Others( )		
	C-2	Modification	Current supplier		
			Current part No.		
			Purpose		
	C-3	Application	Equipment		
			Environment	Indoor/Outdoor use, Stationary/Portable set, High humidity, SO <sub>2</sub> , NaCl	
Temperature			( °C) to ( °C)		
C-4	Mounting	Method	Manual, Automatic		
C-5	Soldering	Method	Manual soldering, Flow soldering		
		Conditions	Temp. ( °C), Time ( s), Dipping times( )		
Electrical	E-1	Conditions	Current ac, dc		
	E-2	Resistance	Total value/Tolerance ( Ω) / ±20 %, ±30 %, Others (± %)		
	E-3	Taper	Taper	B	
			Linearity	1 %, 0.5 %, Others (± %)	
			Hysteresis	( %)	
E-4	Other requirements				
Shapes/ Dimensions	M-1	Shape	Type	Rotary	Slide
			Size	10.0 mm, 15 mm	8.0 mm, 9.0 mm
	M-2	Shaft	Shape		
	M-3	Mounting	Type	PWB Soldering, Screw	
M-4	Terminals	Type	PWB		
Others	L-1	Special requirements for endurance			
	L-2	Other questionnaires			

Notes:

1. When you specify custom types (custom-made), new tooling and jigs, and/or equipment may be required. It will be necessary to confirm your estimates of quantity and development schedule as accurately as possible.
2. Please inform us if you designate your own part number.

\* Previous notations for potentiometer shape "Stand-up type" (Shaft is parallel to PWB.) and "Lay-down type" (Shaft is vertical to PWB.) – have been changed in this edition to "Horizontal type" or "Side-adjust type" (Shaft or knob is parallel to PWB.) and "Vertical type" or "Top-adjust type" (Shaft or knob is vertical to PWB.).


## ■ Application Notes

When using our Position Sensors, please observe the following cautionary items to prevent dangerous accidents and deterioration of device performance.

### 1. Prohibited items and notes in design stage

#### 1. Soldering conditions

- 1) Soldering must be performed to the lead of the terminals. Do not solder on the center (eyelet part) of the terminals.



- 2) Perform soldering only one time. When a product for which soldering has been completed is removed from PWB by soldering iron, etc., the product shall not be used again.
- 3) Do not wash a position sensor after soldering because flux may invade the position sensor, resulting in contact failure. Avoid use of jumper cables near the position sensors because flux may get attached to them.
- 4) Any soldering iron used must be 20 W to 30 W, the temperature must be less than 300 °C, and within 3 seconds.

### 2. Prohibited items and notes on handling

#### 1. Operating temperature range

Use in the range of -10 °C to +70 °C

#### 2. Storage temperature

Store in the range of -40 °C to +70 °C

#### 3. Storage conditions

Do not store the position sensors under high temperatures and/or high humidity, or in a location where corrosive gas may be present. Store the mounted sensors at a room temperature and humidity in its original packaging. Use them within 6 months. Check the date of manufacture on the package box and apply the "first-in-first-out" rule. If unpacked position sensors must be stored as inventory, store them in a polyethylene bag to keep out air.

### 3. Cautionary notes regarding fire and smoking

1. Absolutely avoid use of a position sensor beyond its rated range, it could cause a fire and abnormality. Take proper measures such as current interruption using a protective circuit.
2. The grade of nonflammability for resin used in position sensors is "94HB," which is based on UL94 Standards (flammability test for plastic materials). Prohibit use in a location where a spreading fire may be generated or prepare against a spreading fire.

### 4. For use in equipment requiring high degrees of safety

Although care is taken to ensure position sensor quality, short circuits, or open circuits are some problems that may occur. To design a circuit which places maximum emphasis on safety, review the affect of any single fault of a position sensor in advance and perform virtually fail-safe design to ensure maximum safety by:

1. preparing a protective circuit or a protective device to improve system safety, and
2. preparing a redundant circuit to improve system safety so that the single fault of a position sensor does not cause a dangerous situation.

### 5. For actual use, be sure to refer to "Product Specifications for additional information."

## ■ Minimum Quantity/Packing Unit

Please place an order by an integer multiple of the Quantity/Carton.

Type, Series	Part No.	Packaging	Quantity/ Carton	Minimum Quantity/ Packing Unit	Notes
10 mm GS Sensors	EVWAE EVWAD	Embossed Taping (Reel Pack)	6000 pcs.	1500 pcs.	
Linear Position Sensors	EVAW7	Tray Pack	2000 pcs. 3000 pcs.	200 pcs. 300 pcs.	(8 mm Type) (9 mm Type)
15 mm Position Sensors	EVWBE		500 pcs.	50 pcs.	

## 10 mm GS Sensors

Type: **EVWAE/EVWAD**

Low profile, long life sensor, which is suitable for detecting the angles of rotating axes.




### ■ Features

- Low profile (H=2.2 mm),  
Shaft hole diameters of up to 4 mm are available.
- Long operation life: 1 million operation cycles.
- A wide electrical output angle of a maximum 343 °,  
ready for SMDs

### ■ Recommended Applications

- Detection of robot joint angles
- Detection of air conditioner damper angles
- Detection of various control unit angles


### ■ Explanation of Part Numbers



### ■ Specifications

Mechanical	Rating	0.05 W, 5V
	Operating Force	3 mN·m max.
Electrical	Total Resistance	5 kΩ±30 %, 10 kΩ±30 %
	Linearity	±2 % max.
Endurance	Operating Life	1000000 cycles min. (operation Angle ±30 °)
Minimum Quantity/Packing Unit		1500 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		6000 pcs.


### ■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## Linear Position Sensors (for reference only)

Type: **EVAW7**




### ■ Features

- A wide variety of operation strokes
- Long life and high resolution

### ■ Recommended Applications

- Car headlight angle detection sensor

### ■ Explanation Part Numbers





### ■ Specifications

		EVAW7	
Mechanical	Stroke	9.0 mm±0.5 mm	8.0 mm±0.5 mm
	Operating Force	2 N max.	1 N max.
Electrical	Linearity	±2 %	±1 %
	Total Resistance	10 kΩ±30 %	4.7 kΩ±30 %
	Voltage Rating	5 Vdc max.	12 Vdc max.
	Taper	B	
Endurance	Operating Life	10000 cycles min.	10000 cycles min.
Minimum Quantity/Packing Unit		300 pcs. (Tray Pack)	200 pcs. (Tray Pack)
Quantity/Carton		3000 pcs.	2000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 15 mm Position Sensors (for reference only)

Type: **EVWBE**

### ■ Features


- Simple dustproof structure achieved by insert molding of the resistor element
- Connector terminals
- Long life and high resolution



### ■ Recommended Applications

- Temperature and air flow and mode control for automotive climate control systems


### ■ Explanation Part Numbers



### ■ Specifications

		EVWBE1	EVWBE2	EVWBE3
Mechanical	Rotation Angle	Endless		
	Rotation Torque	15 m·Nm max.		
Electrical	Voltage Rating	5 Vdc		
	Total Resistance	10.5 kΩ±30 %	10.5 kΩ±30 %	21 kΩ±30 %
	Rotation Angle	100 °	150 °	250 °
	Taper	B		
	Linearity	±2 % max.		
Endurance	Operating Life	100000 cycles min.		
Minimum Quantity/Packing Unit		50 pcs. (Tray Pack)		
Quantity/Carton		500 pcs.		

### ■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## CONTENTS

	Page
■ Quick Selection Guide .....	EV36
■ Checklist Before Inquiry .....	EV37
■ Application Notes .....	EV38
■ Minimum Quantity/Packing Unit .....	EV39
■ 10 mm Square GS Encoders (EVQVX) .....	EV40
■ 10 mm Square SMD Encoders (EVQVV) .....	EV42
■ Edge Drive Jog Encoders (EVQWK) .....	EV44
■ 11 mm Square GS Encoders (EVER, EVEU, EVEV, EVEY) .....	EV46
■ 12 mm Square GS Encoders (EVEG, EVEH, EVEK, EVEL) .....	EV49
■ 12 mm Square GS Encoders with Push-on Switch (EVEJB) .....	EV52
■ 16 mm Square Encoders (EVEP/EVEQ) .....	EV54
■ 18 mm Square Encoders (High Rotational Torque / EVQW) .....	EV56
■ 20/12 mm Center Space Encoders (EVQV6) .....	EV57
■ 27/17 mm Center Space Encoders (EVQWF, EVQVP) .....	EV58
■ 27/18 mm Center Space Encoders (EVQV5) .....	EV59
■ 38/25 mm Center Space Encoders (EVQVN) .....	EV60
■ 60/40 mm Center Space Encoders (EVQV0) .....	EV61

## ■ Quick Selection Guide

Type, Series	Appearance	Part Numbers	Country of origin	Resolution	Detents	Operating Life	Page
10 mm Square GS		EVQVX	China	12 Pulses/360 °	24 Points	200000 Cycles	EV40
10 mm Square SMD		EVQVV	Japan	3 Pulses/360 °	Without detents	70000 Cycles	EV42
Edge Drive Jog		EVQWK	Japan	15 Pulses/360 °	15 Points	100000 Cycles	EV44
11 mm Square GS		EVER EVEU EVEV EVEY	Japan Vietnam	8, 12, 15, 16 Pulses/360 °	16 Points, 24 Points, 30 Points, 32 Points	30000 Cycles	EV46
12 mm Square GS		EVEG EVEH EVEK EVEL	Malaysia	12, 20, 24 Pulses/360 °	12 Points, 20 Points, 24 Points, Without detents	30000 Cycles (Heavy-rotation torque 15000 cycles)	EV49
12 mm square GS (with Push-on Switch)		EVEJB	Vietnam	20 Pulses/360 °	20 Points	30000 Cycles	EV52
16 mm Square		EVEP EVEQ	Japan Vietnam	8, 16 Pulses/360 °	16 Points, 32 Points	1000000 Cycles 30000 Cycles	EV54
18 mm square (High Rotational Torque)		EVQW	Japan	Absolute 5 bit	Custom	15000 Cycles	EV56
20/12 mm Center Space		EVQV6	Vietnam	9 Pulses/360 °	18 Points	30000 Cycles	EV57
27/17 mm Center Space		EVQWF EVQVP	Japan	9, 15 Pulses/360 °	18 Points, 30 Points	30000 Cycles	EV58
27/18 mm Center Space		EVQV5	Vietnam	9, 15 Pulses/360 °	18 Points, 30 Points	30000 Cycles	EV59
38/25 mm Center Space		EVQVN	Malaysia	15 Pulses/360 °	30 Points	30000 Cycles	EV60
60/40 mm Center Space		EVQV0	Japan	15 Pulses/360 °	30 Points	30000 Cycles	EV61

Country of origin : As of April 2013

## ■ Checklist Before Inquiry

When specifying Encoders, please take advantage of our standard products for better price and delivery. Please provide the following items before ordering.

Checklist				
Common	C-1	Inquiry purpose		New use, Modification, Others( )
	C-2	Modification	Current supplier	
			Current Part No.	
			Purpose	
	C-3	Application	Equipment	
			Environment	Indoor/Outdoor use, Stationary/Portable set, High humidity, SO <sub>2</sub> , NaCl
			Temperature	( °C) to ( °C)
			Operation	General use, Edge drive, Low torque, High torque
	C-4	Adjustment	Method	Manual, Automatic
	C-5	Mounting	Method	Manual, Automatic
Mounter			Panasert(Model: ), Other mounter(Maker/Model: ),Parts feeder Magazine	
C-6	Soldering	Method	Manual soldering, Flow soldering, Reflow soldering	
		Conditions	Temp. ( °C), Time ( s), Dipping times( )	
		Washing	Machine, Soaking, Applied solvent( )	
Electrical	E-1	Application	Circuit	Volume, Tone, Balance, Circuit regulation, Others( )
	E-2	Conditions	Rating	Max. operating power( W), Operating voltage( V)
			Applied current	Small current use, Applying current( mA)
	E-3	Encoders	Output Signal	2 phase system(Phase A or B), Others( )
			Resolution	8, 9, 12, 15, 16, 20, 24, Pulse, Others/360 °
E-4	Other requirements			
Shapes/Dimensions	M-1	Shape	Type	Rotary, Others( )
			Size	10.0 mm, 11.0 mm, 12.0 mm, 16.0 mm, 18 mm, Others( )
			Shape*	Side Adjustment, Top Adjustment
	M-2	Shaft	Shape	Metal Shaft(F type, S type, P type), Insulated Shaft(F type, S type)
	M-3	Mounting	Type	Bushing, Soldering
			(Type with bushing)	Screw dia.: M7, M9, Screw pitch: 0.75 mm, Bushing length: 5.0 mm, 7.0 mm, 10.0 mm
	M-4	Terminals	Type	Solder lug, PWB
			(PWB terminals)	Length from mounting surface( mm), Layout pattern( )
	M-5	Additional function		
	M-6	Switch	Type	Push-On, Others( )
Poles & Throws			1 pole 1 throw	
Rating			Voltage:( V), Current:( A), Inrush current:( A)	
Terminal Type			PWB terminal, Others( )	
M-7	Detents	16 points, 18 points, 20 points, 24 points, 30 points, 32 points, Others( point)		
Others	L-1	Special requirements for endurance		
	L-2	Other questionnaires		

### Notes:

- When you specify custom types (custom-made), new tooling and jigs, and/or equipment may be required. It will be necessary to confirm your estimates of quantity and development schedule as accurately as possible.
- Please inform us if you designate your own part number.

\* Previous notations for potentiometer shape "Stand-up type" (Shaft is parallel to PWB.) and "Lay-down type" (Shaft is vertical to PWB.) – have been changed in this edition to "Horizontal type" or "Side-adjust type" (Shaft or knob is parallel to PWB.) and "Vertical type" or "Top-adjust type" (Shaft or knob is vertical to PWB.).

## ■ Application Notes

When using our Encoders, please observe the following cautionary items to prevent dangerous accidents and deterioration of performance.

### 1. Prohibited items and notes in design stage

#### 1. Soldering conditions

When performing solder dipping, check the soldering conditions according to the Individual “Product Specifications,” because the conditions vary from product to product.

Do not wash an encoder after solder dipping because flux may invade the encoder, resulting in contact failure. Avoid use of jumper cables near the encoders because flux may get to them.

#### 2. Shaft rotation wobble

If the shaft is long, the rotation wobble increases in proportion to its length. To secure the quality of a set, we recommend use of the types with a bushing.

#### 3. Operating temperature conditions

Tactile feeling in operation is given serious consideration, and rotation torque increases under low temperatures (below  $-10\text{ }^{\circ}\text{C}$ ) depending on the product. If an encoder is expected to be used under low temperatures, specify this in advance.

### 2. Prohibited items and notes on handling

#### 1. Chemical resistance

Before using a potentiometer with an insulated shaft, be sure to check the reactivity of the shaft with any chemicals to be used.

#### 2. Storage conditions

Do not store the encoders under high temperatures and/or high humidity, or in a location where corrosive gas may be generated. Store the encoders at room temperature and room humidity in a packed condition. Use them within a maximum of 6 months. Check the date of manufacture on the package box and apply the “first-in-first-out” rule. If unpacked encoders must be stored as inventory, store them in a polyethylene bag to keep out air.

### 3. Prohibited items on fire and smoking

#### 1. Absolutely avoid use of an encoder beyond its rated range because it may cause a fire.

If misuse or abnormal use may result in conditions in which the encoder is used out of its rated range, take proper measures such as current interruption using a protective circuit.

#### 2. The grade of nonflammability for resin used in encoders is “94HB,” which is based on UL94 Standards (flammability test for plastic materials). Prohibit use in a location where a spreading fire may be generated or prepare against a spreading fire.

#### 4. For use in equipment for which safety is requested

Although care is taken to ensure encoder quality, inferior characteristics, short circuits, and open circuits are some problems that might be generated. To design a set which places maximum emphasis on safety, review the affect of any single fault of an encoder in advance and perform virtually fail-safe design to ensure maximum safety by:

1. preparing a protective circuit or a protective device to improve system safety, and
2. preparing a redundant circuit to improve system safety so that the single fault of an encoder does not cause a dangerous situation.

#### 5. For actual use, be sure to refer to “Product Specifications for information.”

### ■ Minimum Quantity/Packing Unit

Please place an order by an integer multiple of the Quantity/Carton.

Type, Series	Part No.	Packaging	Quantity/ Carton	Minimum Quantity/ Packing Unit	Notes
10 mm Square GS Encoders	EVQVX	Tray Pack	3000 pcs.	300 pcs.	
10 mm Square SMD Encoders	EVQVV	Embossed Taping (Reel Pack)	6000 pcs.	1500 pcs.	
Edge Drive Jog Encoders	EVQWK	Embossed Taping (Reel Pack)	1600 pcs.	400 pcs.	
		Tray Pack	1000 pcs.	100 pcs.	
11 mm Square GS Encoders	EVER EVEU	Tray Pack	250 pcs. or 300 pcs.	50 pcs.	
	EVEV EVEY		500 pcs.	100 pcs.	
12 mm Square GS Encoders	EVEG EVEH EVEK EVEL	Polyethylene Bag (Bulk)	1000 pcs.	100 pcs.	L≤25.0 mm
			2000 pcs.	200 pcs.	L>26.0 mm
12 mm Square GS Encoders (with Push-on Switch)	EVEJB	Polyethylene Bag (Bulk)	500 pcs.	100 pcs.	
16 mm Square Encoders	EVEP EVEQ	Tray Pack	200 pcs.	50 pcs.	
18 mm Square Encoders (High Rotational Torque)	EVQW	Tray Pack	800 pcs.	80 pcs.	
20/12 mm Center Space Encoders	EVQV6	Tray Pack	2000 pcs.	100 pcs.	
27/17 mm Center Space Encoders	EVQWF EVQVP	Tray Pack	800 pcs.	80 pcs.	
27/18 mm Center Space Encoders	EVQV5	Tray Pack	1600 pcs.	80 pcs.	
38/25 mm Center Space Encoders	EVQVN	Tray Pack	250 pcs.	50 pcs.	
60/40 mm Center Space Encoders	EVQV0	Tray Pack	100 pcs.	20 pcs.	

## 10 mm Square GS Encoders

Type: **EVQVX**




### ■ Features

- Compact and thin design (Body thickness: 4 mm)
- Good rotational feel
- Supports vertical self-standing mounting onto printed circuit boards

### ■ Recommended Applications

- Computer peripherals (Mouse)
- Information & communications equipment
- For input devices of measuring instruments and various electronic equipment

### ■ Explanation of Part Numbers



### ■ Specifications



Mechanical	Rotation Angle	360 ° (Endless)
	Rotation Torque	1 mN·m to 10 mN·m
	Detents	24 points
Electrical	Output Signals	Phase A and B
	Resolution	12 pulses/360 °
	Rating	1 mA 10 Vdc (at each bit)
	Contact Resistance	10 Ω max.
	Insulation Resistance	50 MΩ min. (at 50 Vdc)
	Dielectric Withstanding Voltage	50 Vac for 1 minute
	Bouncing	5 ms max.
Endurance	Rotation Life	200000 cycles min.
Minimum Quantity/Packing Unit		300 pcs. (Tray Pack)
Quantity/Carton		3000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.


00 Oct. 2012

■ Dimensions in mm (not to scale)

EVQVX




Shaft hole shape and dimension




--- Leg position

PWB mounting hole for reference (Tolerance : ±0.1)  
(View from mounting side)  
(PWB thickness t=1.6)

■ Phase Difference



■ Test Circuit Diagram



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 10 mm Square SMD Encoders

Type: **EVQVV**




### ■ Features

- Low profile(H=2.2 mm),  
Shaft hole diameters of up to 4 mm.
- Light operation with a rotation torque of 2 mN·m
- Automatic mounting and SMDs.

### ■ Recommended Applications

- Air conditioning temperature controls
- Input of operation units
- Computer peripherals

### ■ Explanation of Part Numbers



### ■ Specifications

Mechanical	Rotation Angle	360 ° (Endless)
	Rotation Torque	2 mN·m max.
Electrical	Output Signals	Phase A and B
	Resolution	3 pulses/360 °
	Rating	1 mA 10 Vdc (at each bit)
	Contact Resistance	10 Ω max.
	Insulation Resistance	50 MΩ min. (at 50 Vdc)
	Dielectric Withstanding Voltage	50 Vac for 1 minute
	Bouncing	5 ms max.
Endurance	Rotation Life	70000 cycles min.
Minimum Quantity/Packing Unit		1500 pcs. Embossed Taping (Reel Pack)
Quantity/Carton		6000 pcs.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012



## Edge Drive Jog Encoders

Type: **EVQWK**




### ■ Features

- Tactile rotary operation and push operation
- Reflow soldering type available
- Anti-electrostatic measures available

### ■ Recommended Applications

- Memory paging and transmitting
- Menu selection and input for Portable Electronic Equipment

### ■ Explanation of Part Numbers





### ■ Specifications

Mechanical	Encoder	Detents	15 points
		Rotation Torque	1 mN·m to 10 mN·m
	Push-on Switch	Travel	0.3 mm (Thin-Type : 0.2 mm)
		Operating Force	4.5 N±1.5 N
Electrical	Encoder	Resolution	15 pulses/360 °
		Output Signals	2-Phases (A and B)
		Contact Resistance	1 Ω max.
	Push-on Switch	Contact Resistance	100 mΩ
Endurance	Encoder	Rotation Life	100000 cycles min.
	Push-on Switch	Operating Life	
Minimum Quantity/Packing Unit			100 pcs. (Tray Pack)
			400 pcs. Embossed Taping (Reel Pack)
Quantity/Carton			1000 pcs.
			1600 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## ■ Dimensions in mm (not to scale)




## 11 mm Square GS Encoders

Type: **EVER/EVEU/EVEV/EVEY**

### ■ Features


- Low Profile : Reflow Type 3.5 mm,  
Wave Soldering Type 4 mm
- Minimized shaft wobble type is also available
- The reflow type allows the product to be automatically mounted and reflow-soldered



### ■ Recommended Applications

- Car audio, car navigation, car air conditioners

### ■ Explanation of Part Numbers



### ■ Specifications

		EVER (Reflow Type)	EVEV (Wave Soldering Type)	EVEU (Minimized Shaft Wobble Reflow Type)	EVEY (Minimized Shaft Wobble Wave Soldering Type)
Mechanical	Rotation Angle	360 ° (Endless)			
	Shaft Pull/Push Strength	100 N min.			
	Shaft Wobble	0.6xL/30 (mm) max.		0.35xL/30 (mm) max.	
	Rotation Torque	3 mN·m to 20 mN·m			
	Detents	16 points, 24 points, 30 points, 32 points			
	Shaft Length Range	L <sub>1</sub> =15 to 20 mm	L <sub>1</sub> =15 to 30 mm	L <sub>1</sub> =16 to 20 mm	
Electrical	Output Signals	Phase A and B			
	Resolution	8, 12, 15, 16 pulses/360 °			
	Rating	1 mA 10 Vdc (at each bit)			
	Contact Resistance	1 Ω max.			
	Chattering	3 ms max.			
	Insulation Resistance	50 MΩ min. (at 250 Vdc)			
	Dielectric Withstanding Voltage	300 Vac for 1 minute			
	Bouncing	5 ms max.			
Switch Part	Type	SPST Push-on			
	Rating	20 mA 16 Vdc			
	Contact Resistance	100 mΩ max.			
	Operating Force	0.4 mm travel type : 3 N, 4 N , 6 N 1.5 mm travel type : 2.5 N, 4 N , 5 N			
	Travel	0.4 mm, 1.5 mm			
Endurance	Rotation Life (Encoder)	30000 cycles min.			
	Operating Life (Switch)	30000 cycles min.			
Minimum Quantity/Packing Unit		50 pcs. (Tray Pack)	100 pcs. (Tray Pack)	50 pcs. (Tray Pack)	100 pcs. (Tray Pack)
Quantity/Carton		250 pcs. or 300 pcs.	500 pcs.	250 pcs. or 300 pcs.	500 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## ■ Dimensions in mm (not to scale)

### No. 1

**EVER**  
(Reflow Type)

Mounting Surface

Shaft shape and dimension

Switch circuit diagram.  
S.P.S.T.

COM — S — S  
(Notice) Commonness of encoder.

Bushing length	L <sup>1</sup>	(L <sup>2</sup> )	
B	5.0 mm	15.0 mm to 17.0 mm	11.5 mm to 13.5 mm
	7.0 mm	17.0 mm to 20.0 mm	13.5 mm to 16.5 mm

\* The position changes with Resolution pulse

### No. 2

**EVEU**  
(Minimized Shaft Wobble Reflow Type)

Mounting Surface

Material: Zinc alloy for die casting  
Shaft shape and dimension

Switch circuit diagram.  
S.P.S.T.

COM — S — S  
(Notice) Commonness of encoder.

L <sup>1</sup>	(L <sup>2</sup> )	(L <sup>3</sup> )
16.0 mm to 20.0 mm	12.5 mm to 16.5 mm	6.5 mm to 10.5 mm

\* The position changes with Resolution pulse

### No. 3

**EVEV**  
(Wave Soldering Type)

Mounting Surface

Shaft shape and dimension

Switch circuit diagram.  
S.P.S.T.

COM — S — S  
(Notice) Commonness of encoder.

Bushing length	L <sup>1</sup>	(L <sup>2</sup> )	
B	5.0 mm	15.0 mm to 17.0 mm	11.0 mm to 13.0 mm
	7.0 mm	17.0 mm to 30.0 mm	13.0 mm to 26.0 mm

\* The position changes with Resolution pulse

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

- EV47 -



## 12 mm Square GS Encoders


Type: **EVEG/EVEH/EVEK/EVEL**

### ■ Features


- Lineup of high rotation-torque-type (50 mN·m)
- A wide range of standard products

### ■ Recommended Applications

- Volume for audio/visual equipment
- Tuner for communication units
- Mode selection for measurement instruments



### ■ Explanation of Part Numbers



### ■ Product Chart

Torque type	Combination of Bushing	Thickness	Height					Detents (Resolution/Pulses)			
			15.0 mm	17.5 mm	20.0 mm	22.5 mm	25.0 mm	30.0 mm	12 points (12 pulses)	24 points (24 pulses)	Without detents (12 pulses, 24 pulses)
Heavy-rotation torque (10 mN·m to 50 mN·m)	Die-cast (7.0,12.0 mm)	5.5 mm					○	○			○
	Sleeve (7.0,12.0 mm)	5.5 mm					○	○			○
Standard type (3 mN·m to 20 mN·m)	Barling (5.0 mm)	5.0 mm		○	○	○	○		○	○	○
	Barling (1.6 mm)	5.0 mm	○						○	○	○
	Die-cast (7.0 mm)	5.5 mm			○	○	○		○	○	○
	Sleeve (7.0 mm)	5.5 mm			○	○	○		○	○	○


### ■ Specifications

Mechanical	Rotation Angle		360 ° (Endless)	
	Shaft Pull/Push Strength		80 N min.	
	Shaft Wobble		0.7xL/30 mm max.	
	Rotation Torque	Standard Type	3 mN·m to 20 mN·m	
		Heavy Rotation Torque	10 mN·m to 50 mN·m	
Detents		12 points, 20 points, 24 points, without detents (Heavy rotation-torque without detents)		
Electrical	Output Signals		Phase A and B	
	Resolution		12, 20, 24 pulses/360 °	
	Rating		1 mA 5 Vdc, 1 mA 10 Vdc	
	Contact Resistance		1 Ω max.	
	Chattering		2 ms max.	
	Insulation Resistance		10 MΩ min. (at 50 Vdc)	
	Dielectric Withstanding Voltage		50 Vac for 1 minute	
	Bouncing		5 ms max.	
Endurance	Operating Life	Standard Type	30000 cycles min.	
		Heavy Rotation Torque	15000 cycles min.	
	Operating Temperature		-10 °C to +60 °C	
Storage Temperature		-40 °C to +85 °C		
Minimum Quantity/Packing Unit			L≤25.0 mm	100 pcs. Polyethylene Bag(Bulk)
Quantity/Carton			L≤25.0 mm	1000 pcs.
			L>26.0 mm	200 pcs. Polyethylene Bag(Bulk)
			L>26.0 mm	2000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.


■ Dimensions in mm (not to scale)

- High rotation-torque / Bushing Type with Sleeve ..... Without detents : EVEKE2




- Standard rotation-torque / Bushing Type with Barling ..... Without detents : EVEGA2

With detents : EVEGA1




- Standard rotation-torque / Bushing Type with Die-cast ..... Without detents : EVEGC2

With detents : EVEGC1




## ■ Shaft Trims and Dimensions in mm

Bushing Type	Dimensions			
	L <sub>1</sub>	L <sub>2</sub>	L <sub>3</sub>	Corner Cut
Barling	15.0 mm	1.6 mm	7.0 mm	1.5 mm
	17.5 mm	5.0 mm	5.0 mm	1.5 mm
	20.0 mm	5.0 mm	7.0 mm	1.5 mm
	22.5 mm	5.0 mm	7.0 mm	1.5 mm
	25.0 mm	5.0 mm	12.0 mm	1.5 mm
Sleeve	20.0 mm	7.0 mm	7.0 mm	1.5 mm
	22.5 mm	7.0 mm	7.0 mm	1.5 mm
	25.0 mm	7.0 mm	12.0 mm	1.5 mm
	*30.0 mm	7.0 mm	*12.0 mm	*1.5 mm
Die-cast	20.0 mm	7.0 mm	7.0 mm	1.5 mm
	22.5 mm	7.0 mm	7.0 mm	1.5 mm
	25.0 mm	7.0 mm	12.0 mm	1.5 mm
	*30.0 mm	12.0 mm	*12.0 mm	*1.5 mm




\*High-rotation torque

## ■ Phase Difference




## ■ Test Circuit Diagram



## 12 mm Square GS Encoders with Push-on Switch

Type: **EVEJB**




### ■ Features

- Thin type encoder with vertical push-on switch
- Insulated shaft or metal shaft types are available

### ■ Recommended Applications

- Volume and tone control for audio/visual and car audio equipment
- Tuner for communication units
- Mode selection for measurement instruments

### ■ Explanation of Part Numbers




### ■ Specifications

Mechanical	Rotation Angle		360 ° (Endless)
	Shaft Pull/Push Strength		80 N min.
	Shaft Wobble		0.7xL/30 mm max.
	Rotation Torque		3 mN·m to 20 mN·m
	Detents		20 points
Electrical	Output Signals		Phase A and B
	Resolution		20 pulses/360 °
	Rating		1 mA 10 Vdc
	Contact Resistance		1 Ω max.
	Chattering		2 ms max.
	Insulation Resistance		10 MΩ min. (at 50 Vdc)
	Dielectric Withstanding Voltage		50 Vac for 1 minute
	Bouncing		5 ms max.
Switch Part	Type		SPST Push-on
	Rating		20 mA 16 Vdc
	Contact Resistance		100 mΩ max.
	Operating Force		3 N, 6 N
	Travel		0.4 mm
Endurance	Operating Life	Encoder	30000 cycles min.
		Switch	15000 cycles min.
	Operating Temperature		-10 °C to +60 °C
	Storage Temperature		-40 °C to +85 °C
Minimum Quantity/Packing Unit			100 pcs. Polyethylene Bag(Bulk)
Quantity/Carton			500 pcs.


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

### ■ Dimensions in mm (not to scale)

- Standard rotation-torque / Bushing Type with Sleeve / with Switches .....With detents : EVEJBB



- Standard rotation-torque / Bushing Type with Sleeve / with Switches .....With detents : EVEJBE




### ■ Shaft Trims and Dimensions in mm


Shaft Type	Dimensions			
	$L_1$	$L_2$	$L_3$	Corner Cut
Metal	15.0 mm	4.0 mm	5.0 mm	0.5 mm
Insulated	20.0 mm	7.0 mm	6.0 mm	1.5 mm
	25.0 mm	9.0 mm	10.0 mm	1.5 mm

Diagram of shaft trim dimensions showing  $L_1$ ,  $L_2$ ,  $L_3$ ,  $4.5$ , and  $6.0$  with a "Corner Cut".

### ■ Phase Difference



### ■ Test Circuit Diagram



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 16 mm Square Encoders

Type: **EVEP/EVEQ**




### ■ Features

- Good operational feel
- Long life due to high click torque
- Shaft wobble : 0.1 mm max.

### ■ Recommended Applications

- Centralized control of automotive audio equipment, navigation systems, and air conditioners.

### ■ Explanation of Part Numbers




### ■ Specifications

		EVEP	EVEQ
Mechanical	Rotation Angle	360 ° (Endless)	
	Shaft Pull/Push Strength	100 N min.	
	Shaft Wobble	0.1 mm max.(Length form mounting surface : 21.5 mm) ( 50 mN·m is applied on the point 2 mm from the shaft tip)	
	Rotation Torque	25 mN·m max.	
	Detents	16 points	32 points
Electrical	Output Signals	Phase A and B	
	Resolution	8 pulses/ 360 °	16 pulses/ 360 °
	Rating	1 mA 10 Vdc (at each bit)	
	Contact Resistance	1 Ω max.	
	Chattering	5 ms max.	
	Insulation Resistance	50 MΩ min. (at 250 Vdc)	
	Dielectric Withstanding Voltage	300 Vac for 1 minute	
Switch Part	Bouncing	5 ms max.	
	Type	SPST Push-on	
	Rating	20 mA 16 Vdc	
	Contact Resistance	100 mΩ max.	
	Operating Force	6 N	
Endurance	Travel	0.5 mm	
	Rotation Life (Encoder)	1000000 cycles min.	30000 cycles min.
	Operating Life (Switch)	1000000 cycles min.	30000 cycles min.
Minimum Quantity/Packing Unit		50 pcs. (Tray Pack)	
Quantity/Carton		200 pcs.	


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


EVEP/EVEQ



■ Phase Difference




■ Test Circuit Diagram



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 18 mm Square Encoders (High Rotational Torque)

Type: **EVQW**




### ■ Features

- External dimensions : 18.0 mm×18.0 mm, Height 8.0 mm
- Absolute 5 bit available

### ■ Recommended Applications

- Function switching/adjusting for control panels of car air conditioners
- Signal input for monitors and audio/visual equipment


### ■ Explanation of Part Numbers



### ■ Specifications

Type	Top Adjustment type, with or without bushing	
Mechanical	Rotation Angle	360 ° (Endless)
	Shaft Pull/Push Strength	80 N min.
	Shaft Wobble	0.7×L/30 (mm) max.
	Rotation Torque	20 mN·m to 100 mN·m
	Detent Pitch	10 ° to 30 °
Electrical	Output Signals	Gray code
	Resolution	Absolute 5 bit (Custom design of 6 bit max. available)
	Rating	5 mA 10 Vdc
	Contact Resistance	1 Ω max.
	Chattering	2 ms max.
	Insulation Resistance	100 MΩ min. (at 250 Vdc)
	Dielectric Withstanding Voltage	300 Vac for 1 minute
Endurance	Bouncing	5 ms max.
	Rotation Life	15000 cycles min.
Minimum Quantity / Packing Unit		80 pcs. (Tray Pack)
Quantity / Carton		800 pcs.

### ■ Dimensions in mm (not to scale)



## 20/12 mm Center Space Encoders

Type: **EVQV6**




### ■ Features

- Multiple unit construction (achieved by mounting switches, LEDs, etc.) (center space) on the printed wiring board
- Good operability and high reliability

### ■ Recommended Applications

- Car audio products (adjustment of volume, tone, tuners, etc.)
- AV equipment (control of edit functions of VCRs, CD players, etc.)


### ■ Explanation of Part Numbers



### ■ Specifications

Mechanical	Rotation Angle	360 ° (Endless)
	Rotation Torque (Detents Torque)	11 mN·m, 18 mN·m
	Detents	18 points
Electrical	Output Signal	Phase A and B
	Resolution	9 pulses/360 °
	Rating	1 mA 10 Vdc
	Contact Resistance	1 Ω max.
	Chattering	5 ms max.
	Insulation Resistance	50 mΩ min. (at 250 Vdc)
Endurance	Dielectric Withstanding Voltage	300 Vac for 1 minute
	Rotation Life	30000 cycles min.
Minimum Quantity/Packing Unit		100 pcs. (Tray Pack)
Quantity/Carton		2000 pcs.

### ■ Dimensions in mm (not to scale)



## 27/17 mm Center Space Encoders

Type: **EVQWF/EVQVP**




### ■ Features

- Multiple unit construction (achieved by mounting switches, LEDs, etc.) (center space) on the printed wiring board
- Good operability and high reliability

### ■ Recommended Applications

- Car audio products (adjustment of volume, tone, tuners, etc.)
- AV equipment (control of edit functions of VCRs, CD players, etc.)


### ■ Explanation of Part Numbers



### ■ Specifications

Mechanical	Rotation Angle	360 ° (Endless)
	Rotation Torque (Detents Torque)	3 mN·m to 20 mN·m
	Detents	18 points, 30 points
Electrical	Output Signal	Phase A and B
	Resolution	9 pulses/360 °, 15 pulses/360 °
	Rating	1 mA 10 Vdc
	Contact Resistance	1 Ω max.
	Chattering	5 ms max.
	Insulation Resistance	50 mΩ min. (at 250 Vdc)
	Dielectric Withstanding Voltage	300 Vac for 1 minute
Endurance	Rotation Life	30000 cycles min.
Minimum Quantity/Packing Unit		80 pcs. (Tray Pack)
Quantity/Carton		800 pcs.

### ■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 27/18 mm Center Space Encoders

Type: **EVQV5**




### ■ Features

- Multiple unit construction (achieved by mounting switches, LEDs, etc.) (center space) on the printed wiring board
- Good operability and high reliability

### ■ Recommended Applications

- Car audio products (adjustment of volume, tone, tuners, etc.)
- AV equipment (control of edit functions of VCRs, CD players, etc.)


### ■ Explanation of Part Numbers



### ■ Specifications

Mechanical	Rotation Angle	360 ° (Endless)
	Rotation Torque (Detents Torque)	9 mN·m, 13.5 mN·m, 18 mN·m
	Detents	18 points, 30 points
Electrical	Output Signal	Phase A and B
	Resolution	9 pulses/360 °, 15 pulses/360 °
	Rating	1 mA 10 Vdc
	Contact Resistance	1 Ω max.
	Chattering	5 ms max.
	Insulation Resistance	50 mΩ min. (at 250 Vdc)
Endurance	Dielectric Withstanding Voltage	300 Vac for 1 minute
	Rotation Life	30000 cycles min.
Minimum Quantity/Packing Unit		80 pcs. (Tray Pack)
Quantity/Carton		1600 pcs.

### ■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 38/25 mm Center Space Encoders

Type: **EVQVN**




### ■ Features

- Multiple unit construction (achieved by mounting switches, LEDs, etc.) (center space) on the printed wiring board
- Good operability and high reliability

### ■ Recommended Applications

- Car audio products (adjustment of volume, tone, tuners, etc.)
- AV equipment (control of edit functions of VCRs, CD players, etc.)


### ■ Explanation of Part Numbers



### ■ Specifications

Mechanical	Rotation Angle	360 ° (Endless)
	Rotation Torque (Detents Torque)	20 mN·m
	Detents	30 points
Electrical	Output Signal	Phase A and B
	Resolution	15 pulses/360 °
	Rating	1 mA 10 Vdc
	Contact Resistance	1 Ω max.
	Chattering	5 ms max.
	Insulation Resistance	50 mΩ min. (at 250 Vdc)
Endurance	Dielectric Withstanding Voltage	300 Vac for 1 minute
	Rotation Life	30000 cycles min.
Minimum Quantity/Packing Unit		50 pcs. (Tray Pack)
Quantity/Carton		250 pcs.

### ■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## 60/40 mm Center Space Encoders

Type: **EVQV0**




### ■ Features

- Multiple unit construction (achieved by mounting switches, LEDs, etc.) (center space) on the printed wiring board
- Good operability and high reliability

### ■ Recommended Applications

- Car audio products (adjustment of volume, tone, tuners, etc.)
- AV equipment (control of edit functions of VCRs, CD players, etc.)


### ■ Explanation of Part Numbers



### ■ Specifications

Mechanical	Rotation Angle	360 ° (Endless)
	Rotation Torque (Detents Torque)	35 mN·m
	Detents	30 points
Electrical	Output Signal	Phase A and B
	Resolution	15 pulses/360 °
	Rating	1 mA 10 Vdc
	Contact Resistance	1 Ω max.
	Chattering	5 ms max.
	Insulation Resistance	50 mΩ min. (at 250 Vdc)
Endurance	Dielectric Withstanding Voltage	300 Vac for 1 minute
	Rotation Life	30000 cycles min.
Minimum Quantity/Packing Unit		20 pcs. (Tray Pack)
Quantity/Carton		100 pcs.

### ■ Dimensions in mm (not to scale)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

## Guidelines and cautions for using the product technical information and the products displayed on this material.

- The products described on this material were designed and manufactured for standard applications such as general electronics devices, office equipment, data and communications equipment, measuring instruments, household appliances and audio-video equipment. For special applications in which quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or cause threat of personal injury (such as for aircraft and aerospace equipment, traffic and transport equipment, combustion equipment, medical equipment, accident prevention and anti-theft devices, and safety equipment), please use only after your company has sufficiently tested our products' suitability for that application.
- When using our products in equipment that requires a high degree of reliability, regardless of the application, it is recommended that you use protection circuits and redundancy circuits for equipment safety and test for safety.
- The products and product specifications described on this material are subject to change for improvement without prior notice. Therefore, be sure to request and confirm in advance the most current specifications, which explain the specifications in detail, before the final stage of your design, purchasing or use for any application.
- The technical information on this material provides examples of the products' typical operations and application circuits. It is not intended to guarantee the non-infringement of or grant license for intellectual property rights of this company or any third party.
- Permission must be obtained from the Japanese government if products, products specifications and technical information on this material that are subject to the "Foreign Exchange and Foreign Trade Law" are to be exported or taken out of Japan.
- The information contained on this material may not be reprinted or reproduced whether wholly or in part, without the prior written permission of Panasonic Corporation.

### Safely Precautions

When using our products, no matter what sort of equipment they might be user for, be sure to confirm the applications and environmental conditions with our specifications in advance.

#### ● Inquiry

Electromechanical Components Business Division  
Automotive & Industrial Systems Company  
Panasonic Corporation  
1006 Kadoma, Kadoma City,  
Osaka 571-8506, Japan

The information in this catalog is valid as of April 2013.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panasonic:](#)

[EVP-AECB2A](#) [EVP-AECE2A](#)