

|                        |                                                                                                                                                   |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Title</b>           | <b><i>Reference Design Report for a 7 W, Wide Range Input, Dual Output, Non-Isolated Flyback Converter Using LinkSwitch™-XT2-900 LNK3696P</i></b> |
| <b>Specification</b>   | 85 VAC – 440 VAC Input;<br>12.0 V / 500 mA, 5.0 V / 200 mA Outputs                                                                                |
| <b>Application</b>     | Embedded Power Supply                                                                                                                             |
| <b>Author</b>          | Applications Engineering Department                                                                                                               |
| <b>Document Number</b> | RDR-736                                                                                                                                           |
| <b>Date</b>            | June 30, 2020                                                                                                                                     |
| <b>Revision</b>        | 1.2                                                                                                                                               |

#### **Summary and Features**

- Highly integrated solution with 900 V rated power MOSFET
- Output voltage regulation: 12 V  $\pm$ 10%, 5 V  $\pm$ 5%
- Programmable current limit selection feature of LinkSwitch-XT2-900
- Extremely fast transient response independent of load timing
- >80% efficiency at full load condition
- <120 mW no-load input power at 230 VAC
- >6 dB conducted EMI margin
- No optocoupler or Zener diode required for regulation
- Can withstand up to 450 VAC line input

#### **PATENT INFORMATION**

The products and applications illustrated herein (including transformer construction and circuits external to the products) may be covered by one or more U.S. and foreign patents, or potentially by pending U.S. and foreign patent applications assigned to Power Integrations. A complete list of Power Integrations' patents may be found at [www.powerint.com](http://www.powerint.com). Power Integrations grants its customers a license under certain patent rights as set forth at <https://www.power.com/company/intellectual-property-licensing/>.

---

#### **Power Integrations**

5245 Hellyer Avenue, San Jose, CA 95138 USA.  
Tel: +1 408 414 9200 Fax: +1 408 414 9201  
[www.power.com](http://www.power.com)

## Table of Contents

|        |                                                 |    |
|--------|-------------------------------------------------|----|
| 1      | Introduction .....                              | 4  |
| 2      | Power Supply Specification .....                | 5  |
| 3      | Schematic .....                                 | 6  |
| 4      | Circuit Description .....                       | 7  |
| 4.1    | Input Rectifier and Filter .....                | 7  |
| 4.2    | LinkSwitch-XT2 Primary-Side .....               | 7  |
| 4.3    | Primary RCD Clamp .....                         | 7  |
| 4.4    | Output Rectification .....                      | 7  |
| 4.5    | Output Feedback .....                           | 8  |
| 4.6    | Output Overvoltage Protection .....             | 8  |
| 4.7    | Line Overvoltage Protection .....               | 8  |
| 5      | PCB Layout .....                                | 9  |
| 6      | Bill of Materials .....                         | 10 |
| 7      | Transformer Specification .....                 | 11 |
| 7.1    | Electrical Diagram .....                        | 11 |
| 7.2    | Electrical Specifications .....                 | 11 |
| 7.3    | Material List .....                             | 11 |
| 7.4    | Transformer Build Diagram .....                 | 12 |
| 7.5    | Transformer Construction .....                  | 12 |
| 7.6    | Transformer Winding Illustrations .....         | 12 |
| 8      | Transformer Design Spreadsheet .....            | 16 |
| 9      | Performance Data .....                          | 20 |
| 9.1    | No-Load Input Power .....                       | 20 |
| 9.2    | Efficiency .....                                | 21 |
| 9.2.1  | Efficiency vs Line .....                        | 21 |
| 9.2.2  | Efficiency vs Load .....                        | 22 |
| 9.2.3  | Average Efficiency .....                        | 23 |
| 9.3    | Output Voltage Regulation .....                 | 24 |
| 9.3.1  | 5 V Load Regulation with Balanced Load .....    | 24 |
| 9.3.2  | 12 V Load Regulation with Balanced Load .....   | 25 |
| 9.3.3  | 5 V Load Regulation with Unbalanced Load .....  | 26 |
| 9.3.4  | 12 V Load Regulation with Unbalanced Load ..... | 28 |
| 9.3.5  | Line Regulation .....                           | 30 |
| 10     | Waveforms .....                                 | 32 |
| 10.1   | Output Voltage Ripple .....                     | 32 |
| 10.1.1 | Ripple Measurement Technique .....              | 32 |
| 10.1.2 | Ripple Waveforms at Full Load .....             | 33 |
| 10.1.3 | Ripple Waveforms at No-Load .....               | 34 |
| 10.1.4 | Ripple vs. Load .....                           | 35 |
| 10.2   | Switching Waveforms .....                       | 37 |
| 10.2.1 | $V_{DS}$ and $I_{DS}$ .....                     | 37 |
| 10.2.2 | 5 V Output Diode Voltage and Current .....      | 38 |



|        |                                                                  |    |
|--------|------------------------------------------------------------------|----|
| 10.2.3 | 12 V Output Diode Voltage and Current.....                       | 39 |
| 10.3   | Start-up Performance.....                                        | 40 |
| 10.3.1 | 12 V Start-up Operation $V_{IN}$ , $V_{OUT}$ and $I_{OUT}$ ..... | 40 |
| 10.3.2 | 5 V Start-up Operation $V_{IN}$ , $V_{OUT}$ and $I_{OUT}$ .....  | 41 |
| 10.3.3 | Start-up Operation $V_{DS}$ and $I_{DS}$ .....                   | 42 |
| 10.4   | Output Load Transient .....                                      | 43 |
| 10.4.1 | 5 V Output Transient.....                                        | 43 |
| 10.4.2 | 12 V Output Transient.....                                       | 44 |
| 10.5   | Fault Waveforms .....                                            | 45 |
| 10.5.1 | 5 V Output Short.....                                            | 45 |
| 10.5.2 | 12 V Output Short.....                                           | 46 |
| 10.5.3 | Line Overvoltage.....                                            | 47 |
| 11     | Thermal Performance .....                                        | 48 |
| 11.1   | Test Set-Up.....                                                 | 48 |
| 11.2   | Room Temperature.....                                            | 49 |
| 11.2.1 | 85 VAC @ Room Temperature .....                                  | 49 |
| 11.2.2 | 440 VAC @ Room Temperature .....                                 | 50 |
| 11.3   | 50 °C Ambient.....                                               | 51 |
| 11.3.1 | 85 VAC @ 50 °C .....                                             | 51 |
| 11.3.2 | 440 VAC @ 50 °C.....                                             | 52 |
| 12     | Conducted EMI.....                                               | 53 |
| 12.1   | EMI Equipment and Load .....                                     | 53 |
| 12.2   | Test Set-up .....                                                | 53 |
| 12.3   | EMI Test Results.....                                            | 54 |
| 12.3.1 | 115 VAC, Floating Output .....                                   | 54 |
| 12.3.2 | 230 VAC, Floating Output .....                                   | 54 |
| 13     | Line Surge .....                                                 | 55 |
| 13.1   | Differential Surge Test .....                                    | 55 |
| 13.2   | Ring Wave Test .....                                             | 55 |
| 14     | Revision History .....                                           | 56 |


**Important Note:**

Although this board is designed to satisfy safety isolation requirements, the engineering prototype has not been agency approved. Therefore, all testing should be performed using an isolation transformer to provide the AC input to the prototype board.


## 1 Introduction

This engineering report describes a non-isolated flyback converter designed to provide dual output of 5 V at 200 mA and 12 V at 500 mA from a wide input voltage range of 85 VAC to 440 VAC. This adapter utilizes the LNK3696P from the LinkSwitch-XT2 900 V family of devices.

This document contains the power supply specification, schematic, bill of materials, transformer documentation, printed circuit layout, and performance data.



**Figure 1** – Populated Circuit Board Photograph, Top.



**Figure 2** – Populated Circuit Board Photograph, Bottom.

## 2 Power Supply Specification

The table below represents the minimum acceptable performance of the design. Actual performance is listed in the results section.

| Description             | Symbol                       | Min                 | Typ   | Max  | Units | Comment                                         |
|-------------------------|------------------------------|---------------------|-------|------|-------|-------------------------------------------------|
| <b>Input</b>            |                              |                     |       |      |       |                                                 |
| Voltage                 | <b>V<sub>IN</sub></b>        | 85                  |       | 440  | VAC   | 2 Wire – no P.E. Verified at 450 VAC.           |
| Frequency               | <b>f<sub>LINE</sub></b>      | 50                  | 50/60 | 60   | Hz    |                                                 |
| No-load Input Power     |                              |                     |       | 200  | mW    |                                                 |
| <b>Output</b>           |                              |                     |       |      |       |                                                 |
| Output Voltage 1        | <b>V<sub>OUT-5</sub></b>     | 4.75                | 5.0   | 5.25 | V     | ±5%                                             |
| Output Current 1        | <b>I<sub>OUT-5</sub></b>     | 50                  | 200   |      | mA    |                                                 |
| Output Voltage 2        | <b>V<sub>OUT-12</sub></b>    | 10.8                | 12.0  | 13.2 | V     | ±10%                                            |
| Output Current 2        | <b>I<sub>OUT-12</sub></b>    | 50                  | 500   |      | mA    |                                                 |
| Output Ripple Voltage   | <b>V<sub>RIPPLE</sub></b>    |                     |       | 200  | mV    | 20 MHz Bandwidth.                               |
| Output Power            | <b>P<sub>OUT</sub></b>       |                     | 7     |      | W     |                                                 |
| <b>Efficiency</b>       |                              |                     |       |      |       |                                                 |
| Full Load               | <b>η<sub>Full-Load</sub></b> | 80                  |       |      | %     | Measured at Output Terminal.                    |
| <b>Environmental</b>    |                              |                     |       |      |       |                                                 |
| Conducted EMI           |                              | CISPR22B / EN55022B |       |      |       | Resistive Load, 6 dB Margin.                    |
| Line Surge              |                              | Load floating       |       |      |       |                                                 |
| Differential Mode (L/N) |                              |                     |       | 1    | kV    |                                                 |
| Ambient Temperature     | <b>T<sub>AMB</sub></b>       | 0                   |       | 40   | °C    | Free Convection, Sea Level in Sealed Enclosure. |

### 3 Schematic




Figure 3 – Schematic.

## 4 Circuit Description

The LinkSwitch-XT2 900 V family of devices integrates a high-voltage (900 V rated) power MOSFET with an internal oscillator and ON/OFF controller inside a single monolithic IC. Unlike conventional pulse width modulation (PWM) controllers, LinkSwitch-XT2 900 V devices utilize a simple ON/OFF control scheme combined with an internal current limit circuitry to regulate the output voltage. The LNK3696P IC was used in a non-isolated flyback with dual output (12 V and 5 V) delivering 500 mA and 200 mA respectively.

### 4.1 Input Rectifier and Filter

The AC input is rectified by bridge rectifier BR1 and filtered by the bulk storage capacitors C2 and C3. Resistor RF1 is a flameproof, fusible, wire wound type and functions as a fuse, inrush current limiter and, together with the filter formed by C1, C2, C3, L1 and L2, differential mode noise attenuator. Resistors R13, R14, R15 and R16 function to balance the voltage between the bulk capacitors in series.

### 4.2 LinkSwitch-XT2 Primary-Side

The rectified and filtered input voltage is applied to the primary winding of flyback transformer T1. T1 is switched and connected to the IC via the DRAIN (D) pin. The D pin provides internal operating current for both start-up and steady-state operating conditions.

During the power MOSFET turn on time, current ramps up in the primary winding, storing energy inside the transformer core, while the two secondaries remain cut-off due to reverse biasing of the diodes. The primary winding current eventually exceeds the internal threshold ( $I_{LIMIT}$ ), causing the power MOSFET to turn off for the remainder of the switching cycle. At the beginning of the next and all succeeding switching cycles, the IC decides whether to turn ON the power MOSFET or let it remain turned OFF. ON/OFF control is performed by comparing the output voltage to the reference voltage  $V_{FB}$ , resulting to the power MOSFET being enabled or disabled. Through the use of ON/OFF control, voltage regulation is maintained by skipping cycles without using an error amplifier and ramp generator, as in traditional power supply controllers.

### 4.3 Primary RCD Clamp

A low cost RCD clamp is connected across the primary winding of transformer T1. This is composed of resistors R20 and R13, capacitor C13 and diode D5. The clamp helps in dissipating the energy stored in the leakage inductance of T1.

### 4.4 Output Rectification

Transformer T1 has two secondary windings on its core – one for each output voltage. For both secondaries, the secondary switching voltage is rectified by Schottky diodes D3 and D4, and then filtered by super low ESR type capacitors C6, C7, C8 and C9. For each

Schottky diode, a snubber network is connected in parallel using resistors R4 and R8, and capacitors C5 and C10. The snubber network helps limit the peak inverse voltage spikes seen by the diode. Pre-load resistors R23 and R23 are connected on each output to improve cross-regulation performance.

#### 4.5 Output Feedback

The two outputs 12 V and 5 V are sensed through resistor dividers R5, R6 and R7. The sensed voltage is fed back to U1 through the FEEDBACK (FB) pin. This voltage  $V_{FB}$  must be accurately maintained at 2 V, so the sensing resistors must have 1% tolerance.

A weighted feedback circuit using resistors R5, R6 and R7 are connected to both output voltages and into the FB pin. The magnitude of the weights are determined by the relative contributions of current delivered into the FB pin, which then determine the values of R5 and R7. In the schematic, a larger current is contributed by the 5 V output, due to the larger current through R5 as compared to R7. Effectively, the 5 V output voltage has better feedback sensitivity and output regulation.

#### 4.6 Output Overvoltage Protection

The BYPASS (BP/M) pin has multiple functions: it provides a connection point for an external bypass capacitor as well current limit value selector via the capacitance value, and it provides a shutdown function. Similar to the FB pin, when the current delivered into the BP/M pin exceeds the internal threshold ( $I_{BP(SD)}$ ) for a time equal to 2 to 3 cycles of the switching frequency, the device enters auto-restart. By designing a circuit that injects current into the BP/M pin due to a fault, the device can be equipped with both output overvoltage and line overvoltage protection.

For the 5 V output, a simple clamp circuit using Zener diode VR3 and resistor R22 is used for overvoltage protection. For the 12 V output, Zener diode VR2, diode D6 and resistor R7 comprise the overvoltage protection circuit. A voltage at the 12 V output the exceeds the sum of the VR2 voltage rating, D2 diode drop, and the bypass voltage will cause a current in excess of  $I_{BP(SD)}$  to be injected into the BP/M pin, which will trigger the auto-restart and protect the power supply from overvoltage.

#### 4.7 Line Overvoltage Protection

The device indirectly senses the DC bus voltage by sampling the secondary voltage during the power MOSFET on-time. During this time, the voltage across the secondary winding is proportional to the voltage across the primary winding. When the DC bus voltage exceeds the limit, Zener diode VR1 and diode D2 are turned on causing current to flow through transistor Q1 and into the FB pin. The device will go into auto-restart mode if the FB pin current limit is exceeded for at least 2 consecutive switching cycles.



## 5 PCB Layout




Figure 4 – Printed Circuit Layout, Top.




Figure 5 – Printed Circuit Layout, Bottom.

## 6 Bill of Materials

| Item | Qty | Ref Des         | Description                                                                | Mfg Part Number    | Mfg                |
|------|-----|-----------------|----------------------------------------------------------------------------|--------------------|--------------------|
| 1    | 1   | BR1             | 1000 V, 0.8 A, Bridge Rectifier, SMD, MBS-1, 4-SOIC                        | B10S-G             | Comchip            |
| 2    | 1   | C1              | 150 nF, 760 V, Polypropylene Film                                          | B32912B3154M       | Epcos              |
| 3    | 2   | C2 C12          | 33 $\mu$ F, 400 V, Electrolytic, (12.5 x 20)                               | KMG401ELL330MK20S  | Nippon Chemi-Con   |
| 4    | 1   | C4              | 100 nF, 25 V, Ceramic, X7R, 1206                                           | C1206F104K3RACTU   | Kemet              |
| 5    | 1   | C5              | 1 nF, 50 V, Ceramic, X7R, 0805                                             | 08055C102KAT2A     | AVX                |
| 6    | 2   | C6 C7           | 330 $\mu$ F, 16 V, Electrolytic, Very Low ESR, 72 m $\Omega$ , (8 x 11.5)  | EKZE160ELL331MHB5D | Nippon Chemi-Con   |
| 7    | 2   | C8 C9           | 470 $\mu$ F, 16 V, Electrolytic, Very Low ESR, 53 m $\Omega$ , (10 x 12.5) | EKZE160ELL471MJC5S | Nippon Chemi-Con   |
| 8    | 2   | C10 C13         | 1 nF, 250 V, Ceramic, X7R, 0805                                            | GRM21AR72E102KW01D | Murata             |
| 9    | 1   | D3              | 60 V, 2 A, Schottky, SMD, DO-214AA                                         | SS26-E3/52T        | Vishay             |
| 10   | 1   | D4              | 200 V, 3 A, DIODE SCHOTTKY 1A 200 V, SMB                                   | SK3200B-LTP        | Micro Commercial   |
| 11   | 1   | D5              | 1000 V, 800 mA, Fast Recovery SMF, 5000 ns,                                | RS1ML              | Taiwan Semi        |
| 12   | 1   | D6              | 100 V, 10 mA, Fast Switching, 4 ns, MINI-MELF, SOD-80                      | FDLL4148           | ON Semi            |
| 13   | 1   | L1              | 1000 $\mu$ H, 0.510 A                                                      | RLB9012-102KL      | Bourns             |
| 14   | 1   | L2              | 3.5 mm x 4.45 mm, 56 $\Omega$ at 100 MHz, #22 AWG hole, Ferrite Bead       | 2761001112         | Fair-Rite          |
| 15   | 1   | R2              | RES, 20.0 k $\Omega$ , 1%, 1/4 W, Thick Film, 1206                         | ERJ-8ENF2002V      | Panasonic          |
| 16   | 2   | R4 R8           | RES, 16 $\Omega$ , 5%, 1/8 W, Thick Film, 0805                             | ERJ-6GEYJ160V      | Panasonic          |
| 17   | 1   | R5              | RES, 5.11 k $\Omega$ , 1%, 1/8 W, Thick Film, 0805                         | ERJ-6ENF5111V      | Panasonic          |
| 18   | 1   | R6              | RES, 2.15 k $\Omega$ , 1%, 1/16 W, Thick Film, 0603                        | ERJ-3EKF2151V      | Panasonic          |
| 19   | 1   | R7              | RES, 24.9 k $\Omega$ , 1%, 1/8 W, Thick Film, 0805                         | ERJ-6ENF2492V      | Panasonic          |
| 20   | 4   | R13 R14 R15 R16 | RES, 2 M $\Omega$ , 5%, 1/4 W, Thick Film, 1206                            | ERJ-8GEYJ205 V     | Panasonic          |
| 21   | 1   | R20             | RES, 20 $\Omega$ , 5%, 1/4 W, Thick Film, 1206                             | ERJ-8GEYJ200V      | Panasonic          |
| 22   | 1   | R21             | RES, 200 k $\Omega$ , 5%, 1/4 W, Thick Film, 1206                          | ERJ-8GEYJ204V      | Panasonic          |
| 23   | 1   | R22             | RES, 4.7 k $\Omega$ , 5%, 1/8 W, Thick Film, 0805                          | ERJ-6GEYJ472V      | Panasonic          |
| 24   | 1   | R23             | RES, 1.2 k $\Omega$ , 5%, 1/8 W, Thick Film, 0805                          | ERJ-6GEYJ122V      | Panasonic          |
| 25   | 1   | R24             | RES, 3.3 k $\Omega$ , 5%, 1/8 W, Thick Film, 0805                          | ERJ-6GEYJ332V      | Panasonic          |
| 26   | 1   | RF1             | RES, 4.7 $\Omega$ , 2 W, Flame Proof, Pulse Withstanding, Wire Wound       | FW20A4R70JA        | Bourns.            |
| 27   | 1   | T1              | Bobbin, EE16, Vertical, 10 pins (4 x 6)                                    | EL-16 (YW-193-02B) | Yih-Hwa            |
| 28   | 1   | U1              | LinkSwitch-XT2-900, DIP-8C                                                 | LNK3696P           | Power Integrations |
| 39   | 1   | VR2             | DIODE ZENER 12 V 500 mW SOD123                                             | MMSZ5242B-7-F      | Diodes, Inc.       |
| 30   | 1   | VR3             | DIODE ZENER 6.2 V 500 mW SOD123                                            | MMSZ5234B-7-F      | Diodes, Inc.       |

### Miscellaneous Parts

| Item | Qty | Ref Des   | Description                               | Mfg Part Number | Mfg      |
|------|-----|-----------|-------------------------------------------|-----------------|----------|
| 1    | 2   | GND GND`  | Test Point, BLK,Miniature THRU-HOLE MOUNT | 5001            | Keystone |
| 2    | 2   | +5V, +12V | Test Point, RED,Miniature THRU-HOLE MOUNT | 5000            | Keystone |
| 3    | 1   | L         | Test Point, WHT,THRU-HOLE MOUNT           | 5012            | Keystone |
| 4    | 1   | N         | Test Point, BLK,THRU-HOLE MOUNT           | 5011            | Keystone |



## 7 Transformer Specification

### 7.1 Electrical Diagram




Figure 6 – Transformer Electrical Diagram.

### 7.2 Electrical Specifications

| Parameter                         | Condition                                                                       | Spec                  |
|-----------------------------------|---------------------------------------------------------------------------------|-----------------------|
| <b>Electrical Strength</b>        | 60 Hz, 1 second, from pins 1-4 to pins 9-10                                     | 3000 VAC              |
| <b>Primary Inductance</b>         | Pins 1-4, all other windings open, measured at 100 kHz, 0.4 V <sub>RMS</sub> .  | 1500 $\mu$ H $\pm$ 7% |
| <b>Primary Leakage Inductance</b> | Pins 1-4, all other windings short, measured at 100 kHz, 0.4 V <sub>RMS</sub> . | <100 $\mu$ H          |

### 7.3 Material List

| Item | Description                                                |
|------|------------------------------------------------------------|
| [1]  | Core: EE16, Gapped.                                        |
| [2]  | Bobbin: EE16, Vertical, 10 pins.                           |
| [3]  | Magnet Wire: #31 AWG.                                      |
| [4]  | Magnet Wire: #28 AWG.                                      |
| [5]  | Magnet Wire: #25 AWG.                                      |
| [6]  | Tape, 3M 1298 Polyester Film, 2.0 Mils Thick, 8.4 mm Wide. |
| [7]  | Tape, 3M 1298 Polyester Film, 2.0 Mils Thick, 4.5 mm Wide. |
| [8]  | Varnish.                                                   |

## 7.4 Transformer Build Diagram









Figure 7 – Transformer Build Diagram.





## 7.5 Transformer Construction

|                                      |                                                                                                                                                                        |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Winding preparation</b>           | Place the bobbin Item [2] such that the pins are facing the winder. Winding direction is counter-clockwise as shown.                                                   |
| <b>W1<br/>1<sup>st</sup> Primary</b> | Starting at pin 4, wind 90 turns of wire Item [3] in three layers. At the last turn, bring the wire back across the windings and into pin 3.                           |
| <b>Insulation</b>                    | Apply two layers of tape Item [6] for insulation.                                                                                                                      |
| <b>W2<br/>12V Winding</b>            | Start at pin 5, wind 20 turns of wire Item [4] in one layer. At the last turn, bring the wire back across the windings and into pin 9.                                 |
| <b>Insulation</b>                    | Use 1 layer of tape Item [6] for insulation.                                                                                                                           |
| <b>W3<br/>5V Winding</b>             | Starting at pin 10, wind 7.7 turns of two strands of wire Item [5] in one layer. At the last turn, bring the wire back across the windings and into pin 9.             |
| <b>Insulation</b>                    | Use 1 layer of tape Item [6] for insulation.                                                                                                                           |
| <b>W4<br/>2<sup>nd</sup> Primary</b> | Continue the primary winding at pin 3. Wind 60 turns of wire Item [3] in two layers. Finish at pin 1.                                                                  |
| <b>Insulation</b>                    | Apply two layers of tape Item [6] for insulation.                                                                                                                      |
| <b>Assembly</b>                      | Grind core halves for specified primary inductance, insert bobbin, and secure core halves with tape Item [7]. Cut pin 3 short. Remove pins 2, 6, 7 and 8. Dip varnish. |

## 7.6 Transformer Winding Illustrations

|                            |                                                                                     |                                                                                                                      |
|----------------------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|
| <b>Winding preparation</b> |  | Place the bobbin Item [2] such that the pins are facing the winder. Winding direction is counter-clockwise as shown. |
|----------------------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|

|                                      |                                                                                     |                                                                                                                                              |
|--------------------------------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>W1<br/>1<sup>st</sup> Primary</b> |    | Starting at pin 4, wind 90 turns of wire Item [3] in three layers. At the last turn, bring the wire back across the windings and into pin 3. |
| <b>Insulation</b>                    |    | Apply two layers of tape Item [6] for insulation.                                                                                            |
| <b>W2<br/>12V Winding</b>            |   | Start at pin 5, wind 20 turns of wire Item [4] in one layer. At the last turn, bring the wire back across the windings and into pin 9.       |
| <b>Insulation</b>                    |  | Use 1 layer of tape Item [6] for insulation.                                                                                                 |

|                                      |                                                                                     |                                                                                                                                                          |
|--------------------------------------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>W3<br/>5V Winding</b>             |    | Starting at pin 10, wind 8 turns of two strands of wire Item [5] in one layer. At the last turn, bring the wire back across the windings and into pin 9. |
| <b>Insulation</b>                    |    | Use 1 layer of tape Item [6] for insulation.                                                                                                             |
| <b>W4<br/>2<sup>nd</sup> Primary</b> |   | Continue the primary winding at pin 3. Wind 60 turns of wire Item [3] in two layers. Finish at pin 1.                                                    |
| <b>Insulation</b>                    |  | Apply two layers of tape Item [6] for insulation.                                                                                                        |

|                        |                                                                                    |                                                                                                                                                                                                    |
|------------------------|------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p><b>Assembly</b></p> |  | <p>Grind core halves for specified primary inductance, insert bobbin, and secure core halves with tape Item [7].</p> <p>Cut pin 3 short.</p> <p>Remove pins 2, 6, 7 and 8.</p> <p>Dip varnish.</p> |
|------------------------|------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## 8 Transformer Design Spreadsheet

**Note:** The output current entered in the spreadsheet was increased such that POUT matches the combined power of the dual outputs.

| <i>ACDC_LinkSwitchXT290<br/>0V_092018; Rev.1.1;<br/>Copyright Power<br/>Integrations 2018</i> | <i>INPUT</i> | <i>INFO</i> | <i>OUTPUT</i> | <i>UNIT</i> | <i>ACDC_LinkSwitchXT2 900V Flyback<br/>Design Spreadsheet</i>                                  |
|-----------------------------------------------------------------------------------------------|--------------|-------------|---------------|-------------|------------------------------------------------------------------------------------------------|
| <b>ENTER APPLICATION VARIABLES</b>                                                            |              |             |               |             |                                                                                                |
| LINE VOLTAGE RANGE                                                                            |              |             | UNIVERSAL     |             | AC line voltage range                                                                          |
| VACMIN                                                                                        | 85.00        |             | 85.00         | Volts       | Minimum AC line voltage                                                                        |
| VACTYP                                                                                        | 115.00       |             | 115.00        | Volts       | Typical AC line voltage                                                                        |
| VACMAX                                                                                        | 440.00       |             | 440.00        | Volts       | Maximum AC line voltage                                                                        |
| fL                                                                                            |              |             | 50            | Hertz       | AC mains frequency                                                                             |
| TIME_BRIDGE_CONDUCTIO<br>N                                                                    |              |             | 2.87          | mseconds    | Input bridge rectifier diode conduction time                                                   |
| LINE RECTIFICATION                                                                            |              |             | F             |             | Select 'F'ull wave rectification or 'H'alf wave rectification                                  |
| VOUT                                                                                          | 12.00        |             | 12.00         | Volts       | Output voltage                                                                                 |
| IOUT                                                                                          | 0.600        |             | 0.600         | Amperes     | Average output current specification                                                           |
| EFFICIENCY                                                                                    | 0.80         |             | 0.80          |             | Efficiency Estimate at output terminals. Under 0.8 if no better data available                 |
| LOSS ALLOCATION FACTOR                                                                        |              |             | 0.50          |             | The ratio of power losses during the MOSFET off-state to the total system losses               |
| POUT                                                                                          |              |             | 7.20          | Watts       | Continuous Output Power                                                                        |
| CIN                                                                                           | 16.50        |             | 16.50         | uFarads     | Input capacitor                                                                                |
| VMIN                                                                                          |              |             | 79.59         | Volts       | Valley of the rectified VACMIN                                                                 |
| VMAX                                                                                          |              |             | 622.25        | Volts       | Peak of the VACMAX                                                                             |
| FEEDBACK                                                                                      | MAIN         |             | MAIN          |             | Select the type of feedback required. (MAIN = feedback via Main Output - Non-isolated)         |
| BIAS WINDING                                                                                  |              |             | NO            |             | Select whether a bias winding is required                                                      |
| <b>LINKSWITCH-XT2 VARIABLES</b>                                                               |              |             |               |             |                                                                                                |
| CURRENT LIMIT MODE                                                                            |              |             | STD           |             | Pick between 'RED' (Reduced) or 'STD' (Standard) current limit mode of operation               |
| PACKAGE                                                                                       |              |             | DIP-8C        |             | Device package                                                                                 |
| ENCLOSURE                                                                                     |              |             | OPEN FRAME    |             | Device enclosure                                                                               |
| GENERIC DEVICE                                                                                | LNK3696      |             | LNK3696       |             | Device series                                                                                  |
| DEVICE CODE                                                                                   |              |             | LNK3696P      |             | Device code                                                                                    |
| PMAX                                                                                          |              |             | 8.00          | Watts       | Device maximum power capability                                                                |
| VOR                                                                                           | 95           |             | 95            | Volts       | Voltage reflected to the primary winding when the MOSFET is off                                |
| VDSON                                                                                         |              |             | 10.0          | Volts       | MOSFET on-time drain to source peak voltage                                                    |
| VDSOFF                                                                                        |              |             | 841.8         | Volts       | The off-time drain to source voltage is higher than 90% of the device breakdown voltage (900V) |
| ILIMITMIN                                                                                     |              |             | 0.446         | Amperes     | Minimum current limit                                                                          |
| ILIMITTYP                                                                                     |              |             | 0.482         | Amperes     | Typical current limit                                                                          |
| ILIMITMAX                                                                                     |              |             | 0.518         | Amperes     | Maximum current limit                                                                          |
| FSMIN                                                                                         |              |             | 62000         | Hertz       | Minimum switching frequency                                                                    |
| FSTYP                                                                                         |              |             | 66000         | Hertz       | Typical switching frequency                                                                    |
| FSMAX                                                                                         |              |             | 70000         | Hertz       | Maximum switching frequency                                                                    |
| RDSON                                                                                         |              |             | 9.70          | Ohms        | MOSFET drain to source resistance at 25degC                                                    |
| <b>PRIMARY WAVEFORM PARAMETERS</b>                                                            |              |             |               |             |                                                                                                |
| MODE OF OPERATION                                                                             |              |             | CCM           |             | Mode of operation                                                                              |
| KRP/KDP                                                                                       |              |             | 0.995         |             | Measure of continuous/discontinuous                                                            |





|                                            |      |  |          |               |                                                                              |
|--------------------------------------------|------|--|----------|---------------|------------------------------------------------------------------------------|
|                                            |      |  |          |               | mode of operation                                                            |
| KP_TRANSIENT                               |      |  | 0.698    |               | KP under conditions of a transient                                           |
| DMAX                                       |      |  | 0.577    |               | Maximum duty cycle at VMIN                                                   |
| TIME_ON                                    |      |  | 9.310    | useconds      | MOSFET conduction time at the minimum line voltage                           |
| TIME_ON_MIN                                |      |  | 1.076    | useconds      | MOSFET conduction time at the maximum line voltage                           |
| IAVG_PRIMARY                               |      |  | 0.129    | Amperes       | Average input current                                                        |
| IRMS_PRIMARY                               |      |  | 0.196    | Amperes       | Root mean squared value of the primary current                               |
| LPRIMARY_MIN                               |      |  | 1314     | uH            | Minimum primary inductance                                                   |
| LPRIMARY_TYP                               |      |  | 1460     | uH            | Typical primary inductance                                                   |
| LPRIMARY_MAX                               |      |  | 1606     | uH            | Maximum primary inductance                                                   |
| LPRIMARY_TOL                               |      |  | 10       |               | Tolerance of the Primary inductance                                          |
| <b>SECONDARY WAVEFORM PARAMETERS</b>       |      |  |          |               |                                                                              |
| IPEAK_SECONDARY                            |      |  | 3.885    | Amperes       | Peak secondary current                                                       |
| IRMS_SECONDARY                             |      |  | 1.462    | Amperes       | Root mean squared value of the secondary current                             |
| PIV_SECONDARY                              |      |  | 94.97    | Volts         | Peak inverse voltage on the secondary diode, not including the leakage spike |
| VF_SECONDARY                               |      |  | 0.70     | Volts         | Secondary diode forward voltage drop                                         |
| <b>TRANSFORMER CONSTRUCTION PARAMETERS</b> |      |  |          |               |                                                                              |
| <b>Core selection</b>                      |      |  |          |               |                                                                              |
| CORE                                       | EE16 |  | EE16     |               | Select the transformer core                                                  |
| BOBBIN                                     |      |  | B-EE16-H |               | Bobbin name                                                                  |
| AE                                         |      |  | 19.20    | mm^2          | Cross sectional area of the core                                             |
| LE                                         |      |  | 35.00    | mm            | Effective magnetic path length of the core                                   |
| AL                                         |      |  | 1140.0   | nH/(turns^2)  | Ungapped effective inductance of the core                                    |
| VE                                         |      |  | 795.0    | mm^3          | Volume of the core                                                           |
| AW                                         |      |  | 14.76    | mm^2          | Window area of the bobbin                                                    |
| BW                                         |      |  | 8.50     | mm            | Width of the bobbin                                                          |
| MLT                                        |      |  | 0.00     | mm            | Mean length per turn of the bobbin                                           |
| MARGIN                                     |      |  | 0.00     | mm            | Safety margin                                                                |
| <b>Primary winding</b>                     |      |  |          |               |                                                                              |
| NPRIMARY                                   |      |  | 150      |               | PrImary number of turns                                                      |
| BMAX_TARGET                                |      |  | 1500     | Gauss         | Target value of the magnetic flux density                                    |
| BMAX_ACTUAL                                |      |  | 2625     | Gauss         | The actual flux density of the device has been exceeded                      |
| BAC                                        |      |  | 1306     | Gauss         | AC flux density                                                              |
| ALG                                        |      |  | 65       | nH/T^2        | Gapped core effective inductance                                             |
| LG                                         |      |  | 0.351    | mm            | Core gap length                                                              |
| LAYERS_PRIMARY                             |      |  | 4        |               | Number of primary layers                                                     |
| AWG_PRIMARY                                |      |  | 33       |               | Primary winding wire AWG                                                     |
| OD_PRIMARY_INSULATED                       |      |  | 0.219    | mm            | Primary winding wire outer diameter with insulation                          |
| OD_PRIMARY_BARE                            |      |  | 0.180    | mm            | Primary winding wire outer diameter without insulation                       |
| CMA_PRIMARY                                |      |  | 256      | mil^2/Amperes | Primary winding wire CMA                                                     |
| <b>Secondary winding</b>                   |      |  |          |               |                                                                              |
| NSECONDARY                                 | 20   |  | 20       |               | Secondary turns                                                              |
| AWG_SECONDARY                              |      |  | 25       |               | Secondary winding wire AWG                                                   |
| OD_SECONDARY_INSULATED                     |      |  | 0.760    | mm            | Secondary winding wire outer diameter with insulation                        |
| OD_SECONDARY_BARE                          |      |  | 0.455    | mm            | Secondary winding wire outer diameter without insulation                     |
| CMA_SECONDARY                              |      |  | 219      | mil^2/Amperes | Secondary winding CMA                                                        |
| <b>Bias winding</b>                        |      |  |          |               |                                                                              |


|                                   |       |  |             |         |                                                                                              |
|-----------------------------------|-------|--|-------------|---------|----------------------------------------------------------------------------------------------|
| NBIAS                             |       |  | N/A         |         | Bias turns                                                                                   |
| VF_BIAS                           |       |  | N/A         | Volts   | Bias diode forward voltage drop                                                              |
| VBIAS                             |       |  | N/A         | Volts   | Bias winding voltage                                                                         |
| PIVB                              |       |  | N/A         | Volts   | Peak inverse voltage on the bias diode                                                       |
| CBP                               |       |  | 0.1         | uF      | BP pin capacitor                                                                             |
| <b>FEEDBACK PARAMETERS</b>        |       |  |             |         |                                                                                              |
| DIODE_BIAS                        |       |  | 1N4003-4007 |         | Recommended diode is 1N4003. Place diode on return leg of bias winding for optimal EMI       |
| RUPPER                            |       |  | 15000       | ohms    | CV bias resistor for CV/CC circuit. See LinkSwitch-XT2 Design Guide                          |
| RLOWER                            |       |  | 3000        | ohms    | Resistor to set CC linearity for CV/CC circuit. See LinkSwitch-XT2 900V Design Guide         |
| <b>MULTIPLE OUTPUT PARAMETERS</b> |       |  |             |         |                                                                                              |
| <b>Output 1</b>                   |       |  |             |         |                                                                                              |
| VOUT1                             |       |  | 12.00       | Volts   | Output Voltage 1                                                                             |
| IOUT1                             |       |  | 0.600       | Amperes | Output Current 1                                                                             |
| POUT1                             |       |  | 7.20        | Watts   | Output Power 1                                                                               |
| VD1                               |       |  | 0.70        | Volts   | Secondary diode forward voltage drop for output 1                                            |
| NS1                               |       |  | 20          |         | Number of turns for output 1                                                                 |
| ISRMS1                            |       |  | 1.462       | Amperes | Root mean squared value of the secondary current for output 1                                |
| IRIPPLE1                          |       |  | 1.333       | Amperes | Current ripple on the secondary waveform for output 1                                        |
| PIV1                              |       |  | 94.97       | Volts   | Peak inverse voltage on the secondary diode for output 1                                     |
| DIODE1_RECOMMENDED                |       |  | BYV27-200   |         | Recommended diode for output 1                                                               |
| PRELOAD                           |       |  | 6.04        | kohms   | Preload resistor to ensure a load of at least 3mA on the first output for BIAS, 2mA for MAIN |
| CMS1                              |       |  | 292.4       | Cmils   | Bare conductor effective area in circular mils for output 1                                  |
| AWGS1                             |       |  | 25          | AWG     | Wire size for output 1                                                                       |
| <b>Output 2</b>                   |       |  |             |         |                                                                                              |
| VOUT2                             | 5.00  |  | 5.00        | Volts   | Output Voltage 2                                                                             |
| IOUT2                             | 0.200 |  | 0.200       | Amperes | Output Current 2                                                                             |
| POUT2                             |       |  | 1.00        | Watts   | Output Power 2                                                                               |
| VD2                               |       |  | 0.70        | Volts   | Secondary diode forward voltage drop for output 2                                            |
| NS2                               |       |  | 9           |         | Number of turns for output 2                                                                 |
| ISRMS2                            |       |  | 0.487       | Amperes | Root mean squared value of the secondary current for output 2                                |
| IRIPPLE2                          |       |  | 0.444       | Amperes | Current ripple on the secondary waveform for output 2                                        |
| PIV2                              |       |  | 42.34       | Volts   | Peak inverse voltage on the secondary diode for output 2                                     |
| DIODE2_RECOMMENDED                |       |  | SB160       |         | Recommended diode for output 2                                                               |
| CMS2                              |       |  | 97.5        | Cmils   | Bare conductor effective area in circular mils for output 2                                  |
| AWGS2                             |       |  | 30          | AWG     | Wire size for output 2                                                                       |
| <b>Output 3</b>                   |       |  |             |         |                                                                                              |
| VOUT3                             |       |  | 0.00        | Volts   | Output Voltage 3                                                                             |
| IOUT3                             |       |  | 0.000       | Amperes | Output Current 3                                                                             |
| POUT3                             |       |  | 0.00        | Watts   | Output Power 3                                                                               |
| VD3                               |       |  | 0.70        | Volts   | Secondary diode forward voltage drop for output 3                                            |
| NS3                               |       |  | 2           |         | Number of turns for output 3                                                                 |
| ISRMS3                            |       |  | 0.000       | Amperes | Root mean squared value of the secondary current for output 3                                |
| IRIPPLE3                          |       |  | 0.000       | Amperes | Current ripple on the secondary                                                              |



|                    |  |  |      |       |                                                                                              |
|--------------------|--|--|------|-------|----------------------------------------------------------------------------------------------|
|                    |  |  |      |       | waveform for output 3                                                                        |
| PIV3               |  |  | 8.30 | Volts | Peak inverse voltage on the secondary diode for output 3                                     |
| DIODE3_RECOMMENDED |  |  | NA   |       | Recommended diode for output 3                                                               |
| CMS3               |  |  | 0.0  | Cmils | Bare conductor effective area in circular mils for output 3                                  |
| AWGS3              |  |  | 0    | AWG   | Wire size output for 3                                                                       |
| PO_TOTAL           |  |  | 8.20 | Watts | The total power of all outputs exceeds the design power                                      |
| NEGATIVE OUTPUT    |  |  | N/A  |       | If negative output exists, enter the output number; e.g. If VO2 is negative output, select 2 |

## 9 Performance Data


### 9.1 No-Load Input Power



**Figure 8** – No-Load Power vs. Input Line Voltage.


## 9.2 Efficiency

### 9.2.1 Efficiency vs Line



**Figure 9** – Full Load Efficiency vs. Input Line Voltage.

## 9.2.2 Efficiency vs Load



**Figure 10** – Efficiency vs. Percent Load, at Different Input Line Voltages.

9.2.3 *Average Efficiency*

## 9.2.3.1 85 VAC Input

| Input Measurement     |                      |                     | Output 1 Measurement |                       |                      | Output 2 Measurement |                       |                      | Efficiency (%) |
|-----------------------|----------------------|---------------------|----------------------|-----------------------|----------------------|----------------------|-----------------------|----------------------|----------------|
| V <sub>IN</sub> (RMS) | I <sub>IN</sub> (mA) | P <sub>IN</sub> (W) | V <sub>OUT</sub> (V) | I <sub>OUT</sub> (mA) | P <sub>OUT</sub> (W) | V <sub>OUT</sub> (V) | I <sub>OUT</sub> (mA) | P <sub>OUT</sub> (W) |                |
| 83                    | 163.1                | 8.71                | 12.01                | 500.0                 | 6.01                 | 4.94                 | 198.1                 | 0.98                 | 80.2           |
| 84                    | 124.1                | 6.52                | 12.02                | 375.0                 | 4.51                 | 4.95                 | 148.0                 | 0.73                 | 80.4           |
| 84                    | 85.8                 | 4.36                | 12.04                | 249.9                 | 3.01                 | 4.95                 | 98.2                  | 0.49                 | 80.1           |
| 84                    | 46.8                 | 2.23                | 12.06                | 145.0                 | 1.51                 | 4.95                 | 48.2                  | 0.24                 | 78.2           |
| Average Efficiency    |                      |                     |                      |                       |                      |                      |                       |                      | 79.7           |

## 9.2.3.2 115 VAC Input

| Input Measurement     |                      |                     | Output 1 Measurement |                       |                      | Output 2 Measurement |                       |                      | Efficiency (%) |
|-----------------------|----------------------|---------------------|----------------------|-----------------------|----------------------|----------------------|-----------------------|----------------------|----------------|
| V <sub>IN</sub> (RMS) | I <sub>IN</sub> (mA) | P <sub>IN</sub> (W) | V <sub>OUT</sub> (V) | I <sub>OUT</sub> (mA) | P <sub>OUT</sub> (W) | V <sub>OUT</sub> (V) | I <sub>OUT</sub> (mA) | P <sub>OUT</sub> (W) |                |
| 114                   | 123.2                | 8.52                | 12.01                | 500.0                 | 6.00                 | 4.94                 | 198.1                 | 0.98                 | 82.0           |
| 114                   | 95.0                 | 6.40                | 12.03                | 375.0                 | 4.51                 | 4.95                 | 148.0                 | 0.73                 | 81.9           |
| 114                   | 66.4                 | 4.30                | 12.04                | 250.0                 | 3.01                 | 4.95                 | 98.1                  | 0.49                 | 81.2           |
| 114                   | 36.6                 | 2.21                | 12.07                | 125.0                 | 1.51                 | 4.95                 | 48.2                  | 0.24                 | 79.1           |
| Average Efficiency    |                      |                     |                      |                       |                      |                      |                       |                      | 81.0           |

## 9.2.3.3 230 VAC Input


| Input Measurement     |                      |                     | Output 1 Measurement |                       |                      | Output 2 Measurement |                       |                      | Efficiency (%) |
|-----------------------|----------------------|---------------------|----------------------|-----------------------|----------------------|----------------------|-----------------------|----------------------|----------------|
| V <sub>IN</sub> (RMS) | I <sub>IN</sub> (mA) | P <sub>IN</sub> (W) | V <sub>OUT</sub> (V) | I <sub>OUT</sub> (mA) | P <sub>OUT</sub> (W) | V <sub>OUT</sub> (V) | I <sub>OUT</sub> (mA) | P <sub>OUT</sub> (W) |                |
| 229                   | 72.1                 | 8.43                | 12.03                | 500.0                 | 6.02                 | 4.94                 | 198.0                 | 0.98                 | 83.0           |
| 229                   | 56.1                 | 6.36                | 12.04                | 374.9                 | 4.52                 | 4.94                 | 148.1                 | 0.73                 | 82.5           |
| 229                   | 39.5                 | 4.29                | 12.06                | 249.9                 | 3.01                 | 4.95                 | 98.1                  | 0.49                 | 81.6           |
| 230                   | 22.0                 | 2.21                | 12.08                | 125.0                 | 1.51                 | 4.95                 | 48.2                  | 0.24                 | 78.9           |
| Average Efficiency    |                      |                     |                      |                       |                      |                      |                       |                      | 81.5           |

## 9.2.3.4 440 VAC Input

| Input Measurement     |                      |                     | Output 1 Measurement |                       |                      | Output 2 Measurement |                       |                      | Efficiency (%) |
|-----------------------|----------------------|---------------------|----------------------|-----------------------|----------------------|----------------------|-----------------------|----------------------|----------------|
| V <sub>IN</sub> (RMS) | I <sub>IN</sub> (mA) | P <sub>IN</sub> (W) | V <sub>OUT</sub> (V) | I <sub>OUT</sub> (mA) | P <sub>OUT</sub> (W) | V <sub>OUT</sub> (V) | I <sub>OUT</sub> (mA) | P <sub>OUT</sub> (W) |                |
| 439                   | 45.0                 | 8.70                | 12.03                | 500.0                 | 6.02                 | 4.94                 | 197.9                 | 0.98                 | 80.4           |
| 439                   | 35.1                 | 6.57                | 12.03                | 375.0                 | 4.51                 | 4.95                 | 148.0                 | 0.73                 | 79.8           |
| 439                   | 24.9                 | 4.45                | 12.05                | 249.9                 | 3.01                 | 4.95                 | 98.2                  | 0.49                 | 78.7           |
| 439                   | 14.0                 | 2.32                | 12.08                | 125.0                 | 1.51                 | 4.95                 | 48.1                  | 0.24                 | 75.4           |
| Average Efficiency    |                      |                     |                      |                       |                      |                      |                       |                      | 78.6           |

## 9.3 Output Voltage Regulation


### 9.3.1 5 V Load Regulation with Balanced Load



**Figure 11** – 5 V Load Regulation.  
Condition: Simultaneous Load Decrement.




## 9.3.2 12 V Load Regulation with Balanced Load




**Figure 12 – 12 V Load Regulation.**  
Condition: Simultaneous Load Decrement.

## 9.3.3 5 V Load Regulation with Unbalanced Load




**Figure 13 – 5 V Load Regulation.**  
Condition: 12 V at 500 mA, 5 V Load Sweep.




**Figure 14 – 5 V Load Regulation.**  
Condition: 12 V at 50 mA, 5 V Load Sweep.


## 9.3.4 12 V Load Regulation with Unbalanced Load




**Figure 15 – 12 V Load Regulation.**  
Condition: 12 V Load Sweep, 5 V at 200 mA.



**Figure 16 – 12 V Load Regulation.**  
Condition: 12 V Load Sweep, 5 V at 50 mA.

9.3.5 *Line Regulation***Figure 17** – 5 V Output Regulation vs. Input Line Voltage.



**Figure 18** – 12 V Output Regulation vs. Input Line Voltage.

## 10 Waveforms

### 10.1 Output Voltage Ripple


#### 10.1.1 *Ripple Measurement Technique*

For DC output ripple measurements, a modified oscilloscope test probe must be utilized in order to reduce spurious signals due to pick-up. Details of the probe modification are provided in the Figures below.

The 4987BA probe adapter is affixed with two capacitors tied in parallel across the probe tip. The capacitors include one (1) 0.1  $\mu\text{F}$  / 50 V ceramic type and one (1) 47  $\mu\text{F}$  / 50 V aluminum electrolytic. The aluminum electrolytic type capacitor is polarized, so proper polarity across DC outputs must be maintained (see below). Ripple measurement done at the end of a 100 m $\Omega$  cable.



**Figure 19** – Oscilloscope Probe Prepared for Ripple Measurement. (End Cap and Ground Lead Removed.)



**Figure 20** – Oscilloscope Probe with Probe Master ([www.probemaster.com](http://www.probemaster.com)) 4987A BNC Adapter. (Modified with wires for ripple measurement, and two parallel decoupling capacitors added.)



2018-05-22 13:45:35

Horizontal: 50 ns/div, Vertical: 100 mV/div, Trigger: Edge, Ch1

12V Ripple

12V Ripple

5V Ripple

5V Ripple

Meas Result 1: 71.146 mV

Meas Result 2: 79.051 mV

Peak to peak: 71.146 mV

Peak to peak: 79.051 mV

200mV 12V Ripple

250mV 12V Ripple

50mV 5V Ripple

50mV 5V Ripple

Horizontal 20MS  
Vol 20mdiv  
Pos 0.0  
Trigger Edge 2  
Coupling AC  
27.87ms

Channel 1  
Sd: 50 mV/div  
Pos: 0.0V  
Cou AC  
BW: 20 MHz

Channel 2  
Sd: 50 mV/div  
Pos: 0.0V  
Cou AC  
BW: 20 MHz

Peak to peak 73.123 mV

Peak to peak 69.87 mV

2018-05-22 13:46:39


Horizontal  
 Scale: 20 MSec  
 Pos: 0 mDiv  
 Trigger: Edge  
 Level: 2 mV  
 Cou: 27.87 mV

Ch1:W1:1  
 Sd: 50 mV/div  
 Pos: 0 mDiv  
 Cpl: AC  
 Dec: TA: Off  
 BW: 20 MHz


Peak Result 1  
 Peak to peak 77.075 mV

Peak Result 2  
 Peak to peak 90.909 mV


9

10.1.3 *Ripple Waveforms at No-Load*


**Figure 25** – 85 VAC Input.  
Vertical: 50 mV / div.  
Horizontal: 50 ms / div.  
12 V Ripple: 59.289 mV<sub>PK-PK</sub>.  
5 V Ripple: 86.957 mV<sub>PK-PK</sub>.




**Figure 26** – 115 VAC Input.  
Vertical: 50 mV / div.  
Horizontal: 50 ms / div.  
12 V Ripple: 61.265 mV<sub>PK-PK</sub>.  
5 V Ripple: 88.933 mV<sub>PK-PK</sub>.



**Figure 27** – 230 VAC Input.  
Vertical: 50 mV / div.  
Horizontal: 50 ms / div.  
12 V Ripple: 73.123 mV<sub>PK-PK</sub>.  
5 V Ripple: 94.862 mV<sub>PK-PK</sub>.



**Figure 28** – 440 VAC Input.  
Vertical: 50 mV / div.  
Horizontal: 50 ms / div.  
12 V Ripple: 90.909 mV<sub>PK-PK</sub>.  
5 V Ripple: 106.72 mV<sub>PK-PK</sub>.

10.1.4 *Ripple vs. Load***Figure 29** – 5 V Output Ripple vs. Percent Load.





Figure 30 – 12 V Output Ripple vs. Percent Load.






Test conditions: 12 V load set to CC at 500 mA, 5 V load set to CC at 200 mA



**Figure 40 – 115 VAC Input.**  
Upper: PIV, 20 V / div., 10  $\mu$ s / div.  
Lower:  $I_{D(MAX)}$ , 500 mA / div.  
PIV: 37.075 V.  
 $I_{D(MAX)}$ : 3.0810 A.




**Figure 42** – 450 VAC Input.  
Upper: PIV, 20 V / div., 10  $\mu$ s / div.  
Lower:  $I_{D(MAX)}$ , 500 mA / div.  
PIV: 109.80 V.  
 $I_{D(MAX)}$ : 3.4763 A.

## 10.3 Start-up Performance


### 10.3.1 12 V Start-up Operation $V_{IN}$ , $V_{OUT}$ and $I_{OUT}$

Test conditions: 12 V load set to CR at 24  $\Omega$ , 5 V load set to CR at 25  $\Omega$




**Figure 43** – 85 VAC Input.

Upper:  $V_{IN}$ , 200 V / div., 20 ms / div.  
Middle:  $V_{OUT}$ , 2 V / div.  
Lower:  $I_{OUT}$ , 100 mA / div.




**Figure 44** – 115 VAC Input.

Upper:  $V_{IN}$ , 200 V / div., 20 ms / div.  
Middle:  $V_{OUT}$ , 2 V / div.  
Lower:  $I_{OUT}$ , 100 mA / div.



**Figure 45** – 230 VAC Input.

Upper:  $V_{IN}$ , 200 V / div., 20 ms / div.  
Middle:  $V_{OUT}$ , 2 V / div.  
Lower:  $I_{OUT}$ , 100 mA / div.




**Figure 46** – 440 VAC Input.

Upper:  $V_{IN}$ , 200 V / div., 20 ms / div.  
Middle:  $V_{OUT}$ , 2 V / div.  
Lower:  $I_{OUT}$ , 100 mA / div.



### 10.3.2 5 V Start-up Operation $V_{IN}$ , $V_{OUT}$ and $I_{OUT}$

Test conditions: 12 V load set to CR at 24 $\Omega$ , 5 V load set to CR at 25 $\Omega$




**Figure 47** – 85 VAC Input.

Upper:  $V_{IN}$ , 200 V / div., 20 ms / div.

Middle:  $V_{OUT}$ , 1 V / div.

Lower:  $I_{OUT}$ , 50 mA / div.




**Figure 48** – 115 VAC Input.

Upper:  $V_{IN}$ , 200 V / div., 20 ms / div.

Middle:  $V_{OUT}$ , 1 V / div.

Lower:  $I_{OUT}$ , 50 mA / div.




**Figure 49** – 230 VAC Input.

Upper:  $V_{IN}$ , 200 V / div., 20 ms / div.

Middle:  $V_{OUT}$ , 1 V / div.

Lower:  $I_{OUT}$ , 50 mA / div.



**Figure 50** – 440 VAC Input.


Upper:  $V_{IN}$ , 200 V / div., 20 ms / div.

Middle:  $V_{OUT}$ , 1 V / div.

Lower:  $I_{OUT}$ , 50 mA / div.


### 10.3.3 Start-up Operation $V_{DS}$ and $I_{DS}$

Test conditions: 12 V load set to CC at 500 mA, 5 V load set to CC at 200 mA




**Figure 51** – 85 VAC Input.

Upper:  $V_{DS}$ , 200 V / div., 2 ms / div.  
 Lower:  $I_{DS}$ , 200 mA / div.  
 Zoom: 200  $\mu$ s / div.  
 $V_{DS(MAX)}$ : 283.79 V.  
 $I_{DS(MAX)}$ : 560.47 mA.




**Figure 52** – 115 VAC Input.

Upper:  $V_{DS}$ , 200 V / div., 2 ms / div.  
 Lower:  $I_{DS}$ , 200 mA / div.  
 Zoom: 200  $\mu$ s / div.  
 $V_{DS(MAX)}$ : 315.42 V.  
 $I_{DS(MAX)}$ : 513.04 mA.



**Figure 53** – 85 VAC Input.

Upper:  $V_{DS}$ , 200 V / div., 2 ms / div.  
 Lower:  $I_{DS}$ , 200 mA / div.  
 Zoom: 200  $\mu$ s / div.  
 $V_{DS(MAX)}$ : 513.04 V.  
 $I_{DS(MAX)}$ : 821.34 mA.



**Figure 54** – 450 VAC Input.

Upper:  $V_{DS}$ , 200 V / div., 10  $\mu$ s / div.  
 Lower:  $I_{DS}$ , 100 mA / div.  
 $V_{DS(MAX)}$ : 797.63 V.  
 $I_{DS(MAX)}$ : 837.15 mA.


## 10.4 Output Load Transient

### 10.4.1 5 V Output Transient

Test conditions: 5 V load swings from 50 mA to full load, 12 V at full load




**Figure 55** – 85 VAC Input.  
Upper: 5 V  $V_{OUT}$ , 400 mV / div., 10 ms / div.  
Lower: 5 V  $I_{OUT}$ , 100 mA / div.  
 $V_{MAX}$ : 5.2055 V.  
 $V_{MIN}$ : 4.8893 V.



**Figure 56** – 115 VAC Input.  
Upper: 5 V  $V_{OUT}$ , 400 mV / div., 10 ms / div.  
Lower: 5 V  $I_{OUT}$ , 100 mA / div.  
 $V_{MAX}$ : 5.2055 V.  
 $V_{MIN}$ : 4.8893 V.



**Figure 57** – 230 VAC Input.  
Upper: 5 V  $V_{OUT}$ , 400 mV / div., 10 ms / div.  
Lower: 5 V  $I_{OUT}$ , 100 mA / div.  
 $V_{MAX}$ : 5.2372 V.  
 $V_{MIN}$ : 4.8893 V.



**Figure 58** – 440 VAC Input.  
Upper: 5 V  $V_{OUT}$ , 400 mV / div., 10 ms / div.  
Lower: 5 V  $I_{OUT}$ , 100 mA / div.  
 $V_{MAX}$ : 5.2846 V.  
 $V_{MIN}$ : 4.8735 V.


### 10.4.2 12 V Output Transient

Test conditions: 12 V load swings from 50 mA to full load, 5 V at full load



**Figure 59** – 85 VAC Input.

Upper: 12 V  $V_{OUT}$ , 2 V / div., 10 ms / div.  
 Lower: 12 V  $I_{OUT}$ , 200 mA / div.  
 $V_{MAX}$ : 12.791 V.  
 $V_{MIN}$ : 11.842 V.




**Figure 60** – 115 VAC Input.

Upper: 12 V  $V_{OUT}$ , 2 V / div., 10 ms / div.  
 Lower: 12 V  $I_{OUT}$ , 200 mA / div.  
 $V_{MAX}$ : 12.791 V.  
 $V_{MIN}$ : 11.921 V.



**Figure 61** – 230 VAC Input.

Upper: 12 V  $V_{OUT}$ , 2 V / div., 10 ms / div.  
 Lower: 12 V  $I_{OUT}$ , 200 mA / div.  
 $V_{MAX}$ : 12.791 V.  
 $V_{MIN}$ : 11.921 V.




**Figure 62** – 440 VAC Input.

Upper: 12 V  $V_{OUT}$ , 2 V / div., 10 ms / div.  
 Lower: 12 V  $I_{OUT}$ , 200 mA / div.  
 $V_{MAX}$ : 12.870 V.  
 $V_{MIN}$ : 11.842 V.


## 10.5 Fault Waveforms

### 10.5.1 5 V Output Short


Test conditions: Both outputs at full load before short




**Figure 63** – 85 VAC Input.  
Upper: 5 V  $V_{OUT}$ , 1 V / div., 400 ms / div.  
Lower:  $I_{DS}$ , 200 mA / div.



**Figure 64** – 115 VAC Input.  
Upper: 5 V  $V_{OUT}$ , 1 V / div., 400 ms / div.  
Lower:  $I_{DS}$ , 200 mA / div.




**Figure 65** – 230 VAC Input.  
Upper: 5 V  $V_{OUT}$ , 1 V / div., 400 ms / div.  
Lower:  $I_{DS}$ , 200 mA / div.




**Figure 66** – 440 VAC Input.  
Upper: 5 V  $V_{OUT}$ , 1 V / div., 400 ms / div.  
Lower:  $I_{DS}$ , 200 mA / div.

## 10.5.2 12 V Output Short


Test conditions: Both outputs at full load before short

**Figure 67** – 85 VAC Input.


Upper: 12 V  $V_{OUT}$ , 2 V / div., 400 ms / div.  
 Lower:  $I_{DS}$ , 200 mA / div.

**Figure 68** – 115 VAC Input.

Upper: 12 V  $V_{OUT}$ , 2 V / div., 400 ms / div.  
 Lower:  $I_{DS}$ , 200 mA / div.

**Figure 69** – 230 VAC Input.


Upper: 12 V  $V_{OUT}$ , 2 V / div., 400 ms / div.  
 Lower:  $I_{DS}$ , 200 mA / div.

**Figure 70** – 440 VAC Input.


Upper: 12 V  $V_{OUT}$ , 2 V / div., 400 ms / div.  
 Lower:  $I_{DS}$ , 200 mA / div.

### 10.5.3 Line Overvoltage

Test conditions: VR1 Zener diode voltage rating set to 102 V, OVP at 520 VAC<sub>RMS</sub>



**Figure 71** – Line +OV at 520 VAC<sub>RMS</sub>.  
Upper: 12 V V<sub>OUT</sub>, 2 V / div., 400 ms / div.  
Lower: I<sub>DS</sub>, 200 mA / div.




**Figure 72** – Line -OV.  
Upper: 12 V V<sub>OUT</sub>, 2 V / div., 400 ms / div.  
Lower: I<sub>DS</sub>, 200 mA / div.



## 11 Thermal Performance

### 11.1 Test Set-Up

Thermal evaluation was performed under two conditions: (1) room temperature with the circuit board enclosed inside an acrylic box and (2), 50 °C ambient inside a thermal chamber. In both conditions, the circuit is soaked for two hours under full load conditions.



**Figure 73** – Thermal Performance Set-up Using an Acrylic Box.




**Figure 74** – Thermal Performance Set-up Using Thermal Chamber.




## 11.2 Room Temperature

### 11.2.1 85 VAC @ Room Temperature


| Ambient<br>(°C) | LinkSwitch-XT2 900 V<br>(U1) | Transformer<br>(T1) | 12 V Output Diode<br>(T2) | Bridge Rectifier<br>(BR1) |
|-----------------|------------------------------|---------------------|---------------------------|---------------------------|
| 27              | 53.3                         | 60.0                | 71.0                      | 47.3                      |




**Figure 75** – Ambient = 27.5 °C.  
LNK-XT2-900, U1 = 53.3 °C.



**Figure 76** – Ambient = 27.5 °C.  
Transformer, T1 = 60.0 °C.




**Figure 77** – Ambient = 27.6 °C.  
12 V Diode, D4 = 71.0 °C.




**Figure 78** – Ambient = 27.6 °C.  
Bridge Rectifier, BR1 = 47.3 °C.

## 11.2.2 440 VAC @ Room Temperature


| Ambient (°C) | LinkSwitch-XT2 900 V (U1) | Transformer (T1) | 12 V Output Diode (T2) | Bridge Rectifier (BR1) |
|--------------|---------------------------|------------------|------------------------|------------------------|
| 27           | 54.6                      | 63.1             | 78.4                   | 37.0                   |




**Figure 79** – Ambient = 26.5 °C.  
LNK-XT2-900, U1 = 54.6 °C.



**Figure 80** – Ambient = 26.5 °C.  
Transformer, T1 = 63.1 °C.




**Figure 81** – Ambient = 27.2 °C.  
12 V Diode, D4 = 78.4 °C.



**Figure 82** – Ambient = 28.1 °C.  
Bridge Rectifier, BR1 = 37.0 °C.

### 11.3 50 °C Ambient

#### 11.3.1 85 VAC @ 50 °C



**Figure 83 —** Component Temperatures at 50 °C Ambient.

11.3.2 440 VAC @ 50 °C





Figure 84 — Component Temperatures at 50 °C Ambient.

## 12 Conducted EMI

### 12.1 EMI Equipment and Load

1. Rohde and Schwarz ENV216 two line V-network.
2. Rohde and Schwarz ESRP EMI test receiver.
3. Hioki 3322 power hitester.
4. Chroma measurement test fixture, model A662003.
5. Resistor load with input voltage set at 115 VAC.

### 12.2 Test Set-up




**Figure 85** — Conducted EMI Test Set-up.




## 12.3 EMI Test Results

### 12.3.1 115 VAC, Floating Output



**Figure 86 – Line.**


Upper: Lowest Peak Delta Limit:  
-16.63 dB, 523.50 kHz.  
Lower: Lowest Average Delta Limit:  
-19.13 dB, 525.75 kHz.



**Figure 87 – Neutral.**


Upper: Lowest Peak Delta Limit:  
-15.29 dB, 523.50 kHz.  
Lower: Lowest Average Delta Limit:  
-18.03 dB, 525.75 kHz.

### 12.3.2 230 VAC, Floating Output



**Figure 88 – Line.**

Upper: Lowest Peak Delta Limit:  
-9.80 dB, 150.00 kHz.  
Lower: Lowest Average Delta Limit:  
-18.92 dB, 530.25 kHz.



**Figure 89 – Neutral.**

Upper: Lowest Peak Delta Limit:  
-9.93 dB, 150.00 kHz.  
Lower: Lowest Average Delta Limit:  
-17.99 dB, 530.25 kHz.

## 13 Line Surge

The unit was subject to  $\pm 2000$  V, 100 kHz ring wave, and  $\pm 1000$  V differential surge test using 10 strikes at each condition. A test failure is defined as a non-recoverable interruption of output requiring repair or recycling of input voltage.

### 13.1 Differential Surge Test

| Surge Voltage (kV) | Phase Angle (°) | IEC Coupling | Generator Impedance ( $\Omega$ ) | Number Strikes | Result |
|--------------------|-----------------|--------------|----------------------------------|----------------|--------|
| +1                 | 0               | L1 / L2      | 2                                | 10             | PASS   |
| -1                 | 0               | L1 / L2      | 2                                | 10             | PASS   |
| +1                 | 90              | L1 / L2      | 2                                | 10             | PASS   |
| -1                 | 90              | L1 / L2      | 2                                | 10             | PASS   |
| +1                 | 180             | L1 / L2      | 2                                | 10             | PASS   |
| -1                 | 180             | L1 / L2      | 2                                | 10             | PASS   |
| +1                 | 270             | L1 / L2      | 2                                | 10             | PASS   |
| -1                 | 270             | L1 / L2      | 2                                | 10             | PASS   |

**Note:** In all PASS results, no damage and no auto-restart was observed.

### 13.2 Ring Wave Test

| Ring Wave Voltage (kV) | Phase Angle (°) | IEC Coupling | Generator Impedance ( $\Omega$ ) | Number Strikes | Result |
|------------------------|-----------------|--------------|----------------------------------|----------------|--------|
| +2                     | 0               | L1 / L2      | 12                               | 10             | PASS   |
| -2                     | 0               | L1 / L2      | 12                               | 10             | PASS   |
| +2                     | 90              | L1 / L2      | 12                               | 10             | PASS   |
| -2                     | 90              | L1 / L2      | 12                               | 10             | PASS   |
| +2                     | 180             | L1 / L2      | 12                               | 10             | PASS   |
| -2                     | 180             | L1 / L2      | 12                               | 10             | PASS   |
| +2                     | 270             | L1 / L2      | 12                               | 10             | PASS   |
| -2                     | 270             | L1 / L2      | 12                               | 10             | PASS   |

**Note:** In all PASS results, no damage and no auto-restart was observed.

## 14 Revision History

| Date      | Author   | Revision | Description & Changes                                  | Reviewed    |
|-----------|----------|----------|--------------------------------------------------------|-------------|
| 26-Sep-18 | IB & JPB | 1.0      | Initial Release.                                       | Mktg & Apps |
| 26-Oct-18 | IB       | 1.1      | Updated Section 8 Transformer Design Spreadsheet.      | Mktg & Apps |
| 30-Jun-20 | KM       | 1.2      | Updated Transformer Assembly Section. Converted to RDR | Mktg & Apps |
|           |          |          |                                                        |             |
|           |          |          |                                                        |             |



**For the latest updates, visit our website: [www.power.com](http://www.power.com)**

Reference Designs are technical proposals concerning how to use Power Integrations' gate drivers in particular applications and/or with certain power modules. These proposals are "as is" and are not subject to any qualification process. The suitability, implementation and qualification are the sole responsibility of the end user. The statements, technical information and recommendations contained herein are believed to be accurate as of the date hereof. All parameters, numbers, values and other technical data included in the technical information were calculated and determined to our best knowledge in accordance with the relevant technical norms (if any). They may base on assumptions or operational conditions that do not necessarily apply in general. We exclude any representation or warranty, express or implied, in relation to the accuracy or completeness of the statements, technical information and recommendations contained herein. No responsibility is accepted for the accuracy or sufficiency of any of the statements, technical information, recommendations or opinions communicated and any liability for any direct, indirect or consequential loss or damage suffered by any person arising therefrom is expressly disclaimed.

Power Integrations reserves the right to make changes to its products at any time to improve reliability or manufacturability. Power Integrations does not assume any liability arising from the use of any device or circuit described herein. POWER INTEGRATIONS MAKES NO WARRANTY HEREIN AND SPECIFICALLY DISCLAIMS ALL WARRANTIES INCLUDING, WITHOUT LIMITATION, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF THIRD PARTY RIGHTS.

**Patent Information**

The products and applications illustrated herein (including transformer construction and circuits' external to the products) may be covered by one or more U.S. and foreign patents, or potentially by pending U.S. and foreign patent applications assigned to Power Integrations. A complete list of Power Integrations' patents may be found at [www.power.com](http://www.power.com). Power Integrations grants its customers a license under certain patent rights as set forth at <http://www.power.com/ip.htm>.

The PI Logo, TOPSwitch, TinySwitch, LinkSwitch, LYTSwitch, InnoSwitch, DPA-Switch, PeakSwitch, CAPZero, SENZero, LinkZero, HiperPFS, HiperTFS, HiperLCS, Qspeed, EcoSmart, Clampless, E-Shield, Filterfuse, FluxLink, StackFET, PI Expert and PI FACTS are trademarks of Power Integrations, Inc. Other trademarks are property of their respective companies. ©Copyright 2015 Power Integrations, Inc.

**Power Integrations Worldwide Sales Support Locations****WORLD HEADQUARTERS**

5245 Hellyer Avenue  
San Jose, CA 95138, USA.  
Main: +1-408-414-9200  
Customer Service:  
Phone: +1-408-414-9665  
Fax: +1-408-414-9765  
e-mail: [usasales@power.com](mailto:usasales@power.com)

**GERMANY**

(IGBT Driver Sales)  
HellwegForum 1  
59469 Ense, Germany  
Tel: +49-2938-64-39990  
Email: [igbt-driver.sales@power.com](mailto:igbt-driver.sales@power.com)

**KOREA**

RM 602, 6FL  
Korea City Air Terminal B/D,  
159-6  
Samsung-Dong, Kangnam-Gu,  
Seoul, 135-728 Korea  
Phone: +82-2-2016-6610  
Fax: +82-2-2016-6630  
e-mail: [koreasales@power.com](mailto:koreasales@power.com)

**CHINA (SHANGHAI)**

Rm 2410, Charity Plaza, No. 88,  
North Caoxi Road,  
Shanghai, PRC 200030  
Phone: +86-21-6354-6323  
Fax: +86-21-6354-6325  
e-mail: [chinasales@power.com](mailto:chinasales@power.com)

**INDIA**

#1, 14<sup>th</sup> Main Road  
Vasanthanagar  
Bangalore-560052  
India  
Phone: +91-80-4113-8020  
Fax: +91-80-4113-8023  
e-mail: [indiasales@power.com](mailto:indiasales@power.com)

**SINGAPORE**

51 Newton Road,  
#19-01/05 Goldhill Plaza  
Singapore, 308900  
Phone: +65-6358-2160  
Fax: +65-6358-2015  
e-mail: [singaporesales@power.com](mailto:singaporesales@power.com)

**CHINA (SHENZHEN)**

17/F, Hivac Building, No. 2, Keji  
Nan 8th Road, Nanshan District,  
Shenzhen, China, 518057  
Phone: +86-755-8672-8689  
Fax: +86-755-8672-8690  
e-mail: [chinasales@power.com](mailto:chinasales@power.com)

**ITALY**

Via Milanese 20, 3<sup>rd</sup> Fl.  
20099 Sesto San Giovanni (MI)  
Italy  
Phone: +39-024-550-8701  
Fax: +39-028-928-6009  
e-mail: [eurossales@power.com](mailto:eurossales@power.com)

**TAIWAN**

5F, No. 318, Nei Hu Rd.,  
Sec. 1  
Nei Hu District  
Taipei 11493, Taiwan R.O.C.  
Phone: +886-2-2659-4570  
Fax: +886-2-2659-4550  
e-mail: [taiwansales@power.com](mailto:taiwansales@power.com)

**GERMANY**

(AC-DC/LED Sales)  
Lindwurmstrasse 114  
80337, Munich  
Germany  
Phone: +49-895-527-39110  
Fax: +49-895-527-39200  
e-mail: [eurossales@power.com](mailto:eurossales@power.com)

**JAPAN**

Kosei Dai-3 Building  
2-12-11, Shin-Yokohama,  
Kohoku-ku, Yokohama-shi,  
Kanagawa 222-0033  
Japan  
Phone: +81-45-471-1021  
Fax: +81-45-471-3717  
e-mail: [japansales@power.com](mailto:japansales@power.com)

**UK**

Cambridge Semiconductor,  
a Power Integrations company  
Westbrook Centre, Block 5, 2nd  
Floor  
Milton Road  
Cambridge CB4 1YG  
Phone: +44 (0) 1223-446483  
e-mail: [eurossales@power.com](mailto:eurossales@power.com)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Power Integrations:](#)

[RDK-736](#)