

### Description

The [SiT3373](#) is a 220.000001 MHz to 725 MHz differential MEMS VCXO engineered for low-jitter applications. Utilizing SiTime's unique DualMEMS® temperature sensing and TurboCompensation® technology, the SiT3373 delivers exceptional dynamic performance by providing resistance to airflow, thermal gradients, shock and vibration. This device also integrates multiple on-chip regulators to filter power supply noise, eliminating the need for a dedicated external LDO.

The SiT3373 can be factory programmed for any combination of frequency, stability, voltage, output signaling, and pull range. Programmability enables designers to optimize clock configurations while eliminating long lead times and customization costs associated with quartz devices where each frequency is custom built.

The wide frequency range and programmability makes this device ideal for telecom, networking, and industrial applications that require a variety of pullable frequencies and operate in noisy environments.

Refer to [Manufacturing Notes](#) for proper reflow profile, tape and reel dimension, and other manufacturing related information.

### Features

- Any frequency between 220.000001 MHz and 725 MHz accurate to 6 decimal places  
(For frequencies 1 MHz to 220 MHz, refer to [SiT3372](#))
- Widest pull range options:  $\pm 25$ ,  $\pm 50$ ,  $\pm 80$ ,  $\pm 100$ ,  $\pm 150$ ,  $\pm 200$ ,  $\pm 400$ ,  $\pm 800$ ,  $\pm 1600$ ,  $\pm 3200$  ppm
- 0.225 ps RMS phase jitter (typ) over 12 kHz to 20 MHz bandwidth
- Frequency stability as low as  $\pm 15$  ppm
- Wide temperature range support from  $-40^{\circ}\text{C}$  to  $105^{\circ}\text{C}$
- Industry-standard packages: 7.0 x 5.0 mm, 5.0 x 3.2 mm, 3.2 x 2.5 mm packages

### Applications

- Cable Modem Termination System (CMTS), Video, Broadcasting System, Audio, Industrial Sensors, Remote Radio Head (RRH)
- SATA, SAS, 10/40/100/400 Gbps Ethernet, Fibre Channel, PCI-Express
- Optical Transport Network (OTN)



INSTANT  
SAMPLES



SEARCH  
INVENTORY



GREEN  
SOLUTIONS



LIFETIME  
WARRANTY

### Block Diagram




Figure 1. SiT3373 Block Diagram

### 3.2 x 2.5 mm Package Pinout





Figure 2. Pin Assignments (Top view)  
(Refer to [Table 6](#) for Pin Descriptions)

Ordering Information



- Notes:
- 1. Bulk is available for sampling only.
  - 2. [Contact SiTime](#) for custom pull range options.
  - 3. "E": Output Enable function is only available in 7.0 x 5.0 mm and 5.0 x 3.2 mm packages.

Table 1. Ordering Codes for Supported Tape & Reel Packing Method

Device Size (mm x mm)	8 mm T&R (3ku)	8 mm T&R (1ku)	12 mm T&R (3ku)	12 mm T&R (1ku)	16 mm T&R (3ku)	16 mm T&R (1ku)
7.0 x 5.0	–	–	–	–	T	Y
5.0 x 3.2	–	–	T	Y	–	–
3.2 x 2.5	D	E	T	Y	–	–

**TABLE OF CONTENTS**

Description.....1

Features .....1

Applications .....1

Block Diagram .....1

Ordering Information.....2

Electrical Characteristics .....4

Waveform Diagrams .....10

Timing Diagrams .....11

Termination Diagrams .....12

    LVPECL.....12

    LVDS .....13

    HCSL.....13

Dimensions and Patterns — 3.2 x 2.5 mm .....14

Dimensions and Patterns — 5.0 x 3.2 mm .....14

Dimensions and Patterns — 7.0 x 5.0 mm .....15

Additional Information .....16

Revision History.....17

## Electrical Characteristics

**Table 2. Electrical Characteristics – Common to LVPECL, LVDS and HCSL**

All Min and Max limits in the Electrical Characteristics tables are specified over temperature and rated operating voltage with standard output termination shown in the termination diagrams. Typical values are at 25°C and nominal supply voltage.

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Frequency Range						
Output Frequency Range	f	220.000001	–	725	MHz	Accurate to 6 decimal places
Frequency Stability						
Frequency Stability	F_stab	-15	–	+15	ppm	Inclusive of initial tolerance, operating temperature, rated power supply voltage, load variations, and first year aging at 25°C, with VIN voltage at Vdd/2. ±15 ppm is only guaranteed for pull range up to ±100 ppm.
		-25	–	+25	ppm	
		-35	–	+35	ppm	
		-50	–	+50	ppm	
Temperature Range						
Operating Temperature Range	T_use	-20	–	+70	°C	Extended Commercial
		-40	–	+85	°C	Industrial
		-40	–	+95	°C	
		-40	–	+105	°C	Extended Industrial
Supply Voltage						
Supply Voltage	Vdd	2.97	3.30	3.63	V	
		2.70	3.00	3.30	V	
		2.52	2.80	3.08	V	
		2.25	2.50	2.75	V	
Voltage Control Characteristics						
Pull Range	PR	±25, ±50, ±80, ±100, ±150, ±200, ±400, ±800, ±1600, ±3200			ppm	See the APR (Absolute Pull Range) <a href="#">Table 11</a> . <a href="#">Contact SiTime</a> for custom pull range options
Upper Control Voltage	VC_U	90%	–	–	Vdd	Voltage at which maximum frequency deviation is guaranteed
Lower Control Voltage	VC_L	–	–	10%	Vdd	Voltage at which minimum frequency deviation is guaranteed
Control Voltage Input Impedance	VC_z	–	10	–	MΩ	
Control Voltage Input Bandwidth	V_c	–	10	–	kHz	<a href="#">Contact SiTime</a> for other input bandwidth options
Pull Range Linearity	Lin	–	–	1.0	%	
Frequency Change Polarity	–	Positive Slope			–	
Input Characteristics						
Input Voltage High	VIH	70%	–	–	Vdd	Pin 2, OE
Input Voltage Low	VIL	–	–	30%	Vdd	Pin 2, OE
Input Pull-up Impedance	Z_in	–	100	-	kΩ	Pin 2, OE logic high or logic low
Output Characteristics						
Duty Cycle	DC	45	–	55	%	
Startup and OE Timing						
Start-up Time	T_start	–	–	3.0	ms	Measured from the time Vdd reaches its rated minimum value.
OE Enable/Disable Time	T_oe	–	–	3.8	μs	f = 322.265625 MHz. Measured from the time OE pin reaches rated VIH and VIL to the time clock pins reach 90% of swing and high-Z. See <a href="#">Figure 9</a> and <a href="#">Figure 10</a>

Table 3. Electrical Characteristics – LVPECL Specific

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Current Consumption						
Current Consumption	I <sub>dd</sub>	–	–	97	mA	Excluding Load Termination Current, V <sub>dd</sub> = 3.3 V or 2.5 V
OE Disable Supply Current	I <sub>OE</sub>	–	–	63	mA	OE = Low
Output Disable Leakage Current	I <sub>leak</sub>	–	0.15	–	μA	OE = Low
Maximum Output Current	I <sub>driver</sub>	–	–	32	mA	Maximum average current drawn from OUT+ or OUT-
Output Characteristics						
Output High Voltage	VOH	V <sub>dd</sub> -1.15	–	V <sub>dd</sub> -0.7	V	See Figure 5
Output Low Voltage	VOL	V <sub>dd</sub> -1.9	–	V <sub>dd</sub> -1.5	V	See Figure 5
Output Differential Voltage Swing	V <sub>Swing</sub>	1.2	1.6	2.0	V	See Figure 6
Rise/Fall Time	Tr, Tf	–	225	290	ps	20% to 80%, see Figure 6
Jitter – 7.0 x 5.0 mm Package						
RMS Period Jitter <sup>[4]</sup>	T <sub>jitt</sub>	–	1.0	1.6	ps	f = 322.265625 MHz, V <sub>dd</sub> = 3.3 V or 2.5 V
RMS Phase Jitter (random)	T <sub>phj</sub>	–	0.220	0.270	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -20 to 70°C and -40 to 85°C
		–	0.220	0.300	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -40 to 95°C and -40 to 105°C
		–	0.1	–	ps	f = 156.25 or 322.265625 MHz, IEEE802.3-2005 10 GbE jitter mask integration bandwidth = 1.875 MHz to 20 MHz, all V <sub>dd</sub> levels
Jitter – 5.0 x 3.2 mm and 3.2 x 2.5 mm Packages						
RMS Period Jitter <sup>[4]</sup>	T <sub>jitt</sub>	–	1.0	1.6	ps	f = 322.265625 MHz, V <sub>dd</sub> = 3.3 V or 2.5 V
RMS Phase Jitter (random)	T <sub>phj</sub>	–	0.225	0.282	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -20 to 70°C and -40 to 85°C
		–	0.225	0.315	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -40 to 95°C and -40 to 105°C
		–	0.1	–	ps	f = 322.265625 MHz, IEEE802.3-2005 10 GbE jitter mask integration bandwidth = 1.875 MHz to 20 MHz, all V <sub>dd</sub> levels

**Notes:**

4. Measured according to JESD65B.

Table 4. Electrical Characteristics – LVDS Specific

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Current Consumption						
Current Consumption	I <sub>dd</sub>	–	–	89	mA	Excluding Load Termination Current, V <sub>dd</sub> = 3.3 V or 2.5 V
OE Disable Supply Current	I <sub>OE</sub>	–	–	67	mA	OE = Low
Output Disable Leakage Current	I <sub>leak</sub>	–	0.15	–	μA	OE = Low
Output Characteristics						
Differential Output Voltage	V <sub>OD</sub>	250	–	450	mV	See Figure 7
Delta V <sub>OD</sub>	ΔV <sub>OD</sub>	–	–	50	mV	See Figure 7
Offset Voltage	V <sub>OS</sub>	1.125	–	1.375	V	See Figure 7
Delta V <sub>OS</sub>	ΔV <sub>OS</sub>	–	–	50	mV	See Figure 7
Rise/Fall Time	T <sub>r</sub> , T <sub>f</sub>	–	370	470	ps	Measured with 2 pF capacitive loading to GND, 20% to 80%, see Figure 8
Jitter – 7.0 x 5.0 mm package						
RMS Period Jitter <sup>[5]</sup>	T <sub>jitt</sub>	–	0.92	1.6	ps	f = 322.265625 MHz, V <sub>dd</sub> = 3.3V or 2.5V
RMS Phase Jitter (random)	T <sub>phj</sub>	–	0.215	0.265	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -20 to 70°C and -40 to 85°C
		–	0.215	0.280	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -40 to 95°C and -40 to 105°C
		–	0.1	–	ps	f = 322.265625 MHz, IEEE802.3-2005 10 GbE jitter mask integration bandwidth = 1.875 MHz to 20 MHz, includes spurs, all V <sub>dd</sub> levels
Jitter – 5.0 x 3.2 mm and 3.2 x 2.5 mm packages						
RMS Period Jitter <sup>[5]</sup>	T <sub>jitt</sub>	–	0.92	1.6	ps	f = 322.265625 MHz, V <sub>dd</sub> = 3.3 V or 2.5 V
RMS Phase Jitter (random)	T <sub>phj</sub>	–	0.235	0.282	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -20 to 70°C and -40 to 85°C
		–	0.235	0.310	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -40 to 95°C and -40 to 105°C
		–	0.1	–	ps	f = 322.265625 MHz, IEEE802.3-2005 10 GbE jitter mask integration bandwidth = 1.875 MHz to 20 MHz, includes spurs, all V <sub>dd</sub> levels

**Notes:**

5. Measured according to JESD65B.

**Table 5. Electrical Characteristics – HCSL Specific**

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Current Consumption						
Current Consumption	I <sub>dd</sub>	–	–	102	mA	Excluding Load Termination Current, V <sub>dd</sub> = 3.3 V or 2.5 V
OE Disable Supply Current	I <sub>OE</sub>	–	–	67	mA	OE = Low
Output Disable Leakage Current	I <sub>leak</sub>	–	0.15	–	μA	OE = Low
Output Characteristics						
Output High Voltage	VOH	0.6	–	0.90	V	See <a href="#">Figure 5</a>
Output Low Voltage	VOL	-0.05	–	0.08	V	See <a href="#">Figure 5</a>
Output Differential Voltage Swing	V <sub>Swing</sub>	1.2	1.4	1.8	V	See <a href="#">Figure 6</a>
Rise/Fall Time	T <sub>r</sub> , T <sub>f</sub>	–	360	470	ps	Measured with 2 pF capacitive loading to GND, 20% to 80%, see <a href="#">Figure 6</a>
Jitter – 7.0 x 5.0 mm package						
RMS Period Jitter <sup>[6]</sup>	T <sub>jitt</sub>	–	1.0	1.6	ps	f = 322.265625 MHz, V <sub>dd</sub> = 3.3 V or 2.5 V
RMS Phase Jitter (random)	T <sub>phj</sub>	–	0.215	0.265	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, Pull Range = ±100 ppm
		–	0.215	0.282	ps	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -20 to 70°C and -40 to 85°C
		–	0.1	–	ps	f = 322.265625 MHz, IEEE802.3-2005 10 GbE jitter mask integration bandwidth = 1.875 MHz to 20 MHz, includes spurs, all V <sub>dd</sub> levels
Jitter – 5.0 x 3.2 mm and 3.2 x 2.5 mm packages						
RMS Period Jitter <sup>[6]</sup>	T <sub>jitt</sub>	–	1.0	1.6	ps	f = 322.265625 MHz, V <sub>dd</sub> = 3.3 V or 2.5 V
RMS Phase Jitter (random)	T <sub>phj</sub>	–	0.235	0.282	0.215	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -20 to 70°C and -40 to 85°C
		–	0.235	0.305	0.215	f = 322.265625 MHz, Integration bandwidth = 12 kHz to 20 MHz, all V <sub>dd</sub> levels, includes spurs, pull range = ±100 ppm. Temperature ranges -40 to 95°C and -40 to 105°C
		–	0.1	–	0.1	f = 322.265625 MHz, IEEE802.3-2005 10 GbE jitter mask integration bandwidth = 1.875 MHz to 20 MHz, includes spurs, all V <sub>dd</sub> levels

**Notes:**

6. Measured according to JESD65B.

Table 6. Pin Description

Pin	Symbol	Functionality	
1	VIN	Input	Control Voltage
2	NC/OE	No Connect (NC)	No Connect: Leave floating or connect to GND for better heat dissipation. NC for all 3.2 x 2.5 mm package options.
		Output Enable (OE)	H <sup>[7,8]</sup> : specified frequency output L: output is high impedance. Only output driver is disabled. OE function only available on 7050 and 5032 packages. Pin 2 on 3225 package is NC.
3	GND	Power	Vdd Power Supply Ground
4	OUT+	Output	Oscillator output
5	OUT-	Output	Complementary oscillator output
6	VDD	Power	Power supply voltage <sup>[9]</sup>




Figure 3. Pin Assignments  
(7.0 x 5.0 mm and  
5.0 x 3.2 mm packages)




Figure 4. Pin Assignments  
(3.2 x 2.5 mm package)

Notes:

7. A pull-up resistor of 10 kΩ or less is recommended if pin 1 is not externally driven.

8. OE mode is only available in the 7050 and 5032 packages. 3225 package is NC.

9. A capacitor of value 0.1 μF or higher between VDD and GND is required. An additional 10 μF capacitor between VDD and GND is required for the best phase jitter performance.



**Table 7. Absolute Maximum Ratings**

Attempted operation outside the absolute maximum ratings may cause permanent damage to the part.  
Actual performance of the IC is only guaranteed within the operational specifications, not at absolute maximum ratings.

Parameter	Min.	Max.	Unit
Continuous Power Supply Voltage Range (Vdd)	-0.5	4.0	V
Input Voltage, Maximum (any input pin)		Vdd + 0.3V	V
Input Voltage, Minimum (any input pin)	-0.3		V
Storage Temperature	-65	150	°C
Maximum Junction Temperature		145	°C
Soldering Temperature (follow standard Pb-free soldering guidelines)		260	°C

**Table 8. Thermal Considerations<sup>[10]</sup>**

Package	$\theta_{JA}$ , 4 Layer Board (°C/W)	$\theta_{JC}$ , Bottom (°C/W)
3225, 6-pin	80	30
5032, 6-pin	53 <sup>[11]</sup>	20
7050, 6-pin	52 <sup>[11]</sup>	19

**Notes:**

10. Refer to JESD51 for  $\theta_{JA}$  and  $\theta_{JC}$  definitions, and reference layout used to determine the  $\theta_{JA}$  and  $\theta_{JC}$  values in the above table.  
11. Value for  $\theta_{JA}$  assumes the center pad is soldered down.

**Table 9. Maximum Operating Junction Temperature<sup>[12]</sup>**

Max Operating Temperature (ambient)	Maximum Operating Junction Temperature: 3225 Package	Maximum Operating Junction Temperature: 5032, 7050 Packages
70°C	105°C	95°C
85°C	130°C	110°C
95°C	130°C	120°C
105°C	145°C	130°C


**Notes:**

12. Datasheet specifications are not guaranteed if junction temperature exceeds the maximum operating junction temperature.


**Table 10. Environmental Compliance**

Parameter	Test Conditions	Value	Unit
Mechanical Shock Resistance	MIL-STD-883F, Method 2002	10,000	g
Mechanical Vibration Resistance	MIL-STD-883F, Method 2007	70	g
Soldering Temperature (follow standard Pb free soldering guidelines)	MIL-STD-883F, Method 2003	260	°C
Moisture Sensitivity Level	MSL1 @ 260°C		
Electrostatic Discharge (HBM)	HBM, JESD22-A114	2,000	V
Charge-Device Model ESD Protection	JESD220C101	750	V
Latch-up Tolerance	JESD78 Compliant		

**Waveform Diagrams**




**Figure 5. LVPECL, HCSL Voltage Levels per Differential Pin (i.e. OUT+, or OUT-)**




**Figure 6. LVPECL, HCSL Voltage Levels across Differential Pair (i.e. OUT+ minus OUT-)**

**Waveform Diagrams (continued)**




**Figure 7. LVDS Voltage Levels per Differential Pin (i.e. OUT+, or OUT-)**




**Figure 8. LVDS Differential Waveform (i.e. OUT+ minus OUT-)**

**Timing Diagrams**



**Figure 9. Hardware OE Enable Timing**



**Figure 10. Hardware OE Disable Timing**

Termination Diagrams

LVPECL




Figure 11. LVPECL with AC-coupled termination




Figure 12. LVPECL DC-coupled load termination with Thevenin equivalent network




Figure 13. LVPECL with Y-Bias termination






Figure 14. LVPECL with DC-coupled parallel shunt load termination

**Termination Diagrams (continued)**


**LVDS**



**Figure 15. LVDS single DC termination at the load**




**Figure 16. LVDS double AC termination with capacitor close to the load**




**Figure 17. LVDS double DC termination**

**HCSL**




**Figure 18. HCSL interface termination**

Dimensions and Patterns — 3.2 x 2.5 mm




Dimensions and Patterns — 5.0 x 3.2 mm



- Notes:
13. Top Marking: Y denotes manufacturing origin and XXXX denotes manufacturing lot number. The value of “Y” will depend on the assembly location of the device.
  14. A capacitor of value 0.1  $\mu$ F or higher between VDD and GND is required. An additional 10  $\mu$ F capacitor between VDD and GND is required for the best phase jitter performance.
  15. The center pad is internally connected to the GND pin. Soldering down the center pad to the GND is recommended for best thermal dissipation, but is optional.

Dimensions and Patterns — 7.0 x 5.0 mm



- Notes:
- 16. Top Marking: Y denotes manufacturing origin and XXXX denotes manufacturing lot number. The value of “Y” will depend on the assembly location of the device.
  - 17. A capacitor of value 0.1  $\mu$ F or higher between VDD and GND is required. An additional 10  $\mu$ F capacitor between VDD and GND is required for the best phase jitter performance.
  - 18. The center pad is internally connected to the GND pin. Soldering down the center pad to the GND is recommended for best thermal dissipation, but is optional.

**Table 11. APR Table**

Absolute pull range (APR) = Nominal pull range (PR) - frequency stability (F\_stab) - aging<sup>[19]</sup>

Nominal Pull Range	Frequency Stability			
	±15	±25	±35	±50
	APR (ppm)			
±25	±5	—	—	—
±50	±30	±20	±10	—
±80	±60	±50	±40	±25
±100	±80	±70	±60	±45
±150	—	±120	±110	±95
±200	—	±170	±160	±145
±400	—	±370	±360	±345
±800	—	±770	±760	±745
±1600	—	±1570	±1560	±1545
±3200	—	±3170	±3160	±3145

**Note:**

19. Aging includes solder down shift and 20-year aging.

## Additional Information

**Table 12. Additional Information**

Document	Description	Download Link
<b>ECCN #: EAR99</b>	Five character designation used on the commerce Control List (CCL) to identify dual use items for export control purposes.	—
<b>HTS Classification Code: 8542.39.0000</b>	A Harmonized Tariff Schedule (HTS) code developed by the World Customs Organization to classify/define internationally traded goods.	—
<b>Part number Generator</b>	Tool used to create the part number based on desired features.	<a href="https://www.sitime.com/part-number-generator">https://www.sitime.com/part-number-generator</a>
<b>Time Machine II</b>	MEMS oscillator programmer	<a href="http://www.sitime.com/support/time-machine-oscillator-programmer">http://www.sitime.com/support/time-machine-oscillator-programmer</a>
<b>Manufacturing Notes</b>	Tape & Reel dimension, reflow profile and other manufacturing related info	<a href="https://www.sitime.com/sites/default/files/gated/Manufacturing-Notes-for-SiTime-Products.pdf">https://www.sitime.com/sites/default/files/gated/Manufacturing-Notes-for-SiTime-Products.pdf</a>
<b>Qualification Reports</b>	RoHS report, reliability reports, composition reports	<a href="http://www.sitime.com/support/quality-and-reliability">http://www.sitime.com/support/quality-and-reliability</a>
<b>Performance Reports</b>	Additional performance data such as phase noise, current consumption, and jitter for selected frequencies	<a href="http://www.sitime.com/support/performance-measurement-report">http://www.sitime.com/support/performance-measurement-report</a>
<b>Termination Techniques</b>	AN10029 Termination design recommendations	<a href="http://www.sitime.com/support/application-notes">http://www.sitime.com/support/application-notes</a>
<b>Layout Techniques</b>	AN10006 Layout recommendations	<a href="http://www.sitime.com/support/application-notes">http://www.sitime.com/support/application-notes</a>
<b>Evaluation Boards</b>	SiT6085EB, SiT6086EB and SiT6097EB for Differential Oscillators	<a href="https://www.sitime.com/support/user-guides">https://www.sitime.com/support/user-guides</a>



## Revision History

Table 13. Revision History

Revision	Release Date	Change Summary
1.0	13-Oct-2017	Initial release
1.01	2-Feb-2018	Corrected ppm ordering codes. Corrected minor formatting errors. Added Additional Information table. Added Extended Industrial temperature range (-40°C – 95°C and -40°C – 105°C )
1.03	10-May-2018	Updated the Part Ordering info with added 5.0 x 3.2 mm package
1.04	29-Oct-2018	±15 ppm option
1.05	7-Jun-2020	Formatting updates Corrected typos Updated package Dimensions Drawings Updated Table 8 Thermal Considerations for 5032 package Added Evaluation Boards SiT6085EB reference in Additional Information Rearranged layout, added Description, Block Diagram and TOC Added HTS classification code Clarified ±15 ppm pull range up to ±100 ppm Modified maximum junction temperatures Removed I <sub>driver</sub> HCSL specification as not applicable
1.06	17-Mar-2021	Updated L1 and Dimple Width package dimensions for 3.2 x 2.5 mm package Updated trademarks and changed rev table date format
1.07	20-Jul-2021	Updated pin direction in package dimensions for 3.2 x 2.5 mm package

**SiTime Corporation, 5451 Patrick Henry Drive, Santa Clara, CA 95054, USA | Phone: +1-408-328-4400 | Fax: +1-408-328-4439**

© SiTime Corporation 2017-2021. The information contained herein is subject to change at any time without notice. SiTime assumes no responsibility or liability for any loss, damage or defect of a Product which is caused in whole or in part by (i) use of any circuitry other than circuitry embodied in a SiTime product, (ii) misuse or abuse including static discharge, neglect or accident, (iii) unauthorized modification or repairs which have been soldered or altered during assembly and are not capable of being tested by SiTime under its normal test conditions, or (iv) improper installation, storage, handling, warehousing or transportation, or (v) being subjected to unusual physical, thermal, or electrical stress.

**Disclaimer:** SiTime makes no warranty of any kind, express or implied, with regard to this material, and specifically disclaims any and all express or implied warranties, either in fact or by operation of law, statutory or otherwise, including the implied warranties of merchantability and fitness for use or a particular purpose, and any implied warranty arising from course of dealing or usage of trade, as well as any common-law duties relating to accuracy or lack of negligence, with respect to this material, any SiTime product and any product documentation. Products sold by SiTime are not suitable or intended to be used in a life support application or component, to operate nuclear facilities, or in other mission critical applications where human life may be involved or at stake. All sales are made conditioned upon compliance with the critical uses policy set forth below.

### CRITICAL USE EXCLUSION POLICY

BUYER AGREES NOT TO USE SITIME'S PRODUCTS FOR ANY APPLICATION OR IN ANY COMPONENTS USED IN LIFE SUPPORT DEVICES OR TO OPERATE NUCLEAR FACILITIES OR FOR USE IN OTHER MISSION-CRITICAL APPLICATIONS OR COMPONENTS WHERE HUMAN LIFE OR PROPERTY MAY BE AT STAKE.

SiTime owns all rights, title and interest to the intellectual property related to SiTime's products, including any software, firmware, copyright, patent, or trademark. The sale of SiTime products does not convey or imply any license under patent or other rights. SiTime retains the copyright and trademark rights in all documents, catalogs and plans supplied pursuant to or ancillary to the sale of products or services by SiTime. Unless otherwise agreed to in writing by SiTime, any reproduction, modification, translation, compilation, or representation of this material shall be strictly prohibited.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SiTime:

[SiT3373AI-1E2-33EG644.531250X](#) [SiT3373AC-2E3-25NZ622.000000X](#) [SiT3373AI-2B2-33NG250.000000X](#)  
[SiT3373AI-4E2-33NH540.000000X](#) [SiT3373AI-2B2-33NB644.531250Y](#)