

P-channel -30 V, 12 mΩ typ., -40 A STripFET™ H6 Power MOSFET in a DPAK package

Datasheet - production data





Figure 1: Internal schematic diagram



Features

Order code	V _{DS}	R _{DS(on)} max	I _D
STD40P3LLH6	-30 V	15 mΩ	-40 A

- Very low on-resistance
- Very low gate charge
- High avalanche ruggedness
- Low gate drive power loss

Applications

- Switching applications

Description

This device is a P-channel Power MOSFET developed using the STripFET™ H6 technology with a new trench gate structure. The resulting Power MOSFET exhibits very low R_{DS(on)} in all packages.

Table 1: Device summary

Order code	Marking	Package	Packing
STD40P3LLH6	40P3LLH6	DPAK	Tape and reel

Contents

1	Electrical ratings	3
2	Electrical characteristics	4
	2.1 Electrical characteristics (curves).....	6
3	Test circuits	8
4	Package information	9
	4.1 DPAK (TO252) type A2 mechanical data.....	10
	4.2 DPAK (TO252) packing information	13
5	Revision history	15

1 Electrical ratings

Table 2: Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{DS}	Drain-source voltage	-30	V
V_{GS}	Gate-source voltage	± 20	V
I_D	Drain current (continuous) at $T_C = 25\text{ }^{\circ}\text{C}$	-40	A
I_D	Drain current (continuous) at $T_C = 100\text{ }^{\circ}\text{C}$	-30.7	A
$I_{DM}^{(1)}$	Drain current (pulsed)	-160	A
P_{TOT}	Total dissipation at $T_C = 25\text{ }^{\circ}\text{C}$	60	W
T_{stg}	Storage temperature range	- 55 to 175	$^{\circ}\text{C}$
T_j	Operating junction temperature range		$^{\circ}\text{C}$

Notes:

⁽¹⁾Pulse width is limited by safe operating area.

Table 3: Thermal data

Symbol	Parameter	Value	Unit
$R_{thj-case}$	Thermal resistance junction-case max	2.5	$^{\circ}\text{C/W}$
$R_{thj-pcb}^{(1)}$	Thermal resistance junction-pcb max	50	

Notes:

⁽¹⁾When mounted on FR-4 board of 1 inch², 2oz Cu.

2 Electrical characteristics

(T_C = 25 °C unless otherwise specified).

Table 4: On /off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V _{(BR)DSS}	Drain-source breakdown voltage	V _{GS} = 0, I _D = -1 mA	-30			V
I _{DSS}	Zero gate voltage drain current	V _{GS} = 0, V _{DS} = -30 V			-1	μA
		V _{GS} = 0, V _{DS} = -30 V, T _C = 125 °C ⁽¹⁾			-10	μA
I _{GSS}	Gate-body leakage current	V _{DS} = 0, V _{GS} = ± 20 V			±100	nA
V _{GS(th)}	Gate threshold voltage	V _{DS} = V _{GS} , I _D = -250 μA	-1		-2.5	V
R _{DS(on)}	Static drain-source on-resistance	V _{GS} = 10 V, I _D = -20 A		12	15	mΩ
		V _{GS} = -4.5 V, I _D = -20 A		18	22.5	mΩ

Notes:

⁽¹⁾Defined by design, not subject to production test.

Table 5: Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C _{iss}	Input capacitance	V _{DS} = -25 V, f = 1 MHz, V _{GS} = 0	-	2615	-	pF
C _{oss}	Output capacitance		-	340	-	pF
C _{rss}	Reverse transfer capacitance		-	235	-	pF
Q _g	Total gate charge	V _{DD} = -15 V, I _D = -40 A, V _{GS} = -4.5 V (see Figure 14: "Gate charge test circuit")	-	24	-	nC
Q _{gs}	Gate-source charge		-	9	-	nC
Q _{gd}	Gate-drain charge		-	8	-	nC

Table 6: Switching times

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
t _{d(on)}	Turn-on delay time	V _{DD} = -15 V, I _D = -20 A, R _G = 4.7 Ω, V _{GS} = -10 V (see Figure 13: "Switching times test circuit for resistive load")	-	13.2	-	ns
t _r	Rise time		-	93	-	ns
t _{d(off)}	Turn-off delay time		-	50	-	ns
t _f	Fall time		-	18	-	ns

Table 7: Source drain diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{SD}^{(1)}$	Forward on voltage	$I_{SD} = -40\text{ A}$, $V_{GS} = 0$	-		-1.1	V
t_{rr}	Reverse recovery time	$I_{SD} = -40\text{ A}$, $di/dt = 100\text{ A}/\mu\text{s}$ $V_{DD} = -24\text{ V}$ (see Figure 15: "Test circuit for inductive load switching and diode recovery times")	-	20		ns
Q_{rr}	Reverse recovery charge		-	16		nC
I_{RRM}	Reverse recovery current		-	-1.6		A

Notes:

⁽¹⁾Pulsed: pulse duration = 300 μs , duty cycle 1.5%

2.1 Electrical characteristics (curves)



Note: For the P-channel Power MOSFET, current and voltage polarities are reversed.




Figure 8: Capacitance variations




Figure 9: Normalized gate threshold voltage vs temperature




Figure 10: Normalized on-resistance vs temperature




Figure 11: Normalized $V_{(BR)DSS}$ vs temperature

Figure 12: Source-drain diode forward characteristics



3 Test circuits

Figure 13: Switching times test circuit for resistive load




Figure 14: Gate charge test circuit





Figure 15: Test circuit for inductive load switching and diode recovery times




4 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: **www.st.com**. ECOPACK® is an ST trademark.

4.1 DPAK (TO252) type A2 mechanical data

Figure 16: DPAK (TO-252) type A2 package outline




0068772_type-A2_rev21

Table 8: DPAK (TO-252) type A2 mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	2.20		2.40
A1	0.90		1.10
A2	0.03		0.23
b	0.64		0.90
b4	5.20		5.40
c	0.45		0.60
c2	0.48		0.60
D	6.00		6.20
D1	4.95	5.10	5.25
E	6.40		6.60
E1	5.10	5.20	5.30
e	2.16	2.28	2.40
e1	4.40		4.60
H	9.35		10.10
L	1.00		1.50
L1	2.60	2.80	3.00
L2	0.65	0.80	0.95
L4	0.60		1.00
R		0.20	
V2	0°		8°

Figure 17: DPAK (TO-252) recommended footprint (dimensions are in mm)



4.2 DPAK (TO252) packing information

Figure 18: DPAK (TO-252) tape outline




Figure 19: DPAK (TO-252) reel outline




Table 9: DPAK (TO-252) tape and reel mechanical data

Tape			Reel		
Dim.	mm		Dim.	mm	
	Min.	Max.		Min.	Max.
A0	6.8	7	A		330
B0	10.4	10.6	B	1.5	
B1		12.1	C	12.8	13.2
D	1.5	1.6	D	20.2	
D1	1.5		G	16.4	18.4
E	1.65	1.85	N	50	
F	7.4	7.6	T		22.4
K0	2.55	2.75			
P0	3.9	4.1	Base qty.		2500
P1	7.9	8.1	Bulk qty.		2500
P2	1.9	2.1			
R	40				
T	0.25	0.35			
W	15.7	16.3			

5 Revision history

Table 10: Document revision history

Date	Revision	Changes
23-Jan-2014	1	First release.
07-Mar-2016	2	Modified: title and $R_{DS(on)}$ max value. Modified: Table 4: "On /off states", Table 5: "Dynamic", Table 6: "Switching times" and Table 7: "Source drain diode". Minor text changes.
21-Mar-2016	3	Modified: Figure 4: "Output characteristics" and Figure 5: "Transfer characteristics". Minor text changes.
30-Mar-2016	4	Updated title. Minor text changes.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[STD40P3LLH6](#)