STGD10NC60HT4

Datasheet

N-channel 600 V, 10 A, very fast IGBT in DPAK package



DPAK



G1C2TE3

Features

Type	V_{CES}	$V_{CE(sat)}$ max.	I_C @100°C
STGD10NC60HT4	600 V	2.5 V	10 A

- Low on-voltage drop ($V_{CE(sat)}$)
- Low CRES / CIES ratio (no cross-conduction susceptibility)

Applications

- High-frequency motor controls
- SMPS and PFC in both hard switch and resonant topologies

Description

This device is a very fast IGBT developed using advanced PowerMESH™ technology. This process guarantees an excellent trade-off between switching performance and low on-state behavior. This device is well-suited for resonant or soft-switching applications.

Product status link
STGD10NC60HT4

Product summary	
Order code	STGD10NC60HT4
Marking	GD10NC60H
Package	DPAK
Packing	Tape and reel

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CES}	Collector-emitter voltage (V_{GE} = 0 V)	600	V
I_C	Continuous collector current at T_C = 25 °C	20	A
I_C	Collector current (continuous) at T_C = 100°C	10	A
I_{CL} (1)	Collector current (pulsed)	40	A
V_{GE}	Gate-emitter voltage	±20	V
P_{TOT}	Total power dissipation at T_C = 25 °C	60	W
T_J	Operating junction temperature range	-55 to 150	°C
T_{stg}	Storage temperature range		

1. *V_{clamp} = 480 V, T_j = 150°C, R_G = 10 Ω, V_{GE} = 15 V*

Table 2. Thermal data

Symbol	Parameter	Value	Unit
$R_{thj\text{-}case}$	Thermal resistance junction-case	2.08	°C/W
$R_{thj\text{-}amb}$	Thermal resistance junction-ambient	62.5	°C/W

2 Electrical characteristics

T_{CASE} = 25 °C unless otherwise specified

Table 3. On/off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)CES}$	Collector-emitter breakdown voltage	I_C = 1 mA, V_{GE} = 0 V	600			V
I_{CES}	Collector cut-off current (V_{GE} = 0 V)	V_{CE} = 600 V			150	µA
		V_{CE} = 600 V, T_C = 125 °C (1)			1	mA
I_{GES}	Gate-emitter leakage current	V_{GE} = ±20 V, V_{CE} = 0 V			±100	nA
$V_{GE(th)}$	Gate threshold voltage	V_{CE} = V_{GE}, I_C = 250 µA	3.75		5.75	V
$V_{CE(sat)}$	Collector-emitter saturation voltage	V_{GE} = 15 V, I_C = 5 A		1.9	2.5	V
		V_{GE} = 15 V, I_C = 5 A, T_C = 125°C		1.7		

1. *Defined by design, not subject to production test.*

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{ies}	Input capacitance	V_{CE} = 25 V, f = 1 MHz, V_{GE} = 0 V	-	365	-	pF
C_{oes}	Output capacitance		-	43	-	pF
C_{res}	Reverse transfer capacitance		-	8.3	-	pF
Q_g	Total gate charge	V_{CE} = 390 V, I_D = 5 A, V_{GE} = 0 to 15 V (see Figure 15. Gate charge test circuit)	-	22	-	nC
Q_{ge}	Gate-emitter charge		-	4.5	-	nC
Q_{gc}	Gate-collector charge		-	7.5	-	nC

Table 5. Switching on/off (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	V_{CC} = 390 V, I_C = 5A	-	14.2	-	ns
t_r	Current rise time	R_G = 10 Ω, V_{GE} = 15 V	-	5	-	ns
$(di/dt)_{on}$	Turn-on current slope	(see Figure 14. Test circuit for inductive load switching and Figure 16. Switching waveform)	-	1000	-	A/µs
$t_{d(on)}$	Turn-on delay time	V_{CC} = 390 V, I_C = 5 A	-	14	-	ns
t_r	Current rise time	R_G = 10 Ω, V_{GE} = 15 V, T_j = 125°C	-	5	-	ns
$(di/dt)_{on}$	Turn-on current slope	(see Figure 14. Test circuit for inductive load switching and Figure 16. Switching waveform)	-	920	-	A/µs

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{r(V_{off})}$	Off voltage rise time	V_{CC} = 390 V, I_C = 5 A,	-	27	-	ns
$td_{(off)}$	Turn-off delay time	R_{GE} = 10 Ω, V_{GE} = 15 V	-	72	-	ns
t_f	Current fall time	(see Figure 14. Test circuit for inductive load switching and Figure 16. Switching waveform)	-	85	-	ns
$t_{r(V_{off})}$	Off voltage rise time	V_{CC} = 390 V, I_C = 5 A,	-	50	-	ns
$td_{(off)}$	Turn-off delay time	R_{GE} = 10 Ω, V_{GE} = 15 V,	-	108	-	ns
t_f	Current fall time	T_j = 125°C (see Figure 14. Test circuit for inductive load switching and Figure 16. Switching waveform)	-	139	-	ns

Table 6. Switching energy (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
E_{on}	Turn-on switching energy	V_{CC} = 390 V, I_C = 5 A	-	31.8	-	µJ
E_{off} (1)	Turn-off switching energy	R_G = 10 Ω, V_{GE} = 15 V	-	95	-	µJ
E_{ts}	Total switching energy	(see Figure 14. Test circuit for inductive load switching)	-	126.8	-	µJ
E_{on}	Turn-on switching energy	V_{CC} = 390 V, I_C = 5 A	-	61.8	-	µJ
E_{off} (1)	Turn-off switching energy	R_G = 10 Ω, V_{GE} = 15 V,	-	173	-	µJ
E_{ts}	Total switching energy	T_j = 125°C (see Figure 14. Test circuit for inductive load switching)	-	234.8	-	µJ

1. *Including the tail of the collector current.*

2.1 Electrical characteristics (curves)

Figure 1. Output characteristics



Figure 2. Transfer characteristics



Figure 3. Collector-emitter on voltage vs temperature



Figure 4. Gate charge vs gate-source voltage



Figure 5. Capacitance variations



Figure 6. Normalized gate threshold voltage vs temperature



Figure 7. Collector-emitter on voltage vs collector current



Figure 8. Normalized breakdown voltage vs temperature



Figure 9. Switching energy vs temperature



Figure 10. Switching energy vs gate resistance



Figure 11. Switching energy vs collector current



Figure 12. Thermal Impedance



Figure 13. **Turn-off SOA**



3 Test circuits

Figure 14. Test circuit for inductive load switching



Figure 15. Gate charge test circuit



Figure 16. Switching waveform



4 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

4.1 DPAK (TO-252) type A2 package information

Figure 17. **DPAK (TO-252) type A2 package outline**



Table 7. **DPAK (TO-252) type A2 mechanical data**

Dim.	mm		
	Min.	Typ.	Max.
A	2.20		2.40
A1	0.90		1.10
A2	0.03		0.23
b	0.64		0.90
b4	5.20		5.40
c	0.45		0.60
c2	0.48		0.60
D	6.00		6.20
D1	4.95	5.10	5.25
E	6.40		6.60
E1	5.10	5.20	5.30
e	2.159	2.286	2.413
e1	4.445	4.572	4.699
H	9.35		10.10
L	1.00		1.50
L1	2.60	2.80	3.00
L2	0.65	0.80	0.95
L4	0.60		1.00
R		0.20	
V2	0°		8°

4.2 DPAK (TO-252) type C2 package information

Figure 18. **DPAK (TO-252) type C2 package outline**



0068772_type-C2_rev26

Table 8. **DPAK (TO-252) type C2 mechanical data**

Dim.	mm		
	Min.	Typ.	Max.
A	2.20	2.30	2.38
A1	0.90	1.01	1.10
A2	0.00		0.10
b	0.72		0.85
b4	5.13	5.33	5.46
c	0.47		0.60
c2	0.47		0.60
D	6.00	6.10	6.20
D1	5.10		5.60
E	6.50	6.60	6.70
E1	5.20		5.50
e	2.186	2.286	2.386
H	9.80	10.10	10.40
L	1.40	1.50	1.70
L1		2.90 REF	
L2	0.90		1.25
L3		0.51 BSC	
L4	0.60	0.80	1.00
L6		1.80 BSC	
θ1	5°	7°	9°
θ2	5°	7°	9°
V2	0°		8°

Figure 19. **DPAK (TO-252) recommended footprint (dimensions are in mm)**



4.3 DPAK (TO-252) packing information

Figure 20. **DPAK (TO-252) tape outline**



Figure 21. **DPAK (TO-252) reel outline**



AM06038v1

Table 9. **DPAK (TO-252) tape and reel mechanical data**

Tape			Reel		
Dim.	mm		Dim.	mm	
	Min.	Max.		Min.	Max.
A0	6.8	7	A		330
B0	10.4	10.6	B	1.5	
B1		12.1	C	12.8	13.2
D	1.5	1.6	D	20.2	
D1	1.5		G	16.4	18.4
E	1.65	1.85	N	50	
F	7.4	7.6	T		22.4
K0	2.55	2.75			
P0	3.9	4.1	Base qty.		2500
P1	7.9	8.1	Bulk qty.		2500
P2	1.9	2.1			
R	40				
T	0.25	0.35			
W	15.7	16.3			

Revision history

Table 10. **Document revision history**

Date	Version	Changes
27-Feb-2019	1	Initial release.

Contents

1 **Electrical ratings** 2

2 **Electrical characteristics** 3

2.1 Electrical characteristics (curves) 5

3 **Test circuits** 8

4 **Package information** 9

4.1 DPAK (TO-252) type A2 package information 9

4.2 DPAK (TO-252) type C2 package information 11

4.3 DPAK (TO-252) packing information 14

Revision history 17

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics:
STGD10NC60HT4