

Notice for TAIYO YUDEN products

Please read this notice before using the TAIYO YUDEN products.



REMINDERS

Product Information in this Catalog

Product information in this catalog is as of January 2021. All of the contents specified herein and production status of the products listed in this catalog are subject to change without notice due to technical improvement of our products, etc. Therefore, please check for the latest information carefully before practical application or use of our products.

Please note that TAIYO YUDEN shall not be in any way responsible for any damages and defects in products or equipment incorporating our products, which are caused under the conditions other than those specified in this catalog or individual product specification sheets.

Approval of Product Specifications

Please contact TAIYO YUDEN for further details of product specifications as the individual product specification sheets are available. When using our products, please be sure to approve our product specifications or make a written agreement on the product specification with TAIYO YUDEN in advance.

Pre-Evaluation in the Actual Equipment and Conditions

Please conduct validation and verification of our products in actual conditions of mounting and operating environment before using our products.

Limited Application

1. Equipment Intended for Use

The products listed in this catalog are intended for general-purpose and standard use in general electronic equipment (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment including, without limitation, mobile phone, and PC) and other equipment specified in this catalog or the individual product specification sheets.

TAIYO YUDEN has the line-up of the products intended for use in automotive electronic equipment, telecommunications infrastructure and industrial equipment, or medical devices classified as GHTF Classes A to C (Japan Classes I to III). Therefore, when using our products for these equipment, please check available applications specified in this catalog or the individual product specification sheets and use the corresponding products.

2. Equipment Requiring Inquiry

Please be sure to contact TAIYO YUDEN for further information before using the products listed in this catalog for the following equipment (excluding intended equipment as specified in this catalog or the individual product specification sheets) which may cause loss of human life, bodily injury, serious property damage and/or serious public impact due to a failure or defect of the products and/or malfunction attributed thereto.

- (1) Transportation equipment (automotive powertrain control system, train control system, and ship control system, etc.)
- (2) Traffic signal equipment
- (3) Disaster prevention equipment, crime prevention equipment
- (4) Medical devices classified as GHTF Class C (Japan Class III)
- (5) Highly public information network equipment, data-processing equipment (telephone exchange, and base station, etc.)
- (6) Any other equipment requiring high levels of quality and/or reliability equal to the equipment listed above

3. Equipment Prohibited for Use

Please do not incorporate our products into the following equipment requiring extremely high levels of safety and/or reliability.

- (1) Aerospace equipment (artificial satellite, rocket, etc.)
- (2) Aviation equipment ^{*1}
- (3) Medical devices classified as GHTF Class D (Japan Class IV), implantable medical devices ^{*2}

- (4) Power generation control equipment (nuclear power, hydroelectric power, thermal power plant control system, etc.)
- (5) Undersea equipment (submarine repeating equipment, underwater work equipment, etc.)
- (6) Military equipment
- (7) Any other equipment requiring extremely high levels of safety and/or reliability equal to the equipment listed above

*Notes:

1. There is a possibility that our products can be used only for aviation equipment that does not directly affect the safe operation of aircraft (e.g., in-flight entertainment, cabin light, electric seat, cooking equipment) if such use meets requirements specified separately by TAIYO YUDEN. Please be sure to contact TAIYO YUDEN for further information before using our products for such aviation equipment.
2. Implantable medical devices contain not only internal unit which is implanted in a body, but also external unit which is connected to the internal unit.

4. Limitation of Liability

Please note that unless you obtain prior written consent of TAIYO YUDEN, TAIYO YUDEN shall not be in any way responsible for any damages incurred by you or third parties arising from use of the products listed in this catalog for any equipment that is not intended for use by TAIYO YUDEN, or any equipment requiring inquiry to TAIYO YUDEN or prohibited for use by TAIYO YUDEN as described above.

Safety Design

When using our products for high safety and/or reliability-required equipment or circuits, please fully perform safety and/or reliability evaluation. In addition, please install (i) systems equipped with a protection circuit and a protection device and/or (ii) systems equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault for a failsafe design to ensure safety.

Intellectual Property Rights

Information contained in this catalog is intended to convey examples of typical performances and/or applications of our products and is not intended to make any warranty with respect to the intellectual property rights or any other related rights of TAIYO YUDEN or any third parties nor grant any license under such rights.

Limited Warranty

Please note that the scope of warranty for our products is limited to the delivered our products themselves and TAIYO YUDEN shall not be in any way responsible for any damages resulting from a failure or defect in our products. Notwithstanding the foregoing, if there is a written agreement (e.g., supply and purchase agreement, quality assurance agreement) signed by TAIYO YUDEN and your company, TAIYO YUDEN will warrant our products in accordance with such agreement.

TAIYO YUDEN's Official Sales Channel

The contents of this catalog are applicable to our products which are purchased from our sales offices or authorized distributors (hereinafter "TAIYO YUDEN's official sales channel"). Please note that the contents of this catalog are not applicable to our products purchased from any seller other than TAIYO YUDEN's official sales channel.

Caution for Export

Some of our products listed in this catalog may require specific procedures for export according to "U.S. Export Administration Regulations", "Foreign Exchange and Foreign Trade Control Law" of Japan, and other applicable regulations. Should you have any questions on this matter, please contact our sales staff.

► This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (<http://www.ty-top.com/>).


Industrial Application Guide

The products described as “For Telecommunications Infrastructure and Industrial Equipment” in this catalog are intended for use in the equipment shown in the below table as its typical example. Therefore, when using our products for these equipment, please check it carefully by referring to the part number or the individual product specification sheets and use the corresponding products. Should you have any questions on this matter, please contact us.

Category	Telecommunications Infrastructure and Industrial Equipment (Typical Example)
Telecommunications Infrastructure	<ul style="list-style-type: none"> • Base Station • Optical Transceiver • Router/Switch (Carrier-Grade) • UPS (Uninterruptible Power Supply), etc.
Factory Automation	<ul style="list-style-type: none"> • PLC (Programmable Logic Controller) • Servomotor/Servo Driver • Industry Robot, etc.
Measurement	<ul style="list-style-type: none"> • Gas Meter • Water Meter • Flow Meter • Pressure Gauge Meter • Magnetometer • Thermometer, etc.
Electric Power Apparatus	<ul style="list-style-type: none"> • Power Conditioner (Solar Power System) • Smart Meter • GFCI (Ground Fault Circuit Interrupter) • Electric Vehicle Charging Station, etc.


Part Numbering System

Multilayer Ceramic Capacitors:



If the 15th code from the left is “8”, it indicates “For Telecommunications Infrastructure and Industrial Equipment” or “For Medical Devices”.

Inductors:




If the 1st code from the right is “8” regardless of the total digit number, it indicates “For Telecommunications Infrastructure and Industrial Equipment” or “For Medical Devices”.

Because there are some exceptions, for details please refer to each page of this catalog where the part numbering system of each product is described.

Medical Application Guide

The products described as “For Medical Devices” in this catalog are intended for use in the medical devices classified as GHTF Classes A to C (Japan Classes I to III) except for all medical devices classified as GHTF Class D (Japan Class IV) and implantable medical devices (bone-anchored hearing aid, artificial retina system, and external unit which is connected to internal unit which is implanted in a body, etc.). Therefore, when using our products for these medical devices, please check it carefully by referring to the part number or the individual product specification sheets and use the corresponding products. Should you have any questions on this matter, please contact us.

Risk Level		Low  High			
Japan	Classification according to the PMD Act of Japan (based on the GHTF Rules)	Class I General Medical Devices (GHTF Class A)	Class II Controlled Medical Devices (GHTF Class B)	Class III Specially-controlled Medical Devices (GHTF Class C)	Class IV Specially-controlled Medical Devices (GHTF Class D)
		Medical devices with extremely low risk to the human body in case of problems [Ex.] • In Vitro Diagnostic Devices • Nebulizer • Blood Gas Analyzer • Plethysmographs • Breathing Sensor • AC-powered Operating Table • Surgical Light • Cholesterol Analysis Device • Blood Type Analysis Device, etc.	Medical devices with relatively low risk to the human body in case of problems [Ex.] • Electronic Thermometer • Electronic Blood Pressure Gauge • Electronic Endoscope • Hearing Aid • Electrocardiograph • MRI • Ultrasonic Diagnostic System • Diagnostic Imaging Equipment • X-ray Diagnostic Equipment • Central Monitor • Pulse Oximeter, etc.	Medical devices with relatively high risk to the human body in case of problems [Ex.] • Dialysis Machine • Radiation Therapy Equipment • Infusion Pump • Respirator • Glucose Monitoring System • AED (Automated External Defibrillator) • Skin Laser Scanner • Electric Surgical Unit • Insulin Pump, etc.	Medical devices highly invasive to patients and with life-threatening risk in case of problems [Ex.] • Cardiac Pacemaker • Video Flexible Angioscope • Implantable Infusion Pump • Cardiac Electrosurgical Unit • Inspection Device with Cardiac Catheter • Defibrillator, etc.
U.S.A.	FDA Classification	Class I General Controls	Class II General Controls and Special Controls	Class III General Controls and Premarket Approval	
		Medical devices without the possibility of causing serious injury or harm to the patient or user even if there is a defect or malfunction in such medical devices	Medical devices with the possibility of causing injury or harm to the patient or user if there is a defect or malfunction in such medical devices	Medical devices with the possibility of causing serious injury, disability or death to the patient or user if a defect or malfunction occurs in such medical devices	

Coverage of those Classes by TAIYO YUDEN Products	Product Series for Medical Devices	
	*Note: It is prohibited that our products are used in some medical devices such as implantable medical devices even if such medical devices are classified as GHTF Class C (Japan Class III).	N/A

SMD POWER INDUCTORS (NR SERIES H TYPE/ S TYPE/ V TYPE)

AEC-Q200 Grade 3 (we conduct the evaluation at the test condition of Grade 3.)

*Operating environment Temp: -40~85°C

REFLOW

AEC-Q200

PART NUMBER

*Operating Temp. : -40~125°C (Including self-generated heat)

N	R	S	4	0	1	8	T	△	1	0	0	M	D	G	V	V
①			②				③		④			⑤			⑥	⑦

△=Blank space

①Series name

Code	Series name
NRH	Coating resin specification
NRS	
NRV	

②Dimensions (L×W×H)

Code	Dimensions (L×W×H) [mm]
2010	2.0×2.0×1.0
2012	2.0×2.0×1.2
2410	2.4×2.4×1.0
2412	2.4×2.4×1.2
3010	3.0×3.0×1.0
3012	3.0×3.0×1.2
3015	3.0×3.0×1.5
4010	4.0×4.0×1.0
4012	4.0×4.0×1.2
4018	4.0×4.0×1.8
5010	4.9×4.9×1.0
5012	4.9×4.9×1.2
5014	4.9×4.9×1.4
5020	4.9×4.9×2.0
5024	4.9×4.9×2.4
5030	4.9×4.9×3.0
5040	4.9×4.9×4.0
6010	6.0×6.0×1.0
6012	6.0×6.0×1.2
6014	6.0×6.0×1.4
6020	6.0×6.0×2.0
6028	6.0×6.0×2.8
6045	6.0×6.0×4.5
8030	8.0×8.0×3.0
8040	8.0×8.0×4.0

③Packaging

Code	Packaging
T△	Taping

④Nominal inductance

Code (example)	Nominal inductance [μH]
2R2	2.2
100	10
101	100

※R=Decimal point


⑤Inductance tolerance

Code	Inductance tolerance
M	±20%
N	±30%

⑥Special code

⑦Internal code

Code	Internal code
V	Inductor for Automotive
8	Inductor for Telecommunications infrastructure and Industrial equipment / Medical devices





Type	A	B	C
NRV2010	0.65	1.35	2.0
NRV2012, NRS2012			
NRH2410			
NRH2412	0.7	1.45	2.0
NRH3010			
NRH3012, NRV3012			
NRS3015	0.8	2.2	2.7
NRS4010			
NRS4012			
NRS4018			
NRS8030	1.2	2.8	3.7
NRS8040			
NRS8040	1.8	5.6	7.5

Unit: mm


Type	L	W	H	e	f	Standard quantity [pcs] Taping
NRV2010	2.0±0.1 (0.079±0.004)	2.0±0.1 (0.079±0.004)	1.0 max (0.039 max)	0.5±0.2 (0.020±0.008)	1.25±0.2 (0.050±0.008)	2500
NRV2012 NRS2012	2.0±0.1 (0.079±0.004)	2.0±0.1 (0.079±0.004)	1.2 max (0.047 max)	0.5±0.2 (0.020±0.008)	1.25±0.2 (0.050±0.008)	2500
NRH2410	2.4±0.1 (0.095±0.004)	2.4±0.1 (0.095±0.004)	1.0 max (0.039 max)	0.6±0.2 (0.024±0.008)	1.45±0.2 (0.057±0.008)	2500
NRH2412	2.4±0.1 (0.095±0.004)	2.4±0.1 (0.095±0.004)	1.2 max (0.047 max)	0.6±0.2 (0.024±0.008)	1.45±0.2 (0.057±0.008)	2500
NRH3010	3.0±0.1 (0.118±0.004)	3.0±0.1 (0.118±0.004)	1.0 max (0.039 max)	0.9±0.2 (0.035±0.008)	1.9±0.2 (0.075±0.008)	2000
NRH3012 NRV3012	3.0±0.1 (0.118±0.004)	3.0±0.1 (0.118±0.004)	1.2 max (0.047 max)	0.9±0.2 (0.035±0.008)	1.9±0.2 (0.075±0.008)	2000
NRS3015	3.0±0.1 (0.118±0.004)	3.0±0.1 (0.118±0.004)	1.5 max (0.059 max)	0.9±0.2 (0.035±0.008)	1.9±0.2 (0.075±0.008)	2000
NRS4010	4.0±0.2 (0.158±0.008)	4.0±0.2 (0.158±0.008)	1.0 max (0.039 max)	1.1±0.2 (0.043±0.008)	2.5±0.2 (0.098±0.008)	5000
NRS4012	4.0±0.2 (0.158±0.008)	4.0±0.2 (0.158±0.008)	1.2 max (0.047 max)	1.1±0.2 (0.043±0.008)	2.5±0.2 (0.098±0.008)	4500
NRS4018	4.0±0.2 (0.158±0.008)	4.0±0.2 (0.158±0.008)	1.8 max (0.071 max)	1.1±0.2 (0.043±0.008)	2.5±0.2 (0.098±0.008)	3500
NRS8030	8.0±0.2 (0.315±0.008)	8.0±0.2 (0.315±0.008)	3.0 max (0.118 max)	1.60±0.3 (0.063±0.012)	5.6±0.3 (0.22±0.012)	1000
NRS8040	8.0±0.2 (0.315±0.008)	8.0±0.2 (0.315±0.008)	*1) 4.2 max (0.165 max) *2) 4.0 max (0.158 max)	1.60±0.3 (0.063±0.012)	5.6±0.3 (0.22±0.012)	1000

*1) 0R9~6R8 type, *2) 100~101type

Unit: mm (inch)



Recommended Land Patterns



Type	A	B	C
NRS5010	1.5	3.6	4.0
NRS5012			
NRS5014			
NRS5020			
NRS5024			
NRS5030	1.6	4.7	5.7
NRS5040			
NRS6010			
NRS6012			
NRS6014			
NRS6020			
NRS6028			
NRS6045			

Unit: mm

Type	L	W	H	e	f	ΔI	Standard quantity [pcs] Taping
NRS5010	4.9±0.2 (0.193±0.008)	4.9±0.2 (0.193±0.008)	1.0 max (0.039 max)	1.2±0.2 (0.047±0.008)	3.3±0.2 (0.130±0.008)	1.3typ (0.051typ)	1000
NRS5012	4.9±0.2 (0.193±0.008)	4.9±0.2 (0.193±0.008)	1.2 max (0.047 max)	1.2±0.2 (0.047±0.008)	3.3±0.2 (0.130±0.008)	1.3typ (0.051typ)	1000
NRS5014	4.9±0.2 (0.193±0.008)	4.9±0.2 (0.193±0.008)	1.4 max (0.055 max)	1.2±0.2 (0.047±0.008)	3.3±0.2 (0.130±0.008)	1.3typ (0.051typ)	1000
NRS5020	4.9±0.2 (0.193±0.008)	4.9±0.2 (0.193±0.008)	2.0 max (0.079 max)	1.2±0.2 (0.047±0.008)	3.3±0.2 (0.130±0.008)	1.3typ (0.051typ)	800
NRS5024	4.9±0.2 (0.193±0.008)	4.9±0.2 (0.193±0.008)	*3) 2.5 max (0.098 max) *4) 2.4 max (0.095 max)	1.2±0.2 (0.047±0.008)	3.3±0.2 (0.130±0.008)	1.3typ (0.051typ)	2500
NRS5030	4.9±0.2 (0.193±0.008)	4.9±0.2 (0.193±0.008)	*5) 3.1 max (0.122 max) *6) 3.0 max (0.118 max)	1.2±0.2 (0.047±0.008)	3.3±0.2 (0.130±0.008)	1.3typ (0.051typ)	500
NRS5040	4.9±0.2 (0.193±0.008)	4.9±0.2 (0.193±0.008)	*7) 4.1 max (0.161 max) *8) 4.0 max (0.158 max)	1.2±0.2 (0.047±0.008)	3.3±0.2 (0.130±0.008)	1.3typ (0.051typ)	1500
NRS6010	6.0±0.2 (0.236±0.008)	6.0±0.2 (0.236±0.008)	1.0 max (0.039 max)	1.35±0.2 (0.053±0.008)	4.0±0.2 (0.158±0.008)	2.3typ (0.091typ)	1000
NRS6012	6.0±0.2 (0.236±0.008)	6.0±0.2 (0.236±0.008)	1.2 max (0.047 max)	1.35±0.2 (0.053±0.008)	4.0±0.2 (0.158±0.008)	2.3typ (0.091typ)	1000
NRS6014	6.0±0.2 (0.236±0.008)	6.0±0.2 (0.236±0.008)	1.4 max (0.055 max)	1.35±0.2 (0.053±0.008)	4.0±0.2 (0.158±0.008)	2.3typ (0.091typ)	1000
NRS6020	6.0±0.2 (0.236±0.008)	6.0±0.2 (0.236±0.008)	2.0 max (0.079 max)	1.35±0.2 (0.053±0.008)	4.0±0.2 (0.158±0.008)	2.3typ (0.091typ)	2500
NRS6028	6.0±0.2 (0.236±0.008)	6.0±0.2 (0.236±0.008)	2.8 max (0.110 max)	1.35±0.2 (0.053±0.008)	4.0±0.2 (0.158±0.008)	2.3typ (0.091typ)	2000
NRS6045	6.0±0.2 (0.236±0.008)	6.0±0.2 (0.236±0.008)	4.5 max (0.177 max)	1.35±0.2 (0.053±0.008)	4.0±0.2 (0.158±0.008)	2.3typ (0.091typ)	1500

Unit: mm (inch)

*3) 1R0~1R5 type, *4) 2R2~330 type
 *5) R47~100 type, *6) 150~470 type
 *7) 1R5~100 type, *8) 150~470 type

PART NUMBER

- All the SMD Power Inductors of the catalog lineup are RoHS compliant.

Notes)

- The exchange of individual specifications is necessary depending on your application and/or circuit condition. Please contact TAIYO YUDEN's official sales channel.
- The products are for Telecommunications infrastructure and Industrial equipment and for Medical devices.
Please consult with TAIYO YUDEN's official sales channel for the details of the product specifications, etc., and please review and approve the product specifications before ordering.
Please be sure to contact us for further information in advance when the products are used for automotive electronic equipment.

●NRV2010 type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRV2010T R47N GF8	0.47	$\pm 30\%$	—	0.052	2,100	2,000	100	
NRV2010T R68N GF8	0.68	$\pm 30\%$	—	0.060	1,850	1,850	100	
NRV2010T 1R0N GF8	1.0	$\pm 30\%$	—	0.080	1,550	1,600	100	
NRV2010T 1R5M GF8	1.5	$\pm 20\%$	—	0.100	1,350	1,450	100	
NRV2010T 2R2M GF8	2.2	$\pm 20\%$	—	0.175	1,100	1,100	100	
NRV2010T 3R3M GF8	3.3	$\pm 20\%$	—	0.250	880	1,000	100	
NRV2010T 4R7M GF8	4.7	$\pm 20\%$	—	0.320	760	820	100	

●NRV2012 type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRV2012T 1R0N GF8	1.0	$\pm 30\%$	—	0.073	2,200	1,650	100	
NRV2012T 1R5N GF8	1.5	$\pm 30\%$	—	0.100	1,800	1,400	100	
NRV2012T 2R2M GF8	2.2	$\pm 20\%$	—	0.129	1,600	1,200	100	
NRV2012T 3R3M GF8	3.3	$\pm 20\%$	—	0.227	1,250	900	100	
NRV2012T 4R7M GF8	4.7	$\pm 20\%$	—	0.325	1,100	750	100	

●NRS2012 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS2012T 1R0N GJ8	1.0	$\pm 30\%$	—	0.070	1,900	1,700	100	
NRS2012T 1R5N GJ8	1.5	$\pm 30\%$	—	0.090	1,650	1,500	100	
NRS2012T 2R2M GJ8	2.2	$\pm 20\%$	—	0.107	1,350	1,370	100	
NRS2012T 3R3M GJ8	3.3	$\pm 20\%$	—	0.190	1,000	1,020	100	
NRS2012T 4R7M GJ8	4.7	$\pm 20\%$	—	0.241	900	910	100	

●NRH2410 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRH2410T R68NN 48	0.68	$\pm 30\%$	120	0.060	2,200	1,570	100	
NRH2410T 1R0NN 48	1.0	$\pm 30\%$	106	0.070	1,800	1,410	100	
NRH2410T 1R5MN 8	1.5	$\pm 20\%$	94	0.110	1,550	1,160	100	
NRH2410T 2R2MN 8	2.2	$\pm 20\%$	77	0.150	1,290	970	100	
NRH2410T 3R3MN 8	3.3	$\pm 20\%$	56	0.220	1,000	770	100	
NRH2410T 4R7MN 8	4.7	$\pm 20\%$	50	0.290	880	670	100	
NRH2410T 6R8MN 8	6.8	$\pm 20\%$	43	0.410	750	570	100	
NRH2410T 100MN 8	10	$\pm 20\%$	32	0.690	550	450	100	
NRH2410T 150MN 8	15	$\pm 20\%$	27	1.02	470	370	100	
NRH2410T 220MN 8	22	$\pm 20\%$	22	1.47	390	300	100	

●NRH2412 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRH2412T R47NNGJ8	0.47	$\pm 30\%$	180	0.050	2,900	2,100	100	
NRH2412T 1R0NNGH8	1.0	$\pm 30\%$	101	0.077	2,350	1,300	100	
NRH2412T 1R5NNGH8	1.5	$\pm 30\%$	89	0.100	2,100	1,150	100	
NRH2412T 2R2MNGH8	2.2	$\pm 20\%$	72	0.140	1,700	1,000	100	
NRH2412T 3R3MNGH8	3.3	$\pm 20\%$	56	0.225	1,400	750	100	
NRH2412T 4R7MNGH8	4.7	$\pm 20\%$	45	0.300	1,150	650	100	
NRH2412T 6R8MNGH8	6.8	$\pm 20\%$	34	0.420	950	550	100	
NRH2412T 100MNGH8	10	$\pm 20\%$	29	0.600	810	450	100	

※) The saturation current value (Idc1) is the DC current value having inductance decrease down to 30%. (at 20°C)

※) The temperature rise current value (Idc2) is the DC current value having temperature increase up to 40°C. (at 20°C)

※) The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

PART NUMBER

NRH3010 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRH3010T 1R2NN 8	1.2	$\pm 30\%$	120	0.065	1,700	1,480	100	
NRH3010T 1R5NN 8	1.5	$\pm 30\%$	99	0.075	1,440	1,370	100	
NRH3010T 2R2MN 8	2.2	$\pm 20\%$	86	0.083	1,300	1,300	100	
NRH3010T 3R3MN 8	3.3	$\pm 20\%$	64	0.130	1,000	1,030	100	
NRH3010T 4R7MN 8	4.7	$\pm 20\%$	50	0.170	850	900	100	
NRH3010T 6R8MN 8	6.8	$\pm 20\%$	44	0.250	700	745	100	
NRH3010T 100MN 8	10	$\pm 20\%$	34	0.350	600	620	100	
NRH3010T 150MN 8	15	$\pm 20\%$	25	0.550	450	480	100	
NRH3010T 220MN 8	22	$\pm 20\%$	22	0.770	380	410	100	
NRH3010T 470MN 8	47	$\pm 20\%$	17	2.05	250	285	100	

NRH3012 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRH3012T R47NN 8	0.47	$\pm 30\%$	160	0.033	2,600	1,900	100	
NRH3012T 1R0NN 8	1.0	$\pm 30\%$	111	0.048	2,200	1,710	100	
NRH3012T 1R5NN 8	1.5	$\pm 30\%$	95	0.055	1,700	1,600	100	
NRH3012T 2R2MN 8	2.2	$\pm 20\%$	78	0.075	1,500	1,370	100	
NRH3012T 3R3MN 8	3.3	$\pm 20\%$	61	0.100	1,200	1,210	100	
NRH3012T 4R7MN 8	4.7	$\pm 20\%$	50	0.130	1,000	1,060	100	
NRH3012T 6R8MN 8	6.8	$\pm 20\%$	43	0.190	850	890	100	
NRH3012T 100MN 8	10	$\pm 20\%$	32	0.270	730	720	100	
NRH3012T 150MN 8	15	$\pm 20\%$	26	0.450	530	570	100	
NRH3012T 220MN 8	22	$\pm 20\%$	22	0.630	500	500	100	

NRV3012 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRV3012T 1R0N 8	1.0	$\pm 30\%$	110	0.065	2,500	1,600	100	
NRV3012T 1R5N 8	1.5	$\pm 30\%$	92	0.075	2,100	1,400	100	
NRV3012T 2R2M 8	2.2	$\pm 20\%$	70	0.120	1,800	1,100	100	
NRV3012T 3R3M 8	3.3	$\pm 20\%$	55	0.150	1,600	1,000	100	
NRV3012T 4R7M 8	4.7	$\pm 20\%$	48	0.190	1,250	850	100	
NRV3012T 6R8M 8	6.8	$\pm 20\%$	40	0.300	950	650	100	
NRV3012T 100M 8	10	$\pm 20\%$	32	0.470	800	550	100	

NRS3015 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS3015T 1R0NNGH8	1.0	$\pm 30\%$	100	0.030	2,100	2,100	100	
NRS3015T 1R5NNGH8	1.5	$\pm 30\%$	87	0.038	1,800	1,820	100	
NRS3015T 2R2MNGH8	2.2	$\pm 20\%$	64	0.058	1,480	1,500	100	
NRS3015T 3R3MNGH8	3.3	$\pm 20\%$	49	0.078	1,210	1,230	100	
NRS3015T 4R7MNGH8	4.7	$\pm 20\%$	40	0.120	1,020	1,040	100	
NRS3015T 6R8MNGH8	6.8	$\pm 20\%$	36	0.160	870	880	100	
NRS3015T 100MNGH8	10	$\pm 20\%$	28	0.220	700	710	100	
NRS3015T 220MNGH8	22	$\pm 20\%$	20	0.520	470	470	100	
NRS3015T 330MNGH8	33	$\pm 20\%$	18	0.780	400	440	100	

NRS4010 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS4010T 1R0NDGG8	1.0	$\pm 30\%$	116	0.056	2,000	1,900	100	
NRS4010T 2R2MDGG8	2.2	$\pm 20\%$	73	0.085	1,200	1,500	100	
NRS4010T 3R3MDGG8	3.3	$\pm 20\%$	58	0.100	1,100	1,400	100	
NRS4010T 4R7MDGG8	4.7	$\pm 20\%$	47	0.140	950	1,200	100	
NRS4010T 6R8MDGG8	6.8	$\pm 20\%$	38	0.200	800	1,000	100	
NRS4010T 100MDGG8	10	$\pm 20\%$	31	0.300	620	750	100	
NRS4010T 150MDGG8	15	$\pm 20\%$	24	0.430	540	600	100	
NRS4010T 220MDGG8	22	$\pm 20\%$	19	0.570	450	500	100	

NRS4012 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS4012T 1R0NDGG8	1.0	$\pm 30\%$	100	0.042	2,800	2,200	100	
NRS4012T 2R2MDGJ8	2.2	$\pm 20\%$	70	0.060	1,650	1,900	100	
NRS4012T 3R3MDGJ8	3.3	$\pm 20\%$	60	0.070	1,400	1,700	100	
NRS4012T 4R7MDGJ8	4.7	$\pm 20\%$	45	0.095	1,200	1,500	100	
NRS4012T 6R8MDGJ8	6.8	$\pm 20\%$	35	0.125	900	1,300	100	
NRS4012T 100MDGJ8	10	$\pm 20\%$	30	0.170	800	1,100	100	
NRS4012T 150MDGJ8	15	$\pm 20\%$	24	0.260	650	750	100	
NRS4012T 220MDGJ8	22	$\pm 20\%$	18	0.400	500	620	100	

※) The saturation current 8alue (Idc1) is the DC current 8alue ha8ing inductance decrease down to 30%. (at 20°C)

※) The temperature rise current 8alue (Idc2) is the DC current 8alue ha8ing temperature increase up to 40°C. (at 20°C)

※) The rated current is the DC current 8alue that satisfies both of current 8alue saturation current 8alue and temperature rise current 8alue.

► This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (<http://www.ty-top.com/>).

■ PART NUMBER

● NRS4018 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS4018T 1R0NDGJ8	1.0	$\pm 30\%$	90	0.027	4,000	3,200	100	
NRS4018T 1R5NDGJ8	1.5	$\pm 30\%$	75	0.037	3,300	2,400	100	
NRS4018T 2R2MDGJ8	2.2	$\pm 20\%$	60	0.042	3,000	2,200	100	
NRS4018T 3R3MDGJ8	3.3	$\pm 20\%$	45	0.055	2,300	2,000	100	
NRS4018T 4R7MDGJ8	4.7	$\pm 20\%$	35	0.070	2,000	1,700	100	
NRS4018T 6R8MDGJ8	6.8	$\pm 20\%$	30	0.098	1,600	1,450	100	
NRS4018T 100MDGJ8	10	$\pm 20\%$	25	0.150	1,300	1,200	100	
NRS4018T 150MDGJ8	15	$\pm 20\%$	18	0.210	1,100	850	100	
NRS4018T 220MDGJ8	22	$\pm 20\%$	15	0.290	900	720	100	
NRS4018T 330MDGJ8	33	$\pm 20\%$	12	0.460	700	550	100	
NRS4018T 470MDGJ8	47	$\pm 20\%$	10	0.650	600	440	100	
NRS4018T 680MDGJ8	68	$\pm 20\%$	8.3	1.00	520	320	100	
NRS4018T 101MDGJ8	100	$\pm 20\%$	6.5	1.45	420	280	100	
NRS4018T 151MDGJ8	150	$\pm 20\%$	5.5	2.30	340	220	100	
NRS4018T 221MDGJ8	220	$\pm 20\%$	4.0	3.80	275	170	100	

● NRS5010 type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS5010T 1R0NMGF8	1.0	$\pm 30\%$	95	0.070	2,350	1,750	100	
NRS5010T 2R2NMGF8	2.2	$\pm 30\%$	65	0.105	1,500	1,400	100	
NRS5010T 3R3MMGF8	3.3	$\pm 20\%$	42	0.125	1,400	1,250	100	
NRS5010T 4R7MMGF8	4.7	$\pm 20\%$	37	0.145	1,200	1,150	100	
NRS5010T 6R8MMGF8	6.8	$\pm 20\%$	33	0.185	1,000	1,000	100	
NRS5010T 100MMGF8	10	$\pm 20\%$	23	0.250	850	900	100	
NRS5010T 150MMGF8	15	$\pm 20\%$	19	0.400	680	650	100	
NRS5010T 220MMGF8	22	$\pm 20\%$	15	0.600	550	450	100	

● NRS5012 type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS5012T 1R0NMGF8	1.0	$\pm 30\%$	100	0.053	4,500	2,300	100	
NRS5012T 1R5NMGF8	1.5	$\pm 30\%$	86	0.070	3,800	2,200	100	
NRS5012T 2R2MMGF8	2.2	$\pm 20\%$	70	0.085	3,100	2,000	100	
NRS5012T 3R3MMGF8	3.3	$\pm 20\%$	48	0.160	2,400	1,450	100	
NRS5012T 4R7MMGF8	4.7	$\pm 20\%$	40	0.180	2,200	1,400	100	
NRS5012T 6R8MMGF8	6.8	$\pm 20\%$	36	0.260	1,700	1,100	100	
NRS5012T 100MMGF8	10	$\pm 20\%$	26	0.420	1,400	850	100	
NRS5012T 150MMGF8	15	$\pm 20\%$	22	0.670	1,200	640	100	

● NRS5014 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS5014T R47NMG8	0.47	$\pm 30\%$	185	0.025	5,800	3,300	100	
NRS5014T 1R2NMG8	1.2	$\pm 30\%$	86	0.045	3,800	2,400	100	
NRS5014T 2R2NMG8	2.2	$\pm 30\%$	56	0.065	2,800	2,000	100	
NRS5014T 3R3NMG8	3.3	$\pm 30\%$	48	0.080	2,350	1,700	100	
NRS5014T 4R7NMG8	4.7	$\pm 30\%$	41	0.100	2,050	1,400	100	
NRS5014T 6R8NMG8	6.8	$\pm 20\%$	33	0.150	1,600	1,200	100	
NRS5014T 100NMG8	10	$\pm 20\%$	27	0.200	1,400	1,050	100	
NRS5014T 150NMG8	15	$\pm 20\%$	20	0.320	1,100	650	100	
NRS5014T 220NMG8	22	$\pm 20\%$	16	0.450	900	550	100	

● NRS5020 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency [kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS5020T R47NMGJ8	0.47	$\pm 30\%$	230	0.012	6,100	5,000	100	
NRS5020T 1R0NMGJ8	1.0	$\pm 30\%$	81	0.021	4,000	3,600	100	
NRS5020T 1R5NMGJ8	1.5	$\pm 30\%$	68	0.026	3,350	3,200	100	
NRS5020T 2R2NMGJ8	2.2	$\pm 30\%$	57	0.035	2,900	2,900	100	
NRS5020T 3R3NMGJ8	3.3	$\pm 30\%$	46	0.048	2,400	2,400	100	
NRS5020T 4R7NMGJ8	4.7	$\pm 20\%$	37	0.060	2,000	2,000	100	
NRS5020T 6R8NMGJ8	6.8	$\pm 20\%$	30	0.090	1,600	1,650	100	
NRS5020T 100NMGJ8	10	$\pm 20\%$	24	0.120	1,300	1,450	100	
NRS5020T 150NMGJ8	15	$\pm 20\%$	20	0.165	1,100	1,200	100	
NRS5020T 220NMGJ8	22	$\pm 20\%$	17	0.260	900	1,000	100	
NRS5020T 470NMGJ8	47	$\pm 20\%$	12	0.435	630	560	100	
NRS5020T 101NMGJ8	100	$\pm 20\%$	7	0.850	420	400	100	

※) The saturation current 8alue (Idc1) is the DC current 8alue ha8ing inductance decrease down to 30%. (at 20°C)

※) The temperature rise current 8alue (Idc2) is the DC current 8alue ha8ing temperature increase up to 40°C. (at 20°C)

※) The rated current is the DC current 8alue that satisfies both of current 8alue saturation current 8alue and temperature rise current 8alue.

PART NUMBER

● NRS5024 Shielded type

Part number	Nominal inductance [μH]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] (±20%)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS5024T 1R0NMGJ8	1.0	±30%	85	0.016	5,800	4,400	100	
NRS5024T 1R5NMGJ8	1.5	±30%	67	0.022	5,200	3,600	100	
NRS5024T 2R2NMGJ8	2.2	±30%	51	0.029	4,100	3,100	100	
NRS5024T 3R3NMGJ8	3.3	±30%	41	0.043	3,100	2,400	100	
NRS5024T 4R7MMGJ8	4.7	±20%	37	0.055	2,700	2,000	100	
NRS5024T 6R8MMGJ8	6.8	±20%	28	0.080	2,200	1,600	100	
NRS5024T 100MMGJ8	10	±20%	21	0.125	1,700	1,200	100	
NRS5024T 150MMGJ8	15	±20%	18	0.170	1,400	1,000	100	
NRS5024T 220MMGJ8	22	±20%	15	0.230	1,200	820	100	
NRS5024T 330MMGJ8	33	±20%	11	0.370	1,000	630	100	

● NRS5030 Shielded type

Part number	Nominal inductance [μH]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] (±30%)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS5030T R47NMGJ8	0.47	±30%	185	0.010	9,000	5,000	100	
NRS5030T 1R0NMGJ8	1.0	±30%	110	0.015	6,600	4,000	100	
NRS5030T 2R2NMGJ8	2.2	±30%	46	0.023	4,200	3,500	100	
NRS5030T 3R3MMGJ8	3.3	±20%	36	0.030	3,600	3,000	100	
NRS5030T 4R7MMGJ8	4.7	±20%	31	0.035	3,100	2,600	100	
NRS5030T 6R8MMGJ8	6.8	±20%	22	0.052	2,500	2,300	100	
NRS5030T 100MMGJ8	10	±20%	20	0.070	2,100	1,700	100	
NRS5030T 150MMGJ8	15	±20%	14	0.125	1,600	1,400	100	
NRS5030T 220MMGJ8	22	±20%	13	0.180	1,400	1,050	100	
NRS5030T 330MMGJ8	33	±20%	10	0.225	1,150	800	100	
NRS5030T 470MMGJ8	47	±20%	9	0.325	950	700	100	

● NRS5040 Shielded type

Part number	Nominal inductance [μH]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] (±30%)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS5040T 1R5NMGJ8	1.5	±30%	60	0.017	6,400	4,500	100	
NRS5040T 2R2NMGJ8	2.2	±30%	42	0.022	5,000	3,700	100	
NRS5040T 3R3NMGJ8	3.3	±30%	32	0.027	4,000	3,300	100	
NRS5040T 4R7NMGK8	4.7	±30%	28	0.029	3,300	3,100	100	
NRS5040T 6R8MMGJ8	6.8	±20%	21	0.049	2,800	2,400	100	
NRS5040T 100MMGJ8	10	±20%	18	0.056	2,300	2,100	100	
NRS5040T 150MMGJ8	15	±20%	13	0.080	2,000	1,800	100	
NRS5040T 220MMGK8	22	±20%	9	0.126	1,500	1,400	100	
NRS5040T 330MMGJ8	33	±20%	7	0.180	1,300	1,200	100	
NRS5040T 470MMGJ8	47	±20%	6	0.310	1,100	900	100	

● NRS6010 type

Part number	Nominal inductance [μH]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] (±20%)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS6010T 1R5MMGF8	1.5	±20%	77	0.090	2,400	1,900	100	
NRS6010T 2R2MMGF8	2.2	±20%	56	0.110	1,900	1,700	100	
NRS6010T 3R3MMGF8	3.3	±20%	42	0.135	1,600	1,500	100	
NRS6010T 4R7MMGF8	4.7	±20%	36	0.165	1,300	1,400	100	
NRS6010T 6R8MMGF8	6.8	±20%	30	0.220	1,200	1,200	100	
NRS6010T 100MMGF8	10	±20%	25	0.270	1,000	1,100	100	
NRS6010T 220MMGF8	22	±20%	12	0.580	650	700	100	

● NRS6012 Shielded type

Part number	Nominal inductance [μH]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] (±20%)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS6012T 1R0NMGJ8	1.0	±30%	95	0.050	3,000	2,400	100	
NRS6012T 1R5NMGJ8	1.5	±30%	69	0.067	2,600	2,100	100	
NRS6012T 2R5NMGJ8	2.5	±30%	45	0.090	2,100	1,800	100	
NRS6012T 3R3NMGJ8	3.3	±30%	42	0.105	1,800	1,700	100	
NRS6012T 4R7MMGJ8	4.7	±20%	36	0.125	1,600	1,550	100	
NRS6012T 5R3MMGJ8	5.3	±20%	34	0.125	1,500	1,550	100	
NRS6012T 6R8MMGJ8	6.8	±20%	30	0.165	1,300	1,350	100	
NRS6012T 100MMGJ8	10	±20%	22	0.200	1,000	1,200	100	
NRS6012T 150MMGJ8	15	±20%	18	0.295	800	800	100	
NRS6012T 220MMGJ8	22	±20%	12	0.465	760	650	100	
NRS6012T 330MMGJ8	33	±20%	8	0.580	590	550	100	
NRS6012T 470MMGJ8	47	±20%	6	0.965	520	460	100	
NRS6012T 680MMGJ8	68	±20%	3	1.16	440	410	100	
NRS6012T 101MMGJ8	100	±20%	1	1.67	350	320	100	

※) The saturation current 8alue (Idc1) is the DC current 8alue ha8ing inductance decrease down to 30%. (at 20°C)

※) The temperature rise current 8alue (Idc2) is the DC current 8alue ha8ing temperature increase up to 40°C. (at 20°C)

※) The rated current is the DC current 8alue that satisfies both of current 8alue saturation current 8alue and temperature rise current 8alue.

► This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (<http://www.ty-top.com/>).

PART NUMBER

● NRS6014 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS6014T 1R2NMG8	1.2	$\pm 30\%$	77	0.042	4,000	2,750	100	
NRS6014T 2R2NMG8	2.2	$\pm 30\%$	61	0.055	3,000	2,300	100	
NRS6014T 3R3NMG8	3.3	$\pm 30\%$	41	0.075	2,500	2,000	100	
NRS6014T 4R7MMG8	4.7	$\pm 20\%$	36	0.090	2,000	1,900	100	
NRS6014T 6R8MMG8	6.8	$\pm 20\%$	30	0.115	1,700	1,650	100	
NRS6014T 100MMG8	10	$\pm 20\%$	24	0.140	1,400	1,400	100	
NRS6014T 150MMG8	15	$\pm 20\%$	20	0.210	1,150	1,200	100	
NRS6014T 220MMG8	22	$\pm 20\%$	16	0.300	950	1,000	100	

● NRS6020 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 20\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS6020T 0R8NMG8	0.8	$\pm 30\%$	110	0.020	6,400	4,100	100	
NRS6020T 1R5NMG8	1.5	$\pm 30\%$	93	0.026	4,300	3,600	100	
NRS6020T 2R2NMG8	2.2	$\pm 30\%$	73	0.034	3,200	2,900	100	
NRS6020T 3R3NMG8	3.3	$\pm 30\%$	55	0.040	2,800	2,750	100	
NRS6020T 4R7NMG8	4.7	$\pm 30\%$	43	0.058	2,400	2,150	100	
NRS6020T 6R8NMG8	6.8	$\pm 30\%$	30	0.085	2,000	1,800	100	
NRS6020T 100MMG8	10	$\pm 20\%$	18	0.125	1,900	1,500	100	
NRS6020T 220MMG8	22	$\pm 20\%$	11	0.290	1,250	950	100	

● NRS6028 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 30\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS6028T 0R9NMG8	0.9	$\pm 30\%$	90	0.013	6,700	4,600	100	
NRS6028T 1R5NMG8	1.5	$\pm 30\%$	78	0.016	5,100	4,200	100	
NRS6028T 2R2NMG8	2.2	$\pm 30\%$	68	0.020	4,200	3,700	100	
NRS6028T 3R0NMG8	3.0	$\pm 30\%$	55	0.023	3,600	3,400	100	
NRS6028T 4R7MMG8	4.7	$\pm 20\%$	39	0.031	2,700	3,000	100	
NRS6028T 6R8MMG8	6.8	$\pm 20\%$	25	0.043	2,600	2,500	100	
NRS6028T 100MMG8	10	$\pm 20\%$	20	0.065	1,900	1,900	100	
NRS6028T 150MMG8	15	$\pm 20\%$	17	0.095	1,600	1,800	100	
NRS6028T 220MMG8	22	$\pm 20\%$	12	0.135	1,300	1,400	100	
NRS6028T 330MMG8	33	$\pm 20\%$	10	0.220	1,100	1,100	100	
NRS6028T 470MMG8	47	$\pm 20\%$	8	0.300	1,000	920	100	
NRS6028T 680MMG8	68	$\pm 20\%$	5	0.420	800	770	100	
NRS6028T 101MMG8	100	$\pm 20\%$	3	0.600	650	660	100	

● NRS6045 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 30\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS6045T 1R0NMG8	1.0	$\pm 30\%$	110	0.014	9,800	4,500	100	
NRS6045T 1R3NMG8	1.3	$\pm 30\%$	95	0.016	8,200	4,200	100	
NRS6045T 1R8NMG8	1.8	$\pm 30\%$	80	0.019	7,200	3,900	100	
NRS6045T 2R3NMG8	2.3	$\pm 30\%$	60	0.022	6,400	3,600	100	
NRS6045T 3R0NMG8	3.0	$\pm 30\%$	45	0.024	5,600	3,300	100	
NRS6045T 4R5MMG8	4.5	$\pm 20\%$	25	0.030	4,400	3,100	100	
NRS6045T 6R3MMG8	6.3	$\pm 20\%$	15	0.036	3,600	3,000	100	
NRS6045T 100MMG8	10	$\pm 20\%$	12	0.046	3,100	2,400	100	
NRS6045T 150MMG8	15	$\pm 20\%$	10	0.070	2,500	1,900	100	
NRS6045T 220MMG8	22	$\pm 20\%$	7	0.107	2,000	1,600	100	
NRS6045T 330MMG8	33	$\pm 20\%$	6	0.141	1,650	1,400	100	
NRS6045T 470MMG8	47	$\pm 20\%$	5	0.211	1,400	1,150	100	
NRS6045T 680MMG8	68	$\pm 20\%$	4	0.304	1,100	950	100	
NRS6045T 101MMG8	100	$\pm 20\%$	3	0.466	900	750	100	

● NRS8030 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 30\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS8030T 1R0NJG8	1.0	$\pm 30\%$	120	0.009	7,800	6,200	100	
NRS8030T 1R5NJG8	1.5	$\pm 30\%$	80	0.012	6,200	5,300	100	
NRS8030T 2R2NJG8	2.2	$\pm 30\%$	60	0.015	4,900	4,800	100	
NRS8030T 3R3MJG8	3.3	$\pm 20\%$	50	0.019	4,200	4,300	100	
NRS8030T 4R7MJG8	4.7	$\pm 20\%$	40	0.022	3,600	4,000	100	
NRS8030T 6R8MJG8	6.8	$\pm 20\%$	32	0.029	3,000	3,400	100	
NRS8030T 100MJG8	10	$\pm 20\%$	27	0.033	2,400	3,000	100	
NRS8030T 150MJG8	15	$\pm 20\%$	20	0.060	2,000	2,200	100	
NRS8030T 220MJG8	22	$\pm 20\%$	16	0.070	1,750	1,900	100	
NRS8030T 330MJG8	33	$\pm 20\%$	13	0.120	1,300	1,500	100	
NRS8030T 470MJG8	47	$\pm 20\%$	11	0.170	1,100	1,300	100	

※) The saturation current 8alue (Idc1) is the DC current 8alue ha8ing inductance decrease down to 30%. (at 20°C)

※) The temperature rise current 8alue (Idc2) is the DC current 8alue ha8ing temperature increase up to 40°C. (at 20°C)

※) The rated current is the DC current 8alue that satisfies both of current 8alue saturation current 8alue and temperature rise current 8alue.

PART NUMBER

● NRS8040 Shielded type

Part number	Nominal inductance [μ H]	Inductance tolerance	Self-resonant frequency [MHz] (min.)	DC Resistance [Ω] ($\pm 30\%$)	Rated current ※) [mA]		Measuring frequency[kHz]	Note
					Saturation current Idc1	Temperature rise current Idc2		
NRS8040T 0R9NJGJ8	0.9	$\pm 30\%$	85	0.006	13,000	7,800	100	
NRS8040T 1R4NJGJ8	1.4	$\pm 30\%$	63	0.007	10,000	7,000	100	
NRS8040T 2R0NJGJ8	2.0	$\pm 30\%$	50	0.009	8,100	6,300	100	
NRS8040T 3R6NJGJ8	3.6	$\pm 30\%$	34	0.015	6,400	4,900	100	
NRS8040T 4R7NJGJ8	4.7	$\pm 30\%$	30	0.018	5,400	4,100	100	
NRS8040T 6R8NJGJ8	6.8	$\pm 30\%$	24	0.025	4,400	3,700	100	
NRS8040T 100MJGJ8	10	$\pm 20\%$	22	0.034	3,800	3,100	100	
NRS8040T 150MJGJ8	15	$\pm 20\%$	16	0.050	2,900	2,400	100	
NRS8040T 220MJGJ8	22	$\pm 20\%$	13	0.066	2,400	2,200	100	
NRS8040T 330MJGK8	33	$\pm 20\%$	12	0.100	2,000	1,700	100	
NRS8040T 470MJGK8	47	$\pm 20\%$	8	0.140	1,500	1,500	100	
NRS8040T 680MJGK8	68	$\pm 20\%$	7	0.210	1,300	1,200	100	
NRS8040T 101MJGK8	100	$\pm 20\%$	6	0.280	1,100	1,000	100	

※) The saturation current value (Idc1) is the DC current value having inductance decrease down to 30%. (at 20°C)
















※) The temperature rise current value (Idc2) is the DC current value having temperature increase up to 40°C. (at 20°C)

※) The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

Derating of Rated Current

NR series H type/S type/V type

Derating of current is necessary for NR series H type/S type/V type depending on ambient temperature.
Please refer to the chart shown below for appropriate derating of current.















► This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our product specification sheets. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our website (<http://www.ty-top.com/>).

Derating of Rated Current

NR series H type/S type/V type

Derating of current is necessary for NR series H type/S type/V type depending on ambient temperature. Please refer to the chart shown below for appropriate derating of current.




■ PACKAGING


Type	Standard Quantity [pcs]
	Tape & Reel
NRV2010	2500
NRS2012	2500
NRV2012	
NRH2410	2500
NRH2412	2500
NR 3010	2000
NRH3010	
NR 3012	2000
NRH3012	
NRV3012	
NR 3015	2000
NRS3015	
NR 4010	5000
NRS4010	
NR 4012	4500
NRS4012	
NR 4018	3500
NRS4018	

Type	Standard Quantity [pcs]
	Tape & Reel
NRS5010	1000
NRS5012	1000
NRS5014	1000
NRS5020	800
NRS5024	2500
NRS5030	500
NR 5040	1500
NRS5040	
NRS6010	1000
NR 6012	1000
NRS6012	
NRS6014	1000
NR 6020	2500
NRS6020	
NR 6028	2000
NRS6028	
NR 6045	1500
NRM6045	
NRS6045	
NRS8030	1000
NR 8040	1000
NRS8040	

● Embossed Tape



● Embossed tape 8mm wide (0.315 inches wide)




i smd NR pack e-E07R01

Type	Chip cavity		Insertion pitch	Tape thickness	
	A	B	F	T	K
NRV2010	2.2±0.1 (0.102±0.004)	2.2±0.1 (0.102±0.004)	4.0±0.1 (0.157±0.004)	0.25±0.05 (0.009±0.002)	1.3±0.1 (0.051±0.004)
NRS2012					
NRV2012					
NRH2410	2.6±0.1 (0.087±0.004)	2.6±0.1 (0.102±0.004)		0.25±0.05 (0.009±0.002)	1.3±0.1 (0.051±0.004)
NRH2412					
NR 3010	3.2±0.1 (0.126±0.004)	3.2±0.1 (0.126±0.004)		0.3±0.05 (0.012±0.002)	1.4±0.1 (0.055±0.004)
NRH3010					1.6±0.1 (0.063±0.004)
NR 3012					1.9±0.1 (0.075±0.004)
NRH3012					
NRV3012					
NR 3015					
NRS3015					

Unit : mm (inch)


● Embossed tape 12mm wide (0.47 inches wide)



Type	Chip cavity		Insertion pitch	Tape thickness		
	A	B		T	K	
NR 4010	4.3±0.1 (0.169±0.004)	4.3±0.1 (0.169±0.004)	8.0±0.1 (0.315±0.004)	0.3±0.1 (0.012±0.004)	1.4±0.1 (0.055±0.004)	
NRS4010					1.6±0.1 (0.063±0.004)	
NR 4012					2.1±0.1 (0.083±0.004)	
NRS4012					1.4±0.1 (0.055±0.004)	
NR 4018	5.25±0.1 (0.207±0.004)	5.25±0.1 (0.207±0.004)			1.6±0.1 (0.063±0.004)	
NRS4018					2.3±0.1 (0.091±0.004)	
NRS5010					2.7±0.1 (0.106±0.004)	
NRS5012					3.2±0.1 (0.126±0.004)	
NRS5014	5.15±0.1 (0.203±0.004)	5.15±0.1 (0.203±0.004)		0.4±0.1 (0.016±0.004)	4.2±0.1 (0.165±0.004)	
NRS5020					1.4±0.1 (0.055±0.004)	
NRS5024					1.6±0.1 (0.063±0.004)	
NRS5030					2.3±0.1 (0.090±0.004)	
NR 5040	6.3±0.1 (0.248±0.004)	6.3±0.1 (0.248±0.004)			0.4±0.1 (0.016±0.004)	3.1±0.1 (0.122±0.004)
NRS5040						4.7±0.1 (0.185±0.004)
NRS6010						
NR 6012						
NRS6012						
NRS6014						
NR 6020						
NRS6020						
NR 6028						
NRS6028						
NR 6045						
NRM6045						
NRS6045						

Unit : mm (inch)

● Embossed tape 16mm wide (0.63 inches wide)




Type	Chip cavity		Insertion pitch	Tape thickness	
	A	B		T	K
NRS8030	8.3 ± 0.1 (0.327 ± 0.004)	8.3 ± 0.1 (0.327 ± 0.004)	12.0 ± 0.1 (0.472 ± 0.004)	0.5 ± 0.1 (0.020 ± 0.004)	3.4 ± 0.1 (0.134 ± 0.004)
NR 8040					4.5 ± 0.1 (0.177 ± 0.004)
NRS8040					4.5 ± 0.1 (0.177 ± 0.004)


Unit : mm (inch)

④ Leader and Blank portion

● NR, NRH, NRS, NRV



⑤ Reel size




Type	Reel size (Reference values)		
	ϕD	ϕd	W
NRV2010	180 ± 0.5 (7.087 ± 0.019)	60 ± 1.0 (2.36 ± 0.04)	10.0 ± 1.5 (0.394 ± 0.059)
NRS2012			
NRV2012			
NRH2410			
NRH2412			
NR 3010			
NRH3010			
NR 3012			
NRH3012			
NRV3012			
NR 3015			
NRS3015			

► This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification.
For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>) .

NRS5010	180±3.0 (7.087±0.118)	60±2.0 (2.36±0.08)	14.0±1.5 (0.551±0.059)
NRS5012			
NRS5014			
NRS5020			
NRS5030			
NRS6010			
NR 6012			
NRS6012			
NRS6014			

Unit: mm (inch)




Type	Reel size (Reference values)			
	ϕD	ϕd	t (max.)	W
NR 4010	330±3.0 (12.99±0.118)	80±2.0 (3.15±0.078)	18.5 (0.72)	13.5±1.0 (0.531±0.04)
NRS4010				
NR 4012				
NRS4012				
NR 4018				
NRS4018				
NRS5024				
NR 5040				
NRS5040				
NR 6020				
NRS6020				
NR 6028				
NRS6028				
NR 6045				
NRM6045				
NRS6045				
NRS8030			22.5 (0.89)	17.5±1.0 (0.689±0.04)
NR 8040				
NRS8040				

Unit: mm (inch)

⑥ Top Tape Strength


The top tape requires a peel-off force of 0.1 to 1.3N in the direction of the arrow as illustrated below.



SMD POWER INDUCTORS (NR SERIES)

RELIABILITY DATA

1. Operating Temperature Range		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	－40～＋125℃(Including self-generated heat)
Test Methods and Remarks	Including self-generated heat	
2. Storage Temperature Range		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	－40～＋85℃
Test Methods and Remarks	－5 to 40℃ for the product with taping.	
3. Rated current		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Within the specified tolerance
4. Inductance		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Within the specified tolerance
Test Methods and Remarks	Measuring equipment : LCR Meter (HP 4285A or equivalent) Measuring frequency : 100kHz, 1V	
5. DC Resistance		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Within the specified tolerance
Test Methods and Remarks	Measuring equipment : DC ohmmeter (HIOKI 3227 or equivalent)	
6. Self resonance frequency		
Specified Value	NRV30Type,NRH24/30Type NRS30/40/50/60/80Type、NRM50/60Type	Within the specified tolerance
	NRV20,NRS20	－
Test Methods and Remarks	NRV30,NRH24/30,NRS30/40/50/60/80Type、NRM50/60Type Measuring equipment : Impedance analyzer/material analyzer(HP4291A or equivalent HP4191A, 4192A or equivalent)	
7. Temperature characteristic		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Inductance change : Within ±20%
Test Methods and Remarks	NRV20/30, NRH24/30, NRS20/30/40/50/60/80 Type、NRM50/60Type : Measurement of inductance shall be taken at temperature range within －40℃～＋85℃. With reference to inductance value at ＋20℃., change rate shall be calculated.	
	Change of maximum inductance deviation in step 1 to 5	
	Step	Temperature(℃)
	1	20
	2	Minimum operating temperature
	3	20 (Standard temperature)
	4	Maximum operating temperature
	5	20

8. Resistance to flexure of substrate					
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type		No damage		
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. As illustrated below, apply force in the direction of the arrow indicating until deflection of the test board reaches to 2 mm.				
	Test board size : 100 × 40 × 1.6 mm				
	Test board material : glass epoxy-resin				
	Solder cream thickness : 0.10mm (NRS20/30, NRH24/30, NRV20/30, NRM50Type)				
	: 0.15mm (NRS40/50/60/80Type,NRM60Type)				
	Land dimension				
		Type	A	B	C
		NRS20, NRV20	0.65	0.7	2.0
		NRH24	0.7	0.75	2.0
		NRV30,NRH30,NRS30	0.8	1.4	2.7
		NRS40	1.2	1.6	3.7
		NRS50	1.5	2.1	4.0
		NRM50	1.9	2.3	3.8
		NRS60	1.6	3.1	5.7
		NRM60	2.4	2.6	4.8
		NRS80	1.8	3.8	7.5

14. Solderability		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	At least 90% of surface of terminal electrode is covered by new solder.
Test Methods and Remarks	The test samples shall be dipped in flux, and then immersed in molten solder as shown in below table. Flux : Methanol solution containing rosin 25%.	
	Solder Temperature	245±5°C
	Time	5±1.0 sec.
※Immersion depth : All sides of mounting terminal shall be immersed.		
15. Resistance to soldering heat		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Inductance change : Within ±10% No significant abnormality in appearance.
Test Methods and Remarks	The test sample shall be exposed to reflow oven at 230±5°C for 40 seconds, with peak temperature at 260±5°C for 5 seconds, 2 times.	
	Test board material	: glass epoxy-resin
	Test board thickness	: 1.0mm
16. Thermal shock		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Inductance change : Within ±10% No significant abnormality in appearance.
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. The test samples shall be placed at specified temperature for specified time by step 1 to step 4 as shown in below table in sequence. The temperature cycle shall be repeated 1000 cycles.	
	Conditions of 1 cycle	
	Step	Temperature (°C)
	1	-40±3
	2	Room temperature
	3	+85±2
	4	Room temperature
17. Damp heat		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Inductance change : Within ±10% No significant abnormality in appearance.
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. The test samples shall be placed in thermostatic oven set at specified temperature and humidity as shown in below table.	
	Temperature	60±2°C
	Humidity	90~95%RH
	Time	1000+24/-0 hour
18. Loading under damp heat		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Inductance change : Within ±10% No significant abnormality in appearance.
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. The test samples shall be placed in thermostatic oven set at specified temperature and humidity and applied the rated current continuously as shown in below table.	
	Temperature	60±2°C
	Humidity	90~95%RH
	Applied current	Rated current
	Time	1000+24/-0 hour
19. Low temperature life test		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Inductance change : Within ±10% No significant abnormality in appearance.
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow. After that, the test samples shall be placed at test conditions as shown in below table.	
	Temperature	-40±2°C
	Time	1000+24/-0 hour
20. High temperature life test		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	—

21. Loading at high temperature life test		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type、NRM50/60Type	Inductance change : Within $\pm 10\%$ No significant abnormality in appearance.
Test Methods and Remarks	The test samples shall be soldered to the test board by the reflow soldering.	
	Temperature	$85 \pm 2^{\circ}\text{C}$
	Applied current	Rated current
	Time	$1000 + 24 / - 0$ hour
22. Standard condition		
Specified Value	NRV20/30Type,NRH24/30Type NRS20/30/40/50/60/80Type NRM50/60Type	Standard test condition : Unless otherwise specified, temperature is $20 \pm 15^{\circ}\text{C}$ and $65 \pm 20\%$ of relative humidity. When there is any question concerning measurement result: In order to provide correlation data, the test shall be condition of $20 \pm 2^{\circ}\text{C}$ of temperature, $65 \pm 5\%$ relative humidity. Inductance is in accordance with our measured value.

SMD POWER INDUCTORS (NR, NS, ES SERIES)

PRECAUTIONS


1. Circuit Design

Precautions	◆Operating environment
	1. The products listed in this catalogue are intended for use in general electronic equipment (e.g., AV equipment, OA equipment, home electric appliances, office equipment, information and communication equipment), general medical equipment, industrial equipment, and automotive interior applications, etc. Please be sure to contact TAIYO YUDEN for further information before using the products for any equipment which may directly cause loss of human life or bodily injury (e.g., specially controlled medical equipment, transportation equipment including, without limitation, automotive powertrain control system, train control system, and ship control system, traffic signal equipment). Please do not incorporate our products into any equipment requiring high levels of safety and/or reliability (e.g., aerospace equipment, aviation equipment, nuclear control equipment, undersea equipment, military equipment, etc.).


2. PCB Design

Precautions	◆Land pattern design
	1. Please refer to a recommended land pattern. 2. There is stress, which has been caused by distortion of a PCB, to the inductor. (NRV20/30, NRH24/30, NRS20/30/40/50/60/80, NRM60 Type) 3. Please consider the arrangement of parts on a PCB. (NRV20/30, NRH24/30, NRS20/30/40/50/60/80, NRM60 Type)



Technical considerations	◆Land pattern design
	Surface Mounting 1. Mounting and soldering conditions should be checked beforehand. 2. Applicable soldering process to this products is reflow soldering only. 3. Please use the recommended land pattern shown as below. Electrical characteristics and the mounting ability of the product are being considered in the recommended land pattern. If a PCB is designed with other dimensions, defective soldering and stress to a product may occur due to misalignment. The performance of the product may not be brought out. If an adopted land pattern is different from the recommended land pattern, stress to the product will increase. It may cause cracks or defective electrical characteristics of the product. Please conduct validation completely before studying adoption of this product and please judge the pros and cons of adoption of this product with taking on responsibility. (NR30/40/50/60/80, NRV20/30, NRH24/30, NRS20/30/40/50/60/80, NRM60 Type) 4. As coefficients of thermal expansion between an inductor and a PCB differs, cracks may occur on a ferrite core when thermal stress is applied to them after mounting an inductor. (Please refer to the drawings below.) Please conduct validation completely before studying adoption of this product and please judge the pros and cons of adoption of this product with taking on responsibility. (NRV20/30, NRH24/30, NRS20/30/40/50/60/80, NRM60 Type)





5. SMD inductors should be located to minimize any possible mechanical stresses from board warp or deflection. When splitting the PC board after mounting inductors and other components, care is required so as not to give any stresses of deflection or twisting to the board. (NRV20/30, NRH24/30, NRS20/30/40/50/60/80, NRM60 Type)



A product tends to undergo stress in order “A>C>B≡D”.
Please consider the layouts of a product to minimize any stresses.

3. Considerations for automatic placement	
Precautions	<p>◆Adjustment of mounting machine</p> <ol style="list-style-type: none"> 1. Excessive impact load should not be imposed on the products when mounting onto the PC boards. 2. Mounting and soldering conditions should be checked beforehand.
Technical considerations	<p>◆Adjustment of mounting machine</p> <ol style="list-style-type: none"> 1. When installing products, care should be taken not to apply distortion stress as it may deform the products. 2. Stress may be applied to a product with a warp or a twist in handling of the product. Please conduct validation completely before studying adoption of this product and please judge the pros and cons of adoption of this product with taking on responsibility. (NRV20/30, NRH24/30, NRS20/30/40/50/60/80, NRM60 Type) <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;"> <p><Wrap></p>  </div> <div style="text-align: center;"> <p><Twist></p>  </div> </div>

4. Soldering	
Precautions	<p>◆Reflow soldering</p> <ol style="list-style-type: none"> 1. Please contact any of our offices for a reflow soldering, and refer to the recommended condition specified. 2. The product shall be used reflow soldering only. 3. Please do not add any stress to a product until it returns in normal temperature after reflow soldering. <p>◆Lead free soldering</p> <ol style="list-style-type: none"> 1. When using products with lead free soldering, we request to use them after confirming adhesion, temperature of resistance to soldering heat, soldering etc sufficiently. <p>◆Recommended conditions for using a soldering iron</p> <ul style="list-style-type: none"> • Put the soldering iron on the land-pattern. • Soldering iron's temperature – Below 350°C • Duration – 3 seconds or less • The soldering iron should not directly touch the inductor.
Technical considerations	<p>◆Reflow soldering</p> <ol style="list-style-type: none"> 1. If products are used beyond the range of the recommended conditions, heat stresses may deform the products, and consequently degrade the reliability of the products. <ul style="list-style-type: none"> • NRV20/30, NRH24/30, NRS20/30/40/50/60/80, NRM60 Type, NS101/125 Type, EST0645/1040/1060 Type <p>Recommended reflow condition (Pb free solder)</p> <div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p><u>NR, NS Series</u></p>  </div> <div style="text-align: center;"> <p><u>ES Series</u></p>  </div> </div>

5. Cleaning	
Precautions	<p>◆Cleaning conditions</p> <ol style="list-style-type: none"> 1. Washing by supersonic waves shall be avoided.
Technical considerations	<p>◆Cleaning conditions</p> <ol style="list-style-type: none"> 1. If washed by supersonic waves, the products might be broken.

6. Handling

► This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification.
For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (<http://www.ty-top.com/>)

Precautions	<ul style="list-style-type: none"> ◆ Handling <ol style="list-style-type: none"> 1. Keep the product away from all magnets and magnetic objects. ◆ Breakaway PC boards (splitting along perforations) <ol style="list-style-type: none"> 1. When splitting the PC board after mounting product, care should be taken not to give any stresses of deflection or twisting to the board. 2. Board separation should not be done manually, but by using the appropriate devices. ◆ Mechanical considerations <ol style="list-style-type: none"> 1. Please do not give the product any excessive mechanical shocks. 2. Please do not add any shock and power to a product in transportation. ◆ Pick-up pressure <ol style="list-style-type: none"> 1. Please do not push to add any pressure to a winding part. Please do not give any shock and push into a ferrite core exposure part. ◆ Packing <ol style="list-style-type: none"> 1. Please avoid accumulation of a packing box as much as possible.
Technical considerations	<ul style="list-style-type: none"> ◆ Handling <ol style="list-style-type: none"> 1. There is a case that a characteristic varies with magnetic influence. ◆ Breakaway PC boards (splitting along perforations) <ol style="list-style-type: none"> 1. The position of the product on PCBs shall be carefully considered to minimize the stress caused from splitting of the PCBs. ◆ Mechanical considerations <ol style="list-style-type: none"> 1. There is a case to be damaged by a mechanical shock. 2. There is a case to be broken by the handling in transportation. ◆ Pick-up pressure <ol style="list-style-type: none"> 1. Damage and a characteristic can vary with an excessive shock or stress. ◆ Packing <ol style="list-style-type: none"> 1. If packing boxes are accumulated, that could cause a deformation on packing tapes or a damage on the products.
7. Storage conditions	
Precautions	<ul style="list-style-type: none"> ◆ Storage <ol style="list-style-type: none"> 1. To maintain the solderability of terminal electrodes and to keep the packing material in good condition, temperature and humidity in the storage area should be controlled. <ul style="list-style-type: none"> ▪ Recommended conditions <div style="margin-left: 20px;">Ambient temperature : $-5\sim 40^{\circ}\text{C}$</div> <div style="margin-left: 20px;">Humidity : Below 70% RH</div> ▪ The ambient temperature must be kept below 30°C. Even under ideal storage conditions, solderability of products electrodes may decrease as time passes. For this reason, product should be used within 6 months from the time of delivery. In case of storage over 6 months, solderability shall be checked before actual usage.
Technical considerations	<ul style="list-style-type: none"> ◆ Storage <ol style="list-style-type: none"> 1. Under a high temperature and humidity environment, problems such as reduced solderability caused by oxidation of terminal electrodes and deterioration of taping/packaging materials may take place.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiyo Yuden:

[NRS3015T2R2MNGH8](#) [NRS5040T100MMGJ8](#) [NRS6020T2R2NMGJ8](#) [NRS4018T150MDGJ8](#)
[NRS4018T4R7MDGJ8](#)