

# SPECIFICATION

Part Number: **MAT.03A**

Product Name: MAT.03A Embedded Active GPS and Cellular Antenna Assembly and Reference Board

Features: 2in1 Embedded Antenna Solution  
Two SMA(F) connectors for Output  
**GPS Antenna – ASGP.1575.25B.4.A.01**

- SMT Active GPS Patch Antenna
- High performance 28dB LNA
- Ultra low power consumption
- Patch 25x25x4mm

**Cellular Antenna- PA.25 Hexa-Band Cellular SMT Antenna**

- 2G and 3G Bands
- GSM/GPRS/CDMA/HSPA
- High efficiency Multi-band SMT antenna
- 35x5x6mm

**RoHS Compliant** ✓

5.



## 1. Introduction

The MAT.03A Reference GPS and Cellular Embedded Antenna board combines the 2G/3G PA.25 Hexa-Band Cellular SMT Antenna and the ASGP.1575.25B.4.A.0 SMT 28dB Active GPS Patch Antenna from Taoglas. It can be used as a reference board design or actual embedded antenna for telematics applications such as fleet management, asset tracking, road pricing, and security/surveillance. Best placement for this reference board in a device would be over the existing mainboard and away from metal to allow for maximum radiated efficiency, and for the GPS antenna to get a view towards the sky.

The board comes with one SMA(F) connector for each antenna feed on the bottom side for easy connection via a cable assembly to a module or test equipment.

### **Cellular Antenna PA.25**

This compact SMT ceramic high performance antenna achieves high efficiency on almost all worldwide 2G and 3G bands, for applications such as GSM/GPRS/CDMA/HSPA. Transmission losses are kept to absolute minimum resulting in much improved over the air (OTA) device performance compared to similar efficiency cable and connector antenna solutions.

### **GPS Antenna ASGP.1575.25B.4.A.01**

The patent pending revolutionary SMT GPS patch antenna allows for optimal GPS performance by combining the ceramic patch, SAW, LNA, and feed pad in one integral sandwich package, mounted on its own ground-plane. Having the SAW filter and LNA right after the feed reduces the chance of noise entering the transmission line and boosts the GPS signal at the source before noise enters, allowing for better signal to noise ratio.

It also frees up space on your board traditionally used for the filter and LNA.


The SAW is placed in front of the LNA, helping to prevent saturation due to nearby radio transmitters, and the possibility of radiated spurious emissions through other radio systems.

Individual specifications on the antennas are available on the Taoglas website. Contact your regional Taoglas office for support on integration of these antennas in your own device such as gerber and layout review, and matching.

## 2. Specification

### 2.1 System Configuration

This antenna specification covers the Hexa-band Cellular Full band and GPS (L1 Band).



**Figure 1.** System configuration

## 2.2 PA.25 Cellular Antenna

| Electrical*           |                                     |              |              |              |
|-----------------------|-------------------------------------|--------------|--------------|--------------|
|                       | 824-960 MHz                         | 1710-1880MHz | 1850-1990MHz | 1920-2170MHz |
| Peak Gain (dBi)       | 0.48                                | 2.13         | 2.54         | 2.25         |
| Efficiency (%)        | 51.41                               | 57.79        | 53.27        | 48.34        |
| Return loss           | <-5 dB                              |              |              |              |
| Impedance             | 50Ω                                 |              |              |              |
| Polarization          | Linear                              |              |              |              |
| Mechanical            |                                     |              |              |              |
| EVB Connector         | SMA(F)                              |              |              |              |
| Dimensions (mm)       | 35 x 6 x 5                          |              |              |              |
| Termination           | Ag (environmental-friendly Pb free) |              |              |              |
| Material              | Ceramic                             |              |              |              |
| Environmental         |                                     |              |              |              |
| Operation Temperature | -40°C to 85°C                       |              |              |              |
| Storage Temperature   | -40°C to 105°C                      |              |              |              |
| Relative Humidity     | Non-condensing 65°C 95% RH          |              |              |              |
| RoHs Compliant        | Yes                                 |              |              |              |

\*Ground plane size 110x40 mm

## 2.3 ASGP.1575.25B.4.A.01 GPS Antenna

| Electrical Specifications - Antenna*   |                               |
|--|-------------------------------|
| Polarization                           | RHCP                          |
| Axial ratio                            | Max 3.0dB@zenith              |
| Input Voltage                          | Min:1.8V Typ.: 3.0V Max: 5.5V |
| Gain                                   | Typ. -1.5dBic @ Zenith        |
| Mechanical Specifications - Antenna    |                               |
| Dimensions (mm)                        | 25 x 25 x 4                   |
| Connection                             | SMT via solder pads           |
| Environmental Specifications - Antenna |                               |
| Operation Temperature                  | -40°C to 85°C                 |
| Storage Temperature                    | -40°C to + 85°C               |
| Relative Humidity                      | 40% to 95%                    |

| Electrical Specifications - LNA*              |                     |                           |                   |
|---|---------------------|---------------------------|-------------------|
| Frequency Range                               | 1575.42 ± 1.023 MHz |                           |                   |
| Output Impedance                              | 50Ω                 |                           |                   |
| Outer Band Attenuation                        | F0=1575.42MHz       |                           |                   |
|   | F0±30MHz 5dB min    |                           |                   |
|   | F0±50MHz 25dB min   |                           |                   |
|   | F0±100MHz 30dB min  |                           |                   |
| Pout at 1dB Gain Compression point            | -7 dBm Typ.         |                           |                   |
| Output VSWR                                   | 2.0 Max             |                           |                   |
| LNA Gain, Power Consumption and Noise Figure* |                     |                           |                   |
| Voltage                                       | LNA Gain (Typ)      | Power Consumption(mA) Typ | Noise Figure(Typ) |
| Min 1.8V                                      | 20dB                | 4.5mA                     | 2.8dB             |
| Typ 3.0V                                      | 28dB                | 9mA                       | 2.7dB             |
| Max 5.5V                                      | 30dB                | 18mA                      | 3.0dB             |


| Electrical Specifications – Overall* |                          |
|--------------------------------------|--------------------------|
| Frequency Range                      | 1575.42MHz +/- 1.023 MHz |
| Gain                                 | At 90° at 3.0V 26.5±4dBi |
| Output Impedance                     | 50Ω                      |
| VSWR                                 | 2.0 Max.                 |

\*Ground plane size 110x40 mm

### 3. Test Setup



(a)




(b)

**Figure 2.** (a) PA.25 Cellular antenna Return Loss and VSWR test setup; (b) Peak gain, Average gain, Efficiency and Radiation pattern test setup


## PA.25 Cellular Antenna

### 3.1 Return Loss




**Figure 3.** Return Loss of the PA.25 Cellular Antenna

### 3.2 Efficiency




**Figure 4.** Efficiency of the PA.25 Cellular Antenna

### 3.3 Peak Gain



**Figure 5.** Peak Gain of the PA.25 Cellular Antenna

### 3.4 Average Gain




**Figure 6.** Average Gain of the PA.25 Cellular Antenna




### 3.5 3D Radiation Pattern


Azimuth=0.0  
Elevation=0.0  
Roll=-45.0




880MHz




960MHz




Azimuth=0.0  
Elevation=0.0  
Roll=-45.0




1710MHz




1880MHz




Azimuth=0.0  
Elevation=0.0  
Roll=-45.0




1850MHz




1990MHz




Azimuth=0.0  
Elevation=0.0  
Roll=-45.0



2110MHz





2170MHz





**Figure 7.** 3D Radiation Pattern of the PA.25 Cellular Antenna

### 3.6 2D Radiation Pattern



#### X-Y plane



## Y-Z plane




## X-Z plane



**Figure 8.** 2D Radiation Pattern of the PA.25 cellular antenna


## 4. ASGP.1575.25B.4.A.01 Active GPS Antenna

### 4.1 LNA Gain and Out Band Rejection @3.0V




**Figure 9.** LNA Gain and Out Band Rejection @3.0V

## 4.2 LNA Noise Figure @3.0V




**Figure 10.** LNA Noise figure @3.0V

### 4.3 GPS Antenna Radiation Pattern




**Figure 11.** X-Z plane






**Figure 12.** Y-Z plane



**Figure 13.** X-Y plane

## 5. Mechanical Drawing

### PA.25 Mechanical Drawing




**Figure 15.** Mechanical Drawing of the PA.25 Antenna.




## 6. Layout Dimensions

### 6.1 PA.25 Layout Dimension




**Figure 17.** Layout dimensions of the PA.25 Antenna.

### 6.2 ASGP.1575.25B.4.A.01 Layout Dimension



**Figure 18.** Layout dimensions of the ASGP.1575.25B.4.A.01 Antenna



## 7. EVB Dimension



**Figure 19.** EVB Dimension of MAT.03A Antenna




## 8. Matching Circuit (PA.25)



| Circuit Symbol | Size | Description                     |
|----------------|------|---------------------------------|
| L1             | 0402 | 6.8nH inductor (001513A000055A) |
| R1             | 0402 | 0Ω resistor (001511J010012A)    |

**Figure 20.** Recommended matching circuit

## 9. Packaging






## 10. Recommended Reflow Temperature Profile

PA.25 and ASGP.1575.25B.4.A.01 can be assembled following either Sn-Pb or Pb-Free assembly processes. The recommended soldering temperatures are as follows:

| Phase                              | Profile Features   | Sn-Pb Assembly   | Pb-Free Assembly (SnAgCu) |
|------------------------------------|--|------------------|---------------------------|
| Ramp-Up                            | Avg. Ramp-Up Rate (T <sub>smax</sub> to T <sub>P</sub> ) | 3°C/second (max) | 3°C/second (max)          |
| Preheat                            | Temperature Min (T <sub>smin</sub> )                     | 100°             | 100°                      |
|                                    | Temperature Max (T <sub>smax</sub> )                     | 150°             | 150°                      |
|                                    | Time (t <sub>smin</sub> to t <sub>smax</sub> )           | 60-120 seconds   | 60-120 seconds            |
| Reflow                             | Temperature (T <sub>L</sub> )                            | 183°C            | 217°C                     |
|                                    | Total Time Above T <sub>L</sub> b(t <sub>L</sub> )       | 60-150 seconds   | 60-150 seconds            |
| Peak                               | Temperature (T <sub>P</sub> )                            | 235°C            | 260°C                     |
|                                    | Time (t <sub>p</sub> )                                   | 10-30 seconds    | 20-40 seconds             |
| Ramp-Down                          | Rate   | 6°C/second (max) | 6°C/second (max)          |
| Time from 25°C to peak Temperature |  | 6 minutes max    | 8 minutes max             |

**Temperature profile – (green area) for the assembly process in reflow ovens**



**Figure 21.** Temperature profile for the assembly process in reflow ovens

*Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited. Copyright © 2014, Taoglas Ltd.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taoglas:](#)

[MAT.03A](#)