

## SPECIFICATION

Part No. : **WCM.01.0151**

Product Name: : 2.4GHz Button Antenna

Features : Tiny Size – 19.8mm\*14.3mm\*16.4mm  
2400MHz to 2500MHz Antenna  
Wi-Fi / Bluetooth  
60%+ Efficiency  
RP SMA(M) Connector  
IP67  
Omnidirectional  
ROHS Compliant

Photo:



## 1. Introduction

The WCM.01 2.4GHz antenna is the smallest RP-SMA(M) external antenna in the market, fitting into spaces no other traditional monopole, dipole or rubber ducky antenna can go. A unique PIFA design ensures omnidirectional gain across 2.4GHz to 2.5GHz ensuring constant reception and transmission to make it a great Wi-Fi antenna for 2.4GHz Wi-Fi and Bluetooth applications.

This antenna features greater than 60% efficiency when connected directly to the ground plane of the device.

### Typical Applications

- Application Points
- Routers
- IoT M2M devices
- Smart home applications

This antenna comes with a RP SMA(M) to be compatible with most Wi-Fi applications and routers in the market. The WCM.01 antenna is also IP67 water resistant. The ideal position for the antenna to radiate is mounted clear of metal. Connector is customizable.

Contact Taoglas regional sales office for more information.


## 2. Specification

ELECTRICAL				
Frequency (MHz)		2400	2450	2500
Efficiency (%)				
In free space		33.30	30.36	29.65
On the 10*10cm	Ground plane(center)	63.43	71.44	66.85
	Ground plane(edge)	55.85	68.43	61.73
On the 20*20cm	Ground plane(center)	64.20	71.40	63.97
	Ground plane(edge)	62.55	81.30	69.73
On the 30*30cm	Ground plane(center)	58.31	70.49	60.87
	Ground plane(edge)	62.11	73.46	61.90
Average gain (dBi)				
In free space		-4.78	-5.18	-5.28
On the 10*10cm	Ground plane(center)	-1.98	-1.46	-1.75
	Ground plane(edge)	-2.53	-1.65	-2.10
On the 20*20cm	Ground plane(center)	-1.92	-1.46	-1.94
	Ground plane(edge)	-2.04	-0.90	-1.57
On the 30*30cm	Ground plane(center)	-2.34	-1.52	-2.16
	Ground plane(edge)	-2.07	-1.34	-2.08
Peak gain (dBi)				
In free space		0.89	0.40	0.12
On the 10*10cm	Ground plane(center)	2.02	2.45	2.37
On the 10*10cm	Ground plane(edge)	3.46	4.09	3.47
On the 20*20cm	Ground plane(center)	4.26	4.54	3.69
On the 20*20cm	Ground plane(edge)	4.02	5.40	4.65
On the 30*30cm	Ground plane(center)	3.64	4.85	4.06
On the 30*30cm	Ground plane(edge)	3.79	4.23	3.15
Radiation	Omnidirectional			
Polarization	Linear			
Impedance	50 Ω			
Input Power	10W			
MECHANICAL				
Antenna Dimension	19.8*14.3*16.4mm			
Casing	ABS			
Connector	RP-SMA(M)			
Weight	6g			
Ingress Protection Rating	IP67			


ENVIRONMENTAL	
Operation Temperature	-40°C ~ + 85°C
Storage Temperature	-40°C ~ + 85°C
Humidity	Non-condensing 65°C 95% RH

## 3. Antenna Characteristics


### 3.1 Testing Setup




a) In free space




b) With 10\*10cm  
ground plane center




c) With 10\*10cm  
ground plane edge



d) With 20\*20cm  
ground plane center



e) With 20\*20cm  
ground plane edge




f) With 30\*30cm  
ground plane center



g) With 30\*30cm  
ground plane edge


**Figure.1** Antenna Measurement Setup

### 3.2 Return Loss (In free space)




**Figure 2.** Return loss of WCM.01 antenna

### 3.3 Return Loss(On the ground plane Center)




**Figure 3.** Return loss of WCM.01 antenna with different ground plane size

### 3.4 Return Loss (On the ground plane Edge)




**Figure 4.** Return loss of WCM.01 antenna with different ground plane size

### 3.5 Efficiency (In free space)




**Figure 5.** Efficiency of WCM.01 antenna

### 3.6 Efficiency (On the ground plane Center)



**Figure 6.** Return loss of WCM.01 antenna with different ground plane size


### 3.7 Efficiency (On the ground plane Edge)



**Figure 7.** Return loss of WCM.01 antenna with different ground plane size




### 3.8 Peak Gain (In free space)




**Figure 8.** Peak gain of WCM.01 antenna with different ground plane size

### 3.9 Peak Gain (On the ground plane Center)




**Figure 9.** Peak gain of WCM.01 antenna with different ground plane size

### 3.10 Peak Gain (On the ground plane Edge)




**Figure 10.** Peak gain of WCM.01 antenna with different ground plane size

### 3.11 Average Gain (In free space)




**Figure 11.** Average gain of WCM.01

### 3.12 Average Gain (On the ground plane Center)



**Figure 12.** Average gain of WCM.01 antenna with different ground plane size

### 3.13 Average Gain (On the ground plane Edge)




**Figure 13.** Average gain of WCM.01 antenna with different ground plane size

## 4. Antenna Radiation Patterns


The antenna radiation patterns were measured in CTIA certified ETS Anechoic Chamber. The measurement setup as below,




In Free Space




On 10\*10cm ground plane (Center)




On 10\*10cm ground plane (Edge)




On 20\*20cm ground plane (Center)



On 20\*20cm ground plane (Edge)



On 30\*30cm ground plane (Center)




On 30\*30cm ground plane (Edge)


**Figure.14.** Testing Setup in ETS Anechoic Chamber

## 4.1 2D Radiation Pattern (In free space)


### XY Plane




### XZ Plane




### YZ Plane




## 4.2 3D Radiation Pattern (In free space)



2400MHz




2450MHz




2500MHz

### 4.3 2D Radiation Pattern (On the 10\*10cm ground plane Center)


#### XY Plane



#### XZ Plane




#### YZ Plane







#### 4.4 3D Radiation Pattern (On the 10\*10cm ground plane Center)



2400MHz




2450MHz




2500MHz

## 4.5 2D Radiation Pattern (On the 10\*10cm ground plane Edge)


### XY Plane




### XZ Plane




### YZ Plane




#### 4.6 3D Radiation Pattern (On the 10\*10cm ground plane Edge)



2400MHz




2450MHz




2500MHz

## 4.7 2D Radiation Pattern (On the 20\*20cm ground plane Center)


### XY Plane




### XZ Plane




### YZ Plane




#### 4.8 3D Radiation Pattern (On the 20\*20cm ground plane Center)



2400MHz




2450MHz




2500MHz

## 4.9 2D Radiation Pattern (On the 20\*20cm ground plane Edge)


### XY Plane




### XZ Plane




### YZ Plane




#### 4.10 3D Radiation Pattern (On the 20\*20cm ground plane Edge)



2400MHz




2450MHz




2500MHz

#### 4.11 2D Radiation Pattern (On the 30\*30cm ground plane Center)


##### XY Plane



##### XZ Plane




##### YZ Plane







#### 4.12 3D Radiation Pattern (On the 30\*30cm ground plane Center)



2400MHz




2450MHz




2500MHz

### 4.13 2D Radiation Pattern (On the 30\*30cm ground plane Edge)


#### XY Plane




#### XZ Plane




#### YZ Plane




#### 4.14 3D Radiation Pattern (On the 30\*30cm ground plane Edge)



2400MHz



2450MHz




2500MHz


## 5. Drawing(Unit: mm)




3D View



Top View



Side View




Bottom View


	Name	Material	Finish	QTY
1	External housing	ABS	Black	1
2	RP-SMA(M)	Brass	Gold	1

## 6. Packaging


1 pcs WCM.01.0151 per PE Bag  
PE Bag Dimensions - 80\*40mm  
Weight - .007g




100 PE Bags per Large PE Bag  
100 pcs WCM.01.0151 per Large PE Bag  
Large Polybag Dimensions - 240\*170mm  
Weight - 0.7kg



15 Large PE bags per carton  
1500 pcs WCM.01.0151 per carton  
Carton Dimensions - 360\*310\*160mm  
Weight - 11kg



Pallet Dimensions 1080mm\*930mm\*1430mm  
72 Cartons per Pallet  
12 Cartons per layer  
6 Layers



Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taoglas:

WCM.01.0151