



# QPA1111

## 8.5 – 10.5 GHz 30 Watt GaN Power Amplifier

### Product Overview


Qorvo's QPA1111 is a high power, packaged X-Band MMIC amplifier fabricated using Qorvo's production 0.15  $\mu\text{m}$  GaN-on-SiC process (QGaN15). The QPA1111 operates from 8.5 – 10.5 GHz, typically provides 30 W saturated output power with power-added efficiency of 45% and small signal gain of 38 dB.

To simplify system integration, the QPA1111 is fully matched to 50 ohms with DC grounded I/O ports for optimum ESD performance. Also, there are on-chip blocking capacitors following the DC grounds on the input and output ports.

The QPA1111 is ideal for supporting communications and radar applications in both commercial and military markets.

The QPA1111 is 100% DC and RF tested to ensure compliance to electrical specifications.

Lead-free and RoHS compliant




### Key Features

- Frequency Range: 8.5 – 10.5 GHz
- $P_{\text{OUT}}$  ( $P_{\text{IN}} = 18 \text{ dBm}$ ): 45 dBm
- PAE ( $P_{\text{IN}} = 18 \text{ dBm}$ ): 45 %
- Power Gain ( $P_{\text{IN}} = 18 \text{ dBm}$ ): 27 dBm
- Small Signal Gain: 38 dB
- Bias: Pulsed  $V_{\text{D}} = 22 \text{ V}$ ,  $I_{\text{DQ}} = 620 \text{ mA}$ ,  $P_{\text{W}} = 100 \mu\text{s}$ ,  $\text{DC} = 10\%$ ,  $V_{\text{G}} = -2.3 \text{ V typ. range}$
- Package Dimensions: 6.0 x 6.0 x 0.85 mm

*Performance is typical across frequency. Please reference electrical specification table and data plots for more details.*

### Functional Block Diagram



### Applications

- Satellite Communications
- Radar
- Datalinks

### Ordering Information

| Part No.   | Description                        |
|------------|------------------------------------|
| QPA1111    | 30 Watt GaN PA Package             |
| QPA1111TR7 | 250 pieces on a 7" reel (standard) |
| QPA1111EVB | Evaluation Board                   |



## Absolute Maximum Ratings

| Parameter                                                                                                                                         | Value / Range                                                                                          |
|---------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------|
| Drain Voltage ( $V_D$ )                                                                                                                           | 29.5 V                                                                                                 |
| Gate Voltage Range ( $V_G$ )                                                                                                                      | -4 V to 0 V                                                                                            |
| Drain Current ( $I_{D1}$ ), 1-sided feed                                                                                                          | 1 A                                                                                                    |
| Drain Current ( $I_{D2}$ ), 1-sided feed                                                                                                          | 2 A                                                                                                    |
| Drain Current ( $I_{D3}$ ), 1-sided feed                                                                                                          | 8 A                                                                                                    |
| Drain Current Total ( $I_D$ )                                                                                                                     | 11 A                                                                                                   |
| Gate Current ( $I_G$ )                                                                                                                            | See p. 20                                                                                              |
| Power Dissipation ( $P_{DISS}$ ), CW,<br>$T_{BASE} = 85\text{ }^{\circ}\text{C}$                                                                  | 65 W                                                                                                   |
| Input Power ( $P_{IN}$ ), 50 $\Omega$ ,<br>Pulsed $V_D = 22\text{ V}$ , $I_{DQ} = 620\text{ mA}$ ,<br>$PW = 100\text{ }\mu\text{s}$ , $DC = 10\%$ | $T_{BASE} = -40\text{ }^{\circ}\text{C}$ : 21 dBm<br>$T_{BASE} = +85\text{ }^{\circ}\text{C}$ : 27 dBm |
| Input Power ( $P_{IN}$ ), 3:1 VSWR,<br>Pulsed $V_D = 22\text{ V}$ , $I_{DQ} = 620\text{ mA}$ ,<br>$PW = 100\text{ }\mu\text{s}$ , $DC = 10\%$     | $T_{BASE} = -40\text{ }^{\circ}\text{C}$ : 18 dBm<br>$T_{BASE} = +85\text{ }^{\circ}\text{C}$ : 25 dBm |
| Mounting Temperature<br>(30 seconds)                                                                                                              | 260 $^{\circ}\text{C}$                                                                                 |
| Storage Temperature                                                                                                                               | -55 to +150 $^{\circ}\text{C}$                                                                         |

Operation of this device outside the parameter ranges given above may cause permanent damage. These are stress ratings only, and functional operation of the device at these conditions is not implied.

## Recommended Operating Conditions

| Parameter                                       | Min                                      | Typ.                          | Max | Units              |
|-------------------------------------------------|------------------------------------------|-------------------------------|-----|--------------------|
| Pulsed <sup>(1)</sup>                           | Width                                    | 100                           | 500 | $\mu\text{s}$      |
|                                                 | Duty Cycle                               | 10                            | 15  | %                  |
| Drain Voltage ( $V_D$ ) – Pulsed <sup>(1)</sup> |                                          | 22                            | 22  | V                  |
| Drain Current Total $I_D$ , Quiescent           |                                          | 620                           |     | mA                 |
| Drain Current Total, RF ( $I_{D\_Drive}$ )      |                                          | See plot page 4, 5, 9, 12, 15 |     | mA                 |
| Gate Voltage Typ. Range ( $V_G$ )               |                                          | -1.6 to -3                    |     | V                  |
| Gate Current, RF ( $I_{G\_Drive}$ )             |                                          | See plot page 4, 5            |     | mA                 |
| Input Power,<br>$P_{IN}$                        | $T_{BASE} = -40\text{ }^{\circ}\text{C}$ | 15                            |     | dBm                |
|                                                 | $T_{BASE} = +25\text{ }^{\circ}\text{C}$ | 18                            |     |                    |
|                                                 | $T_{BASE} = +85\text{ }^{\circ}\text{C}$ | 21                            |     |                    |
| Operating Temp. ( $T_{BASE}$ ) <sup>(2)</sup>   |                                          | -40                           | +85 | $^{\circ}\text{C}$ |

1. CW operating requires thermal consideration

2.  $T_{BASE}$  is back side of QPA1111 (see p. 24 Offset Temperature based on Qorvo's EVB Cu filled vias for reference).

Electrical specifications are measured at specified test conditions. Specifications are not guaranteed over all recommended operating conditions.

## Electrical Specifications







| Parameter                         | Conditions <sup>(1) (2)</sup>                                                                      | Min | Typ.  | Max  | Units                   |
|-----------------------------------|----------------------------------------------------------------------------------------------------|-----|-------|------|-------------------------|
| Operational Frequency Range       |                                                                                                    | 8.5 |       | 10.5 | GHz                     |
| Output Power, $P_{OUT}$           | $P_{IN} = 18\text{ dBm}$                                                                           |     | 45    |      | dBm                     |
| Power Added Efficiency, PAE       | $P_{IN} = 18\text{ dBm}$                                                                           |     | 45    |      | %                       |
| Power Gain                        | $P_{IN} = 18\text{ dBm}$                                                                           |     | 27    |      | dBm                     |
| Small Signal Gain, $S_{21}$       | $P_{IN} = -30\text{ dBm}$                                                                          |     | 38    |      | dB                      |
| Input Return Loss, IRL            |                                                                                                    |     | 15    |      |                         |
| Output Return Loss, ORL           |                                                                                                    |     | 10    |      |                         |
| $P_{OUT}$ Temperature Coefficient | $T_{DIFF} = 25\text{ }^{\circ}\text{C}$ to $85\text{ }^{\circ}\text{C}$ ; $P_{IN} = 18\text{ dBm}$ |     | -0.05 |      | dBm/ $^{\circ}\text{C}$ |
| $S_{21}$ Temperature Coefficient  | $T_{DIFF} = 25\text{ }^{\circ}\text{C}$ to $85\text{ }^{\circ}\text{C}$                            |     | -0.10 |      | dB/ $^{\circ}\text{C}$  |

Notes:

- Test conditions unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $V_G = -2.3\text{ V} \pm 0.7\text{ V}$  typical,  $T_{BASE} = +25^{\circ}\text{C}$ ,  $Z_0 = 50\text{ }\Omega$  (reference planes are at QPA1111).
- $T_{BASE}$  is back side of QPA1111 (see page 24 Offset Temperature based on Qorvo's EVB design for reference).







## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).









## Performance Plots – Large Signal ( Pulsed )

Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).








## Performance Plots – Large Signal (Pulsed)








## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22$  V,  $I_{DQ} = 620$  mA,  $PW = 100$   $\mu$ s,  $DC = 10\%$ ,  $P_{IN} = 17$  dBm,  $T_{BASE} = +25$  °C ( $T_{BASE}$  is backside of QPA1111).








## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22$  V,  $I_{DQ} = 620$  mA,  $PW = 100$   $\mu$ s,  $DC = 10\%$ ,  $P_{IN} = 17$  dBm,  $T_{BASE} = +25$  °C ( $T_{BASE}$  is backside of QPA1111).



## Performance Plots – Large Signal (Pulsed)






Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).










## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).








## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).








## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).








## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).








## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22$  V,  $I_{DQ} = 620$  mA,  $PW = 100$   $\mu$ s,  $DC = 10\%$ ,  $P_{IN} = 17$  dBm,  $T_{BASE} = +25$  °C ( $T_{BASE}$  is backside of QPA1111).








## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).









## Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = 17\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).



## Performance Plots – Harmonics (Pulsed)


Test conditions, unless otherwise noted: Pulsed  $V_D = 22$  V,  $I_{DQ} = 620$  mA,  $PW = 100$   $\mu$ s,  $DC = 10\%$ ,  $T_{BASE} = +25$  °C ( $T_{BASE}$  is backside of QPA1111).





## Performance Plots – Small Signal (Pulsed)


Test conditions, unless otherwise noted: Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $P_{IN} = -30\text{ dBm}$ ,  $T_{BASE} = +25\text{ }^\circ\text{C}$  ( $T_{BASE}$  is backside of QPA1111).




## Performance Plots – Small Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed  $V_D = 22$  V,  $I_{DQ} = 620$  mA,  $PW = 100$   $\mu$ s,  $DC = 10\%$ ,  $P_{IN} = -30$  dBm,  $T_{BASE} = +25$  °C ( $T_{BASE}$  is backside of QPA1111).


Gain vs. Freq. vs.  $I_{DQ}$



Input RL vs. Freq. vs.  $I_{DQ}$



Output RL vs. Freq. vs.  $I_{DQ}$





## Thermal and Reliability Information

| Parameter                                        | Test Conditions                                                                                                                                                                                                                                                     | Value | Units                       |
|--------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------------------------|
| Thermal Resistance, $\theta_{JC}$ <sup>(1)</sup> | Quiescent, no RF                                                                                                                                                                                                                                                    | 1.42  | $^{\circ}\text{C}/\text{W}$ |
| Channel Temperature, $T_{CH}$ <sup>(2)</sup>     | $T_{BASE} = 85^{\circ}\text{C}$ , $V_D = 22\text{ V}$ , $I_{DQ} = 620\text{ mA}$ ,<br>$P_{DISS} = 13.64\text{ W}$                                                                                                                                                   | 104   | $^{\circ}\text{C}$          |
| Thermal Resistance, $\theta_{JC}$ <sup>(1)</sup> | Pulsed, $P_{IN} = 18\text{ dBm}$ , $T_{BASE} = 85^{\circ}\text{C}$ , $V_D = 22\text{ V}$ , $I_{DQ} = 620\text{ mA}$ , $I_{D\_DRIVE} = 3250\text{ mA}$ , $PW = 100\text{ }\mu\text{s}$ , $DC = 10\%$ , $\text{Freq} = 9.75\text{ GHz}$ , $P_{OUT} = 45\text{ dBm}$ , | 1.50  | $^{\circ}\text{C}/\text{W}$ |
| Channel Temperature, $T_{CH}$ <sup>(2)</sup>     | $P_{DISS} = 40\text{ W}$ .                                                                                                                                                                                                                                          | 145   | $^{\circ}\text{C}$          |

Notes:

- Thermal resistance determined to  $T_{BASE}$  ( $T_{BASE}$  is backside of package QPA1111; see p. 24 offset temperature based on Qorvo's EVB design for reference).
- Channel temperature indicated is an IR scan equivalent temperature. Thermal resistance is calculated using this value. Additional information can be found in the Qorvo Applications Note "GaN Device TCHMAX Theta-JC and Reliability Estimates," located here <https://www.qorvo.com/products/d/da006480>


## Dissipated Power



Test conditions, unless otherwise noted.


Pulsed  $V_D = 22\text{ V}$ ,  $I_{DQ} = 620\text{ mA}$ ,  $PW = 100\text{ }\mu\text{s}$ ,  $DC = 10\%$ ,  $T_{BASE} = 85^{\circ}\text{C}$  ( $T_{BASE}$  is back side of QPA1111)

## Pulse Duration




$T_{BASE}$  is back side of QPA1111  
Channel Temperature is an IR scan equivalent

## Maximum Gate Current




Channel Temperature is an IR scan equivalent

## Applications Information



1. Drain and gate can be biased from both or either side;  $V_D$  both sides (or  $V_G$  both sides) can be tied together at the harness level.
2. The external bypassing components are required on both sides (even for non-biased side).

Applications Information (Cont.)



## Bill of Materials

| Reference Des.            | Qty | Value       | Description                                      | Part Number         |
|---------------------------|-----|-------------|--------------------------------------------------|---------------------|
| C1, C2                    | 2   | 10 $\mu$ F  | CAP, 10uF, $\pm$ 20%, 25V, X5R, 0805             |                     |
| C3, C4, C7, C8            | 4   | 1 $\mu$ F   | CAP, 1uF, $\pm$ 10%, 50V, X5R, 0603              |                     |
| C5, C6, C9, C10, C25, C26 | 6   | 0.1 $\mu$ F | CAP, 0.1uF, $\pm$ 10%, 50V, X7R, 0402            |                     |
| R1 – R8                   | 8   | 0 $\Omega$  | RES, 0 Ohm, JMPR, 0402                           |                     |
| PCB                       | 1   |             | PCB for QPA1111 (Cu-filled vias, see page 24)    | Qorvo, Custom       |
| H1, H2                    | 2   |             | DC Header, ST, 2x6, 0.100", SMD                  |                     |
| J1, J2                    | 2   |             | RF Connector, 2.92mm, F, Pin 0.005, Diel 0.029   | Southwest Microwave |
| H-Block                   | 1   |             | H-Block, Copper C110, 1.000 x 2.000 x 0.275 in   | Qorvo, Custom       |
| S1 – S4                   | 4   |             | Screw, Cap, Socket Head, 2-56X1/8"               |                     |
| Solder Preform            |     |             | Solder SAC305, Preform, 0.984 x 1.994 x 0.003 in |                     |
| Solder                    |     |             | Paste, solder, Syntech, Sn63/Pb37                |                     |

## Bias-Up Procedure


1. Set limit:  $I_D$  to 5 A,  $I_G$  to 40 mA each.
2. Set  $V_G = -3.5$  V
3. Set  $V_D = +22$  V. Ensure  $I_D \sim 0$  mA
4. Adjust  $V_G$  more positive until  $I_D = 620$  mA;  
 $V_G \approx -2.3 \pm 0.7$  V typical range
5. Wait 15 seconds; then repeat step 4
6. Apply RF signal

## Bias-Down Procedure

1. Turn off RF signal
2. Reduce  $V_G$  to -3.5 V. Ensure  $I_{DQ} \sim 0$  mA
3. Set  $V_D$  to 0 V
4. Turn off  $V_D$  supply
5. Wait 5 seconds
6. Turn off  $V_G$  supply





## Evaluation Board (EVB) Layout



$T_{BASE}$  is backside QPA1111  
Slide Thermocouple into Carrier's hole  
 $T_{BASE} \approx \text{Thermocouple} + 60^\circ\text{C Offset (40W } P_{DISS})$ ; see chart Offset Temperature vs.  $P_{DISS}$

Thru full loss = 1 dB  
(PCB, 2.9mm connectors)

Use screw (x2) to mount EVB on a cold plate (apply thermal compound between interfaces)




### LAYER STACK LEGEND

| Material                  | Layer            | Thickness | Dielectric Material | Type        |
|---------------------------|------------------|-----------|---------------------|-------------|
|                           | Top Overlay      |           |                     | Legend      |
|                           | Surface Material | 0.0004in  | Solder Resist       | Solder Mask |
| Copper                    | Top Layer        | 0.0014in  |                     | Signal      |
| Core                      |                  | 0.0080in  | RO4003C             | Dielectric  |
| Copper                    | Bottom Layer     | 0.0014in  |                     | Signal      |
| Total thickness: 0.0112in |                  |           |                     |             |


Cu-filled Vias  
193 vias,  
0.006" via dia.

Best recommended:  
Cu coined via





## Mechanical Information



Dimensions (unless otherwise specified): mm.

Tolerances (unless noted): .xx =  $\pm .25$ ; .xxx =  $\pm .100$ ; .xxxx =  $\pm .0254$ ; angles =  $0.5^\circ$

Package is mold encapsulated, non-hermetic, leads are Au plated.

## Pin Description


| Pin Number                          | Symbol            | Description                                                                                                                               |
|-------------------------------------|-------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| 1 – 4, 7 – 11, 20 – 24, 27 – 31, 41 | GND               | Ground; grounded on PCB                                                                                                                   |
| 5, 6                                | RF <sub>IN</sub>  | RF Input. Matched to 50 $\Omega$ , DC blocked, DC shorted to ground                                                                       |
| 12, 39                              | V <sub>G1</sub>   | Gate voltage for stage 1 <sup>(1)</sup>                                                                                                   |
| 13, 38                              | V <sub>G2</sub>   | Gate voltage for stage 2 <sup>(1)</sup>                                                                                                   |
| 14, 37                              | V <sub>G3</sub>   | Gate voltage for stage 3 <sup>(1)</sup>                                                                                                   |
| 15, 10, 36                          | V <sub>D1</sub>   | Drain voltage for stage 1 <sup>(1)</sup>                                                                                                  |
| 16, 17, 34, 35                      | V <sub>D2</sub>   | Drain voltage for stage 2 <sup>(1)</sup>                                                                                                  |
| 18, 19, 32, 33                      | V <sub>D3</sub>   | Drain voltage for stage 3 <sup>(1)</sup>                                                                                                  |
| 25, 26                              | RF <sub>OUT</sub> | RF Output. Matched to 50 $\Omega$ , DC blocked, DC shorted to ground                                                                      |
| 13                                  | GND               | Ground (backside paddle); grounded on PCB; Cu-filled vias should be employed to minimize inductance and thermal resistance <sup>(2)</sup> |

1. External bypassing required; refer to page 21 - 23 for recommendation.


2. Refer to page 24 for Cu-filled vias layout

## Tape & Reel Information

Standard T/R size = 250 pieces on a 7" reel.



| Feature             | Measure                                  | Symbol | Size (in) | Size (mm) |
|---------------------|------------------------------------------|--------|-----------|-----------|
| Cavity              | Length                                   | A0     | 0.248     | 6.3       |
|                     | Width                                    | B0     | 0.248     | 6.3       |
|                     | Depth                                    | K0     | 0.047     | 1.2       |
|                     | Pitch                                    | P1     | 0.472     | 12        |
| Centerline Distance | Cavity to Perforation - Length Direction | P2     | 0.079     | 2.0       |
|                     | Cavity to Perforation - Width Direction  | P3     | 0.295     | 7.50      |
| Cover Tape          | Width                                    | C      | 0.524     | 13.3      |
| Carrier Tape        | Width                                    | W      | 0.630     | 16.0      |




| Feature | Measure              | Symbol | Size (in) | Size (mm) |
|---------|----------------------|--------|-----------|-----------|
| Flange  | Diameter             | A      | 12.992    | 330       |
|         | Thickness            | W2     | 0.882     | 22.4      |
|         | Space Between Flange | W1     | .646      | 16.4      |
| Hub     | Outer Diameter       | N      | 4.016     | 102.0     |
|         | Arbor Hole Diameter  | C      | 0.512     | 13.0      |
|         | Key Slit Width       | B      | 0.079     | 2.0       |
|         | Key Slit Diameter    | D      | .795      | 20.2      |

## Solderability

- Compatible with the latest version of J-STD-020, Lead-free solder, 260 °C
- Do not expose the package lid to temperatures > 280 °C
- Contact plating: Ni-Au
- Solder rework not recommended.

## Recommended Soldering Temperature Profile



## Handling Precautions

| Parameter                        | Rating | Standard              |
|----------------------------------|--------|-----------------------|
| ESD – Human Body Model (HBM)     | 1A     | ANSI/ESD/JEDEC JS-001 |
| ESD – Charged Device Model (CDM) | C3     | ANSI/ESD/JEDEC JS-002 |
| MSL – Moisture Sensitivity Level | 3      | IPC/JEDEC J-STD-020   |



Caution!

ESD-Sensitive Device

## RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Antimony Free
- TBBP-A (C<sub>15</sub>H<sub>12</sub>Br<sub>4</sub>O<sub>2</sub>) Free
- PFOS Free
- SVHC Free
- Halogen Free

## Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

**Web:** [www.qorvo.com](http://www.qorvo.com)

**Tel:** 1-844-890-8163

**Email:** [customer.support@qorvo.com](mailto:customer.support@qorvo.com)

## Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

© 2024 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qorvo:](#)

[QPA1111TR7](#) [QPA1111](#)