



TGA2830-SM

2.7 to 3.5 GHz, 18 W GaN Power Amplifier

Product Overview


Qorvo's TGA2830-SM is a packaged MMIC power amplifier which operates from 2.7 to 3.5 GHz. The TGA2830-SM is designed using Qorvo's TQGaN25 0.25- μ m GaN on SiC process.

The TGA2830-SM typically provides more than 42.5 dBm of saturated output power, 54% power-added efficiency, and 30.5 dB small signal gain. It can operate under both pulse and CW conditions.

The TGA2830-SM is available in a low-cost, surface mount 24 lead 5 x 5 Overmold QFN. It is ideally suited to support both commercial and defense related radar applications.

Both RF ports have integrated DC blocking capacitors and are fully matched to 50 ohms.

Lead-free and RoHS compliant




QFN 5x5 mm 24L

Product Features

- Frequency Range: 2.7-3.5 GHz
- P_{SAT} : > 42.5 dBm (P_{IN} = 18 dBm)
- PAE: > 54 % (P_{IN} = 18 dBm)
- Small Signal Gain: > 30.5 dB
- Return Loss: > 11 dB
- Bias: V_D = 20-32 V, I_{DQ} = 225 mA
- Pulsed V_D : PW = 100 μ s, DC = 10 %
- Package Dimensions: 5.0 x 5.0 x 1.45 mm

Functional Block Diagram



Applications

- Commercial and Military Radar

Ordering Information

Part	Description
TGA2830-SM	2.7-3.5 GHz, 18 W GaN Power Amplifier
TGA2830-SM_EVB	TGA2830-SM Evaluation Board

Absolute Maximum Ratings

Parameter	Value/Range
Drain Voltage (V_D)	40 V
Gate Voltage Range (V_G)	-8 to 0 V
Drain Current (I_{D1})	225 mA
Drain Current (I_{D2})	1250 mA
Gate Current (I_G)	See Graph (page 3)
Power Dissipation (P_{DISS}), 85 °C	35 W
Input Power (P_{IN}), CW, 50 Ω , 85 °C	30 dBm
Input Power (P_{IN}), CW, V_{SWR} 10:1, $V_D = 28$ V, 85 °C	23 dBm
Mounting Temperature (30 Seconds)	260 °C
Storage Temperature	-55 to 150 °C

Operation of this device outside the parameter ranges given above may cause permanent damage. These are stress ratings only, and functional operation of the device at these conditions is not implied.

Recommended Operating Conditions

Parameter	Value/Range
Drain Voltage (V_D)	20–32 V
Drain Current (I_{DQ})	175–275 mA
Drain Current Under RF Drive (I_{D_DRIVE})	See plots p. 8
Gate Voltage Range (V_G)	-2.9 to -2.0 V
Gate Current Under RF Drive (I_{G_DRIVE})	See plots p. 8
Operating Temperature Range	-40 to +85 °C

Electrical specifications are measured at specified test conditions. Specifications are not guaranteed over all recommended operating conditions.






Electrical Specifications

Test conditions unless otherwise noted: 25 °C, $V_D = 28$ V, $I_{DQ} = 225$ mA, Pulsed V_D : PW = 100 μ s, DC = 10 %

Parameter	Min	Typical	Max	Units
Operational Frequency Range	2.7		3.5	GHz
Small Signal Gain		>30.5		dB
Input Return Loss		>15		dB
Output Return Loss		>11		dB
Output Power at Saturation ($P_{IN} = 18$ dBm)		>42.5		dBm
Power-Added Efficiency ($P_{IN} = 18$ dBm)		>54		%
Gate Leakage ($V_D = 10$ V, $V_G = -3.7$ V)	-7.83		-0.0001	mA
Gain Temperature Coefficient		-0.05		dB/°C
Power Temperature Coefficient		-0.004		dBm/°C





Typical Performance (Small Signal)

Condition: CW









Typical Performance: Small Signal

Condition: CW









Typical Performance: Large Signal

Condition: Pulsed V_D , Pulse Width = 100 μ s, Duty Cycle = 10%









Typical Performance: Large Signal

Condition: Pulsed V_D , Pulse Width = 100 us, Duty Cycle = 10%









Typical Performance: Large Signal

Condition: Pulsed V_D , Pulse Width = 100 us, Duty Cycle = 10%









Typical Performance: Large Signal

Condition: Pulsed V_D , Pulse Width = 100 us, Duty Cycle = 10%









Typical Performance: Large Signal and Linearity

Condition: CW







Typical Performance: Large Signal & Linearity

Condition: CW



Typical Performance: Large Signal & Linearity

Condition: CW





Thermal and Reliability Information

Parameter	Test Conditions	Value	Units
Thermal Resistance (θ_{JC}) ⁽¹⁾	$T_{BASE} = 85^\circ\text{C}$, $V_D = 28\text{ V}$, $I_{DQ} = 225\text{ mA}$ (Quiescent DC, CW), $P_{DISS} = 6.3\text{ W}$	2.129	$^\circ\text{C/W}$
Channel Temperature (T_{CH}) ⁽²⁾		98.4	$^\circ\text{C}$
Thermal Resistance (θ_{JC}) ⁽¹⁾	$T_{BASE} = 85^\circ\text{C}$, $V_D = 28\text{ V}$, $I_{D_Drive} = 1185\text{ mA}$ ($PW = 100\text{ }\mu\text{s}$, $DC = 10\%$), $\text{Freq.} = 3.1\text{ GHz}$: $P_{IN} = 18\text{ dBm}$, $P_{OUT} = 42.5\text{ dBm}$, $P_{DISS} = 15\text{ W}$	1.825	$^\circ\text{C/W}$
Channel Temperature (T_{CH}) (Under RF drive) ⁽²⁾		112.4	$^\circ\text{C}$


Notes:

1. Thermal resistance measured to back of package.
2. IR Scan equivalent temperatures. Refer to the following document: [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)

Power Dissipation and Max. Gate Current



Application Information



Notes:

1. Remove 1 uF capacitors if pulsing on drain
2. V_D : Tied V_{D1} & V_{D2} together

Bias-up Procedure

Set I_D limit to 1.4 A, I_G limit to 8 mA

Apply -5 V to V_G

Apply +28 V to V_D ; ensure I_{DQ} is approx. 0 mA

Adjust V_G until $I_{DQ} = 225$ mA

Turn on RF supply

Bias-down Procedure

Turn off RF supply


Reduce V_G to -5 V; ensure I_{DQ} is approx. 0 mA

Set V_D to 0 V

Turn off V_D supply

Turn off V_G supply


Pin Layout



Pin Description

Pin No.	Symbol	Description
1, 2, 4–15, 17–20, 24	NC	No internal connection; can be grounded on PCB or left open
3	RF IN	Input; matched to 50 Ω ; DC blocked
16	RF OUT	Output; matched to 50 Ω ; DC blocked
21	DRAIN 2	Drain voltage; bias network is required; see recommended Application Information on page 13
22	DRAIN 1	Drain voltage; bias network is required; see recommended Application Information on page 13
23	GATE	Gate voltage; bias network is required; see recommended Application Information on page 13
25	GND	Ground Paddle. Multiple vias should be employed to minimize inductance and thermal resistance.


Evaluation Board



Bill of Materials

Reference Des.	Value	Description	Manuf.	Part Number
C1–C3	1 μ F	Cap, 1206, 50 V, 5%, X7R	Various	
C4–C6	1000 pF	Cap, 0402, 100 V, 10%, X7R	Various	
R1–R6	10 Ω	Res, 0402, 5%	Various	

Mechanical Drawing



Units: millimeter (mm)

Tolerances: unless specified

x.xx = ± 0.01

x.xxx = ± 0.005

Materials:

Package Leads are Gold Plated.

Part is Mold Encapsulated.

Marking:


2830: Part number

YY: Part Assembly year

WW: Part Assembly week

MXXX: Batch ID

Recommended Soldering Temperature Profile



Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	1B	JEDEC JS-001
ESD – Charge Device Body Model (CDM)	C3	JESD22-C101
MSL – Moisture Sensitivity Level	MSL-3	IPC/JEDEC J-STD-020



Caution!
ESD-Sensitive Device

Solderability

Compatible with the latest version of J-STD-020, Lead-free solder, 260 °C

RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- PFOS Free
- SVHC Free

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations, and information about Qorvo:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2019 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qorvo:](#)

[TGA2830-SM](#) [TGA2830-SMTR7](#)