



Interference Suppression Film Capacitors MKP Radial Potted Type



FEATURES

- 7.5 mm to 27.5 mm lead pitch
- Supplied loose in box, taped on reel
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912


**RoHS
COMPLIANT**

APPLICATIONS

For standard across the line X2 applications


See also application note: www.vishay.com/doc?28153

QUICK REFERENCE DATA	
Capacitance range (E12 series)	0.001 μ F to 3.3 μ F (preferred values acc. to E6)
Capacitance tolerance	$\pm 20\%$; $\pm 10\%$, $\pm 5\%$
Climatic testing class according to IEC 60068-1	55/110/56/B
Rated AC voltage	310 V _{AC} ; 50 Hz to 60 Hz
Permissible DC voltage	800 V _{DC} at 85 °C, 630 V _{DC} at 110 °C
Maximum application temperature	C $\leq$ 470 nF: 110 °C (125 °C for less than 1000 h), C > 470 nF: 110 °C
Reference standards	IEC 60384-14 ed-4 (2013) and EN 60384-14 IEC 60065 requires pass. flamm. class B UL 60384-14; CSA-E384-14, CQC
Dielectric	Polypropylene film
Electrodes	Metallized film
Construction	Mono construction
Encapsulation	Plastic case, epoxy resin sealed, flame retardant UL-class 94 V-0
Leads	Tinned wire
Marking	C-value; tolerance; rated voltage; sub-class; manufacturer's type designation; code for dielectric material, manufacturer location; manufacturer's logo; year and week; safety approvals

Note

- For more detailed data and test requirements, contact: rfi@vishay.com

DIMENSIONS



COMPOSITION OF CATALOG NUMBER

TYPE AND PITCHES		CAPACITANCE (numerically)		MULTIPLIER (nF)	
338 2	7.5 mm				
X2	10.0 mm			0.1	2
	15.0 mm			1	3
	22.5 mm			10	4
	27.5 mm			100	5

BFC2	338	2X	XX	X
2222(*)	338	2X	XX	X

(*) Old ordering code

Example:
104 = 10 x 10 = 100 nF

TYPE	PACKAGING	STANDARD DIMENSIONS	C-TOL.	PREFERRED TYPES
MKP338 2 X2	Loose in box	Lead length 3.5 mm + 1 mm/- 0.5 mm; pitch ≤ 10.0 mm	± 20 %	BFC2 338 20
		Lead length 3.5 mm ± 0.3 mm; pitch ≥ 15.0 mm		BFC2 338 20
		Lead length 5.0 mm ± 1 mm		BFC2 338 22
		Lead length 25.0 mm ± 2 mm		BFC2 338 24
	Taped ammo ⁽¹⁾	Pitch ≤ 15.0 mm; H = 18.5 mm; P ₀ = 12.7 mm	± 20 % ± 10 % ± 5 %	See tables for details
	Taped reel ⁽¹⁾	Pitch 22.5 mm; H = 18.5 mm; P ₀ = 12.7 mm		
TYPE	PACKAGING	ALTERNATIVE PITCH SIZES AND TOLERANCES	C-TOL.	PREFERRED TYPES
MKP338 2 X2	Loose in box	Packaging like 20 % and alternative pitch sizes	± 5 % ± 10 % ± 20 %	See tables for details

Notes

- ⁽¹⁾ Taped on reel and taped on ammo pitch = 27.5 mm is not available
- For detailed tape specifications refer to packaging information: www.vishay.com/doc?28139

SPECIFIC REFERENCE DATA		
DESCRIPTION	VALUE	
Rated AC voltage (U _{RAC})	310 V	
Permissible DC voltage (U _{RDC})	630 V	
Tangent of loss angle:	at 1 kHz	at 10 kHz
C ≤ 470 nF	≤ 10 x 10 ⁻⁴	≤ 20 x 10 ⁻⁴
470 nF < C ≤ 1 μF	≤ 20 x 10 ⁻⁴	≤ 70 x 10 ⁻⁴
C > 1 μF	≤ 30 x 10 ⁻⁴	-
Rated voltage pulse slope (dU/dt) _R at 435 V _{DC}		
Pitch = 7.5 mm	600 V/μs	
Pitch = 10 mm	600 V/μs	
Pitch = 15 mm and 7.5 mm (bent back)	400 V/μs	
Pitch = 22.5 mm	150 V/μs	
Pitch = 27.5 mm	100 V/μs	
R between leads, for C ≤ 0.33 μF at 100 V; 1 min	> 15 000 MΩ	
RC between leads, for C > 0.33 μF at 100 V; 1 min	> 5000 s	
R between leads and case; 100 V; 1 min	> 30 000 MΩ	
Withstanding (DC) voltage (cut off current 10 mA) ⁽¹⁾ ; rise time ≤ 1000 V/s:		
C ≤ 1 μF	2200 V; 1 min	
C > 1 μF	1800 V; 1 min	
Withstanding (AC) voltage between leads and case	2120 V; 1 min	
Max. application temperature for 0.001 μF ≤ C ≤ 0.47 μF	110 °C (125 °C for less than 1000 h)	
Max. application temperature for C > 0.47 μF	110 °C	

Note

- ⁽¹⁾ See "Voltage Proof Test for Metalized Film Capacitors": www.vishay.com/doc?28169



ELECTRICAL DATA AND ORDERING CODE - PITCH 7.5 mm											
U _{RAC} (V)	CAP. (μF)	DIMENSIONS w x h x l (mm)	MASS (g) ⁽²⁾	CATALOG NUMBER BFC2 338 AND PACKAGING							
				LOOSE IN BOX					AMMOPACK ⁽¹⁾		
				SHORT LEADS			LONG LEADS		H = 18.5 mm P ₀ = 12.7 mm		
				l _t = 3.5 mm + 1 mm/- 0.5 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ		SPQ	
310	PITCH = 7.5 mm ± 0.4 mm; d _t = 0.50 mm ± 0.05 mm; C-TOL. = ± 20 %										
	0.0010	4.0 x 9.0 x 10.0	0.4	20102	22102	1500	24102	1000	26102	1250	
	0.0012			20122	22122		24122		26122		
	0.0015			20152	22152		24152		26152		
	0.0018			20182	22182		24182		26182		
	0.0022			20222	22222		24222		26222		
	0.0027			20272	22272		24272		26272		
	0.0033			20332	22332		24332		26332		
	0.0039			20392	22392		24392		26392		
	0.0047			20472	22472		24472		26472		
	0.0056			20562	22562		24562		26562		
	0.0068			20682	22682		24682		26682		
	0.0082			20822	22822		24822		26822		
	0.010			20103	22103		24103		26103		
	0.012			20123	22123		24123		26123		
	0.015			20153	22153		24153		26153		
	0.018			20183	22183		24183		26183		
	0.022			20223	22223		24223		26223		
	0.027	5.0 x 10.5 x 10.0	0.6	20273	22273	1000	24273	1250	26273	1000	
	0.033			20333	22333		24333		26333		
	0.039	5.0 x 10.5 x 10.0	0.6	20393	22393	750	24393	1000	26393	750	
	0.047			20473	22473		24473		26473		
	PITCH = 7.5 mm ± 0.4 mm; d _t = 0.50 mm ± 0.05 mm; C-TOL. = ± 10 %										
	0.0010	4.0 x 9.0 x 10.0	0.4	28101	28301	1500	28501	1000	28701	1250	
	0.0012			28102	28302		28502		28702		
	0.0015			28103	28303		28503		28703		
	0.0018			28104	28304		28504		28704		
	0.0022			28105	28305		28505		28705		
	0.0027			28106	28306		28506		28706		
	0.0033			28107	28307		28507		28707		
	0.0039			28108	28308		28508		28708		
	0.0047			28109	28309		28509		28709		
	0.0056			28111	28311		28511		28711		
0.0068	28112			28312	28512		28712				
0.0082	28113			28313	28513		28713				
0.010	28114			28314	28514		28714				
0.012	28115			28315	28515		28715				
0.015	28116			28316	28516		28716				
0.018	28117			28317	28517		28717				
0.022	28118			28318	28518		28718				
0.027	5.0 x 10.5 x 10.0	0.6	28119	28319	1000	28519	1250	28719	1000		
0.033			28121	28321		28521		28721			
0.039			28122	28332		28522		28722			
0.047	6.0 x 11.5 x 10.0	0.8	28123	28323	750	28523	1000	28723	750		



ELECTRICAL DATA AND ORDERING CODE - PITCH 7.5 mm										
U _{RAC} (V)	CAP. (μF)	DIMENSIONS w x h x l (mm)	MASS (g) ⁽²⁾	CATALOG NUMBER BFC2 338 AND PACKAGING						
				LOOSE IN BOX					AMMOPACK ⁽¹⁾	
				SHORT LEADS			LONG LEADS		H = 18.5 mm P ₀ = 12.7 mm	
				l _t = 3.5 mm + 1 mm/- 0.5 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ		SPQ
310	PITCH = 7.5 mm ± 0.4 mm; d _t = 0.50 mm ± 0.05 mm; C-TOL. = ± 5 %									
	0.0010	4.0 x 9.0 x 10.0	0.4	28201	28401	1500	28601	1000	28801	1250
	0.0012			28202	28402		28602		28802	
	0.0015			28203	28403		28603		28803	
	0.0018			28204	28404		28604		28804	
	0.0022			28205	28405		28605		28805	
	0.0027			28206	28406		28606		28806	
	0.0033			28207	28407		28607		28807	
	0.0039			28208	28408		28608		28808	
	0.0047			28209	28409		28609		28809	
	0.0056			28211	28411		28611		28811	
	0.0068			28212	28412		28612		28812	
	0.0082			28213	28413		28613		28813	
	0.010			28214	28414		28614		28814	
	0.012			28215	28415		28615		28815	
	0.015			28216	28416		28616		28816	
	0.018			28217	28417		28617		28817	
	0.022			28218	28418		28618		28818	
	0.027			28219	28419	1000	28619	1250	28819	1000
	0.033	5.0 x 10.5 x 10.0	0.6	28221	28421	1000	28621	1250	28821	1000
	0.039			28222	28422	750	28622	1000	28822	750
0.047	6.0 x 11.5 x 10.0	0.8	28223	28423	750	28623	1000	28823	750	

Notes

- SPQ = Standard Packing Quantity

(1) H = In-tape height, P₀ = Sprocket hole distance; for detailed specifications refer to packaging information: www.vishay.com/doc?28139

(2) Weight for short lead product only

ELECTRICAL DATA AND ORDERING CODE - PITCH 10 mm										
U _{RAC} (V)	CAP. (μF)	DIMENSIONS w x h x l (mm)	MASS (g) ⁽²⁾	CATALOG NUMBER BFC2 338 AND PACKAGING						
				LOOSE IN BOX					AMMOPACK ⁽¹⁾	
				SHORT LEADS			LONG LEADS		H = 18.5 mm P ₀ = 12.7 mm	
				I _t = 3.5 mm + 1 mm/- 0.5 mm	I _t = 5.0 mm ± 1.0 mm	SPQ	I _t = 25.0 mm ± 2.0 mm	SPQ		SPQ
310	PITCH = 10.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm; C-TOL. = ± 20 %									
	0.0010	4.0 x 10.0 x 12.5	0.6	21102	23102	1000	25102	1250	Not available	
	0.0012			21122	23122		25122			
	0.0015			21152	23152		25152			
	0.0018			21182	23182		25182			
	0.0022			21222	23222		25222			
	0.0027			21272	23272		25272	1000		
	0.0033			21332	23332		25332			
	0.0039			21392	23392		25392			
	0.0047			21472	23472		25472			
	0.0056			21562	23562		25562			



ELECTRICAL DATA AND ORDERING CODE - PITCH 10 mm												
U _{RAC} (V)	CAP. (μF)	DIMENSIONS w x h x l (mm)	MASS (g) ⁽²⁾	CATALOG NUMBER BFC2 338 AND PACKAGING								
				LOOSE IN BOX					AMMOPACK ⁽¹⁾			
				SHORT LEADS			LONG LEADS		H = 18.5 mm P ₀ = 12.7 mm			
				l _t = 3.5 mm + 1 mm/- 0.5 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ		SPQ		
310	PITCH = 10.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm; C-TOL. = ± 20 %											
	0.0068	4.0 x 10.0 x 12.5	0.6	21682	23682	1000	25682	1000	Not available			
	0.0082			21822	23822		25822					
	0.010			21103	23103		25103					
	0.012			21123	23123		25123					
	0.015			21153	23153		25153					
	0.018			21183	23183		25183					
	0.022			21223	23223		25223					
	0.027			21273	23273		25273					
	0.033			21333	23333		25333					
	0.039			21393	23393		25393					
	0.047			21473	23473		25473					
	0.056	5.0 x 11.0 x 12.5	0.82	20563	22563	750	24563	750	27563	500		
	0.068			20683	22683		24683		27683			
	0.082	6.0 x 12.0 x 12.5	1.1	20823	22823	750	24823	750	27823	500		
	0.10			20104	22104		24104		27104			
	PITCH = 10.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm; C-TOL. = ± 10 %											
	0.0010	4.0 x 10.0 x 12.5	0.6	29194	29217	1000	29241	1250	Not available 500			
	0.0012			29195	29218		29242					
	0.0015			29196	29219		29243					
	0.0018			29197	29221		29244					
	0.0022			29198	29222		29245					
	0.0027			29199	29223		29246					
	0.0033			29201	29224		29247	1000				
	0.0039			29202	29225		29248					
	0.0047			29203	29226		29249					
	0.0056			29204	29227		29251					
	0.0068			29205	29228		29252					
	0.0082			29206	29229		29253					
	0.010			29207	29231		29254					
	0.012			29208	29232		29255					
	0.015			29209	29233		29256					
	0.018			29211	29234		29257					
	0.022			29212	29235		29258					
	0.027			29213	29236		29259					
	0.033			29214	29237		29261					
	0.039			29215	29238		29262					
	0.047			29216	29239		29263					
	0.056	5.0 x 11.0 x 12.5	0.82	28124	28324	750	28524	750	28924			
	0.068			28125	28325		28525		28925			
	0.082	6.0 x 12.0 x 12.5	1.1	28126	28326	750	28526	750	28926			
	PITCH = 10.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm; C-TOL. = ± 5 %											
	0.056	5.0 x 11.0 x 12.5	0.82	28224	28424	750	28624	750	28944	500		
	0.068	6.0 x 12.0 x 12.5	1.1	28225	28425	750	28625	750	28945	500		
	0.082			28226	28426		28626		28946			

Notes

- SPQ = Standard Packing Quantity

⁽¹⁾ H = In-tape height, P₀ = Sprocket hole distance; for detailed specifications refer to packaging information: www.vishay.com/doc?28139

⁽²⁾ Weight for short lead product only



ELECTRICAL DATA AND ORDERING CODE - PITCH 15 mm											
U _{RAC} (V)	CAP. (μF)	DIMENSIONS w x h x l (mm)	MASS (g) ⁽²⁾	CATALOG NUMBER BFC2 338 AND PACKAGING							
				LOOSE IN BOX					AMMOPACK ⁽¹⁾		
				SHORT LEADS			LONG LEADS		H = 18.5 mm P ₀ = 12.7 mm		
				l _t = 3.5 mm ± 0.3 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ		SPQ	
310	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm; C-TOL. = ± 20 %										
	0.010	5.0 x 11.0 x 17.5	1.0	29076	29096	1000	29116	1000	29141	1100	
	0.012			29077	29097		29117		29143		
	0.015			29078	29098		29118		29145		
	0.018			29079	29099		29119		29147		
	0.022			29081	29101		29121		29149		
	0.027			29082	29102		29122		29152		
	0.033			29083	29103		29123		29154		
	0.039			29084	29104		29124		29156		
	0.047			29085	29105		29125		29158		
	0.056			21563	23563		25563		29161		
	0.068			21683	23683		25683		29163		
	0.082			21823	23823		25823		29165		
	0.10			21104	23104		25104		29166		
	0.12			20124	22124		24124		27124	900	
	0.15	6.0 x 12.0 x 17.5	1.4	20154	22154	750	24154	500	27154	800	
	0.18			20184	22184		24184		27184		
	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 20 %										
	0.22	7.0 x 13.5 x 17.5	1.8	20224	22224	750	24224	500	27224	650	
	0.27	8.5 x 15.0 x 17.5	2.4	20274	22274	750	24274	500	27274	650	
	0.33			20334	22334	500	24334	450	27334	600	
	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm; C-TOL. = ± 10 %										
	0.010	5.0 x 11.0 x 17.5	1.0	29066	29086	1000	29106	1000	29139	1100	
	0.012			29067	29087		29107		29142		
	0.015			29068	29088		29108		29144		
	0.018			29069	29089		29109		29146		
	0.022			29071	29091		29111		29148		
	0.027			29072	29092		29112		29151		
	0.033			29073	29093		29113		29153		
	0.039			29074	29094		29114		29155		
	0.047			29075	29095		29115		29157		
	0.056			29126	29131		29135		29159		
	0.068			29127	29132		29136		29162		
	0.082			29128	29133		29137		29164		
	0.10			28127	28327		1000		28527	1000	28927
	0.12	6.0 x 12.0 x 17.5	1.4	28128	28328	750	28528	500	28928	800	
	0.15			28129	28329		28529		28929		
	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 10 %										
	0.18	7.0 x 13.5 x 17.5	1.8	28131	28331	750	28531	500	28931	650	
	0.22	8.5 x 15.0 x 17.5	2.4	28132	28332	500	28532	450	28932	600	
	0.27			28133	28333		28533		28933		
	0.33			29129	29134		29138		29167		
	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm; C-TOL. = ± 5 %										
	0.10	5.0 x 11.0 x 17.5	1.0	28227	28427	1000	28627	1000	28947	900	
	0.12	6.0 x 12.0 x 17.5	1.4	28228	28428	750	28628	500	28948	800	
	0.15			28229	28429		28629		28949		
	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 5 %										
	0.18	7.0 x 13.5 x 17.5	1.8	28231	28431	750	28631	500	28951	650	
	0.22	8.5 x 15.0 x 17.5	2.4	28232	28432	750	28632	500	28952	650	
	0.27			28233	28433	500	28633	450	28953	600	

Notes

- SPQ = Standard Packing Quantity

⁽¹⁾ H = In-tape height, P₀ = Sprocket hole distance; for detailed specifications refer to packaging information: www.vishay.com/doc?28139

⁽²⁾ Weight for short lead product only



ELECTRICAL DATA AND ORDERING CODE - PITCH 22.5 mm										
U _{RAC} (V)	CAP. (μF)	DIMENSIONS w x h x l (mm)	MASS (g) ⁽²⁾	CATALOG NUMBER BFC2 338 AND PACKAGING						
				LOOSE IN BOX					REEL (500 mm) ⁽¹⁾	
				SHORT LEADS			LONG LEADS		H = 18.5 mm P ₀ = 12.7 mm	
				l _t = 3.5 mm ± 0.3 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ		SPQ
310	PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 20 %									
	0.12	6.0 x 15.5 x 26.0	2.4	21124	23124	300	25124	250	29264	600
	0.15			21154	23154		25154		29265	
	0.18			21184	23184	200	25184	250	29266	500
	0.22			21224	23224		25224		29267	
	0.27			21274	23274		25274		29268	
	0.33			21334	23334		25334		29269	
	0.39	7.0 x 16.5 x 26.0	2.9	20394	22394	200	24394	250	27394	450
	0.47			20474	22474		24474		27474	
	0.56	8.5 x 18.0 x 26.0	3.8	20564	22564	200	24564	200	27564	350
	0.68			20684	22684		24684		27684	
	0.82	10.0 x 19.5 x 26.0	6.8	20824	22824	150	24824	200	27824	300
	1.0			20105	22105		24105		27105	
	PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 10 %									
	0.12	6.0 x 15.5 x 26.0	2.4	29169	29175	300	29181	250	29271	600
	0.15			29171	29176		29182		29272	
	0.18			29172	29177	200	29183	250	29273	500
	0.22			29173	29178		29184		29274	
	0.27			29174	29179		29185		29275	
	0.33			28134	28334		28534		28934	450
	0.39	7.0 x 16.5 x 26.0	2.9	28135	28335	200	28535	250	28935	450
	0.47			28136	28336		28536		28936	
	0.56	8.5 x 18.0 x 26.0	3.8	28137	28337		28537	200	28937	350
	0.68	10.0 x 19.5 x 26.0	6.8	28138	28338	150	28538		28938	
	0.82			28139	28339		28539	28939		
	PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 5 %									
	0.33	7.0 x 16.5 x 26.0	2.9	28234	28434	200	28634	250	28954	450
	0.39			28235	28435		28635		28955	
	0.47	8.5 x 18.0 x 26.0	3.8	28236	28436	200	28636	200	28956	350
	0.56			28237	28437		28637		28957	
	0.68	10.0 x 19.5 x 26.0	6.8	28238	28438	150	28638	200	28958	300
	0.82	12.0 x 22.0 x 26.0	7.8	28239	28439	150	28639	200	28959	300

Notes

- SPQ = Standard Packing Quantity

⁽¹⁾ H = In-tape height, P₀ = Sprocket hole distance; for detailed specifications refer to packaging information: www.vishay.com/doc?28139

⁽²⁾ Weight for short lead product only



ELECTRICAL DATA AND ORDERING CODE - PITCH 27.5 mm													
U _{RAC} (V)	CAP. (μF)	DIMENSIONS w x h x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 338 AND PACKAGING									
				LOOSE IN BOX									
				SHORT LEADS			LONG LEADS						
				l _t = 3.5 mm ± 0.3 mm	l _t = 5.0 mm ± 1.0 mm	SPQ	l _t = 25.0 mm ± 2.0 mm	SPQ					
310	PITCH = 27.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 20 %												
	0.39 0.47 0.56 0.68 0.82	9.0 x 19.0 x 31.5	5.5	21394 21474	23394 23474	100	25394 25474	150					
	21564 21684 21824			23564 23684 23824	25564 25684 25824		125						
	1.0 1.2			11.0 x 21.0 x 31.0	7.4			21105 20125	23105 22125	25105 24125			
	1.5 1.8							13.0 x 23.0 x 31.0	9.2	20155 20185	22155 22185	24155 24185	100
	2.2									15.0 x 25.0 x 31.5	12.3	20225 22225	
	2.7 3.3	18.0 x 28.0 x 31.5	16.1	20275 20335	22275 22335		50	24275 24335	75				
	PITCH = 27.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 10 %												
	1.0 1.2	11.0 x 21.0 x 31.0	7.4	28141 28142	28341 28342		100	28541 28542	125				
	1.5			13.0 x 23.0 x 31.0	9.2			28143		28343	28543		
	1.8	15.0 x 25.0 x 31.5	12.3	28144	28344			28544	100				
	2.2			28145	28345	50	28545	75					
	2.7			18.0 x 28.0 x 31.5	16.1		28146		28346	28546			
	PITCH = 27.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm; C-TOL. = ± 5 %												
	1.0	11.0 x 21.0 x 31.0	7.4	28241	28441	100	28641	125					
	1.2	13.0 x 23.0 x 31.0	9.2	28242	28442	100	28642	125					
	1.5			28243	28443		28643						
	1.8	15.0 x 25.0 x 31.5	12.3	28244	28444	100	28644	100					
	2.2	18.0 x 28.0 x 31.5	16.1	28245	28445	50	28645	75					
	2.7			28246	28446		28646						

Notes

- SPQ = Standard Packing Quantity
- ⁽¹⁾ Weight for short lead product only

APPROVALS				
SAFETY APPROVALS X2	VOLTAGE	VALUE	FILE NUMBERS	LINKS
EN 60384-14 (ENEC) (= IEC 60384-14 ed-4 (2013))	310 V _{AC}	1 nF to 3.3 µF	ENEC16/FI/19/10001	www.vishay.com/doc?28179
UL 60384-14	310 V _{AC}	1 nF to 3.3 µF	E354331	www.vishay.com/doc?28184
CSA-E384-14	310 V _{AC}	1 nF to 3.3 µF	E354331	
CQC	310 V _{AC}	1 nF to 3.3 µF	CQC07001018685 (F)	www.vishay.com/doc?28227
			CQC07001021279 (L)	www.vishay.com/doc?28228
CB-test certificate	310 V _{AC}	1 nF to 3.3 µF	FI-39827	www.vishay.com/doc?28175
The ENEC-approval together with the CB-certificate replace all national marks of the following countries (they have already signed the ENEC-agreement): Austria; Belgium; Czech. Republic; Denmark; Finland; France; Germany; Greece; Hungary; Ireland; Italy; Luxembourg; Netherlands; Norway; Portugal; Slovenian; Spain; Sweden; Switzerland; and United Kingdom.				
  				

MOUNTING

Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoleers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to packaging information: www.vishay.com/doc?28139

Specific Method of Mounting to Withstand Vibration and Shock

In order to withstand vibration and shock tests, it must be ensured that the stand-off pips are in good contact with the printed-circuit board:


- For pitches ≤ 15 mm capacitors shall be mechanically fixed by the leads
- For longer pitches the capacitors shall be mounted in the same way and the body clamped

Space Requirements on Printed Circuit Board

The maximum space for length ($l_{max.}$), width ($w_{max.}$) and height ($h_{max.}$) of film capacitors to take in account on the printed circuit board is shown in the drawings.

- For products with pitch ≤ 15 mm, $\Delta w = \Delta l = 0.3$ mm; $\Delta h = 0.1$ mm
- For products with 15 mm $<$ pitch ≤ 27.5 mm, $\Delta w = \Delta l = 0.5$ mm; $\Delta h = 0.1$ mm

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.



SOLDERING

For general soldering conditions and wave soldering profile, we refer to the application note:

“Soldering Guidelines for Film Capacitors”: www.vishay.com/doc?28171

Storage Temperature

T_{stg} = -25 °C to +35 °C with RH maximum 75 % without condensation


Ratings and Characteristics Reference Conditions

Unless otherwise specified, all electrical values apply to an ambient temperature of 23 °C $\pm$ 1 °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of 50 % $\pm$ 2 %.


For reference testing, a conditioning period shall be applied over 96 h $\pm$ 4 h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.




CHARACTERISTICS




Capacitance as a function of ambient temperature (typical curve)




Impedance as a function of frequency (typical curve)




Tangent of loss angle as a function of frequency (typical curve)




Resonant frequency as a function of capacitance (typical curve)



Max. RMS voltage as a function of frequency (typical curve)



Max. RMS current as a function of frequency (typical curve)



Insulation resistance as a function of ambient temperature

APPLICATION NOTES

- For X2 electromagnetic interference suppression in **standard across the line applications** (50 Hz / 60 Hz) with a maximum mains voltage of 310 V_{AC}
- For series impedance applications we refer to application note www.vishay.com/doc?28153
- For capacitors connected in parallel, normally the proof voltage and possibly the rated voltage must be reduced. For information depending of the capacitance value and the number of parallel connections contact: rfi@vishay.com
- These capacitors are not intended for continuous pulse applications. For these situations, capacitors of the AC and pulse programs must be used
- The maximum ambient temperature must not exceed 105 °C (125 °C for less than 1000 h) for C ≤ 470 nF and 110 °C for C > 470 nF
- Rated voltage pulse slope:
if the pulse voltage is lower than the rated voltage, the values of the specific reference data can be multiplied by 435 V_{DC} and divided by the applied voltage

INSPECTION REQUIREMENTS

General Notes

Sub-clause numbers of tests and performance requirements refer to the “Sectional Specification, IEC Publication IEC 60384-14 ed-4 (2013) and Specific Reference Data.”

GROUP C INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1		
4.1 Dimensions (detail)		As specified in chapters “General Data” of this specification
Initial measurements	Capacitance Tangent of loss angle: For C ≤ 1 µF at 10 kHz For C > 1 µF at 1 kHz	
4.3 Robustness of terminations	Tensile: Load 10 N; 10 s Bending: Load 5 N; 4 x 90°	No visible damage
4.4 Resistance to soldering heat	No pre-drying Method: 1A Solder bath: 280 °C ± 5 °C Duration: 10 s	




GROUP C INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1		
4.19 Component solvent resistance	Isopropylalcohol at room temperature Method: 2 Immersion time: 5 min ± 0.5 min Recovery time: Min. 1 h, max. 2 h	
4.4.2 Final measurements	Visual examination Capacitance Tangent of loss angle Insulation resistance	No visible damage Legible marking $ \Delta C/C \leq 5\%$ of the value measured initially Increase of $\tan \delta$: ≤ 0.008 for: $C \leq 1 \mu F$ or ≤ 0.005 for: $C > 1 \mu F$ Compared to values measured initially As specified in section "Insulation resistance" of this specification
SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1		
Initial measurements	Capacitance Tangent of loss angle: For $C \leq 1 \mu F$ at 10 kHz For $C > 1 \mu F$ at 1 kHz	
4.20 Solvent resistance of the marking	Isopropylalcohol at room temperature Method: 1 Rubbing material: Cotton wool Immersion time: 5 min ± 0.5 min	No visible damage Legible marking
4.6 Rapid change of temperature	$\theta A = -55^\circ C$ $\theta B = +110^\circ C$ 5 cycles Duration $t = 30$ min	
4.6.1 Inspection	Visual examination	No visible damage
4.7 Vibration (see note 3.1)	Mounting: See section "Mounting" of this specification Procedure B4 Frequency range: 10 Hz to 55 Hz. Amplitude: 0.75 mm or Acceleration $98 m/s^2$ (whichever is less severe) Total duration 6 h	
4.7.2 Final inspection	Visual examination	No visible damage
4.9 Shock (see note 3)	Mounting: See section "Mounting" for more information Pulse shape: Half sine Acceleration: $490 m/s^2$ Duration of pulse: 11 ms	
4.9.2 Final measurements	Visual examination Capacitance Tangent of loss angle Insulation resistance	No visible damage $ \Delta C/C \leq 5\%$ of the value measured initially Increase of $\tan \delta$: ≤ 0.008 for: $C \leq 1 \mu F$ or ≤ 0.005 for: $C > 1 \mu F$ Compared to values measured initially As specified in section "Insulation resistance" of this specification



GROUP C INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B		
4.11 Climatic sequence		
4.11.1 Initial measurements	Capacitance Measured in 4.4.2 and 4.9.2 Tangent of loss angle: Measured initially in C1A and C1B	
4.11.2 Dry heat	Temperature: 110 °C	
4.11.3 Damp heat cyclic Test Db First cycle	Duration: 16 h	
4.11.4 Cold	Temperature: - 55 °C	
4.11.5 Damp heat cyclic Test Db Remaining cycles	Duration: 2 h	
4.11.6 Final measurements	Visual examination Capacitance Tangent of loss angle Voltage proof 1350 V _{DC} ; 1 min between terminations Insulation resistance	No visible damage Legible marking $ \Delta C/C \leq 5\%$ of the value measured in 4.11.1. Increase of $\tan \delta$: ≤ 0.008 for: $C \leq 1\ \mu\text{F}$ or ≤ 0.005 for: $C > 1\ \mu\text{F}$ Compared to values measured in 4.11.1. No permanent breakdown or flash-over $\geq 50\%$ of values specified in section "Insulation resistance" of this specification
SUB GROUP C2		
4.12 Damp heat steady state	56 days; 40 °C; 90 % to 95 % RH no load	
4.12.1 Initial measurements	Capacitance Tangent of loss angle: at 1 kHz	
4.12.3 Final measurements	Visual examination Capacitance Tangent of loss angle Voltage proof 1350 V _{DC} ; 1 min between term. Insulation resistance	No visible damage Legible marking $ \Delta C/C \leq 5\%$ of the value measured in 4.12.1. Increase of $\tan \delta$: ≤ 0.008 for: $C \leq 1\ \mu\text{F}$ or ≤ 0.005 for: $C > 1\ \mu\text{F}$ Compared to values measured in 4.12.1. No permanent breakdown or flash-over $\geq 50\%$ of values specified in section "Insulation Resistance" of this specification



GROUP C INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C3		
4.13.1 Initial measurements	Capacitance Tangent of loss angle: For $C \leq 1 \mu\text{F}$ at 10 kHz For $C > 1 \mu\text{F}$ at 1 kHz	
4.13 Impulse voltage	3 successive impulses, full wave, peak voltage: X2: 2.5 kV for $C \leq 1 \mu\text{F}$ X2: 2.5 kV/ $\sqrt{C}$ for $C > 1 \mu\text{F}$ Max. 24 pulses	No selfhealing breakdowns or flashover
4.14 Endurance	Duration: 1000 h $1.25 \times U_{\text{RAC}}$ at 110 °C Once in every hour the voltage is increased to 1000 V _{RMS} for 0.1 s via resistor of $47 \Omega \pm 5 \%$	
4.14.7 Final measurements	Visual examination Capacitance Tangent of loss angle Voltage proof 1350 V _{DC} ; 1 min between terminations. 2120 V _{AC} ; 1 min between terminations and case Insulation resistance	No visible damage Legible marking $ \Delta C/C \leq 10 \%$ compared to values measured in 4.13.1. Increase of $\tan \delta$: ≤ 0.008 for: $C \leq 1 \mu\text{F}$ or ≤ 0.005 for: $C > 1 \mu\text{F}$ Compared to values measured in 4.13.1. No permanent breakdown or flash-over $\geq 50 \%$ of values specified in section "Insulation resistance" of this specification
SUB-GROUP C4		
4.15 Charge and discharge	10 000 cycles Charge to 435 V _{DC} Discharge resistance: $R = \frac{435 V_{\text{DC}}}{1.25 \times C (dU/dt)}$	
4.15.1 Initial measurements	Capacitance Tangent of loss angle: For $C \leq 1 \mu\text{F}$ at 10 kHz For $C > 1 \mu\text{F}$ at 1 kHz	
4.15.3 Final measurements	Capacitance Tangent of loss angle Insulation resistance	$ \Delta C/C \leq 10 \%$ compared to values measured in 4.15.1. Increase of $\tan \delta$: ≤ 0.008 for: $C \leq 1 \mu\text{F}$ or ≤ 0.005 for: $C > 1 \mu\text{F}$ Compared to values measured in 4.15.1. $\geq 50 \%$ of values specified in section "Insulation Resistance" of this specification

GROUP C INSPECTION REQUIREMENTS		
SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C5		
4.16 Radio frequency characteristic	Resonance frequency	≥ 0.9 times the value as specified in section "Resonant frequency" of this specification
SUB-GROUP C6		
4.17 Passive flammability Class B	Bore of gas jet: $\varnothing 0.5$ mm Fuel: Butane Test duration for actual volume V in mm³: $V \leq 250$: 10 s $250 < V \leq 500$: 20 s $500 < V \leq 1750$: 30 s $V > 1750$: 60 s One flame application 	After removing test flame from capacitor, the capacitor must not continue to burn for more than 10 s. No burning particle must drop from the sample.
SUB-GROUP C7		
4.18 Active flammability	20 cycles of 2.5 kV discharges on the test capacitor connected to U_{RAC}	The cheese cloth around the capacitors shall not burn with a flame. No electrical measurements are required.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

BFC233820335	BFC233820104	BFC233820155	BFC233822154	BFC233826223	BFC233822102	BFC233822104
BFC233824153	BFC233822103	BFC233826222	BFC233824155	BFC233824152	BFC233824154	BFC233820222
BFC233824474	BFC233824225	BFC233820102	BFC233820332	BFC233824223	BFC233824473	BFC233824334
BFC233824335	BFC233824332	BFC233822223	BFC233822334	BFC233820103	BFC233824222	BFC233820224
BFC233820223	BFC233826332	BFC233824224	BFC233822225	BFC233820153	BFC233822473	BFC233820152
BFC233822224	BFC233822222	BFC233822335	BFC233826682	BFC233822472	BFC233824682	BFC233820473
BFC233826153	BFC233824104	BFC233826152	BFC233824103	BFC233824102	BFC233822683	BFC233826102
BFC233826103	BFC233824105	BFC233822684	BFC233822332	BFC233822682	BFC233824333	BFC233824472
BFC233826473	BFC233822333	BFC233826472	BFC233824684	BFC233822153	BFC233822155	BFC233822152
BFC233820472	BFC233824683	BFC233820225	BFC233822474	BFC233820474	BFC233820682	BFC233820683
BFC233820105	BFC233820684	BFC233820154	BFC233820333	BFC233826333	BFC233820334	BFC233823222
BFC233821104	BFC233821103	BFC233827154	BFC233825223	BFC233825104	BFC233829076	BFC233821474
BFC233821102	BFC233821105	BFC233821152	BFC233821153	BFC233821154	BFC233821222	BFC233828629
BFC233829163	BFC233829166	BFC233829265	BFC233829267	BFC233829269	BFC233828343	BFC233829125
BFC233829141	BFC233829145					