


Solid Tantalum Chip Capacitors

MICROTAN® High Reliability, Low DC Leakage, Leadframeless Molded



PERFORMANCE CHARACTERISTICS

www.vishay.com/doc?40170

Operating Temperature: -55 °C to +125 °C
(above 85 °C, voltage derating is required)

Capacitance Range: 0.33 µF to 47 µF

Capacitance Tolerance: ± 10 % and ± 20 % standard

Voltage Range: 2 V_{DC} to 40 V_{DC}

FEATURES

- High reliability solid surface mount tantalum capacitors
- Low DC leakage for extended battery life
- Small sizes for space constrained applications
- L-shaped face-down terminations for superior board mounting
- The molding compound has been selected to meet the requirements of UL 94 V-0 and outgassing requirements of ASTM E-595
- Suitable for medical implantable applications with additional screening
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912




RoHS*
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details


ORDERING INFORMATION							
TM8 MODEL	R CASE CODE	106 CAPACITANCE	M CAPACITANCE TOLERANCE	016 DC VOLTAGE RATING AT +85 °C	E TERMINATION / PACKAGING	B RELIABILITY LEVEL	A SURGE CURRENT
	See Ratings and Case Codes table	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	K = ± 10 % M = ± 20 %	This is expressed in volts. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V).	Sn / Pb solder E = 7" (178 mm) reels L = 7" (178 mm) reels, ½ reel R = 7" (178 mm) 300 pcs. qty. 100 % tin C = 7" (178 mm) reels H = 7" (178 mm) reels, ½ reel U = 7" (178 mm) 300 pcs. qty. Gold A = 7" (178 mm) reels G = 7" (178 mm) reels, ½ reel P = 7" (178 mm) 300 pcs. qty.	B = 0.1 % weibull FRL S = hi-rel std. (40 h burn-in) Z = non- established reliability	A = 10 cycles at 25 °C B = 10 cycles at -55 °C / +85 °C Z = none

DIMENSIONS in inches [millimeters]


CASE CODE	L	W	H	P1	P2 (MIN.)	C	C1
K	0.045 ± 0.002 [1.14 ± 0.05]	0.026 ± 0.002 [0.66 ± 0.05]	0.024 max. [0.61 max.]	0.010 ± 0.004 [0.25 ± 0.1]	0.020 [0.51]	0.015 ± 0.004 [0.38 ± 0.1]	0.015 ± 0.004 [0.38 ± 0.1]
M	0.063 ± 0.006 [1.60 ± 0.15]	0.033 ± 0.006 [0.84 ± 0.15]	0.033 ± 0.006 [0.84 ± 0.15]	0.020 ± 0.004 [0.51 ± 0.1]	0.026 [0.65]	0.024 ± 0.004 [0.61 ± 0.1]	0.018 ± 0.004 [0.45 ± 0.1]
G	0.063 ± 0.006 [1.60 ± 0.15]	0.033 ± 0.006 [0.84 ± 0.15]	0.047 max. [1.2 max.]	0.020 ± 0.004 [0.51 ± 0.1]	0.026 [0.65]	0.024 ± 0.004 [0.61 ± 0.1]	0.018 ± 0.004 [0.45 ± 0.1]
W	0.081 ± 0.006 [2.06 ± 0.15]	0.053 ± 0.006 [1.35 ± 0.15]	0.047 max. [1.2 max.]	0.020 ± 0.004 [0.51 ± 0.1]	0.035 [0.9]	0.035 ± 0.004 [0.90 ± 0.1]	0.020 ± 0.004 [0.50 ± 0.1]
R	0.081 ± 0.006 [2.06 ± 0.15]	0.053 ± 0.006 [1.35 ± 0.15]	0.058 ± 0.004 [1.47 ± 0.10]	0.020 ± 0.004 [0.51 ± 0.1]	0.035 [0.9]	0.035 ± 0.004 [0.90 ± 0.1]	0.020 ± 0.004 [0.50 ± 0.1]
P	0.096 ± 0.006 [2.45 ± 0.15]	0.059 ± 0.006 [1.5 ± 0.15]	0.049 max. [1.25 max.]	0.020 ± 0.004 [0.51 ± 0.1]	0.051 [1.3]	0.035 ± 0.004 [0.90 ± 0.1]	0.018 ± 0.004 [0.45 ± 0.1]
A	0.126 ± 0.008 [3.2 ± 0.2]	0.063 ± 0.008 [1.6 ± 0.2]	0.071 max. [1.8 max.]	0.031 ± 0.004 [0.8 ± 0.1]	0.063 [1.60]	0.047 ± 0.004 [1.2 ± 0.1]	0.031 ± 0.004 [0.80 ± 0.10]
N	0.138 ± 0.004 [3.5 ± 0.1]	0.110 ± 0.004 [2.80 ± 0.1]	0.047 max. [1.2 max.]	0.0335 ± 0.004 [0.85 ± 0.1]	0.065 [1.65]	0.094 ± 0.004 [2.4 ± 0.10]	0.079 ± 0.004 [2.0 ± 0.10]
T	0.138 ± 0.004 [3.5 ± 0.1]	0.110 ± 0.004 [2.80 ± 0.10]	0.063 max. [1.57 max.]	0.0335 ± 0.004 [0.85 ± 0.1]	0.065 [1.65]	0.094 ± 0.004 [2.4 ± 0.10]	0.079 ± 0.004 [2.0 ± 0.10]

RATINGS AND CASE CODES

μF	2 V	4 V	6.3 V	10 V	16 V	20 V	25 V	40 V
0.33						K		
0.68						M		
1.0		K	K	M	M	M / W	R	P
2.2				M	M			
3.3			M	M / G	R	R		
4.7			M	M			P	
6.8				R	R			
7.5				W		N		
10	K	M	M	R	R / A	A		
15		M	M / R	R				
22				A				
33		P	P					
47		P	P / T	T				

MARKING


VOLTAGE CODE		CAPACITANCE CODE	
V	CODE	CAP, μF	CODE
2	e	0.68	\overline{w}
4	G	1.0	A
6.3	J	2.2	J
10	A	3.3	N
16	C	4.7	S
20	D	6.8	W
25	E	7.5	X
40	g	10	a
		15	e
		22	j
		47	s

STANDARD RATINGS

CAPACITANCE (μF)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μA)	MAX. DF AT +25 °C (%)	MAX. ESR AT +25 °C 100 kHz STD. (Ω)	AVAILABLE RELIABILITY LEVELS
2 V_{DC} AT +85 °C; 1.4 V_{DC} AT +125 °C						
10	K	TM8K106M002(2)(4)(6)	0.50	20	20.0	Z
4 V_{DC} AT +85 °C; 2.7 V_{DC} AT +125 °C						
1.0	K	TM8K105(1)004(2)(3)(6)	0.20	8	20.0	Z, S, B
10	M	TM8M106(1)004(2)(3)(5)	0.20	8	5.0	Z, S, B
15	M	TM8M156(1)004(2)(3)(5)	0.30	8	5.0	Z, S, B
33	P	TM8P336(1)004(2)(3)(5)	0.66	30	6.0	Z, S, B
47	P	TM8P476(1)004(2)(3)(5)	0.94	22	3.0	Z, S, B

Note

- Part number definitions:
 - Capacitance tolerance: K, M
 - Termination and packaging: E, L, R, C, H, U, A, G, P
 - Reliability level: Z, S, B
 - Reliability level: Z only
 - Surge current: Z, A, B
 - Surge current: Z only







STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C (%)	MAX. ESR AT +25 °C 100 kHz STD. (Ω)	AVAILABLE RELIABILITY LEVELS
6.3 V_{DC} AT +85 °C; 4 V_{DC} AT +125 °C						
1.0	K	TM8K105(1)6R3(2)(3)(6)	0.20	8	20.0	Z, S, B
3.3	M	TM8M335(1)6R3(2)(3)(5)	0.20	8	6.0	Z, S, B
4.7	M	TM8M475(1)6R3(2)(3)(5)	0.20	8	6.0	Z, S, B
10	M	TM8M106(1)6R3(2)(3)(5)	0.32	8	5.0	Z, S, B
15	M	TM8M156(1)6R3(2)(3)(5)	0.47	8	5.0	Z, S, B
15	R	TM8R156(1)6R3(2)(3)(5)	0.47	8	5.0	Z, S, B
33	P	TM8P336(1)6R3(2)(3)(5)	1.00	30	6.0	Z, S, B
47	P	TM8P476(1)6R3(2)(3)(5)	1.50	22	3.0	Z, S, B
47	T	TM8T476(1)6R3(2)(3)(5)	1.50	8	0.5	Z, S, B
10 V_{DC} AT +85 °C; 7 V_{DC} AT +125 °C						
1.0	M	TM8M105(1)010(2)(3)(5)	0.20	6	12.0	Z, S, B
2.2	M	TM8M225(1)010(2)(3)(5)	0.20	10	10.0	Z, S, B
3.3	M	TM8M335(1)010(2)(3)(5)	0.20	8	6.0	Z, S, B
4.7	M	TM8M475(1)010(2)(3)(5)	0.24	8	6.0	Z, S, B
3.3	G	TM8G335(1)010(2)(3)(5)	0.20	8	6.0	Z, S, B
7.5	W	TM8W755(1)010(2)(3)(5)	0.38	8	8.0	Z, S, B
6.8	R	TM8R685(1)010(2)(3)(5)	0.34	6	6.0	Z, S, B
10	R	TM8R106(1)010(2)(3)(5)	0.50	8	6.0	Z, S, B
15	R	TM8R156(1)010(2)(3)(5)	0.75	8	5.0	Z, S, B
22	A	TM8A226(1)010(2)(3)(5)	1.10	8	1.5	Z, S, B
47	T	TM8T476(1)010(2)(3)(5)	2.35	8	1.0	Z, S, B
16 V_{DC} AT +85 °C; 10 V_{DC} AT +125 °C						
1.0	M	TM8M105(1)016(2)(3)(5)	0.20	6	12.0	Z, S, B
2.2	M	TM8M225(1)016(2)(3)(5)	0.20	10	10.0	Z, S, B
3.3	R	TM8R335(1)016(2)(3)(5)	0.26	8	8.0	Z, S, B
6.8	R	TM8R685(1)016(2)(3)(5)	0.54	6	6.0	Z, S, B
10	R	TM8R106(1)016(2)(3)(5)	0.80	8	6.0	Z, S, B
10	A	TM8A106(1)016(2)(3)(5)	0.80	8	3.0	Z, S, B
20 V_{DC} AT +85 °C; 13 V_{DC} AT +125 °C						
0.33	K	TM8K334(1)020(2)(3)(6)	0.20	6	100.0	Z, S, B
0.68	M	TM8M684(1)020(2)(3)(5)	0.20	6	20.0	Z, S, B
1.0	M	TM8M105(1)020(2)(3)(5)	0.20	6	12.0	Z, S, B
1.0	W	TM8W105(1)020(2)(3)(5)	0.20	8	8.0	Z, S, B
3.3	R	TM8R335(1)020(2)(3)(5)	0.33	8	8.0	Z, S, B
7.5	N	TM8N755(1)020(2)(3)(5)	0.75	8	6.0	Z, S, B
10	A	TM8A106(1)020(2)(3)(5)	1.00	8	3.0	Z, S, B
25 V_{DC} AT +85 °C; 17 V_{DC} AT +125 °C						
1.0	R	TM8R105(1)025(2)(3)(5)	0.20	6	10.0	Z, S, B
4.7	P	TM8P475(1)025(2)(3)(5)	0.59	6	6.0	Z, S, B
40 V_{DC} AT +85 °C; 27 V_{DC} AT +125 °C						
1.0	P	TM8P105(1)040(2)(3)(5)	0.20	8	10.0	Z, S, B

Note

- Part number definitions:
 - Capacitance tolerance: K, M
 - Termination and packaging: E, L, R, C, H, U, A, G, P
 - Reliability level: Z, S, B
 - Reliability level: Z only
 - Surge current: Z, A, B
 - Surge current: Z only



TYPICAL CURVES AT +25 °C, IMPEDANCE AND ESR VS. FREQUENCY



STANDARD PACKAGING QUANTITY

CASE CODE	QUANTITY (PCS/REEL)		
	7" REEL	½ REEL	PARTIAL REEL
K	5000	2500	300
M	4000	2000	300
G	3000	1500	300
W	2500	1250	300
R	2500	1250	300
P	3000	1500	300
A	2000	1000	300
N	2500	1250	300
T	2500	1250	300



POWER DISSIPATION	
CASE CODE	MAXIMUM PERMISSIBLE POWER DISSIPATION AT +25 °C (W) IN FREE AIR
K	0.015
M	0.025
G	0.025
W	0.040
R	0.045
P	0.045
A	0.075
N	0.075
T	0.084

PRODUCT INFORMATION	
Micro Guide	www.vishay.com/doc?40115
Pad Dimensions	
Packaging Dimensions	
Moisture Sensitivity	www.vishay.com/doc?40135
Typical Performance Characteristics	www.vishay.com/doc?40170
Solid Tantalum Capacitors (With MnO ₂ Electrolyte) Voltage Derating	www.vishay.com/doc?40246
SELECTOR GUIDES	
Solid Tantalum Selector Guide	www.vishay.com/doc?49053
Solid Tantalum Chip Capacitors	www.vishay.com/doc?40091
FAQ	
Frequently Asked Questions	www.vishay.com/doc?40110



Guide for Leadframeless Molded Tantalum Capacitors

INTRODUCTION

Tantalum electrolytic capacitors are the preferred choice in applications where volumetric efficiency, stable electrical parameters, high reliability, and long service life are primary considerations. The stability and resistance to elevated temperatures of the tantalum / tantalum oxide / manganese dioxide system make solid tantalum capacitors an appropriate choice for today's surface mount assembly technology.

Vishay Sprague has been a pioneer and leader in this field, producing a large variety of tantalum capacitor types for consumer, industrial, automotive, military, and aerospace electronic applications.

Tantalum is not found in its pure state. Rather, it is commonly found in a number of oxide minerals, often in combination with Columbium ore. This combination is known as "tantalite" when its contents are more than one-half tantalum. Important sources of tantalite include Australia, Brazil, Canada, China, and several African countries. Synthetic tantalite concentrates produced from tin slags in Thailand, Malaysia, and Brazil are also a significant raw material for tantalum production.

Electronic applications, and particularly capacitors, consume the largest share of world tantalum production. Other important applications for tantalum include cutting tools (tantalum carbide), high temperature super alloys, chemical processing equipment, medical implants, and military ordnance.

Vishay Sprague is a major user of tantalum materials in the form of powder and wire for capacitor elements and rod and sheet for high temperature vacuum processing.

THE BASICS OF TANTALUM CAPACITORS

Most metals form crystalline oxides which are non-protecting, such as rust on iron or black oxide on copper. A few metals form dense, stable, tightly adhering, electrically insulating oxides. These are the so-called "valve" metals and include titanium, zirconium, niobium, tantalum, hafnium, and aluminum. Only a few of these permit the accurate control of oxide thickness by electrochemical means. Of these, the most valuable for the electronics industry are aluminum and tantalum.

Capacitors are basic to all kinds of electrical equipment, from radios and television sets to missile controls and automobile ignitions. Their function is to store an electrical charge for later use.

Capacitors consist of two conducting surfaces, usually metal plates, whose function is to conduct electricity. They are separated by an insulating material or dielectric. The dielectric used in all tantalum electrolytic capacitors is tantalum pentoxide.

Tantalum pentoxide compound possesses high-dielectric strength and a high-dielectric constant. As capacitors are being manufactured, a film of tantalum pentoxide is applied to their electrodes by means of an electrolytic process. The film is applied in various thicknesses and at various voltages and although transparent to begin with, it takes on different colors as light refracts through it. This coloring occurs on the tantalum electrodes of all types of tantalum capacitors.

Rating for rating, tantalum capacitors tend to have as much as three times better capacitance / volume efficiency than aluminum electrolytic capacitors. An approximation of the capacitance / volume efficiency of other types of capacitors may be inferred from the following table, which shows the dielectric constant ranges of the various materials used in each type. Note that tantalum pentoxide has a dielectric constant of 26, some three times greater than that of aluminum oxide. This, in addition to the fact that extremely thin films can be deposited during the electrolytic process mentioned earlier, makes the tantalum capacitor extremely efficient with respect to the number of microfarads available per unit volume. The capacitance of any capacitor is determined by the surface area of the two conducting plates, the distance between the plates, and the dielectric constant of the insulating material between the plates.

COMPARISON OF CAPACITOR DIELECTRIC CONSTANTS

DIELECTRIC	^e DIELECTRIC CONSTANT
Air or Vacuum	1.0
Paper	2.0 to 6.0
Plastic	2.1 to 6.0
Mineral Oil	2.2 to 2.3
Silicone Oil	2.7 to 2.8
Quartz	3.8 to 4.4
Glass	4.8 to 8.0
Porcelain	5.1 to 5.9
Mica	5.4 to 8.7
Aluminum Oxide	8.4
Tantalum Pentoxide	26
Ceramic	12 to 400K

In the tantalum electrolytic capacitor, the distance between the plates is very small since it is only the thickness of the tantalum pentoxide film. As the dielectric constant of the tantalum pentoxide is high, the capacitance of a tantalum capacitor is high if the area of the plates is large:

$$C = \frac{eA}{t}$$

where

C = capacitance

e = dielectric constant

A = surface area of the dielectric

t = thickness of the dielectric

Tantalum capacitors contain either liquid or solid electrolytes. In solid electrolyte capacitors, a dry material (manganese dioxide) forms the cathode plate. A tantalum lead is embedded in or welded to the pellet, which is in turn connected to a termination or lead wire. The drawings show the construction details of the surface mount types of tantalum capacitors shown in this catalog.

SOLID ELECTROLYTE TANTALUM CAPACITORS

Solid electrolyte capacitors contain manganese dioxide, which is formed on the tantalum pentoxide dielectric layer by impregnating the pellet with a solution of manganous nitrate. The pellet is then heated in an oven, and the manganous nitrate is converted to manganese dioxide.

The pellet is next coated with graphite, followed by a layer of metallic silver, which provides a conductive surface between the pellet and the leadframe.

Molded chip tantalum capacitor encases the element in plastic resins, such as epoxy materials. The molding compound has been selected to meet the requirements of UL 94 V-0 and outgassing requirements of ASTM E-595. After assembly, the capacitors are tested and inspected to assure long life and reliability. It offers excellent reliability and high stability for consumer and commercial electronics with the added feature of low cost.

Surface mount designs of "Solid Tantalum" capacitors use lead frames or lead frameless designs as shown in the accompanying drawings.

TANTALUM CAPACITORS FOR ALL DESIGN CONSIDERATIONS

Solid electrolyte designs are the least expensive for a given rating and are used in many applications where their very small size for a given unit of capacitance is of importance. They will typically withstand up to about 10 % of the rated DC working voltage in a reverse direction. Also important are their good low temperature performance characteristics and freedom from corrosive electrolytes.

Vishay Sprague patented the original solid electrolyte capacitors and was the first to market them in 1956. Vishay Sprague has the broadest line of tantalum capacitors and has continued its position of leadership in this field. Data sheets covering the various types and styles of Vishay Sprague capacitors for consumer and entertainment electronics, industry, and military applications are available where detailed performance characteristics must be specified.












Fig. 1 - Leadframeless Molded Capacitors, All Types

SOLID TANTALUM CAPACITORS - LEADFRAMELESS MOLDED				
SERIES	TL8	298D	298W	TR8
PRODUCT IMAGE				
TYPE	Solid tantalum leadframeless molded chip capacitors			
FEATURES	Small size including 0603 and 0402 foot print			
	Ultra low profile	Industrial grade	Industrial grade, extended range	Low ESR
TEMPERATURE RANGE	Operating Temperature: -55 °C to +125 °C (above 40 °C, voltage derating is required)	Operating Temperature: -55 °C to +125 °C (above 85 °C, voltage derating is required)	Operating Temperature: -55 °C to +125 °C (above 40 °C, voltage derating is required)	Operating Temperature: -55 °C to +125 °C (above 85 °C, voltage derating is required)
CAPACITANCE RANGE	0.68 μ F to 220 μ F	0.33 μ F to 220 μ F	2.2 μ F to 220 μ F	1 μ F to 220 μ F
VOLTAGE RANGE	4 V to 25 V	2.5 V to 50 V	4 V to 16 V	2.5 V to 25 V
CAPACITANCE TOLERANCE	$\pm 20 \%$, $\pm 10 \%$			
DISSIPATION FACTOR	6 % to 80 %	6 % to 80 %	30 % to 80 %	6 % to 80 %
CASE CODES	W9, A0, B0	K, M, R, P, Q, A, S, B	K, M, Q	M, R, P, Q, A, B
TERMINATION	100 % tin	100 % tin or gold plated		

SOLID TANTALUM CAPACITORS - LEADFRAMELESS MOLDED			
SERIES	TP8	TM8	DLA 11020
PRODUCT IMAGE			
TYPE	Solid tantalum leadframeless molded chip capacitors		
FEATURES	Small size including 0603 and 0402 foot print		
	High performance, automotive grade	High reliability	High reliability, DLA approved
TEMPERATURE RANGE	Operating Temperature: -55 °C to +125 °C (above 85 °C, voltage derating is required)		
CAPACITANCE RANGE	1 μ F to 100 μ F	0.68 μ F to 47 μ F	1 μ F to 47 μ F
VOLTAGE RANGE	6.3 V to 40 V	2 V to 40 V	6.3 V to 40 V
CAPACITANCE TOLERANCE	$\pm 20 \%$, $\pm 10 \%$		
DISSIPATION FACTOR	6 % to 30 %	6 % to 20 %	6 % to 8 %
CASE CODES	M, W, R, P, A, N, T, B	K, M, G, W, R, P, A, N, T	M, W, R, P, A, N, T
TERMINATION	100 % tin	Tin / lead solder plated, 100 % tin and gold plated	Tin / lead solder plated or gold plated

PLASTIC TAPE AND REEL PACKAGING in inches [millimeters]



Notes

- Metric dimensions will govern. Dimensions in inches are rounded and for reference only
- A₀, B₀, K₀, are determined by the maximum dimensions to the ends of the terminals extending from the component body and / or the body dimensions of the component. The clearance between the ends of the terminals or body of the component to the sides and depth of the cavity (A₀, B₀, K₀) must be within 0.002" (0.05 mm) minimum and 0.020" (0.50 mm) maximum. The clearance allowed must also prevent rotation of the component within the cavity of not more than 20°
- Tape with components shall pass around radius "R" without damage. The minimum trailer length may require additional length to provide "R" minimum for 12 mm embossed tape for reels with hub diameters approaching N minimum
- This dimension is the flat area from the edge of the sprocket hole to either outward deformation of the carrier tape between the embossed cavities or to the edge of the cavity whichever is less
- This dimension is the flat area from the edge of the carrier tape opposite the sprocket holes to either the outward deformation of the carrier tape between the embossed cavity or to the edge of the cavity whichever is less
- The embossed hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location shall be applied independent of each other
- B₁ dimension is a reference dimension tape feeder clearance only

CARRIER TAPE DIMENSIONS in inches [millimeters] FOR 298D, 298W, TR8, TP8, TL8

CASE CODE	TAPE SIZE	B ₁ (MAX.) (1)	D ₁ (MIN.)	F	K ₀ (MAX.)	P ₁	W
M (2)	8 mm	0.075 [1.91]	0.02 [0.5]	0.138 [3.5]	0.043 [1.10]	0.157 [4.0]	0.315 [8.0]
W	8 mm	0.112 [2.85]	0.039 [1.0]	0.138 [3.5]	0.053 [1.35]	0.157 [4.0]	0.315 [8.0]
R	8 mm	0.098 [2.46]	0.039 [1.0]	0.138 [3.5]	0.066 [1.71]	0.157 [4.0]	0.315 [8.0]
P	8 mm	0.108 [2.75]	0.02 [0.5]	0.138 [3.5]	0.054 [1.37]	0.157 [4.0]	0.315 [8.0]
A	8 mm	0.153 [3.90]	0.039 [1.0]	0.138 [3.5]	0.078 [2.00]	0.157 [4.0]	0.315 [8.0]
A0, Q	8 mm	-	0.02 [0.5]	0.138 [3.5]	0.049 [1.25]	0.157 [4.0]	0.315 [8.0]
B	8 mm	0.157 [4.0]	0.039 [1.0]	0.138 [3.5]	0.087 [2.22]	0.157 [4.0]	0.315 [8.0]
W9, S	8 mm	0.126 [3.20]	0.029 [0.75]	0.138 [3.5]	0.045 [1.15]	0.157 [4.0]	0.315 [8.0]
B0	12 mm	0.181 [4.61]	0.059 [1.5]	0.217 [5.5]	0.049 [1.25]	0.157 [4.0]	0.472 [12.0]


Notes

- (1) For reference only
- (2) Packaging of M case in plastic tape is available per request

CARRIER TAPE DIMENSIONS in inches [millimeters] **FOR TM8**

CASE CODE	TAPE SIZE	B ₁ (MAX.) ⁽¹⁾	D ₁ (MIN.)	F	K ₀ (MAX.)	P ₁	W
M	8 mm	0.075 [1.91]	0.02 [0.5]	0.138 [3.5]	0.043 [1.10]	0.157 [4.0]	0.315 [8.0]
G	8 mm	0.077 [1.96]	0.02 [0.5]	0.138 [3.5]	0.051 [1.30]	0.157 [4.0]	0.315 [8.0]
W	8 mm	0.112 [2.85]	0.039 [1.0]	0.138 [3.5]	0.053 [1.35]	0.157 [4.0]	0.315 [8.0]
R	8 mm	0.098 [2.46]	0.039 [1.0]	0.138 [3.5]	0.066 [1.71]	0.157 [4.0]	0.315 [8.0]
P	8 mm	0.108 [2.75]	0.02 [0.5]	0.138 [3.5]	0.054 [1.37]	0.157 [4.0]	0.315 [8.0]
A	8 mm	0.153 [3.90]	0.039 [1.0]	0.138 [3.5]	0.078 [2.00]	0.157 [4.0]	0.315 [8.0]
N	12 mm	0.154 [3.90]	0.059 [1.5]	0.216 [5.5]	0.051 [1.30]	0.157 [4.0]	0.472 [12.0]
T	12 mm	0.154 [3.90]	0.059 [1.5]	0.216 [5.5]	0.067 [1.70]	0.157 [4.0]	0.472 [12.0]

Notes
⁽¹⁾ For reference only


PAPER TAPE AND REEL PACKAGING in inches [millimeters]
FOR 298D, 298W, TR8, TP8, TL8, TM8 (K case only)


CASE SIZE	TAPE SIZE	A ₀	B ₀	D ₀	P ₀	P ₁	P ₂	E	F	W	T
K	8 mm	0.033 ± 0.002 [0.85 ± 0.05]	0.053 ± 0.002 [1.35 ± 0.05]	0.06 ± 0.004 [1.5 ± 0.1]	0.157 ± 0.004 [4.0 ± 0.1]	0.078 ± 0.004 [2.0 ± 0.1]	0.079 ± 0.002 [2.0 ± 0.05]	0.069 ± 0.004 [1.75 ± 0.1]	0.0138 ± 0.002 [3.5 ± 0.05]	0.315 ± 0.008 [8.0 ± 0.2]	0.03 ± 0.002 [0.75 ± 0.05]
M	8 mm	0.041 ± 0.002 [1.05 ± 0.05]	0.071 ± 0.002 [1.8 ± 0.05]	0.06 ± 0.004 [1.5 ± 0.1]	0.157 ± 0.004 [4.0 ± 0.1]	0.157 ± 0.004 [4.0 ± 0.1]	0.079 ± 0.002 [2.0 ± 0.05]	0.069 ± 0.004 [1.75 ± 0.1]	0.0138 ± 0.002 [3.5 ± 0.05]	0.315 ± 0.008 [8.0 ± 0.2]	0.037 ± 0.002 [0.95 ± 0.05]

Note
⁽¹⁾ A₀, B₀ are determined by the maximum dimensions to the ends of the terminals extending from the component body and / or the body dimensions of the component. The clearance between the ends of the terminals or body of the component to the sides and depth of the cavity (A₀, B₀) must be within 0.002" (0.05 mm) minimum and 0.020" (0.50 mm) maximum. The clearance allowed must also prevent rotation of the component within the cavity of not more than 20°


RECOMMENDED REFLOW PROFILES

Capacitors should withstand reflow profile as per J-STD-020 standard, three cycles.









PROFILE FEATURE	SnPb EUTECTIC ASSEMBLY	LEAD (Pb)-FREE ASSEMBLY
PREHEAT AND SOAK		
Temperature min. ($T_{Smin.}$)	100 °C	150 °C
Temperature max. ($T_{Smax.}$)	150 °C	200 °C
Time (t_S) from ($T_{Smin.}$ to $T_{Smax.}$)	60 s to 90 s	60 s to 150 s
RAMP UP		
Ramp-up rate (T_L to T_P)	3 °C/s maximum	
Liquidus temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60 s to 150 s	
Peak package body temperature (T_P) max.	235 °C	260 °C
Time (t_P) within 5 °C of the peak max. temperature	20 s	30 s
RAMP DOWN		
Ramp-down rate (T_P to T_L)	6 °C/s maximum	
Time from 25 °C to peak temperature	6 min maximum	8 min maximum

PAD DIMENSIONS in inches [millimeters]







CASE CODE	A (NOM.)	B (MIN.)	C (NOM.)	D (MIN.)
K	0.021 [0.53]	0.016 [0.41]	0.022 [0.55]	0.054 [1.37]
M, G	0.024 [0.61]	0.027 [0.70]	0.025 [0.64]	0.080 [2.03]
R, W9, S	0.035 [0.89]	0.029 [0.74]	0.041 [1.05]	0.099 [2.52]
W	0.035 [0.89]	0.029 [0.74]	0.037 [0.95]	0.095 [2.41]
P	0.035 [0.89]	0.029 [0.74]	0.054 [1.37]	0.112 [2.84]
A, Q, A0	0.047 [1.19]	0.042 [1.06]	0.065 [1.65]	0.148 [3.76]
B, B0	0.094 [2.39]	0.044 [1.11]	0.072 [1.82]	0.159 [4.03]
N, T	0.094 [2.39]	0.044 [1.11]	0.065 [1.65]	0.152 [3.86]
M2	0.315 [8.00]	0.098 [2.50]	0.197 [5.00]	0.394 [10.0]

TYPICAL CURVES AT +25 °C, IMPEDANCE AND ESR VS. FREQUENCY



TYPICAL CURVES AT +25 °C, IMPEDANCE AND ESR VS. FREQUENCY





GUIDE TO APPLICATION

1. **AC Ripple Current:** the maximum allowable ripple current shall be determined from the formula:

$$I_{RMS} = \sqrt{\frac{P}{R_{ESR}}}$$

where,

P = power dissipation in watts at +25 °C (see paragraph number 5 and the table Power Dissipation as given in the tables in the product datasheets)

R_{ESR} = the capacitor equivalent series resistance at the specified frequency

2. **AC Ripple Voltage:** the maximum allowable ripple voltage shall be determined from the formula:

$$V_{RMS} = Z \sqrt{\frac{P}{R_{ESR}}}$$

or, from the formula:

$$V_{RMS} = I_{RMS} \times Z$$

where,

P = power dissipation in watts at +25 °C (see paragraph number 5 and the table Power Dissipation as given in the tables in the product datasheets)

R_{ESR} = the capacitor equivalent series resistance at the specified frequency

Z = the capacitor impedance at the specified frequency

- 2.1 The sum of the peak AC voltage plus the applied DC voltage shall not exceed the DC voltage rating of the capacitor.
- 2.2 The sum of the negative peak AC voltage plus the applied DC voltage shall not allow a voltage reversal exceeding 10 % of the DC working voltage at +25 °C.
3. **Reverse Voltage:** these capacitors are capable of withstanding peak voltages in the reverse direction equal to 10 % of the DC rating at +25 °C, 5 % of the DC rating at +25 °C, 5 % of the DC rating at +85 °C, and 1 % of the DC rating at +125 °C.
4. **Temperature Derating:** if these capacitors are to be operated at temperatures above +25 °C, the permissible RMS ripple current shall be calculated using the derating factors as shown:

TEMPERATURE	DERATING FACTOR
+25 °C	1.0
+85 °C	0.9
+125 °C	0.4

5. **Power Dissipation:** power dissipation will be affected by the heat sinking capability of the mounting surface. Non-sinusoidal ripple current may produce heating effects which differ from those shown. It is important that the equivalent I_{RMS} value be established when calculating permissible operating levels. (Power Dissipation calculated using +25 °C temperature rise.)

6. **Printed Circuit Board Materials:** molded capacitors are compatible with commonly used printed circuit board materials (alumina substrates, FR4, FR5, G10, PTFE-fluorocarbon and porcelainized steel).

7. **Attachment:**

- 7.1 **Solder Paste:** the recommended thickness of the solder paste after application is 0.007" ± 0.001" [0.178 mm ± 0.025 mm]. Care should be exercised in selecting the solder paste. The metal purity should be as high as practical. The flux (in the paste) must be active enough to remove the oxides formed on the metallization prior to the exposure to soldering heat. In practice this can be aided by extending the solder preheat time at temperatures below the liquidous state of the solder.

- 7.2 **Soldering:** capacitors can be attached by conventional soldering techniques; vapor phase, convection reflow, infrared reflow, wave soldering and hot plate methods. The Soldering Profile charts show recommended time / temperature conditions for soldering. Preheating is recommended. The recommended maximum ramp rate is 3 °C per second. Attachment with a soldering iron is not recommended due to the difficulty of controlling temperature and time at temperature. The soldering iron must never come in contact with the capacitor. For details see www.vishay.com/doc?40214.

- 7.2.1 **Backward and Forward Compatibility:** capacitors with SnPb or 100 % tin termination finishes can be soldered using SnPb or lead (Pb)-free soldering processes.

8. **Cleaning (Flux Removal) After Soldering:** molded capacitors are compatible with all commonly used solvents such as TES, TMS, Prelete, Chloroethane, Terpene and aqueous cleaning media. However, CFC / ODS products are not used in the production of these devices and are not recommended. Solvents containing methylene chloride or other epoxy solvents should be avoided since these will attack the epoxy encapsulation material.

- 8.1 When using ultrasonic cleaning, the board may resonate if the output power is too high. This vibration can cause cracking or a decrease in the adherence of the termination. DO NOT EXCEED 9W/l at 40 kHz for 2 min.

9. **Recommended Mounting Pad Geometries:** proper mounting pad geometries are essential for successful solder connections. These dimensions are highly process sensitive and should be designed to minimize component rework due to unacceptable solder joints. The dimensional configurations shown are the recommended pad geometries for both wave and reflow soldering techniques. These dimensions are intended to be a starting point for circuit board designers and may be fine tuned if necessary based upon the peculiarities of the soldering process and / or circuit board design.



Solid Tantalum Chip Capacitors MICROTAN® High Reliability Leadframeless Molded Capacitors TM8 and DLA 11020


ELECTRICAL PERFORMANCE CHARACTERISTICS				
ITEM	PERFORMANCE CHARACTERISTICS			
Category temperature range	-55 °C to +85 °C (to +125 °C with voltage derating)			
Capacitance tolerance	± 20 %, ± 10 %, tested via bridge method, at 25 °C, 120 Hz			
Dissipation factor	Limits per Standard Ratings table. Tested via bridge method, at 25 °C, 120 Hz.			
ESR	Limits per Standard Ratings table. Tested via bridge method, at 25 °C, 100 kHz.			
Leakage current	After application of rated voltage applied to capacitors for 5 min using a steady source of power with 1 k Ω resistor in series with the capacitor under test, leakage current at 25 °C is not more than described in Standard Ratings table. <i>Note that the leakage current varies with temperature and applied voltage. See graph below for the appropriate adjustment factor.</i>			
Reverse voltage	Capacitors are capable of withstanding peak voltages in the reverse direction equal to: 10 % of the DC rating at +25 °C 5 % of the DC rating at +85 °C 1 % of the DC rating at +125 °C Vishay does not recommend intentional or repetitive application of reverse voltage.			
Ripple current and Temperature derating	For maximum permissible ripple current (I_{RMS}) or/and voltage (V_{RMS}) please refer to product datasheet and Guide to Application. If capacitors are to be used at temperatures above +25 °C, the permissible RMS ripple current or voltage shall be calculated using the derating factors: 1.0 at +25 °C 0.9 at +85 °C 0.4 at +125 °C			
Maximum operating and surge voltages vs. temperature	+85 °C		+125 °C	
	RATED VOLTAGE	SURGE VOLTAGE	CATEGORY VOLTAGE	SURGE VOLTAGE
	V	V	V	V
	2.0	2.6	1.3	1.7
	4.0	5.2	2.7	3.4
	6.3	8.0	4.0	5.0
	10	13	7.0	8.0
	16	20	10	12
	20	26	13	16
	25	32	17	20
	35	46	23	28
	40	52	26	31

Notes


- All information presented in this document reflects typical performance characteristics
- For information about recommended voltage derating see: www.vishay.com/doc?40246
- For temperatures above +85 °C the voltage derating ratio should be applied with respect to category voltage, namely: up to +85 °C: category voltage = rated voltage; at +125 °C: category voltage = 2/3 of rated voltage, between these temperatures it decreases linearly - see graph "Category to Rated Voltage Ratio vs. Operating Temperature"



CATEGORY VOLTAGE VS. TEMPERATURE



TYPICAL LEAKAGE CURRENT TEMPERATURE FACTOR



Notes

- At +25 °C, the leakage current shall not exceed the value listed in the Standard Ratings table.
- At +85 °C, the leakage current shall not exceed 10 times the value listed in the Standard Ratings table.
- At +125 °C, the leakage current shall not exceed 12 times the value listed in the Standard Ratings table



ENVIRONMENTAL AND MECHANICAL PERFORMANCE CHARACTERISTICS		
ITEM	CONDITION	POST TEST PERFORMANCE
Vibration	In accordance with MIL-PRF-55365	In accordance with MIL-PRF-55365 (as for style CWR15)
Thermal shock		
Resistance to solder heat		
Moisture resistance		
Stability at low and high temperatures		
Surge voltage		
Life test		
Solderability		
Resistance to solvents		
Terminal strength/ Shear stress test	Method: AEC-Q200-006, conditions: Pressure load of 5 N for 10 s \pm 1 s	There shall be no mechanical or visual damage and the components shall meet the original electrical requirements.
Flammability	Encapsulation materials meet UL 94 V-0 with an oxygen index of 32 %.	

Note

- All measurements to be performed after 24 h conditioning at room temperature.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

TM8P475K025EBZ008	TM8A226K010UBA	TM8M105K020UBA	TM8M225K016UBA	TM8M335K010UBA
TM8N755K020UBA	TM8M475K010UBA	TM8M105K010UBA	TM8R106K010UBA	TM8T476K010UBA
TM8M105K016UBA	TM8R106K016UBA	TM8R335K020UBA	TM8W105K020UBA	TM8P475K025UBA
TM8R105K025UBA	TM8P105K040UBA	TM8M106K6R3UBA	TM8M156K6R3UBA	TM8W755K010UBA
TM8K106M002CZZ	TM8K106M002EZZ	TM8K106M002HZZ	TM8K106M002LZZ	TM8K106M002RZZ
TM8K106M002UZZ	TM8M105K010CBA	TM8M105K010CBB	TM8M105K010CBZ	TM8M105K010CSA
TM8M105K010CSB	TM8M105K010CSZ	TM8M105K010CZA	TM8M105K010CZB	TM8M105K010CZZ
TM8M105K010EBA	TM8M105K010EBB	TM8M105K010EBZ	TM8M105K010ESA	TM8M105K010ESB
TM8M105K010ESZ	TM8M105K010EZA	TM8M105K010EZB	TM8M105K010EZZ	TM8M105K010HBA
TM8M105K010HBB	TM8M105K010HBZ	TM8M105K010HSA	TM8M105K010HSB	TM8M105K010HSZ
TM8M105K010HZA	TM8M105K010HZB	TM8M105K010HZZ	TM8M105K010LBA	TM8M105K010LBB
TM8M105K010LBZ	TM8M105K010LSA	TM8M105K010LSB	TM8M105K010LSZ	TM8M105K010LZA
TM8M105K010LZB	TM8M105K010LZZ	TM8M105K010RBA	TM8M105K010RBB	TM8M105K010RBZ
TM8M105K010RSA	TM8M105K010RSB	TM8M105K010RSZ	TM8M105K010RZA	TM8M105K010RZB
TM8M105K010RZZ	TM8M105K010UBB	TM8M105K010UBZ	TM8M105K010USA	TM8M105K010USB
TM8M105K010USZ	TM8M105K010UZA	TM8M105K010UZB	TM8M105K010UZZ	TM8M105K016CBA
TM8M105K016CBB	TM8M105K016CBZ	TM8M105K016CSA	TM8M105K016CSB	TM8M105K016CSZ
TM8M105K016CZA	TM8M105K016CZB	TM8M105K016CZZ	TM8M105K016EBA	TM8M105K016EBB
TM8M105K016EBZ	TM8M105K016ESA	TM8M105K016ESB	TM8M105K016ESZ	TM8M105K016EZA
TM8M105K016EZB	TM8M105K016EZZ	TM8M105K016HBA	TM8M105K016HBB	TM8M105K016HBZ