

DATA SHEET

INDUCTOR

Power Inductors

BPSP Series

RoHS compliant & Halogen Free



BPSP Series




Features

- RoHS, Halogen Free and REACH Compliance
- Unshielded power inductor
- Various package size and wide inductance range


Applications

- Graphic cards
- DC/DC converters


Product Identification



Shape and Dimensions



Recommended Pattern



Dimensions in mm				
TYPE	A	B	C	D
BPSP00030315	3.3±0.3	3.0±0.3	1.5±0.3	1.0
BPSP00030321	3.3±0.3	3.0±0.3	2.1±0.3	1.0
BPSP00050432	4.5±0.3	4.0±0.3	3.2±0.3	1.2
BPSP00060525	5.8±0.3	5.2±0.3	2.5±0.3	2.0
BPSP00060530	5.8±0.3	5.2±0.3	3±0.3	2.0
BPSP00060545	5.8±0.3	5.2±0.3	4.5±0.4	1.3
BPSP00080735	7.8±0.3	7.0±0.3	3.5±0.3	2.1
BPSP00080750	7.8±0.3	7.0±0.3	5.0±0.3	2.1
BPSP00109040	10.0±0.3	9.0±0.3	4.0±0.5	2.1
BPSP00100954	10.0±0.4	9.0±0.4	5.4±0.4	2.1
BPSP00100965	10.0±0.4	9.0±0.4	6.5±0.4	2.1

Dimensions in mm		
Dim	A	B
BPSP00030315	4.5	1.0
BPSP00030321	4.5	1.0
BPSP00050432	5.5	1.2
BPSP00060525	6.8	2.0
BPSP00060530	6.8	2.0
BPSP00060545	6.8	1.3
BPSP00080735	8.8	2.1
BPSP00080750	8.8	2.1
BPSP00109040	11	2.1
BPSP00100954	11	2.1
BPSP00100965	11	2.1

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)	Isat (A)	Marking
BPSD000303152R2□00	2.2	20	1 MHz, 1 V	0.10 $\pm$ 30%	0.79	CC
BPSD000303153R3□00	3.3	20	1 MHz, 1 V	0.11 $\pm$ 30%	0.73	DD
BPSD000303154R7□00	4.7	20	1 MHz, 1 V	0.15 $\pm$ 30%	0.65	EH
BPSD000303155R6□00	5.6	20	1 MHz, 1 V	0.15 $\pm$ 30%	0.6	FG
BPSD000303156R8□00	6.8	20	1 MHz, 1 V	0.20 $\pm$ 30%	0.77	GI
BPSD00030315100□00	10	20	1 MHz, 1 V	0.30 $\pm$ 30%	0.45	KA
BPSD00030315150□00	15	20	1 MHz, 1 V	0.58 $\pm$ 30%	0.3	MA
BPSD00030315220□00	22	10, 20	1 MHz, 1 V	0.71 $\pm$ 30%	0.25	LA
BPSD00030315330□00	33	20	1 MHz, 1 V	1.10 $\pm$ 30%	0.2	NA
BPSD00030315390□00	39	20	1 MHz, 1 V	1.30 $\pm$ 30%	0.17	PA
BPSD00030315470□00	47	20	1 MHz, 1 V	1.30 $\pm$ 30%	0.17	OA
BPSD00030315680□00	68	20	1 MHz, 1 V	2.20 $\pm$ 30%	0.13	VA
BPSD00030315101□00	100	20	1 MHz, 1 V	3.50 $\pm$ 30%	0.1	KB
BPSD00030315221□00	220	20	1 MHz, 1 V	10.92Max	0.07	LB

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10%, M= $\pm$ 20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current
- Measure Equipment :
 - L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)
 - SRF : HP4286A
 - RDC : Chroma 16502
 - Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD00030321R82□00	0.82	30	7.96 MHz, 1 V	0.06	2.2	AX
BPSD000303211R0□00	1	20	7.96 MHz, 1 V	0.07	2.08	BA
BPSD000303211R2□00	1.2	20	7.96 MHz, 1 V	0.08	2	BC
BPSD000303211R4□00	1.4	20	7.96 MHz, 1 V	0.09	1.86	BE
BPSD000303211R5□00	1.5	20	7.96 MHz, 1 V	0.11	1.8	BF
BPSD000303211R8□00	1.8	20	7.96 MHz, 1 V	0.11	1.8	BI
BPSD000303212R2□00	2.2	20	7.96 MHz, 1 V	0.13	1.39	CC
BPSD000303212R7□00	2.7	20	7.96 MHz, 1 V	0.14	1.32	CH
BPSD000303213R3□00	3.3	10,20	7.96 MHz, 1 V	0.17	1.25	DD
BPSD000303213R9□00	3.9	20	7.96 MHz, 1 V	0.19	1.2	DJ
BPSD000303214R7□00	4.7	20	7.96 MHz, 1 V	0.21	1.13	EH
BPSD000303215R6□00	5.6	20	7.96 MHz, 1 V	0.22	0.91	FG
BPSD000303216R8□00	6.8	20	7.96 MHz, 1 V	0.25	0.85	GI
BPSD000303217R0□00	7	20	7.96 MHz, 1 V	0.28	0.82	HA
BPSD000303218R2□00	8.2	20	7.96 MHz, 1 V	0.28	0.82	IC
BPSD00030321100□00	10	10,20	2.52 MHz, 1 V	0.32	0.74	KA
BPSD00030321120□00	12	20	2.52 MHz, 1 V	0.35	0.64	QA
BPSD00030321150□00	15	20	2.52 MHz, 1 V	0.4	0.6	MA
BPSD00030321180□00	18	20	2.52 MHz, 1 V	0.48	0.54	RA
BPSD00030321220□00	22	10,20	2.52 MHz, 1 V	0.58	0.5	LA
BPSD00030321270□00	27	20	2.52 MHz, 1 V	0.65	0.43	SA
BPSD00030321330□00	33	20	2.52 MHz, 1 V	0.8	0.4	NA
BPSD00030321390□00	39	20	2.52 MHz, 1 V	0.9	0.37	PA
BPSD00030321470□00	47	20	2.52 MHz, 1 V	1.19	0.36	OA
BPSD00030321500□00	50	20	2.52 MHz, 1 V	1.22	0.33	TA
BPSD00030321560□00	56	20	2.52 MHz, 1 V	1.27	0.31	UA
BPSD00030321680□00	68	10,20	2.52 MHz, 1 V	1.73	0.3	VA
BPSD00030321750□00	75	20	2.52 MHz, 1 V	1.9	0.29	WA

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10%, M= $\pm$ 20%, T= $\pm$ 30%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD00030321820□00	82	10,20	2.52 MHz, 1 V	1.99	0.28	XA
BPSD00030321101□00	100	10,20	1 kHz, 1 V	2.52	0.25	KB
BPSD00030321121□00	120	10,20	1 kHz, 1 V	2.9	0.2	QB
BPSD00030321151□00	150	20	1 kHz, 1 V	3.36	0.19	MB
BPSD00030321181□00	180	20	1 kHz, 1 V	5.1	0.17	RB
BPSD00030321221□00	220	10,20	1 kHz, 1 V	5.8	0.16	LB
BPSD00030321271□00	270	10,20	1 kHz, 1 V	7.8	0.14	SB

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10%, M= $\pm$ 20%, T= $\pm$ 30%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD00050432R15□00	0.15	30	7.96 MHz, 1 V	0.0085	7.5	R15
BPSD000504321R0□00	1.0	10,20	7.96 MHz, 1 V	0.033	3.8	1R0
BPSD000504321R2□00	1.2	20	7.96 MHz, 1 V	0.035	3.5	1R2
BPSD000504321R4□00	1.4	20	7.96 MHz, 1 V	0.038	3.3	1R4
BPSD000504321R8□00	1.8	10,20	7.96 MHz, 1 V	0.042	2.91	1R8
BPSD000504322R2□00	2.2	10,20	7.96 MHz, 1 V	0.047	2.6	2R2
BPSD000504322R7□00	2.7	20	7.96 MHz, 1 V	0.052	2.43	2R7
BPSD000504323R3□00	3.3	10,20	7.96 MHz, 1 V	0.058	2.15	3R3
BPSD000504323R9□00	3.9	20	7.96 MHz, 1 V	0.076	1.98	3R9
BPSD000504324R7□00	4.7	10,20	7.96 MHz, 1 V	0.094	1.7	4R7
BPSD000504325R6□00	5.6	10,20	7.96 MHz, 1 V	0.101	1.6	5R6
BPSD000504326R2□00	6.2	20	7.96 MHz, 1 V	0.11	1.5	6R2
BPSD000504326R8□00	6.8	10,20	7.96 MHz, 1 V	0.117	1.41	6R8
BPSD000504328R2□00	8.2	10,20	7.96 MHz, 1 V	0.132	1.26	8R2
BPSD00050432100□00	10	10,20	2.52 MHz, 1 V	0.182	1.15	100
BPSD00050432120□00	12	20	2.52 MHz, 1 V	0.21	1.05	120
BPSD00050432150□00	15	10,20	2.52 MHz, 1 V	0.235	0.92	150
BPSD00050432180□00	18	20	2.52 MHz, 1 V	0.338	0.84	180
BPSD00050432220□00	22	10,20	2.52 MHz, 1 V	0.378	0.76	220
BPSD00050432270□00	27	10,20	2.52 MHz, 1 V	0.522	0.71	270
BPSD00050432330□00	33	10,20	2.52 MHz, 1 V	0.54	0.64	330
BPSD00050432390□00	39	10,20	2.52 MHz, 1 V	0.587	0.59	390
BPSD00050432470□00	47	10,20	2.52 MHz, 1 V	0.844	0.54	470
BPSD00050432560□00	56	10,20	2.52 MHz, 1 V	0.937	0.5	560
BPSD00050432680□00	68	10,20	2.52 MHz, 1 V	1.117	0.46	680
BPSD00050432101□00	100	10,20	1kHz, 1 V	2	0.4	101
BPSD00050432121□00	120	10,20	1kHz, 1 V	1.8	0.38	121
BPSD00050432151□00	150	10,20	1kHz, 1 V	2.8	0.3	151
BPSD00050432181□00	180	10,20	1kHz, 1 V	3.2	0.25	181
BPSD0005043221□00	220	10,20	1kHz, 1 V	4	0.15	221
BPSD00050432331□00	330	10,20	1kHz, 1 V	5.85	0.21	331

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10% , M= $\pm$ 20% , T= $\pm$ 30%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

• Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm\%$)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD000605251R0□00	1	20	7.96 MHz, 1 V	0.03	4.5	1R0
BPSD000605251R4□00	1.4	20	7.96 MHz, 1 V	0.04	4	1R4
BPSD000605251R8□00	1.8	20	7.96 MHz, 1 V	0.05	3.3	1R8
BPSD000605252R2□00	2.2	20	7.96 MHz, 1 V	0.06	2.94	2R2
BPSD000605252R7□00	2.7	20	7.96 MHz, 1 V	0.07	2.5	2R7
BPSD000605253R3□00	3.3	20	7.96 MHz, 1 V	0.08	2.35	3R3
BPSD000605253R9□00	3.9	20	7.96 MHz, 1 V	0.09	2.2	3R9
BPSD000605254R7□00	4.7	10,20	7.96 MHz, 1 V	0.14	2	4R7
BPSD000605255R6□00	5.6	20	7.96 MHz, 1 V	0.15	1.8	5R6
BPSD000605256R8□00	6.8	20	7.96 MHz, 1 V	0.16	1.7	6R8
BPSD000605258R2□00	8.2	20	7.96 MHz, 1 V	0.17	1.4	8R2
BPSD00060525100□00	10	10,20	2.52 MHz, 1 V	0.18	1.2	100
BPSD00060525120□00	12	20	2.52 MHz, 1 V	0.2	1.18	120
BPSD00060525150□00	15	20	2.52 MHz, 1 V	0.22	1.15	150
BPSD00060525180□00	18	20	2.52 MHz, 1 V	0.25	1.1	180
BPSD00060525220□00	22	10,20	2.52 MHz, 1 V	0.35	1	220
BPSD00060525270□00	27	20	2.52 MHz, 1 V	0.45	0.86	270
BPSD00060525330□00	33	10,20	2.52 MHz, 1 V	0.56	0.76	330
BPSD00060525390□00	39	10,20	2.52 MHz, 1 V	0.69	0.75	390
BPSD00060525470□00	47	10,20	2.52 MHz, 1 V	0.72	0.73	470
BPSD00060525560□00	56	10,20	2.52 MHz, 1 V	0.84	0.55	560
BPSD00060525680□00	68	10,20	2.52 MHz, 1 V	0.9	0.52	680
BPSD00060525820□00	82	10,20	2.52 MHz, 1 V	1.2	0.5	820
BPSD00060525101□00	100	10,20	1 kHz, 1 V	1.3	0.4	101
BPSD00060525121□00	120	10,20	1 kHz, 1 V	1.38	0.36	121
BPSD00060525151□00	150	10,20	1 kHz, 1 V	1.81	0.3	151
BPSD00060525181□00	180	10,20	1 kHz, 1 V	1.95	0.26	181
BPSD00060525221□00	220	10,20	1 kHz, 1 V	3	0.25	221

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm 10\%$, M= $\pm 20\%$

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD00060525271□00	270	10,20	1 kHz, 1 V	3.2	0.21	271
BPSD00060525331□00	330	10,20	1 kHz, 1 V	3.82	0.18	331
BPSD00060525391□00	390	10,20	1 kHz, 1 V	4.68	0.16	391
BPSD00060525471□00	470	10,20	1 kHz, 1 V	5.1	0.15	471
BPSD00060525561□00	560	10,20	1 kHz, 1 V	8.5	0.14	561
BPSD00060525681□00	680	10,20	1 kHz, 1 V	10	0.13	681
BPSD00060525821□00	820	10,20	1 kHz, 1 V	12	0.07	821
BPSD00060525102□00	1000	10,20	1 kHz, 1 V	18	0.05	102

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10%, M= $\pm$ 20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD000605301R0□00	1.0	20	7.96 MHz,1 V	0.03	4.5	1R0
BPSD000605301R2□00	1.2	20	7.96 MHz,1 V	0.03	4.2	1R2
BPSD000605301R5□00	1.5	20	7.96 MHz,1 V	0.03	4.1	1R5
BPSD000605301R8□00	1.8	10,20	7.96 MHz,1 V	0.03	3.7	1R8
BPSD000605302R0□00	2	20	7.96 MHz,1 V	0.03	3.6	2R0
BPSD000605302R2□00	2.2	20	7.96 MHz,1 V	0.03	3.5	2R2
BPSD000605302R7□00	2.7	20	7.96 MHz,1 V	0.04	3.2	2R7
BPSD000605303R3□00	3.3	10,20	7.96 MHz,1 V	0.05	2.8	3R3
BPSD000605303R9□00	3.9	20	7.96 MHz,1 V	0.06	2.6	3R9
BPSD000605304R7□00	4.7	10,20	7.96 MHz,1 V	0.07	2.5	4R7
BPSD000605305R6□00	5.6	20	7.96 MHz,1 V	0.08	2.4	5R6
BPSD000605306R8□00	6.8	20	7.96 MHz,1 V	0.09	2.2	6R8
BPSD000605308R2□00	8.2	20	7.96 MHz,1 V	0.1	2	8R2
BPSD00060530100□00	10	10,20	2.52 MHz,1 V	0.12	1.8	100
BPSD00060530120□00	12	10,20	2.52 MHz,1 V	0.13	1.75	120
BPSD00060530150□00	15	10,20	2.52 MHz,1 V	0.15	1.7	150
BPSD00060530180□00	18	10,20	2.52 MHz,1 V	0.22	1.6	180
BPSD00060530220□00	22	10,20	2.52 MHz,1 V	0.22	1.5	220
BPSD00060530270□00	27	20	2.52 MHz,1 V	0.26	1.4	270
BPSD00060530330□00	33	10,20	2.52 MHz,1 V	0.33	1.1	330
BPSD00060530390□00	39	10,20	2.52 MHz,1 V	0.42	1	390
BPSD00060530470□00	47	10,20	2.52 MHz,1 V	0.5	0.9	470
BPSD00060530560□00	56	10,20	2.52 MHz,1 V	0.55	0.85	560
BPSD00060530680□00	68	10,20	2.52 MHz,1 V	0.65	0.8	680
BPSD00060530820□00	82	10,20	2.52 MHz,1 V	0.8	0.65	820
BPSD00060530101□00	100	10,20	1 kHz,1 V	0.9	0.6	101
BPSD00060530121□00	120	10,20	1 kHz,1 V	1	0.58	121
BPSD00060530151□00	150	10,20	1 kHz,1 V	1.3	0.43	151

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10% , M= $\pm$ 20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current
- Measure Equipment :
 L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)
 SRF : HP4286A
 RDC : Chroma 16502
 Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD00060530181□00	180	10,20	1 kHz,1 V	1.5	0.41	181
BPSD00060530221□00	220	10,20	1 kHz,1 V	2	0.38	221
BPSD00060530271□00	270	10,20	1 kHz,1 V	2.5	0.35	271
BPSD00060530331□00	330	10,20	1 kHz,1 V	3.2	0.28	331
BPSD00060530391□00	390	10,20	1 kHz,1 V	3.5	0.26	391
BPSD00060530471□00	470	10,20	1 kHz,1 V	4.2	0.2	471
BPSD00060530561□00	560	10,20	1 kHz,1 V	4.5	0.19	561
BPSD00060530681□00	680	10,20	1 kHz,1 V	6.5	0.18	681
BPSD00060530821□00	820	10,20	1 kHz,1 V	7.5	0.15	821
BPSD00060530102□00	1000	10,20	1 kHz,1 V	8	0.13	102

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10% , M= $\pm$ 20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD000605451R8□00	1.8	20	7.96 MHz,1 V	0.02	3.5	1R8
BPSD000605452R2□00	2.2	20	7.96 MHz,1 V	0.023	3.2	2R2
BPSD000605453R3□00	3.3	10,20	7.96 MHz,1 V	0.0314	2.59	3R3
BPSD000605453R5□00	3.5	20	7.96 MHz,1 V	0.03	2.4	3R5
BPSD000605454R7□00	4.7	10,20	7.96 MHz,1 V	0.0372	2.3	4R7
BPSD000605456R8□00	6.8	20	7.96 MHz,1 V	0.057	1.8	6R8
BPSD000605458R2□00	8.2	20	7.96 MHz,1 V	0.0594	1.7	8R2
BPSD00060545100□00	10	10,20	2.52 MHz,1 V	0.1	1.44	100
BPSD00060545120□00	12	20	2.52 MHz,1 V	0.12	1.4	120
BPSD00060545150□00	15	10,20	2.52 MHz,1 V	0.14	1.3	150
BPSD00060545180□00	18	20	2.52 MHz,1 V	0.15	1.23	180
BPSD00060545220□00	22	20	2.52 MHz,1 V	0.18	1.11	220
BPSD00060545270□00	27	20	2.52 MHz,1 V	0.2	0.97	270
BPSD00060545330□00	33	10,20	2.52 MHz,1 V	0.23	0.88	330
BPSD00060545390□00	39	10,20	2.52 MHz,1 V	0.32	0.8	390
BPSD00060545470□00	47	10,20	2.52 MHz,1 V	0.37	0.72	470
BPSD00060545560□00	56	10,20	2.52 MHz,1 V	0.42	0.68	560
BPSD00060545680□00	68	10,20	2.52 MHz,1 V	0.46	0.61	680
BPSD00060545820□00	82	10,20	2.52 MHz,1 V	0.6	0.58	820
BPSD00060545101□00	100	10,20	1 kHz,1 V	0.7	0.52	101
BPSD00060545121□00	120	10,20	1 kHz,1 V	0.93	0.48	121
BPSD00060545151□00	150	10,20	1 kHz,1 V	1.1	0.4	151
BPSD00060545181□00	180	10,20	1 kHz,1 V	1.38	0.38	181
BPSD00060545221□00	220	10,20	1 kHz,1 V	1.57	0.35	221
BPSD00060545271□00	270	10,20	1 kHz,1 V	1.85	0.29	271
BPSD00060545331□00	330	10,20	1 kHz,1 V	2	0.28	331
BPSD00060545391□00	390	10,20	1 kHz,1 V	2.6	0.26	391
BPSD00060545471□00	470	10,20	1 kHz,1 V	3	0.12	471

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10% , M= $\pm$ 20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current
- Measure Equipment :
L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)
SRF : HP4286A
RDC : Chroma 16502
Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD00060545561□00	560	10,20	1 kHz, 1 V	4.19	0.1	561
BPSD00060545681□00	680	10,20	1 kHz, 1 V	4.44	0.08	681
BPSD00060545821□00	820	10,20	1 kHz, 1 V	5.12	0.05	821
BPSD00060545102□00	1000	10,20	1 kHz, 1 V	10	0.03	102

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10% , M= $\pm$ 20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD000807352R2□00	2.2	20	7.96 MHz, 1 V	0.03	3.2	2R2
BPSD000807354R7□00	4.7	20	2.52 MHz, 1 V	0.04	1.6	4R7
BPSD00080735100□00	10	20	2.52 MHz, 1 V	0.08	1.44	100
BPSD00080735120□00	12	10,20	2.52 MHz, 1 V	0.09	1.39	120
BPSD00080735150□00	15	10,20	2.52 MHz, 1 V	0.1	1.24	150
BPSD00080735180□00	18	20	2.52 MHz, 1 V	0.11	1.12	180
BPSD00080735220□00	22	20	2.52 MHz, 1 V	0.13	1.07	220
BPSD00080735270□00	27	20	2.52 MHz, 1 V	0.15	0.94	270
BPSD00080735330□00	33	10,20	2.52 MHz, 1 V	0.17	0.85	330
BPSD00080735390□00	39	10,20	2.52 MHz, 1 V	0.22	0.74	390
BPSD00080735470□00	47	10,20	2.52 MHz, 1 V	0.25	0.68	470
BPSD00080735560□00	56	10,20	2.52 MHz, 1 V	0.28	0.64	560
BPSD00080735680□00	68	10,20	2.52 MHz, 1 V	0.33	0.59	680
BPSD00080735820□00	82	10,20	2.52 MHz, 1 V	0.41	0.54	820
BPSD00080735101□00	100	10,20	1 kHz, 1 V	0.48	0.51	101
BPSD00080735121□00	120	10,20	1 kHz, 1 V	0.54	0.49	121
BPSD00080735151□00	150	10,20	1 kHz, 1 V	0.75	0.4	151
BPSD00080735181□00	180	10,20	1 kHz, 1 V	1.02	0.36	181
BPSD00080735221□00	220	10,20	1 kHz, 1 V	1.2	0.31	221
BPSD00080735271□00	270	10,20	1 kHz, 1 V	1.31	0.29	271
BPSD00080735331□00	330	10,20	1 kHz, 1 V	1.5	0.28	331
BPSD00080735561□00	560	10,20	1 kHz, 1 V	2.5	0.14	561

Note: When ordering, please specify tolerance code. Tolerance: K=±10% , M=±20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD000807501R4□00	1.4	20	7.96 MHz, 1 V	0.02	3.7	1R4
BPSD000807501R5□00	1.5	20	7.96 MHz, 1 V	0.02	3.7	1R5
BPSD000807501R8□00	1.8	20	7.96 MHz, 1 V	0.02	3.7	1R8
BPSD000807502R2□00	2.2	20	7.96 MHz, 1 V	0.02	3.7	2R2
BPSD000807502R7□00	2.7	20	7.96 MHz, 1 V	0.02	3.7	2R7
BPSD000807503R0□00	3	20	7.96 MHz, 1 V	0.025	3.7	3R0
BPSD000807503R3□00	3.3	20	7.96 MHz, 1 V	0.03	3.7	3R3
BPSD000807503R6□00	3.6	20	7.96 MHz, 1 V	0.03	3.7	3R6
BPSD000807503R9□00	3.9	20	7.96 MHz, 1 V	0.03	3.7	3R9
BPSD000807504R7□00	4.7	10,20	7.96 MHz, 1 V	0.04	3.5	4R7
BPSD000807505R6□00	5.6	20	7.96 MHz, 1 V	0.04	3.3	5R6
BPSD000807506R8□00	6.8	20	7.96 MHz, 1 V	0.04	3.1	6R8
BPSD000807508R2□00	8.2	20	7.96 MHz, 1 V	0.05	2.7	8R2
BPSD00080750100□00	10	10,20	2.52 MHz, 1 V	0.07	2.3	100
BPSD00080750120□00	12	20	2.52 MHz, 1 V	0.08	2	120
BPSD00080750150□00	15	10,20	2.52 MHz, 1 V	0.09	1.8	150
BPSD00080750180□00	18	20	2.52 MHz, 1 V	0.1	1.6	180
BPSD00080750220□00	22	10,20	2.52 MHz, 1 V	0.11	1.5	220
BPSD00080750270□00	27	20	2.52 MHz, 1 V	0.12	1.3	270
BPSD00080750330□00	33	10,20	2.52 MHz, 1 V	0.13	1.2	330
BPSD00080750390□00	39	10,20	2.52 MHz, 1 V	0.16	1.1	390
BPSD00080750470□00	47	10,20	2.52 MHz, 1 V	0.18	1.1	470
BPSD00080750560□00	56	10,20	2.52 MHz, 1 V	0.24	0.94	560
BPSD00080750680□00	68	10,20	2.52 MHz, 1 V	0.28	0.85	680
BPSD00080750820□00	82	10,20	2.52 MHz, 1 V	0.37	0.78	820
BPSD00080750101□00	100	10,20	1 kHz, 1 V	0.43	0.72	101
BPSD00080750121□00	120	10,20	1 kHz, 1 V	0.47	0.66	121
BPSD00080750151□00	150	10,20	1 kHz, 1 V	0.64	0.58	151

Note: When ordering, please specify tolerance code. Tolerance: K=±10%, M=±20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current
- Measure Equipment :
 L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)
 SRF : HP4286A
 RDC : Chroma 16502
 Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD00080750181□00	180	10,20	1 kHz,1 V	0.71	0.51	181
BPSD00080750221□00	220	10,20	1 kHz,1 V	0.96	0.49	221
BPSD00080750271□00	270	10,20	1 kHz,1 V	1.11	0.42	271
BPSD00080750331□00	330	10,20	1 kHz,1 V	1.26	0.4	331
BPSD00080750391□00	390	10,20	1 kHz,1 V	1.77	0.36	391
BPSD00080750471□00	470	10,20	1 kHz,1 V	1.96	0.34	471
BPSD00080750561□00	560	10,20	1 kHz,1 V	2.41	0.32	561
BPSD00080750681□00	680	10,20	1 kHz,1 V	2.5	0.29	681
BPSD00080750102□00	1000	10,20	1 kHz,1 V	2.8	0.19	102

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10% , M= $\pm$ 20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μH)	Tolerance (±%)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD001009403R3□00	3.3	20	7.96 MHz,1 V	0.022	4.5	3R3
BPSD001009403R8□00	3.8	20	7.96 MHz,1 V	0.022	4.2	3R8
BPSD001009406R8□00	6.8	20	7.96 MHz,1 V	0.04	3	6R8
BPSD00100940100□00	10	20	2.52 MHz,1 V	0.05	2.38	100
BPSD00100940120□00	12	20	2.52 MHz,1 V	0.06	2.13	120
BPSD00100940150□00	15	10,20	2.52 MHz,1 V	0.07	1.87	150
BPSD00100940180□00	18	20	2.52 MHz,1 V	0.08	1.73	180
BPSD00100940220□00	22	10,20	2.52 MHz,1 V	0.09	1.6	220
BPSD00100940270□00	27	20	2.52 MHz,1 V	0.1	1.44	270
BPSD00100940330□00	33	10,20	2.52 MHz,1 V	0.12	1.26	330
BPSD00100940390□00	39	10,20	2.52 MHz,1 V	0.15	1.2	390
BPSD00100940470□00	47	10,20	2.52 MHz,1 V	0.17	1.1	470
BPSD00100940560□00	56	10,20	2.52 MHz,1 V	0.2	1.01	560
BPSD00100940680□00	68	10,20	2.52 MHz,1 V	0.22	0.91	680
BPSD00100940820□00	82	10,20	2.52 MHz,1 V	0.3	0.85	820
BPSD00100940101□00	100	10,20	1 kHz,1 V	0.34	0.74	101
BPSD00100940121□00	120	10,20	1 kHz,1 V	0.4	0.69	121
BPSD00100940151□00	150	10,20	1 kHz,1 V	0.54	0.61	151
BPSD00100940181□00	180	10,20	1 kHz,1 V	0.62	0.56	181
BPSD00100940221□00	220	10,20	1 kHz,1 V	0.72	0.53	221
BPSD00100940271□00	270	10,20	1 kHz,1 V	0.95	0.45	271
BPSD00100940331□00	330	10,20	1 kHz,1 V	1.1	0.42	331
BPSD00100940391□00	390	10,20	1 kHz,1 V	1.24	0.38	391
BPSD00100940471□00	470	10,20	1 kHz,1 V	1.53	0.35	471
BPSD00100940561□00	560	10,20	1 kHz,1 V	1.9	0.32	561

Note: When ordering, please specify tolerance code. Tolerance: K=±10% , M=±20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current

● Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics

Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD001009543R3□00	3.3	20	7.96 MHz,1 V	0.038	2.8	3R3
BPSD001009544R7□00	4.7	20	7.96 MHz,1 V	0.04	2.6	4R7
BPSD001009545R6□00	5.6	20	7.96 MHz,1 V	0.037	4.5	5R6
BPSD001009546R8□00	6.8	20	7.96 MHz,1 V	0.037	4.33	6R8
BPSD001009548R2□00	8.2	20	7.96 MHz,1 V	0.05	3.5	8R2
BPSD00100954100□00	10	10,20	2.52 MHz,1 V	0.06	2.6	100
BPSD00100954120□00	12	20	2.52 MHz,1 V	0.07	2.45	120
BPSD00100954150□00	15	10,20	2.52 MHz,1 V	0.08	2.27	150
BPSD00100954180□00	18	20	2.52 MHz,1 V	0.09	2.15	180
BPSD00100954220□00	22	10,20	2.52 MHz,1 V	0.1	1.95	220
BPSD00100954270□00	27	10,20	2.52 MHz,1 V	0.11	1.76	270
BPSD00100954330□00	33	10,20	2.52 MHz,1 V	0.12	1.5	330
BPSD00100954390□00	39	10,20	2.52 MHz,1 V	0.14	1.37	390
BPSD00100954470□00	47	10,20	2.52 MHz,1 V	0.17	1.28	470
BPSD00100954560□00	56	10,20	2.52 MHz,1 V	0.19	1.17	560
BPSD00100954680□00	68	10,20	2.52 MHz,1 V	0.22	1.11	680
BPSD00100954820□00	82	10,20	2.52 MHz,1 V	0.25	1	820
BPSD00100954101□00	100	10,20	1 kHz,1 V	0.35	0.97	101
BPSD00100954121□00	120	10,20	1 kHz,1 V	0.4	0.89	121
BPSD00100954151□00	150	10,20	1 kHz,1 V	0.47	0.78	151
BPSD00100954181□00	180	10,20	1 kHz,1 V	0.63	0.72	181
BPSD00100954221□00	220	10,20	1 kHz,1 V	0.73	0.66	221
BPSD00100954271□00	270	10,20	1 kHz,1 V	0.97	0.57	271
BPSD00100954331□00	330	10,20	1 kHz,1 V	1.15	0.52	331
BPSD00100954391□00	390	10,20	1 kHz,1 V	1.3	0.48	391
BPSD00100954471□00	470	10,20	1 kHz,1 V	1.48	0.42	471
BPSD00100954561□00	560	10,20	1 kHz,1 V	1.9	0.33	561
BPSD00100954681□00	680	10,20	1 kHz,1 V	2.25	0.28	681
BPSD00100954821□00	820	10,20	1 kHz,1 V	2.55	0.24	821
BPSD00100954102□00	1000	10,20	1 kHz,1 V	3.1	0.2	102

Note: When ordering, please specify tolerance code. Tolerance: K=±10% , M=±20%

- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)

- Isat for Inductance drop 10% from its value without current

- Measure Equipment :

L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)

SRF : HP4286A

RDC : Chroma 16502

Isat : HP4284+42841A or WK3260B+WK3265B

Electrical Characteristics



Part Number	Inductance (μ H)	Tolerance ($\pm$ %)	Test Frequency	RDC (Ω)Max	Isat (A)	Marking
BPSD00100965220□00	22	10,20	2.52 MHz, 1 V	0.08	3.8	220
BPSD00100965471□00	470	10,20	1 kHz, 1 V	1.421	0.82	471
BPSD00100965102□00	1000	10,20	1 kHz, 1 V	2.9	0.6	102
BPSD00100965122□00	1200	10,20	1 kHz, 1 V	3.5	0.5	122
BPSD00100965152□00	1500	10,20	1 kHz, 1 V	3.8	0.6	152
BPSD00100965202□00	2000	10,20	1 kHz, 1 V	6.6	0.4	202
BPSD00100965222□00	2200	10,20	1 kHz, 1 V	6	0.4	222
BPSD00100965602□00	6000	10,20	1 kHz, 1 V	14	0.27	602
BPSD00100965822□00	8200	10,20	1 kHz, 1 V	50	0.2	822

Note: When ordering, please specify tolerance code. Tolerance: K= $\pm$ 10%, M= $\pm$ 20%



- Operating temperature range - 40°C ~ 105°C(Including self - temperature rise)
- Isat for Inductance drop 10% from its value without current
- Measure Equipment :
 - L : Agilent/ E4980 or HP4284A (under 1MHz), HP4285A (over 1MHz)
 - SRF : HP4286A
 - RDC : Chroma 16502
 - Isat : HP4284+42841A or WK3260B+WK3265B

Test Instruments : HP4294A Impedance / Material Analyzer



BPSD00050432



BPSD00060545




BPSD00080735




Test Instruments : HP4294A Impedance / Material Analyzer

BPSD00080750

Inductance vs. Frequency Characteristics




Inductance vs. DC Current




BPSD00100940

Inductance vs. Frequency Characteristics




Inductance vs. DC Current




BPSD00100954

Inductance vs. Frequency Characteristics




Inductance vs. DC Current




Packaging Specifications


Tape Dimensions



Tape Material



Reel Dimensions



Dimensions in mm

TYPE	Tape Dimensions							Reel Dimensions				Quantity PCS / REEL
	K0	D	E	W	P	P0	P2	A	B	C	D	
BPSD00030315	1.80	1.55	1.75	12	8	4	2	330	100	13	13.4	3000
BPSD00030321	2.50	1.55	1.75	12	8	4	2	330	100	13	13.4	3000
BPSD00050432	3.55	1.55	1.75	12	8	4	2	330	100	13	13.4	2000
BPSD00060525	3.30	1.50	1.75	16	8	4	2	330	100	13	16.0	2000
BPSD00060530	3.30	1.50	1.75	16	8	4	2	330	100	13	16.0	2000
BPSD00060545	4.8	1.55	1.75	16	8	4	2	330	100	13	16.0	1500
BPSD00080735	3.8	1.55	1.75	16	12	4	2	330	100	13	16.0	1000
BPSD00080750	5.2	1.55	1.75	16	12	4	2	330	100	13	16.0	700
BPSD00100940	4.5	1.55	1.75	24	12	4	2	330	100	13	24.4	700
BPSD00100954	5.8	1.55	1.75	24	12	4	2	330	100	13	24.4	700
BPSD00100965	7.0	1.55	1.75	24	12	4	2	330	100	13	24.4	500

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

BPSD00030315100M00	BPSD00030315101M00	BPSD00030315150M00	BPSD00030315220K00
BPSD00030315220M00	BPSD00030315221M00	BPSD000303152R2M00	BPSD00030315330M00
BPSD00030315390M00	BPSD000303153R3M00	BPSD00030315470M00	BPSD000303154R7M00
BPSD000303155R6M00	BPSD00030315680M00	BPSD000303156R8M00	BPSD00030321100K00
BPSD00030321100M00	BPSD00030321101K00	BPSD00030321101M00	BPSD00030321120M00
BPSD00030321121K00	BPSD00030321121M00	BPSD00030321150M00	BPSD00030321151M00
BPSD00030321180M00	BPSD00030321181M00	BPSD000303211R0M00	BPSD000303211R4M00
BPSD000303211R5M00	BPSD000303211R8M00	BPSD00030321220K00	BPSD00030321220M00
BPSD00030321221K00	BPSD00030321221M00	BPSD00030321270M00	BPSD00030321271K00
BPSD00030321271M00	BPSD000303212R2M00	BPSD000303212R7M00	BPSD00030321330M00
BPSD00030321390M00	BPSD000303213R3M00	BPSD000303213R9M00	BPSD00030321470M00
BPSD000303214R7M00	BPSD00030321500M00	BPSD00030321560M00	BPSD000303215R6M00
BPSD00030321680K00	BPSD00030321680M00	BPSD000303216R8M00	BPSD00030321750M00
BPSD000303217R0M00	BPSD00030321820K00	BPSD00030321820M00	BPSD000303218R2M00
BPSD00030321R82T00	BPSD00050432100M00	BPSD00050432101K00	BPSD00050432101M00
BPSD00050432120M00	BPSD00050432121K00	BPSD00050432121M00	BPSD00050432150K00
BPSD00050432150M00	BPSD00050432151K00	BPSD00050432151M00	BPSD00050432180M00
BPSD00050432181K00	BPSD00050432181M00	BPSD000504321R0M00	BPSD000504321R2M00
BPSD000504321R4M00	BPSD000504321R8K00	BPSD000504321R8M00	BPSD00050432220K00
BPSD00050432220M00	BPSD00050432221K00	BPSD00050432221M00	BPSD00050432270K00
BPSD00050432270M00	BPSD000504322R2M00	BPSD000504322R7M00	BPSD00050432330K00
BPSD00050432330M00	BPSD00050432331K00	BPSD00050432331M00	BPSD00050432390K00
BPSD00050432390M00	BPSD000504323R3M00	BPSD000504323R9M00	BPSD00050432470K00
BPSD00050432470M00	BPSD000504324R7M00	BPSD00050432560K00	BPSD00050432560M00
BPSD000504325R6K00	BPSD000504325R6M00	BPSD00050432680K00	BPSD00050432680M00