

# **DATA SHEET**

SURFACE-MOUNT CERAMIC MULTILAYER CAPACITORS

General purpose

Class 1, NPO

16 V TO 50 V

0.22 pF to 33 nF

**RoHS compliant & Halogen Free** 



YAGEO Phicomp



15

#### SCOPE

This specification describes NP0 series chip capacitors with leadfree terminations.

### <u>APPLICATIONS</u>

- Consumer electronics for example
  - Tuners
  - Television receivers
  - All types of cameras
- Telecommunications
- Data processing

#### **FEATURES**

- Supplied in tape on reel
- Nickel-barrier end termination
- RoHS compliant
- Halogen Free compliant

# ORDERING INFORMATION-GLOBAL PART NUMBER, PHYCOMP

#### CTC & 12NC

All part numbers are identified by the series, size, tolerance, TC material, packing style, voltage, process code, termination and capacitance value.

## YAGEO BRAND ordering code

#### **GLOBAL PART NUMBER (PREFERRED)**

XXXX X X NPO X BN XXX (2) (3)

## (I) SIZE – INCH BASED (METRIC)

0201 (0603)

0402 (1005)

0603 (1608)

0805 (2012)

1206 (3216)

1210 (3225)

1812 (4532)

#### (2) TOLERANCE

 $B = \pm 0.1 pF$ 

 $C = \pm 0.25 pF$ 

 $D = \pm 0.5 pF$ 

 $F = \pm 1\%$ 

 $G = \pm 2\%$ 

 $| = \pm 5\%$ 

#### (3) PACKING STYLE

R = Paper/PE taping reel; Reel 7 inch

K = Blister taping reel; Reel 7 inch

P = Paper/PE taping reel; Reel 13 inch

F = Blister taping reel; Reel 13 inch

C = Bulk case

# (4) RATED VOLTAGE

7 = 16 V

8 = 25 V

9 = 50 V

#### (5) CAPACITANCE VALUE

2 significant digits+number of zeros

The 3rd digit signifies the multiplying factor, and letter R is decimal point

Example:  $121 = 12 \times 10^{1} = 120 \text{ pF}$ 

#### **PHYCOMP BRAND** ordering codes


GLOBAL PART NUMBER (preferred), PHYCOMP CTC (for North America) and I2NC (traditional) codes are acceptable to order Phycomp brand products.

## **GLOBAL PART NUMBER (PREFERRED)**


For detailed information of GLOBAL PART NUMBER and ordering example, please refer to page 2.

#### 12NC CODE

Ordering information for 16 V to 25 V



# Ordering information for 50 V



- (I) Please refer to "Last 2-digit of I2NC" in "CAPACITANCE RANGE & THICKNESS FOR NP0"
- (2) Please refer to "Last 3-digit of 12NC" in "CAPACITANCE RANGE & THICKNESS FOR NP0"
- (3) Quantity on reel depends on thickness classification; see table 6



# PHYCOMP CTC code (for North America)


● Example: 0603CG271J7B200

0603	CG	271	J	7	В	2	0	0
Size code	Temp. Char.	Capacitance in pF	Tolerance	Voltage	Termination	Packing	Marking	Range identifier
0201 0402 0603 0805 1206 1210 1812	CG = NP0	$101 = 100 \text{ pF}$ ; the third digit signifies the multiplying factor: $0 = \times 1$ $1 = \times 10$ $2 = \times 100$ $3 = \times 1,000$	$B = \pm 0.1 \text{ pF}$ $C = \pm 0.25 \text{ pF}$ $D = \pm 0.5 \text{ pF}$ $F = \pm 1\%$ $G = \pm 2\%$ $J = \pm 5\%$	7 = 16 V 8 = 25 V 9 = 50 V		2 = 180 mm 7" paper 3 = 330 mm 13" paper B = 180 mm 7" blister F = 330 mm 13" blister P = Bulk case	0 = no marking	0 = conv. ceramic

## **CONSTRUCTION**

The capacitor consists of a rectangular block of ceramic dielectric in which a number of interleaved metal electrodes are contained. This structure gives rise to a high capacitance per unit volume.

The inner electrodes are connected to the two end terminations and finally covered with a layer of plated tin (NiSn). The terminations are lead-free. A cross section of the structure is shown in Fig. I.




#### **DIMENSION**

**Table I** For outlines see fig. 2

TYPE	l (mama)	\\/ ()	T (MM)	L <sub>2</sub> / L <sub>3</sub>	(mm)	L <sub>4</sub> (mm)
IIPE	L <sub>I</sub> (mm)	W (mm)	T (MM)	min.	max.	min.
0201	0.6 ±0.03	0.3 ±0.03	=	0.10	0.20	0.20
0402	1.0 ±0.05	0.5 ±0.05	_	0.20	0.30	0.40
0603	1.6 ±0.10	0.8 ±0.10	_	0.20	0.60	0.40
0805	2.0 ±0.10 <sup>(1)</sup>	1.25 ±0.10 <sup>(1)</sup>	5.6	0.25	0.75	0.55
	2.0 ±0.20 <sup>(2)</sup>	1.25 ±0.20 <sup>(2)</sup>	Refer to table 2 to 5	0.25	0.75	0.55
1206	3.2 ±0.15 <sup>(1)</sup>	1.6 ±0.15 <sup>(1)</sup>	table 2 to 3	0.25	0.75	1.40
1200	3.2 ±0.30 <sup>(2)</sup>	1.6 ±0.20 <sup>(2)</sup>	_	0.25	0.75	1.40
1210	3.2 ±0.20	2.5 ±0.20	_	0.25	0.75	1.40
1812	4.5 ±0.20	3.2 ±0.20		0.25	0.75	2.20

#### **OUTLINES**



- 1. Dimension for size 0805 and 1206,  $C \le I \text{ nF}$
- 2. Dimension for size 0805 and 1206, C > 1 nF



5 15

## CAPACITANCE RANGE & THICKNESS FOR NPO

Table 2 Sizes from 0201 to 0603

CAP.	Last 3-digit of 12NC	Last 2-digit of I2NC	0201 25 V	50 V	0402 16 V	25 V	50 V	0603 16 V	25 V	50 V
0.22 pF	227									
0.47 pF	477									
0.82 pF	827									
1.0 pF	108									
I.2 pF	128									
1.5 pF	158									
I.8 pF	188									
2.2 pF	228	On request								
2.7 pF	278									
3.3 pF	338									
3.9 pF	398									
4.7 pF	478									
5.6 pF	568									
6.8 pF	688			0.3±0.03			0.5±0.05			0.8±0.1
8.2 pF	828			0.5±0.05			0.5±0.05			0.0±0.1
10 pF	109	23								
12 pF	129	24								
15 pF	159	25								
18 pF	189	26								
22 pF	229	27								
27 pF	279	28								
33 pF	339	29	0.3±0.03		0.5±0.05	0.5±0.05		0.8±0.1	0.8±0.1	
39 pF	399	31								
47 pF	479	32								
56 pF	569	33								
68 pF		34								
82 pF	829	35								
100 pF	101	36								

- I. Values in shaded cells indicate thickness class in mm
- 2. Capacitance value of non E-12 series is on request
- 3. 16V to 25V, refer to last 2-digit of 12NC  $\,$
- 4. 50V, refer to last 3-digit of I2NC



16 V to 50 V

# CAPACITANCE RANGE & THICKNESS FOR NPO

Table 3 Sizes from 0201 to 0603 (continued)

CAP.		Last 2-digit of 12NC	020 I 25 V	50 V	0402 16 V	25 V	50 V	0603 16 V	25 V	50 V
120 pF	121	37								
150 pF	151	38								
180 pF	181	39								
220 pF	221	41								
270 pF	271	42			0.5±0.05	0.5±0.05	0.5±0.05			
330 pF	331	43								
390 pF	391	44								
470 pF	471	45								
560 pF	561	46						00.01	00.01	00.01
680 pF	681	47						0.8±0.1	0.8±0.1	0.8±0.1
820 pF	821	48								
1.0 nF	102	49								
1.2 nF	122	51								
1.5 nF	152	52								
1.8 nF	182	53								
2.2 nF	222	54								
2.7 nF	272	55								
3.3 nF	332	56								
3.9 nF	392	57								
4.7 nF	472	58								
5.6 nF	562	59								
6.8 nF	682	61								
8.2 nF	822	62								
I0 nF	103	63								
12 nF	123	64								
15 nF	153	65								
18 nF	183	66								
22 nF	223	67								
33 nF	333	69								

- 1. Values in shaded cells indicate thickness class in mm
- 2. Capacitance value of non E-12 series is on request
- 3. 16V to 25V, refer to last 2-digit of 12NC
- 4. 50V, refer to last 3-digit of I2NC



## CAPACITANCE RANGE & THICKNESS FOR NPO

**Table 4** Sizes from 0805 to 1812

CAP.	Last 3-digit of	Last 2-digit of	0805			1206			1210		1812
	12NC	12NC	16 V	25 V	50 V	16 V	25 V	50 V	25 V	50 V	50 V
0.22 pF	227										
0.47 pF	477										
0.82 pF	827										
1.0 pF	108										
I.2 pF	128										
1.5 pF	158										
1.8 pF	188										
2.2 pF	228	On request									
2.7 pF	278										
3.3 pF	338										
3.9 pF	398										
4.7 pF	478										
5.6 pF	568										
6.8 pF	688										
8.2 pF	828				0.6±0.1			0.6±0.1			
10 pF	109	23									
12 pF	129	24									
15 pF	159	25									
18 pF	189	26									
22 pF	229	27									
27 pF	279	28									
33 pF	339	29	0.6±0.1	0.6±0.1		0.6±0.1	0.6±0.1				
39 pF	399	31									
47 pF	479	32									
56 pF	569	33									
68 pF	689	34							1.25±0.2	1.25±0.2	
82 pF	829	35									
100 pF	101	36									

- I. Values in shaded cells indicate thickness class in mm
- 2. Capacitance value of non E-12 series is on request
- 3. 16V to 25V, refer to last 2-digit of 12NC  $\,$
- 4. 50V, refer to last 3-digit of I2NC

NP0

16 V to 50 V

## CAPACITANCE RANGE & THICKNESS FOR NPO

Table 5 Sizes from 0805 to 1812 (continued)

CAP.	Last 3-digit of	Last 2-digit of	0805			1206			1210		1812
	12NC	12NC	16 V	25 V	50 V	16 V	25 V	50 V	25 V	50 V	50 V
120 pF	121	37									
150 pF	151	38									
180 pF	181	39									
220 pF	221	41									
270 pF	271	42									
330 pF	331	43	0.6±0.1	0.6±0.1	0.6±0.1						
390 pF	391	44	0.020.1	0.020.1	0.020.1						
470 pF	471	45									
560 pF	561	46				0.6±0.1	0.6±0.1	0.6±0.1	1.25±0.2	1.25±0.2	
680 pF	681	47									
820 pF	821	48									
I.O nF	102	49									
1.2 nF	122	51									
1.5 nF	152	52		0.85±0.1 1.25±0.2							
1.8 nF	182	53									
2.2 nF	222	54									
2.7 nF	272	55									1.25±0.2
3.3 nF	332	56									
3.9 nF	392	57									
4.7 nF	472	58	1.25±0.2	1.25±0.2	1.25±0.2	0.85±0.1	0.85±0.1	0.85±0.1			
5.6 nF	562	59							1.0±0.15	1.0±0.15	
6.8 nF	682	61									
8.2 nF	822	62									
10 nF	103	63					125102	125102			
12 nF	123	64				125.02	1.25±0.2	1.25±0.2			
15 nF	153	65				1.25±0.2			1.25±0.2	1.25±0.2	
18 nF	183	66									
22 nF	223	67							2.0±0.2	2.0±0.2	
33 nF	333	69				1.6±0.2					

- 1. Values in shaded cells indicate thickness class in mm
- 2. Capacitance value of non E-12 series is on request
- 3. 16V to 25V, refer to last 2-digit of 12NC
- 4. 50V, refer to last 3-digit of I2NC



# THICKNESS CLASSES AND PACKING QUANTITY

SIZE	THICKNESS	TAPE WIDTH –	Ø180 MM	/7 INCH	Ø330 MM /	/ 13 INCH	QUANTITY
CODE	CLASSIFICATION	QUANTITY PER REEL	Paper	Blister	Paper	Blister	PER BULK CASE
0201	0.3 ±0.03 mm	8 mm	15,000		50,000		
0402	0.5 ±0.05 mm	8 mm	10,000		50,000		50,000
0603	0.8 ±0.1 mm	8 mm	4,000		15,000		15,000
	0.6 ±0.1 mm	8 mm	4,000		20,000		10,000
0805	0.85 ±0.1 mm	8 mm	4,000		15,000		8,000
	1.25 ±0.2 mm	8 mm		3,000		10,000	5,000
	0.6 ±0.1 mm	8 mm	4,000		20,000		
_	0.85 ±0.1 mm	8 mm	4,000		15,000		
1206	1.00 / 1.15 ±0.1 mm	8 mm		3,000		10,000	
1206	1.25 ±0.2 mm	8 mm		3,000		10,000	
	1.6 ±0.15 mm	8 mm		2,500		10,000	
	1.6 ±0.2 mm	8 mm		2,000		10,000	
	0.6 / 0.7 ±0.1 mm	8 mm		4,000		15,000	
_	0.85 ±0.1 mm	8 mm		4,000		10,000	
_	1.0 ±0.1 mm	8 mm		3,000		10,000	
_	1.15 ±0.1 mm	8 mm		3,000		10,000	
_	1.15 ±0.15 mm	8 mm		3,000		10,000	
1210	1.25 ±0.2 mm	8 mm		3,000			
	1.5 ±0.1 mm	8 mm		2,000			
_	1.6 / 1.9 ±0.2 mm	8 mm		2,000			
_	2.0 ±0.2 mm	8 mm		2,000 1,000			
	2.5 ±0.2 mm	8 mm		1,000 500			
_	1.15 ±0.15 mm	I2 mm		3,000			
	1.25 ±0.2 mm	I2 mm		3,000			
1808	1.35 ±0.15 mm	I2 mm		2,000			
1000	1.5 ±0.1 mm	I2 mm		2,000			
	1.6 ±0.2 mm	I2 mm		2,000			
	2.0 ±0.2 mm	I2 mm		2,000			
_	0.6 / 0.85 ±0.1 mm	I2 mm		2,000			
_	1.15 ±0.1 mm	I2 mm		1,000			
	1.15 ±0.15 mm	I2 mm		1,000			
1812	1.35 ±0.15 mm	I2 mm		1,000			
1012	1.5 ±0.1 mm	12 mm		1,000			
	1.6 ±0.2 mm	12 mm		1,000			
	2.0 ±0.2 mm	I2 mm		1,000			
	2.5 ±0.2 mm	12 mm		500			

15


#### **ELECTRICAL CHARACTERISTICS**


# NP0 DIELECTRIC CAPACITORS; NISN TERMINATIONS


Unless otherwise stated all electrical values apply at an ambient temperature of 20±1 °C, an atmospheric pressure of 86 to 106 kPa, and a relative humidity of 63 to 67%.

_	_			-
	la	bl	le	1

Table 7		
DESCRIPTION		VALUE
Capacitance range		0.22 pF to 33 nF
Capacitance tolerance		
	C < 10 pF	±0.1 pF, ±0.25 pF, ±0.5 pF
	C ≥ 10 pF	±1%, ±2%, ±5%
Dissipation factor (D.F.	)	
	C < 30 pF	≤ I / ( 400 + 20C )
	C ≥ 30 pF	≤ 0.1 %
Insulation resistance aft	ter I minute at U <sub>r</sub> (DC)	$R_{ins} \ge 10 \text{ G}\Omega$ or $R_{ins} \times C_r \ge 500$ seconds whichever is less
Maximum capacitance of	change as a function of temperature	
(temperature character	ristic/coefficient):	±30 ppm/°C
Operating temperature	e range:	_55 °C to +125 °C







# SOLDERING RECOMMENDATION

Table 8

SOLDERING METHOD	SIZE 0402	0603	0805	1206	≥ 1210
Reflow	≥ 0.1 µF	≥ 1.0 µF	≥ 2.2 µF	≥ 4.7 µF	Reflow only
Reflow/Wave	< 0.1 µF	< 1.0 µF	< 2.2 µF	< 4.7 µF	

16 V to 50 V

# TESTS AND REQUIREMENTS

**Table 9** Test procedures and requirements

TEST	TEST METH	HOD	PROCEDURE	REQUIREMENTS
Mounting	IEC 60384- 21/22	4.3	The capacitors may be mounted on printed-circuit boards or ceramic substrates	No visible damage
Visual inspection and dimension check		4.4	Any applicable method using × 10 magnification	In accordance with specification
Capacitance		4.5.1	Class I: $f = I \text{ MHz for C} \le I \text{ nF, measuring at voltage } I \text{ V}_{rms} \text{ at } 20 \text{ °C}$ $f = I \text{ KHz for C} > I \text{ nF, measuring at voltage } I \text{ V}_{rms} \text{ at } 20 \text{ °C}$	Within specified tolerance
Dissipation factor (D.F.)		4.5.2	Class I: $f = I \text{ MHz for C} \le I \text{ nF , measuring at voltage } I \text{ V}_{rms} \text{ at } 20 \text{ °C}$ $f = I \text{ KHz for C} > I \text{ nF, measuring at voltage } I \text{ V}_{rms} \text{ at } 20 \text{ °C}$	In accordance with specification
Insulation resistance		4.5.3	At U <sub>r</sub> (DC) for I minute	In accordance with specification
Temperature coefficient		4.6	Class 1:  Between minimum and maximum temperature  NP0: -55 °C to +125 °C  Normal Temperature: 20 °C	<general purpose="" series=""> ΔC/C: Class I: NP0: ±30 ppm/°C</general>
Adhesion		4.7	A force applied for 10 seconds to the line joining the terminations and in a plane parallel to the substrate	Force size ≥ 0603: 5N size = 0402: 2.5N size = 0201: 1N
Bond strength of		4.8	Mounting in accordance with IEC 60384-22 paragraph 4.3	No visible damage
plating on end face			Conditions: bending I mm at a rate of I mm/s, radius jig 340 mm	<pre><general purpose="" series=""> ΔC/C Class 1: NP0: within ±1% or 0.5 pF whichever is greater</general></pre>

TEST	TEST METI	HOD	PROCEDURE	REQUIREMENTS	
Resistance to soldering heat	IEC 60384- 21/22	4.9	Precondition: 150 +0/−10 °C for I hour, then keep for 24 ±1 hours at room temperature  Preheating: for size ≤ 1206: 120 °C to 150 °C for I minute  Preheating: for size >1206: 100 °C to 120 °C for I minute and 170 °C to 200 °C for I minute	Dissolution of the end face plating shal not exceed 25% of the length of the edge concerned	
				<general purpose="" series=""></general>	
			Solder bath temperature: 260 ±5 °C	ΔC/C	
			Dipping time: 10 ±0.5 seconds	Class I:	
			Recovery time: 24 ±2 hours	NP0: within ±0.5% or 0.5 pF	
			recovery time. 21 12 hours	whichever is greater	
			-	D.F. within initial specified value	
				R <sub>ins</sub> within initial specified value	
Solderability		4.10	Preheated the temperature of 80 °C to 140 °C and maintained for 30 seconds to 60 seconds.	The solder should cover over 95% of the critical area of each termination	
			Test conditions for lead containing solder alloy		
			Temperature: 235 ±5 °C		
			Dipping time: 2 ±0.2 seconds		
			Depth of immersion: 10 mm		
			Alloy Composition: 60/40 Sn/Pb		
			Number of immersions: I		
			Test conditions for lead-free containing solder alloy		
			Temperature: 245 ±5 °C		
			Dipping time: 3 ±0.3 seconds		
			Depth of immersion: 10 mm		
			Alloy Composition: SAC305		
			Number of immersions: I		
Rapid change		4.11	Preconditioning;	No visual damage	
of			150 +0/-10 °C for I hour, then keep for		
temperature			24 ±1 hours at room temperature	<general purpose="" series=""></general>	
			5 cycles with following detail:	ΔC/C	
			30 minutes at lower category temperature	Class 1:	
			30 minutes at upper category temperature	NP0: within ±1% or 1 pF	
			Recovery time 24 ±2 hours	whichever is greater	
			-	D.F. meet initial specified value	
				R <sub>ins</sub> meet initial specified value	

# Surface-Mount Ceramic Multilayer Capacitors General Purpose NPO

16 V to 50 V

TEST	TEST METHOD		PROCEDURE	REQUIREMENTS
Damp heat with U <sub>r</sub> load	IEC 60384- 21/22	4.13	1. Preconditioning, class 2 only:  150 +0/-10 °C /I hour, then keep for  24 ±1 hour at room temp  2. Initial measure:  Spec: refer to initial spec C, D, IR  3. Damp heat test:  500 ±12 hours at 40 ±2 °C;  90 to 95% R.H. 1.0 U <sub>r</sub> applied  4. Recovery:  Class I: 6 to 24 hours  5. Final measure: C, D, IR  P.S. If the capacitance value is less than the minimum value permitted, then after the other measurements have been made the capacitor shall be preconditioned according to "IEC 60384 4.1" and then the requirement shall be met.	No visual damage after recovery
Endurance		4.14	<ol> <li>Preconditioning, class 2 only:         <ul> <li>150 +0/-10 °C /1 hour, then keep for</li> <li>24 ±1 hour at room temp</li> </ul> </li> <li>Initial measure:         <ul> <li>Spec: refer to initial spec C, D, IR</li> </ul> </li> <li>Endurance test:         <ul> <li>Temperature: NP0: 125 °C</li> <li>Specified stress voltage applied for 1,000 hours:</li></ul></li></ol>	No visual damage
Voltage proof	IEC 60384-1	4.6	Specified stress voltage applied for 1 minute $U_r \le 100 \text{ V}$ : series applied 2.5 $U_r$ $100 \text{ V} < U_r \le 200 \text{ V}$ series applied (1.5 $U_r + 100$ ) $200 \text{ V} < U_r \le 500 \text{ V}$ series applied (1.3 $U_r + 100$ ) $U_r > 500 \text{ V}$ : 1.3 $U_r$ 1: 7.5 mA	No breakdown or flashover

16 V to 50 V

# REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 8	Aug 05, 2011		- Product range updated
Version 7	Jun 14, 2011		- Size1210 T=1,0mm SPQ added
		-	- Dimension updated
Version 6	Jan 06, 2011	-	- Dimension updated
Version 5	Dec 29, 2010	-	- Dimension updated
Version 4	Nov 23, 2010	-	- Dimension updated
Version 3	Apr 20, 2010	-	- The statement of "Halogen Free" on the cover added
			- Dimension updated
Version 2	Oct 26, 2009	-	- Typo updated
Version I	Jun 02, 2009	-	- I2NC code updated
Version 0	Apr 15, 2009	-	- New datasheet for general purpose NP0 series with RoHS compliant
			- Replace the "16V to 50V" part of pdf files: NP0_16V_7, NP0_16V-to-100V_6, NP0_25V_7, NP0_50-to-500V_11
			- Combine 0201 from pdf files: UP-NP0X5RX7RY5V_0201_6.3-to-50V_2 and UY-NP0X5RX7RY5V_0201_6.3-to-50V_2
			- Define global part number
			- Description of "Halogen Free compliant" added
			- Test method and procedure updated

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Yageo:

```
CC0603BRNPO9BNR60 CC1206JRNPO9BN393 CC0603FRNPO9BN910 CC0603BRNPO9BN7R0
CC0603BRNPO9BNR90 CC0201BRNPO9BN9R5 CC0201BRNPO8BN3R0 CC0603CRNPO9BNR80
CC0805CRNPO9BN5R1 CC1206DRNPO9BN7R5 CC1206CRNPO9BN3R0 CC0603BRNPO9BN8R0
CC1206JRNPO9BN750 CC0603BRNPO9BN2R5 CC0201GRNPO9BN200 CC0603FRNPO9BN241
CC0100CRNPO7BN2R0 CC0100CRNPO7BN5R0 CC0100CRNPO7BN3R0 CC0100CRNPO7BN2R4
CC0100CRNPO7BN7R0 CC0100CRNPO7BN4R0
                                    CC0100BRNPO7BNR50 CC0100CRNPO7BN8R0
CC0100JRNPO7BN300 CC0603CRNPO9BN4R5 CC0603FRNPO9BN511 CC0603GRNPO9BN301
CC0805JRNPO9BN562 CC0603FRNPO9BN111 CC0805FRNPO9BN621 CC1812JKNPO9BN752
CC0805GRNPO9BN510 CC0603JRNPO8BN300 CC0805BRNPO9BN3R0 CC0603BRNPO9BN4R3
CC0805FRNPO9BN301 CC0805GRNPO9BN910 CC1206JRNPO8BN751 CC0805GRNPO9BN750
CC1206BRNPO9BNR50 CC0805BRNPO9BN5R1
                                    CC0603FRNPO9BN431 CC0805CRNPO9BNR75
CC1206JRNPO9BN362 CC0805BRNPO9BN2R0 CC0805GRNPO9BN620 CC0201GRNPO8BN160
CC0805BRNPO9BN9R1 CC0805DRNPO9BN7R2 CC0805CRNPO9BN2R5 CC1206CRNPO9BN5R0
CC1206FRNPO9BN362 CC0603DRNPO9BN9R1 CC0402CRNPO9BN1R6 CC0603BRNPO9BN9R0
CC0805CRNPO9BN6R2 CC0603BRNPO9BN1R1 CC0201JRNPO9BN300 CC1206JKNPO9BN153
CC0603BRNPO9BN6R0 CC0201FRNPO8BN160 CC0603GRNPO9BN111 CC0402GRNPO9BN130
CC1206JRNPO9BN201 CC0805JRNPO9BN140
```

# YAGEO:

CC0805JRNPO9BN131 CC0201JRNPO7BN330