

AC and Pulse Metallized Polypropylene Film Capacitors KP/MKP Radial Lacquered Type



Dimensions in mm

(1) Hole $\varnothing$ 1.3 for $d_t = 0.8$ mm

(2) $0 \leq \alpha < 50^\circ$

(3) $|F - F'| < 0.3$ mm

$F = 7.5 + 0.6 / - 0.1$ mm

(4) $A = 2.0 + 1.0 / - 0.5$ mm for 10 mm pitch

$A = 2.5 + 1.5 / - 0.5$ mm for 15 mm pitch

$A = 2.5 + 1.4 / - 0.5$ mm for pitch > 22.5 mm



Dimensions in mm

APPLICATIONS

Where high currents and steep pulses occur. For deflection circuits in television sets.

REFERENCE SPECIFICATIONS

IEC 60384-17

MARKING

C-value; tolerance; rated voltage; manufacturer's type; manufacturer's location

DIELECTRIC

Polypropylene film

ELECTRODES

Metallized and aluminum

CONSTRUCTION

Internal serial construction

RATED (DC) VOLTAGE

630 V, 1000 V, 1600 V, 2000 V

RATED (AC) VOLTAGE

300 V, 400 V, 500 V, 600 V

RATED PEAK-TO-PEAK VOLTAGE

850 V, 1100 V, 1400 V, 1700 V

FEATURES

- 10 mm to 27.5 mm pitch
- Supplied loose in box (including lock lead versions) and taped
- Bent back version for automatic insertion available
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

ENCAPSULATION

Flame retardant epoxy material
(Class UL 94 V-0)

CLIMATIC TESTING CLASS ACCORDING TO IEC 60068-1

55/105/56

CAPACITANCE RANGE (E24 SERIES)

0.1 nF to 270 nF

CAPACITANCE TOLERANCE

$\pm 5\%$; $\pm 3.5\%$

LEADS

Tinned wire

RATED TEMPERATURE

85 °C

MAXIMUM APPLICATION TEMPERATURE

105 °C

PERFORMANCE GRADE

for $C > 5.6$ nF: grade 1 (long life)

for $C \leq 5.6$ nF: grade 2

STABILITY GRADE

Grade 2


DETAIL SPECIFICATION

For more detailed data and test requirements contact:

dc-film@vishay.com



COMPOSITION OF CATALOG NUMBER



TYPE	PACKAGING	LEAD CONFIGURATION	PREFERRED TYPES				
			C-TOL.	630 V	1000 V	1600 V	2000 V
375	Loose in box	Lead length 5.0 mm ± 1.0 mm	± 5 %	14	24	34	44
		Lock lead 4.0 mm + 1.0/- 0.5 mm	± 5 %	90	90	90	90
	Taped on reel ⁽²⁾ (bent back)	H = 16.0 mm; P ₀ = 15.0 mm; Reel diameter 500 mm	± 5 %	16	26	36	46
Dimensions of this code numbers stays between brackets							
ON REQUEST							
375	Loose in box	Lead length 5.0 ± 1.0 mm	± 3.5 %	15	25	35	45
		Lead length 3.5 ± 0.5 mm	± 5 %	10	20	30	40
			± 3.5 %	11	21	31	41
	Taped on reel ⁽²⁾	H = 16.0 mm; P ₀ = 12.7 mm; Reel diameter = 500 mm	± 5 %	12	22	32	42
			± 3.5 %	13	23	33	43
				17	27	37	47
	Taped on reel ⁽²⁾ (bent back)	H = 16.0 mm; P ₀ = 15.0 mm; Reel diameter = 500 mm	± 3.5 %	Dimensions of this code numbers stays between brackets			
		H = 16.0 mm; P ₀ = 15.0 mm; Reel diameter = 356 mm	± 5 %	18	28	38	48

Note

⁽²⁾ For detailed tape specifications refer to "Packaging Information" www.vishay.com/doc?28139 or end of catalog

SPECIFIC REFERENCE DATA (630 V_{DC})

DESCRIPTION	VALUE	
Tangent of loss angle at (x 10 ⁻⁴)	10 kHz	100 kHz
Pitch = 10 mm, 15 mm, and 7.5 mm (bent back)	≤ 6	≤ 10
Pitch = 22.5 mm	≤ 8	≤ 15
Pitch = 27.5 mm	≤ 8	≤ 20
Rated voltage pulse slope (dU/dt) _R :		
Pitch = 10 mm	15 000 V/μs	
Pitch = 15 mm and 7.5 mm (bent back)	8000 V/μs	
Pitch = 22.5 mm	2800 V/μs	
Pitch = 27.5 mm	1900 V/μs	
R between leads at 500 V, 1 min	> 100 000 MΩ	
R between interconnected leads and case, 500 V, 1 min	> 100 000 MΩ	
Ionization (AC) voltage (typical value) at 50 pC peak discharge at 50 pC peak discharge at 20 pC peak discharge	> 400 V	
Withstanding (DC) voltage (cut off current 10 mA), rise time 1000 V/s for C ≤ 47 nF for C > 47 nF	1008 V, 1 min	
Withstanding (DC) voltage between leads and case	2840 V, 1 min	
Maximum application temperature	105 °C	



$U_{RDC} = 630 \text{ V}$; $U_{RAC} = 300 \text{ V}$; $U_{PP} = 850 \text{ V (KINKED)}$; $C\text{-TOL.} = \pm 5 \%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING				
			LEADS 5 mm ± 1.0 mm	REEL			C VALUE ..YYY
				ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		
				Ø 500 mm	Ø 500 mm	Ø 356 mm	
			XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	
C (pF)	PITCH = 10.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm		PITCH = 10.0 mm	PITCH = 7.5 mm (BENT BACK)			
680 750	5.0 x 13.0 x 14.5	0.65	14... (2000)	12... (1200)			681 751
820 910 1000	5.5 x 13.5 x 14.5	0.70	14... (2000)	12... (1100)			821 911 102
1100 1200 1300		0.75					112 122 132
1500 1600		0.80 0.85					152 162
1800 2000 2200 2400		0.80 0.85 0.90 1.0					14... (1750)
2700	6.5 x 14.5 x 14.5	1.1	14... (1500)	12... (900)			272

Notes

- SPQ = Standard Packing Quantity

⁽¹⁾ Net weight for short lead product only



$U_{RDC} = 630 \text{ V}$; $U_{RAC} = 300 \text{ V}$; $U_{PP} = 850 \text{ (KINKED)}$; $C\text{-TOL.} = \pm 5 \%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING				
			LOOSE IN BOX	REEL			C VALUE
				LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)	
					XX (SPQ)	Ø 500 mm	Ø 500 mm
C (pF)	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm			PITCH = 7.5 mm (BENT BACK)			
3000 3300	5.0 x 14.0 (16.0) x 18.5	1.0	14... (2000)	12... (1200)	16... (1000)	18... (550)	302 332
3600 3900 4300 4700 5100 5600	5.5 x 14.5 (16.0) x 18.5	1.1	14... (2000)	12... (1100)	16... (900)	18... (500)	362 392 432 472 512 562
6200 6800 7500 8200 9100 10 000 11 000 12 000 13 000 15 000 16 000	6.0 x 15.0 (16.0) x 18.5	1.2	14... (2000)	12... (1000)	16... (800)	18... (450)	622 682 752 822 912 103 113 123 133 153 163
18 000 20 000	6.5 x 15.5 (17.0) x 18.5	1.3	14... (1500)	12... (900)	16... (750)	18... (400)	183 203
22 000	7.0 x 16.0 (17.5) x 18.5	1.5	14... (1500)	12... (800)	16... (700)	18... (400)	223
24 000	7.5 x 16.5 (18.0) x 18.5	1.6	14... (1250)	12... (800)	16... (650)	18... (350)	243
27 000 30 000	8.0 x 17.0 (18.5) x 18.5	1.9	14... (1250)	12... (750)	16... (600)	18... (350)	273 303
33 000	8.5 x 17.5 (19.0) x 18.5	2	14... (1000)	12... (700)	16... (550)	18... (300)	333
36 000 39 000	9.0 x 18.5 (20.0) x 18.5	2.3	14... (900)	12... (600)	16... (500)	18... (300)	On request
C (µF)	PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 22.5 mm	PITCH = 7.5 mm (BENT BACK)			
0.036 0.039 0.043 0.047 0.051 0.056 0.062	7.0 x 20.0 x 26.0	2.7	14... (650)	-	-	-	363 393 433 473 513 563 623
0.068	7.5 x 20.5 x 26.0	3	14... (600)	-	-	-	683
0.075 0.082	8.0 x 21.0 x 26.0	3.3	14... (550)	-	-	-	753 823
0.091	8.5 x 21.5 x 26.0	3.8	14... (500)	-	-	-	913
0.1	9.0 x 22.0 x 26.0	4	14... (450)	-	-	-	104

Notes

- SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only



$U_{RDC} = 630 \text{ V}$; $U_{RAC} = 300 \text{ V}$; $U_{PP} = 850 \text{ (KINKED)}$; $C\text{-TOL.} = \pm 5 \%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING				
			LOOSE IN BOX	REEL			C VALUE
			LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		..YYY
				Ø 500 mm	Ø 500 mm	Ø 356 mm	
			XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	
C (µF)	PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 22.5 mm	PITCH = 7.5 mm (BENT BACK)			
0.11	9.5 x 22.5 x 26.0	4.3	14... (400)	-	-	-	114
0.12	10.0 x 23.0 x 26.0	4.7	14... (400)				124
C (µF)	PITCH = 27.5 mm ± 0.5 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 27.5 mm	PITCH = 7.5 mm (BENT BACK)			
0.13	9.5 x 22.5 x 30.0	4.7	14... (500)	-	-	-	134
0.15	10.0 x 23.0 x 30.0	5.2	14... (500)				154
0.16	10.5 x 23.5 x 30.0	5.5	14... (450)				164
0.18	11.0 x 24.0 x 30.0	6	14... (400)				184
0.2	11.5 x 24.5 x 30.0	6.6	14... (400)				204
0.22	12.5 x 25.5 x 30.0	7.1	14... (350)				224
0.24	13.0 x 26.0 x 30.0	7.7	14... (300)				244
0.27	13.5 x 26.5 x 30.0	8.5	14... (300)				274

Notes

- Loose in box, all lengths have same SPQ
- SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only

$U_{RDC} = 630 \text{ V}$; $U_{RAC} = 300 \text{ V}$; $U_{PP} = 850 \text{ V (LOCK LEAD)}$; $C\text{-TOL.} = \pm 5 \%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING	
			LOOSE IN BOX	
			$l_t = 4.0 \text{ mm} + 1.0 \text{ mm/- } 0.5 \text{ mm}$	
			(SPQ)	
C (pF)			PITCH = 10.0 mm $\pm$ 1.0 mm; $d_t = 0.60 \text{ mm} \pm 0.06 \text{ mm}$	
680 750	5.0 x 16.0 x 14.5	0.65	90308 90309	(2000)
820 910 1000 1100 1300 1500 1600	5.5 x 16.5 x 14.5	0.7 0.7 0.7 0.75 0.75 0.80 0.85	90311 90312 90313 90314 90316 90317 90318	(2000)
1800 2000 2200 2400	6.0 x 17.0 x 14.5	0.80 0.85 0.90 1.0	90319 90321 90322 90323	(1750)
2700	6.5 x 17.5 x 14.5	1.1	90324	(1500)

Notes

- SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only



$U_{RDC} = 630 \text{ V}$; $U_{RAC} = 300 \text{ V}$; $U_{PP} = 850 \text{ V (LOCK LEAD)}$; $C\text{-TOL.} = \pm 5 \%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING	
			LOOSE IN BOX	
			l _t = 4.0 mm + 1.0 mm/- 0.5 mm	
			(SPQ)	
C (pF)	PITCH = 15.0 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
3000 3300	5.0 x 17.0 x 18.5	1	90325 90326	(2000)
3600 3900 4300 4700 5100 5600	5.5 x 17.5 x 18.5	1.1	90327 90328 90329 90331 90332 90333	(2000)
6200 6800 7500 8200 9100 10 000 11 000 12 000 13 000 15 000 16 000	6.0 x 18.0 x 18.5	1.3	90334 90335 90336 90337 90338 90339 90236 90341 90342 90343 90344	(2000)
18 000 20 000	6.5 x 18.5 x 18.5	1.4	90218 90345	(1750)
22 000	7.0 x 19.0 x 18.5	1.5	90219	(1500)
24 000	7.5 x 19.5 x 18.5	1.6	90221	(1400)
27 000 30 000	8.0 x 20.0 x 18.5	1.9	90223 90346	(1250)
33 000	8.5 x 20.5 x 18.5	2	90347	(1200)
36 000 39 000	9.0 x 21.5 x 18.5	2.3	On request	(1000)
C (µF)	PITCH = 22.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.036 0.039 0.043 0.047 0.051 0.056 0.062	7.0 x 23.0 x 26.0	2.7	90348 90349 90351 90352 90353 90354 90355	(600)
0.068	7.5 x 23.5 x 26.0	3	90356	(550)
0.075 0.082	8.0 x 24.0 x 26.0	3.3	90357 90358	(500)
0.091	8.5 x 24.5 x 26.0	3.8	90359	(450)



C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XYYYY AND PACKAGING	
			LOOSE IN BOX	
			l _t = 4.0 mm + 1.0 mm/- 0.5 mm	
				(SPQ)
C (μF)	PITCH = 22.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.1	9.0 x 25.0 x 26.0	4.0	90361	(450)
0.11	9.5 x 25.5 x 26.0	4.3	90362	(400)
0.12	10.0 x 26.0 x 26.0	4.7	90363	(350)
C (μF)	PITCH = 27.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.13	9.5 x 25.5 x 30.0	4.7	90364	(450)
0.15	10.0 x 26.0 x 30.0	5.2	90365	(400)
0.16	10.5 x 26.5 x 30.0	5.5	90366	(350)
0.18	11.0 x 27.0 x 30.0	6.0	90367	(350)
0.2	11.5 x 27.5 x 30.0	6.6	90368	(350)
0.22	12.5 x 28.5 x 30.0	7.1	90369	(300)
0.24	13.0 x 29.0 x 30.0	7.7	90371	(250)
0.27	13.5 x 29.5 x 30.0	8.5	90372	(250)

Notes

- SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only

SPECIFIC REFERENCE DATA (1000 V_{DC})

DESCRIPTION	VALUE	
Tangent of loss angle at (x 10 ⁻⁴)	10 kHz	100 kHz
Pitch = 10 mm, 15 mm, and 7.5 mm (bent back)	≤ 6	≤ 10
Pitch = 22.5 mm	≤ 8	≤ 15
Pitch = 27.5 mm	≤ 8	≤ 20
Rated voltage pulse slope (dU/dt):		
Pitch = 10 mm	27 000 V/μs	
Pitch = 15 mm and 7.5 mm (bent back)	15 000 V/μs	
Pitch = 22.5 mm	5000 V/μs	
Pitch = 27.5 mm	3300 V/μs	
R between leads at 500 V, 1 min	> 100 000 MΩ	
R between interconnected leads and case, 500 V, 1 min	> 100 000 MΩ	
Ionization (AC) voltage (typical value)		
at 50 pC peak discharge	> 500 V	
at 20 pC peak discharge		
Withstanding (DC) voltage (cut off current 10 mA), rise time 1000 V/s		
for C ≤ 47 nF	1600 V, 1 min	
for C > 47 nF	[1.6 - (0.0364 x (C - 47))] x 1000 V, 1 min	
Withstanding (DC) voltage between leads and case	2840 V, 1 min	
Maximum application temperature	105 °C	



$U_{RDC} = 1000 \text{ V}$; $U_{RAC} = 400 \text{ V}$; $U_{PP} = 1100 \text{ V (KINKED)}$; $C\text{-TOL.} = \pm 5 \%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XYYYY AND PACKAGING				C VALUE	
			LOOSE IN BOX	REEL				..YYY
				LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		
					XX (SPQ)	Ø 500 mm	Ø 500 mm	
			XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)		
C (pF)	PITCH = 10.0 mm ± 0.4 mm; d _t = 0.60 mm ± 0.06 mm		PITCH = 10.0 mm		PITCH = 7.5 mm (BENT BACK)			
100	5.0 x 13.0 x 14.5	0.5	24... (2000)	22... (1200)	-	-	101	
110							111	
120							121	
130							131	
150							151	
160	5.5 x 13.5 x 14.5	0.55	24... (2000)	22... (1100)	-	-	161	
180		0.55					181	
200		0.55					201	
220		0.60					221	
240		0.60					241	
270		0.60					271	
300		0.60					301	
330		0.60					331	
360		0.60					361	
390		0.65					391	
430		0.70					431	
470		0.75					471	
510		0.75					511	
560		0.80					561	
620		0.80					621	
680		0.80					681	
750		0.70					751	
820		0.70					821	
910		0.70					911	
1000	6.0 x 14.0 x 14.5	0.75	24... (1750)	22... (1000)	-	-	102	
1100		0.85					112	
1200		0.90					122	
1300		0.85					132	
1500		0.90					152	
C (pF)	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 15.0 mm		PITCH = 7.5 mm (BENT BACK)			
1600	5.5 x 14.5 (16.0) x 18.5	1.1	24... (2000)	22... (1100)	26... (900)	28... (500)	162	
1800							182	
2000							202	
2200							222	
2400							242	
2700	6.0 x 15.0 (16.5) x 18.5	1.2	24... (2000)	22... (1000)	26... (800)	28... (450)	272	
3000							302	
3300							332	
3600							362	
3900							392	
4300							432	
4700							472	
5100							512	
5600							562	

Notes

- Loose in box, all lengths have same SPQ
- SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only



$U_{RDC} = 1000\text{ V}$; $U_{RAC} = 400\text{ V}$; $U_{PP} = 1100\text{ V (KINKED)}$; $C\text{-TOL.} = \pm 5\%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING				
			LOOSE IN BOX	REEL			C VALUE
			LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		..YYY
				Ø 500 mm	Ø 500 mm	Ø 356 mm	
			XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	
C (pF)	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 15.0 mm	PITCH = 7.5 mm (BENT BACK)			
6200 6800	6.0 x 15.0 (16.5) x 18.5	1.2	24... (2000)	22... (1000)	26... (800)	28... (450)	622 682
7500 8200 9100	7.0 x 16.0 (17.5) x 18.5	1.4	24... (1500)	22... (800)	26... (700)	28... (400)	752 822 912
10 000	7.5 x 16.5 (18.0) x 18.5	1.6	24... (1250)	22... (800)	26... (650)	28... (350)	103
11 000 12 000	8.0 x 17.0 (18.5) x 18.5	1.8	24... (1250)	22... (750)	26... (600)	28... (350)	113 123
13 000	8.5 x 17.5 (19.0) x 18.5	1.9	24... (1000)	22... (700)	26... (550)	28... (300)	133
15 000	9.0 x 18.5 (19.5) x 18.5	2.1	24... (1000)	22... (650)	26... (550)	28... (300)	153
C (µF)	PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 22.5 mm	PITCH = 7.5 mm (BENT BACK)			
0.016 0.018	6.0 x 19.0 x 26.0	2.2	24... (800)	-	-	-	163 183
0.02 0.022	6.5 x 19.5 x 26.0	2.5	24... (750)				203 223
0.024	7.0 x 20.0 x 26.0	2.7	24... (650)				243
0.027 0.03	7.5 x 20.5 x 26.0	3.1	24... (600)				273 303
0.033	8.0 x 21.0 x 26.0	3.4	24... (550)				333
0.036 0.039	8.5 x 21.5 x 26.0	3.7	24... (500)				363 393
0.043	9.0 x 22.0 x 26.0	4.1	24... (450)				433
C (µF)	PITCH = 27.5 mm ± 0.5 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 27.5 mm	PITCH = 7.5 mm (BENT BACK)			
0.047	7.0 x 20.0 x 30.0	3.1	24... (1000)	-	-	-	473
0.051 0.056	7.5 x 20.5 x 30.0	3.4	24... (750)				513 563
0.062	8.0 x 21.0 x 30.0	3.8	24... (650)				623
0.068	8.5 x 21.5 x 30.0	4.0	24... (550)				683
0.075	9.0 x 22.0 x 30.0	4.4	24... (550)				753
0.082	9.5 x 22.5 x 30.0	4.7	24... (500)				823
0.091	10.0 x 23.0 x 30.0	5.1	24... (500)				913
0.10	10.5 x 23.5 x 30.0	5.5	24... (450)				104
0.11	11.0 x 24.0 x 30.0	5.9	24... (400)				114
0.12	11.5 x 24.5 x 30.0	6.3	24... (400)				124
0.13	12.0 x 25.0 x 30.0	6.8	24... (350)				134
0.15	12.5 x 25.5 x 30.0	7.6	24... (350)				154

Notes

- Loose in box, all lengths have same SPQ
- SPQ = Standard Packing Quantity

⁽¹⁾ Net weight for short lead product only



$U_{RDC} = 1000\text{ V}$; $U_{RAC} = 400\text{ V}$; $U_{PP} = 1100\text{ V}$ (LOCK LEAD); $C\text{-TOL.} = \pm 5\%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING	
			LOOSE IN BOX	
			l _t = 4.0 mm + 1.0 mm/- 0.5 mm	
				(SPQ)
C (pF)	PITCH = 10.0 mm ± 1.0 mm; d _t = 0.60 mm ± 0.06 mm			
100	5.0 x 16.0 x 14.5	0.5	90373	(2000)
110			90374	
120			90375	
130			90376	
150	5.5 x 16.5 x 14.5	0.55	90377	(2000)
160		0.55	90378	
180		0.55	90379	
200		0.55	90281	
220		0.60	90382	
240		0.60	90383	
270		0.60	90384	
300		0.60	90385	
330		0.60	90386	
360		0.60	90387	
390		0.65	90388	
430		0.70	90389	
470		0.75	90391	
510		0.75	90392	
560		0.80	90393	
620		0.80	90394	
680		0.80	90395	
750		0.70	90396	
820		0.70	90397	
910		0.70	90398	
1000	6.0 x 17.0 x 14.5	0.75	90399	(1750)
1100		0.85	90401	
1200		0.90	90402	
1300		0.85	90403	
1500		0.90	90404	
C (pF)	PITCH = 15.0 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
1600	5.5 x 17.5 x 18.5	1.1	90405	(2000)
1800			90406	
2000			90407	
2200			90408	
2400			90409	
2700	6.0 x 18.0 x 18.5	1.2	90411	(2000)
3000			90412	
3300			90413	
3600			90414	
3900			90415	
4300			90416	
4700			90417	
5100			90418	
5600			90419	
6200			90421	
6800			90422	



C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XYYYY AND PACKAGING	
			LOOSE IN BOX	
			l _t = 4.0 mm + 1.0 mm/- 0.5 mm	
			(SPQ)	
C (pF)	PITCH = 15.0 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
7500 8200 9100	7.0 x 19.0 x 18.5	1.5	90232 90423 90424	(1500)
10 000	7.5 x 19.5 x 18.5	1.6	90425	(1400)
11 000 12 000	8.0 x 20.0 x 18.5	1.8	90426 90427	(1250)
13 000	8.5 x 20.5 x 18.5	1.9	90428	(1200)
15 000	9.0 x 21.0 x 18.5	2.1	90429	(1100)
C (μF)	PITCH = 22.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.016 0.018	6.0 x 22.0 x 26.0	2.2	90431 90432	(750)
0.02 0.022	6.5 x 22.5 x 26.0	2.5	90433 90434	(700)
0.024	7.0 x 23.0 x 26.0	2.7	90435	(600)
0.027 0.03	7.5 x 23.5 x 26.0	3.1	90436 90437	(550)
0.033	8.0 x 24.0 x 26.0	3.4	90438	(500)
0.036 0.039	8.5 x 24.5 x 26.0	3.8	90439 90224	(450)
0.043	9.0 x 25.0 x 26.0	4.1	90441	(450)
C (μF)	PITCH = 27.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.047	7.0 x 23.0 x 30.0	3.1	90442	(800)
0.051 0.056	7.5 x 23.5 x 30.0	3.4	90443 90444	(600)
0.062	8.0 x 24.0 x 30.0	3.8	90445	(550)
0.068	8.5 x 24.5 x 30.0	4.0	90446	(550)
0.075	9.0 x 25.0 x 30.0	4.4	90447	(450)
0.082	9.5 x 25.5 x 30.0	4.7	90448	(450)
0.091	10.0 x 26.0 x 30.0	5.1	90449	(400)
0.1	10.5 x 26.5 x 30.0	5.5	90451	(350)
0.11	11.0 x 27.0 x 30.0	5.9	90452	(350)
0.12	11.5 x 27.5 x 30.0	6.3	90453	(350)
0.13	12.0 x 28.0 x 30.0	6.8	90454	(350)
0.15	12.0 x 28.5 x 30.0	7.6	90455	(300)

Notes

- SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only

**SPECIFIC REFERENCE DATA (1600 V_{DC})**

DESCRIPTION	VALUE	
Tangent of loss angle at ($\times 10^{-4}$):	10 kHz	100 kHz
Pitch = 10 mm, 15 mm and 7.5 mm (bent back)	≤ 6	≤ 10
Pitch = 22.5 mm	≤ 6	≤ 15
Pitch = 27.5 mm	≤ 6	≤ 20
Rated voltage pulse slope (dU/dt):		
Pitch = 10 mm	21 000 V/ μ s	
Pitch = 15 mm and 7.5 mm (bent back)	7000 V/ μ s	
Pitch = 22.5 mm	4700 V/ μ s	
Pitch = 27.5 mm		
R between leads at 500 V, 1 min	> 100 000 M Ω	
R between interconnected leads and case, 500 V, 1 min	> 100 000 M Ω	
Ionization (AC) voltage (typical value)		
at 50 pC peak discharge	> 550 V	
at 10 pC peak discharge		
Withstanding (DC) voltage (cut off current 10 mA), rise time 1000 V/s		
for $C \leq 47$ nF	2560 V, 1 min	
for $C > 47$ nF		
Withstanding (DC) voltage between leads and case	2840 V, 1 min	
Maximum application temperature	105 °C	

U_{RDC} = 1600 V; U_{RAC} = 500 V; U_{PP} = 1400 V (KINKED); C-TOL. = ± 5 %

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING					
			LOOSE IN BOX	REEL			C VALUE	
				LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		..YYY
					Ø 500 mm	Ø 500 mm	Ø 356 mm	
			XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)		
C (pF)	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 15.0 mm	PITCH = 7.5 mm (BENT BACK)				
680	5.5 x 14.5 (15.0) x 18.5	0.75	34... (2000)	32... (1100)	36... (900)	38... (500)	681	
750							751	
820							821	
910	6.0 x 15.0 (15.5) x 18.5	0.8	34... (2000)	32... (1000)	36... (800)	38... (450)	911	
1000		0.85					102	
1100		0.85					112	
1200		0.90					122	
1300		0.95					132	
1500	5.5 x 14.5 (16.0) x 18.5	1.1	34... (2000)	32... (1100)	36... (900)	38... (500)	152	
1600							162	
1800	6.0 x 15.0 (16.5) x 18.5	1.2	34... (2000)	32... (1000)	36... (800)	38... (450)	182	
2000	6.5 x 15.5 (17.0) x 18.5	1.3	34... (1500)	32... (900)	36... (750)	38... (400)	202	
2200							222	
2400	7.0 x 16.0 (17.5) x 18.5	1.4	34... (1500)	32... (800)	36... (700)	38... (400)	242	
2700	7.5 x 16.5 (18.0) x 18.5	1.6	34... (1250)	32... (800)	36... (650)	38... (350)	272	
3000							302	
3300	8.0 x 17.0 (18.5) x 18.5	1.7	34... (1250)	32... (750)	36... (600)	38... (350)	332	
3600	8.5 x 17.5 (19.0) x 18.5	1.8	34... (1000)	32... (700)	36... (550)	38... (300)	362	
3900	9.0 x 18.5 (19.5) x 18.5	2.0	34... (1000)	32... (650)	36... (550)	38... (300)	392	
4300							432	



C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XYYYY AND PACKAGING							
			LOOSE IN BOX	REEL			C VALUE			
				LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		..YYY		
					Ø 500 mm	Ø 500 mm	Ø 356 mm			
			XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)				
C (µF)	PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 22.5 mm	PITCH = 7.5 mm (BENT BACK)						
0.0047	6.0 x 19.0 x 26.0	2.0	34... (800)	-	-	-	472			
0.0051							512			
0.0056							562			
0.0062	6.5 x 19.5 x 26.0	2.1	34... (750)				622			
0.0068							682			
0.0075	7.0 x 20.0 x 26.0	2.3	34... (650)				752			
0.0082							822			
0.0091	7.5 x 20.5 x 26.0	2.5	34... (600)				912			
0.01	8.0 x 21.0 x 26.0	2.6	34... (550)				103			
0.011	8.5 x 21.5 x 26.0	2.9	34... (500)				113			
0.012							123			
0.013	9.0 x 22.0 x 26.0	3.1	34... (450)				133			
0.015	9.5 x 22.5 x 26.0	3.5	34... (400)				153			
0.016	10.0 x 23.0 x 26.0	3.6	34... (400)				163			
0.018	10.5 x 23.5 x 26.0	4.0	34... (350)				183			
C (µF)	PITCH = 27.5 mm ± 0.5 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 27.5 mm	PITCH = 7.5 mm (BENT BACK)						
0.02	9.0 x 22.0 x 30.0	4.2	34... (550)	-	-	-	203			
0.022	9.5 x 22.5 x 30.0	4.4	34... (500)				223			
0.024	10.0 x 23.0 x 30.0	4.7	34... (500)				243			
0.027	10.5 x 23.5 x 30.0	5.2	34... (450)				273			
0.03	11.0 x 24.0 x 30.0	5.6	34... (400)				303			
0.033	11.5 x 24.5 x 30.0	6.0	34... (400)				333			
0.036	12.0 x 25.0 x 30.0	6.5	34... (350)				363			
0.039	12.5 x 25.5 x 30.0	6.9	34... (350)				393			

Notes

- Loose in box, all lengths have same SPQ
 - SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only



$U_{RDC} = 1600\text{ V}$; $U_{RAC} = 500\text{ V}$; $U_{PP} = 1400\text{ V}$ (LOCK LEAD); $C\text{-TOL.} = \pm 5\%$

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XYYYY AND PACKAGING	
			LOOSE IN BOX	
			l _t = 4.0 mm + 1.0 mm/- 0.5 mm	
				(SPQ)
C (pF)	PITCH = 15.0 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
680 750 820	5.5 x 17.5 x 18.5	0.75	90456 90457 90458	(2000)
910 1000 1100 1200 1300	6.0 x 18.0 x 18.5	0.80 0.85 0.85 0.90 0.95	90459 90461 90462 90463 90464	(2000)
1500 1600	5.5 x 17.5 x 18.5	1.1	90465 90466	(2000)
1800	6.0 x 18.0 x 18.5	1.2	90467	(2000)
2000 2200	6.5 x 18.5 x 18.5	1.3	90468 90469	(1750)
2400	7.0 x 19.0 x 18.5	1.4	90471	(1500)
2700 3000	7.5 x 19.5 x 18.5	1.6	90472 90473	(1400)
3300	8.0 x 20.0 x 18.5	1.9	90141	(1250)
3600	8.5 x 20.5 x 18.5	2.3	90142	(1200)
3900 4300	9.0 x 21.5 x 18.5	2.5	90143 90144	(1100)
C (µF)	PITCH = 22.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.0047 0.0051 0.0056	6.0 x 22.0 x 26.0	2.4	90145 90146 90147	(750)
0.0062 0.0068	6.5 x 22.5 x 26.0	2.6	90148 90149	(700)
0.0075 0.0082 0.0083	7.0 x 23.0 x 26.0	2.8	90151 90152 90202	(600)
0.0091	7.5 x 23.5 x 26.0	2.9	90153	(550)
0.01	8.0 x 24.0 x 26.0	3.2	90154	(500)
0.011 0.012	8.5 x 24.5 x 26.0	3.4	90155 90156	(450)
0.013	9.0 x 25.0 x 26.0	3.6	90157	(450)
0.015	9.5 x 25.5 x 26.0	4.0	90158	(400)
0.016	10.0 x 26.0 x 26.0	4.3	90159	(350)
0.018	10.5 x 26.5 x 26.0	4.7	90161	(350)
C (µF)	PITCH = 27.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.02	9.0 x 25.0 x 30.0	4.2	90474	(450)
0.022	9.5 x 25.5 x 30.0	4.4	90475	(450)
0.024	10.0 x 26.0 x 30.0	4.7	90476	(400)
0.027	10.5 x 26.5 x 30.0	5.2	90477	(350)
0.03	11.0 x 27.0 x 30.0	5.6	90478	(350)
0.033	11.5 x 27.5 x 30.0	6.0	90479	(350)
0.036	12.0 x 28.0 x 30.0	6.5	90481	(300)
0.039	12.5 x 28.5 x 30.0	6.9	90482	(300)

Notes

- SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only

**SPECIFIC REFERENCE DATA (2000 V_{DC})**

DESCRIPTION	VALUE	
Tangent of loss angle at ($\times 10^{-4}$):	10 kHz	100 kHz
Pitch = 10 mm, 15 mm, and 7.5 mm (bent back)	≤ 6	≤ 10
Pitch = 22.5 mm	≤ 6	≤ 10
Pitch = 27.5 mm	≤ 6	≤ 15
Rated voltage pulse slope (dU/dt):		
Pitch = 10 mm	30 000 V/ μ s	
Pitch = 15 mm and 7.5 mm (bent back)	10 000 V/ μ s	
Pitch = 22.5 mm	6700 V/ μ s	
Pitch = 27.5 mm		
R between leads at 500 V, 1 min	> 100 000 M Ω	
R between interconnected leads and case, 500 V, 1 min	> 100 000 M Ω	
Ionization (AC) voltage (typical value)		
at 50 pC peak discharge	> 600 V	
at 20 pC peak discharge		
Withstanding (DC) voltage (cut off current 10 mA), rise time 1000 V/s		
for $C \leq 47$ nF	3200 V, 1 min	
for $C > 47$ nF		
Withstanding (DC) voltage between leads and case	2840 V, 1 min	
Maximum application temperature	105 °C	

U_{RDC} = 2000 V; U_{RAC} = 600 V; U_{PP} = 1700 (KINKED); C-TOL. = ± 5 %

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING				
			LOOSE IN BOX	REEL			C VALUE
			LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		..YYY
				Ø 500 mm	Ø 500 mm	Ø 356 mm	
			XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)	
C (pF)	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm		PITCH = 15.0 mm	PITCH = 7.5 mm (BENT BACK)			
100	5.5 x 14.5 (15.0) x 18.5	0.75	44... (2000)	42... (1100)	46... (900)	48... (500)	101
110		0.75					111
120		0.75					121
130		0.75					131
150		0.75					151
160		0.75					161
180		0.75					181
200		0.75					201
220		0.75					221
240		0.75					241
270		0.75					271
300		0.75					301
330		0.75					331
360		0.75					361
390		0.75					391
430		0.75					431
470		0.80					471
510	0.80	511					
560	0.80	561					



C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XXYYY AND PACKAGING							
			LOOSE IN BOX	REEL			C VALUE			
			LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		..YYY			
				Ø 500 mm	Ø 500 mm	Ø 356 mm				
XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)							
C (pF)	PITCH = 15.0 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm	PITCH = 15.0 mm	PITCH = 7.5 mm (BENT BACK)							
620	6.0 x 15.0 (15.5) x 18.5	0.85	44... (2000)	42... (1000)	46... (800)	48... (450)	621			
680		0.85					681			
750		0.90					751			
820	6.5 x 15.5 (16.0) x 18.5	0.95	44... (1500)	42... (900)	46... (750)	48... (400)	821			
910	5.5 x 14.5 (16.0) x 18.5	1.1	44... (2000)	42... (420)	46... (900)	48... (500)	911			
1000	6.0 x 15.0 (16.5) x 18.5	1.2	44... (2000)	42... (1000)	46... (800)	48... (450)	102			
1100							112			
1200							122			
1300	6.5 x 15.5 (17.0) x 18.5	1.3	44... (1500)	42... (900)	46... (750)	48... (400)	132			
1500	7.0 x 16.0 (17.5) x 18.5	1.4	44... (1500)	42... (800)	46... (700)	48... (400)	152			
1600	7.5 x 16.5 (18.0) x 18.5	1.5	44... (1250)	42... (800)	46... (650)	48... (350)	162			
1800							182			
2000	8.0 x 17.0 (18.5) x 18.5	1.6	44... (1250)	42... (750)	46... (600)	48... (350)	202			
2200	8.5 x 17.5 (19.0) x 18.5	1.7	44... (1000)	42... (700)	46... (550)	48... (300)	222			
2400	9.0 x 18.0 (19.5) x 18.5	1.8	44... (1000)	42... (650)	46... (550)	48... (300)	242			
2700	9.5 x 18.5 (20.0) x 18.5	2.0	44... (900)	42... (600)	46... (500)	48... (300)	272			
C (µF)	PITCH = 22.5 mm ± 0.4 mm; d _t = 0.80 mm ± 0.08 mm	PITCH = 22.5 mm	PITCH = 7.5 mm (BENT BACK)							
0.003	6.0 x 19.0 x 26.0	2.1	44... (800)	-	-	-	302			
0.0033							332			
0.0036							362			
0.0039							392			
0.0043	6.5 x 19.5 x 26.0	2.3	44... (750)				432			
0.0047							472			
0.0051	7.0 x 20.0 x 26.0	2.6	44... (650)				512			
0.0056							562			
0.0062	7.5 x 20.5 x 26.0	2.8	44... (600)				622			
0.0068	8.0 x 21.0 x 26.0	3.0	44... (550)				682			
0.0075							752			
0.0082	8.5 x 21.5 x 26.0	3.3	44... (500)				822			
0.0091	9.0 x 22.0 x 26.0	3.6	44... (450)				912			
0.01	9.5 x 22.5 x 26.0	3.8	44... (400)				103			



C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XYYYY AND PACKAGING				
			LEADS 5 mm ± 1.0 mm	ORIGINAL PITCH	PITCH = 7.5 mm (BENT BACK)		C VALUE ..YYY
				Ø 500 mm	Ø 500 mm	Ø 356 mm	
XX (SPQ)	XX (SPQ)	XX (SPQ)	XX (SPQ)				
C (µF)	PITCH = 27.5 mm ± 0.5 mm; d _t = 0.80 mm ± 0.08 mm	PITCH = 27.5 mm	PITCH = 7.5 mm (BENT BACK)				
0.011	9.0 x 22.0 x 30.0	3.8	44... (550)	-	-	-	113
0.012	9.5 x 22.5 x 30.0	4.1	44... (500)				123
0.013	10.0 x 23.0 x 30.0	4.4	44... (500)				133
0.015	10.5 x 23.5 x 30.0	4.9	44... (450)				153
0.016	11.0 x 24.0 x 30.0	5.1	44... (400)				163
0.018	11.5 x 24.5 x 30.0	5.6	44... (400)				183
0.02	12.5 x 25.5 x 30.0	6.1	44... (350)				203
0.022	13.0 x 26.0 x 30.0	6.5	44... (300)				223

Notes

- Loose in box, all lengths have same SPQ
- SPQ = Standard Packing Quantity

⁽¹⁾ Net weight for short lead product only

U_{RDC} = 2000 V; U_{RAC} = 600 V; U_{PP} = 1700 V (LOCK LEAD)

C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XYYYY AND PACKAGING	
			LOOSE IN BOX	
			l _t = 4.0 mm + 1.0 mm/- 0.5 mm	
				(SPQ)
C (pF)	PITCH = 15.0 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
100	5.5 x 17.5 x 18.5	0.75	90483	(2000)
110		0.75	90484	
120		0.75	90485	
130		0.75	90486	
150		0.75	90487	
160		0.75	90488	
180		0.75	90489	
200		0.75	90491	
220		0.75	90276	
240		0.75	90492	
270		0.75	90493	
300		0.75	90494	
330		0.75	90495	
360		0.75	90496	
390		0.75	90188	
430		0.75	90497	
470		0.80	90498	
510		0.80	90499	
560		0.80	90501	



C	DIMENSIONS w x h (h') x l (mm)	MASS (g) ⁽¹⁾	CATALOG NUMBER BFC2 375 XYYYY AND PACKAGING	
			LOOSE IN BOX	
			l _t = 4.0 mm + 1.0 mm/- 0.5 mm	
			(SPQ)	
C (pF)	PITCH = 15.0 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
620	6.0 x 18.0 x 18.5	0.85	90502	(2000)
680		0.85	90229	
750		0.90	90503	
820	6.5 x 18.5 x 18.5	0.95	90504	(1750)
910	5.5 x 17.5 x 18.5	1.1	90505	(2000)
1000	6.0 x 18.0 x 18.5	1.3	90225	(2000)
1100			90506	
1200			90226	
1300	6.5 x 18.5 x 18.5	1.3	90507	(1750)
1500	7.0 x 19.0 x 18.5	1.5	90266	(1500)
1600	7.5 x 19.5 x 18.5	1.7	90508	(1400)
1800			90237	
2000	8.0 x 20.0 x 18.5	1.7	90509	(1250)
2200	8.5 x 20.5 x 18.5	2.3	90227	(1200)
2400	9.0 x 21.0 x 18.5	1.8	90511	(1100)
2700	9.5 x 21.5 x 18.5	2.7	90228	(1000)
C (μF)	PITCH = 22.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.003	6.0 x 22.0 x 26.0	2.2	90512	(750)
0.0033			90162	
0.0036			90163	
0.0039			90164	
0.0043	6.5 x 22.5 x 26.0	2.4	90165	(700)
0.0047			90166	
0.0051	7.0 x 23.0 x 26.0	2.6	90167	(600)
0.0056			90168	
0.0062	7.5 x 23.5 x 26.0	2.8	90169	(550)
0.0068	8.0 x 24.0 x 26.0	3.0	90171	(500)
0.0075			90172	
0.0082	8.5 x 24.5 x 26.0	3.2	90173	(450)
0.0091	9.0 x 25.0 x 26.0	3.5	90174	(450)
0.01	9.5 x 25.5 x 26.0	3.8	90175	(400)
C (μF)	PITCH = 27.5 mm ± 1.0 mm; d _t = 0.80 mm ± 0.08 mm			
0.011	9.0 x 25.0 x 30.0	4.4	90176	(450)
0.012	9.5 x 25.5 x 30.0	4.6	90177	(450)
0.013	10.0 x 26.0 x 30.0	5.0	90178	(400)
0.015	10.5 x 26.5 x 30.0	5.4	90179	(350)
0.016	11.0 x 27.0 x 30.0	5.8	90181	(350)
0.018	11.5 x 27.5 x 30.0	6.2	90182	(350)
0.02	12.5 x 28.5 x 30.0	6.1	90513	(300)
0.022	13.0 x 29.0 x 30.0	6.5	90514	(250)

Notes

- SPQ = Standard Packing Quantity
- ⁽¹⁾ Net weight for short lead product only



MOUNTING

Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to “Packaging information” www.vishay.com/doc?28139 or end of catalog.

Specific Method of Mounting to Withstand Vibration and Shock

- For pitches ≤ 15 mm capacitors shall be mechanically fixed by the leads
- For larger pitches the capacitors shall be mounted in the same way and the body clamped

Storage Temperature

$T_{stg} = -25\text{ °C to }+35\text{ °C}$ with RH maximum 75 % without condensation

Ratings and Characteristics Reference Conditions

Unless otherwise specified, all electrical values apply to an ambient temperature of $23\text{ °C} \pm 1\text{ °C}$, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of $50\% \pm 2\%$.


For reference testing, a conditioning period shall be applied over $96\text{ h} \pm 4\text{ h}$ by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.



CHARACTERISTICS



Capacitance as a function of ambient temperature
(typical curve)




Impedance as a function of frequency
(typical curve)




Maximum DC voltage as a function of temperature




Maximum allowed component temperature rise
as a function of ambient temperature




Max. RMS voltage (sinewave) as a function of frequency




Max. RMS voltage (sinewave) as a function of frequency




Max. RMS voltage (sinewave) as a function of frequency



Max. RMS voltage (sinewave) as a function of frequency



Max. RMS voltage (sinewave) as a function of frequency




Max. RMS voltage (sinewave) as a function of frequency




Max. RMS voltage (sinewave) as a function of frequency



Max. RMS voltage (sinewave) as a function of frequency



1. KP/MPK 10.0 mm and 15 mm pitch all versions
22.5 mm pitch, 1000 V, 1600 V, 2000 V and 2500 V versions
2. KP/MPK 22.5 mm pitch, 630 V versions
27.5 mm pitch, 1000 V, 1600 V and 2000 V versions
3. KP/MPK 27.5 mm pitch, 630 V versions

Tangent of loss angle
(typical curve)


1. KP/MPK 10.0 mm and 15 mm pitch all versions
22.5 mm pitch, 1000 V, 1600 V, 2000 V and 2500 V versions
2. KP/MPK 22.5 mm pitch, 630 V versions
27.5 mm pitch, 1000 V, 1600 V and 2000 V versions
3. KP/MPK 27.5 mm pitch, 630 V versions

Maximum curves



Insulation resistance as a function of ambient temperature

**HEAT CONDUCTIVITY (G) AS A FUNCTION OF (ORIGINAL) PITCH AND CAPACITOR BODY THICKNESS IN mW/°C**

W _{max.} (mm)	HEAT CONDUCTIVITY (mW/°C)			
	PITCH 10 mm	PITCH 15 mm	PITCH 22.5 mm	PITCH 27.5 mm
4.0	4.0	5.0	-	-
4.5	4.5	6.0	-	-
5.0	5.0	6.0	12.0	13.0
5.5	6.0	6.5	13.0	15.0
6.0	6.0	6.5	13.0	15.0
6.5	6.5	8.0	15.0	17.0
7.0	-	8.0	15.0	17.0
7.5	-	9.0	17.0	18.0
8.0	-	9.0	17.0	20.0
8.5	-	11.0	18.0	20.0
9.0	-	11.0	18.0	22.0
9.5	-	12.0	20.0	22.0
10.0	-	12.0	20.0	23.0
10.5	-	-	22.0	25.0
11.0	-	-	22.0	25.0
11.5	-	-	23.0	27.0
12.0	-	-	-	27.0
12.5	-	-	-	30.0
13.0	-	-	-	30.0
13.5	-	-	-	30.0
14.0	-	-	-	30.0
14.5	-	-	-	33.0
15.0	-	-	-	33.0
15.5	-	-	-	37.0
16.0	-	-	-	37.0

POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free ambient temperature.

The power dissipation can be calculated according type detail specification "HQN-384-01/101: Technical Information Film Capacitors"

The component temperature rise (ΔT) can be measured (see section "Measuring the component temperature" for more details) or calculated by $\Delta T = P/G$:

- ΔT = component temperature rise (°C)
- P = power dissipation of the component (mW)
- G = heat conductivity of the component (mW/°C)

MEASURING THE COMPONENT TEMPERATURE

A thermocouple must be attached to the capacitor body as in:



The temperature is measured in unloaded (T_{amb}) and maximum loaded condition (T_C).

The temperature rise is given by $\Delta T = T_C - T_{amb}$.

To avoid radiation or convection, the capacitor should be tested in a wind-free box.

APPLICATION NOTE AND LIMITING CONDITIONS

To select the capacitor for a certain application, the following conditions must be checked:

1. The peak voltage (U_P) shall not be greater than the rated DC voltage (U_{RDC}).
2. The peak-to-peak voltage (U_{PP}) shall not be greater than the maximum (U_{P-P}) to avoid the ionization inception level.
3. The voltage pulse slope (dU/dt) shall not exceed the rated voltage pulse slope in an RC-circuit at rated voltage and without ringing. If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by U_{RDC} and divided by the applied voltage.

For all other pulses following equation must be fulfilled:

$$2 \times \int_0^T \left(\frac{dU}{dt} \right)^2 \times dt < U_{RDC} \times \left(\frac{dU}{dt} \right)_{rated}$$

T is the pulse duration.

4. The maximum component surface temperature rise must be lower than the limits.

Example

$C = 10 \text{ nF}$ 1600 V, KP/MPK

This is a signal as in the drawing below

$U_{P-P} = 1200 \text{ V}$; $U_P = 1100 \text{ V}$; $T_1 = 12 \text{ } \mu\text{s}$; $T_2 = 64 \text{ } \mu\text{s}$

The ambient temperature is $50 \text{ } ^\circ\text{C}$

Checking conditions:

1. The peak voltage $U_P = 1100 \text{ V}$ is lower than 1600 V_{DC}
2. The peak-to-peak voltage 1200 V is lower than $2\sqrt{02} \times 550 \text{ V}_{AC} = 1414 \text{ V}_{P-P}$
3. The voltage pulse slope (dU/dt) = 320 V is much lower than $7000 \text{ V}/\mu\text{s}$
4. The dissipated power is 170 mW as calculated with fourier terms

This gives a temperature rise of $170 \text{ mW}/(17 \text{ mW}/^\circ\text{C}) = 10 \text{ } ^\circ\text{C}$ which is allowed according Fig. "Max. allowed temperature rise as a function of ambient temperature" for an ambient temperature of $50 \text{ } ^\circ\text{C}$



**INSPECTION REQUIREMENTS****General Notes**

Sub-clause numbers of tests and performance requirements refer to the “Sectional Specification, Publication IEC 60384-17 and Specific Reference Data”.

Group C Inspection Requirements

SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1		
4.1 Dimensions (detail)		As specified in chapters “General Data” of this specification
4.3.1 Initial measurements	Capacitance Tangent of loss angle at 100 kHz	
4.3 Robustness of terminations	Tensile: load 10 N; 10 s Bending: load 5 N; 4 x 90°	No visible damage
4.4 Resistance to soldering heat	Method: 1A Solder bath: 280 °C ± 5 °C Duration: 10 s	
4.14 Component solvent resistance	Isopropylalcohol at room temperature Method: 2 Immersion time: 5 min ± 0.5 min Recovery time: min. 1 h, max. 2 h	
4.4.2 Final measurements	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \leq 1\% + 5 \text{ pF}$ of the value measured initially
	Tangent of loss angle	Increase of $\tan \delta$: ≤ 0.0005 Compared to values measured in 4.3.1
SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1		
4.6.1 Initial measurements	Capacitance Tangent of loss angle at 100 kHz	
4.15 Solvent resistance of the marking	Isopropylalcohol at room temperature Method: 1 Rubbing material: cotton wool Immersion time: 5 min ± 0.5 min	No visible damage Legible marking
4.6 Rapid change of temperature	$\theta A = -55\text{ °C}$ $\theta B = +105\text{ °C}$ 5 cycles Duration $t = 30 \text{ min}$	
4.7 Vibration	Visual examination Mounting: See section “Mounting” of this specification Procedure B4 Frequency range: 10 Hz to 55 Hz Amplitude: 0.75 mm or Acceleration 98 m/s ² (whichever is less severe) Total duration 6 h	No visible damage



SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
4.7.2 Final inspection	Visual examination	No visible damage
4.9 Shock	Mounting: see section "Mounting" of this specification Pulse shape: half sine Acceleration: 490 m/s ² Duration of pulse: 11 ms	
4.9.3 Final measurements	Visual examination	No visible damage
	Capacitance	For $C > 0.027\mu\text{F}$: $ \Delta C/C \leq 2\%$ or for $C \leq 0.027\mu\text{F}$: $ \Delta C/C \leq 3\% + 5\text{ pF}$ of the value measured in 4.6.1.
	Tangent of loss angle	Increase of $\tan \delta: \leq 0.0005$ Compared to values measured in 4.6.1
	Insulation resistance	As specified in chapter "General data" of this specification
SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B		
4.10 Climatic sequence		
4.10.2 Dry heat	Temperature: +105 °C Duration: 16 h	
4.10.3 Damp heat cyclic Test Db, first cycle		
4.10.4 Cold	Temperature: -55 °C Duration: 2 h	
4.10.6 Damp heat cyclic Test Db, remaining cycles		
4.10.6.2 Final measurements	Voltage proof = U_{RDC} for 1 min within 15 min after removal from testchamber	No breakdown of flash-over
	Visual examination	No visible damage Legible marking
	Capacitance	$ \Delta C/C \leq 3\%$ of the value measured in 4.4.2 or 4.9.3
	Tangent of loss angle	Increase of $\tan \delta: \leq 0.001$ Compared to values measured in 4.3.1 or 4.6.1
	Insulation resistance	$\geq 50\%$ of values specified in chapters "General data" of this specification



SUB-CLAUSE NUMBER AND TEST	CONDITIONS	PERFORMANCE REQUIREMENTS
SUB-GROUP C2		
4.11 Damp heat steady state	56 days, 40 °C, 90 % to 95 % RH	
4.11.1 Initial measurements	Capacitance Tangent of loss angle at 1 kHz	
4.11.3 Final measurements	Voltage proof = U_{RDC} for 1 min within 15 min after removal from testchamber Visual examination Capacitance Tangent of loss angle Insulation resistance	No breakdown of flash-over No visible damage Legible marking $ \Delta C/C \leq 1 \% + 5 \text{ pF}$ of the value measured in 4.11.1. Increase of $\tan \delta \leq 0.0005$ Compared to values measured in 4.11.1 $\geq 50 \%$ of values specified in section "Insulation Resistance" of this specification
SUB GROUP C3		
4.12.1 Endurance	Duration: 2000 h Temperature: 85 °C Voltage: $1.25 \times \max. U_{RDC} V_{RMS}$, 50 Hz Duration: 2000 h Temperature: 105 °C	
4.12.1.1 Initial measurements	Voltage: $0.875 \times \max. U_{RDC} V_{RMS}$, 50 Hz Capacitance Tangent of loss angle at 100 kHz	
4.12.1.3 Final measurements	Visual examination Capacitance Tangent of loss angle Insulation resistance	No visible damage Legible marking Temperature: 85 °C For $C > 0.056 \mu\text{F}$: $ \Delta C/C \leq 2 \% + 5 \text{ pF}$ or for $C > 0.056 \mu\text{F}$: $ \Delta C/C \leq 3 \% + 5 \text{ pF}$ of the value measured in 4.12.1.1 Temperature: 105 °C $ \Delta C/C \leq 5 \% + 5 \text{ pF}$ Increase of $\tan \delta: \leq 0.001$ Compared to values measured in 4.12.1 $\geq 50 \%$ of values specified in chapters "General data" of this specification
SUB-GROUP C4		
4.2.6 Temperature characteristics	Capacitance Insulation resistance	As specified in section "Capacitance" of this specification As specified in chapters "General data" of this specification



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

BFC237525621	BFC237524432	BFC237524243	BFC237525131	BFC237540332	BFC237525623	BFC237531362
BFC237527302	BFC237523243	BFC237521393	BFC237534182	BFC237530273	BFC237525134	BFC237522161
BFC237535822	BFC237535152	BFC237530123	BFC237541112	BFC237530682	BFC237521471	BFC237533102
BFC237534822	BFC237530203	BFC237521391	BFC237524563	BFC237521821	BFC237536152	BFC237531123
BFC237540181	BFC237531912	BFC237531751	BFC237525223	BFC237532332	BFC237523242	BFC237534392
BFC237535682	BFC237540182	BFC237537132	BFC237532362	BFC237530751	BFC237535153	BFC237521473
BFC237541151	BFC237541182	BFC237527912	BFC237536162	BFC237523561	BFC237540183	BFC237524162
BFC237521823	BFC237525222	BFC237530432	BFC237540102	BFC237530681	BFC237534103	BFC237530112
BFC237531911	BFC237524161	BFC237530122	BFC237527272	BFC237522821	BFC237536242	BFC237541152
BFC237525221	BFC237534183	BFC237523153	BFC237524163	BFC237536392	BFC237531363	BFC237530202
BFC237524562	BFC237524241	BFC237525132	BFC237533103	BFC237521822	BFC237523562	BFC237525133
BFC237523241	BFC237521182	BFC237536821	BFC237535332	BFC237530362	BFC237521123	BFC237534153
BFC237526242	BFC237522112	BFC237530162	BFC237526562	BFC237540911	BFC237521271	BFC237521512
BFC237521122	BFC237522153	BFC237525912	BFC237531333	BFC237523123	BFC237534911	BFC237526302
BFC237524823	BFC237524131					