

Solid Tantalum Surface Mount Chip Capacitors

TANTAMOUNT™ Molded Case, High Performance, Automotive Grade



LINKS TO ADDITIONAL RESOURCES



3D Models



Calculators



Related Documents



Infographics



Did You Know?



Technical Notes

PERFORMANCE / ELECTRICAL CHARACTERISTICS

www.vishay.com/doc?40215

Operating Temperature: -55 °C to +125 °C
(above 85 °C, voltage derating is required)

Capacitance Range: 0.10 µF to 470 µF

Capacitance Tolerance: ± 10 %, ± 20 %

Voltage Rating: 4 V_{DC} to 50 V_{DC}

Note

- For recommended voltage derating guidelines see "Typical Performance Characteristics"

FEATURES

- AEC-Q200 qualified
- Low ESR
- 100 % surge current tested (B, C, D, and E case sizes)
- High ripple current carrying capability
- Molded case available in five case codes
- Terminations: 100 % matte tin standard, tin / lead available
- Compatible with "high volume" automatic pick and place equipment
- Meets EIA-535-BAAC mechanical and performance requirements
- Compliant terminations
- Moisture sensitivity level 1
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

APPLICATIONS

- Automotive
- Industrial
- General purpose




ORDERING INFORMATION

TP3	D	226	K	035	C	0500	AS
TYPE	CASE CODE	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT +85 °C	TERMINATION / PACKAGING	ESR	SPECIFICATION OPTION
	See Ratings and Case Codes table	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	K = ± 10 % M = ± 20 %	This is expressed in V. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V)	Matte tin C = 7" (178 mm) reel D = 13" (330 mm) reel V = 7" (178 mm) reel, dry pack U = 13" (330 mm) reel, dry pack Tin / lead E = 7" (178 mm) reel F = 13" (330 mm) reel T = 7" (178 mm) reel, dry pack W = 13" (330 mm) reel, dry pack	Maximum 100 kHz ESR 0500 = 500 mΩ 5000 = 5.0 Ω 10R0 = 10.0 Ω	AS = standard

Notes

- We reserve the right to supply higher voltage ratings and tighter capacitance tolerance capacitors in the same case size. Voltage substitutions will be marked with the higher voltage rating
- Dry pack as specified in J-STD-033

DIMENSIONS in inches [millimeters]


CASE CODE	EIA SIZE	L	W	H	P	T _W	T _H (MIN.)
A	3216-18	0.126 ± 0.008 [3.2 ± 0.20]	0.063 ± 0.008 [1.6 ± 0.20]	0.063 ± 0.008 [1.6 ± 0.20]	0.031 ± 0.012 [0.80 ± 0.30]	0.047 ± 0.004 [1.2 ± 0.10]	0.028 [0.70]
B	3528-21	0.138 ± 0.008 [3.5 ± 0.20]	0.110 ± 0.008 [2.8 ± 0.20]	0.075 ± 0.008 [1.9 ± 0.20]	0.031 ± 0.012 [0.80 ± 0.30]	0.087 ± 0.004 [2.2 ± 0.10]	0.028 [0.70]
C	6032-28	0.236 ± 0.012 [6.0 ± 0.30]	0.126 ± 0.012 [3.2 ± 0.30]	0.098 ± 0.012 [2.5 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.087 ± 0.004 [2.2 ± 0.10]	0.039 [1.0]
D	7343-31	0.287 ± 0.012 [7.3 ± 0.30]	0.169 ± 0.012 [4.3 ± 0.30]	0.110 ± 0.012 [2.8 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.094 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]
E	7343-43	0.287 ± 0.012 [7.3 ± 0.30]	0.169 ± 0.012 [4.3 ± 0.30]	0.157 ± 0.012 [4.0 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.094 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]

Note

- Glue pad (non-conductive, part of molded case) is dedicated for glue attachment (as user option)



RATINGS AND CASE CODES

μF	4 V	6.3 V	10 V	16 V	20 V	25 V	35 V	50 V
0.10							A (20.00, 10.00)	A (19.00, 10.00)
0.15								
0.22							A (15.00, 6.00)	A (15.00) B (12.00, 8.50)
0.33							A (13.00, 6.00)	B (10.00, 4.50)
0.47						A (12.00, 9.00)	A (10.00, 4.00) B (8.00, 2.50)	B (8.40, 4.00)
0.68					A (10.00, 8.00)	A (8.40) B (7.00, 5.00)	A (7.60, 4.00) B (6.50, 2.50)	
1.0				A (9.30, 6.00)	A (8.40, 5.50)	A (7.60, 4.00) B (5.00, 2.00)	A (7.50, 6.00, 4.00) B (5.00, 2.00)	B (6.70) C (4.60, 1.60)
1.5			A (8.00, 6.00)	A (6.70, 6.00)	A (6.30)	A (6.70, 4.00) B (4.60, 2.00)	B (4.20, 2.00) C (3.80)	
2.2		A (7.60, 6.00)	A (6.30, 4.60)	A (5.90, 4.00) B (4.60, 2.50)	A (5.90, 4.00) B (3.50, 1.50)	A (6.30, 4.00) B (4.00; 3.80, 1.50) C (2.20)	B (3.80, 2.00) C (2.90, 0.90)	C (2.90, 1.50) D (2.10, 0.80)
3.3		A (6.30, 5.00)	A (5.50)	A (5.00, 4.00, 3.50) B (3.5, 2.0)	A (5.90, 4.00) B (3.00, 1.30)	B (3.10, 1.50) C (2.30, 1.00)	B (3.50) C (2.10, 0.70)	C (2.50, 1.50) D (1.70, 0.80)
4.7	A (6.30)	A (5.50, 3.50)	A (5.00, 4.50, 3.00, 2.00, 1.40) B (3.40, 1.50)	A (5.00, 2.50, 2.00) B (2.90, 1.50)	A (5.00, 3.50) B (2.90, 1.00) C (2.30, 0.60)	B (2.80, 1.50) C (2.00, 0.525)	B (3.10, 1.50) C (1.90, 0.50) D (1.30, 0.45)	D (1.20, 0.60, 0.30)
6.8		A (5.00) B (3.40)	A (4.20, 3.00) B (2.90, 1.20)	A (4.20, 3.80, 3.00) B (2.50) C (1.90, 0.60)	B (2.50, 1.00) C (1.90, 0.55)	B (1.50) C (1.70, 0.50)	C (1.80, 0.475) D (1.8, 1.10, 0.30)	D (0.90, 0.60)
10		A (3.40, 2.00, 1.50) B (2.90, 1.00)	A (3.40, 3.00, 2.00) B (2.50, 0.60, 0.80) C (1.80, 0.55)	A (3.00, 1.70) B (2.00, 0.80) C (1.80, 0.45)	B (2.10, 2.5, 1.00) C (1.70, 0.50, 0.45)	C (1.50, 0.45) D (1.00, 0.30)	C (1.60, 0.45) D (0.80, 0.30, 0.25, 0.135)	D (0.80, 0.55) E (0.80, 0.55, 0.30)
15		A (2.90, 2.00) B (2.50)	A (2.90, 2.00) B (2.00, 1.20, 0.70) C (1.80, 0.50)	B (2.00, 0.80) C (1.50, 0.40)	B (2.30, 1.00) C (1.50, 0.40) D (0.90, 0.30)	C (1.20, 0.425) D (0.80, 0.25)	D (0.70, 0.30, 0.26, 0.225)	

RATINGS AND CASE CODES								
μF	4 V	6.3 V	10 V	16 V	20 V	25 V	35 V	50 V
22		A (2.90, 2.00) B (2.00, 0.60) C (1.80, 0.50)	A (2.50, 1.50) B (1.90, 0.60, 0.70) C (1.50, 0.40, 0.345, 0.245)	B (1.90, 0.70, 0.60) C (1.40, 0.8, 0.375, 0.35) D (0.80, 0.25)	C (1.10, 0.375) D (0.70, 0.225, 0.18)	C (1.20, 0.40) D (0.70, 0.20)	D (0.60, 0.30, 0.26, 0.20) E (0.60, 0.275)	
33	B (2.00) C (2.0, 1.80, 0.50)	A (2.50, 0.80) B (1.90, 0.60) C (1.50, 0.375)	B (1.90, 1.50, 0.60) C (1.40, 0.60, 0.30) D (0.80, 0.25)	C (1.10, 0.30) D (0.70, 0.225)	C (1.00, 0.35) D (0.70, 0.20)	D (0.70, 0.30, 0.20) E (0.60, 0.30, 0.20)	D (0.70, 0.40) E (0.70, 0.40)	
47		A (1.60) B (1.90, 0.60, 0.55, 0.50) C (1.40, 0.30, 0.25) D (0.80, 0.20)	B (1.80, 0.60) C (1.10, 0.30) D (0.70, 0.20)	C (1.00, 0.30) D (0.70, 0.20, 0.15, 0.12)	D (0.70, 0.25, 0.20, 0.15) E (0.60, 0.15)	E (0.60, 0.20)		
68	B (1.4) C (1.4)	B (1.80, 0.55) C (0.80, 0.275) D (0.70, 0.20)	C (1.00, 0.275) D (0.70, 0.15)	D (0.60, 0.15)				
100		B (0.9, 1.7) C (0.80, 0.25) D (0.70, 0.15, 0.14, 0.13)	C (0.90, 0.25, 0.20) D (0.60, 0.15, 0.10, 0.08)	D (0.60, 0.15, 0.125) E (0.60, 0.10)	E (0.50, 0.15)			
150		C (0.70, 0.30, 0.20) D (0.60, 0.15)	D (0.60, 0.10) E (0.50, 0.10)	E (0.50, 0.10)				
220		D (0.60, 0.10) E (0.50, 0.10)	D (0.60, 0.125, 0.10) E (0.50, 0.10)	E (0.50, 0.10)				
330		D (0.60, 0.125) E (0.50, 0.10)						
470		E (0.50, 0.10)						

Note

- ESR limits in Ω shown in parenthesis

MARKING		
 A Case	"A" CASE VOLTAGE CODE	
	VOLTS	CODE
	4.0	G
	6.3	J
	10	A
	16	C
	20	D
	25	E
	35	V
	50	T
	 B, C, D, E Cases	

Marking

Capacitor marking includes an anode (+) polarity band, capacitance in microfarads and the voltage rating. "A" case capacitors use a letter code for the voltage and EIA capacitance code.

The Vishay identification marking is included if space permits. Vishay marking ("circled 2") may show additives in the form of short lines, depicting actual manufacturing facility. For A case capacitors discontinuation in polarity bar maybe used as actual manufacturing facility designation. Capacitors rated at 6.3 V are marked 6 V.

A manufacturing date code is marked on all capacitors, for details see FAQ: www.vishay.com/doc?40110.

Call the factory for further explanation.

Note

- (1) Capital letter indicates lead (Pb)-free



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	MAX. ESR AT +25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
4 V _{DC} AT +85 °C; 2.7 V _{DC} AT +125 °C						
4.7	A	TP3A475(1)004(2)6300AS	0.5	6	6.300	0.11
33	B	TP3B336(1)004(2)2000AS	1.3	6	2.000	0.21
33	C	TP3C336(1)004(2)2000AS	1.3	6	2.000	0.25
33	C	TP3C336(1)004(2)1800AS	1.3	6	1.800	0.25
33	C	TP3C336(1)004(2)0500AS	1.3	6	0.500	0.47
68	B	TP3B686(1)004(2)1400AS	2.7	6	1.400	0.28
68	C	TP3C686(1)004(2)1400AS	2.7	6	1.400	0.28
6.3 V _{DC} AT +85 °C; 4 V _{DC} AT +125 °C						
2.2	A	TP3A225(1)6R3(2)7600AS	0.5	6	7.600	0.10
2.2	A	TP3A225(1)6R3(2)6000AS	0.5	6	6.000	0.11
3.3	A	TP3A335(1)6R3(2)6300AS	0.5	6	6.300	0.11
3.3	A	TP3A335(1)6R3(2)5000AS	0.5	6	5.000	0.12
4.7	A	TP3A475(1)6R3(2)5500AS	0.5	6	5.500	0.12
4.7	A	TP3A475(1)6R3(2)3500AS	0.5	6	3.500	0.15
6.8	A	TP3A685(1)6R3(2)5000AS	0.5	6	5.000	0.12
6.8	B	TP3B685(1)6R3(2)3400AS	0.5	6	3.400	0.16
10	A	TP3A106(1)6R3(2)3400AS	0.6	6	3.400	0.15
10	A	TP3A106(1)6R3(2)2000AS	0.6	6	2.000	0.19
10	A	TP3A106(1)6R3(2)1500AS	0.6	6	1.500	0.22
10	B	TP3B106(1)6R3(2)2900AS	0.6	6	2.900	0.17
10	B	TP3B106(1)6R3(2)1000AS	0.6	6	1.000	0.29
15	A	TP3A156(1)6R3(2)2900AS	0.9	6	2.900	0.16
15	A	TP3A156(1)6R3(2)2000AS	0.9	6	2.000	0.19
15	B	TP3B156(1)6R3(2)2500AS	0.9	6	2.500	0.18
22	A	TP3A226(1)6R3(2)2900AS	1.3	6	2.900	0.16
22	A	TP3A226(1)6R3(2)2000AS	1.3	6	2.000	0.19
22	B	TP3B226(1)6R3(2)2000AS	1.3	6	2.000	0.21
22	B	TP3B226(1)6R3(2)0600AS	1.3	6	0.600	0.38
22	C	TP3C226(1)6R3(2)1800AS	1.3	6	1.800	0.25
22	C	TP3C226(1)6R3(2)0500AS	1.3	6	0.500	0.47
33	A	TP3A336(1)6R3(2)2500AS	2.0	14	2.500	0.17
33	A	TP3A336(1)6R3(2)0800AS	2.0	14	0.800	0.31
33	B	TP3B336(1)6R3(2)1900AS	2.0	6	1.900	0.21
33	B	TP3B336(1)6R3(2)0600AS	2.0	6	0.600	0.38
33	C	TP3C336(1)6R3(2)1500AS	2.0	6	1.500	0.27
33	C	TP3C336(1)6R3(2)0375AS	2.0	6	0.375	0.54
47	A	TP3A476(1)6R3(2)1600AS	2.8	12	1.600	0.22
47	B	TP3B476(1)6R3(2)1900AS	2.8	6	1.900	0.21
47	B	TP3B476(1)6R3(2)0600AS	2.8	6	0.600	0.38
47	B	TP3B476(1)6R3(2)0550AS	2.8	6	0.550	0.39
47	B	TP3B476(1)6R3(2)0500AS	2.8	6	0.500	0.41
47	C	TP3C476(1)6R3(2)1400AS	2.8	6	1.400	0.28
47	C	TP3C476(1)6R3(2)0300AS	2.8	6	0.300	0.61
47	C	TP3C476(1)6R3(2)0250AS	2.1	6	0.250	0.66
47	D	TP3D476(1)6R3(2)0800AS	2.8	6	0.800	0.43
47	D	TP3D476(1)6R3(2)0200AS	2.8	6	0.200	0.87

Note

- Part number definitions:
 - (1) Capacitance tolerance codes: K, M
 - (2) Terminations and packaging codes: C, D, E, F, V, U, T, W



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	MAX. ESR AT +25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
6.3 V _{DC} AT +85 °C; 4 V _{DC} AT 125 °C						
68	B	TP3B686(1)6R3(2)1800AS	4.1	6	1.800	0.22
68	B	TP3B686(1)6R3(2)0550AS	4.1	6	0.550	0.39
68	C	TP3C686(1)6R3(2)0800AS	4.1	6	0.800	0.37
68	C	TP3C686(1)6R3(2)0275AS	4.1	6	0.275	0.63
68	D	TP3D686(1)6R3(2)0700AS	4.1	6	0.700	0.46
68	D	TP3D686(1)6R3(2)0200AS	4.1	6	0.200	0.87
100	B	TP3B107(1)6R3(2)0900AS	6.0	10	0.900	0.22
100	B	TP3B107(1)6R3(2)1700AS	6.0	10	1.700	0.22
100	C	TP3C107(1)6R3(2)0800AS	6.0	6	0.800	0.37
100	C	TP3C107(1)6R3(2)0250AS	6.0	6	0.250	0.66
100	D	TP3D107(1)6R3(2)0700AS	6.0	6	0.700	0.46
100	D	TP3D107(1)6R3(2)0150AS	6.0	6	0.150	1.00
100	D	TP3D107(1)6R3(2)0140AS	6.0	6	0.140	1.04
100	D	TP3D107(1)6R3(2)0130AS	6.0	6	0.130	1.07
150	C	TP3C157(1)6R3(2)0700AS	9.0	8	0.700	0.40
150	C	TP3C157(1)6R3(2)0300AS	9.0	8	0.300	0.61
150	C	TP3C157(1)6R3(2)0200AS	9.0	8	0.200	0.74
150	D	TP3D157(1)6R3(2)0600AS	9.0	8	0.600	0.60
150	D	TP3D157(1)6R3(2)0150AS	9.0	8	0.150	1.10
220	D	TP3D227(1)6R3(2)0600AS	13.2	8	0.600	0.50
220	D	TP3D227(1)6R3(2)0100AS	13.2	8	0.100	1.22
220	E	TP3E227(1)6R3(2)0500AS	13.2	8	0.500	0.57
220	E	TP3E227(1)6R3(2)0100AS	13.2	8	0.100	1.28
330	D	TP3D337(1)6R3(2)0600AS	19.8	8	0.600	0.50
330	D	TP3D337(1)6R3(2)0125AS	19.8	8	0.125	1.10
330	E	TP3E337(1)6R3(2)0500AS	19.8	8	0.500	0.57
330	E	TP3E337(1)6R3(2)0100AS	19.8	8	0.100	1.28
470	E	TP3E477(1)6R3(2)0500AS	28.2	10	0.500	0.57
470	E	TP3E477(1)6R3(2)0100AS	28.2	10	0.100	1.28
10 V _{DC} AT +85 °C; 7 V _{DC} AT 125 °C						
1.5	A	TP3A155(1)010(2)8000AS	0.5	6	8.000	0.10
1.5	A	TP3A155(1)010(2)6000AS	0.5	6	6.000	0.11
2.2	A	TP3A225(1)010(2)6300AS	0.5	6	6.300	0.11
2.2	A	TP3A225(1)010(2)4600AS	0.5	6	4.600	0.13
3.3	A	TP3A335(1)010(2)5500AS	0.5	6	5.500	0.12
4.7	A	TP3A475(1)010(2)5000AS	0.5	6	5.000	0.12
4.7	A	TP3A475(1)010(2)4500AS	0.5	6	4.500	0.13
4.7	A	TP3A475(1)010(2)3000AS	0.5	6	3.000	0.16
4.7	A	TP3A475(1)010(2)2000AS	0.5	6	2.000	0.19
4.7	A	TP3A475(1)010(2)1400AS	0.5	6	1.400	0.23
4.7	B	TP3B475(1)010(2)3400AS	0.5	6	3.400	0.16
4.7	B	TP3B475(1)010(2)1500AS	0.5	6	1.500	0.24
6.8	A	TP3A685(1)010(2)4200AS	0.7	6	4.200	0.13
6.8	A	TP3A685(1)010(2)3000AS	0.7	6	3.000	0.16
6.8	B	TP3B685(1)010(2)2900AS	0.7	6	2.900	0.17
6.8	B	TP3B685(1)010(2)1200AS	0.7	6	1.200	0.27
10	A	TP3A106(1)010(2)3400AS	1.0	6	3.400	0.15
10	A	TP3A106(1)010(2)3000AS	1.0	6	3.000	0.16
10	A	TP3A106(1)010(2)2000AS	1.0	6	2.000	0.19
10	B	TP3B106(1)010(2)2500AS	1.0	6	2.500	0.18
10	B	TP3B106(1)010(2)0800AS	1.0	6	0.800	0.33
10	B	TP3B106(1)010(2)0600AS	1.0	6	0.600	0.38
10	C	TP3C106(1)010(2)1800AS	1.0	6	1.800	0.25
10	C	TP3C106(1)010(2)0550AS	1.0	6	0.550	0.45

Note

- Part number definitions:
 - Capacitance tolerance codes: K, M
 - Terminations and packaging codes: C, D, E, F, V, U, T, W



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	MAX. ESR AT +25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
10 V _{DC} AT +85 °C; 7 V _{DC} AT 125 °C						
15	A	TP3A156(1)010(2)2900AS	1.5	6	2.900	0.16
15	A	TP3A156(1)010(2)2000AS	1.5	6	2.000	0.19
15	B	TP3B156(1)010(2)2000AS	1.5	6	2.000	0.21
15	B	TP3B156(1)010(2)1200AS	1.5	6	1.200	0.27
15	B	TP3B156(1)010(2)0700AS	1.5	6	0.700	0.35
15	C	TP3C156(1)010(2)1800AS	1.5	6	1.800	0.25
15	C	TP3C156(1)010(2)0500AS	1.5	6	0.500	0.47
22	A	TP3A226(1)010(2)2500AS	2.2	8	2.500	0.17
22	A	TP3A226(1)010(2)1500AS	2.2	8	1.500	0.22
22	B	TP3B226(1)010(2)1900AS	2.2	6	1.900	0.21
22	B	TP3B226(1)010(2)0700AS	2.2	6	0.700	0.35
22	B	TP3B226(1)010(2)0600AS	2.2	6	0.600	0.38
22	C	TP3C226(1)010(2)1500AS	2.2	6	1.500	0.27
22	C	TP3C226(1)010(2)0400AS	2.2	6	0.400	0.52
22	C	TP3C226(1)010(2)0345AS	2.2	6	0.345	0.56
22	C	TP3C226(1)010(2)0245AS	2.2	6	0.245	0.67
33	B	TP3B336(1)010(2)1900AS	3.3	6	1.900	0.21
33	B	TP3B336(1)010(2)1500AS	3.3	6	1.500	0.24
33	B	TP3B336(1)010(2)0600AS	3.3	6	0.600	0.38
33	C	TP3C336(1)010(2)1400AS	3.3	6	1.400	0.28
33	C	TP3C336(1)010(2)0600AS	3.3	6	0.600	0.28
33	C	TP3C336(1)010(2)0300AS	3.3	6	0.300	0.61
33	D	TP3D336(1)010(2)0800AS	3.3	6	0.800	0.43
33	D	TP3D336(1)010(2)0250AS	3.3	6	0.250	0.77
47	B	TP3B476(1)010(2)1800AS	4.7	6	1.800	0.22
47	B	TP3B476(1)010(2)0600AS	4.7	6	0.600	0.38
47	C	TP3C476(1)010(2)1100AS	4.7	6	1.100	0.32
47	C	TP3C476(1)010(2)0300AS	4.7	6	0.300	0.61
47	D	TP3D476(1)010(2)0700AS	4.7	6	0.700	0.46
47	D	TP3D476(1)010(2)0200AS	4.7	6	0.200	0.87
68	C	TP3C686(1)010(2)1000AS	6.8	6	1.000	0.33
68	C	TP3C686(1)010(2)0275AS	6.8	6	0.275	0.63
68	D	TP3D686(1)010(2)0700AS	6.8	6	0.700	0.46
68	D	TP3D686(1)010(2)0150AS	6.8	6	0.150	1.00
100	C	TP3C107(1)010(2)0900AS	10.0	8	0.900	0.35
100	C	TP3C107(1)010(2)0250AS	10.0	8	0.250	0.66
100	C	TP3C107(1)010(2)0200AS	10.0	8	0.200	0.74
100	D	TP3D107(1)010(2)0600AS	10.0	8	0.600	0.50
100	D	TP3D107(1)010(2)0150AS	10.0	8	0.150	1.00
100	D	TP3D107(1)010(2)0100AS	10.0	8	0.100	1.22
100	D	TP3D107(1)010(2)0080AS	10.0	8	0.080	1.37
150	D	TP3D157(1)010(2)0600AS	15.0	8	0.600	0.50
150	D	TP3D157(1)010(2)0100AS	15.0	8	0.100	1.22
150	E	TP3E157(1)010(2)0500AS	15.0	8	0.500	0.57
150	E	TP3E157(1)010(2)0100AS	15.0	8	0.100	1.28
220	D	TP3D227(1)010(2)0600AS	22.0	8	0.600	0.50
220	D	TP3D227(1)010(2)0125AS	22.0	8	0.125	1.10
220	D	TP3D227(1)010(2)0100AS	22.0	8	0.100	1.22
220	E	TP3E227(1)010(2)0500AS	22.0	8	0.500	0.57
220	E	TP3E227(1)010(2)0100AS	22.0	8	0.100	1.28

Note

- Part number definitions:
 - (1) Capacitance tolerance codes: K, M
 - (2) Terminations and packaging codes: C, D, E, F, V, U, T, W



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	MAX. ESR AT +25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
16 V _{DC} AT +85 °C; 10 V _{DC} AT +125 °C						
1.0	A	TP3A105(1)016(2)9300AS	0.5	4	9.300	0.09
1.0	A	TP3A105(1)016(2)6000AS	0.5	4	6.000	0.11
1.5	A	TP3A155(1)016(2)6700AS	0.5	6	6.700	0.11
1.5	A	TP3A155(1)016(2)6000AS	0.5	6	6.000	0.11
2.2	A	TP3A225(1)016(2)5900AS	0.5	6	5.900	0.11
2.2	A	TP3A225(1)016(2)4000AS	0.5	6	4.000	0.14
2.2	B	TP3B225(1)016(2)4600AS	0.5	6	4.600	0.14
2.2	B	TP3B225(1)016(2)2500AS	0.5	6	2.500	0.18
3.3	A	TP3A335(1)016(2)5000AS	0.5	6	5.000	0.12
3.3	A	TP3A335(1)016(2)4000AS	0.5	6	4.000	0.14
3.3	A	TP3A335(1)016(2)3500AS	0.5	6	3.500	0.15
3.3	B	TP3B335(1)016(2)3500AS	0.5	6	3.500	0.16
3.3	B	TP3B335(1)016(2)2000AS	0.5	6	2.000	0.21
4.7	A	TP3A475(1)016(2)5000AS	0.8	6	5.000	0.12
4.7	A	TP3A475(1)016(2)2500AS	0.8	6	2.500	0.17
4.7	A	TP3A475(1)016(2)2000AS	0.8	6	2.000	0.19
4.7	B	TP3B475(1)016(2)2900AS	0.8	6	2.900	0.17
4.7	B	TP3B475(1)016(2)1500AS	0.8	6	1.500	0.24
6.8	A	TP3A685(1)016(2)4200AS	1.1	6	4.200	0.13
6.8	A	TP3A685(1)016(2)3800AS	1.1	6	3.800	0.14
6.8	A	TP3A685(1)016(2)3000AS	1.1	6	3.000	0.16
6.8	B	TP3B685(1)016(2)2500AS	1.1	6	2.500	0.18
6.8	C	TP3C685(1)016(2)1900AS	1.1	6	1.900	0.24
6.8	C	TP3C685(1)016(2)0600AS	1.1	6	0.600	0.43
10	A	TP3A106(1)016(2)3000AS	1.6	6	3.000	0.16
10	A	TP3A106(1)016(2)1700AS	1.6	6	1.700	0.21
10	B	TP3B106(1)016(2)2000AS	1.6	6	2.000	0.21
10	B	TP3B106(1)016(2)0800AS	1.6	6	0.800	0.33
10	C	TP3C106(1)016(2)1800AS	1.6	6	1.800	0.25
10	C	TP3C106(1)016(2)0450AS	1.6	6	0.450	0.49
15	B	TP3B156(1)016(2)2000AS	2.4	6	2.000	0.21
15	B	TP3B156(1)016(2)0800AS	2.4	6	0.800	0.33
15	C	TP3C156(1)016(2)1500AS	2.4	6	1.500	0.27
15	C	TP3C156(1)016(2)0400AS	2.4	6	0.400	0.52
22	B	TP3B226(1)016(2)1900AS	3.5	6	1.900	0.21
22	B	TP3B226(1)016(2)0700AS	3.5	6	0.700	0.35
22	B	TP3B226(1)016(2)0600AS	3.5	6	0.600	0.38
22	C	TP3C226(1)016(2)1400AS	3.5	6	1.400	0.28
22	C	TP3C226(1)016(2)0800AS	3.5	6	0.800	0.28
22	C	TP3C226(1)016(2)0375AS	3.5	6	0.375	0.54
22	C	TP3C226(1)016(2)0350AS	3.5	6	0.350	0.56
22	D	TP3D226(1)016(2)0800AS	3.5	6	0.800	0.43
22	D	TP3D226(1)016(2)0250AS	3.5	6	0.250	0.77
33	C	TP3C336(1)016(2)1100AS	5.3	6	1.100	0.32
33	C	TP3C336(1)016(2)0300AS	5.3	6	0.300	0.61

Note

- Part number definitions:
 - Capacitance tolerance codes: K, M
 - Terminations and packaging codes: C, D, E, F, V, U, T, W



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	MAX. ESR AT +25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
16 V _{DC} AT +85 °C; 10 V _{DC} AT +125 °C						
33	D	TP3D336(1)016(2)0700AS	5.3	6	0.700	0.46
33	D	TP3D336(1)016(2)0225AS	5.3	6	0.225	0.82
47	C	TP3C476(1)016(2)1000AS	7.5	6	1.000	0.33
47	C	TP3C476(1)016(2)0300AS	7.5	6	0.300	0.61
47	D	TP3D476(1)016(2)0700AS	7.5	6	0.700	0.46
47	D	TP3D476(1)016(2)0200AS	7.5	6	0.200	0.87
47	D	TP3D476(1)016(2)0150AS	7.5	6	0.150	1.00
47	D	TP3D476(1)016(2)0120AS	7.5	6	0.120	1.12
68	D	TP3D686(1)016(2)0600AS	10.9	6	0.600	0.50
68	D	TP3D686(1)016(2)0150AS	10.9	6	0.150	1.00
100	D	TP3D107(1)016(2)0600AS	16.0	8	0.600	0.50
100	D	TP3D107(1)016(2)0150AS	16.0	8	0.150	1.00
100	D	TP3D107(1)016(2)0125AS	16.0	8	0.125	1.10
100	E	TP3E107(1)016(2)0600AS	16.0	8	0.600	0.52
100	E	TP3E107(1)016(2)0100AS	16.0	8	0.100	1.28
150	E	TP3E157(1)016(2)0500AS	24.0	8	0.500	0.57
150	E	TP3E157(1)016(2)0100AS	24.0	8	0.100	1.28
220	E	TP3E227(1)016(2)0500AS	35.2	14	0.500	0.57
220	E	TP3E227(1)016(2)0100AS	35.2	14	0.100	1.28
20 V _{DC} AT +85 °C; 13 V _{DC} AT +125 °C						
0.68	A	TP3A684(1)020(2)10R0AS	0.5	4	10.000	0.09
0.68	A	TP3A684(1)020(2)8000AS	0.5	4	8.000	0.10
1.0	A	TP3A105(1)020(2)8400AS	0.5	4	8.400	0.09
1.0	A	TP3A105(1)020(2)5500AS	0.5	4	5.500	0.12
1.5	A	TP3A155(1)020(2)6300AS	0.5	6	6.300	0.11
2.2	A	TP3A225(1)020(2)5900AS	0.5	6	5.900	0.11
2.2	A	TP3A225(1)020(2)4000AS	0.5	6	4.000	0.14
2.2	B	TP3B225(1)020(2)3500AS	0.5	6	3.500	0.16
2.2	B	TP3B225(1)020(2)1500AS	0.5	6	1.500	0.24
3.3	A	TP3A335(1)020(2)5900AS	0.7	6	5.900	0.11
3.3	A	TP3A335(1)020(2)4000AS	0.7	6	4.000	0.14
3.3	B	TP3B335(1)020(2)3000AS	0.7	6	3.000	0.17
3.3	B	TP3B335(1)020(2)1300AS	0.7	6	1.300	0.26
4.7	A	TP3A475(1)020(2)5000AS	0.9	6	5.000	0.12
4.7	A	TP3A475(1)020(2)3500AS	0.9	6	3.500	0.15
4.7	B	TP3B475(1)020(2)2900AS	0.9	6	2.900	0.17
4.7	B	TP3B475(1)020(2)1000AS	0.9	6	1.000	0.29
4.7	C	TP3C475(1)020(2)2300AS	0.9	6	2.300	0.22
4.7	C	TP3C475(1)020(2)0600AS	0.9	6	0.600	0.43
6.8	B	TP3B685(1)020(2)2500AS	1.4	6	2.500	0.18
6.8	B	TP3B685(1)020(2)1000AS	1.4	6	1.000	0.29
6.8	C	TP3C685(1)020(2)1900AS	1.4	6	1.900	0.24
6.8	C	TP3C685(1)020(2)0550AS	1.4	6	0.550	0.45
10	B	TP3B106(1)020(2)2500AS	2.0	6	2.500	0.18
10	B	TP3B106(1)020(2)2100AS	2.0	6	2.100	0.20
10	B	TP3B106(1)020(2)1000AS	2.0	6	1.000	0.29
10	C	TP3C106(1)020(2)1700AS	2.0	6	1.700	0.25
10	C	TP3C106(1)020(2)0500AS	2.0	6	0.500	0.47
10	C	TP3C106(1)020(2)0450AS	2.0	6	0.450	0.49

Note

- Part number definitions:
 - (1) Capacitance tolerance codes: K, M
 - (2) Terminations and packaging codes: C, D, E, F, V, U, T, W



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	MAX. ESR AT +25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
20 V _{DC} AT +85 °C; 13 V _{DC} AT +125 °C						
15	B	TP3B156(1)020(2)2300AS	3.0	6	2.300	0.19
15	B	TP3B156(1)020(2)1000AS	3.0	6	1.000	0.29
15	C	TP3C156(1)020(2)1500AS	3.0	6	1.500	0.27
15	C	TP3C156(1)020(2)0400AS	3.0	6	0.400	0.52
15	D	TP3D156(1)020(2)0900AS	3.0	6	0.900	0.41
15	D	TP3D156(1)020(2)0300AS	3.0	6	0.300	0.71
22	C	TP3C226(1)020(2)1100AS	4.4	6	1.100	0.32
22	C	TP3C226(1)020(2)0375AS	4.4	6	0.375	0.54
22	D	TP3D226(1)020(2)0700AS	4.4	6	0.700	0.46
22	D	TP3D226(1)020(2)0225AS	4.4	6	0.225	0.82
22	D	TP3D226(1)020(2)0180AS	4.4	6	0.180	0.91
33	C	TP3C336(1)020(2)1000AS	6.6	6	1.000	0.33
33	C	TP3C336(1)020(2)0350AS	6.6	6	0.350	0.56
33	D	TP3D336(1)020(2)0700AS	6.6	6	0.700	0.46
33	D	TP3D336(1)020(2)0200AS	6.6	6	0.200	0.87
47	D	TP3D476(1)020(2)0700AS	9.4	6	0.700	0.46
47	D	TP3D476(1)020(2)0250AS	9.4	6	0.250	0.77
47	D	TP3D476(1)020(2)0200AS	9.4	6	0.200	0.87
47	D	TP3D476(1)020(2)0150AS	9.4	6	0.150	1.00
47	E	TP3E476(1)020(2)0600AS	9.4	6	0.600	0.52
47	E	TP3E476(1)020(2)0150AS	9.4	6	0.150	1.05
100	E	TP3E107(1)020(2)0500AS	20.0	8	0.500	0.57
100	E	TP3E107(1)020(2)0150AS	20.0	8	0.150	1.05
25 V _{DC} AT +85 °C; 17 V _{DC} AT +125 °C						
0.47	A	TP3A474(1)025(2)12R0AS	0.5	4	12.000	0.08
0.47	A	TP3A474(1)025(2)9000AS	0.5	4	9.000	0.09
0.68	A	TP3A684(1)025(2)8400AS	0.5	4	8.400	0.09
0.68	B	TP3B684(1)025(2)7000AS	0.5	4	7.000	0.11
0.68	B	TP3B684(1)025(2)5000AS	0.5	4	5.000	0.13
1.0	A	TP3A105(1)025(2)7600AS	0.5	4	7.600	0.10
1.0	A	TP3A105(1)025(2)4000AS	0.5	4	4.000	0.14
1.0	B	TP3B105(1)025(2)5000AS	0.5	4	5.000	0.13
1.0	B	TP3B105(1)025(2)2000AS	0.5	4	2.000	0.21
1.5	A	TP3A155(1)025(2)6700AS	0.5	6	6.700	0.11
1.5	A	TP3A155(1)025(2)4000AS	0.5	6	4.000	0.14
1.5	B	TP3B155(1)025(2)4600AS	0.5	6	4.600	0.14
1.5	B	TP3B155(1)025(2)2000AS	0.5	6	2.000	0.21
2.2	A	TP3A225(1)025(2)6300AS	0.6	6	6.300	0.11
2.2	A	TP3A225(1)025(2)4000AS	0.6	6	4.000	0.14
2.2	B	TP3B225(1)025(2)3800AS	0.6	6	3.800	0.15
2.2	B	TP3B225(1)025(2)1500AS	0.6	6	1.500	0.24
2.2	B	TP3B225(1)025(2)4000AS	0.6	6	4.000	0.24
2.2	C	TP3C225(1)025(2)2200AS	0.6	6	2.200	0.22
3.3	B	TP3B335(1)025(2)3100AS	0.8	6	3.100	0.17
3.3	B	TP3B335(1)025(2)1500AS	0.8	6	1.500	0.24
3.3	C	TP3C335(1)025(2)2300AS	0.8	6	2.300	0.22
3.3	C	TP3C335(1)025(2)1000AS	0.8	6	1.000	0.33
4.7	B	TP3B475(1)025(2)2800AS	1.2	6	2.800	0.17
4.7	B	TP3B475(1)025(2)1500AS	1.2	6	1.500	0.24
4.7	C	TP3C475(1)025(2)2000AS	1.2	6	2.000	0.24
4.7	C	TP3C475(1)025(2)0525AS	1.2	6	0.525	0.46
6.8	B	TP3B685(1)025(2)1500AS	1.7	6	1.500	0.24
6.8	C	TP3C685(1)025(2)1700AS	1.7	6	1.700	0.25
6.8	C	TP3C685(1)025(2)0500AS	1.7	6	0.500	0.47

Note

- Part number definitions:
 - Capacitance tolerance codes: K, M
 - Terminations and packaging codes: C, D, E, F, V, U, T, W



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	MAX. ESR AT +25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
25 V _{DC} AT +85 °C; 17 V _{DC} AT +125 °C						
10	C	TP3C106(1)025(2)1500AS	2.5	6	1.500	0.27
10	C	TP3C106(1)025(2)0450AS	2.5	6	0.450	0.49
10	D	TP3D106(1)025(2)1000AS	2.5	6	1.000	0.39
10	D	TP3D106(1)025(2)0300AS	2.5	6	0.300	0.71
15	C	TP3C156(1)025(2)1200AS	3.8	6	1.200	0.30
15	C	TP3C156(1)025(2)0425AS	3.8	6	0.425	0.51
15	D	TP3D156(1)025(2)0800AS	3.8	6	0.800	0.43
15	D	TP3D156(1)025(2)0250AS	3.8	6	0.250	0.77
22	C	TP3C226(1)025(2)1200AS	5.5	6	1.200	0.30
22	C	TP3C226(1)025(2)0400AS	5.5	6	0.400	0.52
22	D	TP3D226(1)025(2)0700AS	5.5	6	0.700	0.46
22	D	TP3D226(1)025(2)0200AS	5.5	6	0.200	0.87
33	D	TP3D336(1)025(2)0700AS	8.3	6	0.700	0.46
33	D	TP3D336(1)025(2)0300AS	8.3	6	0.300	0.71
33	D	TP3D336(1)025(2)0200AS	8.3	6	0.200	0.87
33	E	TP3E336(1)025(2)0600AS	8.3	6	0.600	0.52
33	E	TP3E336(1)025(2)0300AS	8.3	6	0.300	0.74
33	E	TP3E336(1)025(2)0200AS	8.3	6	0.200	0.91
47	E	TP3E476(1)025(2)0600AS	11.8	6	0.600	0.52
47	E	TP3E476(1)025(2)0200AS	11.8	6	0.200	0.91
35 V _{DC} AT +85 °C; 23 V _{DC} AT +125 °C						
0.10	A	TP3A104(1)035(2)20R0AS	0.5	4	20.000	0.06
0.10	A	TP3A104(1)035(2)10R0AS	0.5	4	10.000	0.09
0.22	A	TP3A224(1)035(2)15R0AS	0.5	4	15.000	0.07
0.22	A	TP3A224(1)035(2)6000AS	0.5	4	6.000	0.11
0.33	A	TP3A334(1)035(2)13R0AS	0.5	4	13.000	0.08
0.33	A	TP3A334(1)035(2)6000AS	0.5	4	6.000	0.11
0.47	A	TP3A474(1)035(2)10R0AS	0.5	4	10.000	0.09
0.47	A	TP3A474(1)035(2)4000AS	0.5	4	4.000	0.14
0.47	B	TP3B474(1)035(2)8000AS	0.5	4	8.000	0.10
0.47	B	TP3B474(1)035(2)2500AS	0.5	4	2.500	0.18
0.68	A	TP3A684(1)035(2)7600AS	0.5	4	7.600	0.10
0.68	A	TP3A684(1)035(2)4000AS	0.5	4	4.000	0.14
0.68	B	TP3B684(1)035(2)6500AS	0.5	4	6.500	0.11
0.68	B	TP3B684(1)035(2)2500AS	0.5	4	2.500	0.18
1.0	A	TP3A105(1)035(2)7500AS	0.5	4	7.500	0.10
1.0	A	TP3A105(1)035(2)6000AS	0.5	4	6.000	0.11
1.0	A	TP3A105(1)035(2)4000AS	0.5	4	4.000	0.14
1.0	B	TP3B105(1)035(2)5000AS	0.5	4	5.000	0.13
1.0	B	TP3B105(1)035(2)2000AS	0.5	4	2.000	0.21
1.5	B	TP3B155(1)035(2)4200AS	0.5	6	4.200	0.14
1.5	B	TP3B155(1)035(2)2000AS	0.5	6	2.000	0.21
1.5	C	TP3C155(1)035(2)3800AS	0.5	6	3.800	0.17
2.2	B	TP3B225(1)035(2)3800AS	0.8	6	3.800	0.15
2.2	B	TP3B225(1)035(2)2000AS	0.8	6	2.000	0.21
2.2	C	TP3C225(1)035(2)2900AS	0.8	6	2.900	0.20
2.2	C	TP3C225(1)035(2)0900AS	0.8	6	0.900	0.35
3.3	B	TP3B335(1)035(2)3500AS	1.2	6	3.500	0.16
3.3	C	TP3C335(1)035(2)2100AS	1.2	6	2.100	0.23
3.3	C	TP3C335(1)035(2)0700AS	1.2	6	0.700	0.40
4.7	B	TP3B475(1)035(2)3100AS	1.7	6	3.100	0.17
4.7	B	TP3B475(1)035(2)1500AS	1.7	6	1.500	0.24
4.7	C	TP3C475(1)035(2)1900AS	1.6	6	1.900	0.24
4.7	C	TP3C475(1)035(2)0500AS	1.6	6	0.500	0.47
4.7	D	TP3D475(1)035(2)1300AS	1.6	6	1.300	0.34
4.7	D	TP3D475(1)035(2)0450AS	1.6	6	0.450	0.58

Note



- Part number definitions:
 - (1) Capacitance tolerance codes: K, M
 - (2) Terminations and packaging codes: C, D, E, F, V, U, T, W



STANDARD RATINGS						
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	MAX. ESR AT +25 °C 100 kHz (Ω)	MAX. RIPPLE 100 kHz I_{RMS} (A)
35 V _{DC} AT +85 °C; 23 V _{DC} AT +125 °C						
6.8	C	TP3C685(1)035(2)1800AS	2.4	6	1.800	0.25
6.8	C	TP3C685(1)035(2)0475AS	2.4	6	0.475	0.48
6.8	D	TP3D685(1)035(2)1800AS	2.4	6	1.800	0.37
6.8	D	TP3D685(1)035(2)1100AS	2.4	6	1.100	0.37
6.8	D	TP3D685(1)035(2)0300AS	2.4	6	0.300	0.71
10	C	TP3C106(1)035(2)1600AS	3.5	6	1.600	0.26
10	C	TP3C106(1)035(2)0450AS	3.5	6	0.450	0.49
10	D	TP3D106(1)035(2)0800AS	3.5	6	0.800	0.43
10	D	TP3D106(1)035(2)0300AS	3.5	6	0.300	0.71
10	D	TP3D106(1)035(2)0250AS	3.5	6	0.250	0.77
10	D	TP3D106(1)035(2)0135AS	3.5	6	0.135	1.05
15	D	TP3D156(1)035(2)0700AS	5.3	6	0.700	0.46
15	D	TP3D156(1)035(2)0300AS	5.3	6	0.300	0.71
15	D	TP3D156(1)035(2)0260AS	5.3	6	0.260	0.76
15	D	TP3D156(1)035(2)0225AS	5.3	6	0.225	0.82
22	D	TP3D226(1)035(2)0600AS	7.7	6	0.600	0.50
22	D	TP3D226(1)035(2)0300AS	7.7	6	0.300	0.71
22	D	TP3D226(1)035(2)0260AS	7.7	6	0.260	0.76
22	D	TP3D226(1)035(2)0200AS	7.7	6	0.200	0.87
22	E	TP3E226(1)035(2)0600AS	7.7	6	0.600	0.52
22	E	TP3E226(1)035(2)0275AS	7.7	6	0.275	0.77
33	D	TP3D336M035(2)0400AS	11.6	6	0.400	0.61
33	D	TP3D336M035(2)0700AS	11.6	6	0.700	0.46
33	E	TP3E336M035(2)0400AS	11.6	6	0.400	0.64
33	E	TP3E336M035(2)0700AS	11.6	6	0.700	0.49
50 V _{DC} AT +85 °C; 33 V _{DC} AT +125 °C						
0.10	A	TP3A104(1)050(2)19R0AS	0.5	4	19.000	0.06
0.10	A	TP3A104(1)050(2)10R0AS	0.5	4	10.000	0.09
0.22	A	TP3A224(1)050(2)15R0AS	0.5	4	15.000	0.07
0.22	B	TP3B224(1)050(2)12R0AS	0.5	4	12.000	0.08
0.22	B	TP3B224(1)050(2)8500AS	0.5	4	8.500	0.10
0.33	B	TP3B334(1)050(2)10R0AS	0.5	4	10.000	0.09
0.33	B	TP3B334(1)050(2)4500AS	0.5	4	4.500	0.14
0.47	B	TP3B474(1)050(2)8400AS	0.5	4	8.400	0.10
0.47	B	TP3B474(1)050(2)4000AS	0.5	4	4.000	0.15
1.0	B	TP3B105(1)050(2)6700AS	0.5	4	6.700	0.11
1.0	C	TP3C105(1)050(2)4600AS	0.5	4	4.600	0.16
1.0	C	TP3C105(1)050(2)1600AS	0.5	4	1.600	0.26
2.2	C	TP3C225(1)050(2)2900AS	1.1	6	2.900	0.20
2.2	C	TP3C225(1)050(2)1500AS	1.1	6	1.500	0.27
2.2	D	TP3D225(1)050(2)2100AS	1.1	6	2.100	0.27
2.2	D	TP3D225(1)050(2)0800AS	1.1	6	0.800	0.43
3.3	C	TP3C335(1)050(2)2500AS	1.7	6	2.500	0.21
3.3	C	TP3C335(1)050(2)1500AS	1.7	6	1.500	0.27
3.3	D	TP3D335(1)050(2)1700AS	1.7	6	1.700	0.30
3.3	D	TP3D335(1)050(2)0800AS	1.7	6	0.800	0.43
4.7	D	TP3D475(1)050(2)1200AS	2.4	6	1.200	0.37
4.7	D	TP3D475(1)050(2)0600AS	2.4	6	0.600	0.50
4.7	D	TP3D475(1)050(2)0300AS	2.4	6	0.300	0.71
6.8	D	TP3D685(1)050(2)0900AS	3.4	6	0.900	0.41
6.8	D	TP3D685(1)050(2)0600AS	3.4	6	0.600	0.50
10	D	TP3D106(1)050(2)0800AS	5.0	6	0.800	0.43
10	D	TP3D106(1)050(2)0550AS	5.0	6	0.550	0.52
10	E	TP3E106(1)050(2)0800AS	5.0	6	0.800	0.45
10	E	TP3E106(1)050(2)0550AS	5.0	6	0.550	0.55
10	E	TP3E106(1)050(2)0300AS	5.0	6	0.300	0.74

Note

- Part number definitions:
 - Capacitance tolerance codes: K, M
 - Terminations and packaging codes: C, D, E, F, V, U, T, W

TYPICAL CURVES AT +25 °C, IMPEDANCE AND ESR VS. FREQUENCY

POWER DISSIPATION

CASE CODE	MAXIMUM PERMISSIBLE POWER DISSIPATION AT +25 °C (W) IN FREE AIR
A	0.075
B	0.085
C	0.110
D	0.150
E	0.165

STANDARD PACKAGING QUANTITY

CASE CODE	UNITS PER REEL	
	7" REEL	13" REEL
A	2000	9000
B	2000	8000
C	500	3000
D	500	2500
E	400	1500

PRODUCT INFORMATION

Guide for Molded Tantalum Capacitors	www.vishay.com/doc?40074
Pad Dimensions	
Packaging Dimensions	
Moisture Sensitivity	www.vishay.com/doc?40135
SELECTOR GUIDES	
Solid Tantalum Selector Guide	www.vishay.com/doc?49053
Solid Tantalum Chip Capacitors	www.vishay.com/doc?40091
FAQ	
Frequently Asked Questions	www.vishay.com/doc?40110



Guide for Molded Tantalum Capacitors

INTRODUCTION

Tantalum electrolytic capacitors are the preferred choice in applications where volumetric efficiency, stable electrical parameters, high reliability, and long service life are primary considerations. The stability and resistance to elevated temperatures of the tantalum / tantalum oxide / manganese dioxide system make solid tantalum capacitors an appropriate choice for today's surface mount assembly technology.

Vishay Sprague has been a pioneer and leader in this field, producing a large variety of tantalum capacitor types for consumer, industrial, automotive, military, and aerospace electronic applications.

Tantalum is not found in its pure state. Rather, it is commonly found in a number of oxide minerals, often in combination with Columbium ore. This combination is known as "tantalite" when its contents are more than one-half tantalum. Important sources of tantalite include Australia, Brazil, Canada, China, and several African countries. Synthetic tantalite concentrates produced from tin slags in Thailand, Malaysia, and Brazil are also a significant raw material for tantalum production.

Electronic applications, and particularly capacitors, consume the largest share of world tantalum production. Other important applications for tantalum include cutting tools (tantalum carbide), high temperature super alloys, chemical processing equipment, medical implants, and military ordnance.

Vishay Sprague is a major user of tantalum materials in the form of powder and wire for capacitor elements and rod and sheet for high temperature vacuum processing.

THE BASICS OF TANTALUM CAPACITORS

Most metals form crystalline oxides which are non-protecting, such as rust on iron or black oxide on copper. A few metals form dense, stable, tightly adhering, electrically insulating oxides. These are the so-called "valve" metals and include titanium, zirconium, niobium, tantalum, hafnium, and aluminum. Only a few of these permit the accurate control of oxide thickness by electrochemical means. Of these, the most valuable for the electronics industry are aluminum and tantalum.

Capacitors are basic to all kinds of electrical equipment, from radios and television sets to missile controls and automobile ignitions. Their function is to store an electrical charge for later use.

Capacitors consist of two conducting surfaces, usually metal plates, whose function is to conduct electricity. They are separated by an insulating material or dielectric. The dielectric used in all tantalum electrolytic capacitors is tantalum pentoxide.

Tantalum pentoxide compound possesses high-dielectric strength and a high-dielectric constant. As capacitors are being manufactured, a film of tantalum pentoxide is applied to their electrodes by means of an electrolytic process. The film is applied in various thicknesses and at various voltages and although transparent to begin with, it takes on different colors as light refracts through it. This coloring occurs on the tantalum electrodes of all types of tantalum capacitors.

Rating for rating, tantalum capacitors tend to have as much as three times better capacitance / volume efficiency than aluminum electrolytic capacitors. An approximation of the capacitance / volume efficiency of other types of capacitors may be inferred from the following table, which shows the dielectric constant ranges of the various materials used in each type. Note that tantalum pentoxide has a dielectric constant of 26, some three times greater than that of aluminum oxide. This, in addition to the fact that extremely thin films can be deposited during the electrolytic process mentioned earlier, makes the tantalum capacitor extremely efficient with respect to the number of microfarads available per unit volume. The capacitance of any capacitor is determined by the surface area of the two conducting plates, the distance between the plates, and the dielectric constant of the insulating material between the plates.

COMPARISON OF CAPACITOR DIELECTRIC CONSTANTS

DIELECTRIC	ϵ DIELECTRIC CONSTANT
Air or vacuum	1.0
Paper	2.0 to 6.0
Plastic	2.1 to 6.0
Mineral oil	2.2 to 2.3
Silicone oil	2.7 to 2.8
Quartz	3.8 to 4.4
Glass	4.8 to 8.0
Porcelain	5.1 to 5.9
Mica	5.4 to 8.7
Aluminum oxide	8.4
Tantalum pentoxide	26
Ceramic	12 to 400K

In the tantalum electrolytic capacitor, the distance between the plates is very small since it is only the thickness of the tantalum pentoxide film. As the dielectric constant of the tantalum pentoxide is high, the capacitance of a tantalum capacitor is high if the area of the plates is large:

$$C = \frac{\epsilon A}{t}$$

where

C = capacitance

ϵ = dielectric constant

A = surface area of the dielectric

t = thickness of the dielectric

Tantalum capacitors contain either liquid or solid electrolytes. In solid electrolyte capacitors, a dry material (manganese dioxide) forms the cathode plate. A tantalum lead is embedded in or welded to the pellet, which is in turn connected to a termination or lead wire. The drawings show the construction details of the surface mount types of tantalum capacitors shown in this catalog.

SOLID ELECTROLYTE TANTALUM CAPACITORS

Solid electrolyte capacitors contain manganese dioxide, which is formed on the tantalum pentoxide dielectric layer by impregnating the pellet with a solution of manganous nitrate. The pellet is then heated in an oven, and the manganous nitrate is converted to manganese dioxide.

The pellet is next coated with graphite, followed by a layer of metallic silver, which provides a conductive surface between the pellet and the leadframe.

Molded Chip tantalum capacitor encases the element in plastic resins, such as epoxy materials. The molding compound has been selected to meet the requirements of UL 94 V-0 and outgassing requirements of ASTM E-595. After assembly, the capacitors are tested and inspected to assure long life and reliability. It offers excellent reliability and high stability for consumer and commercial electronics with the added feature of low cost


Surface mount designs of "Solid Tantalum" capacitors use lead frames or lead frameless designs as shown in the accompanying drawings.

TANTALUM CAPACITORS FOR ALL DESIGN CONSIDERATIONS

Solid electrolyte designs are the least expensive for a given rating and are used in many applications where their very small size for a given unit of capacitance is of importance. They will typically withstand up to about 10 % of the rated DC working voltage in a reverse direction. Also important are their good low temperature performance characteristics and freedom from corrosive electrolytes.

Vishay Sprague patented the original solid electrolyte capacitors and was the first to market them in 1956. Vishay Sprague has the broadest line of tantalum capacitors and has continued its position of leadership in this field. Data sheets covering the various types and styles of Vishay Sprague capacitors for consumer and entertainment electronics, industry, and military applications are available where detailed performance characteristics must be specified.

MOLDED CHIP CAPACITOR



COMMERCIAL PRODUCTS


SOLID TANTALUM CAPACITORS - MOLDED CASE						
SERIES	293D	793DX-CTC3-CTC4	593D	TR3	TP3	TL3
PRODUCT IMAGE						
TYPE	Surface mount TANTAMOUNT™, molded case					
FEATURES	Standard industrial grade	CECC approved	Low ESR	Low ESR	High performance, automotive grade	Very low DCL
TEMPERATURE RANGE	-55 °C to +125 °C					
CAPACITANCE RANGE	0.1 µF to 1000 µF	0.1 µF to 100 µF	1 µF to 470 µF	0.47 µF to 1000 µF	0.1 µF to 470 µF	0.1 µF to 470 µF
VOLTAGE RANGE	4 V to 75 V	4 V to 50 V	4 V to 50 V	4 V to 75 V	4 V to 50 V	4 V to 50 V
CAPACITANCE TOLERANCE	± 10 %, ± 20 %					
LEAKAGE CURRENT	0.01 CV or 0.5 µA, whichever is greater					0.005 CV or 0.25 µA, whichever is greater
DISSIPATION FACTOR	4 % to 30 %	4 % to 6 %	4 % to 15 %	4 % to 30 %	4 % to 15 %	4 % to 15 %
CASE CODES	A, B, C, D, E	A, B, C, D	A, B, C, D, E	A, B, C, D, E, W	A, B, C, D, E	A, B, C, D, E
TERMINATION	100 % matte tin standard, tin / lead available					

SOLID TANTALUM CAPACITORS - MOLDED CASE			
SERIES	TH3	TH4	TH5
PRODUCT IMAGE			
TYPE	Surface mount TANTAMOUNT™, molded case		
FEATURES	High temperature +150 °C, automotive grade	High temperature +175 °C, automotive grade	Very high temperature +200 °C
TEMPERATURE RANGE	-55 °C to +150 °C	-55 °C to +175 °C	-55 °C to +200 °C
CAPACITANCE RANGE	0.33 µF to 220 µF	10 µF to 100 µF	4.7 µF to 100 µF
VOLTAGE RANGE	6.3 V to 50 V	6.3 V to 35 V	5 V to 24 V
CAPACITANCE TOLERANCE	± 10 %, ± 20 %		
LEAKAGE CURRENT	0.01 CV or 0.5 µA, whichever is greater		
DISSIPATION FACTOR	4 % to 8 %	4.5 % to 8 %	6 % to 10 %
CASE CODES	A, B, C, D, E	B, C, D, E	D, E
TERMINATION	100 % matte tin standard, tin / lead and gold plated available	100 % matte tin	Gold plated

HIGH RELIABILITY PRODUCTS

SOLID TANTALUM CAPACITORS - MOLDED CASE				
SERIES	TM3	T83	CWR11	95158
PRODUCT IMAGE				
TYPE	TANTAMOUNT™, molded case, hi-rel.	TANTAMOUNT™, molded case, hi-rel. COTS	TANTAMOUNT™, molded case, DLA approved	
FEATURES	High reliability, for medical Instruments	High reliability, standard and low ESR	MIL-PRF-55365/8 qualified	Low ESR
TEMPERATURE RANGE	-55 °C to +125 °C			
CAPACITANCE RANGE	1 µF to 220 µF	0.1 µF to 470 µF	0.1 µF to 100 µF	4.7 µF to 220 µF
VOLTAGE RANGE	4 V to 20 V	4 V to 63 V	4 V to 50 V	
CAPACITANCE TOLERANCE	± 10 %, ± 20 %		± 5 %, ± 10 %, ± 20 %	± 10 %, ± 20 %
LEAKAGE CURRENT	0.005 CV or 0.25 µA, whichever is greater	0.01 CV or 0.5 µA, whichever is greater		
DISSIPATION FACTOR	4 % to 8 %	4 % to 15 %	4 % to 6 %	4 % to 12 %
CASE CODES	A, B, C, D, E	A, B, C, D, E	A, B, C, D	C, D, E
TERMINATION	100 % matte tin; tin / lead	100 % matte tin; tin / lead; tin / lead solder fused	Tin / lead; tin / lead solder fused	Tin / lead solder plated; gold plated

PLASTIC TAPE AND REEL PACKAGING in inches [millimeters]




Notes

- Metric dimensions will govern. Dimensions in inches are rounded and for reference only
- A_0 , B_0 , K_0 , are determined by the maximum dimensions to the ends of the terminals extending from the component body and / or the body dimensions of the component. The clearance between the ends of the terminals or body of the component to the sides and depth of the cavity (A_0 , B_0 , K_0) must be within 0.002" (0.05 mm) minimum and 0.020" (0.50 mm) maximum. The clearance allowed must also prevent rotation of the component within the cavity of not more than 20°
- Tape with components shall pass around radius "R" without damage. The minimum trailer length may require additional length to provide "R" minimum for 12 mm embossed tape for reels with hub diameters approaching N minimum
- This dimension is the flat area from the edge of the sprocket hole to either outward deformation of the carrier tape between the embossed cavities or to the edge of the cavity whichever is less
- This dimension is the flat area from the edge of the carrier tape opposite the sprocket holes to either the outward deformation of the carrier tape between the embossed cavity or to the edge of the cavity whichever is less
- The embossed hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location shall be applied independent of each other
- B_1 dimension is a reference dimension tape feeder clearance only

CASE CODE	TAPE SIZE	B_1 (MAX.)	D_1 (MIN.)	F	K_0 (MAX.)	P_1	W
MOLDED CHIP CAPACITORS; ALL TYPES							
A	8 mm	0.165	0.039	0.138 ± 0.002	0.094	0.157 ± 0.004	0.315 ± 0.012
B		[4.2]	[1.0]	[3.5 ± 0.05]	[2.4]	[4.0 ± 1.0]	[8.0 ± 0.30]
C							
D	12 mm	0.32	0.059	0.217 ± 0.00	0.177	0.315 ± 0.004	0.472 ± 0.012
E		[8.2]	[1.5]	[5.5 ± 0.05]	[4.5]	[8.0 ± 1.0]	[12.0 ± 0.30]
W							

RECOMMENDED REFLOW PROFILES


Capacitors should withstand reflow profile as per J-STD-020 standard, three cycles.



PROFILE FEATURE	SnPb EUTECTIC ASSEMBLY	LEAD (Pb)-FREE ASSEMBLY
Preheat / soak		
Temperature min. ($T_{s \text{ min.}}$)	100 °C	150 °C
Temperature max. ($T_{s \text{ max.}}$)	150 °C	200 °C
Time (t_s) from ($T_{s \text{ min.}}$ to $T_{s \text{ max.}}$)	60 s to 120 s	60 s to 120 s
Ramp-up		
Ramp-up rate (T_L to T_p)	3 °C/s max.	3 °C/s max.
Liquidus temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60 s to 150 s	60 s to 150 s
Peak package body temperature (T_p)	Depends on case size - see table below	
Time (t_p) within 5 °C of the specified classification temperature (T_C)	20 s	30 s
Time 25 °C to peak temperature	6 min max.	8 min max.
Ramp-down		
Ramp-down rate (T_p to T_L)	6 °C/s max.	6 °C/s max.

PEAK PACKAGE BODY TEMPERATURE (T_p)

CASE CODE	PEAK PACKAGE BODY TEMPERATURE (T_p)	
	SnPb EUTECTIC PROCESS	LEAD (Pb)-FREE PROCESS
A, B, C	235 °C	260 °C
D, E, W	220 °C	250 °C

PAD DIMENSIONS in inches [millimeters]


CASE CODE	A (MIN.)	B (NOM.)	C (NOM.)	D (NOM.)
MOLDED CHIP CAPACITORS, ALL TYPES				
A	0.071 [1.80]	0.067 [1.70]	0.053 [1.35]	0.187 [4.75]
B	0.118 [3.00]	0.071 [1.80]	0.065 [1.65]	0.207 [5.25]
C	0.118 [3.00]	0.094 [2.40]	0.118 [3.00]	0.307 [7.80]
D	0.157 [4.00]	0.098 [2.50]	0.150 [3.80]	0.346 [8.80]
E	0.157 [4.00]	0.098 [2.50]	0.150 [3.80]	0.346 [8.80]
W	0.185 [4.70]	0.098 [2.50]	0.150 [3.80]	0.346 [8.80]



GUIDE TO APPLICATION

1. **AC Ripple Current:** the maximum allowable ripple current shall be determined from the formula:

$$I_{RMS} = \sqrt{\frac{P}{R_{ESR}}}$$

where,

P = power dissipation in W at +25 °C as given in the tables in the product datasheets (Power Dissipation).

R_{ESR} = the capacitor equivalent series resistance at the specified frequency

2. **AC Ripple Voltage:** the maximum allowable ripple voltage shall be determined from the formula:

$$V_{RMS} = I_{RMS} \times Z$$

or, from the formula:

$$V_{RMS} = Z \sqrt{\frac{P}{R_{ESR}}}$$

where,

P = power dissipation in W at +25 °C as given in the tables in the product datasheets (Power Dissipation).

R_{ESR} = the capacitor equivalent series resistance at the specified frequency

Z = the capacitor impedance at the specified frequency

- 2.1 The sum of the peak AC voltage plus the applied DC voltage shall not exceed the DC voltage rating of the capacitor.
- 2.2 The sum of the negative peak AC voltage plus the applied DC voltage shall not allow a voltage reversal exceeding 10 % of the DC working voltage at +25 °C.
3. **Reverse Voltage:** solid tantalum capacitors are not intended for use with reverse voltage applied. However, they have been shown to be capable of withstanding momentary reverse voltage peaks of up to 10 % of the DC rating at 25 °C and 5 % of the DC rating at +85 °C.
4. **Temperature Derating:** if these capacitors are to be operated at temperatures above +25 °C, the permissible RMS ripple current shall be calculated using the derating factors as shown:

TEMPERATURE (°C)	DERATING FACTOR
+25	1.0
+85	0.9
+125	0.4
+150 ⁽¹⁾	0.3
+175 ⁽¹⁾	0.2
+200 ⁽¹⁾	0.1

Note

⁽¹⁾ Applicable for dedicated high temperature product series

5. **Power Dissipation:** power dissipation will be affected by the heat sinking capability of the mounting surface. Non-sinusoidal ripple current may produce heating effects which differ from those shown. It is important that the equivalent I_{RMS} value

be established when calculating permissible operating levels. (Power dissipation calculated using +25 °C temperature rise).

6. **Printed Circuit Board Materials:** molded capacitors are compatible with commonly used printed circuit board materials (alumina substrates, FR4, FR5, G10, PTFE-fluorocarbon and porcelainized steel).

7. **Attachment:**

- 7.1 **Solder Paste:** the recommended thickness of the solder paste after application is 0.007" ± 0.001" [0.178 mm ± 0.025 mm]. Care should be exercised in selecting the solder paste. The metal purity should be as high as practical. The flux (in the paste) must be active enough to remove the oxides formed on the metallization prior to the exposure to soldering heat. In practice this can be aided by extending the solder preheat time at temperatures below the liquidous state of the solder.

- 7.2 **Soldering:** capacitors can be attached by conventional soldering techniques; vapor phase, convection reflow, infrared reflow, wave soldering, and hot plate methods. The soldering profile charts show recommended time / temperature conditions for soldering. Preheating is recommended. The recommended maximum ramp rate is 3 °C per second. Attachment with a soldering iron is not recommended due to the difficulty of controlling temperature and time at temperature. The soldering iron must never come in contact with the capacitor. For details see www.vishay.com/doc?40214.

- 7.2.1 **Backward and Forward Compatibility:** capacitors with SnPb or 100 % tin termination finishes can be soldered using SnPb or lead (Pb)-free soldering processes.

8. **Cleaning (Flux Removal) After Soldering:** molded capacitors are compatible with all commonly used solvents such as TES, TMS, Prelete, Chloroethane, Terpene and aqueous cleaning media. However, CFC / ODS products are not used in the production of these devices and are not recommended. Solvents containing methylene chloride or other epoxy solvents should be avoided since these will attack the epoxy encapsulation material.

- 8.1 When using ultrasonic cleaning, the board may resonate if the output power is too high. This vibration can cause cracking or a decrease in the adherence of the termination. DO NOT EXCEED 9W/l at 40 kHz for 2 min.

9. **Recommended Mounting Pad Geometries:** proper mounting pad geometries are essential for successful solder connections. These dimensions are highly process sensitive and should be designed to minimize component rework due to unacceptable solder joints. The dimensional configurations shown are the recommended pad geometries for both wave and reflow soldering techniques. These dimensions are intended to be a starting point for circuit board designers and may be fine tuned if necessary based upon the peculiarities of the soldering process and / or circuit board design.



Molded Chip Tantalum Capacitors, Automotive Grade

ELECTRICAL PERFORMANCE CHARACTERISTICS					
ITEM	PERFORMANCE CHARACTERISTICS				
Category temperature range	-55 °C to +85 °C (to +125 °C / +150 °C / +175 °C with voltage derating - refer to graph "Category Voltage vs. Temperature") ⁽¹⁾				
Capacitance tolerance	± 20 %, ± 10 %, tested via bridge method, at 25 °C, 120 Hz				
Dissipation factor	Limits per Standard Ratings table. Tested via bridge method, at 25 °C, 120 Hz				
ESR	Limits per Standard Ratings table. Tested via bridge method, at 25 °C, 100 kHz				
Leakage current	After application of rated voltage applied to capacitors for 5 min using a steady source of power with 1 kΩ resistor in series with the capacitor under test, leakage current at 25 °C is not more than 0.01 CV or 0.5 μA, whichever is greater. <i>Note that the leakage current varies with temperature and applied voltage. See graph "Typical Leakage Current Temperature Factor" for the appropriate adjustment factor.</i>				
Capacitance change by temperature	+30 % max. (at +175 °C) +20 % max. (at +125 °C and +150 °C) +10 % max. (at +85 °C) -10 % max. (at -55 °C)				
Reverse voltage	Capacitors are capable of withstanding peak voltages in the reverse direction equal to: 10 % of the DC rating at +25 °C 5 % of the DC rating at +85 °C 1 % of the DC rating at +125 °C				
Ripple current	For maximum ripple current values (at 25 °C) refer to relevant datasheet. If capacitors are to be used at temperatures above +25 °C, the permissible RMS ripple current (or voltage) shall be calculated using the derating factors: 1.0 at +25 °C 0.9 at +85 °C 0.4 at +125 °C 0.3 at +150 °C 0.2 at +175 °C				
Maximum operating and surge voltages vs. temperature	+85 °C		+125 °C		+150 °C / +175 °C
	RATED VOLTAGE (V)	SURGE VOLTAGE (V)	CATEGORY VOLTAGE (V)	SURGE VOLTAGE (V)	CATEGORY VOLTAGE (V)
	4	5.2	2.7	3.4	n/a
	6.3	8	4	5	3
	10	13	7	8	5
	16	20	10	12	8
	20	26	13	16	10
	25	32	17	20	12.5
	35	46	23	28	17.5
	50	65	33	40	25
	50 ⁽²⁾	60	33	40	n/a
	63	75	42	50	n/a
	75 ⁽³⁾	75	50	50	n/a

Notes

- All information presented in this document reflects typical performance characteristics

⁽¹⁾ Series TH3 - up to 150 °C; TH4 - up to 175 °C

⁽²⁾ Capacitance value 15 μF and higher

⁽³⁾ For 293D and TR3 only




RECOMMENDED VOLTAGE DERATING GUIDELINES (for temperature below +85 °C)

VOLTAGE RAIL	CAPACITOR VOLTAGE RATING
≤ 3.3	6.3
5	10
10	20
12	25
15	35
≥ 24	50 or series configuration

Notes

- For temperatures above +85 °C the same voltage derating ratio is recommended, but with respect to category voltage.
Up to +85 °C: category voltage = rated voltage
At +125 °C: category voltage = 2/3 of rated voltage
At 150 °C / 175 °C: category voltage = 1/2 of rated voltage
- For more information about recommended voltage derating see: www.vishay.com/doc?40246


CATEGORY VOLTAGE VS. TEMPERATURE



Note

- Below 85 °C category voltage is equal to rated voltage

TYPICAL LEAKAGE CURRENT FACTOR



Note

- At +25 °C, the leakage current shall not exceed the value listed in the Standard Ratings table.
- At +85 °C, the leakage current shall not exceed 10 times the value listed in the Standard Ratings table.
- At +125 °C, the leakage current shall not exceed 12 times the value listed in the Standard Ratings table.
- At +150 °C, the leakage current shall not exceed 15 times the value listed in the Standard Ratings table.
- At +175 °C, the leakage current shall not exceed 18 times the value listed in the Standard Ratings table

**ENVIRONMENTAL PERFORMANCE CHARACTERISTICS**

ITEM	CONDITION	POST TEST PERFORMANCE	
High temperature exposure (storage)	MIL-STD-202, method 108 1000 h, at maximum rated temperature, unpowered	Capacitance change Dissipation factor Leakage current ESR	Within $\pm 20\%$ of initial value Initial specified limit Initial specified limit Initial specified limit
Operational life test at +125 °C	AEC-Q200 1000 h application 2/3 of rated voltage	Capacitance change Dissipation factor Leakage current ESR	Within $\pm 20\%$ of initial value Initial specified limit Shall not exceed 10 times the initial limit Initial specified limit
Operational life test at +150 °C (for TH3) and at +175 °C (for TH4)	AEC-Q200 1000 h application 1/2 of rated voltage	Capacitance change Dissipation factor Leakage current ESR	Within $\pm 20\%$ of initial value Shall not exceed 3 times the initial limit Shall not exceed 10 times the initial limit Shall not exceed 3 times the initial limit
Surge voltage	MIL-PRF-55365: 1000 successive test cycles at 85 °C of surge voltage (as specified in the table above), in series with a 33 Ω resistor at the rate of 30 s ON, 30 s OFF	Capacitance change Dissipation factor Leakage current ESR	Within $\pm 30\%$ of initial value Shall not exceed 1.5 times the initial limit Shall not exceed 2 times the initial limit Shall not exceed 1.5 times the initial limit
Biased humidity test	AEC-Q200 At 85 °C / 85 % RH, 1000 h, with rated voltage applied	Capacitance change Dissipation factor Leakage current ESR	Within $\pm 20\%$ of initial value Shall not exceed 3 times the initial limit Shall not exceed 10 times the initial limit Shall not exceed 3 times the initial limit
Temperature cycling	AEC-Q200 / JESD22, method JA-104 -55 °C / +125 °C, for 1000 cycles	Capacitance change Dissipation factor Leakage current ESR	Within $\pm 20\%$ of initial value Initial specified limit Initial specified limit Initial specified limit

MECHANICAL PERFORMANCE CHARACTERISTICS

ITEM	CONDITION	POST TEST PERFORMANCE	
Vibration	MIL-STD-202, method 204: 10 Hz to 2000 Hz, 5 g peak for 20 min, 12 cycles each of 3 orientations (total 36 cycles), at rated voltage	Capacitance change Dissipation factor Leakage current	Within $\pm 20\%$ of initial value Initial specified limit Initial specified limit
		There shall be no mechanical or visual damage to capacitors post-conditioning.	
Mechanical shock	MIL-STD-202, method 213, condition F, 1500 g peak, 0.5 ms, half-sine	Capacitance change Dissipation factor Leakage current	Within $\pm 20\%$ of initial value Initial specified limit Initial specified limit
		There shall be no mechanical or visual damage to capacitors post-conditioning.	
Resistance to solder heat	MIL-STD-202, method 210, condition D Solder dip 260 °C ± 5 °C, 10 s	Capacitance change Dissipation factor Leakage current	Within $\pm 20\%$ of initial value Initial specified limit Initial specified limit
Resistance to solvents	MIL-STD-202, method 215	Capacitance change Dissipation factor Leakage current	Within $\pm 20\%$ of initial value Initial specified limit Initial specified limit
		There shall be no mechanical or visual damage to capacitors post-conditioning. Body marking shall remain legible.	
Solderability	AEC-Q200 / J-STD-002	Electrical test not required	
Terminal strength / Shear force test	AEC-Q200-006 Apply a pressure load of 17.7 N (1.8 kg) for 60 s horizontally to the center of capacitor side body Exception: for case size 0603 pressure load is 5N	Part should not be sheared off the pads and no body cracking post-conditioning. Electrical test not required.	
Flammability	Encapsulation materials meet UL 94 V-0 with an oxygen index of 32 %	n/a	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

TP3A475K016C2500AS	TP3A106K010C3400AS	TP3A225M010D6300AS	TP3A225M010C6300AS
TP3B107K6R3C1700AS	TP3B155M025C4600AS	TP3B105K035C5000AS	TP3E106K050C0300AS
TP3B336M010C1500AS	TP3B226M010C1900AS	TP3A106K016C1700AS	TP3A225K025C4000AS
TP3A226K010C1500AS	TP3B106K016C0800AS	TP3B106K016C2000AS	TP3B336K010C0600AS
TP3B336M010D1500AS	TP3B475K025C1500AS	TP3C105K050C1600AS	TP3C156K016C0400AS
TP3D106K035C0300AS	TP3D106K050C0550AS	TP3D156K025C0250AS	TP3D156K035C0300AS
TP3D226K035C0200AS	TP3D476K020C0150AS	TP3E107K020C0150AS	TP3E476K025C0200AS
TP3D336M010C0800AS	TP3C107K010D0900AS	TP3D227K010C0125AS	TP3A105K035C7500AS
TP3A334K035C6000AS	TP3D106M035C0300AS	TP3D685K035C1100AS	TP3D686K016C0150AS
TP3C107K010C0200AS	TP3B475M016C2900AS	TP3B226K016C0700AS	TP3D227M010C0100AS
TP3D106K025C1000AS	TP3E107K016V0100AS	TP3D226K016D0800AS	TP3B335K025C3100AS
TP3B225K025C3800AS	TP3C225K035D2900AS	TP3D336M020C0200AS	TP3C475K025C0525AS
TP3D226K020C0225AS	TP3B476K010C1800AS	TP3E226K035C0600AS	TP3A105K020C5500AS
TP3D226M035C0600AS	TP3D336K020C0700AS	TP3C226M016D0350AS	TP3C106M025C1500AS
TP3B226K010D1900AS	TP3C476K016C1000AS	TP3C475M020C2300AS	TP3B106K010C0800AS
TP3D106M035C0800AS	TP3D225K050C2100AS	TP3A104K050C10R0AS	TP3D475K050C0600AS
TP3D226K025C0700AS	TP3B335K016C3500AS	TP3B336K6R3C1900AS	TP3B475K016C1500AS
TP3A226K6R3C2900AS	TP3E337M6R3C0500AS	TP3A105M016C9300AS	TP3C685K020C1900AS
TP3D156K025C0800AS	TP3B476M6R3C1900AS	TP3B475K020C2900AS	TP3C226M025C0400AS
TP3D106K035C0800AS	TP3C156M010C1800AS	TP3B475M010C3400AS	TP3C107K010C0250AS
TP3B476M010C1800AS	TP3A474K025C9000AS	TP3D475M050C0300AS	TP3A225K016C4000AS
TP3C226K6R3C1800AS	TP3C225K035C0900AS	TP3C106K016C0450AS	TP3D225K050C0800AS
TP3A475K016C2000AS	TP3D475K050C0300AS	TP3D107M016C0150AS	TP3D685M050C0900AS
TP3A475K016C5000AS	TP3D336K010C0800AS	TP3C335K035C2100AS	TP3B475K016C2900AS
TP3C226K016C1400AS	TP3C106M035C0450AS	TP3B155K025C4600AS	TP3D107K010C0100AS