

DATA SHEET

SURFACE-MOUNT CERAMIC MULTILAYER CAPACITORS

C-Array

NP0/X7R/Y5V

16 V TO 50 V

sizes 0508 (4 x 0402) / 0612 (4 x 0603)

RoHS compliant & Halogen Free



SCOPE

This specification describes NP0/X7R/Y5V 4-capacitor Array with lead-free terminations.

APPLICATIONS

- Professional electronics
- High density consumer electronics

FEATURES

- Supplied in tape on reel
- Nickel-barrier end termination
- 0508 (4x0402) / 0612 (4x0603) capacitors (of the same capacitance value) per array
- Less than 50% board space of an equivalent discrete component
- High volumetric efficiency
- Increased throughput, by time saved in mounting
- RoHS compliant
- Halogen Free compliant

ORDERING INFORMATION - GLOBAL PART NUMBER, PHYCOMP**CTC & I2NC**

All part numbers are identified by the series, size, tolerance, TC material, packing style, voltage, process code, termination and capacitance value. Please note that 12 digits ordering code will expire at the end of 2010.

YAGEO BRAND ordering code**GLOBAL PART NUMBER (PREFERRED)**

CA XXXX X X XXX X **B** X XXX
 (1) (2) (3) (4) (5) (6) (7)

(1) SIZE – INCH BASED (METRIC)

0508 (1220)

0612 (1632)

(2) TOLERANCE

J = ±5%

K = ±10%

M = ±20%

Z = -20% to +80%

(3) PACKING STYLE

R = Paper/PE taping reel; Reel 7 inch

P = Paper/PE taping reel; Reel 13 inch

(4) TC MATERIAL

NPO

X7R

Y5V

(5) RATED VOLTAGE

7 = 16 V

8 = 25 V

9 = 50 V

(6) PROCESS

N = NP0

B = class 2 material

(7) CAPACITANCE VALUE

2 significant digits+number of zeros

The 3rd digit signifies the multiplying factor, and letter R is decimal point

Example: 121 = $12 \times 10^1 = 120 \text{ pF}$

CONSTRUCTION

The capacitor consists of a rectangular block of ceramic dielectric in which a number of interleaved metal electrodes are contained. This structure gives rise to a high capacitance per unit volume.

The inner electrodes are connected to the two end terminations and finally covered with a layer of plated tin (NiSn).

The terminations are lead-free.

An outline of the structure is shown in Fig. I.




Fig. I Simplified outline

DIMENSIONS

Table I

TYPE	0508 (4 X 0402)	0612 (4 X 0603)
L (mm)	2.0 ±0.15	3.2 ±0.15
W (mm)	1.25 ±0.15	1.60 ±0.15
T _{min.} (mm)	0.50	0.70
T _{max.} (mm)	0.70	0.90
A (mm)	0.28 ±0.10	0.4 ±0.10
B (mm)	0.2 ±0.10	0.3 ±0.20
P (mm)	0.5 ±0.10	0.8 ±0.10

OUTLINES

For dimensions see Table I




Fig. 2 Surface mounted multilayer ceramic capacitor dimension

CAPACITANCE RANGE & THICKNESS FOR 4C-ARRAY
Table 2 Temperature characteristic material from NP0

CAPACITANCE	0508 (4 x 0402)	0612 (4 x 0603)	100V
	50 V	50 V	
10 pF	0.6±0.1	0.8±0.1	0.8±0.1
15 pF			
18 pF			
22 pF			
33 pF			
39 pF			
47 pF			
56 pF			
68 pF			
82 pF			
100 pF			
120 pF			
150 pF			
180 pF			
220 pF			
270 pF			
330 pF			
390 pF			
470 pF			
560 pF			
680 pF			
820 pF			
1.0 nF			

NOTE

Values in shaded cells indicate thickness class in mm

CAPACITANCE RANGE & THICKNESS FOR 4C-ARRAY**Table 3** Temperature characteristic material from X7R

CAPACITANCE	0508 (4 × 0402)			0612 (4 × 0603)		
	16 V	25 V	50 V	16 V	25 V	50 V
180 pF						
220 pF						
270 pF						
330 pF						
390 pF						
470 pF						
560 pF						
680 pF						
820 pF						
1.0 nF			0.6±0.1			
1.2 nF						0.8±0.1
1.5 nF						
1.8 nF						
2.2 nF						
2.7 nF					0.8±0.1	
3.3 nF		0.6±0.1				
3.9 nF				0.8±0.1		
4.7 nF						
5.6 nF						
6.8 nF						
8.2 nF						
10 nF	0.6±0.1					
12 nF						
15 nF						
18 nF						
22 nF						
27 nF						
33 nF						
47 nF						
56 nF						
68 nF						
82 nF						
100 nF						

NOTE

Values in shaded cells indicate thickness class in mm

CAPACITANCE RANGE & THICKNESS FOR 4C-ARRAY

Table 4 Temperature characteristic material from Y5V

CAPACITANCE

0612 (4 x 0603)

25 V

10 nF	0.6±0.1
22 nF	
47 nF	
100 nF	

NOTE

Values in shaded cells indicate thickness class in mm

THICKNESS CLASSES AND PACKING QUANTITY

Table 5

SIZE CODE	THICKNESS CLASSIFICATION	TAPE WIDTH	QUANTITY PER REEL	Ø180 MM / 7 INCH Paper	Ø180 MM / 13 INCH Paper
0508	0.6 ±0.1 mm		8 mm	4,000	20,000
0612	0.8 ±0.1 mm		8 mm	4,000	15,000

ELECTRICAL CHARACTERISTICS**4C-ARRAY DIELECTRIC CAPACITORS; NISN TERMINATIONS**

Unless otherwise stated all electrical values apply at an ambient temperature of 20 ± 1 °C, an atmospheric pressure of 86 to 106 kPa, and a relative humidity of 63 to 67%.

Table 6

DESCRIPTION	VALUE
Capacitance range	10 pF to 100 nF
Rated voltage	
	NP0 50 V
	X7R 0508: 16 V, 0612: 16 V to 50 V
	Y5V 0612: 25 V
Capacitance tolerance	
	NP0 $\pm 5\%$, $\pm 10\%$
	X7R $\pm 10\%$, $\pm 20\%$
	Y5V -20% to $+80\%$
Dissipation factor (D.F.)	
	NP0 $\leq 0.1\%$
	X7R $16\text{ V} \leq 3.5\%$, $25\text{ V} \leq 2.5\%$, $50\text{ V} \leq 2.5\%$ $12\text{ nF} \sim 100\text{ nF}$, $\text{Df} \leq 5\%$
	Y5V $0508 \leq 9\%$, $0612 \leq 7\%$
Insulation resistance after 1 minute at U_r (DC)	$R_{\text{ins}} \geq 10\text{ G}\Omega$ or $R_{\text{ins}} \times C_r \geq 500$ seconds whichever is less
Maximum capacitance change as a function of temperature (temperature characteristic/coefficient):	
	NP0 $\pm 30\text{ ppm}/^\circ\text{C}$
	X7R $\pm 15\%$
	Y5V $+22\%$ to -82%
Operating temperature range:	
	NP0 $-55\text{ }^\circ\text{C}$ to $+125\text{ }^\circ\text{C}$
	X7R $-55\text{ }^\circ\text{C}$ to $+125\text{ }^\circ\text{C}$
	Y5V $-30\text{ }^\circ\text{C}$ to $+85\text{ }^\circ\text{C}$

NP0 0508/0612 50 V

Sample limits (broken lines)
Requirement levels (dotted lines)




Fig. 3 Typical temperature coefficient as a function of temperature




Fig. 4 Typical tan δ as a function of temperature




Fig. 5 Typical capacitance change with respect to the capacitance at 1 V as a function of DC voltage


X7R 0508 16 V


Fig. 6 Typical capacitance change with respect to the capacitance at 1 V as a function of DC voltage at 20 °C




Fig. 7 Typical tan δ as a function of temperature




Fig. 8 Typical capacitance change as a function of temperature

X7R 0612 16 V to 50 V

Curve 1 = 16 V product
Curve 2 = 25 V product
Curve 3 = 50 V product




Fig. 9 Typical capacitance change with respect to the capacitance at 1 V as a function of DC voltage at 25 °C

Curve 1 = 16 V product
Curve 2 = 25 V product
Curve 3 = 50 V product




Fig. 10 Typical tan δ as a function of temperature




Fig. 11 Typical capacitance change as a function of temperature


Y5V 0612 25 V


Fig. 12 Typical capacitance change with respect to the capacitance at 1 V as a function of DC voltage at 25 °C




Fig. 13 Typical tan δ as a function of temperature




Fig. 14 Typical capacitance change as a function of temperature

TESTS AND REQUIREMENTS**Table 7** Test procedures and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Mounting	IEC 60384-21/22	4.3 The capacitors may be mounted on printed-circuit boards or ceramic substrates	No visible damage
Visual Inspection and Dimension Check		4.4 Any applicable method using $\times 10$ magnification	In accordance with specification
Capacitance		4.5.1 Class 1: $f = 1 \text{ MHz}$ for $C \leq 1 \text{ nF}$, measuring at voltage $1 V_{\text{rms}}$ at 20°C $f = 1 \text{ KHz}$ for $C > 1 \text{ nF}$, measuring at voltage $1 V_{\text{rms}}$ at 20°C Class 2: $f = 1 \text{ KHz}$ for $C \leq 10 \mu\text{F}$, measuring at voltage $1 V_{\text{rms}}$ at 20°C $f = 120 \text{ Hz}$ for $C > 10 \mu\text{F}$, measuring at voltage $0.5 V_{\text{rms}}$ at 20°C	Within specified tolerance
Dissipation Factor (D.F.)		4.5.2 Class 1: $f = 1 \text{ MHz}$ for $C \leq 1 \text{ nF}$, measuring at voltage $1 V_{\text{rms}}$ at 20°C $f = 1 \text{ KHz}$ for $C > 1 \text{ nF}$, measuring at voltage $1 V_{\text{rms}}$ at 20°C Class 2: $f = 1 \text{ KHz}$ for $C \leq 10 \mu\text{F}$, measuring at voltage $1 V_{\text{rms}}$ at 20°C $f = 120 \text{ Hz}$ for $C > 10 \mu\text{F}$, measuring at voltage $0.5 V_{\text{rms}}$ at 20°C	In accordance with specification
Insulation Resistance		4.5.3 At U_r (DC) for 1 minute	In accordance with specification

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS									
Temperature Coefficient	4.6	Capacitance shall be measured by the steps shown in the following table. The capacitance change should be measured after 5 min at each specified temperature stage.	<General purpose series> Class1: Δ C/C: ±30ppm Class2: X7R: Δ C/C: ±15% Y5V: Δ C/C: 22~-82% <High Capacitance series> Class2: X7R/X5R: Δ C/C: ±15% Y5V: Δ C/C: 22~-82%									
		<table><tr><th>Step</th><th>Temperature(°C)</th></tr><tr><td>a</td><td>25±2</td></tr><tr><td>b</td><td>Lower temperature±3°C</td></tr><tr><td>c</td><td>25±2</td></tr><tr><td>d</td><td>Upper Temperature±2°C</td></tr><tr><td>e</td><td>25±2</td></tr></table> <p>(1) Class I</p> <p>Temperature Coefficient shall be calculated from the formula as below</p> $\text{Temp. Coefficient} = \frac{C2 - C1}{C1 \times \Delta T} \times 10^6 \text{ [ppm/°C]}$ <p>C1: Capacitance at step c C2: Capacitance at 125°C ΔT: 100°C(=125°C-25°C)</p> <p>(2) Class II</p> <p>Capacitance Change shall be calculated from the formula as below</p> $\Delta C = \frac{C2 - C1}{C1} \times 100\%$ <p>C1: Capacitance at step c C2: Capacitance at step b or d</p>	Step	Temperature(°C)	a	25±2	b	Lower temperature±3°C	c	25±2	d	Upper Temperature±2°C
Step	Temperature(°C)											
a	25±2											
b	Lower temperature±3°C											
c	25±2											
d	Upper Temperature±2°C											
e	25±2											
Adhesion	4.7	A force applied for 10 seconds to the line joining the terminations and in a plane parallel to the substrate	Force size ≥ 0603: 5N size = 0402: 2.5N size = 0201: 1N									

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Bond Strength of Plating on End Face	IEC 60384-21/22 4.8	Mounting in accordance with IEC 60384-22 paragraph 4.3 Conditions: bending 1 mm at a rate of 1 mm/s, radius jig 340 mm	No visible damage <General purpose series> $\Delta C/C$ Class 1: NP0: within $\pm 1\%$ or 0.5 pF, whichever is greater Class2: X5R/X7R/Y5V: $\pm 10\%$ <High Capacitance series> $\Delta C/C$ Class2: X5R/X7R/Y5V: $\pm 10\%$
Resistance to Soldering Heat	4.9	Precondition: 150 $\pm 0/-10$ °C for 1 hour, then keep for 24 ± 1 hours at room temperature Preheating: for size ≤ 1206 : 120 °C to 150 °C for 1 minute Preheating: for size >1206 : 100 °C to 120 °C for 1 minute and 170 °C to 200 °C for 1 minute Solder bath temperature: 260 ± 5 °C Dipping time: 10 ± 0.5 seconds Recovery time: 24 ± 2 hours	Dissolution of the end face plating shall not exceed 25% of the length of the edge concerned <General purpose series> $\Delta C/C$ Class 1: NP0: within $\pm 0.5\%$ or 0.5 pF, whichever is greater Class2: X5R/X7R: $\pm 10\%$ Y5V: $\pm 20\%$ <High Capacitance series> $\Delta C/C$ Class2: X5R/X7R: $\pm 10\%$ Y5V: $\pm 20\%$ D.F. within initial specified value R_{ins} within initial specified value
Solderability	4.10	Preheated the temperature of 80 °C to 140 °C and maintained for 30 seconds to 60 seconds. Test conditions for lead containing solder alloy Temperature: 235 ± 5 °C Dipping time: 2 ± 0.2 seconds Depth of immersion: 10 mm Alloy Composition: 60/40 Sn/Pb Number of immersions: 1 Test conditions for leadfree containing solder alloy Temperature: 245 ± 5 °C Dipping time: 3 ± 0.3 seconds Depth of immersion: 10 mm Alloy Composition: SAC305 Number of immersions: 1	The solder should cover over 95% of the critical area of each termination

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Rapid Change of Temperature	IEC 60384-21/22 4.11	<p>Preconditioning: 150 +0/-10 °C for 1 hour, then keep for 24 ±1 hours at room temperature</p> <p>5 cycles with following detail: 30 minutes at lower category temperature 30 minutes at upper category temperature</p> <p>Recovery time 24 ±2 hours</p>	<p>No visual damage</p> <hr/> <p><General purpose series></p> <p>ΔC/C</p> <p>Class 1: NP0: within ±1% or 1 pF, whichever is greater</p> <p>Class2: X5R/X7R: ±15% Y5V: ±20%</p> <p><High Capacitance series></p> <p>ΔC/C</p> <p>Class2: X5R/X7R: ±15% Y5V: ±20%</p> <hr/> <p>D.F. meet initial specified value R_{ins} meet initial specified value</p>
Damp Heat with U _r Load	4.13	<p>1. Preconditioning, class 2 only: 150 +0/-10 °C /1 hour, then keep for 24 ±1 hour at room temp</p> <p>2. Initial measure: Spec: refer initial spec C, D, IR</p> <p>3. Damp heat test: 500 ±12 hours at 40 ±2 °C; 90 to 95% R.H. 1.0 U_r applied</p> <p>4. Recovery: Class 1: 6 to 24 hours Class 2: 24 ±2 hours</p> <p>5. Final measure: C, D, IR</p> <p>P.S. If the capacitance value is less than the minimum value permitted, then after the other measurements have been made the capacitor shall be precondition according to “IEC 60384 4.1” and then the requirement shall be met.</p>	<p>No visual damage after recovery</p> <hr/> <p><General purpose series></p> <p>ΔC/C</p> <p>Class 1: NP0: within ±2% or 1 pF, whichever is greater</p> <p>Class2: X5R/X7R: ±15%; Y5V: ±30%</p> <p>D.F.</p> <p>Class 1: NP0: ≤ 2 × specified value</p> <p>Class2: X5R/X7R: ≤ 16V: ≤ 7% ≥ 25V: ≤ 5% Y5V: ≤ 15%</p> <p>R_{ins}</p> <p>Class 1: NP0: ≥ 2,500 MΩ or R_{ins} × C_r ≥ 25s whichever is less</p> <p>Class2: X5R/X7R/Y5V: ≥ 500 MΩ or R_{ins} × C_r ≥ 25s whichever is less</p> <p><High Capacitance series></p> <p>ΔC/C</p> <p>Class2: X5R/X7R: ±20%; Y5V: ±30%</p> <p>D.F.</p> <p>Class2: 2 × initial value max</p> <p>R_{ins}</p> <p>Class2: 500 MΩ or R_{ins} × C_r ≥ 25s, whichever is less</p>

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Endurance	IEC 60384-21/22 4.14	<ol style="list-style-type: none"> Preconditioning, class 2 only: 150 \pm 0/-10 $^{\circ}$C /1 hour, then keep for 24 \pm 1 hour at room temp Initial measure: Spec: refer initial spec C, D, IR Endurance test: Temperature: NP0/X7R: 125 $^{\circ}$C X5R/Y5V: 85 $^{\circ}$C Specified stress voltage applied for 1,000 hours: Applied 2.0 \times U_r for general product. Applied 1.5 \times U_r for high cap. product. High voltage series follows with below stress condition: Applied 1.3 \times U_r for 500V series Applied 1.2 \times U_r for 1KV, 2KV, 3KV series Recovery time: 24 \pm 2 hours Final measure: C, D, IR <p>P.S. If the capacitance value is less than the minimum value permitted, then after the other measurements have been made the capacitor shall be precondition according to "IEC 60384 4.1" and then the requirement shall be met.</p>	<p>No visual damage</p> <hr/> <p><General purpose series></p> <p>$\Delta C/C$</p> <p>Class I: NP0: within $\pm 2\%$ or 1 pF, whichever is greater</p> <p>Class2: X5R/X7R: $\pm 15\%$; Y5V: $\pm 30\%$</p> <p>D.F.</p> <p>Class I: NP0: $\leq 2 \times$ specified value</p> <p>Class2: X5R/X7R: $\leq 16V: \leq 7\%$ $\geq 25V: \leq 5\%$</p> <p>Y5V: $\leq 15\%$</p> <p>R_{ins}</p> <p>Class I: NP0: $\geq 4,000 M\Omega$ or $R_{ins} \times C_r \geq 40s$ whichever is less</p> <p>Class2: X5R/X7R/Y5V: $\geq 1,000 M\Omega$ or $R_{ins} \times C_r \geq 50s$ whichever is less</p> <p><High Capacitance series></p> <p>$\Delta C/C$</p> <p>Class 2: X5R/X7R: $\pm 20\%$; Y5V: $\pm 30\%$</p> <p>D.F.</p> <p>Class 2: 2 \times initial value max</p> <p>R_{ins}</p> <p>Class 2: 1,000 $M\Omega$ or $R_{ins} \times C_r \geq 50s$, whichever is less</p>
Voltage Proof	IEC 60384-1 4.6	<p>Specified stress voltage applied for 1 minute</p> <p>$U_r \leq 100 V$: series applied 2.5 U_r</p> <p>100 V < $U_r \leq 200 V$ series applied (1.5 U_r + 100)</p> <p>200 V < $U_r \leq 500 V$ series applied (1.3 U_r + 100)</p> <p>$U_r > 500 V$: 1.3 U_r</p> <p>I: 7.5 mA</p>	No breakdown or flashover

REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 3	May 21, 2014	-	- Product range updated
Version 2	Jun. 17, 2013	-	- Product range updated
Version 1	Feb 05, 2010	-	- The statement of "Halogen Free" on the cover added
Version 0	Jun 22, 2009	-	<ul style="list-style-type: none"> - New datasheet for 4C-Array series with RoHS compliant - Replace from pdf files: 0508_16V to 50V_1, 0612_16V to 50V_0, C-Array_NP0_50V_0508_7, C-Array_NP0_50V_0612_7, C-Array_X7R_16V_25V_50V_0612_6, C-Array_X7R_16V_0508_5, C-Array_Y5V_25V_0508_0, C-Array_Y5V_25V_0612_5 - Define global part number - Description of "Halogen Free compliant" added - Test method and procedure updated

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Yageo:

[CA0612JRNPO9BN101](#) [CA0612KRX7R7BB104](#) [CA0612KRX7R7BB473](#) [CA0612KRX7R8BB473](#)
[CA0612JRNPO9BN220](#) [CA0612JRNPO9BN471](#) [CA0612JRNPO9BN470](#) [CA0612JRNPO9BN221](#)
[CA0612JRNPO9BN331](#) [CA0612ZRY5V8BB104](#) [CA0612KRX7R7BB103](#) [CA0612KRX7R9BB102](#)
[CA0612KRX7R8BB103](#) [CA0612KRX7R8BB153](#)