4DLCD-43480272-IPS Series

4DLCD-43480272-IPS 4DLCD-43480272-IPS-RTP 4DLCD-43480272-IPS-CTP 4DLCD-43480272-IPS-CTP-CLB



Datasheet

Revision 1.4

Copyright © 2024 4D Systems

Contents

1. General Specification	4
2. TFT LCD Display Drawing (Non-Touch Version)	6
3. TFT LCD Display Drawing (Resistive Touch Version)	7
4. TFT LCD Display Drawing (Capacitive Touch Version)	8
5. TFT LCD Display Drawing (Capacitive Touch Version with Cover Lens Bezel)	9
6. Absolute Maximum Ratings	10
7. Electrical Characteristics	10
8. Electro-Optical Characteristics	11
9. Backlight Characteristics	12
10. Interface Descriptions	14
10.1. LCD Interface	14
10.2. CTP Interface	17
11. Backlight Example Circuit	18
12. LCD Timing Details	19
12.1. Timing Chart	19
12.2. Timing Characteristic	21
12.3. SYNC Mode Timing Diagram	21
12.4. SYNC-DE Mode Timing Diagram	21
12.5. Reset Timing	22
12.6. Power On Sequence	22
12.7. Power-off Sequence	23
13. Reliability Test	24
14. Precautions for Using LCD Modules	25
14.1. Handing Precautions	25
14.2. Storage Precautions	27
15. Revision History	28
16. Legal Information	29
16.1. Proprietary Information	29

4DLCD-43480272-IPS Series General Specification

1. General Specification

4DLCD-43480272-IPS is a colour active matrix LCD module incorporating amorphous silicon TFT IPS (Thin Film Transistor). It is composed of a colour TFT-LCD panel, driver IC, FPC and a backlight unit with/without a Resistive/Capacitive Touch Panel (RTP or CTP), and with/without Cover Lens Bezel (CLB). The module display area contains 480 x 272 pixels. This product accords with RoHS environmental criteria.

Part Number Details:

4DLCD - 4D Systems LCD Display

43480272 - 4.3-inch, 480 x 272 Resolution

IPS - In-Plane Switching

RTP - Resistive Touch

CTP - Capacitive Touch

CLB - Cover Lens Bezel






Note

- RoHS compliant
- LCD weight tolerance: ±5%.


4DLCD-43480272-IPS Series General Specification

ITEM	CONTENTS	UNIT
LCD Type	TFT / Transmissive / IPS	
Size	4.3	Inch
Viewing Direction	ALL	
Display Mode	Normally Black	
LCD(W×H×T)	4DLCD-43480272-IPS: 105.50 x 67.20 x 2.90	mm
	4DLCD-43480272-IPS-RTP: 105.50 x 67.20 x 4.10	
	4DLCD-43480272-IPS-CTP: 105.50 x 67.20 x 4.42	
	4DLCD-43480272-IPS-CTP-CLB: 123.04 x 84.46 x 4.42 (Including CLB)	
Active Area (W × H)	95.04 × 53.856	mm
Dot Pitch (W × H)	0.198 × 0.198	mm
Number of Dots (Pixels)	480 (RGB) × 272	
Driver IC	Source: SC7283	
Backlight Type	10 LEDs	
Surface Luminance	4DLCD-43480272-IPS: 600 (typical)	cd/ m2
	4DLCD-43480272-IPS-RTP: 510 (typical)	
	4DLCD-43480272-IPS-CTP: 540 (typical)	
	4DLCD-43480272-IPS-CTP-CLB: 540(typical)	
Interface Type	Parallel RGB 16/24-bit	
Color Depth	16.7M	
Pixel Arrangement	RGB Vertical Stripe	
Surface Treatment	AG	
Input Voltage	3.3(typical)	V
With/Without TP (Touch Panel)	4DLCD-43480272-IPS – Without TP 4DLCD-43480272-IPS-RTP – With Resistive Touch 4DLCD-43480272-IPS-CTP – With Capacitive Touch 4DLCD-43480272-IPS-CTP-CLB – With Capacitive Touch and Cover Lens Bezel	
Weight	4DLCD-43480272-IPS: 48.0	g
	4DLCD-43480272-IPS-RTP: 62.2	
	4DLCD-43480272-IPS-CTP: 69.0	
	4DLCD-43480272-IPS-CTP-CLB: 73.0	


2. TFT LCD Display Drawing (Non-Touch Version)




3. TFT LCD Display Drawing (Resistive Touch Version)



4. TFT LCD Display Drawing (Capacitive Touch Version)



5. TFT LCD Display Drawing (Capacitive Touch Version with Cover Lens Bezel)



4DLCD-43480272-IPS Series Absolute Maximum Ratings

6. Absolute Maximum Ratings

🗀 Absolute Maximum Ratings				
PARAMETER	SYMBOL	MIN	MAX	UNIT
Supply Voltage for LCD Logic	VDD/VCC	-0.3	4.0	V
Supply Voltage for TP Logic	VDD/VCC-VSS	-	3.6	V
Input Voltage for Logic	VIN	VSS-0.5	VDD	V
LED forward voltage (each LED)	IF	-	25	mΑ
Operating Temperature	TOP	-20	70	°C
Storage Temperature	TST	-30	80	°C
Humidity	RH	-	90% (Max60°C)	RH

7. Electrical Characteristics

Electrical Characteristics					
PARAMETER	SYMBOL	MIN	TYP	MAX	UNIT
Power Voltage	VDD/DCC	2.6	3.3	3.6	V
Input Current	IVDD	-	13	-	mΑ
Input Voltage 'H' Level	VIH	0.7 VDD	_	VDD	V
Input Voltage 'L' Level	VIL	0	_	0.3 VDD	V

8. Electro-Optical Characteristics

Electro-Optical Chara	cteristics						
ITEM	SYM	CONDITION	MIN	TYP	MAX	UNIT	REMARKS
Response Time	Tr+Tf	θ=0		30	40	ms	see figure
Contrast Ratio	Cr	0	-	800	-	-	see figure
Luminance Uniformity	δ WHITE	Ø=0	-	80	-	%	see figure
Surface Luminance	Lv	4DLCD-43480272	-	600	-	cd/ m2	see figure
		4DLCD-43480272-RTP	-	510	-	cd/ m2	
		4DLCD-43480272-CTP	-	540	-	cd/ m2	
		4DLCD-43480272-CTP-CLB	-	540	-	cd/ m2	
Viewing Angle Range	θ	Ø = 90°	70	80	-	deg	see figure
	θ	Ø = 270°	70	80	-	deg	
	θ	Ø = 0°	70	80	-	deg	
	θ	Ø = 180°	70	80	-	deg	
CIE (x,y) Cromacity	Red: x			0.629			
	Red: y			0.326			
	Green: x	θ=0°		0.337			
	Green: y	Ø=0°	-0.1	0.546	+0.1		see figure
	Blue: x	Ta=25		0.136			
	Blue: y			0.142			
	White: x			0.320			
	White: y			0.345			

4DLCD-43480272-IPS Series Backlight Characteristics

9. Backlight Characteristics

Backlight Characteristics					
PARAMETER	SYMBOL	MIN	TYP	MAX	UNIT
Voltage for LED backlight (Each LED)	VI	3.0	3.2	3.4	V
Voltage for LED backlight (entire String – 10 LEDs)	VISTRING	15	16	17	mΑ
Current for LED backlight (Each LED)	II	-	20	30	mΑ
Current for LED backlight (entire String – 10 LEDs)	IISTRING	-	20	30	mΑ
LED Lifetime (50% of original brightness)	-	30000	-	-	Hrs

Note

The LED lifetime is defined as the module brightness decreasing to 50% original brightness at Ta=25°C.

1. Contrast Ratio(CR) is defined mathematically as below, for more information see figure.

$$Contrast \ Ratio = \frac{Average \ Surface \ Luminance \ with \ all \ white \ pixels \ (P1, \ P2, \ P3, \ P4, \ P5)}{Average \ Surface \ Luminance \ with \ all \ black \ pixels \ (P1, \ P2, \ P3, \ P4, \ P5)}$$


Surface luminance is the LCD surface from the surface with all pixels displaying white. For more information, see figure.

$$Lv = \text{Average Surface Luminance with all white pixels (P1, P2, P3, P4, P5)}$$

3. The uniformity in surface luminance δ WHITE is determined by measuring luminance at each test position 1 through 5, and then dividing the maximum luminance of 5 points luminance by the minimum luminance of 5 points luminance. For more information, see figure.


$$\delta \text{WHITE} = \frac{\text{Minimum Surface Luminance with all white pixels (P1, P2, P3, P4, P5)}}{\text{Maximum Surface Luminance with all white pixels (P1, P2, P3, P4, P5)}}$$

- 4. Response time is the time required for the display to transition from white to black (Rise Time, Tr) and from black to white (Decay Time, Tf). For additional information see figure. The test equipment is the Autronic-Melchers ConoScope series.
- 5. CIE (x, y) chromaticity, the x and y value is determined by measuring luminance at each test position 1 through 5, and then making the average value.
- 6. Viewing angle is the angle at which the contrast ratio is greater than 2. For the TFT module, the contrast ratio is greater than 10. The angles are determined for the horizontal or x-axis and the vertical or y-axis to the z-axis which is normal to the LCD surface. For more information, see figure.
- 7. For viewing angle and response time testing, the testing data is based on the Autronic-Melchers ConoScope series. Instruments for Contrast Ratio, Surface Luminance, Luminance Uniformity, and CIE the test data is based on TOPCONs BM-5 photodetector.




The definition of response time

4DLCD-43480272-IPS Series Backlight Characteristics



Measuring method for Contrast ratio, surface luminance, Luminance uniformity, CIE(x, y) chromaticity



The definition of viewing angle

4DLCD-43480272-IPS Series Interface Descriptions

10. Interface Descriptions

10.1. LCD Interface

BL_V	- 1	LEDK
BL_V	+ 2	LEDA
+3.3V	3	GND
	4	VCC
LCD_R0	. 5	R0
LCD_R1	6	R1
LCD_R2	7	R2
LCD_R3	8	R3
LCD_R4	9	R4
LCD_R5	10	R5
LCD_R6	11	R6
LCD_R7	12	R7
LCD_G0	13	G0
LCD_G1	14	G0 G1
LCD G2	15	G2
LCD_G3	16	
LCD_G3 LCD_G4	17	G3
LCD_G5	18	G4 G5
LCD_G6	19	G6
LCD_G7	20	
LCD_B0	21 22	G7
LCD_B1	22	B0
LCD_B2	23	B1
LCD_B3	24	B2
LCD_B4	25	B3
LCD_B5	25 26 27	B4
LCD_B6	27	B5
LCD_B7	28	B6
·-	29	B7
LCD_DCLK	30	GND
LCD_DISP	31	CLK
LCD_HSYNC	32	DISP
LCD_VSYNC	33	HSYNC
LCD_DE	34	VSYNC
	35	DEN
	36	NC CND
XR*	. 37	GND
YD*	38	XR
XL *	39	YD
YU *	40	XL
•		YU
围	=	

^{*} This has no connection (NC) for Non-touch displays

* This has no connection (NC) for Non-touch displays

24 Bit mode

18 Bit mode

LEDK BL ۷+ 2 LEDA +3.3V 3 GND 4 VCC 5 R0 6 R1 7 LCD R0 R2 LCD R1 8 R3 9 LCD R2 R4 LCD R3 10 R5 LCD R4 11 R6 LCD R5 12 R7 13 G0 14 G1 LCD G0 15 G2 LCD G1 16 G3 LCD G2 17 G4 LCD G3 18 G5 19 LCD G4 G6 LCD G5 20 G7 B0 22 B1 LCD B0 23 B2 LCD B1 24 B3 LCD B2 25 B4 LCD B3 26 B5 LCD B4 B6 LCD B5 28 B7 29 GND LCD_DCLK 30 CLK LCD RESET 31 DISP LCD HSYNC 32 HSYNC LCD VSYNC 33 VSYNC LCD DE 34 DEN 35 NC 36 GND 37 XR 38 YD 39 XL40 YU

4DLCD-43480272-IPS Series LCD Interface

	LCD Interf	ace	
PIN N	NO.SYMBO	LDESCRIPTION	REMAI
1	LED-	Cathode of LED Backlight	
2	LED+	Anode of LED Backlight	
3	GND	Ground	
4	DVDD	Power supply	
5	R0	Red data input R0	Note 1
6	R1	Red data input R1	Note 1
7	R2	Red data input R2	Note 1
8	R3	Red data input R3	Note 1
9	R4	Red data input R4	Note 1
10	R5	Red data input R5	Note 1
11	R6	Red data input R6	Note 1
12	R7	Red data input R7	Note 1
13	GO	Green data input G0	Note 1
14	G1	Green data input G1	Note 1
15	G2	Green data input G2	Note 1
16	G3	Green data input G3	Note 1
17	G4	Green data input G4	Note 1
18	G5	Green data input G5	Note 1
19	G6	Green data input G6	Note 1
20	G7	Green data input G7	Note 1
21	В0	Blue data input B0	Note 1
22	B1	Blue data input B1	Note 1
23	B2	Blue data input B2	Note 1
24	В3	Blue data input B3	Note 1

4DLCD-43480272-IPS Series LCD Interface

PIN N	O.SYMBO	L DESCRIPTION	REMAR
25	B4	Blue data input B4	Note 1
26	B5	Blue data input B5	Note 1
27	В6	Blue data input B6	Note 1
28	В7	Blue data input B7	Note 1
29	GND	Ground	
30	DCLK	Clock for input data. Data latched rising/falling edge of this signal. Default is falling edge.	
31	DISP	Standby mode control. (Normally pull high) STBYB="L", enter standby mode for power saving. Timing controller source driver will turn off, all outputs are Hi-Z. STBYB="H", normal operation.	
32	HS	Horizontal sync input	
33	VS	Vertical sync input	
34	DE	Input data enable control. When DE mode, active High to enable data input (Normally pull low)	
35	NC	No Connection	
36	GND	Ground	
37	XR/ NC	The touch panel X right pin (RTP only, NC for other touch types)	Note 2
38	YD/ NC	The touch panel Y down pin (RTP only, NC for other touch types)	Note 2
39	XL/ NC	The touch panel X left pin (RTP only, NC for other touch types)	Note 2
40	YU/ NC	The touch panel Y up pin (RTP only, NC for other touch types)	Note 2

Note

- 1. For applications that use less than 24 bits, pins are tied to the ground to reduce the total bits used.
- 2. Pins 37, 38, 39 and, 40 are only applicable to touchscreen displays (4DLCD-xxxxxxxx-RTP).

4DLCD-43480272-IPS Series CTP Interface

10.2. CTP Interface

The Capacitive Touch is driven by a **Focaltech FT5446** capacitive touch driver IC, which utilizes an I2C interface, and is capable of 5-point touch.

Сар	acitive To	uch Interface	
PIN NO.	SYMBOL	DESCRIPTION	REMARK
1	NC	No Connect	Only connected to the CTP Panel, not connected to the LCD itself
2	NC	No Connect	
3	RST	Reset pin	
4	GND	Ground	
5	INT	Interrupt signal from CTP	
6	SDA	I2C SDA	
7	SCL	I2C SCL	N/A for Non-touch and RTP models.
8	GND	Ground	
9	GND	Ground	
10	VDD	Power Supply (3.3V)	

4DLCD-43480272-IPS Series Backlight Example Circuit

11. Backlight Example Circuit


The backlight circuit of this LCD needs an appropriate backlight driver. It can not be simply driven directly by a 3.3V or 5.0V supply like smaller displays, this is because of the number of LEDs connected in series and parallel, which is known as an LED String. A backlight driver is required to boost the voltage from the input supply to the requirements for the LED string.

There are many backlight driver ICs on the market. Some examples are:

- Texas Instruments TPS61165
- Texas Instruments TPS61080
- On-Semi FAN5333B

On selecting the backlight driver, ensure it is capable of driving the number of LEDs in the string featured in this display, and it supports the input voltage you are looking to supply. Often 3.3V or 5V is possible to supply into the backlight drivers, and it will boost it to the required output based on the requirements of the leds. The current can then be set with a resistor. Please refer to the datasheet for the selected Driver IC of your choice.

In this example, the TPS61165 is depicted.




The RSet calculation is found in the Datasheet for the backlight driver. Each one will vary, as well as the circuit and the components required. Please refer to their datasheets.

Refer to the Backlight Characteristics section for information specific to the backlight requirements, as well as the drawing of the display to see the configuration of the backlight LED string.

4DLCD-43480272-IPS Series LCD Timing Details

12. LCD Timing Details

12.1. Timing Chart



Timing parameter (VDD=3.3V, GND=0V, Ta=25°C)

4DLCD-43480272-IPS Series Timing Chart


□ Timing Chart						
PARAMETER	SYMBOL	MIN	TYP	MAX	UNIT	CONDITION
CLK Clock Time	Tclk	1/Max(FCLK)	-	1/Min(FCLK)	ns	-
CLK Pulse Duty	Tchw	40	50	60	%	TCLK
HSYNC to CLK	Thc	-	-	1	CLK	-
HSYNC Width	Thwh	1	-	-	CLK	-
VSYNC Width	Tvwh	1	-	-	ns	-
HSYNC Period Time	Th	60	63.56	67	ns	-
VSYNC Set-up Time	Tvst	12	-	-	ns	-
VSYNC Hold Time	Tvhd	12	-	_	ns	-
HSYNC Setup Time	Thst	12	-	-	ns	-
HSYNC Hold Time	Thhd	12	-	-	ns	-
Data Set-up Time	Tdsu	12	-	-	ns	D00~D23 to CLK
Data Hold Time	Tdhd	12	-	-	ns	D00~D23 to CLK
DEN Set-up Time	Tesu	12	-	-	ns	DEN to CLK

4DLCD-43480272-IPS Series Timing Characteristic


12.2. Timing Characteristic

Timing Character	istic					
ITEM	SYMBOL	MIN	TYP	MAX	UNIT	
DCLK Frequency	Fclk	8	9	12	MHz	
DCLK Period	Tclk	83	111	125	Ns	
Hsync	Period Time: Th	485	531	598	DCLK	
	Display Period: Thdisp	-	480	-	DCLK	By H BLANKING setting
	Back Porch: Thbp	3	43	-	DCLK	
	Front Porch: Thfp	2	8	75	DCLK	
	Pulse Width: Thw	2	4	43	DCLK	
Vsync	Period Time: Tv	276	292	321	Н	
	Display Period: Tvdisp	-	272	-	Н	
	Back Porch: Thbp	2	12	12	Н	By V BLANKING setting
	Front Porch: Thfp	2	8	37	Н	
	Pulse Width: Thw	2	4	12	Н	

12.3. SYNC Mode Timing Diagram




12.4. SYNC-DE Mode Timing Diagram



4DLCD-43480272-IPS Series Reset Timing

12.5. Reset Timing




🗀 Reset Tim	Reset Timing						
SIGNAL	SYMBOL	PARAMETER	MIN	MAX	UNIT		
RESET	tRW	Reset low pulse width	40	-	us		
	tRT	Reset complete time	-	5 (note1)	ms		
			-	120 (note2)	ms		




- 1. When reset applied during SLPIN mode
- 2. When reset applied during SLPOUT mode.

12.6. Power On Sequence



4DLCD-43480272-IPS Series Power-off Sequence

12.7. Power-off Sequence





When normally-black LC is used, please send a black pattern to discharge the panel. When normally-white LC is used, please send a white pattern to discharge the panel.

4DLCD-43480272-IPS Series Reliability Test

13. Reliability Test

	Reliability Test		
No.	SYMBOL	TEST CONDITION	REMARK
1	High Temperature Storage	80°C±2°C 96H Restore 2H at 25°C Power off	
2	Low Temperature Storage	-30°C±2°C 96H Restore 2H at 25°C Power off	
3	High Temperature Operation	70°C±2°C 96H Power on	
4	Low Temperature Operation	-20°C±2°C 96H Power on	
5	High Temperature & Humidity Operation	60°C±2°C 90%RH 96H Power on	After test cosmetic and electrical defects should not happen.
6	Temperature Cycle	-20°C←→25°C←→70°C 30min 5min 30min After 10 cycles, restore 2H at 25°C Power off	
7	Vibration Test	10Hz~150Hz, 100m/s ² , 120min	
8	Shock Test	Half-sinewave, 300m/s ² , 11ms	

Note

The Displays are of the highest rated 'Grade A', which allows for 0-4 defective pixels. A defective pixel could be solid Black (Dead), White, Red, Green or Blue.

14. Precautions for Using LCD Modules

14.1. Handing Precautions

- The display panel is made of glass and a polarizer. The glass is fragile. It tends to be chipped during handling, especially on the edges. Please avoid dropping or jarring. Please be careful not subject it to a mechanical shock by dropping it on impact.
- If the display panel is damaged and the liquid crystal substance leaks out, be sure not to get any of it in your mouth. If the substance contacts your skin or clothes, wash it off using soap and water.
- Do not apply excessive force to the display surface or the adjoining areas since this may cause the color tone to vary. Do not touch the display with bare hands. This will stain the display area and degrade insulation between terminals (some cosmetics are determined by the polarizer).
- The polarizer covering the display surface of the LCD module is soft and easily scratched. Handle this polarizer carefully. Do not touch, push or rub the exposed polarizer with anything harder than an HB pencil lead (e.g., glass, tweezers, etc.). Do not put or attach anything to the display area to avoid leaving marks on it.

 Condensation on the surface and contact with terminals due to cold temperatures will damage, stain or contaminate the polarizer. After products are tested at low temperatures they must be warmed up in a container before coming into contact with room-temperature air.
- If the display surface becomes contaminated, breathe on the surface and gently wipe it with a soft dry cloth. If it is heavily contaminated, moisten the cloth with one of the following solvents
 - Isopropyl alcohol
 - Ethyl alcohol Do not scrub hard as it might damage the display surface.
- Solvents other than those mentioned above may damage the polarizer. Especially the following.
 - Water
 - Ketone
 - Aromatic solvents Wipe off saliva or water drops immediately, contact with water over a long period may cause deformation or color fading. Avoid contact with oil and fat.
- Take necessary precautions to minimize corrosion of the electrode. Corrosion of the electrodes is accelerated by water droplets, moisture condensation or current flow in a high-humidity environment.
- Install the LCD Module by using the mounting holes. When mounting the LCD module, make sure it is free of twisting, warping and distortion. In particular, do not forcibly pull or bend the I/O cable or the backlight cable.
- Do not attempt to disassemble or process the LCD module.
- NC terminal should be open. Do not connect anything to it.
- If the logic circuit power is off, do not apply input signals.

4DLCD-43480272-IPS Series Handing Precautions

• Control Electro-Static Discharge. Since this module uses a CMOS LSI, the same careful attention should be paid to electrostatic discharge as for an ordinary CMOS IC. To prevent the destruction of the elements by static electricity, ensure that an optimum work environment is maintained.

- Before removing the LCM from its packing case or incorporating it into a set, be sure that the module and your body have the same electric potential. Be sure to ground your body when handling the LCD modules.
- To reduce the amount of static electricity generated, do not conduct assembly and other work under dry conditions. To reduce the generation of static electricity, please ensure that the air in the work environment is not too dry. Relative humidity of 50%-60% is recommended. As much as possible, make the electric potential of your work clothes and that of the workbench the ground potential.
- The LCD module is coated with a film to protect the display surface. Be careful when peeling off this protective film since static electricity may be generated.
- Since the LCM has been assembled and adjusted with a high degree of precision, avoid applying excessive shocks to the module or making any alterations or modifications to it.
 - Do not alter, modify or change the shape of the tab on the metal frame.
 - Do not make extra holes on the printed circuit board, modify its shape or change the positions of the components to be attached.
 - Do not damage or modify the pattern writing on the printed circuit board.
 - Do not modify the zebra rubber strip (conductive rubber) or heat seal connector.
 - Do not drop, bend or twist the LCM.

4DLCD-43480272-IPS Series Storage Precautions

14.2. Storage Precautions

When storing the LCD modules, the following precautions are necessary.

- Store them in a sealed polyethylene bag. If properly sealed, there is no need for the desiccant.
- Store them in a dark place. Do not expose to sunlight or fluorescent light, keep the temperature between 0°C and 35°C, and keep the relative humidity between 40%RH and 60%RH.
- The polarizer surface should not come in contact with any other objects. (We advise you to store them in an anti-static electricity container in which they were shipped. Some Liquid crystals solidify under low temperatures (below the storage temperature range) leading to defective orientation or the generation of air bubbles (black or white). Air bubbles may also be generated if the module is subjected to low temperatures.
- If the LCD modules have been operating for a long time showing the same display patterns, the display patterns may remain on the screen as ghost images and a slight contrast irregularity may also appear. A normal operating status can be regained by suspending use for some time. It should be noted that this phenomenon does not adversely affect performance reliability.
- To minimize the performance degradation of the LCD modules resulting from the destruction caused by static electricity etc., please avoid holding the following sections when handling the modules'
 - The exposed area of the printed circuit board
 - Terminal electrode sections

4DLCD-43480272-IPS Series Revision History

15. Revision History

□ Docum	ent Revision	
REVISION	DATE	COMMENT
1.0	10/09/2020	Initial Version
1.1	22/02/2021	Information clarification / improvement. Updated LED voltage/current information
1.2	09/06/2021	Updating viewing angles and brightness values which were incorrect.
1.3	24/06/2021	Added logic current consumption data, added backlight circuit example.
1.4	20/01/2023	Modified datasheet for web-based documentation

4DLCD-43480272-IPS Series Legal Information

16. Legal Information

16.1. Proprietary Information

The information contained in this document is the property of 4D LCD Pty. Ltd.; these may be the subject of patents pending or granted, and must not be copied or disclosed without prior written permission. 4D LCD endeavors to ensure that the information in this document is correct and fairly stated but does not accept liability for any error or omission. The development of 4D LCD products and services is continuous and published information may not be up to date. It is important to check the current position with 4D LCD. 4D LCD reserves the right to modify, update or makes changes to Specifications or written material without prior notice at any time.

All trademarks belong to their respective owners and are recognised and acknowledged.

16.2. Disclaimer of Warranties & Limitations of Liabilities

4D LCD Pty Ltd makes no warranty, either expressed or implied with respect to any product, and specifically disclaims all other warranties, including but without limitation to; warranties for merchantability, non-infringement and fitness for any particular purpose.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

Images and graphics used throughout this document are for illustrative purposes only. All images and graphics used are possible to be displayed on the 4D LCD range of products, however the quality may vary.

In no event shall 4D LCD be liable to the buyer or to any third party for any indirect, incidental, special, consequential, punitive or exemplary damages (including but without limitation to; lost profits, lost savings, or loss of business opportunity) arising out of or relating to any product or service provided or to be provided by 4D LCD, or the use or inability to use the same, even if 4D LCD has been advised of the possibility of such damages.

4D LCD products are not fault tolerant nor designed, manufactured or intended for use or resale as on line control equipment in hazardous environments requiring fail - safe performance, such as in the operation of nuclear facilities, aircraft navigation or communication systems, air traffic control, direct life support machines or weapons systems in which the failure of the product could lead directly to death, personal injury or severe physical or environmental damage ('High Risk Activities'). 4D LCD and its suppliers specifically disclaim any expressed or implied warranty of fitness for High Risk Activities.

Use of 4D LCD products and devices in 'High Risk Activities' and in any other application is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless 4D LCD from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any 4D LCD intellectual property rights.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

4D Systems:

4DLCD-43480272-CTP-CLB-IPS 4DLCD-43480272-CTP-IPS 4DLCD-43480272-IPS 4DLCD-43480272-RTP-IPS