

# OSRAM GW KADEBB.GM

## Datasheet

Published by **ams-OSRAM AG**

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

[ams-osram.com](http://ams-osram.com)

© All rights reserved



## SOLERIQ® S 6

# GW KADEBB.GM

The SOLERIQ® S products were specifically designed for applications requiring large flux packages out of a compact area.



### Applications

- Indoor Lighting

### Features

- Package: Chip-on-Board
- Typ. Radiation: 120°
- Color temperature: 2700K - 5000K
- CRI: 96 (min.), 97 (typ.)
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- Luminous Flux: typ. 824 lm @ 3000 K, 25 °C
- Luminous efficacy: typ. 117 lm/W @ 3000 K, 25 °C

Ordering Information

Type	Color temperature	Luminous Flux <sup>1)</sup> $I_F = 200 \text{ mA}$ $\Phi_V$	Ordering Code
GW KADEBB.GM-B1-27A2D2	2700 K	737.0 ... 815.0 lm	Q65113A7084
GW KADEBB.GM-B2-30A2D2	3000 K	783.0 ... 865.0 lm	Q65113A7082
GW KADEBB.GM-B2-35A2D2	3500 K	783.0 ... 865.0 lm	Q65113A7081
GW KADEBB.GM-B3-40A2D2	4000 K	814.0 ... 900.0 lm	Q65113A7083
GW KADEBB.GM-B11-50A2D2	5000 K	860.0 ... 960.0 lm	Q65113A9298

Maximum Ratings

Parameter	Symbol		Values
Operating Temperature	$T_{op}$	min.	-40 °C
		max.	105 °C
Storage Temperature	$T_{stg}$	min.	-40 °C
		max.	105 °C
Junction Temperature	$T_j$	max.	125 °C
Forward Current $T_j = 25\text{ °C}$	$I_F$	min.	20 mA
		max.	460 mA
Reverse voltage <sup>2)</sup>	$V_R$	Not designed for reverse operation	
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	$V_{ESD}$	2 kV	

Characteristics


$I_F = 200\text{ mA}$ ;  $T_J = 25\text{ °C}$

Parameter	Symbol	Values	
Viewing angle at 50% $I_V$	$2\phi$	typ.	110 °
Forward Voltage <sup>3)</sup> $I_F = 200\text{ mA}$	$V_F$	min.	32.00 V
		typ.	35.00 V
		max.	39.00 V
Reverse current <sup>2)</sup>	$I_R$	Not designed for reverse operation	
Color Rendering Index <sup>4)</sup>	CRI	min.	96
		typ.	97
Electrical thermal resistance junction/solderpoint with efficiency $\eta_e = 45.87\text{ %}$	$R_{thJS\text{ elec.}}$	typ.	1.8 K / W

Brightness Groups

Group	Luminous Flux <sup>1)</sup>	Luminous Flux <sup>1)</sup>
	$I_F = 200\text{ mA}$ min. $\Phi_V$	$I_F = 200\text{ mA}$ max. $\Phi_V$
B1	737.0 lm	815.0 lm
B2	783.0 lm	865.0 lm
B3	814.0 lm	900.0 lm
B11	860.0 lm	960.0 lm

Chromaticity Coordinate Groups <sup>5)</sup>




Chromaticity Coordinate Groups

CCT	Center Cx	Center Cy	a	b				Ø
2700 K	0.4577	0.4098	0.008	0.0041	0.0133	0.0068		54.1
3000 K	0.4339	0.4032	0.0086	0.0042	0.0142	0.0069		53.7
3500 K	0.4077	0.3929	0.0093	0.0042	0.0155	0.0069		53.9
4000 K	0.3818	0.3796	0.0094	0.0041	0.0157	0.0068		53.4
5000 K	0.3446	0.3551	0.0081	0.0035	0.0135	0.0059		59.8


## Relative Spectral Emission <sup>6)</sup>

$\Phi_{\text{rel}} = f(\lambda)$ ;  $I_F = 200 \text{ mA}$ ;  $T_J = 25 \text{ °C}$




## Radiation Characteristics <sup>6)</sup>

$I_{\text{rel}} = f(\varphi)$ ;  $T_J = 25 \text{ °C}$




## Forward current <sup>6)</sup>

$$I_F = f(V_F); T_J = 25\text{ °C}$$




## Relative Luminous Flux <sup>6), 7)</sup>

$$\Phi_V / \Phi_V(200\text{ mA}) = f(I_F); T_J = 25\text{ °C}$$




## Chromaticity Coordinate Shift <sup>6)</sup>

$$\Delta Cx, \Delta Cy = f(I_F); T_J = 25\text{ °C}$$




**Forward Voltage** <sup>6)</sup>


$$\Delta V_F = V_F - V_F(25^\circ\text{C}) = f(T_j); I_F = 200\text{ mA}$$

**Relative Luminous Flux** <sup>6)</sup>

$$\Phi_V / \Phi_V(25^\circ\text{C}) = f(T_j); I_F = 200\text{ mA}$$


**Chromaticity Coordinate Shift** <sup>6)</sup>

$$\Delta C_x, \Delta C_y = f(T_j); I_F = 200\text{ mA}$$




## Max. Permissible Forward Current <sup>8)</sup>

$$I_F = f(T)$$




### Marking on backside of COB device



12 | Version 1.6 | 2024-09-09

Tray <sup>9)</sup>

50 pieces per tray



C67062-A0359-X1-02

Barcode-Product-Label (BPL)

**OSRAM**

LX XXXX      BIN1: XX-XX-X-XXX-X

RoHS Compliant

(6P) BATCH NO: 1234567890

(1T) LOT NO: 1234567890      (9D) D/C: 1234

(X) PROD NO: 123456789(Q)QTY: 9999      (G) GROUP: XX-XX-X-X

ML Temp    ST  
X    XXX °C X

Pack: RXX  
DEMY    XXX  
X\_X123\_1234.1234 X

OHA04563

---

## Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **moderate risk (exposure time 0.25 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

This device is designed for specific/recommended applications only. Please consult OSRAM Opto Semiconductors Sales Staff in advance for detailed information on other non-recommended applications (e.g. automotive).

Change management for this component is aligned with the requirements of the lighting market.

For further application related information please visit <https://ams-osram.com/support/application-notes>

---

## Disclaimer

### Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on our website.

### Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

### Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

---

## Glossary

- 1) **Brightness:** Brightness values are measured during a current pulse of typically 10 ms, with a tolerance of +/- 7%.
- 2) **Reverse Operation:** Not designed for reverse operation. Continuous reverse operation can cause migration and damage of the device.
- 3) **Forward Voltage:** The Forward voltage is measured during a current pulse duration of typically 1 ms with a tolerance of  $\pm 0.05V$ .
- 4) **Color reproduction index:** Color reproduction index values (CRI-RA) are measured during a current pulse of typically 10 ms and with a tolerance of  $\pm 2$ .
- 5) **Chromaticity coordinate groups:** Chromaticity coordinate groups are measured during a current pulse duration of typically 10ms with a tolerance of  $\pm 0.005$ .
- 6) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 7) **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- 8) **Thermal Resistance:**  $R_{th\ max}$  is based on statistic values ( $6\sigma$ ) used for Derating.
- 9) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with  $\pm 0.1$  and dimensions are specified in mm.

Revision History

Version	Date	Change
1.0	2022-09-28	Applications
1.1	2023-01-19	Ordering Information
1.2	2023-04-11	Tray
1.3	2023-09-08	Ordering Information Brightness Groups Chromaticity Coordinate Groups
1.4	2023-10-03	Features Characteristics Chromaticity Coordinate Groups Dimensional Drawing
1.5	2023-10-19	Features
1.6	2024-09-09	Features Ordering Information Brightness Groups Chromaticity Coordinate Groups



EU RoHS and China RoHS compliant product

此产品符合欧盟 RoHS 指令的要求；  
按照中国的相关法规和标准，  
不含有毒有害物质或元素。

**Published by ams-OSRAM AG**

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

[ams-osram.com](http://ams-osram.com)

© All rights reserved

**am**

**OSRAM**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ams OSRAM:](#)

[GW KADEBB.GM-B3-40A2D2-200-T05](#) [GW KADEBB.GM-B2-30A2D2-200-T05](#) [GW KADEBB.GM-B1-27A2D2-200-T05](#) [GW KADEBB.GM-B2-35A2D2-200-T05](#)