

OSRAM SFH 7014C

Datasheet

Published by **ams-OSRAM AG**

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

ams-osram.com

© All rights reserved



Multi Chip LED

SFH 7014C

Green (530 nm), Red (655 nm),
Infrared Emitter (850 nm)
and Infrared Emitter (940 nm)



Applications

- Digital Diagnostic Devices
- Vital Sign Monitoring

Features

- Package: clear silicone
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- SMT package
- Suitable for SMT assembly
- Available on tape and reel
- Emitters can be controlled separately

Ordering Information

Type	Brightness ¹⁾²⁾	Ordering Code
SFH 7014C		Q65113A4769
● green	● $I_e = 2.20 \dots 5.40 \text{ mW/sr}$ ($I_F = 20 \text{ mA}$)	
● red	● $I_e = 2.50 \dots 7.00 \text{ mW/sr}$ ($I_F = 20 \text{ mA}$)	
● infrared (850 nm)	● $I_e = 1.65 \dots 4.05 \text{ mW/sr}$ ($I_F = 20 \text{ mA}$)	
● infrared (940 nm)	● $I_e = 1.65 \dots 4.05 \text{ mW/sr}$ ($I_F = 20 \text{ mA}$)	

Maximum Ratings

 $T_A = 25\text{ °C}$

Parameter	Symbol		Values ● green	Values ● red	Values ● infrared (850 nm)	Values ● infrared (940 nm)
Operating temperature	T_{op}	min.	-40 °C	-40 °C	-40 °C	-40 °C
		max.	85 °C	85 °C	85 °C	85 °C
Storage temperature	T_{stg}	min.	-40 °C	-40 °C	-40 °C	-40 °C
		max.	85 °C	85 °C	85 °C	85 °C
Junction temperature	T_j	max.	100 °C	100 °C	100 °C	100 °C
Forward current	I_F	max.	30 mA	40 mA	60 mA	60 mA
Forward current pulsed	$I_{F\ pulse}$	max.	0.75 A	0.3 A	1 A	1 A
$t_p \leq 60\ \mu s$; $D \leq 0.005$						
Power consumption	P_{tot}	max.	90 mW	110 mW	100 mW	90 mW
ESD withstand voltage	V_{ESD}	max.	2 kV	2 kV	2 kV	2 kV
acc. to ANSI/ESDA/ JEDEC JS-001 (HBM, Class 2)						

The stated maximum ratings refer to one chip, unless otherwise specified.


Characteristics

$I_F = 20 \text{ mA}$; $t_p = 20 \text{ ms}$; $T_A = 25 \text{ °C}$

Parameter	Symbol		Values ● green	Values ● red	Values ● infrared (850 nm)	Values ● infrared (940 nm)
Peak wavelength	λ_{peak}	typ.	524.0 nm	662.0 nm	860.0 nm	950.0 nm
Centroid wavelength ³⁾	$\lambda_{\text{centroid}}$	min.	522.5 nm	652.5 nm	840.5 nm	930.5 nm
		typ.	530.0 nm	655.0 nm	850.0 nm	940.0 nm
		max.	541.5 nm	657.5 nm	859.5 nm	949.5 nm
Spectral bandwidth at 50% $I_{\text{rel,max}}$ (FWHM)	$\Delta\lambda$	typ.	32.0 nm	17.0 nm	30.0 nm	42.0 nm
Half angle	φ	typ.	60 °	60 °	60 °	60 °
Dimensions of active chip area	L x W	typ.	0.5 x 0.5 mm x mm	0.3 x 0.3 mm x mm	0.3 x 0.3 mm x mm	0.3 x 0.3 mm x mm
Rise time (10% / 90%) $I_F = 20 \text{ mA}$; $R_L = 50 \text{ } \Omega$	t_r	typ.	59 ns	17 ns	12 ns	16 ns
Fall time (10% / 90%) $I_F = 20 \text{ mA}$; $R_L = 50 \text{ } \Omega$	t_f	typ.	59 ns	17 ns	12 ns	16 ns
Forward voltage ⁴⁾	V_F	min.	1.60 V	1.75 V	1.20 V	1.10 V
		typ.	2.50 V	1.90 V	1.40 V	1.30 V
		max.	2.90 V	2.70 V	1.60 V	1.50 V
Reverse current ⁵⁾ $V_R = 5 \text{ V}$	I_R	max.	10 μA	10 μA	10 μA	10 μA
Radiant intensity ¹⁾²⁾ $I_F = 20 \text{ mA}$; $t_p = 20 \text{ ms}$	I_e	min.	2.2 mW/sr	2.5 mW/sr	1.65 mW/sr	1.65 mW/sr
		typ.	3.65 mW/sr	4.2 mW/sr	3 mW/sr	3 mW/sr
		max.	5.4 mW/sr	7 mW/sr	4.05 mW/sr	4.05 mW/sr
Total radiant flux ⁶⁾ $I_F = 20 \text{ mA}$; $t_p = 20 \text{ ms}$	Φ_e	typ.	12.5 mW	15 mW	10 mW	10 mW
Temperature coeffi- cient of voltage	TC_V	typ.	-3.6 mV / K	-1.7 mV / K	-0.7 mV / K	-0.8 mV / K
Temperature coeffi- cient of brightness	TC_I	typ.	-0.35 % / K	-0.7 % / K	-0.5 % / K	-0.3 % / K
Temperature coeffi- cient of wavelength	TC_λ	typ.	0.03 nm / K	0.18 nm / K	0.3 nm / K	0.3 nm / K
Thermal resistance junction solder point real ⁷⁾	$R_{\text{thJS real}}$	max.	140 K / W	190 K / W	220 K / W	200 K / W


Relative Spectral Emission 8), 9)

- green: $I_{e,rel} = f(\lambda)$; $I_F = 20 \text{ mA}$; $t_p = 20 \text{ ms}$




Relative Spectral Emission 8), 9)

- red: $I_{e,rel} = f(\lambda)$; $I_F = 20 \text{ mA}$; $t_p = 20 \text{ ms}$




Relative Spectral Emission 8), 9)


- infrared (850 nm): $I_{e,rel} = f(\lambda)$; $I_F = 20 \text{ mA}$; $t_p = 20 \text{ ms}$



Relative Spectral Emission 8), 9)


- infrared (940 nm): $I_{e,rel} = f(\lambda)$; $I_F = 20 \text{ mA}$; $t_p = 20 \text{ ms}$




Radiation Characteristics 8), 9)green/ red/ infrared: $I_{\text{rel}} = f(\phi)$ 

Forward current 8), 9)


- green: $I_F = f(V_F)$; single pulse; $t_p = 100 \mu s$

**Forward current** 8), 9)


- red: $I_F = f(V_F)$; single pulse; $t_p = 100 \mu s$

**Forward current** 8), 9)

- infrared (850 nm): $I_F = f(V_F)$; s.p.; $t_p = 100 \mu s$


**Forward current** 8), 9)

- infrared (940 nm): $I_F = f(V_F)$; s.p.; $t_p = 100 \mu s$




Relative Radiant Intensity ^{8), 9)}

- green: $I_e/I_e(20\text{mA}) = f(I_F)$; single pulse; $t_p = 100\ \mu\text{s}$




Relative Radiant Intensity ^{8), 9)}

- red: $I_e/I_e(20\text{mA}) = f(I_F)$; single pulse; $t_p = 100\ \mu\text{s}$




Relative Radiant Intensity ^{8), 9)}

- infrared (850 nm): $I_e/I_e(20\text{mA}) = f(I_F)$; s.p.; $t_p = 100\ \mu\text{s}$




Relative Radiant Intensity ^{8), 9)}

- infrared (940 nm): $I_e/I_e(20\text{mA}) = f(I_F)$; s.p.; $t_p = 100\ \mu\text{s}$




Max. Permissible Forward Current

- green: $I_F = f(T_S)$; $R_{th_{js}} = 135 \text{ K/W}$




Permissible Pulse Handling Capability

- green: $I_F = f(t_p)$; $D = \text{parameter}$; $T_S = 25 \text{ °C}$




Permissible Pulse Handling Capability

- green: $I_F = f(t_p)$; $D = \text{parameter}$; $T_S = 85 \text{ °C}$




Max. Permissible Forward Current

- red: $I_F = f(T_S)$; $R_{th_{js}} = 190 \text{ K / W}$




Permissible Pulse Handling Capability

- red: $I_F = f(t_p)$; $D = \text{parameter}$; $T_S = 25 \text{ °C}$




Permissible Pulse Handling Capability

- red: $I_F = f(t_p)$; $D = \text{parameter}$; $T_S = 85 \text{ °C}$





Max. Permissible Forward Current

- infrared (850 nm): $I_F = f(T_S)$; $R_{th_{js}} = 220 \text{ K/W}$




Permissible Pulse Handling Capability

- infrared (850 nm): $I_F = f(t_p)$; $D = \text{parameter}$; $T_S = 25 \text{ °C}$
- infrared (850 nm): $I_F = f(t_p)$; $D = \text{parameter}$; $T_S = 85 \text{ °C}$





Max. Permissible Forward Current

- infrared (940 nm): $I_F = f(T_S)$; $R_{th_{js}} = 195 \text{ K/W}$




Permissible Pulse Handling Capability

- infrared (940 nm): $I_F = f(t_p)$; $D = \text{parameter}$; $T_S = 25 \text{ °C}$
- infrared (940 nm): $I_F = f(t_p)$; $D = \text{parameter}$; $T_S = 85 \text{ °C}$



Dimensional Drawing ¹⁰⁾




Further Information:


Approximate Weight: 3.0 mg

Pin	Description
1	Cathode IR Emitter (940 nm)
2	Anode green/ red/ 850 nm/ 940 nm
3	Cathode green Emitter (530 nm)
4	Cathode red Emitter (655 nm)
5	Anode green/ red/ 850 nm/ 940 nm
6	Cathode IR Emitter (850 nm)

Recommended Solder Pad 10)




Component Location on Pad



E062.3010.315 -01

Reflow Soldering Profile

Product complies to MSL Level 3 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	Pb-Free (SnAgCu) Assembly			Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat ^{*)} 25 °C to 150 °C			2	3	K/s
Time t_s T_{Smin} to T_{Smax}	t_s	60	100	120	s
Ramp-up rate to peak ^{*)} T_{Smax} to T_p			2	3	K/s
Liquidus temperature	T_L		217		$^{\circ}\text{C}$
Time above liquidus temperature	t_L		80	100	s
Peak temperature	T_p		245	260	$^{\circ}\text{C}$
Time within 5 °C of the specified peak temperature $T_p - 5\text{ K}$	t_p	10	20	30	s
Ramp-down rate [*] T_p to 100 °C			3	6	K/s
Time 25 °C to T_p				480	s

All temperatures refer to the center of the package, measured on the top of the component


* slope calculation DT/Dt : Dt max. 5 s; fulfillment for the whole T-range

Taping ¹⁰⁾



C67062-A0277-B3-01


Tape and Reel ¹¹⁾




Reel Dimensions

A	W	N _{min}	W ₁	W _{2 max}	Pieces per PU
180 mm	8 + 0.3 / - 0.1 mm	60 mm	8.4 + 2 mm	14.4 mm	3000

Barcode-Product-Label (BPL)



Dry Packing Process and Materials ¹⁰⁾



OHA00539

Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet falls into **exempt risk group - Exempt**.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes

Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

Glossary

- 1) **Radiant intensity:** Measured at a solid angle of $\Omega = 0.01$ sr
- 2) **Brightness:** The brightness values are measured with a tolerance of $\pm 11\%$.
- 3) **Wavelength:** The wavelengths are measured with a tolerance of ± 1 nm.
- 4) **Forward Voltage:** The forward voltages are measured with a tolerance of ± 0.1 V.
- 5) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- 6) **Total radiant flux:** Measured with integrating sphere.
- 7) **Thermal resistance:** junction - soldering point, of the device only, mounted on an ideal heatsink (e.g. metal block)
- 8) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 9) **Testing temperature:** $T_A = 25^\circ\text{C}$ (unless otherwise specified)
- 10) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ± 0.1 and dimensions are specified in mm.
- 11) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

Revision History

Version	Date	Change
1.0	2023-02-09	Initial Version



EU RoHS and China RoHS compliant product

此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，
不含有毒有害物质或元素。

Published by ams-OSRAM AG

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

ams-osram.com

© All rights reserved

am

OSRAM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ams OSRAM:](#)

[SFH 7014C](#)