OSRAM KR DMLQ32.23 **Datasheet**





SYNIOS® P2720

KR DMLQ32.23 specified @ 700mA

This compact LED device is part of the SYNIOS P2720 family. Given the scalability of this product family, it provides full performance and flexibility with just one footprint. The KR DMLQ32.23 product is meant to provide superior light quality in ½ mm² chip size class. The next generation SYNIOS® P2720 Kx DMLQ32.23 delivers higher performance, while remaining fully footprint- and solder pad-compatible to the previous version.





Applications

- Static Signaling

Features

- Package: white SMT package, colorless clear silicone resin
- Chip technology: Thinfilm
- Typ. Radiation: 120° (Lambertian emitter)
- Color: λ_{dom} = 621 nm (• red)
- Corrosion Robustness Class: 3B
- Qualifications: AEC-Q102 Qualified with RV-level 1
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)





Ordering Information

Type Luminous Flux 1) Ordering Code

 $I_{c} = 700 \text{ mA}$

 $\boldsymbol{\Phi}_{\!\scriptscriptstyle V}$

80.0 ... 224.0 lm KR DMLQ32.23-6K6M-26-M3W3 Q65113A6243



Maximum Ratings Parameter	Symbol		Values
Operating Temperature	T _{op}	min. max.	-40 °C 125 °C
Storage Temperature	T_{stg}	min. max.	-40 °C 125 °C
Junction Temperature	T _i	max.	150 °C
Junction Temperature for short time applications*	T _i	max.	175 °C
Forward current T _s = 25 °C	I _F	min. max.	10 mA 800 mA
Surge current t \leq 10 μ s; D = 0.005 ; T _s = 25 °C	I _{FS}	max.	1500 mA
Reverse voltage ²⁾ T _S = 25 °C	V_R	max.	12 V
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	V_{ESD}		2 kV

^{*} The median lifetime (L70/B50) for Tj = 175° C is 100h.



Characteristics

 $I_F = 700 \text{ mA}; T_S = 25 \text{ }^{\circ}\text{C}$

Parameter	Symbol	Symbol	
Peak Wavelength	$\lambda_{\sf peak}$	typ.	630 nm
Dominant Wavelength 3)	λ_{dom}	min.	612 nm
$I_{\rm F} = 700 \text{mA}$	dom	typ.	621 nm
		max.	630 nm
Spectral Bandwidth at 50% I _{rel,max}	Δλ	typ.	18 nm
Viewing angle at 50% I _v	2φ	typ.	120 °
Forward Voltage 4)	V _F	min.	2.15 V
$I_{\rm F} = 700 \text{mA}$,	typ.	2.55 V
		max.	2.75 V
Reverse current 2)	I _R	typ.	0.01 μΑ
V _R = 12 V		max.	10 μΑ
Real thermal resistance junction/solderpoint ⁵⁾	R _{thJS real}	typ.	11.0 K / W
	aloc real	max.	13.0 K / W
Electrical thermal resistance junction/solderpoint 5)	R _{thJS elec.}	typ.	7.3 K / W
with efficiency η_e = 34 %	thoo elec.	max.	8.6 K / W



Brightness Groups

Group	Luminous Flux ¹⁾ $I_F = 700 \text{ mA}$ min. Φ_V	Luminous Flux ¹⁾ $I_F = 700 \text{ mA}$ max. Φ_V	Luminous Intensity $^{6)}$ I _F = 700 mA typ. I _v	
6K	80.0 lm	90.0 lm	28.1 cd	
7K	90.0 lm	100.0 lm	31.4 cd	
8K	100.0 lm	112.0 lm	35.0 cd	
5L	112.0 lm	125.0 lm	39.1 cd	
6L	125.0 lm	140.0 lm	43.7 cd	
7L	140.0 lm	159.0 lm	49.3 cd	
8L	159.0 lm	180.0 lm	55.9 cd	
5M	180.0 lm	201.0 lm	62.9 cd	
6M	201.0 lm	224.0 lm	70.1 cd	

Forward Voltage Groups

Group	Forward Voltage 4) I _F = 700 mA min. V _F	Forward Voltage ⁴⁾ I _F = 700 mA max. V _F	
M3	2.15 V	2.30 V	
Q3	2.30 V	2.45 V	
T3	2.45 V	2.60 V	
W3	2.60 V	2.75 V	



Wavelength Groups

Group	Dominant Wavelength ³⁾ I _F = 700 mA	Dominant Wavelength ³⁾ I _F = 700 mA	
	min.	max.	
	$\lambda_{\sf dom}$	$\lambda_{\sf dom}$	
2	612 nm	616 nm	
3	616 nm	620 nm	
4	620 nm	624 nm	
5	624 nm	627 nm	
6	627 nm	630 nm	



Group Name on Label


Example: 5L-2-M3

Brightness	Wavelength	Forward Voltage
5L	2	M3




Relative Spectral Emission 6)

$$\Phi_{rel}$$
 = f (λ); I_F = 700 mA; T_S = 25 °C



Radiation Characteristics 6)


$$I_{rel} = f(\phi); T_S = 25 °C$$






Forward current 6)

$$I_F = f(V_F); T_S = 25 \, ^{\circ}C$$



Relative Luminous Flux 6), 7)


$$\Phi_{V}/\Phi_{V}(700 \text{ mA}) = f(I_{F}); T_{S} = 25 \text{ °C}$$






Forward Voltage 6)

$$\Delta V_F = V_F - V_F (25 \ ^{\circ}C) = f(T_i); I_F = 700 \ mA$$




Relative Luminous Flux 6)

$$\Phi_{v}/\Phi_{v}(25~^{\circ}C) = f(T_{i}); I_{F} = 700~mA$$



Dominant Wavelength 6)


$$\Delta \lambda_{dom} = \lambda_{dom} - \lambda_{dom} (25 \ ^{\circ}C) = f(T_{j}); \ I_{F} = 700 \ mA$$






Max. Permissible Forward Current 5)

 $I_F = f(T)$




Permissible Pulse Handling Capability


 $I_F = f(t_p)$; D: Duty cycle






Dimensional Drawing 8)







General tolerance ±0.1

Lead finish Au

C67062-A0116-A8..-04

Further Information:

Approximate Weight: 12.0 mg

Package marking: Cathode


Corrosion test: Class: 3B

Test condition: 40°C / 90 % RH / 15 ppm H₂S / 14 days (stricter than IEC


60068-2-43)



Electrical Internal Circuit



Recommended Solder Pad 8)




For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere.



Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




K/s
S
K/s
°C
S
°C
S
K/s
S

All temperatures refer to the center of the package, measured on the top of the component

^{*} slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range




Taping 8)



C67062-A0116-B14-04



Tape and Reel 9)




Reel Dimensions


Α	W	N_{\min}	W_1	$W_{2 max}$	Pieces per PU
180 mm	8 + 0.3 / - 0.1 mm	60 mm	8.4 + 2 mm	14.4 mm	4000



Barcode-Product-Label (BPL)



Dry Packing Process and Materials 8)



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class exempt group (exposure time 10000 s). Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit https://ams-osram.com/support/application-notes



Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.



Glossary

- Brightness: Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of ±8 % and an expanded uncertainty of ±11 % (acc. to GUM with a coverage factor of k = 3).
- Reverse Operation: This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- Wavelength: The wavelength is measured at a current pulse of typically 25 ms, with an internal reproducibility of ±0.5 nm and an expanded uncertainty of ±1 nm (acc. to GUM with a coverage factor of k =
- Forward Voltage: The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of ±0.05 V and an expanded uncertainty of ±0.1 V (acc. to GUM with a coverage factor of k = 3).
- 5) Thermal Resistance: Rth max is based on statistic values (6 σ) used for Derating.
- Typical Values: Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- Characteristic curve: In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- 9) Tape and Reel: All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



Revision History

Version	Date	Change
1.0	2023-06-12	Initial Version
1.1	2023-09-19	Description



EU RoHS and China RoHS compliant product 此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准, 不含有毒有害物质或元素。

Published by ams-OSRAM AG

Tobelbader Strasse 30, 8141 Premstaetten, Austria Phone +43 3136 500-0 ams-osram.com © All rights reserved





Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ams OSRAM:

KR DMLQ32.23-6K6M-26-M3W3