

LA G6SP.01 - Dual binning

Advanced Power TOPLED®

Latest version of Advanced Power TOPLED with increased brightness and improved thermal management.



Applications

- Signalling

Features:

- Package: white SMT package, colorless clear silicone resin
- Chip technology: Thinfilm
- Typ. Radiation: 120° (Lambertian emitter)
- Color: $\lambda_{\text{dom}} = 617 \text{ nm}$ (● amber)
- Corrosion Robustness Class: 3B
- Qualifications: AEC-Q102 Qualified with RV-level 1
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)

Ordering Information

| Type | Luminous Intensity ¹⁾ $I_F = 10 \text{ mA}$ I_v | Luminous Intensity ¹⁾ $I_F = 140 \text{ mA}$ I_v | Ordering Code |
|----------------------------------|--|---|---------------|
| LA G6SP.01-U1V1-1-1+8D6F-24-G3R3 | 450 ... 900 mcd | 6.3 ... 14.0 cd | Q65112A5883 |

Maximum Ratings

| Parameter | Symbol | | Values |
|--|-----------|--------------|------------------|
| Operating Temperature | T_{op} | min. max. | -40 °C 125 °C |
| Storage Temperature | T_{stg} | min. max. | -40 °C 125 °C |
| Junction Temperature ²⁾ | T_j | max. | 135 °C |
| Junction Temperature for short time applications* | T_j | max. | 150 °C |
| Forward current | I_F | min. max. | 5 mA 200 mA |
| Surge Current $t \leq 10 \mu s$; $D = 0.005$ | I_{FS} | max. | 1000 mA |
| Reverse voltage ³⁾ | V_R | max. | 12 V |
| ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2) | V_{ESD} | | 2 kV |

* The median lifetime (L70/B50) for $T_j = 150^\circ\text{C}$ is 100h.

Characteristics

$I_F = 140 \text{ mA}$; $T_s = 25 \text{ °C}$

| Parameter | Symbol | | Values |
|---|-------------------------|----------------------|--|
| Peak Wavelength | λ_{peak} | typ. | 624 nm |
| Dominant Wavelength ⁴⁾ $I_F = 140 \text{ mA}$ | λ_{dom} | min. typ. max. | 612 nm 617 nm 624 nm |
| Spectral Bandwidth at 50% $I_{\text{rel,max}}$ | $\Delta\lambda$ | typ. | 18 nm |
| Viewing angle at 50% I_V | 2ϕ | typ. | 120 ° |
| Forward Voltage ⁵⁾ $I_F = 140 \text{ mA}$ | V_F | min. typ. max. | 1.90 V 2.20 V 2.50 V |
| Reverse current ³⁾ $V_R = 12 \text{ V}$ | I_R | typ. max. | 0.01 μA 10 μA |
| Real thermal resistance junction/solderpoint ⁶⁾ | $R_{\text{thJS real}}$ | typ. max. | 35 K / W 50 K / W |
| Electrical thermal resistance junction/solderpoint ⁶⁾ with efficiency $\eta_e = 37 \text{ %}$ | $R_{\text{thJS elec.}}$ | typ. max. | 22 K / W 32 K / W |

Brightness Groups

| Group | Luminous Intensity ¹⁾ $I_F = 10 \text{ mA}$ min. I_v | Luminous Intensity ¹⁾ $I_F = 10 \text{ mA}$ max. I_v | Luminous Flux ⁷⁾ $I_F = 10 \text{ mA}$ typ. Φ_v |
|-------|--|--|--|
| U1 | 450 mcd | 560 mcd | 1500 mlm |
| U2 | 560 mcd | 710 mcd | 1900 mlm |
| V1 | 710 mcd | 900 mcd | 2400 mlm |

Brightness Groups

| Group | Luminous Intensity ¹⁾ $I_F = 140 \text{ mA}$ min. I_v | Luminous Intensity ¹⁾ $I_F = 140 \text{ mA}$ max. I_v | Luminous Flux ⁷⁾ $I_F = 140 \text{ mA}$ typ. Φ_v |
|-------|---|---|---|
| 8D | 6.3 cd | 7.1 cd | 20.1 lm |
| 5E | 7.1 cd | 8.0 cd | 22.7 lm |
| 6E | 8.0 cd | 9.0 cd | 25.5 lm |
| 7E | 9.0 cd | 10.0 cd | 28.5 lm |
| 8E | 10.0 cd | 11.2 cd | 31.8 lm |
| 5F | 11.2 cd | 12.5 cd | 35.6 lm |
| 6F | 12.5 cd | 14.0 cd | 39.8 lm |

Forward Voltage Groups

| Group | Forward Voltage ⁵⁾ $I_F = 10 \text{ mA}$ min. V_F | Forward Voltage ⁵⁾ $I_F = 10 \text{ mA}$ max. V_F |
|-------|---|---|
| A3 | 1.60 V | 1.75 V |
| D3 | 1.75 V | 1.90 V |

Forward Voltage Groups

| Group | Forward Voltage ⁵⁾ $I_F = 140 \text{ mA}$ min. V_F | Forward Voltage ⁵⁾ $I_F = 140 \text{ mA}$ max. V_F |
|-------|--|--|
| G3 | 1.90 V | 2.05 V |
| K3 | 2.05 V | 2.20 V |
| N3 | 2.20 V | 2.35 V |
| R3 | 2.35 V | 2.50 V |

Wavelength Groups

| Group | Dominant Wavelength ⁴⁾ $I_F = 10 \text{ mA}$ min. λ_{dom} | Dominant Wavelength ⁴⁾ $I_F = 10 \text{ mA}$ max. λ_{dom} |
|-------|--|--|
| 1 | 611 nm | 624 nm |

Wavelength Groups

| Group | Dominant Wavelength ⁴⁾ $I_F = 140 \text{ mA}$ min. λ_{dom} | Dominant Wavelength ⁴⁾ $I_F = 140 \text{ mA}$ max. λ_{dom} |
|-------|---|---|
| 2 | 612 nm | 616 nm |
| 3 | 616 nm | 620 nm |
| 4 | 620 nm | 624 nm |

Group Name on Label

Example: U1-1-A3

Brightness

Wavelength

Forward Voltage


U1

1

A3


Relative Spectral Emission ⁷⁾

$I_{\text{rel}} = f(\lambda)$; $I_F = 140 \text{ mA}$; $T_S = 25 \text{ °C}$




Radiation Characteristics ⁷⁾

$I_{\text{rel}} = f(\phi)$; $T_S = 25 \text{ °C}$




Forward current ⁷⁾

$$I_F = f(V_F); T_S = 25\text{ °C}$$




Relative Luminous Intensity ^{7), 8)}

$$I_V/I_V(I_{F\text{ group}}) = f(I_F); T_S = 25\text{ °C}$$




Forward Voltage ⁷⁾


$$\Delta V_F = V_F - V_F(25^\circ\text{C}) = f(T_j); I_F = 140\text{ mA}$$

**Relative Luminous Intensity** ⁷⁾

$$I_V/I_V(25^\circ\text{C}) = f(T_j); I_F = 140\text{ mA}$$


**Dominant Wavelength** ⁷⁾

$$\Delta\lambda_{\text{dom}} = \lambda_{\text{dom}} - \lambda_{\text{dom}}(25^\circ\text{C}) = f(T_j); I_F = 140\text{ mA}$$




Max. Permissible Forward Current

$$I_F = f(T)$$




Permissible Pulse Handling Capability

$$I_F = f(t_p); D: \text{Duty cycle}$$




Permissible Pulse Handling Capability

$$I_F = f(t_p); D: \text{Duty cycle}$$



Dimensional Drawing ⁹⁾




Further Information:

Approximate Weight: 40.0 mg

Package marking: Cathode

Corrosion test: Class: 3B
 Test condition: 40°C / 90 % RH / 15 ppm H₂S / 14 days (stricter than IEC 60068-2-43)


Recommended Solder Pad ⁹⁾



For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Package not suitable for ultra sonic cleaning.

Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




| Profile Feature | Symbol | Pb-Free (SnAgCu) Assembly | | | Unit |
|--|--------|---------------------------|----------------|---------|------|
| | | Minimum | Recommendation | Maximum | |
| Ramp-up rate to preheat ^{*)} 25 °C to 150 °C | | | 2 | 3 | K/s |
| Time t_s T_{Smin} to T_{Smax} | t_s | 60 | 100 | 120 | s |
| Ramp-up rate to peak ^{*)} T_{Smax} to T_p | | | 2 | 3 | K/s |
| Liquidus temperature | T_L | | 217 | | °C |
| Time above liquidus temperature | t_L | | 80 | 100 | s |
| Peak temperature | T_p | | 245 | 260 | °C |
| Time within 5 °C of the specified peak temperature $T_p - 5\text{ K}$ | t_p | 10 | 20 | 30 | s |
| Ramp-down rate* T_p to 100 °C | | | 3 | 6 | K/s |
| Time 25 °C to T_p | | | | 480 | s |

All temperatures refer to the center of the package, measured on the top of the component


* slope calculation DT/Dt : Dt max. 5 s; fulfillment for the whole T-range

Taping ⁹⁾



C63062-A3786-B6-02

Tape and Reel ¹⁰⁾




Reel Dimensions


| A | W | N _{min} | W ₁ | W _{2 max} | Pieces per PU |
|--------|---------------------|------------------|----------------|--------------------|---------------|
| 180 mm | 12 + 0.3 / - 0.1 mm | 60 mm | 12.4 + 2 mm | 18.4 mm | 1000 |

Barcode-Product-Label (BPL)


OSRAM Opto Semiconductors


LX XXXX BIN1: XX-XX-X-XXX-X

(6P) BATCH NO: 1234567890



RoHS Compliant


ML Temp ST
 X XXX °C X




(1T) LOT NO: 1234567890


(9D) D/C: 1234
 Pack: RXX
 DEMY XXX
 X_X123_1234.1234 X

(X) PROD NO: 123456789(Q)QTY: 9999 (G) GROUP: XX-XX-X-X


OHA04563

Dry Packing Process and Materials ⁹⁾



OHA00539

Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet falls into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes

Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on the OSRAM OS website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

OSRAM OS products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using OSRAM OS components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and buyer and /or customer will analyze and coordinate the customer-specific request between OSRAM OS and buyer and/or customer.

Glossary

- 1) **Brightness:** Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of $\pm 8\%$ and an expanded uncertainty of $\pm 11\%$ (acc. to GUM with a coverage factor of $k = 3$).
- 2) **Package discoloration:** The LED chip exhibits excellent performance but slight package discoloration occurs at highest temperatures.
- 3) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- 4) **Wavelength:** The wavelength is measured at a current pulse of typically 25 ms, with an internal reproducibility of $\pm 0.5\text{ nm}$ and an expanded uncertainty of $\pm 1\text{ nm}$ (acc. to GUM with a coverage factor of $k = 3$).
- 5) **Forward Voltage:** The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of $\pm 0.05\text{ V}$ and an expanded uncertainty of $\pm 0.1\text{ V}$ (acc. to GUM with a coverage factor of $k = 3$).
- 6) **Thermal Resistance:** $R_{th\text{ max}}$ is based on statistic values (6σ).
- 7) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 8) **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- 9) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ± 0.1 and dimensions are specified in mm.
- 10) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

Revision History

| Version | Date | Change |
|---------|------------|--|
| 1.1 | 2019-11-25 | Features Disclaimer |
| 1.2 | 2020-06-15 | Glossary Schematic Transportation Box Dimensions of Transportation Box |

Published by OSRAM Opto Semiconductors GmbH
Leibnizstraße 4, D-93055 Regensburg
www.osram-os.com © All Rights Reserved.

EU RoHS and China RoHS compliant product



此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，不含有毒有害物质或元素。

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ams OSRAM:](#)

[LA G6SP.01-U1V1-1-1+8D6F-24-G3R3](#)