

MODEL	LDA10F-3	LDA10F-5	LDA10F-12	LDA10F-15	LDA10F-24
MAX OUTPUT WATTAGE[W]	6	10	10.8	10.5	12
DC OUTPUT	3V 2.0A	5V 2.0A	12V 0.9A	15V 0.7A	24V 0.5A

	MODEL		LDA10F-3	LDA10F-5	LDA10F-12	LDA10F-15	LDA10F-24			
	VOLTAGE[V]		AC85 - 264 1 φ or DC	2110 - 370						
		ACIN 100V	0.25typ (lo=100%)							
	CURRENT[A]	ACIN 200V	0.16typ (lo=100%)							
INPUT	FREQUENCY[Hz]		47 - 440 or DC							
INPUT	EFFICIENCY[%]		68typ	72typ	74typ	74typ	78typ			
	INRUSH CURRENT[A]	ACIN 100V	15typ (lo=100%) (At c	old start)						
	INRUSH CURRENT[A]	ACIN 200V	30typ (Io=100%) (At c	cold start)						
	LEAKAGE CURREN	T[mA]	0.75max (60Hz, Accor	rding to UL, CSA, VDE	and DEN-AN)					
	VOLTAGE[V]		3	5	12	15	24			
	CURRENT[A]		2	2	0.9	0.7	0.5			
	LINE REGULATION[mV]	20max	20max	48max	60max	96max			
	LOAD REGULATION		40max	40max	100max	120max	150max			
	RIPPLE[mVp-p]	-	80max	80max	120max	120max	120max			
	IIII I CE[IIIVP-P]	-10 - 0℃	140max	140max	160max	160max	160max			
OUTPUT	RIPPLE NOISE[mVp-p]	0 to +50℃	120max	120max	150max	150max	150max			
COIFOI		-10 - 0℃	160max	160max	180max	180max	180max			
	TEMPERATURE REGULA	TION[mV]	50max	50max	120max	150max	240max			
	DRIFT[mV]	*1	20max	20max	48max	60max	96max			
	START-UP TIME[ms]]	200max (ACIN 100V,	,						
	HOLD-UP TIME[ms]		21 ·	100%) 20typ (ACIN 100						
	OUTPUT VOLTAGE ADJUSTMEN	T RANGE[V]	2.85 - 3.6		e adjusted the output is	available as option :5,	12, 15, 24V ±10			
	OUTPUT VOLTAGE SET			4.9 - 5.3 11.5 - 12.5 14.4 - 15.6 23.0 - 25.0						
			Works over 105% of ra	ating and recovers auto						
PROTECTION	OVERVOLTAGE PROT		4.00V min	Works over 115% of ra	ating, by zener diode cl	amping				
CIRCUIT AND OTHERS	OPERATING INDICA	TION	Not provided							
UTHERS	REMOTE SENSING		Not provided							
	REMOTE ON/OFF		Not provided							
	INPUT-OUTPUT			utoff current = 10mA, D						
ISOLATION	INPUT-FG			utoff current = 10mA, D		· · ·				
	OUTPUT-FG			off current = 100mA, DC						
				%RH (Non condensing)			feet) max			
ENVIRONMENT	STORAGE TEMP.,HUMID.AND	ALTITUDE		%RH (Non condensing)						
	VIBRATION			2G), 3minutes period, 6		Y and Z axis				
	IMPACT			is, once each X, Y and						
NOISE	AGENCY APPROVA			-1, EN50178, CSA C22.		with DEN-AN and IEC	60950-1			
REGULATIONS	CONDUCTED NOISE			, CISPR22-B, EN55022-	· · · · · · · · · · · · · · · · · · ·					
OTHERS	CASE SIZE/WEIGHT		50 x 21 x 105mm (W x H x D) /75g max (without chassis and cover)							
	COOLING METHOD		Convection							


*1 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.
 *2 Please contact us about safety approvals for the model with option.

Avoid prolonged use under over-load. *

Series/Parallel operation with other model is not possible. Derating is required when operated with chassis and cover. *


LDA10F | CO\$EL

External view




Performance data







OVERCURRENT CHARACTERISTICS (LDA10F-5)




■RISE TIME & FALL TIME (LDA10F-5)



DERATING CURVE



LDA



MODEL	LDA15F-3	LDA15F-5	LDA15F-12	LDA15F-15	LDA15F-24
MAX OUTPUT WATTAGE[W]	9	15	15.6	15	16.8
DC OUTPUT	3V 3.0A	5V 3.0A	12V 1.3A	15V 1.0A	24V 0.7A

	MODEL		LDA15F-3	LDA15F-5	LDA15F-12	LDA15F-15	LDA15F-24				
	VOLTAGE[V]		AC85 - 264 1 ¢ or DC	2110 - 370							
	CURRENT[A]		0.37typ (lo=100%)								
	CONNENT[A]	ACIN 200V	0.23typ (lo=100%)								
INPUT	FREQUENCY[Hz]		47 - 440 or DC								
INFOI	EFFICIENCY[%]	_	70typ	74typ	76typ	76typ	78typ				
	INRUSH CURRENT[A]	ACIN 100V	15typ (lo=100%) (At c	old start)							
		ACIN 200V	30typ (lo=100%) (At c								
	LEAKAGE CURREN	T[mA]	0.75max (60Hz, Accor	rding to UL, CSA, VDE							
	VOLTAGE[V]		3	5	12	15	24				
	CURRENT[A]		3	3	1.3	1	0.7				
	LINE REGULATION[-	20max	20max	48max	60max	96max				
	LOAD REGULATION		40max	40max	100max	120max	150max				
	RIPPLE[mVp-p]	0 to +50℃		80max	120max	120max	120max				
	III.I.CE[III.Ab-b]	-10 - 0℃	140max	140max	160max	160max	160max				
OUTPUT	RIPPLE NOISE[mVp-p]		120max	120max	150max	150max	150max				
Control		-10 - 0℃	160max	160max	180max	180max	180max				
	TEMPERATURE REGULA	TION[mV]	50max	50max	120max	150max	240max				
	DRIFT[mV]	*1	20max	20max	48max	60max	96max				
	START-UP TIME[ms]		200max (ACIN 100V,	,							
	HOLD-UP TIME[ms]		21 .	100%) 20typ (ACIN 100							
	OUTPUT VOLTAGE ADJUSTMEN	T RANGE[V]									
	OUTPUT VOLTAGE SET			4.9 - 5.3 11.5 - 12.5 14.4 - 15.6 23.0 - 25.0							
ŀ			Works over 105% of ra	ating and recovers auto	,						
FRUIECHUN	OVERVOLTAGE PROT		4.00V min	Works over 115% of r	ating, by zener diode cl	amping					
OTUEDO	OPERATING INDICA	TION	Not provided								
	REMOTE SENSING		Not provided								
	REMOTE ON/OFF		Not provided								
ŀ	INPUT-OUTPUT			utoff current = 10mA, D							
ISOLATION	INPUT-FG			utoff current = 10mA, D		· ·					
	OUTPUT-FG			off current = 100mA, DO							
	OPERATING TEMP.,HUMID.AND			%RH (Non condensing)			feet) max				
ENVIRONMENT	STORAGE TEMP.,HUMID.AND	ALTITUDE	-	%RH (Non condensing)							
	VIBRATION		10 - 55Hz, 19.6m/s ² (2G), 3minutes period, 60minutes each along X, Y and Z axis								
	IMPACT			is, once each X, Y and							
SAFETY AND NOISE	AGENCY APPROVA	LS		-1, EN50178, CSA C22		with DEN-AN and IEC	60950-1				
REGULATIONS	CONDUCTED NOISE			, CISPR22-B, EN55022-	· · · · · · · · · · · · · · · · · · ·						
OTHERS 1	CASE SIZE/WEIGHT		50×21×125mm (W×H×D) /95g max (without chassis and cover)								
	COOLING METHOD		Convection								


*1 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.
 *2 Please contact us about safety approvals for the model with option.


Avoid prolonged use under over-load. *

Series/Parallel operation with other model is not possible. Derating is required when operated with chassis and cover. *

LDA15F | CO\$EL

External view







					<pin< p=""></pin<>	CONNE	CTION>					* Weight: 95g or less (Without chassis and co
	1/0	Connector	Mating Connector	Terminal		Pin No.	Input AC(L)			Pin No.	Output	* Tolerance : ±1
c	N1	B3P5-VH	VHR-5N	Chain:SVH-21T-P1.1 Loose:BVH-21T-P1.1	CNI	2	AC(L)	С	N2	2	V	X Dimensions in mm.
F		-	XHP-4	Chain: SXH-001T-P0.6	CN1	3	AC(N)			3	+V	* PCB Material : Glass composite (CEM3)
Ľ	ΝZ	B4B-XH-A	XHP-4	Loose: BXH-001T-P0.6		4	FG			4	+V	※ Chassis and cover is optional.
				(Mfr : J.S.T.)								Mounting torque: 0.6N·m (6.3kgf·cm) max

Performance data


STATIC CHARACTERISTICS (LDA15F-5)




OVERCURRENT CHARACTERISTICS (LDA15F-5)




■RISE TIME & FALL TIME (LDA15F-5)



DERATING CURVE



cover)



MODEL	LDA30F-3	LDA30F-5	LDA30F-12	LDA30F-15	LDA30F-24
MAX OUTPUT WATTAGE[W]	18	30	30	30	31.2
DC OUTPUT	3V 6.0A	5V 6.0A	12V 2.5A	15V 2.0A	24V 1.3A

	MODEL		LDA30F-3	LDA30F-5	LDA30F-12	LDA30F-15	LDA30F-24			
	VOLTAGE[V]		AC85 - 264 1 ϕ or DC	2110 - 370						
	CURRENT[A]	ACIN 100V	0.8typ (lo=100%)							
		ACIN 200V	0.4typ (lo=100%)							
	FREQUENCY[Hz]		47 - 440 or DC							
INPUT	EFFICIENCY[%]		70typ	75typ	77typ	78typ	79typ			
	INRUSH CURRENT[A]	ACIN 100V	15typ (lo=100%) (At c	cold start)						
			30typ (Io=100%) (At c							
	LEAKAGE CURREN	T[mA]	0.75max (60Hz, Accor	rding to UL, CSA, VDE	and DEN-AN)					
	VOLTAGE[V]		3	5	12	15	24			
	CURRENT[A]		6	6	2.5	2	1.3			
	LINE REGULATION	mV]	20max	20max	48max	60max	96max			
	LOAD REGULATION	<u> </u>	40max	40max	100max	120max	150max			
	RIPPLE[mVp-p]	0 to +50℃		80max	120max	120max	120max			
	1001 66[0046 6]		140max	140max	160max	160max	160max			
OUTPUT	RIPPLE NOISE[mVp-p]	-	120max	120max	150max	150max	150max			
Contor		-10 - 0℃	160max	160max	180max	180max	180max			
- F	TEMPERATURE REGULA	TION[mV]	60max	60max	150max	180max	290max			
	DRIFT[mV]	*1	20max	20max	48max	60max	96max			
	START-UP TIME[ms]		200max (ACIN 100V,	,						
	HOLD-UP TIME[ms]			100%) 20typ (ACIN 100						
	OUTPUT VOLTAGE ADJUSTMEN		2.85 - 3.6		e adjusted the output is					
	OUTPUT VOLTAGE SET			4.9 - 5.3	11.5 - 12.5	14.4 - 15.6	23.0 - 25.0			
				ating and recovers auto						
FRUIECHON	OVERVOLTAGE PROTI		4.00 - 5.25V	Works at 115 - 140%	of rating					
	OPERATING INDICA	TION	Not provided							
	REMOTE SENSING		Not provided							
	REMOTE ON/OFF		Not provided							
	INPUT-OUTPUT			utoff current = 10mA, D						
	INPUT-FG			utoff current = 10mA, D						
	OUTPUT-FG			off current = 100mA, DC			-)			
ŀ	OPERATING TEMP., HUMID. AND			%RH (Non condensing)			feet) max			
	STORAGE TEMP.,HUMID.AND	ALTITUDE		%RH (Non condensing)						
	VIBRATION			2G), 3minutes period, 6	<u>v</u>	Y and Z axis				
	IMPACT			ns, once each X, Y and						
NOISE	AGENCY APPROVAL	-		-1, EN50178, CSA C22.		with DEN-AN and IEC	60950-1			
	CONDUCTED NOISE			, CISPR22-B, EN55022-						
OTHERS	CASE SIZE/WEIGHT		55 x 26 x 133mm (W x H x D) /200g max (without chassis and cover)							
	COOLING METHOD		Convection							

*1 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.
 *2 Please contact us about safety approvals for the model with option.


Avoid prolonged use under over-load.

*

Series/Parallel operation with other model is not possible. Derating is required when operated with chassis and cover. *


LDA30F | CO\$EL

External view




Performance data


STATIC CHARACTERISTICS (LDA30F-5)





OVERCURRENT CHARACTERISTICS (LDA30F-5)



RISE TIME & FALL TIME (LDA30F-5)







MODEL	LDA50F-3	LDA50F-5	LDA50F-9	LDA50F-12	LDA50F-15	LDA50F-18	LDA50F-24	LDA50F-24-H	LDA50F-24-HR	LDA50F-30
MAX OUTPUT WATTAGE[W]	30	50	50.4	51.6	52.5	50.4	50.4	50.4	50.4	51
DC OUTPUT *3	3V 10A	5V 10A	9V 5.6A	12V 4.3A	15V 3.5A	18V 2.8A	24V 2.1A	24V 2.1(3)A	24V 2.1(3)A	30V 1.7A

	MODEL		LDA50F-3	LDA50F-5	LDA50F-9	LDA50F-12	LDA50F-15	LDA50F-18	LDA50F-24	LDA50F-24-H	LDA50F-24-HR	LDA50F-3	
,	VOLTAGE[V]		AC85 - 264	4 1 φ or DC	110 - 370								
		ACIN 100V	1.3typ (lo=	100%)									
	CURRENT[A]	ACIN 200V	0.7typ (lo=	100%)									
	FREQUENCY[Hz]	1	47 - 440 oi	r DC									
	EFFICIENCY[%]		73typ	77typ	78typ	80typ	81typ	81typ	82typ	82typ	82typ	82typ	
-		ACIN 100V	15typ (lo=1	100%) (At co	old start)		, ,,	71	71		, ,,	, ,,	
1	INRUSH CURRENT[A]	ACIN 200V	30typ (lo=1	100%) (At co	old start)								
1	LEAKAGE CURREN					CSA, VDE a	and DEN-AN	1)					
	VOLTAGE[V]		3	5	9	12	15	18	24	24	24	30	
	CURRENT[A]	*1	10	10	5.6	4.3	3.5	2.8	2.1	2.1 (3)	2.1 (3)	1.7	
, in the second s	LINE REGULATION	[mV]	20max	20max	36max	48max	60max	72max	96max	96max	96max	120ma	
7	LOAD REGULATION	v[mV]	40max	40max	100max	100max	120max	120max	150max	150max	150max	180ma	
Γ.		0 to +50℃	80max	80max	120max	120max	120max	120max	120max	120max	120max	120ma	
1	RIPPLE[mVp-p]	-10 - 0℃	140max	140max	160max	160max	160max	160max	160max	160max	160max	160ma	
		0 to +50℃	120max	120max	150max	150max	150max	150max	150max	250max	250max	150ma	
OUTPUT	RIPPLE NOISE[mVp-p]	-10 - 0℃	160max	160max	180max	180max	180max	180max	180max	280max	280max	180ma	
1	TEMPERATURE REGULA	TION[mV]	60max	60max	120max	150max	180max	200max	290max	290max	290max	360ma	
7	DRIFT[mV]	*2	20max	20max	36max	48max	60max	72max	96max	96max	96max	120ma	
?	START-UP TIME[ms]	200max (A	CIN 100V, I	o=100%)								
1	HOLD-UP TIME[ms]	-	10typ (ACI	N 85V, lo=1	00%) 20typ	(ACIN 100)	V, lo=100%)						
(OUTPUT VOLTAGE ADJUSTMEN	NT RANGE[V]	2.85 - 3.6	Fixed ("Y"w	vhich can b	e adjusted t	he output is	available as	option :5, 9	9, 12, 15, 18	3, 24, 30V <u>+</u>	<u>⊦</u> 10%)	
(OUTPUT VOLTAGE SETTING[V]			4.9 - 5.3	8.6 - 9.4	11.5 - 12.5	14.4 - 15.6	17.3 - 18.7	23.0 - 25.0	23.0 - 25.0	23.0 - 25.0	28.5 - 3	
	OVERCURRENT PRO	TECTION	4.9 - 5.3 8.6 - 9.4 11.5 - 12.5 14.4 - 15.6 17.3 - 18.7 23.0 - 25.0 23.0 - 25.0 23.0 - 25.0 23.0 - 25.0 28.5 - 31 Works over 105% of rating (-H : peak) and recovers automatically										
PROTECTION	OVERVOLTAGE PROT	ECTION	4.00 - 5.25V Works at 115 - 140% of rating										
CIRCUIT AND	OPERATING INDICA	ATION	Not provided										
OTHERS	REMOTE SENSING		Not provided										
1	REMOTE ON/OFF		Option (Refer to Instruction Manual)										
1	INPUT-OUTPUT		AC3,000V	1minute, Cu	utoff current	= 10mA, D	C500V 50M	Ω min (At F	loom Tempe	erature)			
ISOLATION I	INPUT-FG		AC2,000V	1minute, Cu	utoff current	= 10mA, D	C500V 50M	Ω min (At F	loom Tempe	erature)			
(OUTPUT-FG		AC500V 1r	ninute, Cuto	off current =	100mA, DC	2500V 50M	2 min (At R	oom Tempe	rature)			
(OPERATING TEMP.,HUMID.AN	D ALTITUDE	-10 to +60°	C,20-90%	6RH (Non c	ondensing)	(Refer to DE	RATING CL	JRVE) 3,00	0m (10,000f	eet) max		
	STORAGE TEMP.,HUMID.AND) ALTITUDE	-20 to +75°	C,20-90%	6RH (Non c	ondensing)	9,000m (30,	000feet) ma	х				
ENVIRONMENT	VIBRATION		10 - 55Hz,	19.6m/s ² (2	G), 3minute	es period, 60	Ominutes ea	ch along X,	Y and Z ax	is			
	IMPACT		196.1m/s ²	(20G), 11ms	s, once eac	h X, Y and Z	Z axis						
	AGENCY APPROVA		UL60950-1	, EN60950-	1, EN50178	, CSA C22.	2 No.60950	1 Complies	with DEN-A	AN and IEC	60950-1		
REGULATIONS	CONDUCTED NOIS	E	Complies v	vith FCC-B,	CISPR22-E	3, EN55022-	B, VCCI-B						
OTHERS	CASE SIZE/WEIGHT	Г	55×26×1	95mm (W 🗙	H×D) /250	g max (with	out chassis	and cover)					
			Convoction	Convection									

wattage(24V:50.4W) *2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at


 $25^\circ\!C$,with the input voltage held constant at the rated input/output.

*3 (): peak current
*4 Please contact us about safety approvals for the model with option.

*


LDA50F | CO\$EL

External view




Performance data







OVERCURRENT CHARACTERISTICS (LDA50F-5)




RISE TIME & FALL TIME (LDA50F-5)





LDA



MODEL	LDA75F-3	LDA75F-5	LDA75F-9	LDA75F-12	LDA75F-15	LDA75F-18	LDA75F-24	LDA75F-24-H	LDA75F-24-HR	LDA75F-30
MAX OUTPUT WATTAGE[W]	45	75	76.5	75.6	75	75.6	76.8	76.8	76.8	75
DC OUTPUT *3	3V 15A	5V 15A	9V 8.5A	12V 6.3A	15V 5A	18V 4.2A	24V 3.2A	24V 3.2(4.5)A	24V 3.2(4.5)A	30V 2.5A

	MODEL				LDA75F-9	LDA/SF-12	LUA/SF-15	LDA/5F-18	LDA/5F-24	LDA/SF-24-H	LDA/OF-24-RR	LDA/5	
_	VOLTAGE[V]			41φ or DC	110 - 370								
	CURRENT[A]		1.8typ (lo=										
		ACIN 200V	1.0typ (lo=	100%)									
INPUT	FREQUENCY[Hz]		47 - 440										
	EFFICIENCY[%]		73typ	79typ	79typ	80typ	81typ	81typ	82typ	82typ	82typ	82typ	
	INRUSH CURRENT[A]	ACIN 200V											
	LEAKAGE CURREN	T[mA]	0.75max (6	60Hz, Accor	ding to UL,	CSA, VDE a	and DEN-AN	1)					
	VOLTAGE[V]		3	5	9	12	15	18	24	24	24	30	
	CURRENT[A]	*1	15	15	8.5	6.3	5	4.2	3.2	3.2 (4.5)	3.2 (4.5)	2.5	
	LINE REGULATION[mV]	20max	20max	36max	48max	60max	72max	96max	96max	96max	120m	
[LOAD REGULATION	[mV]	40max	40max	100max	100max	120max	120max	150max	150max	150max	180m	
	RIPPLE[mVp-p]	0 to +50℃	80max	80max	120max	120max	120max	120max	120max	120max	120max	120m	
	RIPPLE[mvp-p]	-10 - 0℃	140max	140max	160max	160max	160max	160max	160max	160max	160max	160m	
OUTPUT		0 to +50℃	120max	120max	150max	150max	150max	150max	150max	250max	250max	150m	
OUIPUI	RIPPLE NOISE[mVp-p]	-10 - 0℃	160max	160max	180max	180max	180max	180max	180max	280max	280max	180m	
[TEMPERATURE REGULA	TION[mV]	60max	60max	120max	150max	180max	200max	290max	290max	290max	360m	
	DRIFT[mV]	*2	20max	20max	36max	48max	60max	72max	96max	96max	96max	120m	
[START-UP TIME[ms]		200max (A	CIN 100V, I	o=100%)								
	HOLD-UP TIME[ms]		10typ (ACI	N 85V, lo=1	00%) 20typ	(ACIN 100)	V, lo=100%)						
[OUTPUT VOLTAGE ADJUSTMEN	T RANGE[V]	2.85 - 3.6	Fixed ("Y"v	vhich can b	e adjusted t	he output is	available as	option:5,	9, 12, 15, 1	8, 24, 30V	±10%)	
	OUTPUT VOLTAGE SET	TING[V]		4.9 - 5.3	8.6 - 9.4	11.5 - 12.5	14.4 - 15.6	17.3 - 18.7	23.0 - 25.0	23.0 - 25.0	23.0 - 25.0	28.5 -	
	OVERCURRENT PROT	ECTION	Works over 105% of rating (-H : peak) and recovers automatically										
PROTECTION	OVERVOLTAGE PROT	ECTION	4.00 - 5.25V Works at 115 - 140% of rating										
CIRCUIT AND	OPERATING INDICA	TION	Not provided										
OTHERS	REMOTE SENSING		Not provided										
	REMOTE ON/OFF		Option (Re	fer to Instru	ction Manua	al)							
	INPUT-OUTPUT		AC3,000V	1minute, Cu	utoff current	= 10mA, D	C500V 50M	Ω min (At F	loom Tempe	erature)			
ISOLATION	INPUT-FG		AC2,000V	1minute, Cu	utoff current	= 10mA, D	C500V 50M	Ω min (At F	loom Tempe	erature)			
	OUTPUT-FG		AC500V 1	minute, Cuto	off current =	100mA, DC	500V 50M	2 min (At R	oom Tempe	rature)			
	OPERATING TEMP.,HUMID.AND	ALTITUDE	-10 to +60	C, 20 - 90%	6RH (Non c	ondensing)	(Refer to DE	RATING CU	JRVE) 3,000	0m (10,000f	eet) max		
	STORAGE TEMP.,HUMID.AND	ALTITUDE	-20 to +75	C, 20 - 90%	6RH (Non c	ondensing)	9,000m (30,	000feet) ma	х				
ENVIRONMENT	VIBRATION		10 - 55Hz,	19.6m/s ² (2	G), 3minute	es period, 60	Ominutes ea	ch along X,	Y and Z ax	is			
	IMPACT		196.1m/s ²	(20G), 11m	s, once eac	h X, Y and Z	Z axis						
SAFETY AND	AGENCY APPROVA	LS					2 No.60950-	1 Complies	with DEN-A	AN and IEC	60950-1		
REGULATIONS	CONDUCTED NOISE		Complies v	vith FCC-B,	CISPR22-E	3, EN55022-	B, VCCI-B						
	CASE SIZE/WEIGHT	55x32x222mm (WxHxD) /320g max (without chassis and cover)											
OTHERS	COOLING METHOD		Convection										


wattage(24V:76.8W). *2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at

 $25^\circ\!C$,with the input voltage held constant at the rated input/output.

*3 (): peak current
*4 Please contact us about safety approvals for the model with option.

*







	1/0	Connector	Mating Connector	Terminal		Pin No.	Input		Pin No.	Output		Pin No	D. Remote ON/	
С	N 1	B3P5-VH	VHR-5N	Chain:SVH-21T-P1.1 Loose:BVH-21T-P1.1	CN1	1 2	AC(L)	CN2	1~3	-V	CN	13	RC(+)	* Tolerance . I T
С	N2	B6P-VH	VHR-6N	Chain:SVH-21T-P1.1 Loose:BVH-21T-P1.1		4	AC(N)		4~6	+V		2	RC(-)	 ※ Dimensions in mm. ※ PCB Material : Glass composite
С	NЗ	B2B-XH-A	XHP-2	Chain:SXH-001T-P0.6 Loose:BXH-001T-P0.6	×Ke	5 ep drav	FG wing cu	urrent p	ber pin	below	5A fo	or CN2		(CEM3)
				(Mfr :J.S.T.)			-							% Chassis and cover is optional. %Mounting torque :1.5 N·m (16 kgf·cm) max

Performance data


■STATIC CHARACTERISTICS (LDA75F-5)




OVERCURRENT CHARACTERISTICS (LDA75F-5)



RISE TIME & FALL TIME (LDA75F-5)



DERATING CURVE



LDA

COSEL AC-DC Power Supplies Open Frame/Enclosed type

LDA100W

Ordering information

1




Recommended EMI/EMC Filter NAC-06-472

 Series name
 Output wattage
 Autoranging input Output voltage (5) Optional *4
 C: with Coating
 G: Low leakage current
 R: with Remote ON/OFF

- S :with Chassis
- SN:with Chassis & cover

Υ	:with	Potentiometer



MODEL	LDA100W-3	LDA100W-5	LDA100W-9	LDA100W-12	LDA100W-15	LDA100W-18	LDA100W-24	LDA100W-24-H	LDA100W-30	LDA100W-48
MAX OUTPUT WATTAGE[W]	60	100	103.5	102	100.5	100.8	103.2	103.2	105	96
DC OUTPUT *3	3V 20A	5V 20A	9V 11.5A	12V 8.5A	15V 6.7A	18V 5.6A	24V 4.3A	24V 4.3(6.5)A	30V 3.5A	48V 2.0A

SPECIFICATIONS

RoHS

	MODEL					LDA100W-12	LDA100W-15	LDA100W-18	LDA100W-24	LDA100W-24-H	LDA100W-30	LDA100V				
	VOLTAGE[V]		AC 85 - $132 / 170 - 264 1 \phi$													
	CURRENT[A]	ACIN 100V	V 2.4typ (lo=100%)													
	CONNENTIAJ	ACIN 200V	1.2typ (lo=100%)													
INPUT	FREQUENCY[Hz]		47 - 440													
	EFFICIENCY[%]				80typ	81typ	82typ	82typ	83typ	83typ	83typ	82typ				
	INRUSH CURRENT[A]	ACIN 200V	75typ 79typ 80typ 81typ 82typ 83typ 83typ 83typ 82typ 30typ (lo=100%) (At cold start) 82typ 82typ 83typ 83typ 82typ 83typ 83typ 82typ													
	LEAKAGE CURREN	T[mA]	0.75max (60Hz, According to UL, CSA, VDE and DEN-AN)													
	VOLTAGE[V]		3	5	9	12	15	18	24	24	30	48				
	CURRENT[A]	*1	20	20	11.5	8.5	6.7	5.6	4.3	4.3 (6.5)	3.5	2.0				
	LINE REGULATION	mV]	20max	20max	36max	48max	60max	72max	96max	96max	120max	192ma				
	LOAD REGULATION	l[mV]	40max	40max	100max	100max	120max	120max	150max	150max	180max	240ma				
		0 to +50℃	80max	80max	120max	120max	120max	120max	120max	120max	120max	150m				
	RIPPLE[mVp-p]	-10 - 0℃	140max	140max	160max	160max	160max	160max	160max	160max	160max	200m				
ουτρυτ		0 to +50℃	120max	120max	150max	150max	150max	150max	150max	250max	150max	400m				
	RIPPLE NOISE[mVp-p]	-10 - 0℃	160max	160max	180max	180max	180max	180max	180max	280max	180max	600m				
	TEMPERATURE REGULA	TION[mV]	60max	60max	120max	150max	180max	200max	290max	290max	360max	560m				
	DRIFT[mV]	20max	20max	36max	48max	60max	72max	96max	96max	120max	192m					
	START-UP TIME[ms	200max (ACIN 100V, lo=100%)														
	HOLD-UP TIME[ms]		10typ (ACIN 85V, Io=100%) 20typ (ACIN 100V, Io=100%)													
	OUTPUT VOLTAGE ADJUSTMEN	2.85 - 3.6	4.5 - 5.5	Fixed ("Y"w	hich can be	adjusted the	output is ava	ilable as opti	on :9, 12, 15	, 18, 24, 30,	48V ±1					
	OUTPUT VOLTAGE SETTING[V]				8.6 - 9.4	11.5 - 12.5	14.4 - 15.6	17.3 - 18.7	23.0 - 25.0	23.0 - 25.0	28.8 - 31.2	46.0 -				
	OVERCURRENT PRO	·····														
PROTECTION	OVERVOLTAGE PROT	OVERVOLTAGE PROTECTION			4.00 - 5.25V Works at 115 - 140% of rating											
CIRCUIT AND	OPERATING INDICA	OPERATING INDICATION			Not provided											
OTHERS	REMOTE SENSING	Not provided														
	REMOTE ON/OFF	Option (Refer to Instruction Manual)														
	INPUT-OUTPUT		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature)													
ISOLATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At Room Temperature)													
	OUTPUT-FG		AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (At Room Temperature)													
	OPERATING TEMP.,HUMID.AN) ALTITUDE	-10 to +60°C, 20 - 90%RH (Non condensing) (Refer to DERATING CURVE) 3,000m (10,000feet) max													
ENVIRONMENT	STORAGE TEMP.,HUMID.AND	ALTITUDE	-20 to +75°C, 20 - 90%RH (Non condensing) 9,000m (30,000feet) max													
ENVIRONMENT	VIBRATION		10 - 55Hz,	19.6m/s ² (2	2G), 3minute	es period, 60	Ominutes ea	ch along X,	Y and Z ax	is						
	IMPACT		196.1m/s ²	(20G), 11m	s, once eac	h X, Y and I	Z axis									
NOICE		-	UL60950-1	, EN60950-	1, EN50178	3, CSA C22.	2 No.234 Co	omplies with	DEN-AN a	nd IEC6095	0-1					
REGULATIONS	CONDUCTED NOIS	Ε	Complies w	vith FCC-B,	CISPR22-E	3, EN55022-	B, VCCI-B									
OTHERS	CASE SIZE/WEIGHT		62×35×2	22mm (W 🗙	H x D) /360	g max (with	out chassis	and cover)								
UITENS	COOLING METHOD	Convection				62 × 35 × 222mm (W × H × D) /360g max (without chassis and cover)										


*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C,

with the input voltage held constant at the rated input/output. *3 (): peak current *4 Please contact us about safety approvals for the model with option.

*


LDA100W | CO\$EL

External view




Performance data


STATIC CHARACTERISTICS (LDA100W-5)




OVERCURRENT CHARACTERISTICS (LDA100W-5)




RISE TIME & FALL TIME (LDA100W-5)





Ordering information **COSEL** AC-DC Power Supplies Open Frame/Enclosed type LDA150W LDA 150 W -5 2 1 3



MODEL	LDA150W-3	LDA150W-5	LDA150W-9	LDA150W-12	LDA150W-15	LDA150W-18	LDA150W-24	LDA150W-24-H	LDA150W-30	LDA150W-48
MAX OUTPUT WATTAGE[W]	90	150	153	150	150	153	151.2	151.2	150	144
DC OUTPUT *3	3V 30A	5V 30A	9V 17A	12V 12.5A	15V 10A	18V 8.5A	24V 6.3A	24V 6.3(10)A	30V 5A	48V 3A

SPECIFICATIONS

	MODEL					LDA150W-12	LDA150W-15	LDA150W-18	LDA150W-24	LDA150W-24-H	LDA150W-30	LDA150V			
	VOLTAGE[V]			82 / 170 - 26	641φ										
			/ 3.6typ (lo=100%)												
		ACIN 200V	2.0typ (lo=100%)												
INPUT	FREQUENCY[Hz]		47 - 440												
	EFFICIENCY[%]		75typ	79typ	79typ	82typ	83typ	84typ	85typ	85typ	85typ	82typ			
	INRUSH CURRENT[A]	INRUSH CURRENT[A] ACIN 200V		30typ (Io=100%) (At cold start)											
	LEAKAGE CURREN	T[mA]	0.75max (60Hz, According to UL, CSA, VDE and DEN-AN)												
	VOLTAGE[V]		3	5	9	12	15	18	24	24	30	48			
	CURRENT[A]	*1	30	30	17	12.5	10	8.5	6.3	6.3(10)	5	3			
	LINE REGULATION	mV]	20max	20max	36max	48max	60max	72max	96max	96max	120max	192m			
	LOAD REGULATION	l[mV]	40max	40max	100max	100max	120max	120max	150max	150max	180max	240m			
		0 to +50℃	80max	80max	120max	120max	120max	120max	120max	220max	120max	150m			
	RIPPLE[mVp-p]	-10 - 0℃	140max	140max	160max	160max	160max	160max	160max	260max	160max	200m			
Ουτρυτ		0 to +50℃	120max	120max	150max	150max	150max	150max	150max	250max	150max	400m			
	RIPPLE NOISE[mVp-p]	-10 - 0℃	160max	160max	180max	180max	180max	180max	180max	280max	180max	600m			
	TEMPERATURE REGULA	TION[mV]	60max	60max	120max	150max	180max	200max	290max	290max	360max	560m			
	DRIFT[mV]	20max	20max	36max	48max	60max	72max	96max	96max	120max	192m				
	START-UP TIME[ms]]	200max (ACIN 100V, Io=100%)												
	HOLD-UP TIME[ms]		10typ (ACIN 85V, lo=100%) 20typ (ACIN 100V, lo=100%) 2.85 - 3.6 4.5 - 5.5 Fixed ("Y"which can be adjusted the output is available as option :9, 12, 15, 18, 24, 30, 48V ±1												
	OUTPUT VOLTAGE ADJUSTMEN	T RANGE[V]	2.85 - 3.6	4.5 - 5.5	Fixed ("Y"w	hich can be	adjusted the	output is avai	ilable as opti	on :9, 12, 15	, 18, 24, 30,	48V ±1			
	OUTPUT VOLTAGE SETTING[V]				8.6 - 9.4	11.5 - 12.5	14.4 - 15.6	17.3 - 18.7	23.0 - 25.0	23.0 - 25.0	28.5 - 31.5	46.0 -			
	OVERCURRENT PROT	Works over 105% of rating (-H : peak) and recovers automatically													
PROTECTION	OVERVOLTAGE PROT	4.00 - 5.25V Works at 115 - 140% of rating													
CIRCUIT AND	OPERATING INDICA	TION	Not provided												
OTHERS	REMOTE SENSING	Not provided													
	REMOTE ON/OFF	Option (Refer to Instruction Manual)													
	INPUT-OUTPUT		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature)												
ISOLATION	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50M Ω min (At Room Temperature)												
	OUTPUT-FG		AC500V 1 minute, Cutoff current = 100mA, DC500V 50M Ω min (At Room Temperature)												
	OPERATING TEMP.,HUMID.ANI	ALTITUDE	-10 to +60°C, 20 - 90%RH (Non condensing) (Refer to DERATING CURVE) 3,000m (10,000feet) max												
ENVIRONMENT	STORAGE TEMP.,HUMID.AND	ALTITUDE													
	VIBRATION		10 - 55Hz,	19.6m/s ² (2	G), 3minute	es period, 60	Ominutes ea	ch along X,	Y and Z ax	is					
	IMPACT		196.1m/s ²	(20G), 11m	s, once eac	h X, Y and	Z axis								
SAFETY AND	AGENOTATINOTA	-	UL60950-1	, EN60950-	1, EN50178	3, CSA C22.	2 No.234 Co	omplies with	DEN-AN a	nd IEC6095	i0-1				
REGULATIONS	CONDUCTED NOISI	E	Complies v	with FCC-B,	CISPR22-E	3, EN55022-	B, VCCI-B								
OTHERS	CASE SIZE/WEIGHT		75×37×2	22mm (W 🗙	HXD) /510	g max (with	out chassis	and cover)							
UITENS	COOLING METHOD		75×37×222mm (W×H×D) /510g max (without chassis and cover) Convection												


*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C,

with the input voltage held constant at the rated input/output. *3 (): peak current *4 Please contact us about safety approvals for the model with option.

*


LDA150W | CO\$EL

External view




Performance data


STATIC CHARACTERISTICS (LDA150W-5)




OVERCURRENT CHARACTERISTICS (LDA150W-5)



■RISE TIME & FALL TIME (LDA150W-5)






Ordering information **COSEL** AC-DC Power Supplies Open Frame/Enclosed type

LDA300W





MODEL	LDA300W-3	LDA300W-5	LDA300W-9	LDA300W-12	LDA300W-15	LDA300W-18	LDA300W-24	LDA300W-30	LDA300W-48
MAX OUTPUT WATTAGE[W]	180	300	306	324	330	306	336	300	302.4
DC OUTPUT	3V 60A	5V 60A	9V 34A	12V 27A	15V 22A	18V 17A	24V 14A	30V 10A	48V 6.3A

SPECIFICATIONS


	MODEL		LDA300W-3	LDA300W-5	LDA300W-9	LDA300W-12	LDA300W-15	LDA300W-18	LDA300W-24	LDA300W-30	LDA300W-			
	VOLTAGE[V]		AC 85 - 132	AC 85 - 132 / 170 - 264 1 φ										
			7.5typ (lo=100%)											
	CORRENT[A]	ACIN 200V	4.5typ (lo=100%)											
	FREQUENCY[Hz]		47 - 440											
INPUT	EFFICIENCY[%]	ACIN 100V	72typ	78typ	78typ	80typ	81typ	81typ	83typ	83typ	83typ			
		ACIN 200V	74typ	81typ	81typ	83typ	84typ	84typ	86typ	86typ	86typ			
	INRUSH CURRENT[A]	ACIN 100V												
		ACIN 200V			dary Surge C			an 3sec.to re-	-start)					
	LEAKAGE CURREN	T[mA]	0.75max (60Hz, According to UL, CSA, VDE and DEN-AN)											
	VOLTAGE[V]		3	5	9	12	15	18	24	30	48			
	CURRENT[A]	Forced air		60	34	27	22	17	14	10	6.3			
		Convection * 1	40 (60)	40 (60)	23 (34)	17 (27)	14 (22)	12 (17)	9 (14)	7 (10)	4.2 (6.3			
	LINE REGULATION	mV]	20max	20max	36max	48max	60max	72max	96max	120max	192ma>			
	LOAD REGULATION	l[mV]	40max	40max	100max	100max	120max	120max	150max	180max	240ma>			
	RIPPLE[mVp-p]	0 to +50℃ *2	80max	80max	120max	120max	120max	120max	120max	120max	150ma			
Ουτρυτ		-10 - 0℃ *2	140max	140max	160max	160max	160max	160max	160max	160max	200max			
	RIPPLE NOISE[mvp-p]	0 to +50℃ *2	120max	120max	150max	150max	150max	150max	150max	150max	400ma			
		-10 - 0℃ *2	160max	160max	180max	180max	180max	180max	180max	180max	600max			
	TEMPERATURE REGULA	TION[mV]		60max	120max	150max	180max	200max	290max	360max	560max			
	DRIFT[mV]	20max	20max	36max	48max	60max	72max	96max	120max	192ma>				
- F	START-UP TIME[ms]	200max (ACIN 100V, Io=100%)												
ŀ	HOLD-UP TIME[ms]	10typ (ACIN 85V, Io=100%) 20typ (ACIN 100V, Io=100%)												
	OUTPUT VOLTAGE ADJUSTMEN		2.85 - 3.6 5, 9, 12, 15, 18, 24, 30, 48V ±10%											
ŀ	OVERCURRENT PROT				ng and recove		ally							
FROILCHON	OVERVOLTAGE PROT		4.00 - 5.25V Works at 115 - 140% of rating											
CIRCUIT AND OTHERS	OPERATING INDICA	Not provided												
	REMOTE SENSING		Provided											
	REMOTE ON/OFF		Option (Refer to Instruction Manual)											
	INPUT-OUTPUT		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At Room Temperature)											
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At Room Temperature)											
	OUTPUT-FG		AC500V 1minute, Cutoff current = 100mA, DC500V 50M Ω min (At Room Temperature)											
	OPERATING TEMP.,HUMID.AND													
ENVIRONMENT	STORAGE TEMP.,HUMID.AND	ALTITUDE	-			0, :		,						
	VIBRATION				, 3minutes pe			ng X, Y and Z	z axis					
					once each X,									
	AGENCY APPROVAL				950-1, EN501			and IEC609	950-1					
	CONDUCTED NOISE		<u> </u>		SPR22-B, EN									
OTHERS 1	CASE SIZE/WEIGHT	-			IXD) /1kg ma									
	COOLING METHOD		Convection	Forced air (Refer to DER	ALING CUR	/E)							

*1

Peak load for 30sec. or less is acceptable if the total wattage is less than the rated wattage. This is the value that measured on measuring board with capacitor of 22 µ F within 150mm from output terminal. *2


*3 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C, with the input voltage held constant at the rated input/output.


Please contact us about safety approvals for the model with option. Parallel operation with other model is not possible. *4




Performance data


STATIC CHARACTERISTICS (LDA300W-5)





RISETIME & FALL TIME (LDA300W-5)





Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cosel:

S-LDA300 N-LDA75 N-LDA150 N-LDA10 S-LDA15 N-LDA30 S-LDA150 S-LDA50 S-LDA10 N-LDA100 S-LDA100 N-LDA50 S-LDA75 S-LDA30 N-LDA15 LDA50F-5-SNR LDA100W-24-H LDA100W-30-SNY LDA30F-24-SNG LDA75F-12-S LDA50F-12-Y LDA75F-24-SY LDA150W-9-RY LDA300W-5-RT LDA10F-12-SNY LDA150W-48-SN LDA100W-48 LDA30F-12-SY LDA50F-24-GY LDA300W-3-CT LDA300W-24-R LDA150W-12-CR LDA75F-5-CY LDA10F-24-M LDA50F-24-S LDA30F-24 LDA100W-15-RY LDA15F-5-GY LDA150W-18 LDA15F-15-GY LDA10F-3-SNC LDA75F-12-M LDA50F-24-CR LDA50F-12-R LDA75F-24-R LDA75F-30-SNR LDA50F-3-M LDA30F-24-SN LDA15F-3-S LDA75F-5-V LDA75F-15-Y LDA300W-3-R LDA10F-15-SNQ LDA50F-24-SN LDA100W-9-Y LDA50F-15-SN LDA150W-30-TD28 LDA300W-48-S LDA30F-15-SNY LDA50F-9-SNC LDA10F-5-S LDA75F-9-SN LDA150W-5-L LDA150W-30 LDA300W-30-CT LDA150W-12-Y LDA100W-48-SNY LDA150W-3-C LDA30F-5-Y LDA50F-130 LDA30F-12-G LDA75F-24-C LDA100W-12-SNRY LDA300W-24-C LDA100W-24-SNH LDA15F-5-Q LDA50F-30 LDA75F-15 LDA75F-9-Y LDA50F-5-G LDA30F-3-SNC LDA10F-5-SNC LDA30F-3-SN LDA50F-30 LDA75F-15 LDA75F-9-Y LDA50F-5-G LDA30F-3-SNC LDA10F-24-SNY LDA50F-3-SN LDA100W-48-CY LDA100W-5-CR LDA150W-24-SHY LDA10F-24-SNY LDA50F-3-SN LDA50F-30-SNRY LDA10F-5-SNY LDA300W-24-L LDA100W-5-SNC LDA30F-3-SN LDA50F-30-SNRY LDA10F-5-SNY LDA300W-24-L LDA100W-5-SNC LDA300W-30-R LDA15F-12-S LDA100W-24-HY LDA50F-24-HY LDA50F-5-Y LDA50F-5-Y LDA50F-5-Y