

### FEATURES

#### Electrical

- Efficiency up to 92.2%
- Fully protected: Input UVLO, Output OVP, OCP and OTP
- Multiple packaging (open frame, potting with standard case and flanged case)
- Wide output voltage trim range
- Monotonic and pre-biased startup
- No minimum load required
- Operating Baseplate Temperature: -40°C ~ +105°C
- Up to 4242Vdc isolation
- Working altitude up to 5500 m

#### Safety & Certificate

- IEC/EN/UL/CSA 60950-1, 62368-1
- Compliance to EN50155
- Compliance to EN45545-2
- ISO 9001, TL 9000, ISO 14001, QS 9000, OHSAS18001 certified manufacturing facility

#### Soldering Method

- Wave soldering
- Hand soldering

Input voltage: 9~60Vdc  
 Single output: 5V, 12V, 24V, 48V  
 Output power: 150W @24Vin, 48Vin  
 120W @12Vin

### Recommended Part Number

| Model Name     | Input  | Output |         | Eff. @ 100% Load | Others                  |
|----------------|--------|--------|---------|------------------|-------------------------|
| E35SE05030PDPG | 9V~60V | 5V     | 30A/24A | 92.2% @ 24Vin    | Positive on/off Potting |
| E35SE12013PDPG |        | 12V    | 13A/10A | 91.0% @ 24Vin    |                         |
| E35SE24006PDPG |        | 24V    | 6A/5A   | 92.2% @ 24Vin    |                         |
| E35SE48003PDPG |        | 48V    | 3A/2.5A | 91.2% @ 24Vin    |                         |

### Part Numbering System

| E             | 35            | S                 | E                 | xxxxx                                                                         | P                            | D                                   | P                                                                       | G                                                                                                                   |
|---------------|---------------|-------------------|-------------------|-------------------------------------------------------------------------------|------------------------------|-------------------------------------|-------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Form Factor   | Input Voltage | Number Of Outputs | Product Series    | Output Voltage & Current                                                      | ON/OFF Logic                 | Pin Length                          | Operating Ambient Temperature                                           | Option Code                                                                                                         |
| E - 1/8 Brick | 35 - 9~60V    | S - Single        | E - Series Number | 05030 - 5V & 30A<br>12013 - 12V & 13A<br>24006 - 24V & 6A<br>48003 - 48V & 3A | P - Positive<br>N - Negative | D - 0.24"<br>T - 0.22"<br>R - 0.17" | P - -40~85°C<br>M - -45~100°C<br>H - -55~100°C<br><small>*Note1</small> | A - Open Frame<br>H - With baseplate<br>G - With potting and regular Case<br>F - With potting and flanged Baseplate |

\*Note1: 'M' and 'H' available only for Option Code = 'G' or 'F'.

All of the modules are intended for wave soldering assembly onto system boards; please do not subject the modules through reflow temperature profile.

| Attribute           |                                                     |                                    | Model                  | E35SE05030         | E35SE12013 | E35SE24006 | E35SE48003 |
|---------------------|-----------------------------------------------------|------------------------------------|------------------------|--------------------|------------|------------|------------|
| INPUT               | Voltage                                             | continuous                         |                        | 9~60Vdc            |            |            |            |
|                     | Current                                             | @9Vin, full load, max.             |                        | 17.5A              | 17.5A      | 17.5A      | 17.5A      |
|                     |                                                     | @24Vin, no load, typ.              |                        | 190mA              | 300mA      | 160mA      | 220mA      |
|                     |                                                     | @Enable off, typ.                  |                        | 3 mA               |            |            |            |
|                     |                                                     | Inrush( I <sup>2</sup> t), typ.    |                        | 1 A <sup>2</sup> S |            |            |            |
|                     | Efficiency                                          | Reflected-ripple, typ.             |                        | 52mA               | 40mA       | 72mA       | 110mA      |
|                     |                                                     | 24Vin, 100% load, typ.             |                        | 92.2%              | 91.0%      | 92.2%      | 91.2%      |
|                     |                                                     | 24Vin, 60% load, typ.              |                        | 92.3%              | 90.4%      | 92.9%      | 92.2%      |
|                     |                                                     | 48Vin, 100% load, typ.             |                        | 91.3%              | 90.1%      | 91.1%      | 91.2%      |
|                     | 48Vin, 60% load, typ.                               |                                    | 91.7%                  | 88.2%              | 91.6%      | 90.2%      |            |
| OUTPUT              | Voltage Setting                                     |                                    | 5V±1%                  | 12V±1%             | 24V±1%     | 48V±1%     |            |
|                     | Current Rating                                      | 24~60Vin                           | 0~30A                  | 0~13A              | 0~6A       | 0~3A       |            |
|                     |                                                     | 9~24Vin                            | 0~24A                  | 0~10A              | 0~5A       | 0~2.5A     |            |
|                     |                                                     | 18~24Vin <sup>*Note 2</sup> , max. | 30A                    | 13A                | 6A         | 3A         |            |
|                     | Voltage adjustment range <sup>*Note 3</sup>         |                                    | -20%~+20%              |                    |            |            |            |
|                     | Ripple & Noise(Peak-Peak) <sup>*Note 4</sup> , typ. |                                    | 20mV                   | 85mV               | 230mV      | 200mV      |            |
|                     | Output Regulation                                   | Line                               | 0.2% max               |                    |            |            |            |
|                     |                                                     | Load                               | 0.2% max               |                    |            |            |            |
|                     |                                                     | Temperature                        | 1% max                 |                    |            |            |            |
|                     | Start-up Time <sup>*Note 5</sup>                    | Delay from input, typ.             | 250ms                  | 250ms              | 250mS      | 250ms      |            |
|                     |                                                     | Delay from on/off, typ.            | 250ms                  | 250ms              | 250ms      | 250ms      |            |
|                     |                                                     | Rise time, typ.                    | 6ms                    | 35ms               | 35ms       | 25ms       |            |
|                     | Transient response <sup>*Note 6</sup>               | Voltage deviation                  | 3% Vo,nom              |                    |            |            |            |
| Response time, typ. |                                                     | 200uS                              |                        |                    |            |            |            |
| Output capacitance  |                                                     |                                    | 0~10000uF              | 0~5200uF           | 0~2400uF   | 0~1200uF   |            |
| PROTECTION          | Output Over Current (hiccup)                        |                                    | 110%~180% Io,max       |                    |            |            |            |
|                     | Output Over Voltage (hiccup)                        |                                    | 120%~150% Vo,nom       |                    |            |            |            |
|                     | Input UVLO                                          | On threshold                       | 8.5V (8~9V)            |                    |            |            |            |
|                     |                                                     | Off threshold                      | 7.5V (7~8V)            |                    |            |            |            |
|                     |                                                     | Hysteresis, typ.                   | 1V                     |                    |            |            |            |
|                     | OTP shutdown                                        | NTC resistor <sup>*Note 7</sup>    | 128°C                  |                    |            |            |            |
| ISOLATION           | Voltage, Input to Output <sup>*Note 8</sup>         |                                    | 4242Vdc max            |                    |            |            |            |
|                     | Resistance (at 500Vdc)                              |                                    | 10 MΩ min              |                    |            |            |            |
|                     | Capacitance                                         |                                    | 500pF                  |                    |            |            |            |
| ENVIRONMENT         | Operating ambient temperature                       |                                    | -40~85°C with derating |                    |            |            |            |
|                     | Operating baseplate temperature                     |                                    | -40~105°Cwith derating |                    |            |            |            |
|                     | Storage temperature                                 |                                    | -55~125°C              |                    |            |            |            |
|                     | Operating Humidity                                  |                                    | Max 95%                |                    |            |            |            |
| Enable control      | Logic low                                           |                                    | -0.7~0.8V              |                    |            |            |            |
|                     | Logic high                                          |                                    | 2.4~5.0V               |                    |            |            |            |
|                     | Current (Von/off=0V), max.                          |                                    | 1.5mA max              |                    |            |            |            |
| Others              | Fixed Switching Frequency                           |                                    | 380 kHz                | 380 kHz            | 330kHz     | 290 kHz    |            |
|                     | MTBF (80% load,300LFM,25°C)                         |                                    | ≥1.4 Mhours            |                    |            |            |            |
|                     | Weight                                              | Open frame                         | 27.9g                  |                    |            |            |            |
|                     |                                                     | With baseplate                     | 33.5g                  |                    |            |            |            |
|                     |                                                     | With Potting                       | 50.5g                  |                    |            |            |            |
| Potting+ fanged     |                                                     | 54.5g                              |                        |                    |            |            |            |

## Notes

All specifications valid at 24Vin,100% Rated load and 25°C ambient, unless otherwise indicated.

\*2. Maximum output power is 150W at 18~24Vin which is guaranteed by design.

\*3. Maximum output power & current of the module should not over rated power & current.

\*4. Ripple & Noise measurement bandwidth is 0-20MHz, Vin=24V, full load, Cout=Refer ripple waveform for detailed value information.

\*5. "Delay from input": from Vin reaching turn-on threshold to 10% Vout (pre-applied enable); "Delay from on/off": From enable to 10% Vout (pre-applied Vin); "Rise time" From 10% to 90% Vout.


\*6. Load transient test condition: 24Vin, 10uF Low ESR Polymer & 1uF ceramic load cap & electrolytic capacitor, 50%~75% Load step, 0.1A/us.

\*7. Thermal test condition: 24Vin, 80% load, 200LFM, Airflow from Vin+ to Vin-.

\*8. With baseplate version, max input to output voltage is 3000Vdc.


## Mechanical Drawing

### Open Frame




NOTES:  
DIMENSIONS ARE IN MILLIMETERS AND (INCHES)  
TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.)  
X.XXmm±0.25mm(X.XXX in.±0.010 in.)


### With Baseplate



### With Regular Baseplate & Potting



### With Flanged Baseplate & Potting




NOTES:  
DIMENSIONS ARE IN MILLIMETERS AND (INCHES)  
TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.)  
X.XXmm±0.25mm(X.XXX in.±0.010 in.)


Note: All pins are copper alloy with matte Tin (Pb free) plated over Nickel under plating.

## Recommended Pad Layout

### For Open Frame and Regular Baseplate




### For Flanged Baseplate



NOTES:  
 DIMENSIONS ARE IN MILLIMETERS AND (INCHES)  
 TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.)  
 X.XXmm±0.25mm(X.XXX in.±0.010 in.)

## Typical EMI Filter Circuit for EN55032 Class A Conducted Emission




\* Compliance to EN50155


\*1,\*2: Please refer to page12 for the On/Off (pin2) and Trim (pin6) implementation.

| Location | Vendor P/N           | Description               | Qty | Vendor     | Purpose |
|----------|----------------------|---------------------------|-----|------------|---------|
| C1       | D3D2H505KB00352      | 500V 5uF K S27.5 32*11*20 | 2   | FARATRONIC | EMC     |
| FL1      | PH9455.155NL         | 19A 1.62mH NPB SRF 10MHz  | 1   | Pulse      | EMC     |
| CY1      | CS12-F2GA472MYNSAC   | 250VAC 4700pF M F VI7.5   | 5   | TDK        | EMC     |
| CY2      | CS12-F2GA472MYNSAC   | 250VAC 4700pF M F VI7.5   | 5   | TDK        | EMC     |
| C2       | 100PX220MGA12.5X20   | 100V 220uF M 12.5*20      | 1   | RUBYCON    | EMC     |
| C3       | C1210X475K101TX      | 100V 4.7uF K X7R 1210     | 2   | HOLY STONE | EMC     |
| C4       | GRM32NR72A104KA01L   | 100V 0.1uF K X7R 1210     | 2   | MURATA     | EMC     |
| C5       | 100ZLH33MEFCTA8X11.5 | 100V 33uF M 8*11.5        | 1   | RUBYCON    | EMC     |
| C6       | ZGD2AM100E11A        | 100V 10uF M 6.3*11        | 1   | LUMINOUS   | EMC     |
| C7       | GRM31CR72A105KA01L   | 100V 1uF K X7R 1206       | 1   | MURATA     | EMC     |


\*The components for EMC purpose can be deleted if no EMC requirement.




Efficiency vs. load current for various input voltage at 25°C.




Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (100ms/div).  
Top Trace: Vout, 1V/div; Bottom Trace: ON/OFF input, 2V/div.




Turn-on transient at full load current (100ms/div).  
Top Trace: Vout, 1V/div; Bottom Trace: input voltage, 10V/div.




Output voltage ripple at nominal input voltage and max load current (10mV/div, 2us/div)  
Load cap: 10μF Low ESR Polymer; 1μF ceramic capacitor  
270μF\*2 Low ESR Polymer;  
Bandwidth: 20MHz




Top trace Vout dynamic AC Value, 200mV/div, 200us/div  
Load cap: 10μF Low ESR Polymer; 1μF ceramic capacitor  
270μF\*2 Low ESR Polymer;  
Bottom Trace :load 50% to 75% of rated lout 10A/div,  
Bandwidth:20MHz




Efficiency vs. load current for various input voltage at 25°C.




Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (100ms/div).  
Top Trace: Vout, 4V/div; Bottom Trace: ON/OFF input, 2V/div.



Turn-on transient at full load current (100ms/div).  
Top Trace: Vout, 4V/div; Bottom Trace: input voltage, 10V/div.




Output voltage ripple at nominal input voltage and max load current (50mV/div, 2us/div)  
Load cap: 33 $\mu$ F\*5, Low ESR Polymer; 10 $\mu$ F, Low ESR Polymer; 1 $\mu$ F ceramic capacitor  
Bandwidth: 20MHz




Top trace Vout dynamic AC value, 200mV/div, 100us/div  
Load cap: 33 $\mu$ F\*5, Low ESR Polymer; 10 $\mu$ F Low ESR Polymer, 1 $\mu$ F ceramic capacitor  
Bandwidth: 20MHz







Efficiency vs. load current for various input voltage at 25°C.




Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (50ms/div).  
Top Trace: Vout, 10V/div; Bottom Trace: ON/OFF input, 2V/div.



Turn-on transient at full load current (50ms/div).  
Top Trace: Vout, 10V/div; Bottom Trace: input voltage, 10V/div.




Output voltage ripple at nominal input voltage and max load current (100mV/div, 2us/div)  
Load Cap: 33μF Low ESR Polymer; 10μF Low ESR Polymer;  
1μF Ceramic capacitor  
Bandwidth: 20MHz




Top trace Vout dynamic AC value, 500mV/div, 200us/div  
Load Cap: 33μF Low ESR Polymer; 10μF Low ESR Polymer;  
1μF Ceramic capacitor  
Bottom Trace, load 50% to 70% of rated Io, 2A/div, ,  
Bandwidth: 20MHz







Efficiency vs. load current for various input voltage at 25°C.




Power dissipation vs. load current at 25°C.




Turn-on transient at full load current (100ms/div).  
Top Trace: Vout, 10V/div; Bottom Trace: ON/OFF input, 2V/div.



Turn-on transient at full load current (100ms/div).  
Top Trace: Vout, 10V/div; Bottom Trace: input voltage, 20V/div.



Output voltage ripple at nominal input voltage and max load current (100mV/div, 2us/div)  
Load cap: 33uF Low ESR Polymer; 10uF Low ESR Polymer;  
1uF ceramic capacitor  
Bandwidth: 20MHz




Top trace Vout dynamic AC value, 500mV/div, 200us/div,  
Load Cap: 33uF Low ESR Polymer; 10uF Low ESR Polymer;  
1uF ceramic capacitor Bottom Trace, load 50% to 70% of rated  
Io, 1A/div,  
Bandwidth: 20MHz


## Input Source Impedance

The impedance of the input source connecting to the DC/DC power modules will interact with the modules and affect the stability. A low ac-impedance input source is recommended. If the source inductance is more than a few  $\mu\text{H}$ , we advise a  $100\mu\text{F}$  electrolytic capacitor mounted close to the input of the module to improve the stability.


## Input Reflected Ripple Current



Test set-up diagram showing measurement points for Input Terminal Ripple Current and Input Reflected Ripple Current. Measured input reflected-ripple current with a simulated source Inductance (LTEST) of  $12\mu\text{H}$ . Capacitor Cs offset possible battery impedance.




Input Terminal Ripple Current,  $i_c$ , at full rated output current and nominal input voltage with  $12\mu\text{H}$  source impedance and  $100\mu\text{F}$  electrolytic capacitor (500 mA/div, 5us/div).



Input reflected ripple current,  $i_s$ , through a  $12\mu\text{H}$  source inductor at nominal input voltage and rated load current (50 mA/div, 5us/div)

## Output Ripple Noise




Output voltage ripple test setup. Load capacitance:  $1\mu\text{F}$  ceramic capacitor and some extra Polymer capacitor may be needed. Bandwidth: 20 MHz. Scope measurements should be made using a BNC cable (length shorter than 20 inches). Position the load between 51 mm to 76 mm (2 inches to 3 inches) from the module.

## Layout and EMI Considerations


Delta's DC/DC power modules are designed to operate in a wide variety of systems and applications. For design assistance with EMC compliance and related PWB layout issues, please contact Delta's technical support team.

Below is the EN55032 Class A Conducted Emission test result using typical EMI filter circuit.


At T = +25°C, Typical input voltage and full load.




**E35SE05030**  
EN55032 Class A Conducted Emission Test Result



**E35SE12013**  
EN55032 Class A Conducted Emission Test Result



**E35SE24006**  
EN55032 Class A Conducted Emission Test Result



**E35SE48003**  
EN55032 Class A Conducted Emission Test Result

## Recommended PCB Layout

It is suggested to use multiple layers PCB and large size copper on system board which connects to pins of module, that can achieve better thermal performance.

## Features Descriptions

### Over-Current Protection

The modules include an internal output over-current protection circuit, which will endure current limiting for an unlimited duration during output overload. If the output current exceeds the OCP set point, the modules will shut down (hiccup mode).

The modules will try to restart after shutdown. If the overload condition still exists, the module will shut down again. This restart trial will continue until the overload condition is corrected.

### Over-Voltage Protection

The modules include an internal output over-voltage protection circuit, which monitors the voltage on the output terminals. If this voltage exceeds the over-voltage set point, the modules will shut down, and then restart after a hiccup-time (hiccup mode).

### Over-Temperature Protection


The over-temperature protection consists of circuitry that provides protection from thermal damage. If the over-temperature is detected the module will shut down, and restart after the temperature is within specification.

### Remote On/Off

The remote on/off feature on the module can be either negative or positive logic depend on the part number options on the last page.

- ❖ For Negative logic version, turns the module on during an external logic low and off during a logic high. If the remote on/off feature is not used, please short the on/off pin to Vi (-).
- ❖ For Positive logic version, turns the modules on during an external logic high and off during a logic low. If the remote on/off feature is not used, please leave the on/off pin to floating.


Remote on/off can be controlled by an external switch between the on/off terminal and the Vi (-) terminal. The switch can be an open collector or open drain.



Remote on/off implementation


### Output Voltage Adjustment (TRIM)

To increase the output voltage set point, connect an external resistor between the TRIM pin and the Sense(+).



Circuit for trim-up (increase output voltage)

To decrease the output voltage set point, connect an external resistor between the TRIM pin and the Sense(-).



Circuit for trim-down (decrease output voltage)

The maximum adjust range is  $\pm 20\%$ , the TRIM pin should be left open if this feature is not used.

Take E35SE12013 as example, for trim down, the external resistor value required to obtain a percentage of output voltage change  $\Delta$  is defined as:

$$R_{trim-down} = \left[ \frac{5.11}{\Delta} - 10.22 \right] (K\Omega)$$

Ex. When Trim-down -10% ( $12V \times 0.9 = 10.8V$ )

$$R_{trim-down} = \left[ \frac{5.11}{10\%} - 10.22 \right] (K\Omega) = 40.88 (K\Omega)$$

For trim up, the external resistor value required to obtain a percentage output voltage change  $\Delta$  is defined as:

$$R_{trim-up} = \left[ \frac{45}{\Delta} + 40 \right] K\Omega$$

Ex. When Trim-up +10% ( $12V \times 110\% = 13.2V$ )

$$R_{trim-up} = \left[ \frac{45}{10\%} + 40 \right] = 490 (K\Omega)$$

| Models     | Rtrim-up /kohm       | Rtrim-down/kohm       |
|------------|----------------------|-----------------------|
| E35SE05030 | $15.8/\Delta + 10.6$ | $5.11/\Delta - 10.22$ |
| E35SE12013 | $45/\Delta + 40$     | $5.11/\Delta - 10.22$ |
| E35SE24006 | $95/\Delta + 90$     | $5.11/\Delta - 10.22$ |
| E35SE48003 | $195/\Delta + 190$   | $5.11/\Delta - 10.22$ |

Where

$\Delta = |V_{nom} - V_{adj}| / V_{nom}$

$V_{nom}$  = Typical Output Voltage

$V_{adj}$  = Disired Output Voltage

## Safety Considerations

The power module must be installed in compliance with the spacing and separation requirements of the end-user's safety agency standard, i.e., EN 60950-1: 2006 + A11: 2009 + A1: 2010 + A12: 2011 + A2: 2013, IEC 60950-1: 2005, 2<sup>nd</sup> Edition + A1: 2009 + A2: 2013, CSA C22.2 No. 60950-1-07, 2<sup>nd</sup> Edition, 2014-10 and UL 60950-1, 2<sup>nd</sup> Edition, 2014-10-14, EN 62368-1: 2014, IEC 62368-1: 2014, CSA C22.2 No. 62368-1-14, 2<sup>nd</sup> Edition and UL 62368-1, 2<sup>nd</sup> Edition, if the system in which the power module is to be used must meet safety agency requirements.

This power module is not internally fused. To achieve optimum safety and system protection, an input line fuse is highly recommended. The safety agencies require a fast-blow fuse with 30A maximum rating to be installed in the ungrounded lead. A lower rated fuse can be used based on the maximum inrush transient energy and maximum input current.

## Soldering and Cleaning Considerations

Post solder cleaning is usually the final board assembly process before the board or system undergoes electrical testing. Inadequate cleaning and/or drying may lower the reliability of a power module and severely affect the finished circuit board assembly test. Adequate cleaning and/or drying is especially important for un-encapsulated and/or open frame type power modules. For assistance on appropriate soldering and cleaning procedures, please contact Delta's technical support team


## Thermal Testing Setup (Airflow Cooling)

Thermal management is an important part of the system design. To ensure proper, reliable operation, sufficient cooling of the power module is needed over the entire temperature range of the module. Convection cooling is usually the dominant mode of heat transfer.

Hence, the choice of equipment to characterize the thermal performance of the power module is a wind tunnel.

Delta's DC/DC power modules are characterized in heated vertical wind tunnels that simulate the thermal environments encountered in most electronics equipment. This type of equipment commonly uses vertically mounted circuit cards in cabinet racks in which the power modules are mounted.

The following figure shows the wind tunnel characterization setup. The power module is mounted on a 185mmX185mm, 105µm (3Oz), 6 layers' test PWB and is vertically positioned within the wind tunnel. The space between the neighboring PWB and the top of the power module is constantly kept at 6.35mm (0.25").




Note: Wind Tunnel Test Setup Figure Dimensions are in millimeters and (Inches)

**Figure 1: Wind Tunnel Test Setup**

## Thermal Derating


Heat can be removed by increasing airflow over the module. To enhance system reliability, the power module should always be operated below the maximum operating temperature. If the temperature exceeds the maximum module temperature, reliability of the unit may be affected.

## Thermal Curves (Open Frame)




**Figure 2: \* Hot spot1 temperature measured point.**  
The allowed maximum hotspot1 temperature is defined at 120°C.

## Thermal Curves (E35SE05030, Open Frame)




**Figure 3: E35SE05030 Output current vs. ambient temperature and air velocity @Vin=24V (Transverse Orientation, Airflow from Vin+ to Vin-, Open Frame)**




**Figure 4: E35SE05030 Output current vs. ambient temperature and air velocity @Vin=48V (Transverse Orientation, Airflow from Vin+ to Vin-, Open Frame)**



## Thermal Curves (E35SE12013, Open Frame)




**Figure 5: E35SE12013** Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, Open Frame)




**Figure 6: E35SE12013** Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, Open Frame)

## Thermal Curves (E35SE24006, Open Frame)




**Figure 7: E35SE24006** Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, Open Frame)

## Thermal Curves (E35SE24006, Open Frame)




**Figure 8: E35SE24006** Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, Open Frame)

## Thermal Curves (E35SE48003, Open Frame)




**Figure 9: E35SE48003** Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, Open Frame)



**Figure 10: E35SE48003** Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, Open Frame)




## Thermal Curves (With Base Plate)




**Figure 11:** \* Hot spot2 temperature measured point.  
The allowed maximum hotspot2 temperature is defined at 110°C.

## Thermal Curves(E35SE12013,With Base Plate)




**Figure 14:**E35SE12013 Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from  $V_{in+}$  to  $V_{in-}$ , With Base Plate)


## Thermal Curves (E35SE05030,With Base Plate)



**Figure 12:**E35SE05030 Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from  $V_{in+}$  to  $V_{in-}$ , With Base Plate)




**Figure 15:**E35SE12013 Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from  $V_{in+}$  to  $V_{in-}$ , With Base Plate)




**Figure 13:** E35SE05030 Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from  $V_{in+}$  to  $V_{in-}$ , With Base Plate)

## Thermal Curves(E35SE24006,With Base Plate)




**Figure 16:E35SE24006** Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Base Plate)


## Thermal Curves(E35SE48003,With Base Plate)



**Figure 18:E35SE48003** Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Base Plate)




**Figure 17:E35SE24006** Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Base Plate)




**Figure 19:E35SE48003** Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Base Plate)

## Thermal Curves (With Regular Baseplate & Potting)




**Figure 20:** \* Hot spot3 temperature measured point.  
The allowed maximum hotspot3 temperature is defined at 106°C.

## Thermal Curves (E35SE05030, With Regular Baseplate & Potting)




**Figure 21:** E35SE05030 Output current vs. ambient temperature and air velocity @  $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Regular Baseplate & Potting)




**Figure 22:** E35SE05030 Output current vs. ambient temperature and air velocity @  $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Regular Baseplate & Potting)

## Thermal Curves (E35SE12013, With Regular Baseplate & Potting)




**Figure 23:** E35SE12013 Output current vs. ambient temperature and air velocity @  $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Regular Baseplate & Potting)




**Figure 24:** E35SE12013 Output current vs. ambient temperature and air velocity @  $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Regular Baseplate & Potting)

## Thermal Curves (E35SE24006, With Regular Baseplate & Potting)




**Figure 25:E35SE24006** Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Regular Baseplate & Potting)


## Thermal Curves (E35SE48003, With Regular Baseplate & Potting)



**Figure 27:E35SE48003** Output current vs. ambient temperature and air velocity @ $V_{in}=24V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Regular Baseplate & Potting)




**Figure 26:E35SE24006** Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Regular Baseplate & Potting)



**Figure 28:E35SE48003** Output current vs. ambient temperature and air velocity @ $V_{in}=48V$  (Transverse Orientation, Airflow from Vin+ to Vin-, With Regular Baseplate & Potting)


## Thermal Testing Setup (Cold Plate Cooling)

The following figure shows cold plate cooling test setup. The power module is mounted on a 185mmX185mm,105μm (3Oz),6 layers' test PWB and attach to a cold plate with thermal interface material (TIM).




**Figure 29: Cold Plate Cooling Test Setup**

## Thermal Curves (With Regular Baseplate & Potting, Attach to Cold Plate)




**Figure 30:** \* Hot spot4 temperature measured point. The allowed maximum hotspot4 temperature is defined at 103°C.

## Thermal Curves (E35SE05030, With Regular Baseplate & Potting, Attach to Cold Plate)




**Figure 31:E35SE05030** Output Current vs. Hot Spot on Metal Case Temperature @Vin=24V&48V (With Regular Baseplate & Potting, Attach to Cold Plate)

## Thermal Curves (E35SE12013, With Regular Baseplate & Potting, Attach to Cold Plate)




**Figure 32:E35SE12013** Output Current vs. Hot Spot on Metal Case Temperature @Vin=24V&48V (With Regular Baseplate & Potting, Attach to Cold Plate)

## Thermal Curves (E35SE24006, With Regular Baseplate & Potting, Attach to Cold Plate)




**Figure 33:E35SE24006** Output Current vs. Hot Spot on Metal Case Temperature @Vin=24V&48V (With Regular Baseplate & Potting, Attach to Cold Plate)

## Thermal Curves (E35SE48003, With Regular Baseplate & Potting, Attach to Cold Plate)




**Figure 34:E35SE48003** Output Current vs. Hot Spot on Metal Case Temperature @Vin=24V&48V (With Regular Baseplate & Potting, Attach to Cold Plate)

## Thermal Curves (With Flanged Baseplate & Potting, Attach to Cold Plate)




**Figure 35:** \* Hot spot5 on metal case temperature measured point. The allowed maximum hotspot5 temperature is defined at 103°C

## Thermal Curves (E35SE05030, With Flanged Baseplate & Potting, Attach to Cold Plate)




**Figure 36:**E35SE05030 Output Current vs. Hot Spot on Metal Case Temperature @Vin=24V&48V (With Flanged Baseplate & Potting, Attach to Cold Plate)

## Thermal Curves (E35SE12016, With Flanged Baseplate & Potting, Attach to Cold Plate)




**Figure 37:** E35SE12013 Output Current vs. Hot Spot on Metal Case Temperature @Vin=24V&48V (With Flanged Baseplate & Potting, Attach to Cold Plate)

## Thermal Curves (E35SE24006, With Flanged Baseplate & Potting, Attach to Cold Plate)



**Figure 38:**E35SE24006 Output Current vs. Hot Spot on Metal Case Temperature @Vin=24V&48V (With Flanged Baseplate & Potting, Attach to Cold Plate)

## Thermal Curves (E35SE48003, With Flanged Baseplate & Potting, Attach to Cold Plate)



**Figure 39:**E35SE48003 Output Current vs. Hot Spot on Metal Case Temperature @Vin=24V&48V (With Flanged Baseplate & Potting, Attach to Cold Plate)




Generally, as the most common mass soldering method for the solder attachment, wave soldering is used for through-hole power modules and reflow soldering is used for surface-mount ones. Delta recommended soldering methods and process parameters are provided in this document for solder attachment of power modules onto system board. SAC305 is the suggested lead-free solder alloy for all soldering methods.

Reflow soldering is not a suggested method for through-hole power modules due to many process and reliability concerns. If you have this kind of application requirement, please contact Delta sales or FAE for further confirmation.

## Wave Soldering (Lead-free)

Delta's power modules are designed to be compatible with single-wave or dual wave soldering. The suggested soldering process must keep the power module's internal temperature below the critical temperature of 217°C continuously. The recommended wave-soldering profile is shown in following figure.



The typical recommended (for double-side circuit board) preheat temperature is 115+/-10°C on the top side (component side) of the circuit board. The circuit-board bottom-side preheat temperature is typically recommended to be greater than 135°C and preferably within 100 °C of the solder-wave temperature. A maximum recommended preheat up rate is 3°C /s. A maximum recommended solder pot temperature is 255+/-5°C with solder-wave dwell time of 3~6 seconds. The cooling down rate is typically recommended to be 6°C/s maximum.

## Hand Soldering (Lead Free)

Hand soldering is the least preferred method because the amount of solder applied, the time the soldering iron is held on the joint, the temperature of the iron, and the temperature of the solder joint are variable. The recommended hand soldering guideline is listed in Table below. The suggested soldering process must keep the power module's internal temperature below the critical temperature of 217°C continuously.

**Table Hand-Soldering Guideline**

| Parameter              | Single-side Circuit Board | Double-side Circuit Board | Multi-layers Circuit Board |
|------------------------|---------------------------|---------------------------|----------------------------|
| Soldering Iron Wattage | 90                        | 90                        | 90                         |
| Tip Temperature        | 385+/-10°C                | 420+/-10°C                | 420+/-10°C                 |
| Soldering Time         | 2 ~ 6 seconds             | 4 ~ 10 seconds            | 4 ~ 10 seconds             |



**Website:** [www.deltaww.com/dcdc](http://www.deltaww.com/dcdc)

**USA:**

Telephone:

East Coast: 978-656-3993

West Coast: 510-668-5100

Fax: (978) 656 3964

**Email:** [dcdc@deltaww.com](mailto:dcdc@deltaww.com)

**Europe:**

Phone: +31-20-655-0967

Fax: +31-20-655-0999

**Asia & the rest of world:**

Telephone: +886 3 4526107

ext 6220~6226

Fax: +886 3 4513485

## **WARRANTY**

Delta offers a two (2) years limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delta Electronics:](#)

[E35SE05030PDPG](#) [E35SE12013PDPG](#) [E35SE24006PDPG](#) [E35SE48003PDPG](#)