

Description

The XU devices are low phase noise quartz-based PLL oscillators supporting a large range of frequencies and output interface types. These devices are designed to operate at three different power supplies and are available in multiple package sizes as well as temperature grades.

With a patented one-time program (OTP) allowing for infinite memory shelf life, the XU devices can be programmed to generate an output frequency from 16kHz to 1500MHz with a resolution as low as 1Hz accuracy. The configuration capability of this family of devices allows for fast delivery times for both sample and large production orders.

Pin Assignments

Note: To minimize power supply line noise, a 0.01μF bypass capacitor should be placed between V_{DD} (Pin 6) and GND (Pin 3).




Table 1. Pin Description

Pin #	Name	Description
1	E/D NC	Enable/Disable ^{[a][b]} No connect
2	NC E/D	No connect Enable/Disable ^{[a][b]}
3	GND	Connect to ground
4	OUT	Output
5	OUT2	Complementary output ^[c]
6	V _{DD}	Supply voltage

[a] Pulled high internally = output enabled.

[b] Low = output disabled.

[c] Do not connect for LVCMOS. For XLVCMOS both OUT and OUT2 are ON and in opposite phase.

See [Ordering Information](#) for more details.

Features

- Frequency range: 0.016MHz to 1500MHz^[1]
- Output types: LVDS, LVPECL, HCSL, LVCMOS
- Supply voltage options: 1.8V, 2.5V, or 3.3V
- Phase jitter (1.875MHz to 20MHz): 100fs typical
- Phase jitter (12kHz to 20MHz): 300fs typical
- Package options:
 - 5.0 × 3.2 × 1.2 mm
 - 7.0 × 5.0 × 1.3 mm
- Operating temperature: -20°C to +70°C
 - Frequency stability options: ±20, ±25, ±50, or ±100 ppm
- Operating temperature: -40°C to +85°C
 - Frequency stability options: ±25, ±50, or ±100 ppm
- Operating temperature: -40°C to +105°C
 - Frequency stability options: ±50 or ±100 ppm

[1] There is a dead zone between 1037.5MHz to 1300MHz.
Contact [support](#) for frequencies above 1300MHz.

Ordering Information




Table 2. Frequency Stability and Operating Temperature Decoder

“Precision” and “Temperature Range” Codes	Operating Temperature	Frequency Stability		
		Minimum	Maximum	Units
“8” and “X”	-20°C to +70°C	-20	+20	ppm
“6” and “X”	-20°C to +70°C	-25	+25	ppm
“5” and “X”	-20°C to +70°C	-50	+50	ppm
“0” and “X”	-20°C to +70°C	-100	+100	ppm
“6” and “I”	-40°C to +85°C	-25	+25	ppm
“5” and “I”	-40°C to +85°C	-50	+50	ppm
“0” and “I”	-40°C to +85°C	-100	+100	ppm
“5” and “K”	-40° to +105°C	-50	+50	ppm
“0” and “K”	-40° to +105°C	-100	+100	ppm

Contents

Description	1
Pin Assignments	1
Features	1
Ordering Information	2
Absolute Maximum Ratings	4
ESD Compliance	4
Mechanical Testing	4
Solder Reflow Profile	4
DC Electrical Characteristics	5
AC Electrical Characteristics	8
Output Waveforms	12
Package Outline Drawings	14
Marking Diagrams	14
Revision History	15

Absolute Maximum Ratings

Stresses above the ratings listed below can cause permanent damage to the device. The ratings, which are standard values for Renesas commercially rated parts, are stress ratings only. Functional operation of the device at these or any other conditions above those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods can affect product reliability. Electrical parameters are guaranteed only over the recommended operating temperature range.

Table 3. Absolute Maximum Ratings

Item	Rating			
V _{DD}	-0.5 to +5.0V			
E/D	-0.5V to V _{DD} + 0.5V			
OUT	-0.5V to V _{DD} + 0.5V			
Storage Temperature	-55°C to 125°C			
Maximum Junction Temperature	125°C			
Core Current	65mA maximum			
Theta J _A	JU6	75.9 °C/W	JS6	89.6 °C/W
Theta J _B		48.6 °C/W		54.3 °C/W

ESD Compliance

Table 4. ESD Compliance

Human Body Model (HBM)	1000V
------------------------	-------


Mechanical Testing

Table 5. Mechanical Testing *

Parameter	Test Method
Mechanical Shock	Half-sine wave with 0.3ms 3000G. X, Y, Z each direction 1 time.
Mechanical Vibration	Frequency: 10 – 55MHz amplitude: 1.5mm. Frequency: 55 – 2000Hz peak value: 20G. Duration time: 4H for each X,Y,Z axis; total 12hours.
High Temp Operating Life (HTOL)	2000 hours at 125°C (under power).
Hermetic Seal	Gross leak (air leak test). Fine leak (Helium leak test) He-pressure: 6kgf/cm ² 2 hours.

* MSL level does not apply.

Solder Reflow Profile



DC Electrical Characteristics

Note for all DC Electrical Characteristics tables: A pull-up resistor from V_{DD} to E/D enables output when pin 1 is left open.

Table 6. 3.3V IDD DC Electrical Characteristics

$V_{DD} = 3.3V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$.

Symbol	Parameter	Output Type	Conditions	Minimum	Typical	Maximum	Units
I_{DD}	Current Consumption	LVDS	0.016MHz to 400MHz.			97	mA
			400.000+MHz to 1.5GHz.			122	
		LVPECL	0.016MHz to 212.5MHz.			115	
			212.5+MHz to 400MHz.			128	
			400+MHz to 670MHz.			142	
		HCSL	0.016MHz to 670MHz.			145	
		LVCMOS	0.016MHz to 62.5MHz.			98	
			62.5+MHz to 167MHz.			108	

Table 7. 2.5V IDD DC Electrical Characteristics

$V_{DD} = 2.5V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$.

Symbol	Parameter	Output Type	Conditions	Minimum	Typical	Maximum	Units
I_{DD}	Current Consumption	LVDS	0.016MHz to 400MHz.			90	mA
			400.000+MHz to 1.35GHz.			103	
		LVPECL	0.016MHz to 156.25MHz.			102	
			156.25+MHz to 400MHz.			112	
			400+MHz to 670MHz.			118	
		HCSL	0.016MHz to 400MHz.			102	
			400.000+MHz to 670MHz.			112	
		LVCMOS	0.016MHz to 62.5MHz.			80	
			62.5+MHz to 125MHz.			85	
			125+MHz to 167MHz.			92	

Table 8. 1.8V IDD DC Electrical Characteristics
 $V_{DD} = 3.3V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$.

Symbol	Parameter	Output Type	Conditions	Minimum	Typical	Maximum	Units
I_{DD}	Current Consumption	LVDS	0.016MHz to 400MHz.			65	mA
			400.000+MHz to 1.0GHz.			72	
		LVPECL	0.016MHz to 250MHz.			75	
			250.000+MHz to 670MHz.			97	
		HCSL	0.016MHz to 400MHz.			68	
			400.000+MHz to 670MHz.			77	
		LVC MOS	0.016MHz to 125MHz.			58	

Table 9. LVDS DC Electrical Characteristics
 $V_{DD} = 3.3V, 2.5V, 1.8V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$. Below are guaranteed for listed standard frequencies.

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
V_{OD}	Differential Output Voltage		0.25	0.4	0.5	V
V_{OS}	Output Offset Voltage		1	1.17	1.375	
V_{IH}	Enable/Disable Input High Voltage		$70\%V_{DD}$			
V_{IL}	Enable/Disable Input Low Voltage				$30\%V_{DD}$	

Table 10. LVPECL DC Electrical Characteristics
 $V_{DD} = 3.3V, 2.5V, 1.8V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$. Below are guaranteed for listed standard frequencies.

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
V_{OH}	Output High Voltage	$V_{DD} = 3.3V \pm 5\%$.	1.85		2.3	V
		$V_{DD} = 2.5V \pm 5\%$.	1.1		1.45	
		$V_{DD} = 1.8V \pm 5\%$.	0.5		0.8	
V_{OL}	Output Low Voltage	$V_{DD} = 3.3V \pm 5\%$.	1.1		1.65	
		$V_{DD} = 2.5V \pm 5\%$.	0.35		0.85	
		$V_{DD} = 1.8V \pm 5\%$.	0		0.25	
V_{IH}	Enable/Disable Input High Voltage		$70\%V_{DD}$			
V_{IL}	Enable/Disable Input Low Voltage				$30\%V_{DD}$	

Table 11. HCSL DC Electrical Characteristics

$V_{DD} = 3.3V, 2.5V, 1.8V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$. Below are guaranteed for listed standard frequencies.

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
V_{OH}	Output High Voltage	$V_{DD} = 3.3V \pm 5\%$	0.6		1.1	V
		$V_{DD} = 2.5V \pm 5\%$	0.55		0.95	
		$V_{DD} = 1.8V \pm 5\%$	0.45		0.7	
V_{OL}	Output Low Voltage		0		0.2	
V_{IH}	Enable/Disable Input High Voltage		$70\%V_{DD}$			
V_{IL}	Enable/Disable Input Low Voltage				$30\%V_{DD}$	

Table 12. LVCMOS DC Electrical Characteristics

$V_{DD} = 3.3V, 2.5V, 1.8V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$. Below are guaranteed for listed standard frequencies.

Symbol	Parameter	Conditions	Minimum	Typical	Maximum	Units
V_{OH}	Differential Output Voltage		$90\%V_{DD}$			V
V_{OL}	Output Offset Voltage				$10\%V_{DD}$	
V_{IH}	Enable/Disable Input High Voltage		$70\%V_{DD}$			
V_{IL}	Enable/Disable Input Low Voltage				$30\%V_{DD}$	

AC Electrical Characteristics

Table 13. 3.3V AC Electrical Characteristics
 $V_{DD} = 3.3V \pm 5\%$, $T_A = -20^{\circ}C$ to $+70^{\circ}C$; $-40^{\circ}C$ to $+85^{\circ}C$; $-40^{\circ}C$ to $+105^{\circ}C$.

Symbol	Parameter	Test Condition		Minimum	Typical	Maximum	Units
F	Output Frequency Range	LVDS.		0.016		1500	MHz
		LVPECL, HCSL.		0.016		670	
		LVCMOS.		0.016		167	
	Frequency Stability	Temperature = $-20^{\circ}C$ to $+70^{\circ}C$.		-20		+20	ppm
				-25		+25	
				-50		+50	
				-100		+100	
		Temperature = $-40^{\circ}C$ to $+85^{\circ}C$.		-25		+25	ppm
				-50		+50	
		Temperature = $-40^{\circ}C$ to $+105^{\circ}C$.		-50		+50	ppm
				-100		+100	
	Output Load	LVDS.	Differential.		100		Ω
		LVPECL.	$V_{DD} - 2.0V$.		50		
		HCSL.	To GND.		50		
		LVCMOS.	To GND.		15		pF
T_{ST}	Start-up Time	Output valid time after V_{DD} meets minimum specified level.				10	ms
t_R	Output Rise Time	LVDS.	20% to 80% Vpk-pk.		275	380	ps
		LVPECL.				400	
		HCSL.				330	
		LVCMOS.	10% to 90% V_{DD} .			3	ns
t_F	Output Fall Time	LVDS.	80% to 20% Vpk-pk.		275	380	ps
		LVPECL.				400	
		HCSL.				330	
		LVCMOS.	90% to 10% V_{DD} .			3	ns
O_{DC}	Output Clock Duty Cycle	LVDS.		45		55	%
		LVPECL.	$F_{OUT} \leq 312.5MHz$.	45		55	
			$F_{OUT} > 312.5MHz$.	40		60	
		HCSL.		45		55	
		LVCMOS.	$F_{OUT} \leq 62.5MHz$.	45		55	
			$F_{OUT} > 62.5MHz$.	40		60	
T_{OE}	Output Enable/ Disable Time					100	ns

Table 13. 3.3V AC Electrical Characteristics (Cont.)
 $V_{DD} = 3.3V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$.

Symbol	Parameter	Test Condition		Minimum	Typical	Maximum	Units
f_{JITTER}	Phase Jitter (12kHz–20MHz)	LVDS.			300	400	fsec
		LVPECL.			300	400	
		HCSL.			300	400	
		LVC MOS.	$F_{OUT} = 100MHz.$		300	400	

Table 14. 2.5V AC Electrical Characteristics
 $V_{DD} = 2.5V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$.

Symbol	Parameter	Test Condition		Minimum	Typical	Maximum	Units
F	Output Frequency Range	LVDS.		0.016		1350	MHz
		LVPECL.		0.016		670	
		HCSL.		0.016		670	
		LVC MOS.		0.016		167	
	Frequency Stability	Temperature = $-20^\circ C$ to $+70^\circ C$.		-20		+20	ppm
				-25		+25	
				-50		+50	
				-100		+100	
		Temperature = $-40^\circ C$ to $+85^\circ C$.		-25		+25	ppm
				-50		+50	
	Output Load	Temperature = $-40^\circ C$ to $+105^\circ C$.		-50		+50	ppm
				-100		+100	
		LVDS.	Differential.		100		Ω
			$V_{DD} - 2.0V.$		50		
			To GND.		50		
			To GND.		15		pF
T_{ST}	Start-up Time	Output valid time after V_{DD} meets minimum specified level.				10	ms
t_R	Output Rise Time	LVDS.	20% to 80% Vpk-pk.		300	400	ps
		LVPECL.			250	630	
		HCSL.				315	
		LVC MOS.	10% to 90% V_{DD} .			3	ns
t_F	Output Fall Time	LVDS.	80% to 20% Vpk-pk.		300	400	ps
		LVPECL.			360	630	
		HCSL.				315	
		LVC MOS.	90% to 10% V_{DD} .			3	ns

Table 14. 2.5V AC Electrical Characteristics (Cont.)
 $V_{DD} = 2.5V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$.

Symbol	Parameter	Test Condition	Minimum	Typical	Maximum	Units
O_{DC}	Output Clock Duty Cycle	LVDS.	45		55	%
		LVPECL.	$F_{OUT} \leq 156.25MHz.$		55	
			$F_{OUT} \leq 156.25MHz.$		60	
		HCSL.	45		55	
		LVCMOS.	$F_{OUT} \leq 62.5MHz.$		55	
			$F_{OUT} > 62.5MHz.$		60	
T_{OE}	Output Enable/ Disable Time				100	ns
f_{JITTER}	Phase Jitter (12kHz–20MHz)	LVDS.		400	500	fsec
		LVPECL.		350	500	
		HCSL.		350	500	
		LVCMOS.	$F_{OUT} = 100MHz.$	350	500	

Table 15. 1.8V AC Electrical Characteristics
 $V_{DD} = 1.8V \pm 5\%$, $T_A = -20^\circ C$ to $+70^\circ C$; $-40^\circ C$ to $+85^\circ C$, $-40^\circ C$ to $+105^\circ C$.

Symbol	Parameter	Test Condition	Minimum	Typical	Maximum	Units
F	Output Frequency Range	LVDS.	0.016		1000	MHz
		LVPECL, HCSL.	0.016		670	
		LVCMOS.	0.016		125	
	Frequency Stability	Temperature = $-20^\circ C$ to $+70^\circ C$.	-20		+20	ppm
			-25		+25	
			-50		+50	
		Temperature = $-40^\circ C$ to $+85^\circ C$.	-100		+100	ppm
			-25		+25	
			-50		+50	
	Output Load	Temperature = $-40^\circ C$ to $+105^\circ C$.	-100		+100	ppm
			-50		+50	
			-100		+100	
		LVDS.	Differential.	100		Ω
		LVPECL, HCSL.	To GND.	50		
		LVCMOS.	To GND.	10		pF
T_{ST}	Start-up Time	Output valid time after V_{DD} meets minimum specified level.			10	ms
t_R	Output Rise Time	LVDS.	20% to 80% Vpk-pk.	250	315	ps
		LVPECL.		250	350	
		HCSL.			320	
		LVCMOS.	10% to 90% V_{DD} .	5		ns

Table 15. 1.8V AC Electrical Characteristics (Cont.)
 $V_{DD} = 1.8V \pm 5\%$, $T_A = -20^{\circ}C$ to $+70^{\circ}C$; $-40^{\circ}C$ to $+85^{\circ}C$, $-40^{\circ}C$ to $+105^{\circ}C$.

Symbol	Parameter	Test Condition		Minimum	Typical	Maximum	Units
t_F	Output Fall Time	LVDS.	80% to 20% V _{pk-pk} .		250	315	ps
		LVPECL.			250	350	
		HCSL.				320	
		LVC MOS.	90% to 10% V _{DD} .		5		ns
O_{DC}	Output Clock Duty Cycle	LVDS.	$F_{OUT} \leq 156.25MHz.$	45		55	%
			$F_{OUT} \leq 156.25MHz.$	40		60	
		LVPECL.	$F_{OUT} \leq 312.5MHz.$	45		55	
			$F_{OUT} > 312.5MHz.$	40		60	
		HCSL.		40		60	
		LVC MOS.	$F_{OUT} \leq 62.5MHz.$	45		55	
			$F_{OUT} > 62.5MHz.$	40		60	
T_{OE}	Output Enable/ Disable Time					100	ns
f_{JITTER}	Phase Jitter (12kHz–20MHz)	LVDS.			800	1200	fsec
		LVPECL.			750	1200	
		HCSL.			100	1200	
		LVC MOS.	$F_{OUT} = 100MHz.$		800	1200	

Notes for all AC Electrical Characteristics tables:
¹ A pull-up resistor from V_{DD} to E/D enables output when pin 1 is left open.

² Installation should include a 0.01μF bypass capacitor placed between VDD and GND to minimize power supply line noise.

³ Stability is inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, aging, shock and vibration.

⁴ Standard LVC MOS frequencies include 10MHz, 12MHz, 12.288MHz, 16MHz, 20MHz, 24MHz, 24.576MHz, 25MHz, 33.333MHz, 40MHz, 48MHz, 50MHz, 100MHz, 125MHz and 156.25MHz.

⁵ Standard differential frequencies include 100MHz, 106.25MHz, 125MHz, 150MHz, 155.52MHz, 156.25MHz, 200MHz, 212.5MHz, 250MHz, 300MHz, 312.5MHz and 400MHz.

Output Waveforms

Figure 1. LVDS Output Waveforms




Figure 2. LVPECL Output Waveforms




Figure 3. HCSL Output Waveforms





Figure 4. LVCMOS Output Waveforms




Package Outline Drawings

The package outline drawings (JS6, JU6) are appended at the end of this document. The package information is the most current data available.


Marking Diagrams

JS6 5.0 × 3.2 mm Package Option (example based on XUH510040.000000I)



- Line 1:
 - “XU” = family; “H” = output type; “5” = package size; “1” = voltage; “0” = precision level. This number will vary depending upon the output type, voltage, and precision values selected in the orderable part number.
- Line 2:
 - “040” denotes last three digits to the left of the decimal point as shown in the above example. This number will vary depending upon the frequency value selected in the orderable part number.
 - “YW” denotes the last digit of the year and work week the part was assembled.

JU6 7.0 × 5.0 mm Package Option (example based on XUH738044.736000X)




- Line 1:
 - “XU” = family; “H” = output type; “7” = package size; “3” = voltage; “8” = precision level. This number will vary depending upon the output type, voltage, and precision values selected in the orderable part number.
- Line 2:
 - “044” denotes last three digits to the left of the decimal point as shown in the above example. This number will vary depending upon the frequency value selected in the orderable part number.
 - “YW” denotes the last digit of the year and work week the part was assembled.


Revision History

Revision Date	Description of Change
January 11, 2022	- Updated Frequency Stability values in Table 15. - Removed Aging parameters in Table 13, Table 14 and Table 15.
December 7, 2021	- Updated Frequency Stability values in Table 13 and Table 14. - Removed I2C section.
November 23, 2021	Added Frequency Stability and Operating Temperature Decoder table after Ordering Information.
August 18, 2021	Moved Ordering Information table to just after Pin Descriptions.
January 19, 2021	- Removed 4-pin package description table, figure, and package drawing references. - Added footnote for pin 5 in Table 1. - Added footnote under “Output Type” in Ordering Information.
January 12, 2021	Added Marking Diagrams section and updated Package Outline Drawings links.
February 11, 2020	Added I2C Bus Characteristics tables.
June 28, 2019	Added footnote to frequency range bullet under front page Features.
June 25, 2018	Updated Package Outline Drawings section.
November 22, 2017	- Updated Theta JA and JB in Absolute Maximum Ratings table. - Added MSL statement under Mechanical Testing table. - Updated ordering information.
October 19, 2017	- Updated document title. - Updated Features bullets. - Updated Absolute Maximum Ratings and ESD Compliance tables. - Added -40°C to +105°C rating to all electrical tables. - Removed phase noise charts. - Updated Ordering Information table.
May 12, 2017	- Reformatted embedded tables. - Removed “Jitter Performance” tables and moved the “Phase Jitter (12kHz–20MHz)” parameter to its respective AC Electrical Characteristics table. - Updated all Output Waveform drawings.
December 1, 2016	Initial release.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	04/2/12	DP
01	ADDED LID IN TOP VIEW	07/12/12	KS
02	UPDATED LID TOLERANCES	12/03/12	KS
03	UPDATE PACKAGE DRAWING	8/8/14	JHUA



TOP VIEW



BOTTOM VIEW



SIDE VIEW

NOTES:
1. ALL DIMENSIONS IN MM.

TOLERANCES UNLESS SPECIFIED		6024 Silver Creek Valley Rd San Jose, CA 95138 PHONE: (408) 727-6116 FAX: (408) 492-8674	
DECIMAL	ANGULAR	 IDT™ www.IDT.com	
XX±	±		
XXX±			
XXXX±			
APPROVALS	DATE	TITLE JS6 PACKAGE OUTLINE	
DRAWN <i>QAC</i>	04/2/12	5.0 x 3.2 mm BODY	
CHECKED		1.1 mm Thick	
SIZE	DRAWING No.	REV	
C	PSC-4411	03	
DO NOT SCALE DRAWING			SHEET 1 OF 2

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.0 Mar 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Renesas Electronics:

[XUN535100.000JS6I8](#) [XUP535212.500JS6I8](#) [XUP535156.250JS6I8](#) [XUP535150.000JS6I8](#) [XUP535100.000JS6I8](#)
[XUP535125.000JS6I8](#) [XUL535212.500JS6I8](#) [XUL535100.000JS6I8](#) [XUL535156.250JS6I8](#) [XUL535150.000JS6I8](#)
[XUL535125.000JS6I8](#) [XUL525312.500JS6I](#) [XUL525400.000JS6I](#) [XUL535125.000JS6I](#) [XUL525156.250JS6I8](#)
[XUL525400.000JS6I8](#) [XUL535250.000JS6I8](#) [XUL525125.000JS6I](#) [XUL535212.500JS6I](#) [XUL525106.250JS6I8](#)
[XUL525150.000JS6I](#) [XUL525250.000JS6I](#) [XUL525100.000JS6I8](#) [XUL525300.000JS6I8](#) [XUL535106.250JS6I](#)
[XUL535312.500JS6I8](#) [XUL535300.000JS6I](#) [XUL525212.500JS6I8](#) [XUL525155.520JS6I8](#) [XUL525200.000JS6I](#)
[XUL535025.000JS6I8](#) [XUL535400.000JS6I](#) [XUL535250.000JS6I](#) [XUL525106.250JS6I](#) [XUL535312.500JS6I](#)
[XUL525025.000JS6I](#) [XUL535156.250JS6I](#) [XUL535025.000JS6I](#) [XUL535200.000JS6I8](#) [XUL525150.000JS6I8](#)
[XUL535300.000JS6I8](#) [XUL535400.000JS6I8](#) [XUL525312.500JS6I8](#) [XUL525125.000JS6I8](#) [XUL525025.000JS6I8](#)
[XUL535155.520JS6I](#) [XUL525250.000JS6I8](#) [XUL535200.000JS6I](#) [XUL535150.000JS6I](#) [XUL535106.250JS6I8](#)
[XUL525155.520JS6I](#) [XUL535155.520JS6I8](#) [XUL525100.000JS6I](#) [XUL525300.000JS6I](#) [XUL525200.000JS6I8](#)
[XUL535100.000JS6I](#) [XUL525212.500JS6I](#) [XUL525156.250JS6I](#) [XUN525150.000JS6I8](#) [XUN525125.000JS6I8](#)
[XUN535150.000JS6I8](#) [XUN535312.500JS6I](#) [XUN525400.000JS6I](#) [XUN535125.000JS6I8](#) [XUN535400.000JS6I](#)
[XUN525212.500JS6I](#) [XUN535400.000JS6I8](#) [XUN525155.520JS6I](#) [XUN525300.000JS6I](#) [XUN525312.500JS6I](#)
[XUN525300.000JS6I8](#) [XUN525155.520JS6I8](#) [XUN535250.000JS6I8](#) [XUN535106.250JS6I](#) [XUN535300.000JS6I8](#)
[XUN525100.000JS6I](#) [XUN525150.000JS6I](#) [XUN535312.500JS6I8](#) [XUN525312.500JS6I8](#) [XUN535156.250JS6I8](#)
[XUN525106.250JS6I8](#) [XUN535150.000JS6I](#) [XUN525200.000JS6I](#) [XUN525212.500JS6I8](#) [XUN535155.520JS6I](#)
[XUN535200.000JS6I](#) [XUN535200.000JS6I8](#) [XUN535250.000JS6I](#) [XUN525156.250JS6I8](#) [XUN535100.000JS6I](#)
[XUN535300.000JS6I](#) [XUN535156.250JS6I](#) [XUN535106.250JS6I8](#) [XUN525250.000JS6I](#) [XUN525100.000JS6I8](#)
[XUN535155.520JS6I8](#) [XUN535212.500JS6I8](#) [XUN525106.250JS6I](#) [XUN535125.000JS6I](#) [XUN525250.000JS6I8](#)