


PRELIMINARY

XLamp® XP-G4 LEDs



PRODUCT DESCRIPTION

XLamp® XP-G4 LEDs are the fourth generation of Cree LED's standard-setting XP-G product family, featuring both best-in-class efficacy and optical performance. New features in this generation include a higher maximum drive current of 3000 mA and an optimized optical profile that maximizes on-axis light output.

With the same mechanical dimensions as XP-G3, the XP-G4 is an easy upgrade path for many high-power LED designs. XP-G4 provides higher maximum current and lower thermal resistance than competing high-power LEDs, enabling new levels of output and reliability for many lighting applications.

XLamp XP-G4 LEDs are optimized for a wide range of directional lighting applications where light control and long lifetime are critical, including outdoor, indoor premium, architectural, portable and entertainment.

FEATURES

- Available in no CRI minimum white, 70-, 80- and 90-CRI white
- 3-step and 5-step options
- Binned at 85 °C
- Maximum drive current: 3000 mA
- Low thermal resistance: 1.3 °C/W
- Wide viewing angle: 115°
- Unlimited floor life at ≤ 30 °C/85% RH
- Reflow solderable - JEDEC J-STD-020C
- Electrically neutral thermal path
- RoHS and REACH compliant



Cree LED / 4001 E. Hwy. 54, Suite 2000 / Durham, NC 27709 USA / +1.919.313.5330 / www.cree-led.com

PRELIMINARY

TABLE OF CONTENTS

Characteristics	3
Flux Characteristics	4
Relative Spectral Power Distribution	16
Relative Flux vs. Junction Temperature.....	16
Electrical Characteristics.....	17
Relative Luminous Flux vs. Current.....	17
Relative Chromaticity vs. Current and Temperature	18
Typical Spatial Distribution.....	19
Thermal Design	19
Performance Groups - Luminous Flux.....	20
Performance Groups - Chromaticity	21
Cree LED's Standard Cool White Kits Plotted on ANSI Standard Chromaticity Regions	25
Cree LED's Standard Warm and Neutral White Kits Plotted on ANSI Standard Chromaticity Regions	26
Cree LED's EasyWhite® White Kits Plotted on ANSI Standard Chromaticity Regions	27
Cree LED's Standard Chromaticity Kits.....	28
Bin and Order Code Formats	29
Reflow Soldering Characteristics.....	30
Notes	31
Mechanical Dimensions	33
Tape and Reel.....	35
Packaging.....	37

PRELIMINARY

CHARACTERISTICS

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point [ⓓ]	°C/W		1.3	
Viewing angle (FWHM)	degrees		120	
Temperature coefficient of voltage	mV/°C		-1.3	
ESD withstand voltage (HBM per Mil-Std-883D)			Class 3B	
DC forward current	mA			3000
Reverse voltage	V			5
Forward voltage (@ 700 mA, 85 °C)	V		2.8	3.3
Forward voltage (@ 1000 mA, 85 °C)	V		2.92	
Forward voltage (@ 2000 mA, 85 °C)	V		3.14	
Forward voltage (@ 3000 mA, 85 °C)	V		3.32	
LED junction temperature	°C			150

Note:

- ⓓ Thermal resistance measurement was performed per the JEDEC JESD51-14 standard. See the [Thermal Resistance Measurement application note](#) for more details.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$

The following table provides order codes for XLamp XP-G4 LEDs. For a complete description of the order code nomenclature, please see the Bin and Order Code Formats section (page 29). For definitions of the chromaticity kits, please see the Cree LED's Standard Chromaticity Kits section (page 28).

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
DT	7000 K	D1	350	382	XPGEWT-01-0000-000000RDT			
		C5	340	371	XPGEWT-01-0000-000000QDT			
		C4	330	360	XPGEWT-01-0000-000000PDT	XPGEWT-01-0000-000000BPD		
		C3	320	349		XPGEWT-01-0000-000000BND		
		C2	310	338		XPGEWT-01-0000-000000BMD		
		C1	300	327			XPGEWT-01-0000-000000HLD	
		B5	290	316			XPGEWT-01-0000-000000HKD	
E0	>6500 K	D2	360	393	XPGEWT-01-0000-000000SEO			
		D1	350	382	XPGEWT-01-0000-000000REO			
		C5	340	371				
		C4	330	360		XPGEWT-01-0000-000000BPEO		
		C3	320	349		XPGEWT-01-0000-000000BNEO		
		C2	310	338		XPGEWT-01-0000-000000BMEO		
		C1	300	327			XPGEWT-01-0000-000000HLEO	
		B5	290	316			XPGEWT-01-0000-000000HKEO	

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
E1	6500 K	D1	350	382	XPGEWT-01-0000-000000RE1			
		C5	340	371	XPGEWT-01-0000-000000QE1	XPGEWT-01-0000-000000BQE1		
		C4	330	360	XPGEWT-01-0000-000000PE1	XPGEWT-01-0000-000000BPE1		
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-000000HME1	
		C1	300	327			XPGEWT-01-0000-000000HLE1	
DV	6000 K	C5	340	371	XPGEWT-01-0000-000000QDV	XPGEWT-01-0000-000000BQDV		
		C4	330	360	XPGEWT-01-0000-000000PDV	XPGEWT-01-0000-000000BPDV		
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-000000HMDV	
		C1	300	327			XPGEWT-01-0000-000000HLDV	
50	6000 K	C5	340	371	XPGEWT-01-0000-000000Q50	XPGEWT-01-0000-000000BQ50		
		C4	330	360	XPGEWT-01-0000-000000P50	XPGEWT-01-0000-000000BP50		
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-000000HM50	
		C1	300	327			XPGEWT-01-0000-000000HL50	

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
2E	5700 K	C5	340	371		XPGEWT-01-0000-00000BQ2E		
		C4	330	360		XPGEWT-01-0000-00000BP2E		
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-00000HM2E	
		C1	300	327			XPGEWT-01-0000-00000HL2E	
		B5	290	316				
		B4	280	305				XPGEWT-01-0000-00000UJ2E
		B3	270	294				XPGEWT-01-0000-00000UH2E
E2	5700 K	C5	340	371	XPGEWT-01-0000-000000QE2	XPGEWT-01-0000-00000BQE2		
		C4	330	360	XPGEWT-01-0000-000000PE2	XPGEWT-01-0000-00000BPE2		
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-00000HME2	
		C1	300	327			XPGEWT-01-0000-00000HLE2	
		B5	290	316				
		B4	280	305				XPGEWT-01-0000-00000UJE2
		B3	270	294				XPGEWT-01-0000-00000UHE2

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25 °C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
3E	5000 K	C5	340	371		XPGEWT-01-0000-00000BQ3E		
		C4	330	360		XPGEWT-01-0000-00000BP3E		
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-00000HM3E	
		C1	300	327			XPGEWT-01-0000-00000HL3E	
		B5	290	316				
		B4	280	305				XPGEWT-01-0000-00000UJ3E
		B3	270	294				XPGEWT-01-0000-00000UH3E
E3	5000 K	C5	340	371	XPGEWT-01-0000-000000QE3	XPGEWT-01-0000-00000BQE3		
		C4	330	360	XPGEWT-01-0000-000000PE3	XPGEWT-01-0000-00000BPE3		
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-00000HME3	
		C1	300	327			XPGEWT-01-0000-00000HLE3	
		B5	290	316				
		B4	280	305				XPGEWT-01-0000-00000UJE3
		B3	270	294				XPGEWT-01-0000-00000UHE3

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
F4	4750 K	C5	340	371		XPGEWT-01-0000-00000BQF4		
		C4	330	360	XPGEWT-01-0000-000000PF4	XPGEWT-01-0000-00000BPF4		
		C3	320	349	XPGEWT-01-0000-000000NF4			
		C2	310	338			XPGEWT-01-0000-00000HMF4	
		C1	300	327			XPGEWT-01-0000-00000HLF4	
		B5	290	316				
		B4	280	305				
		B3	270	294				XPGEWT-01-0000-00000UHF4
		B2	260	284				XPGEWT-01-0000-00000UGF4
4E	4500K	D1	360	382		XPGEWT-01-0000-00000BR4E		
		C5	340	371		XPGEWT-01-0000-00000BQ4E		
		C4	330	360				
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-00000HM4E	
		C1	300	327			XPGEWT-01-0000-00000HL4E	
		B5	290	316				
		B4	280	305				
		B3	270	294				XPGEWT-01-0000-00000UH4E
		B2	260	284				XPGEWT-01-0000-00000UG4E

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
E4	4500 K	D1	360	382		XPGEWT-01-0000-00000BRE4		
		C5	340	371		XPGEWT-01-0000-00000BQE4		
		C4	330	360	XPGEWT-01-0000-000000PE4			
		C3	320	349	XPGEWT-01-0000-000000NE4			
		C2	310	338			XPGEWT-01-0000-00000HME4	
		C1	300	327			XPGEWT-01-0000-00000HLE4	
		B5	290	316				
		B4	280	305				
		B3	270	294				XPGEWT-01-0000-00000UHE4
		B2	260	284				XPGEWT-01-0000-00000UGE4
F5	4200 K	C5	340	371		XPGEWT-01-0000-00000BQF5		
		C4	330	360	XPGEWT-01-0000-000000PF5	XPGEWT-01-0000-00000BPF5		
		C3	320	349	XPGEWT-01-0000-000000NF5			
		C2	310	338			XPGEWT-01-0000-00000HMF5	
		C1	300	327			XPGEWT-01-0000-00000HLF5	
		B5	290	316				
		B4	280	305				
		B3	270	294				XPGEWT-01-0000-00000UHF5
		B2	260	284				XPGEWT-01-0000-00000UGF5

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
5E	4000 K	C5	340	371		XPGEWT-01-0000-00000BQ5E		
		C4	330	360		XPGEWT-01-0000-00000BP5E		
		C3	320	349				
		C2	310	338			XPGEWT-01-0000-00000HM5E	
		C1	300	327			XPGEWT-01-0000-00000HL5E	
		B5	290	316				
		B4	280	305				
		B3	270	294				XPGEWT-01-0000-00000UH5E
		B2	260	284				XPGEWT-01-0000-00000UG5E
E5	4000 K	C5	340	371		XPGEWT-01-0000-00000BQE5		
		C4	330	360	XPGEWT-01-0000-000000PE5	XPGEWT-01-0000-00000BPE5		
		C3	320	349	XPGEWT-01-0000-000000NE5			
		C2	310	338			XPGEWT-01-0000-00000HME5	
		C1	300	327			XPGEWT-01-0000-00000HLE5	
		B5	290	316				
		B4	280	305				
		B3	270	294				XPGEWT-01-0000-00000UHE5
		B2	260	284				XPGEWT-01-0000-00000UGE5

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
F6	3700 K	C4	330	360	XPGEWT-01-0000-000000PF6	XPGEWT-01-0000-000000BPF6		
		C3	320	349	XPGEWT-01-0000-000000NF6	XPGEWT-01-0000-000000BNF6		
		C2	310	338				
		C1	300	327			XPGEWT-01-0000-000000HLF6	
		B5	290	316			XPGEWT-01-0000-000000HKF6	
		B4	280	305				
		B3	270	294				
		B2	260	284				XPGEWT-01-0000-000000UGF6
		B1	250	273				XPGEWT-01-0000-000000UFF6
6E	3500 K	C4	330	360		XPGEWT-01-0000-000000BP6E		
		C3	320	349		XPGEWT-01-0000-000000BN6E		
		C2	310	338				
		C1	300	327			XPGEWT-01-0000-000000HL6E	
		B5	290	316			XPGEWT-01-0000-000000HK6E	
		B4	280	305				
		B3	270	294				
		B2	260	284				XPGEWT-01-0000-000000UG6E
		B1	250	273				XPGEWT-01-0000-000000UF6E
6G	3500 K	B2	260	284				XPGEWT-01-0000-000000UG6G
		B1	250	273				XPGEWT-01-0000-000000UF6G

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
E6	3500 K	C4	330	360	XPGEWT-01-0000-000000PE6	XPGEWT-01-0000-000000BPE6		
		C3	320	349	XPGEWT-01-0000-000000NE6	XPGEWT-01-0000-000000BNE6		
		C2	310	338				
		C1	300	327			XPGEWT-01-0000-000000HLE6	
		B5	290	316			XPGEWT-01-0000-000000HKE6	
		B4	280	305				
		B3	270	294				
		B2	260	284				XPGEWT-01-0000-000000UGE6
		B1	250	273				XPGEWT-01-0000-000000UFE6
F7	3200K	C4	330	360	XPGEWT-01-0000-000000PF7	XPGEWT-01-0000-000000BPF7		
		C3	320	349	XPGEWT-01-0000-000000NF7	XPGEWT-01-0000-000000BNF7		
		C2	310	338	XPGEWT-01-0000-000000MF7			
		C1	300	327				
		B5	290	316			XPGEWT-01-0000-000000HKF7	
		B4	280	305			XPGEWT-01-0000-000000HJF7	
		B3	270	294				
		B2	260	284				
		B1	250	273				XPGEWT-01-0000-000000UFF7
		A5	240	262				XPGEWT-01-0000-000000UEF7

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
7E	3000 K	C4	330	360		XPGEWT-01-0000-00000BP7E		
		C3	320	349		XPGEWT-01-0000-00000BN7E		
		C2	310	338				
		C1	300	327				
		B5	290	316			XPGEWT-01-0000-00000HK7E	
		B4	280	305			XPGEWT-01-0000-00000HJ7E	
		B3	270	294				
		B2	260	284				
		B1	250	273				XPGEWT-01-0000-00000UF7E
		A5	240	262				XPGEWT-01-0000-00000UE7E
7G	3000 K	B1	250	273				XPGEWT-01-0000-00000UF7G
		A5	240	262				XPGEWT-01-0000-00000UE7G
E7	3000 K	C4	330	360	XPGEWT-01-0000-000000PE7	XPGEWT-01-0000-00000BPE7		
		C3	320	349	XPGEWT-01-0000-000000NE7	XPGEWT-01-0000-00000BNE7		
		C2	310	338	XPGEWT-01-0000-000000ME7			
		C1	300	327				
		B5	290	316			XPGEWT-01-0000-00000HKE7	
		B4	280	305			XPGEWT-01-0000-00000HJE7	
		B3	270	294				
		B2	260	284				
		B1	250	273				XPGEWT-01-0000-00000UFE7
		A5	240	262				XPGEWT-01-0000-00000UEE7

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)

Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
F8	2850 K	C2	310	338	XPGEWT-01-0000-00000MF8	XPGEWT-01-0000-00000BMF8		
		C1	300	327	XPGEWT-01-0000-00000LF8	XPGEWT-01-0000-00000BLF8		
		B5	290	316	XPGEWT-01-0000-00000KF8			
		B4	280	305			XPGEWT-01-0000-00000HJF8	
		B3	270	294			XPGEWT-01-0000-00000HHF8	
		B2	260	284			XPGEWT-01-0000-00000HGF8	
		B1	250	273				
		A5	240	262				
		A4	230	251				XPGEWT-01-0000-00000UDF8
		A3	220	240				XPGEWT-01-0000-00000UCF8
8E	2700 K	C2	310	338		XPGEWT-01-0000-00000BM8E		
		C1	300	327		XPGEWT-01-0000-00000BL8E		
		B5	290	316				
		B4	280	305			XPGEWT-01-0000-00000HJ8E	
		B3	270	294			XPGEWT-01-0000-00000HH8E	
		B2	260	284			XPGEWT-01-0000-00000HG8E	
		B1	250	273				
		A5	240	262				
		A4	230	251				XPGEWT-01-0000-00000UD8E
		A3	220	240				XPGEWT-01-0000-00000UC8E
8G	2700 K	A4	230	251				XPGEWT-01-0000-00000UD8G
		A3	220	240				XPGEWT-01-0000-00000UC8G

Notes

- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

FLUX CHARACTERISTICS - $T_j = 85^\circ\text{C}$ (CONTINUED)


Chromaticity		Minimum Luminous Flux (lm) @ 700 mA			Order Codes			
Kit	CCT	Code	Flux (lm) @ 85 °C	Flux (lm) @ 25 °C*	70 CRI Typical	70 CRI Minimum	80 CRI Minimum	90 CRI Minimum
E8	2700K	C2	310	338	XPGEWT-01-0000-000000ME8	XPGEWT-01-0000-000000BME8		
		C1	300	327	XPGEWT-01-0000-000000LE8	XPGEWT-01-0000-000000BLE8		
		B5	290	316	XPGEWT-01-0000-000000KE8			
		B4	280	305			XPGEWT-01-0000-000000HJE8	
		B3	270	294			XPGEWT-01-0000-000000HHE8	
		B2	260	284			XPGEWT-01-0000-000000HGE8	
		B1	250	273				
		A5	240	262				
		A4	230	251				XPGEWT-01-0000-000000UDE8
		A3	220	240				XPGEWT-01-0000-000000UCE8
EA	2200 K	B3	270	294	XPGEWT-01-0000-000000HEA	XPGEWT-01-0000-000000BHEA		
		B2	260	284	XPGEWT-01-0000-000000GEA	XPGEWT-01-0000-000000BGEA		
		B1	250	273	XPGEWT-01-0000-000000FEA	XPGEWT-01-0000-000000BFEA		
AE	2200 K	B3	270	294		XPGEWT-01-0000-000000BHAE		
		B2	260	284		XPGEWT-01-0000-000000BGAE		
		B1	250	273		XPGEWT-01-0000-000000BFAE		
BE	1800 K	A4	230	251	XPGEWT-01-0000-000000DBE	XPGEWT-01-0000-000000BDBE		
		A3	220	240	XPGEWT-01-0000-000000CBE	XPGEWT-01-0000-000000BCBE		

Notes


- Cree LED maintains a tolerance of $\pm 7\%$ on flux and power measurements, ± 0.005 on chromaticity (CCx, CCy) measurements and a tolerance of ± 2 on CRI measurements. See the Measurements section (page 31).
- XLamp XP-G4 LED order codes specify only a minimum flux bin and not a maximum. Cree LED may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity bin restrictions specified by the order code.
- * Flux values @ 25°C are calculated and for reference only.

PRELIMINARY

RELATIVE SPECTRAL POWER DISTRIBUTION




RELATIVE FLUX VS. JUNCTION TEMPERATURE - $I_f = 700$ mA




PRELIMINARY

ELECTRICAL CHARACTERISTICS - $T_j = 85^\circ\text{C}$





RELATIVE LUMINOUS FLUX VS. CURRENT - $T_j = 85^\circ\text{C}$



PRELIMINARY


RELATIVE CHROMATICITY VS. CURRENT AND TEMPERATURE

Data shown is representative of typical XP-G4 70 CRI performance.




PRELIMINARY

TYPICAL SPATIAL DISTRIBUTION



THERMAL DESIGN

The maximum forward current is determined by the thermal resistance between the LED junction and ambient. It is crucial for the end product to be designed in a manner that minimizes the thermal resistance from the solder point to ambient in order to optimize lamp life and optical characteristics.



PRELIMINARY

PERFORMANCE GROUPS - LUMINOUS FLUX

XLamp XP-G4 LEDs are tested for luminous flux and placed into one of the following luminous-flux groups.

Group Code	Minimum Luminous Flux (lm) @ 700 mA	Maximum Luminous Flux (lm) @ 700 mA
A1	200	210
A2	210	220
A3	220	230
A4	230	240
A5	240	250
B1	250	260
B2	260	270
B3	270	280
B4	280	290
B5	290	300
C1	300	310
C2	310	320
C3	320	330
C4	330	340
C5	340	350
D1	350	360
D2	360	370
D3	370	380
D4	380	390
D5	390	400

PRELIMINARY

PERFORMANCE GROUPS - CHROMATICITY

Region	x	y	Region	x	y	Region	x	y	Region	x	y
0A	0.2950	0.2970	0B	0.2920	0.3060	0C	0.2984	0.3133	0D	0.2984	0.3133
	0.2920	0.3060		0.2895	0.3135		0.2962	0.3220		0.3048	0.3207
	0.2984	0.3133		0.2962	0.3220		0.3028	0.3304		0.3068	0.3113
	0.3009	0.3042		0.2984	0.3133		0.3048	0.3207		0.3009	0.3042
0R	0.2980	0.2880	0S	0.2895	0.3135	0T	0.2962	0.3220	0U	0.3037	0.2937
	0.2950	0.2970		0.2870	0.3210		0.2937	0.3312		0.3009	0.3042
	0.3009	0.3042		0.2937	0.3312		0.3005	0.3415		0.3068	0.3113
	0.3037	0.2937		0.2962	0.3220		0.3028	0.3304		0.3093	0.2993
1A	0.3048	0.3207	1B	0.3028	0.3304	1C	0.3115	0.3391	1D	0.3130	0.3290
	0.3130	0.3290		0.3115	0.3391		0.3205	0.3481		0.3213	0.3373
	0.3144	0.3186		0.3130	0.3290		0.3213	0.3373		0.3221	0.3261
	0.3068	0.3113		0.3048	0.3207		0.3130	0.3290		0.3144	0.3186
1R	0.3068	0.3113	1S	0.3005	0.3415	1T	0.3099	0.3509	1U	0.3144	0.3186
	0.3144	0.3186		0.3099	0.3509		0.3196	0.3602		0.3221	0.3261
	0.3161	0.3059		0.3115	0.3391		0.3205	0.3481		0.3231	0.3120
	0.3093	0.2993		0.3028	0.3304		0.3115	0.3391		0.3161	0.3059
2A	0.3215	0.3350	2B	0.3207	0.3462	2C	0.3290	0.3538	2D	0.3290	0.3417
	0.3290	0.3417		0.3290	0.3538		0.3376	0.3616		0.3371	0.3490
	0.3290	0.3300		0.3290	0.3417		0.3371	0.3490		0.3366	0.3369
	0.3222	0.3243		0.3215	0.3350		0.3290	0.3417		0.3290	0.3300
2R	0.3222	0.3243	2S	0.3196	0.3602	2T	0.3290	0.3690	2U	0.3290	0.3300
	0.3290	0.3300		0.3290	0.3690		0.3381	0.3762		0.3366	0.3369
	0.3290	0.3180		0.3290	0.3538		0.3376	0.3616		0.3361	0.3245
	0.3231	0.3120		0.3207	0.3462		0.3290	0.3538		0.3290	0.3180
3A	0.3371	0.3490	3B	0.3376	0.3616	3C	0.3463	0.3687	3D	0.3451	0.3554
	0.3451	0.3554		0.3463	0.3687		0.3551	0.3760		0.3533	0.3620
	0.3440	0.3427		0.3451	0.3554		0.3533	0.3620		0.3515	0.3487
	0.3366	0.3369		0.3371	0.3490		0.3451	0.3554		0.3440	0.3427
4A	0.3530	0.3597	4B	0.3548	0.3736	4C	0.3641	0.3804	4D	0.3615	0.3659
	0.3615	0.3659		0.3641	0.3804		0.3736	0.3874		0.3702	0.3722
	0.3590	0.3521		0.3615	0.3659		0.3702	0.3722		0.3670	0.3578
	0.3512	0.3465		0.3530	0.3597		0.3615	0.3659		0.3590	0.3521
5A1	0.3670	0.3578	5A2	0.3686	0.3649	5A3	0.3744	0.3685	5A4	0.3726	0.3612
	0.3686	0.3649		0.3702	0.3722		0.3763	0.3760		0.3744	0.3685
	0.3744	0.3685		0.3763	0.3760		0.3825	0.3798		0.3804	0.3721
	0.3726	0.3612		0.3744	0.3685		0.3804	0.3721		0.3783	0.3646

PRELIMINARY

PERFORMANCE GROUPS - CHROMATICITY (CONTINUED)

Region	x	y	Region	x	y	Region	x	y	Region	x	y
5B1	0.3702	0.3722	5B2	0.3719	0.3797	5B3	0.3782	0.3837	5B4	0.3763	0.3760
	0.3719	0.3797		0.3736	0.3874		0.3802	0.3916		0.3782	0.3837
	0.3782	0.3837		0.3802	0.3916		0.3869	0.3958		0.3847	0.3877
	0.3763	0.3760		0.3782	0.3837		0.3847	0.3877		0.3825	0.3798
5C1	0.3825	0.3798	5C2	0.3847	0.3877	5C3	0.3912	0.3917	5C4	0.3887	0.3836
	0.3847	0.3877		0.3869	0.3958		0.3937	0.4001		0.3912	0.3917
	0.3912	0.3917		0.3937	0.4001		0.4006	0.4044		0.3978	0.3958
	0.3887	0.3836		0.3912	0.3917		0.3978	0.3958		0.3950	0.3875
5D1	0.3783	0.3646	5D2	0.3804	0.3721	5D3	0.3863	0.3758	5D4	0.3840	0.3681
	0.3804	0.3721		0.3825	0.3798		0.3887	0.3836		0.3863	0.3758
	0.3863	0.3758		0.3887	0.3836		0.3950	0.3875		0.3924	0.3794
	0.3840	0.3681		0.3863	0.3758		0.3924	0.3794		0.3898	0.3716
6A1	0.3889	0.3690	6A2	0.3915	0.3768	6A3	0.3981	0.3800	6A4	0.3953	0.3720
	0.3915	0.3768		0.3941	0.3848		0.4010	0.3882		0.3981	0.3800
	0.3981	0.3800		0.4010	0.3882		0.4080	0.3916		0.4048	0.3832
	0.3953	0.3720		0.3981	0.3800		0.4048	0.3832		0.4017	0.3751
6B1	0.3941	0.3848	6B2	0.3968	0.3930	6B3	0.4040	0.3966	6B4	0.4010	0.3882
	0.3968	0.3930		0.3996	0.4015		0.4071	0.4052		0.4040	0.3966
	0.4040	0.3966		0.4071	0.4052		0.4146	0.4089		0.4113	0.4001
	0.4010	0.3882		0.4040	0.3966		0.4113	0.4001		0.4080	0.3916
6C1	0.4080	0.3916	6C2	0.4113	0.4001	6C3	0.4186	0.4037	6C4	0.4150	0.3950
	0.4113	0.4001		0.4146	0.4089		0.4222	0.4127		0.4186	0.4037
	0.4186	0.4037		0.4222	0.4127		0.4299	0.4165		0.4259	0.4073
	0.4150	0.3950		0.4186	0.4037		0.4259	0.4073		0.4221	0.3984
6D1	0.4017	0.3751	6D2	0.4048	0.3832	6D3	0.4116	0.3865	6D4	0.4082	0.3782
	0.4048	0.3832		0.4080	0.3916		0.4150	0.3950		0.4116	0.3865
	0.4116	0.3865		0.4150	0.3950		0.4221	0.3984		0.4183	0.3898
	0.4082	0.3782		0.4116	0.3865		0.4183	0.3898		0.4147	0.3814
7A1	0.4147	0.3814	7A2	0.4183	0.3898	7A3	0.4242	0.3919	7A4	0.4203	0.3833
	0.4183	0.3898		0.4221	0.3984		0.4281	0.4006		0.4242	0.3919
	0.4242	0.3919		0.4281	0.4006		0.4342	0.4028		0.4300	0.3939
	0.4203	0.3833		0.4242	0.3919		0.4300	0.3939		0.4259	0.3853
7B1	0.4221	0.3984	7B2	0.4259	0.4073	7B3	0.4322	0.4096	7B4	0.4281	0.4006
	0.4259	0.4073		0.4299	0.4165		0.4364	0.4188		0.4322	0.4096
	0.4322	0.4096		0.4364	0.4188		0.4430	0.4212		0.4385	0.4119
	0.4281	0.4006		0.4322	0.4096		0.4385	0.4119		0.4342	0.4028

PRELIMINARY

PERFORMANCE GROUPS - CHROMATICITY (CONTINUED)

Region	x	y	Region	x	y	Region	x	y	Region	x	y
7C1	0.4342	0.4028	7C2	0.4385	0.4119	7C3	0.4449	0.4141	7C4	0.4403	0.4049
	0.4385	0.4119		0.4430	0.4212		0.4496	0.4236		0.4449	0.4141
	0.4449	0.4141		0.4496	0.4236		0.4562	0.4260		0.4513	0.4164
	0.4403	0.4049		0.4449	0.4141		0.4513	0.4164		0.4465	0.4071
7D1	0.4259	0.3853	7D2	0.4300	0.3939	7D3	0.4359	0.3960	7D4	0.4316	0.3873
	0.4300	0.3939		0.4342	0.4028		0.4403	0.4049		0.4359	0.3960
	0.4359	0.3960		0.4403	0.4049		0.4465	0.4071		0.4418	0.3981
	0.4316	0.3873		0.4359	0.3960		0.4418	0.3981		0.4373	0.3893
8A1	0.4373	0.3893	8A2	0.4418	0.3981	8A3	0.4475	0.3994	8A4	0.4428	0.3906
	0.4418	0.3981		0.4465	0.4071		0.4523	0.4085		0.4475	0.3994
	0.4475	0.3994		0.4523	0.4085		0.4582	0.4099		0.4532	0.4008
	0.4428	0.3906		0.4475	0.3994		0.4532	0.4008		0.4483	0.3919
8B1	0.4465	0.4071	8B2	0.4513	0.4164	8B3	0.4573	0.4178	8B4	0.4523	0.4085
	0.4513	0.4164		0.4562	0.4260		0.4624	0.4274		0.4573	0.4178
	0.4573	0.4178		0.4624	0.4274		0.4687	0.4289		0.4634	0.4193
	0.4523	0.4085		0.4573	0.4178		0.4634	0.4193		0.4582	0.4099
8C1	0.4582	0.4099	8C2	0.4634	0.4193	8C3	0.4695	0.4207	8C4	0.4641	0.4112
	0.4634	0.4193		0.4687	0.4289		0.4750	0.4304		0.4695	0.4207
	0.4695	0.4207		0.4750	0.4304		0.4813	0.4319		0.4756	0.4221
	0.4641	0.4112		0.4695	0.4207		0.4756	0.4221		0.4700	0.4126
8D1	0.4483	0.3919	8D2	0.4532	0.4008	8D3	0.4589	0.4021	8D4	0.4538	0.3931
	0.4532	0.4008		0.4582	0.4099		0.4641	0.4112		0.4589	0.4021
	0.4589	0.4021		0.4641	0.4112		0.4700	0.4126		0.4646	0.4034
	0.4538	0.3931		0.4589	0.4021		0.4646	0.4034		0.4593	0.3944
AA1	0.4822	0.3973	AA2	0.4884	0.4067	AA3	0.4942	0.4066	AA4	0.4879	0.3972
	0.4884	0.4067		0.4946	0.4162		0.5006	0.4160		0.4942	0.4066
	0.4942	0.4066		0.5006	0.4160		0.5066	0.4158		0.5001	0.4064
	0.4879	0.3972		0.4942	0.4066		0.5001	0.4064		0.4936	0.3970
AB1	0.4946	0.4162	AB2	0.5008	0.4256	AB3	0.5069	0.4254	AB4	0.5006	0.4160
	0.5008	0.4256		0.5070	0.4350		0.5133	0.4348		0.5069	0.4254
	0.5069	0.4254		0.5133	0.4348		0.5196	0.4346		0.5131	0.4252
	0.5006	0.4160		0.5069	0.4254		0.5131	0.4252		0.5066	0.4158
AC1	0.5066	0.4158	AC2	0.5131	0.4252	AC3	0.5192	0.4250	AC4	0.5126	0.4156
	0.5131	0.4252		0.5196	0.4346		0.5258	0.4343		0.5192	0.4250
	0.5192	0.4250		0.5258	0.4343		0.5321	0.4341		0.5253	0.4248
	0.5126	0.4156		0.5192	0.4250		0.5253	0.4248		0.5186	0.4154

PRELIMINARY

PERFORMANCE GROUPS - CHROMATICITY (CONTINUED)

Region	x	y	Region	x	y	Region	x	y	Region	x	y
AD1	0.4936	0.3970	AD2	0.5001	0.4064	AD3	0.5059	0.4062	AD4	0.4993	0.3969
	0.5001	0.4064		0.5066	0.4158		0.5126	0.4156		0.5059	0.4062
	0.5059	0.4062		0.5126	0.4156		0.5186	0.4154		0.5118	0.4061
	0.4993	0.3969		0.5059	0.4062		0.5118	0.4061		0.5050	0.3967


XLamp XP-G4 LEDs are tested for chromaticity and placed into one of the regions defined by the following bounding coordinates.

EasyWhite Color Temperatures – 3-Step Ellipse						
Bin Code	CCT	Center Point		Major Axis	Minor Axis	Rotation Angle (°)
		x	y	a	b	
6G	3500 K	0.4073	0.3917	0.00927	0.00414	54.0
7G	3000 K	0.4338	0.4030	0.00834	0.00408	53.2
8G	2700 K	0.4577	0.4099	0.00834	0.00420	48.5

EasyWhite Color Temperatures – 5-Step Ellipse						
Bin Code	CCT	Center Point		Major Axis	Minor Axis	Rotation Angle (°)
		x	y	a	b	
2E	5700 K	0.3287	0.3417	0.01230	0.00600	72.0
3E	5000 K	0.3447	0.3553	0.01400	0.00520	65.0
4E	4500 K	0.3611	0.3658	0.01420	0.00550	61.5
5E	4000 K	0.3818	0.3797	0.01565	0.00670	53.7
6E	3500 K	0.4073	0.3917	0.01545	0.00690	54.0
7E	3000 K	0.4338	0.4030	0.01390	0.00680	53.2
8E	2700 K	0.4577	0.4099	0.01350	0.00700	48.5
AE	2200 K	0.5066	0.4158	0.01633	0.00800	45.5
BE	1800 K	0.5492	0.4082	0.00683	0.01546	40.0



PRELIMINARY

CREE LED'S STANDARD COOL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS




PRELIMINARY

CREE LED'S STANDARD WARM AND NEUTRAL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS




PRELIMINARY

CREE LED'S STANDARD WARM AND NEUTRAL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS - CONTINUED



CREE LED'S EASYWHITE® WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS



PRELIMINARY

CREE LED'S STANDARD CHROMATICITY KITS



The following table provides the chromaticity bins associated with chromaticity kits.

Color	CCT	Kit	Chromaticity Bins
Cool White	7000 K	DT	0A, 0B, 0C, 0D, 0R, 0S, 0T, 0U, 1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U
	>6500 K	E0	0A, 0B, 0C, 0D
	6500 K	E1	1A, 1B, 1C, 1D
	6000 K	DV	1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U, 2A, 2B, 2C, 2D, 2R, 2S, 2T, 2U
	6200 K	50	1A, 1B, 1C, 1D, 2A, 2B, 2C, 2D
	5700 K	E2	2A, 2B, 2C, 2D
	5700 K	2E	57E
Neutral White	5000 K	3E	50E
	5000 K	E3	3A, 3B, 3C, 3D
	4750 K	F4	3C, 3D, 4A, 4B
	4500 K	4E	45E
	4500 K	E4	4A, 4B, 4C, 4D
	4250 K	F5	4C, 4D, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4
	4000 K	5E	40E
	4000 K	E5	5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4
Warm White	3750 K	F6	5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4
	3500 K	6E	35E, 35G
	3500 K	6G	35G
	3500 K	E6	6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4, 6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4
	3250 K	F7	6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4, 7A1, 7A2, 7A3, 7A4, 7B1, 7B2, 7B3, 7B4
	3000 K	7E	30E, 30G
	3000 K	7G	30G
	3000 K	E7	7A1, 7A2, 7A3, 7A4, 7B1, 7B2, 7B3, 7B4, 7C1, 7C2, 7C3, 7C4, 7D1, 7D2, 7D3, 7D4
	2850 K	F8	7C1, 7C2, 7C3, 7C4, 7D1, 7D2, 7D3, 7D4, 8A1, 8A2, 8A3, 8A4, 8B1, 8B2, 8B3, 8B4
	2700 K	8E	27E, 27G
	2700 K	8G	27G
	2700 K	E8	8A1, 8A2, 8A3, 8A4, 8B1, 8B2, 8B3, 8B4, 8C1, 8C2, 8C3, 8C4, 8D1, 8D2, 8D3, 8D4
	2200 K	EA	AA1, AA2, AA3, AA4, AB1, AB2, AB3, AB4, AC1, AC2, AC3, AC4, AD1, AD2, AD3, AD4
	2200 K	AE	22E
	1800 K	BE	18E

PRELIMINARY

BIN AND ORDER CODE FORMATS

XP-G4 bin codes and order codes are configured in the following manner:




PRELIMINARY

REFLOW SOLDERING CHARACTERISTICS

In testing, Cree LED has found XLamp XP-G4 LEDs to be compatible with JEDEC J-STD-020C, with the exception of the peak temperature requirements listed in the table below. As a general guideline, Cree LED recommends that users follow the recommended soldering profile provided by the manufacturer of the solder paste used, and therefore it is the lamp or luminaire manufacturer's responsibility to determine applicable soldering requirements.

Note that this general guideline may not apply to all PCB designs and configurations of reflow soldering equipment.



Profile Feature	Lead-Free Solder
Average Ramp-Up Rate ($T_{s_{max}}$ to T_p)	1.2 °C/second
Preheat: Temperature Min ($T_{s_{min}}$)	120 °C
Preheat: Temperature Max ($T_{s_{max}}$)	170 °C
Preheat: Time ($t_{s_{min}}$ to $t_{s_{max}}$)	65-150 seconds
Time Maintained Above: Temperature (T_l)	217 °C
Time Maintained Above: Time (t_l)	45-90 seconds
Peak/Classification Temperature (T_p)	235 - 245 °C
Time Within 5 °C of Actual Peak Temperature (t_p)	20-40 seconds
Ramp-Down Rate	1 - 6 °C/second
Time 25 °C to Peak Temperature	4 minutes max.

Note: All temperatures refer to topside of the package, measured on the package body surface.

PRELIMINARY

NOTES

Measurements

The luminous flux, radiant power, chromaticity, forward voltage and CRI measurements in this document are binning specifications only and solely represent product measurements as of the date of shipment. These measurements will change over time based on a number of factors that are not within Cree LED's control and are not intended or provided as operational specifications for the products. Calculated values are provided for informational purposes only and are not intended or provided as specifications.

Pre-Release Qualification Testing

Please read the [LED Reliability Overview](#) for details of the qualification process Cree LED applies to ensure long-term reliability for XLamp LEDs and details of Cree LED's pre-release qualification testing for XLamp LEDs. Cree LED did not perform Room Temperature Operating Life (RTOL) testing on the XP-G4 LED.

Lumen Maintenance

Cree LED now uses standardized IES LM-80-08 and TM-21-11 methods for collecting long-term data and extrapolating LED lumen maintenance. For information on the specific LM-80 data sets available for this LED, refer to the public [LM-80 results document](#).

Please read the [Long-Term Lumen Maintenance application note](#) for more details on Cree LED's lumen maintenance testing and forecasting. Please read the [Thermal Management application note](#) for details on how thermal design, ambient temperature, and drive current affect the LED junction temperature.

Moisture Sensitivity

Cree LED recommends keeping XLamp LEDs in the provided, resealable moisture-barrier packaging (MBP) until immediately prior to soldering. Unopened MBPs that contain XLamp LEDs do not need special storage for moisture sensitivity.

Once the MBP is opened, XLamp XP-G4 LEDs may be stored as MSL 1 per JEDEC J-STD-033, meaning they have unlimited floor life in conditions of $\leq 30^{\circ}\text{C}/85\%$ relative humidity (RH). Regardless of the storage condition, Cree LED recommends sealing any unsoldered LEDs in the original MBP.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree LED representative or from the [Product Ecology](#) section of the Cree LED website.

REACH Compliance

REACH substances of very high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Cree LED representative to insure you get the most up-to-date REACH Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

PRELIMINARY

NOTES - CONTINUED



Vision Advisory

WARNING: Do not look at an exposed lamp in operation. Eye injury can result. For more information about LEDs and eye safety, please refer to the [LED Eye Safety application note](#).

PRELIMINARY**MECHANICAL DIMENSIONS ($T_A = 25\text{ }^{\circ}\text{C}$)**

Thermal vias, if present, are not shown on these drawings.


All measurements are $\pm 0.13\text{ mm}$ unless otherwise indicated.




PRELIMINARY

MECHANICAL DIMENSIONS ($T_A = 25\text{ }^{\circ}\text{C}$) - CONTINUED

All measurements are $\pm 0.13\text{ mm}$ unless otherwise indicated.



Recommended PCB Footprint



Recommended Stencil Openings*

Notes:

- Cree LED recommends using thermal pad kickouts to maximize component thermal performance.
- Cree LED recommends using white solder mask material to minimize system optical loss.
- * This stencil has been tested and optimized for the avoidance of voiding when using ALPHA® LUMET® P30 Maxrel solder paste. For other solder pastes, a "window pane" design for the thermal pad stencil may result in a lower voiding percentage. Contact your local Cree LED Field Applications Engineer for consultation regarding your specific application.


PRELIMINARY

TAPE AND REEL

All Cree LED carrier tapes conform to EIA-481D, Automated Component Handling Systems Standard.

All dimensions in mm.



All measurements are ± 0.15 mm unless otherwise indicated.



Item	Ao	Bo	Ko	Po	P1	P2	T	E	F	Do	D1	W	R
Dim.	3.70	3.70	2.40	4.00	8.00	2.00	0.30	1.75	5.50	1.55	1.50	12.00	5°

PRELIMINARY


TAPE AND REEL - CONTINUED



PRELIMINARY


PACKAGING

Unpackaged Reel



Label with Cree LED Bin Code, Quantity, Reel ID


Packaged Reel



Label with Cree LED Order Code, Quantity, Reel ID, PO#

Label with Cree LED Bin Code, Quantity, Reel ID

Boxed Reel



Label with Cree LED Order Code, Quantity, Reel ID, PO#

Label with Cree LED Bin Code, Quantity, Reel ID

Patent Label (on bottom of box)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cree LED:

[XPGWWT-01-0000-000000MF8](#) [XPGWWT-01-0000-000000PF4](#) [XPGWWT-01-0000-000000BNE7](#) [XPGWWT-01-0000-000000BPE1](#) [XPGWWT-01-0000-000000BQ5E](#) [XPGWWT-01-0000-000000HN2E](#) [XPGWWT-01-0000-000000UF6E](#) [XPGWWT-01-0000-000000UH3E](#) [XPGWWT-02-0000-000000HJE7](#) [XPGWWT-02-0000-000000HLE7](#) [XPGWWT-02-0000-000000HLF6](#) [XPGWWT-02-0000-000000UDE8](#) [XPGWWT-02-0000-000000UG6E](#) [XPGWWT-02-0000-000000UHE5](#) [XPGWWT-02-0000-000000UHF5](#) [XPGWWT-01-0000-000000BHEA](#) [XPGWWT-01-0000-000000BN8E](#) [XPGWWT-01-0000-000000BNF6](#) [XPGWWT-01-0000-000000BRDV](#) [XPGWWT-01-0000-000000BRF5](#) [XPGWWT-01-0000-000000HME2](#) [XPGWWT-01-0000-000000HME6](#) [XPGWWT-01-0000-000000HN50](#) [XPGWWT-01-0000-000000UGF5](#) [XPGWWT-01-0000-000000UHE3](#) [XPGWWT-01-0000-000000UJE2](#) [XPGWWT-02-0000-000000HL7E](#) [XPGWWT-01-0000-000000EBE](#) [XPGWWT-01-0000-000000HEA](#) [XPGWWT-01-0000-000000QE4](#) [XPGWWT-01-0000-000000BM8E](#) [XPGWWT-01-0000-000000BRF4](#) [XPGWWT-01-0000-000000HKF7](#) [XPGWWT-01-0000-000000HLE4](#) [XPGWWT-01-0000-000000HLE5](#) [XPGWWT-01-0000-000000HME0](#) [XPGWWT-01-0000-000000HME1](#) [XPGWWT-01-0000-000000HNDT](#) [XPGWWT-01-0000-000000UG6G](#) [XPGWWT-02-0000-000000HKE7](#) [XPGWWT-02-0000-000000HKE8](#) [XPGWWT-02-0000-000000UF7G](#) [XPGWWT-01-0000-000000QF4](#) [XPGWWT-01-0000-000000RE1](#) [XPGWWT-01-0000-000000BJEA](#) [XPGWWT-01-0000-000000BNF8](#) [XPGWWT-01-0000-000000BP7E](#) [XPGWWT-01-0000-000000BQE1](#) [XPGWWT-01-0000-000000BRE2](#) [XPGWWT-01-0000-000000HLE0](#) [XPGWWT-01-0000-000000HN3E](#) [XPGWWT-02-0000-000000HKF8](#) [XPGWWT-02-0000-000000UE7E](#) [XPGWWT-02-0000-000000UFF7](#) [XPGWWT-02-0000-000000UH5E](#) [XPGWWT-01-0000-000000CBE](#) [XPGWWT-01-0000-000000LE8](#) [XPGWWT-01-0000-000000NF6](#) [XPGWWT-01-0000-000000QDT](#) [XPGWWT-01-0000-000000QE6](#) [XPGWWT-01-0000-000000RE3](#) [XPGWWT-01-0000-000000BDBE](#) [XPGWWT-01-0000-000000BPE6](#) [XPGWWT-01-0000-000000HK8E](#) [XPGWWT-01-0000-000000HL2E](#) [XPGWWT-01-0000-000000HLF5](#) [XPGWWT-01-0000-000000UCF8](#) [XPGWWT-02-0000-000000UFE7](#) [XPGWWT-01-0000-000000Q50](#) [XPGWWT-01-0000-000000BMF8](#) [XPGWWT-01-0000-000000BR5E](#) [XPGWWT-01-0000-000000BRE1](#) [XPGWWT-01-0000-000000HJ7E](#) [XPGWWT-01-0000-000000HLF4](#) [XPGWWT-01-0000-000000HNE5](#) [XPGWWT-01-0000-000000UFF6](#) [XPGWWT-02-0000-000000UE7G](#) [XPGWWT-01-0000-000000QE1](#) [XPGWWT-01-0000-000000BFAE](#) [XPGWWT-01-0000-000000BQ50](#) [XPGWWT-01-0000-000000HK6E](#) [XPGWWT-01-0000-000000UE7E](#) [XPGWWT-01-0000-000000UFF7](#) [XPGWWT-01-0000-000000UGE6](#) [XPGWWT-02-0000-000000HK7E](#) [XPGWWT-02-0000-000000HME6](#) [XPGWWT-02-0000-000000UGE6](#) [XPGWWT-01-0000-000000GEA](#) [XPGWWT-01-0000-000000RF5](#) [XPGWWT-01-0000-000000BME8](#) [XPGWWT-01-0000-000000BP2E](#) [XPGWWT-01-0000-000000BP3E](#) [XPGWWT-01-0000-000000BPF5](#) [XPGWWT-01-0000-000000BQE6](#) [XPGWWT-01-0000-000000HMDT](#) [XPGWWT-01-0000-000000UDF8](#) [XPGWWT-01-0000-000000UHF4](#) [XPGWWT-01-0000-000000UHF5](#) [XPGWWT-02-0000-000000HKF7](#) [XPGWWT-02-0000-000000HMF6](#)