

# CS4352

# 192 kHz Stereo DAC with 2 Vrms Line Out

### Features


- Multi-bit Delta-Sigma Modulator
- 24-Bit Resolution
- Supports Sample Rates up to 192 kHz
- 106 dB A-wt Dynamic Range
- ♦ -93 dB THD+N
- Integrated Line Driver
- 2 Vrms Output into 5 k $\Omega$  AC Load
- Analog Low-Pass Filter
- Stereo Mutes with Auto-Mute Function
- Low Clock-Jitter Sensitivity
- Low-Latency Digital Filtering
- Popguard<sup>®</sup> Technology for Control of Clicks and Pops
- Single-Ended Outputs
- +3.3 V Core, +9 to 12 V Analog, and +1.5 to 3.3 V Interface Power Supplies
- Low Power Consumption
- 20-pin TSSOP, Lead-Free Assembly

### Description

The CS4352 is a complete stereo digital-to-analog system including digital interpolation, fifth-order multi-bit delta-sigma digital-to-analog conversion, digital de-emphasis, analog filtering, and on-chip 2 Vrms line-level driver. The advantages of this architecture include ideal differential linearity, no distortion mechanisms due to resistor matching errors, no linearity drift over time and temperature, high tolerance to clock jitter, and a minimal set of external components.

The CS4352 is available in a 20-pin TSSOP package in both Commercial grade (-40°C to +85°C) and Automotive grade (-40°C to +105°C). The CDB4352 Customer Demonstration Board is also available for device evaluation and implementation suggestions. Please see "Ordering Information" on page 20 for complete details.

These features are ideal for cost-sensitive, 2-channel audio systems including video game consoles, DVD players, A/V receivers, set-top boxes, digital TVs and DVD Recorders, mini-component systems, and mixing consoles.



CIRRUS LOGIC<sup>®</sup> <u>http://www.cirrus.com</u>



# TABLE OF CONTENTS

1. PIN DESCRIPTIONS	3
2. CHARACTERISTICS AND SPECIFICATIONS	4
RECOMMENDED OPERATING CONDITIONS	4
ABSOLUTE MAXIMUM RATINGS	4
DAC ANALOG CHARACTERISTICS - COMMERCIAL (-CZZ)	5
DAC ANALOG CHARACTERISTICS - AUTOMOTIVE (-DZZ)	6
COMBINED INTERPOLATION & ON-CHIP ANALOG FILTER RESPONSE	7
SWITCHING SPECIFICATIONS - SERIAL AUDIO INTERFACE	
DIGITAL CHARACTERISTICS	
POWER AND THERMAL CHARACTERISTICS	
3. TYPICAL CONNECTION DIAGRAM	
4. APPLICATIONS	
4.6.1 Capacitor Placement	
4.7.1 Power-Up	14
4.7.2 Power-Down	14
4.7.3 Discharge Time	14
5. DIGITAL FILTER RESPONSE PLOTS	
6. PARAMETER DEFINITIONS	
7. PACKAGE DIMENSIONS	19
8. ORDERING INFORMATION	20
9. REVISION HISTORY	20

# LIST OF FIGURES

Figure 1.Serial Input Timing	8
Figure 2. Typical Connection Diagram	10
Figure 3.I <sup>2</sup> S, up to 24-Bit Data	
Figure 4.Right-Justified Data	12
Figure 5.Left-Justified up to 24-Bit Data	12
Figure 6.De-Emphasis Curve	13
Figure 7.Single-Speed Stopband Rejection	16
Figure 8.Single-Speed Transition Band	16
Figure 9.Single-Speed Transition Band (detail)	
Figure 10.Single-Speed Passband Ripple	
Figure 11.Double-Speed Stopband Rejection	
Figure 12.Double-Speed Transition Band	16
Figure 13.Double-Speed Transition Band (detail)	17
Figure 14.Double-Speed Passband Ripple	17
Figure 15.Quad-Speed Stopband Rejection	
Figure 16.Quad-Speed Transition Band	17
Figure 17.Quad-Speed Transition Band (detail)	
Figure 18.Quad-Speed Passband Ripple	17

## LIST OF TABLES

Table 1. CS4352 Auto-Detect	11
Table 2. Single-Speed Mode Standard Frequencies	11
Table 3. Double-Speed Mode Standard Frequencies	11
Table 4. Quad-Speed Mode Standard Frequencies	11
Table 5. Digital Interface Format	12



# **1. PIN DESCRIPTIONS**

SDIN	1	20	VL
SCLK	2	19	AMUTEC
LRCK	3	18	AOUTA
MCLK	4	17	VA_H
VD	5	16	GND
GND	6	15	AOUTB
DIF1	7	14	BMUTEC
DIF0	8	13	VQ
DEM	9	12	VBIAS
RST	10	11	VA

Pin Name	Pin #	Pin Description
SDIN	1	Serial Audio Data Input (Input) - Input for two's complement serial audio data.
SCLK	2	Serial Clock (Input) - Serial clock for the serial audio interface.
LRCK	3	Left / Right Clock ( <i>Input</i> ) - Determines which channel, Left or Right, is currently active on the serial audio data line.
MCLK	4	Master Clock (Input) - Clock source for the delta-sigma modulator and digital filters.
VD	5	Digital Power (Input) - Positive power supply for the digital section.
GND	6 16	Ground (Input) - Ground reference.
DIF0	8	Digital Interface Format (Input) - Defines the required relationship between the Left/Right Clock, Serial
DIF1	7	Clock, and Serial Audio Data.
DEM	9	<b>De-emphasis</b> ( <i>Input</i> ) - Selects the standard 15 $\mu$ s/50 $\mu$ s digital de-emphasis filter response for 44.1 kHz sample rates
RST	10	<b>Reset</b> ( <i>Input</i> ) - Powers down the device and resets all internal registers to their default settings when enabled.
VA	11	Low Voltage Analog Power (Input) - Positive power supply for the analog section.
VBIAS	12	Positive Voltage Reference (Output) - Positive reference voltage for the internal DAC.
VQ	13	Quiescent Voltage (Output) - Filter connection for internal quiescent voltage.
VA_H	17	High Voltage Analog Power (Input) - Positive power supply for the analog section.
VL	20	Serial Audio Interface Power (Input) - Positive power for the serial audio interface
BMUTEC	14	Note Control (Outro). Orated simplificational mode simplifi
AMUTEC	19	<b>Mute Control</b> ( <i>Output</i> ) - Control signal for optional mute circuit.
AOUTB	15	Analog Outputs (Output) - The full-scale analog line output level is specified in the Analog Characteris-
AOUTA	18	tics table.



# 2. CHARACTERISTICS AND SPECIFICATIONS

### **RECOMMENDED OPERATING CONDITIONS**

(GND = 0 V; all voltages with respect to ground.)

Р	Symbol	Min	Тур	Max	Units	
DC Power Supply	V <sub>A_H</sub>	8.40	9	12.6	V	
	Low Voltage Analog power	VA	3.13	3.3	3.47	V
	Digital power	VD	3.13	3.3	3.47	V
	Interface power	VL	1.43	1.5	3.47	V
Ambient Operating Temperation	ure (power applied) -CZZ		-40	-	+85	°C
	-DZZ	I A	-40	-	+105	°C

### **ABSOLUTE MAXIMUM RATINGS**

(GND = 0 V; all voltages with respect to ground.)

Pa	arameters	Symbol	Min	Max	Units
DC Power Supply	High Voltage Analog power	V <sub>A_H</sub>	-0.3	14.0	V
	Low Voltage Analog power			3.63	V
	Digital power	VD	-0.3	3.63	V
	Interface power	VL	-0.3	3.63	V
Input Current, Any Pin Excep	t Supplies	l <sub>in</sub>	-	±10	mA
Digital Input Voltage	V <sub>IN-L</sub>	-0.3	V <sub>L</sub> + 0.4	V	
Ambient Operating Temperati	T <sub>A</sub>	-55	+125	°C	
Storage Temperature	T <sub>stg</sub>	-65	+150	°C	

Operation at or beyond these limits may result in permanent damage to the device. Normal operation is not guaranteed at these extremes.



# **DAC ANALOG CHARACTERISTICS - COMMERCIAL (-CZZ)**

Test conditions (unless otherwise specified):  $T_A = 25$  °C,  $VA_H = 9$  V, VA = 3.3 V, VD = 3.3 V GND = 0 V; VBIAS+ and VQ capacitors as shown in Figure 2 on page 10; input test signal is a 997 Hz sine wave at 0 dBFS; measurement bandwidth 10 Hz to 20 kHz.

Parameter		Symbol	Min	Тур	Max	Unit
All Speed Modes Fs =	- 48, 96, an	d 192 kHz				
Dynamic Range (Note 1) 24-bit	A-Weighted		100	106	-	dB
	unweighted		97	103	-	dB
16-bit	A-Weighted		-	98	-	dB
	unweighted		-	95	-	dB
Total Harmonic Distortion + Noise	(Note 1)		-			
24-bit	0 dB		-	-93	-89	dB
	-20 dB		-	-83	-77	dB
	-60 dB	THD+N	-	-43	-37	dB
16-bit	0 dB		-	-93	-	dB
	-20 dB		-	-75	-	dB
	-60 dB		-	-35	-	dB
Idle Channel Noise / Signal-to-noise ratio	o (A-wt)		-	106	-	dB
Interchannel Isolation	(1 kHz)		-	99	-	dB
Analog Output - All Modes						
Full Scale Output Voltage			1.84	2.00	2.11	Vrms
Common Mode Voltage		V <sub>Q</sub>	-	4	-	Vdc
Max Current draw from an AOUT pin		I <sub>OUTmax</sub>	-	575	-	μΑ
Max Current draw from VQ		I <sub>Qmax</sub>	-	1	-	μΑ
Interchannel Gain Mismatch			-	0.1	-	dB
Gain Drift			-	100	-	ppm/°C
Output Impedance		Z <sub>OUT</sub>	-	50	-	Ω
AC-Load Resistance		RL	5	-	-	kΩ
Load Capacitance		CL	-	-	100	pF

Notes:

1. One-half LSB of triangular PDF dither is added to data.



# **DAC ANALOG CHARACTERISTICS - AUTOMOTIVE (-DZZ)**

Test conditions (unless otherwise specified):  $T_A = -40^{\circ}C$  to 85°C, VA\_H = 9 V, VA = 3.3 V, VD = 3.3 V GND = 0 V; VBIAS+ and VQ capacitors as shown in Figure 2 on page 10; input test signal is a 997 Hz sine wave at 0 dBFS; measurement bandwidth 10 Hz to 20 kHz.

Parameter		Symbol	Min	Тур	Max	Unit
All Speed Modes Fs =	: 48, 96, an	d 192 kHz				
Dynamic Range (Note 2) 24-bit	A-Weighted		96	106	-	dB
	unweighted		93	103	-	dB
16-bit	A-Weighted		-	98	-	dB
	unweighted		-	95	-	dB
Total Harmonic Distortion + Noise	(Note 2)		-			
24-bit	0 dB		-	-93	-89	dB
	-20 dB		-	-83	-73	dB
	-60 dB	THD+N	-	-43	-33	dB
16-bit	0 dB		-	-93	-	dB
	-20 dB		-	-75	-	dB
	-60 dB		-	-35	-	dB
Idle Channel Noise / Signal-to-noise ratio	o (A-wt)		-	106	-	dB
Interchannel Isolation	(1 kHz)		-	99	-	dB
Analog Output - All Modes						
Full Scale Output Voltage			1.81	2.00	2.17	Vrms
Common Mode Voltage		V <sub>Q</sub>	-	4	-	Vdc
Max Current draw from an AOUT pin		I <sub>OUTmax</sub>	-	575	-	μΑ
Max Current draw from VQ		I <sub>Qmax</sub>	-	1	-	μA
Interchannel Gain Mismatch			-	0.1	-	dB
Gain Drift			-	100	-	ppm/°C
Output Impedance		Z <sub>OUT</sub>	-	50	-	Ω
AC-Load Resistance		RL	5	-	-	kΩ
Load Capacitance		CL	-	-	100	pF

Notes:

2. One-half LSB of triangular PDF dither is added to data.



### **COMBINED INTERPOLATION & ON-CHIP ANALOG FILTER RESPONSE**

(The filter characteristics have been normalized to the sample rate (Fs) and can be referenced to the desired sample rate by multiplying the given characteristic by Fs. Amplitude vs. frequency plots of the data in the table below are available in "Digital Filter Response Plots" on page 16.)

Parameter		Min	Тур	Max	Unit
Combined Digital and On-chip Analog Filte	er Response - Single	-Speed Mo	de - 48 kHz		
Passband (Note 3)	to -0.01 dB corner	0	-	.454	Fs
	to -3 dB corner	0	-	.499	Fs
Frequency Response 10 Hz to 20 kHz		-0.01	-	+0.01	dB
StopBand		0.547	-	-	Fs
StopBand Attenuation	(Note 4)	102	-	-	dB
Total Group Delay (Fs = Output Sample Rate)		-	9.4/Fs	-	S
Intra-channel Phase Deviation		-	-	±0.56/Fs	S
Inter-channel Phase Deviation		-	-	0	S
De-emphasis Error (Note 5)(Relative to 1 kHz)	Fs = 44.1 kHz	-	-	±0.14	dB
Combined Digital and On-chip Analog Filte	er Response - Doubl	e-Speed Mo	ode - 96 kHz		
Passband (Note 3)	to -0.01 dB corner	0	-	.430	Fs
	to -3 dB corner	0	-	.499	Fs
Frequency Response 10 Hz to 20 kHz		-0.01	-	0.01	dB
StopBand		.583	-	-	Fs
StopBand Attenuation	(Note 4)	80	-	-	dB
Total Group Delay (Fs = Output Sample Rate)		-	4.6/Fs	-	S
Intra-channel Phase Deviation		-	-	±0.03/Fs	S
Inter-channel Phase Deviation		-	-	0	S
Combined Digital and On-chip Analog Filte	er Response - Quad-	Speed Mod	e - 192 kHz		
Passband (Note 3)	to -0.01 dB corner	0	-	.105	Fs
	to -3 dB corner	0	-	.490	Fs
Frequency Response 10 Hz to 20 kHz		-0.01	-	0.01	dB
StopBand		.635	-	-	Fs
StopBand Attenuation	(Note 4)	90	-	-	dB
Total Group Delay (Fs = Output Sample Rate)		-	4.7/Fs	-	S
Intra-channel Phase Deviation		-	-	±0.01/Fs	S
Inter-channel Phase Deviation		-	-	0	S

Notes:

- 3. Response is clock-dependent and will scale with Fs.
- 4. For Single-Speed Mode, the Measurement Bandwidth is from stopband to 3 Fs. For Double-Speed Mode, the Measurement Bandwidth is from stopband to 3 Fs. For Quad-Speed Mode, the Measurement Bandwidth is from stopband to 1.34 Fs.
- 5. De-emphasis is available only in Single-Speed Mode.



# **SWITCHING SPECIFICATIONS - SERIAL AUDIO INTERFACE**

Parameters		Symbol	Min	Max	Units
MCLK Frequency			1.024	48.0	MHz
MCLK Duty Cycle			45	55	%
Input Sample Rate (Auto selection)	Single-Speed Mode Double-Speed Mode Quad-Speed Mode	Fs Fs Fs	4 84 170	54 108 216	kHz kHz kHz
LRCK Duty Cycle			40	60	%
SCLK Pulse Width Low		t <sub>sciki</sub>	20	-	ns
SCLK Pulse Width High		t <sub>sclkh</sub>	20	-	ns
SCLK Period	Single-Speed Mode	t <sub>sclkw</sub>	$\frac{1}{(128)Fs}$	-	-
	Double-Speed Mode	t <sub>sclkw</sub>	$\frac{1}{(64)Fs}$	-	-
	Quad-Speed Mode	t <sub>sclkw</sub>	2 MCLK	-	-
SCLK rising to LRCK edge delay		t <sub>slrd</sub>	20	-	ns
SCLK rising to LRCK edge setup time		t <sub>slrs</sub>	20	-	ns
SDIN valid to SCLK rising setup time		t <sub>sdlrs</sub>	20	-	ns
SCLK rising to SDIN hold time		t <sub>sdh</sub>	20	-	ns




Figure 1. Serial Input Timing



### **DIGITAL CHARACTERISTICS**

Parameters		Symbol	Min	Тур	Max	Units
High-Level Input Voltage	V <sub>L</sub> = 3.3 V	V <sub>IH</sub>	2.0	-	-	V
	V <sub>1</sub> = 2.5 V	V <sub>IH</sub>	1.7	-	-	V
	V <sub>L</sub> = 1.5 V	N /	1.05	-	-	V
Low-Level Input Voltage	V <sub>L</sub> = 3.3 V	VIL	-	-	0.8	V
	V <sub>1</sub> = 2.5 V	VIL	-	-	0.7	V
	V <sub>L</sub> = 1.5 V		-	-	0.38	V
Input Leakage Current		l <sub>in</sub>	-	-	±10	μA
Input Capacitance			-	8	-	pF
Maximum MUTEC Drive Current			-	2	-	mA
MUTEC High-Level Output Voltage		V <sub>OH</sub>	-	VA_H	-	V
MUTEC Low-Level Output Voltage		V <sub>OL</sub>	-	0	-	V

### POWER AND THERMAL CHARACTERISTICS

Pa	rameters	Symbol	Min	Тур	Мах	Units
Power Supplies						
Power Supply Current	normal operation, $V_{A H} = 12 V$	I <sub>A H</sub>	-	12	21	mA
(Note 6)	V <sub>A</sub> <sub>H</sub> = 9 V	I <sub>A_H</sub>	-	10	16	mA
	$V_A = 3.3 V$	IA	-	3	4	mA
	$V_{\rm D}$ = 3.3 V	I <sub>D</sub>	-	12	16	mA
	Interface current $V_1 = 3.3 V$	۱L	-	0.02	0.09	mA
	I <sub>pd</sub>	-	380	-	μA	
	power-down state, all supplies (Note 7)	P.2				•
Power Dissipation (all supplies	(Note 6)					
VA_H = 12 V	normal operation		-	121	158	mW
	power-down (Note 7)		-	1	-	mW
VA_H = 9 V	normal operation		-	91	122	mW
	power-down (Note 7)		-	1	-	mW
Power Supply Rejection Ratio (Note 8) (1 kHz) (60 Hz)		PSRR	-	60	-	dB
			-	60	-	dB

#### Notes:

- 6. Current consumption increases with increasing FS and increasing MCLK. Typ and Max values are based on highest FS and highest MCLK. Variance between speed modes is small.
- 7. Power down mode is defined as  $\overline{\text{RST}}$  pin = Low with all clock and data lines held static low. All digital inputs have a weak pull-down which is only present during reset. Opposing this pull-down will slightly increase the power-down current (pull-down is equivalent to a 50 k $\Omega$  resistor per pin).
- Valid with the recommended capacitor values on VQ and V<sub>BIAS</sub> as shown in the typical connection diagram in Section 3.



# 3. TYPICAL CONNECTION DIAGRAM




Figure 2. Typical Connection Diagram



### 4. APPLICATIONS

### 4.1 Sample Rate Range/Operational Mode Detect

The device operates in one of three operational modes. The allowed sample rate range in each mode is auto-detected.

The CS4352 will auto-detect the correct mode when the input sample rate (Fs), defined by the LRCK frequency, falls within one of the ranges illustrated in Table 1. Sample rates outside the specified range for each mode are not supported.

Input Sample Rate (F <sub>S</sub> )	Mode
4 kHz - 54 kHz	Single-Speed Mode
84 kHz - 108 kHz	Double-Speed Mode
170 kHz - 216 kHz	Quad-Speed Mode

Table 1. CS4352 Auto-Detect

### 4.2 System Clocking

The device requires external generation of the master (MCLK), left/right (LRCK) and serial (SCLK) clocks. The left/right clock, defined also as the input sample rate (F<sub>s</sub>), must be synchronously derived from the MCLK according to specified ratios. The specified ratios of MCLK to LRCK, along with several standard audio sample rates and the required MCLK frequency, are illustrated in Tables 2-4.

Refer to Section 4.3 for the required SCLK timing associated with the selected Digital Interface Format and to "Switching Specifications - Serial Audio Interface" on page 8 for the maximum allowed clock frequencies.

Sample Rate	MCLK (MHz)						
(kHz)	256x	384x	512x	768x	1024x		
32	8.1920	12.2880	16.3840	24.5760	32.7680		
44.1	11.2896	16.9344	22.5792	33.8688	45.1584		
48	12.2880	18.4320	24.5760	36.8640	49.1520		

#### Table 2. Single-Speed Mode Standard Frequencies

Sample Rate	MCLK (MHz)						
(kHz)	128x	192x	256x	384x	512x		
88.2	11.2896	16.9344	22.5792	33.8688	45.1584		
96	12.2880	18.4320	24.5760	36.8640	49.1520		

 Table 3. Double-Speed Mode Standard Frequencies

Sample Rate		MCLK (MHz)	
(kHz)	128x	192x	256x
176.4	22.5792	33.8688	45.1584
192	24.5760	36.8640	49.1520

 Table 4. Quad-Speed Mode Standard Frequencies



#### 4.3 Digital Interface Format

The device will accept audio samples in 1 of 4 digital interface formats, as illustrated in Table 5.

The desired format is selected via the DIF1 and DIF0 pins. For an illustration of the required relationship between the LRCK, SCLK and SDIN, see Figures 3-5. For all formats, SDIN is valid on the rising edge of SCLK. Also, SCLK must have at least 32 cycles per LRCK period in format 2 and 48 cycles per LRCK period in format 3.

For more information about serial audio formats, refer to Cirrus Logic Application Note AN282: *The 2-Chan*nel Serial Audio Interface: A Tutorial, available at www.cirrus.com.

DIF1	DIF0	DESCRIPTION	FORMAT	FIGURE
0	0	I <sup>2</sup> S, up to 24-bit Data	0	3
0	1	Right-Justified, 24-bit Data	1	4
1	0	Left-Justified, up to 24-bit Data	2	5
1	1	Right-Justified, 16-bit Data	3	4

**Table 5. Digital Interface Format** 





Figure 5. Left-Justified up to 24-Bit Data



#### 4.4 De-Emphasis Control

The device includes on-chip digital de-emphasis. Figure 6 shows the de-emphasis curve for Fs equal to 44.1 kHz. The frequency response of the de-emphasis curve scales with changes in sample rate, Fs. The De-emphasis error will increase for sample rates other than 44.1 kHz

When pulled to VL, the DEM pin activates the 44.1 kHz de-emphasis filter. When pulled to GND, the DEM pin turns off the de-emphasis filter.





#### 4.5 Recommended Power-Up Sequence

Note:

- 1. Hold RST low until the power supplies and configuration pins are stable, and the master and left/right clocks are locked to the appropriate frequencies, as discussed in Section 4.2. In this state, VQ will remain low and VBIAS will be connected to VA.
- 2. Bring RST high. The device will remain in a low power state with VQ low and will initiate the power-up sequence after approximately 512 LRCK cycles in Single-Speed Mode (1024 LRCK cycles in Double-Speed Mode, and 2048 LRCK cycles in Quad-Speed Mode).

#### 4.6 Grounding and Power Supply Arrangements

As with any high-resolution converter, the CS4352 requires careful attention to power supply and grounding arrangements if its potential performance is to be realized. Figure 2 shows the recommended power arrangements, with VA\_H, VA, VD, and VL connected to clean supplies. If the ground planes are split between digital ground and analog ground, the GND pins of the CS4352 should be connected to the analog ground plane.

All signals, especially clocks, should be kept away from the VBIAS and VQ pins in order to avoid unwanted coupling into the DAC.

#### 4.6.1 Capacitor Placement

Decoupling capacitors should be placed as close to the DAC as possible, with the low-value ceramic capacitor being the closest. To further minimize impedance, these capacitors should be located on the same layer as the DAC. If desired, all supply pins may be connected to the same supply, but a decoupling capacitor should still be placed on each supply pin.

**Note:** All decoupling capacitors should be referenced to analog ground.

The CDB4352 evaluation board demonstrates the optimum layout and power supply arrangements.



### 4.7 Popguard Transient Control

The CS4352 uses a novel technique to minimize the effects of output transients during power-up and powerdown. This technology, when used with external DC-blocking capacitors in series with the audio outputs, minimizes the audio transients commonly produced by single-ended, single-supply converters. It is activated inside the DAC when the RST pin is toggled and requires no other external control, aside from choosing the appropriate DC-blocking capacitors.

#### 4.7.1 Power-Up

When the device is initially powered-up, the audio outputs, AOUTA and AOUTB, are clamped to GND. Following a delay of approximately 1000 sample periods, each output begins to ramp toward the quiescent voltage. Approximately 10,000 LRCK cycles later, the outputs reach  $V_Q$  and audio output begins. This gradual voltage ramping allows time for the external DC-blocking capacitors to charge to the quiescent voltage, minimizing audible power-up transients.

#### 4.7.2 Power-Down

To prevent audible transients at power-down, the device must first enter its power-down state. When this occurs, audio output ceases, and the internal output buffers are disconnected from AOUTA and AOUTB. In their place, a soft-start current sink is substituted that allows the DC-blocking capacitors to slowly discharge. Once this charge is dissipated, the power to the device may be turned off, and the system is ready for the next power-on.

#### 4.7.3 Discharge Time

To prevent an audio transient at the next power-on, the DC-blocking capacitors must fully discharge before turning on the power or exiting the power-down state. If full discharge does not occur, a transient will occur when the audio outputs are initially clamped to GND. The time that the device must remain in the power-down state is related to the value of the DC-blocking capacitance and the output load. For example, with a 3.3  $\mu$ F capacitor, the minimum power-down time will be approximately 0.4 seconds.


#### 4.8 Mute Control

The Mute Control pins go active during power-up initialization, reset, muting, or if the MCLK to LRCK ratio is incorrect. These pins are intended to be used as control for external mute circuits to prevent the clicks and pops that can occur in any single-ended, single-supply system.

Use of the Mute Control function is not mandatory but recommended for designs requiring the absolute minimum in extraneous clicks and pops. Also, use of the Mute Control function can enable the system designer to achieve idle channel noise/signal-to-noise ratios which are only limited by the external mute circuit. Please see the CDB4352 data sheet for a suggested mute circuit for dual-supply systems. Alternately, the FET muting circuit from the CS4351 data sheet may be used as well. This FET circuit must be placed in series after the RC filter; otherwise noise may occur during muting conditions. Further ESD protection will need to be taken into consideration for the FET used.



### 4.9 Initialization and Power-Down Sequence Diagram





# 5. DIGITAL FILTER RESPONSE PLOTS




Figure 7. Single-Speed Stopband Rejection




Figure 9. Single-Speed Transition Band (detail)




Figure 11. Double-Speed Stopband Rejection




Figure 8. Single-Speed Transition Band




Figure 10. Single-Speed Passband Ripple




Figure 12. Double-Speed Transition Band






Figure 13. Double-Speed Transition Band (detail)




Figure 15. Quad-Speed Stopband Rejection




Figure 17. Quad-Speed Transition Band (detail)




Figure 14. Double-Speed Passband Ripple




Figure 16. Quad-Speed Transition Band




Figure 18. Quad-Speed Passband Ripple



### 6. PARAMETER DEFINITIONS

#### Total Harmonic Distortion + Noise (THD+N)

The ratio of the rms value of the signal to the rms sum of all other spectral components over the specified bandwidth (typically 10 Hz to 20 kHz), including distortion components. Expressed in decibels.

#### **Dynamic Range**

The ratio of the full-scale rms value of the signal to the rms sum of all other spectral components over the specified bandwidth. Dynamic range is a signal-to-noise measurement over the specified bandwidth made with a -60 dBFS signal. 60 dB is then added to the resulting measurement to refer the measurement to full scale. This technique ensures that the distortion components are below the noise level and do not effect the measurement. This measurement technique has been accepted by the Audio Engineering Society, AES17-1991, and the Electronic Industries Association of Japan, EIAJ CP-307.

#### **Interchannel Isolation**

A measure of crosstalk between the left and right channels. Measured for each channel at the converter's output with all zeros to the input under test and a full-scale signal applied to the other channel. Units in decibels.

#### **Interchannel Gain Mismatch**

The gain difference between left and right channels. Units in decibels.

#### **Gain Error**

The deviation from the nominal full-scale analog output for a full-scale digital input.

#### Gain Drift

The change in gain value with temperature. Units in ppm/°C.

#### Intra-channel Phase Deviation

The deviation from linear phase within a given channel.


#### **Inter-channel Phase Deviation**


The difference in phase between channels.



# 7. PACKAGE DIMENSIONS







		INCHES			MILLIMETERS	;	NOTE
DIM	MIN	NOM	MAX	MIN	NOM	MAX	
A			0.043			1.10	
A1	0.002	0.004	0.006	0.05		0.15	
A2	0.03346	0.0354	0.037	0.85	0.90	0.95	
b	0.00748	0.0096	0.012	0.19	0.245	0.30	2,3
D	0.252	0.256	0.259	6.40	6.50	6.60	1
E	0.248	0.2519	0.256	6.30	6.40	6.50	
E1	0.169	0.1732	0.177	4.30	4.40	4.50	1
е			0.026			0.65	
L	0.020	0.024	0.028	0.50	0.60	0.70	
μ	0°	4°	8°	0°	4°	8°	

#### JEDEC #: MO-153

Controlling Dimension is Millimeters.

- 1. "D" and "E1" are reference datums and do not included mold flash or protrusions, but do include mold mismatch and are measured at the parting line, mold flash or protrusions shall not exceed 0.20 mm per side.
- 2. Dimension "b" does not include dambar protrusion/intrusion. Allowable dambar protrusion shall be 0.13 mm total in excess of "b" dimension at maximum material condition. Dambar intrusion shall not reduce dimension "b" by more than 0.07 mm at least material condition.
- 3. These dimensions apply to the flat section of the lead between 0.10 and 0.25 mm from lead tips.

Parameters		Symbol	Min	Тур	Max	Units
Package Thermal Resistance	20L TSSOP	$\theta_{JA}$	-	72	-	°C/Watt



### 8. ORDERING INFORMATION

Product	Description	Package	Pb-Free	Grade	Temp Range	Container	Order #		
	20 pin 102 kHz Stores		Hz Stereo		-40° to +85° C	Rail	CS4352-CZZ		
CS4352	20-pin, 192 kHz Stereo DAC with 2 Vrms Line	20-pin	20-nin	YES		oin VES	-+0 10 +05 0	Tape & Reel	CS4352-CZZR
034352	Out	TSSOP	P · · · · ·		-40° to +105° C	Rail	CS4352-DZZ		
	Out			Automotive	-40 10 +105 C	Tape & Reel	CS4352-DZZR		
CDB4352	CS4352 Evaluation Board		-	-	-	-	CDB4352		

# 9. REVISION HISTORY

Release	Changes					
PP1	Lowered $V_{A_H}$ minimum specification. Updated Idle channel noise specification to A-wt. Updated AOUT current draw specification. Updated $V_{IL}$ for VL=1.5V.					
F1	Updated performance specifications and limits based on statistical data.					
F2	Added Automotive grade specifications and ordering information. Updated Commercial grade idle channel noise specification. Lowered V <sub>IL</sub> maximum specification. Updated power supply current specification. Updated MCLK maximum specification.					

### **Contacting Cirrus Logic Support**

For all product questions and inquiries, contact a Cirrus Logic Sales Representative.

To find the one nearest you, go to www.cirrus.com.

#### IMPORTANT NOTICE

Cirrus Logic, Inc. and its subsidiaries ("Cirrus") believe that the information contained in this document is accurate and reliable. However, the information is subject to change without notice and is provided "AS IS" without warranty of any kind (express or implied). Customers are advised to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgment, including those pertaining to warranty, indemnification, and limitation of liability. No responsibility is assumed by Cirrus for the use of this information, including use of this information as the basis for manufacture or sale of any items, or for infringement of patents or other rights of third parties. This document is the property of Cirrus and by furnishing this information, Cirrus grants no license, express or implied under any patents, mask work rights, copyrights, trademarks, trade secrets or other intellectual property rights. Cirrus owns the copyrights associated with the information contained herein and gives consent does not extend to other copying such as copying for general distribution, advertising or promotional purposes, or for creating any work for resale.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROP-ERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). CIRRUS PRODUCTS ARE NOT DESIGNED, AUTHORIZED OR WARRANTED FOR USE IN AIRCRAFT SYSTEMS, MILITARY APPLICATIONS, PRODUCTS SURGICALLY IMPLANTED INTO THE BODY, AUTOMOTIVE SAFETY OR SEVERE PROP-VICES, LIFE SUPPORT PRODUCTS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF CIRRUS PRODUCTS IN SUCH APPLICATIONS IS UNDER-STOOD TO BE FULLY AT THE CUSTOMER'S RISK AND CIRRUS DISCLAIMS AND MAKES NO WARRANTY, EXPRESS, STATUTORY OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR PARTICULAR PURPOSE, WITH REGARD TO ANY CIRRUS PRODUCT THAT IS USED IN SUCH A MANNER. IF THE CUSTOMER OR CUSTOMER'S CUSTOMER USES OR PERMITS THE USE OF CIRRUS PRODUCTS IN CRITICAL APPLICATIONS, CUSTOMER AGREES, BY SUCH USE, TO FULLY INDEMNIFY CIRRUS, ITS OFFICERS, DIRECTORS, EMPLOYEES, DISTRIBUTORS AND OTHER AGENTS FROM ANY AND ALL LIABILITY, INCLUDING ATTORNEYS' FEES AND COSTS, THAT MAY RESULT FROM OR ARISE IN CONNECTION WITH THESE USES.

Cirrus Logic, Cirrus, the Cirrus Logic logo designs, and Popguard are trademarks of Cirrus Logic, Inc. All other brand and product names in this document may be trademarks or service marks of their respective owners.