

Akustica, Inc.

Data sheet AKU450P / AKU450 / AKU451 Digital, HD Voice Silicon MEMS Microphone



AKU450P / AKU450 / AKU451 - Data Sheet

Package type	5-pad LGA bottom port
Document revision	1.01a
Document release date	01 November 2016
Document number	AKU-AKU450P-DS49
Technical Reference Code(s)	0 273 0A0 041 0 273 0A0 046 0 273 0A0 tbd
Notes	AKU451 information is preliminary in this datasheet. Specifications are subject to change without notice. Product photos and pictures are for illustration purposes only and may differ from the real product's appearance.





AKU450P / AKU450 / AKU451 Digital, HD Voice Silicon MEMS Microphone

Key features

- Digital PDM output
- Omni-directional silicon acoustic sensor
- Excellent acoustic performance: 65dB SNR
- Sensitivity: -26dBFS
- Uniform sensitivity tolerance: AKU450 ± 3dB; AKU450P ± 1dB; AKU451 ± 1dB
- Compatible with Microsoft[®] Windows[®], LYNC[®] & Skype[®] logo certifications, Intel[®] Ultrabook[™] and Google[®] Chromebook[™] requirements for digital microphones
- Compatible with Microsoft[®] Cortana[®] ASR Premium requirements
- Robust digital-output & metal lid package immune to RF/EM interference
- · Matched microphones in frequency and phase response for array applications
- Output supports dual-microphone, single-wire multiplexing
- Industry standard microphone interface compatible with multiple codecs
- Low current power-down mode
- Lead-free surface-mountable and RoHS2 compliant
- Halogen-free compliance, IEC61249-2-21
- Thin profile, SMT packaging
- Small package: 3.5 x 2.65 x 0.98 mm³

Typical applications

- Mobile phones
- Media tablets
- Ultrabooks
- Wearable
- Smart home accessories
- Microphone arrays
- Webcams and camera modules

General description

AKU450P is an HD Voice quality, bottom port, digital output MEMS semiconductor microphone. It is a microphone consisting of a MEMS acoustic sensor and an integrated circuit (IC) with a preamplifier, analog-to-digital converter, charge pump and supporting circuitry in a small $3.5 \times 2.65 \times 0.98 \text{ mm}^3$ package.

The robust digital output stream from the AKU450P is virtually immune to all forms of Radio Frequency Interference (RFI) and Electromagnetic Interference (EMI) allowing designers the flexibility to integrate the component anywhere on the platform and obtain consistent SNR regardless of proximity to displays, Wi-Fi antennae, or other sources of interference that would degrade the signal of conventional analog microphones.

The device provide a pulse density modulated (PDM), single-bit digital output stream designed to enable the multiplexing of stereo microphone data onto a single wire. With a user selectable L/R channel option, it is ideal for use in multiple microphone applications.

AKU-AKU450P-DS49 | Version 1.01 | November 2016

[©] Akustica, Inc. reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. Bosch Group and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



Index of Contents

1. ABSOLUTE MAXIMUM RATINGS4
2. STANDARD OPERATING CONDITIONS4
3. ELECTRICAL AND ELECTRO-ACOUSTIC SPECIFICATIONS
4. TYPICAL DEVICE CHARACTERISTICS6
 4.1 FREQUENCY RESPONSE 4.2 IDD VS. VDD 4.3 SENSITIVITY VS. VDD 4.4 IDD VS. CLOCK FREQUENCY 4.5 PSR VS. FREQUENCY 4.6 TOTAL HARMONIC DISTORTION
5. MECHANICAL SPECIFICATIONS8
6. PIN-OUT AND CONNECTION DIAGRAMS
7. MANUFACTURING NOTES10
7.1 SOLDER REFLOW 7.2 PART HANDLING 7.3 PCB LAND PATTERN AND STENCIL PATTERN
8. RELIABILITY SPECIFICATIONS
9. PART MARKING INFORMATION14
10. PACKAGING INFORMATION14
11. ORDERING INFORMATION15
12. LEGAL DISCLAIMER
13. DOCUMENT HISTORY AND MODIFICATION17

AKU-AKU450P-DS49 | Version 1.01 | November 2016



1. Absolute maximum ratings

Supply Voltage, V_{DD} to GND	5.5V
ESD Tolerance	
Human Body Model	2000V
Machine Model	200V
Storage Temperature Range	-40°C to 105°C

2. Standard operating conditions

Operating Temperature Range	-40°C to 85°C
Supply Voltage (V _{DD})	1.62V to 3.6V
Clock Frequency	1.00MHz to 3.25MHz

3. Electrical and electro-acoustic specifications

Unless otherwise noted, test conditions are: V_{DD} = 1.8V T_a = 25°C RH = 50%

CLK = 2.4MHz

Parameter		Test Conditions	Min.	Тур.	Max.	Unit	
Directivity			Omni-directional				
Signal to Nois	e Ratio (SNR)	f _{in} = 1kHz, A-weighted		65		dB	
Low Frequence	y Corner	-3dB from 1kHz sensitivity value		40		Hz	
High Frequence	cy Corner	+3dB from 1kHz sensitivity value		11.5		kHz	
	AKU450	1kHz, 94dB SPL.	-29	-26	-23		
Sensitivity ¹	AKU450P	full-scale = 100% 1's density at	-27	-26	-25	dBFS	
	AKU451	PDM output of microphone	-27	-26	-25		
Total Harmoni	c Distortion	@ 100dB SPL, f _{in} = 1kHz			1	0/	
(THD)		@ 115dB SPL, $f_{in} = 1kHz^1$		1	5	70	
Acoustic Overload Point (AOP)		< 10% THD, fin = 1kHz, V _{DD} = 3.3V		120		dBSPL	
Power Supply Rejection (PSR)		100mVpp square wave, @ 217Hz, A-weighted		-86		dBFS(A)	
Part-to-part phase matching from nominal		f _{in} = 1kHz		± 2		0	
Current Consumption ¹ (with no load)		Clock on (CLK = 2.8MHz)		730	850	μA	
		Clock off			7	μΑ	
V _{DD} ramp-up time (from 0V to 1.62V)					7	ms	
Power-up initialization		Data invalid time from clock on			32	ms	
Polarity		Increasing sound pressure	und pressure Increasing 1's density		nsity		

Note 1: parameter 100% tested

AKU-AKU450P-DS49 | Version 1.01 | November 2016

[©] Akustica, Inc. reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. Bosch Group and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

3.1 Timing Characteristics

(Typical performance with load capacitance <20pF and a clock frequency of 2.4MHz)

	Typical Mode	Data Valid	Data Sampled	L/R SELECT Connected to
DATAL	Left	Falling clock	Rising clock	GND
$DATA_R$	Right	Rising clock	Falling clock	V _{DD}



Output	Parameter	Typical Value	Description
DATA _R	t1	6ns	Time from falling edge of clock until data becomes high impedance
	t ₂	61ns	Time from falling edge of clock until data becomes valid
DATAL	t3	6ns	Time from rising edge of clock until data becomes high impedance
DATA _R	t ₄	53ns	Time from rising edge of clock until data becomes valid

AKU-AKU450P-DS49 | Version 1.01 | November 2016

Akustica, Inc.



3.2 Digital Logic Characteristics

(Typical performance with load capacitance <20pF and a clock frequency of 2.4MHz)

Symbol	Parameter	Min	Max	Units
VIL MAX	Maximum level considered a logic 0		0.4*V _{DD}	V
V _{IH MIN}	Minimum level considered a logic 1	0.5*V _{DD}		V
V ol max	Maximum level a driven output logic 0 can be		0.05*V _{DD}	۷
V _{OH MIN}	Minimum level a driven output logic 1 can be	0.95*V _{DD}		V

3.3 Sleep Mode and Active Mode

The AKU450P enters Sleep Mode within 5μ S of the clock signal becoming inactive (i.e. clock frequency = 0Hz).

In Sleep Mode the microphone PDM Data output pin is in high impedance state.

The microphone returns from Sleep Mode to Active Mode 65,536 cycles after the clock becomes active (i.e. clock frequency \ge 1.0MHz). With a 3.072MHz clock, the microphone start-up time is 21.4ms; for a 2.4MHz clock the microphone start-up time is 27.4ms.

3.4 Radio Frequency Interference (RFI) Immunity

The AKU45x components are virtually immune to all forms of Radio Frequency Interference (RFI) and Electromagnetic Interference (EMI). Select devices in the family have additional built-in RF filter(s), as shown in the microphone block diagram below.



Please refer to the ordering information table in section 11, for available device options.

AKU-AKU450P-DS49 | Version 1.01 | November 2016

[©] Akustica, Inc. reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. Bosch Group and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



4. Typical device characteristics

4.1 Frequency Response

(Measured frequency response normalized to 1kHz)



4.3 Sensitivity vs. V_{DD}

(Measured sensitivity changes relative to supply voltage)



4.5 PSRR vs. Frequency (Typical PSRR relative to frequency)



4.2 I_{DD} vs. V_{DD}

(Measured current consumption relative to supply voltage)



4.4 I_{DD} vs. Clock Frequency

(Measured current consumption relative to clock frequency)



4.6 Total Harmonic Distortion

(THD relative to mic. input pressure level)



AKU-AKU450P-DS49 | Version 1.01 | November 2016

Akustica, Inc.

Top View

5. Mechanical Specifications

Bottom View







Side View

Pin 1 Indicator



ltem	Dimension	Tolerance	Units	
Length (L)	3.50	± 0.10	mm	
Width (W)	2.65	± 0.10	mm	
Height (H)	0.98	± 0.10	mm	
Acoustic Port (AP)	0.325	± 0.05	mm	
Planarity	Top/Bottom	± 0.05	mm	
All dimensions in mm Tolerance ± 0.05mm unless otherwise specified				

AKU-AKU450P-DS49 | Version 1.01 | November 2016

Akustica, Inc.

[©] Akustica, Inc. reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. Bosch Group and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



6. Pin-Out and connection diagrams

6.1 Pin-Out

(As viewed from bottom of package)



Pin	Name	Function
1	DATA	PDM Data output
2	L/R*	Left / Right Select
3	GND	Ground
4	CLK	Clock
5	V _{DD}	Power

*Must be electrically connected directly to either ground or V_{DD} with no components in between, and shortest possible traces.



6.2 Typical Application Schematic

AKU-AKU450P-DS49 | Version 1.01 | November 2016



7. Manufacturing notes

7.1 Solder Reflow

Typical solder reflow profile



Description	Parameter	Pb free
Average ramp-up rate	T_L to T_P	max. 3°C/s
Time between Ts _{min} (150°C) and Ts _{max} (200°C)	ts	60s – 120s
Time above liquidous temperature T_L (217°C)	tL	60s – 90s
Peak temperature	T _P	max. 260°C
Time at T _P	t _P	max. 20s
Average ramp-down rate	T_P to 25°C	max. 6°C/s

Note: It is recommended to fine-tune the reflow process to optimize for variations in materials, environment, handling, PCB board size and thickness, etc.

Please refer to AN60-Handling, Soldering, and Mounting Instructions for more detailed information and precautions.

AKU-AKU450P-DS49 | Version 1.01 | November 2016

[©] Akustica, Inc. reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. Bosch Group and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



7.2. Microphone Handling

Although the microphone may not appear damaged immediately due to inappropriate handling, there can be long term effects that affect the lifetime of the component.

Rule of thumb: The microphone is an artificial ear so treat it like your own ear.

- Do not blow air into the acoustic port of the microphone for any reason. Do not subject it to pressurized air
 - e.g. when cleaning the board or other components on the same board
- Do not apply vacuum to the acoustic port of the microphone
- Do not insert liquids
 - If populated circuit boards are washed, the microphone must be protected
- Do not insert dust
 - The production facilities must be clean
 - e.g. if PCB routing/sawing is done close to the microphone after SMT assembly and reflow
- Do not insert any objects
 - If assembly or rework is done manually, care must be taken that the tools cannot enter the microphone sound port
 - It is best to choose tool size so that it does not fit through the sound port of the microphone
- Do not cover the acoustic port with tape when heating during assembly or reflow
- Do not apply extreme mechanical stresses on the microphone, including mechanical shocks above 10kG or compression of the microphone package.
- After a bottom port microphone has been assembled on a circuit board, protect the sound port (now on the other side of the board) from dust, liquids, and other foreign materials as well as any tools and pressurized air.

ESD Handling Procedures



Follow CMOS handling procedures with MEMS microphones. Handle the microphone with proper workplace grounding to include wrist straps and ionized airflow over open trays and reels of microphones. Do not hot-swap/hot-plug during testing. Device pins have ESD ratings of 2kV/200V for HBM/MM respectively.

AKU-AKU450P-DS49 | Version 1.01 | November 2016

7.3 PCB Land Pattern & Stencil Pattern



Note: the aperture of the stencil pattern may require adjustment / optimization based on the thickness of the stencil.

Please refer to AN60-Handling, Soldering, and Mounting Instructions for more detailed information and precautions.

AKU-AKU450P-DS49 | Version 1.01 | November 2016



8. Reliability Specifications

The microphone sensitivity after stress must deviate by no more than 3dB from the initial value.

	Test	Test Condition	Standard
1	Cold Temp Operation	Temperature = -40°C, 1000 hours (with bias)	IEC 60068-2-1
2	Hot Temp Operation	Temperature = 105°C, 1000 hours (with bias)	IEC 60068-2-2
3	Humidity Operation	Temperature = 85°C, RH = 85%, 1000 hours (with bias)	JESD22-A101-B
4	Cold Temp Storage	Temperature = -40°C, 1000 hours (without bias)	IEC 60068-2-1
5	Hot Temp Storage	Temperature = 105°C, 1000 hours (without bias)	IEC 60068-2-2
6	Humidity Storage	Temperature = 85°C, RH = 85%, 1000 hours (without bias)	JESD22-A101-B
7	Thermal Cycle	100 Cycles, -40°C to +125°C, 15min soaks, <30sec ramps	IEC 60068-2-4
8	Vibration	Sinusoidal Vibration, 20Hz-2000Hz, 4min sweeps, 16min along each of 3 axis, amplitude 3 limits of 20G and 0.06"	Mil-Std-883E, Test A
9	Mechanical Shock	10,000G shocks, 5 impacts along each of 6 axes	MIL-STD-883E
10	Drop Test, Standard	Using 150gm aluminum fixture, 3 drops along each of 6 axes (total 18 drops) from 1.5m height onto concrete drop surface.	IEC 60068-2-32
11	Drop Test, Air Hammer	1.0m height, drops onto polished granite using 165g aluminum fixture. 20x drops, starting at 1^{st} drop, with 1x drop increment	Custom
12	ESD (HBM)	+/- 2000V, 1 discharge for each polarity, 11 pin combinations, 22 total discharges per microphone	JESD22-A114-B
13	ESD (MM)	+/- 200V, 1 discharge for each polarity, 11 pin combinations, 22 total discharges per microphone	JESD22-A115-A
14	ESD	+/- 8kV, contact discharge to lid with DUT grounded	IEC 61000-4-2
15	Moisture Sensitivity Level 1	24 hour bake at 125°C, followed by 168 hours at 85°C, 85%RH, followed by 3 passes solder reflow (MSL Level 1)	JSTD020D-01
16	Reflow Solder	3 pass reflow, peak temperature = 260°C, time duration - see reflow profile in section 7	JSTD020D-01

AKU-AKU450P-DS49 | Version 1.01 | November 2016

Akustica, Inc.



9. Part marking information

Acoustic Port below



Line 1: A45XF (A = Akustica | 45X = Part Code. X = 0, 1 | F = Assy. Facility) Line 2: WWYLL (WW = Work Week | Y = Year | LL = Lot Number Processed During Work Week)

10. Packaging information

10.1 Tape Specification



Notes:

- 1. 10 sprocket hole pitch cumulative tolerance +/- 0.2
- 2. Camber in compliance with EIA-481
- 3. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole

AKU-AKU450P-DS49 | Version 1.01 | November 2016

[©] Akustica, Inc. reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. Bosch Group and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.



10.2 Component Orientation



11. Ordering information

Order Number	Sensitivity Tolerance (dB)	RF Filter	Part Code	Package	Shipping Method	Standard Quantity
0 273 0A0 041	+/- 3	No	A450	5-Pad LGA	13" Reel	5,900
0 273 0A0 046	+/- 1	No	A450	5-Pad LGA	13" Reel	5,900
TBA*	+/- 1	Yes	A451	5-Pad LGA	13" Reel	5,900

*AKU451 ordering part number (OPN) to be assigned when commercial samples are available. Please check with your local Bosch sales representative.

AKU-AKU450P-DS49 | Version 1.01 | November 2016



12. Legal Disclaimer

12.1 Engineering samples

Engineering Samples are marked with an asterisk (*) or (e). Samples may vary from the valid technical specifications of the product series contained in this data sheet. They are therefore not intended or fit for resale to third parties or for use in end products. Their sole purpose is internal client testing. The testing of an engineering sample may in no way replace the testing of a product series. Akustica assumes no liability for the use of engineering samples. The Purchaser shall indemnify Akustica from all claims arising from the use of engineering samples.

12.2 Product use

Akustica products are developed for the consumer goods industry. They may only be used within the parameters of this product data sheet. They are not fit for use in life-sustaining or security sensitive systems. Security sensitive systems are those for which a malfunction is expected to lead to bodily harm or significant property damage. In addition, they are not fit for use in products which interact with motor vehicle systems.

The resale and/or use of products are at the purchaser's own risk and his own responsibility. The examination of fitness for the intended use is the sole responsibility of the Purchaser.

The purchaser shall indemnify Akustica from all third party claims arising from any product use not covered by the parameters of this product data sheet or not approved by Akustica and reimburse Akustica for all costs in connection with such claims.

The purchaser must monitor the market for the purchased products, particularly with regard to product safety, and inform Akustica without delay of all security relevant incidents.

12.3 Application examples and hints

With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Akustica hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights or copyrights of any third party. The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. They are provided for illustrative purposes only and no evaluation regarding infringement of intellectual property rights or copyrights or regarding functionality, performance or error has been made.

AKU-AKU450P-DS49 | Version 1.01 | November 2016

[©] Akustica, Inc. reserves all rights even in the event of industrial property rights. We reserve all rights of disposal such as copying and passing on to third parties. Bosch Group and the symbol are registered trademarks of Robert Bosch GmbH, Germany. Note: Specifications within this document are subject to change without notice.

BOSCH AKU450P Data sheet	Page 17
-----------------------------	---------

13. Document history and modification

Revision Number	Chapter	Description of modification/changes	Date
1.0a	All	Released version 1.0 of datasheet. Added AKU451 to table.	21-Sep-16
1.01a	8	Updated table - added test #11	01-Nov-16

Akustica, Inc. 2555 Smallman Street, Suite 200 Pittsburgh, PA / USA 15222 (412) 390-1730

sales@akustica.com www.akustica.com/contact.asp

Modifications reserved | Printed in USA Specifications subject to change without notice

AKU-AKU450P-DS49 | Version 1.01 | November 2016

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

 Akustica:

 AKU450P
 AKU450