RICOH

R5101G SERIES

Microprocessor power management with Watchdog Timer

NO. EA-071-130424

OUTLINE

The R5101G Series are CMOS-based μ con power management ICs with high accuracy output voltage and detector threshold and with ultra low supply current. Each of these ICs consists of a voltage regulator, a voltage detector and a watchdog timer. Thus, the R5101G Series have the function of a power management for microprocessor, a monitor of the voltage of a power source and a microprocessor supervisor.

The built-in voltage regulator with an internal driver transistor can supply typically 50mA current to a system when the voltage difference between input and output is 2V. Therefore these ICs are very suitable for various power supply systems for microprocessors. The output voltage is monitored by the voltage detector which is built-in these ICs.

The built-in voltage detector has an output delay function and the delay time can be set by an external capacitor (C_D).

The output voltage and the detector threshold voltage can be set individually for each IC by laser trimming.

Furthermore, when a microprocessor works incorrectly, the watchdog timer which checks over microprocessor generates reset signals intermittently to prevent a whole system from being malfunction.

The timeout periods for watchdog and reset can also be set individually by an external capacitor (CTW).

FEATURES

- Built-in a watchdog timer
- Timeout period for watchdog and generating a reset signal can be set by an external capacitor
- Watchdog timer can be stopped individually by CE Pin
- Supply Current...... Typ. 5µA
- Output Voltage Accuracy±2.5%
- Detector Threshold Range......1.7V to 4.5V (0.1V step)
- Detector Threshold Accuracy.....±2.5%
- Power-on Reset Delay Time can be set by an external capacitor
- Output Current Typ. 50mA (at VIN-VOUT=2V)
- Package.....SSOP-8G

APPLICATIONS

• Power source for microprocessors

BLOCK DIAGRAMS



SELECTION GUIDE

The output voltage and the detector threshold for the ICs can be selected at the users' request.

Product Name	Package	Quantity per Reel	Pb Free	Halogen Free		
R5101GxxxA-TR-FE	SSOP-8G	3,000 pcs	Yes	Yes		
xxx: The combination of output voltage and detector threshold for each channel can be designated by serial numbers. (For details, please refer to MARK INFORMATIONS.)						

PIN CONFIGURATION



PIN DESCRIPTIONS

Pin No.	Symbol	Description
1	SCK	Clock Input Pin from Microprocessor
2	Ср	External Capacitor Pin for Setting Delay Time of Voltage Detector
3	Стw	External Capacitor Pin for Setting Reset and Watchdog Timeout Periods
4	Vdd	Power supply Pin
5	Vout	Output Pin for Voltage Regulator
6	GND	Ground Pin
7	CE	Control Switch Pin for Watchdog timer ("H" active, "L" inactive)
8	RESET	Output Pin for Reset signal of Watchdog timer and Voltage Detector. (Output Type is Nch Open Drain, Output "L" at detecting Detector Threshold and Watchdog Timer Reset.)

ABSOLUTE MAXIMUM RATINGS

Topt=25°C, Vss=0V

Symbol	Item		Rating	Unit
Vdd	Supply Voltage		–0.3 to 12	V
Vcd		Voltage of C _D Pin	Vss-0.3 to VDD+0.3	V
Vстw		Voltage of CTW Pin	Vss-0.3 to VDD+0.3	V
Vout		Voltage of Vout Pin	Vss-0.3 to VDD+0.3	V
VRESET		Voltage of RESET Pin	Vss-0.3 to 12	V
Vce		Voltage of CE Pin	Vss-0.3 to VDD+0.3	V
Vscк	input voltage	Voltage of SCK Pin	Vss-0.3 to VDD+0.3	V
Ιουτ	Output Current	Current of Vout Pin	150	mA
IRESET		Current of RESET Pin	10	mA
PD	Power Dissipation (SSOP-8G)*		380	mW
Topt	Operating Temper	ature Range	-40 to 85	О°
Tstg	Storage Temperature Range		-55 to 125	°C

*) For Power Dissipation, please refer to PACKAGE INFORMATION.

ABSOLUTE MAXIMUM RATINGS

Electronic and mechanical stress momentarily exceeded absolute maximum ratings may cause the permanent damages and may degrade the life time and safety for both device and system using the device in the field.

The functional operation at or over these absolute maximum ratings is not assured.

ELECTRICAL CHARACTERISTICS

•	R5101GxxxA	١
---	------------	---

• R510	R5101GxxxA Topt=25°C						=25°C
Symbol	Item	Cond	litions	Min.	Тур.	Max.	Unit
Vdd	Operating Voltage			1.5		10	V
Iss-On	Supply Current (WDT active)	VDD=CE=VOUT+2.0V			5	15	μA
Iss-Off	Supply Current (WDT inactive)	VDD=VOUT+2.0V, CE=GND			6	18	μA
Vout	Output Voltage	VDD=VOUT+2.0V, IOUT=10mA		×0.975		×1.025	V
Іоυт	Output Current ^{*1}	Vdd=Vout+2.0V		50			mA
Vdif	Dropout Voltage		Refer to the foll	owing ta	ble		
ΔVουτ/ ΔΙουτ	Load Regulation	V _{DD} =V _{OUT} +2.0V, (In case that 3.0) 1mA≤IouT≤50m/	1mA≤Iouт≤30mA V≤Vouт≤5.0V, A)		50	100	mV
$\Delta V_{OUT}/\Delta V_{DD}$	Line Regulation	Iout=10mA Vout+0.5V≤Vdd≤	10V		0.1	0.2	%/V
ILIM	Current Limit (Short mode)	Vout=GND		10	50	100	mA
$\Delta V_{OUT}/\Delta T_{OPt}$	Output Voltage Temperature Coefficient	lou ⊤=10mA -40°C≤Topt≤85°0	2		±100		ppm/ °C
-Vdet	Detector Threshold			×0.975		×1.025	V
VHYS	Hysteresis Range				-V _{DET} ×0.05	-V _{DET} ×0.07	V
Vdetmgn	Regulator Voltage Margin against Released Voltage	Vout-((-Vdet)+Vhys), Iout=10mA		0.02			V
Δ -V _{DET} / Δ Topt	Detector Threshold Temperature Coefficient	-40°C≤Topt≤85°C			±100		ppm/ °C
t PR	Reset Delay Time	Vdd=Vout+2.0V, Cd=0.001µF		7	14	35	ms
twd	Watchdog Timeout period	Vdd=Vout+2.0V, Cw=0.01µF		50	120	250	ms
twr	Reset Hold Time of WDT	Vdd=Vout+2.0V, Cw=0.01µF		5	12	25	ms
Vінscк	SCK Input Voltage "H"	Vdd=Vout+2.0V		0.8 ×Vоит		Vdd	V
Vilisck	SCK Input Voltage "I "	VDD=VOUT+2 OV	1.8V≤Vouт≤2.9V	0		0.1 ×Vоит	V
V LOOK		100 100112101	3.0V≤Vout≤5.0V	0		0.2 ×Vоит	•
VIHCE	CE Input Voltage "H"			1.2		Vdd	V
VILCE	CE Input Voltage "L"			0.0		0.2	V
Інск	SCK Input Current "H"	VDD=SCK=VOUT+2.0V		-1		1	μA
IILSCK	SCK Input Current "L"	VDD=VOUT+2.0V, SCK=GND		-1		1	μA
Rpu	CE Pull-up Resistance			2	4	10	MΩ
Іср	C _D Pin Output Current	VDD=1.5V, VDS=0.5V		1	2		mA
Істw	C⊤w Pin Output Current	VDD=1.5V, VDS=0.5V		1	2		mA
RESET	RESET Pin Output Current	Vdd=1.5V, Vds=0.5V		1	2		mA
lleak	RESET Pin Leakage Current	VDD=10.0V, CE=GND, VDS=10.0V		-1		1	μA
Тѕски	SCK Input Pulse Width	VDD=VOUT+2.0V		500			ns

Symbol	ltem	Conditions	Min.	Тур.	Max.	Unit
Vstart	Minimum Operating Voltage of Voltage Detector			0.9	1.5	V

*1) In case that Vout<2V, please use lout with 0.1mA or more.

• Dropout Voltage by Output Voltage

Topt=25°C

Output Voltage	Dropout Voltage VDIF (V)					
Vout (V)	Condition	Min.	Тур.	Max.		
$1.8 \le V_{\text{OUT}} \le 2.9$	louτ=10mA	0.100	0.350	0.650		
$3.0 \le V_{\text{OUT}} \le 3.9$	- Iout=30mA	0.100	0.500	0.850		
$4.0 \le V_{OUT} \le 5.0$		0.100	0.350	0.650		

RECOMMENDED OPERATING CONDITIONS (ELECTRICAL CHARACTERISTICS)

All of electronic equipment should be designed that the mounted semiconductor devices operate within the recommended operating conditions. The semiconductor devices cannot operate normally over the recommended operating conditions, even if when they are used over such conditions by momentary electronic noise or surge. And the semiconductor devices may receive serious damage when they continue to operate over the recommended operating conditions.

TYPICAL APPLICATIONS



TECHNICAL NOTES

The minimum value of the operation margin for releasing the voltage detector is specified as 0.02V.

This IC is sensing the output voltage of the regulator of this IC itself, and depending on the input voltage transient or load transient, the operation margin may be disappeared.

The power line noise may cause a mis-operation of the watchdog timer, therefore V_{DD} and GND lines must be sufficient enough for avoiding the mis-operation.

If the power line has some noise, the output of the regulator of this IC may generate the noise, in such a case, the built-in detector may detect the output noise of the voltage regulator and $\overrightarrow{\mathsf{RESET}}$ signal may output.

To prevent the IC from this kind of mis-operation, we recommend using a capacitor in the capacitance range from 1μ F to 2.2μ F between Vout pin and GND pin.

To avoid the mis-operation, during watchdog timer monitoring time, there is some ignoring time against clock pulse. Therefore, during the ignoring time, input clock pulse (rising edge trigger) is ignored. The ignoring time is approximately as follows:

1) The time interval for VCTW pin voltage from Vref2H to (Vref2H-Vref2H/20)

2) The time interval for VcTW pin voltage from Vref2L+Vref2L/20 to Vref2L

TIMING CHART



OPERATION

- When V_{DD} is turned on and Input Voltage reaches Vstart (nearly equal 0.8V), the output of RESET pin becomes "L" level.
- ② An External Capacitor starts to be charged through the C_D pin when an Output Voltage of the Voltage Regulator, V_{OUT}, crosses the Released Voltage, +V_{DET}, from Lower to Higher. The V_{RESET} is kept "L" level until Voltage of the C_D pin, V_{CD}, reaches to the Vref2H, and after that the V_{RESET} becomes to "H" level.
- tPR: Time interval between the timing of starting edge of forcing voltage to VDD pin and the timing of reverse the voltage level of VRESET.
 tPR can be set by connecting an external capacitor to CD pin, tPR can be calculated as shown below;

t_{PR}(ms) \approx 14000× C_D(µF); C_D means a value of an external capacitor connected to C_D pin.

- ③ When the voltage level of V_{CD} reaches to the Vref2H, the external capacitor starts to be charged through the C_{TW} pin and the watchdog timer begins to operate.
- ④ The operation mode for the external capacitor changes from charging mode to discharging mode through C_{TW} pin when the voltage level of C_{TW} pin, V_{CTW}, reaches to the Vref2H.
- ⑤ While the C_{TW} pin is on the discharging mode, if a clock pulse is entered (synchronous with a rising edge of the pulse), the operation mode of C_{TW} pin changes from discharging mode to charging mode. And the external capacitor connected to C_{TW} pin is charged until its voltage level reaches to Vref2H.
- ⑥ While the C^{TW} pin is on the discharging mode, if V_{CTW} level drops to Vref2L without clock pulse to CLK pin, the voltage level of RESET pin becomes from "H" to "L".
- * Watchdog Timeout period, twp,: Discharging Time of CTW pin level from Vref2H to Vref2L twp can be set by connecting an external capacitor to CW pin, twp can be calculated as shown below; twp (ms) $\approx 12000 \times$ CW (µF); CW means a value of an external capacitor connected to CW pin.
- \odot C_{TW} pin is changed to charging mode from discharging mode when the Reset signal is generated.
- Reset timeout period of the watchdog timer, twR,: Time interval between Charging time of the CTW pin from Vref2L to Vref2H. twR can be calculated by the next equation as shown below; twR (ms) ≈ twD/10
- In the Output Voltage level of RESET pin becomes from "H" to "L", or a Reset signal is generated when an output voltage of the Voltage Regulator drops to a level at equal or less than -VDET.
- In watchdog timer will be halted when a Voltage level of CE pin becomes to "L". In this case, only the watchdog timer is stopped and monitoring the output voltage is continued. After that, if the voltage level of CE pin becomes to "H", CTW pin starts to be on charging mode.

TEST CIRCUIT



Detector Threshold(VDET) Test Circuit



SCK Input Current Test Circuit



RESET Output leakage Current Test Circuit



Output Voltage Test Circuit



Reset and Watchdog Timeout Periods Test Circuit



Output Current Test Circuit



Minimum Input Voltage for RESET Output Test Circuit



TYPICAL CHARACTERISTICS

1) Output Voltage vs. Output Current













R5101G (VR=5V)



R5101G (VR=5V)



RICOH













6) Detector Threshold vs. Temperature R5101G (VD=2.7V)







4) Output Voltage vs. Temperature

9) RESET Pin Output Current vs. Input Voltage







13) tPR vs. External Capacitance of CD Pin



10) Delay Time of Released Voltage vs. Temperature R5101G



12) Reset Timeout period vs. Temperature









15) CE Pull-up Resistance vs. Temperature





R5101G









- 1. The products and the product specifications described in this document are subject to change or discontinuation of production without notice for reasons such as improvement. Therefore, before deciding to use the products, please refer to Ricoh sales representatives for the latest information thereon.
- 2. The materials in this document may not be copied or otherwise reproduced in whole or in part without prior written consent of Ricoh.
- 3. Please be sure to take any necessary formalities under relevant laws or regulations before exporting or otherwise taking out of your country the products or the technical information described herein.
- 4. The technical information described in this document shows typical characteristics of and example application circuits for the products. The release of such information is not to be construed as a warranty of or a grant of license under Ricoh's or any third party's intellectual property rights or any other rights.
- 5. The products listed in this document are intended and designed for use as general electronic components in standard applications (office equipment, telecommunication equipment, measuring instruments, consumer electronic products, amusement equipment etc.). Those customers intending to use a product in an application requiring extreme quality and reliability, for example, in a highly specific application where the failure or misoperation of the product could result in human injury or death (aircraft, spacevehicle, nuclear reactor control system, traffic control system, automotive and transportation equipment, combustion equipment, safety devices, life support system etc.) should first contact us.
- 6. We are making our continuous effort to improve the quality and reliability of our products, but semiconductor products are likely to fail with certain probability. In order to prevent any injury to persons or damages to property resulting from such failure, customers should be careful enough to incorporate safety measures in their design, such as redundancy feature, fire containment feature and fail-safe feature. We do not assume any liability or responsibility for any loss or damage arising from misuse or inappropriate use of the products.
- 7. Anti-radiation design is not implemented in the products described in this document.
- 8. The X-ray exposure can influence functions and characteristics of the products. Confirm the product functions and characteristics in the evaluation stage.
- 9. WLCSP products should be used in light shielded environments. The light exposure can influence functions and characteristics of the products under operation or storage.
- 10. There can be variation in the marking when different AOI (Automated Optical Inspection) equipment is used. In the case of recognizing the marking characteristic with AOI, please contact Ricoh sales or our distributor before attempting to use AOL
- 11. Please contact Ricoh sales representatives should you have any questions or comments concerning the products or the technical information.



<u>/</u>

Ricoh is committed to reducing the environmental loading materials in electrical devices with a view to contributing to the protection of human health and the environment. Ricoh has been providing RoHS compliant products since April 1, 2006 and Halogen-free products since April 1, 2012.

RICOH RICOH ELECTRONIC DEVICES CO., LTD.

http://www.e-devices.ricoh.co.jp/en/

Sales & Support Offices

RICOH ELECTRONIC DEVICES CO., LTD. Higashi-Shinagawa Office (International Sales) 3-32-3, Higashi-Shinagawa, Shinagawa-ku, Tokyo 140-8655, Japan Phone: +81-3-5479-2857 Fax: +81-3-5479-0502

RICOH EUROPE (NETHERLANDS) B.V. Semiconductor Support Centre Prof. W.H. Keesomlaan 1, 1183 DJ Amstelveen, The Netherlands Phone: +31-20-5474-309

RICOH INTERNATIONAL B.V. - German Branch Semiconductor Sales and Support Centre Oberrather Strasse 6, 40472 Düsseldorf, Germany Phone: +49-211-6546-0

RICOH ELECTRONIC DEVICES KOREA CO., LTD. 3F, Haesung Bldg, 504, Teheran-ro, Gangnam-gu, Se Phone: +82-2-2135-5700 Fax: +82-2-2051-5713

RICOH ELECTRONIC DEVICES SHANGHAI CO., LTD. Room 403, No.2 Building, No.690 Bibo Road, Pu Dong New District, Shanghai 201203, People's Republic of China

Phone: +86-21-5027-3200 Fax: +86-21-5027-3299

RICOH ELECTRONIC DEVICES CO., LTD.

 Taipei office

 Room 109, 10F-1, No.51, Hengyang Rd., Taipei City, Taiwan (R.O.C.)

 Phone: +886-2-2313-1621/1622

 Fax: +886-2-2313-1621/1622

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ricoh Electronics: R5101G001A-TR-FE R5101G002A-TR-FE R5101G006A-TR-FE