# Cree<sup>®</sup> J Series<sup>™</sup> 5050 6-V, 9-V, 24-V & 36-V LEDs

**PRODUCT DESCRIPTION** 

CREE 🔶

J Series<sup>™</sup> LEDs extend Cree's industry-leading portfolio of lighting-class LEDs to a broader set of applications. The J Series 5050 LEDs deliver high-power light output, high efficacy and excellent value in a reliable package. The J Series 5050 LEDs are optimized for medium-density lighting applications where high efficacy and long lifetime are critical, such as street lights, outdoor area and indoor directional lights.

#### **FEATURES**

- Industry-compatible size: 5.0 x 5.0 x 0.7 mm
- 6-V, 9-V, 24-V, and 36-V configurations
- Flux binned at 25 °C, chromaticity binned at 85 °C
- 6500 K-2700 K ANSI CCTs available
- 70, 80 & 90 CRI available for all CCTs
- RoHS and REACh compliant
- UL<sup>®</sup> recognized component (E495478)

D	D	0		i i	ОТ	CU		 ٨	,
Г	П	U	υ	υ	C I	30	IVI	А	

Draduat	Power	Test	Test	Typical Forward	4000 K, 70 CRI		3000 K	Maximum	
Product	Class	Temperature	Current	Voltage	Typical Flux	Typical Efficacy	Typical Flux	Typical Efficacy	Current
JR5050 6-V Q Class	5 W	25 °C	400 mA	5.8 V	425 lm	183 LPW	385 lm	166 LPW	1000 mA
JR5050 9-V Q Class	5 W	25 °C	260 mA	8.6 V	410 lm	183 LPW	367 lm	164 LPW	660 mA
JR5050 24-V Q Class	5 W	25 °C	100 mA	23.5 V	420 lm	179 LPW	380 lm	162 LPW	240 mA
JR5050 36-V Q Class	5 W	25 °C	65 mA	34.5 V	410 lm	183 LPW	367 lm	164 LPW	165 mA
JR5050 6-V P Class	5 W	25 °C	400 mA	5.77 V	442 lm	192 LPW	394 lm	171 LPW	1000 mA
JR5050 24-V P Class	5 W	25 °C	100 mA	23.08 V	442 lm	192 LPW	394 lm	171 LPW	240 mA

J Series<sup>™</sup> Products are sold exclusively by Cree Venture LED Company Limited ("Cree Venture"), regardless of geography. Any orders for J Series Products that are submitted to Cree, Inc. or any of its other subsidiaries will be directed to Cree Venture for acknowledgement and order fulfillment.

Copyright © 2018-2019 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree® and the Cree logo are registered trademarks and J Series™ is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC. J Series products are marketed by Cree, Inc. for the benefit of Cree Venture LED Company Limited.

### **TABLE OF CONTENTS**

	~
Order Code & Bin Code Formats	.3
Characteristics - JR5050 6-V Q Class	.4
Operating Limits - JR5050 6-V Q Class	.4
Flux Characteristics, Order Codes and Bins - JR5050 6-V	
Q Class	.5
Relative Luminous Flux vs. Current - JR5050 6-V Q Class	.6
Electrical Characteristics - JR5050 6-V Q Class	.6
Relative Chromaticity vs. Current - JR5050 6-V Q Class	.7
Relative Chromaticity vs. Temperature - JR5050 6-V Q Class	.7
Characteristics - JR5050 9-V Q Class	.8
Operating Limits - JR5050 9-V Q Class	.8
Flux Characteristics, Order Codes and Bins - JR5050 9-V	
Q Class	.9
Relative Luminous Flux vs. Current - JR5050 9-V Q Class 1	0
Electrical Characteristics - JR5050 9-V Q Class 1	0
Relative Chromaticity vs. Current - JR5050 9-V Q Class 1	1
Relative Chromaticity vs. Temperature - JR5050 9-V Q Class 1	1
Characteristics - JR5050 24-V Q Class 1	2
Operating Limits - JR5050 24-V O Class 1	2
Flux Characteristics. Order Codes and Bins - JR5050 24-V	
0 Class 1	3
Relative Luminous Flux vs. Current - JR5050 24-V O Class	4
Electrical Characteristics - JR5050 24-V O Class	4
Relative Chromaticity vs. Current - JR5050 24-V O Class 1	15
Relative Chromaticity vs. Temperature - IR5050.24-V O Class 1	15
Characteristics - IR5050 36-V O Class	16
Operating Limits - IP5050 36-V O Class	16
Elux Characteristics Order Codes and Pine IDE0E0.26 V	0
	-
Q Class	/
Relative Luminous Flux vs. Current - JR5050 36-V Q Class 1	.8
Electrical Characteristics - JR5050 36-V Q Class	.8
Relative Chromaticity vs. Current - JR5050 36-V Q Class	9
Relative Chromaticity vs. Temperature - JR5050 36-V Q Class 1	9
Characteristics - JR5050 6-V P Class 2	20
Operating Limits - JR5050 6-V P Class 2	20
Flux Characteristics, Order Codes and Bins - JR5050 6-V	
P Class	21
Relative Luminous Flux vs. Current - JR5050 6-V P Class 2	22
Electrical Characteristics - JR5050 6-V P Class 2	22

Relative Chromaticity vs. Current - JR5050 6-V P Class	23
Relative Chromaticity vs. Temperature - JR5050 6-V P Class	23
Characteristics - JR5050 24-V P Class	24
Operating Limits - JR5050 24-V P Class	24
Flux Characteristics, Order Codes and Bins - JR5050 24-V	
P Class	25
Relative Luminous Flux vs. Current - JR5050 24-V P Class	26
Electrical Characteristics - JR5050 24-V P Class	26
Relative Chromaticity vs. Current - JR5050 24-V P Class	27
Relative Chromaticity vs. Temperature - JR5050 24-V P Class	27
Relative Spectral Power Distribution	28
Relative Luminous Flux vs. Junction Temperature	29
Typical Spatial Distribution	29
Performance Groups - Luminous Flux	30
Performance Groups - Forward Voltage	31
Performance Groups - Chromaticity	32
Reflow Soldering Characteristics	41
Notes	42
Mechanical Dimensions	44
Tape & Reel	45
Packaging	46

Copyright © 2018-2019 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree® and the Cree logo are registered trademarks and J Series™ is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC. J Series products are marketed by Cree, Inc. for the benefit of Cree Venture LED Company Limited.

CREE 🔶

#### **ORDER CODE & BIN CODE FORMATS**

Order codes and bin codes for J Series 5050 LEDs are configured in the following manner:





Copyright © 2018-2019 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree® and the Cree logo are registered trademarks and J Series<sup>™</sup> is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC. J Series products are marketed by Cree, Inc. for the benefit of Cree Venture LED Company Limited.

#### **CHARACTERISTICS - JR5050 6-V Q CLASS**

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point	°C/W		3	
Viewing angle (FWHM)	degrees		120	
Temperature coefficient of voltage	mV/°C		-2	
ESD withstand voltage (JEDEC JS-001-2012)			Class 2	
DC forward current	mA			1000
Reverse voltage	V			5
Forward voltage (@ 400 mA, 25 °C)	V		5.8	6.0
LED junction temperature	°C			125
Operating temperature	°C	-40		105

#### **OPERATING LIMITS - JR5050 6-V Q CLASS**

The maximum forward current is determined by the thermal resistance between the LED junction and ambient.



### FLUX CHARACTERISTICS, ORDER CODES AND BINS - JR5050 6-V Q CLASS ( $I_F = 400 \text{ mA}, T_i = 25 \text{ °C}$ )

The following table provides order codes for J Series 5050 6-V Q Class LEDs. For a complete description of the order code nomenclature, please see the Order Code and Bin Code Formats section (page 3). For definitions of the chromaticity kits, please see the Performance Groups - Chromaticity section (page 32).

	Nominal CCT	Minimum CRI <sup>¢</sup>	Minimum Flux (lm) @ 25 °C	Typical Flux (lm) @ 25 °C	Typical Flux (lm) @ 85 °C*	Kitted 3-Step Order Code**
		70	350	415	376	JR5050AWT-Q-B65EB0000-N0000001
	6500 K	80	350	395	358	JR5050AWT-Q-H65EB0000-N0000001
		90	300	335	304	JR5050AWT-Q-U65EB0000-N0000001
		70	350	425	385	JR5050AWT-Q-B57EB0000-N0000001
	5700 K	80	350	405	367	JR5050AWT-Q-H57EB0000-N0000001
		90	300	345	313	JR5050AWT-Q-U57EB0000-N0000001
		70	350	425	385	JR5050AWT-Q-B50EB0000-N0000001
	5000 K	80	350	405	367	JR5050AWT-Q-H50EB0000-N0000001
		90	300	345	313	JR5050AWT-Q-U50EB0000-N0000001
		70	350	425	385	JR5050AWT-Q-B45EB0000-N0000001
	4500 K	80	350	405	367	JR5050AWT-Q-H45EB0000-N0000001
		90	300	345	313	JR5050AWT-Q-U45EB0000-N0000001
		70	350	425	385	JR5050AWT-Q-B40EB0000-N0000001
	4000 K	80	350	405	367	JR5050AWT-Q-H40EB0000-N0000001
		90	300	345	313	JR5050AWT-Q-U40EB0000-N0000001
		70	350	410	372	JR5050AWT-Q-B35EB0000-N0000001
	3500 K	80	350	395	358	JR5050AWT-Q-H35EB0000-N0000001
		90	300	330	299	JR5050AWT-Q-U35EB0000-N0000001
		70	350	405	367	JR5050AWT-Q-B30EB0000-N0000001
	3000 K	80	350	385	349	JR5050AWT-Q-H30EB0000-N0000001
		90	250	320	290	JR5050AWT-Q-U30EB0000-N0000001
		70	350	385	349	JR5050AWT-Q-B27EB0000-N0000001
	2700 K	80	300	365	331	JR5050AWT-Q-H27EB0000-N0000001
		90	250	305	277	JR5050AWT-Q-U27EB0000-N0000001

The order Customers

The order codes shown here are in a recently released order code format that is different than the previous format. Customers are strongly encouraged to use this new order code format; the previous format will soon be unavailable. See CVL-PCN-1903.

Notes:

- Cree Venture maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and ±2 on CRI measurements. See the Measurements section (page 42).
- Cree Venture J Series 5050 LED order codes specify only a minimum flux bin and not a maximum. Cree Venture may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity restrictions specified by the order code.
- CRI R9 minimum is 0 for 80 CRI minimum LEDs and 50 for 90 CRI minimum LEDs, with a ±3 tolerance.
- \* Flux values @ 85 °C are calculated and for reference only.
- \*\* Contact your Cree sales representative for kitted 3-step order code details.

### **RELATIVE LUMINOUS FLUX VS. CURRENT - JR5050 6-V Q CLASS**



#### **ELECTRICAL CHARACTERISTICS - JR5050 6-V Q CLASS**





### **RELATIVE CHROMATICITY VS. CURRENT - JR5050 6-V Q CLASS**



#### **RELATIVE CHROMATICITY VS. TEMPERATURE - JR5050 6-V Q CLASS**



Copyright © 2018-2019 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree® and the Cree logo are registered trademarks and J Series™ is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC. J Series products are marketed by Cree, Inc. for the benefit of Cree Venture LED Company Limited.

#### **CHARACTERISTICS - JR5050 9-V Q CLASS**

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point	°C/W		3	
Viewing angle (FWHM)	degrees		120	
Temperature coefficient of voltage	mV/°C		-2.7	
ESD withstand voltage (JEDEC JS-001-2012)			Class 2	
DC forward current	mA			660
Reverse voltage	V			5
Forward voltage (@ 260 mA, 25 °C)	V		8.6	9.5
LED junction temperature	°C			125
Operating temperature	°C	-40		105

#### **OPERATING LIMITS - JR5050 9-V Q CLASS**

The maximum forward current is determined by the thermal resistance between the LED junction and ambient.



### FLUX CHARACTERISTICS, ORDER CODES AND BINS - JR5050 9-V Q CLASS ( $I_F = 260 \text{ mA}, T_i = 25 \text{ °C}$ )

The following table provides order codes for J Series 5050 9-V Q Class LEDs. For a complete description of the order code nomenclature, please see the Order Code and Bin Code Formats section (page 3). For definitions of the chromaticity kits, please see the Performance Groups - Chromaticity section (page 32).

	Nominal CCT	Minimum CRI <sup>¢</sup>	Minimum Flux (lm) @ 25 °C	Typical Flux (lm) @ 25 °C	Typical Flux (lm) @ 85 °C*	Kitted 3-Step Order Code**
		70	350	400	364	JR5050AWT-Q-B65EC0000-N0000001
	6500 K	80	300	377	343	JR5050AWT-Q-H65EC0000-N0000001
		90	250	320	291	JR5050AWT-Q-U65EC0000-N0000001
		70	350	410	373	JR5050AWT-Q-B57EC0000-N0000001
	5700 K	80	300	387	352	JR5050AWT-Q-H57EC0000-N0000001
		90	250	330	300	JR5050AWT-Q-U57EC0000-N0000001
		70	350	410	373	JR5050AWT-Q-B50EC0000-N0000001
	5000 K	80	300	387	352	JR5050AWT-Q-H50EC0000-N0000001
		90	250	330	300	JR5050AWT-Q-U50EC0000-N0000001
		70	350	410	373	JR5050AWT-Q-B45EC0000-N0000001
	4500 K	80	300	387	352	JR5050AWT-Q-H45EC0000-N0000001
		90	250	330	300	JR5050AWT-Q-U45EC0000-N0000001
		70	350	410	373	JR5050AWT-Q-B40EC0000-N0000001
	4000 K	80	300	387	352	JR5050AWT-Q-H40EC0000-N0000001
		90	250	330	300	JR5050AWT-Q-U40EC0000-N0000001
		70	350	400	364	JR5050AWT-Q-B35EC0000-N0000001
	3500 K	80	300	377	343	JR5050AWT-Q-H35EC0000-N0000001
		90	250	320	291	JR5050AWT-Q-U35EC0000-N0000001
		70	350	390	355	JR5050AWT-Q-B30EC0000-N0000001
	3000 K	80	300	367	334	JR5050AWT-Q-H30EC0000-N0000001
		90	250	315	286	JR5050AWT-Q-U30EC0000-N0000001
		70	300	372	338	JR5050AWT-Q-B27EC0000-N0000001
	2700 K	80	300	352	320	JR5050AWT-Q-H27EC0000-N0000001
		90	250	298	271	JR5050AWT-Q-U27EC0000-N0000001

The order codes shown here are in a recently released order code format that is different than the previous format. Customers are strongly encouraged to use this new order code format; the previous format will soon be unavailable. See CVL-PCN-1903.

Notes:

- Cree Venture maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and ±2 on CRI measurements. See the Measurements section (page 42).
- Cree Venture J Series 5050 LED order codes specify only a minimum flux bin and not a maximum. Cree Venture may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity restrictions specified by the order code.
- CRI R9 minimum is 0 for 80 CRI minimum LEDs and 50 for 90 CRI minimum LEDs, with a ±3 tolerance.
- \* Flux values @ 85 °C are calculated and for reference only.
- \*\* Contact your Cree sales representative for kitted 3-step order code details.

### **RELATIVE LUMINOUS FLUX VS. CURRENT - JR5050 9-V Q CLASS**



#### **ELECTRICAL CHARACTERISTICS - JR5050 9-V Q CLASS**





CREE 🔶



#### **RELATIVE CHROMATICITY VS. TEMPERATURE - JR5050 9-V Q CLASS**



Copyright © 2018-2019 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree<sup>®</sup> and the Cree logo are registered trademarks and J Series™ is a trademark of Cree, Inc. UL<sup>®</sup> and the UR logo are registered trademarks of UL LLC. J Series products are marketed by Cree, Inc. for the benefit of Cree Venture LED Company Limited.

#### **CHARACTERISTICS - JR5050 24-V Q CLASS**

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point	°C/W		3	
Viewing angle (FWHM)	degrees		120	
Temperature coefficient of voltage	mV/°C		-6.7	
ESD withstand voltage (JEDEC JS-001-2012			Class 2	
DC forward current	mA			240
Reverse voltage	V			5
Forward voltage (@ 100 mA, 25 °C)	V		23.5	24.5
LED junction temperature	°C			125
Operating temperature	°C	-40		105

#### **OPERATING LIMITS - JR5050 24-V Q CLASS**

The maximum forward current is determined by the thermal resistance between the LED junction and ambient.



### FLUX CHARACTERISTICS, ORDER CODES AND BINS - JR5050 24-V Q CLASS ( $I_F = 100 \text{ mA}, T_i = 25 \text{ °C}$ )

The following table provides order codes for J Series 5050 24-V Q Class LEDs. For a complete description of the order code nomenclature, please see the Order Code and Bin Code Formats section (page 3). For definitions of the chromaticity kits, please see the Performance Groups - Chromaticity section (page 32).

	Nominal CCT	Minimum CRI <sup>¢</sup>	Minimum Flux (lm) @ 25 °C	Typical Flux (lm) @ 25 °C	Typical Flux (lm) @ 85 °C*	Kitted 3-Step Order Code**
		70	350	420	383	JR5050AWT-Q-B65EH0000-N0000001
	6500 K	80	350	400	365	JR5050AWT-Q-H65EH0000-N0000001
		90	300	340	310	JR5050AWT-Q-U65EH0000-N0000001
		70	350	420	383	JR5050AWT-Q-B57EH0000-N0000001
	5700 K	80	350	400	365	JR5050AWT-Q-H57EH0000-N0000001
		90	300	340	310	JR5050AWT-Q-U57EH0000-N0000001
		70	350	420	383	JR5050AWT-Q-B50EH0000-N0000001
	5000 K	80	350	400	365	JR5050AWT-Q-H50EH0000-N0000001
		90	300	340	310	JR5050AWT-Q-U50EH0000-N0000001
		70	350	420	383	JR5050AWT-Q-B45EH0000-N0000001
	4500 K	80	350	400	365	JR5050AWT-Q-H45EH0000-N0000001
		90	300	340	310	JR5050AWT-Q-U45EH0000-N0000001
		70	350	420	383	JR5050AWT-Q-B40EH0000-N0000001
	4000 K	80	350	400	365	JR5050AWT-Q-H40EH0000-N0000001
		90	300	340	310	JR5050AWT-Q-U40EH0000-N0000001
		70	350	410	374	JR5050AWT-Q-B35EH0000-N0000001
	3500 K	80	350	390	356	JR5050AWT-Q-H35EH0000-N0000001
		90	300	330	301	JR5050AWT-Q-U35EH0000-N0000001
		70	350	400	365	JR5050AWT-Q-B30EH0000-N0000001
	3000 K	80	300	380	347	JR5050AWT-Q-H30EH0000-N0000001
		90	250	320	292	JR5050AWT-Q-U30EH0000-N0000001
		70	300	385	351	JR5050AWT-Q-B27EH0000-N0000001
	2700 K	80	300	365	333	JR5050AWT-Q-H27EH0000-N0000001
		90	250	310	283	JR5050AWT-Q-U27EH0000-N0000001

-

The order codes shown here are in a recently released order code format that is different than the previous format. Customers are strongly encouraged to use this new order code format; the previous format will soon be unavailable. See CVL-PCN-1903.

Notes:

- Cree Venture maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and ±2 on CRI measurements. See the Measurements section (page 42).
- Cree Venture J Series 5050 LED order codes specify only a minimum flux bin and not a maximum. Cree Venture may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity restrictions specified by the order code.
- CRI R9 minimum is 0 for 80 CRI minimum LEDs and 50 for 90 CRI minimum LEDs, with a ±3 tolerance.
- \* Flux values @ 85 °C are calculated and for reference only.
- \*\* Contact your Cree sales representative for kitted 3-step order code details.

### **RELATIVE LUMINOUS FLUX VS. CURRENT - JR5050 24-V Q CLASS**



#### **ELECTRICAL CHARACTERISTICS - JR5050 24-V Q CLASS**





### **RELATIVE CHROMATICITY VS. CURRENT - JR5050 24-V Q CLASS**



### **RELATIVE CHROMATICITY VS. TEMPERATURE - JR5050 24-V Q CLASS**



#### **CHARACTERISTICS - JR5050 36-V Q CLASS**

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point	°C/W		3	
Viewing angle (FWHM)	degrees		120	
Temperature coefficient of voltage	mV/°C		-10	
ESD withstand voltage (JEDEC JS-001-2012)			Class 2	
DC forward current	mA			165
Reverse voltage	V			5
Forward voltage (@ 65 mA, 25 °C)	V		34.5	36.0
LED junction temperature	°C			125
Operating temperature	°C	-40		105

#### **OPERATING LIMITS - JR5050 36-V Q CLASS**

The maximum forward current is determined by the thermal resistance between the LED junction and ambient.



### FLUX CHARACTERISTICS, ORDER CODES AND BINS - JR5050 36-V Q CLASS ( $I_F = 65 \text{ mA}, T_i = 25 \text{ °C}$ )

The following table provides order codes for J Series 5050 36-V Q Class LEDs. For a complete description of the order code nomenclature, please see the Order Code and Bin Code Formats section (page 3). For definitions of the chromaticity kits, please see the Performance Groups - Chromaticity section (page 32).

	Nominal CCT	Minimum CRI <sup>¢</sup>	Minimum Flux (lm) @ 25 °C	Typical Flux (lm) @ 25 °C	Typical Flux (lm) @ 85 °C*	Kitted 3-Step Order Code**
		70	350	400	364	JR5050AWT-Q-B65EN0000-N0000001
	6500 K	80	300	377	343	JR5050AWT-Q-H65EN0000-N0000001
		90	250	320	291	JR5050AWT-Q-U65EN0000-N0000001
		70	350	410	373	JR5050AWT-Q-B57EN0000-N0000001
	5700 K	80	300	387	352	JR5050AWT-Q-H57EN0000-N0000001
		90	250	330	300	JR5050AWT-Q-U57EN0000-N0000001
		70	350	410	373	JR5050AWT-Q-B50EN0000-N0000001
	5000 K	80	300	387	352	JR5050AWT-Q-H50EN0000-N0000001
		90	250	330	300	JR5050AWT-Q-U50EN0000-N0000001
		70	350	410	373	JR5050AWT-Q-B45EN0000-N0000001
	4500 K	80	300	387	352	JR5050AWT-Q-H45EN0000-N0000001
		90	250	330	300	JR5050AWT-Q-U45EN0000-N0000001
		70	350	410	373	JR5050AWT-Q-B40EN0000-N0000001
	4000 K	80	300	387	352	JR5050AWT-Q-H40EN0000-N0000001
		90	250	330	300	JR5050AWT-Q-U40EN0000-N0000001
		70	350	400	364	JR5050AWT-Q-B35EN0000-N0000001
	3500 K	80	300	377	343	JR5050AWT-Q-H35EN0000-N0000001
		90	250	320	291	JR5050AWT-Q-U35EN0000-N0000001
		70	350	390	355	JR5050AWT-Q-B30EN0000-N0000001
	3000 K	80	300	367	334	JR5050AWT-Q-H30EN0000-N0000001
		90	250	315	286	JR5050AWT-Q-U30EN0000-N0000001
		70	300	372	338	JR5050AWT-Q-B27EN0000-N0000001
	2700 K	80	300	352	320	JR5050AWT-Q-H27EN0000-N0000001
		90	250	298	271	JR5050AWT-Q-U27EN0000-N0000001

The order codes shown here are in a recently released order code format that is different than the previous format. Customers are strongly encouraged to use this new order code format; the previous format will soon be unavailable. See CVL-PCN-1903.

Notes:

- Cree Venture maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and ±2 on CRI measurements. See the Measurements section (page 42).
- Cree Venture J Series 5050 LED order codes specify only a minimum flux bin and not a maximum. Cree Venture may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity restrictions specified by the order code.
- CRI R9 minimum is 0 for 80 CRI minimum LEDs and 50 for 90 CRI minimum LEDs, with a ±3 tolerance.
- \* Flux values @ 85 °C are calculated and for reference only.
- \*\* Contact your Cree sales representative for kitted 3-step order code details.



### **RELATIVE LUMINOUS FLUX VS. CURRENT - JR5050 36-V Q CLASS**



#### **ELECTRICAL CHARACTERISTICS - JR5050 36-V Q CLASS**





### **RELATIVE CHROMATICITY VS. CURRENT - JR5050 36-V Q CLASS**



#### **RELATIVE CHROMATICITY VS. TEMPERATURE - JR5050 36-V Q CLASS**



#### **CHARACTERISTICS - JR5050 6-V P CLASS**

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point	°C/W		3	
Viewing angle (FWHM)	degrees		120	
Temperature coefficient of voltage	mV/°C		-1.8	
ESD withstand voltage (JEDEC JS-001-2012)			Class 2	
DC forward current	mA			1000
Reverse voltage	V			5
Forward voltage (@ 400 mA, 25 °C)	V		5.77	6.0
LED junction temperature	°C			125
Operating temperature	°C	-40		105

#### **OPERATING LIMITS - JR5050 6-V P CLASS**

The maximum forward current is determined by the thermal resistance between the LED junction and ambient.



### FLUX CHARACTERISTICS, ORDER CODES AND BINS - JR5050 6-V P CLASS (I<sub>F</sub> = 400 mA, T<sub>i</sub> = 25 °C)

The following table provides order codes for J Series 5050 6-V P Class LEDs. For a complete description of the order code nomenclature, please see the Order Code and Bin Code Formats section (page 3). For definitions of the chromaticity kits, please see the Performance Groups - Chromaticity section (page 32).

Nominal CCT	Minimum CRI <sup>¢</sup>	Minimum Flux (lm) @ 25 °C	Typical Flux (lm) @ 25 °C	Typical Flux (lm) @ 85 °C*	Kitted 3-Step Order Code**
	70	400	442	405	JR5050AWT-P-B65EB0000-N0000001
6500 K	80	350	414	380	JR5050AWT-P-H65EB0000-N0000001
	90	300	351	322	JR5050AWT-P-U65EB0000-N0000001
	70	400	442	405	JR5050AWT-P-B57EB0000-N0000001
5700 K	80	350	414	380	JR5050AWT-P-H57EB0000-N0000001
	90	300	351	322	JR5050AWT-P-U57EB0000-N0000001
	70	400	442	405	JR5050AWT-P-B50EB0000-N0000001
5000 K	80	350	414	380	JR5050AWT-P-H50EB0000-N0000001
	90	300	351	322	JR5050AWT-P-U50EB0000-N0000001
	70	400	442	405	JR5050AWT-P-B40EB0000-N0000001
4000 K	80	350	414	380	JR5050AWT-P-H40EB0000-N0000001
	90	300	351	322	JR5050AWT-P-U40EB0000-N0000001
	70	350	427	392	JR5050AWT-P-B35EB0000-N0000001
3500 K	80	350	404	371	JR5050AWT-P-H35EB0000-N0000001
	90	300	341	313	JR5050AWT-P-U35EB0000-N0000001
	70	350	417	383	JR5050AWT-P-B30EB0000-N0000001
3000 K	80	350	394	361	JR5050AWT-P-H30EB0000-N0000001
	90	300	331	304	JR5050AWT-P-U30EB0000-N0000001
	70	350	402	369	JR5050AWT-P-B27EB0000-N0000001
2700 K	80	350	379	348	JR5050AWT-P-H27EB0000-N0000001
	90	250	321	294	JR5050AWT-P-U27EB0000-N0000001

Notes:

- Cree Venture maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and ±2 on CRI measurements. See the Measurements section (page 42).
- Cree Venture J Series 5050 LED order codes specify only a minimum flux bin and not a maximum. Cree Venture may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity restrictions specified by the order code.
- CRI R9 minimum is 0 for 80 CRI minimum LEDs and 50 for 90 CRI minimum LEDs, with a ±3 tolerance.
- \* Flux values @ 85 °C are calculated and for reference only.
- \*\* Contact your Cree sales representative for kitted 3-step order code details.

### **RELATIVE LUMINOUS FLUX VS. CURRENT - JR5050 6-V P CLASS**



#### **ELECTRICAL CHARACTERISTICS - JR5050 6-V P CLASS**





### **RELATIVE CHROMATICITY VS. CURRENT - JR5050 6-V P CLASS**



#### **RELATIVE CHROMATICITY VS. TEMPERATURE - JR5050 6-V P CLASS**



Copyright © 2018-2019 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree® and the Cree logo are registered trademarks and J Series™ is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC. J Series products are marketed by Cree, Inc. for the benefit of Cree Venture LED Company Limited.

#### **CHARACTERISTICS - JR5050 24-V P CLASS**

Characteristics	Unit	Minimum	Typical	Maximum
Thermal resistance, junction to solder point	°C/W		3.2	
Viewing angle (FWHM)	degrees		120	
Temperature coefficient of voltage	mV/°C		-8.5	
ESD withstand voltage (JEDEC JS-001-2012			Class 2	
DC forward current	mA			240
Reverse voltage	V			5
Forward voltage (@ 100 mA, 25 °C)	V		23.08	24.5
LED junction temperature	°C			125
Operating temperature	°C	-40		105

#### **OPERATING LIMITS - JR5050 24-V P CLASS**

The maximum forward current is determined by the thermal resistance between the LED junction and ambient.



### FLUX CHARACTERISTICS, ORDER CODES AND BINS - JR5050 24-V P CLASS ( $I_F = 100 \text{ mA}, T_i = 25 \text{ °C}$ )

The following table provides order codes for J Series 5050 24-V P Class LEDs. For a complete description of the order code nomenclature, please see the Order Code and Bin Code Formats section (page 3). For definitions of the chromaticity kits, please see the Performance Groups - Chromaticity section (page 32).

	Nominal CCT	Minimum CRI <sup>¢</sup>	Minimum Flux (lm) @ 25 °C	Typical Flux (lm) @ 25 °C	Typical Flux (lm) @ 85 °C*	Kitted 3-Step Order Code**
		70	400	442	405	JR5050AWT-P-B65EH0000-N0000001
	6500 K	80	350	414	380	JR5050AWT-P-H65EH0000-N0000001
		90	300	351	322	JR5050AWT-P-U65EH0000-N0000001
		70	400	442	405	JR5050AWT-P-B57EH0000-N0000001
	5700 K	80	350	414	380	JR5050AWT-P-H57EH0000-N0000001
		90	300	351	322	JR5050AWT-P-U57EH0000-N0000001
		70	400	442	405	JR5050AWT-P-B50EH0000-N0000001
	5000 K	80	350	414	380	JR5050AWT-P-H50EH0000-N0000001
		90	300	351	322	JR5050AWT-P-U50EH0000-N0000001
		70	400	442	405	JR5050AWT-P-B40EH0000-N0000001
	4000 K	80	350	414	380	JR5050AWT-P-H40EH0000-N0000001
		90	300	351	322	JR5050AWT-P-U40EH0000-N0000001
		70	350	427	392	JR5050AWT-P-B35EH0000-N0000001
	3500 K	80	350	404	371	JR5050AWT-P-H35EH0000-N0000001
		90	300	341	313	JR5050AWT-P-U35EH0000-N0000001
		70	350	417	383	JR5050AWT-P-B30EH0000-N0000001
	3000 K	80	350	394	361	JR5050AWT-P-H30EH0000-N0000001
		90	300	331	304	JR5050AWT-P-U30EH0000-N0000001
		70	350	402	369	JR5050AWT-P-B27EH0000-N0000001
	2700 K	80	350	379	348	JR5050AWT-P-H27EH0000-N0000001
		90	250	321	294	JR5050AWT-P-U27EH0000-N0000001

Notes:

- Cree Venture maintains a tolerance of ±7% on flux and power measurements, ±0.005 on chromaticity (CCx, CCy) measurements and ±2 on CRI measurements. See the Measurements section (page 42).
- Cree Venture J Series 5050 LED order codes specify only a minimum flux bin and not a maximum. Cree Venture may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity restrictions specified by the order code.
- CRI R9 minimum is 0 for 80 CRI minimum LEDs and 50 for 90 CRI minimum LEDs, with a ±3 tolerance.
- \* Flux values @ 85 °C are calculated and for reference only.
- \*\* Contact your Cree sales representative for kitted 3-step order code details.

### **RELATIVE LUMINOUS FLUX VS. CURRENT - JR5050 24-V P CLASS**



#### **ELECTRICAL CHARACTERISTICS - JR5050 24-V P CLASS**





### **RELATIVE CHROMATICITY VS. CURRENT - JR5050 24-V P CLASS**



#### **RELATIVE CHROMATICITY VS. TEMPERATURE - JR5050 24-V P CLASS**



CREE 🔶

### **RELATIVE SPECTRAL POWER DISTRIBUTION**



Copyright © 2018-2019 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree® and the Cree logo are registered trademarks and J Series™ is a trademark of Cree, Inc. UL® and the UR logo are registered trademarks of UL LLC. J Series products are marketed by Cree, Inc. for the benefit of Cree Venture LED Company Limited.

### **RELATIVE LUMINOUS FLUX VS. JUNCTION TEMPERATURE**



### **TYPICAL SPATIAL DISTRIBUTION**



### PERFORMANCE GROUPS - LUMINOUS FLUX (T<sub>i</sub> = 25 °C)

J Series JR5050 LEDs are tested for luminous flux at the following current levels.

JR5050 LED	Tested For Luminous Flux At		
6 V	400 mA		
9 V	260 mA		
24 V	100 mA		
36 V	65 mA		

Once tested, J Series JR5050 LEDs are placed into one of the following luminous-flux groups.

Group Code	Minimum Luminous Flux (Im)	Maximum Luminous Flux (Im)
P4	250	300
Q2	300	350
Q4	350	400
R2	400	450
R4	450	500

### **PERFORMANCE GROUPS - FORWARD VOLTAGE (T<sub>i</sub> = 25 °C)**

J Series 5050 LEDs are tested for forward voltage and placed into one of the following voltage bins.

The following voltage bins are indicated in the Forward Voltage Bin field in the bin code for JR5050 6-V LEDs.

Voltage Bin	Minimum Forward Voltage (V)	Maximum Forward Voltage (V)
BN	5.6	5.8
BP	5.8	6

The following voltage bins are indicated in the Forward Voltage Bin field in the bin code for JR5050 9-V LEDs.

Voltage Bin	Minimum Forward Voltage (V)	Maximum Forward Voltage (V)
СТ	8.0	8.5
CU	8.5	9.0
CV	9.0	9.5

The following voltage bins are indicated in the Forward Voltage Bin field in the bin code for JR5050 24-V LEDs.

Voltage Bin	Minimum Forward Voltage (V)	Maximum Forward Voltage (V)
HC	21.5	22.5
HD	22.5	23.5
HE	23.5	24.5

The following voltage bins are indicated in the Forward Voltage Bin field in the bin code for JR5050 36-V LEDs.

Voltage Bin	Minimum Forward Voltage (V)	Maximum Forward Voltage (V)
NF	33	34
NG	34	35
NH	35	36

### **PERFORMANCE GROUPS - CHROMATICITY (T<sub>i</sub> = 85 °C)**

J Series 5050 LEDs are tested for chromaticity and placed into one of the regions defined by the following bounding coordinates.





сст	MacAdam Ellipse	Included Bins	Center Point		Major Axis	Minor Axis	Detation Angle (°)
			x	у	а	b	Rotation Angle ()
6500 K	3-step	1G0	0.3123	0.3282	0.00669	0.00285	58.57
	Kitted 3-step	1G0, 1EA, 1EB, 1EC, 1ED	0.3123	0.3282	0.01115	0.00475	58.57

CREE 🔶



сст	MacAdam Ellipse	Included Bins	Center Point		Major Axis	Minor Axis	Dotation Angle (°)
			x	у	а	b	Kotation Angle ()
	3-step	2G0	0.3287	0.3417	0.00746	0.00320	59.09
5700 K	Kitted 3-step	2G0, 2EA, 2EB, 2EC, 2ED	0.3287	0.3417	0.01243	0.00533	59.09

CREE 🔶



сст	CT Maa A dam Ellinga Included Ding		Center Point		Major Axis	Minor Axis	Dotation Angle (°)
CCI			x	У	а	b	Rotation Angle ()
	3-step	3G0	0.3447	0.3553	0.00822	0.00354	59.62
5000 K	Kitted 3-step	3G0, 3EA, 3EB, 3EC, 3ED	0.3447	0.3553	0.01370	0.00590	59.62

### PERFORMANCE GROUPS - CHROMATICITY - CONTINUED (T<sub>i</sub> = 85 °C)

CREE 🔶



COT	CCT MasAdam Ellinos		Center	r Point	Major Axis	Minor Axis	Dotation Angle (°)
CCI			x	у	а	b	Rotation Angle ()
	3-step	4G0	0.3613	0.3670	0.00756	0.00338	57.58
4500 K	Kitted 3-step	4G0, 4EA, 4EB, 4EC, 4ED	0.3613	0.3670	0.01260	0.00563	57.58

CREE 🔶



сст			Cente	r Point	Major Axis	Minor Axis	Dotation Angle (°)
001			x	У	а	b	Kotation Angle ()
	3-step	5GA, 5GB	0.3818	0.3797	0.00939	0.00402	53.72
4000 K	Kitted 3-step	5GA, 5GB, 5EA, 5EB, 5EC, 5ED	0.3818	0.3797	0.01565	0.00670	53.72



	Included Dine	Center Point		Major Axis	Minor Axis	Dotation Angle (°)	
		x	у	а	b	Rotation Angle ()	
	3-step	6GA, 6GB	0.4073	0.3917	0.00927	0.00414	53.22
3500 K	Kitted 3-step	6GA, 6GB, 6EA, 6EB, 6EC, 6ED	0.4073	0.3917	0.01545	0.00690	53.22

CREE 🔶



COT	CCT MagAdam Ellinga Inglu		Center Point		Major Axis	Minor Axis	Detation Angle (°)
			x	у	а	b	Rotation Angle ()
	3-step	7GA, 7GB	0.4338	0.4030	0.00834	0.00408	53.22
3000 K	Kitted 3-step	7GA, 7GB, 7EA, 7EB, 7EC, 7ED	0.4338	0.4030	0.01390	0.00680	53.22

CREE 🔶



COT	Maa Adam Ellinaa	o A dam Ellingo Included Pino		Center Point		Minor Axis	Detetion Angle (°)
CCI			x	у	а	b	Kotation Angle ()
	3-step	8GA, 8GB	0.4578	0.4101	0.00810	0.00420	53.70
2700 K	Kitted 3-step	8GA, 8GB, 8EA, 8EB, 8EC, 8ED	0.4578	0.4101	0.01350	0.00700	53.70

#### **REFLOW SOLDERING CHARACTERISTICS**

In testing, Cree Venture has found J Series 5050 LEDs to be compatible with JEDEC J-STD-020C, using the parameters listed below. As a general guideline, Cree Venture recommends that users follow the recommended soldering profile provided by the manufacturer of the solder paste used, and therefore it is the lamp or luminaire manufacturer's responsibility to determine applicable soldering requirement.

Note that this general guideline may not apply to all PCB designs and configurations of reflow soldering equipment.



IPC/JEDEC J-STD-020C

Profile Feature	Lead-Free Solder
Temperature Min. (Ts <sub>min</sub> )	150 °C
Temperature Max. (Ts <sub>max</sub> )	200 °C
Time (ts) from Ts <sub>min</sub> to Ts <sub>max</sub>	60-120 seconds
Ramp-Up Rate ( $T_L$ to $T_p$ )	3 °C/second
Liquidus Temperature ( $T_L$ )	217 °C
Time (t <sub>L</sub> ) Maintained Above T <sub>L</sub>	60-150 seconds
Peak Package Body Temperature (Tp)	260 °C max.
Time (tp) Within 5 °C of the Specified Classification Temperature (Tc)	30 seconds max.
Ramp-Down Rate $(T_p \text{ to } T_L)$	6 °C/second max.
Time 25 °C to Peak Temperature	8 minutes max.

Note: All temperatures refer to the topside of the package, measured on the package body surface.

#### **NOTES**

#### Measurements

The luminous flux, radiant power, chromaticity, forward voltage and CRI measurements in this document are binning specifications only and solely represent product measurements as of the date of shipment. These measurements will change over time based on a number of factors that are not within Cree Venture's control and are not intended or provided as operational specifications for the products. Calculated values are provided for informational purposes only and are not intended or provided as specifications.

#### **Pre-Release Qualification Testing**

Please read the J Series Reliability Overview for the details of the pre-release qualification testing for J Series LEDs.

#### Lumen Maintenance

Cree Venture uses standardized IES LM-80-08 and TM-21-11 methods for collecting long-term data and extrapolating LED lumen maintenance. For information on the specific LM-80 data sets available for this LED, refer to the public J Series LM-80 results document.

Please read the Thermal Management application note for details on how thermal design, ambient temperature, and drive current affect the LED junction temperature.

#### **Moisture Sensitivity**

Cree Venture recommends keeping J Series 5050 LEDs in the provided, resealable moisture-barrier packaging (MBP) until immediately prior to soldering. Unopened MBP that contains J Series 5050 LEDs does not need special storage for moisture sensitivity.

Once the MBP is opened, J Series 5050 LEDs should be handled and stored as MSL 3 per JEDEC J-STD-033, meaning they have limited exposure time before damage to the LED may occur during the soldering operation. The table on the right specifies the maximum exposure time in days depending on temperature and humidity conditions. LEDs with exposure time longer than the specified maximums must be baked according to the baking conditions listed below.

Moisture	_	Maximum Percent Relative Humidity						
Level	Temp.	50%	60%	70%	80%	90%		
Level 3	35 °C	8	5	1	0.5	0.5		
Level 3	30 °C	11	7	1	1	1		
Level 3	25 °C	14	10	2	1	1		
Level 3	20 °C	20	13	2	1	1		

#### **Baking Conditions**

It is not necessary to bake all J Series 5050 LEDs. Only the LEDs that meet all of the following criteria must be baked:

- 1. LEDs that have been removed from the original MBP.
- 2. LEDs that have been exposed to a humid environment longer than listed in the Moisture Sensitivity section above.
- 3. LEDs that have not been soldered.

LEDs should be baked at 60 °C for 24 hours. LEDs may be baked in the original reels. Remove LEDs from the MBP before baking. Do not bake parts at temperatures higher than 60 °C. This baking operation resets the exposure time as defined in the Moisture Sensitivity section above.

#### **NOTES - CONTINUED**

#### **RoHS Compliance**

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree representative or from the Product Ecology section of the Cree website.

#### **REACh Compliance**

REACh substances of very high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Cree representative to insure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

#### **UL® Recognized Component**

This product meets the requirements to be considered a UL Recognized Component with Level 4 enclosure consideration. The LED package or a portion thereof has been investigated as a fire and electrical enclosure per ANSI/UL 8750.

#### **Vision Advisory**

WARNING: Do not look at an exposed lamp in operation. Eye injury can result. For more information about LEDs and eye safety, please refer to the J Series LED Eye Safety application note.

CREE 🔶

### **MECHANICAL DIMENSIONS**

Thermal vias, if present, are not shown on these drawings. All measurements are  $\pm 0.2$  mm unless otherwise indicated.



All measurements are ±0.1 mm unless otherwise indicated.



**Recommended Solder Pad** 



Recommended Stencil Pattern (Shaded Area Is Open)

#### **TAPE & REEL**

All Cree Venture carrier tapes conform to EIA-481D, Automated Component Handling Systems Standard.

All dimensions in mm.







#### PACKAGING

#### **Unpackaged Reel**



Label with Cree Venture Order - Code, Lot Number, Quantity, Product Parameters



#### **PACKAGING - CONTINUED**

J Series 5050 LEDs are packaged in boxes for shipment. Box sizes and the number of reels per box are as follows.

Box	Box Dimensions	Maximum Number of Reels per Box
1	250 x 210 x 30 mm	2
2	250 x 210 x 50 mm	3
3	530 x 230 x 275 mm	32
4	530 x 443 x 275 mm	64

Each box has at least one label (shown as a white square in the diagrams below) showing the order code, lot number, quantity, and product parameters.



Box 3



Box 2

Box 4



# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Cree, Inc.:

JR5050AWT-00-0000-000D0BQ227E JR5050AWT-00-0000-000D0BQ230E JR5050AWT-00-0000-000D0BQ435E JR5050AWT-00-0000-000D0BQ440E JR5050AWT-00-0000-000D0BQ445E JR5050AWT-00-0000-000D0BQ450E JR5050AWT-00-0000-000N0UP435E JR5050AWT-00-0000-000N0UP440E JR5050AWT-00-0000-000N0UP445E JR5050AWT-00-0000-000N0UP450E JR5050AWT-00-0000-000N0UP457E JR5050AWT-00-0000-000N0UP465E JR5050AWT-00-0000-000N0HQ257E JR5050AWT-00-0000-000N0HQ245E JR5050AWT-00-0000-000N0HQ250E JR5050AWT-00-0000-000N0HQ265E JR5050AWT-00-0000-000N0UP227E JR5050AWT-00-0000-000N0UP230E JR5050AWT-00-0000-000N0BQ257E JR5050AWT-00-0000-000N0BQ265E JR5050AWT-00-0000-000N0HP427E JR5050AWT-00-0000-000N0HP430E JR5050AWT-00-0000-000N0HQ235E JR5050AWT-00-0000-000N0HQ240E JR5050AWT-00-0000-000N0BP427E JR5050AWT-00-0000-000N0BQ230E JR5050AWT-00-0000-000N0BQ235E JR5050AWT-00-0000-000N0BQ240E JR5050AWT-00-0000-000N0BQ245E JR5050AWT-00-0000-000N0BQ250E JR5050AWT-00-0000-000H0UP435E JR5050AWT-00-0000-000H0UQ240E JR5050AWT-00-0000-000H0UQ245E JR5050AWT-00-0000-000H0UQ250E JR5050AWT-00-0000-000H0UQ257E JR5050AWT-00-0000-000H0UQ265E JR5050AWT-00-0000-000H0HQ445E JR5050AWT-00-0000-000H0HQ450E JR5050AWT-00-0000-000H0HQ457E JR5050AWT-00-0000-000H0HQ465E JR5050AWT-00-0000-000H0UP427E JR5050AWT-00-0000-000H0UP430E JR5050AWT-00-0000-000H0BQ457E JR5050AWT-00-0000-000H0BQ465E JR5050AWT-00-0000-000H0HQ227E JR5050AWT-00-0000-000H0HQ230E JR5050AWT-00-0000-000H0HQ435E JR5050AWT-00-0000-000H0HQ440E JR5050AWT-00-0000-000H0BQ227E JR5050AWT-00-0000-000H0BQ230E JR5050AWT-00-0000-000H0BQ435E JR5050AWT-00-0000-000H0BQ440E JR5050AWT-00-0000-000H0BQ445E JR5050AWT-00-0000-000H0BQ450E JR5050AWT-00-0000-000D0UP435E JR5050AWT-00-0000-000D0UQ240E JR5050AWT-00-0000-000D0UQ245E JR5050AWT-00-0000-000D0UQ250E JR5050AWT-00-0000-000D0UQ257E JR5050AWT-00-0000-000D0UQ265E JR5050AWT-00-0000-000D0HQ445E JR5050AWT-00-0000-000D0HQ450E JR5050AWT-00-0000-000D0HQ457E JR5050AWT-00-0000-000D0HQ465E JR5050AWT-00-0000-000D0UP427E JR5050AWT-00-0000-000D0UP430E JR5050AWT-00-0000-000D0BQ457E JR5050AWT-00-0000-000D0BQ465E JR5050AWT-00-0000-000D0HQ227E JR5050AWT-00-0000-000D0HQ440E JR5050AWT-00-0000-000D0HQ230E JR5050AWT-00-0000-000D0HQ435E