

# USB Type-C Analog Audio Switch with Protection

## Function, Moisture detection and Audio Jack Detection

### Features

- Power supply: 2.7 V to 5.5 V
- Version information:
  - DIO4485 default: DP\_R~DP1; DN\_L~DN1; SBU1~SBU1\_H; SBU2~SBU2\_H turn on
  - DIO4485B default: DP\_R~DP1; DN\_L~DN1 turn on
- USB 2.0 switch -3dB bandwidth: 1.05 GHz
- Audio switch:
  - Negative rail capability: -3.6 V to 3.6 V;
  - THD+N = -110 dB, 1V<sub>RMS</sub>, f = 20 Hz~20 kHz, 32 Ω load;
  - 3dB bandwidth: 940 MHz
- UART switch -3dB bandwidth: 800 MHz
- High voltage protection:
  - +20 V DC tolerance on USB Type-C pins
  - ±25 V surge capable on USB Type-C pins
- Overvoltage protection:
 

DP\_R, DN\_L, SBU1/SBU2/GSBU1/GSBU2 V<sub>TH</sub> = 4.4 V (default), 4.4 V ~ 5.0 V configurable, 0.2V/step
- Support OMTP, CTIA and 3-pole audio jack pinout
- Built-in moisture detection function, including moisture resistor and moisture voltage mode. Support single-pin mode and multi-pin mode. Support polling mode, and polling time is I<sup>2</sup>C configurable.
- Support 1.2 V and 1.8 V I/O logic

### Applications

- Mobile phone
- Tablets

### Package Information


| Part Number | Package  | Body Size         |
|-------------|----------|-------------------|
| DIO4485/B   | WLCSP-25 | 2.24 mm × 2.28 mm |

### Description

The DIO4485 / DIO4485B is a high-performance USB Type-C analog switch for the use in portable multimedia devices, supporting analog audio headsets. The DIO4485 / DIO4485B can detect OMTP, CTIA, or 3-pole headsets and configure pinouts automatically. The DIO4485 / DIO4485B shares common Type-C pins to pass USB 2.0 signals and analog audio signals; the sideband uses wires and analog microphone signals. The DIO4485 / DIO4485B also supports high voltage and surge on SBUx pins and USB pins on the USB Type-C receptacle side.

The DIO4485 / DIO4485B supports the moisture detection for five pins, including CC\_IN, DP\_R, DN\_L, SBU1 and SBU2. Moisture detection function can detect both moisture resistance and voltage. The detection mode includes single-pin mode and multi-pin mode. The multi-pin mode supports the detection polling, and the polling time can be configured through I<sup>2</sup>C.

### Simplified Schematic



## ■ Ordering Information

| Ordering Part No. | Top Marking | MSL | RoHS  | T <sub>A</sub> | Package  |                   |
|-------------------|-------------|-----|-------|----------------|----------|-------------------|
| DIO4485WL25       | D4HE        | 1   | Green | -40 to 85°C    | WLCSP-25 | Tape & Reel, 3000 |
| DIO4485BWL25      | DH5B        | 1   | Green | -40 to 85°C    | WLCSP-25 | Tape & Reel, 3000 |

If you encounter any issue in the process of using the device, please contact our customer service at [marketing@dioo.com](mailto:marketing@dioo.com) or phone us at (+86)-21-62116882. If you have any improvement suggestions regarding the datasheet, we encourage you to contact our technical writing team at [docs@dioo.com](mailto:docs@dioo.com). Your feedback is invaluable for us to provide a better user experience.


## List of Contents

|                                                   |    |
|---------------------------------------------------|----|
| 1. Pin Assignment and Functions .....             | 1  |
| 2. Absolute Maximum Ratings .....                 | 2  |
| 3. Recommended Operating Conditions .....         | 3  |
| 4. ESD Ratings .....                              | 3  |
| 5. Electrical Characteristics .....               | 4  |
| 5.1. DC electrical characteristics .....          | 4  |
| 5.2. AC electrical characteristics .....          | 7  |
| 5.3. Comparator electrical characteristics .....  | 9  |
| 5.4. Capacitance .....                            | 9  |
| 5.5. I <sup>2</sup> C specification .....         | 10 |
| 6. Block Diagram .....                            | 11 |
| 7. Application Information .....                  | 12 |
| 7.1. Overvoltage protection .....                 | 12 |
| 7.2. Watchdog timer .....                         | 12 |
| 7.3. Headset detection .....                      | 12 |
| 7.4. MIC switch auto-off function .....           | 12 |
| 7.5. Audio jack detection and configuration ..... | 12 |
| 7.6. I <sup>2</sup> C interface .....             | 13 |
| 7.7. Moisture detection .....                     | 13 |
| 8. Register Maps .....                            | 18 |
| 8.1. I <sup>2</sup> C slave address .....         | 22 |
| 8.2. Register definition .....                    | 22 |
| 9. Physical Dimensions: WLCSP-25 .....            | 36 |

## List of Figures

|                                                                                              |    |
|----------------------------------------------------------------------------------------------|----|
| Figure 1. Definition of timing for full-speed mode devices on the I <sup>2</sup> C bus ..... | 10 |
| Figure 2. I <sup>2</sup> C write example .....                                               | 13 |
| Figure 3. I <sup>2</sup> C read example .....                                                | 13 |
| Figure 4. Single-pin mode (with current source enabled) .....                                | 14 |
| Figure 5. Single-pin mode (with current source disabled) .....                               | 14 |
| Figure 6. Multi-pin mode (with current source enabled) .....                                 | 15 |
| Figure 7. Multi-pin mode (with current source disabled) .....                                | 15 |
| Figure 8. Single-pin polling mode (with current source enabled) .....                        | 16 |
| Figure 9. Single-pin polling mode (with current source disabled) .....                       | 16 |
| Figure 10. Multi-pin polling mode (with current source enabled) .....                        | 16 |
| Figure 11. Multi-pin polling mode (with current source disabled) .....                       | 17 |

## 1. Pin Assignment and Functions



**WLCSP-25 (Top view)**

| Pin No. | Name           | Description                                                                                                         |
|---------|----------------|---------------------------------------------------------------------------------------------------------------------|
| A5      | VCC            | Power supply (2.7 to 5.5 V)                                                                                         |
| B5      | GND            | Chip ground                                                                                                         |
| D5      | DP_R           | USB/Audio common pin                                                                                                |
| D4      | DN_L           | USB/Audio common pin                                                                                                |
| E5      | DP1            | USB data1 (differential +)                                                                                          |
| E4      | DN1            | USB data1 (differential –)                                                                                          |
| C5      | R              | Audio – right channel                                                                                               |
| C4      | L              | Audio – left channel                                                                                                |
| A3      | SBU1           | Sideband use wire 1                                                                                                 |
| A2      | SBU2           | Sideband use wire 2                                                                                                 |
| C1      | MIC            | Microphone signal                                                                                                   |
| B2      | AGND           | Audio signal ground                                                                                                 |
| B3      | AGND           | Audio signal ground                                                                                                 |
| E2      | SENSE          | Audio ground reference output                                                                                       |
| C3      | INT/<br>CMPOUT | Open-drain comparator output, set as CMPOUT when 0x12h bit [4] = 1                                                  |
|         |                | Open-drain output, set as INT when 0x12h bit [4] = 0.<br>I <sup>2</sup> C interrupt output, active low (open-drain) |
| D2      | CC_IN          | Audio accessory attachment detection input                                                                          |
| D1      | GSBU1          | Audio sense path 1 to headset jack GND                                                                              |
| E1      | GSBU2          | Audio sense path 2 to headset jack GND                                                                              |

|    |               |                                                                                                                          |
|----|---------------|--------------------------------------------------------------------------------------------------------------------------|
| C2 | DET/<br>CMPIN | Comparator input, set as COMPIN when 0x12h bit [4] = 1                                                                   |
|    |               | Open-drain output, set as DET when 0x12h bit [4] = 0.<br>DET is low when CC_IN > 1.5 V<br>DET is high when CC_IN < 1.2 V |
| D3 | SCL           | I <sup>2</sup> C clock                                                                                                   |
| E3 | SDA           | I <sup>2</sup> C data                                                                                                    |
| B1 | SBU2_H        | Host side sideband use wire 2                                                                                            |
| A1 | SBU1_H        | Host side sideband use wire 1                                                                                            |
| A4 | DP2           | USB data2 (differential +)                                                                                               |
| B4 | DN2           | USB data2 (differential -)                                                                                               |

## 2. Absolute Maximum Ratings

Exceeding the maximum ratings listed under Absolute Maximum Ratings when designing is likely to damage the device permanently. Do not design to the maximum limits because long-time exposure to them might impact the device's reliability. The ratings are obtained over an operating free-air temperature range unless otherwise specified.

| Symbol                    | Parameter                                                                                                |                       | Min  | Max | Unit |
|---------------------------|----------------------------------------------------------------------------------------------------------|-----------------------|------|-----|------|
| V <sub>CC</sub>           | Supply voltage from V <sub>CC</sub>                                                                      |                       | -0.5 | 6.5 | V    |
| V <sub>CC_IN</sub>        | V <sub>CC_IN</sub> , to GND                                                                              |                       | -0.5 | 20  | V    |
| V <sub>SW_C</sub>         | V <sub>DP_R</sub> to GND, V <sub>DN_L</sub> to GND                                                       |                       | -3.5 | 20  | V    |
| V <sub>SW_USB</sub>       | V <sub>DP1</sub> to GND, V <sub>DN1</sub> to GND                                                         |                       | -0.5 | 6.5 | V    |
| V <sub>SW_Audio</sub>     | V <sub>L</sub> to GND, V <sub>R</sub> to GND                                                             |                       | -3.6 | 6.5 | V    |
| V <sub>SW_UART</sub>      | V <sub>DP2</sub> to GND, V <sub>DN2</sub> to GND                                                         |                       | -3.6 | 6.5 | V    |
| V <sub>V_SBUx/GSBUx</sub> | V <sub>SBU1</sub> to GND, V <sub>SBU2</sub> to GND, V <sub>GSBU1</sub> to GND, V <sub>GSBU2</sub> to GND |                       | -0.5 | 20  | V    |
| V <sub>VSBUx_H</sub>      | V <sub>SBU1_H</sub> to GND, V <sub>SBU2_H</sub> to GND                                                   |                       | -0.5 | 6.5 | V    |
| V <sub>I/O</sub>          | SENSE, MIC to GND                                                                                        |                       | -0.5 | 6.5 | V    |
| V <sub>CNTRL</sub>        | Control input voltage                                                                                    | SDA, SCL              | -0.5 | 6.5 | V    |
| V <sub>comparator</sub>   | Comparator input and output                                                                              | DET/CMPIN, INT/CMPOUT | -0.5 | 6.5 | V    |
| I <sub>SW_Audio</sub>     | Switch I/O current, audio path                                                                           |                       | -250 | 250 | mA   |
| I <sub>SW_USB</sub>       | Switch I/O current, USB path                                                                             |                       |      | 100 | mA   |
| I <sub>SW_MIC</sub>       | Switch I/O current, MIC to SBU1 or SBU2                                                                  |                       |      | 50  | mA   |
| I <sub>SW_SBUx</sub>      | Switch I/O current, SBUx to SBUx_H                                                                       |                       |      | 50  | mA   |
| I <sub>SW_SENSE</sub>     | Switch I/O current, SENSE to GSBU1 or GSBU2                                                              |                       |      | 100 | mA   |
| I <sub>SW_AGND</sub>      | Switch I/O current, AGND to SBU1 or SBU2                                                                 |                       |      | 500 | mA   |
| I <sub>IK</sub>           | DC input diode current                                                                                   |                       | -50  |     | mA   |
| T <sub>A</sub>            | Absolute maximum operating temperature                                                                   |                       | -40  | 85  | °C   |
| T <sub>STG</sub>          | Storage temperature                                                                                      |                       | -65  | 150 | °C   |

### 3. Recommended Operating Conditions

Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. The ratings are obtained over an operating free-air temperature range unless otherwise specified.

| Symbol                 | Parameter                                                                                                  | Min   | Typ | Max             | Unit |
|------------------------|------------------------------------------------------------------------------------------------------------|-------|-----|-----------------|------|
| V <sub>CC</sub>        | Supply voltage                                                                                             | 2.7   |     | 5.5             | V    |
| V <sub>SW_USB</sub>    | V <sub>DP</sub> to GND, V <sub>DN</sub> to GND, V <sub>DP_R</sub> to GND, V <sub>DN_L</sub> to GND         | 0     |     | 3.6             | V    |
| V <sub>SW_Audio</sub>  | V <sub>DP_R</sub> to GND, V <sub>DN_L</sub> to GND, V <sub>L</sub> to GND, V <sub>R</sub> to GND           | -3.6  |     | 3.6             | V    |
| V <sub>VSBU_MIC</sub>  | V <sub>SBU1</sub> to GND, V <sub>SBU2</sub> to GND, V <sub>MIC</sub> to GND                                | 0     |     | 3.6             | V    |
| V <sub>VGSBU_SEN</sub> | V <sub>GSBU1</sub> to GND, V <sub>GSBU2</sub> to GND, V <sub>SENSE</sub> to GND                            | 0     |     | 3.6             | V    |
| V <sub>VGSBU</sub>     | V <sub>SBU1</sub> to GND, V <sub>SBU2</sub> to GND, V <sub>SBU1_H</sub> to GND, V <sub>SBU2_H</sub> to GND | 0     |     | 3.6             | V    |
| V <sub>CC_IN</sub>     | V <sub>CC_IN</sub> to GND                                                                                  | 0     |     | 5.5             | V    |
| V <sub>IH</sub>        | Input voltage high                                                                                         | 0.825 |     | V <sub>CC</sub> | V    |
| V <sub>IL</sub>        | Input voltage low                                                                                          |       |     | 0.3             | V    |
| T <sub>A</sub>         | Ambient operating temperature                                                                              | -40   | 25  | 85              | °C   |

### 4. ESD Ratings

When a statically-charged person or object touches an electrostatic discharge sensitive device, the electrostatic charge might be drained through sensitive circuitry in the device. If the electrostatic discharge possesses sufficient energy, damage might occur to the device due to localized overheating.

| Model                      | Metric                 | Value | Unit |
|----------------------------|------------------------|-------|------|
| Human-body model (HBM)     | ANSI/ESDA/JEDEC JS-001 | ±5000 | V    |
| Charged device model (CDM) | ANSI/ESDA/JEDEC JS-002 | ±2000 | V    |
| Latch-up                   |                        | 200   | mA   |

## 5. Electrical Characteristics

### 5.1. DC electrical characteristics

The values are obtained under these conditions unless otherwise specified:  $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ ,  $V_{CC} = 3.3\text{ V}$  (Typ.),  $T_A = -40^\circ\text{C to }85^\circ\text{C}$ , and  $T_A = 25^\circ\text{C}$  (Typ.).

| Symbol                              | Parameter                                              | Conditions                                               | Power                            | Min | Typ  | Max | Unit |
|-------------------------------------|--------------------------------------------------------|----------------------------------------------------------|----------------------------------|-----|------|-----|------|
| I <sub>CC</sub>                     | Supply current                                         | USB switches on, SBUx to SBUx_H switches on              | V <sub>CC</sub> = 4.2 V          |     | 65   |     | μA   |
|                                     |                                                        | Audio switches on, MIC switch on and Audio GND switch on |                                  |     | 63   |     | μA   |
| I <sub>CCZ</sub>                    | Standby current                                        | 04H'b7 = 0                                               |                                  |     |      | 4   |      |
| USB/Audio common pins: DP_R, DN_L   |                                                        |                                                          |                                  |     |      |     |      |
| I <sub>OZ</sub>                     | Off leakage current of DP_R and DN_L                   | DN_L, DP_R = -3 V to 3.6 V                               | V <sub>CC</sub> = 2.7 V to 5.5 V | -3  |      | 3   | μA   |
| I <sub>OFF</sub>                    | Power-off leakage current of DP_R and DN_L             | DN_L, DP_R = 0 V to 3.6 V                                | Power off                        | -3  |      | 3   | μA   |
| V <sub>OV_TRIP</sub> <sup>(1)</sup> | Input OVP lockout                                      | Rising edge, 0x12h bit [7:6] = 00                        | V <sub>CC</sub> = 2.7 V to 5.5 V | 4.2 | 4.4  | 4.6 | V    |
| V <sub>OV_HYS</sub> <sup>(1)</sup>  | Input OVP hysteresis                                   |                                                          |                                  |     | 0.24 |     | V    |
| Audio switch                        |                                                        |                                                          |                                  |     |      |     |      |
| I <sub>ON</sub>                     | On leakage current of audio switch                     | DN_L, DP_R = -3 V to 3 V, DP, DN, R, L = Float           | V <sub>CC</sub> = 2.7 V to 5.5 V | -4  |      | 3   | μA   |
| I <sub>OFF</sub>                    | Power-off leakage current of L and R                   | L, R = 0 V to 3 V, DP_R, DN_L = Float                    | Power off                        | -1  |      | 1   | μA   |
| R <sub>ON</sub>                     | Switch on resistance                                   | I <sub>SW</sub> = 100 mA, V <sub>SW</sub> = -3 V to 3 V  | V <sub>CC</sub> = 2.7 V to 5.5 V |     | 1.2  |     | Ω    |
| R <sub>SHUNT</sub>                  | Pull-down resistor on R/L pin when audio switch is off | L= R = 3 V                                               |                                  | 6   | 10   | 14  | kΩ   |
| USB switch                          |                                                        |                                                          |                                  |     |      |     |      |
| I <sub>ON</sub>                     | On leakage current of USB switch                       | DN_L, DP_R = 0 V to 3.6 V, DP1, DN1, R, L = Float        | V <sub>CC</sub> = 2.7 V to 5.5 V | -3  |      | 3   | μA   |

|                                     |                                        |                                                    |                                  |     |      |     |    |
|-------------------------------------|----------------------------------------|----------------------------------------------------|----------------------------------|-----|------|-----|----|
| I <sub>OZ</sub>                     | Off leakage current of DP and DN       | DP_R to DP1, DN_L to DN1 = 0 V to 3.6 V            |                                  | -3  |      | 3   | μA |
| I <sub>OFF</sub>                    | Power-off leakage current of DP and DN | DP_R to DP1, DN_L to DN1 = 0 V to 3.6 V            | Power off                        | -3  |      | 3   | μA |
| R <sub>ON_USB</sub>                 | USB switch on resistance               | I <sub>SW</sub> = 8 mA, V <sub>SW</sub> = 0.4 V    | V <sub>CC</sub> = 2.7 V to 5.5 V |     | 4.6  |     | Ω  |
| UART switch                         |                                        |                                                    |                                  |     |      |     |    |
| I <sub>OZ</sub>                     | Off leakage current of DP and DN       | DP_R to DP2, DN_L to DN2 = 0 V to 3.6 V            |                                  | -3  |      | 3   | μA |
| I <sub>OFF</sub>                    | Power-off leakage current of DP and DN | DP_R to DP2, DN_L to DN2 = 0 V to 3.6 V            | Power off                        | -3  |      | 3   | μA |
| R <sub>ON_UART</sub>                | UART switch on resistance              | I <sub>SW</sub> = 3 mA, V <sub>SW</sub> = 0.4 V    | V <sub>CC</sub> = 2.7 V to 5.5 V |     | 10   |     | Ω  |
| I <sub>ON</sub>                     | On leakage current UART switch         | DN_L, DP_R = 0 V to 3.6 V, DP2, DN2, R, L = Float  | V <sub>CC</sub> = 2.7 V to 5.5 V |     | 1.6  |     | μA |
| SENSE-AGND switch                   |                                        |                                                    |                                  |     |      |     |    |
| R <sub>ON</sub>                     | SENSE switch on resistance             | I <sub>OUT</sub> = 100 mA, V <sub>SW</sub> = 1.0 V | V <sub>CC</sub> = 2.7 V to 5.5 V |     | 8    |     | Ω  |
| SENSE switch                        |                                        |                                                    |                                  |     |      |     |    |
| I <sub>ON</sub>                     | SENSE path leakage current             | GSBUx = 0 V to 1 V, SENSE is floating              | V <sub>CC</sub> = 2.7 V to 5.5 V | -2  |      | 2   | μA |
| R <sub>ON</sub>                     | SENSE switch on resistance             | I <sub>OUT</sub> = 100 mA, V <sub>SW</sub> = 1.0 V | V <sub>CC</sub> = 2.7 V to 5.5 V |     | 330  |     | mΩ |
| I <sub>OFF</sub>                    | Power-off leakage current of SENSE     | GSBUx to SENSE = 0 V to 1.0 V                      | V <sub>CC</sub> = 2.7 V to 5.5 V | -2  |      | 2   | μA |
|                                     | Power-off leakage current of GSBUx     | GSBUx = 0 V to 3.6 V                               |                                  | -3  |      | 3   | μA |
| V <sub>OV_TRIP</sub> <sup>(1)</sup> | Input OVP lockout on GSBUx             | Rising edge, 0x12h bit [7:6] = 00                  | V <sub>CC</sub> = 2.7 V to 5.5 V | 4.2 | 4.4  | 4.6 | V  |
| V <sub>OV_HYS</sub> <sup>(1)</sup>  | Input OVP hysteresis of GSBUx          |                                                    |                                  |     | 0.24 |     | V  |
| SBUx pins                           |                                        |                                                    |                                  |     |      |     |    |
| I <sub>OZ</sub>                     | Off leakage current of SBUx            | SBUx = 0 V to 3.6 V                                | V <sub>CC</sub> = 2.7 V to 5.5 V | -3  |      | 3   | μA |



|                                       |                                     |                                                                 |                                         |     |      |     |            |
|---------------------------------------|-------------------------------------|-----------------------------------------------------------------|-----------------------------------------|-----|------|-----|------------|
| $I_{OFF}$                             | Power-off leakage current port SBUx | SBUx = 0 V to 3.6 V                                             | Power off                               | -2  |      | 10  | $\mu A$    |
| $V_{OV\_TRIP}^{(1)}$                  | Input OVP lockout                   | Rising edge, 0x12h bit [7:6] = 00                               | $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ | 4.2 | 4.4  | 4.6 | V          |
| $V_{OV\_HYS}^{(1)}$                   | Input OVP hysteresis                |                                                                 |                                         |     | 0.24 |     | V          |
| MIC switch                            |                                     |                                                                 |                                         |     |      |     |            |
| $I_{ON}$                              | On leakage current of MIC switch    | SBUx = 0 V to 3.6 V, MIC is floating                            | $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ | -3  |      | 3   | $\mu A$    |
| $I_{OZ}$                              | Off leakage current of MIC          | MIC = 0 V to 3.6 V                                              |                                         | -1  |      | 1   | $\mu A$    |
| $I_{OFF}$                             | Power-off leakage current of MIC    | MIC = 0 V to 3.6 V                                              | Power off                               | -1  |      | 1   | $\mu A$    |
| $R_{ON}$                              | MIC switch on resistance            | $V_{SW} = 3.6\text{ V}$ , $I_{SW} = 30\text{ mA}$               | $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ |     | 3.1  |     | $\Omega$   |
| SBUx_H switch                         |                                     |                                                                 |                                         |     |      |     |            |
| $I_{ON}$                              | On leakage current of SBUx_H switch | SBUx = 0 V to 3.6 V, SBUx_H is floating                         | $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ | -3  |      | 3   | $\mu A$    |
| $I_{OZ}$                              | Off leakage of SBUx_H               | SBUx_H = 0 V to 3.6 V                                           |                                         | -1  |      | 1   | $\mu A$    |
| $I_{OFF}$                             | Power off leakage current of SBUx_H | SBUx_H = 0 V to 3.6 V                                           | Power off                               | -1  |      | 1   | $\mu A$    |
| $R_{ON}$                              | SBUx_H switch on resistance         | $V_{SW} = 0\text{ V to }3.6\text{ V}$ , $I_{SW} = 30\text{ mA}$ | $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ |     | 2.8  |     | $\Omega$   |
| Audio ground switch pin: AGND to SBUx |                                     |                                                                 |                                         |     |      |     |            |
| $R_{ON}$                              | AGND switch on resistance           | $I_{SOURCE} = 100\text{ mA}$ on SBUx                            | $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ |     | 66   |     | m $\Omega$ |
| CC_IN pin                             |                                     |                                                                 |                                         |     |      |     |            |
| $V_{TH\_L}$                           | Input low threshold                 |                                                                 | $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ |     | 1.2  |     | V          |
| $V_{TH\_H}$                           | Input high threshold                |                                                                 |                                         |     | 1.5  |     | V          |
| $I_{IN}$                              | Input leakage of CC_IN              | CC_IN = 0 V to 5.5 V                                            |                                         |     |      | 1.0 | $\mu A$    |
| SDS, SCL pins                         |                                     |                                                                 |                                         |     |      |     |            |
| $V_{IL12C}$                           | Low-level input voltage             |                                                                 | $V_{CC} = 2.7\text{ V to }5.5\text{ V}$ |     |      | 0.3 | V          |

|             |                                   |                        |  |       |  |     |         |
|-------------|-----------------------------------|------------------------|--|-------|--|-----|---------|
| $V_{IH2C}$  | High-level input voltage          |                        |  | 0.825 |  |     | V       |
| $I_{I2C}$   | Input current of SDA and SCL pins | SCL/SDA = 0 V to 3.6 V |  | -5    |  | 5   | $\mu$ A |
| $V_{OLSDA}$ | Low-level output voltage          | $I_{OL} = 2$ mA        |  |       |  | 0.3 | V       |
| $I_{OLSDA}$ | Low-level output current          | $V_{OLSDA} = 0.2$ V    |  | 10    |  |     | mA      |

**Note:**

- (1) The OVP voltage can be adjusted by bit [7:6] for 12h: 4.4 V, 4.6 V, 4.8 V, 5 V.  
(2) Specifications subject to change without notice.

## 5.2. AC electrical characteristics

The values are obtained under these conditions unless otherwise specified:  $V_{CC} = 2.7$  V to 5.5 V,  $V_{CC}$  (Typ.) = 3.3 V,  $T_A = -40^{\circ}\text{C}$  to  $85^{\circ}\text{C}$ , and  $T_A$  (Typ.) =  $25^{\circ}\text{C}$ .

| Symbol                         | Parameter                                                             | Conditions                                                                                       | Power                   | Min | Typ  | Max | Unit |
|--------------------------------|-----------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|-------------------------|-----|------|-----|------|
| Audio switch                   |                                                                       |                                                                                                  |                         |     |      |     |      |
| t <sub>delay</sub>             | Audio switch turn-on delay time                                       | DP_R = DN_L = 1 V,<br>R <sub>L</sub> = 32 Ω                                                      | V <sub>CC</sub> = 3.3 V |     | 20   |     | μs   |
| t <sub>rise</sub>              | Audio switch turn-on rising time                                      | DP_R = DN_L = 1 V,<br>R <sub>L</sub> = 32 Ω                                                      |                         |     | 60   |     | μs   |
| t <sub>OFF</sub>               | Audio switch turn-off time                                            | DP_R = DN_L = 1 V,<br>R <sub>L</sub> = 32 Ω                                                      | V <sub>CC</sub> = 3.3 V |     | 2    |     | μs   |
| X <sub>TALK</sub>              | Cross talk (adjacent)                                                 | f = 1 kHz, R <sub>L</sub> = 50 Ω,<br>V <sub>SW</sub> = 1 V <sub>RMS</sub>                        |                         |     | -90  |     | dB   |
| BW                             | -3 dB bandwidth                                                       | R <sub>L</sub> = 50 Ω                                                                            |                         |     | 940  |     | MHz  |
| O <sub>IRR</sub>               | Off isolation                                                         | f = 1 kHz, R <sub>L</sub> = 50 Ω,<br>C <sub>L</sub> = 0 pF, V <sub>SW</sub> = 1 V <sub>RMS</sub> |                         |     | -110 |     | dB   |
| THD+N                          | Total harmonic distortion + noise performance with A-weighting filter | R <sub>L</sub> = 600 Ω,<br>f = 20 Hz ~ 20 kHz,<br>V <sub>SW</sub> = 2 V <sub>RMS</sub>           |                         |     | -110 |     | dB   |
|                                |                                                                       | R <sub>L</sub> = 32 Ω,<br>f = 20 Hz ~ 20 kHz,<br>V <sub>SW</sub> = 1 V <sub>RMS</sub>            |                         |     | -110 |     | dB   |
|                                |                                                                       | R <sub>L</sub> = 16 Ω,<br>f = 20 Hz ~ 20 kHz,<br>V <sub>SW</sub> = 0.5 V <sub>RMS</sub>          |                         |     | -108 |     | dB   |
| USB switch                     |                                                                       |                                                                                                  |                         |     |      |     |      |
| t <sub>ON</sub> <sup>(1)</sup> | USB switch turn-on time                                               | DP_R = DN_L = 1.5 V,<br>R <sub>L</sub> = 50 Ω                                                    | V <sub>CC</sub> = 3.3 V |     | 32   |     | μs   |

|                                  |                                                   |                                                                                          |                          |  |      |  |         |
|----------------------------------|---------------------------------------------------|------------------------------------------------------------------------------------------|--------------------------|--|------|--|---------|
| $t_{OFF}$                        | USB switch turn-off time                          | DP_R = DN_L = 1.5 V,<br>$R_L = 50 \Omega$                                                |                          |  | 2    |  | $\mu s$ |
| BW                               | -3 dB bandwidth                                   | $R_L = 50 \Omega$                                                                        |                          |  | 1.05 |  | GHz     |
| $O_{IRR}$                        | Off isolation between DP, DN and common node pins | $f = 1 \text{ kHz}$ , $R_L = 50 \Omega$ ,<br>$C_L = 0 \text{ pF}$ , $V_{SW} = 1 V_{RMS}$ |                          |  | -110 |  | dB      |
| $t_{OVP}$                        | DP_R and DN_L pins OVP response time              | $V_{SW} = 3.5 \text{ V to } 5.5 \text{ V}$                                               |                          |  | 0.4  |  | $\mu s$ |
| <b>UART switch</b>               |                                                   |                                                                                          |                          |  |      |  |         |
| BW                               | -3 dB bandwidth                                   | $R_L = 50 \Omega$                                                                        | $V_{CC} = 3.3 \text{ V}$ |  | 800  |  | MHz     |
| <b>MIC / Audio ground switch</b> |                                                   |                                                                                          |                          |  |      |  |         |
| $t_{delay\_MIC}$                 | MIC switch turn-on delay time                     | $SBUx = 1 \text{ V}$ , $R_L = 50 \Omega$                                                 | $V_{CC} = 3.3 \text{ V}$ |  | 70   |  | $\mu s$ |
| $t_{rise\_MIC}$                  | MIC switch turn-on rising time                    |                                                                                          |                          |  | 120  |  |         |
| $t_{delay\_AGND}$                | AGND switch turn-on time                          | $SBUx$ pulled to 0.5 V by 16 $\Omega$ , AGND connect to GND                              |                          |  | 1.6  |  | ms      |
| $t_{rise\_AGND}$                 | AGND switch turn-on rising time                   |                                                                                          |                          |  | 1    |  | ms      |
| $t_{OFF\_MIC}$                   | MIC switch turn-off time                          | $SBUx = 2.5 \text{ V}$ , $R_L = 50 \Omega$                                               |                          |  | 2    |  | $\mu s$ |
| $t_{OFF\_Audio\_GND}$            | AGND switch turn-off time                         | $SBUx$ : $I_{SOURCE} = 10 \text{ mA}$ , clamp to 2.5 V                                   |                          |  | 50   |  | $\mu s$ |
| BW                               | MIC switch bandwidth                              | $R_L = 50 \Omega$                                                                        |                          |  | 52   |  | MHz     |
| <b>SBUx_H switch</b>             |                                                   |                                                                                          |                          |  |      |  |         |
| $t_{ON}$                         | SBUx_H switch turn-on time                        | $SBUx = 2.5 \text{ V}$ , $R_L = 50 \Omega$                                               | $V_{CC} = 3.3 \text{ V}$ |  | 45   |  | $\mu s$ |
| $t_{OFF}$                        | SBUx_H switch turn-off time                       |                                                                                          |                          |  | 2    |  | $\mu s$ |
| BW                               | Bandwidth                                         | $R_L = 50 \Omega$                                                                        |                          |  | 45   |  | MHz     |
| $t_{OVP}$                        | SBUx pins OVP response time                       | $V_{SW} = 3.5 \text{ V to } 5.5 \text{ V}$                                               |                          |  | 0.4  |  | $\mu s$ |

**Note:**

- (1) The Turn-on timing can be adjusted by the I<sup>2</sup>C register.
- (2) Specifications subject to change without notice.

### 5.3. Comparator electrical characteristics

The values are obtained under these conditions unless otherwise specified:  $T_A = 25^\circ\text{C}$ ,  $V_{CC} = 2.7\text{ V to }5\text{ V}$ ,  $C_L = 15\text{ pF}$ .

| Symbol                                   | Parameter                  | Condition                                     | Min   | Typ | Max            | Unit                         |
|------------------------------------------|----------------------------|-----------------------------------------------|-------|-----|----------------|------------------------------|
| <b>Offset voltage</b>                    |                            |                                               |       |     |                |                              |
| $V_{REF}$                                | Reference voltage          | $T_A = 25^\circ\text{C to }65^\circ\text{C}$  | 218.5 | 225 | 231.5          | mV                           |
| $V_{HYS}$                                | Hysteresis                 |                                               |       | 30  | 40             | mV                           |
| $dV_{OS}/dT$                             | Input offset voltage drift | $T_A = -40^\circ\text{C to }85^\circ\text{C}$ |       |     | $\pm 70$       | $\mu\text{V}/^\circ\text{C}$ |
| <b>Input voltage range</b>               |                            |                                               |       |     |                |                              |
| $V_{CM}$                                 | Common-mode voltage range  | $T_A = -40^\circ\text{C to }85^\circ\text{C}$ | -0.1  |     | $V_{CC} + 0.1$ | V                            |
| <b>Input bias current <sup>(1)</sup></b> |                            |                                               |       |     |                |                              |
| $I_B$                                    | Input bias current         | $T_A = 25^\circ\text{C}$                      |       | 30  | 100            | pA                           |
|                                          |                            | $T_A = -40^\circ\text{C to }85^\circ\text{C}$ |       |     | 20             | nA                           |
| $I_{OS}$                                 | Input offset current       |                                               |       | 8   |                | pA                           |
| $C_{LOAD}$                               | Capacitive load drive      |                                               |       | 60  |                | pF                           |
| <b>Output type</b>                       |                            | Open-drain                                    |       |     |                |                              |

**Note:**

- (1) Guaranteed by design.
- (2) Specifications subject to change without notice.

### 5.4. Capacitance

The values are obtained under these conditions unless otherwise specified:  $V_{CC} (\text{Typ.}) = 3.3\text{ V}$ ,  $T_A = -40^\circ\text{C to }85^\circ\text{C}$ , and  $T_A (\text{Typ.}) = 25^\circ\text{C}$ .

| Symbol                     | Parameter                          | Conditions                                                             | Min | Typ | Max | Unit |
|----------------------------|------------------------------------|------------------------------------------------------------------------|-----|-----|-----|------|
| $C_{ON\_USB/Audio}^{(1)}$  | On capacitance (common port)       | $f = 1\text{ MHz}$ , $100\text{ mV}_{PK-PK}$ , $100\text{ mV DC bias}$ |     | 8   |     | pF   |
| $C_{OFF\_USB/Audio}^{(1)}$ | Off capacitance (common port)      | $f = 1\text{ MHz}$ , $100\text{ mV}_{PK-PK}$ , $100\text{ mV DC bias}$ |     | 6.5 |     | pF   |
| $C_{OFF\_USB}^{(1)}$       | Off capacitance (non-common ports) | $f = 1\text{ MHz}$ , $100\text{ mV}_{PK-PK}$ , $100\text{ mV DC bias}$ |     | 2.6 |     | pF   |
| $C_{ON\_SENSE\_SW}^{(1)}$  | On capacitance (common ports)      | $f = 1\text{ MHz}$ , $100\text{ mV}_{PK-PK}$ , $100\text{ mV DC bias}$ |     | 55  |     | pF   |
| $C_{OFF\_SENSE\_SW}^{(1)}$ | Off capacitance (common ports)     | $f = 1\text{ MHz}$ , $100\text{ mV}_{PK-PK}$ , $100\text{ mV DC bias}$ |     | 88  |     | pF   |
| $C_{ON\_MIC\_SW}^{(1)}$    | On capacitance (common ports)      | $f = 1\text{ MHz}$ , $100\text{ mV}_{PK-PK}$ , $100\text{ mV DC bias}$ |     | 170 |     | pF   |

|                             |                                |                                                                           |  |     |  |    |
|-----------------------------|--------------------------------|---------------------------------------------------------------------------|--|-----|--|----|
| $C_{OFF\_MIC\_SW}^{(1)}$    | Off capacitance (common ports) | $f = 1 \text{ MHz}$ , $100 \text{ mV}_{PK-PK}$ , $100 \text{ mV DC bias}$ |  | 10  |  | pF |
| $C_{ON\_AGND\_SW}^{(1)}$    | On capacitance (common port)   | $f = 1 \text{ MHz}$ , $100 \text{ mV}_{PK-PK}$ , $100 \text{ mV DC bias}$ |  | 125 |  | pF |
| $C_{ON\_SBUx\_H\_SW}^{(1)}$ | On capacitance (common port)   | $f = 1 \text{ MHz}$ , $100 \text{ mV}_{PK-PK}$ , $100 \text{ mV DC bias}$ |  | 160 |  | pF |

**Note:**

- (1) Guaranteed by design.  
(2) Specifications subject to change without notice.


## 5.5. I<sup>2</sup>C specification

The values are obtained under these conditions unless otherwise specified:  $V_{CC} = 2.7 \text{ V}$  to  $5.5 \text{ V}$ ,  $V_{CC} = 3.3 \text{ V}$  (Typ.),  $T_A = -40^\circ\text{C}$  to  $85^\circ\text{C}$ , and  $T_A$  (Typ.) =  $25^\circ\text{C}$ .

| Symbol              | Parameter                                                             | Min            | Typ | Max | Unit          |
|---------------------|-----------------------------------------------------------------------|----------------|-----|-----|---------------|
| $f_{SCL}$           | I <sup>2</sup> C_SCL clock frequency                                  |                |     | 400 | kHz           |
| $t_{HD; STA}$       | Hold time (repeated) START condition                                  | 0.6            |     |     | $\mu\text{s}$ |
| $t_{LOW}$           | Low period of I <sup>2</sup> C_SCL clock                              | 1.3            |     |     | $\mu\text{s}$ |
| $t_{HIGH}$          | High period of I <sup>2</sup> C_SCL clock                             | 0.6            |     |     | $\mu\text{s}$ |
| $t_{SU; STA}$       | Set-up time for repeated START condition                              | 0.6            |     |     | $\mu\text{s}$ |
| $t_{HD; DAT}^{(1)}$ | Data hold time                                                        | 0              |     | 0.9 | $\mu\text{s}$ |
| $t_{SU; DAT}^{(2)}$ | Data set-up time                                                      | 100            |     |     | ns            |
| $t_r^{(2)}$         | Rising time of I <sup>2</sup> C_SDA and I <sup>2</sup> C_SCL signals  | $20 + 0.1 C_b$ |     | 300 | ns            |
| $t_f^{(2)}$         | Falling time of I <sup>2</sup> C_SDA and I <sup>2</sup> C_SCL signals | $20 + 0.1 C_b$ |     | 300 | ns            |
| $t_{SU; STO}$       | Set-up time for STOP condition                                        | 0.6            |     |     | $\mu\text{s}$ |
| $t_{BUF}$           | Bus-free time between STOP and START conditions                       | 1.3            |     |     | $\mu\text{s}$ |
| $t_{SP}$            | Pulse width of spikes that must be suppressed by the input filter     | 0              |     | 50  | ns            |


**Note:**

- (1) Guaranteed by characterization. Not production tested.  
(2) A fast-mode I<sup>2</sup>C-bus device can be used in a standard-mode I<sup>2</sup>C-bus system, but the requirement  $t_{SU; DAT} \geq \pm 250 \text{ ns}$  must be met. This is automatically the case if the device does not stretch the LOW period of the I<sup>2</sup>C\_SCL signal. If such a device does stretch the LOW period of the I<sup>2</sup>C\_SCL signal, it must output the next data bit to the I<sup>2</sup>C\_SDA line  $t_{r\_max} + t_{SU; DAT} = 1000 + 250 = 1250 \text{ ns}$  (according to the standard-mode I<sup>2</sup>C bus specification) before the I<sup>2</sup>C\_SCL line is released.



**Figure 1. Definition of timing for full-speed mode devices on the I<sup>2</sup>C bus**

## 6. Block Diagram



## 7. Application Information

**Important notice:** Validation and testing are the most reliable ways to confirm system functionality. The application information is not part of the specification and is for reference purposes only.

### 7.1. Overvoltage protection

The DIO4485/DIO4485B features an overvoltage protection (OVP) on receptacle side pins that turns off the internal signal routing path if the voltage exceeds the OVP threshold. If an OVP is occurred, flag register 0x02h and 0x03h will indicate which pin had the OVP event. OVP threshold voltage is configurable by 0x12h, bit [7:6].

### 7.2. Watchdog timer

The function of watchdog is to continuously monitor I<sup>2</sup>C communication. A timer will start as long as the watchdog is enabled. The watchdog receives either read or write command from the master to be reset with I<sup>2</sup>C communication.

In case there's no I<sup>2</sup>C communication detected after the timer counting down to zero, DIO4485/DIO4485B will control Register 0x04h, 0x05h and 0x12h bit[1] to their default value by transmitting an interrupt and reset switch setting and moisture detection enable/disable signals. Watchdog timer can be programmed through Register 0x20h.

### 7.3. Headset detection

The DIO4485/DIO4485B integrates headset unplug detection function by detecting the CC\_IN voltage. The function will be active when device is enabled. Register 0x11h, bit [1:0] Output can indicate if CC\_IN is low (CC\_IN < 1.2 V) or high (CC\_IN > 1.5 V).

|               | 0x11h, bit [1] | 0x11h, bit [0] |
|---------------|----------------|----------------|
| CC_IN < 1.2 V | 0              | 1              |
| CC_IN > 1.5 V | 1              | 0              |

### 7.4. MIC switch auto-off function

The function is active during control bit 0x12h bit [2] = 1. When CC\_IN is changed from low to high, and L, R, and AGND switches are on, the MIC switch will be off and receptacle side pin will be pulled to ground for 50 µs first. Then it shows high-Z status under MIC switch is set on status.

### 7.5. Audio jack detection and configuration

The function is active when control bit 0x12h bit [0] = 1. When the headset is inserted, the DIO4485 / DIO4485B can detect OMTP, CTIA or 3-pole headset and configure pinout automatically. During detection and configuration, the R, L, Sense, MIC and Audio ground switches will be off. After detection and configuration, R, L, MIC, Sense and AGND switches will turn on according to detection results and timing control setting.


## 7.6. I<sup>2</sup>C interface

The DIO4485 / DIO4485B includes a full I<sup>2</sup>C slave controller. The I<sup>2</sup>C slave fully complies with the I<sup>2</sup>C specification version 2.1 requirements. This block is designed for fast mode, 400 kHz, signals. Examples of an I<sup>2</sup>C write and read sequence are shown in below figures respectively.



**Figure 2. I<sup>2</sup>C write example**

**Note:** Single-byte read is initiated by the master with P immediately following the first data byte.



**Figure 3. I<sup>2</sup>C read example**

**Note:** If the register is not specified, the master will begin reading from the current register. In this case only sequence showing in the red bracket is needed

## 7.7. Moisture detection

The DIO4485 / DIO4485B can detect moisture in type-C connector. When moisture detection is enabled, all the related channels will be closed. The voltage can be measured from the selected pin with current source enabled or disabled according to 0x13h bit [3]. Leakage between the selected pins and GND/VBUS can be detected by comparing the measured results with pre-set thresholds, and it will pull down 'INT', when moisture is found. The related channels will be recovered when the pin detection is completed.


An internal current source will be applied to the pin first during detection of the leakage between GND and pin CC\_IN, DP\_R, DN\_L, SBU1 or SBU2. After getting the result reflecting the resistance from this pin to GND, the result will be stored to corresponding register.

The voltage from the pin without current source will be measured during detection of the leakage between VBUS and pin CC\_IN, DP\_R, DN\_L, SBU1 or SBU2. For the leakage from VBUS and the voltage drop from this pin to ground, they will be detected by the measurement when the moisture detection is performed. The moisture detection has single-pin mode and multi-pin mode.


### 7.7.1. Single-pin mode

In single-pin mode, the moisture detection result would be stored separately in register 0x14h ( with current source enabled) or 0x30h (with current source disabled).





*Figure 4. Single-pin mode (with current source enabled)*



*Figure 5. Single-pin mode (with current source disabled)*

### 7.7.2. Multi-pin mode


In multi-pin mode, if all pins are selected, the turn of moisture detecting sequence will be CC\_IN, DP\_R, DN\_L, SBU1, SBU2. In case some pins are not selected, the detection will ignore the unselected pins and performed on the next selected pins. For example, if the pin CC\_IN, DP\_L are not selected, the moisture detection will be performed on DP\_R first, then SBU1 and SBU2 in turn.

As soon as the detection starts, whether the setup of the current source or pin selection would be ignored. And all the related channels would be forced off during the whole round detection (from the 1st pin to the last pin). The related channels will be recovered after the detection for all pins are completed.


If moisture error is detected in some pins (result > 0x32h for detection with current source disabled , or the result < 0x15h with current source enabled), DIO4485 / 4485B will complete the whole round, and then stop moisture detection and indicate the flag of "Moisture detection completion".

0x31h bit [5] will select the blank time between two adjacent detections.

It's shown in figure 6, figure 7 as below.



**Figure 6. Multi-pin mode (with current source enabled)**




**Figure 7. Multi-pin mode (with current source disabled)**


### 7.7.3. Polling

With 0x16h bit [1:0] = 1, DIO4485 / 4485B can also repeatedly perform moisture detection on its own. A list of scenarios with the combination set of 0x16h bit [1:0] is shown as below.

In single-pin mode, when there's no moisture detected (result <= 0x32h for detection with current source disabled, or result >= 0x15h with current source enabled), the moisture detection will be restarted after a period set by 0x16h bit [1:0].



**Figure 8. Single-pin polling mode (with current source enabled)**




**Figure 9. Single-pin polling mode (with current source disabled)**


In multi-pin mode, when the measured result is ok after one round detection for selected pins, a new round will be restart after the period set by Polling time.

In the polling period, any attempt of changing the setup of current source or selecting the pins will be noticed in preparation of the next new round.

During the detection, all the related channels will be closed as soon as the first pin detection starts and the channels will not be recover until the last pin detection finishes, which means this round detection is completed. To exit polling immediately, there are two situations: one situation is writing 0x13h bit [7] = 1, the other one is an OVP event detected.



**Figure 10. Multi-pin polling mode (with current source enabled)**



**Figure 11. Multi-pin polling mode (with current source disabled)**

## 8. Register Maps

| ADDR | Register Name                                            | Type | Reset Value    | Bit7                                                             | Bit6                    | Bit5                      | Bit4                      | Bit3                      | Bit2                     | Bit1                     | Bit0                  |  |
|------|----------------------------------------------------------|------|----------------|------------------------------------------------------------------|-------------------------|---------------------------|---------------------------|---------------------------|--------------------------|--------------------------|-----------------------|--|
| 00H  | Device ID                                                | R    | 0XF6           | 1                                                                | 1                       | 1                         | 1                         | 0                         | 1                        | 0                        | 1                     |  |
| 02H  | OVP interrupt flag                                       | R/C  | 0x00           | Reserved                                                         | Reserved                | OVP/<br>DP_R              | OVP/<br>DN_L              | OVP/<br>SBU1,SBU2         |                          | OVP/<br>GSBU1            | OVP/<br>GSBU2         |  |
| 03H  | OVP status                                               | R    | 0x00           | Reserved [7:6]                                                   |                         | OVP/<br>DP_R              | OVP/<br>DN_L              | OVP/<br>SBU1, SBU2 [3:2]  |                          | OVP/<br>GSBU1            | OVP/<br>GSBU2         |  |
| 04H  | Switch settings enable                                   | R/W  | 4485:<br>0xF8  | Device enable                                                    | SBU1_H to SBUx switches | SBU2_H to SBUx switches   | DN_L to DN or L switches  | DP_R to DP or R switches  | Sense to GSBUs switches  | MIC to SBUx switches     | AGND to SBUx switches |  |
|      |                                                          |      | 4485B:<br>0x98 |                                                                  |                         |                           |                           |                           |                          |                          |                       |  |
| 05H  | Switch select                                            | R/W  | 0x18           | USB2 switch select                                               | SBU1_H switches         | SBU2_H switches           | DN_L to DN1 or L switches | DP_R to DP1 or R switches | Sense to GSBUs switches  | MIC to SBUx switches     | AGND to SBUx switches |  |
| 06H  | Switch status0                                           | R    | 0x05           | Reserved [7:6]                                                   |                         | Sense switch status [5:4] |                           | DP_R switch status [3:2]  |                          | DN_L switch status [1:0] |                       |  |
| 07H  | Switch status1                                           | R    | 4485:<br>0x23  | Reserved [7:6]                                                   |                         | SBU2 switch status [5:3]  |                           |                           | SBU1 switch status [2:0] |                          |                       |  |
|      |                                                          |      | 4485B:<br>0x00 |                                                                  |                         |                           |                           |                           |                          |                          |                       |  |
| 08H  | Audio switch left channel turn-on control                | R/W  | 0x01           | Audio switch left channel slow control                           |                         |                           |                           |                           |                          |                          |                       |  |
| 09H  | Audio switch right channel turn-on control               | R/W  | 0x01           | Audio switch right channel slow control                          |                         |                           |                           |                           |                          |                          |                       |  |
| 0AH  | MIC switch turn-on control                               | R/W  | 0x01           | MIC switch slow control                                          |                         |                           |                           |                           |                          |                          |                       |  |
| 0BH  | Sense switch turn-on control                             | R/W  | 0x01           | Sense switch slow control                                        |                         |                           |                           |                           |                          |                          |                       |  |
| 0CH  | Audio ground switch turn-on control                      | R/W  | 0x01           | Audio ground switch slow control                                 |                         |                           |                           |                           |                          |                          |                       |  |
| 0DH  | Timing delay between R switch enable and switch on order | R/W  | 0x00           | Timing delay between R switch enable and switch on order control |                         |                           |                           |                           |                          |                          |                       |  |

|     |                                                                     |     |      |                                                                             |                                         |                       |                                       |                                                                |                                                         |                                                |
|-----|---------------------------------------------------------------------|-----|------|-----------------------------------------------------------------------------|-----------------------------------------|-----------------------|---------------------------------------|----------------------------------------------------------------|---------------------------------------------------------|------------------------------------------------|
| 0EH | Timing delay between MIC switch enable and switch on order          | R/W | 0x00 | Timing delay between MIC switch enable and switch on order control          |                                         |                       |                                       |                                                                |                                                         |                                                |
| 0FH | Timing delay between Sense switch enable and switch on order        | R/W | 0x00 | Timing delay between sense switch enable and switch on order control        |                                         |                       |                                       |                                                                |                                                         |                                                |
| 10H | Timing delay between Audio ground switch enable and switch on order | R/W | 0x00 | Timing delay between audio ground switch enable and switch on order control |                                         |                       |                                       |                                                                |                                                         |                                                |
| 11H | Audio accessory status                                              | R   | 0x01 | Reserved [7:2]                                                              |                                         |                       |                                       |                                                                | CC_IN                                                   | Reserved                                       |
| 12H | Function enable                                                     | R/W | 0x00 | OVP threshold voltage configuration [7:6]                                   | Current source for resistance detection | Role of Pin C2 and C3 | Slow turn on control enable           | MIC auto break out control enable                              | Moisture detection enable                               | Audio jack detection and configurati-on enable |
| 13H | Detection control0                                                  | R/W | 0x00 | Moisture detection force off control                                        | Reserved [6:4]                          |                       | Current source for moisture detection | Select the pin for moisture detection in single-pin mode [2:0] |                                                         |                                                |
| 14H | Single-pin mode resistor detection results                          | R   | 0xFF | Moisture detection result in single-pin mode with current source enabled    |                                         |                       |                                       |                                                                |                                                         |                                                |
| 15H | Moisture resistor detection threshold                               | R/W | 0x16 | Threshold moisture detection with current source enabled                    |                                         |                       |                                       |                                                                |                                                         |                                                |
| 16H | Function control1                                                   | R/W | 0x00 | Reserved [7:3]                                                              |                                         |                       |                                       | Select moisture detection mode                                 | Set the time span between two moisture detections [1:0] |                                                |
| 17H | MIC detection status                                                | R   | 0x01 | Reserved [7:4]                                                              |                                         |                       | 4 pole                                | 4 pole                                                         | 3 pole                                                  | No audio                                       |

|     |                                                   |     |      |                                                                           |                                              |                    |                                         |                               |                                    |                   |
|-----|---------------------------------------------------|-----|------|---------------------------------------------------------------------------|----------------------------------------------|--------------------|-----------------------------------------|-------------------------------|------------------------------------|-------------------|
| 18H | System flag                                       | R/C | 0x00 | Reserved [7:4]                                                            |                                              | Watchdog timeout   | Audio jack detection & Configuration    | Moisture detection error      | Detection completion               |                   |
| 19H | System mask                                       | R/W | 0×00 | Reserved [7:4]                                                            |                                              | Watchdog timeout   | Audio jack detection and configura-tion | Moisture detection error mask | Moisture detection completion mask |                   |
| 1CH | MIC detection threshold data0                     | R/W | 0x20 | MIC detection threshold data0                                             |                                              |                    |                                         |                               |                                    |                   |
| 1DH | MIC detection threshold data1                     | R/W | 0xFF | MIC detection threshold data1                                             |                                              |                    |                                         |                               |                                    |                   |
| 1EH | I²C reset                                         | W/C | 0x00 | Reserved [7:1]                                                            |                                              |                    |                                         |                               | I²C reset                          |                   |
| 1FH | Bias current setting                              | R/W | 0x07 | Reserved [7:3]                                                            |                                              |                    | Bias current setting [2:0]              |                               |                                    |                   |
| 20H | Watchdog setting                                  | R/W | 0x03 | Watchdog enable                                                           | Reserved [6:3]                               |                    | Watchdog timer [2:0]                    |                               |                                    |                   |
| 21H | Timing delay setting                              | R/W | 0x00 | Timing delay between L switch enable and switch on order                  |                                              |                    |                                         |                               |                                    |                   |
| 30H | Detection data1                                   | R   | 0x00 | Moisture detection result in single-pin mode with current source disabled |                                              |                    |                                         |                               |                                    |                   |
| 31H | Detection control1                                | R/W | 0x00 | Reserved [7:6]                                                            | Multi-pin mode moisture detection blank time | Select pin (CC_IN) | Select pin (DP_R)                       | Select pin (DN_L)             | Select pin (SBU1)                  | Select pin (SBU2) |
| 32H | Moisture voltage detection threshold              | R/W | 0x00 | Threshold for moisture detection with current source disabled             |                                              |                    |                                         |                               |                                    |                   |
| 33H | Multi-pin mode resistor detection result of CC_IN | R   | 0xFF | Moisture detection result in multi-pin mode with current source enabled   |                                              |                    |                                         |                               |                                    |                   |
| 34H | Multi-pin mode resistor detection result of DP_R  | R   | 0xFF | Moisture detection result in multi-pin mode with current source enabled   |                                              |                    |                                         |                               |                                    |                   |

|     |                                                           |   |      |                                                                          |
|-----|-----------------------------------------------------------|---|------|--------------------------------------------------------------------------|
| 35H | Multi-pin mode<br>resistor<br>detection result<br>of DN_L | R | 0xFF | Moisture detection result in multi-pin mode with current source enabled  |
| 36H | Multi-pin mode<br>resistor<br>detection result<br>of SBU1 | R | 0xFF | Moisture detection result in multi-pin mode with current source enabled  |
| 37H | Multi-pin mode<br>resistor<br>detection result<br>of SBU2 | R | 0xFF | Moisture detection result in multi-pin mode with current source enabled  |
| 38H | Multi-pin mode<br>voltage<br>detection result<br>of CC_IN | R | 0x00 | Moisture detection result in multi-pin mode with current source disabled |
| 39H | Multi-pin mode<br>voltage<br>detection result<br>of DP_R  | R | 0x00 | Moisture detection result in multi-pin mode with current source disabled |
| 3A  | Multi-pin mode<br>voltage<br>detection result<br>of DN_L  | R | 0x00 | Moisture detection result in multi-pin mode with current source disabled |
| 3B  | Multi-pin mode<br>voltage<br>detection result<br>of SBU1  | R | 0x00 | Moisture detection result in multi-pin mode with current source disabled |
| 3C  | Multi-pin mode<br>voltage<br>detection result<br>of SBU2  | R | 0x00 | Moisture detection result in multi-pin mode with current source disabled |



## 8.1. I<sup>2</sup>C slave address

| Bit7 | Bit6 | Bit5 | Bit4 | Bit3 | Bit2 | Bit1 | Bit0 |
|------|------|------|------|------|------|------|------|
| 1    | 0    | 0    | 0    | 0    | 1    | 0    | R/W  |

## 8.2. Register definition

### 8.2.1. Device ID

Address: 00h

Reset Value: 8'b 1111\_0110

Type: Read

| Bits  | Name        | Size | Description         |
|-------|-------------|------|---------------------|
| [7:6] | Vendor ID   | 2    | Vendor ID           |
| [5:3] | Version ID  | 3    | Device version ID   |
| [2:0] | Revision ID | 3    | Revision history ID |

### 8.2.2. OVP interrupt flag

Address: 02h

Reset Value: 8'b 0000\_0000

Type: Read Clear

| Bits  | Name             | Size | Description                                                                             |
|-------|------------------|------|-----------------------------------------------------------------------------------------|
| [7:6] | Reserved         | 2    | Do not use                                                                              |
| 5     | DP_R OVP         | 1    | 0: OVP event has not occurred<br>1: OVP event has occurred                              |
| 4     | DN_L OVP         | 1    | 0: OVP event has not occurred<br>1: OVP event has occurred                              |
| [3:2] | SBU1    SBU2 OVP | 2    | 0: OVP event has not occurred<br>1: At least one of SBU1 or SBU2 OVP event has occurred |
| 1     | GSRU1 OVP        | 1    | 0: OVP event has not occurred<br>1: OVP event has occurred                              |
| 0     | GSRU2 OVP        | 1    | 0: OVP event has not occurred<br>1: OVP event has occurred                              |

### 8.2.3. OVP status

Address: 03h

Reset Value: 8'b 0000\_0000

Type: Read

| Bits  | Name            | Size | Description                                                |
|-------|-----------------|------|------------------------------------------------------------|
| [7:6] | Reserved        | 2    | Do not use                                                 |
| 5     | OVP on DP_R PIN | 1    | 0: OVP event has not occurred<br>1: OVP event has occurred |
| 4     | OVP on DN_L PIN | 1    | 0: OVP event has not occurred<br>1: OVP event has occurred |

|       |                   |   |                                                                                         |
|-------|-------------------|---|-----------------------------------------------------------------------------------------|
| [3:2] | SBU1    SBU2 OVP  | 2 | 0: OVP event has not occurred<br>1: At least one of SBU1 or SBU2 OVP event has occurred |
| 1     | OVP on GSBUS1 PIN | 1 | 0: OVP event has not occurred<br>1: OVP event has occurred                              |
| 0     | OVP on GSBUS2 PIN | 1 | 0: OVP event has not occurred<br>1: OVP event has occurred                              |

#### 8.2.4. Switching setting enable

Address: 04h

Reset Value: DIO4485: 8'b 1111\_1000

DIO4485B: 8'b 1001\_1000

Type: Read/Write

| Bits | Name                        | Size | Description                                                                                                               |
|------|-----------------------------|------|---------------------------------------------------------------------------------------------------------------------------|
| 7    | Device enable               | 1    | 1: Device enable.<br>0: Device disable; L, R pull down by 10 kΩ and other switch nodes will be high-Z for positive input. |
| 6    | SBU1_H to SBUx switches     | 1    | 0: Switch disable; SBU1_H will be high-Z for positive input<br>1: Switch enable                                           |
| 5    | SBU2_H to SBUx switches     | 1    | 0: Switch disable; SBU2_H will be high-Z for positive input<br>1: Switch enable                                           |
| 4    | DN_L to DN1/2 or L switches | 1    | 0: Switch disable; DN_L, DN1/2 will be high-Z for positive input. L pull down by 10 kΩ<br>1: Switch enable                |
| 3    | DP_R to DP1/2 or R switches | 1    | 0: Switch disable; DP_R, DP1/2 will be high-Z for positive input. R pull down by 10 kΩ<br>1: Switch enable                |
| 2    | Sense to GSBUSx switches    | 1    | 0: Switch disable; Sense, GSBUS1 and GSBUS2 will be high-Z for positive input<br>1: Switch enable                         |
| 1    | MIC to SBUx switches        | 1    | 0: Switch disable: MIC will be high-Z for positive input.<br>1: Switch enable                                             |
| 0    | AGND to SBUx switches       | 1    | 0: Switch disable: AGND will be high-Z for positive input.<br>1: Switch enable                                            |

#### 8.2.5. Switch select

Address: 05h

Reset Value: 8'b 0001\_1000

Type: Read/Write

| Bits | Name               | Size | Description                                                                                                                                                            |
|------|--------------------|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 7    | USB2 switch select | 1    | 0: USB2 off. USB1 or Audio switch depend on 05h, bit [4:3] and 04h, bit [4:3]<br>1: DP/R~DP2, DN/L~DN2 switches ON, if 04h, bit [4:3] = '11' and 05h, bit [4:3] = '11' |

|   |                           |   |                                                            |
|---|---------------------------|---|------------------------------------------------------------|
| 6 | SBU1_H switches           | 1 | 0: SBU1_H to SBU1 switch ON<br>1: SBU1_H to SBU2 switch ON |
| 5 | SBU2_H switches           | 1 | 0: SBU2_H to SBU2 switch ON<br>1: SBU2_H to SBU1 switch ON |
| 4 | DN_L to DN1 or L switches | 1 | 0: DN_L to L switch ON<br>1: DN_L to DN1 switch ON         |
| 3 | DP_R to DP1 or R switches | 1 | 0: DP_R to R switch ON<br>1: DP_R to DP1 switch ON         |
| 2 | Sense to GSBUX switches   | 1 | 0: Sense to GSBU1 switch ON<br>1: Sense to GSBU2 switch ON |
| 1 | MIC to SBUx switches      | 1 | 0: MIC to SBU2 switch ON<br>1: MIC to SBU1 switch ON       |
| 0 | AGND to SBUx switches     | 1 | 0: AGND to SBU1 switch ON<br>1: AGND to SBU2 switch ON     |

**Note:** If want to change to USB2 mode, you must first write 0x05h = 0x98h, then write 0x04h = 0x98h

### 8.2.6. Switch status0

Address: 06h

Reset Value: 8'b 0000\_0101

Type: Read

| Bits  | Name                | Size | Description                                                                                                               |
|-------|---------------------|------|---------------------------------------------------------------------------------------------------------------------------|
| [7:6] | Reserved            | 2    | Do not use                                                                                                                |
| [5:2] | Sense switch status | 2    | 00: Sense switch is Open / Not Connected<br>01: Sense connected to GSBU1<br>10: Sense connected to GSBU2<br>11: Not valid |
| [3:2] | DP_R switch status  | 2    | 00: DP_R Switch Open / Not Connected<br>01: DP_R connected to DP1<br>10: DP_R connected to R<br>11: DP_R connected to DP2 |
| [1:0] | DN_L switch status  | 2    | 00: DN_L Switch Open / Not Connected<br>01: DN_L connected to DN1<br>10: DN_L connected to L<br>11: DN_L connected to DN2 |

### 8.2.7. Switch status1

Address: 07h

Reset Value: DIO4485: 8' b 0010\_0011

DIO4485B: 8' b 0000\_0000

Type: Read

| Bits  | Name               | Size | Description                                                                                                                                                                                                                                    |
|-------|--------------------|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:6] | Reserved           | 2    | Do not use                                                                                                                                                                                                                                     |
| [5:3] | SBU2 switch status | 3    | 000: SBU2 switch is Open / Not Connected<br>001: SBU2 connected to MIC<br>010: SBU2 connected to AGND<br>011: SBU2 connected to SBU1_H<br>100: SBU2 connected to SBU2_H<br>101: SBU2 connected both SBU1_H and SBU2_H<br>110...111: Do not use |
| [2:0] | SBU1 switch status | 3    | 000: SBU1 switch is Open / Not Connected<br>001: SBU1 connected to MIC<br>010: SBU1 connected to AGND<br>011: SBU1 connected to SBU1_H<br>100: SBU1 connected to SBU2_H<br>101: SBU1 connected both SBU1_H and SBU2_H<br>110...111: Do not use |

### 8.2.8. Audio switch left channel slow turn-on

Address: 08h

Reset Value: 8'b 0000\_0001

Type: Read/Write

| Bits  | Name                               | Size | Description             |
|-------|------------------------------------|------|-------------------------|
| [7:0] | Switch turn on rising time setting | 8    | 11111111: 25600 $\mu$ s |
|       |                                    |      | ...                     |
|       |                                    |      | 00000001: 200 $\mu$ s   |
|       |                                    |      | 00000000: 100 $\mu$ s   |

### 8.2.9. Audio switch right channel slow turn-on

Address: 09h

Reset Value: 8'b 0000\_0001

Type: Read/Write

| Bits  | Name                               | Size | Description             |
|-------|------------------------------------|------|-------------------------|
| [7:0] | Switch turn on rising time setting | 8    | 11111111: 25600 $\mu$ s |
|       |                                    |      | ...                     |
|       |                                    |      | 00000001: 200 $\mu$ s   |
|       |                                    |      | 00000000: 100 $\mu$ s   |

### 8.2.10. MIC switch slow turn-on

Address: 0Ah

Reset Value: 8'b 0000\_0001

Type: Read/Write

| Bits  | Name                               | Size | Description             |
|-------|------------------------------------|------|-------------------------|
| [7:0] | Switch turn on rising time setting | 8    | 11111111: 25700 $\mu$ s |
|       |                                    |      | ...                     |
|       |                                    |      | 00000010: 350 $\mu$ s   |
|       |                                    |      | 00000001: 250 $\mu$ s   |
|       |                                    |      | 00000000: not valid     |

### 8.2.11. Sense switch slow turn-on

Address: 0Bh

Reset Value: 8'b 0000\_0001

Type: Read/Write

| Bits  | Name                               | Size | Description             |
|-------|------------------------------------|------|-------------------------|
| [7:0] | Switch turn-on rising time setting | 8    | 11111111: 25600 $\mu$ s |
|       |                                    |      | ...                     |
|       |                                    |      | 00000001: 200 $\mu$ s   |
|       |                                    |      | 00000000: 100 $\mu$ s   |

### 8.2.12. Audio ground switch slow turn-on

Address: 0Ch

Reset Value: 8'b 0000\_0001

Type: Read/Write

| Bits  | Name                               | Size | Description              |
|-------|------------------------------------|------|--------------------------|
| [7:0] | Switch turn-on rising time setting | 8    | 11111111: 179000 $\mu$ s |
|       |                                    |      | ...                      |
|       |                                    |      | 00000001: 1400 $\mu$ s   |
|       |                                    |      | 00000000: 700 $\mu$ s    |

### 8.2.13. Timing delay between R switch enable and switch on order

Address: 0Dh

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                 | Size | Description           |
|-------|----------------------|------|-----------------------|
| [7:0] | Delay timing setting | 8    | 11111111: 102 ms      |
|       |                      |      | 11111110: 101.6 ms    |
|       |                      |      | ...                   |
|       |                      |      | 00000001: 400 $\mu$ s |
|       |                      |      | 00000000: 0 $\mu$ s   |

#### 8.2.14. Timing delay between MIC switch enable and switch on order

Address: 0Eh

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                 | Size | Description             |
|-------|----------------------|------|-------------------------|
| [7:0] | Delay timing setting | 8    | 11111111: 102 ms        |
|       |                      |      | 11111110: 101.6 $\mu$ s |
|       |                      |      | ...                     |
|       |                      |      | 00000001: 400 $\mu$ s   |
|       |                      |      | 00000000: 0 $\mu$ s     |

#### 8.2.15. Timing delay between sense switch enable and switch on order

Address: 0Fh

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                 | Size | Description           |
|-------|----------------------|------|-----------------------|
| [7:0] | Delay timing setting | 8    | 11111111: 102 ms      |
|       |                      |      | 11111110: 101.6 ms    |
|       |                      |      | ...                   |
|       |                      |      | 00000001: 400 $\mu$ s |
|       |                      |      | 00000000: 0 $\mu$ s   |

#### 8.2.16. Timing delay between audio ground switch enable and switch on order

Address: 10h

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                 | Size | Description           |
|-------|----------------------|------|-----------------------|
| [7:0] | Delay timing setting | 8    | 11111111: 102 ms      |
|       |                      |      | 11111110: 101.6 ms    |
|       |                      |      | ...                   |
|       |                      |      | 00000001: 400 $\mu$ s |
|       |                      |      | 00000000: 0 $\mu$ s   |

#### 8.2.17. Audio accessory status

Address: 11h

Reset Value: 8'b 0000\_0001

Type: Read

| Bits  | Name     | Size | Description                          |
|-------|----------|------|--------------------------------------|
| [7:2] | Reserved | 6    | Do not use                           |
| 1     | CC_IN    | 1    | 0: CC_IN < 1.2 V<br>1: CC_IN > 1.5 V |
| 0     | Reserved | 1    | Do not use                           |

### 8.2.18. Function enable

Address: 12h

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                                          | Size | Description                                                                                                                                  |
|-------|-----------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------------------------------|
| [7:6] | OVP threshold voltage configuration           | 2    | 00: 4.4 V<br>01: 4.6 V<br>10: 4.8 V<br>11: 5.0 V                                                                                             |
| 5     | Current source for resistance detection       | 1    | If 0×13h bit [3] = 0.<br>0: 4.5 μA<br>1: 0.9 μA                                                                                              |
| 4     | Role of pin C2 and C3                         | 1    | 0: Set C2 as DET and C3 as INT<br>1: Set C2 as COMPIN and C3 as COMPOUT                                                                      |
| 3     | Slow turn on control enable                   | 1    | 1: Enable<br>0: Disable                                                                                                                      |
| 2     | MIC auto break out control enable             | 1    | 1: Enable<br>0: Disable                                                                                                                      |
| 1     | Moisture detection enable                     | 1    | 1: Enable. It would return to '0' after the detection was finished.<br>0: Disable<br>(This bit can be reset by POR, I <sup>2</sup> C or WTD) |
| 0     | Audio jack detection and configuration enable | 1    | 1: Enable; will be changed to '0' after audio jack detection and configuration<br>0: Disable                                                 |

### 8.2.19. Detection control0

Address: 13h

Reset Value: 8'b 0000\_0000

Type: R/W

| Bits  | Name                                                     | Size | Description                                                                                                                 |
|-------|----------------------------------------------------------|------|-----------------------------------------------------------------------------------------------------------------------------|
| 7     | Moisture detection force off control                     | 1    | 0: Moisture detection on and off control would follow 0×12h bit [1].<br>1: Moisture detection would be turned off forcibly. |
| [6:4] | Reserved                                                 | 3    | Do not use.                                                                                                                 |
| 3     | Current source for moisture detection                    | 1    | 0: Enable<br>1: Disable                                                                                                     |
| [2:0] | Select the pin for moisture detection in single-pin mode | 3    | 000: CC_IN<br>001: DP_R<br>010: DN_L<br>011: SBU1<br>100: SBU2<br>101...111: Reserved                                       |

### 8.2.20. Single-pin mode resistor detection results

Address: 14h

Reset Value: 11111111

Type: Read

| Bits  | Name                                                                     | Size | Description                                                                                   |
|-------|--------------------------------------------------------------------------|------|-----------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection result in single-pin mode with current source enabled | 8    | 0x00 ~ 0xFF:<br>2 kΩ * Bits, with 0x12h bit [5] = 0;<br>10 kΩ * Bits, with 0x12h bit [5] = 1. |

### 8.2.21. Moisture resistor detection threshold

Address: 15h

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                                                          | Size | Description                                                                                                                                                               |
|-------|---------------------------------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:0] | Threshold for moisture detection with current source enabled. | 8    | DIO4485/4485B would issue 'Moisture detection error' once any contents from 0x14h (in single pin mode) or 0x33h ~ 0x37h (in multi-pin mode) is lower than this threshold. |

### 8.2.22. Function control1

Address: 16h

Reset Value: 8'b 0000\_0001

Type: Read/Write

| Bits  | Name                                              | Size | Description                                                                                                                                                                                                                                                                                             |
|-------|---------------------------------------------------|------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:3] | Reserved                                          | 5    | Do not use.                                                                                                                                                                                                                                                                                             |
| 2     | Select moisture detection mode                    | 1    | 0: Single-pin mode, will perform moisture on single pin.<br>1: Multi-pin mode, will perform moisture on multiple pins.                                                                                                                                                                                  |
| [1:0] | Set the time span between two moisture detections | 2    | 00: No polling.<br>In single-pin mode, perform single detection for the selected pin (0x13h bit [2:0]).<br>In multi-pin mode, perform single detection for all selected pins (0x31h bit [4:0]).<br>01: Polling with 100 ms time span<br>10: Polling with 1s time span<br>11: Polling with 10s time span |

### 8.2.23. MIC detection status

Address: 17h

Reset Value: 8'b 0000\_0001

Type: Read

| Bits  | Name     | Size | Description |
|-------|----------|------|-------------|
| [7:4] | Reserved | 4    | Do not use  |



|   |                    |   |                                                          |
|---|--------------------|---|----------------------------------------------------------|
| 3 | 4 pole             | 1 | 1: 4 Pole SBU2 to MIC, SBU1 to audio ground<br>0: others |
| 2 | 4 pole             | 1 | 1: 4 Pole SBU1 to MIC, SBU2 to audio ground<br>0: others |
| 1 | 3 pole             | 1 | 1: 3 pole<br>0: others                                   |
| 0 | No audio accessory | 1 | 1: No audio accessory<br>0: Audio accessory attached     |

### 8.2.24. System flag

Address: 18h

Reset Value: 8'b 0000\_0000

Type: Read Clear

| Bits  | Name                                   | Size | Description                                                                                                                                                                                                                                   |
|-------|----------------------------------------|------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:4] | Reserved                               | 4    | Do not use                                                                                                                                                                                                                                    |
| 3     | Watchdog timeout                       | 1    | 0: Watchdog timeout has not occurred<br>1: Watchdog timeout has occurred                                                                                                                                                                      |
| 2     | Audio jack detection and configuration | 1    | 0: Audio jack detection and configuration has not completed.<br>1: Audio jack detection and configuration is completed.                                                                                                                       |
| 1     | Moisture detection error               | 1    | 0: Moisture occurs.<br>For resistance detection, result(s) $\geq$ TH0<br>For voltage detection, result(s) $\leq$ TH1<br>1: Moisture doesn't occur.<br>For resistance detection, result(s) $<$ TH0<br>For voltage detection, result(s) $>$ TH1 |
| 0     | Moisture detection completion          | 1    | 0: Moisture detection has been not completed<br>1: Moisture detection is completed.                                                                                                                                                           |

### 8.2.25. System mask

Address: 19h

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                                        | Size | Description                                                                                                                  |
|-------|---------------------------------------------|------|------------------------------------------------------------------------------------------------------------------------------|
| [7:4] | Reserved                                    | 4    | Do not use.                                                                                                                  |
| 3     | Watchdog timeout mask                       | 1    | 0: "Watchdog timeout" bit is not masked.<br>1: "Watchdog timeout" bit is masked.                                             |
| 2     | Audio jack detection and configuration mask | 1    | 0: "Audio jack detection and configuration" bit is not masked.<br>1: "Audio jack detection and configuration" bit is masked. |
| 1     | Moisture detection error mask               | 1    | 0: "Moisture detection error" bit is not masked.<br>1: "Moisture detection error" bit is masked.                             |
| 0     | Moisture detection completion mask          | 1    | 0: "Moisture detection completion" bit is not masked.<br>1: "Moisture detection completion" bit is masked.                   |

### 8.2.26. MIC detection threshold data0

Address: 1Ch

Reset Value: 8'b 0010\_0000

Type: Write

| Bits  | Name                          | Size | Description                    |
|-------|-------------------------------|------|--------------------------------|
| [7:0] | MIC detection threshold data0 | 8    | MIC detection threshold data0. |

### 8.2.27. MIC detection threshold data1

Address: 1Dh

Reset Value: 8'b 1111\_1111

Type: Read/Write

| Bits  | Name                          | Size | Description                    |
|-------|-------------------------------|------|--------------------------------|
| [7:0] | MIC detection threshold data1 | 8    | MIC detection threshold data1. |

### 8.2.28. I<sup>2</sup>C reset

Address: 1Eh

Reset Value: 8'b 0000\_0000

Type: W/C

| Bits  | Name                   | Size | Description                             |
|-------|------------------------|------|-----------------------------------------|
| [7:1] | Reserved               | 7    | Reserved                                |
| 0     | I <sup>2</sup> C reset | 1    | 0: default<br>1: I <sup>2</sup> C reset |

### 8.2.29. Bias current setting

Address: 1Fh

Reset Value: 8'b 0000\_0111

Type: Read/Write

| Bits  | Name                 | Size | Description                                                                  |
|-------|----------------------|------|------------------------------------------------------------------------------|
| [7:3] | Reserved             | 4    | Do not use                                                                   |
| [2:0] | Bias current setting | 4    | Setting bias current for audio jack detection.<br>0000 ~ 1111: Bits × 100 μA |

### 8.2.30. Watchdog setting

Address: 20h

Reset Value: 8'b 0000\_0011

Type: Read/Write

| Bits  | Name            | Size | Description                                 |
|-------|-----------------|------|---------------------------------------------|
| 7     | Watchdog enable | 1    | 0: Watchdog disabled<br>1: Watchdog enabled |
| [6:3] | Reserved        | 4    | Do not use                                  |

|       |                |   |                                                                                                     |
|-------|----------------|---|-----------------------------------------------------------------------------------------------------|
| [2:0] | Watchdog timer | 3 | 000: 0.5 s<br>001: 1 s<br>010: 2 s<br>011: 5 s<br>100: 10 s<br>101: 30 s<br>110: 60 s<br>111: 5 min |
|-------|----------------|---|-----------------------------------------------------------------------------------------------------|

### 8.2.31. Timing delay between L switch enable and switch on order

Address: 21h

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                 | Size | Description           |
|-------|----------------------|------|-----------------------|
| [7:0] | Delay timing setting | 8    | 11111111: 102 ms      |
|       |                      |      | 11111110: 101.6 ms    |
|       |                      |      | ...                   |
|       |                      |      | 00000001: 400 $\mu$ s |
|       |                      |      | 00000000: 0 $\mu$ s   |

### 8.2.32. Detection data1

Address: 30h

Reset Value: 8'b 0000\_0000

Type: Read

| Bits  | Name            | Size | Description                                                                                                                         |
|-------|-----------------|------|-------------------------------------------------------------------------------------------------------------------------------------|
| [7:0] | Detection data1 | 8    | Moisture detection result in single-pin mode with current source disabled:<br>0x00 ~ 0xFF: Bits $\times$ 9 $\times$ 0.001 [Unit: V] |

### 8.2.33. Detection control1

Address: 31h

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                                         | Size | Description                                                                                       |
|-------|----------------------------------------------|------|---------------------------------------------------------------------------------------------------|
| [7:6] | Reserved                                     | 2    | Do not use.                                                                                       |
| 5     | Multi-pin mode moisture detection blank time | 1    | In multi-pin mode, set blank time between detections for different pins.<br>0: 10 ms<br>1: 100 ms |
| 4     | Select pin (CC_IN)                           | 1    | Select pin for moisture detection in multi-pin mode.<br>0: not selected<br>1: selected            |

|   |                   |   |                                                                                        |
|---|-------------------|---|----------------------------------------------------------------------------------------|
| 3 | Select pin (DP_R) | 1 | Select pin for moisture detection in multi-pin mode.<br>0: not selected<br>1: selected |
| 2 | Select pin (DN_L) | 1 | Select pin for moisture detection in multi-pin mode.<br>0: not selected<br>1: selected |
| 1 | Select pin (SBU1) | 1 | Select pin for moisture detection in multi-pin mode.<br>0: not selected<br>1: selected |
| 0 | Select pin (SBU2) | 1 | Select pin for moisture detection in multi-pin mode.<br>0: not selected<br>1: selected |

### 8.2.34. Moisture voltage detection threshold

Address: 32h

Reset Value: 8'b 0000\_0000

Type: Read/Write

| Bits  | Name                                                          | Size | Description                                                                                                                                                                                                                                           |
|-------|---------------------------------------------------------------|------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:0] | Threshold for moisture detection with current source disabled | 8    | Threshold for moisture detection with current source disabled.<br>DIO4485/DIO4485B would issue "Moisture detection error" as soon as any contents from 0x30h (in single-pin mode) or 0x38h ~ 0x3Ch (in multi-pin mode) is higher than this threshold. |

### 8.2.35. Multi-pin mode resistor detection result of CC\_IN

Address: 33h

Reset Value: 8'b 1111\_1111

Type: Read

| Bits  | Name                                         | Size | Description                                                                                                                                                             |
|-------|----------------------------------------------|------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (CC_IN) | 8    | Moisture detection result in multi-pin mode with current source enabled:<br>0x00 ~ 0xFF: 2 kΩ * Bits, with 0x12h bit [5] = 0;<br>10 kΩ * Bits,, with 0x12h bit [5] = 1. |

### 8.2.36. Multi-pin mode resistor detection result of DP\_R

Address: 34h

Reset Value: 8'b 1111\_1111

Type: Read

| Bits  | Name                                        | Size | Description                                                                                                                                                            |
|-------|---------------------------------------------|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (DP_R) | 8    | Moisture detection result in multi-pin mode with current source enabled:<br>0x00 ~ 0xFF: 2 kΩ * Bits, with 0x12h bit [5] = 0;<br>10 kΩ * Bits, with 0x12h bit [5] = 1. |

**8.2.37. Multi-pin mode resistor detection result of DN\_L**

Address: 35h

Reset Value: 8'b 1111\_1111

Type: Read

| Bits  | Name                                        | Size | Description                                                                                                                                                            |
|-------|---------------------------------------------|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (DN_L) | 8    | Moisture detection result in multi-pin mode with current source enabled:<br>0x00 ~ 0xFF: 2 kΩ * Bits, with 0x12h bit [5] = 0;<br>10 kΩ * Bits, with 0x12h bit [5] = 1. |

**8.2.38. Multi-pin mode resistor detection result of SBU1**

Address: 36h

Reset Value: 8'b 1111\_1111

Type: Read

| Bits  | Name                                        | Size | Description                                                                                                                                                            |
|-------|---------------------------------------------|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (SBU1) | 8    | Moisture detection result in multi-pin mode with current source enabled:<br>0x00 ~ 0xFF: 2 kΩ * Bits, with 0x12h bit [5] = 0;<br>10 kΩ * Bits, with 0x12h bit [5] = 1. |

**8.2.39. Multi-pin mode resistor detection result of SBU2**

Address: 37h

Reset Value: 8'b 1111\_1111

Type: Read

| Bits  | Name                                        | Size | Description                                                                                                                                                            |
|-------|---------------------------------------------|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (SBU2) | 8    | Moisture detection result in multi-pin mode with current source enabled:<br>0x00 ~ 0xFF: 2 kΩ * Bits, with 0x12h bit [5] = 0;<br>10 kΩ * Bits, with 0x12h bit [5] = 1. |

**8.2.40. Multi-pin mode voltage detection result of CC\_IN**

Address: 38h

Reset Value: 8'b 0000\_0000

Type: Read

| Bits  | Name                                         | Size | Description                                                                                                          |
|-------|----------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (CC_IN) | 8    | Moisture detection result in multi-pin mode with current source disabled.<br>0x00 ~ 0xFF: Bits × 9 × 0.001 [unit: V] |

**8.2.41. Multi-pin mode voltage detection result of DP\_R**

Address: 39h

Reset Value: 8'b 0000\_0000

Type: Read

| Bits  | Name                                        | Size | Description                                                                                                          |
|-------|---------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (DP_R) | 8    | Moisture detection result in multi-pin mode with current source disabled.<br>0x00 ~ 0xFF: Bits × 9 × 0.001 [unit: V] |

**8.2.42. Multi-pin mode voltage detection result of DN\_L**

Address: 3A

Reset Value: 8'b 0000\_0000

Type: Read

| Bits  | Name                                        | Size | Description                                                                                                          |
|-------|---------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (DN_L) | 8    | Moisture detection result in multi-pin mode with current source disabled.<br>0x00 ~ 0xFF: Bits × 9 × 0.001 [unit: V] |

**8.2.43. Multi-pin mode voltage detection result of SBU1**

Address: 3B

Reset Value: 8'b 0000\_0000

Type: Read

| Bits  | Name                                        | Size | Description                                                                                                          |
|-------|---------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (SBU1) | 8    | Moisture detection result in multi-pin mode with current source disabled.<br>0x00 ~ 0xFF: Bits × 9 × 0.001 [unit: V] |

**8.2.44. Multi-pin mode voltage detection result of SBU2**


Address: 3C

Reset Value: 8'b 0000\_0000


Type: Read

| Bits  | Name                                        | Size | Description                                                                                                          |
|-------|---------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------|
| [7:0] | Moisture detection in multi-pin mode (SBU2) | 8    | Moisture detection result in multi-pin mode with current source disabled.<br>0x00 ~ 0xFF: Bits × 9 × 0.001 [unit: V] |


## 9. Physical Dimensions: WLCSP-25



TOP VIEW  
(MARK SIDE)



BOTTOM VIEW  
(BALL SIDE)



SIDE VIEW

| Common Dimensions<br>(Units of measure = Millimeter) |           |       |       |
|------------------------------------------------------|-----------|-------|-------|
| Symbol                                               | Min       | Nom   | Max   |
| A                                                    | 0.541     | 0.586 | 0.631 |
| A1                                                   | 0.190     | 0.210 | 0.230 |
| A2                                                   | 0.351     | 0.376 | 0.401 |
| D                                                    | 2.250     | 2.280 | 2.310 |
| D1                                                   | 1.600 BSC |       |       |
| E                                                    | 2.210     | 2.240 | 2.270 |
| E1                                                   | 1.600 BSC |       |       |
| b                                                    | 0.238     | 0.258 | 0.278 |
| e                                                    | 0.400 BSC |       |       |
| x1                                                   | 0.320 REF |       |       |
| x2                                                   | 0.320 REF |       |       |
| y1                                                   | 0.340 REF |       |       |
| y2                                                   | 0.340 REF |       |       |

### **Disclaimer**

This specification and information contained herein are provided on an “AS IS” basis and WITH ALL FAULTS. All product specifications, statements, information, and data (collectively, the “Information”) in this datasheet or made available on the website of [www.dioo.com](http://www.dioo.com) are subject to change without notice. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to his/her application. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, express or implied.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DIOO:](#)

[DIO4485WL25](#) [DIO4485BWL25](#)