

74HC4020; 74HCT4020

14-stage binary ripple counter

Rev. 6 — 3 February 2016

Product data sheet

1. General description

The 74HT4020; 74HCT4020 is a 14-stage binary ripple counter with a clock input (CP), an overriding asynchronous master reset input (MR) and 12 buffered parallel outputs (Q0, and Q3 to Q13). The counter advances on the HIGH-to-LOW transition of CP. A HIGH on MR clears all counter stages and forces all outputs LOW, independent of the state of CP. Each counter stage is a static toggle flip-flop. This device features reduced input threshold levels to allow interfacing to TTL logic levels. Inputs also include clamp diodes, this enables the use of current limiting resistors to interface inputs to voltages in excess of V_{CC} .

2. Features and benefits

- Wide supply voltage range from 2.0 V to 6.0 V
- Input levels:
 - ◆ For 74HC4020: CMOS level
 - ◆ For 74HCT4020: TTL level
- Multiple package options
- Complies with JEDEC standard no. 7A
- Specified from -40 °C to $+85\text{ °C}$ and from -40 °C to $+125\text{ °C}$

3. Applications

- Frequency dividing circuits
- Time delay circuits
- Control counters

4. Ordering information

Table 1. Ordering information

| Type number | Package | | | |
|-------------|-------------------------------------|--------|---|----------|
| | Temperature range | Name | Description | Version |
| 74HC4020D | -40 °C to $+125\text{ °C}$ | SO16 | plastic small outline package; 16 leads; body width 3.9 mm | SOT109-1 |
| 74HCT4020D | | | | |
| 74HC4020DB | -40 °C to $+125\text{ °C}$ | SSOP16 | plastic shrink small outline package; 16 leads; body width 5.3 mm | SOT338-1 |
| 74HCT4020DB | | | | |

Table 1. Ordering information ...continued

| Type number | Package | | | Version |
|-------------|-------------------|----------|--|----------|
| | Temperature range | Name | Description | |
| 74HC4020PW | -40 °C to +125 °C | TSSOP16 | plastic thin shrink small outline package; 16 leads; body width 4.4 mm | SOT403-1 |
| 74HCT4020PW | | | | |
| 74HC4020BQ | -40 °C to +125 °C | DHVQFN16 | plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 × 3.5 × 0.85 mm | SOT763-1 |
| 74HCT4020BQ | | | | |

5. Functional diagram




Fig 1. Functional diagram




Fig 2. Logic symbol

Fig 3. IEC logic symbol




Fig 4. Logic diagram

6. Pinning information

6.1 Pinning




Fig 5. Pin configuration SO16, SSOP16 and TSSOP16




Fig 6. Pin configuration DHVQFN16

6.2 Pin description

Table 2. Pin description

| Symbol | Pin | Description |
|---------------|--|---|
| Q0, Q3 to Q13 | 9, 7, 5, 4, 6, 13, 12, 14, 15, 1, 2, 3 | output |
| GND | 8 | ground (0 V) |
| CP | 10 | clock input (HIGH-to-LOW, edge-triggered) |
| MR | 11 | master reset input (active HIGH) |
| VCC | 16 | positive supply voltage |

7. Functional description

Table 3. Function table

| Input | | Output |
|-------|----|---------------|
| CP | MR | Q0, Q3 to Q13 |
| ↑ | L | no change |
| ↓ | L | count |
| X | H | L |

[1] H = HIGH voltage level; L = LOW voltage level; X = don't care; ↑ = LOW-to-HIGH clock transition; ↓ = HIGH-to-LOW clock transition.

7.1 Timing diagram




Fig 7. Timing diagram

8. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

| Symbol | Parameter | Conditions | Min | Max | Unit |
|-----------|-------------------------|---|------|----------|------|
| V_{CC} | supply voltage | | -0.5 | +7 | V |
| I_{IK} | input clamping current | $V_I < -0.5\text{ V}$ or $V_I > V_{CC} + 0.5\text{ V}$ | - | ± 20 | mA |
| I_{OK} | output clamping current | $V_I < -0.5\text{ V}$ or $V_I > V_{CC} + 0.5\text{ V}$ | - | ± 20 | mA |
| I_O | output current | $-0.5\text{ V} < V_O < V_{CC} + 0.5\text{ V}$ | - | ± 25 | mA |
| I_{CC} | supply current | | - | ± 50 | mA |
| I_{GND} | ground current | | - | ± 50 | mA |
| T_{stg} | storage temperature | | -65 | +150 | °C |
| P_{tot} | total power dissipation | $T_{amb} = -40\text{ °C}$ to $+125\text{ °C}$ [1] | | | |
| | | SO16, SSOP16, TSSOP16 and DHVQFN16 packages | - | 500 | mW |

- [1] For SO16 package: P_{tot} derates linearly with 8 mW/K above 70 °C.
 For SSOP16 and TSSOP16 packages: P_{tot} derates linearly with 5.5 mW/K above 60 °C.
 For DHVQFN16 package: P_{tot} derates linearly with 4.5 mW/K above 60 °C.

9. Recommended operating conditions

Table 5. Recommended operating conditions

| Symbol | Parameter | Conditions | 74HC4020 | | | 74HCT4020 | | | Unit |
|---------------------|-------------------------------------|-----------------------------------|----------|------|----------|-----------|------|----------|------|
| | | | Min | Typ | Max | Min | Typ | Max | |
| V_{CC} | supply voltage | | 2.0 | 5.0 | 6.0 | 4.5 | 5.0 | 5.5 | V |
| V_I | input voltage | | 0 | - | V_{CC} | 0 | - | V_{CC} | V |
| V_O | output voltage | | 0 | - | V_{CC} | 0 | - | V_{CC} | V |
| $\Delta t/\Delta V$ | input transition rise and fall rate | except for Schmitt trigger inputs | | | | | | | |
| | | $V_{CC} = 2.0\text{ V}$ | - | - | 625 | - | - | - | ns/V |
| | | $V_{CC} = 4.5\text{ V}$ | - | 1.67 | 139 | - | 1.67 | 139 | ns/V |
| | | $V_{CC} = 6.0\text{ V}$ | - | - | 83 | - | - | - | ns/V |
| T_{amb} | ambient temperature | | -40 | +25 | +125 | -40 | +25 | +125 | °C |

10. Static characteristics

Table 6. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

| Symbol | Parameter | Conditions | 25 °C | | | -40 °C to +85 °C | | -40 °C to +125 °C | | Unit |
|------------------|---------------------------|---|----------------|---|------|------------------|------|-------------------|------|------|
| | | | Min | Typ | Max | Min | Max | Min | Max | |
| 74HC4020 | | | | | | | | | | |
| V _{IH} | HIGH-level input voltage | V _{CC} = 2.0 V | 1.5 | 1.2 | - | 1.5 | - | 1.5 | - | V |
| | | V _{CC} = 4.5 V | 3.15 | 2.4 | - | 3.15 | - | 3.15 | - | V |
| | | V _{CC} = 6.0 V | 4.2 | 3.2 | - | 4.2 | - | 4.2 | - | V |
| V _{IL} | LOW-level input voltage | V _{CC} = 2.0 V | - | 0.8 | 0.5 | - | 0.5 | - | 0.5 | V |
| | | V _{CC} = 4.5 V | - | 2.1 | 1.35 | - | 1.35 | - | 1.35 | V |
| | | V _{CC} = 6.0 V | - | 2.8 | 1.8 | - | 1.8 | - | 1.8 | V |
| V _{OH} | HIGH-level output voltage | V _I = V _{IH} or V _{IL} | | | | | | | | |
| | | I _O = -20 μA; V _{CC} = 2.0 V | 1.9 | 2.0 | - | 1.9 | - | 1.9 | - | V |
| | | I _O = -20 μA; V _{CC} = 4.5 V | 4.4 | 4.5 | - | 4.4 | - | 4.4 | - | V |
| | | I _O = -20 μA; V _{CC} = 6.0 V | 5.9 | 6.0 | - | 5.9 | - | 5.9 | - | V |
| | | I _O = -4.0 mA; V _{CC} = 4.5 V | 3.98 | 4.32 | - | 3.84 | - | 3.7 | - | V |
| V _{OL} | LOW-level output voltage | V _I = V _{IH} or V _{IL} | | | | | | | | |
| | | I _O = 20 μA; V _{CC} = 2.0 V | - | 0 | 0.1 | - | 0.1 | - | 0.1 | V |
| | | I _O = 20 μA; V _{CC} = 4.5 V | - | 0 | 0.1 | - | 0.1 | - | 0.1 | V |
| | | I _O = 20 μA; V _{CC} = 6.0 V | - | 0 | 0.1 | - | 0.1 | - | 0.1 | V |
| | | I _O = 4.0 mA; V _{CC} = 4.5 V | - | 0.15 | 0.26 | - | 0.33 | - | 0.4 | V |
| I _I | input leakage current | V _I = V _{CC} or GND; V _{CC} = 6.0 V | - | - | ±0.1 | - | ±1 | - | ±1 | μA |
| | | I _{CC} | supply current | V _I = V _{CC} or GND; I _O = 0 A; V _{CC} = 6.0 V | - | - | 8.0 | - | 80 | - |
| C _I | input capacitance | | - | 3.5 | - | - | - | - | - | pF |
| 74HCT4020 | | | | | | | | | | |
| V _{IH} | HIGH-level input voltage | V _{CC} = 4.5 V to 5.5 V | 2.0 | 1.6 | - | 2.0 | - | 2.0 | - | V |
| V _{IL} | LOW-level input voltage | V _{CC} = 4.5 V to 5.5 V | - | 1.2 | 0.8 | - | 0.8 | - | 0.8 | V |
| V _{OH} | HIGH-level output voltage | V _I = V _{IH} or V _{IL} ; V _{CC} = 4.5 V | | | | | | | | |
| | | I _O = -20 μA | 4.4 | 4.5 | - | 4.4 | - | 4.4 | - | V |
| | | I _O = -4.0 mA | 3.98 | 4.32 | - | 3.84 | - | 3.7 | - | V |
| V _{OL} | LOW-level output voltage | V _I = V _{IH} or V _{IL} ; V _{CC} = 4.5 V | | | | | | | | |
| | | I _O = 20 μA; V _{CC} = 4.5 V | - | 0 | 0.1 | - | 0.1 | - | 0.1 | V |
| | | I _O = 4.0 mA; V _{CC} = 4.5 V | - | 0.15 | 0.26 | - | 0.33 | - | 0.4 | V |
| I _I | input leakage current | V _I = V _{CC} or GND; V _{CC} = 5.5 V | - | - | ±0.1 | - | ±1 | - | ±1 | μA |

Table 6. Static characteristics ...continued

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

| Symbol | Parameter | Conditions | 25 °C | | | -40 °C to +85 °C | | -40 °C to +125 °C | | Unit |
|-----------------|---------------------------|---|-------|-----|-----|------------------|-----|-------------------|-----|---------|
| | | | Min | Typ | Max | Min | Max | Min | Max | |
| I_{CC} | supply current | $V_I = V_{CC}$ or GND; $I_O = 0$ A; $V_{CC} = 5.5$ V | - | - | 8.0 | - | 80 | - | 160 | μ A |
| ΔI_{CC} | additional supply current | $V_I = V_{CC} - 2.1$ V; $I_O = 0$ A; other inputs at V_{CC} or GND; $V_{CC} = 4.5$ V to 5.5 V | | | | | | | | |
| | | pin MR | - | 110 | 396 | - | 495 | - | 539 | μ A |
| | | pin \overline{CP} | - | 85 | 306 | - | 383 | - | 417 | μ A |
| C_I | input capacitance | | - | 3.5 | - | - | - | - | - | pF |

11. Dynamic characteristics

Table 7. Dynamic characteristicsGND (ground = 0 V); $C_L = 50$ pF unless otherwise specified; for test circuit, see [Figure 10](#)

| Symbol | Parameter | Conditions | 25 °C | | | -40 °C to +85 °C | | -40 °C to +125 °C | | Unit |
|-----------------|-------------------------------|--|-------|-----|-----|------------------|-----|-------------------|-----|------|
| | | | Min | Typ | Max | Min | Max | Min | Max | |
| 74HC4020 | | | | | | | | | | |
| t_{pd} | propagation delay | \overline{CP} to Q0; see Figure 8 ^[1] | | | | | | | | |
| | | $V_{CC} = 2.0$ V; $C_L = 50$ pF | - | 39 | 140 | - | 175 | - | 210 | ns |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | - | 14 | 28 | - | 35 | - | 42 | ns |
| | | $V_{CC} = 5.0$ V; $C_L = 15$ pF | - | 11 | - | - | - | - | - | ns |
| | | $V_{CC} = 6.0$ V; $C_L = 50$ pF | - | 11 | 24 | - | 30 | - | 36 | ns |
| | | Qn to Qn+1; see Figure 9 | | | | | | | | |
| | | $V_{CC} = 2.0$ V; $C_L = 50$ pF | - | 22 | 75 | - | 95 | - | 110 | ns |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | - | 8 | 15 | - | 19 | - | 22 | ns |
| t_{PHL} | HIGH to LOW propagation delay | $V_{CC} = 5.0$ V; $C_L = 15$ pF | - | 6 | - | - | - | - | - | ns |
| | | $V_{CC} = 6.0$ V; $C_L = 50$ pF | - | 6 | 13 | - | 16 | - | 19 | ns |
| | | MR to Qn; see Figure 8 | | | | | | | | |
| | | $V_{CC} = 2.0$ V; $C_L = 50$ pF | - | 55 | 170 | - | 215 | - | 225 | ns |
| t_t | transition time | $V_{CC} = 4.5$ V; $C_L = 50$ pF | - | 20 | 34 | - | 43 | - | 51 | ns |
| | | $V_{CC} = 5.0$ V; $C_L = 15$ pF | - | 17 | - | - | - | - | - | ns |
| | | $V_{CC} = 6.0$ V; $C_L = 50$ pF | - | 16 | 29 | - | 37 | - | 43 | ns |
| | | Qn; see Figure 8 ^[2] | | | | | | | | |
| t_t | transition time | $V_{CC} = 2.0$ V; $C_L = 50$ pF | - | 19 | 75 | - | 95 | - | 110 | ns |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | - | 7 | 15 | - | 19 | - | 22 | ns |
| | | $V_{CC} = 6.0$ V; $C_L = 50$ pF | - | 6 | 13 | - | 16 | - | 19 | ns |

Table 7. Dynamic characteristics ...continuedGND (ground = 0 V); $C_L = 50$ pF unless otherwise specified; for test circuit, see [Figure 10](#)

| Symbol | Parameter | Conditions | 25 °C | | | -40 °C to +85 °C | | -40 °C to +125 °C | | Unit |
|------------------|-------------------------------|---|-------|-----|-----|------------------|-----|-------------------|-----|------|
| | | | Min | Typ | Max | Min | Max | Min | Max | |
| t_W | pulse width | \overline{CP} HIGH or LOW; see Figure 8 | | | | | | | | |
| | | $V_{CC} = 2.0$ V; $C_L = 50$ pF | 80 | 14 | - | 100 | - | 120 | - | ns |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | 16 | 4 | - | 20 | - | 24 | - | ns |
| | | $V_{CC} = 6.0$ V; $C_L = 50$ pF | 14 | 3 | - | 17 | - | 20 | - | ns |
| | | MR HIGH; see Figure 8 | | | | | | | | |
| | | $V_{CC} = 2.0$ V; $C_L = 50$ pF | 80 | 17 | - | 100 | - | 120 | - | ns |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | 16 | 6 | - | 20 | - | 24 | - | ns |
| t_{rec} | recovery time | MR to \overline{CP} ; see Figure 8 | | | | | | | | |
| | | $V_{CC} = 2.0$ V; $C_L = 50$ pF | 50 | 6 | - | 65 | - | 75 | - | ns |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | 10 | 2 | - | 13 | - | 15 | - | ns |
| | | $V_{CC} = 6.0$ V; $C_L = 50$ pF | 9 | 2 | - | 11 | - | 13 | - | ns |
| f_{max} | maximum frequency | see Figure 8 | | | | | | | | |
| | | $V_{CC} = 2.0$ V; $C_L = 50$ pF | 6.0 | 30 | - | 4.8 | - | 4.0 | - | MHz |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | 30 | 92 | - | 24 | - | 20 | - | MHz |
| | | $V_{CC} = 5.0$ V; $C_L = 15$ pF | - | 101 | - | - | - | - | - | MHz |
| | | $V_{CC} = 6.0$ V; $C_L = 50$ pF | 35 | 109 | - | 28 | - | 24 | - | MHz |
| C_{PD} | power dissipation capacitance | [3] | - | 19 | - | - | - | - | - | pF |
| 74HCT4020 | | | | | | | | | | |
| t_{pd} | propagation delay | \overline{CP} to Q0; see Figure 8 [1] | | | | | | | | |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | - | 18 | 36 | - | 45 | - | 54 | ns |
| | | $V_{CC} = 5.0$ V; $C_L = 15$ pF | - | 15 | - | - | - | - | - | ns |
| | | Qn to Qn+1; see Figure 9 | | | | | | | | |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | - | 8 | 15 | - | 19 | - | 22 | ns |
| t_{PHL} | HIGH to LOW propagation delay | $V_{CC} = 4.5$ V; $C_L = 50$ pF | - | 22 | 45 | - | 56 | - | 68 | ns |
| | | $V_{CC} = 5.0$ V; $C_L = 15$ pF | - | 19 | - | - | - | - | - | ns |
| t_t | transition time | Qn; see Figure 8 [2] | | | | | | | | |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | - | 7 | 15 | - | 19 | - | 22 | ns |
| t_W | pulse width | \overline{CP} HIGH or LOW; see Figure 8 | | | | | | | | |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | 20 | 7 | - | 25 | - | 30 | - | ns |
| | | MR HIGH; see Figure 8 | | | | | | | | |
| t_{rec} | recovery time | $V_{CC} = 4.5$ V; $C_L = 50$ pF | 20 | 8 | - | 25 | - | 30 | - | ns |
| | | MR to \overline{CP} ; see Figure 8 | | | | | | | | |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | 10 | 2 | - | 13 | - | 15 | - | ns |


Table 7. Dynamic characteristics ...continued

GND (ground = 0 V); $C_L = 50$ pF unless otherwise specified; for test circuit, see [Figure 10](#)

| Symbol | Parameter | Conditions | 25 °C | | | -40 °C to +85 °C | | -40 °C to +125 °C | | Unit |
|-----------|-------------------------------|---------------------------------|-------|-----|-----|------------------|-----|-------------------|-----|------|
| | | | Min | Typ | Max | Min | Max | Min | Max | |
| f_{max} | maximum frequency | see Figure 8 | | | | | | | | |
| | | $V_{CC} = 4.5$ V; $C_L = 50$ pF | 25 | 47 | - | 20 | - | 17 | - | MHz |
| | | $V_{CC} = 5.0$ V; $C_L = 15$ pF | - | 52 | - | - | - | - | - | MHz |
| C_{PD} | power dissipation capacitance | [3] | - | 20 | - | - | - | - | - | pF |

- [1] t_{pd} is the same as t_{PHL} and t_{PLH} .
- [2] t_t is the same as t_{THL} and t_{TLH} .
- [3] C_{PD} is used to determine the dynamic power dissipation (P_D in μ W).
 $P_D = C_{PD} \times V_{CC}^2 \times f_i + \Sigma (C_L \times V_{CC}^2 \times f_o)$ where:
 f_i = input frequency in MHz;
 f_o = output frequency in MHz;
 $\Sigma (C_L \times V_{CC}^2 \times f_o)$ = sum of outputs;
 C_L = output load capacitance in pF;
 V_{CC} = supply voltage in V.

12. Waveforms



Measurement points are given in [Table 8](#).
 V_{OL} and V_{OH} are typical voltage output levels that occur with the output load.

Fig 8. Clock timing, propagation delays, pulse widths and measurement points





Table 8. Measurement points

| Type | Input | Output |
|-----------|---------------------|---------------------|
| | V_M | V_M |
| 74HC4020 | $0.5 \times V_{CC}$ | $0.5 \times V_{CC}$ |
| 74HCT4020 | 1.3 V | 1.3 V |



001aah768

Test data is given in [Table 9](#).

Definitions test circuit:

R_T = Termination resistance should be equal to output impedance Z_o of the pulse generator.

C_L = Load capacitance including jig and probe capacitance.

Fig 10. Test circuit for measuring switching times

Table 9. Test data

| Type | Input | | Load |
|-----------|----------|------------|--------------|
| | V_I | t_r, t_f | C_L |
| 74HC4020 | V_{CC} | 6 ns | 15 pF, 50 pF |
| 74HCT4020 | 3 V | 6 ns | 15 pF, 50 pF |

13. Package outline

SO16: plastic small outline package; 16 leads; body width 3.9 mm

SOT109-1




Fig 11. Package outline SOT109-1 (SO16)

SSOP16: plastic shrink small outline package; 16 leads; body width 5.3 mm

SOT338-1




Fig 12. Package outline SOT338-1 (SSOP16)

TSSOP16: plastic thin shrink small outline package; 16 leads; body width 4.4 mm

SOT403-1




Fig 13. Package outline SOT403-1 (TSSOP16)

DHVQFN16: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 16 terminals; body 2.5 x 3.5 x 0.85 mm

SOT763-1




Fig 14. Package outline SOT763-1 (DHVQFN16)

14. Abbreviations

Table 10. Abbreviations

| Acronym | Abbreviation |
|---------|---|
| CMOS | Complementary Metal Oxide Semiconductor |
| DUT | Device Under Test |

15. Revision history

Table 11. Revision history

| Document ID | Release date | Data sheet status | Change notice | Supersedes |
|----------------------|--|-----------------------|---------------|----------------------|
| 74HC_HCT4020 v.6 | 20160203 | Product data sheet | - | 74HC_HCT4020 v.5 |
| Modifications: | <ul style="list-style-type: none"> Type numbers 74HC4020N and 74HCT4020N (SOT38-4) removed. | | | |
| 74HC_HCT4020 v.5 | 20120806 | Product data sheet | - | 74HC_HCT4020 v.4 |
| Modifications: | <ul style="list-style-type: none"> Measurement points added to figure 8 (errata). | | | |
| 74HC_HCT4020 v.4 | 20111213 | Product data sheet | - | 74HC_HCT4020 v.3 |
| Modifications: | <ul style="list-style-type: none"> Legal pages updated. | | | |
| 74HC_HCT4020 v.3 | 20100120 | Product data sheet | - | 74HC_HCT4020_CNV v.2 |
| 74HC_HCT4020_CNV v.2 | 19970901 | Product specification | - | - |

16. Legal information

16.1 Data sheet status

| Document status ^{[1][2]} | Product status ^[3] | Definition |
|-----------------------------------|-------------------------------|---|
| Objective [short] data sheet | Development | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification | This document contains data from the preliminary specification. |
| Product [short] data sheet | Production | This document contains the product specification. |

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nexperia.com>.

16.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

16.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond

Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

16.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

17. Contact information

For more information, please visit: <http://www.nexperia.com>

For sales office addresses, please send an email to: salesaddresses@nexperia.com

18. Contents

| | | |
|-----------|---|-----------|
| 1 | General description | 1 |
| 2 | Features and benefits | 1 |
| 3 | Applications | 1 |
| 4 | Ordering information | 1 |
| 5 | Functional diagram | 2 |
| 6 | Pinning information | 3 |
| 6.1 | Pinning | 3 |
| 6.2 | Pin description | 3 |
| 7 | Functional description | 4 |
| 7.1 | Timing diagram | 4 |
| 8 | Limiting values | 5 |
| 9 | Recommended operating conditions | 5 |
| 10 | Static characteristics | 6 |
| 11 | Dynamic characteristics | 7 |
| 12 | Waveforms | 9 |
| 13 | Package outline | 12 |
| 14 | Abbreviations | 16 |
| 15 | Revision history | 16 |
| 16 | Legal information | 17 |
| 16.1 | Data sheet status | 17 |
| 16.2 | Definitions | 17 |
| 16.3 | Disclaimers | 17 |
| 16.4 | Trademarks | 18 |
| 17 | Contact information | 18 |
| 18 | Contents | 19 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nexperia:

[74HC4020DB](#) [74HC4020D](#) [74HC4020N](#) [74HC4020PW](#) [74HCT4020DB](#) [74HCT4020N](#) [74HCT4020PW](#)
[74HC4020D,652](#) [74HC4020DB,112](#) [74HC4020DB,118](#) [74HC4020D,653](#) [74HC4020N,652](#) [74HC4020PW,112](#)
[74HC4020PW,118](#) [74HCT4020D,652](#) [74HCT4020DB,112](#) [74HCT4020DB,118](#) [74HCT4020D,653](#) [74HCT4020N,652](#)
[74HCT4020PW,112](#) [74HCT4020PW,118](#) [74HC4020BQ,115](#) [74HCT4020BQ,115](#)