

Soft starter, Altistart 480, 170A, 208 to 690V AC, control supply 110 to 230V AC

ATS480C17Y

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Altivar Soft Starter ATS480	
Product or Component Type	Soft starter	
Product destination	Asynchronous motors	
Product Specific Application	Process and infrastructures	
Device short name	ATS480	
Phase	3 phase	
Utilisation category	AC-3A AC-53A	
Ue power supply voltage	208690 V - 1510 %	
power supply frequency	5060 Hz - 2020 %	
[le] rated operational current	Normal duty 170.0 A 104 °F (40 °C))	
rated current in heavy duty	140.0 A at 104 °F (40 °C) heavy duty	
IP Degree of Protection	IP00	
Motor power kW	45.0 kW 230 V in the motor supply line normal duty 37.0 kW 230 V in the motor supply line heavy duty 90.0 kW 400 V in the motor supply line normal duty 75.0 kW 400 V in the motor supply line heavy duty 90.0 kW 440 V in the motor supply line normal duty 75.0 kW 440 V in the motor supply line normal duty 75.0 kW 440 V in the motor supply line heavy duty 110.0 kW 500 V in the motor supply line normal duty 90.0 kW 500 V in the motor supply line heavy duty 110.0 kW 525 V in the motor supply line normal duty 90.0 kW 525 V in the motor supply line heavy duty 132.0 kW 660 V in the motor supply line heavy duty 110.0 kW 690 V in the motor supply line heavy duty 160.0 kW 690 V in the motor supply line heavy duty 90.0 kW 230 V to the motor delta terminals normal duty 75.0 kW 230 V to the motor delta terminals heavy duty 132.0 kW 400 V to the motor delta terminals heavy duty	
Maximum Horse Power Rating	50.0 hp 208 V normal duty 40.0 hp 208 V heavy duty 60.0 hp 230 V normal duty 50.0 hp 230 V heavy duty 125.0 hp 460 V normal duty 100.0 hp 460 V heavy duty 150.0 hp 575 V normal duty	
Option card	Communication module Profibus DP V1 Communication module Modbus TCP/EtherNet/IP Communication module CANopen daisy chain Communication module CANopen Sub-D Communication module CANopen open style Communication module PROFINET	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Complementary

Complementary		
Device connection	In the motor supply line To the motor delta terminals	
[Us] control circuit voltage	110230 V AC 50/60 Hz - 1510 %	
Apparent power	0.09 kVA	
Integrated motor overload protection	True	
motor thermal protection class	Class 10E	
Protection type	Phase failure line	
	Integrated thermal protection motor	
	Thermal protection starter Current overload motor	
	Underload motor	
	Excessive starting time, locked rotor motor	
	Motor phase loss motor	
	Line supply phase loss line	
	Line supply phase loss motor	
	Thermal protection motor	
current limiting %In (5 x le maximum)	150��700 %	
[In] Rated current pwr loss specifctn	170.0 A	
Power loss static current independent	25.0 W	
Power loss per device current dependent	459.0 W	
Standards	IEC 60947-4-2	
	UL 60947-4-2	
	IEC 60664-1	
Product Certifications	CE	
	cULus	
	CCC	
	UKCA	
	RCM	
	EAC DNV	
	ABS	
	BV	
	CCS	
Marking	CE	
3	CCC	
	UKCA	
	EAC	
	RCM	
	CULus	
[Uc] control circuit voltage	24 V DC	
Discrete input number	4	
Discrete input type	STOP) logic inputs, 3500 Ohm	
	RUN) logic inputs, 3500 Ohm	
	DI3) programmable as logic input, 3500 Ohm	
	DI4) programmable as logic input, 3500 Ohm	
Input compatibility	STOP discrete input level 1 PLC IEC 61131-2	
•	RUN discrete input level 1 PLC IEC 61131-2	
	DI3 discrete input level 1 PLC IEC 61131-2	
	DI4 discrete input level 1 PLC IEC 61131-2	
Discrete input logic	Programmable digital input < 5 V	
Relay output number	3	
Relay output type	Relay outputs R1A 1 NO	
	Relay outputs R1B 1 NO	
	Relay outputs RIC NO/NC programmable	
Minimum switching current	100 mA 12 V DC relay outputs	
	20.00, oupon	

-		
Maximum switching current	Relay outputs 2 A 250 V AC	
	Relay outputs 2 A 30 V DC	
	Relay outputs	
Discrete output number	2	
	2	
Discrete output type	DQ1) programmable digital output <= 30 V	
	DQ2) programmable digital output <= 30 V	
Output compatibility	Open collector level 1 PLC IEC 65A-68	
Analogue input number	1	
 		
Analogue input type	AI1/PTC PTC/Pt 100 temperature probe	
	PTC2 PTC/Pt 100 temperature probe	
	PTC3 PTC/Pt 100 temperature probe	
Analogue output number	1	
Analogue output type	Current output AQ1 020 mA or 010 V 500 Ohm	
Communication Port Protocol	Modbus serial	
Connector Type	1 RJ45	
Communication data link	Serial	
Physical interface	2-wire RS 485	
Transmission Rate	1200256000 bit/s	
Transmission frame	RTU	
Data format	8 bits, configurable odd, even or no parity	
Type of polarization	No impedance Modbus serial	
Number of addresses	0227 Modbus serial	
Method of access	Slave Modbus serial	
Function Available	External bypass control	
	Pre-heating	
	Smoke extraction	
	Multi-motor cascade	
	Second motor set	
	User management	
	Ports and services hardening	
	Security event logging	
	Cybersecure firmware update	
	Single direction	
Display screen available	True	
Operating position	Vertical +/- 10 degree	
Height	13.4 in (340.0 mm)	
Width	7.9 in (200.0 mm)	
Depth	10.7 in (272.0 mm)	
Product Weight	27.3 lb(US) (12.4 kg)	

Environment

Electromagnetic compatibility	Conducted and radiated emissions level A conforming to IEC 60947-4-2 Conducted and radiated emissions with bypass level B conforming to IEC 60947-4-2 Damped oscillating waves level 3 conforming to IEC 61000-4-12 Electrostatic discharge level 3 conforming to IEC 61000-4-11 Immunity to electrical transients level 4 conforming to IEC 61000-4-4 Immunity to radiated radio-electrical interference level 3 conforming to IEC 61000-4-3 Voltage/current impulse level 3 conforming to IEC 61000-4-5
Pollution degree	Level 3
[Uimp] rated impulse withstand voltage	6 kV

[Ui] rated insulation voltage	690 V	
Environmental class (during operation)	Class 3C3 according to IEC 60721-3-3 Class 3S2 according to IEC 60721-3-3	
Relative humidity	095 % without condensation or dripping water IEC 60068-2-3	
Ambient air temperature for operation	104140 °F (4060 °C) (with current derating of 2 % per °C) 5104 °F (-1540 °C) (without derating)	
Ambient Air Temperature for Storage	-13158 °F (-2570 °C)	
Operating altitude	<= 3280.84 ft (1000 m) without derating > 3280.8413123.36 ft (> 10004000 m) with current derating 1 % per 100 m	
Maximum deflection under vibratory load (during operation)	1.5 mm at 213 Hz	
Maximum deflection under vibratory load (during storage)	1.75 mm at 29 Hz	
Maximum deflection under vibratory load (during transport)	1.75 mm at 29 Hz	
Maximum acceleration under vibrational stress (during operation)	10 m/s² at 13200 Hz	
Maximum acceleration under vibratory load (during storage)	15 m/s² at 200500 Hz 10 m/s² at 9200 Hz	
Maximum acceleration under vibratory load (during transport)	15 m/s² at 200500 Hz 10 m/s² at 9200 Hz	
Maximum acceleration under shock impact (during operation)	150 m/s² at 11 ms	
Maximum acceleration under shock load (during storage)	100 m/s² at 11 ms	
Maximum acceleration under shock load (during transport)	100 m/s² at 11 ms	

Ordering and shipping details

Category	US1CP1G22588
Discount Schedule	CP1G
GTIN	3606481089090
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	16.93 in (43.0 cm)
Package 1 Width	12.60 in (32.0 cm)
Package 1 Length	17.91 in (45.5 cm)
Package weight(Lbs)	31.674 lb(US) (14.367 kg)
Unit Type of Package 2	S06
Number of Units in Package 2	2
Package 2 Height	29.53 in (75.0 cm)
Package 2 Width	23.62 in (60.0 cm)
Package 2 Length	31.50 in (80.0 cm)
Package 2 Weight	92.2 lb(US) (41.8 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	12270
Environmental Disclosure	Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	235fade3-9149-48f1-bcbb-f7f8456807da
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions Drawings


Dimensions

Front, Side and Rear View



Connections and Schema


Power Connections



(1): Mains side (2): Motor side

1/L1, 3/L2, 5/L3 : Mains supply inputs 2/T1, 4/T2, 6/T3 : Outputs to motor A2, B2, C2 : Soft starter bypass


Connection in line, with line contactor, no bypass, type 1 or 2 coordination, non-reversing, 2-wire or 3-wire control



- (1): Installation of additional fast-acting fuses to upgrade to type 2 coordination according to IEC 60947–4–2.
- (2): Take into account the electrical characteristics of the relays (Control Terminal Characteristics).
- (3) : The transformer must supply 110...230 VAC +10% 15%, 50/60Hz.
- (4): RUN and STOP Management (3-wire control).
- (5): RUN and STOP Management (2-wire control).


ATS480C17Y

Connection in line, with line and bypass contactor, freewheel or controlled stop, type 1 or 2 coordination, non reversing, 2-wire or 3-wire




- (1): Installation of additional fast-acting fuses to upgrade to type 2 coordination according to IEC 60947-4-2.
- (2): Take into account the electrical characteristics of the relays (Control Terminal Characteristics).
- (3): The transformer must supply 110...230 VAC +10% 15%, 50/60Hz.
- (4): Take into account the electrical characteristics of the relays, especially when connecting to high rating contactor (Control Terminal Characteristics).
- (5): RUN and STOP Management (3-wire control).
- (6): RUN and STOP Management (2-wire control).
- (7): PC or PLC control

Connection inside the delta, with line and bypass contactor, type 1 and 2 coordination, non reversing, 2 wire or 3 wire



- (1): Installation of additional fast-acting fuses to upgrade to type 2 coordination according to IEC 60947–4–2.
- (2): Take into account the electrical characteristics of the relays (Control Terminal Characteristics).
- (3): The transformer must supply 110...230 VAC +10% 15%, 50/60Hz.
- (4): Take into account the electrical characteristics of the relays, especially when connecting to high rating contactor (Control Terminal Characteristics).
- (5): RUN and STOP Management (3-wire control).
- (6): RUN and STOP Management (2-wire control).
- (7): PC or PLC control

Control block wiring diagram



(1): Control power supply 110-230 VAC

(2) : External supply 24 VDC(3) : 2 Wires PTC/PT100

R1A, R1C, R3A, R3C : Sequence relay

R2A, R2C : End of start

STOP, RUN, DI3, DI4 : Digital inputs


AQ1: Analogue output

PTC1/AI1, PTC2, PTC3: PTC or PT100 connection

DQ1, DQ2, DQ+ : Digital outputs

Mounting and Clearance

Mounting Position



Technical Illustration

Dimensions




Image of product / Alternate images

Alternative











