



# Ai-WB2-32S Specification

Version V1.0.1

Copyright ©2022

## Document resume


| Version | Date      | Develop/revise content  | Edition     | Approve  |
|---------|-----------|-------------------------|-------------|----------|
| V1.0.0  | 2022.6.20 | First Edition           | NanNan Yuan | NingGuan |
| V1.0.1  | 2022.7.21 | Update Rendering Figure | NanNan Yuan | NingGuan |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |
|         |           |                         |             |          |

## Content

|                                                            |    |
|------------------------------------------------------------|----|
| 1. Product Overview .....                                  | 4  |
| 1.1. Characteristic .....                                  | 5  |
| 2. Main parameters .....                                   | 6  |
| 2.1. Static electricity requirement .....                  | 6  |
| 2.2. Electrical characteristics .....                      | 7  |
| 2.3. Wi-Fi RF Performance .....                            | 7  |
| 2.4. BLERF Performance .....                               | 8  |
| 2.5. Power .....                                           | 8  |
| 3. Appearance Dimensions .....                             | 9  |
| 4. Pin Definition .....                                    | 10 |
| 5. Schematic .....                                         | 12 |
| 6. Antenna parameters .....                                | 13 |
| 6.1. Schematic diagram of the antenna test prototype ..... | 13 |
| 6.2. Antenna S parameter .....                             | 14 |
| 6.3. Antenna Gain and Efficiency .....                     | 14 |
| 6.4. Antenna pattern .....                                 | 15 |
| 7. Design Guidance .....                                   | 16 |
| 7.1. Module application circuit .....                      | 16 |
| 7.2. Recommend PCB footprint size .....                    | 17 |
| 7.3. Antenna layout requirements .....                     | 17 |
| 7.4. Power supply .....                                    | 18 |
| 7.5. GPIO .....                                            | 19 |
| 8. Storage conditions .....                                | 20 |
| 9. Reflow welding curve diagram .....                      | 20 |
| 10. Product Packaging Information .....                    | 21 |
| 11. Contact us .....                                       | 21 |
| Disclaimer and copyright notice .....                      | 22 |
| Notice .....                                               | 22 |

## 1. Product Overview

Ai-WB2-32S is a Wi-Fi& BT module developed by Shenzhen Ai-Thinker Technology Co., LTD. The module is equipped with BL602 chip as the core processor and supports Wi-Fi 802.11b/ g/n protocol and BLE 5.0 protocol. The BL602 chip has a low-power 32-bit RISC CPU, 276KB RAM, and a wealth of peripheral interfaces, including SDIO, SPI, UART, I2C, IR Remote, PWM, ADC, DAC, PIR and GPIO. It can be widely used in Internet of Things (IoT), mobile devices, wearable electronic devices, smart home and other fields.



**Figure 1 Main chip architecture diagram**

## 1.1. Characteristic

- The package is SMD-38
- Support IEEE 802.11 b/g/n protocol
- Wi-Fi Security Support WPS/WEP/WPA/WPA2 Personal/WPA2 Enterprise/WPA3
- Support 20MHz bandwidth and Max rate is 72.2 Mbps
- Bluetooth BLE 5.0, Bluetooth Mesh
- Support Station + BLE、 Station + SoftAP + BLE
- Support 32-bit RISC CPU, 276KB RAM
- Secure startup, supports mirroring with ECC-256 signature
- Support QSPI/SPI Flash On-The-Fly AES Decryption, support AES 128 CTR
- Support AES 128/192/256-bit encryption engine
- Support SHA-1/224/256
- Support true Random number generator (TRNG)
- Public key Accelerator (PKA), support large number basic operations, software provides signature, verification and other application program interface
- Support SDIO, SPI, UART, I2C, IR remote, PWM, ADC, DAC, PIR, GPIO etc
- Integrated Wi-Fi MAC/BB/RF/PA/LNA/BT
- Support a variety of sleep modes, deep sleep current 12μA
- Universal AT instruction for quick start
- Support secondary development, integrated Windows, Linux development environment

## 2. Main parameters

**Table 1 Description of the main parameters**

|                              |                                                   |
|------------------------------|---------------------------------------------------|
| <b>Model</b>                 | Ai-WB2-32S                                        |
| <b>Package</b>               | SMD-38                                            |
| <b>Size</b>                  | 25.5*18.0*3.1(±0.2)mm                             |
| <b>Antenna</b>               | on-board PCB antenna、IPEX connector               |
| <b>Frequency</b>             | 2400 ~ 2483.5MHz                                  |
| <b>Operating temperature</b> | -40°C ~ 85°C                                      |
| <b>Storage temperature</b>   | -40°C ~ 125°C, < 90%RH                            |
| <b>Power supply</b>          | Support voltage 2.7V ~ 3.6V,supply current ≥500mA |
| <b>Interface</b>             | UART/GPIO/ADC/PWM/I2C/SPI                         |
| <b>IO</b>                    | 15                                                |
| <b>UART rate</b>             | Default 115200 bps                                |
| <b>Security</b>              | WPS/WEP/WPA/WPA2 Personal/WPA2 Enterprise/WPA3    |
| <b>Flash</b>                 | Default 4MByte,Support expansion                  |

### 2.1. Static electricity requirement

Ai-WB2-32S is an electrostatic sensitive device. Therefore, you need to take special precautions when carrying it.



**Figure 2 ESD preventive measures**

## 2.2. Electrical characteristics

Table 2 Electrical characteristics table

| Parameters     | Condition | Min. | Typical value | Max.      | Unit |
|----------------|-----------|------|---------------|-----------|------|
| Voltage Supply | VDD       | 2.7  | 3.3           | 3.6       | V    |
| I/O            | VIL       | -    | -             | 0.3*VDDIO | V    |
|                | VIH       | -    | 0.7*VDDIO     | -         | V    |
|                | VOL       | -    | 0.1*VDDIO     | -         | V    |
|                | VOH       | -    | 0.9*VDDIO     | -         | V    |
|                | IMAX      | -    | -             | 15        | mA   |

## 2.3. Wi-Fi RF Performance

Table 3 Wi-Fi RF performance table

| Description                    | Typical value    |               |      | Unit |
|--------------------------------|------------------|---------------|------|------|
| Frequency range                | 2400 ~ 2483.5MHz |               |      | MHz  |
| Output Power                   |                  |               |      |      |
| Mode                           | Min.             | Typical value | Max. | Unit |
| 11n Mode HT20, PA output power | -                | 16            | -    | dBm  |
| 11g Mode, PA output power      | -                | 17            | -    | dBm  |
| 11b Mode, PA output power      | -                | 19            | -    | dBm  |
| Receive Sensitivity            |                  |               |      |      |
| Mode                           | Min.             | Typical value | Max. | Unit |
| 11b, 1 Mbps                    | -                | -98           | -    | dBm  |
| 11b, 11 Mbps                   | -                | -90           | -    | dBm  |
| 11g, 6 Mbps                    | -                | -93           | -    | dBm  |
| 11g, 54 Mbps                   | -                | -76           | -    | dBm  |
| 11n, HT20 (MCS7)               | -                | -73           | -    | dBm  |

## 2.4. BLERF Performance

**Table 4 BLE RF performance table**

| Description                | Typical value    |               |      | Unit |
|----------------------------|------------------|---------------|------|------|
| Frequency range            | 2400 ~ 2483.5MHz |               |      | MHz  |
| Output Power               |                  |               |      |      |
| Rate Mode                  | Min.             | Typical value | Max. | Unit |
| 1Mbps                      | -                | 9             | 15   | dBm  |
| Receive Sensitivity        |                  |               |      |      |
| Rate Mode                  | Min.             | Typical value | Max. | Unit |
| 1Mbps sensitivity@30.8%PER | -                | -96           | -    | dBm  |

## 2.5. Power

The following power consumption data are based on a 3.3V power supply, 25°C ambient temperature, and measured using an internal voltage regulator.

- All measurements are made at the antenna interface with a filter.
- All transmission data are based on 100% duty cycle in continuous transmission mode.

**Table 5 Power consumption**

| Mode                               | Min. | AVG | Max. | Unit |
|------------------------------------|------|-----|------|------|
| Tx 802.11b, 11Mbps, POUT=+21dBm    | -    | 260 | -    | mA   |
| Tx802.11g, 54Mbps, POUT =+18dBm    | -    | 245 | -    | mA   |
| Tx802.11n, MCS7, POUT =+17dBm      | -    | 230 | -    | mA   |
| Rx 802.11b,packet length 1024 byte | -    | 65  | -    | mA   |
| Rx 802.11g,packet length 1024 byte | -    | 65  | -    | mA   |
| Rx 802.11n,Packet length 1024 byte | -    | 65  | -    | mA   |
| Deep-Sleep                         | -    | 12  | -    | μA   |

### 3. Appearance Dimensions




Figure 3 Appearance diagram (Rendering figure is for reference only, subject to physical objects)






Figure 4 Dimension diagram



### Figure 5 Shield printing information

## 4. Pin Definition

Ai-WB2-32S module is connected with a total of 38 pins, as shown in the pin schematic diagram, pin function definition table is the interface definition.



**Figure 6 Schematic diagram of module pins**


**Table 6 Pin function definition table**

| No.                        | Name   | Function                                                                                                                                                                                 |
|----------------------------|--------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1,15,38                    | GND    | Ground                                                                                                                                                                                   |
| 2                          | VDD    | 3.3V power supply; It is recommended that the output current of the external power supply be higher than 500mA                                                                           |
| 3                          | EN     | Default chip enable pin, active-high.                                                                                                                                                    |
| 4,6,7,16-24,26,29,32,33,37 | NC     | NC is not available                                                                                                                                                                      |
| 5                          | GPIO11 | GPIO11/SPI_SCLK/IIC_SDA/ADC_CH10/JTAG_TDI/TDO                                                                                                                                            |
| 8                          | IO14   | GPIO14/SPI_SS/IIC_SCL/PWM_CH4/ADC_CH2/JTAG_TCK/TMS                                                                                                                                       |
| 9                          | IO17   | GPIO17/SPI_MOSI/MISO/IIC_SDA/PWM_CH2/JTAG_TCK/TMS                                                                                                                                        |
| 10                         | IO3    | GPIO3/SPI_SCLK/IIC_SDA/PWM_CH3/JTAG_TDO/TDI                                                                                                                                              |
| 11                         | IO20   | It is not recommended to use. It is shared with the Flash in the module. If you need to use it, please contact Ai-Thinker.<br>GPIO20/SPI_MOSI/MISO/IIC_SCL/PWM_CH0/JTAG_TMS/TCK          |
| 12                         | IO22   | It is not recommended to use. It is shared with the Flash in the module. If you need to use it, please contact Ai-Thinker.<br>GPIO22/SPI_SS/IIC_SCL/PWM_CH2/JTAG_TCK/TMS                 |
| 13                         | IO0    | It is not recommended to use. It is shared with the Flash in the module. If you need to use it, please contact Ai-Thinker.<br>GPIO0/SDIO_CLK//SPI_MOSI/MISO/IIC_SCL/PWM_CH0/JTAG_TMS/TCK |
| 14                         | IO21   | It is not recommended to use. It is shared with the Flash in the module. If you need to use it, please contact Ai-Thinker.<br>GPIO21/SPI_MOSI/MISO/IIC_SDA/PWM_CH1/JTAG_TDI/TDO          |
| 25                         | IO8/NC | Default NC, unavailable                                                                                                                                                                  |
| 27                         | IO4    | GPIO4/SPI_MOSI/MISO/IIC_SCL/PWM_CH4/ADC_CH1                                                                                                                                              |
| 28                         | IO2    | It is not recommended to use. It is shared with the Flash in the module. If you need to use it, please contact Ai-Thinker. GPIO2/SPI_SS/IIC_SCL/PWM_CH2                                  |
| 30                         | IO1    | It is not recommended to use. It is shared with the Flash in the module. If you need to use it, please contact Ai-Thinker.<br>GPIO1/SPI_MOSI/MISO/IIC_SDA/PWM_CH1                        |
| 31                         | IO5    | GPIO5/SPI_MOSI/MISO/IIC_SDA/PWM_CH0/ADC_CH4/JTAG_TMS/TCK                                                                                                                                 |
| 34                         | RXD    | RXD/GPIO7/SPI_SCLK/IIC_SDA/PWM_CH2/JTAG_TDO/TDI                                                                                                                                          |
| 35                         | TXD    | TXD/GPIO16/SPI_MOSI/MISO/IIC_SCL/PWM_CH1/JTAG_TMS/TCK                                                                                                                                    |
| 36                         | IO12   | GPIO12/SPI_MOSI/MISO/IIC_SCL/PWM_CH2/ADC_CH0/JTAG_TMS/TCK                                                                                                                                |

### Figure 7 Module schematic

## 6. Antenna parameters

### 6.1. Schematic diagram of the antenna test prototype



**Figure 8 Schematic diagram of the antenna test prototype**

## 6.2. Antenna S parameter




Figure 9 Antenna S parameters

## 6.3. Antenna Gain and Efficiency

Table 7 Antenna Gain and efficiency

| Frequency ID   | 1     | 2     | 3     | 4     | 5     | 6     | 7     | 8     | 9     | 10    | 11    |
|----------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| Frequency(MHz) | 2400  | 2410  | 2420  | 2430  | 2440  | 2450  | 2460  | 2470  | 2480  | 2490  | 2500  |
| Gain (dBi)     | 1.23  | 1.22  | 1.36  | 1.51  | 1.78  | 1.91  | 2.00  | 2.08  | 2.03  | 1.89  | 1.85  |
| Efficiency (%) | 63.80 | 64.44 | 66.01 | 68.50 | 71.44 | 73.28 | 73.61 | 73.59 | 72.45 | 68.30 | 67.66 |

## 6.4. Antenna pattern





Figure 10 Antenna pattern

## 7. Design Guidance

### 7.1. Module application circuit



**Figure 11 Application circuit diagram**

- If the IO port is used as PWM, it is recommended to reserve a 4.7K pull-down resistor around the module. Especially in the application of light control, it can prevent the flashing light phenomenon at the moment of power-on start.
- The IO0/IO1/IO2/IO8/NC/IO20/IO21/IO22 pins, which are not available by default. If you need to use it, please contact Ai-Thinker.

## 7.2. Recommend PCB footprint size




Figure 12 Recommend PCB footprint size


## 7.3. Antenna layout requirements

- The following two methods are recommended for the installation position on the mainboard:

Option 1: put the module on the edge of the motherboard, and the antenna area extends out of the edge of the motherboard.

Option 2: put the module on the edge of the motherboard, the edge of the motherboard at the antenna position hollowed out an area.


- In order to meet the performance of onboard antenna, it is forbidden to place metal parts around the antenna and keep away from high frequency devices.



**Figure 13 Antenna layout diagram**

## 7.4. Power supply

- Recommended 3.3V voltage, peak current over 500mA.
- Power supply is recommend to use LDO; if the DC-DC is used, the ripple is recommended to be controlled within 30mV
- DC-DC power supply circuit proposes to reserve the dynamic response capacitance to optimize the output ripple with large load changes.
- It is recommended to add ESD devices to the 3.3V power interface.



**Figure 14 DC-DC step-down circuit diagram**

## 7.5. GPIO

- There are some IO ports on the periphery of the module. If you need to use it, it is recommended to connect a 10-100 ohm resistor in series with the IO port. This inhibits overshoot and makes both sides level more stable. It is helpful for EMI and ESD.
- For special I/O ports to be pulled up and down, refer to the usage instructions in the specifications, which may affect the module startup configuration.
- The IO port of the module is 3.3V. If the IO level of the main control and the module do not match, a level conversion circuit needs to be added.
- If the I/O port is directly connected to a peripheral port or terminals, for example, a pin row, reserve an ESD device near the terminal of the I/O cable.




Figure 15 Level convert circuit


## 8. Storage conditions

Products sealed in moisture-proof bags should be stored in a non-condensing atmosphere of  $<40^{\circ}\text{C}/90\%\text{RH}$ .

The module has a moisture sensitivity rating of MSL 3.

After the vacuum bag is opened, it must be used within 168 hours at  $25\pm 5^{\circ}\text{C}/60\%\text{RH}$ , otherwise it needs to be baked before it can be put on line again.

## 9. Reflow welding curve diagram



**Figure 16 Reflow welding diagram**

## 10. Product Packaging Information

Ai-WB2-32S module was packaged in a tape, 800pcs/reel. As shown in the below image:



Figure 17 Package and packing diagram

## 11. Contact us

[Ai-Thinker official website](#)

[Office forum](#)

[Develop DOCS](#)

[LinkedIn](#)

[Tmall shop](#)

[Taobao shop](#)

[Alibaba shop](#)

[Technical support email: support@aithinker.com](#)

[Domestic business cooperation: sales@aithinker.com](#)

[Overseas business cooperation: overseas@aithinker.com](#)

Company Address: Room 403,408-410, Block C, Huafeng Smart Innovation Port, Gushu 2nd Road, Xixiang, Baoan District, Shenzhen.

Tel: +86-0755-29162996



WeChat mini program



WeChat official account

## Disclaimer and copyright notice

The information in this article, including the URL address for reference, is subject to change without notice.

The document is provided "as is" without any guarantee responsibility, including any guarantee for merchantability, suitability for a specific purpose, or non-infringement, and any guarantee mentioned elsewhere in any proposal, specification or sample. This document does not bear any responsibility, including the responsibility for infringement of any patent rights arising from the use of the information in this document. This document does not grant any license for the use of intellectual property rights in estoppel or other ways, whether express or implied.

The test data obtained in the article are all obtained from Ai-Thinker's laboratory tests, and the actual results may vary slightly.

All brand names, trademarks and registered trademarks mentioned in this article are the property of their respective owners, and it is hereby declared.

The final interpretation right belongs to Shenzhen Ai-Thinker Technology Co., Ltd.

## Notice

Due to product version upgrades or other reasons, the contents of this manual may be changed.

Shenzhen Ai-Thinker Technology Co., Ltd. reserves the right to modify the contents of this manual without any notice or prompt.

This manual is only used as a guide. Shenzhen Ai-Thinker Technology Co., Ltd. makes every effort to provide accurate information in this manual. However, Shenzhen Ai-Thinker Technology Co., Ltd. does not guarantee that the contents of the manual are completely free of errors. All statements and information in this manual And the suggestion does not constitute any express or implied guarantee.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RF Solutions:](#)

[Ai-WB2-32S](#)