

# **MIC5891**

## 8-Bit Serial-Input Latched Source Driver


#### **Features**

- · High-Voltage, High-Current Outputs
- · Output Transient Protection Diodes
- CMOS-, PMOS-, NMOS-, and TTL-Compatible Inputs
- · 5 MHz Typical Data Input Rate
- · Low-Power CMOS Latches

#### **Applications**

- · Alphanumeric and Bar Graph Displays
- · LED and Incandescent Displays
- · Relay and Solenoid Drivers
- · Other High-Power Loads

#### **Package Type**



#### **General Description**

The MIC5891 latched driver is a high-voltage, high-current integrated circuit comprised of eight CMOS data latches, CMOS control circuitry for the common STROBE and OUTPUT ENABLE, and bipolar Darlington transistor drivers for each latch.

Bipolar/MOS construction provides extremely low power latches with maximum interface flexibility.

The MIC5891 will typically operate at 5 MHz with a 5V logic supply.

The CMOS inputs are compatible with standard CMOS, PMOS, and NMOS logic levels. TTL circuits may be used with appropriate pull-up resistors to ensure a proper logic-high input.


A CMOS serial data output allows additional drivers to be cascaded when more than 8 bits are required.

The MIC5891 has open-emitter outputs with suppression diodes for protection against inductive load transients. The output transistors are capable of sourcing 500 mA and will sustain at least 35V in the on-state.

Simultaneous operation of all drivers at maximum rated current requires a reduction in duty cycle due to package power limitations. Outputs may be paralleled for higher load current capability.

The MIC5891 is available in a 16-pin plastic DIP package (N) and 16-pin wide SOIC package (WM).

## **Functional Diagram**



#### 1.0 ELECTRICAL CHARACTERISTICS

#### Absolute Maximum Ratings † (Note 1, Note 2, Note 3)

| Output Voltage (V <sub>OUT</sub> )             | +50V          |
|--|---------------|
| Logic Supply Voltage Range (V <sub>DD</sub> )  |               |
| Load Supply Voltage Range (V <sub>BB</sub> )   | +5.0V to +50V |
| Input Voltage Range (V <sub>IN</sub> )         |               |
| Continuous Collector Current (I <sub>C</sub> ) | , 22          |
| Package Power Dissipation                      |               |

**† Notice:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

- **Note 1:**  $T_A = +25^{\circ}C$ .
  - 2: Derate at the rate of 20 mW/°C above T<sub>A</sub> = +25°C.
  - **3:** Microchip CMOS devices have input-static protection, but are susceptible to damage when exposed to extremely high static electrical charges.

TABLE 1-1: ALLOWABLE DUTY CYCLES

| Number of Outputs ON at    | Maximum Allowable Duty Cycles at a T <sub>A</sub> of: |       |       |  |  |
|----------------------------|---|-------|-------|--|--|
| I <sub>OUT</sub> = -200 mA | +50°C   | +60°C | +70°C |  |  |
| 8                          | 53%   | 47%   | 41%   |  |  |
| 7                          | 60%   | 54%   | 48%   |  |  |
| 6                          | 70%   | 64%   | 56%   |  |  |
| 5                          | 83%   | 75%   | 67%   |  |  |
| 4                          | 100%  | 94%   | 84%   |  |  |
| 3                          | 100%  | 100%  | 100%  |  |  |
| 2                          | 100%  | 100%  | 100%  |  |  |
| 1                          | 100%  | 100%  | 100%  |  |  |

## **MIC5891**

#### **Electrical Characteristics**

| <b>Electrical Characteristics:</b> $V_{BB} = 50V$ , $V_{DD} = 5V$ to 12V; $T_A = 25$ °C, unless noted. (Note 1). |                       |                      |      |                      |          |  |  |  |
|--|-----------------------|----------------------|------|----------------------|----------|--|--|--|
| Parameters   | Sym.                  | Min.                 | Тур. | Max.                 | Units    | Conditions   |  |  |
| Output Leekene Cument  | I <sub>CEX</sub>      | _                    | _    | -50                  | μA       | T <sub>A</sub> = +25°C                                 |  |  |
| Output Leakage Current   |                       | _                    | _    | -100                 | μA       | T <sub>A</sub> = +85°C                                 |  |  |
|  |                       | _                    | _    | 2.3                  | ٧        | $I_{OUT} = -100 \text{ mA}, T_A = +85^{\circ}\text{C}$ |  |  |
| Output Saturation Voltage  | V <sub>CE(SAT)</sub>  | _                    | _    | 2.4                  | ٧        | $I_{OUT} = -225 \text{ mA}, T_A = +85^{\circ}\text{C}$ |  |  |
|  |                       | _                    | _    | 2.5                  | <b>V</b> | $I_{OUT} = -350 \text{ mA}, T_A = +85^{\circ}\text{C}$ |  |  |
| Output Sustaining Voltage  | V <sub>CE(SUS)</sub>  | 35                   | _    | _                    | V        | I <sub>OUT</sub> = –350 mA, L = 2 mH                   |  |  |
|  |                       | 3.5                  | _    | V <sub>DD</sub> +0.3 | V        | V <sub>DD</sub> = 5.0V                                 |  |  |
| Input Voltage  | $V_{IN(1)} V_{IN(0)}$ | 10.5                 | _    | V <sub>DD</sub> +0.3 | V        | V <sub>DD</sub> = 12V                                  |  |  |
|  | - 114(0)              | V <sub>SS</sub> -0.3 | _    | 0.8                  | V        | V <sub>DD</sub> = 5.0V to 12V                          |  |  |
| Input Current  | 1                     | _                    | _    | 120                  | μΑ       | $V_{DD} = V_{IN} = 5.0V$                               |  |  |
| input Guirent  | I <sub>IN(1)</sub>    | _                    | _    | 240                  | μA       | V <sub>DD</sub> = 12V                                  |  |  |
| Input Impedance  | 7                     | 100                  | _    | _                    | kΩ       | V <sub>DD</sub> = 5.0V                                 |  |  |
| input impedance  | Z <sub>IN</sub>       | 50                   | _    | _                    | kΩ       | V <sub>DD</sub> = 12V                                  |  |  |
| Maximum Clock Frequency  | f <sub>c</sub>        | 3.3                  | _    | _                    | MHz      | _  |  |  |
| Serial Data Output Resistance  |                       |                      | _    | 20                   | kΩ       | V <sub>DD</sub> = 5.0V                                 |  |  |
| Serial Data Output Resistance  | R <sub>OUT</sub>      | _                    | _    | 6.0                  | kΩ       | V <sub>DD</sub> = 12V                                  |  |  |
| Turn-On Delay  | t <sub>PLH</sub>      | —                    | _    | 2.0                  | μs       | Output Enable to Output,<br>I <sub>OUT</sub> = –350 mA |  |  |
| Turn-Off Delay   | t <sub>PHL</sub>      | _                    | _    | 10                   | μs       | Output Enable to Output,<br>I <sub>OUT</sub> = –350 mA |  |  |
|  | I <sub>BB</sub>       | _                    | _    | 10                   | mA       | All outputs on, all outputs open                       |  |  |
|  |                       | _                    | _    | 200                  | μΑ       | All outputs off  |  |  |
|  |                       | _                    | _    | 100                  | μΑ       | V <sub>DD</sub> = 5V, all outputs off,<br>inputs = 0V  |  |  |
| Supply Current   |                       | _                    | _    | 200                  | μA       | V <sub>DD</sub> = 12V, all outputs off,<br>inputs = 0V |  |  |
|  | l <sub>DD</sub>       | _                    | _    | 1.0                  | mA       | V <sub>DD</sub> = 5V, one output on,<br>inputs = 0V    |  |  |
|  |                       | _                    |      | 3.0                  | mA       | V <sub>DD</sub> = 12V, one output on,<br>inputs = 0V   |  |  |
| Diada Lashana C  |                       | _                    | _    | 50                   | μA       | T <sub>A</sub> = +25°C; Max. V <sub>BB</sub>           |  |  |
| Diode Leakage Current  | I <sub>H</sub>        | _                    | _    | 100                  | μA       | T <sub>A</sub> = +85°C; Max. V <sub>BB</sub>           |  |  |
| Diode Forward Voltage  | V <sub>F</sub>        |                      |      | 2.0                  | V        | I <sub>F</sub> = 350 mA; V <sub>BB</sub> open          |  |  |

Note 1: Specification for packaged product only.

<sup>2:</sup> Positive (negative) current is defined as going into (coming out of) the specified device pin.

**<sup>3:</sup>** Operation of these devices with standard TTL may require the use of appropriate pull-up resistors.

#### **TEMPERATURE SPECIFICATIONS**

| Parameters                  | Sym.           | Min. | Тур. | Max. | Units | Conditions |  |  |
|-----------------------------|----------------|------|------|------|-------|------------|--|--|
| Temperature Ranges          |                |      |      |      |       |            |  |  |
| Operating Temperature Range | T <sub>A</sub> | -40  | _    | +85  | °C    | Note 1     |  |  |
| Storage Temperature Range   | T <sub>S</sub> | -65  | _    | +150 | °C    | _          |  |  |

Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T<sub>A</sub>, T<sub>J</sub>, θ<sub>JA</sub>). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum +125°C rating. Sustained junction temperatures above +125°C can impact the device reliability.

## **Typical Circuits**




FIGURE 1-1: Typical Input Circuit





FIGURE 1-2: Typical Output Circuit.

#### 2.0 TYPICAL PERFORMANCE CURVES

Note:

The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.



**FIGURE 2-1:** Allowable Package Power Dissipation vs. Temperature.

#### 3.0 TIMING CONDITIONS

The descriptions of the timing conditions are listed below Figure 3-1.




FIGURE 3-1: Timing Conditions.

TABLE 3-1: TIMING CONDITIONS PARAMETERS

| V <sub>DD</sub> = 5.0V, Logic levels are V <sub>DD</sub> and ground. |  |                                |  |  |  |  |  |
|--|--|--------------------------------|--|--|--|--|--|
| Reference  | Parameter  | Value                          |  |  |  |  |  |
| Α  | Minimum data active time before clock pulse (data set-up time) | 75 ns                          |  |  |  |  |  |
| В  | Minimum data active time after clock pulse (data hold time)    | 75 ns                          |  |  |  |  |  |
| С  | Minimum data pulse width                                       | 150 ns                         |  |  |  |  |  |
| D  | Minimum clock pulse width                                      | 150 ns                         |  |  |  |  |  |
| Е  | Minimum time between clock activation and strobe               | 300 ns                         |  |  |  |  |  |
| F  | Minimum strobe pulse width                                     | 100 ns                         |  |  |  |  |  |
| G  | Typical time between strobe activation and output transition   | 1.0 µs                         |  |  |  |  |  |
| Н  | Turn-off delay   | See Electrical Characteristics |  |  |  |  |  |
| I  | Turn-on delay  | See Electrical Characteristics |  |  |  |  |  |

TABLE 3-2: TRUTH TABLE

| Serial<br>Data | Clock | Shift Register<br>Contents   | Serial<br>Data   | Strobe |  | Latch Contents | Output<br>Enable   | Output Content |
|----------------|-------|--|------------------|--------|--|----------------|--|----------------|
| Input          | Input | l <sub>1</sub> l <sub>2</sub> l <sub>3</sub> l <sub>N-1</sub> l <sub>N</sub> | Output           | Input  | l <sub>1</sub> l <sub>2</sub> l <sub>3</sub> l <sub>N-1</sub> l <sub>N</sub> | Ellable        | l <sub>1</sub> l <sub>2</sub> l <sub>3</sub> l <sub>N-1</sub> l <sub>N</sub> |                |
| Н              |       | H R <sub>1</sub> R <sub>2</sub> R <sub>N-2</sub> R <sub>N-1</sub>            | R <sub>N-1</sub> |        |  |                |  |                |
| L              | 7     | L R <sub>1</sub> R <sub>2</sub> R <sub>N-2</sub> R <sub>N-1</sub>            | R <sub>N-1</sub> | _      | _  | _              | _  |                |
| Х              | 7     | R <sub>1</sub> R <sub>2</sub> R <sub>3</sub> R <sub>N-1</sub> R <sub>N</sub> | $R_N$            |        |  |                |  |                |
|                |       | X X X X X  | Х                | L      | R <sub>1</sub> R <sub>2</sub> R <sub>3</sub> R <sub>N-1</sub> R <sub>N</sub> |                |  |                |
| _              | _     | P <sub>1</sub> P <sub>2</sub> P <sub>3</sub> P <sub>N-1</sub> P <sub>N</sub> | $P_N$            | Н      | P <sub>1</sub> P <sub>2</sub> P <sub>3</sub> P <sub>N-1</sub> P <sub>N</sub> | L              | P <sub>1</sub> P <sub>2</sub> P <sub>3</sub> P <sub>N-1</sub> P <sub>N</sub> |                |
|                |       | _  | _                | _      | X X X X X  | Н              | LLLLL  |                |

L = Low Logic Level, H = High Logic Level, X = Irrelevant, P = Present State, R = Previous State.

## MIC5891

#### 4.0 APPLICATION INFORMATION

Serial data present at the input is transferred into the shift register on the rising edge of the CLOCK input pulse. Additional CLOCK pulses shift data information towards the SERIAL DATA OUTPUT. The serial data must appear at the input prior to the rising edge of the CLOCK input waveform.

The 8 bits present in the shift register are transferred to the respective latches when the STROBE is high (serial-to-parallel conversion). The latches will continue to accept new data as long as the STROBE is held high. Most applications where the latching feature is not used (STROBE tied high) require the OUTPUT ENABLE input to be high during serial data entry.

Outputs are active (controlled by the latch state) when the OUTPUT ENABLE is low. All outputs are low (disabled) when the OUTPUT ENABLE is high. OUTPUT ENABLE does not affect the data in the shift register or latch.

#### 5.0 PACKAGING INFORMATION

#### 5.1 Package Marking Information

16-Pin PDIP\*

Example



MICS891YN 1312

16-Pin SOICW\*

Example



MICREL MIC5891YWM 1632

**Legend:** XX...X Product code or customer-specific information

Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')

NNN Alphanumeric traceability code

(e3) Pb-free JEDEC® designator for Matte Tin (Sn)

This package is Pb-free. The Pb-free JEDEC designator ((e3)) can be found on the outer packaging for this package.

•, ▲, ▼ Pin one index is identified by a dot, delta up, or delta down (triangle mark).

**Note**: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.


Underbar (\_) and/or Overbar (¯) symbol may not be to scale.

**Note:** If the full seven-character YYWWNNN code cannot fit on the package, the following truncated codes are used based on the available marking space:


6 Characters = YWWNNN; 5 Characters = WWNNN; 4 Characters = WNNN; 3 Characters = NNN;

2 Characters = NN; 1 Character = N

## 16-Lead PDIP Package Outline and Recommended Land Pattern



#### 16-Lead SOICW Package Outline and Recommended Land Pattern





NOTES:

### **APPENDIX A: REVISION HISTORY**

#### **Revision A (October 2016)**

- Converted Micrel document MIC5891 to Microchip data sheet DS20005638B.
- · Minor text changes throughout.
- Operating temperature range corrected in the Temperature Specifications section.
- Maximum Saturation Voltage values updated in Table .
- First Input Current maximum value updated in Table .

## Revision B (February 2022)

• Corrected the device marking specification in Section 5.1, Package Marking Information.



NOTES:

#### PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

Examples: PART NO. a) MIC5891YN: 8-Bit Serial-Input Latched Source Driver, -40°C to +85°C **Device** Package Media Type Junction Junction Temperature Range, **Temperature Range** 16-Lead PDIP, 25/Tube Device: MIC5891: 8-Bit Serial-Input Latched Source Driver a) MIC5891YWM: 8-Bit Serial-Input Latched Source Driver, -40°C to +85°C Junction Temperature Range, Junction -40°C to +85°C 16-Lead SOICW, 47/Tube Temperature Range: a) MIC5891YWM-TR: 8-Bit Serial-Input Latched Source Driver, –40°C to +85°C Junction Temperature Range, Package: 16-Lead PDIP 16-Lead SOICW, 1,000/Reel WM = 16-Lead SOICW Media Type: = 1,000/Reel for WM Package (blank)= 25/Tube for N Package (blank)= 47/Tube for WM Package



NOTES:

#### Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
  mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to
  continuously improving the code protection features of our products.

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at <a href="https://www.microchip.com/en-us/support/design-help/client-support-services">https://www.microchip.com/en-us/support/design-help/client-support-services</a>.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, TrueTime, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the LLS A

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, GridTime, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, NVM Express, NVMe, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

 $\ensuremath{\mathsf{SQTP}}$  is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, Symmcom, and Trusted Time are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2016 - 2022, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-5224-9832-2



## **Worldwide Sales and Service**

#### **AMERICAS**

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200

Fax: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta Duluth, GA

Tel: 678-957-9614 Fax: 678-957-1455

**Austin, TX** Tel: 512-257-3370

Boston

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** Addison, TX Tel: 972-818-7423

Fax: 972-818-2924 **Detroit** Novi, MI

Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Tel: 951-273-7800 Raleigh, NC

Tel: 919-844-7510 **New York, NY** Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110 Tel: 408-436-4270

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

**China - Beijing** Tel: 86-10-8569-7000

China - Chengdu Tel: 86-28-8665-5511

**China - Chongqing** Tel: 86-23-8980-9588

**China - Dongguan** Tel: 86-769-8702-9880

**China - Guangzhou** Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

**China - Nanjing** Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

**China - Shenyang** Tel: 86-24-2334-2829

China - Shenzhen Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan

Tel: 86-27-5980-5300 **China - Xian** Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

**China - Zhuhai** Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

**Japan - Osaka** Tel: 81-6-6152-7160

**Japan - Tokyo** Tel: 81-3-6880- 3770

Korea - Daegu

Tel: 82-53-744-4301 **Korea - Seoul** Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

**Singapore** Tel: 65-6334-8870

**Taiwan - Hsin Chu** Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

#### **EUROPE**

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

**Denmark - Copenhagen** Tel: 45-4485-5910 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

**Germany - Haan** Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-72400

**Germany - Karlsruhe** Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

**Netherlands - Drunen** Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

**Poland - Warsaw** Tel: 48-22-3325737

**Romania - Bucharest** Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**Sweden - Gothenberg** Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820